

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428285

Luminaire Tested: SQ2W-PR1-K-125U-075D-L935-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428285
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-9)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PR1-K-125U-075D-L935-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE RIPPLE LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8313.5 lumens
Efficiency: N/A
Efficacy: 117.6 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.34 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 70.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428285

CATALOG NUMBER: SQ2W-PR1-K-125U-075D-L935-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428285

CATALOG NUMBER: SQ2W-PR1-K-125U-075D-L935-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41				41
1	96	92	89	85	88	84	81	78	69	67	65	56	54	53	43	42	41				36	
2	88	81	75	70	80	74	69	65	61	58	55	49	47	45	39	37	36				31	
3	81	72	65	59	73	66	60	55	55	50	47	44	41	39	35	33	31				26	
4	74	64	56	50	67	58	52	47	49	44	40	40	36	33	31	29	27				23	
5	68	57	49	43	62	52	46	40	44	39	35	36	32	29	28	26	24				20	
6	63	51	43	38	57	47	40	35	39	34	30	32	29	26	26	23	21				18	
7	58	46	38	33	53	43	36	31	36	31	27	29	26	23	24	21	19				16	
8	54	42	34	29	49	39	32	27	33	28	24	27	23	20	22	19	17				14	
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15				13	
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14				12	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	22849	22849	22849	22849
5°	22820	23240	22820	23240
10°	23059	24005	23059	24005
15°	23052	23366	23052	23366
20°	22680	23795	22680	23795
25°	22616	24773	22616	24773
30°	22592	25012	22592	25012
35°	22377	23287	22377	23287
40°	21861	20493	21861	20493
45°	20685	16205	20685	16205
50°	18806	12574	18806	12574
55°	16526	9787	16526	9787
60°	14302	8060	14302	8060
65°	12344	7056	12344	7056
70°	11098	6264	11098	6264
75°	10168	5758	10168	5758
80°	8852	5634	8852	5634
85°	6410	2668	6410	2668

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 22208 cd/sqm



TEST NUMBER: P1428285

CATALOG NUMBER: SQ2W-PR1-K-125U-075D-L935-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.7	1.6
10°-20°	395.6	4.8
20°-30°	611.6	7.4
30°-40°	735.5	8.8
40°-50°	660.5	7.9
50°-60°	442.5	5.3
60°-70°	257.4	3.1
70°-80°	132.2	1.6
80°-90°	39.6	0.5
90°-100°	133.6	1.6
100°-110°	389.6	4.7
110°-120°	635.9	7.6
120°-130°	806.9	9.7
130°-140°	863.4	10.4
140°-150°	806.2	9.7
150°-160°	663.4	8.0
160°-170°	444.9	5.4
170°-180°	158.0	1.9
0°-30°	1143.9	13.8
0°-40°	1879.3	22.6
0°-60°	2982.3	35.9
0°-90°	3411.5	41.0
90°-120°	1159.2	13.9
90°-150°	3635.7	43.7
90°-180°	4902.0	59.0
0°-180°	8313.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1415	1415	1415	1415	1415	
5°	1408	1434	1408	1434	1408	134
15°	1379	1398	1379	1398	1379	387
25°	1270	1391	1270	1391	1270	585
35°	1135	1182	1135	1182	1135	708
45°	906	710	906	710	906	693
55°	587	348	587	348	587	528
65°	323	185	323	185	323	327
75°	163	92	163	92	163	173
85°	35	14	35	14	35	43
90°	5	37	5	73	5	5
95°	53	39	53	229	53	63
105°	248	397	248	546	248	263
115°	475	658	475	811	475	468
125°	702	1043	702	994	702	628
135°	955	1365	955	1101	955	738
145°	1219	1574	1219	1124	1219	763
155°	1448	1709	1448	1167	1448	666
165°	1601	1782	1601	1343	1601	451
175°	1674	1745	1674	1575	1674	159
180°	1679	1679	1679	1679	1679	



TEST NUMBER: P1428285

CATALOG NUMBER: SQ2W-PR1-K-125U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2
2.5°	1409.4	1417.1	1424.8	1421.3	1414.1	1410.8	1411.3	1412.1	1413.6	1415.2	1413.6
5°	1408.0	1418.9	1429.8	1427.2	1420.1	1417.3	1418.5	1421.1	1427.5	1433.9	1427.5
7.5°	1407.7	1423.2	1438.7	1439.9	1436.3	1436.4	1440.1	1445.0	1453.4	1461.9	1453.4
10°	1406.5	1425.1	1443.7	1446.4	1443.9	1442.9	1443.5	1446.3	1455.2	1464.2	1455.2
12.5°	1399.6	1421.3	1442.9	1440.7	1430.4	1424.8	1423.9	1424.5	1429.3	1434.2	1429.3
15°	1379.1	1404.8	1430.4	1420.0	1397.5	1387.3	1389.2	1391.4	1394.7	1397.9	1394.7
17.5°	1343.0	1369.8	1396.6	1387.3	1365.9	1358.6	1365.5	1372.3	1378.6	1384.9	1378.6
20°	1320.0	1346.2	1372.5	1366.1	1348.8	1344.6	1353.6	1363.1	1374.0	1384.9	1374.0
22.5°	1299.2	1325.5	1351.8	1347.7	1333.4	1332.6	1345.2	1358.3	1373.3	1388.3	1373.3
25°	1269.5	1292.6	1315.6	1316.1	1309.1	1316.1	1337.3	1357.3	1374.0	1390.6	1374.0
27.5°	1238.3	1251.9	1265.5	1274.5	1281.9	1299.9	1328.5	1352.9	1364.6	1376.2	1364.6
30°	1211.8	1220.7	1229.7	1246.4	1265.6	1287.7	1312.7	1332.6	1337.1	1341.6	1337.1
32.5°	1182.9	1188.3	1193.7	1217.2	1246.6	1268.0	1281.2	1289.7	1283.9	1278.1	1283.9
35°	1135.3	1139.8	1144.3	1174.3	1212.7	1226.8	1216.6	1205.8	1193.7	1181.5	1193.7
37.5°	1078.8	1088.0	1097.2	1121.7	1151.1	1150.9	1120.9	1094.9	1080.9	1066.9	1080.9
40°	1037.2	1052.6	1068.0	1084.3	1101.0	1086.9	1042.0	1004.4	988.3	972.3	988.3
42.5°	986.4	1011.1	1035.7	1039.3	1036.0	1005.7	948.5	900.7	881.1	861.5	881.1
45°	905.9	939.3	972.6	953.5	917.0	867.6	805.4	753.3	731.5	709.7	731.5
47.5°	811.0	845.3	879.5	843.5	784.2	726.7	671.2	624.4	604.1	583.7	604.1
50°	748.7	776.3	803.8	763.1	699.7	641.9	590.0	545.5	523.0	500.6	523.0
52.5°	685.2	705.1	725.0	684.6	624.3	568.1	516.2	472.1	451.7	431.3	451.7
55°	587.1	597.4	607.6	570.3	517.1	465.8	416.4	375.9	361.8	347.7	361.8
57.5°	497.1	503.7	510.2	474.8	425.4	379.8	337.9	303.8	293.4	283.0	293.4
60°	442.9	447.4	451.8	415.9	366.6	325.5	292.8	266.2	257.9	249.6	257.9
62.5°	393.2	396.7	400.2	365.5	318.2	281.6	255.5	234.4	228.2	221.9	228.2
65°	323.1	326.3	329.5	300.1	259.7	229.5	209.7	193.6	189.1	184.7	189.1
67.5°	267.5	269.1	270.8	246.5	213.5	189.2	173.6	160.8	156.6	152.3	156.6
70°	235.1	235.8	236.4	214.9	186.1	164.6	150.5	139.1	135.9	132.7	135.9
72.5°	206.3	205.4	204.5	185.3	160.1	141.7	130.1	120.9	118.7	116.6	118.7
75°	163.0	161.1	159.2	143.3	122.8	108.7	101.0	94.9	93.6	92.3	93.6
77.5°	121.8	119.7	117.7	104.4	87.5	77.8	75.2	73.3	73.3	73.3	73.3
80°	95.2	92.6	90.1	79.8	67.0	60.6	60.6	60.6	60.6	60.6	60.6
82.5°	71.0	67.4	63.8	57.5	50.3	46.7	46.7	46.6	46.1	45.6	46.1
85°	34.6	31.4	28.2	27.4	27.4	25.5	21.6	18.3	16.3	14.4	16.3
87.5°	10.3	11.6	13.3	12.7	11.2	10.2	10.2	10.6	10.9	10.9	10.9
90°	5.1	11.9	20.3	27.1	32.2	33.9	33.9	35.6	37.3	37.3	37.3
92.5°	18.7	29.5	29.8	29.8	36.3	39.3	42.1	42.4	44.1	44.1	44.1
95°	52.6	57.7	86.5	84.8	57.7	45.8	39.0	39.0	39.0	39.0	39.0
97.5°	100.4	107.9	112.6	150.9	159.4	154.0	125.5	105.5	94.3	89.2	94.3
100°	142.4	145.8	156.0	157.7	200.1	240.8	220.5	195.0	186.5	181.5	186.5
102.5°	184.5	186.5	202.1	209.3	219.1	242.2	312.7	304.9	299.1	298.1	299.1
105°	247.6	249.3	278.1	291.7	298.5	298.5	296.8	330.7	385.0	396.8	385.0
107.5°	315.1	322.9	356.8	393.1	400.9	402.9	394.1	389.0	387.0	388.3	387.0
110°	361.2	373.1	413.8	459.6	471.4	474.8	471.4	466.3	463.0	463.0	463.0



TEST NUMBER: P1428285

CATALOG NUMBER: SQ2W-PR1-K-125U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	406.0	423.3	469.4	522.0	542.0	552.2	544.7	541.0	537.6	540.3	537.6
115°	474.8	500.3	561.3	615.6	656.3	661.4	659.7	659.7	658.0	658.0	658.0
117.5°	538.6	579.3	647.8	710.9	758.0	771.6	778.4	776.3	774.3	777.7	774.3
120°	583.4	630.8	708.9	780.1	825.9	846.2	853.0	849.6	853.0	849.6	853.0
122.5°	630.8	689.2	765.8	839.8	893.7	916.8	924.9	925.6	926.3	924.2	926.3
125°	702.1	773.3	863.2	939.5	995.4	1022.6	1029.4	1031.1	1034.4	1042.9	1034.4
127.5°	774.0	854.7	953.4	1027.0	1084.3	1117.2	1127.7	1131.4	1138.6	1142.3	1138.6
130°	824.2	915.7	1015.8	1085.3	1141.3	1176.9	1195.6	1200.6	1209.1	1207.4	1209.1
132.5°	877.1	972.7	1074.1	1146.4	1198.3	1236.6	1252.5	1267.1	1270.2	1272.5	1270.2
135°	954.7	1058.2	1159.9	1231.2	1280.3	1317.7	1338.0	1351.6	1360.0	1365.1	1360.0
137.5°	1036.5	1145.7	1243.4	1306.8	1356.3	1388.5	1411.6	1425.8	1434.7	1438.7	1434.7
140°	1092.1	1197.2	1292.2	1358.3	1402.4	1434.7	1455.0	1472.0	1482.1	1482.1	1482.1
142.5°	1145.0	1248.8	1341.1	1407.2	1445.9	1475.4	1497.1	1510.0	1521.5	1521.5	1521.5
145°	1219.3	1322.7	1407.5	1473.7	1505.9	1533.0	1556.8	1566.9	1573.7	1573.7	1573.7
147.5°	1297.0	1388.5	1465.9	1529.3	1556.4	1588.3	1607.0	1615.1	1623.6	1619.8	1623.6
150°	1343.1	1427.9	1502.5	1561.8	1589.0	1619.5	1638.2	1644.9	1653.4	1648.3	1653.4
152.5°	1387.9	1468.6	1536.4	1591.7	1614.8	1645.3	1666.6	1673.4	1679.2	1675.5	1679.2
155°	1448.2	1519.5	1582.2	1633.1	1653.4	1682.3	1702.6	1711.1	1717.9	1709.4	1717.9
157.5°	1502.2	1563.5	1618.1	1665.0	1686.7	1711.4	1730.4	1740.9	1747.7	1744.0	1747.7
160°	1534.7	1590.7	1639.9	1683.9	1704.3	1726.3	1746.7	1758.6	1765.3	1760.3	1765.3
162.5°	1561.8	1612.4	1658.8	1698.9	1716.5	1735.8	1760.3	1770.8	1777.6	1771.1	1777.6
165°	1600.9	1641.6	1682.3	1716.2	1731.4	1746.7	1772.1	1784.0	1789.1	1782.3	1789.1
167.5°	1630.4	1661.6	1694.5	1723.6	1734.8	1749.7	1775.2	1785.0	1791.5	1783.0	1791.5
170°	1646.6	1673.8	1702.6	1726.3	1734.8	1748.4	1773.8	1782.3	1787.4	1778.9	1787.4
172.5°	1660.2	1680.6	1704.0	1725.0	1729.4	1740.2	1764.3	1772.8	1776.5	1769.4	1776.5
175°	1673.8	1685.6	1702.6	1716.2	1714.5	1721.3	1741.6	1748.4	1755.2	1745.0	1755.2
177.5°	1680.2	1685.6	1691.1	1699.2	1693.8	1693.8	1708.7	1712.8	1714.1	1708.7	1714.1
180°	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9



TEST NUMBER: P1428285

CATALOG NUMBER: SQ2W-PR1-K-125U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2
2.5°	1412.1	1411.3	1410.8	1414.1	1421.3	1424.8	1417.1	1409.4	1417.1	1424.8	1421.3
5°	1421.1	1418.5	1417.3	1420.1	1427.2	1429.8	1418.9	1408.0	1418.9	1429.8	1427.2
7.5°	1445.0	1440.1	1436.4	1436.3	1439.9	1438.7	1423.2	1407.7	1423.2	1438.7	1439.9
10°	1446.3	1443.5	1442.9	1443.9	1446.4	1443.7	1425.1	1406.5	1425.1	1443.7	1446.4
12.5°	1424.5	1423.9	1424.8	1430.4	1440.7	1442.9	1421.3	1399.6	1421.3	1442.9	1440.7
15°	1391.4	1389.2	1387.3	1397.5	1420.0	1430.4	1404.8	1379.1	1404.8	1430.4	1420.0
17.5°	1372.3	1365.5	1358.6	1365.9	1387.3	1396.6	1369.8	1343.0	1369.8	1396.6	1387.3
20°	1363.1	1353.6	1344.6	1348.8	1366.1	1372.5	1346.2	1320.0	1346.2	1372.5	1366.1
22.5°	1358.3	1345.2	1332.6	1333.4	1347.7	1351.8	1325.5	1299.2	1325.5	1351.8	1347.7
25°	1357.3	1337.3	1316.1	1309.1	1316.1	1315.6	1292.6	1269.5	1292.6	1315.6	1316.1
27.5°	1352.9	1328.5	1299.9	1281.9	1274.5	1265.5	1251.9	1238.3	1251.9	1265.5	1274.5
30°	1332.6	1312.7	1287.7	1265.6	1246.4	1229.7	1220.7	1211.8	1220.7	1229.7	1246.4
32.5°	1289.7	1281.2	1268.0	1246.6	1217.2	1193.7	1188.3	1182.9	1188.3	1193.7	1217.2
35°	1205.8	1216.6	1226.8	1212.7	1174.3	1144.3	1139.8	1135.3	1139.8	1144.3	1174.3
37.5°	1094.9	1120.9	1150.9	1151.1	1121.7	1097.2	1088.0	1078.8	1088.0	1097.2	1121.7
40°	1004.4	1042.0	1086.9	1101.0	1084.3	1068.0	1052.6	1037.2	1052.6	1068.0	1084.3
42.5°	900.7	948.5	1005.7	1036.0	1039.3	1035.7	1011.1	986.4	1011.1	1035.7	1039.3
45°	753.3	805.4	867.6	917.0	953.5	972.6	939.3	905.9	939.3	972.6	953.5
47.5°	624.4	671.2	726.7	784.2	843.5	879.5	845.3	811.0	845.3	879.5	843.5
50°	545.5	590.0	641.9	699.7	763.1	803.8	776.3	748.7	776.3	803.8	763.1
52.5°	472.1	516.2	568.1	624.3	684.6	725.0	705.1	685.2	705.1	725.0	684.6
55°	375.9	416.4	465.8	517.1	570.3	607.6	597.4	587.1	597.4	607.6	570.3
57.5°	303.8	337.9	379.8	425.4	474.8	510.2	503.7	497.1	503.7	510.2	474.8
60°	266.2	292.8	325.5	366.6	415.9	451.8	447.4	442.9	447.4	451.8	415.9
62.5°	234.4	255.5	281.6	318.2	365.5	400.2	396.7	393.2	396.7	400.2	365.5
65°	193.6	209.7	229.5	259.7	300.1	329.5	326.3	323.1	326.3	329.5	300.1
67.5°	160.8	173.6	189.2	213.5	246.5	270.8	269.1	267.5	269.1	270.8	246.5
70°	139.1	150.5	164.6	186.1	214.9	236.4	235.8	235.1	235.8	236.4	214.9
72.5°	120.9	130.1	141.7	160.1	185.3	204.5	205.4	206.3	205.4	204.5	185.3
75°	94.9	101.0	108.7	122.8	143.3	159.2	161.1	163.0	161.1	159.2	143.3
77.5°	73.3	75.2	77.8	87.5	104.4	117.7	119.7	121.8	119.7	117.7	104.4
80°	60.6	60.6	60.6	67.0	79.8	90.1	92.6	95.2	92.6	90.1	79.8
82.5°	46.6	46.7	46.7	50.3	57.5	63.8	67.4	71.0	67.4	63.8	57.5
85°	18.3	21.6	25.5	27.4	27.4	28.2	31.4	34.6	31.4	28.2	27.4
87.5°	10.6	10.2	10.2	11.2	12.7	13.3	11.6	10.3	11.6	13.0	13.4
90°	35.6	33.9	33.9	32.2	27.1	20.3	11.9	5.1	11.9	18.7	30.5
92.5°	42.4	42.1	39.3	36.3	29.8	29.8	29.5	18.7	32.2	45.8	65.8
95°	39.0	39.0	45.8	57.7	84.8	86.5	57.7	52.6	74.6	105.1	132.3
97.5°	105.5	125.5	154.0	159.4	150.9	112.6	107.9	100.4	136.7	166.9	210.6
100°	195.0	220.5	240.8	200.1	157.7	156.0	145.8	142.4	181.5	210.3	252.7
102.5°	304.9	312.7	242.2	219.1	209.3	202.1	186.5	184.5	223.5	263.2	298.8
105°	330.7	296.8	298.5	298.5	291.7	278.1	249.3	247.6	291.7	337.5	381.6
107.5°	389.0	394.1	402.9	400.9	393.1	356.8	322.9	315.1	354.8	409.7	458.2
110°	466.3	471.4	474.8	471.4	459.6	413.8	373.1	361.2	396.8	454.5	507.0



TEST NUMBER: P1428285

CATALOG NUMBER: SQ2W-PR1-K-125U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	541.0	544.7	552.2	542.0	522.0	469.4	423.3	406.0	441.6	500.6	554.5
115°	659.7	659.7	661.4	656.3	615.6	561.3	500.3	474.8	505.4	559.6	619.0
117.5°	776.3	778.4	771.6	758.0	710.9	647.8	579.3	538.6	562.7	620.0	681.0
120°	849.6	853.0	846.2	825.9	780.1	708.9	630.8	583.4	602.0	658.0	719.0
122.5°	925.6	924.9	916.8	893.7	839.8	765.8	689.2	630.8	638.6	690.5	750.2
125°	1031.1	1029.4	1022.6	995.4	939.5	863.2	773.3	702.1	691.9	736.0	797.0
127.5°	1131.4	1127.7	1117.2	1084.3	1027.0	953.4	854.7	774.0	751.2	779.1	835.0
130°	1200.6	1195.6	1176.9	1141.3	1085.3	1015.8	915.7	824.2	791.9	808.9	858.1
132.5°	1267.1	1252.5	1236.6	1198.3	1146.4	1074.1	972.7	877.1	832.6	840.1	878.4
135°	1351.6	1338.0	1317.7	1280.3	1231.2	1159.9	1058.2	954.7	893.7	886.9	909.0
137.5°	1425.8	1411.6	1388.5	1356.3	1306.8	1243.4	1145.7	1036.5	959.5	936.8	945.2
140°	1472.0	1455.0	1434.7	1402.4	1358.3	1292.2	1197.2	1092.1	1005.6	973.4	968.3
142.5°	1510.0	1497.1	1475.4	1445.9	1407.2	1341.1	1248.8	1145.0	1053.1	1011.4	999.5
145°	1566.9	1556.8	1533.0	1505.9	1473.7	1407.5	1322.7	1219.3	1127.7	1073.5	1048.0
147.5°	1615.1	1607.0	1588.3	1556.4	1529.3	1465.9	1388.5	1297.0	1203.0	1135.9	1103.0
150°	1644.9	1638.2	1619.5	1589.0	1561.8	1502.5	1427.9	1343.1	1253.2	1182.0	1139.6
152.5°	1673.4	1666.6	1645.3	1614.8	1591.7	1536.4	1468.6	1387.9	1296.6	1225.4	1181.6
155°	1711.1	1702.6	1682.3	1653.4	1633.1	1582.2	1519.5	1448.2	1370.2	1295.6	1246.4
157.5°	1740.9	1730.4	1711.4	1686.7	1665.0	1618.1	1563.5	1502.2	1434.0	1362.8	1312.6
160°	1758.6	1746.7	1726.3	1704.3	1683.9	1639.9	1590.7	1534.7	1472.0	1407.5	1353.3
162.5°	1770.8	1760.3	1735.8	1716.5	1698.9	1658.8	1612.4	1561.8	1505.9	1449.6	1399.4
165°	1784.0	1772.1	1746.7	1731.4	1716.2	1682.3	1641.6	1600.9	1553.4	1507.6	1466.9
167.5°	1785.0	1775.2	1749.7	1734.8	1723.6	1694.5	1661.6	1630.4	1593.4	1557.4	1523.5
170°	1782.3	1773.8	1748.4	1734.8	1726.3	1702.6	1673.8	1646.6	1617.8	1587.3	1560.2
172.5°	1772.8	1764.3	1740.2	1729.4	1725.0	1704.0	1680.6	1660.2	1635.4	1613.1	1591.4
175°	1748.4	1741.6	1721.3	1714.5	1716.2	1702.6	1685.6	1673.8	1658.5	1644.9	1633.1
177.5°	1712.8	1708.7	1693.8	1693.8	1699.2	1691.1	1685.6	1680.2	1673.4	1669.4	1665.3
180°	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9



TEST NUMBER: P1428285

CATALOG NUMBER: SQ2W-PR1-K-125U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2
2.5°	1414.1	1410.8	1411.3	1412.1	1413.6	1415.2	1413.6	1412.1	1411.3	1410.8	1414.1
5°	1420.1	1417.3	1418.5	1421.1	1427.5	1433.9	1427.5	1421.1	1418.5	1417.3	1420.1
7.5°	1436.3	1436.4	1440.1	1445.0	1453.4	1461.9	1453.4	1445.0	1440.1	1436.4	1436.3
10°	1443.9	1442.9	1443.5	1446.3	1455.2	1464.2	1455.2	1446.3	1443.5	1442.9	1443.9
12.5°	1430.4	1424.8	1423.9	1424.5	1429.3	1434.2	1429.3	1424.5	1423.9	1424.8	1430.4
15°	1397.5	1387.3	1389.2	1391.4	1394.7	1397.9	1394.7	1391.4	1389.2	1387.3	1397.5
17.5°	1365.9	1358.6	1365.5	1372.3	1378.6	1384.9	1378.6	1372.3	1365.5	1358.6	1365.9
20°	1348.8	1344.6	1353.6	1363.1	1374.0	1384.9	1374.0	1363.1	1353.6	1344.6	1348.8
22.5°	1333.4	1332.6	1345.2	1358.3	1373.3	1388.3	1373.3	1358.3	1345.2	1332.6	1333.4
25°	1309.1	1316.1	1337.3	1357.3	1374.0	1390.6	1374.0	1357.3	1337.3	1316.1	1309.1
27.5°	1281.9	1299.9	1328.5	1352.9	1364.6	1376.2	1364.6	1352.9	1328.5	1299.9	1281.9
30°	1265.6	1287.7	1312.7	1332.6	1337.1	1341.6	1337.1	1332.6	1312.7	1287.7	1265.6
32.5°	1246.6	1268.0	1281.2	1289.7	1283.9	1278.1	1283.9	1289.7	1281.2	1268.0	1246.6
35°	1212.7	1226.8	1216.6	1205.8	1193.7	1181.5	1193.7	1205.8	1216.6	1226.8	1212.7
37.5°	1151.1	1150.9	1120.9	1094.9	1080.9	1066.9	1080.9	1094.9	1120.9	1150.9	1151.1
40°	1101.0	1086.9	1042.0	1004.4	988.3	972.3	988.3	1004.4	1042.0	1086.9	1101.0
42.5°	1036.0	1005.7	948.5	900.7	881.1	861.5	881.1	900.7	948.5	1005.7	1036.0
45°	917.0	867.6	805.4	753.3	731.5	709.7	731.5	753.3	805.4	867.6	917.0
47.5°	784.2	726.7	671.2	624.4	604.1	583.7	604.1	624.4	671.2	726.7	784.2
50°	699.7	641.9	590.0	545.5	523.0	500.6	523.0	545.5	590.0	641.9	699.7
52.5°	624.3	568.1	516.2	472.1	451.7	431.3	451.7	472.1	516.2	568.1	624.3
55°	517.1	465.8	416.4	375.9	361.8	347.7	361.8	375.9	416.4	465.8	517.1
57.5°	425.4	379.8	337.9	303.8	293.4	283.0	293.4	303.8	337.9	379.8	425.4
60°	366.6	325.5	292.8	266.2	257.9	249.6	257.9	266.2	292.8	325.5	366.6
62.5°	318.2	281.6	255.5	234.4	228.2	221.9	228.2	234.4	255.5	281.6	318.2
65°	259.7	229.5	209.7	193.6	189.1	184.7	189.1	193.6	209.7	229.5	259.7
67.5°	213.5	189.2	173.6	160.8	156.6	152.3	156.6	160.8	173.6	189.2	213.5
70°	186.1	164.6	150.5	139.1	135.9	132.7	135.9	139.1	150.5	164.6	186.1
72.5°	160.1	141.7	130.1	120.9	118.7	116.6	118.7	120.9	130.1	141.7	160.1
75°	122.8	108.7	101.0	94.9	93.6	92.3	93.6	94.9	101.0	108.7	122.8
77.5°	87.5	77.8	75.2	73.3	73.3	73.3	73.3	73.3	75.2	77.8	87.5
80°	67.0	60.6	60.6	60.6	60.6	60.6	60.6	60.6	60.6	60.6	67.0
82.5°	50.3	46.7	46.7	46.6	46.1	45.6	46.1	46.6	46.7	46.7	50.3
85°	27.4	25.5	21.6	18.3	16.3	14.4	16.3	18.3	21.6	25.5	27.4
87.5°	12.5	13.6	16.0	17.4	18.7	18.0	18.7	17.4	16.0	13.6	12.5
90°	39.0	50.9	62.7	69.5	76.3	72.9	76.3	69.5	62.7	50.9	39.0
92.5°	78.3	98.4	112.9	125.2	130.6	129.9	130.6	125.2	112.9	98.4	78.3
95°	157.7	181.5	205.2	222.2	232.3	228.9	232.3	222.2	205.2	181.5	157.7
97.5°	243.2	275.1	301.5	317.5	327.6	334.4	327.6	317.5	301.5	275.1	243.2
100°	300.2	330.7	361.2	379.9	396.8	403.6	396.8	379.9	361.2	330.7	300.2
102.5°	346.3	386.3	419.5	439.6	453.8	460.6	453.8	439.6	419.5	386.3	346.3
105°	422.3	464.7	500.3	525.7	541.0	546.1	541.0	525.7	500.3	464.7	422.3
107.5°	498.2	542.0	574.9	603.0	621.7	632.5	621.7	603.0	574.9	542.0	498.2
110°	557.9	593.5	629.1	654.6	673.2	680.0	673.2	654.6	629.1	593.5	557.9

TEST NUMBER: P1428285

CATALOG NUMBER: SQ2W-PR1-K-125U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	608.1	647.8	683.4	708.9	730.2	739.7	730.2	708.9	683.4	647.8	608.1
115°	678.3	730.9	763.1	786.9	802.1	810.6	802.1	786.9	763.1	730.9	678.3
117.5°	736.7	791.6	826.9	845.2	852.3	858.4	852.3	845.2	826.9	791.6	736.7
120°	773.3	824.2	864.9	888.6	897.1	900.5	897.1	888.6	864.9	824.2	773.3
122.5°	807.2	855.4	894.7	923.9	937.8	941.2	937.8	923.9	894.7	855.4	807.2
125°	854.7	900.5	941.2	970.0	985.3	993.7	985.3	970.0	941.2	900.5	854.7
127.5°	896.1	945.6	982.9	1009.0	1023.9	1030.7	1023.9	1009.0	982.9	945.6	896.1
130°	919.1	970.0	1007.3	1036.1	1049.7	1056.5	1049.7	1036.1	1007.3	970.0	919.1
132.5°	936.8	990.4	1029.0	1055.1	1070.1	1076.8	1070.1	1055.1	1029.0	990.4	936.8
135°	958.1	1014.1	1054.8	1080.2	1093.8	1100.6	1093.8	1080.2	1054.8	1014.1	958.1
137.5°	976.8	1027.7	1070.1	1096.9	1109.1	1113.5	1109.1	1096.9	1070.1	1027.7	976.8
140°	990.4	1034.4	1076.8	1102.3	1115.8	1117.5	1115.8	1102.3	1076.8	1034.4	990.4
142.5°	1008.0	1042.6	1079.6	1105.0	1118.6	1121.6	1118.6	1105.0	1079.6	1042.6	1008.0
145°	1039.5	1059.9	1085.3	1109.1	1120.9	1124.3	1120.9	1109.1	1085.3	1059.9	1039.5
147.5°	1079.2	1085.7	1098.9	1114.5	1126.0	1128.4	1126.0	1114.5	1098.9	1085.7	1079.2
150°	1109.1	1107.4	1112.5	1122.6	1132.8	1131.1	1132.8	1122.6	1112.5	1107.4	1109.1
152.5°	1143.0	1133.1	1132.8	1137.6	1142.3	1142.0	1142.3	1137.6	1132.8	1133.1	1143.0
155°	1200.6	1182.0	1171.8	1168.4	1168.4	1166.7	1168.4	1168.4	1171.8	1182.0	1200.6
157.5°	1264.1	1237.9	1222.7	1214.5	1212.2	1208.4	1212.2	1214.5	1222.7	1237.9	1264.1
160°	1307.5	1278.6	1263.4	1249.8	1244.7	1239.6	1244.7	1249.8	1263.4	1278.6	1307.5
162.5°	1348.2	1320.7	1304.1	1291.9	1286.8	1279.0	1286.8	1291.9	1304.1	1320.7	1348.2
165°	1414.3	1385.5	1366.8	1356.7	1349.9	1343.1	1349.9	1356.7	1366.8	1385.5	1414.3
167.5°	1480.4	1448.9	1436.7	1425.2	1418.7	1406.5	1418.7	1425.2	1436.7	1448.9	1480.4
170°	1521.1	1492.3	1485.5	1475.4	1463.5	1449.9	1463.5	1475.4	1485.5	1492.3	1521.1
172.5°	1556.4	1537.1	1530.3	1520.1	1516.4	1505.5	1516.4	1520.1	1530.3	1537.1	1556.4
175°	1607.6	1592.4	1592.4	1590.7	1585.6	1575.4	1585.6	1590.7	1592.4	1592.4	1607.6
177.5°	1650.4	1642.2	1647.7	1647.7	1646.3	1636.8	1646.3	1647.7	1647.7	1642.2	1650.4
180°	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9	1678.9



TEST NUMBER: P1428285

CATALOG NUMBER: SQ2W-PR1-K-125U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1415.2	1415.2	1415.2	1415.2
2.5°	1421.3	1424.8	1417.1	1409.4
5°	1427.2	1429.8	1418.9	1408.0
7.5°	1439.9	1438.7	1423.2	1407.7
10°	1446.4	1443.7	1425.1	1406.5
12.5°	1440.7	1442.9	1421.3	1399.6
15°	1420.0	1430.4	1404.8	1379.1
17.5°	1387.3	1396.6	1369.8	1343.0
20°	1366.1	1372.5	1346.2	1320.0
22.5°	1347.7	1351.8	1325.5	1299.2
25°	1316.1	1315.6	1292.6	1269.5
27.5°	1274.5	1265.5	1251.9	1238.3
30°	1246.4	1229.7	1220.7	1211.8
32.5°	1217.2	1193.7	1188.3	1182.9
35°	1174.3	1144.3	1139.8	1135.3
37.5°	1121.7	1097.2	1088.0	1078.8
40°	1084.3	1068.0	1052.6	1037.2
42.5°	1039.3	1035.7	1011.1	986.4
45°	953.5	972.6	939.3	905.9
47.5°	843.5	879.5	845.3	811.0
50°	763.1	803.8	776.3	748.7
52.5°	684.6	725.0	705.1	685.2
55°	570.3	607.6	597.4	587.1
57.5°	474.8	510.2	503.7	497.1
60°	415.9	451.8	447.4	442.9
62.5°	365.5	400.2	396.7	393.2
65°	300.1	329.5	326.3	323.1
67.5°	246.5	270.8	269.1	267.5
70°	214.9	236.4	235.8	235.1
72.5°	185.3	204.5	205.4	206.3
75°	143.3	159.2	161.1	163.0
77.5°	104.4	117.7	119.7	121.8
80°	79.8	90.1	92.6	95.2
82.5°	57.5	63.8	67.4	71.0
85°	27.4	28.2	31.4	34.6
87.5°	13.4	13.0	11.6	10.3
90°	30.5	18.7	11.9	5.1
92.5°	65.8	45.8	32.2	18.7
95°	132.3	105.1	74.6	52.6
97.5°	210.6	166.9	136.7	100.4
100°	252.7	210.3	181.5	142.4
102.5°	298.8	263.2	223.5	184.5
105°	381.6	337.5	291.7	247.6
107.5°	458.2	409.7	354.8	315.1
110°	507.0	454.5	396.8	361.2

TEST NUMBER: P1428285

CATALOG NUMBER: SQ2W-PR1-K-125U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	554.5	500.6	441.6	406.0
115°	619.0	559.6	505.4	474.8
117.5°	681.0	620.0	562.7	538.6
120°	719.0	658.0	602.0	583.4
122.5°	750.2	690.5	638.6	630.8
125°	797.0	736.0	691.9	702.1
127.5°	835.0	779.1	751.2	774.0
130°	858.1	808.9	791.9	824.2
132.5°	878.4	840.1	832.6	877.1
135°	909.0	886.9	893.7	954.7
137.5°	945.2	936.8	959.5	1036.5
140°	968.3	973.4	1005.6	1092.1
142.5°	999.5	1011.4	1053.1	1145.0
145°	1048.0	1073.5	1127.7	1219.3
147.5°	1103.0	1135.9	1203.0	1297.0
150°	1139.6	1182.0	1253.2	1343.1
152.5°	1181.6	1225.4	1296.6	1387.9
155°	1246.4	1295.6	1370.2	1448.2
157.5°	1312.6	1362.8	1434.0	1502.2
160°	1353.3	1407.5	1472.0	1534.7
162.5°	1399.4	1449.6	1505.9	1561.8
165°	1466.9	1507.6	1553.4	1600.9
167.5°	1523.5	1557.4	1593.4	1630.4
170°	1560.2	1587.3	1617.8	1646.6
172.5°	1591.4	1613.1	1635.4	1660.2
175°	1633.1	1644.9	1658.5	1673.8
177.5°	1665.3	1669.4	1673.4	1680.2
180°	1678.9	1678.9	1678.9	1678.9



TEST NUMBER: P1428285
 CATALOG NUMBER: SQ2W-PR1-K-125U-075D-L935-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.64	17.39	17.68	18.43	19.83	13.01	13.76	14.05	14.80	16.20
	3H	17.84	18.51	18.89	19.56	20.98	14.16	14.84	15.21	15.88	17.30
	4H	18.32	18.96	19.38	20.01	21.43	14.62	15.26	15.68	16.31	17.73
	6H	18.61	19.20	19.68	20.25	21.69	14.96	15.54	16.03	16.60	18.03
	8H	18.71	19.27	19.78	20.34	21.77	15.09	15.65	16.17	16.72	18.15
	12H	18.75	19.28	19.83	20.34	21.79	15.12	15.65	16.20	16.71	18.17
4H	2H	16.73	17.37	17.80	18.42	19.84	13.71	14.34	14.77	15.39	16.82
	3H	18.18	18.71	19.25	19.79	21.22	15.05	15.58	16.13	16.66	18.10
	4H	18.80	19.29	19.88	20.36	21.82	15.59	16.08	16.67	17.15	18.61
	6H	19.23	19.65	20.32	20.74	22.19	16.02	16.44	17.11	17.53	18.98
	8H	19.39	19.78	20.48	20.86	22.33	16.20	16.59	17.29	17.67	19.14
	12H	19.45	19.80	20.55	20.90	22.37	16.25	16.60	17.35	17.69	19.17
8H	4H	18.82	19.21	19.91	20.30	21.76	15.91	16.30	17.00	17.39	18.85
	6H	19.35	19.67	20.46	20.80	22.26	16.45	16.77	17.56	17.90	19.36
	8H	19.59	19.87	20.70	20.97	22.46	16.71	16.99	17.83	18.10	19.59
	12H	19.70	19.95	20.82	21.05	22.57	16.80	17.05	17.92	18.15	19.68
12H	4H	18.78	19.13	19.88	20.23	21.70	15.93	16.28	17.03	17.38	18.85
	6H	19.34	19.62	20.46	20.73	22.21	16.52	16.80	17.64	17.91	19.40
	8H	19.59	19.84	20.71	20.94	22.46	16.81	17.05	17.93	18.16	19.68