

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428336

Luminaire Tested: SQ2W-PW1-0U-100D-L835-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428336
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PW1-0U-100D-L835-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE WAVES LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT N/A - DIRECT ONLY
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5114.0 lumens
Efficiency: N/A
Efficacy: 136.0 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.11 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428336

CATALOG NUMBER: SQ2W-PW1-0U-100D-L835-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428336

CATALOG NUMBER: SQ2W-PW1-0U-100D-L835-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	88	83	99	92	87	82	89	84	80	85	82	78	82	79	76	74				74
3	93	84	76	70	91	82	75	70	79	73	69	77	72	67	74	70	66	64				64
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56				56
5	80	68	59	53	78	67	59	53	65	58	52	63	57	52	61	56	51	49				49
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44				44
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	46	41	39				39
8	64	52	44	38	63	51	43	38	50	43	38	48	42	37	47	42	37	35				35
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32				32
10	57	44	37	32	55	44	36	31	43	36	31	42	36	31	41	35	31	29				29

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	37211	37211	37211	37211
5°	36961	37602	36961	37602
10°	37029	37929	37029	37929
15°	37019	38156	37019	38156
20°	37034	37412	37034	37412
25°	36834	34762	36834	34762
30°	36584	31427	36584	31427
35°	36298	28381	36298	28381
40°	35575	25075	35575	25075
45°	34181	21902	34181	21902
50°	31812	18746	31812	18746
55°	29100	15200	29100	15200
60°	26082	13113	26082	13113
65°	22808	11656	22808	11656
70°	18651	10570	18651	10570
75°	14516	9719	14516	9719
80°	10813	8573	10813	8573
85°	7317	4872	7317	4872

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 34181 cd/sqm



TEST NUMBER: P1428336

CATALOG NUMBER: SQ2W-PW1-0U-100D-L835-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.5	4.3
10°-20°	635.9	12.4
20°-30°	935.8	18.3
30°-40°	1023.1	20.0
40°-50°	917.8	17.9
50°-60°	684.6	13.4
60°-70°	432.7	8.5
70°-80°	214.4	4.2
80°-90°	50.2	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1791.1	35.0
0°-40°	2814.2	55.0
0°-60°	4416.7	86.4
0°-90°	5114.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5114.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2305	2305	2305	2305	2305	
5°	2280	2320	2280	2320	2280	217
15°	2215	2283	2215	2283	2215	625
25°	2068	1951	2068	1951	2068	952
35°	1842	1440	1842	1440	1842	1149
45°	1497	959	1497	959	1497	1148
55°	1034	540	1034	540	1034	923
65°	597	305	597	305	597	592
75°	233	156	233	156	233	256
85°	40	26	40	26	40	51
90°	0	0	0	0	0	



TEST NUMBER: P1428336

CATALOG NUMBER: SQ2W-PW1-0U-100D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2304.7	2304.7	2304.7	2304.7	2304.7	2304.7	2304.7	2304.7	2304.7	2304.7	2304.7
2.5°	2288.9	2302.2	2315.4	2312.3	2303.7	2299.8	2300.6	2301.8	2304.1	2306.4	2304.1
5°	2280.5	2297.1	2313.7	2311.3	2302.5	2298.6	2299.6	2302.5	2311.3	2320.1	2311.3
7.5°	2269.1	2285.9	2302.7	2301.9	2295.3	2293.6	2296.9	2301.6	2310.2	2318.7	2310.2
10°	2258.6	2276.2	2293.7	2293.7	2287.9	2287.4	2292.3	2297.9	2305.7	2313.5	2305.7
12.5°	2244.5	2262.9	2281.2	2282.6	2278.3	2279.0	2284.6	2290.8	2298.6	2306.4	2298.6
15°	2214.7	2234.2	2253.7	2257.9	2256.9	2259.8	2266.6	2273.0	2277.9	2282.7	2277.9
17.5°	2180.0	2199.5	2219.0	2222.9	2221.5	2221.7	2223.5	2225.4	2227.7	2230.1	2227.7
20°	2155.4	2174.9	2194.5	2197.1	2194.2	2189.3	2182.5	2177.4	2177.4	2177.4	2177.4
22.5°	2120.3	2141.4	2162.5	2162.6	2155.8	2143.1	2124.6	2109.1	2102.9	2096.6	2102.9
25°	2067.6	2088.1	2108.6	2099.1	2079.6	2050.8	2012.8	1980.6	1965.9	1951.3	1965.9
27.5°	2006.2	2022.8	2039.3	2014.5	1975.9	1929.5	1875.5	1829.9	1809.6	1789.3	1809.6
30°	1962.3	1975.0	1987.6	1948.4	1891.8	1833.8	1774.2	1724.7	1705.2	1685.7	1705.2
32.5°	1916.6	1921.5	1926.4	1874.6	1804.0	1737.8	1675.9	1624.3	1603.2	1582.1	1603.2
35°	1841.6	1832.8	1824.0	1755.2	1666.4	1590.8	1528.4	1477.0	1458.4	1439.9	1458.4
37.5°	1752.9	1726.7	1700.6	1623.1	1528.5	1448.5	1383.1	1329.0	1308.5	1288.0	1308.5
40°	1687.9	1650.8	1613.8	1530.6	1432.1	1350.1	1284.8	1230.6	1210.1	1189.7	1210.1
42.5°	1615.9	1569.5	1523.0	1437.5	1339.0	1257.1	1191.7	1137.4	1116.1	1094.8	1116.1
45°	1497.0	1442.3	1387.7	1298.7	1198.2	1116.3	1052.8	1000.2	979.7	959.2	979.7
47.5°	1363.1	1308.8	1254.6	1165.8	1065.5	984.7	923.2	872.7	855.1	837.6	855.1
50°	1266.5	1213.8	1161.1	1076.3	980.7	902.1	840.7	789.2	767.7	746.3	767.7
52.5°	1168.1	1120.9	1073.7	992.0	898.7	820.6	757.5	703.0	673.7	644.4	673.7
55°	1033.8	988.9	944.1	867.0	779.2	700.2	629.9	573.1	556.5	540.0	556.5
57.5°	895.5	856.7	817.9	748.6	669.2	597.6	533.8	482.5	468.9	455.2	468.9
60°	807.7	773.6	739.5	673.1	596.0	530.7	477.0	433.4	419.7	406.1	419.7
62.5°	723.5	693.2	663.0	599.4	524.6	465.9	423.2	388.3	377.0	365.7	377.0
65°	597.0	574.6	552.2	499.7	437.3	388.5	353.4	324.6	314.9	305.1	314.9
67.5°	474.1	461.6	449.1	409.9	361.7	322.2	291.3	266.6	260.2	253.7	260.2
70°	395.1	391.2	387.3	354.8	312.9	279.2	253.9	233.6	228.8	223.9	228.8
72.5°	326.6	328.2	329.7	302.8	266.3	238.1	218.2	202.4	199.1	195.8	199.1
75°	232.7	240.5	248.3	230.5	204.1	184.1	170.5	159.7	157.8	155.8	157.8
77.5°	158.5	170.2	181.9	170.3	151.0	136.3	126.1	118.1	116.6	115.0	116.6
80°	116.3	128.0	139.7	131.7	117.1	105.8	98.0	92.2	92.2	92.2	92.2
82.5°	81.2	90.6	99.9	94.2	83.5	76.2	72.3	69.4	69.4	69.4	69.4
85°	39.5	44.4	49.3	47.6	43.7	38.8	32.9	28.3	27.3	26.3	27.3
87.5°	10.5	12.9	15.2	12.9	9.0	6.6	5.9	5.3	5.3	5.3	5.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1428336

CATALOG NUMBER: SQ2W-PW1-0U-100D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2304.7	2304.7	2304.7	2304.7	2304.7	2304.7	2304.7	2304.7	2304.7	2304.7	2304.7
2.5°	2301.8	2300.6	2299.8	2303.7	2312.3	2315.4	2302.2	2288.9	2302.2	2315.4	2312.3
5°	2302.5	2299.6	2298.6	2302.5	2311.3	2313.7	2297.1	2280.5	2297.1	2313.7	2311.3
7.5°	2301.6	2296.9	2293.6	2295.3	2301.9	2302.7	2285.9	2269.1	2285.9	2302.7	2301.9
10°	2297.9	2292.3	2287.4	2287.9	2293.7	2293.7	2276.2	2258.6	2276.2	2293.7	2293.7
12.5°	2290.8	2284.6	2279.0	2278.3	2282.6	2281.2	2262.9	2244.5	2262.9	2281.2	2282.6
15°	2273.0	2266.6	2259.8	2256.9	2257.9	2253.7	2234.2	2214.7	2234.2	2253.7	2257.9
17.5°	2225.4	2223.5	2221.7	2221.5	2222.9	2219.0	2199.5	2180.0	2199.5	2219.0	2222.9
20°	2177.4	2182.5	2189.3	2194.2	2197.1	2194.5	2174.9	2155.4	2174.9	2194.5	2197.1
22.5°	2109.1	2124.6	2143.1	2155.8	2162.6	2162.5	2141.4	2120.3	2141.4	2162.5	2162.6
25°	1980.6	2012.8	2050.8	2079.6	2099.1	2108.6	2088.1	2067.6	2088.1	2108.6	2099.1
27.5°	1829.9	1875.5	1929.5	1975.9	2014.5	2039.3	2022.8	2006.2	2022.8	2039.3	2014.5
30°	1724.7	1774.2	1833.8	1891.8	1948.4	1987.6	1975.0	1962.3	1975.0	1987.6	1948.4
32.5°	1624.3	1675.9	1737.8	1804.0	1874.6	1926.4	1921.5	1916.6	1921.5	1926.4	1874.6
35°	1477.0	1528.4	1590.8	1666.4	1755.2	1824.0	1832.8	1841.6	1832.8	1824.0	1755.2
37.5°	1329.0	1383.1	1448.5	1528.5	1623.1	1700.6	1726.7	1752.9	1726.7	1700.6	1623.1
40°	1230.6	1284.8	1350.1	1432.1	1530.6	1613.8	1650.8	1687.9	1650.8	1613.8	1530.6
42.5°	1137.4	1191.7	1257.1	1339.0	1437.5	1523.0	1569.5	1615.9	1569.5	1523.0	1437.5
45°	1000.2	1052.8	1116.3	1198.2	1298.7	1387.7	1442.3	1497.0	1442.3	1387.7	1298.7
47.5°	872.7	923.2	984.7	1065.5	1165.8	1254.6	1308.8	1363.1	1308.8	1254.6	1165.8
50°	789.2	840.7	902.1	980.7	1076.3	1161.1	1213.8	1266.5	1213.8	1161.1	1076.3
52.5°	703.0	757.5	820.6	898.7	992.0	1073.7	1120.9	1168.1	1120.9	1073.7	992.0
55°	573.1	629.9	700.2	779.2	867.0	944.1	988.9	1033.8	988.9	944.1	867.0
57.5°	482.5	533.8	597.6	669.2	748.6	817.9	856.7	895.5	856.7	817.9	748.6
60°	433.4	477.0	530.7	596.0	673.1	739.5	773.6	807.7	773.6	739.5	673.1
62.5°	388.3	423.2	465.9	524.6	599.4	663.0	693.2	723.5	693.2	663.0	599.4
65°	324.6	353.4	388.5	437.3	499.7	552.2	574.6	597.0	574.6	552.2	499.7
67.5°	266.6	291.3	322.2	361.7	409.9	449.1	461.6	474.1	461.6	449.1	409.9
70°	233.6	253.9	279.2	312.9	354.8	387.3	391.2	395.1	391.2	387.3	354.8
72.5°	202.4	218.2	238.1	266.3	302.8	329.7	328.2	326.6	328.2	329.7	302.8
75°	159.7	170.5	184.1	204.1	230.5	248.3	240.5	232.7	240.5	248.3	230.5
77.5°	118.1	126.1	136.3	151.0	170.3	181.9	170.2	158.5	170.2	181.9	170.3
80°	92.2	98.0	105.8	117.1	131.7	139.7	128.0	116.3	128.0	139.7	131.7
82.5°	69.4	72.3	76.2	83.5	94.2	99.9	90.6	81.2	90.6	99.9	94.2
85°	28.3	32.9	38.8	43.7	47.6	49.3	44.4	39.5	44.4	49.3	47.6
87.5°	5.3	5.9	6.6	9.0	12.9	15.2	12.9	10.5	12.9	15.2	12.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1428336

CATALOG NUMBER: SQ2W-PW1-0U-100D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2304.7	2304.7	2304.7	2304.7	2304.7	2304.7	2304.7	2304.7	2304.7	2304.7	2304.7
2.5°	2303.7	2299.8	2300.6	2301.8	2304.1	2306.4	2304.1	2301.8	2300.6	2299.8	2303.7
5°	2302.5	2298.6	2299.6	2302.5	2311.3	2320.1	2311.3	2302.5	2299.6	2298.6	2302.5
7.5°	2295.3	2293.6	2296.9	2301.6	2310.2	2318.7	2310.2	2301.6	2296.9	2293.6	2295.3
10°	2287.9	2287.4	2292.3	2297.9	2305.7	2313.5	2305.7	2297.9	2292.3	2287.4	2287.9
12.5°	2278.3	2279.0	2284.6	2290.8	2298.6	2306.4	2298.6	2290.8	2284.6	2279.0	2278.3
15°	2256.9	2259.8	2266.6	2273.0	2277.9	2282.7	2277.9	2273.0	2266.6	2259.8	2256.9
17.5°	2221.5	2221.7	2223.5	2225.4	2227.7	2230.1	2227.7	2225.4	2223.5	2221.7	2221.5
20°	2194.2	2189.3	2182.5	2177.4	2177.4	2177.4	2177.4	2177.4	2182.5	2189.3	2194.2
22.5°	2155.8	2143.1	2124.6	2109.1	2102.9	2096.6	2102.9	2109.1	2124.6	2143.1	2155.8
25°	2079.6	2050.8	2012.8	1980.6	1965.9	1951.3	1965.9	1980.6	2012.8	2050.8	2079.6
27.5°	1975.9	1929.5	1875.5	1829.9	1809.6	1789.3	1809.6	1829.9	1875.5	1929.5	1975.9
30°	1891.8	1833.8	1774.2	1724.7	1705.2	1685.7	1705.2	1724.7	1774.2	1833.8	1891.8
32.5°	1804.0	1737.8	1675.9	1624.3	1603.2	1582.1	1603.2	1624.3	1675.9	1737.8	1804.0
35°	1666.4	1590.8	1528.4	1477.0	1458.4	1439.9	1458.4	1477.0	1528.4	1590.8	1666.4
37.5°	1528.5	1448.5	1383.1	1329.0	1308.5	1288.0	1308.5	1329.0	1383.1	1448.5	1528.5
40°	1432.1	1350.1	1284.8	1230.6	1210.1	1189.7	1210.1	1230.6	1284.8	1350.1	1432.1
42.5°	1339.0	1257.1	1191.7	1137.4	1116.1	1094.8	1116.1	1137.4	1191.7	1257.1	1339.0
45°	1198.2	1116.3	1052.8	1000.2	979.7	959.2	979.7	1000.2	1052.8	1116.3	1198.2
47.5°	1065.5	984.7	923.2	872.7	855.1	837.6	855.1	872.7	923.2	984.7	1065.5
50°	980.7	902.1	840.7	789.2	767.7	746.3	767.7	789.2	840.7	902.1	980.7
52.5°	898.7	820.6	757.5	703.0	673.7	644.4	673.7	703.0	757.5	820.6	898.7
55°	779.2	700.2	629.9	573.1	556.5	540.0	556.5	573.1	629.9	700.2	779.2
57.5°	669.2	597.6	533.8	482.5	468.9	455.2	468.9	482.5	533.8	597.6	669.2
60°	596.0	530.7	477.0	433.4	419.7	406.1	419.7	433.4	477.0	530.7	596.0
62.5°	524.6	465.9	423.2	388.3	377.0	365.7	377.0	388.3	423.2	465.9	524.6
65°	437.3	388.5	353.4	324.6	314.9	305.1	314.9	324.6	353.4	388.5	437.3
67.5°	361.7	322.2	291.3	266.6	260.2	253.7	260.2	266.6	291.3	322.2	361.7
70°	312.9	279.2	253.9	233.6	228.8	223.9	228.8	233.6	253.9	279.2	312.9
72.5°	266.3	238.1	218.2	202.4	199.1	195.8	199.1	202.4	218.2	238.1	266.3
75°	204.1	184.1	170.5	159.7	157.8	155.8	157.8	159.7	170.5	184.1	204.1
77.5°	151.0	136.3	126.1	118.1	116.6	115.0	116.6	118.1	126.1	136.3	151.0
80°	117.1	105.8	98.0	92.2	92.2	92.2	92.2	92.2	98.0	105.8	117.1
82.5°	83.5	76.2	72.3	69.4	69.4	69.4	69.4	69.4	72.3	76.2	83.5
85°	43.7	38.8	32.9	28.3	27.3	26.3	27.3	28.3	32.9	38.8	43.7
87.5°	9.0	6.6	5.9	5.3	5.3	5.3	5.3	5.3	5.9	6.6	9.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1428336

CATALOG NUMBER: SQ2W-PW1-0U-100D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	2304.7	2304.7	2304.7	2304.7
2.5°	2312.3	2315.4	2302.2	2288.9
5°	2311.3	2313.7	2297.1	2280.5
7.5°	2301.9	2302.7	2285.9	2269.1
10°	2293.7	2293.7	2276.2	2258.6
12.5°	2282.6	2281.2	2262.9	2244.5
15°	2257.9	2253.7	2234.2	2214.7
17.5°	2222.9	2219.0	2199.5	2180.0
20°	2197.1	2194.5	2174.9	2155.4
22.5°	2162.6	2162.5	2141.4	2120.3
25°	2099.1	2108.6	2088.1	2067.6
27.5°	2014.5	2039.3	2022.8	2006.2
30°	1948.4	1987.6	1975.0	1962.3
32.5°	1874.6	1926.4	1921.5	1916.6
35°	1755.2	1824.0	1832.8	1841.6
37.5°	1623.1	1700.6	1726.7	1752.9
40°	1530.6	1613.8	1650.8	1687.9
42.5°	1437.5	1523.0	1569.5	1615.9
45°	1298.7	1387.7	1442.3	1497.0
47.5°	1165.8	1254.6	1308.8	1363.1
50°	1076.3	1161.1	1213.8	1266.5
52.5°	992.0	1073.7	1120.9	1168.1
55°	867.0	944.1	988.9	1033.8
57.5°	748.6	817.9	856.7	895.5
60°	673.1	739.5	773.6	807.7
62.5°	599.4	663.0	693.2	723.5
65°	499.7	552.2	574.6	597.0
67.5°	409.9	449.1	461.6	474.1
70°	354.8	387.3	391.2	395.1
72.5°	302.8	329.7	328.2	326.6
75°	230.5	248.3	240.5	232.7
77.5°	170.3	181.9	170.2	158.5
80°	131.7	139.7	128.0	116.3
82.5°	94.2	99.9	90.6	81.2
85°	47.6	49.3	44.4	39.5
87.5°	12.9	15.2	12.9	10.5
90°	0.0	0.0	0.0	0.0



TEST NUMBER: P1428336
 CATALOG NUMBER: SQ2W-PW1-0U-100D-L835-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	23.40	24.90	23.77	25.22	25.53	19.65	21.15	20.01	21.46	21.78
	3H	24.75	26.09	25.13	26.42	26.78	20.96	22.31	21.34	22.64	23.00
	4H	25.18	26.45	25.58	26.79	27.17	21.50	22.76	21.90	23.11	23.49
	6H	25.39	26.56	25.81	26.93	27.32	21.84	23.00	22.25	23.37	23.76
	8H	25.45	26.56	25.88	26.95	27.35	21.97	23.08	22.40	23.47	23.87
	12H	25.47	26.54	25.91	26.92	27.35	22.02	23.08	22.45	23.46	23.89
4H	2H	23.61	24.87	24.01	25.22	25.60	20.53	21.79	20.93	22.14	22.52
	3H	25.20	26.24	25.61	26.64	27.05	22.03	23.08	22.45	23.48	23.88
	4H	25.77	26.71	26.20	27.12	27.56	22.64	23.57	23.07	23.99	24.43
	6H	26.11	26.93	26.57	27.37	27.83	23.05	23.87	23.51	24.31	24.77
	8H	26.22	26.98	26.68	27.42	27.89	23.21	23.98	23.68	24.42	24.89
	12H	26.27	26.95	26.75	27.42	27.90	23.29	23.97	23.77	24.44	24.92
8H	4H	25.85	26.61	26.32	27.06	27.53	23.02	23.78	23.49	24.23	24.70
	6H	26.30	26.92	26.79	27.42	27.89	23.54	24.17	24.04	24.66	25.14
	8H	26.47	27.03	26.98	27.54	28.03	23.76	24.32	24.27	24.83	25.32
	12H	26.57	27.07	27.08	27.56	28.13	23.87	24.37	24.38	24.86	25.42
12H	4H	25.84	26.52	26.32	27.00	27.47	23.07	23.75	23.55	24.23	24.70
	6H	26.29	26.86	26.81	27.37	27.85	23.61	24.18	24.13	24.69	25.18
	8H	26.51	27.01	27.02	27.50	28.06	23.89	24.38	24.40	24.88	25.44