

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428426

Luminaire Tested: SQ2W-PW1-K-100U-075D-L835-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428426
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PW1-K-100U-075D-L835-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE WAVES LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8185.2 lumens
Efficiency: N/A
Efficacy: 136.9 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.11 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428426

CATALOG NUMBER: SQ2W-PW1-K-100U-075D-L835-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428426

CATALOG NUMBER: SQ2W-PW1-K-100U-075D-L835-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53	47				47
1	98	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46				40	
2	89	82	76	71	82	76	71	67	64	60	57	53	50	48	43	41	39				35	
3	82	73	66	60	75	67	61	56	57	52	49	47	44	41	38	36	34				30	
4	75	65	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30				26	
5	69	58	50	44	63	54	47	42	46	40	36	38	34	31	31	28	26				23	
6	64	52	44	39	58	48	41	36	41	36	32	35	31	28	28	26	23				20	
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21				18	
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19				16	
9	51	39	32	27	47	37	30	26	31	26	23	27	23	20	22	19	17				15	
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16				14	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	27675	27675	27675	27675
5°	27491	27967	27491	27967
10°	27541	28210	27541	28210
15°	27533	28379	27533	28379
20°	27544	27826	27544	27826
25°	27395	25854	27395	25854
30°	27210	23375	27210	23375
35°	26997	21108	26997	21108
40°	26459	18649	26459	18649
45°	25423	16289	25423	16289
50°	23661	13943	23661	13943
55°	21644	11305	21644	11305
60°	19400	9752	19400	9752
65°	16962	8668	16962	8668
70°	13874	7860	13874	7860
75°	10792	7230	10792	7230
80°	8043	6378	8043	6378
85°	5446	3631	5446	3631

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 25423 cd/sqm



TEST NUMBER: P1428426

CATALOG NUMBER: SQ2W-PW1-K-100U-075D-L835-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.2	2.0
10°-20°	472.9	5.8
20°-30°	696.0	8.5
30°-40°	761.0	9.3
40°-50°	682.7	8.3
50°-60°	509.2	6.2
60°-70°	321.8	3.9
70°-80°	159.5	1.9
80°-90°	43.5	0.5
90°-100°	119.3	1.5
100°-110°	347.8	4.2
110°-120°	567.6	6.9
120°-130°	720.2	8.8
130°-140°	770.6	9.4
140°-150°	719.6	8.8
150°-160°	592.1	7.2
160°-170°	397.1	4.9
170°-180°	141.0	1.7
0°-30°	1332.1	16.3
0°-40°	2093.1	25.6
0°-60°	3285.0	40.1
0°-90°	3809.8	46.5
90°-120°	1034.6	12.6
90°-150°	3245.1	39.6
90°-180°	4375.0	53.5
0°-180°	8185.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1714	1714	1714	1714	1714	
5°	1696	1726	1696	1726	1696	161
15°	1647	1698	1647	1698	1647	465
25°	1538	1451	1538	1451	1538	708
35°	1370	1071	1370	1071	1370	854
45°	1113	713	1113	713	1113	854
55°	769	402	769	402	769	687
65°	444	227	444	227	444	440
75°	173	116	173	116	173	191
85°	29	20	29	20	29	37
90°	4	33	4	65	4	5
95°	47	35	47	204	47	57
105°	221	354	221	487	221	235
115°	424	587	424	724	424	418
125°	627	931	627	887	627	561
135°	852	1218	852	982	852	659
145°	1088	1405	1088	1004	1088	681
155°	1293	1526	1293	1041	1293	594
165°	1429	1591	1429	1199	1429	402
175°	1494	1558	1494	1406	1494	142
180°	1498	1498	1498	1498	1498	



TEST NUMBER: P1428426

CATALOG NUMBER: SQ2W-PW1-K-100U-075D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1
2.5°	1702.4	1712.3	1722.1	1719.8	1713.4	1710.5	1711.1	1712.0	1713.7	1715.5	1713.7
5°	1696.2	1708.5	1720.9	1719.0	1712.5	1709.6	1710.3	1712.5	1719.0	1725.6	1719.0
7.5°	1687.7	1700.2	1712.7	1712.1	1707.1	1705.9	1708.4	1711.8	1718.2	1724.6	1718.2
10°	1679.9	1692.9	1706.0	1706.0	1701.6	1701.3	1704.9	1709.1	1714.9	1720.7	1714.9
12.5°	1669.4	1683.1	1696.7	1697.7	1694.5	1695.0	1699.2	1703.8	1709.6	1715.5	1709.6
15°	1647.2	1661.7	1676.2	1679.3	1678.6	1680.8	1685.8	1690.6	1694.2	1697.8	1694.2
17.5°	1621.4	1635.9	1650.4	1653.3	1652.3	1652.4	1653.7	1655.2	1656.9	1658.6	1656.9
20°	1603.1	1617.6	1632.2	1634.2	1632.0	1628.3	1623.3	1619.5	1619.5	1619.5	1619.5
22.5°	1577.0	1592.7	1608.4	1608.5	1603.4	1594.0	1580.2	1568.7	1564.0	1559.4	1564.0
25°	1537.8	1553.1	1568.3	1561.2	1546.7	1525.3	1497.0	1473.1	1462.2	1451.3	1462.2
27.5°	1492.1	1504.5	1516.8	1498.3	1469.6	1435.1	1394.9	1361.0	1345.9	1330.8	1345.9
30°	1459.5	1468.9	1478.3	1449.1	1407.1	1363.9	1319.6	1282.8	1268.3	1253.8	1268.3
32.5°	1425.5	1429.1	1432.8	1394.3	1341.8	1292.5	1246.5	1208.1	1192.4	1176.7	1192.4
35°	1369.7	1363.2	1356.6	1305.5	1239.4	1183.2	1136.8	1098.5	1084.7	1070.9	1084.7
37.5°	1303.7	1284.3	1264.8	1207.2	1136.8	1077.3	1028.7	988.4	973.2	958.0	973.2
40°	1255.4	1227.8	1200.3	1138.4	1065.1	1004.2	955.6	915.3	900.1	884.8	900.1
42.5°	1201.9	1167.3	1132.8	1069.2	995.9	935.0	886.3	845.9	830.1	814.3	830.1
45°	1113.4	1072.7	1032.1	965.9	891.2	830.2	783.1	743.9	728.6	713.4	728.6
47.5°	1013.8	973.5	933.1	867.1	792.5	732.3	686.6	649.1	636.0	623.0	636.0
50°	942.0	902.8	863.6	800.5	729.4	671.0	625.3	587.0	571.0	555.1	571.0
52.5°	868.8	833.7	798.6	737.8	668.4	610.3	563.4	522.8	501.1	479.3	501.1
55°	768.9	735.5	702.2	644.8	579.5	520.8	468.5	426.3	413.9	401.6	413.9
57.5°	666.1	637.2	608.3	556.8	497.7	444.5	397.0	358.9	348.7	338.6	348.7
60°	600.8	575.4	550.0	500.6	443.3	394.7	354.8	322.3	312.2	302.0	312.2
62.5°	538.1	515.6	493.1	445.8	390.2	346.5	314.7	288.8	280.4	272.0	280.4
65°	444.0	427.4	410.7	371.7	325.2	289.0	262.8	241.4	234.2	226.9	234.2
67.5°	352.6	343.3	334.0	304.8	269.0	239.6	216.7	198.3	193.5	188.7	193.5
70°	293.9	291.0	288.0	263.9	232.7	207.7	188.8	173.8	170.1	166.5	170.1
72.5°	242.9	244.1	245.2	225.2	198.0	177.1	162.3	150.6	148.1	145.6	148.1
75°	173.0	178.9	184.7	171.4	151.8	137.0	126.8	118.8	117.4	115.9	117.4
77.5°	117.9	126.6	135.3	126.7	112.3	101.4	93.8	87.9	86.7	85.5	86.7
80°	86.5	95.2	103.9	98.0	87.1	78.7	72.9	68.6	68.6	68.6	68.6
82.5°	60.4	67.4	74.3	70.1	62.1	56.7	53.8	51.6	51.6	51.6	51.6
85°	29.4	33.0	36.6	35.4	32.5	28.8	24.5	21.0	20.3	19.6	20.3
87.5°	8.7	11.7	15.0	14.4	12.4	11.0	10.4	10.3	10.6	10.6	10.6
90°	4.5	10.6	18.2	24.2	28.8	30.3	30.3	31.8	33.3	33.3	33.3
92.5°	16.7	26.3	26.6	26.6	32.4	35.1	37.5	37.8	39.4	39.4	39.4
95°	46.9	51.5	77.2	75.7	51.5	40.9	34.8	34.8	34.8	34.8	34.8
97.5°	89.6	96.3	100.5	134.7	142.3	137.4	112.0	94.1	84.2	79.6	84.2
100°	127.1	130.2	139.3	140.8	178.6	214.9	196.8	174.1	166.5	162.0	166.5
102.5°	164.7	166.5	180.4	186.8	195.6	216.1	279.1	272.2	267.0	266.1	267.0
105°	221.0	222.5	248.2	260.3	266.4	266.4	264.9	295.2	343.6	354.2	343.6
107.5°	281.2	288.2	318.5	350.9	357.8	359.6	351.8	347.2	345.4	346.6	345.4
110°	322.4	333.0	369.3	410.2	420.8	423.8	420.8	416.3	413.2	413.2	413.2

TEST NUMBER: P1428426

CATALOG NUMBER: SQ2W-PW1-K-100U-075D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	362.4	377.8	419.0	465.9	483.8	492.8	486.2	482.9	479.8	482.2	479.8
115°	423.8	446.5	501.0	549.5	585.8	590.3	588.8	588.8	587.3	587.3	587.3
117.5°	480.7	517.1	578.2	634.5	676.6	688.7	694.8	692.9	691.1	694.2	691.1
120°	520.7	563.1	632.7	696.3	737.1	755.3	761.4	758.3	761.4	758.3	761.4
122.5°	563.1	615.1	683.6	749.6	797.7	818.3	825.5	826.2	826.8	824.9	826.8
125°	626.7	690.2	770.4	838.6	888.5	912.7	918.8	920.3	923.3	930.9	923.3
127.5°	690.8	762.9	851.0	916.7	967.8	997.2	1006.6	1009.9	1016.3	1019.6	1016.3
130°	735.6	817.4	906.7	968.7	1018.7	1050.5	1067.1	1071.7	1079.2	1077.7	1079.2
132.5°	782.9	868.2	958.7	1023.2	1069.5	1103.8	1118.0	1131.0	1133.7	1135.8	1133.7
135°	852.2	944.5	1035.3	1098.9	1142.8	1176.1	1194.3	1206.4	1213.9	1218.5	1213.9
137.5°	925.1	1022.6	1109.8	1166.4	1210.6	1239.4	1260.0	1272.7	1280.5	1284.2	1280.5
140°	974.8	1068.6	1153.4	1212.4	1251.8	1280.5	1298.7	1313.8	1322.9	1322.9	1322.9
142.5°	1022.0	1114.7	1197.0	1256.0	1290.5	1316.9	1336.3	1347.8	1358.0	1358.0	1358.0
145°	1088.3	1180.6	1256.3	1315.4	1344.1	1368.3	1389.5	1398.6	1404.7	1404.7	1404.7
147.5°	1157.6	1239.4	1308.4	1365.0	1389.2	1417.7	1434.3	1441.6	1449.2	1445.8	1449.2
150°	1198.8	1274.5	1341.1	1394.1	1418.3	1445.5	1462.2	1468.2	1475.8	1471.3	1475.8
152.5°	1238.8	1310.8	1371.4	1420.7	1441.3	1468.5	1487.6	1493.7	1498.8	1495.5	1498.8
155°	1292.7	1356.2	1412.2	1457.6	1475.8	1501.5	1519.7	1527.3	1533.3	1525.8	1533.3
157.5°	1340.8	1395.6	1444.3	1486.1	1505.5	1527.6	1544.5	1553.9	1560.0	1556.6	1560.0
160°	1369.9	1419.8	1463.7	1503.1	1521.2	1540.9	1559.1	1569.7	1575.7	1571.2	1575.7
162.5°	1394.1	1439.2	1480.7	1516.4	1532.1	1549.4	1571.2	1580.6	1586.6	1580.9	1586.6
165°	1428.9	1465.2	1501.5	1531.8	1545.4	1559.1	1581.8	1592.4	1596.9	1590.8	1596.9
167.5°	1455.2	1483.1	1512.4	1538.5	1548.5	1561.8	1584.5	1593.3	1599.0	1591.5	1599.0
170°	1469.8	1494.0	1519.7	1540.9	1548.5	1560.6	1583.3	1590.8	1595.4	1587.8	1595.4
172.5°	1481.9	1500.0	1520.9	1539.7	1543.6	1553.3	1574.8	1582.4	1585.7	1579.3	1585.7
175°	1494.0	1504.6	1519.7	1531.8	1530.3	1536.4	1554.5	1560.6	1566.6	1557.5	1566.6
177.5°	1499.7	1504.6	1509.4	1516.7	1511.8	1511.8	1525.2	1528.8	1530.0	1525.2	1530.0
180°	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5

TEST NUMBER: P1428426

CATALOG NUMBER: SQ2W-PW1-K-100U-075D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1
2.5°	1712.0	1711.1	1710.5	1713.4	1719.8	1722.1	1712.3	1702.4	1712.3	1722.1	1719.8
5°	1712.5	1710.3	1709.6	1712.5	1719.0	1720.9	1708.5	1696.2	1708.5	1720.9	1719.0
7.5°	1711.8	1708.4	1705.9	1707.1	1712.1	1712.7	1700.2	1687.7	1700.2	1712.7	1712.1
10°	1709.1	1704.9	1701.3	1701.6	1706.0	1706.0	1692.9	1679.9	1692.9	1706.0	1706.0
12.5°	1703.8	1699.2	1695.0	1694.5	1697.7	1696.7	1683.1	1669.4	1683.1	1696.7	1697.7
15°	1690.6	1685.8	1680.8	1678.6	1679.3	1676.2	1661.7	1647.2	1661.7	1676.2	1679.3
17.5°	1655.2	1653.7	1652.4	1652.3	1653.3	1650.4	1635.9	1621.4	1635.9	1650.4	1653.3
20°	1619.5	1623.3	1628.3	1632.0	1634.2	1632.2	1617.6	1603.1	1617.6	1632.2	1634.2
22.5°	1568.7	1580.2	1594.0	1603.4	1608.5	1608.4	1592.7	1577.0	1592.7	1608.4	1608.5
25°	1473.1	1497.0	1525.3	1546.7	1561.2	1568.3	1553.1	1537.8	1553.1	1568.3	1561.2
27.5°	1361.0	1394.9	1435.1	1469.6	1498.3	1516.8	1504.5	1492.1	1504.5	1516.8	1498.3
30°	1282.8	1319.6	1363.9	1407.1	1449.1	1478.3	1468.9	1459.5	1468.9	1478.3	1449.1
32.5°	1208.1	1246.5	1292.5	1341.8	1394.3	1432.8	1429.1	1425.5	1429.1	1432.8	1394.3
35°	1098.5	1136.8	1183.2	1239.4	1305.5	1356.6	1363.2	1369.7	1363.2	1356.6	1305.5
37.5°	988.4	1028.7	1077.3	1136.8	1207.2	1264.8	1284.3	1303.7	1284.3	1264.8	1207.2
40°	915.3	955.6	1004.2	1065.1	1138.4	1200.3	1227.8	1255.4	1227.8	1200.3	1138.4
42.5°	845.9	886.3	935.0	995.9	1069.2	1132.8	1167.3	1201.9	1167.3	1132.8	1069.2
45°	743.9	783.1	830.2	891.2	965.9	1032.1	1072.7	1113.4	1072.7	1032.1	965.9
47.5°	649.1	686.6	732.3	792.5	867.1	933.1	973.5	1013.8	973.5	933.1	867.1
50°	587.0	625.3	671.0	729.4	800.5	863.6	902.8	942.0	902.8	863.6	800.5
52.5°	522.8	563.4	610.3	668.4	737.8	798.6	833.7	868.8	833.7	798.6	737.8
55°	426.3	468.5	520.8	579.5	644.8	702.2	735.5	768.9	735.5	702.2	644.8
57.5°	358.9	397.0	444.5	497.7	556.8	608.3	637.2	666.1	637.2	608.3	556.8
60°	322.3	354.8	394.7	443.3	500.6	550.0	575.4	600.8	575.4	550.0	500.6
62.5°	288.8	314.7	346.5	390.2	445.8	493.1	515.6	538.1	515.6	493.1	445.8
65°	241.4	262.8	289.0	325.2	371.7	410.7	427.4	444.0	427.4	410.7	371.7
67.5°	198.3	216.7	239.6	269.0	304.8	334.0	343.3	352.6	343.3	334.0	304.8
70°	173.8	188.8	207.7	232.7	263.9	288.0	291.0	293.9	291.0	288.0	263.9
72.5°	150.6	162.3	177.1	198.0	225.2	245.2	244.1	242.9	244.1	245.2	225.2
75°	118.8	126.8	137.0	151.8	171.4	184.7	178.9	173.0	178.9	184.7	171.4
77.5°	87.9	93.8	101.4	112.3	126.7	135.3	126.6	117.9	126.6	135.3	126.7
80°	68.6	72.9	78.7	87.1	98.0	103.9	95.2	86.5	95.2	103.9	98.0
82.5°	51.6	53.8	56.7	62.1	70.1	74.3	67.4	60.4	67.4	74.3	70.1
85°	21.0	24.5	28.8	32.5	35.4	36.6	33.0	29.4	33.0	36.6	35.4
87.5°	10.3	10.4	11.0	12.4	14.4	15.0	11.7	8.7	11.7	14.6	15.0
90°	31.8	30.3	30.3	28.8	24.2	18.2	10.6	4.5	10.6	16.7	27.2
92.5°	37.8	37.5	35.1	32.4	26.6	26.6	26.3	16.7	28.8	40.9	58.7
95°	34.8	34.8	40.9	51.5	75.7	77.2	51.5	46.9	66.6	93.8	118.1
97.5°	94.1	112.0	137.4	142.3	134.7	100.5	96.3	89.6	122.0	148.9	188.0
100°	174.1	196.8	214.9	178.6	140.8	139.3	130.2	127.1	162.0	187.7	225.5
102.5°	272.2	279.1	216.1	195.6	186.8	180.4	166.5	164.7	199.5	234.9	266.7
105°	295.2	264.9	266.4	266.4	260.3	248.2	222.5	221.0	260.3	301.2	340.6
107.5°	347.2	351.8	359.6	357.8	350.9	318.5	288.2	281.2	316.7	365.7	409.0
110°	416.3	420.8	423.8	420.8	410.2	369.3	333.0	322.4	354.2	405.7	452.6



TEST NUMBER: P1428426

CATALOG NUMBER: SQ2W-PW1-K-100U-075D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	482.9	486.2	492.8	483.8	465.9	419.0	377.8	362.4	394.2	446.8	495.0
115°	588.8	588.8	590.3	585.8	549.5	501.0	446.5	423.8	451.1	499.5	552.5
117.5°	692.9	694.8	688.7	676.6	634.5	578.2	517.1	480.7	502.2	553.4	607.9
120°	758.3	761.4	755.3	737.1	696.3	632.7	563.1	520.7	537.3	587.3	641.8
122.5°	826.2	825.5	818.3	797.7	749.6	683.6	615.1	563.1	570.0	616.4	669.6
125°	920.3	918.8	912.7	888.5	838.6	770.4	690.2	626.7	617.6	656.9	711.4
127.5°	1009.9	1006.6	997.2	967.8	916.7	851.0	762.9	690.8	670.5	695.4	745.3
130°	1071.7	1067.1	1050.5	1018.7	968.7	906.7	817.4	735.6	706.9	722.0	765.9
132.5°	1131.0	1118.0	1103.8	1069.5	1023.2	958.7	868.2	782.9	743.2	749.9	784.1
135°	1206.4	1194.3	1176.1	1142.8	1098.9	1035.3	944.5	852.2	797.7	791.6	811.3
137.5°	1272.7	1260.0	1239.4	1210.6	1166.4	1109.8	1022.6	925.1	856.4	836.1	843.7
140°	1313.8	1298.7	1280.5	1251.8	1212.4	1153.4	1068.6	974.8	897.6	868.8	864.3
142.5°	1347.8	1336.3	1316.9	1290.5	1256.0	1197.0	1114.7	1022.0	940.0	902.7	892.1
145°	1398.6	1389.5	1368.3	1344.1	1315.4	1256.3	1180.6	1088.3	1006.6	958.1	935.4
147.5°	1441.6	1434.3	1417.7	1389.2	1365.0	1308.4	1239.4	1157.6	1073.8	1013.8	984.5
150°	1468.2	1462.2	1445.5	1418.3	1394.1	1341.1	1274.5	1198.8	1118.6	1055.0	1017.2
152.5°	1493.7	1487.6	1468.5	1441.3	1420.7	1371.4	1310.8	1238.8	1157.3	1093.8	1054.7
155°	1527.3	1519.7	1501.5	1475.8	1457.6	1412.2	1356.2	1292.7	1223.0	1156.4	1112.5
157.5°	1553.9	1544.5	1527.6	1505.5	1486.1	1444.3	1395.6	1340.8	1279.9	1216.4	1171.6
160°	1569.7	1559.1	1540.9	1521.2	1503.1	1463.7	1419.8	1369.9	1313.8	1256.3	1207.9
162.5°	1580.6	1571.2	1549.4	1532.1	1516.4	1480.7	1439.2	1394.1	1344.1	1293.9	1249.1
165°	1592.4	1581.8	1559.1	1545.4	1531.8	1501.5	1465.2	1428.9	1386.5	1345.6	1309.3
167.5°	1593.3	1584.5	1561.8	1548.5	1538.5	1512.4	1483.1	1455.2	1422.2	1390.1	1359.9
170°	1590.8	1583.3	1560.6	1548.5	1540.9	1519.7	1494.0	1469.8	1444.0	1416.8	1392.6
172.5°	1582.4	1574.8	1553.3	1543.6	1539.7	1520.9	1500.0	1481.9	1459.8	1439.8	1420.4
175°	1560.6	1554.5	1536.4	1530.3	1531.8	1519.7	1504.6	1494.0	1480.4	1468.2	1457.6
177.5°	1528.8	1525.2	1511.8	1511.8	1516.7	1509.4	1504.6	1499.7	1493.7	1490.0	1486.4
180°	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5



TEST NUMBER: P1428426

CATALOG NUMBER: SQ2W-PW1-K-100U-075D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1	1714.1
2.5°	1713.4	1710.5	1711.1	1712.0	1713.7	1715.5	1713.7	1712.0	1711.1	1710.5	1713.4
5°	1712.5	1709.6	1710.3	1712.5	1719.0	1725.6	1719.0	1712.5	1710.3	1709.6	1712.5
7.5°	1707.1	1705.9	1708.4	1711.8	1718.2	1724.6	1718.2	1711.8	1708.4	1705.9	1707.1
10°	1701.6	1701.3	1704.9	1709.1	1714.9	1720.7	1714.9	1709.1	1704.9	1701.3	1701.6
12.5°	1694.5	1695.0	1699.2	1703.8	1709.6	1715.5	1709.6	1703.8	1699.2	1695.0	1694.5
15°	1678.6	1680.8	1685.8	1690.6	1694.2	1697.8	1694.2	1690.6	1685.8	1680.8	1678.6
17.5°	1652.3	1652.4	1653.7	1655.2	1656.9	1658.6	1656.9	1655.2	1653.7	1652.4	1652.3
20°	1632.0	1628.3	1623.3	1619.5	1619.5	1619.5	1619.5	1619.5	1623.3	1628.3	1632.0
22.5°	1603.4	1594.0	1580.2	1568.7	1564.0	1559.4	1564.0	1568.7	1580.2	1594.0	1603.4
25°	1546.7	1525.3	1497.0	1473.1	1462.2	1451.3	1462.2	1473.1	1497.0	1525.3	1546.7
27.5°	1469.6	1435.1	1394.9	1361.0	1345.9	1330.8	1345.9	1361.0	1394.9	1435.1	1469.6
30°	1407.1	1363.9	1319.6	1282.8	1268.3	1253.8	1268.3	1282.8	1319.6	1363.9	1407.1
32.5°	1341.8	1292.5	1246.5	1208.1	1192.4	1176.7	1192.4	1208.1	1246.5	1292.5	1341.8
35°	1239.4	1183.2	1136.8	1098.5	1084.7	1070.9	1084.7	1098.5	1136.8	1183.2	1239.4
37.5°	1136.8	1077.3	1028.7	988.4	973.2	958.0	973.2	988.4	1028.7	1077.3	1136.8
40°	1065.1	1004.2	955.6	915.3	900.1	884.8	900.1	915.3	955.6	1004.2	1065.1
42.5°	995.9	935.0	886.3	845.9	830.1	814.3	830.1	845.9	886.3	935.0	995.9
45°	891.2	830.2	783.1	743.9	728.6	713.4	728.6	743.9	783.1	830.2	891.2
47.5°	792.5	732.3	686.6	649.1	636.0	623.0	636.0	649.1	686.6	732.3	792.5
50°	729.4	671.0	625.3	587.0	571.0	555.1	571.0	587.0	625.3	671.0	729.4
52.5°	668.4	610.3	563.4	522.8	501.1	479.3	501.1	522.8	563.4	610.3	668.4
55°	579.5	520.8	468.5	426.3	413.9	401.6	413.9	426.3	468.5	520.8	579.5
57.5°	497.7	444.5	397.0	358.9	348.7	338.6	348.7	358.9	397.0	444.5	497.7
60°	443.3	394.7	354.8	322.3	312.2	302.0	312.2	322.3	354.8	394.7	443.3
62.5°	390.2	346.5	314.7	288.8	280.4	272.0	280.4	288.8	314.7	346.5	390.2
65°	325.2	289.0	262.8	241.4	234.2	226.9	234.2	241.4	262.8	289.0	325.2
67.5°	269.0	239.6	216.7	198.3	193.5	188.7	193.5	198.3	216.7	239.6	269.0
70°	232.7	207.7	188.8	173.8	170.1	166.5	170.1	173.8	188.8	207.7	232.7
72.5°	198.0	177.1	162.3	150.6	148.1	145.6	148.1	150.6	162.3	177.1	198.0
75°	151.8	137.0	126.8	118.8	117.4	115.9	117.4	118.8	126.8	137.0	151.8
77.5°	112.3	101.4	93.8	87.9	86.7	85.5	86.7	87.9	93.8	101.4	112.3
80°	87.1	78.7	72.9	68.6	68.6	68.6	68.6	68.6	72.9	78.7	87.1
82.5°	62.1	56.7	53.8	51.6	51.6	51.6	51.6	51.6	53.8	56.7	62.1
85°	32.5	28.8	24.5	21.0	20.3	19.6	20.3	21.0	24.5	28.8	32.5
87.5°	13.6	14.0	15.6	16.3	17.5	16.9	17.5	16.3	15.6	14.0	13.6
90°	34.8	45.4	56.0	62.1	68.1	65.1	68.1	62.1	56.0	45.4	34.8
92.5°	69.9	87.8	100.8	111.7	116.6	115.9	116.6	111.7	100.8	87.8	69.9
95°	140.8	162.0	183.2	198.3	207.4	204.3	207.4	198.3	183.2	162.0	140.8
97.5°	217.1	245.5	269.1	283.4	292.4	298.5	292.4	283.4	269.1	245.5	217.1
100°	267.9	295.2	322.4	339.1	354.2	360.2	354.2	339.1	322.4	295.2	267.9
102.5°	309.1	344.8	374.5	392.3	405.1	411.1	405.1	392.3	374.5	344.8	309.1
105°	376.9	414.7	446.5	469.2	482.9	487.4	482.9	469.2	446.5	414.7	376.9
107.5°	444.7	483.8	513.1	538.3	554.9	564.6	554.9	538.3	513.1	483.8	444.7
110°	498.0	529.8	561.6	584.3	600.9	607.0	600.9	584.3	561.6	529.8	498.0



TEST NUMBER: P1428426

CATALOG NUMBER: SQ2W-PW1-K-100U-075D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	542.8	578.2	610.0	632.7	651.8	660.3	651.8	632.7	610.0	578.2	542.8
115°	605.5	652.4	681.1	702.3	716.0	723.5	716.0	702.3	681.1	652.4	605.5
117.5°	657.5	706.6	738.1	754.4	760.8	766.2	760.8	754.4	738.1	706.6	657.5
120°	690.2	735.6	772.0	793.2	800.7	803.7	800.7	793.2	772.0	735.6	690.2
122.5°	720.5	763.5	798.6	824.6	837.0	840.1	837.0	824.6	798.6	763.5	720.5
125°	762.9	803.7	840.1	865.8	879.4	887.0	879.4	865.8	840.1	803.7	762.9
127.5°	799.8	844.0	877.3	900.6	913.9	920.0	913.9	900.6	877.3	844.0	799.8
130°	820.4	865.8	899.1	924.8	937.0	943.0	937.0	924.8	899.1	865.8	820.4
132.5°	836.1	884.0	918.5	941.8	955.1	961.2	955.1	941.8	918.5	884.0	836.1
135°	855.2	905.2	941.5	964.2	976.3	982.4	976.3	964.2	941.5	905.2	855.2
137.5°	871.9	917.3	955.1	979.0	989.9	993.9	989.9	979.0	955.1	917.3	871.9
140°	884.0	923.3	961.2	983.9	996.0	997.5	996.0	983.9	961.2	923.3	884.0
142.5°	899.7	930.6	963.6	986.3	998.4	1001.1	998.4	986.3	963.6	930.6	899.7
145°	927.9	946.0	968.7	989.9	1000.5	1003.6	1000.5	989.9	968.7	946.0	927.9
147.5°	963.3	969.0	980.8	994.8	1005.1	1007.2	1005.1	994.8	980.8	969.0	963.3
150°	989.9	988.4	993.0	1002.0	1011.1	1009.6	1011.1	1002.0	993.0	988.4	989.9
152.5°	1020.2	1011.4	1011.1	1015.4	1019.6	1019.3	1019.6	1015.4	1011.1	1011.4	1020.2
155°	1071.7	1055.0	1045.9	1042.9	1042.9	1041.4	1042.9	1042.9	1045.9	1055.0	1071.7
157.5°	1128.3	1105.0	1091.3	1084.1	1082.0	1078.6	1082.0	1084.1	1091.3	1105.0	1128.3
160°	1167.0	1141.3	1127.7	1115.6	1111.0	1106.5	1111.0	1115.6	1127.7	1141.3	1167.0
162.5°	1203.4	1178.8	1164.0	1153.1	1148.6	1141.6	1148.6	1153.1	1164.0	1178.8	1203.4
165°	1262.4	1236.7	1220.0	1210.9	1204.9	1198.8	1204.9	1210.9	1220.0	1236.7	1262.4
167.5°	1321.4	1293.3	1282.4	1272.1	1266.3	1255.4	1266.3	1272.1	1282.4	1293.3	1321.4
170°	1357.7	1332.0	1326.0	1316.9	1306.3	1294.2	1306.3	1316.9	1326.0	1332.0	1357.7
172.5°	1389.2	1372.0	1365.9	1356.8	1353.5	1343.8	1353.5	1356.8	1365.9	1372.0	1389.2
175°	1434.9	1421.3	1421.3	1419.8	1415.3	1406.2	1415.3	1419.8	1421.3	1421.3	1434.9
177.5°	1473.1	1465.8	1470.7	1470.7	1469.5	1461.0	1469.5	1470.7	1470.7	1465.8	1473.1
180°	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5	1498.5



TEST NUMBER: P1428426

CATALOG NUMBER: SQ2W-PW1-K-100U-075D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1714.1	1714.1	1714.1	1714.1
2.5°	1719.8	1722.1	1712.3	1702.4
5°	1719.0	1720.9	1708.5	1696.2
7.5°	1712.1	1712.7	1700.2	1687.7
10°	1706.0	1706.0	1692.9	1679.9
12.5°	1697.7	1696.7	1683.1	1669.4
15°	1679.3	1676.2	1661.7	1647.2
17.5°	1653.3	1650.4	1635.9	1621.4
20°	1634.2	1632.2	1617.6	1603.1
22.5°	1608.5	1608.4	1592.7	1577.0
25°	1561.2	1568.3	1553.1	1537.8
27.5°	1498.3	1516.8	1504.5	1492.1
30°	1449.1	1478.3	1468.9	1459.5
32.5°	1394.3	1432.8	1429.1	1425.5
35°	1305.5	1356.6	1363.2	1369.7
37.5°	1207.2	1264.8	1284.3	1303.7
40°	1138.4	1200.3	1227.8	1255.4
42.5°	1069.2	1132.8	1167.3	1201.9
45°	965.9	1032.1	1072.7	1113.4
47.5°	867.1	933.1	973.5	1013.8
50°	800.5	863.6	902.8	942.0
52.5°	737.8	798.6	833.7	868.8
55°	644.8	702.2	735.5	768.9
57.5°	556.8	608.3	637.2	666.1
60°	500.6	550.0	575.4	600.8
62.5°	445.8	493.1	515.6	538.1
65°	371.7	410.7	427.4	444.0
67.5°	304.8	334.0	343.3	352.6
70°	263.9	288.0	291.0	293.9
72.5°	225.2	245.2	244.1	242.9
75°	171.4	184.7	178.9	173.0
77.5°	126.7	135.3	126.6	117.9
80°	98.0	103.9	95.2	86.5
82.5°	70.1	74.3	67.4	60.4
85°	35.4	36.6	33.0	29.4
87.5°	15.0	14.6	11.7	8.7
90°	27.2	16.7	10.6	4.5
92.5°	58.7	40.9	28.8	16.7
95°	118.1	93.8	66.6	46.9
97.5°	188.0	148.9	122.0	89.6
100°	225.5	187.7	162.0	127.1
102.5°	266.7	234.9	199.5	164.7
105°	340.6	301.2	260.3	221.0
107.5°	409.0	365.7	316.7	281.2
110°	452.6	405.7	354.2	322.4



TEST NUMBER: P1428426

CATALOG NUMBER: SQ2W-PW1-K-100U-075D-L835-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	495.0	446.8	394.2	362.4
115°	552.5	499.5	451.1	423.8
117.5°	607.9	553.4	502.2	480.7
120°	641.8	587.3	537.3	520.7
122.5°	669.6	616.4	570.0	563.1
125°	711.4	656.9	617.6	626.7
127.5°	745.3	695.4	670.5	690.8
130°	765.9	722.0	706.9	735.6
132.5°	784.1	749.9	743.2	782.9
135°	811.3	791.6	797.7	852.2
137.5°	843.7	836.1	856.4	925.1
140°	864.3	868.8	897.6	974.8
142.5°	892.1	902.7	940.0	1022.0
145°	935.4	958.1	1006.6	1088.3
147.5°	984.5	1013.8	1073.8	1157.6
150°	1017.2	1055.0	1118.6	1198.8
152.5°	1054.7	1093.8	1157.3	1238.8
155°	1112.5	1156.4	1223.0	1292.7
157.5°	1171.6	1216.4	1279.9	1340.8
160°	1207.9	1256.3	1313.8	1369.9
162.5°	1249.1	1293.9	1344.1	1394.1
165°	1309.3	1345.6	1386.5	1428.9
167.5°	1359.9	1390.1	1422.2	1455.2
170°	1392.6	1416.8	1444.0	1469.8
172.5°	1420.4	1439.8	1459.8	1481.9
175°	1457.6	1468.2	1480.4	1494.0
177.5°	1486.4	1490.0	1493.7	1499.7
180°	1498.5	1498.5	1498.5	1498.5



TEST NUMBER: P1428426
 CATALOG NUMBER: SQ2W-PW1-K-100U-075D-L835-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.12	18.91	19.11	19.92	21.24	14.36	15.16	15.36	16.16	17.49
	3H	19.41	20.13	20.42	21.14	22.48	15.63	16.34	16.64	17.35	18.70
	4H	19.82	20.49	20.84	21.51	22.86	16.13	16.81	17.15	17.82	19.17
	6H	20.00	20.62	21.02	21.63	23.00	16.44	17.06	17.47	18.08	19.44
	8H	20.04	20.63	21.07	21.66	23.02	16.55	17.14	17.58	18.17	19.53
	12H	20.04	20.60	21.07	21.62	23.01	16.58	17.14	17.62	18.17	19.55
4H	2H	18.24	18.91	19.27	19.93	21.28	15.17	15.84	16.19	16.85	18.21
	3H	19.77	20.33	20.81	21.38	22.74	16.61	17.17	17.64	18.21	19.57
	4H	20.32	20.83	21.36	21.86	23.25	17.18	17.70	18.22	18.73	20.12
	6H	20.63	21.06	21.68	22.12	23.51	17.57	18.00	18.61	19.06	20.44
	8H	20.72	21.13	21.77	22.17	23.57	17.71	18.12	18.76	19.17	20.57
	12H	20.74	21.10	21.80	22.17	23.57	17.75	18.12	18.82	19.19	20.59
8H	4H	20.35	20.76	21.40	21.81	23.21	17.52	17.93	18.57	18.98	20.38
	6H	20.77	21.11	21.84	22.20	23.60	18.01	18.35	19.09	19.44	20.84
	8H	20.94	21.24	22.02	22.31	23.73	18.23	18.53	19.31	19.60	21.02
	12H	21.02	21.28	22.10	22.35	23.81	18.31	18.57	19.40	19.64	21.10
12H	4H	20.31	20.68	21.38	21.74	23.15	17.54	17.91	18.61	18.97	20.38
	6H	20.77	21.06	21.85	22.14	23.55	18.09	18.39	19.17	19.46	20.88
	8H	20.95	21.21	22.04	22.28	23.74	18.33	18.59	19.41	19.66	21.12