

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428423

Luminaire Tested: SQ2W-PW1-K-100U-050D-L935-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428423
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PW1-K-100U-050D-L935-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE WAVES LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6201.7 lumens
Efficiency: N/A
Efficacy: 121.8 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.11 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 50.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428423

CATALOG NUMBER: SQ2W-PW1-K-100U-050D-L935-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428423

CATALOG NUMBER: SQ2W-PW1-K-100U-050D-L935-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	76	76	76	60	60	60	45	45	45	38
1	95	91	88	84	86	83	80	77	68	65	64	53	52	51	40	39	39	33
2	87	80	74	70	79	73	68	64	60	56	53	47	45	43	36	34	33	28
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29	24
4	73	63	55	50	66	58	51	46	47	43	39	38	35	32	29	27	25	21
5	67	56	48	43	61	51	45	40	42	37	34	34	31	28	26	24	22	19
6	62	50	43	37	56	46	39	35	38	33	29	31	27	24	24	22	20	16
7	57	46	38	33	52	42	35	30	35	30	26	28	24	22	22	19	18	15
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16	13
9	50	38	31	26	45	35	28	24	29	24	21	24	20	18	19	16	14	12
10	46	35	28	23	42	32	26	22	27	22	19	22	18	16	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16953	16953	16953	16953
5°	16839	17131	16839	17131
10°	16870	17280	16870	17280
15°	16866	17384	16866	17384
20°	16872	17044	16872	17044
25°	16781	15837	16781	15837
30°	16667	14318	16667	14318
35°	16537	12930	16537	12930
40°	16208	11423	16208	11423
45°	15572	9978	15572	9978
50°	14493	8540	14493	8540
55°	13258	6925	13258	6925
60°	11883	5974	11883	5974
65°	10391	5310	10391	5310
70°	8497	4815	8497	4815
75°	6612	4429	6612	4429
80°	4928	3905	4928	3905
85°	3334	2223	3334	2223

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15572 cd/sqm



TEST NUMBER: P1428423

CATALOG NUMBER: SQ2W-PW1-K-100U-050D-L935-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.0	1.6
10°-20°	289.7	4.7
20°-30°	426.3	6.9
30°-40°	466.1	7.5
40°-50°	418.2	6.7
50°-60°	311.9	5.0
60°-70°	197.1	3.2
70°-80°	97.7	1.6
80°-90°	28.3	0.5
90°-100°	105.4	1.7
100°-110°	307.3	5.0
110°-120°	501.5	8.1
120°-130°	636.4	10.3
130°-140°	681.0	11.0
140°-150°	635.9	10.3
150°-160°	523.2	8.4
160°-170°	350.9	5.7
170°-180°	124.6	2.0
0°-30°	816.0	13.2
0°-40°	1282.2	20.7
0°-60°	2012.2	32.4
0°-90°	2335.4	37.7
90°-120°	914.2	14.7
90°-150°	2867.5	46.2
90°-180°	3866.0	62.3
0°-180°	6201.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1050	1050	1050	1050	1050	
5°	1039	1057	1039	1057	1039	99
15°	1009	1040	1009	1040	1009	285
25°	942	889	942	889	942	434
35°	839	656	839	656	839	523
45°	682	437	682	437	682	523
55°	471	246	471	246	471	421
65°	272	139	272	139	272	270
75°	106	71	106	71	106	117
85°	18	12	18	12	18	23
90°	4	29	4	58	4	4
95°	42	31	42	181	42	50
105°	195	313	195	431	195	208
115°	374	519	374	639	374	369
125°	554	823	554	784	554	495
135°	753	1077	753	868	753	582
145°	962	1241	962	887	962	602
155°	1142	1348	1142	920	1142	525
165°	1263	1406	1263	1059	1263	355
175°	1320	1376	1320	1243	1320	125
180°	1324	1324	1324	1324	1324	



TEST NUMBER: P1428423

CATALOG NUMBER: SQ2W-PW1-K-100U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1050.0	1050.0	1050.0	1050.0	1050.0	1050.0	1050.0	1050.0	1050.0	1050.0	1050.0
2.5°	1042.8	1048.9	1054.9	1053.5	1049.6	1047.8	1048.1	1048.7	1049.7	1050.8	1049.7
5°	1039.0	1046.6	1054.1	1053.0	1049.0	1047.2	1047.7	1049.0	1053.0	1057.0	1053.0
7.5°	1033.8	1041.5	1049.1	1048.7	1045.7	1045.0	1046.5	1048.6	1052.5	1056.4	1052.5
10°	1029.0	1037.0	1045.0	1045.0	1042.3	1042.1	1044.3	1046.9	1050.5	1054.0	1050.5
12.5°	1022.6	1031.0	1039.3	1039.9	1038.0	1038.3	1040.9	1043.7	1047.3	1050.8	1047.3
15°	1009.0	1017.9	1026.8	1028.7	1028.2	1029.6	1032.7	1035.6	1037.8	1040.0	1037.8
17.5°	993.2	1002.1	1011.0	1012.7	1012.1	1012.2	1013.0	1013.9	1014.9	1016.0	1014.9
20°	982.0	990.9	999.8	1001.0	999.7	997.5	994.3	992.0	992.0	992.0	992.0
22.5°	966.0	975.6	985.2	985.3	982.2	976.4	967.9	960.9	958.1	955.2	958.1
25°	942.0	951.3	960.7	956.3	947.5	934.3	917.0	902.3	895.7	889.0	895.7
27.5°	914.0	921.6	929.1	917.8	900.2	879.1	854.5	833.7	824.5	815.2	824.5
30°	894.0	899.8	905.6	887.7	861.9	835.5	808.3	785.8	776.9	768.0	776.9
32.5°	873.2	875.4	877.7	854.1	821.9	791.7	763.5	740.0	730.4	720.8	730.4
35°	839.0	835.0	831.0	799.7	759.2	724.8	696.3	672.9	664.5	656.0	664.5
37.5°	798.6	786.7	774.8	739.5	696.4	659.9	630.1	605.5	596.1	586.8	596.1
40°	769.0	752.1	735.2	697.3	652.5	615.1	585.3	560.7	551.3	542.0	551.3
42.5°	736.2	715.1	693.9	654.9	610.1	572.7	542.9	518.2	508.5	498.8	508.5
45°	682.0	657.1	632.2	591.7	545.9	508.6	479.7	455.7	446.3	437.0	446.3
47.5°	621.0	596.3	571.6	531.1	485.4	448.6	420.6	397.6	389.6	381.6	389.6
50°	577.0	553.0	529.0	490.3	446.8	411.0	383.0	359.6	349.8	340.0	349.8
52.5°	532.2	510.7	489.2	451.9	409.4	373.8	345.1	320.3	306.9	293.6	306.9
55°	471.0	450.6	430.1	395.0	355.0	319.0	287.0	261.1	253.6	246.0	253.6
57.5°	408.0	390.3	372.6	341.1	304.9	272.3	243.2	219.8	213.6	207.4	213.6
60°	368.0	352.4	336.9	306.7	271.6	241.8	217.3	197.4	191.2	185.0	191.2
62.5°	329.6	315.8	302.0	273.1	239.0	212.3	192.8	176.9	171.8	166.6	171.8
65°	272.0	261.8	251.6	227.7	199.2	177.0	161.0	147.9	143.4	139.0	143.4
67.5°	216.0	210.3	204.6	186.7	164.8	146.8	132.7	121.5	118.5	115.6	118.5
70°	180.0	178.2	176.4	161.7	142.6	127.2	115.7	106.4	104.2	102.0	104.2
72.5°	148.8	149.5	150.2	137.9	121.3	108.5	99.4	92.2	90.7	89.2	90.7
75°	106.0	109.6	113.1	105.0	93.0	83.9	77.7	72.8	71.9	71.0	71.9
77.5°	72.2	77.5	82.9	77.6	68.8	62.1	57.5	53.8	53.1	52.4	53.1
80°	53.0	58.3	63.7	60.0	53.3	48.2	44.7	42.0	42.0	42.0	42.0
82.5°	37.0	41.3	45.5	42.9	38.0	34.7	32.9	31.6	31.6	31.6	31.6
85°	18.0	20.2	22.4	21.7	19.9	17.7	15.0	12.9	12.4	12.0	12.4
87.5°	5.6	7.7	10.1	10.1	9.2	8.4	8.0	8.0	8.3	8.3	8.3
90°	4.0	9.4	16.1	21.4	25.4	26.8	26.8	28.1	29.4	29.4	29.4
92.5°	14.7	23.3	23.5	23.5	28.6	31.0	33.2	33.4	34.8	34.8	34.8
95°	41.5	45.5	68.2	66.9	45.5	36.1	30.8	30.8	30.8	30.8	30.8
97.5°	79.2	85.1	88.8	119.0	125.7	121.4	99.0	83.2	74.4	70.4	74.4
100°	112.4	115.0	123.1	124.4	157.8	189.9	173.9	153.8	147.1	143.1	147.1
102.5°	145.5	147.1	159.4	165.1	172.8	191.0	246.6	240.5	235.9	235.1	235.9
105°	195.3	196.6	219.4	230.1	235.4	235.4	234.1	260.8	303.6	313.0	303.6
107.5°	248.5	254.7	281.4	310.0	316.2	317.8	310.8	306.8	305.2	306.3	305.2
110°	284.9	294.3	326.4	362.5	371.8	374.5	371.8	367.8	365.1	365.1	365.1



TEST NUMBER: P1428423

CATALOG NUMBER: SQ2W-PW1-K-100U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	320.2	333.9	370.2	411.7	427.5	435.5	429.6	426.7	424.0	426.1	424.0
115°	374.5	394.6	442.7	485.5	517.6	521.6	520.3	520.3	519.0	519.0	519.0
117.5°	424.8	456.9	510.9	560.7	597.9	608.6	613.9	612.3	610.7	613.4	610.7
120°	460.1	497.6	559.1	615.3	651.4	667.4	672.8	670.1	672.8	670.1	672.8
122.5°	497.6	543.6	604.0	662.4	704.9	723.1	729.5	730.0	730.6	729.0	730.6
125°	553.7	609.9	680.8	741.0	785.1	806.5	811.9	813.2	815.9	822.6	815.9
127.5°	610.5	674.1	752.0	810.0	855.2	881.2	889.5	892.4	898.0	901.0	898.0
130°	650.0	722.3	801.2	856.0	900.2	928.3	943.0	947.0	953.7	952.3	953.7
132.5°	691.8	767.2	847.2	904.2	945.1	975.3	987.9	999.4	1001.8	1003.7	1001.8
135°	753.0	834.6	914.9	971.1	1009.8	1039.3	1055.3	1066.0	1072.7	1076.7	1072.7
137.5°	817.5	903.6	980.7	1030.7	1069.8	1095.2	1113.4	1124.6	1131.6	1134.8	1131.6
140°	861.4	944.3	1019.2	1071.4	1106.1	1131.6	1147.6	1161.0	1169.0	1169.0	1169.0
142.5°	903.1	985.0	1057.7	1109.9	1140.4	1163.7	1180.8	1190.9	1200.0	1200.0	1200.0
145°	961.7	1043.3	1110.2	1162.3	1187.7	1209.1	1227.9	1235.9	1241.2	1241.2	1241.2
147.5°	1023.0	1095.2	1156.2	1206.2	1227.6	1252.7	1267.5	1273.9	1280.6	1277.6	1280.6
150°	1059.3	1126.2	1185.1	1231.9	1253.3	1277.4	1292.1	1297.4	1304.1	1300.1	1304.1
152.5°	1094.6	1158.3	1211.8	1255.4	1273.6	1297.7	1314.5	1319.9	1324.4	1321.5	1324.4
155°	1142.3	1198.4	1247.9	1288.1	1304.1	1326.8	1342.9	1349.6	1354.9	1348.2	1354.9
157.5°	1184.8	1233.2	1276.3	1313.2	1330.3	1349.9	1364.8	1373.1	1378.5	1375.5	1378.5
160°	1210.5	1254.6	1293.4	1328.2	1344.2	1361.6	1377.7	1387.0	1392.4	1388.4	1392.4
162.5°	1231.9	1271.7	1308.4	1340.0	1353.9	1369.1	1388.4	1396.7	1402.0	1396.9	1402.0
165°	1262.6	1294.7	1326.8	1353.6	1365.6	1377.7	1397.7	1407.1	1411.1	1405.8	1411.1
167.5°	1285.9	1310.5	1336.5	1359.5	1368.3	1380.1	1400.1	1407.9	1413.0	1406.3	1413.0
170°	1298.8	1320.2	1342.9	1361.6	1368.3	1379.0	1399.1	1405.8	1409.8	1403.1	1409.8
172.5°	1309.5	1325.5	1344.0	1360.6	1364.0	1372.6	1391.6	1398.3	1401.2	1395.6	1401.2
175°	1320.2	1329.5	1342.9	1353.6	1352.3	1357.6	1373.7	1379.0	1384.4	1376.3	1384.4
177.5°	1325.2	1329.5	1333.8	1340.2	1335.9	1335.9	1347.7	1350.9	1352.0	1347.7	1352.0
180°	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2



TEST NUMBER: P1428423

CATALOG NUMBER: SQ2W-PW1-K-100U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1050.0	1050.0	1050.0	1050.0	1050.0	1050.0	1050.0	1050.0	1050.0	1050.0	1050.0
2.5°	1048.7	1048.1	1047.8	1049.6	1053.5	1054.9	1048.9	1042.8	1048.9	1054.9	1053.5
5°	1049.0	1047.7	1047.2	1049.0	1053.0	1054.1	1046.6	1039.0	1046.6	1054.1	1053.0
7.5°	1048.6	1046.5	1045.0	1045.7	1048.7	1049.1	1041.5	1033.8	1041.5	1049.1	1048.7
10°	1046.9	1044.3	1042.1	1042.3	1045.0	1045.0	1037.0	1029.0	1037.0	1045.0	1045.0
12.5°	1043.7	1040.9	1038.3	1038.0	1039.9	1039.3	1031.0	1022.6	1031.0	1039.3	1039.9
15°	1035.6	1032.7	1029.6	1028.2	1028.7	1026.8	1017.9	1009.0	1017.9	1026.8	1028.7
17.5°	1013.9	1013.0	1012.2	1012.1	1012.7	1011.0	1002.1	993.2	1002.1	1011.0	1012.7
20°	992.0	994.3	997.5	999.7	1001.0	999.8	990.9	982.0	990.9	999.8	1001.0
22.5°	960.9	967.9	976.4	982.2	985.3	985.2	975.6	966.0	975.6	985.2	985.3
25°	902.3	917.0	934.3	947.5	956.3	960.7	951.3	942.0	951.3	960.7	956.3
27.5°	833.7	854.5	879.1	900.2	917.8	929.1	921.6	914.0	921.6	929.1	917.8
30°	785.8	808.3	835.5	861.9	887.7	905.6	899.8	894.0	899.8	905.6	887.7
32.5°	740.0	763.5	791.7	821.9	854.1	877.7	875.4	873.2	875.4	877.7	854.1
35°	672.9	696.3	724.8	759.2	799.7	831.0	835.0	839.0	835.0	831.0	799.7
37.5°	605.5	630.1	659.9	696.4	739.5	774.8	786.7	798.6	786.7	774.8	739.5
40°	560.7	585.3	615.1	652.5	697.3	735.2	752.1	769.0	752.1	735.2	697.3
42.5°	518.2	542.9	572.7	610.1	654.9	693.9	715.1	736.2	715.1	693.9	654.9
45°	455.7	479.7	508.6	545.9	591.7	632.2	657.1	682.0	657.1	632.2	591.7
47.5°	397.6	420.6	448.6	485.4	531.1	571.6	596.3	621.0	596.3	571.6	531.1
50°	359.6	383.0	411.0	446.8	490.3	529.0	553.0	577.0	553.0	529.0	490.3
52.5°	320.3	345.1	373.8	409.4	451.9	489.2	510.7	532.2	510.7	489.2	451.9
55°	261.1	287.0	319.0	355.0	395.0	430.1	450.6	471.0	450.6	430.1	395.0
57.5°	219.8	243.2	272.3	304.9	341.1	372.6	390.3	408.0	390.3	372.6	341.1
60°	197.4	217.3	241.8	271.6	306.7	336.9	352.4	368.0	352.4	336.9	306.7
62.5°	176.9	192.8	212.3	239.0	273.1	302.0	315.8	329.6	315.8	302.0	273.1
65°	147.9	161.0	177.0	199.2	227.7	251.6	261.8	272.0	261.8	251.6	227.7
67.5°	121.5	132.7	146.8	164.8	186.7	204.6	210.3	216.0	210.3	204.6	186.7
70°	106.4	115.7	127.2	142.6	161.7	176.4	178.2	180.0	178.2	176.4	161.7
72.5°	92.2	99.4	108.5	121.3	137.9	150.2	149.5	148.8	149.5	150.2	137.9
75°	72.8	77.7	83.9	93.0	105.0	113.1	109.6	106.0	109.6	113.1	105.0
77.5°	53.8	57.5	62.1	68.8	77.6	82.9	77.5	72.2	77.5	82.9	77.6
80°	42.0	44.7	48.2	53.3	60.0	63.7	58.3	53.0	58.3	63.7	60.0
82.5°	31.6	32.9	34.7	38.0	42.9	45.5	41.3	37.0	41.3	45.5	42.9
85°	12.9	15.0	17.7	19.9	21.7	22.4	20.2	18.0	20.2	22.4	21.7
87.5°	8.0	8.0	8.4	9.2	10.1	10.1	7.7	5.6	7.7	9.9	10.7
90°	28.1	26.8	26.8	25.4	21.4	16.1	9.4	4.0	9.4	14.7	24.1
92.5°	33.4	33.2	31.0	28.6	23.5	23.5	23.3	14.7	25.4	36.1	51.9
95°	30.8	30.8	36.1	45.5	66.9	68.2	45.5	41.5	58.9	82.9	104.3
97.5°	83.2	99.0	121.4	125.7	119.0	88.8	85.1	79.2	107.8	131.6	166.1
100°	153.8	173.9	189.9	157.8	124.4	123.1	115.0	112.4	143.1	165.9	199.3
102.5°	240.5	246.6	191.0	172.8	165.1	159.4	147.1	145.5	176.3	207.6	235.7
105°	260.8	234.1	235.4	235.4	230.1	219.4	196.6	195.3	230.1	266.2	300.9
107.5°	306.8	310.8	317.8	316.2	310.0	281.4	254.7	248.5	279.8	323.2	361.4
110°	367.8	371.8	374.5	371.8	362.5	326.4	294.3	284.9	313.0	358.5	399.9



TEST NUMBER: P1428423

CATALOG NUMBER: SQ2W-PW1-K-100U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	426.7	429.6	435.5	427.5	411.7	370.2	333.9	320.2	348.3	394.8	437.4
115°	520.3	520.3	521.6	517.6	485.5	442.7	394.6	374.5	398.6	441.4	488.2
117.5°	612.3	613.9	608.6	597.9	560.7	510.9	456.9	424.8	443.8	489.0	537.2
120°	670.1	672.8	667.4	651.4	615.3	559.1	497.6	460.1	474.8	519.0	567.1
122.5°	730.0	729.5	723.1	704.9	662.4	604.0	543.6	497.6	503.7	544.6	591.7
125°	813.2	811.9	806.5	785.1	741.0	680.8	609.9	553.7	545.7	580.5	628.6
127.5°	892.4	889.5	881.2	855.2	810.0	752.0	674.1	610.5	592.5	614.5	658.6
130°	947.0	943.0	928.3	900.2	856.0	801.2	722.3	650.0	624.6	638.0	676.8
132.5°	999.4	987.9	975.3	945.1	904.2	847.2	767.2	691.8	656.7	662.6	692.8
135°	1066.0	1055.3	1039.3	1009.8	971.1	914.9	834.6	753.0	704.9	699.5	716.9
137.5°	1124.6	1113.4	1095.2	1069.8	1030.7	980.7	903.6	817.5	756.8	738.9	745.5
140°	1161.0	1147.6	1131.6	1106.1	1071.4	1019.2	944.3	861.4	793.2	767.8	763.7
142.5°	1190.9	1180.8	1163.7	1140.4	1109.9	1057.7	985.0	903.1	830.6	797.7	788.3
145°	1235.9	1227.9	1209.1	1187.7	1162.3	1110.2	1043.3	961.7	889.5	846.7	826.6
147.5°	1273.9	1267.5	1252.7	1227.6	1206.2	1156.2	1095.2	1023.0	948.9	895.9	869.9
150°	1297.4	1292.1	1277.4	1253.3	1231.9	1185.1	1126.2	1059.3	988.4	932.3	898.8
152.5°	1319.9	1314.5	1297.7	1273.6	1255.4	1211.8	1158.3	1094.6	1022.7	966.5	932.0
155°	1349.6	1342.9	1326.8	1304.1	1288.1	1247.9	1198.4	1142.3	1080.7	1021.9	983.1
157.5°	1373.1	1364.8	1349.9	1330.3	1313.2	1276.3	1233.2	1184.8	1131.0	1074.9	1035.3
160°	1387.0	1377.7	1361.6	1344.2	1328.2	1293.4	1254.6	1210.5	1161.0	1110.2	1067.4
162.5°	1396.7	1388.4	1369.1	1353.9	1340.0	1308.4	1271.7	1231.9	1187.7	1143.3	1103.7
165°	1407.1	1397.7	1377.7	1365.6	1353.6	1326.8	1294.7	1262.6	1225.2	1189.1	1157.0
167.5°	1407.9	1400.1	1380.1	1368.3	1359.5	1336.5	1310.5	1285.9	1256.8	1228.4	1201.7
170°	1405.8	1399.1	1379.0	1368.3	1361.6	1342.9	1320.2	1298.8	1276.0	1251.9	1230.5
172.5°	1398.3	1391.6	1372.6	1364.0	1360.6	1344.0	1325.5	1309.5	1289.9	1272.3	1255.2
175°	1379.0	1373.7	1357.6	1352.3	1353.6	1342.9	1329.5	1320.2	1308.1	1297.4	1288.1
177.5°	1350.9	1347.7	1335.9	1335.9	1340.2	1333.8	1329.5	1325.2	1319.9	1316.7	1313.5
180°	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2



TEST NUMBER: P1428423

CATALOG NUMBER: SQ2W-PW1-K-100U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1050.0	1050.0	1050.0	1050.0	1050.0	1050.0	1050.0	1050.0	1050.0	1050.0	1050.0
2.5°	1049.6	1047.8	1048.1	1048.7	1049.7	1050.8	1049.7	1048.7	1048.1	1047.8	1049.6
5°	1049.0	1047.2	1047.7	1049.0	1053.0	1057.0	1053.0	1049.0	1047.7	1047.2	1049.0
7.5°	1045.7	1045.0	1046.5	1048.6	1052.5	1056.4	1052.5	1048.6	1046.5	1045.0	1045.7
10°	1042.3	1042.1	1044.3	1046.9	1050.5	1054.0	1050.5	1046.9	1044.3	1042.1	1042.3
12.5°	1038.0	1038.3	1040.9	1043.7	1047.3	1050.8	1047.3	1043.7	1040.9	1038.3	1038.0
15°	1028.2	1029.6	1032.7	1035.6	1037.8	1040.0	1037.8	1035.6	1032.7	1029.6	1028.2
17.5°	1012.1	1012.2	1013.0	1013.9	1014.9	1016.0	1014.9	1013.9	1013.0	1012.2	1012.1
20°	999.7	997.5	994.3	992.0	992.0	992.0	992.0	992.0	994.3	997.5	999.7
22.5°	982.2	976.4	967.9	960.9	958.1	955.2	958.1	960.9	967.9	976.4	982.2
25°	947.5	934.3	917.0	902.3	895.7	889.0	895.7	902.3	917.0	934.3	947.5
27.5°	900.2	879.1	854.5	833.7	824.5	815.2	824.5	833.7	854.5	879.1	900.2
30°	861.9	835.5	808.3	785.8	776.9	768.0	776.9	785.8	808.3	835.5	861.9
32.5°	821.9	791.7	763.5	740.0	730.4	720.8	730.4	740.0	763.5	791.7	821.9
35°	759.2	724.8	696.3	672.9	664.5	656.0	664.5	672.9	696.3	724.8	759.2
37.5°	696.4	659.9	630.1	605.5	596.1	586.8	596.1	605.5	630.1	659.9	696.4
40°	652.5	615.1	585.3	560.7	551.3	542.0	551.3	560.7	585.3	615.1	652.5
42.5°	610.1	572.7	542.9	518.2	508.5	498.8	508.5	518.2	542.9	572.7	610.1
45°	545.9	508.6	479.7	455.7	446.3	437.0	446.3	455.7	479.7	508.6	545.9
47.5°	485.4	448.6	420.6	397.6	389.6	381.6	389.6	397.6	420.6	448.6	485.4
50°	446.8	411.0	383.0	359.6	349.8	340.0	349.8	359.6	383.0	411.0	446.8
52.5°	409.4	373.8	345.1	320.3	306.9	293.6	306.9	320.3	345.1	373.8	409.4
55°	355.0	319.0	287.0	261.1	253.6	246.0	253.6	261.1	287.0	319.0	355.0
57.5°	304.9	272.3	243.2	219.8	213.6	207.4	213.6	219.8	243.2	272.3	304.9
60°	271.6	241.8	217.3	197.4	191.2	185.0	191.2	197.4	217.3	241.8	271.6
62.5°	239.0	212.3	192.8	176.9	171.8	166.6	171.8	176.9	192.8	212.3	239.0
65°	199.2	177.0	161.0	147.9	143.4	139.0	143.4	147.9	161.0	177.0	199.2
67.5°	164.8	146.8	132.7	121.5	118.5	115.6	118.5	121.5	132.7	146.8	164.8
70°	142.6	127.2	115.7	106.4	104.2	102.0	104.2	106.4	115.7	127.2	142.6
72.5°	121.3	108.5	99.4	92.2	90.7	89.2	90.7	92.2	99.4	108.5	121.3
75°	93.0	83.9	77.7	72.8	71.9	71.0	71.9	72.8	77.7	83.9	93.0
77.5°	68.8	62.1	57.5	53.8	53.1	52.4	53.1	53.8	57.5	62.1	68.8
80°	53.3	48.2	44.7	42.0	42.0	42.0	42.0	42.0	44.7	48.2	53.3
82.5°	38.0	34.7	32.9	31.6	31.6	31.6	31.6	31.6	32.9	34.7	38.0
85°	19.9	17.7	15.0	12.9	12.4	12.0	12.4	12.9	15.0	17.7	19.9
87.5°	10.2	11.0	12.6	13.4	14.4	13.9	14.4	13.4	12.6	11.0	10.2
90°	30.8	40.1	49.5	54.8	60.2	57.5	60.2	54.8	49.5	40.1	30.8
92.5°	61.8	77.6	89.1	98.7	103.0	102.5	103.0	98.7	89.1	77.6	61.8
95°	124.4	143.1	161.8	175.2	183.2	180.6	183.2	175.2	161.8	143.1	124.4
97.5°	191.8	216.9	237.8	250.4	258.4	263.8	258.4	250.4	237.8	216.9	191.8
100°	236.7	260.8	284.9	299.6	313.0	318.3	313.0	299.6	284.9	260.8	236.7
102.5°	273.1	304.7	330.9	346.7	357.9	363.3	357.9	346.7	330.9	304.7	273.1
105°	333.0	366.5	394.6	414.6	426.7	430.7	426.7	414.6	394.6	366.5	333.0
107.5°	393.0	427.5	453.4	475.6	490.3	498.9	490.3	475.6	453.4	427.5	393.0
110°	440.1	468.1	496.2	516.3	531.0	536.4	531.0	516.3	496.2	468.1	440.1



TEST NUMBER: P1428423

CATALOG NUMBER: SQ2W-PW1-K-100U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	479.6	510.9	539.0	559.1	575.9	583.4	575.9	559.1	539.0	510.9	479.6
115°	535.0	576.5	601.9	620.6	632.7	639.3	632.7	620.6	601.9	576.5	535.0
117.5°	581.0	624.4	652.2	666.6	672.3	677.1	672.3	666.6	652.2	624.4	581.0
120°	609.9	650.0	682.1	700.9	707.6	710.2	707.6	700.9	682.1	650.0	609.9
122.5°	636.7	674.7	705.7	728.7	739.7	742.3	739.7	728.7	705.7	674.7	636.7
125°	674.1	710.2	742.3	765.1	777.1	783.8	777.1	765.1	742.3	710.2	674.1
127.5°	706.8	745.8	775.2	795.8	807.6	813.0	807.6	795.8	775.2	745.8	706.8
130°	724.9	765.1	794.5	817.2	827.9	833.3	827.9	817.2	794.5	765.1	724.9
132.5°	738.9	781.1	811.6	832.2	844.0	849.3	844.0	832.2	811.6	781.1	738.9
135°	755.7	799.9	832.0	852.0	862.7	868.1	862.7	852.0	832.0	799.9	755.7
137.5°	770.4	810.6	844.0	865.1	874.8	878.2	874.8	865.1	844.0	810.6	770.4
140°	781.1	815.9	849.3	869.4	880.1	881.4	880.1	869.4	849.3	815.9	781.1
142.5°	795.0	822.3	851.5	871.5	882.2	884.7	882.2	871.5	851.5	822.3	795.0
145°	819.9	836.0	856.0	874.8	884.1	886.8	884.1	874.8	856.0	836.0	819.9
147.5°	851.2	856.3	866.7	879.0	888.1	890.0	888.1	879.0	866.7	856.3	851.2
150°	874.8	873.4	877.4	885.5	893.5	892.1	893.5	885.5	877.4	873.4	874.8
152.5°	901.5	893.7	893.5	897.2	901.0	900.7	901.0	897.2	893.5	893.7	901.5
155°	947.0	932.3	924.2	921.6	921.6	920.2	921.6	921.6	924.2	932.3	947.0
157.5°	997.0	976.4	964.4	957.9	956.1	953.1	956.1	957.9	964.4	976.4	997.0
160°	1031.2	1008.5	996.5	985.8	981.8	977.7	981.8	985.8	996.5	1008.5	1031.2
162.5°	1063.3	1041.7	1028.6	1018.9	1014.9	1008.8	1014.9	1018.9	1028.6	1041.7	1063.3
165°	1115.5	1092.8	1078.1	1070.0	1064.7	1059.3	1064.7	1070.0	1078.1	1092.8	1115.5
167.5°	1167.7	1142.8	1133.2	1124.1	1119.0	1109.4	1119.0	1124.1	1133.2	1142.8	1167.7
170°	1199.8	1177.0	1171.7	1163.7	1154.3	1143.6	1154.3	1163.7	1171.7	1177.0	1199.8
172.5°	1227.6	1212.4	1207.0	1199.0	1196.0	1187.5	1196.0	1199.0	1207.0	1212.4	1227.6
175°	1268.0	1256.0	1256.0	1254.6	1250.6	1242.6	1250.6	1254.6	1256.0	1256.0	1268.0
177.5°	1301.7	1295.3	1299.6	1299.6	1298.5	1291.0	1298.5	1299.6	1299.6	1295.3	1301.7
180°	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2



TEST NUMBER: P1428423

CATALOG NUMBER: SQ2W-PW1-K-100U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1050.0	1050.0	1050.0	1050.0
2.5°	1053.5	1054.9	1048.9	1042.8
5°	1053.0	1054.1	1046.6	1039.0
7.5°	1048.7	1049.1	1041.5	1033.8
10°	1045.0	1045.0	1037.0	1029.0
12.5°	1039.9	1039.3	1031.0	1022.6
15°	1028.7	1026.8	1017.9	1009.0
17.5°	1012.7	1011.0	1002.1	993.2
20°	1001.0	999.8	990.9	982.0
22.5°	985.3	985.2	975.6	966.0
25°	956.3	960.7	951.3	942.0
27.5°	917.8	929.1	921.6	914.0
30°	887.7	905.6	899.8	894.0
32.5°	854.1	877.7	875.4	873.2
35°	799.7	831.0	835.0	839.0
37.5°	739.5	774.8	786.7	798.6
40°	697.3	735.2	752.1	769.0
42.5°	654.9	693.9	715.1	736.2
45°	591.7	632.2	657.1	682.0
47.5°	531.1	571.6	596.3	621.0
50°	490.3	529.0	553.0	577.0
52.5°	451.9	489.2	510.7	532.2
55°	395.0	430.1	450.6	471.0
57.5°	341.1	372.6	390.3	408.0
60°	306.7	336.9	352.4	368.0
62.5°	273.1	302.0	315.8	329.6
65°	227.7	251.6	261.8	272.0
67.5°	186.7	204.6	210.3	216.0
70°	161.7	176.4	178.2	180.0
72.5°	137.9	150.2	149.5	148.8
75°	105.0	113.1	109.6	106.0
77.5°	77.6	82.9	77.5	72.2
80°	60.0	63.7	58.3	53.0
82.5°	42.9	45.5	41.3	37.0
85°	21.7	22.4	20.2	18.0
87.5°	10.7	9.9	7.7	5.6
90°	24.1	14.7	9.4	4.0
92.5°	51.9	36.1	25.4	14.7
95°	104.3	82.9	58.9	41.5
97.5°	166.1	131.6	107.8	79.2
100°	199.3	165.9	143.1	112.4
102.5°	235.7	207.6	176.3	145.5
105°	300.9	266.2	230.1	195.3
107.5°	361.4	323.2	279.8	248.5
110°	399.9	358.5	313.0	284.9



TEST NUMBER: P1428423

CATALOG NUMBER: SQ2W-PW1-K-100U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	437.4	394.8	348.3	320.2
115°	488.2	441.4	398.6	374.5
117.5°	537.2	489.0	443.8	424.8
120°	567.1	519.0	474.8	460.1
122.5°	591.7	544.6	503.7	497.6
125°	628.6	580.5	545.7	553.7
127.5°	658.6	614.5	592.5	610.5
130°	676.8	638.0	624.6	650.0
132.5°	692.8	662.6	656.7	691.8
135°	716.9	699.5	704.9	753.0
137.5°	745.5	738.9	756.8	817.5
140°	763.7	767.8	793.2	861.4
142.5°	788.3	797.7	830.6	903.1
145°	826.6	846.7	889.5	961.7
147.5°	869.9	895.9	948.9	1023.0
150°	898.8	932.3	988.4	1059.3
152.5°	932.0	966.5	1022.7	1094.6
155°	983.1	1021.9	1080.7	1142.3
157.5°	1035.3	1074.9	1131.0	1184.8
160°	1067.4	1110.2	1161.0	1210.5
162.5°	1103.7	1143.3	1187.7	1231.9
165°	1157.0	1189.1	1225.2	1262.6
167.5°	1201.7	1228.4	1256.8	1285.9
170°	1230.5	1251.9	1276.0	1298.8
172.5°	1255.2	1272.3	1289.9	1309.5
175°	1288.1	1297.4	1308.1	1320.2
177.5°	1313.5	1316.7	1319.9	1325.2
180°	1324.2	1324.2	1324.2	1324.2



TEST NUMBER: P1428423

CATALOG NUMBER: SQ2W-PW1-K-100U-050D-L935-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.47	16.20	16.53	17.27	18.71	11.72	12.45	12.78	13.51	14.95
	3H	16.76	17.42	17.83	18.49	19.95	12.98	13.63	14.05	14.70	16.16
	4H	17.16	17.79	18.25	18.86	20.32	13.48	14.10	14.56	15.17	16.64
	6H	17.34	17.91	18.43	18.98	20.46	13.78	14.35	14.87	15.43	16.90
	8H	17.38	17.92	18.47	19.01	20.48	13.89	14.43	14.99	15.52	16.99
	12H	17.37	17.89	18.47	18.97	20.47	13.92	14.43	15.02	15.52	17.01
4H	2H	15.59	16.21	16.68	17.28	18.74	12.51	13.13	13.60	14.20	15.67
	3H	17.11	17.63	18.21	18.73	20.21	13.95	14.46	15.04	15.56	17.04
	4H	17.65	18.13	18.76	19.22	20.72	14.52	14.99	15.62	16.08	17.58
	6H	17.96	18.36	19.07	19.48	20.97	14.90	15.30	16.01	16.42	17.91
	8H	18.05	18.43	19.16	19.53	21.04	15.05	15.42	16.15	16.53	18.04
	12H	18.06	18.41	19.19	19.52	21.04	15.08	15.42	16.21	16.54	18.05
8H	4H	17.68	18.06	18.79	19.17	20.67	14.85	15.23	15.96	16.34	17.84
	6H	18.10	18.41	19.23	19.56	21.06	15.34	15.65	16.47	16.80	18.31
	8H	18.27	18.54	19.41	19.67	21.20	15.56	15.83	16.70	16.96	18.49
	12H	18.34	18.58	19.48	19.71	21.27	15.64	15.88	16.78	17.00	18.56
12H	4H	17.64	17.98	18.76	19.10	20.61	14.87	15.21	15.99	16.33	17.84
	6H	18.09	18.37	19.23	19.50	21.02	15.42	15.69	16.55	16.82	18.34
	8H	18.28	18.52	19.42	19.64	21.20	15.66	15.90	16.80	17.02	18.58