

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428489

Luminaire Tested: SQ2W-PW1-K-150U-125D-L935-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428489
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PW1-K-150U-125D-L935-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE WAVES LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11449.5 lumens
Efficiency: N/A
Efficacy: 109.8 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.11 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 104.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428489

CATALOG NUMBER: SQ2W-PW1-K-150U-125D-L935-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428489

CATALOG NUMBER: SQ2W-PW1-K-150U-125D-L935-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49				
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48	43				
2	90	83	77	72	83	77	72	67	65	61	58	54	52	49	45	43	41	37				
3	82	73	66	61	76	68	62	57	58	53	50	49	45	42	40	38	36	32				
4	76	65	58	52	69	61	54	49	52	47	43	44	40	37	36	33	31	28				
5	70	58	50	45	64	54	47	42	47	41	37	39	35	32	33	30	27	24				
6	64	52	45	39	59	49	42	37	42	37	33	36	32	29	30	27	24	22				
7	59	48	40	34	55	44	37	33	38	33	29	33	29	25	27	24	22	19				
8	55	43	36	31	51	40	34	29	35	30	26	30	26	23	25	22	20	17				
9	52	40	32	27	48	37	30	26	32	27	23	28	24	21	23	20	18	16				
10	48	36	29	25	45	34	28	23	30	25	21	26	22	19	22	19	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	40942	40942	40942	40942
5°	40669	41372	40669	41372
10°	40742	41733	40742	41733
15°	40731	41983	40731	41983
20°	40748	41162	40748	41162
25°	40528	38248	40528	38248
30°	40253	34580	40253	34580
35°	39937	31227	39937	31227
40°	39143	27589	39143	27589
45°	37609	24098	37609	24098
50°	35002	20624	35002	20624
55°	32019	16723	32019	16723
60°	28697	14428	28697	14428
65°	25096	12825	25096	12825
70°	20521	11627	20521	11627
75°	15970	10698	15970	10698
80°	11901	9428	11901	9428
85°	8058	5372	8058	5372

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 37609 cd/sqm



TEST NUMBER: P1428489

CATALOG NUMBER: SQ2W-PW1-K-150U-125D-L935-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.5	2.1
10°-20°	699.6	6.1
20°-30°	1029.6	9.0
30°-40°	1125.7	9.8
40°-50°	1009.9	8.8
50°-60°	753.3	6.6
60°-70°	476.1	4.2
70°-80°	235.9	2.1
80°-90°	63.5	0.6
90°-100°	158.5	1.4
100°-110°	462.2	4.0
110°-120°	754.2	6.6
120°-130°	957.1	8.4
130°-140°	1024.1	8.9
140°-150°	956.3	8.4
150°-160°	786.9	6.9
160°-170°	527.7	4.6
170°-180°	187.4	1.6
0°-30°	1970.7	17.2
0°-40°	3096.4	27.0
0°-60°	4859.6	42.4
0°-90°	5635.1	49.2
90°-120°	1374.9	12.0
90°-150°	4312.4	37.7
90°-180°	5814.0	50.8
0°-180°	11449.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2536	2536	2536	2536	2536	
5°	2509	2553	2509	2553	2509	239
15°	2437	2512	2437	2512	2437	688
25°	2275	2147	2275	2147	2275	1048
35°	2026	1584	2026	1584	2026	1264
45°	1647	1055	1647	1055	1647	1263
55°	1138	594	1138	594	1138	1016
65°	657	336	657	336	657	651
75°	256	172	256	172	256	282
85°	44	29	44	29	44	55
90°	6	44	6	86	6	6
95°	62	46	62	272	62	75
105°	294	471	294	648	294	312
115°	563	780	563	962	563	555
125°	833	1237	833	1179	833	745
135°	1132	1619	1132	1306	1132	875
145°	1446	1867	1446	1334	1446	905
155°	1718	2028	1718	1384	1718	790
165°	1899	2114	1899	1593	1899	535
175°	1985	2070	1985	1869	1985	188
180°	1991	1991	1991	1991	1991	



TEST NUMBER: P1428489

CATALOG NUMBER: SQ2W-PW1-K-150U-125D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2535.8	2535.8	2535.8	2535.8	2535.8	2535.8	2535.8	2535.8	2535.8	2535.8	2535.8
2.5°	2518.4	2533.0	2547.6	2544.2	2534.7	2530.4	2531.3	2532.6	2535.2	2537.7	2535.2
5°	2509.3	2527.5	2545.7	2543.1	2533.4	2529.1	2530.2	2533.4	2543.1	2552.7	2543.1
7.5°	2496.7	2515.2	2533.6	2532.8	2525.5	2523.6	2527.3	2532.4	2541.8	2551.3	2541.8
10°	2485.1	2504.4	2523.7	2523.7	2517.3	2516.8	2522.1	2528.3	2536.9	2545.5	2536.9
12.5°	2469.6	2489.8	2510.0	2511.5	2506.8	2507.5	2513.8	2520.6	2529.2	2537.7	2529.2
15°	2436.8	2458.3	2479.7	2484.3	2483.2	2486.4	2494.0	2500.9	2506.3	2511.7	2506.3
17.5°	2398.6	2420.1	2441.6	2445.8	2444.3	2444.5	2446.5	2448.6	2451.1	2453.7	2451.1
20°	2371.6	2393.1	2414.5	2417.5	2414.3	2408.9	2401.4	2395.7	2395.7	2395.7	2395.7
22.5°	2333.0	2356.1	2379.3	2379.5	2372.0	2358.0	2337.6	2320.6	2313.7	2306.9	2313.7
25°	2275.0	2297.5	2320.1	2309.6	2288.1	2256.5	2214.6	2179.2	2163.1	2147.0	2163.1
27.5°	2207.4	2225.6	2243.9	2216.5	2174.0	2123.1	2063.6	2013.4	1991.1	1968.8	1991.1
30°	2159.1	2173.0	2187.0	2143.8	2081.5	2017.7	1952.2	1897.7	1876.2	1854.8	1876.2
32.5°	2108.8	2114.2	2119.6	2062.6	1984.9	1912.0	1844.0	1787.1	1764.0	1740.8	1764.0
35°	2026.2	2016.6	2006.9	1931.2	1833.6	1750.4	1681.7	1625.1	1604.7	1584.3	1604.7
37.5°	1928.7	1899.9	1871.1	1785.9	1681.7	1593.7	1521.8	1462.2	1439.7	1417.2	1439.7
40°	1857.2	1816.4	1775.6	1684.1	1575.7	1485.5	1413.6	1354.0	1331.5	1309.0	1331.5
42.5°	1778.0	1726.9	1675.8	1581.7	1473.3	1383.1	1311.2	1251.4	1228.0	1204.6	1228.0
45°	1647.1	1587.0	1526.9	1428.9	1318.4	1228.2	1158.4	1100.5	1077.9	1055.4	1077.9
47.5°	1499.8	1440.1	1380.4	1282.7	1172.4	1083.4	1015.8	960.2	940.9	921.6	940.9
50°	1393.5	1335.5	1277.6	1184.2	1079.0	992.6	925.0	868.3	844.7	821.1	844.7
52.5°	1285.3	1233.3	1181.4	1091.4	988.8	902.9	833.5	773.5	741.3	709.1	741.3
55°	1137.5	1088.1	1038.7	954.0	857.3	770.4	693.1	630.6	612.4	594.1	612.4
57.5°	985.3	942.6	899.9	823.7	736.3	657.5	587.3	530.9	515.9	500.9	515.9
60°	888.7	851.2	813.6	740.6	655.8	583.9	524.9	476.8	461.8	446.8	461.8
62.5°	796.0	762.7	729.5	659.5	577.3	512.6	465.6	427.3	414.8	402.3	414.8
65°	656.9	632.2	607.5	549.8	481.1	427.5	388.8	357.2	346.4	335.7	346.4
67.5°	521.7	507.9	494.2	451.0	397.9	354.5	320.6	293.3	286.3	279.2	286.3
70°	434.7	430.4	426.1	390.4	344.3	307.2	279.3	257.1	251.7	246.3	251.7
72.5°	359.4	361.1	362.8	333.1	293.0	262.0	240.1	222.7	219.1	215.4	219.1
75°	256.0	264.6	273.2	253.6	224.6	202.6	187.6	175.8	173.6	171.5	173.6
77.5°	174.4	187.2	200.1	187.4	166.2	149.9	138.8	130.0	128.3	126.5	128.3
80°	128.0	140.9	153.8	144.9	128.8	116.5	107.9	101.4	101.4	101.4	101.4
82.5°	89.4	99.7	110.0	103.7	91.9	83.8	79.5	76.3	76.3	76.3	76.3
85°	43.5	48.8	54.2	52.3	48.0	42.7	36.2	31.1	30.1	29.0	30.1
87.5°	12.8	17.0	21.6	20.6	17.5	15.3	14.5	14.2	14.6	14.6	14.6
90°	6.0	14.1	24.1	32.2	38.2	40.2	40.2	42.2	44.3	44.3	44.3
92.5°	22.1	35.0	35.4	35.4	43.0	46.7	49.9	50.3	52.3	52.3	52.3
95°	62.4	68.4	102.6	100.6	68.4	54.3	46.3	46.3	46.3	46.3	46.3
97.5°	119.1	127.9	133.6	179.0	189.1	182.6	148.8	125.1	111.8	105.8	111.8
100°	169.0	173.0	185.1	187.1	237.4	285.6	261.5	231.3	221.3	215.2	221.3
102.5°	218.8	221.3	239.8	248.2	259.9	287.2	370.9	361.7	354.8	353.6	354.8
105°	293.7	295.7	329.9	346.0	354.0	354.0	352.0	392.2	456.6	470.7	456.6
107.5°	373.7	383.0	423.2	466.3	475.5	477.9	467.5	461.4	459.0	460.6	459.0
110°	428.4	442.5	490.8	545.1	559.2	563.2	559.2	553.2	549.1	549.1	549.1



TEST NUMBER: P1428489

CATALOG NUMBER: SQ2W-PW1-K-150U-125D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	481.5	502.1	556.8	619.1	642.9	654.9	646.1	641.7	637.6	640.9	637.6
115°	563.2	593.4	665.8	730.2	778.4	784.5	782.5	782.5	780.5	780.5	780.5
117.5°	638.8	687.1	768.4	843.2	899.1	915.2	923.3	920.9	918.4	922.5	918.4
120°	692.0	748.3	840.8	925.3	979.6	1003.7	1011.8	1007.8	1011.8	1007.8	1011.8
122.5°	748.3	817.5	908.4	996.1	1060.1	1087.4	1097.1	1097.9	1098.7	1096.3	1098.7
125°	832.8	917.2	1023.8	1114.4	1180.7	1212.9	1221.0	1223.0	1227.0	1237.1	1227.0
127.5°	918.0	1013.8	1130.9	1218.2	1286.1	1325.2	1337.6	1342.1	1350.5	1354.9	1350.5
130°	977.6	1086.2	1204.9	1287.3	1353.7	1396.0	1418.1	1424.1	1434.2	1432.2	1434.2
132.5°	1040.3	1153.8	1274.1	1359.8	1421.3	1466.8	1485.7	1503.0	1506.6	1509.4	1506.6
135°	1132.5	1255.2	1375.9	1460.3	1518.7	1562.9	1587.1	1603.2	1613.2	1619.2	1613.2
137.5°	1229.4	1359.0	1474.8	1550.0	1608.8	1647.0	1674.4	1691.3	1701.7	1706.5	1701.7
140°	1295.4	1420.1	1532.8	1611.2	1663.5	1701.7	1725.9	1746.0	1758.0	1758.0	1758.0
142.5°	1358.2	1481.3	1590.7	1669.1	1715.0	1750.0	1775.7	1791.0	1804.7	1804.7	1804.7
145°	1446.3	1569.0	1669.5	1748.0	1786.2	1818.4	1846.5	1858.6	1866.7	1866.7	1866.7
147.5°	1538.4	1647.0	1738.7	1814.0	1846.1	1884.0	1906.1	1915.7	1925.8	1921.4	1925.8
150°	1593.1	1693.7	1782.2	1852.6	1884.8	1921.0	1943.1	1951.1	1961.2	1955.2	1961.2
152.5°	1646.2	1741.9	1822.4	1888.0	1915.3	1951.5	1976.9	1984.9	1991.8	1987.3	1991.8
155°	1717.8	1802.3	1876.7	1937.1	1961.2	1995.4	2019.5	2029.6	2037.6	2027.6	2037.6
157.5°	1781.8	1854.6	1919.4	1974.9	2000.6	2030.0	2052.5	2065.0	2073.0	2068.6	2073.0
160°	1820.4	1886.8	1945.1	1997.4	2021.5	2047.7	2071.8	2085.9	2094.0	2087.9	2094.0
162.5°	1852.6	1912.5	1967.6	2015.1	2036.0	2059.0	2087.9	2100.4	2108.4	2100.8	2108.4
165°	1898.8	1947.1	1995.4	2035.6	2053.7	2071.8	2102.0	2116.1	2122.1	2114.1	2122.1
167.5°	1933.8	1970.9	2009.9	2044.5	2057.7	2075.4	2105.6	2117.3	2124.9	2114.9	2124.9
170°	1953.2	1985.3	2019.5	2047.7	2057.7	2073.8	2104.0	2114.1	2120.1	2110.0	2120.1
172.5°	1969.2	1993.4	2021.1	2046.1	2051.3	2064.2	2092.7	2102.8	2107.2	2098.8	2107.2
175°	1985.3	1999.4	2019.5	2035.6	2033.6	2041.7	2065.8	2073.8	2081.9	2069.8	2081.9
177.5°	1993.0	1999.4	2005.9	2015.5	2009.1	2009.1	2026.8	2031.6	2033.2	2026.8	2033.2
180°	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1428489

CATALOG NUMBER: SQ2W-PW1-K-150U-125D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2535.8	2535.8	2535.8	2535.8	2535.8	2535.8	2535.8	2535.8	2535.8	2535.8	2535.8
2.5°	2532.6	2531.3	2530.4	2534.7	2544.2	2547.6	2533.0	2518.4	2533.0	2547.6	2544.2
5°	2533.4	2530.2	2529.1	2533.4	2543.1	2545.7	2527.5	2509.3	2527.5	2545.7	2543.1
7.5°	2532.4	2527.3	2523.6	2525.5	2532.8	2533.6	2515.2	2496.7	2515.2	2533.6	2532.8
10°	2528.3	2522.1	2516.8	2517.3	2523.7	2523.7	2504.4	2485.1	2504.4	2523.7	2523.7
12.5°	2520.6	2513.8	2507.5	2506.8	2511.5	2510.0	2489.8	2469.6	2489.8	2510.0	2511.5
15°	2500.9	2494.0	2486.4	2483.2	2484.3	2479.7	2458.3	2436.8	2458.3	2479.7	2484.3
17.5°	2448.6	2446.5	2444.5	2444.3	2445.8	2441.6	2420.1	2398.6	2420.1	2441.6	2445.8
20°	2395.7	2401.4	2408.9	2414.3	2417.5	2414.5	2393.1	2371.6	2393.1	2414.5	2417.5
22.5°	2320.6	2337.6	2358.0	2372.0	2379.5	2379.3	2356.1	2333.0	2356.1	2379.3	2379.5
25°	2179.2	2214.6	2256.5	2288.1	2309.6	2320.1	2297.5	2275.0	2297.5	2320.1	2309.6
27.5°	2013.4	2063.6	2123.1	2174.0	2216.5	2243.9	2225.6	2207.4	2225.6	2243.9	2216.5
30°	1897.7	1952.2	2017.7	2081.5	2143.8	2187.0	2173.0	2159.1	2173.0	2187.0	2143.8
32.5°	1787.1	1844.0	1912.0	1984.9	2062.6	2119.6	2114.2	2108.8	2114.2	2119.6	2062.6
35°	1625.1	1681.7	1750.4	1833.6	1931.2	2006.9	2016.6	2026.2	2016.6	2006.9	1931.2
37.5°	1462.2	1521.8	1593.7	1681.7	1785.9	1871.1	1899.9	1928.7	1899.9	1871.1	1785.9
40°	1354.0	1413.6	1485.5	1575.7	1684.1	1775.6	1816.4	1857.2	1816.4	1775.6	1684.1
42.5°	1251.4	1311.2	1383.1	1473.3	1581.7	1675.8	1726.9	1778.0	1726.9	1675.8	1581.7
45°	1100.5	1158.4	1228.2	1318.4	1428.9	1526.9	1587.0	1647.1	1587.0	1526.9	1428.9
47.5°	960.2	1015.8	1083.4	1172.4	1282.7	1380.4	1440.1	1499.8	1440.1	1380.4	1282.7
50°	868.3	925.0	992.6	1079.0	1184.2	1277.6	1335.5	1393.5	1335.5	1277.6	1184.2
52.5°	773.5	833.5	902.9	988.8	1091.4	1181.4	1233.3	1285.3	1233.3	1181.4	1091.4
55°	630.6	693.1	770.4	857.3	954.0	1038.7	1088.1	1137.5	1088.1	1038.7	954.0
57.5°	530.9	587.3	657.5	736.3	823.7	899.9	942.6	985.3	942.6	899.9	823.7
60°	476.8	524.9	583.9	655.8	740.6	813.6	851.2	888.7	851.2	813.6	740.6
62.5°	427.3	465.6	512.6	577.3	659.5	729.5	762.7	796.0	762.7	729.5	659.5
65°	357.2	388.8	427.5	481.1	549.8	607.5	632.2	656.9	632.2	607.5	549.8
67.5°	293.3	320.6	354.5	397.9	451.0	494.2	507.9	521.7	507.9	494.2	451.0
70°	257.1	279.3	307.2	344.3	390.4	426.1	430.4	434.7	430.4	426.1	390.4
72.5°	222.7	240.1	262.0	293.0	333.1	362.8	361.1	359.4	361.1	362.8	333.1
75°	175.8	187.6	202.6	224.6	253.6	273.2	264.6	256.0	264.6	273.2	253.6
77.5°	130.0	138.8	149.9	166.2	187.4	200.1	187.2	174.4	187.2	200.1	187.4
80°	101.4	107.9	116.5	128.8	144.9	153.8	140.9	128.0	140.9	153.8	144.9
82.5°	76.3	79.5	83.8	91.9	103.7	110.0	99.7	89.4	99.7	110.0	103.7
85°	31.1	36.2	42.7	48.0	52.3	54.2	48.8	43.5	48.8	54.2	52.3
87.5°	14.2	14.5	15.3	17.5	20.6	21.6	17.0	12.8	17.0	21.2	21.4
90°	42.2	40.2	40.2	38.2	32.2	24.1	14.1	6.0	14.1	22.1	36.2
92.5°	50.3	49.9	46.7	43.0	35.4	35.4	35.0	22.1	38.2	54.3	78.0
95°	46.3	46.3	54.3	68.4	100.6	102.6	68.4	62.4	88.5	124.7	156.9
97.5°	125.1	148.8	182.6	189.1	179.0	133.6	127.9	119.1	162.1	197.9	249.8
100°	231.3	261.5	285.6	237.4	187.1	185.1	173.0	169.0	215.2	249.4	299.7
102.5°	361.7	370.9	287.2	259.9	248.2	239.8	221.3	218.8	265.1	312.2	354.4
105°	392.2	352.0	354.0	354.0	346.0	329.9	295.7	293.7	346.0	400.3	452.6
107.5°	461.4	467.5	477.9	475.5	466.3	423.2	383.0	373.7	420.8	486.0	543.5
110°	553.2	559.2	563.2	559.2	545.1	490.8	442.5	428.4	470.7	539.1	601.4



TEST NUMBER: P1428489

CATALOG NUMBER: SQ2W-PW1-K-150U-125D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	641.7	646.1	654.9	642.9	619.1	556.8	502.1	481.5	523.8	593.8	657.8
115°	782.5	782.5	784.5	778.4	730.2	665.8	593.4	563.2	599.4	663.8	734.2
117.5°	920.9	923.3	915.2	899.1	843.2	768.4	687.1	638.8	667.4	735.4	807.8
120°	1007.8	1011.8	1003.7	979.6	925.3	840.8	748.3	692.0	714.1	780.5	852.9
122.5°	1097.9	1097.1	1087.4	1060.1	996.1	908.4	817.5	748.3	757.5	819.1	889.9
125°	1223.0	1221.0	1212.9	1180.7	1114.4	1023.8	917.2	832.8	820.7	873.0	945.4
127.5°	1342.1	1337.6	1325.2	1286.1	1218.2	1130.9	1013.8	918.0	891.1	924.1	990.5
130°	1424.1	1418.1	1396.0	1353.7	1287.3	1204.9	1086.2	977.6	939.4	959.5	1017.8
132.5°	1503.0	1485.7	1466.8	1421.3	1359.8	1274.1	1153.8	1040.3	987.6	996.5	1041.9
135°	1603.2	1587.1	1562.9	1518.7	1460.3	1375.9	1255.2	1132.5	1060.1	1052.0	1078.2
137.5°	1691.3	1674.4	1647.0	1608.8	1550.0	1474.8	1359.0	1229.4	1138.1	1111.1	1121.2
140°	1746.0	1725.9	1701.7	1663.5	1611.2	1532.8	1420.1	1295.4	1192.8	1154.6	1148.6
142.5°	1791.0	1775.7	1750.0	1715.0	1669.1	1590.7	1481.3	1358.2	1249.1	1199.6	1185.6
145°	1858.6	1846.5	1818.4	1786.2	1748.0	1669.5	1569.0	1446.3	1337.6	1273.3	1243.1
147.5°	1915.7	1906.1	1884.0	1846.1	1814.0	1738.7	1647.0	1538.4	1426.9	1347.3	1308.3
150°	1951.1	1943.1	1921.0	1884.8	1852.6	1782.2	1693.7	1593.1	1486.5	1402.0	1351.7
152.5°	1984.9	1976.9	1951.5	1915.3	1888.0	1822.4	1741.9	1646.2	1538.0	1453.5	1401.6
155°	2029.6	2019.5	1995.4	1961.2	1937.1	1876.7	1802.3	1717.8	1625.3	1536.8	1478.4
157.5°	2065.0	2052.5	2030.0	2000.6	1974.9	1919.4	1854.6	1781.8	1700.9	1616.4	1556.9
160°	2085.9	2071.8	2047.7	2021.5	1997.4	1945.1	1886.8	1820.4	1746.0	1669.5	1605.2
162.5°	2100.4	2087.9	2059.0	2036.0	2015.1	1967.6	1912.5	1852.6	1786.2	1719.4	1659.9
165°	2116.1	2102.0	2071.8	2053.7	2035.6	1995.4	1947.1	1898.8	1842.5	1788.2	1739.9
167.5°	2117.3	2105.6	2075.4	2057.7	2044.5	2009.9	1970.9	1933.8	1890.0	1847.3	1807.1
170°	2114.1	2104.0	2073.8	2057.7	2047.7	2019.5	1985.3	1953.2	1919.0	1882.7	1850.6
172.5°	2102.8	2092.7	2064.2	2051.3	2046.1	2021.1	1993.4	1969.2	1939.9	1913.3	1887.6
175°	2073.8	2065.8	2041.7	2033.6	2035.6	2019.5	1999.4	1985.3	1967.2	1951.1	1937.1
177.5°	2031.6	2026.8	2009.1	2009.1	2015.5	2005.9	1999.4	1993.0	1984.9	1980.1	1975.3
180°	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1428489

CATALOG NUMBER: SQ2W-PW1-K-150U-125D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2535.8	2535.8	2535.8	2535.8	2535.8	2535.8	2535.8	2535.8	2535.8	2535.8	2535.8
2.5°	2534.7	2530.4	2531.3	2532.6	2535.2	2537.7	2535.2	2532.6	2531.3	2530.4	2534.7
5°	2533.4	2529.1	2530.2	2533.4	2543.1	2552.7	2543.1	2533.4	2530.2	2529.1	2533.4
7.5°	2525.5	2523.6	2527.3	2532.4	2541.8	2551.3	2541.8	2532.4	2527.3	2523.6	2525.5
10°	2517.3	2516.8	2522.1	2528.3	2536.9	2545.5	2536.9	2528.3	2522.1	2516.8	2517.3
12.5°	2506.8	2507.5	2513.8	2520.6	2529.2	2537.7	2529.2	2520.6	2513.8	2507.5	2506.8
15°	2483.2	2486.4	2494.0	2500.9	2506.3	2511.7	2506.3	2500.9	2494.0	2486.4	2483.2
17.5°	2444.3	2444.5	2446.5	2448.6	2451.1	2453.7	2451.1	2448.6	2446.5	2444.5	2444.3
20°	2414.3	2408.9	2401.4	2395.7	2395.7	2395.7	2395.7	2395.7	2401.4	2408.9	2414.3
22.5°	2372.0	2358.0	2337.6	2320.6	2313.7	2306.9	2313.7	2320.6	2337.6	2358.0	2372.0
25°	2288.1	2256.5	2214.6	2179.2	2163.1	2147.0	2163.1	2179.2	2214.6	2256.5	2288.1
27.5°	2174.0	2123.1	2063.6	2013.4	1991.1	1968.8	1991.1	2013.4	2063.6	2123.1	2174.0
30°	2081.5	2017.7	1952.2	1897.7	1876.2	1854.8	1876.2	1897.7	1952.2	2017.7	2081.5
32.5°	1984.9	1912.0	1844.0	1787.1	1764.0	1740.8	1764.0	1787.1	1844.0	1912.0	1984.9
35°	1833.6	1750.4	1681.7	1625.1	1604.7	1584.3	1604.7	1625.1	1681.7	1750.4	1833.6
37.5°	1681.7	1593.7	1521.8	1462.2	1439.7	1417.2	1439.7	1462.2	1521.8	1593.7	1681.7
40°	1575.7	1485.5	1413.6	1354.0	1331.5	1309.0	1331.5	1354.0	1413.6	1485.5	1575.7
42.5°	1473.3	1383.1	1311.2	1251.4	1228.0	1204.6	1228.0	1251.4	1311.2	1383.1	1473.3
45°	1318.4	1228.2	1158.4	1100.5	1077.9	1055.4	1077.9	1100.5	1158.4	1228.2	1318.4
47.5°	1172.4	1083.4	1015.8	960.2	940.9	921.6	940.9	960.2	1015.8	1083.4	1172.4
50°	1079.0	992.6	925.0	868.3	844.7	821.1	844.7	868.3	925.0	992.6	1079.0
52.5°	988.8	902.9	833.5	773.5	741.3	709.1	741.3	773.5	833.5	902.9	988.8
55°	857.3	770.4	693.1	630.6	612.4	594.1	612.4	630.6	693.1	770.4	857.3
57.5°	736.3	657.5	587.3	530.9	515.9	500.9	515.9	530.9	587.3	657.5	736.3
60°	655.8	583.9	524.9	476.8	461.8	446.8	461.8	476.8	524.9	583.9	655.8
62.5°	577.3	512.6	465.6	427.3	414.8	402.3	414.8	427.3	465.6	512.6	577.3
65°	481.1	427.5	388.8	357.2	346.4	335.7	346.4	357.2	388.8	427.5	481.1
67.5°	397.9	354.5	320.6	293.3	286.3	279.2	286.3	293.3	320.6	354.5	397.9
70°	344.3	307.2	279.3	257.1	251.7	246.3	251.7	257.1	279.3	307.2	344.3
72.5°	293.0	262.0	240.1	222.7	219.1	215.4	219.1	222.7	240.1	262.0	293.0
75°	224.6	202.6	187.6	175.8	173.6	171.5	173.6	175.8	187.6	202.6	224.6
77.5°	166.2	149.9	138.8	130.0	128.3	126.5	128.3	130.0	138.8	149.9	166.2
80°	128.8	116.5	107.9	101.4	101.4	101.4	101.4	101.4	107.9	116.5	128.8
82.5°	91.9	83.8	79.5	76.3	76.3	76.3	76.3	76.3	79.5	83.8	91.9
85°	48.0	42.7	36.2	31.1	30.1	29.0	30.1	31.1	36.2	42.7	48.0
87.5°	19.1	19.4	21.3	22.3	23.9	23.1	23.9	22.3	21.3	19.4	19.1
90°	46.3	60.3	74.4	82.5	90.5	86.5	90.5	82.5	74.4	60.3	46.3
92.5°	92.9	116.7	134.0	148.4	154.9	154.1	154.9	148.4	134.0	116.7	92.9
95°	187.1	215.2	243.4	263.5	275.6	271.6	275.6	263.5	243.4	215.2	187.1
97.5°	288.4	326.3	357.6	376.5	388.6	396.7	388.6	376.5	357.6	326.3	288.4
100°	356.0	392.2	428.4	450.6	470.7	478.7	470.7	450.6	428.4	392.2	356.0
102.5°	410.7	458.2	497.6	521.4	538.3	546.3	538.3	521.4	497.6	458.2	410.7
105°	500.9	551.1	593.4	623.6	641.7	647.7	641.7	623.6	593.4	551.1	500.9
107.5°	591.0	642.9	681.9	715.3	737.4	750.3	737.4	715.3	681.9	642.9	591.0
110°	661.8	704.0	746.3	776.4	798.6	806.6	798.6	776.4	746.3	704.0	661.8



TEST NUMBER: P1428489

CATALOG NUMBER: SQ2W-PW1-K-150U-125D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	721.3	768.4	810.6	840.8	866.1	877.4	866.1	840.8	810.6	768.4	721.3
115°	804.6	866.9	905.2	933.3	951.4	961.5	951.4	933.3	905.2	866.9	804.6
117.5°	873.8	939.0	980.8	1002.5	1011.0	1018.2	1011.0	1002.5	980.8	939.0	873.8
120°	917.2	977.6	1025.9	1054.0	1064.1	1068.1	1064.1	1054.0	1025.9	977.6	917.2
122.5°	957.5	1014.6	1061.3	1095.9	1112.4	1116.4	1112.4	1095.9	1061.3	1014.6	957.5
125°	1013.8	1068.1	1116.4	1150.6	1168.7	1178.7	1168.7	1150.6	1116.4	1068.1	1013.8
127.5°	1062.9	1121.6	1165.9	1196.8	1214.5	1222.6	1214.5	1196.8	1165.9	1121.6	1062.9
130°	1090.2	1150.6	1194.8	1229.0	1245.1	1253.2	1245.1	1229.0	1194.8	1150.6	1090.2
132.5°	1111.1	1174.7	1220.6	1251.5	1269.2	1277.3	1269.2	1251.5	1220.6	1174.7	1111.1
135°	1136.5	1202.9	1251.1	1281.3	1297.4	1305.5	1297.4	1281.3	1251.1	1202.9	1136.5
137.5°	1158.6	1219.0	1269.2	1301.0	1315.5	1320.7	1315.5	1301.0	1269.2	1219.0	1158.6
140°	1174.7	1227.0	1277.3	1307.5	1323.6	1325.6	1323.6	1307.5	1277.3	1227.0	1174.7
142.5°	1195.6	1236.7	1280.5	1310.7	1326.8	1330.4	1326.8	1310.7	1280.5	1236.7	1195.6
145°	1233.0	1257.2	1287.3	1315.5	1329.6	1333.6	1329.6	1315.5	1287.3	1257.2	1233.0
147.5°	1280.1	1287.8	1303.4	1321.9	1335.6	1338.4	1335.6	1321.9	1303.4	1287.8	1280.1
150°	1315.5	1313.5	1319.5	1331.6	1343.7	1341.7	1343.7	1331.6	1319.5	1313.5	1315.5
152.5°	1355.7	1344.1	1343.7	1349.3	1354.9	1354.5	1354.9	1349.3	1343.7	1344.1	1355.7
155°	1424.1	1402.0	1389.9	1385.9	1385.9	1383.9	1385.9	1385.9	1389.9	1402.0	1424.1
157.5°	1499.4	1468.4	1450.3	1440.6	1437.8	1433.4	1437.8	1440.6	1450.3	1468.4	1499.4
160°	1550.9	1516.7	1498.6	1482.5	1476.4	1470.4	1476.4	1482.5	1498.6	1516.7	1550.9
162.5°	1599.1	1566.5	1546.8	1532.3	1526.3	1517.1	1526.3	1532.3	1546.8	1566.5	1599.1
165°	1677.6	1643.4	1621.3	1609.2	1601.1	1593.1	1601.1	1609.2	1621.3	1643.4	1677.6
167.5°	1756.0	1718.6	1704.1	1690.5	1682.8	1668.3	1682.8	1690.5	1704.1	1718.6	1756.0
170°	1804.3	1770.1	1762.1	1750.0	1735.9	1719.8	1735.9	1750.0	1762.1	1770.1	1804.3
172.5°	1846.1	1823.2	1815.2	1803.1	1798.7	1785.8	1798.7	1803.1	1815.2	1823.2	1846.1
175°	1906.9	1888.8	1888.8	1886.8	1880.7	1868.7	1880.7	1886.8	1888.8	1888.8	1906.9
177.5°	1957.6	1947.9	1954.4	1954.4	1952.7	1941.5	1952.7	1954.4	1954.4	1947.9	1957.6
180°	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1428489

CATALOG NUMBER: SQ2W-PW1-K-150U-125D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	2535.8	2535.8	2535.8	2535.8
2.5°	2544.2	2547.6	2533.0	2518.4
5°	2543.1	2545.7	2527.5	2509.3
7.5°	2532.8	2533.6	2515.2	2496.7
10°	2523.7	2523.7	2504.4	2485.1
12.5°	2511.5	2510.0	2489.8	2469.6
15°	2484.3	2479.7	2458.3	2436.8
17.5°	2445.8	2441.6	2420.1	2398.6
20°	2417.5	2414.5	2393.1	2371.6
22.5°	2379.5	2379.3	2356.1	2333.0
25°	2309.6	2320.1	2297.5	2275.0
27.5°	2216.5	2243.9	2225.6	2207.4
30°	2143.8	2187.0	2173.0	2159.1
32.5°	2062.6	2119.6	2114.2	2108.8
35°	1931.2	2006.9	2016.6	2026.2
37.5°	1785.9	1871.1	1899.9	1928.7
40°	1684.1	1775.6	1816.4	1857.2
42.5°	1581.7	1675.8	1726.9	1778.0
45°	1428.9	1526.9	1587.0	1647.1
47.5°	1282.7	1380.4	1440.1	1499.8
50°	1184.2	1277.6	1335.5	1393.5
52.5°	1091.4	1181.4	1233.3	1285.3
55°	954.0	1038.7	1088.1	1137.5
57.5°	823.7	899.9	942.6	985.3
60°	740.6	813.6	851.2	888.7
62.5°	659.5	729.5	762.7	796.0
65°	549.8	607.5	632.2	656.9
67.5°	451.0	494.2	507.9	521.7
70°	390.4	426.1	430.4	434.7
72.5°	333.1	362.8	361.1	359.4
75°	253.6	273.2	264.6	256.0
77.5°	187.4	200.1	187.2	174.4
80°	144.9	153.8	140.9	128.0
82.5°	103.7	110.0	99.7	89.4
85°	52.3	54.2	48.8	43.5
87.5°	21.4	21.2	17.0	12.8
90°	36.2	22.1	14.1	6.0
92.5°	78.0	54.3	38.2	22.1
95°	156.9	124.7	88.5	62.4
97.5°	249.8	197.9	162.1	119.1
100°	299.7	249.4	215.2	169.0
102.5°	354.4	312.2	265.1	218.8
105°	452.6	400.3	346.0	293.7
107.5°	543.5	486.0	420.8	373.7
110°	601.4	539.1	470.7	428.4



TEST NUMBER: P1428489

CATALOG NUMBER: SQ2W-PW1-K-150U-125D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	657.8	593.8	523.8	481.5
115°	734.2	663.8	599.4	563.2
117.5°	807.8	735.4	667.4	638.8
120°	852.9	780.5	714.1	692.0
122.5°	889.9	819.1	757.5	748.3
125°	945.4	873.0	820.7	832.8
127.5°	990.5	924.1	891.1	918.0
130°	1017.8	959.5	939.4	977.6
132.5°	1041.9	996.5	987.6	1040.3
135°	1078.2	1052.0	1060.1	1132.5
137.5°	1121.2	1111.1	1138.1	1229.4
140°	1148.6	1154.6	1192.8	1295.4
142.5°	1185.6	1199.6	1249.1	1358.2
145°	1243.1	1273.3	1337.6	1446.3
147.5°	1308.3	1347.3	1426.9	1538.4
150°	1351.7	1402.0	1486.5	1593.1
152.5°	1401.6	1453.5	1538.0	1646.2
155°	1478.4	1536.8	1625.3	1717.8
157.5°	1556.9	1616.4	1700.9	1781.8
160°	1605.2	1669.5	1746.0	1820.4
162.5°	1659.9	1719.4	1786.2	1852.6
165°	1739.9	1788.2	1842.5	1898.8
167.5°	1807.1	1847.3	1890.0	1933.8
170°	1850.6	1882.7	1919.0	1953.2
172.5°	1887.6	1913.3	1939.9	1969.2
175°	1937.1	1951.1	1967.2	1985.3
177.5°	1975.3	1980.1	1984.9	1993.0
180°	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1428489
 CATALOG NUMBER: SQ2W-PW1-K-150U-125D-L935-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.74	20.55	20.71	21.54	22.82	15.98	16.80	16.96	17.78	19.07
	3H	21.04	21.77	22.02	22.76	24.06	17.25	17.98	18.23	18.97	20.28
	4H	21.44	22.13	22.44	23.13	24.44	17.76	18.45	18.75	19.44	20.76
	6H	21.62	22.26	22.63	23.25	24.58	18.06	18.70	19.07	19.69	21.02
	8H	21.66	22.26	22.67	23.28	24.60	18.17	18.78	19.19	19.79	21.12
	12H	21.66	22.23	22.68	23.24	24.59	18.20	18.78	19.22	19.79	21.13
4H	2H	19.86	20.55	20.87	21.55	22.86	16.79	17.48	17.79	18.47	19.79
	3H	21.40	21.97	22.41	22.99	24.32	18.23	18.81	19.24	19.83	21.16
	4H	21.94	22.47	22.96	23.48	24.83	18.81	19.33	19.83	20.35	21.70
	6H	22.25	22.70	23.28	23.74	25.09	19.19	19.64	20.22	20.68	22.03
	8H	22.34	22.76	23.37	23.79	25.16	19.34	19.76	20.37	20.79	22.16
	12H	22.36	22.74	23.41	23.79	25.16	19.38	19.76	20.43	20.81	22.17
8H	4H	21.98	22.40	23.01	23.43	24.79	19.15	19.57	20.18	20.60	21.96
	6H	22.40	22.75	23.45	23.82	25.18	19.64	19.99	20.69	21.06	22.42
	8H	22.57	22.87	23.63	23.93	25.31	19.86	20.16	20.92	21.22	22.60
	12H	22.65	22.91	23.71	23.97	25.39	19.94	20.21	21.01	21.26	22.68
12H	4H	21.94	22.31	22.98	23.36	24.73	19.17	19.54	20.21	20.59	21.96
	6H	22.39	22.70	23.45	23.76	25.14	19.72	20.02	20.78	21.08	22.46
	8H	22.58	22.85	23.65	23.90	25.32	19.96	20.23	21.02	21.28	22.70