

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427556

Luminaire Tested: SQ2W-BBM-K-150U-050D-L935-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2024
Report Number: P1427556
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2104-222-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-BBM-K-150U-050D-L935-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - BLACK DISCREET BAFFLE, MEDIUM 80-DEGREE OPTIC
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7830.2 lumens
Efficiency: N/A
Efficacy: 107.0 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.17 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 73.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1427556

CATALOG NUMBER: SQ2W-BBM-K-150U-050D-L935-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1427556

CATALOG NUMBER: SQ2W-BBM-K-150U-050D-L935-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26
1	93	90	86	83	83	80	77	75	63	61	59	46	45	44	31	31	30	24
2	86	79	74	70	77	71	67	63	56	53	51	42	40	39	29	28	27	22
3	79	71	64	59	70	64	58	54	50	47	44	38	36	34	27	25	24	20
4	73	63	56	51	65	57	51	47	45	41	38	35	32	30	25	23	22	18
5	67	57	50	44	60	51	45	41	41	37	34	32	29	27	23	21	20	16
6	62	51	44	39	55	46	40	36	37	33	30	29	26	24	21	19	18	15
7	57	46	39	34	51	42	36	32	34	30	26	27	24	21	19	18	16	14
8	53	42	35	30	48	38	32	28	31	27	24	24	21	19	18	16	15	12
9	50	39	32	27	45	35	29	25	29	24	21	23	20	18	17	15	14	12
10	47	35	29	24	42	32	27	23	26	22	19	21	18	16	16	14	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21685	21685	21685	21685
5°	21854	21886	21854	21886
10°	22129	22097	22129	22097
15°	22529	22079	22529	22079
20°	22556	21680	22556	21680
25°	21999	21137	21999	21137
30°	20679	19715	20679	19715
35°	18354	17666	18354	17666
40°	15053	14246	15053	14246
45°	8973	8423	8973	8423
50°	2801	2650	2801	2650
55°	1058	1058	1058	1058
60°	65	23	65	23
65°	0	0	0	0
70°	0	0	0	0
75°	0	0	0	0
80°	0	0	0	0
85°	0	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 40°
 Vertical Angle: 45°
 Luminance: 10508 cd/sqm



TEST NUMBER: P1427556

CATALOG NUMBER: SQ2W-BBM-K-150U-050D-L935-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.4	1.6
10°-20°	376.2	4.8
20°-30°	553.4	7.1
30°-40°	565.6	7.2
40°-50°	325.8	4.2
50°-60°	56.1	0.7
60°-70°	2.0	0.0
70°-80°	0.0	0.0
80°-90°	10.6	0.1
90°-100°	158.5	2.0
100°-110°	462.2	5.9
110°-120°	754.2	9.6
120°-130°	957.1	12.2
130°-140°	1024.1	13.1
140°-150°	956.3	12.2
150°-160°	786.9	10.0
160°-170°	527.7	6.7
170°-180°	187.4	2.4
0°-30°	1058.0	13.5
0°-40°	1623.6	20.7
0°-60°	2005.5	25.6
0°-90°	2018.1	25.8
90°-120°	1374.9	17.6
90°-150°	4312.4	55.1
90°-180°	5814.0	74.3
0°-180°	7830.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1343	1343	1343	1343	1343	
5°	1348	1350	1348	1350	1348	129
15°	1348	1321	1348	1321	1348	380
25°	1235	1186	1235	1186	1235	563
35°	931	896	931	896	931	575
45°	393	369	393	369	393	304
55°	38	38	38	38	38	40
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	6	44	6	86	6	5
95°	62	46	62	272	62	75
105°	294	471	294	648	294	312
115°	563	780	563	962	563	555
125°	833	1237	833	1179	833	745
135°	1132	1619	1132	1306	1132	875
145°	1446	1867	1446	1334	1446	905
155°	1718	2028	1718	1384	1718	790
165°	1899	2114	1899	1593	1899	535
175°	1985	2070	1985	1869	1985	188
180°	1991	1991	1991	1991	1991	



TEST NUMBER: P1427556

CATALOG NUMBER: SQ2W-BBM-K-150U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1343.1	1343.1	1343.1	1343.1	1343.1	1343.1	1343.1	1343.1	1343.1	1343.1	1343.1
2.5°	1349.0	1347.3	1345.6	1341.6	1336.8	1337.2	1342.7	1346.5	1345.3	1344.1	1345.3
5°	1348.4	1346.9	1345.4	1341.3	1336.2	1337.7	1345.7	1351.6	1351.0	1350.4	1351.0
7.5°	1347.6	1346.6	1345.6	1342.6	1339.1	1340.6	1347.2	1351.8	1350.3	1348.8	1350.3
10°	1349.8	1349.5	1349.2	1344.6	1338.6	1339.1	1346.0	1350.7	1349.2	1347.8	1349.2
12.5°	1350.8	1352.7	1354.5	1348.0	1338.7	1336.8	1342.2	1345.6	1342.9	1340.2	1342.9
15°	1347.8	1352.8	1357.9	1348.6	1334.6	1328.0	1328.9	1328.6	1324.8	1320.9	1324.8
17.5°	1332.7	1339.9	1347.0	1334.8	1316.1	1305.1	1301.8	1298.0	1292.5	1287.0	1292.5
20°	1312.8	1321.2	1329.5	1316.2	1295.6	1282.4	1276.8	1271.3	1266.5	1261.8	1266.5
22.5°	1284.9	1292.5	1300.2	1287.3	1267.7	1254.3	1247.2	1240.9	1237.1	1233.3	1237.1
25°	1234.9	1240.0	1245.0	1232.0	1212.9	1200.6	1195.2	1190.7	1188.6	1186.5	1188.6
27.5°	1164.1	1165.5	1166.9	1156.5	1142.2	1131.7	1125.0	1119.3	1116.6	1113.9	1116.6
30°	1109.2	1109.2	1109.2	1101.2	1090.4	1081.5	1074.3	1067.7	1062.6	1057.5	1062.6
32.5°	1045.3	1044.6	1043.8	1037.9	1030.3	1022.5	1014.6	1007.5	1002.4	997.3	1002.4
35°	931.2	934.5	937.8	933.7	927.1	919.9	912.2	905.2	900.7	896.3	900.7
37.5°	807.7	809.0	810.2	806.8	801.9	795.2	786.8	779.6	775.9	772.1	775.9
40°	714.2	714.5	714.8	710.6	704.9	699.1	693.1	687.2	681.6	675.9	681.6
42.5°	605.1	611.1	617.1	614.6	609.1	601.6	592.1	584.3	582.0	579.7	582.0
45°	393.0	419.6	446.2	456.0	460.2	456.9	446.1	430.4	399.6	368.9	399.6
47.5°	197.5	230.6	263.7	286.6	306.1	300.6	270.0	238.8	206.3	173.7	206.3
50°	111.5	131.2	150.9	181.6	216.0	210.3	164.6	127.6	116.5	105.5	116.5
52.5°	74.4	83.2	91.9	116.6	146.6	144.7	110.7	83.6	77.4	71.1	77.4
55°	37.6	40.0	42.4	53.3	67.0	66.7	52.4	41.2	39.4	37.6	39.4
57.5°	12.8	16.0	19.2	24.1	29.4	29.6	24.5	20.0	17.0	14.1	17.0
60°	2.0	5.0	8.0	11.9	16.1	15.6	10.5	6.0	3.4	0.7	3.4
62.5°	0.4	1.2	2.1	5.2	9.2	9.1	5.0	1.7	0.9	0.1	0.9
65°	0.0	0.0	0.0	0.2	0.5	0.5	0.2	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	1.2	2.8	4.8	6.4	7.6	8.0	8.0	8.4	8.9	8.9	8.9
90°	6.0	14.1	24.1	32.2	38.2	40.2	40.2	42.2	44.3	44.3	44.3
92.5°	22.1	35.0	35.4	35.4	43.0	46.7	49.9	50.3	52.3	52.3	52.3
95°	62.4	68.4	102.6	100.6	68.4	54.3	46.3	46.3	46.3	46.3	46.3
97.5°	119.1	127.9	133.6	179.0	189.1	182.6	148.8	125.1	111.8	105.8	111.8
100°	169.0	173.0	185.1	187.1	237.4	285.6	261.5	231.3	221.3	215.2	221.3
102.5°	218.8	221.3	239.8	248.2	259.9	287.2	370.9	361.7	354.8	353.6	354.8
105°	293.7	295.7	329.9	346.0	354.0	354.0	352.0	392.2	456.6	470.7	456.6
107.5°	373.7	383.0	423.2	466.3	475.5	477.9	467.5	461.4	459.0	460.6	459.0
110°	428.4	442.5	490.8	545.1	559.2	563.2	559.2	553.2	549.1	549.1	549.1



TEST NUMBER: P1427556

CATALOG NUMBER: SQ2W-BBM-K-150U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	481.5	502.1	556.8	619.1	642.9	654.9	646.1	641.7	637.6	640.9	637.6
115°	563.2	593.4	665.8	730.2	778.4	784.5	782.5	782.5	780.5	780.5	780.5
117.5°	638.8	687.1	768.4	843.2	899.1	915.2	923.3	920.9	918.4	922.5	918.4
120°	692.0	748.3	840.8	925.3	979.6	1003.7	1011.8	1007.8	1011.8	1007.8	1011.8
122.5°	748.3	817.5	908.4	996.1	1060.1	1087.4	1097.1	1097.9	1098.7	1096.3	1098.7
125°	832.8	917.2	1023.8	1114.4	1180.7	1212.9	1221.0	1223.0	1227.0	1237.1	1227.0
127.5°	918.0	1013.8	1130.9	1218.2	1286.1	1325.2	1337.6	1342.1	1350.5	1354.9	1350.5
130°	977.6	1086.2	1204.9	1287.3	1353.7	1396.0	1418.1	1424.1	1434.2	1432.2	1434.2
132.5°	1040.3	1153.8	1274.1	1359.8	1421.3	1466.8	1485.7	1503.0	1506.6	1509.4	1506.6
135°	1132.5	1255.2	1375.9	1460.3	1518.7	1562.9	1587.1	1603.2	1613.2	1619.2	1613.2
137.5°	1229.4	1359.0	1474.8	1550.0	1608.8	1647.0	1674.4	1691.3	1701.7	1706.5	1701.7
140°	1295.4	1420.1	1532.8	1611.2	1663.5	1701.7	1725.9	1746.0	1758.0	1758.0	1758.0
142.5°	1358.2	1481.3	1590.7	1669.1	1715.0	1750.0	1775.7	1791.0	1804.7	1804.7	1804.7
145°	1446.3	1569.0	1669.5	1748.0	1786.2	1818.4	1846.5	1858.6	1866.7	1866.7	1866.7
147.5°	1538.4	1647.0	1738.7	1814.0	1846.1	1884.0	1906.1	1915.7	1925.8	1921.4	1925.8
150°	1593.1	1693.7	1782.2	1852.6	1884.8	1921.0	1943.1	1951.1	1961.2	1955.2	1961.2
152.5°	1646.2	1741.9	1822.4	1888.0	1915.3	1951.5	1976.9	1984.9	1991.8	1987.3	1991.8
155°	1717.8	1802.3	1876.7	1937.1	1961.2	1995.4	2019.5	2029.6	2037.6	2027.6	2037.6
157.5°	1781.8	1854.6	1919.4	1974.9	2000.6	2030.0	2052.5	2065.0	2073.0	2068.6	2073.0
160°	1820.4	1886.8	1945.1	1997.4	2021.5	2047.7	2071.8	2085.9	2094.0	2087.9	2094.0
162.5°	1852.6	1912.5	1967.6	2015.1	2036.0	2059.0	2087.9	2100.4	2108.4	2100.8	2108.4
165°	1898.8	1947.1	1995.4	2035.6	2053.7	2071.8	2102.0	2116.1	2122.1	2114.1	2122.1
167.5°	1933.8	1970.9	2009.9	2044.5	2057.7	2075.4	2105.6	2117.3	2124.9	2114.9	2124.9
170°	1953.2	1985.3	2019.5	2047.7	2057.7	2073.8	2104.0	2114.1	2120.1	2110.0	2120.1
172.5°	1969.2	1993.4	2021.1	2046.1	2051.3	2064.2	2092.7	2102.8	2107.2	2098.8	2107.2
175°	1985.3	1999.4	2019.5	2035.6	2033.6	2041.7	2065.8	2073.8	2081.9	2069.8	2081.9
177.5°	1993.0	1999.4	2005.9	2015.5	2009.1	2009.1	2026.8	2031.6	2033.2	2026.8	2033.2
180°	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1427556

CATALOG NUMBER: SQ2W-BBM-K-150U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1343.1	1343.1	1343.1	1343.1	1343.1	1343.1	1343.1	1343.1	1343.1	1343.1	1343.1
2.5°	1346.5	1342.7	1337.2	1336.8	1341.6	1345.6	1347.3	1349.0	1347.3	1345.6	1341.6
5°	1351.6	1345.7	1337.7	1336.2	1341.3	1345.4	1346.9	1348.4	1346.9	1345.4	1341.3
7.5°	1351.8	1347.2	1340.6	1339.1	1342.6	1345.6	1346.6	1347.6	1346.6	1345.6	1342.6
10°	1350.7	1346.0	1339.1	1338.6	1344.6	1349.2	1349.5	1349.8	1349.5	1349.2	1344.6
12.5°	1345.6	1342.2	1336.8	1338.7	1348.0	1354.5	1352.7	1350.8	1352.7	1354.5	1348.0
15°	1328.6	1328.9	1328.0	1334.6	1348.6	1357.9	1352.8	1347.8	1352.8	1357.9	1348.6
17.5°	1298.0	1301.8	1305.1	1316.1	1334.8	1347.0	1339.9	1332.7	1339.9	1347.0	1334.8
20°	1271.3	1276.8	1282.4	1295.6	1316.2	1329.5	1321.2	1312.8	1321.2	1329.5	1316.2
22.5°	1240.9	1247.2	1254.3	1267.7	1287.3	1300.2	1292.5	1284.9	1292.5	1300.2	1287.3
25°	1190.7	1195.2	1200.6	1212.9	1232.0	1245.0	1240.0	1234.9	1240.0	1245.0	1232.0
27.5°	1119.3	1125.0	1131.7	1142.2	1156.5	1166.9	1165.5	1164.1	1165.5	1166.9	1156.5
30°	1067.7	1074.3	1081.5	1090.4	1101.2	1109.2	1109.2	1109.2	1109.2	1109.2	1101.2
32.5°	1007.5	1014.6	1022.5	1030.3	1037.9	1043.8	1044.6	1045.3	1044.6	1043.8	1037.9
35°	905.2	912.2	919.9	927.1	933.7	937.8	934.5	931.2	934.5	937.8	933.7
37.5°	779.6	786.8	795.2	801.9	806.8	810.2	809.0	807.7	809.0	810.2	806.8
40°	687.2	693.1	699.1	704.9	710.6	714.8	714.5	714.2	714.5	714.8	710.6
42.5°	584.3	592.1	601.6	609.1	614.6	617.1	611.1	605.1	611.1	617.1	614.6
45°	430.4	446.1	456.9	460.2	456.0	446.2	419.6	393.0	419.6	446.2	456.0
47.5°	238.8	270.0	300.6	306.1	286.6	263.7	230.6	197.5	230.6	263.7	286.6
50°	127.6	164.6	210.3	216.0	181.6	150.9	131.2	111.5	131.2	150.9	181.6
52.5°	83.6	110.7	144.7	146.6	116.6	91.9	83.2	74.4	83.2	91.9	116.6
55°	41.2	52.4	66.7	67.0	53.3	42.4	40.0	37.6	40.0	42.4	53.3
57.5°	20.0	24.5	29.6	29.4	24.1	19.2	16.0	12.8	16.0	19.2	24.1
60°	6.0	10.5	15.6	16.1	11.9	8.0	5.0	2.0	5.0	8.0	11.9
62.5°	1.7	5.0	9.1	9.2	5.2	2.1	1.2	0.4	1.2	2.1	5.2
65°	0.0	0.2	0.5	0.5	0.2	0.0	0.0	0.0	0.0	0.0	0.2
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	8.4	8.0	8.0	7.6	6.4	4.8	2.8	1.2	2.8	4.4	7.2
90°	42.2	40.2	40.2	38.2	32.2	24.1	14.1	6.0	14.1	22.1	36.2
92.5°	50.3	49.9	46.7	43.0	35.4	35.4	35.0	22.1	38.2	54.3	78.0
95°	46.3	46.3	54.3	68.4	100.6	102.6	68.4	62.4	88.5	124.7	156.9
97.5°	125.1	148.8	182.6	189.1	179.0	133.6	127.9	119.1	162.1	197.9	249.8
100°	231.3	261.5	285.6	237.4	187.1	185.1	173.0	169.0	215.2	249.4	299.7
102.5°	361.7	370.9	287.2	259.9	248.2	239.8	221.3	218.8	265.1	312.2	354.4
105°	392.2	352.0	354.0	354.0	346.0	329.9	295.7	293.7	346.0	400.3	452.6
107.5°	461.4	467.5	477.9	475.5	466.3	423.2	383.0	373.7	420.8	486.0	543.5
110°	553.2	559.2	563.2	559.2	545.1	490.8	442.5	428.4	470.7	539.1	601.4



TEST NUMBER: P1427556

CATALOG NUMBER: SQ2W-BBM-K-150U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	641.7	646.1	654.9	642.9	619.1	556.8	502.1	481.5	523.8	593.8	657.8
115°	782.5	782.5	784.5	778.4	730.2	665.8	593.4	563.2	599.4	663.8	734.2
117.5°	920.9	923.3	915.2	899.1	843.2	768.4	687.1	638.8	667.4	735.4	807.8
120°	1007.8	1011.8	1003.7	979.6	925.3	840.8	748.3	692.0	714.1	780.5	852.9
122.5°	1097.9	1097.1	1087.4	1060.1	996.1	908.4	817.5	748.3	757.5	819.1	889.9
125°	1223.0	1221.0	1212.9	1180.7	1114.4	1023.8	917.2	832.8	820.7	873.0	945.4
127.5°	1342.1	1337.6	1325.2	1286.1	1218.2	1130.9	1013.8	918.0	891.1	924.1	990.5
130°	1424.1	1418.1	1396.0	1353.7	1287.3	1204.9	1086.2	977.6	939.4	959.5	1017.8
132.5°	1503.0	1485.7	1466.8	1421.3	1359.8	1274.1	1153.8	1040.3	987.6	996.5	1041.9
135°	1603.2	1587.1	1562.9	1518.7	1460.3	1375.9	1255.2	1132.5	1060.1	1052.0	1078.2
137.5°	1691.3	1674.4	1647.0	1608.8	1550.0	1474.8	1359.0	1229.4	1138.1	1111.1	1121.2
140°	1746.0	1725.9	1701.7	1663.5	1611.2	1532.8	1420.1	1295.4	1192.8	1154.6	1148.6
142.5°	1791.0	1775.7	1750.0	1715.0	1669.1	1590.7	1481.3	1358.2	1249.1	1199.6	1185.6
145°	1858.6	1846.5	1818.4	1786.2	1748.0	1669.5	1569.0	1446.3	1337.6	1273.3	1243.1
147.5°	1915.7	1906.1	1884.0	1846.1	1814.0	1738.7	1647.0	1538.4	1426.9	1347.3	1308.3
150°	1951.1	1943.1	1921.0	1884.8	1852.6	1782.2	1693.7	1593.1	1486.5	1402.0	1351.7
152.5°	1984.9	1976.9	1951.5	1915.3	1888.0	1822.4	1741.9	1646.2	1538.0	1453.5	1401.6
155°	2029.6	2019.5	1995.4	1961.2	1937.1	1876.7	1802.3	1717.8	1625.3	1536.8	1478.4
157.5°	2065.0	2052.5	2030.0	2000.6	1974.9	1919.4	1854.6	1781.8	1700.9	1616.4	1556.9
160°	2085.9	2071.8	2047.7	2021.5	1997.4	1945.1	1886.8	1820.4	1746.0	1669.5	1605.2
162.5°	2100.4	2087.9	2059.0	2036.0	2015.1	1967.6	1912.5	1852.6	1786.2	1719.4	1659.9
165°	2116.1	2102.0	2071.8	2053.7	2035.6	1995.4	1947.1	1898.8	1842.5	1788.2	1739.9
167.5°	2117.3	2105.6	2075.4	2057.7	2044.5	2009.9	1970.9	1933.8	1890.0	1847.3	1807.1
170°	2114.1	2104.0	2073.8	2057.7	2047.7	2019.5	1985.3	1953.2	1919.0	1882.7	1850.6
172.5°	2102.8	2092.7	2064.2	2051.3	2046.1	2021.1	1993.4	1969.2	1939.9	1913.3	1887.6
175°	2073.8	2065.8	2041.7	2033.6	2035.6	2019.5	1999.4	1985.3	1967.2	1951.1	1937.1
177.5°	2031.6	2026.8	2009.1	2009.1	2015.5	2005.9	1999.4	1993.0	1984.9	1980.1	1975.3
180°	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1427556

CATALOG NUMBER: SQ2W-BBM-K-150U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1343.1	1343.1	1343.1	1343.1	1343.1	1343.1	1343.1	1343.1	1343.1	1343.1	1343.1
2.5°	1336.8	1337.2	1342.7	1346.5	1345.3	1344.1	1345.3	1346.5	1342.7	1337.2	1336.8
5°	1336.2	1337.7	1345.7	1351.6	1351.0	1350.4	1351.0	1351.6	1345.7	1337.7	1336.2
7.5°	1339.1	1340.6	1347.2	1351.8	1350.3	1348.8	1350.3	1351.8	1347.2	1340.6	1339.1
10°	1338.6	1339.1	1346.0	1350.7	1349.2	1347.8	1349.2	1350.7	1346.0	1339.1	1338.6
12.5°	1338.7	1336.8	1342.2	1345.6	1342.9	1340.2	1342.9	1345.6	1342.2	1336.8	1338.7
15°	1334.6	1328.0	1328.9	1328.6	1324.8	1320.9	1324.8	1328.6	1328.9	1328.0	1334.6
17.5°	1316.1	1305.1	1301.8	1298.0	1292.5	1287.0	1292.5	1298.0	1301.8	1305.1	1316.1
20°	1295.6	1282.4	1276.8	1271.3	1266.5	1261.8	1266.5	1271.3	1276.8	1282.4	1295.6
22.5°	1267.7	1254.3	1247.2	1240.9	1237.1	1233.3	1237.1	1240.9	1247.2	1254.3	1267.7
25°	1212.9	1200.6	1195.2	1190.7	1188.6	1186.5	1188.6	1190.7	1195.2	1200.6	1212.9
27.5°	1142.2	1131.7	1125.0	1119.3	1116.6	1113.9	1116.6	1119.3	1125.0	1131.7	1142.2
30°	1090.4	1081.5	1074.3	1067.7	1062.6	1057.5	1062.6	1067.7	1074.3	1081.5	1090.4
32.5°	1030.3	1022.5	1014.6	1007.5	1002.4	997.3	1002.4	1007.5	1014.6	1022.5	1030.3
35°	927.1	919.9	912.2	905.2	900.7	896.3	900.7	905.2	912.2	919.9	927.1
37.5°	801.9	795.2	786.8	779.6	775.9	772.1	775.9	779.6	786.8	795.2	801.9
40°	704.9	699.1	693.1	687.2	681.6	675.9	681.6	687.2	693.1	699.1	704.9
42.5°	609.1	601.6	592.1	584.3	582.0	579.7	582.0	584.3	592.1	601.6	609.1
45°	460.2	456.9	446.1	430.4	399.6	368.9	399.6	430.4	446.1	456.9	460.2
47.5°	306.1	300.6	270.0	238.8	206.3	173.7	206.3	238.8	270.0	300.6	306.1
50°	216.0	210.3	164.6	127.6	116.5	105.5	116.5	127.6	164.6	210.3	216.0
52.5°	146.6	144.7	110.7	83.6	77.4	71.1	77.4	83.6	110.7	144.7	146.6
55°	67.0	66.7	52.4	41.2	39.4	37.6	39.4	41.2	52.4	66.7	67.0
57.5°	29.4	29.6	24.5	20.0	17.0	14.1	17.0	20.0	24.5	29.6	29.4
60°	16.1	15.6	10.5	6.0	3.4	0.7	3.4	6.0	10.5	15.6	16.1
62.5°	9.2	9.1	5.0	1.7	0.9	0.1	0.9	1.7	5.0	9.1	9.2
65°	0.5	0.5	0.2	0.0	0.0	0.0	0.0	0.0	0.2	0.5	0.5
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	9.3	12.1	14.9	16.5	18.1	17.3	18.1	16.5	14.9	12.1	9.3
90°	46.3	60.3	74.4	82.5	90.5	86.5	90.5	82.5	74.4	60.3	46.3
92.5°	92.9	116.7	134.0	148.4	154.9	154.1	154.9	148.4	134.0	116.7	92.9
95°	187.1	215.2	243.4	263.5	275.6	271.6	275.6	263.5	243.4	215.2	187.1
97.5°	288.4	326.3	357.6	376.5	388.6	396.7	388.6	376.5	357.6	326.3	288.4
100°	356.0	392.2	428.4	450.6	470.7	478.7	470.7	450.6	428.4	392.2	356.0
102.5°	410.7	458.2	497.6	521.4	538.3	546.3	538.3	521.4	497.6	458.2	410.7
105°	500.9	551.1	593.4	623.6	641.7	647.7	641.7	623.6	593.4	551.1	500.9
107.5°	591.0	642.9	681.9	715.3	737.4	750.3	737.4	715.3	681.9	642.9	591.0
110°	661.8	704.0	746.3	776.4	798.6	806.6	798.6	776.4	746.3	704.0	661.8



TEST NUMBER: P1427556

CATALOG NUMBER: SQ2W-BBM-K-150U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	721.3	768.4	810.6	840.8	866.1	877.4	866.1	840.8	810.6	768.4	721.3
115°	804.6	866.9	905.2	933.3	951.4	961.5	951.4	933.3	905.2	866.9	804.6
117.5°	873.8	939.0	980.8	1002.5	1011.0	1018.2	1011.0	1002.5	980.8	939.0	873.8
120°	917.2	977.6	1025.9	1054.0	1064.1	1068.1	1064.1	1054.0	1025.9	977.6	917.2
122.5°	957.5	1014.6	1061.3	1095.9	1112.4	1116.4	1112.4	1095.9	1061.3	1014.6	957.5
125°	1013.8	1068.1	1116.4	1150.6	1168.7	1178.7	1168.7	1150.6	1116.4	1068.1	1013.8
127.5°	1062.9	1121.6	1165.9	1196.8	1214.5	1222.6	1214.5	1196.8	1165.9	1121.6	1062.9
130°	1090.2	1150.6	1194.8	1229.0	1245.1	1253.2	1245.1	1229.0	1194.8	1150.6	1090.2
132.5°	1111.1	1174.7	1220.6	1251.5	1269.2	1277.3	1269.2	1251.5	1220.6	1174.7	1111.1
135°	1136.5	1202.9	1251.1	1281.3	1297.4	1305.5	1297.4	1281.3	1251.1	1202.9	1136.5
137.5°	1158.6	1219.0	1269.2	1301.0	1315.5	1320.7	1315.5	1301.0	1269.2	1219.0	1158.6
140°	1174.7	1227.0	1277.3	1307.5	1323.6	1325.6	1323.6	1307.5	1277.3	1227.0	1174.7
142.5°	1195.6	1236.7	1280.5	1310.7	1326.8	1330.4	1326.8	1310.7	1280.5	1236.7	1195.6
145°	1233.0	1257.2	1287.3	1315.5	1329.6	1333.6	1329.6	1315.5	1287.3	1257.2	1233.0
147.5°	1280.1	1287.8	1303.4	1321.9	1335.6	1338.4	1335.6	1321.9	1303.4	1287.8	1280.1
150°	1315.5	1313.5	1319.5	1331.6	1343.7	1341.7	1343.7	1331.6	1319.5	1313.5	1315.5
152.5°	1355.7	1344.1	1343.7	1349.3	1354.9	1354.5	1354.9	1349.3	1343.7	1344.1	1355.7
155°	1424.1	1402.0	1389.9	1385.9	1385.9	1383.9	1385.9	1385.9	1389.9	1402.0	1424.1
157.5°	1499.4	1468.4	1450.3	1440.6	1437.8	1433.4	1437.8	1440.6	1450.3	1468.4	1499.4
160°	1550.9	1516.7	1498.6	1482.5	1476.4	1470.4	1476.4	1482.5	1498.6	1516.7	1550.9
162.5°	1599.1	1566.5	1546.8	1532.3	1526.3	1517.1	1526.3	1532.3	1546.8	1566.5	1599.1
165°	1677.6	1643.4	1621.3	1609.2	1601.1	1593.1	1601.1	1609.2	1621.3	1643.4	1677.6
167.5°	1756.0	1718.6	1704.1	1690.5	1682.8	1668.3	1682.8	1690.5	1704.1	1718.6	1756.0
170°	1804.3	1770.1	1762.1	1750.0	1735.9	1719.8	1735.9	1750.0	1762.1	1770.1	1804.3
172.5°	1846.1	1823.2	1815.2	1803.1	1798.7	1785.8	1798.7	1803.1	1815.2	1823.2	1846.1
175°	1906.9	1888.8	1888.8	1886.8	1880.7	1868.7	1880.7	1886.8	1888.8	1888.8	1906.9
177.5°	1957.6	1947.9	1954.4	1954.4	1952.7	1941.5	1952.7	1954.4	1954.4	1947.9	1957.6
180°	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1427556

CATALOG NUMBER: SQ2W-BBM-K-150U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1343.1	1343.1	1343.1	1343.1
2.5°	1341.6	1345.6	1347.3	1349.0
5°	1341.3	1345.4	1346.9	1348.4
7.5°	1342.6	1345.6	1346.6	1347.6
10°	1344.6	1349.2	1349.5	1349.8
12.5°	1348.0	1354.5	1352.7	1350.8
15°	1348.6	1357.9	1352.8	1347.8
17.5°	1334.8	1347.0	1339.9	1332.7
20°	1316.2	1329.5	1321.2	1312.8
22.5°	1287.3	1300.2	1292.5	1284.9
25°	1232.0	1245.0	1240.0	1234.9
27.5°	1156.5	1166.9	1165.5	1164.1
30°	1101.2	1109.2	1109.2	1109.2
32.5°	1037.9	1043.8	1044.6	1045.3
35°	933.7	937.8	934.5	931.2
37.5°	806.8	810.2	809.0	807.7
40°	710.6	714.8	714.5	714.2
42.5°	614.6	617.1	611.1	605.1
45°	456.0	446.2	419.6	393.0
47.5°	286.6	263.7	230.6	197.5
50°	181.6	150.9	131.2	111.5
52.5°	116.6	91.9	83.2	74.4
55°	53.3	42.4	40.0	37.6
57.5°	24.1	19.2	16.0	12.8
60°	11.9	8.0	5.0	2.0
62.5°	5.2	2.1	1.2	0.4
65°	0.2	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0
87.5°	7.2	4.4	2.8	1.2
90°	36.2	22.1	14.1	6.0
92.5°	78.0	54.3	38.2	22.1
95°	156.9	124.7	88.5	62.4
97.5°	249.8	197.9	162.1	119.1
100°	299.7	249.4	215.2	169.0
102.5°	354.4	312.2	265.1	218.8
105°	452.6	400.3	346.0	293.7
107.5°	543.5	486.0	420.8	373.7
110°	601.4	539.1	470.7	428.4



TEST NUMBER: P1427556

CATALOG NUMBER: SQ2W-BBM-K-150U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	657.8	593.8	523.8	481.5
115°	734.2	663.8	599.4	563.2
117.5°	807.8	735.4	667.4	638.8
120°	852.9	780.5	714.1	692.0
122.5°	889.9	819.1	757.5	748.3
125°	945.4	873.0	820.7	832.8
127.5°	990.5	924.1	891.1	918.0
130°	1017.8	959.5	939.4	977.6
132.5°	1041.9	996.5	987.6	1040.3
135°	1078.2	1052.0	1060.1	1132.5
137.5°	1121.2	1111.1	1138.1	1229.4
140°	1148.6	1154.6	1192.8	1295.4
142.5°	1185.6	1199.6	1249.1	1358.2
145°	1243.1	1273.3	1337.6	1446.3
147.5°	1308.3	1347.3	1426.9	1538.4
150°	1351.7	1402.0	1486.5	1593.1
152.5°	1401.6	1453.5	1538.0	1646.2
155°	1478.4	1536.8	1625.3	1717.8
157.5°	1556.9	1616.4	1700.9	1781.8
160°	1605.2	1669.5	1746.0	1820.4
162.5°	1659.9	1719.4	1786.2	1852.6
165°	1739.9	1788.2	1842.5	1898.8
167.5°	1807.1	1847.3	1890.0	1933.8
170°	1850.6	1882.7	1919.0	1953.2
172.5°	1887.6	1913.3	1939.9	1969.2
175°	1937.1	1951.1	1967.2	1985.3
177.5°	1975.3	1980.1	1984.9	1993.0
180°	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1427556
 CATALOG NUMBER: SQ2W-BBM-K-150U-050D-L935-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00