

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428597

Luminaire Tested: SQ2W-WBN-K-025U-125D-L935-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428597
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2308-130-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-WBN-K-025U-125D-L935-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - WHITE DISCREET BAFFLE, NARROW 35-DEGREE OPTIC
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6446.8 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.58 / 0.63
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 57.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428597

CATALOG NUMBER: SQ2W-WBN-K-025U-125D-L935-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428597

CATALOG NUMBER: SQ2W-WBN-K-025U-125D-L935-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	115	115	115	115	111	111	111	111	103	103	103	95	95	95	88	88	88	85
1	109	106	104	101	105	103	100	98	96	94	92	90	88	87	84	83	82	79
2	103	98	94	90	100	95	91	88	89	86	84	84	82	80	79	78	76	74
3	98	91	86	81	94	88	84	80	84	80	77	79	76	74	75	73	71	68
4	92	84	79	74	89	82	77	73	78	74	71	74	71	68	71	68	66	64
5	87	79	73	68	85	77	71	67	73	69	65	70	66	63	67	64	62	60
6	83	74	68	63	80	72	67	62	69	64	61	66	62	59	64	60	58	56
7	79	69	63	59	76	68	62	58	65	60	57	63	59	56	60	57	54	53
8	75	65	59	55	73	64	58	54	62	57	53	60	55	52	57	54	51	50
9	71	62	56	52	69	61	55	51	58	54	50	57	52	49	55	51	48	47
10	68	58	53	49	66	57	52	48	56	51	47	54	50	47	52	49	46	44

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	152299	152299	152299	152299
5°	147050	147212	147050	147212
10°	127104	127406	127104	127406
15°	101143	98345	101143	98345
20°	71851	71419	71851	71419
25°	51691	50321	51691	50321
30°	39496	38342	39496	38342
35°	31004	29683	31004	29683
40°	23490	22044	23490	22044
45°	13143	11729	13143	11729
50°	4624	4077	4624	4077
55°	2826	2685	2826	2685
60°	2160	1999	2160	1999
65°	1983	1853	1983	1853
70°	1898	1737	1898	1737
75°	1772	1672	1772	1672
80°	1553	1553	1553	1553
85°	1556	1241	1556	1241

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 40°
 Vertical Angle: 45°
 Luminance: 15586 cd/sqm



TEST NUMBER: P1428597

CATALOG NUMBER: SQ2W-WBN-K-025U-125D-L935-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	818.8	12.7
10°-20°	1627.4	25.2
20°-30°	1347.7	20.9
30°-40°	969.5	15.0
40°-50°	493.9	7.7
50°-60°	128.4	2.0
60°-70°	53.3	0.8
70°-80°	29.6	0.5
80°-90°	10.2	0.2
90°-100°	26.4	0.4
100°-110°	76.9	1.2
110°-120°	125.6	1.9
120°-130°	159.3	2.5
130°-140°	170.5	2.6
140°-150°	159.2	2.5
150°-160°	131.0	2.0
160°-170°	87.9	1.4
170°-180°	31.2	0.5
0°-30°	3793.9	58.8
0°-40°	4763.5	73.9
0°-60°	5385.8	83.5
0°-90°	5478.8	85.0
90°-120°	228.9	3.6
90°-150°	717.9	11.1
90°-180°	968.0	15.0
0°-180°	6446.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	9433	9433	9433	9433	9433	
5°	9073	9083	9073	9083	9073	818
15°	6051	5884	6051	5884	6051	1643
25°	2902	2825	2902	2825	2902	1365
35°	1573	1506	1573	1506	1573	987
45°	576	514	576	514	576	460
55°	100	95	100	95	100	99
65°	52	48	52	48	52	52
75°	28	27	28	27	28	30
85°	8	7	8	7	8	9
90°	1	7	1	14	1	1
95°	10	8	10	45	10	13
105°	49	78	49	108	49	52
115°	94	130	94	160	94	92
125°	139	206	139	196	139	124
135°	188	270	188	217	188	146
145°	241	311	241	222	241	151
155°	286	338	286	230	286	131
165°	316	352	316	265	316	89
175°	330	345	330	311	330	31
180°	332	332	332	332	332	



TEST NUMBER: P1428597

CATALOG NUMBER: SQ2W-WBN-K-025U-125D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	9432.9	9432.9	9432.9	9432.9	9432.9	9432.9	9432.9	9432.9	9432.9	9432.9	9432.9
2.5°	9418.1	9411.0	9403.9	9372.2	9332.3	9329.0	9362.4	9385.3	9376.9	9368.6	9376.9
5°	9073.1	9067.1	9061.2	9034.0	8999.8	9011.7	9069.7	9109.9	9096.5	9083.1	9096.5
7.5°	8360.6	8365.6	8370.7	8356.8	8336.5	8352.1	8403.4	8438.3	8424.0	8409.8	8424.0
10°	7752.8	7766.2	7779.6	7760.6	7730.9	7753.5	7828.7	7872.3	7821.8	7771.2	7821.8
12.5°	7082.1	7073.5	7064.8	7047.5	7027.3	7023.2	7035.2	7037.3	7009.3	6981.4	7009.3
15°	6051.0	6019.7	5988.5	5940.5	5887.0	5869.5	5888.1	5900.0	5891.8	5883.6	5891.8
17.5°	4873.9	4885.9	4898.0	4865.5	4818.2	4793.7	4791.9	4788.3	4779.0	4769.8	4779.0
20°	4181.8	4185.5	4189.2	4169.0	4140.7	4134.0	4148.9	4159.7	4158.2	4156.7	4158.2
22.5°	3624.9	3625.6	3626.4	3599.6	3563.6	3556.6	3578.6	3591.8	3578.4	3565.0	3578.4
25°	2901.6	2899.4	2897.2	2879.3	2856.3	2839.2	2828.0	2820.2	2822.4	2824.7	2822.4
27.5°	2379.6	2370.3	2361.1	2345.9	2328.6	2323.7	2331.1	2335.3	2329.8	2324.3	2329.8
30°	2118.5	2111.1	2103.6	2088.4	2070.5	2063.8	2068.3	2070.0	2063.3	2056.6	2063.3
32.5°	1884.2	1884.5	1884.8	1871.1	1852.6	1842.4	1840.3	1837.5	1832.6	1827.7	1832.6
35°	1573.0	1577.4	1581.9	1570.8	1554.4	1540.6	1529.5	1519.4	1512.7	1506.0	1512.7
37.5°	1295.2	1299.4	1303.5	1294.2	1280.4	1265.3	1248.9	1235.2	1229.6	1223.9	1229.6
40°	1114.5	1117.4	1120.4	1113.9	1104.2	1089.7	1070.4	1054.8	1050.3	1045.9	1050.3
42.5°	917.7	930.2	942.7	938.5	928.9	915.0	896.8	880.8	870.9	861.1	870.9
45°	575.6	615.1	654.5	672.1	682.6	677.7	657.6	628.3	571.0	513.7	571.0
47.5°	291.2	345.8	400.3	439.5	473.6	462.7	407.0	351.1	294.9	238.6	294.9
50°	184.1	222.0	259.9	307.9	359.2	348.1	274.4	212.9	187.6	162.3	187.6
52.5°	141.2	160.7	180.2	225.8	280.1	274.9	210.2	158.2	144.2	130.2	144.2
55°	100.4	107.8	115.3	140.6	171.8	169.9	135.0	107.3	101.3	95.4	101.3
57.5°	77.6	81.8	86.0	95.4	106.5	105.5	92.3	81.4	77.7	74.0	77.7
60°	66.9	69.9	72.9	77.5	82.7	82.0	75.3	69.4	65.6	61.9	65.6
62.5°	60.2	62.0	63.8	65.9	68.2	67.1	62.8	59.2	57.9	56.6	57.9
65°	51.9	52.6	53.4	53.5	53.5	52.8	51.3	50.0	49.3	48.5	49.3
67.5°	44.2	44.9	45.7	45.7	45.6	45.1	44.4	43.7	42.9	42.2	42.9
70°	40.2	40.9	41.6	41.3	40.5	39.8	39.0	38.3	37.6	36.8	37.6
72.5°	34.8	35.6	36.3	35.9	35.2	34.7	34.6	34.3	33.5	32.8	33.5
75°	28.4	28.4	28.4	28.4	28.4	28.1	27.3	26.8	26.8	26.8	26.8
77.5°	22.1	22.2	22.4	21.9	21.1	20.7	20.7	20.6	20.0	19.4	20.0
80°	16.7	17.5	18.2	17.8	17.1	16.7	16.7	16.7	16.7	16.7	16.7
82.5°	14.1	14.2	14.4	13.8	13.1	12.7	12.7	12.7	12.7	12.7	12.7
85°	8.4	8.4	8.4	7.8	7.1	7.1	7.8	8.2	7.4	6.7	7.4
87.5°	2.9	3.1	3.5	3.7	3.9	4.0	4.0	4.1	4.2	4.2	4.2
90°	1.0	2.3	4.0	5.4	6.4	6.7	6.7	7.0	7.4	7.4	7.4
92.5°	3.7	5.8	5.9	5.9	7.2	7.8	8.3	8.4	8.7	8.7	8.7
95°	10.4	11.4	17.1	16.7	11.4	9.0	7.7	7.7	7.7	7.7	7.7
97.5°	19.8	21.3	22.2	29.8	31.5	30.4	24.8	20.8	18.6	17.6	18.6
100°	28.1	28.8	30.8	31.1	39.5	47.6	43.5	38.5	36.8	35.8	36.8
102.5°	36.4	36.8	39.9	41.3	43.3	47.8	61.8	60.2	59.1	58.9	59.1
105°	48.9	49.2	54.9	57.6	58.9	58.9	58.6	65.3	76.0	78.4	76.0
107.5°	62.2	63.8	70.5	77.6	79.2	79.6	77.8	76.8	76.4	76.7	76.4
110°	71.3	73.7	81.7	90.8	93.1	93.8	93.1	92.1	91.4	91.4	91.4



TEST NUMBER: P1428597

CATALOG NUMBER: SQ2W-WBN-K-025U-125D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	80.2	83.6	92.7	103.1	107.0	109.0	107.6	106.8	106.2	106.7	106.2
115°	93.8	98.8	110.8	121.6	129.6	130.6	130.3	130.3	129.9	129.9	129.9
117.5°	106.4	114.4	127.9	140.4	149.7	152.4	153.7	153.3	152.9	153.6	152.9
120°	115.2	124.6	140.0	154.0	163.1	167.1	168.4	167.8	168.4	167.8	168.4
122.5°	124.6	136.1	151.2	165.8	176.5	181.0	182.6	182.8	182.9	182.5	182.9
125°	138.6	152.7	170.5	185.5	196.6	201.9	203.3	203.6	204.3	206.0	204.3
127.5°	152.8	168.8	188.3	202.8	214.1	220.6	222.7	223.4	224.8	225.6	224.8
130°	162.8	180.8	200.6	214.3	225.4	232.4	236.1	237.1	238.8	238.4	238.8
132.5°	173.2	192.1	212.1	226.4	236.6	244.2	247.3	250.2	250.8	251.3	250.8
135°	188.5	209.0	229.1	243.1	252.8	260.2	264.2	266.9	268.6	269.6	268.6
137.5°	204.7	226.2	245.5	258.1	267.8	274.2	278.8	281.6	283.3	284.1	283.3
140°	215.7	236.4	255.2	268.2	276.9	283.3	287.3	290.7	292.7	292.7	292.7
142.5°	226.1	246.6	264.8	277.9	285.5	291.3	295.6	298.2	300.5	300.5	300.5
145°	240.8	261.2	277.9	291.0	297.4	302.7	307.4	309.4	310.8	310.8	310.8
147.5°	256.1	274.2	289.5	302.0	307.4	313.6	317.3	318.9	320.6	319.9	320.6
150°	265.2	282.0	296.7	308.4	313.8	319.8	323.5	324.8	326.5	325.5	326.5
152.5°	274.1	290.0	303.4	314.3	318.9	324.9	329.1	330.5	331.6	330.9	331.6
155°	286.0	300.1	312.4	322.5	326.5	332.2	336.2	337.9	339.2	337.6	339.2
157.5°	296.6	308.8	319.5	328.8	333.1	338.0	341.7	343.8	345.1	344.4	345.1
160°	303.1	314.1	323.8	332.5	336.6	340.9	344.9	347.3	348.6	347.6	348.6
162.5°	308.4	318.4	327.6	335.5	339.0	342.8	347.6	349.7	351.0	349.7	351.0
165°	316.1	324.2	332.2	338.9	341.9	344.9	349.9	352.3	353.3	352.0	353.3
167.5°	322.0	328.1	334.6	340.4	342.6	345.5	350.6	352.5	353.8	352.1	353.8
170°	325.2	330.5	336.2	340.9	342.6	345.3	350.3	352.0	353.0	351.3	353.0
172.5°	327.8	331.9	336.5	340.6	341.5	343.7	348.4	350.1	350.8	349.4	350.8
175°	330.5	332.9	336.2	338.9	338.6	339.9	343.9	345.3	346.6	344.6	346.6
177.5°	331.8	332.9	333.9	335.5	334.5	334.5	337.4	338.2	338.5	337.4	338.5
180°	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5



TEST NUMBER: P1428597

CATALOG NUMBER: SQ2W-WBN-K-025U-125D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	9432.9	9432.9	9432.9	9432.9	9432.9	9432.9	9432.9	9432.9	9432.9	9432.9	9432.9
2.5°	9385.3	9362.4	9329.0	9332.3	9372.2	9403.9	9411.0	9418.1	9411.0	9403.9	9372.2
5°	9109.9	9069.7	9011.7	8999.8	9034.0	9061.2	9067.1	9073.1	9067.1	9061.2	9034.0
7.5°	8438.3	8403.4	8352.1	8336.5	8356.8	8370.7	8365.6	8360.6	8365.6	8370.7	8356.8
10°	7872.3	7828.7	7753.5	7730.9	7760.6	7779.6	7766.2	7752.8	7766.2	7779.6	7760.6
12.5°	7037.3	7035.2	7023.2	7027.3	7047.5	7064.8	7073.5	7082.1	7073.5	7064.8	7047.5
15°	5900.0	5888.1	5869.5	5887.0	5940.5	5988.5	6019.7	6051.0	6019.7	5988.5	5940.5
17.5°	4788.3	4791.9	4793.7	4818.2	4865.5	4898.0	4885.9	4873.9	4885.9	4898.0	4865.5
20°	4159.7	4148.9	4134.0	4140.7	4169.0	4189.2	4185.5	4181.8	4185.5	4189.2	4169.0
22.5°	3591.8	3578.6	3556.6	3563.6	3599.6	3626.4	3625.6	3624.9	3625.6	3626.4	3599.6
25°	2820.2	2828.0	2839.2	2856.3	2879.3	2897.2	2899.4	2901.6	2899.4	2897.2	2879.3
27.5°	2335.3	2331.1	2323.7	2328.6	2345.9	2361.1	2370.3	2379.6	2370.3	2361.1	2345.9
30°	2070.0	2068.3	2063.8	2070.5	2088.4	2103.6	2111.1	2118.5	2111.1	2103.6	2088.4
32.5°	1837.5	1840.3	1842.4	1852.6	1871.1	1884.8	1884.5	1884.2	1884.5	1884.8	1871.1
35°	1519.4	1529.5	1540.6	1554.4	1570.8	1581.9	1577.4	1573.0	1577.4	1581.9	1570.8
37.5°	1235.2	1248.9	1265.3	1280.4	1294.2	1303.5	1299.4	1295.2	1299.4	1303.5	1294.2
40°	1054.8	1070.4	1089.7	1104.2	1113.9	1120.4	1117.4	1114.5	1117.4	1120.4	1113.9
42.5°	880.8	896.8	915.0	928.9	938.5	942.7	930.2	917.7	930.2	942.7	938.5
45°	628.3	657.6	677.7	682.6	672.1	654.5	615.1	575.6	615.1	654.5	672.1
47.5°	351.1	407.0	462.7	473.6	439.5	400.3	345.8	291.2	345.8	400.3	439.5
50°	212.9	274.4	348.1	359.2	307.9	259.9	222.0	184.1	222.0	259.9	307.9
52.5°	158.2	210.2	274.9	280.1	225.8	180.2	160.7	141.2	160.7	180.2	225.8
55°	107.3	135.0	169.9	171.8	140.6	115.3	107.8	100.4	107.8	115.3	140.6
57.5°	81.4	92.3	105.5	106.5	95.4	86.0	81.8	77.6	81.8	86.0	95.4
60°	69.4	75.3	82.0	82.7	77.5	72.9	69.9	66.9	69.9	72.9	77.5
62.5°	59.2	62.8	67.1	68.2	65.9	63.8	62.0	60.2	62.0	63.8	65.9
65°	50.0	51.3	52.8	53.5	53.5	53.4	52.6	51.9	52.6	53.4	53.5
67.5°	43.7	44.4	45.1	45.6	45.7	45.7	44.9	44.2	44.9	45.7	45.7
70°	38.3	39.0	39.8	40.5	41.3	41.6	40.9	40.2	40.9	41.6	41.3
72.5°	34.3	34.6	34.7	35.2	35.9	36.3	35.6	34.8	35.6	36.3	35.9
75°	26.8	27.3	28.1	28.4	28.4	28.4	28.4	28.4	28.4	28.4	28.4
77.5°	20.6	20.7	20.7	21.1	21.9	22.4	22.2	22.1	22.2	22.4	21.9
80°	16.7	16.7	16.7	17.1	17.8	18.2	17.5	16.7	17.5	18.2	17.8
82.5°	12.7	12.7	12.7	13.1	13.8	14.4	14.2	14.1	14.2	14.4	13.8
85°	8.2	7.8	7.1	7.1	7.8	8.4	8.4	8.4	8.4	8.4	7.8
87.5°	4.1	4.0	4.0	3.9	3.7	3.5	3.1	2.9	3.1	3.4	3.9
90°	7.0	6.7	6.7	6.4	5.4	4.0	2.3	1.0	2.3	3.7	6.0
92.5°	8.4	8.3	7.8	7.2	5.9	5.9	5.8	3.7	6.4	9.0	13.0
95°	7.7	7.7	9.0	11.4	16.7	17.1	11.4	10.4	14.7	20.8	26.1
97.5°	20.8	24.8	30.4	31.5	29.8	22.2	21.3	19.8	27.0	33.0	41.6
100°	38.5	43.5	47.6	39.5	31.1	30.8	28.8	28.1	35.8	41.5	49.9
102.5°	60.2	61.8	47.8	43.3	41.3	39.9	36.8	36.4	44.1	52.0	59.0
105°	65.3	58.6	58.9	58.9	57.6	54.9	49.2	48.9	57.6	66.6	75.3
107.5°	76.8	77.8	79.6	79.2	77.6	70.5	63.8	62.2	70.1	80.9	90.5
110°	92.1	93.1	93.8	93.1	90.8	81.7	73.7	71.3	78.4	89.7	100.1



TEST NUMBER: P1428597

CATALOG NUMBER: SQ2W-WBN-K-025U-125D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	106.8	107.6	109.0	107.0	103.1	92.7	83.6	80.2	87.2	98.9	109.5
115°	130.3	130.3	130.6	129.6	121.6	110.8	98.8	93.8	99.8	110.5	122.2
117.5°	153.3	153.7	152.4	149.7	140.4	127.9	114.4	106.4	111.1	122.4	134.5
120°	167.8	168.4	167.1	163.1	154.0	140.0	124.6	115.2	118.9	129.9	142.0
122.5°	182.8	182.6	181.0	176.5	165.8	151.2	136.1	124.6	126.1	136.4	148.2
125°	203.6	203.3	201.9	196.6	185.5	170.5	152.7	138.6	136.6	145.3	157.4
127.5°	223.4	222.7	220.6	214.1	202.8	188.3	168.8	152.8	148.4	153.8	164.9
130°	237.1	236.1	232.4	225.4	214.3	200.6	180.8	162.8	156.4	159.7	169.4
132.5°	250.2	247.3	244.2	236.6	226.4	212.1	192.1	173.2	164.4	165.9	173.5
135°	266.9	264.2	260.2	252.8	243.1	229.1	209.0	188.5	176.5	175.1	179.5
137.5°	281.6	278.8	274.2	267.8	258.1	245.5	226.2	204.7	189.5	185.0	186.7
140°	290.7	287.3	283.3	276.9	268.2	255.2	236.4	215.7	198.6	192.2	191.2
142.5°	298.2	295.6	291.3	285.5	277.9	264.8	246.6	226.1	208.0	199.7	197.4
145°	309.4	307.4	302.7	297.4	291.0	277.9	261.2	240.8	222.7	212.0	207.0
147.5°	318.9	317.3	313.6	307.4	302.0	289.5	274.2	256.1	237.6	224.3	217.8
150°	324.8	323.5	319.8	313.8	308.4	296.7	282.0	265.2	247.5	233.4	225.0
152.5°	330.5	329.1	324.9	318.9	314.3	303.4	290.0	274.1	256.0	242.0	233.3
155°	337.9	336.2	332.2	326.5	322.5	312.4	300.1	286.0	270.6	255.8	246.1
157.5°	343.8	341.7	338.0	333.1	328.8	319.5	308.8	296.6	283.2	269.1	259.2
160°	347.3	344.9	340.9	336.6	332.5	323.8	314.1	303.1	290.7	277.9	267.2
162.5°	349.7	347.6	342.8	339.0	335.5	327.6	318.4	308.4	297.4	286.3	276.3
165°	352.3	349.9	344.9	341.9	338.9	332.2	324.2	316.1	306.7	297.7	289.7
167.5°	352.5	350.6	345.5	342.6	340.4	334.6	328.1	322.0	314.7	307.6	300.9
170°	352.0	350.3	345.3	342.6	340.9	336.2	330.5	325.2	319.5	313.4	308.1
172.5°	350.1	348.4	343.7	341.5	340.6	336.5	331.9	327.8	323.0	318.5	314.3
175°	345.3	343.9	339.9	338.6	338.9	336.2	332.9	330.5	327.5	324.8	322.5
177.5°	338.2	337.4	334.5	334.5	335.5	333.9	332.9	331.8	330.5	329.7	328.9
180°	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5



TEST NUMBER: P1428597

CATALOG NUMBER: SQ2W-WBN-K-025U-125D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	9432.9	9432.9	9432.9	9432.9	9432.9	9432.9	9432.9	9432.9	9432.9	9432.9	9432.9
2.5°	9332.3	9329.0	9362.4	9385.3	9376.9	9368.6	9376.9	9385.3	9362.4	9329.0	9332.3
5°	8999.8	9011.7	9069.7	9109.9	9096.5	9083.1	9096.5	9109.9	9069.7	9011.7	8999.8
7.5°	8336.5	8352.1	8403.4	8438.3	8424.0	8409.8	8424.0	8438.3	8403.4	8352.1	8336.5
10°	7730.9	7753.5	7828.7	7872.3	7821.8	7771.2	7821.8	7872.3	7828.7	7753.5	7730.9
12.5°	7027.3	7023.2	7035.2	7037.3	7009.3	6981.4	7009.3	7037.3	7035.2	7023.2	7027.3
15°	5887.0	5869.5	5888.1	5900.0	5891.8	5883.6	5891.8	5900.0	5888.1	5869.5	5887.0
17.5°	4818.2	4793.7	4791.9	4788.3	4779.0	4769.8	4779.0	4788.3	4791.9	4793.7	4818.2
20°	4140.7	4134.0	4148.9	4159.7	4158.2	4156.7	4158.2	4159.7	4148.9	4134.0	4140.7
22.5°	3563.6	3556.6	3578.6	3591.8	3578.4	3565.0	3578.4	3591.8	3578.6	3556.6	3563.6
25°	2856.3	2839.2	2828.0	2820.2	2822.4	2824.7	2822.4	2820.2	2828.0	2839.2	2856.3
27.5°	2328.6	2323.7	2331.1	2335.3	2329.8	2324.3	2329.8	2335.3	2331.1	2323.7	2328.6
30°	2070.5	2063.8	2068.3	2070.0	2063.3	2056.6	2063.3	2070.0	2068.3	2063.8	2070.5
32.5°	1852.6	1842.4	1840.3	1837.5	1832.6	1827.7	1832.6	1837.5	1840.3	1842.4	1852.6
35°	1554.4	1540.6	1529.5	1519.4	1512.7	1506.0	1512.7	1519.4	1529.5	1540.6	1554.4
37.5°	1280.4	1265.3	1248.9	1235.2	1229.6	1223.9	1229.6	1235.2	1248.9	1265.3	1280.4
40°	1104.2	1089.7	1070.4	1054.8	1050.3	1045.9	1050.3	1054.8	1070.4	1089.7	1104.2
42.5°	928.9	915.0	896.8	880.8	870.9	861.1	870.9	880.8	896.8	915.0	928.9
45°	682.6	677.7	657.6	628.3	571.0	513.7	571.0	628.3	657.6	677.7	682.6
47.5°	473.6	462.7	407.0	351.1	294.9	238.6	294.9	351.1	407.0	462.7	473.6
50°	359.2	348.1	274.4	212.9	187.6	162.3	187.6	212.9	274.4	348.1	359.2
52.5°	280.1	274.9	210.2	158.2	144.2	130.2	144.2	158.2	210.2	274.9	280.1
55°	171.8	169.9	135.0	107.3	101.3	95.4	101.3	107.3	135.0	169.9	171.8
57.5°	106.5	105.5	92.3	81.4	77.7	74.0	77.7	81.4	92.3	105.5	106.5
60°	82.7	82.0	75.3	69.4	65.6	61.9	65.6	69.4	75.3	82.0	82.7
62.5°	68.2	67.1	62.8	59.2	57.9	56.6	57.9	59.2	62.8	67.1	68.2
65°	53.5	52.8	51.3	50.0	49.3	48.5	49.3	50.0	51.3	52.8	53.5
67.5°	45.6	45.1	44.4	43.7	42.9	42.2	42.9	43.7	44.4	45.1	45.6
70°	40.5	39.8	39.0	38.3	37.6	36.8	37.6	38.3	39.0	39.8	40.5
72.5°	35.2	34.7	34.6	34.3	33.5	32.8	33.5	34.3	34.6	34.7	35.2
75°	28.4	28.1	27.3	26.8	26.8	26.8	26.8	26.8	27.3	28.1	28.4
77.5°	21.1	20.7	20.7	20.6	20.0	19.4	20.0	20.6	20.7	20.7	21.1
80°	17.1	16.7	16.7	16.7	16.7	16.7	16.7	16.7	16.7	16.7	17.1
82.5°	13.1	12.7	12.7	12.7	12.7	12.7	12.7	12.7	12.7	12.7	13.1
85°	7.1	7.1	7.8	8.2	7.4	6.7	7.4	8.2	7.8	7.1	7.1
87.5°	4.2	4.7	5.2	5.4	5.7	5.6	5.7	5.4	5.2	4.7	4.2
90°	7.7	10.0	12.4	13.7	15.1	14.4	15.1	13.7	12.4	10.0	7.7
92.5°	15.5	19.4	22.3	24.7	25.8	25.7	25.8	24.7	22.3	19.4	15.5
95°	31.1	35.8	40.5	43.9	45.9	45.2	45.9	43.9	40.5	35.8	31.1
97.5°	48.0	54.3	59.5	62.7	64.7	66.0	64.7	62.7	59.5	54.3	48.0
100°	59.3	65.3	71.3	75.0	78.4	79.7	78.4	75.0	71.3	65.3	59.3
102.5°	68.4	76.3	82.8	86.8	89.6	91.0	89.6	86.8	82.8	76.3	68.4
105°	83.4	91.8	98.8	103.8	106.8	107.8	106.8	103.8	98.8	91.8	83.4
107.5°	98.4	107.0	113.5	119.1	122.8	124.9	122.8	119.1	113.5	107.0	98.4
110°	110.2	117.2	124.2	129.3	132.9	134.3	132.9	129.3	124.2	117.2	110.2



TEST NUMBER: P1428597

CATALOG NUMBER: SQ2W-WBN-K-025U-125D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	120.1	127.9	135.0	140.0	144.2	146.1	144.2	140.0	135.0	127.9	120.1
115°	134.0	144.3	150.7	155.4	158.4	160.1	158.4	155.4	150.7	144.3	134.0
117.5°	145.5	156.3	163.3	166.9	168.3	169.5	168.3	166.9	163.3	156.3	145.5
120°	152.7	162.8	170.8	175.5	177.2	177.8	177.2	175.5	170.8	162.8	152.7
122.5°	159.4	168.9	176.7	182.4	185.2	185.9	185.2	182.4	176.7	168.9	159.4
125°	168.8	177.8	185.9	191.6	194.6	196.2	194.6	191.6	185.9	177.8	168.8
127.5°	176.9	186.7	194.1	199.3	202.2	203.5	202.2	199.3	194.1	186.7	176.9
130°	181.5	191.6	198.9	204.6	207.3	208.6	207.3	204.6	198.9	191.6	181.5
132.5°	185.0	195.6	203.2	208.4	211.3	212.6	211.3	208.4	203.2	195.6	185.0
135°	189.2	200.3	208.3	213.3	216.0	217.3	216.0	213.3	208.3	200.3	189.2
137.5°	192.9	202.9	211.3	216.6	219.0	219.9	219.0	216.6	211.3	202.9	192.9
140°	195.6	204.3	212.6	217.7	220.4	220.7	220.4	217.7	212.6	204.3	195.6
142.5°	199.1	205.9	213.2	218.2	220.9	221.5	220.9	218.2	213.2	205.9	199.1
145°	205.3	209.3	214.3	219.0	221.4	222.0	221.4	219.0	214.3	209.3	205.3
147.5°	213.1	214.4	217.0	220.1	222.4	222.8	222.4	220.1	217.0	214.4	213.1
150°	219.0	218.7	219.7	221.7	223.7	223.4	223.7	221.7	219.7	218.7	219.0
152.5°	225.7	223.8	223.7	224.6	225.6	225.5	225.6	224.6	223.7	223.8	225.7
155°	237.1	233.4	231.4	230.7	230.7	230.4	230.7	230.7	231.4	233.4	237.1
157.5°	249.6	244.5	241.4	239.8	239.4	238.6	239.4	239.8	241.4	244.5	249.6
160°	258.2	252.5	249.5	246.8	245.8	244.8	245.8	246.8	249.5	252.5	258.2
162.5°	266.2	260.8	257.5	255.1	254.1	252.6	254.1	255.1	257.5	260.8	266.2
165°	279.3	273.6	269.9	267.9	266.6	265.2	266.6	267.9	269.9	273.6	279.3
167.5°	292.3	286.1	283.7	281.4	280.2	277.7	280.2	281.4	283.7	286.1	292.3
170°	300.4	294.7	293.4	291.3	289.0	286.3	289.0	291.3	293.4	294.7	300.4
172.5°	307.4	303.5	302.2	300.2	299.4	297.3	299.4	300.2	302.2	303.5	307.4
175°	317.5	314.5	314.5	314.1	313.1	311.1	313.1	314.1	314.5	314.5	317.5
177.5°	325.9	324.3	325.4	325.4	325.1	323.2	325.1	325.4	325.4	324.3	325.9
180°	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5



TEST NUMBER: P1428597

CATALOG NUMBER: SQ2W-WBN-K-025U-125D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	9432.9	9432.9	9432.9	9432.9
2.5°	9372.2	9403.9	9411.0	9418.1
5°	9034.0	9061.2	9067.1	9073.1
7.5°	8356.8	8370.7	8365.6	8360.6
10°	7760.6	7779.6	7766.2	7752.8
12.5°	7047.5	7064.8	7073.5	7082.1
15°	5940.5	5988.5	6019.7	6051.0
17.5°	4865.5	4898.0	4885.9	4873.9
20°	4169.0	4189.2	4185.5	4181.8
22.5°	3599.6	3626.4	3625.6	3624.9
25°	2879.3	2897.2	2899.4	2901.6
27.5°	2345.9	2361.1	2370.3	2379.6
30°	2088.4	2103.6	2111.1	2118.5
32.5°	1871.1	1884.8	1884.5	1884.2
35°	1570.8	1581.9	1577.4	1573.0
37.5°	1294.2	1303.5	1299.4	1295.2
40°	1113.9	1120.4	1117.4	1114.5
42.5°	938.5	942.7	930.2	917.7
45°	672.1	654.5	615.1	575.6
47.5°	439.5	400.3	345.8	291.2
50°	307.9	259.9	222.0	184.1
52.5°	225.8	180.2	160.7	141.2
55°	140.6	115.3	107.8	100.4
57.5°	95.4	86.0	81.8	77.6
60°	77.5	72.9	69.9	66.9
62.5°	65.9	63.8	62.0	60.2
65°	53.5	53.4	52.6	51.9
67.5°	45.7	45.7	44.9	44.2
70°	41.3	41.6	40.9	40.2
72.5°	35.9	36.3	35.6	34.8
75°	28.4	28.4	28.4	28.4
77.5°	21.9	22.4	22.2	22.1
80°	17.8	18.2	17.5	16.7
82.5°	13.8	14.4	14.2	14.1
85°	7.8	8.4	8.4	8.4
87.5°	3.9	3.4	3.1	2.9
90°	6.0	3.7	2.3	1.0
92.5°	13.0	9.0	6.4	3.7
95°	26.1	20.8	14.7	10.4
97.5°	41.6	33.0	27.0	19.8
100°	49.9	41.5	35.8	28.1
102.5°	59.0	52.0	44.1	36.4
105°	75.3	66.6	57.6	48.9
107.5°	90.5	80.9	70.1	62.2
110°	100.1	89.7	78.4	71.3



TEST NUMBER: P1428597

CATALOG NUMBER: SQ2W-WBN-K-025U-125D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	109.5	98.9	87.2	80.2
115°	122.2	110.5	99.8	93.8
117.5°	134.5	122.4	111.1	106.4
120°	142.0	129.9	118.9	115.2
122.5°	148.2	136.4	126.1	124.6
125°	157.4	145.3	136.6	138.6
127.5°	164.9	153.8	148.4	152.8
130°	169.4	159.7	156.4	162.8
132.5°	173.5	165.9	164.4	173.2
135°	179.5	175.1	176.5	188.5
137.5°	186.7	185.0	189.5	204.7
140°	191.2	192.2	198.6	215.7
142.5°	197.4	199.7	208.0	226.1
145°	207.0	212.0	222.7	240.8
147.5°	217.8	224.3	237.6	256.1
150°	225.0	233.4	247.5	265.2
152.5°	233.3	242.0	256.0	274.1
155°	246.1	255.8	270.6	286.0
157.5°	259.2	269.1	283.2	296.6
160°	267.2	277.9	290.7	303.1
162.5°	276.3	286.3	297.4	308.4
165°	289.7	297.7	306.7	316.1
167.5°	300.9	307.6	314.7	322.0
170°	308.1	313.4	319.5	325.2
172.5°	314.3	318.5	323.0	327.8
175°	322.5	324.8	327.5	330.5
177.5°	328.9	329.7	330.5	331.8
180°	331.5	331.5	331.5	331.5



TEST NUMBER: P1428597
 CATALOG NUMBER: SQ2W-WBN-K-025U-125D-L935-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.68	7.58	7.30	8.18	8.85	6.31	7.20	6.93	7.80	8.48
	3H	7.91	8.70	8.55	9.32	10.03	7.52	8.31	8.16	8.92	9.64
	4H	8.44	9.17	9.09	9.80	10.53	8.04	8.78	8.70	9.40	10.14
	6H	8.79	9.47	9.46	10.11	10.85	8.38	9.05	9.04	9.69	10.43
	8H	8.94	9.58	9.62	10.23	10.98	8.52	9.15	9.20	9.81	10.56
	12H	9.04	9.64	9.72	10.29	11.06	8.59	9.19	9.27	9.84	10.61
4H	2H	7.01	7.75	7.67	8.38	9.11	6.70	7.44	7.36	8.06	8.80
	3H	8.51	9.12	9.18	9.78	10.53	8.17	8.77	8.84	9.44	10.19
	4H	9.16	9.70	9.84	10.37	11.15	8.81	9.35	9.49	10.02	10.80
	6H	9.65	10.11	10.35	10.81	11.61	9.27	9.73	9.97	10.42	11.22
	8H	9.86	10.29	10.57	10.98	11.78	9.46	9.89	10.16	10.58	11.38
	12H	10.00	10.38	10.72	11.10	11.90	9.57	9.95	10.29	10.67	11.47
8H	4H	9.32	9.75	10.03	10.44	11.24	9.00	9.44	9.71	10.13	10.93
	6H	9.95	10.30	10.69	11.04	11.84	9.60	9.94	10.33	10.68	11.49
	8H	10.26	10.57	11.01	11.31	12.13	9.88	10.19	10.63	10.93	11.75
	12H	10.50	10.77	11.24	11.49	12.38	10.08	10.35	10.83	11.08	11.97
12H	4H	9.30	9.68	10.03	10.40	11.21	9.00	9.38	9.72	10.10	10.90
	6H	9.98	10.29	10.73	11.03	11.85	9.64	9.95	10.39	10.69	11.51
	8H	10.33	10.60	11.08	11.33	12.22	9.97	10.23	10.71	10.96	11.85