

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427799

Luminaire Tested: SQ2W-F-K-150U-050D-L935-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1427799
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-20)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-F-K-150U-050D-L935-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - FROSTED CONTINUOUS ROLL LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7883.2 lumens
Efficiency: N/A
Efficacy: 108.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 72.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1427799

CATALOG NUMBER: SQ2W-F-K-150U-050D-L935-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1427799

CATALOG NUMBER: SQ2W-F-K-150U-050D-L935-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	91	91	91	91	70	70	70	51	51	51	34	34	34	26
1	92	88	84	81	82	79	76	73	61	59	57	45	44	42	30	29	29	22
2	84	77	71	66	75	69	64	59	53	50	47	39	37	35	26	25	24	18
3	76	67	60	55	68	60	54	49	47	43	39	35	32	30	23	22	20	15
4	70	59	52	46	62	53	47	42	42	37	33	31	28	25	21	19	17	13
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	19	17	15	11
6	59	47	39	34	52	42	36	31	33	28	25	25	21	19	17	15	13	10
7	54	42	35	29	48	38	31	27	30	25	22	22	19	17	15	13	12	9
8	50	38	31	26	45	34	28	23	27	22	19	20	17	15	14	12	10	8
9	47	35	28	23	41	31	25	21	25	20	17	19	15	13	13	11	9	7
10	43	32	25	20	39	29	23	18	23	18	15	17	14	12	12	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11820	11820	11820	11820
5°	11749	11883	11749	11883
10°	11707	11842	11707	11842
15°	11644	11789	11644	11789
20°	11570	11685	11570	11685
25°	11444	11546	11444	11546
30°	11324	11400	11324	11400
35°	11178	11251	11178	11251
40°	11050	11084	11050	11084
45°	10889	10889	10889	10889
50°	10670	10698	10670	10698
55°	10421	10435	10421	10435
60°	10139	10139	10139	10139
65°	9811	9769	9811	9769
70°	9347	9248	9347	9248
75°	8715	8521	8715	8521
80°	7764	7382	7764	7382
85°	6206	5261	6206	5261

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 10962 cd/sqm



TEST NUMBER: P1427799

CATALOG NUMBER: SQ2W-F-K-150U-050D-L935-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.3	0.9
10°-20°	197.9	2.5
20°-30°	297.9	3.8
30°-40°	356.3	4.5
40°-50°	367.9	4.7
50°-60°	331.8	4.2
60°-70°	254.2	3.2
70°-80°	146.9	1.9
80°-90°	46.4	0.6
90°-100°	158.5	2.0
100°-110°	462.2	5.9
110°-120°	754.2	9.6
120°-130°	957.1	12.1
130°-140°	1024.1	13.0
140°-150°	956.3	12.1
150°-160°	786.9	10.0
160°-170°	527.7	6.7
170°-180°	187.4	2.4
0°-30°	565.2	7.2
0°-40°	921.5	11.7
0°-60°	1621.2	20.6
0°-90°	2068.7	26.2
90°-120°	1374.9	17.4
90°-150°	4312.4	54.7
90°-180°	5814.0	73.8
0°-180°	7883.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	732	732	732	732	732	
5°	725	733	725	733	725	69
15°	697	705	697	705	697	196
25°	642	648	642	648	642	296
35°	567	571	567	571	567	355
45°	477	477	477	477	477	367
55°	370	371	370	371	370	331
65°	257	256	257	256	257	254
75°	140	137	140	137	140	148
85°	34	28	34	28	34	39
90°	6	44	6	86	6	6
95°	62	46	62	272	62	75
105°	294	471	294	648	294	312
115°	563	780	563	962	563	555
125°	833	1237	833	1179	833	745
135°	1132	1619	1132	1306	1132	875
145°	1446	1867	1446	1334	1446	905
155°	1718	2028	1718	1384	1718	790
165°	1899	2114	1899	1593	1899	535
175°	1985	2070	1985	1869	1985	188
180°	1991	1991	1991	1991	1991	



TEST NUMBER: P1427799

CATALOG NUMBER: SQ2W-F-K-150U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1
2.5°	728.4	731.9	735.4	733.9	730.8	729.6	730.3	731.0	731.4	731.7	731.4
5°	724.9	729.5	734.1	732.5	728.8	727.2	727.7	728.6	730.9	733.2	730.9
7.5°	719.0	723.6	728.2	726.7	723.2	721.8	722.3	723.3	725.7	728.1	725.7
10°	714.1	718.7	723.2	721.6	718.0	716.6	717.5	718.7	720.5	722.3	720.5
12.5°	707.9	712.5	717.1	715.7	712.4	711.1	711.6	712.5	714.5	716.6	714.5
15°	696.6	701.1	705.7	704.5	701.3	700.0	700.7	701.7	703.5	705.3	703.5
17.5°	682.8	687.1	691.5	690.3	687.3	686.2	687.0	688.0	689.6	691.2	689.6
20°	673.4	677.5	681.6	680.4	677.4	676.0	676.3	676.8	678.5	680.1	678.5
22.5°	661.8	665.9	670.1	669.0	666.2	664.5	664.0	664.2	666.1	668.1	666.1
25°	642.4	646.5	650.7	649.8	647.3	645.7	645.0	644.9	646.5	648.1	646.5
27.5°	622.2	625.6	629.1	628.4	626.3	625.0	624.5	624.5	625.6	626.7	625.6
30°	607.4	610.8	614.2	613.4	611.1	609.7	609.2	609.2	610.3	611.5	610.3
32.5°	591.7	594.9	598.2	597.0	594.4	593.0	592.9	593.2	594.5	595.8	594.5
35°	567.1	569.9	572.6	571.4	568.9	567.8	568.0	568.5	569.6	570.8	569.6
37.5°	542.5	544.6	546.7	545.5	543.2	542.0	541.9	542.1	543.1	544.0	543.1
40°	524.3	526.6	528.9	527.6	525.1	523.7	523.5	523.6	524.8	525.9	524.8
42.5°	505.8	507.5	509.3	508.1	505.9	504.9	505.1	505.3	505.9	506.5	505.9
45°	476.9	478.5	480.1	479.0	476.9	475.9	475.9	476.0	476.5	476.9	476.5
47.5°	446.7	447.9	449.2	448.3	446.7	445.7	445.5	445.4	446.2	446.9	446.2
50°	424.8	426.4	428.0	427.2	425.6	424.6	424.2	424.0	425.0	425.9	425.0
52.5°	403.4	405.2	407.0	406.2	404.6	403.5	402.8	402.5	403.3	404.0	403.3
55°	370.2	372.3	374.3	373.8	372.4	371.3	370.4	369.8	370.2	370.7	370.2
57.5°	336.3	338.3	340.3	339.9	338.7	337.6	336.5	335.8	336.4	337.1	336.4
60°	314.0	315.8	317.7	317.1	315.7	314.6	313.6	313.1	313.5	314.0	313.5
62.5°	291.3	293.1	295.0	294.3	292.7	291.5	290.5	290.0	290.4	290.9	290.4
65°	256.8	258.4	260.0	259.3	258.0	256.8	255.9	255.3	255.5	255.7	255.5
67.5°	221.9	223.3	224.7	224.0	222.7	221.3	220.0	219.1	219.5	219.8	219.5
70°	198.0	199.4	200.7	200.2	199.1	197.9	196.8	195.9	195.9	195.9	195.9
72.5°	174.9	176.1	177.3	176.6	175.2	174.1	173.1	172.4	172.4	172.4	172.4
75°	139.7	140.4	141.1	140.8	140.1	139.2	138.0	137.1	136.9	136.6	136.9
77.5°	105.8	105.8	105.8	105.1	104.3	103.4	102.5	101.8	101.5	101.3	101.5
80°	83.5	83.5	83.5	83.0	82.3	81.6	80.9	80.3	79.9	79.4	79.9
82.5°	62.9	62.5	62.2	61.6	60.9	60.0	58.9	58.3	58.7	59.2	58.7
85°	33.5	33.1	32.6	32.0	31.3	30.5	29.6	28.8	28.6	28.4	28.6
87.5°	11.5	12.8	14.4	15.5	16.2	15.9	15.2	15.0	15.2	15.0	15.2
90°	6.0	14.1	24.1	32.2	38.2	40.2	40.2	42.2	44.3	44.3	44.3
92.5°	22.1	35.0	35.4	35.4	43.0	46.7	49.9	50.3	52.3	52.3	52.3
95°	62.4	68.4	102.6	100.6	68.4	54.3	46.3	46.3	46.3	46.3	46.3
97.5°	119.1	127.9	133.6	179.0	189.1	182.6	148.8	125.1	111.8	105.8	111.8
100°	169.0	173.0	185.1	187.1	237.4	285.6	261.5	231.3	221.3	215.2	221.3
102.5°	218.8	221.3	239.8	248.2	259.9	287.2	370.9	361.7	354.8	353.6	354.8
105°	293.7	295.7	329.9	346.0	354.0	354.0	352.0	392.2	456.6	470.7	456.6
107.5°	373.7	383.0	423.2	466.3	475.5	477.9	467.5	461.4	459.0	460.6	459.0
110°	428.4	442.5	490.8	545.1	559.2	563.2	559.2	553.2	549.1	549.1	549.1



TEST NUMBER: P1427799

CATALOG NUMBER: SQ2W-F-K-150U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	481.5	502.1	556.8	619.1	642.9	654.9	646.1	641.7	637.6	640.9	637.6
115°	563.2	593.4	665.8	730.2	778.4	784.5	782.5	782.5	780.5	780.5	780.5
117.5°	638.8	687.1	768.4	843.2	899.1	915.2	923.3	920.9	918.4	922.5	918.4
120°	692.0	748.3	840.8	925.3	979.6	1003.7	1011.8	1007.8	1011.8	1007.8	1011.8
122.5°	748.3	817.5	908.4	996.1	1060.1	1087.4	1097.1	1097.9	1098.7	1096.3	1098.7
125°	832.8	917.2	1023.8	1114.4	1180.7	1212.9	1221.0	1223.0	1227.0	1237.1	1227.0
127.5°	918.0	1013.8	1130.9	1218.2	1286.1	1325.2	1337.6	1342.1	1350.5	1354.9	1350.5
130°	977.6	1086.2	1204.9	1287.3	1353.7	1396.0	1418.1	1424.1	1434.2	1432.2	1434.2
132.5°	1040.3	1153.8	1274.1	1359.8	1421.3	1466.8	1485.7	1503.0	1506.6	1509.4	1506.6
135°	1132.5	1255.2	1375.9	1460.3	1518.7	1562.9	1587.1	1603.2	1613.2	1619.2	1613.2
137.5°	1229.4	1359.0	1474.8	1550.0	1608.8	1647.0	1674.4	1691.3	1701.7	1706.5	1701.7
140°	1295.4	1420.1	1532.8	1611.2	1663.5	1701.7	1725.9	1746.0	1758.0	1758.0	1758.0
142.5°	1358.2	1481.3	1590.7	1669.1	1715.0	1750.0	1775.7	1791.0	1804.7	1804.7	1804.7
145°	1446.3	1569.0	1669.5	1748.0	1786.2	1818.4	1846.5	1858.6	1866.7	1866.7	1866.7
147.5°	1538.4	1647.0	1738.7	1814.0	1846.1	1884.0	1906.1	1915.7	1925.8	1921.4	1925.8
150°	1593.1	1693.7	1782.2	1852.6	1884.8	1921.0	1943.1	1951.1	1961.2	1955.2	1961.2
152.5°	1646.2	1741.9	1822.4	1888.0	1915.3	1951.5	1976.9	1984.9	1991.8	1987.3	1991.8
155°	1717.8	1802.3	1876.7	1937.1	1961.2	1995.4	2019.5	2029.6	2037.6	2027.6	2037.6
157.5°	1781.8	1854.6	1919.4	1974.9	2000.6	2030.0	2052.5	2065.0	2073.0	2068.6	2073.0
160°	1820.4	1886.8	1945.1	1997.4	2021.5	2047.7	2071.8	2085.9	2094.0	2087.9	2094.0
162.5°	1852.6	1912.5	1967.6	2015.1	2036.0	2059.0	2087.9	2100.4	2108.4	2100.8	2108.4
165°	1898.8	1947.1	1995.4	2035.6	2053.7	2071.8	2102.0	2116.1	2122.1	2114.1	2122.1
167.5°	1933.8	1970.9	2009.9	2044.5	2057.7	2075.4	2105.6	2117.3	2124.9	2114.9	2124.9
170°	1953.2	1985.3	2019.5	2047.7	2057.7	2073.8	2104.0	2114.1	2120.1	2110.0	2120.1
172.5°	1969.2	1993.4	2021.1	2046.1	2051.3	2064.2	2092.7	2102.8	2107.2	2098.8	2107.2
175°	1985.3	1999.4	2019.5	2035.6	2033.6	2041.7	2065.8	2073.8	2081.9	2069.8	2081.9
177.5°	1993.0	1999.4	2005.9	2015.5	2009.1	2009.1	2026.8	2031.6	2033.2	2026.8	2033.2
180°	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1427799

CATALOG NUMBER: SQ2W-F-K-150U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1
2.5°	731.0	730.3	729.6	730.8	733.9	735.4	731.9	728.4	731.9	735.4	733.9
5°	728.6	727.7	727.2	728.8	732.5	734.1	729.5	724.9	729.5	734.1	732.5
7.5°	723.3	722.3	721.8	723.2	726.7	728.2	723.6	719.0	723.6	728.2	726.7
10°	718.7	717.5	716.6	718.0	721.6	723.2	718.7	714.1	718.7	723.2	721.6
12.5°	712.5	711.6	711.1	712.4	715.7	717.1	712.5	707.9	712.5	717.1	715.7
15°	701.7	700.7	700.0	701.3	704.5	705.7	701.1	696.6	701.1	705.7	704.5
17.5°	688.0	687.0	686.2	687.3	690.3	691.5	687.1	682.8	687.1	691.5	690.3
20°	676.8	676.3	676.0	677.4	680.4	681.6	677.5	673.4	677.5	681.6	680.4
22.5°	664.2	664.0	664.5	666.2	669.0	670.1	665.9	661.8	665.9	670.1	669.0
25°	644.9	645.0	645.7	647.3	649.8	650.7	646.5	642.4	646.5	650.7	649.8
27.5°	624.5	624.5	625.0	626.3	628.4	629.1	625.6	622.2	625.6	629.1	628.4
30°	609.2	609.2	609.7	611.1	613.4	614.2	610.8	607.4	610.8	614.2	613.4
32.5°	593.2	592.9	593.0	594.4	597.0	598.2	594.9	591.7	594.9	598.2	597.0
35°	568.5	568.0	567.8	568.9	571.4	572.6	569.9	567.1	569.9	572.6	571.4
37.5°	542.1	541.9	542.0	543.2	545.5	546.7	544.6	542.5	544.6	546.7	545.5
40°	523.6	523.5	523.7	525.1	527.6	528.9	526.6	524.3	526.6	528.9	527.6
42.5°	505.3	505.1	504.9	505.9	508.1	509.3	507.5	505.8	507.5	509.3	508.1
45°	476.0	475.9	475.9	476.9	479.0	480.1	478.5	476.9	478.5	480.1	479.0
47.5°	445.4	445.5	445.7	446.7	448.3	449.2	447.9	446.7	447.9	449.2	448.3
50°	424.0	424.2	424.6	425.6	427.2	428.0	426.4	424.8	426.4	428.0	427.2
52.5°	402.5	402.8	403.5	404.6	406.2	407.0	405.2	403.4	405.2	407.0	406.2
55°	369.8	370.4	371.3	372.4	373.8	374.3	372.3	370.2	372.3	374.3	373.8
57.5°	335.8	336.5	337.6	338.7	339.9	340.3	338.3	336.3	338.3	340.3	339.9
60°	313.1	313.6	314.6	315.7	317.1	317.7	315.8	314.0	315.8	317.7	317.1
62.5°	290.0	290.5	291.5	292.7	294.3	295.0	293.1	291.3	293.1	295.0	294.3
65°	255.3	255.9	256.8	258.0	259.3	260.0	258.4	256.8	258.4	260.0	259.3
67.5°	219.1	220.0	221.3	222.7	224.0	224.7	223.3	221.9	223.3	224.7	224.0
70°	195.9	196.8	197.9	199.1	200.2	200.7	199.4	198.0	199.4	200.7	200.2
72.5°	172.4	173.1	174.1	175.2	176.6	177.3	176.1	174.9	176.1	177.3	176.6
75°	137.1	138.0	139.2	140.1	140.8	141.1	140.4	139.7	140.4	141.1	140.8
77.5°	101.8	102.5	103.4	104.3	105.1	105.8	105.8	105.8	105.8	105.8	105.1
80°	80.3	80.9	81.6	82.3	83.0	83.5	83.5	83.5	83.5	83.5	83.0
82.5°	58.3	58.9	60.0	60.9	61.6	62.2	62.5	62.9	62.5	62.2	61.6
85°	28.8	29.6	30.5	31.3	32.0	32.6	33.1	33.5	33.1	32.6	32.0
87.5°	15.0	15.2	15.9	16.2	15.5	14.4	12.8	11.5	12.8	14.0	16.3
90°	42.2	40.2	40.2	38.2	32.2	24.1	14.1	6.0	14.1	22.1	36.2
92.5°	50.3	49.9	46.7	43.0	35.4	35.4	35.0	22.1	38.2	54.3	78.0
95°	46.3	46.3	54.3	68.4	100.6	102.6	68.4	62.4	88.5	124.7	156.9
97.5°	125.1	148.8	182.6	189.1	179.0	133.6	127.9	119.1	162.1	197.9	249.8
100°	231.3	261.5	285.6	237.4	187.1	185.1	173.0	169.0	215.2	249.4	299.7
102.5°	361.7	370.9	287.2	259.9	248.2	239.8	221.3	218.8	265.1	312.2	354.4
105°	392.2	352.0	354.0	354.0	346.0	329.9	295.7	293.7	346.0	400.3	452.6
107.5°	461.4	467.5	477.9	475.5	466.3	423.2	383.0	373.7	420.8	486.0	543.5
110°	553.2	559.2	563.2	559.2	545.1	490.8	442.5	428.4	470.7	539.1	601.4



TEST NUMBER: P1427799

CATALOG NUMBER: SQ2W-F-K-150U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	641.7	646.1	654.9	642.9	619.1	556.8	502.1	481.5	523.8	593.8	657.8
115°	782.5	782.5	784.5	778.4	730.2	665.8	593.4	563.2	599.4	663.8	734.2
117.5°	920.9	923.3	915.2	899.1	843.2	768.4	687.1	638.8	667.4	735.4	807.8
120°	1007.8	1011.8	1003.7	979.6	925.3	840.8	748.3	692.0	714.1	780.5	852.9
122.5°	1097.9	1097.1	1087.4	1060.1	996.1	908.4	817.5	748.3	757.5	819.1	889.9
125°	1223.0	1221.0	1212.9	1180.7	1114.4	1023.8	917.2	832.8	820.7	873.0	945.4
127.5°	1342.1	1337.6	1325.2	1286.1	1218.2	1130.9	1013.8	918.0	891.1	924.1	990.5
130°	1424.1	1418.1	1396.0	1353.7	1287.3	1204.9	1086.2	977.6	939.4	959.5	1017.8
132.5°	1503.0	1485.7	1466.8	1421.3	1359.8	1274.1	1153.8	1040.3	987.6	996.5	1041.9
135°	1603.2	1587.1	1562.9	1518.7	1460.3	1375.9	1255.2	1132.5	1060.1	1052.0	1078.2
137.5°	1691.3	1674.4	1647.0	1608.8	1550.0	1474.8	1359.0	1229.4	1138.1	1111.1	1121.2
140°	1746.0	1725.9	1701.7	1663.5	1611.2	1532.8	1420.1	1295.4	1192.8	1154.6	1148.6
142.5°	1791.0	1775.7	1750.0	1715.0	1669.1	1590.7	1481.3	1358.2	1249.1	1199.6	1185.6
145°	1858.6	1846.5	1818.4	1786.2	1748.0	1669.5	1569.0	1446.3	1337.6	1273.3	1243.1
147.5°	1915.7	1906.1	1884.0	1846.1	1814.0	1738.7	1647.0	1538.4	1426.9	1347.3	1308.3
150°	1951.1	1943.1	1921.0	1884.8	1852.6	1782.2	1693.7	1593.1	1486.5	1402.0	1351.7
152.5°	1984.9	1976.9	1951.5	1915.3	1888.0	1822.4	1741.9	1646.2	1538.0	1453.5	1401.6
155°	2029.6	2019.5	1995.4	1961.2	1937.1	1876.7	1802.3	1717.8	1625.3	1536.8	1478.4
157.5°	2065.0	2052.5	2030.0	2000.6	1974.9	1919.4	1854.6	1781.8	1700.9	1616.4	1556.9
160°	2085.9	2071.8	2047.7	2021.5	1997.4	1945.1	1886.8	1820.4	1746.0	1669.5	1605.2
162.5°	2100.4	2087.9	2059.0	2036.0	2015.1	1967.6	1912.5	1852.6	1786.2	1719.4	1659.9
165°	2116.1	2102.0	2071.8	2053.7	2035.6	1995.4	1947.1	1898.8	1842.5	1788.2	1739.9
167.5°	2117.3	2105.6	2075.4	2057.7	2044.5	2009.9	1970.9	1933.8	1890.0	1847.3	1807.1
170°	2114.1	2104.0	2073.8	2057.7	2047.7	2019.5	1985.3	1953.2	1919.0	1882.7	1850.6
172.5°	2102.8	2092.7	2064.2	2051.3	2046.1	2021.1	1993.4	1969.2	1939.9	1913.3	1887.6
175°	2073.8	2065.8	2041.7	2033.6	2035.6	2019.5	1999.4	1985.3	1967.2	1951.1	1937.1
177.5°	2031.6	2026.8	2009.1	2009.1	2015.5	2005.9	1999.4	1993.0	1984.9	1980.1	1975.3
180°	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1427799

CATALOG NUMBER: SQ2W-F-K-150U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1
2.5°	730.8	729.6	730.3	731.0	731.4	731.7	731.4	731.0	730.3	729.6	730.8
5°	728.8	727.2	727.7	728.6	730.9	733.2	730.9	728.6	727.7	727.2	728.8
7.5°	723.2	721.8	722.3	723.3	725.7	728.1	725.7	723.3	722.3	721.8	723.2
10°	718.0	716.6	717.5	718.7	720.5	722.3	720.5	718.7	717.5	716.6	718.0
12.5°	712.4	711.1	711.6	712.5	714.5	716.6	714.5	712.5	711.6	711.1	712.4
15°	701.3	700.0	700.7	701.7	703.5	705.3	703.5	701.7	700.7	700.0	701.3
17.5°	687.3	686.2	687.0	688.0	689.6	691.2	689.6	688.0	687.0	686.2	687.3
20°	677.4	676.0	676.3	676.8	678.5	680.1	678.5	676.8	676.3	676.0	677.4
22.5°	666.2	664.5	664.0	664.2	666.1	668.1	666.1	664.2	664.0	664.5	666.2
25°	647.3	645.7	645.0	644.9	646.5	648.1	646.5	644.9	645.0	645.7	647.3
27.5°	626.3	625.0	624.5	624.5	625.6	626.7	625.6	624.5	624.5	625.0	626.3
30°	611.1	609.7	609.2	609.2	610.3	611.5	610.3	609.2	609.2	609.7	611.1
32.5°	594.4	593.0	592.9	593.2	594.5	595.8	594.5	593.2	592.9	593.0	594.4
35°	568.9	567.8	568.0	568.5	569.6	570.8	569.6	568.5	568.0	567.8	568.9
37.5°	543.2	542.0	541.9	542.1	543.1	544.0	543.1	542.1	541.9	542.0	543.2
40°	525.1	523.7	523.5	523.6	524.8	525.9	524.8	523.6	523.5	523.7	525.1
42.5°	505.9	504.9	505.1	505.3	505.9	506.5	505.9	505.3	505.1	504.9	505.9
45°	476.9	475.9	475.9	476.0	476.5	476.9	476.5	476.0	475.9	475.9	476.9
47.5°	446.7	445.7	445.5	445.4	446.2	446.9	446.2	445.4	445.5	445.7	446.7
50°	425.6	424.6	424.2	424.0	425.0	425.9	425.0	424.0	424.2	424.6	425.6
52.5°	404.6	403.5	402.8	402.5	403.3	404.0	403.3	402.5	402.8	403.5	404.6
55°	372.4	371.3	370.4	369.8	370.2	370.7	370.2	369.8	370.4	371.3	372.4
57.5°	338.7	337.6	336.5	335.8	336.4	337.1	336.4	335.8	336.5	337.6	338.7
60°	315.7	314.6	313.6	313.1	313.5	314.0	313.5	313.1	313.6	314.6	315.7
62.5°	292.7	291.5	290.5	290.0	290.4	290.9	290.4	290.0	290.5	291.5	292.7
65°	258.0	256.8	255.9	255.3	255.5	255.7	255.5	255.3	255.9	256.8	258.0
67.5°	222.7	221.3	220.0	219.1	219.5	219.8	219.5	219.1	220.0	221.3	222.7
70°	199.1	197.9	196.8	195.9	195.9	195.9	195.9	195.9	196.8	197.9	199.1
72.5°	175.2	174.1	173.1	172.4	172.4	172.4	172.4	172.4	173.1	174.1	175.2
75°	140.1	139.2	138.0	137.1	136.9	136.6	136.9	137.1	138.0	139.2	140.1
77.5°	104.3	103.4	102.5	101.8	101.5	101.3	101.5	101.8	102.5	103.4	104.3
80°	82.3	81.6	80.9	80.3	79.9	79.4	79.9	80.3	80.9	81.6	82.3
82.5°	60.9	60.0	58.9	58.3	58.7	59.2	58.7	58.3	58.9	60.0	60.9
85°	31.3	30.5	29.6	28.8	28.6	28.4	28.6	28.8	29.6	30.5	31.3
87.5°	17.8	20.0	22.0	23.0	24.5	23.5	24.5	23.0	22.0	20.0	17.8
90°	46.3	60.3	74.4	82.5	90.5	86.5	90.5	82.5	74.4	60.3	46.3
92.5°	92.9	116.7	134.0	148.4	154.9	154.1	154.9	148.4	134.0	116.7	92.9
95°	187.1	215.2	243.4	263.5	275.6	271.6	275.6	263.5	243.4	215.2	187.1
97.5°	288.4	326.3	357.6	376.5	388.6	396.7	388.6	376.5	357.6	326.3	288.4
100°	356.0	392.2	428.4	450.6	470.7	478.7	470.7	450.6	428.4	392.2	356.0
102.5°	410.7	458.2	497.6	521.4	538.3	546.3	538.3	521.4	497.6	458.2	410.7
105°	500.9	551.1	593.4	623.6	641.7	647.7	641.7	623.6	593.4	551.1	500.9
107.5°	591.0	642.9	681.9	715.3	737.4	750.3	737.4	715.3	681.9	642.9	591.0
110°	661.8	704.0	746.3	776.4	798.6	806.6	798.6	776.4	746.3	704.0	661.8



TEST NUMBER: P1427799

CATALOG NUMBER: SQ2W-F-K-150U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	721.3	768.4	810.6	840.8	866.1	877.4	866.1	840.8	810.6	768.4	721.3
115°	804.6	866.9	905.2	933.3	951.4	961.5	951.4	933.3	905.2	866.9	804.6
117.5°	873.8	939.0	980.8	1002.5	1011.0	1018.2	1011.0	1002.5	980.8	939.0	873.8
120°	917.2	977.6	1025.9	1054.0	1064.1	1068.1	1064.1	1054.0	1025.9	977.6	917.2
122.5°	957.5	1014.6	1061.3	1095.9	1112.4	1116.4	1112.4	1095.9	1061.3	1014.6	957.5
125°	1013.8	1068.1	1116.4	1150.6	1168.7	1178.7	1168.7	1150.6	1116.4	1068.1	1013.8
127.5°	1062.9	1121.6	1165.9	1196.8	1214.5	1222.6	1214.5	1196.8	1165.9	1121.6	1062.9
130°	1090.2	1150.6	1194.8	1229.0	1245.1	1253.2	1245.1	1229.0	1194.8	1150.6	1090.2
132.5°	1111.1	1174.7	1220.6	1251.5	1269.2	1277.3	1269.2	1251.5	1220.6	1174.7	1111.1
135°	1136.5	1202.9	1251.1	1281.3	1297.4	1305.5	1297.4	1281.3	1251.1	1202.9	1136.5
137.5°	1158.6	1219.0	1269.2	1301.0	1315.5	1320.7	1315.5	1301.0	1269.2	1219.0	1158.6
140°	1174.7	1227.0	1277.3	1307.5	1323.6	1325.6	1323.6	1307.5	1277.3	1227.0	1174.7
142.5°	1195.6	1236.7	1280.5	1310.7	1326.8	1330.4	1326.8	1310.7	1280.5	1236.7	1195.6
145°	1233.0	1257.2	1287.3	1315.5	1329.6	1333.6	1329.6	1315.5	1287.3	1257.2	1233.0
147.5°	1280.1	1287.8	1303.4	1321.9	1335.6	1338.4	1335.6	1321.9	1303.4	1287.8	1280.1
150°	1315.5	1313.5	1319.5	1331.6	1343.7	1341.7	1343.7	1331.6	1319.5	1313.5	1315.5
152.5°	1355.7	1344.1	1343.7	1349.3	1354.9	1354.5	1354.9	1349.3	1343.7	1344.1	1355.7
155°	1424.1	1402.0	1389.9	1385.9	1385.9	1383.9	1385.9	1385.9	1389.9	1402.0	1424.1
157.5°	1499.4	1468.4	1450.3	1440.6	1437.8	1433.4	1437.8	1440.6	1450.3	1468.4	1499.4
160°	1550.9	1516.7	1498.6	1482.5	1476.4	1470.4	1476.4	1482.5	1498.6	1516.7	1550.9
162.5°	1599.1	1566.5	1546.8	1532.3	1526.3	1517.1	1526.3	1532.3	1546.8	1566.5	1599.1
165°	1677.6	1643.4	1621.3	1609.2	1601.1	1593.1	1601.1	1609.2	1621.3	1643.4	1677.6
167.5°	1756.0	1718.6	1704.1	1690.5	1682.8	1668.3	1682.8	1690.5	1704.1	1718.6	1756.0
170°	1804.3	1770.1	1762.1	1750.0	1735.9	1719.8	1735.9	1750.0	1762.1	1770.1	1804.3
172.5°	1846.1	1823.2	1815.2	1803.1	1798.7	1785.8	1798.7	1803.1	1815.2	1823.2	1846.1
175°	1906.9	1888.8	1888.8	1886.8	1880.7	1868.7	1880.7	1886.8	1888.8	1888.8	1906.9
177.5°	1957.6	1947.9	1954.4	1954.4	1952.7	1941.5	1952.7	1954.4	1954.4	1947.9	1957.6
180°	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1427799

CATALOG NUMBER: SQ2W-F-K-150U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	732.1	732.1	732.1	732.1
2.5°	733.9	735.4	731.9	728.4
5°	732.5	734.1	729.5	724.9
7.5°	726.7	728.2	723.6	719.0
10°	721.6	723.2	718.7	714.1
12.5°	715.7	717.1	712.5	707.9
15°	704.5	705.7	701.1	696.6
17.5°	690.3	691.5	687.1	682.8
20°	680.4	681.6	677.5	673.4
22.5°	669.0	670.1	665.9	661.8
25°	649.8	650.7	646.5	642.4
27.5°	628.4	629.1	625.6	622.2
30°	613.4	614.2	610.8	607.4
32.5°	597.0	598.2	594.9	591.7
35°	571.4	572.6	569.9	567.1
37.5°	545.5	546.7	544.6	542.5
40°	527.6	528.9	526.6	524.3
42.5°	508.1	509.3	507.5	505.8
45°	479.0	480.1	478.5	476.9
47.5°	448.3	449.2	447.9	446.7
50°	427.2	428.0	426.4	424.8
52.5°	406.2	407.0	405.2	403.4
55°	373.8	374.3	372.3	370.2
57.5°	339.9	340.3	338.3	336.3
60°	317.1	317.7	315.8	314.0
62.5°	294.3	295.0	293.1	291.3
65°	259.3	260.0	258.4	256.8
67.5°	224.0	224.7	223.3	221.9
70°	200.2	200.7	199.4	198.0
72.5°	176.6	177.3	176.1	174.9
75°	140.8	141.1	140.4	139.7
77.5°	105.1	105.8	105.8	105.8
80°	83.0	83.5	83.5	83.5
82.5°	61.6	62.2	62.5	62.9
85°	32.0	32.6	33.1	33.5
87.5°	16.3	14.0	12.8	11.5
90°	36.2	22.1	14.1	6.0
92.5°	78.0	54.3	38.2	22.1
95°	156.9	124.7	88.5	62.4
97.5°	249.8	197.9	162.1	119.1
100°	299.7	249.4	215.2	169.0
102.5°	354.4	312.2	265.1	218.8
105°	452.6	400.3	346.0	293.7
107.5°	543.5	486.0	420.8	373.7
110°	601.4	539.1	470.7	428.4



TEST NUMBER: P1427799

CATALOG NUMBER: SQ2W-F-K-150U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	657.8	593.8	523.8	481.5
115°	734.2	663.8	599.4	563.2
117.5°	807.8	735.4	667.4	638.8
120°	852.9	780.5	714.1	692.0
122.5°	889.9	819.1	757.5	748.3
125°	945.4	873.0	820.7	832.8
127.5°	990.5	924.1	891.1	918.0
130°	1017.8	959.5	939.4	977.6
132.5°	1041.9	996.5	987.6	1040.3
135°	1078.2	1052.0	1060.1	1132.5
137.5°	1121.2	1111.1	1138.1	1229.4
140°	1148.6	1154.6	1192.8	1295.4
142.5°	1185.6	1199.6	1249.1	1358.2
145°	1243.1	1273.3	1337.6	1446.3
147.5°	1308.3	1347.3	1426.9	1538.4
150°	1351.7	1402.0	1486.5	1593.1
152.5°	1401.6	1453.5	1538.0	1646.2
155°	1478.4	1536.8	1625.3	1717.8
157.5°	1556.9	1616.4	1700.9	1781.8
160°	1605.2	1669.5	1746.0	1820.4
162.5°	1659.9	1719.4	1786.2	1852.6
165°	1739.9	1788.2	1842.5	1898.8
167.5°	1807.1	1847.3	1890.0	1933.8
170°	1850.6	1882.7	1919.0	1953.2
172.5°	1887.6	1913.3	1939.9	1969.2
175°	1937.1	1951.1	1967.2	1985.3
177.5°	1975.3	1980.1	1984.9	1993.0
180°	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1427799

CATALOG NUMBER: SQ2W-F-K-150U-050D-L935-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.69	14.38	14.82	15.50	17.08	13.60	14.29	14.74	15.42	16.99
	3H	15.47	16.08	16.61	17.22	18.81	15.36	15.98	16.51	17.11	18.70
	4H	16.15	16.74	17.31	17.87	19.47	16.04	16.62	17.19	17.76	19.35
	6H	16.58	17.12	17.74	18.26	19.86	16.44	16.98	17.60	18.12	19.72
	8H	16.74	17.25	17.90	18.40	20.00	16.58	17.09	17.74	18.25	19.84
	12H	16.81	17.30	17.98	18.45	20.07	16.64	17.12	17.81	18.27	19.89
4H	2H	14.25	14.83	15.41	15.97	17.56	14.18	14.77	15.34	15.90	17.50
	3H	16.25	16.74	17.42	17.90	19.51	16.16	16.65	17.33	17.81	19.42
	4H	17.06	17.51	18.23	18.66	20.29	16.95	17.40	18.12	18.55	20.17
	6H	17.60	17.99	18.78	19.16	20.78	17.46	17.85	18.63	19.02	20.63
	8H	17.81	18.17	18.98	19.34	20.97	17.65	18.01	18.82	19.18	20.81
	12H	17.92	18.24	19.11	19.42	21.06	17.73	18.06	18.92	19.23	20.87
8H	4H	17.29	17.65	18.46	18.81	20.45	17.19	17.55	18.36	18.72	20.35
	6H	17.97	18.27	19.16	19.47	21.10	17.84	18.14	19.03	19.34	20.97
	8H	18.27	18.53	19.47	19.72	21.37	18.12	18.38	19.31	19.56	21.21
	12H	18.45	18.68	19.65	19.86	21.54	18.26	18.48	19.46	19.67	21.35
12H	4H	17.27	17.60	18.46	18.78	20.41	17.18	17.51	18.37	18.68	20.32
	6H	18.02	18.28	19.22	19.46	21.11	17.89	18.15	19.09	19.34	20.99
	8H	18.34	18.57	19.55	19.75	21.44	18.19	18.42	19.39	19.60	21.28