

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427811

Luminaire Tested: SQ2W-F-K-150U-100D-L935-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1427811
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-20)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-F-K-150U-100D-L935-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - FROSTED CONTINUOUS ROLL LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9819.1 lumens
Efficiency: N/A
Efficacy: 105.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 92.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1427811

CATALOG NUMBER: SQ2W-F-K-150U-100D-L935-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1427811

CATALOG NUMBER: SQ2W-F-K-150U-100D-L935-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	91	87	84	87	83	80	77	68	66	64	55	53	52	42	41	40	34
2	87	79	73	68	79	73	67	63	60	56	53	48	45	43	37	35	33	28
3	79	70	62	57	72	64	57	52	52	48	44	42	39	36	32	30	28	24
4	72	62	54	48	66	56	49	44	46	41	37	37	34	31	29	26	24	20
5	66	55	47	41	60	50	43	38	41	36	32	33	30	26	26	23	21	18
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	21	18	15
7	56	44	36	31	51	41	34	29	34	28	24	27	23	20	21	18	16	14
8	52	40	32	27	47	37	30	25	31	25	22	25	21	18	20	17	15	12
9	48	36	29	24	44	34	27	22	28	23	19	23	19	16	18	15	13	11
10	45	33	26	21	41	31	24	20	26	21	17	21	17	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	22927	22927	22927	22927
5°	22787	23047	22787	23047
10°	22707	22969	22707	22969
15°	22582	22866	22582	22866
20°	22439	22663	22439	22663
25°	22197	22393	22197	22393
30°	21962	22111	21962	22111
35°	21681	21819	21681	21819
40°	21435	21498	21435	21498
45°	21121	21121	21121	21121
50°	20697	20747	20697	20747
55°	20211	20239	20211	20239
60°	19665	19665	19665	19665
65°	19025	18949	19025	18949
70°	18127	17938	18127	17938
75°	16905	16531	16905	16531
80°	15063	14319	15063	14319
85°	12041	10189	12041	10189

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 21262 cd/sqm



TEST NUMBER: P1427811

CATALOG NUMBER: SQ2W-F-K-150U-100D-L935-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.4	1.4
10°-20°	383.9	3.9
20°-30°	577.9	5.9
30°-40°	691.1	7.0
40°-50°	713.6	7.3
50°-60°	643.6	6.6
60°-70°	493.0	5.0
70°-80°	285.0	2.9
80°-90°	82.2	0.8
90°-100°	158.5	1.6
100°-110°	462.2	4.7
110°-120°	754.2	7.7
120°-130°	957.1	9.7
130°-140°	1024.1	10.4
140°-150°	956.3	9.7
150°-160°	786.9	8.0
160°-170°	527.7	5.4
170°-180°	187.4	1.9
0°-30°	1096.2	11.2
0°-40°	1787.2	18.2
0°-60°	3144.4	32.0
0°-90°	4004.7	40.8
90°-120°	1374.9	14.0
90°-150°	4312.4	43.9
90°-180°	5814.0	59.2
0°-180°	9819.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1420	1420	1420	1420	1420	
5°	1406	1422	1406	1422	1406	133
15°	1351	1368	1351	1368	1351	381
25°	1246	1257	1246	1257	1246	574
35°	1100	1107	1100	1107	1100	688
45°	925	925	925	925	925	713
55°	718	719	718	719	718	642
65°	498	496	498	496	498	492
75°	271	265	271	265	271	287
85°	65	55	65	55	65	76
90°	6	44	6	86	6	8
95°	62	46	62	272	62	75
105°	294	471	294	648	294	312
115°	563	780	563	962	563	555
125°	833	1237	833	1179	833	745
135°	1132	1619	1132	1306	1132	875
145°	1446	1867	1446	1334	1446	905
155°	1718	2028	1718	1384	1718	790
165°	1899	2114	1899	1593	1899	535
175°	1985	2070	1985	1869	1985	188
180°	1991	1991	1991	1991	1991	



TEST NUMBER: P1427811

CATALOG NUMBER: SQ2W-F-K-150U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0
2.5°	1412.8	1419.6	1426.3	1423.5	1417.4	1415.1	1416.5	1417.8	1418.5	1419.2	1418.5
5°	1406.0	1414.9	1423.8	1420.7	1413.6	1410.4	1411.3	1413.1	1417.6	1422.0	1417.6
7.5°	1394.6	1403.5	1412.4	1409.5	1402.8	1399.9	1401.0	1403.0	1407.6	1412.2	1407.6
10°	1385.0	1393.9	1402.8	1399.7	1392.6	1389.9	1391.7	1393.9	1397.4	1401.0	1397.4
12.5°	1373.0	1381.9	1390.8	1388.2	1381.8	1379.1	1380.2	1382.0	1385.9	1389.8	1385.9
15°	1351.0	1359.9	1368.8	1366.3	1360.1	1357.7	1359.0	1360.9	1364.4	1368.0	1364.4
17.5°	1324.4	1332.8	1341.1	1338.9	1333.1	1331.0	1332.5	1334.4	1337.5	1340.6	1337.5
20°	1306.0	1314.0	1322.0	1319.7	1313.9	1311.2	1311.7	1312.8	1315.9	1319.0	1315.9
22.5°	1283.6	1291.6	1299.6	1297.5	1292.1	1288.9	1287.9	1288.2	1292.0	1295.8	1292.0
25°	1246.0	1254.0	1262.0	1260.3	1255.4	1252.3	1251.0	1250.8	1253.9	1257.0	1253.9
27.5°	1206.8	1213.5	1220.1	1218.7	1214.6	1212.2	1211.3	1211.2	1213.4	1215.6	1213.4
30°	1178.0	1184.7	1191.3	1189.7	1185.2	1182.6	1181.7	1181.6	1183.8	1186.0	1183.8
32.5°	1147.6	1153.9	1160.2	1157.9	1152.8	1150.1	1149.9	1150.4	1153.0	1155.6	1153.0
35°	1100.0	1105.3	1110.7	1108.3	1103.4	1101.2	1101.7	1102.6	1104.8	1107.0	1104.8
37.5°	1052.2	1056.3	1060.4	1058.0	1053.5	1051.2	1051.1	1051.5	1053.3	1055.2	1053.3
40°	1017.0	1021.4	1025.9	1023.3	1018.4	1015.8	1015.3	1015.6	1017.8	1020.0	1017.8
42.5°	981.0	984.4	987.8	985.5	981.3	979.3	979.6	980.1	981.2	982.4	981.2
45°	925.0	928.1	931.2	929.0	925.0	923.0	923.0	923.2	924.1	925.0	924.1
47.5°	866.4	868.8	871.2	869.5	866.4	864.5	864.0	864.0	865.4	866.8	865.4
50°	824.0	827.1	830.2	828.7	825.6	823.6	822.7	822.4	824.2	826.0	824.2
52.5°	782.4	785.9	789.3	787.9	784.8	782.6	781.3	780.8	782.2	783.6	782.2
55°	718.0	722.0	726.0	725.0	722.3	720.1	718.3	717.2	718.1	719.0	718.1
57.5°	652.2	656.1	660.0	659.3	657.0	654.7	652.6	651.3	652.6	653.8	652.6
60°	609.0	612.6	616.1	615.0	612.3	610.1	608.3	607.2	608.1	609.0	608.1
62.5°	565.0	568.6	572.1	570.7	567.7	565.3	563.5	562.4	563.3	564.2	563.3
65°	498.0	501.1	504.2	503.0	500.3	498.1	496.3	495.1	495.6	496.0	495.6
67.5°	430.4	433.1	435.7	434.5	431.9	429.3	426.7	425.0	425.7	426.4	425.7
70°	384.0	386.7	389.3	388.3	386.1	383.9	381.7	380.0	380.0	380.0	380.0
72.5°	339.2	341.5	343.8	342.5	339.9	337.7	335.8	334.4	334.4	334.4	334.4
75°	271.0	272.3	273.7	273.0	271.7	269.9	267.7	265.9	265.4	265.0	265.4
77.5°	205.2	205.2	205.2	203.9	202.2	200.6	198.9	197.5	196.9	196.4	196.9
80°	162.0	162.0	162.0	161.0	159.7	158.3	157.0	155.8	154.9	154.0	154.9
82.5°	122.0	121.3	120.6	119.4	118.1	116.4	114.3	113.0	113.9	114.8	113.9
85°	65.0	64.1	63.2	62.0	60.7	59.1	57.3	55.9	55.4	55.0	55.4
87.5°	21.2	22.1	23.4	24.0	24.2	23.3	21.9	21.2	21.2	20.9	21.2
90°	6.0	14.1	24.1	32.2	38.2	40.2	40.2	42.2	44.3	44.3	44.3
92.5°	22.1	35.0	35.4	35.4	43.0	46.7	49.9	50.3	52.3	52.3	52.3
95°	62.4	68.4	102.6	100.6	68.4	54.3	46.3	46.3	46.3	46.3	46.3
97.5°	119.1	127.9	133.6	179.0	189.1	182.6	148.8	125.1	111.8	105.8	111.8
100°	169.0	173.0	185.1	187.1	237.4	285.6	261.5	231.3	221.3	215.2	221.3
102.5°	218.8	221.3	239.8	248.2	259.9	287.2	370.9	361.7	354.8	353.6	354.8
105°	293.7	295.7	329.9	346.0	354.0	354.0	352.0	392.2	456.6	470.7	456.6
107.5°	373.7	383.0	423.2	466.3	475.5	477.9	467.5	461.4	459.0	460.6	459.0
110°	428.4	442.5	490.8	545.1	559.2	563.2	559.2	553.2	549.1	549.1	549.1



TEST NUMBER: P1427811

CATALOG NUMBER: SQ2W-F-K-150U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	481.5	502.1	556.8	619.1	642.9	654.9	646.1	641.7	637.6	640.9	637.6
115°	563.2	593.4	665.8	730.2	778.4	784.5	782.5	782.5	780.5	780.5	780.5
117.5°	638.8	687.1	768.4	843.2	899.1	915.2	923.3	920.9	918.4	922.5	918.4
120°	692.0	748.3	840.8	925.3	979.6	1003.7	1011.8	1007.8	1011.8	1007.8	1011.8
122.5°	748.3	817.5	908.4	996.1	1060.1	1087.4	1097.1	1097.9	1098.7	1096.3	1098.7
125°	832.8	917.2	1023.8	1114.4	1180.7	1212.9	1221.0	1223.0	1227.0	1237.1	1227.0
127.5°	918.0	1013.8	1130.9	1218.2	1286.1	1325.2	1337.6	1342.1	1350.5	1354.9	1350.5
130°	977.6	1086.2	1204.9	1287.3	1353.7	1396.0	1418.1	1424.1	1434.2	1432.2	1434.2
132.5°	1040.3	1153.8	1274.1	1359.8	1421.3	1466.8	1485.7	1503.0	1506.6	1509.4	1506.6
135°	1132.5	1255.2	1375.9	1460.3	1518.7	1562.9	1587.1	1603.2	1613.2	1619.2	1613.2
137.5°	1229.4	1359.0	1474.8	1550.0	1608.8	1647.0	1674.4	1691.3	1701.7	1706.5	1701.7
140°	1295.4	1420.1	1532.8	1611.2	1663.5	1701.7	1725.9	1746.0	1758.0	1758.0	1758.0
142.5°	1358.2	1481.3	1590.7	1669.1	1715.0	1750.0	1775.7	1791.0	1804.7	1804.7	1804.7
145°	1446.3	1569.0	1669.5	1748.0	1786.2	1818.4	1846.5	1858.6	1866.7	1866.7	1866.7
147.5°	1538.4	1647.0	1738.7	1814.0	1846.1	1884.0	1906.1	1915.7	1925.8	1921.4	1925.8
150°	1593.1	1693.7	1782.2	1852.6	1884.8	1921.0	1943.1	1951.1	1961.2	1955.2	1961.2
152.5°	1646.2	1741.9	1822.4	1888.0	1915.3	1951.5	1976.9	1984.9	1991.8	1987.3	1991.8
155°	1717.8	1802.3	1876.7	1937.1	1961.2	1995.4	2019.5	2029.6	2037.6	2027.6	2037.6
157.5°	1781.8	1854.6	1919.4	1974.9	2000.6	2030.0	2052.5	2065.0	2073.0	2068.6	2073.0
160°	1820.4	1886.8	1945.1	1997.4	2021.5	2047.7	2071.8	2085.9	2094.0	2087.9	2094.0
162.5°	1852.6	1912.5	1967.6	2015.1	2036.0	2059.0	2087.9	2100.4	2108.4	2100.8	2108.4
165°	1898.8	1947.1	1995.4	2035.6	2053.7	2071.8	2102.0	2116.1	2122.1	2114.1	2122.1
167.5°	1933.8	1970.9	2009.9	2044.5	2057.7	2075.4	2105.6	2117.3	2124.9	2114.9	2124.9
170°	1953.2	1985.3	2019.5	2047.7	2057.7	2073.8	2104.0	2114.1	2120.1	2110.0	2120.1
172.5°	1969.2	1993.4	2021.1	2046.1	2051.3	2064.2	2092.7	2102.8	2107.2	2098.8	2107.2
175°	1985.3	1999.4	2019.5	2035.6	2033.6	2041.7	2065.8	2073.8	2081.9	2069.8	2081.9
177.5°	1993.0	1999.4	2005.9	2015.5	2009.1	2009.1	2026.8	2031.6	2033.2	2026.8	2033.2
180°	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1427811

CATALOG NUMBER: SQ2W-F-K-150U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0
2.5°	1417.8	1416.5	1415.1	1417.4	1423.5	1426.3	1419.6	1412.8	1419.6	1426.3	1423.5
5°	1413.1	1411.3	1410.4	1413.6	1420.7	1423.8	1414.9	1406.0	1414.9	1423.8	1420.7
7.5°	1403.0	1401.0	1399.9	1402.8	1409.5	1412.4	1403.5	1394.6	1403.5	1412.4	1409.5
10°	1393.9	1391.7	1389.9	1392.6	1399.7	1402.8	1393.9	1385.0	1393.9	1402.8	1399.7
12.5°	1382.0	1380.2	1379.1	1381.8	1388.2	1390.8	1381.9	1373.0	1381.9	1390.8	1388.2
15°	1360.9	1359.0	1357.7	1360.1	1366.3	1368.8	1359.9	1351.0	1359.9	1368.8	1366.3
17.5°	1334.4	1332.5	1331.0	1333.1	1338.9	1341.1	1332.8	1324.4	1332.8	1341.1	1338.9
20°	1312.8	1311.7	1311.2	1313.9	1319.7	1322.0	1314.0	1306.0	1314.0	1322.0	1319.7
22.5°	1288.2	1287.9	1288.9	1292.1	1297.5	1299.6	1291.6	1283.6	1291.6	1299.6	1297.5
25°	1250.8	1251.0	1252.3	1255.4	1260.3	1262.0	1254.0	1246.0	1254.0	1262.0	1260.3
27.5°	1211.2	1211.3	1212.2	1214.6	1218.7	1220.1	1213.5	1206.8	1213.5	1220.1	1218.7
30°	1181.6	1181.7	1182.6	1185.2	1189.7	1191.3	1184.7	1178.0	1184.7	1191.3	1189.7
32.5°	1150.4	1149.9	1150.1	1152.8	1157.9	1160.2	1153.9	1147.6	1153.9	1160.2	1157.9
35°	1102.6	1101.7	1101.2	1103.4	1108.3	1110.7	1105.3	1100.0	1105.3	1110.7	1108.3
37.5°	1051.5	1051.1	1051.2	1053.5	1058.0	1060.4	1056.3	1052.2	1056.3	1060.4	1058.0
40°	1015.6	1015.3	1015.8	1018.4	1023.3	1025.9	1021.4	1017.0	1021.4	1025.9	1023.3
42.5°	980.1	979.6	979.3	981.3	985.5	987.8	984.4	981.0	984.4	987.8	985.5
45°	923.2	923.0	923.0	925.0	929.0	931.2	928.1	925.0	928.1	931.2	929.0
47.5°	864.0	864.0	864.5	866.4	869.5	871.2	868.8	866.4	868.8	871.2	869.5
50°	822.4	822.7	823.6	825.6	828.7	830.2	827.1	824.0	827.1	830.2	828.7
52.5°	780.8	781.3	782.6	784.8	787.9	789.3	785.9	782.4	785.9	789.3	787.9
55°	717.2	718.3	720.1	722.3	725.0	726.0	722.0	718.0	722.0	726.0	725.0
57.5°	651.3	652.6	654.7	657.0	659.3	660.0	656.1	652.2	656.1	660.0	659.3
60°	607.2	608.3	610.1	612.3	615.0	616.1	612.6	609.0	612.6	616.1	615.0
62.5°	562.4	563.5	565.3	567.7	570.7	572.1	568.6	565.0	568.6	572.1	570.7
65°	495.1	496.3	498.1	500.3	503.0	504.2	501.1	498.0	501.1	504.2	503.0
67.5°	425.0	426.7	429.3	431.9	434.5	435.7	433.1	430.4	433.1	435.7	434.5
70°	380.0	381.7	383.9	386.1	388.3	389.3	386.7	384.0	386.7	389.3	388.3
72.5°	334.4	335.8	337.7	339.9	342.5	343.8	341.5	339.2	341.5	343.8	342.5
75°	265.9	267.7	269.9	271.7	273.0	273.7	272.3	271.0	272.3	273.7	273.0
77.5°	197.5	198.9	200.6	202.2	203.9	205.2	205.2	205.2	205.2	205.2	203.9
80°	155.8	157.0	158.3	159.7	161.0	162.0	162.0	162.0	162.0	162.0	161.0
82.5°	113.0	114.3	116.4	118.1	119.4	120.6	121.3	122.0	121.3	120.6	119.4
85°	55.9	57.3	59.1	60.7	62.0	63.2	64.1	65.0	64.1	63.2	62.0
87.5°	21.2	21.9	23.3	24.2	24.0	23.4	22.1	21.2	22.1	23.0	24.8
90°	42.2	40.2	40.2	38.2	32.2	24.1	14.1	6.0	14.1	22.1	36.2
92.5°	50.3	49.9	46.7	43.0	35.4	35.4	35.0	22.1	38.2	54.3	78.0
95°	46.3	46.3	54.3	68.4	100.6	102.6	68.4	62.4	88.5	124.7	156.9
97.5°	125.1	148.8	182.6	189.1	179.0	133.6	127.9	119.1	162.1	197.9	249.8
100°	231.3	261.5	285.6	237.4	187.1	185.1	173.0	169.0	215.2	249.4	299.7
102.5°	361.7	370.9	287.2	259.9	248.2	239.8	221.3	218.8	265.1	312.2	354.4
105°	392.2	352.0	354.0	354.0	346.0	329.9	295.7	293.7	346.0	400.3	452.6
107.5°	461.4	467.5	477.9	475.5	466.3	423.2	383.0	373.7	420.8	486.0	543.5
110°	553.2	559.2	563.2	559.2	545.1	490.8	442.5	428.4	470.7	539.1	601.4



TEST NUMBER: P1427811

CATALOG NUMBER: SQ2W-F-K-150U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	641.7	646.1	654.9	642.9	619.1	556.8	502.1	481.5	523.8	593.8	657.8
115°	782.5	782.5	784.5	778.4	730.2	665.8	593.4	563.2	599.4	663.8	734.2
117.5°	920.9	923.3	915.2	899.1	843.2	768.4	687.1	638.8	667.4	735.4	807.8
120°	1007.8	1011.8	1003.7	979.6	925.3	840.8	748.3	692.0	714.1	780.5	852.9
122.5°	1097.9	1097.1	1087.4	1060.1	996.1	908.4	817.5	748.3	757.5	819.1	889.9
125°	1223.0	1221.0	1212.9	1180.7	1114.4	1023.8	917.2	832.8	820.7	873.0	945.4
127.5°	1342.1	1337.6	1325.2	1286.1	1218.2	1130.9	1013.8	918.0	891.1	924.1	990.5
130°	1424.1	1418.1	1396.0	1353.7	1287.3	1204.9	1086.2	977.6	939.4	959.5	1017.8
132.5°	1503.0	1485.7	1466.8	1421.3	1359.8	1274.1	1153.8	1040.3	987.6	996.5	1041.9
135°	1603.2	1587.1	1562.9	1518.7	1460.3	1375.9	1255.2	1132.5	1060.1	1052.0	1078.2
137.5°	1691.3	1674.4	1647.0	1608.8	1550.0	1474.8	1359.0	1229.4	1138.1	1111.1	1121.2
140°	1746.0	1725.9	1701.7	1663.5	1611.2	1532.8	1420.1	1295.4	1192.8	1154.6	1148.6
142.5°	1791.0	1775.7	1750.0	1715.0	1669.1	1590.7	1481.3	1358.2	1249.1	1199.6	1185.6
145°	1858.6	1846.5	1818.4	1786.2	1748.0	1669.5	1569.0	1446.3	1337.6	1273.3	1243.1
147.5°	1915.7	1906.1	1884.0	1846.1	1814.0	1738.7	1647.0	1538.4	1426.9	1347.3	1308.3
150°	1951.1	1943.1	1921.0	1884.8	1852.6	1782.2	1693.7	1593.1	1486.5	1402.0	1351.7
152.5°	1984.9	1976.9	1951.5	1915.3	1888.0	1822.4	1741.9	1646.2	1538.0	1453.5	1401.6
155°	2029.6	2019.5	1995.4	1961.2	1937.1	1876.7	1802.3	1717.8	1625.3	1536.8	1478.4
157.5°	2065.0	2052.5	2030.0	2000.6	1974.9	1919.4	1854.6	1781.8	1700.9	1616.4	1556.9
160°	2085.9	2071.8	2047.7	2021.5	1997.4	1945.1	1886.8	1820.4	1746.0	1669.5	1605.2
162.5°	2100.4	2087.9	2059.0	2036.0	2015.1	1967.6	1912.5	1852.6	1786.2	1719.4	1659.9
165°	2116.1	2102.0	2071.8	2053.7	2035.6	1995.4	1947.1	1898.8	1842.5	1788.2	1739.9
167.5°	2117.3	2105.6	2075.4	2057.7	2044.5	2009.9	1970.9	1933.8	1890.0	1847.3	1807.1
170°	2114.1	2104.0	2073.8	2057.7	2047.7	2019.5	1985.3	1953.2	1919.0	1882.7	1850.6
172.5°	2102.8	2092.7	2064.2	2051.3	2046.1	2021.1	1993.4	1969.2	1939.9	1913.3	1887.6
175°	2073.8	2065.8	2041.7	2033.6	2035.6	2019.5	1999.4	1985.3	1967.2	1951.1	1937.1
177.5°	2031.6	2026.8	2009.1	2009.1	2015.5	2005.9	1999.4	1993.0	1984.9	1980.1	1975.3
180°	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1427811

CATALOG NUMBER: SQ2W-F-K-150U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0
2.5°	1417.4	1415.1	1416.5	1417.8	1418.5	1419.2	1418.5	1417.8	1416.5	1415.1	1417.4
5°	1413.6	1410.4	1411.3	1413.1	1417.6	1422.0	1417.6	1413.1	1411.3	1410.4	1413.6
7.5°	1402.8	1399.9	1401.0	1403.0	1407.6	1412.2	1407.6	1403.0	1401.0	1399.9	1402.8
10°	1392.6	1389.9	1391.7	1393.9	1397.4	1401.0	1397.4	1393.9	1391.7	1389.9	1392.6
12.5°	1381.8	1379.1	1380.2	1382.0	1385.9	1389.8	1385.9	1382.0	1380.2	1379.1	1381.8
15°	1360.1	1357.7	1359.0	1360.9	1364.4	1368.0	1364.4	1360.9	1359.0	1357.7	1360.1
17.5°	1333.1	1331.0	1332.5	1334.4	1337.5	1340.6	1337.5	1334.4	1332.5	1331.0	1333.1
20°	1313.9	1311.2	1311.7	1312.8	1315.9	1319.0	1315.9	1312.8	1311.7	1311.2	1313.9
22.5°	1292.1	1288.9	1287.9	1288.2	1292.0	1295.8	1292.0	1288.2	1287.9	1288.9	1292.1
25°	1255.4	1252.3	1251.0	1250.8	1253.9	1257.0	1253.9	1250.8	1251.0	1252.3	1255.4
27.5°	1214.6	1212.2	1211.3	1211.2	1213.4	1215.6	1213.4	1211.2	1211.3	1212.2	1214.6
30°	1185.2	1182.6	1181.7	1181.6	1183.8	1186.0	1183.8	1181.6	1181.7	1182.6	1185.2
32.5°	1152.8	1150.1	1149.9	1150.4	1153.0	1155.6	1153.0	1150.4	1149.9	1150.1	1152.8
35°	1103.4	1101.2	1101.7	1102.6	1104.8	1107.0	1104.8	1102.6	1101.7	1101.2	1103.4
37.5°	1053.5	1051.2	1051.1	1051.5	1053.3	1055.2	1053.3	1051.5	1051.1	1051.2	1053.5
40°	1018.4	1015.8	1015.3	1015.6	1017.8	1020.0	1017.8	1015.6	1015.3	1015.8	1018.4
42.5°	981.3	979.3	979.6	980.1	981.2	982.4	981.2	980.1	979.6	979.3	981.3
45°	925.0	923.0	923.0	923.2	924.1	925.0	924.1	923.2	923.0	923.0	925.0
47.5°	866.4	864.5	864.0	864.0	865.4	866.8	865.4	864.0	864.0	864.5	866.4
50°	825.6	823.6	822.7	822.4	824.2	826.0	824.2	822.4	822.7	823.6	825.6
52.5°	784.8	782.6	781.3	780.8	782.2	783.6	782.2	780.8	781.3	782.6	784.8
55°	722.3	720.1	718.3	717.2	718.1	719.0	718.1	717.2	718.3	720.1	722.3
57.5°	657.0	654.7	652.6	651.3	652.6	653.8	652.6	651.3	652.6	654.7	657.0
60°	612.3	610.1	608.3	607.2	608.1	609.0	608.1	607.2	608.3	610.1	612.3
62.5°	567.7	565.3	563.5	562.4	563.3	564.2	563.3	562.4	563.5	565.3	567.7
65°	500.3	498.1	496.3	495.1	495.6	496.0	495.6	495.1	496.3	498.1	500.3
67.5°	431.9	429.3	426.7	425.0	425.7	426.4	425.7	425.0	426.7	429.3	431.9
70°	386.1	383.9	381.7	380.0	380.0	380.0	380.0	380.0	381.7	383.9	386.1
72.5°	339.9	337.7	335.8	334.4	334.4	334.4	334.4	334.4	335.8	337.7	339.9
75°	271.7	269.9	267.7	265.9	265.4	265.0	265.4	265.9	267.7	269.9	271.7
77.5°	202.2	200.6	198.9	197.5	196.9	196.4	196.9	197.5	198.9	200.6	202.2
80°	159.7	158.3	157.0	155.8	154.9	154.0	154.9	155.8	157.0	158.3	159.7
82.5°	118.1	116.4	114.3	113.0	113.9	114.8	113.9	113.0	114.3	116.4	118.1
85°	60.7	59.1	57.3	55.9	55.4	55.0	55.4	55.9	57.3	59.1	60.7
87.5°	25.8	27.4	28.8	29.2	30.5	29.3	30.5	29.2	28.8	27.4	25.8
90°	46.3	60.3	74.4	82.5	90.5	86.5	90.5	82.5	74.4	60.3	46.3
92.5°	92.9	116.7	134.0	148.4	154.9	154.1	154.9	148.4	134.0	116.7	92.9
95°	187.1	215.2	243.4	263.5	275.6	271.6	275.6	263.5	243.4	215.2	187.1
97.5°	288.4	326.3	357.6	376.5	388.6	396.7	388.6	376.5	357.6	326.3	288.4
100°	356.0	392.2	428.4	450.6	470.7	478.7	470.7	450.6	428.4	392.2	356.0
102.5°	410.7	458.2	497.6	521.4	538.3	546.3	538.3	521.4	497.6	458.2	410.7
105°	500.9	551.1	593.4	623.6	641.7	647.7	641.7	623.6	593.4	551.1	500.9
107.5°	591.0	642.9	681.9	715.3	737.4	750.3	737.4	715.3	681.9	642.9	591.0
110°	661.8	704.0	746.3	776.4	798.6	806.6	798.6	776.4	746.3	704.0	661.8



TEST NUMBER: P1427811

CATALOG NUMBER: SQ2W-F-K-150U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	721.3	768.4	810.6	840.8	866.1	877.4	866.1	840.8	810.6	768.4	721.3
115°	804.6	866.9	905.2	933.3	951.4	961.5	951.4	933.3	905.2	866.9	804.6
117.5°	873.8	939.0	980.8	1002.5	1011.0	1018.2	1011.0	1002.5	980.8	939.0	873.8
120°	917.2	977.6	1025.9	1054.0	1064.1	1068.1	1064.1	1054.0	1025.9	977.6	917.2
122.5°	957.5	1014.6	1061.3	1095.9	1112.4	1116.4	1112.4	1095.9	1061.3	1014.6	957.5
125°	1013.8	1068.1	1116.4	1150.6	1168.7	1178.7	1168.7	1150.6	1116.4	1068.1	1013.8
127.5°	1062.9	1121.6	1165.9	1196.8	1214.5	1222.6	1214.5	1196.8	1165.9	1121.6	1062.9
130°	1090.2	1150.6	1194.8	1229.0	1245.1	1253.2	1245.1	1229.0	1194.8	1150.6	1090.2
132.5°	1111.1	1174.7	1220.6	1251.5	1269.2	1277.3	1269.2	1251.5	1220.6	1174.7	1111.1
135°	1136.5	1202.9	1251.1	1281.3	1297.4	1305.5	1297.4	1281.3	1251.1	1202.9	1136.5
137.5°	1158.6	1219.0	1269.2	1301.0	1315.5	1320.7	1315.5	1301.0	1269.2	1219.0	1158.6
140°	1174.7	1227.0	1277.3	1307.5	1323.6	1325.6	1323.6	1307.5	1277.3	1227.0	1174.7
142.5°	1195.6	1236.7	1280.5	1310.7	1326.8	1330.4	1326.8	1310.7	1280.5	1236.7	1195.6
145°	1233.0	1257.2	1287.3	1315.5	1329.6	1333.6	1329.6	1315.5	1287.3	1257.2	1233.0
147.5°	1280.1	1287.8	1303.4	1321.9	1335.6	1338.4	1335.6	1321.9	1303.4	1287.8	1280.1
150°	1315.5	1313.5	1319.5	1331.6	1343.7	1341.7	1343.7	1331.6	1319.5	1313.5	1315.5
152.5°	1355.7	1344.1	1343.7	1349.3	1354.9	1354.5	1354.9	1349.3	1343.7	1344.1	1355.7
155°	1424.1	1402.0	1389.9	1385.9	1385.9	1383.9	1385.9	1385.9	1389.9	1402.0	1424.1
157.5°	1499.4	1468.4	1450.3	1440.6	1437.8	1433.4	1437.8	1440.6	1450.3	1468.4	1499.4
160°	1550.9	1516.7	1498.6	1482.5	1476.4	1470.4	1476.4	1482.5	1498.6	1516.7	1550.9
162.5°	1599.1	1566.5	1546.8	1532.3	1526.3	1517.1	1526.3	1532.3	1546.8	1566.5	1599.1
165°	1677.6	1643.4	1621.3	1609.2	1601.1	1593.1	1601.1	1609.2	1621.3	1643.4	1677.6
167.5°	1756.0	1718.6	1704.1	1690.5	1682.8	1668.3	1682.8	1690.5	1704.1	1718.6	1756.0
170°	1804.3	1770.1	1762.1	1750.0	1735.9	1719.8	1735.9	1750.0	1762.1	1770.1	1804.3
172.5°	1846.1	1823.2	1815.2	1803.1	1798.7	1785.8	1798.7	1803.1	1815.2	1823.2	1846.1
175°	1906.9	1888.8	1888.8	1886.8	1880.7	1868.7	1880.7	1886.8	1888.8	1888.8	1906.9
177.5°	1957.6	1947.9	1954.4	1954.4	1952.7	1941.5	1952.7	1954.4	1954.4	1947.9	1957.6
180°	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1427811

CATALOG NUMBER: SQ2W-F-K-150U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1420.0	1420.0	1420.0	1420.0
2.5°	1423.5	1426.3	1419.6	1412.8
5°	1420.7	1423.8	1414.9	1406.0
7.5°	1409.5	1412.4	1403.5	1394.6
10°	1399.7	1402.8	1393.9	1385.0
12.5°	1388.2	1390.8	1381.9	1373.0
15°	1366.3	1368.8	1359.9	1351.0
17.5°	1338.9	1341.1	1332.8	1324.4
20°	1319.7	1322.0	1314.0	1306.0
22.5°	1297.5	1299.6	1291.6	1283.6
25°	1260.3	1262.0	1254.0	1246.0
27.5°	1218.7	1220.1	1213.5	1206.8
30°	1189.7	1191.3	1184.7	1178.0
32.5°	1157.9	1160.2	1153.9	1147.6
35°	1108.3	1110.7	1105.3	1100.0
37.5°	1058.0	1060.4	1056.3	1052.2
40°	1023.3	1025.9	1021.4	1017.0
42.5°	985.5	987.8	984.4	981.0
45°	929.0	931.2	928.1	925.0
47.5°	869.5	871.2	868.8	866.4
50°	828.7	830.2	827.1	824.0
52.5°	787.9	789.3	785.9	782.4
55°	725.0	726.0	722.0	718.0
57.5°	659.3	660.0	656.1	652.2
60°	615.0	616.1	612.6	609.0
62.5°	570.7	572.1	568.6	565.0
65°	503.0	504.2	501.1	498.0
67.5°	434.5	435.7	433.1	430.4
70°	388.3	389.3	386.7	384.0
72.5°	342.5	343.8	341.5	339.2
75°	273.0	273.7	272.3	271.0
77.5°	203.9	205.2	205.2	205.2
80°	161.0	162.0	162.0	162.0
82.5°	119.4	120.6	121.3	122.0
85°	62.0	63.2	64.1	65.0
87.5°	24.8	23.0	22.1	21.2
90°	36.2	22.1	14.1	6.0
92.5°	78.0	54.3	38.2	22.1
95°	156.9	124.7	88.5	62.4
97.5°	249.8	197.9	162.1	119.1
100°	299.7	249.4	215.2	169.0
102.5°	354.4	312.2	265.1	218.8
105°	452.6	400.3	346.0	293.7
107.5°	543.5	486.0	420.8	373.7
110°	601.4	539.1	470.7	428.4



TEST NUMBER: P1427811

CATALOG NUMBER: SQ2W-F-K-150U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	657.8	593.8	523.8	481.5
115°	734.2	663.8	599.4	563.2
117.5°	807.8	735.4	667.4	638.8
120°	852.9	780.5	714.1	692.0
122.5°	889.9	819.1	757.5	748.3
125°	945.4	873.0	820.7	832.8
127.5°	990.5	924.1	891.1	918.0
130°	1017.8	959.5	939.4	977.6
132.5°	1041.9	996.5	987.6	1040.3
135°	1078.2	1052.0	1060.1	1132.5
137.5°	1121.2	1111.1	1138.1	1229.4
140°	1148.6	1154.6	1192.8	1295.4
142.5°	1185.6	1199.6	1249.1	1358.2
145°	1243.1	1273.3	1337.6	1446.3
147.5°	1308.3	1347.3	1426.9	1538.4
150°	1351.7	1402.0	1486.5	1593.1
152.5°	1401.6	1453.5	1538.0	1646.2
155°	1478.4	1536.8	1625.3	1717.8
157.5°	1556.9	1616.4	1700.9	1781.8
160°	1605.2	1669.5	1746.0	1820.4
162.5°	1659.9	1719.4	1786.2	1852.6
165°	1739.9	1788.2	1842.5	1898.8
167.5°	1807.1	1847.3	1890.0	1933.8
170°	1850.6	1882.7	1919.0	1953.2
172.5°	1887.6	1913.3	1939.9	1969.2
175°	1937.1	1951.1	1967.2	1985.3
177.5°	1975.3	1980.1	1984.9	1993.0
180°	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1427811
 CATALOG NUMBER: SQ2W-F-K-150U-100D-L935-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.83	18.62	18.86	19.66	21.06	17.74	18.54	18.77	19.58	20.97
	3H	19.61	20.33	20.65	21.37	22.79	19.51	20.22	20.55	21.27	22.69
	4H	20.31	20.98	21.36	22.03	23.45	20.19	20.87	21.24	21.92	23.34
	6H	20.74	21.36	21.80	22.42	23.85	20.60	21.22	21.66	22.27	23.71
	8H	20.90	21.49	21.97	22.56	23.99	20.74	21.33	21.81	22.40	23.83
	12H	20.98	21.54	22.05	22.61	24.06	20.80	21.37	21.88	22.43	23.88
4H	2H	18.40	19.08	19.46	20.13	21.55	18.33	19.01	19.39	20.06	21.48
	3H	20.42	20.98	21.48	22.06	23.49	20.32	20.89	21.39	21.96	23.40
	4H	21.23	21.74	22.30	22.81	24.27	21.12	21.63	22.19	22.70	24.16
	6H	21.78	22.22	22.86	23.31	24.76	21.63	22.08	22.72	23.17	24.62
	8H	21.99	22.40	23.07	23.49	24.96	21.83	22.24	22.91	23.33	24.80
	12H	22.10	22.48	23.20	23.57	25.05	21.91	22.29	23.01	23.39	24.86
8H	4H	21.47	21.88	22.55	22.97	24.43	21.37	21.78	22.45	22.87	24.34
	6H	22.15	22.50	23.26	23.62	25.09	22.02	22.36	23.13	23.49	24.96
	8H	22.46	22.76	23.57	23.87	25.35	22.30	22.60	23.41	23.71	25.19
	12H	22.64	22.90	23.75	24.01	25.53	22.45	22.71	23.56	23.81	25.34
12H	4H	21.46	21.83	22.56	22.93	24.40	21.36	21.74	22.46	22.84	24.31
	6H	22.20	22.50	23.31	23.61	25.10	22.08	22.38	23.19	23.49	24.97
	8H	22.53	22.80	23.65	23.90	25.42	22.38	22.65	23.50	23.75	25.27