

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1435779

Luminaire Tested: SQ2W-FA-K-050U-100D-L935-UNV-STD-W-WM-4

Issue Date: 3/24/2026

Test Information

Test Method: LM-79-2024
Report Number: P1435779
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2502-345-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/24/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-FA-K-050U-100D-L935-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - FROSTED CONTINUOUS ASYMMETRIC ROLL LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5652.8 lumens
Efficiency: N/A
Efficacy: 107.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.23 / 1.34
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 52.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1435779

CATALOG NUMBER: SQ2W-FA-K-050U-100D-L935-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1435779

CATALOG NUMBER: SQ2W-FA-K-050U-100D-L935-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	92	92	92	81	81	81	71	71	71	66
1	102	97	93	90	96	92	88	85	81	79	76	72	70	68	63	62	60	56
2	93	85	79	74	87	80	75	70	71	67	63	63	60	57	56	53	51	47
3	85	75	67	61	79	71	64	59	63	58	53	56	52	48	49	46	43	40
4	77	66	58	52	73	63	55	50	56	50	46	50	45	41	44	40	37	34
5	71	59	51	45	67	56	48	43	50	44	39	45	40	36	40	36	33	30
6	66	53	45	39	62	50	43	37	45	39	34	41	35	32	36	32	29	26
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	26	23
8	56	44	36	30	53	42	34	29	38	31	27	34	29	25	30	26	23	21
9	53	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	21	19
10	49	37	29	24	46	35	28	24	32	26	22	29	24	20	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	24377	24377	24377	24377
5°	24090	25228	24090	20107
10°	23985	25520	23985	18229
15°	23573	25725	23573	20150
20°	22924	25539	22924	21013
25°	21787	25332	21787	21267
30°	20073	24766	20073	21492
35°	17763	24222	17763	21108
40°	15293	23557	15293	21338
45°	15100	22715	15100	21379
50°	14405	21607	14405	21461
55°	14331	19932	14331	21250
60°	12849	17763	12849	21164
65°	10953	15648	10953	20569
70°	8842	13260	8842	19062
75°	7667	10954	7667	17523
80°	6527	8164	6527	14142
85°	4335	4335	4335	8670

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 40°
 Vertical Angle: 45°
 Luminance: 23427 cd/sqm



TEST NUMBER: P1435779

CATALOG NUMBER: SQ2W-FA-K-050U-100D-L935-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.8	2.4
10°-20°	379.6	6.7
20°-30°	576.4	10.2
30°-40°	676.8	12.0
40°-50°	686.8	12.1
50°-60°	601.6	10.6
60°-70°	426.7	7.5
70°-80°	219.7	3.9
80°-90°	48.8	0.9
90°-100°	51.8	0.9
100°-110°	151.1	2.7
110°-120°	246.5	4.4
120°-130°	312.9	5.5
130°-140°	334.8	5.9
140°-150°	312.6	5.5
150°-160°	257.2	4.6
160°-170°	172.5	3.1
170°-180°	61.3	1.1
0°-30°	1091.9	19.3
0°-40°	1768.6	31.3
0°-60°	3057.0	54.1
0°-90°	3752.1	66.4
90°-120°	449.4	8.0
90°-150°	1409.7	24.9
90°-180°	1901.0	33.6
0°-180°	5652.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1510	1510	1510	1510	1510	
5°	1486	1557	1486	1241	1486	141
15°	1410	1539	1410	1206	1410	396
25°	1223	1422	1223	1194	1223	558
35°	901	1229	901	1071	901	561
45°	661	995	661	936	661	506
55°	509	708	509	755	509	440
65°	287	410	287	538	287	286
75°	123	176	123	281	123	133
85°	23	23	23	47	23	29
90°	2	14	2	28	2	2
95°	20	15	20	89	20	25
105°	96	154	96	212	96	102
115°	184	255	184	314	184	181
125°	272	404	272	385	272	244
135°	370	529	370	427	370	286
145°	473	610	473	436	473	296
155°	562	663	562	452	562	258
165°	621	691	621	521	621	175
175°	649	677	649	611	649	62
180°	651	651	651	651	651	



TEST NUMBER: P1435779

CATALOG NUMBER: SQ2W-FA-K-050U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1509.8	1509.8	1509.8	1509.8	1509.8	1509.8	1509.8	1509.8	1509.8	1509.8	1509.8
2.5°	1500.4	1510.8	1521.2	1523.8	1523.8	1523.8	1523.8	1523.8	1523.8	1523.8	1523.8
5°	1486.4	1504.6	1522.8	1531.2	1536.4	1540.3	1542.9	1546.2	1551.4	1556.6	1551.4
7.5°	1472.3	1496.8	1521.2	1533.2	1541.0	1547.2	1551.9	1556.1	1558.7	1561.3	1558.7
10°	1463.0	1491.6	1520.2	1533.2	1541.0	1546.2	1548.8	1551.4	1554.0	1556.6	1554.0
12.5°	1448.9	1479.6	1510.3	1525.4	1535.3	1541.5	1544.1	1546.7	1549.3	1551.9	1549.3
15°	1410.3	1451.9	1493.5	1509.8	1517.6	1524.1	1529.3	1533.8	1536.4	1539.0	1536.4
17.5°	1362.3	1412.8	1463.2	1483.6	1494.0	1501.6	1506.3	1510.3	1512.4	1514.5	1512.4
20°	1334.2	1388.8	1443.5	1464.9	1475.3	1481.8	1484.4	1486.4	1486.4	1486.4	1486.4
22.5°	1296.8	1357.6	1418.5	1441.5	1451.9	1457.4	1457.9	1458.8	1460.9	1463.0	1460.9
25°	1223.0	1293.3	1363.5	1392.7	1408.3	1414.8	1412.2	1411.6	1416.8	1422.0	1416.8
27.5°	1132.9	1221.3	1309.8	1339.7	1350.1	1356.6	1359.2	1361.1	1361.1	1361.1	1361.1
30°	1076.7	1175.6	1274.4	1306.9	1317.3	1323.8	1326.4	1328.4	1328.4	1328.4	1328.4
32.5°	1006.5	1124.1	1241.6	1277.3	1285.6	1290.0	1290.5	1290.9	1290.9	1290.9	1290.9
35°	901.2	1044.2	1187.3	1226.9	1232.1	1234.7	1234.7	1234.1	1231.5	1228.9	1231.5
37.5°	795.9	958.1	1120.4	1166.9	1174.7	1176.7	1173.1	1169.7	1167.1	1164.5	1167.1
40°	725.6	902.5	1079.3	1129.4	1137.2	1137.2	1129.4	1122.9	1120.3	1117.7	1120.3
42.5°	688.2	863.0	1037.7	1087.3	1095.1	1094.0	1084.2	1076.1	1073.5	1070.9	1073.5
45°	661.3	817.3	973.4	1018.2	1026.0	1024.7	1014.3	1005.2	1000.0	994.8	1000.0
47.5°	620.3	757.6	894.9	939.0	952.0	950.7	935.1	922.1	916.9	911.7	916.9
50°	573.5	708.7	844.0	887.5	900.5	899.2	883.6	870.6	865.4	860.2	865.4
52.5°	540.7	667.6	794.6	834.5	845.4	842.0	824.3	809.8	804.6	799.4	804.6
55°	509.1	615.7	722.4	754.9	762.7	757.5	739.3	723.7	715.9	708.1	715.9
57.5°	435.4	536.8	638.2	669.8	678.2	671.9	651.1	633.3	624.5	615.6	624.5
60°	397.9	489.0	580.0	610.5	620.9	615.7	594.9	576.1	563.1	550.1	563.1
62.5°	355.8	436.4	517.0	548.1	562.7	559.6	538.8	519.9	506.9	493.9	506.9
65°	286.7	357.0	427.2	458.4	476.6	475.3	454.5	435.6	422.6	409.6	422.6
67.5°	224.7	285.1	345.4	376.1	396.9	395.8	373.0	353.2	342.8	332.4	342.8
70°	187.3	239.3	291.3	319.9	340.7	340.7	319.9	301.7	291.3	280.9	291.3
72.5°	163.9	203.4	242.9	270.0	292.9	292.9	270.0	250.7	242.4	234.1	242.4
75°	122.9	146.3	169.7	195.1	221.1	223.7	202.9	186.0	180.8	175.6	180.8
77.5°	88.9	99.9	110.8	130.7	153.6	156.2	138.5	124.7	122.6	120.5	122.6
80°	70.2	72.8	75.4	91.7	112.5	115.1	99.5	87.8	87.8	87.8	87.8
82.5°	46.8	49.4	52.0	63.6	78.2	79.7	68.3	59.2	57.1	55.0	57.1
85°	23.4	23.4	23.4	27.3	32.5	32.5	27.3	23.4	23.4	23.4	23.4
87.5°	5.1	5.6	6.3	8.3	10.8	11.0	8.9	7.4	7.6	7.6	7.6
90°	2.0	4.6	7.9	10.5	12.5	13.2	13.2	13.8	14.5	14.5	14.5
92.5°	7.2	11.4	11.6	11.6	14.1	15.3	16.3	16.4	17.1	17.1	17.1
95°	20.4	22.4	33.5	32.9	22.4	17.8	15.1	15.1	15.1	15.1	15.1
97.5°	38.9	41.8	43.7	58.5	61.8	59.7	48.7	40.9	36.6	34.6	36.6
100°	55.2	56.5	60.5	61.1	77.6	93.4	85.5	75.6	72.3	70.4	72.3
102.5°	71.5	72.3	78.4	81.1	85.0	93.9	121.2	118.2	116.0	115.6	116.0
105°	96.0	96.7	107.8	113.1	115.7	115.7	115.1	128.2	149.3	153.9	149.3
107.5°	122.2	125.2	138.3	152.4	155.4	156.2	152.8	150.8	150.0	150.6	150.0
110°	140.1	144.7	160.4	178.2	182.8	184.1	182.8	180.8	179.5	179.5	179.5



TEST NUMBER: P1435779

CATALOG NUMBER: SQ2W-FA-K-050U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	157.4	164.1	182.0	202.4	210.1	214.1	211.2	209.8	208.4	209.5	208.4
115°	184.1	194.0	217.6	238.7	254.5	256.4	255.8	255.8	255.1	255.1	255.1
117.5°	208.8	224.6	251.2	275.6	293.9	299.2	301.8	301.0	300.2	301.5	300.2
120°	226.2	244.6	274.8	302.5	320.2	328.1	330.7	329.4	330.7	329.4	330.7
122.5°	244.6	267.2	296.9	325.6	346.5	355.5	358.6	358.9	359.1	358.4	359.1
125°	272.2	299.8	334.7	364.3	386.0	396.5	399.1	399.8	401.1	404.4	401.1
127.5°	300.1	331.4	369.7	398.2	420.4	433.2	437.3	438.7	441.5	442.9	441.5
130°	319.6	355.1	393.9	420.8	442.5	456.3	463.6	465.5	468.8	468.2	468.8
132.5°	340.1	377.2	416.5	444.5	464.6	479.5	485.6	491.3	492.5	493.4	492.5
135°	370.2	410.3	449.7	477.4	496.4	510.9	518.8	524.0	527.3	529.3	527.3
137.5°	401.9	444.2	482.1	506.7	525.9	538.4	547.3	552.8	556.3	557.8	556.3
140°	423.4	464.2	501.0	526.7	543.8	556.3	564.2	570.7	574.7	574.7	574.7
142.5°	444.0	484.2	520.0	545.6	560.6	572.0	580.5	585.5	589.9	589.9	589.9
145°	472.8	512.9	545.7	571.4	583.9	594.4	603.6	607.6	610.2	610.2	610.2
147.5°	502.9	538.4	568.4	593.0	603.5	615.8	623.1	626.2	629.5	628.1	629.5
150°	520.8	553.6	582.6	605.6	616.1	627.9	635.2	637.8	641.1	639.1	641.1
152.5°	538.1	569.4	595.7	617.2	626.1	637.9	646.2	648.8	651.1	649.6	651.1
155°	561.5	589.1	613.5	633.2	641.1	652.3	660.2	663.4	666.1	662.8	666.1
157.5°	582.4	606.2	627.4	645.6	654.0	663.6	670.9	675.0	677.6	676.2	677.6
160°	595.1	616.8	635.8	652.9	660.8	669.4	677.3	681.9	684.5	682.5	684.5
162.5°	605.6	625.2	643.2	658.7	665.5	673.0	682.5	686.6	689.2	686.7	689.2
165°	620.7	636.5	652.3	665.4	671.3	677.3	687.1	691.7	693.7	691.1	693.7
167.5°	632.1	644.2	657.0	668.3	672.6	678.4	688.3	692.1	694.6	691.3	694.6
170°	638.5	649.0	660.2	669.4	672.6	677.9	687.8	691.1	693.0	689.7	693.0
172.5°	643.7	651.6	660.7	668.8	670.5	674.8	684.1	687.4	688.8	686.1	688.8
175°	649.0	653.6	660.2	665.4	664.8	667.4	675.3	677.9	680.5	676.6	680.5
177.5°	651.5	653.6	655.7	658.8	656.7	656.7	662.5	664.1	664.6	662.5	664.6
180°	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9



TEST NUMBER: P1435779

CATALOG NUMBER: SQ2W-FA-K-050U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1509.8	1509.8	1509.8	1509.8	1509.8	1509.8	1509.8	1509.8	1509.8	1509.8	1509.8
2.5°	1523.8	1523.8	1523.8	1523.8	1523.8	1521.2	1510.8	1500.4	1500.4	1500.4	1492.6
5°	1546.2	1542.9	1540.3	1536.4	1531.2	1522.8	1504.6	1486.4	1478.6	1470.8	1437.6
7.5°	1556.1	1551.9	1547.2	1541.0	1533.2	1521.2	1496.8	1472.3	1437.5	1402.6	1328.8
10°	1551.4	1548.8	1546.2	1541.0	1533.2	1520.2	1491.6	1463.0	1392.7	1322.5	1252.3
12.5°	1546.7	1544.1	1541.5	1535.3	1525.4	1510.3	1479.6	1448.9	1349.6	1250.2	1186.8
15°	1533.8	1529.3	1524.1	1517.6	1509.8	1493.5	1451.9	1410.3	1298.5	1186.6	1133.3
17.5°	1510.3	1506.3	1501.6	1494.0	1483.6	1463.2	1412.8	1362.3	1245.3	1128.2	1093.9
20°	1486.4	1484.4	1481.8	1475.3	1464.9	1443.5	1388.8	1334.2	1217.2	1100.1	1084.5
22.5°	1458.8	1457.9	1457.4	1451.9	1441.5	1418.5	1357.6	1296.8	1181.8	1066.9	1067.4
25°	1411.6	1412.2	1414.8	1408.3	1392.7	1363.5	1293.3	1223.0	1121.6	1020.2	1037.7
27.5°	1361.1	1359.2	1356.6	1350.1	1339.7	1309.8	1221.3	1132.9	1052.8	972.7	1001.8
30°	1328.4	1326.4	1323.8	1317.3	1306.9	1274.4	1175.6	1076.7	1009.1	941.5	975.3
32.5°	1290.9	1290.5	1290.0	1285.6	1277.3	1241.6	1124.1	1006.5	957.6	908.7	944.1
35°	1234.1	1234.7	1234.7	1232.1	1226.9	1187.3	1044.2	901.2	880.4	859.6	901.2
37.5°	1169.7	1173.1	1176.7	1174.7	1166.9	1120.4	958.1	795.9	802.6	809.4	859.8
40°	1122.9	1129.4	1137.2	1137.2	1129.4	1079.3	902.5	725.6	749.0	772.4	827.1
42.5°	1076.1	1084.2	1094.0	1095.1	1087.3	1037.7	863.0	688.2	713.7	739.2	795.9
45°	1005.2	1014.3	1024.7	1026.0	1018.2	973.4	817.3	661.3	676.9	692.5	747.1
47.5°	922.1	935.1	950.7	952.0	939.0	894.9	757.6	620.3	631.7	643.2	699.1
50°	870.6	883.6	899.2	900.5	887.5	844.0	708.7	573.5	589.1	604.7	663.2
52.5°	809.8	824.3	842.0	845.4	834.5	794.6	667.6	540.7	550.1	559.4	622.6
55°	723.7	739.3	757.5	762.7	754.9	722.4	615.7	509.1	501.3	493.5	557.9
57.5°	633.3	651.1	671.9	678.2	669.8	638.2	536.8	435.4	428.6	421.9	491.6
60°	576.1	594.9	615.7	620.9	610.5	580.0	489.0	397.9	384.9	371.9	444.7
62.5°	519.9	538.8	559.6	562.7	548.1	517.0	436.4	355.8	347.0	338.1	408.8
65°	435.6	454.5	475.3	476.6	458.4	427.2	357.0	286.7	291.9	297.1	360.9
67.5°	353.2	373.0	395.8	396.9	376.1	345.4	285.1	224.7	241.9	259.0	316.4
70°	301.7	319.9	340.7	340.7	319.9	291.3	239.3	187.3	210.7	234.1	286.7
72.5°	250.7	270.0	292.9	292.9	270.0	242.9	203.4	163.9	187.3	210.7	254.0
75°	186.0	202.9	223.7	221.1	195.1	169.7	146.3	122.9	146.3	169.7	202.9
77.5°	124.7	138.5	156.2	153.6	130.7	110.8	99.9	88.9	108.2	127.4	150.6
80°	87.8	99.5	115.1	112.5	91.7	75.4	72.8	70.2	83.2	96.2	113.1
82.5°	59.2	68.3	79.7	78.2	63.6	52.0	49.4	46.8	57.7	68.7	80.4
85°	23.4	27.3	32.5	32.5	27.3	23.4	23.4	23.4	28.6	33.8	39.0
87.5°	7.4	8.9	11.0	10.8	8.3	6.3	5.6	5.1	7.7	10.3	11.7
90°	13.8	13.2	13.2	12.5	10.5	7.9	4.6	2.0	4.6	7.2	11.8
92.5°	16.4	16.3	15.3	14.1	11.6	11.6	11.4	7.2	12.5	17.8	25.5
95°	15.1	15.1	17.8	22.4	32.9	33.5	22.4	20.4	28.9	40.8	51.3
97.5°	40.9	48.7	59.7	61.8	58.5	43.7	41.8	38.9	53.0	64.7	81.7
100°	75.6	85.5	93.4	77.6	61.1	60.5	56.5	55.2	70.4	81.5	98.0
102.5°	118.2	121.2	93.9	85.0	81.1	78.4	72.3	71.5	86.7	102.0	115.9
105°	128.2	115.1	115.7	115.7	113.1	107.8	96.7	96.0	113.1	130.8	147.9
107.5°	150.8	152.8	156.2	155.4	152.4	138.3	125.2	122.2	137.6	158.9	177.7
110°	180.8	182.8	184.1	182.8	178.2	160.4	144.7	140.1	153.9	176.2	196.6



TEST NUMBER: P1435779

CATALOG NUMBER: SQ2W-FA-K-050U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	209.8	211.2	214.1	210.1	202.4	182.0	164.1	157.4	171.2	194.1	215.0
115°	255.8	255.8	256.4	254.5	238.7	217.6	194.0	184.1	195.9	217.0	240.0
117.5°	301.0	301.8	299.2	293.9	275.6	251.2	224.6	208.8	218.2	240.4	264.1
120°	329.4	330.7	328.1	320.2	302.5	274.8	244.6	226.2	233.4	255.1	278.8
122.5°	358.9	358.6	355.5	346.5	325.6	296.9	267.2	244.6	247.6	267.7	290.9
125°	399.8	399.1	396.5	386.0	364.3	334.7	299.8	272.2	268.3	285.4	309.0
127.5°	438.7	437.3	433.2	420.4	398.2	369.7	331.4	300.1	291.3	302.1	323.8
130°	465.5	463.6	456.3	442.5	420.8	393.9	355.1	319.6	307.1	313.6	332.7
132.5°	491.3	485.6	479.5	464.6	444.5	416.5	377.2	340.1	322.8	325.7	340.6
135°	524.0	518.8	510.9	496.4	477.4	449.7	410.3	370.2	346.5	343.9	352.4
137.5°	552.8	547.3	538.4	525.9	506.7	482.1	444.2	401.9	372.0	363.2	366.5
140°	570.7	564.2	556.3	543.8	526.7	501.0	464.2	423.4	389.9	377.4	375.4
142.5°	585.5	580.5	572.0	560.6	545.6	520.0	484.2	444.0	408.3	392.1	387.5
145°	607.6	603.6	594.4	583.9	571.4	545.7	512.9	472.8	437.3	416.2	406.4
147.5°	626.2	623.1	615.8	603.5	593.0	568.4	538.4	502.9	466.4	440.4	427.7
150°	637.8	635.2	627.9	616.1	605.6	582.6	553.6	520.8	485.9	458.3	441.9
152.5°	648.8	646.2	637.9	626.1	617.2	595.7	569.4	538.1	502.7	475.1	458.2
155°	663.4	660.2	652.3	641.1	633.2	613.5	589.1	561.5	531.3	502.3	483.3
157.5°	675.0	670.9	663.6	654.0	645.6	627.4	606.2	582.4	556.0	528.4	508.9
160°	681.9	677.3	669.4	660.8	652.9	635.8	616.8	595.1	570.7	545.7	524.7
162.5°	686.6	682.5	673.0	665.5	658.7	643.2	625.2	605.6	583.9	562.1	542.6
165°	691.7	687.1	677.3	671.3	665.4	652.3	636.5	620.7	602.3	584.5	568.8
167.5°	692.1	688.3	678.4	672.6	668.3	657.0	644.2	632.1	617.8	603.9	590.7
170°	691.1	687.8	677.9	672.6	669.4	660.2	649.0	638.5	627.3	615.4	604.9
172.5°	687.4	684.1	674.8	670.5	668.8	660.7	651.6	643.7	634.1	625.4	617.0
175°	677.9	675.3	667.4	664.8	665.4	660.2	653.6	649.0	643.1	637.8	633.2
177.5°	664.1	662.5	656.7	656.7	658.8	655.7	653.6	651.5	648.8	647.3	645.7
180°	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9



TEST NUMBER: P1435779

CATALOG NUMBER: SQ2W-FA-K-050U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1509.8	1509.8	1509.8	1509.8	1509.8	1509.8	1509.8	1509.8	1509.8	1509.8	1509.8
2.5°	1482.2	1473.9	1467.6	1462.4	1460.4	1458.3	1460.4	1462.4	1467.6	1473.9	1482.2
5°	1396.0	1351.8	1305.0	1266.6	1253.6	1240.6	1253.6	1266.6	1305.0	1351.8	1396.0
7.5°	1241.9	1188.6	1168.8	1152.9	1148.8	1144.6	1148.8	1152.9	1168.8	1188.6	1241.9
10°	1182.1	1139.2	1123.6	1111.9	1111.9	1111.9	1111.9	1111.9	1123.6	1139.2	1182.1
12.5°	1135.3	1109.0	1108.0	1109.8	1120.2	1130.6	1120.2	1109.8	1108.0	1109.0	1135.3
15°	1099.5	1103.4	1145.0	1179.5	1192.5	1205.5	1192.5	1179.5	1145.0	1103.4	1099.5
17.5°	1087.1	1109.5	1161.0	1202.2	1212.6	1223.0	1212.6	1202.2	1161.0	1109.5	1087.1
20°	1102.8	1131.4	1170.4	1202.2	1212.6	1223.0	1212.6	1202.2	1170.4	1131.4	1102.8
22.5°	1106.4	1141.2	1171.9	1197.6	1208.0	1218.4	1208.0	1197.6	1171.9	1141.2	1106.4
25°	1094.9	1136.6	1162.6	1183.4	1188.6	1193.8	1188.6	1183.4	1162.6	1136.6	1094.9
27.5°	1067.4	1113.2	1139.2	1159.6	1163.2	1166.9	1163.2	1159.6	1139.2	1113.2	1067.4
30°	1042.9	1089.7	1115.8	1137.2	1145.0	1152.8	1145.0	1137.2	1115.8	1089.7	1042.9
32.5°	1007.6	1055.4	1087.7	1112.2	1113.8	1115.4	1113.8	1112.2	1087.7	1055.4	1007.6
35°	963.6	1013.0	1049.4	1076.1	1073.5	1070.9	1073.5	1076.1	1049.4	1013.0	963.6
37.5°	924.9	973.2	1005.0	1029.5	1032.7	1035.8	1032.7	1029.5	1005.0	973.2	924.9
40°	892.1	941.5	975.3	1002.0	1007.2	1012.4	1007.2	1002.0	975.3	941.5	892.1
42.5°	863.0	913.4	947.2	973.9	979.1	984.3	979.1	973.9	947.2	913.4	863.0
45°	814.7	866.7	903.1	931.1	933.7	936.3	933.7	931.1	903.1	866.7	814.7
47.5°	769.8	822.1	855.9	881.9	884.5	887.1	884.5	881.9	855.9	822.1	769.8
50°	736.0	789.4	823.2	849.2	851.8	854.4	851.8	849.2	823.2	789.4	736.0
52.5°	703.8	759.2	788.8	811.7	814.3	816.9	814.3	811.7	788.8	759.2	703.8
55°	646.3	704.8	733.4	754.9	754.9	754.9	754.9	754.9	733.4	704.8	646.3
57.5°	586.7	646.8	671.8	691.3	694.4	697.5	694.4	691.3	671.8	646.8	586.7
60°	546.2	607.3	628.1	645.0	650.2	655.4	650.2	645.0	628.1	607.3	546.2
62.5°	506.1	565.2	586.0	602.4	605.5	608.6	605.5	602.4	586.0	565.2	506.1
65°	444.1	496.1	516.9	533.2	535.8	538.4	535.8	533.2	516.9	496.1	444.1
67.5°	387.1	429.8	444.4	455.8	457.9	460.0	457.9	455.8	444.4	429.8	387.1
70°	349.2	385.6	396.0	403.8	403.8	403.8	403.8	403.8	396.0	385.6	349.2
72.5°	303.9	334.1	344.5	352.8	354.9	357.0	354.9	352.8	344.5	334.1	303.9
75°	239.3	261.4	269.2	275.7	278.3	280.9	278.3	275.7	269.2	261.4	239.3
77.5°	175.0	189.6	194.3	198.4	201.0	203.6	201.0	198.4	194.3	189.6	175.0
80°	131.3	141.7	144.3	146.9	149.5	152.1	149.5	146.9	144.3	141.7	131.3
82.5°	92.3	99.6	102.2	104.3	104.8	105.3	104.8	104.3	102.2	99.6	92.3
85°	44.2	46.8	46.8	46.8	46.8	46.8	46.8	46.8	46.8	46.8	44.2
87.5°	12.4	13.3	14.2	14.8	15.3	15.0	15.3	14.8	14.2	13.3	12.4
90°	15.1	19.7	24.3	27.0	29.6	28.3	29.6	27.0	24.3	19.7	15.1
92.5°	30.4	38.1	43.8	48.5	50.6	50.4	50.6	48.5	43.8	38.1	30.4
95°	61.1	70.4	79.6	86.1	90.1	88.8	90.1	86.1	79.6	70.4	61.1
97.5°	94.3	106.7	116.9	123.1	127.0	129.7	127.0	123.1	116.9	106.7	94.3
100°	116.4	128.2	140.1	147.3	153.9	156.5	153.9	147.3	140.1	128.2	116.4
102.5°	134.3	149.8	162.7	170.4	176.0	178.6	176.0	170.4	162.7	149.8	134.3
105°	163.7	180.2	194.0	203.8	209.8	211.7	209.8	203.8	194.0	180.2	163.7
107.5°	193.2	210.1	222.9	233.8	241.0	245.3	241.0	233.8	222.9	210.1	193.2
110°	216.3	230.1	243.9	253.8	261.0	263.7	261.0	253.8	243.9	230.1	216.3



TEST NUMBER: P1435779

CATALOG NUMBER: SQ2W-FA-K-050U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	235.8	251.2	265.0	274.8	283.1	286.8	283.1	274.8	265.0	251.2	235.8
115°	263.0	283.4	295.9	305.1	311.0	314.3	311.0	305.1	295.9	283.4	263.0
117.5°	285.6	306.9	320.6	327.7	330.5	332.8	330.5	327.7	320.6	306.9	285.6
120°	299.8	319.6	335.3	344.5	347.8	349.1	347.8	344.5	335.3	319.6	299.8
122.5°	313.0	331.7	346.9	358.2	363.6	364.9	363.6	358.2	346.9	331.7	313.0
125°	331.4	349.1	364.9	376.1	382.0	385.3	382.0	376.1	364.9	349.1	331.4
127.5°	347.4	366.6	381.1	391.2	397.0	399.6	397.0	391.2	381.1	366.6	347.4
130°	356.4	376.1	390.6	401.7	407.0	409.6	407.0	401.7	390.6	376.1	356.4
132.5°	363.2	384.0	399.0	409.1	414.9	417.5	414.9	409.1	399.0	384.0	363.2
135°	371.5	393.2	409.0	418.8	424.1	426.7	424.1	418.8	409.0	393.2	371.5
137.5°	378.7	398.5	414.9	425.3	430.0	431.7	430.0	425.3	414.9	398.5	378.7
140°	384.0	401.1	417.5	427.4	432.7	433.3	432.7	427.4	401.1	384.0	384.0
142.5°	390.8	404.2	418.6	428.4	433.7	434.9	433.7	428.4	418.6	404.2	390.8
145°	403.1	411.0	420.8	430.0	434.6	435.9	434.6	430.0	420.8	411.0	403.1
147.5°	418.4	420.9	426.1	432.1	436.6	437.5	436.6	432.1	426.1	420.9	418.4
150°	430.0	429.4	431.3	435.3	439.2	438.6	439.2	435.3	431.3	429.4	430.0
152.5°	443.2	439.4	439.2	441.1	442.9	442.8	442.9	441.1	439.2	439.4	443.2
155°	465.5	458.3	454.3	453.0	453.0	452.4	453.0	453.0	454.3	458.3	465.5
157.5°	490.1	480.0	474.1	470.9	470.0	468.6	470.0	470.9	474.1	480.0	490.1
160°	507.0	495.8	489.9	484.6	482.6	480.7	482.6	484.6	489.9	495.8	507.0
162.5°	522.7	512.1	505.6	500.9	498.9	495.9	498.9	500.9	505.6	512.1	522.7
165°	548.4	537.2	530.0	526.0	523.4	520.8	523.4	526.0	530.0	537.2	548.4
167.5°	574.0	561.8	557.1	552.6	550.1	545.4	550.1	552.6	557.1	561.8	574.0
170°	589.8	578.6	576.0	572.0	567.4	562.2	567.4	572.0	576.0	578.6	589.8
172.5°	603.5	596.0	593.4	589.4	588.0	583.8	588.0	589.4	593.4	596.0	603.5
175°	623.3	617.4	617.4	616.8	614.8	610.8	614.8	616.8	617.4	617.4	623.3
177.5°	639.9	636.7	638.9	638.9	638.3	634.6	638.3	638.9	638.9	636.7	639.9
180°	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9



TEST NUMBER: P1435779

CATALOG NUMBER: SQ2W-FA-K-050U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1509.8	1509.8	1509.8	1509.8
2.5°	1492.6	1500.4	1500.4	1500.4
5°	1437.6	1470.8	1478.6	1486.4
7.5°	1328.8	1402.6	1437.5	1472.3
10°	1252.3	1322.5	1392.7	1463.0
12.5°	1186.8	1250.2	1349.6	1448.9
15°	1133.3	1186.6	1298.5	1410.3
17.5°	1093.9	1128.2	1245.3	1362.3
20°	1084.5	1100.1	1217.2	1334.2
22.5°	1067.4	1066.9	1181.8	1296.8
25°	1037.7	1020.2	1121.6	1223.0
27.5°	1001.8	972.7	1052.8	1132.9
30°	975.3	941.5	1009.1	1076.7
32.5°	944.1	908.7	957.6	1006.5
35°	901.2	859.6	880.4	901.2
37.5°	859.8	809.4	802.6	795.9
40°	827.1	772.4	749.0	725.6
42.5°	795.9	739.2	713.7	688.2
45°	747.1	692.5	676.9	661.3
47.5°	699.1	643.2	631.7	620.3
50°	663.2	604.7	589.1	573.5
52.5°	622.6	559.4	550.1	540.7
55°	557.9	493.5	501.3	509.1
57.5°	491.6	421.9	428.6	435.4
60°	444.7	371.9	384.9	397.9
62.5°	408.8	338.1	347.0	355.8
65°	360.9	297.1	291.9	286.7
67.5°	316.4	259.0	241.9	224.7
70°	286.7	234.1	210.7	187.3
72.5°	254.0	210.7	187.3	163.9
75°	202.9	169.7	146.3	122.9
77.5°	150.6	127.4	108.2	88.9
80°	113.1	96.2	83.2	70.2
82.5°	80.4	68.7	57.7	46.8
85°	39.0	33.8	28.6	23.4
87.5°	11.7	10.3	7.7	5.1
90°	11.8	7.2	4.6	2.0
92.5°	25.5	17.8	12.5	7.2
95°	51.3	40.8	28.9	20.4
97.5°	81.7	64.7	53.0	38.9
100°	98.0	81.5	70.4	55.2
102.5°	115.9	102.0	86.7	71.5
105°	147.9	130.8	113.1	96.0
107.5°	177.7	158.9	137.6	122.2
110°	196.6	176.2	153.9	140.1



TEST NUMBER: P1435779

CATALOG NUMBER: SQ2W-FA-K-050U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	215.0	194.1	171.2	157.4
115°	240.0	217.0	195.9	184.1
117.5°	264.1	240.4	218.2	208.8
120°	278.8	255.1	233.4	226.2
122.5°	290.9	267.7	247.6	244.6
125°	309.0	285.4	268.3	272.2
127.5°	323.8	302.1	291.3	300.1
130°	332.7	313.6	307.1	319.6
132.5°	340.6	325.7	322.8	340.1
135°	352.4	343.9	346.5	370.2
137.5°	366.5	363.2	372.0	401.9
140°	375.4	377.4	389.9	423.4
142.5°	387.5	392.1	408.3	444.0
145°	406.4	416.2	437.3	472.8
147.5°	427.7	440.4	466.4	502.9
150°	441.9	458.3	485.9	520.8
152.5°	458.2	475.1	502.7	538.1
155°	483.3	502.3	531.3	561.5
157.5°	508.9	528.4	556.0	582.4
160°	524.7	545.7	570.7	595.1
162.5°	542.6	562.1	583.9	605.6
165°	568.8	584.5	602.3	620.7
167.5°	590.7	603.9	617.8	632.1
170°	604.9	615.4	627.3	638.5
172.5°	617.0	625.4	634.1	643.7
175°	633.2	637.8	643.1	649.0
177.5°	645.7	647.3	648.8	651.5
180°	650.9	650.9	650.9	650.9



TEST NUMBER: P1435779
 CATALOG NUMBER: SQ2W-FA-K-050U-100D-L935-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.86	19.89	19.67	20.72	21.73	20.06	21.09	20.87	21.92	22.93
	3H	19.97	20.89	20.78	21.72	22.77	21.32	22.24	22.14	23.08	24.12
	4H	20.33	21.20	21.16	22.04	23.09	21.72	22.59	22.55	23.43	24.49
	6H	20.50	21.30	21.34	22.15	23.22	21.89	22.69	22.73	23.54	24.61
	8H	20.53	21.30	21.39	22.17	23.24	21.92	22.68	22.77	23.55	24.62
	12H	20.54	21.26	21.40	22.13	23.22	21.91	22.63	22.77	23.50	24.59
4H	2H	19.75	20.62	20.59	21.47	22.52	20.67	21.54	21.50	22.38	23.44
	3H	21.16	21.88	22.01	22.76	23.83	22.15	22.87	23.00	23.75	24.82
	4H	21.62	22.28	22.48	23.15	24.25	22.63	23.29	23.49	24.16	25.26
	6H	21.86	22.43	22.74	23.32	24.43	22.86	23.43	23.74	24.33	25.43
	8H	21.92	22.45	22.80	23.34	24.46	22.91	23.44	23.79	24.34	25.45
	12H	21.93	22.41	22.83	23.32	24.44	22.91	23.39	23.81	24.30	25.42
8H	4H	22.02	22.55	22.90	23.44	24.55	22.84	23.37	23.72	24.26	25.38
	6H	22.37	22.81	23.28	23.75	24.86	23.16	23.60	24.07	24.53	25.65
	8H	22.49	22.88	23.41	23.81	24.94	23.26	23.65	24.18	24.57	25.71
	12H	22.54	22.88	23.46	23.80	24.98	23.28	23.62	24.20	24.54	25.73
12H	4H	22.03	22.51	22.93	23.42	24.54	22.81	23.29	23.72	24.21	25.33
	6H	22.44	22.83	23.36	23.76	24.89	23.18	23.57	24.10	24.50	25.63
	8H	22.60	22.94	23.52	23.86	25.04	23.30	23.64	24.22	24.56	25.75