

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1435735

Luminaire Tested: SQ2W-FA-0U-125D-L840-UNV-STD-W-WM-4

Issue Date: 3/24/2026

Test Information

Test Method: LM-79-2024
Report Number: P1435735
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2502-345-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/24/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-FA-0U-125D-L840-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - FROSTED CONTINUOUS ASYMMETRIC ROLL LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT N/A - DIRECT ONLY
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5440.8 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.23 / 1.34
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 49.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1435735

CATALOG NUMBER: SQ2W-FA-0U-125D-L840-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1435735

CATALOG NUMBER: SQ2W-FA-0U-125D-L840-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	102	99	95	98	95	92	94	92	90	91	89	87	85
2	100	92	85	80	97	90	84	79	86	81	77	83	79	75	80	76	73	71
3	91	81	73	66	89	79	72	66	76	70	65	73	68	64	71	66	62	60
4	83	72	63	57	81	70	62	56	68	61	55	66	60	55	63	58	54	52
5	77	64	55	49	75	63	55	49	61	54	48	59	53	47	57	52	47	45
6	71	58	49	43	69	57	49	43	55	48	42	53	47	42	52	46	41	39
7	66	53	44	38	64	52	43	38	50	43	37	49	42	37	47	41	37	35
8	61	48	40	34	60	47	39	34	46	39	33	45	38	33	44	38	33	31
9	57	44	36	30	56	43	36	30	42	35	30	41	35	30	40	34	30	28
10	54	41	33	28	53	40	33	28	39	32	27	38	32	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	35372	35372	35372	35372
5°	34957	36609	34957	29176
10°	34804	37032	34804	26451
15°	34207	37330	34207	29240
20°	33266	37059	33266	30494
25°	31617	36761	31617	30860
30°	29130	35937	29130	31188
35°	25775	35147	25775	30629
40°	22194	34184	22194	30964
45°	21911	32962	21911	31024
50°	20903	31355	20903	31141
55°	20796	28923	20796	30834
60°	18645	25775	18645	30712
65°	15897	22708	15897	29845
70°	12826	19241	12826	27658
75°	11123	15889	11123	25427
80°	9475	11845	9475	20530
85°	6298	6298	6298	12578

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 40°
 Vertical Angle: 45°
 Luminance: 33996 cd/sqm



TEST NUMBER: P1435735

CATALOG NUMBER: SQ2W-FA-0U-125D-L840-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	197.1	3.6
10°-20°	550.8	10.1
20°-30°	836.5	15.4
30°-40°	982.1	18.1
40°-50°	996.6	18.3
50°-60°	872.9	16.0
60°-70°	619.2	11.4
70°-80°	318.8	5.9
80°-90°	66.8	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1584.4	29.1
0°-40°	2566.5	47.2
0°-60°	4436.0	81.5
0°-90°	5440.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5440.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2191	2191	2191	2191	2191	
5°	2157	2259	2157	1800	2157	205
15°	2046	2233	2046	1749	2046	575
25°	1775	2064	1775	1732	1775	810
35°	1308	1783	1308	1554	1308	815
45°	960	1444	960	1359	960	734
55°	739	1028	739	1095	739	639
65°	416	594	416	781	416	416
75°	178	255	178	408	178	193
85°	34	34	34	68	34	43
90°	0	0	0	0	0	



TEST NUMBER: P1435735

CATALOG NUMBER: SQ2W-FA-0U-125D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2190.8	2190.8	2190.8	2190.8	2190.8	2190.8	2190.8	2190.8	2190.8	2190.8	2190.8
2.5°	2177.3	2192.4	2207.5	2211.2	2211.2	2211.2	2211.2	2211.2	2211.2	2211.2	2211.2
5°	2156.9	2183.3	2209.7	2222.0	2229.5	2235.2	2239.0	2243.7	2251.2	2258.8	2251.2
7.5°	2136.5	2172.0	2207.5	2224.8	2236.1	2245.2	2252.0	2258.0	2261.8	2265.6	2261.8
10°	2122.9	2164.4	2205.9	2224.8	2236.1	2243.7	2247.5	2251.2	2255.0	2258.8	2255.0
12.5°	2102.5	2147.1	2191.6	2213.5	2227.8	2236.9	2240.7	2244.4	2248.2	2252.0	2248.2
15°	2046.5	2106.9	2167.3	2190.8	2202.2	2211.6	2219.2	2225.8	2229.5	2233.3	2229.5
17.5°	1976.9	2050.1	2123.3	2152.9	2168.0	2179.0	2185.8	2191.6	2194.6	2197.6	2194.6
20°	1936.1	2015.4	2094.6	2125.7	2140.8	2150.3	2154.0	2156.9	2156.9	2156.9	2156.9
22.5°	1881.7	1970.1	2058.4	2091.8	2106.9	2114.8	2115.6	2116.9	2119.9	2122.9	2119.9
25°	1774.8	1876.7	1978.6	2021.0	2043.7	2053.1	2049.3	2048.4	2055.9	2063.5	2055.9
27.5°	1644.0	1772.3	1900.6	1944.0	1959.1	1968.6	1972.3	1975.2	1975.2	1975.2	1975.2
30°	1562.5	1705.9	1849.3	1896.5	1911.6	1921.0	1924.8	1927.6	1927.6	1927.6	1927.6
32.5°	1460.6	1631.2	1801.7	1853.4	1865.5	1871.9	1872.7	1873.3	1873.3	1873.3	1873.3
35°	1307.7	1515.3	1722.9	1780.4	1788.0	1791.7	1791.7	1790.8	1787.0	1783.2	1787.0
37.5°	1154.9	1390.4	1625.9	1693.2	1704.6	1707.6	1702.3	1697.4	1693.6	1689.8	1693.6
40°	1053.0	1309.6	1566.2	1638.9	1650.2	1650.2	1638.9	1629.5	1625.7	1621.9	1625.7
42.5°	998.6	1252.2	1505.9	1577.7	1589.1	1587.6	1573.2	1561.5	1557.7	1554.0	1557.7
45°	959.6	1186.0	1412.4	1477.5	1488.9	1487.0	1471.9	1458.7	1451.1	1443.6	1451.1
47.5°	900.1	1099.4	1298.7	1362.6	1381.5	1379.6	1357.0	1338.1	1330.5	1323.0	1330.5
50°	832.2	1028.4	1224.7	1287.9	1306.8	1304.9	1282.2	1263.4	1255.8	1248.3	1255.8
52.5°	784.6	968.8	1153.0	1210.9	1226.8	1221.9	1196.2	1175.1	1167.5	1160.0	1167.5
55°	738.8	893.5	1048.2	1095.4	1106.7	1099.2	1072.8	1050.1	1038.8	1027.5	1038.8
57.5°	631.8	779.0	926.2	972.0	984.1	975.0	944.8	919.0	906.2	893.3	906.2
60°	577.4	709.5	841.6	886.0	901.1	893.5	863.3	836.0	817.1	798.2	817.1
62.5°	516.3	633.3	750.3	795.4	816.5	812.0	781.8	754.4	735.6	716.7	735.6
65°	416.1	518.0	619.9	665.2	691.6	689.7	659.5	632.2	613.3	594.4	613.3
67.5°	326.1	413.6	501.2	545.7	575.9	574.4	541.2	512.5	497.4	482.3	497.4
70°	271.7	347.2	422.7	464.2	494.4	494.4	464.2	437.8	422.7	407.6	422.7
72.5°	237.8	295.1	352.5	391.7	425.0	425.0	391.7	363.8	351.7	339.7	351.7
75°	178.3	212.3	246.3	283.1	320.8	324.6	294.4	269.8	262.3	254.7	262.3
77.5°	129.1	144.9	160.8	189.6	222.9	226.6	201.0	181.0	177.9	174.9	177.9
80°	101.9	105.7	109.4	133.0	163.2	167.0	144.4	127.4	127.4	127.4	127.4
82.5°	67.9	71.7	75.5	92.3	113.4	115.7	99.1	85.9	82.8	79.8	82.8
85°	34.0	34.0	34.0	39.6	47.2	47.2	39.6	34.0	34.0	34.0	34.0
87.5°	6.8	6.8	6.8	9.1	12.1	12.1	9.1	6.8	6.8	6.8	6.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1435735

CATALOG NUMBER: SQ2W-FA-0U-125D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2190.8	2190.8	2190.8	2190.8	2190.8	2190.8	2190.8	2190.8	2190.8	2190.8	2190.8
2.5°	2211.2	2211.2	2211.2	2211.2	2211.2	2207.5	2192.4	2177.3	2177.3	2177.3	2165.9
5°	2243.7	2239.0	2235.2	2229.5	2222.0	2209.7	2183.3	2156.9	2145.6	2134.2	2086.1
7.5°	2258.0	2252.0	2245.2	2236.1	2224.8	2207.5	2172.0	2136.5	2085.9	2035.4	1928.2
10°	2251.2	2247.5	2243.7	2236.1	2224.8	2205.9	2164.4	2122.9	2021.0	1919.1	1817.2
12.5°	2244.4	2240.7	2236.9	2227.8	2213.5	2191.6	2147.1	2102.5	1958.4	1814.2	1722.1
15°	2225.8	2219.2	2211.6	2202.2	2190.8	2167.3	2106.9	2046.5	1884.2	1721.9	1644.5
17.5°	2191.6	2185.8	2179.0	2168.0	2152.9	2123.3	2050.1	1976.9	1807.0	1637.2	1587.4
20°	2156.9	2154.0	2150.3	2140.8	2125.7	2094.6	2015.4	1936.1	1766.3	1596.4	1573.8
22.5°	2116.9	2115.6	2114.8	2106.9	2091.8	2058.4	1970.1	1881.7	1714.9	1548.1	1548.9
25°	2048.4	2049.3	2053.1	2043.7	2021.0	1978.6	1876.7	1774.8	1627.6	1480.4	1505.9
27.5°	1975.2	1972.3	1968.6	1959.1	1944.0	1900.6	1772.3	1644.0	1527.7	1411.5	1453.8
30°	1927.6	1924.8	1921.0	1911.6	1896.5	1849.3	1705.9	1562.5	1464.3	1366.2	1415.3
32.5°	1873.3	1872.7	1871.9	1865.5	1853.4	1801.7	1631.2	1460.6	1389.6	1318.7	1370.0
35°	1790.8	1791.7	1791.7	1788.0	1780.4	1722.9	1515.3	1307.7	1277.5	1247.3	1307.7
37.5°	1697.4	1702.3	1707.6	1704.6	1693.2	1625.9	1390.4	1154.9	1164.7	1174.5	1247.7
40°	1629.5	1638.9	1650.2	1650.2	1638.9	1566.2	1309.6	1053.0	1086.9	1120.9	1200.2
42.5°	1561.5	1573.2	1587.6	1589.1	1577.7	1505.9	1252.2	998.6	1035.6	1072.6	1154.9
45°	1458.7	1471.9	1487.0	1488.9	1477.5	1412.4	1186.0	959.6	982.2	1004.8	1084.1
47.5°	1338.1	1357.0	1379.6	1381.5	1362.6	1298.7	1099.4	900.1	916.7	933.3	1014.5
50°	1263.4	1282.2	1304.9	1306.8	1287.9	1224.7	1028.4	832.2	854.8	877.5	962.4
52.5°	1175.1	1196.2	1221.9	1226.8	1210.9	1153.0	968.8	784.6	798.2	811.8	903.5
55°	1050.1	1072.8	1099.2	1106.7	1095.4	1048.2	893.5	738.8	727.5	716.1	809.5
57.5°	919.0	944.8	975.0	984.1	972.0	926.2	779.0	631.8	622.0	612.2	713.3
60°	836.0	863.3	893.5	901.1	886.0	841.6	709.5	577.4	558.6	539.7	645.4
62.5°	754.4	781.8	812.0	816.5	795.4	750.3	633.3	516.3	503.5	490.6	593.3
65°	632.2	659.5	689.7	691.6	665.2	619.9	518.0	416.1	423.6	431.2	523.7
67.5°	512.5	541.2	574.4	575.9	545.7	501.2	413.6	326.1	351.0	375.9	459.1
70°	437.8	464.2	494.4	494.4	464.2	422.7	347.2	271.7	305.7	339.7	416.1
72.5°	363.8	391.7	425.0	425.0	391.7	352.5	295.1	237.8	271.7	305.7	368.5
75°	269.8	294.4	324.6	320.8	283.1	246.3	212.3	178.3	212.3	246.3	294.4
77.5°	181.0	201.0	226.6	222.9	189.6	160.8	144.9	129.1	157.0	184.9	218.5
80°	127.4	144.4	167.0	163.2	133.0	109.4	105.7	101.9	120.8	139.6	164.2
82.5°	85.9	99.1	115.7	113.4	92.3	75.5	71.7	67.9	83.8	99.6	116.6
85°	34.0	39.6	47.2	47.2	39.6	34.0	34.0	34.0	41.5	49.1	56.6
87.5°	6.8	9.1	12.1	12.1	9.1	6.8	6.8	6.8	9.8	12.8	13.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1435735

CATALOG NUMBER: SQ2W-FA-0U-125D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2190.8	2190.8	2190.8	2190.8	2190.8	2190.8	2190.8	2190.8	2190.8	2190.8	2190.8
2.5°	2150.8	2138.8	2129.7	2122.2	2119.1	2116.1	2119.1	2122.2	2129.7	2138.8	2150.8
5°	2025.7	1961.6	1893.6	1838.0	1819.1	1800.2	1819.1	1838.0	1893.6	1961.6	2025.7
7.5°	1802.1	1724.7	1696.1	1673.0	1667.0	1661.0	1667.0	1673.0	1696.1	1724.7	1802.1
10°	1715.3	1653.0	1630.4	1613.4	1613.4	1613.4	1613.4	1613.4	1630.4	1653.0	1715.3
12.5°	1647.4	1609.3	1607.8	1610.4	1625.5	1640.6	1625.5	1610.4	1607.8	1609.3	1647.4
15°	1595.5	1601.1	1661.5	1711.5	1730.4	1749.3	1730.4	1711.5	1661.5	1601.1	1595.5
17.5°	1577.6	1610.0	1684.7	1744.6	1759.7	1774.8	1759.7	1744.6	1684.7	1610.0	1577.6
20°	1600.2	1641.7	1698.3	1744.6	1759.7	1774.8	1759.7	1744.6	1698.3	1641.7	1600.2
22.5°	1605.5	1656.1	1700.6	1737.8	1752.9	1768.0	1752.9	1737.8	1700.6	1656.1	1605.5
25°	1588.9	1649.3	1687.0	1717.2	1724.7	1732.3	1724.7	1717.2	1687.0	1649.3	1588.9
27.5°	1548.9	1615.3	1653.0	1682.7	1688.0	1693.2	1688.0	1682.7	1653.0	1615.3	1548.9
30°	1513.4	1581.3	1619.1	1650.2	1661.5	1672.9	1661.5	1650.2	1619.1	1581.3	1513.4
32.5°	1462.1	1531.5	1578.3	1614.0	1616.2	1618.5	1616.2	1614.0	1578.3	1531.5	1462.1
35°	1398.3	1470.0	1522.8	1561.5	1557.7	1554.0	1557.7	1561.5	1522.8	1470.0	1398.3
37.5°	1342.1	1412.3	1458.3	1494.0	1498.5	1503.0	1498.5	1494.0	1458.3	1412.3	1342.1
40°	1294.5	1366.2	1415.3	1454.0	1461.5	1469.1	1461.5	1454.0	1415.3	1366.2	1294.5
42.5°	1252.2	1325.5	1374.5	1413.2	1420.7	1428.3	1420.7	1413.2	1374.5	1325.5	1252.2
45°	1182.2	1257.7	1310.5	1351.1	1354.9	1358.7	1354.9	1351.1	1310.5	1257.7	1182.2
47.5°	1117.1	1193.0	1242.0	1279.8	1283.6	1287.3	1283.6	1279.8	1242.0	1193.0	1117.1
50°	1068.1	1145.4	1194.5	1232.2	1236.0	1239.8	1236.0	1232.2	1194.5	1145.4	1068.1
52.5°	1021.3	1101.6	1144.7	1177.9	1181.7	1185.4	1181.7	1177.9	1144.7	1101.6	1021.3
55°	937.9	1022.8	1064.3	1095.4	1095.4	1095.4	1095.4	1095.4	1064.3	1022.8	937.9
57.5°	851.4	938.6	974.8	1003.1	1007.7	1012.2	1007.7	1003.1	974.8	938.6	851.4
60°	792.6	881.2	911.4	936.0	943.5	951.1	943.5	936.0	911.4	881.2	792.6
62.5°	734.4	820.1	850.3	874.1	878.6	883.1	878.6	874.1	850.3	820.1	734.4
65°	644.4	719.9	750.1	773.7	777.5	781.2	777.5	773.7	750.1	719.9	644.4
67.5°	561.8	623.7	644.8	661.4	664.4	667.4	664.4	661.4	644.8	623.7	561.8
70°	506.7	559.5	574.6	585.9	585.9	585.9	585.9	585.9	574.6	559.5	506.7
72.5°	441.0	484.8	499.9	512.0	515.0	518.0	515.0	512.0	499.9	484.8	441.0
75°	347.2	379.3	390.6	400.1	403.8	407.6	403.8	400.1	390.6	379.3	347.2
77.5°	254.0	275.1	281.9	288.0	291.7	295.5	291.7	288.0	281.9	275.1	254.0
80°	190.6	205.7	209.5	213.2	217.0	220.8	217.0	213.2	209.5	205.7	190.6
82.5°	134.0	144.5	148.3	151.3	152.1	152.8	152.1	151.3	148.3	144.5	134.0
85°	64.2	67.9	67.9	67.9	67.9	67.9	67.9	67.9	67.9	67.9	64.2
87.5°	13.6	13.6	13.6	13.6	13.6	13.6	13.6	13.6	13.6	13.6	13.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1435735

CATALOG NUMBER: SQ2W-FA-0U-125D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	2190.8	2190.8	2190.8	2190.8
2.5°	2165.9	2177.3	2177.3	2177.3
5°	2086.1	2134.2	2145.6	2156.9
7.5°	1928.2	2035.4	2085.9	2136.5
10°	1817.2	1919.1	2021.0	2122.9
12.5°	1722.1	1814.2	1958.4	2102.5
15°	1644.5	1721.9	1884.2	2046.5
17.5°	1587.4	1637.2	1807.0	1976.9
20°	1573.8	1596.4	1766.3	1936.1
22.5°	1548.9	1548.1	1714.9	1881.7
25°	1505.9	1480.4	1627.6	1774.8
27.5°	1453.8	1411.5	1527.7	1644.0
30°	1415.3	1366.2	1464.3	1562.5
32.5°	1370.0	1318.7	1389.6	1460.6
35°	1307.7	1247.3	1277.5	1307.7
37.5°	1247.7	1174.5	1164.7	1154.9
40°	1200.2	1120.9	1086.9	1053.0
42.5°	1154.9	1072.6	1035.6	998.6
45°	1084.1	1004.8	982.2	959.6
47.5°	1014.5	933.3	916.7	900.1
50°	962.4	877.5	854.8	832.2
52.5°	903.5	811.8	798.2	784.6
55°	809.5	716.1	727.5	738.8
57.5°	713.3	612.2	622.0	631.8
60°	645.4	539.7	558.6	577.4
62.5°	593.3	490.6	503.5	516.3
65°	523.7	431.2	423.6	416.1
67.5°	459.1	375.9	351.0	326.1
70°	416.1	339.7	305.7	271.7
72.5°	368.5	305.7	271.7	237.8
75°	294.4	246.3	212.3	178.3
77.5°	218.5	184.9	157.0	129.1
80°	164.2	139.6	120.8	101.9
82.5°	116.6	99.6	83.8	67.9
85°	56.6	49.1	41.5	34.0
87.5°	13.6	12.8	9.8	6.8
90°	0.0	0.0	0.0	0.0



TEST NUMBER: P1435735
 CATALOG NUMBER: SQ2W-FA-0U-125D-L840-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	22.60	24.20	22.96	24.52	24.83	23.80	25.40	24.16	25.72	26.03
	3H	23.74	25.19	24.12	25.51	25.87	25.09	26.54	25.47	26.87	27.23
	4H	24.12	25.49	24.52	25.83	26.21	25.52	26.88	25.91	27.23	27.60
	6H	24.32	25.58	24.73	25.95	26.34	25.71	26.97	26.12	27.34	27.73
	8H	24.38	25.58	24.80	25.97	26.37	25.76	26.96	26.18	27.35	27.75
	12H	24.40	25.55	24.83	25.93	26.36	25.77	26.92	26.20	27.30	27.73
4H	2H	23.55	24.91	23.95	25.26	25.64	24.47	25.83	24.86	26.17	26.55
	3H	25.01	26.14	25.42	26.54	26.94	26.00	27.13	26.40	27.53	27.93
	4H	25.49	26.51	25.92	26.93	27.37	26.50	27.53	26.93	27.94	28.38
	6H	25.76	26.65	26.22	27.09	27.55	26.76	27.66	27.22	28.10	28.55
	8H	25.84	26.67	26.30	27.11	27.58	26.83	27.66	27.29	28.11	28.57
	12H	25.87	26.62	26.35	27.10	27.57	26.85	27.60	27.33	28.08	28.55
8H	4H	25.93	26.77	26.39	27.21	27.67	26.75	27.59	27.22	28.03	28.50
	6H	26.31	27.00	26.81	27.49	27.97	27.10	27.79	27.59	28.28	28.76
	8H	26.44	27.06	26.95	27.56	28.05	27.20	27.82	27.71	28.33	28.81
	12H	26.51	27.06	27.02	27.55	28.11	27.25	27.80	27.76	28.29	28.85
12H	4H	25.97	26.72	26.45	27.19	27.66	26.76	27.51	27.24	27.98	28.45
	6H	26.39	27.01	26.90	27.52	28.00	27.12	27.74	27.63	28.25	28.74
	8H	26.57	27.12	27.08	27.61	28.17	27.27	27.82	27.78	28.31	28.87