

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1435905

Luminaire Tested: SQ2W-FB-0U-125D-L935-UNV-STD-W-WM-4

Issue Date: 3/24/2026

Test Information

Test Method: LM-79-2019
Report Number: P1435905
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-12)
Test Lab: INNOVATION CENTER
Issue Date: 3/24/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-FB-0U-125D-L935-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - FROSTED CONTINUOUS BATWING ROLL LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT N/A - DIRECT ONLY
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4961.3 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.52
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 49.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1435905

CATALOG NUMBER: SQ2W-FB-0U-125D-L935-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1435905

CATALOG NUMBER: SQ2W-FB-0U-125D-L935-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	104	100	96	106	102	98	94	97	94	91	93	91	88	90	88	86	84
2	98	90	83	77	96	88	82	76	84	79	74	81	77	73	78	74	71	69
3	89	78	70	63	87	77	69	63	74	67	61	71	65	60	68	63	59	57
4	81	69	60	53	79	67	59	52	65	58	52	63	56	51	60	55	50	48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41
6	68	54	45	39	66	53	45	38	52	44	38	50	43	38	48	42	37	35
7	63	49	40	34	61	48	40	33	47	39	33	45	38	33	44	37	33	31
8	58	44	36	30	57	44	35	29	42	35	29	41	34	29	40	34	29	27
9	54	40	32	26	53	40	32	26	39	31	26	38	31	26	37	30	26	24
10	51	37	29	23	49	37	29	23	36	28	23	35	28	23	34	28	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8110	8110	8110	8110
5°	7906	14364	7906	14364
10°	7404	27953	7404	27953
15°	6701	32173	6701	32173
20°	5935	33693	5935	33693
25°	5248	34247	5248	34247
30°	4638	34669	4638	34669
35°	4141	37272	4141	37272
40°	3766	39601	3766	39601
45°	3473	41467	3473	41467
50°	3275	42221	3275	42221
55°	3195	42556	3195	42556
60°	3274	42347	3274	42347
65°	3415	41149	3415	41149
70°	3536	31123	3536	31123
75°	3918	17174	3918	17174
80°	4045	15946	4045	15946
85°	4020	6706	4020	6706

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 52.5°
 Luminance: 42942 cd/sqm



TEST NUMBER: P1435905

CATALOG NUMBER: SQ2W-FB-0U-125D-L935-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.2	1.7
10°-20°	384.0	7.7
20°-30°	675.7	13.6
30°-40°	874.7	17.6
40°-50°	964.7	19.4
50°-60°	900.4	18.1
60°-70°	695.6	14.0
70°-80°	320.7	6.5
80°-90°	61.3	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1143.9	23.1
0°-40°	2018.6	40.7
0°-60°	3883.7	78.3
0°-90°	4961.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4961.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	502	502	502	502	502	
5°	488	886	488	886	488	45
15°	401	1925	401	1925	401	112
25°	295	1922	295	1922	295	135
35°	210	1891	210	1891	210	132
45°	152	1816	152	1816	152	118
55°	114	1512	114	1512	114	102
65°	89	1077	89	1077	89	88
75°	63	275	63	275	63	64
85°	22	36	22	36	22	24
90°	0	0	0	0	0	



TEST NUMBER: P1435905

CATALOG NUMBER: SQ2W-FB-OU-125D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3
2.5°	498.5	507.9	517.4	527.4	537.8	548.9	560.9	571.2	576.4	581.5	576.4
5°	487.8	520.0	552.2	598.9	650.5	709.0	774.4	830.5	858.4	886.3	858.4
7.5°	469.0	534.5	600.0	738.7	901.8	1071.2	1246.8	1392.5	1448.3	1504.1	1448.3
10°	451.6	542.9	634.1	869.4	1152.8	1370.7	1523.1	1644.9	1675.0	1705.0	1675.0
12.5°	432.3	556.2	680.0	970.5	1316.6	1543.1	1650.0	1737.9	1768.8	1799.7	1768.8
15°	400.9	578.0	755.1	1083.6	1462.4	1695.4	1782.3	1856.1	1890.5	1924.8	1890.5
17.5°	368.5	604.2	840.0	1175.0	1543.2	1770.3	1856.4	1925.6	1944.3	1963.0	1944.3
20°	345.4	622.3	899.2	1234.9	1590.2	1804.9	1878.9	1937.4	1949.2	1961.0	1949.2
22.5°	324.1	633.7	943.2	1279.3	1624.3	1824.8	1880.8	1926.0	1938.7	1951.4	1938.7
25°	294.6	643.5	992.3	1327.5	1658.1	1841.1	1876.5	1905.2	1913.8	1922.4	1913.8
27.5°	266.1	634.7	1003.3	1334.2	1652.6	1823.4	1846.6	1866.0	1874.4	1882.8	1874.4
30°	248.8	623.4	998.0	1325.9	1638.2	1803.0	1820.1	1836.0	1847.8	1859.6	1847.8
32.5°	233.3	609.6	985.9	1309.8	1616.1	1777.4	1793.7	1812.4	1837.9	1863.5	1837.9
35°	210.1	580.4	950.7	1271.1	1574.9	1739.6	1765.4	1796.5	1843.8	1891.0	1843.8
37.5°	190.3	543.0	895.7	1212.8	1518.1	1697.7	1751.6	1803.3	1848.9	1894.4	1848.9
40°	178.7	516.8	854.9	1169.7	1476.7	1666.1	1738.0	1801.6	1840.3	1878.9	1840.3
42.5°	167.1	487.2	807.3	1119.5	1429.0	1625.8	1709.7	1782.3	1821.0	1859.6	1821.0
45°	152.1	439.8	727.5	1036.9	1353.5	1561.2	1659.9	1743.1	1779.6	1816.1	1779.6
47.5°	138.1	388.0	637.9	948.6	1279.7	1497.5	1602.3	1687.5	1714.2	1740.8	1714.2
50°	130.4	353.7	576.9	888.7	1230.1	1452.3	1555.3	1637.9	1659.4	1680.9	1659.4
52.5°	122.7	320.2	517.7	830.1	1180.9	1404.8	1501.8	1579.6	1599.3	1619.1	1599.3
55°	113.5	274.5	435.5	744.6	1103.1	1324.8	1409.6	1477.5	1494.7	1511.8	1494.7
57.5°	105.3	235.2	365.0	664.5	1020.4	1234.5	1306.9	1364.6	1378.6	1392.5	1378.6
60°	101.4	214.1	326.8	614.2	959.9	1165.4	1230.9	1283.5	1297.4	1311.4	1297.4
62.5°	95.6	193.7	291.8	564.0	894.2	1089.4	1149.7	1198.2	1211.3	1224.4	1211.3
65°	89.4	168.8	248.2	493.5	794.0	969.5	1020.0	1059.9	1068.5	1077.1	1068.5
67.5°	80.7	148.1	215.5	428.9	691.0	837.8	869.1	888.6	872.5	856.4	872.5
70°	74.9	137.1	199.4	389.6	622.5	744.4	755.1	751.6	705.5	659.3	705.5
72.5°	71.0	126.4	181.8	346.5	547.6	636.4	612.8	573.2	485.9	398.5	485.9
75°	62.8	107.9	153.0	276.9	427.2	450.8	347.8	271.0	273.2	275.3	273.2
77.5°	51.2	84.9	118.6	194.8	285.2	303.1	248.6	208.2	210.1	212.0	210.1
80°	43.5	70.3	97.1	127.2	158.3	172.8	170.7	169.3	170.4	171.5	170.4
82.5°	35.7	55.7	75.7	93.7	111.1	120.9	123.0	124.2	122.7	121.2	122.7
85°	21.7	33.5	45.3	52.3	57.7	56.1	47.5	40.5	38.4	36.2	38.4
87.5°	7.7	12.0	16.3	14.8	11.4	9.7	9.7	9.7	9.7	9.7	9.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1435905

CATALOG NUMBER: SQ2W-FB-OU-125D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3
2.5°	571.2	560.9	548.9	537.8	527.4	517.4	507.9	498.5	507.9	517.4	527.4
5°	830.5	774.4	709.0	650.5	598.9	552.2	520.0	487.8	520.0	552.2	598.9
7.5°	1392.5	1246.8	1071.2	901.8	738.7	600.0	534.5	469.0	534.5	600.0	738.7
10°	1644.9	1523.1	1370.7	1152.8	869.4	634.1	542.9	451.6	542.9	634.1	869.4
12.5°	1737.9	1650.0	1543.1	1316.6	970.5	680.0	556.2	432.3	556.2	680.0	970.5
15°	1856.1	1782.3	1695.4	1462.4	1083.6	755.1	578.0	400.9	578.0	755.1	1083.6
17.5°	1925.6	1856.4	1770.3	1543.2	1175.0	840.0	604.2	368.5	604.2	840.0	1175.0
20°	1937.4	1878.9	1804.9	1590.2	1234.9	899.2	622.3	345.4	622.3	899.2	1234.9
22.5°	1926.0	1880.8	1824.8	1624.3	1279.3	943.2	633.7	324.1	633.7	943.2	1279.3
25°	1905.2	1876.5	1841.1	1658.1	1327.5	992.3	643.5	294.6	643.5	992.3	1327.5
27.5°	1866.0	1846.6	1823.4	1652.6	1334.2	1003.3	634.7	266.1	634.7	1003.3	1334.2
30°	1836.0	1820.1	1803.0	1638.2	1325.9	998.0	623.4	248.8	623.4	998.0	1325.9
32.5°	1812.4	1793.7	1777.4	1616.1	1309.8	985.9	609.6	233.3	609.6	985.9	1309.8
35°	1796.5	1765.4	1739.6	1574.9	1271.1	950.7	580.4	210.1	580.4	950.7	1271.1
37.5°	1803.3	1751.6	1697.7	1518.1	1212.8	895.7	543.0	190.3	543.0	895.7	1212.8
40°	1801.6	1738.0	1666.1	1476.7	1169.7	854.9	516.8	178.7	516.8	854.9	1169.7
42.5°	1782.3	1709.7	1625.8	1429.0	1119.5	807.3	487.2	167.1	487.2	807.3	1119.5
45°	1743.1	1659.9	1561.2	1353.5	1036.9	727.5	439.8	152.1	439.8	727.5	1036.9
47.5°	1687.5	1602.3	1497.5	1279.7	948.6	637.9	388.0	138.1	388.0	637.9	948.6
50°	1637.9	1555.3	1452.3	1230.1	888.7	576.9	353.7	130.4	353.7	576.9	888.7
52.5°	1579.6	1501.8	1404.8	1180.9	830.1	517.7	320.2	122.7	320.2	517.7	830.1
55°	1477.5	1409.6	1324.8	1103.1	744.6	435.5	274.5	113.5	274.5	435.5	744.6
57.5°	1364.6	1306.9	1234.5	1020.4	664.5	365.0	235.2	105.3	235.2	365.0	664.5
60°	1283.5	1230.9	1165.4	959.9	614.2	326.8	214.1	101.4	214.1	326.8	614.2
62.5°	1198.2	1149.7	1089.4	894.2	564.0	291.8	193.7	95.6	193.7	291.8	564.0
65°	1059.9	1020.0	969.5	794.0	493.5	248.2	168.8	89.4	168.8	248.2	493.5
67.5°	888.6	869.1	837.8	691.0	428.9	215.5	148.1	80.7	148.1	215.5	428.9
70°	751.6	755.1	744.4	622.5	389.6	199.4	137.1	74.9	137.1	199.4	389.6
72.5°	573.2	612.8	636.4	547.6	346.5	181.8	126.4	71.0	126.4	181.8	346.5
75°	271.0	347.8	450.8	427.2	276.9	153.0	107.9	62.8	107.9	153.0	276.9
77.5°	208.2	248.6	303.1	285.2	194.8	118.6	84.9	51.2	84.9	118.6	194.8
80°	169.3	170.7	172.8	158.3	127.2	97.1	70.3	43.5	70.3	97.1	127.2
82.5°	124.2	123.0	120.9	111.1	93.7	75.7	55.7	35.7	55.7	75.7	93.7
85°	40.5	47.5	56.1	57.7	52.3	45.3	33.5	21.7	33.5	45.3	52.3
87.5°	9.7	9.7	9.7	11.4	14.8	16.3	12.0	7.7	12.0	16.3	14.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1435905

CATALOG NUMBER: SQ2W-FB-OU-125D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3
2.5°	537.8	548.9	560.9	571.2	576.4	581.5	576.4	571.2	560.9	548.9	537.8
5°	650.5	709.0	774.4	830.5	858.4	886.3	858.4	830.5	774.4	709.0	650.5
7.5°	901.8	1071.2	1246.8	1392.5	1448.3	1504.1	1448.3	1392.5	1246.8	1071.2	901.8
10°	1152.8	1370.7	1523.1	1644.9	1675.0	1705.0	1675.0	1644.9	1523.1	1370.7	1152.8
12.5°	1316.6	1543.1	1650.0	1737.9	1768.8	1799.7	1768.8	1737.9	1650.0	1543.1	1316.6
15°	1462.4	1695.4	1782.3	1856.1	1890.5	1924.8	1890.5	1856.1	1782.3	1695.4	1462.4
17.5°	1543.2	1770.3	1856.4	1925.6	1944.3	1963.0	1944.3	1925.6	1856.4	1770.3	1543.2
20°	1590.2	1804.9	1878.9	1937.4	1949.2	1961.0	1949.2	1937.4	1878.9	1804.9	1590.2
22.5°	1624.3	1824.8	1880.8	1926.0	1938.7	1951.4	1938.7	1926.0	1880.8	1824.8	1624.3
25°	1658.1	1841.1	1876.5	1905.2	1913.8	1922.4	1913.8	1905.2	1876.5	1841.1	1658.1
27.5°	1652.6	1823.4	1846.6	1866.0	1874.4	1882.8	1874.4	1866.0	1846.6	1823.4	1652.6
30°	1638.2	1803.0	1820.1	1836.0	1847.8	1859.6	1847.8	1836.0	1820.1	1803.0	1638.2
32.5°	1616.1	1777.4	1793.7	1812.4	1837.9	1863.5	1837.9	1812.4	1793.7	1777.4	1616.1
35°	1574.9	1739.6	1765.4	1796.5	1843.8	1891.0	1843.8	1796.5	1765.4	1739.6	1574.9
37.5°	1518.1	1697.7	1751.6	1803.3	1848.9	1894.4	1848.9	1803.3	1751.6	1697.7	1518.1
40°	1476.7	1666.1	1738.0	1801.6	1840.3	1878.9	1840.3	1801.6	1738.0	1666.1	1476.7
42.5°	1429.0	1625.8	1709.7	1782.3	1821.0	1859.6	1821.0	1782.3	1709.7	1625.8	1429.0
45°	1353.5	1561.2	1659.9	1743.1	1779.6	1816.1	1779.6	1743.1	1659.9	1561.2	1353.5
47.5°	1279.7	1497.5	1602.3	1687.5	1714.2	1740.8	1714.2	1687.5	1602.3	1497.5	1279.7
50°	1230.1	1452.3	1555.3	1637.9	1659.4	1680.9	1659.4	1637.9	1555.3	1452.3	1230.1
52.5°	1180.9	1404.8	1501.8	1579.6	1599.3	1619.1	1599.3	1579.6	1501.8	1404.8	1180.9
55°	1103.1	1324.8	1409.6	1477.5	1494.7	1511.8	1494.7	1477.5	1409.6	1324.8	1103.1
57.5°	1020.4	1234.5	1306.9	1364.6	1378.6	1392.5	1378.6	1364.6	1306.9	1234.5	1020.4
60°	959.9	1165.4	1230.9	1283.5	1297.4	1311.4	1297.4	1283.5	1230.9	1165.4	959.9
62.5°	894.2	1089.4	1149.7	1198.2	1211.3	1224.4	1211.3	1198.2	1149.7	1089.4	894.2
65°	794.0	969.5	1020.0	1059.9	1068.5	1077.1	1068.5	1059.9	1020.0	969.5	794.0
67.5°	691.0	837.8	869.1	888.6	872.5	856.4	872.5	888.6	869.1	837.8	691.0
70°	622.5	744.4	755.1	751.6	705.5	659.3	705.5	751.6	755.1	744.4	622.5
72.5°	547.6	636.4	612.8	573.2	485.9	398.5	485.9	573.2	612.8	636.4	547.6
75°	427.2	450.8	347.8	271.0	273.2	275.3	273.2	271.0	347.8	450.8	427.2
77.5°	285.2	303.1	248.6	208.2	210.1	212.0	210.1	208.2	248.6	303.1	285.2
80°	158.3	172.8	170.7	169.3	170.4	171.5	170.4	169.3	170.7	172.8	158.3
82.5°	111.1	120.9	123.0	124.2	122.7	121.2	122.7	124.2	123.0	120.9	111.1
85°	57.7	56.1	47.5	40.5	38.4	36.2	38.4	40.5	47.5	56.1	57.7
87.5°	11.4	9.7	9.7	9.7	9.7	9.7	9.7	9.7	9.7	9.7	11.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1435905

CATALOG NUMBER: SQ2W-FB-0U-125D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	502.3	502.3	502.3	502.3
2.5°	527.4	517.4	507.9	498.5
5°	598.9	552.2	520.0	487.8
7.5°	738.7	600.0	534.5	469.0
10°	869.4	634.1	542.9	451.6
12.5°	970.5	680.0	556.2	432.3
15°	1083.6	755.1	578.0	400.9
17.5°	1175.0	840.0	604.2	368.5
20°	1234.9	899.2	622.3	345.4
22.5°	1279.3	943.2	633.7	324.1
25°	1327.5	992.3	643.5	294.6
27.5°	1334.2	1003.3	634.7	266.1
30°	1325.9	998.0	623.4	248.8
32.5°	1309.8	985.9	609.6	233.3
35°	1271.1	950.7	580.4	210.1
37.5°	1212.8	895.7	543.0	190.3
40°	1169.7	854.9	516.8	178.7
42.5°	1119.5	807.3	487.2	167.1
45°	1036.9	727.5	439.8	152.1
47.5°	948.6	637.9	388.0	138.1
50°	888.7	576.9	353.7	130.4
52.5°	830.1	517.7	320.2	122.7
55°	744.6	435.5	274.5	113.5
57.5°	664.5	365.0	235.2	105.3
60°	614.2	326.8	214.1	101.4
62.5°	564.0	291.8	193.7	95.6
65°	493.5	248.2	168.8	89.4
67.5°	428.9	215.5	148.1	80.7
70°	389.6	199.4	137.1	74.9
72.5°	346.5	181.8	126.4	71.0
75°	276.9	153.0	107.9	62.8
77.5°	194.8	118.6	84.9	51.2
80°	127.2	97.1	70.3	43.5
82.5°	93.7	75.7	55.7	35.7
85°	52.3	45.3	33.5	21.7
87.5°	14.8	16.3	12.0	7.7
90°	0.0	0.0	0.0	0.0



TEST NUMBER: P1435905
 CATALOG NUMBER: SQ2W-FB-0U-125D-L935-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.21	18.89	17.57	19.21	19.52	26.81	28.49	27.17	28.81	29.12
	3H	18.21	19.73	18.58	20.06	20.42	28.47	30.00	28.85	30.32	30.68
	4H	18.64	20.08	19.04	20.42	20.80	28.69	30.12	29.08	30.47	30.84
	6H	18.94	20.27	19.35	20.63	21.02	28.80	30.13	29.21	30.50	30.89
	8H	19.05	20.33	19.48	20.71	21.11	28.84	30.12	29.27	30.50	30.90
	12H	19.13	20.35	19.56	20.73	21.16	28.85	30.07	29.28	30.45	30.88
4H	2H	22.03	23.46	22.42	23.81	24.18	27.27	28.70	27.67	29.05	29.43
	3H	23.23	24.43	23.64	24.83	25.23	29.23	30.43	29.64	30.83	31.23
	4H	23.55	24.63	23.98	25.04	25.48	29.49	30.57	29.92	30.99	31.42
	6H	23.73	24.68	24.18	25.12	25.57	29.67	30.62	30.12	31.05	31.51
	8H	23.79	24.68	24.25	25.12	25.58	29.73	30.62	30.19	31.06	31.53
	12H	23.83	24.63	24.31	25.10	25.57	29.76	30.55	30.24	31.03	31.49
8H	4H	24.81	25.69	25.27	26.14	26.60	29.65	30.53	30.11	30.98	31.44
	6H	25.11	25.84	25.60	26.33	26.80	29.88	30.62	30.38	31.10	31.58
	8H	25.21	25.87	25.72	26.38	26.86	29.99	30.64	30.49	31.15	31.63
	12H	25.30	25.87	25.80	26.36	26.92	30.03	30.61	30.54	31.10	31.66
12H	4H	24.87	25.67	25.35	26.14	26.61	29.64	30.44	30.12	30.91	31.38
	6H	25.22	25.88	25.73	26.39	26.87	29.88	30.53	30.39	31.04	31.52
	8H	25.40	25.98	25.91	26.47	27.03	30.02	30.60	30.52	31.09	31.65