

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1435917

Luminaire Tested: SQ2W-FB-K-025U-075D-L935-UNV-STD-W-WM-4

Issue Date: 3/24/2026

Test Information

Test Method: LM-79-2019
Report Number: P1435917
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-12)
Test Lab: INNOVATION CENTER
Issue Date: 3/24/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-FB-K-025U-075D-L935-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - FROSTED CONTINUOUS BATWING ROLL LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3932.9 lumens
Efficiency: N/A
Efficacy: 115.0 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.52
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 34.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1435917

CATALOG NUMBER: SQ2W-FB-K-025U-075D-L935-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1435917

CATALOG NUMBER: SQ2W-FB-K-025U-075D-L935-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	75				
1	103	99	94	91	98	94	90	87	85	82	80	77	75	73	70	68	67	63				
2	94	85	79	73	89	82	76	70	74	69	65	67	63	60	61	58	55	52				
3	85	75	67	60	80	71	64	58	65	59	54	59	54	50	53	49	46	43				
4	77	66	57	50	73	63	55	49	57	51	45	52	46	42	47	43	39	36				
5	71	58	49	43	67	55	47	41	51	44	39	46	40	36	42	37	33	31				
6	65	52	43	37	61	50	41	36	45	38	33	41	36	31	38	33	29	26				
7	60	47	38	32	57	45	37	31	41	34	29	37	32	27	34	29	25	23				
8	55	42	34	28	53	40	33	27	37	30	26	34	28	24	31	26	22	20				
9	52	38	30	25	49	37	29	24	34	27	23	31	25	21	28	24	20	18				
10	48	35	27	22	46	34	26	22	31	25	20	29	23	19	26	21	18	16				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4845	4845	4845	4845
5°	4723	8580	4723	8580
10°	4423	16698	4423	16698
15°	4003	19217	4003	19217
20°	3545	20127	3545	20127
25°	3135	20457	3135	20457
30°	2770	20709	2770	20709
35°	2474	22263	2474	22263
40°	2251	23654	2251	23654
45°	2076	24770	2076	24770
50°	1957	25218	1957	25218
55°	1908	25421	1908	25421
60°	1957	25294	1957	25294
65°	2040	24580	2040	24580
70°	2110	18590	2110	18590
75°	2339	10262	2339	10262
80°	2417	9521	2417	9521
85°	2408	4001	2408	4001

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 52.5°
 Luminance: 25649 cd/sqm



TEST NUMBER: P1435917

CATALOG NUMBER: SQ2W-FB-K-025U-075D-L935-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.3	1.3
10°-20°	229.4	5.8
20°-30°	403.6	10.3
30°-40°	522.5	13.3
40°-50°	576.2	14.7
50°-60°	537.8	13.7
60°-70°	415.5	10.6
70°-80°	191.5	4.9
80°-90°	38.0	1.0
90°-100°	26.4	0.7
100°-110°	76.9	2.0
110°-120°	125.6	3.2
120°-130°	159.3	4.1
130°-140°	170.5	4.3
140°-150°	159.2	4.0
150°-160°	131.0	3.3
160°-170°	87.9	2.2
170°-180°	31.2	0.8
0°-30°	683.3	17.4
0°-40°	1205.8	30.7
0°-60°	2319.8	59.0
0°-90°	2964.9	75.4
90°-120°	228.9	5.8
90°-150°	717.9	18.3
90°-180°	968.0	24.6
0°-180°	3932.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	300	300	300	300	300	
5°	291	529	291	529	291	27
15°	240	1150	240	1150	240	67
25°	176	1148	176	1148	176	81
35°	126	1130	126	1130	126	79
45°	91	1085	91	1085	91	70
55°	68	903	68	903	68	61
65°	53	643	53	643	53	52
75°	38	164	38	164	38	38
85°	13	22	13	22	13	14
90°	1	7	1	14	1	1
95°	10	8	10	45	10	13
105°	49	78	49	108	49	52
115°	94	130	94	160	94	92
125°	139	206	139	196	139	124
135°	188	270	188	217	188	146
145°	241	311	241	222	241	151
155°	286	338	286	230	286	131
165°	316	352	316	265	316	89
175°	330	345	330	311	330	31
180°	332	332	332	332	332	



TEST NUMBER: P1435917

CATALOG NUMBER: SQ2W-FB-K-025U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1
2.5°	297.7	303.4	309.0	315.1	321.2	327.9	335.1	341.2	344.3	347.4	344.3
5°	291.4	310.6	329.9	357.8	388.5	423.5	462.6	496.1	512.8	529.4	512.8
7.5°	280.1	319.3	358.4	441.2	538.7	639.9	744.8	831.8	865.1	898.4	865.1
10°	269.8	324.3	378.8	519.3	688.6	818.7	909.8	982.6	1000.5	1018.5	1000.5
12.5°	258.2	332.2	406.2	579.7	786.4	921.7	985.6	1038.1	1056.5	1075.0	1056.5
15°	239.5	345.3	451.0	647.2	873.6	1012.7	1064.6	1108.7	1129.2	1149.7	1129.2
17.5°	220.1	360.9	501.7	701.9	921.8	1057.4	1108.9	1150.2	1161.4	1172.5	1161.4
20°	206.3	371.7	537.1	737.6	949.9	1078.1	1122.3	1157.3	1164.3	1171.4	1164.3
22.5°	193.6	378.5	563.4	764.2	970.2	1090.0	1123.5	1150.5	1158.0	1165.6	1158.0
25°	176.0	384.4	592.7	792.9	990.4	1099.7	1120.9	1138.0	1143.2	1148.3	1143.2
27.5°	159.0	379.1	599.3	797.0	987.1	1089.1	1103.0	1114.6	1119.6	1124.6	1119.6
30°	148.6	372.3	596.1	792.0	978.5	1077.0	1087.2	1096.7	1103.7	1110.8	1103.7
32.5°	139.4	364.1	588.9	782.4	965.3	1061.7	1071.5	1082.6	1097.8	1113.1	1097.8
35°	125.5	346.7	567.9	759.3	940.7	1039.1	1054.5	1073.1	1101.3	1129.5	1101.3
37.5°	113.7	324.4	535.0	724.5	906.8	1014.1	1046.3	1077.2	1104.4	1131.6	1104.4
40°	106.8	308.7	510.7	698.7	882.1	995.2	1038.2	1076.2	1099.2	1122.3	1099.2
42.5°	99.8	291.0	482.2	668.7	853.6	971.1	1021.2	1064.6	1087.7	1110.8	1087.7
45°	90.9	262.7	434.5	619.3	808.5	932.5	991.5	1041.2	1063.0	1084.8	1063.0
47.5°	82.5	231.8	381.0	566.6	764.4	894.5	957.1	1008.0	1023.9	1039.8	1023.9
50°	77.9	211.3	344.6	530.9	734.8	867.5	929.0	978.4	991.2	1004.0	991.2
52.5°	73.3	191.3	309.2	495.9	705.4	839.1	897.1	943.5	955.3	967.1	955.3
55°	67.8	164.0	260.1	444.8	658.9	791.3	842.0	882.5	892.8	903.1	892.8
57.5°	62.9	140.5	218.1	396.9	609.5	737.4	780.6	815.1	823.5	831.8	823.5
60°	60.6	127.9	195.2	366.9	573.3	696.1	735.2	766.7	775.0	783.3	775.0
62.5°	57.1	115.7	174.3	336.9	534.1	650.7	686.8	715.7	723.6	731.4	723.6
65°	53.4	100.8	148.3	294.8	474.3	579.1	609.2	633.1	638.3	643.4	638.3
67.5°	48.2	88.4	128.7	256.2	412.8	500.4	519.1	530.8	521.2	511.5	521.2
70°	44.7	81.9	119.1	232.7	371.9	444.6	451.0	449.0	421.4	393.8	421.4
72.5°	42.4	75.5	108.6	207.0	327.1	380.1	366.0	342.4	290.2	238.0	290.2
75°	37.5	64.4	91.4	165.4	255.2	269.3	207.7	161.9	163.2	164.5	163.2
77.5°	30.6	50.7	70.8	116.4	170.4	181.1	148.5	124.4	125.5	126.7	125.5
80°	26.0	42.0	58.0	76.0	94.6	103.2	101.9	101.1	101.8	102.4	101.8
82.5°	21.4	33.3	45.2	56.0	66.4	72.2	73.5	74.2	73.3	72.4	73.3
85°	13.0	20.0	27.1	31.3	34.5	33.5	28.4	24.2	22.9	21.6	22.9
87.5°	4.8	7.6	10.5	9.9	8.1	7.1	7.1	7.2	7.2	7.2	7.2
90°	1.0	2.3	4.0	5.4	6.4	6.7	6.7	7.0	7.4	7.4	7.4
92.5°	3.7	5.8	5.9	5.9	7.2	7.8	8.3	8.4	8.7	8.7	8.7
95°	10.4	11.4	17.1	16.7	11.4	9.0	7.7	7.7	7.7	7.7	7.7
97.5°	19.8	21.3	22.2	29.8	31.5	30.4	24.8	20.8	18.6	17.6	18.6
100°	28.1	28.8	30.8	31.1	39.5	47.6	43.5	38.5	36.8	35.8	36.8
102.5°	36.4	36.8	39.9	41.3	43.3	47.8	61.8	60.2	59.1	58.9	59.1
105°	48.9	49.2	54.9	57.6	58.9	58.9	58.6	65.3	76.0	78.4	76.0
107.5°	62.2	63.8	70.5	77.6	79.2	79.6	77.8	76.8	76.4	76.7	76.4
110°	71.3	73.7	81.7	90.8	93.1	93.8	93.1	92.1	91.4	91.4	91.4



TEST NUMBER: P1435917

CATALOG NUMBER: SQ2W-FB-K-025U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	80.2	83.6	92.7	103.1	107.0	109.0	107.6	106.8	106.2	106.7	106.2
115°	93.8	98.8	110.8	121.6	129.6	130.6	130.3	130.3	129.9	129.9	129.9
117.5°	106.4	114.4	127.9	140.4	149.7	152.4	153.7	153.3	152.9	153.6	152.9
120°	115.2	124.6	140.0	154.0	163.1	167.1	168.4	167.8	168.4	167.8	168.4
122.5°	124.6	136.1	151.2	165.8	176.5	181.0	182.6	182.8	182.9	182.5	182.9
125°	138.6	152.7	170.5	185.5	196.6	201.9	203.3	203.6	204.3	206.0	204.3
127.5°	152.8	168.8	188.3	202.8	214.1	220.6	222.7	223.4	224.8	225.6	224.8
130°	162.8	180.8	200.6	214.3	225.4	232.4	236.1	237.1	238.8	238.4	238.8
132.5°	173.2	192.1	212.1	226.4	236.6	244.2	247.3	250.2	250.8	251.3	250.8
135°	188.5	209.0	229.1	243.1	252.8	260.2	264.2	266.9	268.6	269.6	268.6
137.5°	204.7	226.2	245.5	258.1	267.8	274.2	278.8	281.6	283.3	284.1	283.3
140°	215.7	236.4	255.2	268.2	276.9	283.3	287.3	290.7	292.7	292.7	292.7
142.5°	226.1	246.6	264.8	277.9	285.5	291.3	295.6	298.2	300.5	300.5	300.5
145°	240.8	261.2	277.9	291.0	297.4	302.7	307.4	309.4	310.8	310.8	310.8
147.5°	256.1	274.2	289.5	302.0	307.4	313.6	317.3	318.9	320.6	319.9	320.6
150°	265.2	282.0	296.7	308.4	313.8	319.8	323.5	324.8	326.5	325.5	326.5
152.5°	274.1	290.0	303.4	314.3	318.9	324.9	329.1	330.5	331.6	330.9	331.6
155°	286.0	300.1	312.4	322.5	326.5	332.2	336.2	337.9	339.2	337.6	339.2
157.5°	296.6	308.8	319.5	328.8	333.1	338.0	341.7	343.8	345.1	344.4	345.1
160°	303.1	314.1	323.8	332.5	336.6	340.9	344.9	347.3	348.6	347.6	348.6
162.5°	308.4	318.4	327.6	335.5	339.0	342.8	347.6	349.7	351.0	349.7	351.0
165°	316.1	324.2	332.2	338.9	341.9	344.9	349.9	352.3	353.3	352.0	353.3
167.5°	322.0	328.1	334.6	340.4	342.6	345.5	350.6	352.5	353.8	352.1	353.8
170°	325.2	330.5	336.2	340.9	342.6	345.3	350.3	352.0	353.0	351.3	353.0
172.5°	327.8	331.9	336.5	340.6	341.5	343.7	348.4	350.1	350.8	349.4	350.8
175°	330.5	332.9	336.2	338.9	338.6	339.9	343.9	345.3	346.6	344.6	346.6
177.5°	331.8	332.9	333.9	335.5	334.5	334.5	337.4	338.2	338.5	337.4	338.5
180°	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5



TEST NUMBER: P1435917

CATALOG NUMBER: SQ2W-FB-K-025U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1
2.5°	341.2	335.1	327.9	321.2	315.1	309.0	303.4	297.7	303.4	309.0	315.1
5°	496.1	462.6	423.5	388.5	357.8	329.9	310.6	291.4	310.6	329.9	357.8
7.5°	831.8	744.8	639.9	538.7	441.2	358.4	319.3	280.1	319.3	358.4	441.2
10°	982.6	909.8	818.7	688.6	519.3	378.8	324.3	269.8	324.3	378.8	519.3
12.5°	1038.1	985.6	921.7	786.4	579.7	406.2	332.2	258.2	332.2	406.2	579.7
15°	1108.7	1064.6	1012.7	873.6	647.2	451.0	345.3	239.5	345.3	451.0	647.2
17.5°	1150.2	1108.9	1057.4	921.8	701.9	501.7	360.9	220.1	360.9	501.7	701.9
20°	1157.3	1122.3	1078.1	949.9	737.6	537.1	371.7	206.3	371.7	537.1	737.6
22.5°	1150.5	1123.5	1090.0	970.2	764.2	563.4	378.5	193.6	378.5	563.4	764.2
25°	1138.0	1120.9	1099.7	990.4	792.9	592.7	384.4	176.0	384.4	592.7	792.9
27.5°	1114.6	1103.0	1089.1	987.1	797.0	599.3	379.1	159.0	379.1	599.3	797.0
30°	1096.7	1087.2	1077.0	978.5	792.0	596.1	372.3	148.6	372.3	596.1	792.0
32.5°	1082.6	1071.5	1061.7	965.3	782.4	588.9	364.1	139.4	364.1	588.9	782.4
35°	1073.1	1054.5	1039.1	940.7	759.3	567.9	346.7	125.5	346.7	567.9	759.3
37.5°	1077.2	1046.3	1014.1	906.8	724.5	535.0	324.4	113.7	324.4	535.0	724.5
40°	1076.2	1038.2	995.2	882.1	698.7	510.7	308.7	106.8	308.7	510.7	698.7
42.5°	1064.6	1021.2	971.1	853.6	668.7	482.2	291.0	99.8	291.0	482.2	668.7
45°	1041.2	991.5	932.5	808.5	619.3	434.5	262.7	90.9	262.7	434.5	619.3
47.5°	1008.0	957.1	894.5	764.4	566.6	381.0	231.8	82.5	231.8	381.0	566.6
50°	978.4	929.0	867.5	734.8	530.9	344.6	211.3	77.9	211.3	344.6	530.9
52.5°	943.5	897.1	839.1	705.4	495.9	309.2	191.3	73.3	191.3	309.2	495.9
55°	882.5	842.0	791.3	658.9	444.8	260.1	164.0	67.8	164.0	260.1	444.8
57.5°	815.1	780.6	737.4	609.5	396.9	218.1	140.5	62.9	140.5	218.1	396.9
60°	766.7	735.2	696.1	573.3	366.9	195.2	127.9	60.6	127.9	195.2	366.9
62.5°	715.7	686.8	650.7	534.1	336.9	174.3	115.7	57.1	115.7	174.3	336.9
65°	633.1	609.2	579.1	474.3	294.8	148.3	100.8	53.4	100.8	148.3	294.8
67.5°	530.8	519.1	500.4	412.8	256.2	128.7	88.4	48.2	88.4	128.7	256.2
70°	449.0	451.0	444.6	371.9	232.7	119.1	81.9	44.7	81.9	119.1	232.7
72.5°	342.4	366.0	380.1	327.1	207.0	108.6	75.5	42.4	75.5	108.6	207.0
75°	161.9	207.7	269.3	255.2	165.4	91.4	64.4	37.5	64.4	91.4	165.4
77.5°	124.4	148.5	181.1	170.4	116.4	70.8	50.7	30.6	50.7	70.8	116.4
80°	101.1	101.9	103.2	94.6	76.0	58.0	42.0	26.0	42.0	58.0	76.0
82.5°	74.2	73.5	72.2	66.4	56.0	45.2	33.3	21.4	33.3	45.2	56.0
85°	24.2	28.4	33.5	34.5	31.3	27.1	20.0	13.0	20.0	27.1	31.3
87.5°	7.2	7.1	7.1	8.1	9.9	10.5	7.6	4.8	7.6	10.5	10.1
90°	7.0	6.7	6.7	6.4	5.4	4.0	2.3	1.0	2.3	3.7	6.0
92.5°	8.4	8.3	7.8	7.2	5.9	5.9	5.8	3.7	6.4	9.0	13.0
95°	7.7	7.7	9.0	11.4	16.7	17.1	11.4	10.4	14.7	20.8	26.1
97.5°	20.8	24.8	30.4	31.5	29.8	22.2	21.3	19.8	27.0	33.0	41.6
100°	38.5	43.5	47.6	39.5	31.1	30.8	28.8	28.1	35.8	41.5	49.9
102.5°	60.2	61.8	47.8	43.3	41.3	39.9	36.8	36.4	44.1	52.0	59.0
105°	65.3	58.6	58.9	58.9	57.6	54.9	49.2	48.9	57.6	66.6	75.3
107.5°	76.8	77.8	79.6	79.2	77.6	70.5	63.8	62.2	70.1	80.9	90.5
110°	92.1	93.1	93.8	93.1	90.8	81.7	73.7	71.3	78.4	89.7	100.1



TEST NUMBER: P1435917

CATALOG NUMBER: SQ2W-FB-K-025U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	106.8	107.6	109.0	107.0	103.1	92.7	83.6	80.2	87.2	98.9	109.5
115°	130.3	130.3	130.6	129.6	121.6	110.8	98.8	93.8	99.8	110.5	122.2
117.5°	153.3	153.7	152.4	149.7	140.4	127.9	114.4	106.4	111.1	122.4	134.5
120°	167.8	168.4	167.1	163.1	154.0	140.0	124.6	115.2	118.9	129.9	142.0
122.5°	182.8	182.6	181.0	176.5	165.8	151.2	136.1	124.6	126.1	136.4	148.2
125°	203.6	203.3	201.9	196.6	185.5	170.5	152.7	138.6	136.6	145.3	157.4
127.5°	223.4	222.7	220.6	214.1	202.8	188.3	168.8	152.8	148.4	153.8	164.9
130°	237.1	236.1	232.4	225.4	214.3	200.6	180.8	162.8	156.4	159.7	169.4
132.5°	250.2	247.3	244.2	236.6	226.4	212.1	192.1	173.2	164.4	165.9	173.5
135°	266.9	264.2	260.2	252.8	243.1	229.1	209.0	188.5	176.5	175.1	179.5
137.5°	281.6	278.8	274.2	267.8	258.1	245.5	226.2	204.7	189.5	185.0	186.7
140°	290.7	287.3	283.3	276.9	268.2	255.2	236.4	215.7	198.6	192.2	191.2
142.5°	298.2	295.6	291.3	285.5	277.9	264.8	246.6	226.1	208.0	199.7	197.4
145°	309.4	307.4	302.7	297.4	291.0	277.9	261.2	240.8	222.7	212.0	207.0
147.5°	318.9	317.3	313.6	307.4	302.0	289.5	274.2	256.1	237.6	224.3	217.8
150°	324.8	323.5	319.8	313.8	308.4	296.7	282.0	265.2	247.5	233.4	225.0
152.5°	330.5	329.1	324.9	318.9	314.3	303.4	290.0	274.1	256.0	242.0	233.3
155°	337.9	336.2	332.2	326.5	322.5	312.4	300.1	286.0	270.6	255.8	246.1
157.5°	343.8	341.7	338.0	333.1	328.8	319.5	308.8	296.6	283.2	269.1	259.2
160°	347.3	344.9	340.9	336.6	332.5	323.8	314.1	303.1	290.7	277.9	267.2
162.5°	349.7	347.6	342.8	339.0	335.5	327.6	318.4	308.4	297.4	286.3	276.3
165°	352.3	349.9	344.9	341.9	338.9	332.2	324.2	316.1	306.7	297.7	289.7
167.5°	352.5	350.6	345.5	342.6	340.4	334.6	328.1	322.0	314.7	307.6	300.9
170°	352.0	350.3	345.3	342.6	340.9	336.2	330.5	325.2	319.5	313.4	308.1
172.5°	350.1	348.4	343.7	341.5	340.6	336.5	331.9	327.8	323.0	318.5	314.3
175°	345.3	343.9	339.9	338.6	338.9	336.2	332.9	330.5	327.5	324.8	322.5
177.5°	338.2	337.4	334.5	334.5	335.5	333.9	332.9	331.8	330.5	329.7	328.9
180°	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5



TEST NUMBER: P1435917

CATALOG NUMBER: SQ2W-FB-K-025U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1
2.5°	321.2	327.9	335.1	341.2	344.3	347.4	344.3	341.2	335.1	327.9	321.2
5°	388.5	423.5	462.6	496.1	512.8	529.4	512.8	496.1	462.6	423.5	388.5
7.5°	538.7	639.9	744.8	831.8	865.1	898.4	865.1	831.8	744.8	639.9	538.7
10°	688.6	818.7	909.8	982.6	1000.5	1018.5	1000.5	982.6	909.8	818.7	688.6
12.5°	786.4	921.7	985.6	1038.1	1056.5	1075.0	1056.5	1038.1	985.6	921.7	786.4
15°	873.6	1012.7	1064.6	1108.7	1129.2	1149.7	1129.2	1108.7	1064.6	1012.7	873.6
17.5°	921.8	1057.4	1108.9	1150.2	1161.4	1172.5	1161.4	1150.2	1108.9	1057.4	921.8
20°	949.9	1078.1	1122.3	1157.3	1164.3	1171.4	1164.3	1157.3	1122.3	1078.1	949.9
22.5°	970.2	1090.0	1123.5	1150.5	1158.0	1165.6	1158.0	1150.5	1123.5	1090.0	970.2
25°	990.4	1099.7	1120.9	1138.0	1143.2	1148.3	1143.2	1138.0	1120.9	1099.7	990.4
27.5°	987.1	1089.1	1103.0	1114.6	1119.6	1124.6	1119.6	1114.6	1103.0	1089.1	987.1
30°	978.5	1077.0	1087.2	1096.7	1103.7	1110.8	1103.7	1096.7	1087.2	1077.0	978.5
32.5°	965.3	1061.7	1071.5	1082.6	1097.8	1113.1	1097.8	1082.6	1071.5	1061.7	965.3
35°	940.7	1039.1	1054.5	1073.1	1101.3	1129.5	1101.3	1073.1	1054.5	1039.1	940.7
37.5°	906.8	1014.1	1046.3	1077.2	1104.4	1131.6	1104.4	1077.2	1046.3	1014.1	906.8
40°	882.1	995.2	1038.2	1076.2	1099.2	1122.3	1099.2	1076.2	1038.2	995.2	882.1
42.5°	853.6	971.1	1021.2	1064.6	1087.7	1110.8	1087.7	1064.6	1021.2	971.1	853.6
45°	808.5	932.5	991.5	1041.2	1063.0	1084.8	1063.0	1041.2	991.5	932.5	808.5
47.5°	764.4	894.5	957.1	1008.0	1023.9	1039.8	1023.9	1008.0	957.1	894.5	764.4
50°	734.8	867.5	929.0	978.4	991.2	1004.0	991.2	978.4	929.0	867.5	734.8
52.5°	705.4	839.1	897.1	943.5	955.3	967.1	955.3	943.5	897.1	839.1	705.4
55°	658.9	791.3	842.0	882.5	892.8	903.1	892.8	882.5	842.0	791.3	658.9
57.5°	609.5	737.4	780.6	815.1	823.5	831.8	823.5	815.1	780.6	737.4	609.5
60°	573.3	696.1	735.2	766.7	775.0	783.3	775.0	766.7	735.2	696.1	573.3
62.5°	534.1	650.7	686.8	715.7	723.6	731.4	723.6	715.7	686.8	650.7	534.1
65°	474.3	579.1	609.2	633.1	638.3	643.4	638.3	633.1	609.2	579.1	474.3
67.5°	412.8	500.4	519.1	530.8	521.2	511.5	521.2	530.8	519.1	500.4	412.8
70°	371.9	444.6	451.0	449.0	421.4	393.8	421.4	449.0	451.0	444.6	371.9
72.5°	327.1	380.1	366.0	342.4	290.2	238.0	290.2	342.4	366.0	380.1	327.1
75°	255.2	269.3	207.7	161.9	163.2	164.5	163.2	161.9	207.7	269.3	255.2
77.5°	170.4	181.1	148.5	124.4	125.5	126.7	125.5	124.4	148.5	181.1	170.4
80°	94.6	103.2	101.9	101.1	101.8	102.4	101.8	101.1	101.9	103.2	94.6
82.5°	66.4	72.2	73.5	74.2	73.3	72.4	73.3	74.2	73.5	72.2	66.4
85°	34.5	33.5	28.4	24.2	22.9	21.6	22.9	24.2	28.4	33.5	34.5
87.5°	8.3	7.8	8.2	8.5	8.8	8.7	8.8	8.5	8.2	7.8	8.3
90°	7.7	10.0	12.4	13.7	15.1	14.4	15.1	13.7	12.4	10.0	7.7
92.5°	15.5	19.4	22.3	24.7	25.8	25.7	25.8	24.7	22.3	19.4	15.5
95°	31.1	35.8	40.5	43.9	45.9	45.2	45.9	43.9	40.5	35.8	31.1
97.5°	48.0	54.3	59.5	62.7	64.7	66.0	64.7	62.7	59.5	54.3	48.0
100°	59.3	65.3	71.3	75.0	78.4	79.7	78.4	75.0	71.3	65.3	59.3
102.5°	68.4	76.3	82.8	86.8	89.6	91.0	89.6	86.8	82.8	76.3	68.4
105°	83.4	91.8	98.8	103.8	106.8	107.8	106.8	103.8	98.8	91.8	83.4
107.5°	98.4	107.0	113.5	119.1	122.8	124.9	122.8	119.1	113.5	107.0	98.4
110°	110.2	117.2	124.2	129.3	132.9	134.3	132.9	129.3	124.2	117.2	110.2



TEST NUMBER: P1435917

CATALOG NUMBER: SQ2W-FB-K-025U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	120.1	127.9	135.0	140.0	144.2	146.1	144.2	140.0	135.0	127.9	120.1
115°	134.0	144.3	150.7	155.4	158.4	160.1	158.4	155.4	150.7	144.3	134.0
117.5°	145.5	156.3	163.3	166.9	168.3	169.5	168.3	166.9	163.3	156.3	145.5
120°	152.7	162.8	170.8	175.5	177.2	177.8	177.2	175.5	170.8	162.8	152.7
122.5°	159.4	168.9	176.7	182.4	185.2	185.9	185.2	182.4	176.7	168.9	159.4
125°	168.8	177.8	185.9	191.6	194.6	196.2	194.6	191.6	185.9	177.8	168.8
127.5°	176.9	186.7	194.1	199.3	202.2	203.5	202.2	199.3	194.1	186.7	176.9
130°	181.5	191.6	198.9	204.6	207.3	208.6	207.3	204.6	198.9	191.6	181.5
132.5°	185.0	195.6	203.2	208.4	211.3	212.6	211.3	208.4	203.2	195.6	185.0
135°	189.2	200.3	208.3	213.3	216.0	217.3	216.0	213.3	208.3	200.3	189.2
137.5°	192.9	202.9	211.3	216.6	219.0	219.9	219.0	216.6	211.3	202.9	192.9
140°	195.6	204.3	212.6	217.7	220.4	220.7	220.4	217.7	212.6	204.3	195.6
142.5°	199.1	205.9	213.2	218.2	220.9	221.5	220.9	218.2	213.2	205.9	199.1
145°	205.3	209.3	214.3	219.0	221.4	222.0	221.4	219.0	214.3	209.3	205.3
147.5°	213.1	214.4	217.0	220.1	222.4	222.8	222.4	220.1	217.0	214.4	213.1
150°	219.0	218.7	219.7	221.7	223.7	223.4	223.7	221.7	219.7	218.7	219.0
152.5°	225.7	223.8	223.7	224.6	225.6	225.5	225.6	224.6	223.7	223.8	225.7
155°	237.1	233.4	231.4	230.7	230.7	230.4	230.7	230.7	231.4	233.4	237.1
157.5°	249.6	244.5	241.4	239.8	239.4	238.6	239.4	239.8	241.4	244.5	249.6
160°	258.2	252.5	249.5	246.8	245.8	244.8	245.8	246.8	249.5	252.5	258.2
162.5°	266.2	260.8	257.5	255.1	254.1	252.6	254.1	255.1	257.5	260.8	266.2
165°	279.3	273.6	269.9	267.9	266.6	265.2	266.6	267.9	269.9	273.6	279.3
167.5°	292.3	286.1	283.7	281.4	280.2	277.7	280.2	281.4	283.7	286.1	292.3
170°	300.4	294.7	293.4	291.3	289.0	286.3	289.0	291.3	293.4	294.7	300.4
172.5°	307.4	303.5	302.2	300.2	299.4	297.3	299.4	300.2	302.2	303.5	307.4
175°	317.5	314.5	314.5	314.1	313.1	311.1	313.1	314.1	314.5	314.5	317.5
177.5°	325.9	324.3	325.4	325.4	325.1	323.2	325.1	325.4	325.4	324.3	325.9
180°	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5



TEST NUMBER: P1435917

CATALOG NUMBER: SQ2W-FB-K-025U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	300.1	300.1	300.1	300.1
2.5°	315.1	309.0	303.4	297.7
5°	357.8	329.9	310.6	291.4
7.5°	441.2	358.4	319.3	280.1
10°	519.3	378.8	324.3	269.8
12.5°	579.7	406.2	332.2	258.2
15°	647.2	451.0	345.3	239.5
17.5°	701.9	501.7	360.9	220.1
20°	737.6	537.1	371.7	206.3
22.5°	764.2	563.4	378.5	193.6
25°	792.9	592.7	384.4	176.0
27.5°	797.0	599.3	379.1	159.0
30°	792.0	596.1	372.3	148.6
32.5°	782.4	588.9	364.1	139.4
35°	759.3	567.9	346.7	125.5
37.5°	724.5	535.0	324.4	113.7
40°	698.7	510.7	308.7	106.8
42.5°	668.7	482.2	291.0	99.8
45°	619.3	434.5	262.7	90.9
47.5°	566.6	381.0	231.8	82.5
50°	530.9	344.6	211.3	77.9
52.5°	495.9	309.2	191.3	73.3
55°	444.8	260.1	164.0	67.8
57.5°	396.9	218.1	140.5	62.9
60°	366.9	195.2	127.9	60.6
62.5°	336.9	174.3	115.7	57.1
65°	294.8	148.3	100.8	53.4
67.5°	256.2	128.7	88.4	48.2
70°	232.7	119.1	81.9	44.7
72.5°	207.0	108.6	75.5	42.4
75°	165.4	91.4	64.4	37.5
77.5°	116.4	70.8	50.7	30.6
80°	76.0	58.0	42.0	26.0
82.5°	56.0	45.2	33.3	21.4
85°	31.3	27.1	20.0	13.0
87.5°	10.1	10.5	7.6	4.8
90°	6.0	3.7	2.3	1.0
92.5°	13.0	9.0	6.4	3.7
95°	26.1	20.8	14.7	10.4
97.5°	41.6	33.0	27.0	19.8
100°	49.9	41.5	35.8	28.1
102.5°	59.0	52.0	44.1	36.4
105°	75.3	66.6	57.6	48.9
107.5°	90.5	80.9	70.1	62.2
110°	100.1	89.7	78.4	71.3



TEST NUMBER: P1435917

CATALOG NUMBER: SQ2W-FB-K-025U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	109.5	98.9	87.2	80.2
115°	122.2	110.5	99.8	93.8
117.5°	134.5	122.4	111.1	106.4
120°	142.0	129.9	118.9	115.2
122.5°	148.2	136.4	126.1	124.6
125°	157.4	145.3	136.6	138.6
127.5°	164.9	153.8	148.4	152.8
130°	169.4	159.7	156.4	162.8
132.5°	173.5	165.9	164.4	173.2
135°	179.5	175.1	176.5	188.5
137.5°	186.7	185.0	189.5	204.7
140°	191.2	192.2	198.6	215.7
142.5°	197.4	199.7	208.0	226.1
145°	207.0	212.0	222.7	240.8
147.5°	217.8	224.3	237.6	256.1
150°	225.0	233.4	247.5	265.2
152.5°	233.3	242.0	256.0	274.1
155°	246.1	255.8	270.6	286.0
157.5°	259.2	269.1	283.2	296.6
160°	267.2	277.9	290.7	303.1
162.5°	276.3	286.3	297.4	308.4
165°	289.7	297.7	306.7	316.1
167.5°	300.9	307.6	314.7	322.0
170°	308.1	313.4	319.5	325.2
172.5°	314.3	318.5	323.0	327.8
175°	322.5	324.8	327.5	330.5
177.5°	328.9	329.7	330.5	331.8
180°	331.5	331.5	331.5	331.5



TEST NUMBER: P1435917
 CATALOG NUMBER: SQ2W-FB-K-025U-075D-L935-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.71	14.90	14.41	15.62	16.48	23.30	24.50	24.00	25.22	26.07
	3H	14.67	15.75	15.38	16.48	17.36	24.93	26.01	25.65	26.74	27.63
	4H	15.08	16.10	15.81	16.84	17.74	25.13	26.14	25.86	26.88	27.78
	6H	15.36	16.29	16.10	17.04	17.96	25.22	26.16	25.96	26.91	27.82
	8H	15.46	16.35	16.21	17.12	18.04	25.25	26.14	26.00	26.91	27.83
	12H	15.52	16.37	16.28	17.14	18.08	25.24	26.09	26.00	26.85	27.80
4H	2H	18.47	19.48	19.20	20.22	21.12	23.71	24.72	24.44	25.47	26.36
	3H	19.63	20.47	20.38	21.25	22.17	25.63	26.48	26.38	27.25	28.17
	4H	19.92	20.69	20.69	21.47	22.42	25.87	26.63	26.63	27.41	28.36
	6H	20.08	20.75	20.86	21.55	22.50	26.02	26.68	26.80	27.49	28.44
	8H	20.13	20.75	20.91	21.55	22.51	26.07	26.69	26.86	27.49	28.46
	12H	20.15	20.71	20.95	21.53	22.50	26.07	26.63	26.88	27.45	28.42
8H	4H	21.15	21.77	21.93	22.57	23.53	25.99	26.61	26.77	27.41	28.37
	6H	21.42	21.93	22.24	22.78	23.74	26.20	26.71	27.01	27.55	28.52
	8H	21.52	21.98	22.35	22.82	23.80	26.29	26.75	27.12	27.59	28.57
	12H	21.58	21.98	22.41	22.81	23.85	26.31	26.72	27.15	27.55	28.59
12H	4H	21.19	21.75	21.99	22.57	23.54	25.95	26.51	26.76	27.34	28.31
	6H	21.53	21.99	22.36	22.83	23.81	26.19	26.64	27.01	27.48	28.47
	8H	21.69	22.09	22.52	22.92	23.96	26.30	26.70	27.13	27.53	28.57