

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1435771

Luminaire Tested: SQ2W-FA-K-050U-075D-L840-UNV-STD-W-WM-4

Issue Date: 3/24/2026

Test Information

Test Method: LM-79-2024
Report Number: P1435771
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2502-345-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/24/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-FA-K-050U-075D-L840-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - FROSTED CONTINUOUS ASYMMETRIC ROLL LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5468.1 lumens
Efficiency: N/A
Efficacy: 131.4 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.23 / 1.34
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 41.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1435771

CATALOG NUMBER: SQ2W-FA-K-050U-075D-L840-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1435771

CATALOG NUMBER: SQ2W-FA-K-050U-075D-L840-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	59
1	100	96	92	88	93	90	86	83	78	75	73	67	66	64	58	56	55	50
2	91	84	77	72	85	78	73	68	68	64	61	59	56	53	51	48	46	42
3	83	74	66	60	77	69	62	57	60	55	51	52	48	45	45	42	40	36
4	76	65	57	51	71	61	54	48	54	48	44	47	42	39	40	37	34	31
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30	27
6	64	52	44	38	60	49	42	36	43	37	33	38	33	29	33	29	26	23
7	60	47	39	33	56	44	37	32	39	33	29	34	30	26	30	26	23	21
8	55	43	35	30	52	40	33	28	36	30	26	32	27	23	27	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	25	22	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21130	21130	21130	21130
5°	20881	21867	20881	17428
10°	20790	22120	20790	15799
15°	20433	22298	20433	17466
20°	19871	22137	19871	18214
25°	18885	21958	18885	18433
30°	17400	21466	17400	18628
35°	15396	20995	15396	18295
40°	13257	20419	13257	18495
45°	13088	19689	13088	18531
50°	12486	18728	12486	18602
55°	12422	17275	12422	18418
60°	11137	15396	11137	18345
65°	9494	13566	9494	17830
70°	7662	11495	7662	16522
75°	6644	9494	6644	15190
80°	5662	7076	5662	12264
85°	3761	3761	3761	7521

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 40°
 Vertical Angle: 45°
 Luminance: 20306 cd/sqm



TEST NUMBER: P1435771

CATALOG NUMBER: SQ2W-FA-K-050U-075D-L840-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.7	2.2
10°-20°	329.0	6.0
20°-30°	499.7	9.1
30°-40°	586.6	10.7
40°-50°	595.3	10.9
50°-60°	521.4	9.5
60°-70°	369.8	6.8
70°-80°	190.4	3.5
80°-90°	43.1	0.8
90°-100°	60.4	1.1
100°-110°	176.1	3.2
110°-120°	287.3	5.3
120°-130°	364.6	6.7
130°-140°	390.1	7.1
140°-150°	364.3	6.7
150°-160°	299.8	5.5
160°-170°	201.0	3.7
170°-180°	71.4	1.3
0°-30°	946.4	17.3
0°-40°	1533.0	28.0
0°-60°	2649.8	48.5
0°-90°	3253.1	59.5
90°-120°	523.8	9.6
90°-150°	1642.8	30.0
90°-180°	2215.0	40.5
0°-180°	5468.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1309	1309	1309	1309	1309	
5°	1288	1349	1288	1075	1288	122
15°	1222	1334	1222	1045	1222	343
25°	1060	1233	1060	1035	1060	484
35°	781	1065	781	928	781	487
45°	573	862	573	812	573	438
55°	441	614	441	654	441	382
65°	248	355	248	467	248	248
75°	106	152	106	244	106	115
85°	20	20	20	41	20	25
90°	2	17	2	33	2	2
95°	24	18	24	103	24	29
105°	112	179	112	247	112	119
115°	215	297	215	366	215	211
125°	317	471	317	449	317	284
135°	431	617	431	497	431	333
145°	551	711	551	508	551	345
155°	654	772	654	527	654	301
165°	723	805	723	607	723	204
175°	756	788	756	712	756	72
180°	759	759	759	759	759	



TEST NUMBER: P1435771

CATALOG NUMBER: SQ2W-FA-K-050U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7
2.5°	1300.5	1309.6	1318.6	1320.8	1320.8	1320.8	1320.8	1320.8	1320.8	1320.8	1320.8
5°	1288.4	1304.1	1319.9	1327.3	1331.8	1335.1	1337.4	1340.2	1344.7	1349.2	1344.7
7.5°	1276.2	1297.4	1318.6	1328.9	1335.7	1341.1	1345.2	1348.8	1351.0	1353.3	1351.0
10°	1268.1	1292.9	1317.7	1328.9	1335.7	1340.2	1342.5	1344.7	1347.0	1349.2	1347.0
12.5°	1255.9	1282.5	1309.1	1322.2	1330.7	1336.2	1338.4	1340.7	1342.9	1345.2	1342.9
15°	1222.4	1258.5	1294.6	1308.7	1315.4	1321.1	1325.6	1329.5	1331.8	1334.0	1331.8
17.5°	1180.8	1224.6	1268.3	1286.0	1295.0	1301.6	1305.6	1309.1	1310.9	1312.7	1310.9
20°	1156.5	1203.8	1251.2	1269.8	1278.8	1284.4	1286.7	1288.4	1288.4	1288.4	1288.4
22.5°	1124.0	1176.8	1229.5	1249.5	1258.5	1263.2	1263.7	1264.5	1266.3	1268.1	1266.3
25°	1060.1	1121.0	1181.8	1207.2	1220.7	1226.4	1224.1	1223.6	1228.1	1232.6	1228.1
27.5°	982.0	1058.6	1135.3	1161.2	1170.2	1175.9	1178.1	1179.8	1179.8	1179.8	1179.8
30°	933.3	1019.0	1104.6	1132.8	1141.8	1147.5	1149.7	1151.4	1151.4	1151.4	1151.4
32.5°	872.4	974.3	1076.2	1107.1	1114.3	1118.2	1118.6	1118.9	1118.9	1118.9	1118.9
35°	781.1	905.1	1029.1	1063.5	1068.0	1070.3	1070.3	1069.7	1067.4	1065.2	1067.4
37.5°	689.8	830.5	971.2	1011.4	1018.2	1020.0	1016.8	1013.9	1011.6	1009.4	1011.6
40°	629.0	782.3	935.6	979.0	985.7	985.7	979.0	973.3	971.1	968.8	971.1
42.5°	596.5	748.0	899.5	942.4	949.2	948.3	939.7	932.7	930.5	928.2	930.5
45°	573.2	708.4	843.7	882.6	889.3	888.2	879.2	871.3	866.8	862.3	866.8
47.5°	537.7	656.7	775.7	813.9	825.2	824.1	810.6	799.3	794.8	790.3	794.8
50°	497.1	614.3	731.5	769.3	780.6	779.4	765.9	754.6	750.1	745.6	750.1
52.5°	468.7	578.7	688.7	723.3	732.8	729.8	714.5	701.9	697.4	692.9	697.4
55°	441.3	533.7	626.1	654.3	661.1	656.6	640.8	627.3	620.5	613.7	620.5
57.5°	377.4	465.3	553.2	580.6	587.8	582.4	564.4	548.9	541.3	533.6	541.3
60°	344.9	423.8	502.7	529.2	538.2	533.7	515.7	499.3	488.1	476.8	488.1
62.5°	308.4	378.3	448.2	475.1	487.7	485.0	467.0	450.6	439.4	428.1	439.4
65°	248.5	309.4	370.3	397.3	413.1	412.0	393.9	377.6	366.3	355.1	366.3
67.5°	194.8	247.1	299.4	326.0	344.0	343.1	323.3	306.1	297.1	288.1	297.1
70°	162.3	207.4	252.5	277.3	295.3	295.3	277.3	261.5	252.5	243.5	252.5
72.5°	142.0	176.3	210.6	234.0	253.8	253.8	234.0	217.3	210.1	202.9	210.1
75°	106.5	126.8	147.1	169.1	191.6	193.9	175.8	161.2	156.7	152.2	156.7
77.5°	77.1	86.6	96.0	113.3	133.1	135.4	120.0	108.1	106.3	104.5	106.3
80°	60.9	63.1	65.4	79.5	97.5	99.8	86.2	76.1	76.1	76.1	76.1
82.5°	40.6	42.8	45.1	55.1	67.7	69.1	59.2	51.3	49.5	47.7	49.5
85°	20.3	20.3	20.3	23.7	28.2	28.2	23.7	20.3	20.3	20.3	20.3
87.5°	4.5	5.1	5.9	7.9	10.1	10.3	8.5	7.3	7.4	7.4	7.4
90°	2.3	5.4	9.2	12.3	14.6	15.3	15.3	16.1	16.9	16.9	16.9
92.5°	8.4	13.3	13.5	13.5	16.4	17.8	19.0	19.2	19.9	19.9	19.9
95°	23.8	26.1	39.1	38.3	26.1	20.7	17.6	17.6	17.6	17.6	17.6
97.5°	45.4	48.7	50.9	68.2	72.0	69.6	56.7	47.7	42.6	40.3	42.6
100°	64.4	65.9	70.5	71.3	90.4	108.8	99.6	88.1	84.3	82.0	84.3
102.5°	83.4	84.3	91.3	94.6	99.0	109.4	141.3	137.8	135.2	134.7	135.2
105°	111.9	112.6	125.7	131.8	134.9	134.9	134.1	149.4	173.9	179.3	173.9
107.5°	142.4	145.9	161.2	177.6	181.1	182.1	178.1	175.8	174.9	175.5	174.9
110°	163.2	168.6	187.0	207.7	213.0	214.6	213.0	210.7	209.2	209.2	209.2



TEST NUMBER: P1435771

CATALOG NUMBER: SQ2W-FA-K-050U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	183.4	191.3	212.1	235.9	244.9	249.5	246.1	244.4	242.9	244.1	242.9
115°	214.6	226.1	253.6	278.2	296.6	298.8	298.1	298.1	297.3	297.3	297.3
117.5°	243.4	261.8	292.7	321.2	342.5	348.7	351.7	350.8	349.9	351.4	349.9
120°	263.6	285.1	320.3	352.5	373.2	382.4	385.4	383.9	385.4	383.9	385.4
122.5°	285.1	311.4	346.1	379.5	403.8	414.3	417.9	418.2	418.5	417.6	418.5
125°	317.2	349.4	390.0	424.5	449.8	462.1	465.1	465.9	467.4	471.3	467.4
127.5°	349.7	386.2	430.8	464.1	490.0	504.8	509.6	511.3	514.5	516.2	514.5
130°	372.4	413.8	459.0	490.4	515.7	531.8	540.2	542.5	546.4	545.6	546.4
132.5°	396.3	439.5	485.4	518.0	541.5	558.8	566.0	572.6	573.9	575.0	573.9
135°	431.4	478.2	524.1	556.3	578.5	595.4	604.6	610.7	614.6	616.9	614.6
137.5°	468.4	517.7	561.8	590.5	612.9	627.4	637.9	644.3	648.3	650.1	648.3
140°	493.5	541.0	583.9	613.8	633.7	648.3	657.5	665.1	669.7	669.7	669.7
142.5°	517.4	564.3	606.0	635.9	653.3	666.7	676.5	682.3	687.5	687.5	687.5
145°	551.0	597.7	636.0	665.9	680.5	692.7	703.4	708.0	711.1	711.1	711.1
147.5°	586.1	627.4	662.4	691.0	703.3	717.7	726.1	729.8	733.6	732.0	733.6
150°	606.9	645.2	678.9	705.7	718.0	731.8	740.2	743.3	747.1	744.8	747.1
152.5°	627.1	663.6	694.2	719.2	729.7	743.4	753.1	756.2	758.8	757.1	758.8
155°	654.4	686.6	714.9	737.9	747.1	760.1	769.3	773.2	776.2	772.4	776.2
157.5°	678.8	706.5	731.2	752.3	762.1	773.3	781.9	786.7	789.7	788.0	789.7
160°	693.5	718.8	741.0	760.9	770.1	780.1	789.3	794.6	797.7	795.4	797.7
162.5°	705.7	728.6	749.6	767.7	775.6	784.4	795.4	800.1	803.2	800.3	803.2
165°	723.4	741.8	760.1	775.5	782.4	789.3	800.8	806.1	808.4	805.4	808.4
167.5°	736.7	750.8	765.7	778.8	783.9	790.6	802.1	806.6	809.5	805.7	809.5
170°	744.1	756.3	769.3	780.1	783.9	790.0	801.5	805.4	807.7	803.8	807.7
172.5°	750.2	759.4	770.0	779.5	781.5	786.4	797.2	801.1	802.8	799.5	802.8
175°	756.3	761.7	769.3	775.5	774.7	777.8	787.0	790.0	793.1	788.5	793.1
177.5°	759.2	761.7	764.1	767.8	765.4	765.4	772.1	773.9	774.6	772.1	774.6
180°	758.6	758.6	758.6	758.6	758.6	758.6	758.6	758.6	758.6	758.6	758.6



TEST NUMBER: P1435771

CATALOG NUMBER: SQ2W-FA-K-050U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7
2.5°	1320.8	1320.8	1320.8	1320.8	1320.8	1318.6	1309.6	1300.5	1300.5	1300.5	1293.8
5°	1340.2	1337.4	1335.1	1331.8	1327.3	1319.9	1304.1	1288.4	1281.6	1274.8	1246.1
7.5°	1348.8	1345.2	1341.1	1335.7	1328.9	1318.6	1297.4	1276.2	1246.0	1215.8	1151.7
10°	1344.7	1342.5	1340.2	1335.7	1328.9	1317.7	1292.9	1268.1	1207.2	1146.3	1085.5
12.5°	1340.7	1338.4	1336.2	1330.7	1322.2	1309.1	1282.5	1255.9	1169.8	1083.7	1028.7
15°	1329.5	1325.6	1321.1	1315.4	1308.7	1294.6	1258.5	1222.4	1125.5	1028.5	982.3
17.5°	1309.1	1305.6	1301.6	1295.0	1286.0	1268.3	1224.6	1180.8	1079.4	977.9	948.2
20°	1288.4	1286.7	1284.4	1278.8	1269.8	1251.2	1203.8	1156.5	1055.0	953.6	940.1
22.5°	1264.5	1263.7	1263.2	1258.5	1249.5	1229.5	1176.8	1124.0	1024.4	924.7	925.2
25°	1223.6	1224.1	1226.4	1220.7	1207.2	1181.8	1121.0	1060.1	972.2	884.3	899.5
27.5°	1179.8	1178.1	1175.9	1170.2	1161.2	1135.3	1058.6	982.0	912.6	843.1	868.4
30°	1151.4	1149.7	1147.5	1141.8	1132.8	1104.6	1019.0	933.3	874.7	816.1	845.4
32.5°	1118.9	1118.6	1118.2	1114.3	1107.1	1076.2	974.3	872.4	830.1	787.7	818.3
35°	1069.7	1070.3	1070.3	1068.0	1063.5	1029.1	905.1	781.1	763.1	745.1	781.1
37.5°	1013.9	1016.8	1020.0	1018.2	1011.4	971.2	830.5	689.8	695.7	701.6	745.3
40°	973.3	979.0	985.7	985.7	979.0	935.6	782.3	629.0	649.3	669.5	716.9
42.5°	932.7	939.7	948.3	949.2	942.4	899.5	748.0	596.5	618.6	640.7	689.8
45°	871.3	879.2	888.2	889.3	882.6	843.7	708.4	573.2	586.7	600.2	647.6
47.5°	799.3	810.6	824.1	825.2	813.9	775.7	656.7	537.7	547.6	557.5	606.0
50°	754.6	765.9	779.4	780.6	769.3	731.5	614.3	497.1	510.6	524.1	574.9
52.5°	701.9	714.5	729.8	732.8	723.3	688.7	578.7	468.7	476.8	484.9	539.7
55°	627.3	640.8	656.6	661.1	654.3	626.1	533.7	441.3	434.5	427.8	483.6
57.5°	548.9	564.4	582.4	587.8	580.6	553.2	465.3	377.4	371.5	365.7	426.1
60°	499.3	515.7	533.7	538.2	529.2	502.7	423.8	344.9	333.6	322.4	385.5
62.5°	450.6	467.0	485.0	487.7	475.1	448.2	378.3	308.4	300.7	293.1	354.4
65°	377.6	393.9	412.0	413.1	397.3	370.3	309.4	248.5	253.1	257.6	312.8
67.5°	306.1	323.3	343.1	344.0	326.0	299.4	247.1	194.8	209.7	224.5	274.2
70°	261.5	277.3	295.3	295.3	277.3	252.5	207.4	162.3	182.6	202.9	248.5
72.5°	217.3	234.0	253.8	253.8	234.0	210.6	176.3	142.0	162.3	182.6	220.1
75°	161.2	175.8	193.9	191.6	169.1	147.1	126.8	106.5	126.8	147.1	175.8
77.5°	108.1	120.0	135.4	133.1	113.3	96.0	86.6	77.1	93.8	110.5	130.5
80°	76.1	86.2	99.8	97.5	79.5	65.4	63.1	60.9	72.1	83.4	98.1
82.5°	51.3	59.2	69.1	67.7	55.1	45.1	42.8	40.6	50.0	59.5	69.7
85°	20.3	23.7	28.2	28.2	23.7	20.3	20.3	20.3	24.8	29.3	33.8
87.5°	7.3	8.5	10.3	10.1	7.9	5.9	5.1	4.5	6.9	9.4	10.9
90°	16.1	15.3	15.3	14.6	12.3	9.2	5.4	2.3	5.4	8.4	13.8
92.5°	19.2	19.0	17.8	16.4	13.5	13.5	13.3	8.4	14.6	20.7	29.7
95°	17.6	17.6	20.7	26.1	38.3	39.1	26.1	23.8	33.7	47.5	59.8
97.5°	47.7	56.7	69.6	72.0	68.2	50.9	48.7	45.4	61.8	75.4	95.2
100°	88.1	99.6	108.8	90.4	71.3	70.5	65.9	64.4	82.0	95.0	114.2
102.5°	137.8	141.3	109.4	99.0	94.6	91.3	84.3	83.4	101.0	118.9	135.0
105°	149.4	134.1	134.9	134.9	131.8	125.7	112.6	111.9	131.8	152.5	172.4
107.5°	175.8	178.1	182.1	181.1	177.6	161.2	145.9	142.4	160.3	185.1	207.0
110°	210.7	213.0	214.6	213.0	207.7	187.0	168.6	163.2	179.3	205.4	229.1

TEST NUMBER: P1435771

CATALOG NUMBER: SQ2W-FA-K-050U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	244.4	246.1	249.5	244.9	235.9	212.1	191.3	183.4	199.5	226.2	250.6
115°	298.1	298.1	298.8	296.6	278.2	253.6	226.1	214.6	228.4	252.9	279.7
117.5°	350.8	351.7	348.7	342.5	321.2	292.7	261.8	243.4	254.3	280.2	307.7
120°	383.9	385.4	382.4	373.2	352.5	320.3	285.1	263.6	272.0	297.3	324.9
122.5°	418.2	417.9	414.3	403.8	379.5	346.1	311.4	285.1	288.6	312.0	339.0
125°	465.9	465.1	462.1	449.8	424.5	390.0	349.4	317.2	312.6	332.6	360.2
127.5°	511.3	509.6	504.8	490.0	464.1	430.8	386.2	349.7	339.5	352.0	377.3
130°	542.5	540.2	531.8	515.7	490.4	459.0	413.8	372.4	357.9	365.5	387.7
132.5°	572.6	566.0	558.8	541.5	518.0	485.4	439.5	396.3	376.2	379.6	396.9
135°	610.7	604.6	595.4	578.5	556.3	524.1	478.2	431.4	403.8	400.8	410.7
137.5°	644.3	637.9	627.4	612.9	590.5	561.8	517.7	468.4	433.6	423.3	427.1
140°	665.1	657.5	648.3	633.7	613.8	583.9	541.0	493.5	454.4	439.8	437.5
142.5°	682.3	676.5	666.7	653.3	635.9	606.0	564.3	517.4	475.9	457.0	451.6
145°	708.0	703.4	692.7	680.5	665.9	636.0	597.7	551.0	509.6	485.1	473.6
147.5°	729.8	726.1	717.7	703.3	691.0	662.4	627.4	586.1	543.6	513.3	498.4
150°	743.3	740.2	731.8	718.0	705.7	678.9	645.2	606.9	566.3	534.1	514.9
152.5°	756.2	753.1	743.4	729.7	719.2	694.2	663.6	627.1	585.9	553.7	533.9
155°	773.2	769.3	760.1	747.1	737.9	714.9	686.6	654.4	619.2	585.4	563.2
157.5°	786.7	781.9	773.3	762.1	752.3	731.2	706.5	678.8	648.0	615.8	593.1
160°	794.6	789.3	780.1	770.1	760.9	741.0	718.8	693.5	665.1	636.0	611.5
162.5°	800.1	795.4	784.4	775.6	767.7	749.6	728.6	705.7	680.5	655.0	632.3
165°	806.1	800.8	789.3	782.4	775.5	760.1	741.8	723.4	701.9	681.2	662.8
167.5°	806.6	802.1	790.6	783.9	778.8	765.7	750.8	736.7	720.0	703.8	688.4
170°	805.4	801.5	790.0	783.9	780.1	769.3	756.3	744.1	731.0	717.2	705.0
172.5°	801.1	797.2	786.4	781.5	779.5	770.0	759.4	750.2	739.0	728.9	719.1
175°	790.0	787.0	777.8	774.7	775.5	769.3	761.7	756.3	749.4	743.3	737.9
177.5°	773.9	772.1	765.4	765.4	767.8	764.1	761.7	759.2	756.2	754.3	752.5
180°	758.6	758.6	758.6	758.6	758.6	758.6	758.6	758.6	758.6	758.6	758.6



TEST NUMBER: P1435771

CATALOG NUMBER: SQ2W-FA-K-050U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7
2.5°	1284.8	1277.5	1272.1	1267.6	1265.8	1264.0	1265.8	1267.6	1272.1	1277.5	1284.8
5°	1210.0	1171.7	1131.1	1097.9	1086.6	1075.3	1086.6	1097.9	1131.1	1171.7	1210.0
7.5°	1076.5	1030.2	1013.1	999.4	995.7	992.1	995.7	999.4	1013.1	1030.2	1076.5
10°	1024.6	987.4	973.9	963.7	963.7	963.7	963.7	963.7	973.9	987.4	1024.6
12.5°	984.0	961.3	960.4	961.9	971.0	980.0	971.0	961.9	960.4	961.3	984.0
15°	953.0	956.4	992.5	1022.3	1033.6	1044.9	1033.6	1022.3	992.5	956.4	953.0
17.5°	942.3	961.7	1006.3	1042.1	1051.1	1060.1	1051.1	1042.1	1006.3	961.7	942.3
20°	955.8	980.6	1014.5	1042.1	1051.1	1060.1	1051.1	1042.1	1014.5	980.6	955.8
22.5°	959.0	989.2	1015.8	1038.0	1047.0	1056.1	1047.0	1038.0	1015.8	989.2	959.0
25°	949.1	985.2	1007.7	1025.7	1030.2	1034.7	1030.2	1025.7	1007.7	985.2	949.1
27.5°	925.2	964.9	987.4	1005.1	1008.3	1011.4	1008.3	1005.1	987.4	964.9	925.2
30°	904.0	944.6	967.1	985.7	992.5	999.2	992.5	985.7	967.1	944.6	904.0
32.5°	873.3	914.8	942.8	964.1	965.4	966.8	965.4	964.1	942.8	914.8	873.3
35°	835.2	878.1	909.6	932.7	930.5	928.2	930.5	932.7	909.6	878.1	835.2
37.5°	801.6	843.6	871.1	892.4	895.1	897.8	895.1	892.4	871.1	843.6	801.6
40°	773.2	816.1	845.4	868.5	873.0	877.5	873.0	868.5	845.4	816.1	773.2
42.5°	748.0	791.7	821.0	844.1	848.7	853.2	848.7	844.1	821.0	791.7	748.0
45°	706.2	751.3	782.8	807.1	809.3	811.6	809.3	807.1	782.8	751.3	706.2
47.5°	667.3	712.6	741.9	764.5	766.7	769.0	766.7	764.5	741.9	712.6	667.3
50°	638.0	684.2	713.5	736.0	738.3	740.6	738.3	736.0	713.5	684.2	638.0
52.5°	610.0	658.0	683.7	703.6	705.8	708.1	705.8	703.6	683.7	658.0	610.0
55°	560.2	610.9	635.7	654.3	654.3	654.3	654.3	635.7	610.9	560.2	560.2
57.5°	508.6	560.7	582.3	599.2	601.9	604.6	601.9	599.2	582.3	560.7	508.6
60°	473.4	526.4	544.4	559.1	563.6	568.1	563.6	559.1	544.4	526.4	473.4
62.5°	438.7	489.9	507.9	522.1	524.8	527.5	524.8	522.1	507.9	489.9	438.7
65°	384.9	430.0	448.1	462.1	464.4	466.7	464.4	462.1	448.1	430.0	384.9
67.5°	335.6	372.5	385.2	395.1	396.9	398.7	396.9	395.1	385.2	372.5	335.6
70°	302.6	334.2	343.2	350.0	350.0	350.0	350.0	350.0	343.2	334.2	302.6
72.5°	263.4	289.6	298.6	305.8	307.6	309.4	307.6	305.8	298.6	289.6	263.4
75°	207.4	226.6	233.3	239.0	241.2	243.5	241.2	239.0	233.3	226.6	207.4
77.5°	151.7	164.3	168.4	172.0	174.3	176.5	174.3	172.0	168.4	164.3	151.7
80°	113.8	122.9	125.1	127.4	129.6	131.9	129.6	127.4	125.1	122.9	113.8
82.5°	80.0	86.3	88.6	90.4	90.9	91.3	90.9	90.4	88.6	86.3	80.0
85°	38.3	40.6	40.6	40.6	40.6	40.6	40.6	40.6	40.6	40.6	38.3
87.5°	11.6	12.7	13.8	14.4	15.0	14.7	15.0	14.4	13.8	12.7	11.6
90°	17.6	23.0	28.4	31.4	34.5	33.0	34.5	31.4	28.4	23.0	17.6
92.5°	35.4	44.4	51.0	56.6	59.0	58.7	59.0	56.6	51.0	44.4	35.4
95°	71.3	82.0	92.7	100.4	105.0	103.4	105.0	100.4	92.7	82.0	71.3
97.5°	109.9	124.3	136.2	143.4	148.0	151.1	148.0	143.4	136.2	124.3	109.9
100°	135.6	149.4	163.2	171.6	179.3	182.4	179.3	171.6	163.2	149.4	135.6
102.5°	156.5	174.6	189.6	198.6	205.1	208.1	205.1	198.6	189.6	174.6	156.5
105°	190.8	210.0	226.1	237.5	244.4	246.7	244.4	237.5	226.1	210.0	190.8
107.5°	225.1	244.9	259.8	272.5	280.9	285.8	280.9	272.5	259.8	244.9	225.1
110°	252.1	268.2	284.3	295.8	304.2	307.3	304.2	295.8	284.3	268.2	252.1



TEST NUMBER: P1435771

CATALOG NUMBER: SQ2W-FA-K-050U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	274.8	292.7	308.8	320.3	330.0	334.3	330.0	320.3	308.8	292.7	274.8
115°	306.5	330.3	344.8	355.6	362.5	366.3	362.5	355.6	344.8	330.3	306.5
117.5°	332.9	357.7	373.6	381.9	385.1	387.9	385.1	381.9	373.6	357.7	332.9
120°	349.4	372.4	390.8	401.5	405.4	406.9	405.4	401.5	390.8	372.4	349.4
122.5°	364.7	386.5	404.3	417.5	423.8	425.3	423.8	417.5	404.3	386.5	364.7
125°	386.2	406.9	425.3	438.3	445.2	449.0	445.2	438.3	425.3	406.9	386.2
127.5°	404.9	427.3	444.1	455.9	462.7	465.7	462.7	455.9	444.1	427.3	404.9
130°	415.3	438.3	455.2	468.2	474.3	477.4	474.3	468.2	455.2	438.3	415.3
132.5°	423.3	447.5	465.0	476.8	483.5	486.6	483.5	476.8	465.0	447.5	423.3
135°	432.9	458.2	476.6	488.1	494.3	497.3	494.3	488.1	476.6	458.2	432.9
137.5°	441.4	464.4	483.5	495.6	501.1	503.1	501.1	495.6	483.5	464.4	441.4
140°	447.5	467.4	486.6	498.1	504.2	505.0	504.2	498.1	486.6	467.4	447.5
142.5°	455.5	471.1	487.8	499.3	505.4	506.8	505.4	499.3	487.8	471.1	455.5
145°	469.7	478.9	490.4	501.1	506.5	508.0	506.5	501.1	490.4	478.9	469.7
147.5°	487.7	490.6	496.5	503.6	508.8	509.9	508.8	503.6	496.5	490.6	487.7
150°	501.1	500.4	502.7	507.3	511.9	511.1	511.9	507.3	502.7	500.4	501.1
152.5°	516.5	512.0	511.9	514.0	516.2	516.0	516.2	514.0	511.9	512.0	516.5
155°	542.5	534.1	529.5	528.0	528.0	527.2	528.0	528.0	529.5	534.1	542.5
157.5°	571.2	559.4	552.5	548.8	547.7	546.1	547.7	548.8	552.5	559.4	571.2
160°	590.8	577.8	570.9	564.7	562.4	560.2	562.4	564.7	570.9	577.8	590.8
162.5°	609.2	596.8	589.3	583.8	581.5	577.9	581.5	583.8	589.3	596.8	609.2
165°	639.1	626.1	617.6	613.0	610.0	606.9	610.0	613.0	617.6	626.1	639.1
167.5°	669.0	654.7	649.2	644.0	641.1	635.6	641.1	644.0	649.2	654.7	669.0
170°	687.4	674.3	671.3	666.7	661.3	655.2	661.3	666.7	671.3	674.3	687.4
172.5°	703.3	694.6	691.5	686.9	685.2	680.3	685.2	686.9	691.5	694.6	703.3
175°	726.4	719.5	719.5	718.8	716.5	711.9	716.5	718.8	719.5	719.5	726.4
177.5°	745.7	742.1	744.5	744.5	743.9	739.6	743.9	744.5	744.5	742.1	745.7
180°	758.6	758.6	758.6	758.6	758.6	758.6	758.6	758.6	758.6	758.6	758.6



TEST NUMBER: P1435771

CATALOG NUMBER: SQ2W-FA-K-050U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1308.7	1308.7	1308.7	1308.7
2.5°	1293.8	1300.5	1300.5	1300.5
5°	1246.1	1274.8	1281.6	1288.4
7.5°	1151.7	1215.8	1246.0	1276.2
10°	1085.5	1146.3	1207.2	1268.1
12.5°	1028.7	1083.7	1169.8	1255.9
15°	982.3	1028.5	1125.5	1222.4
17.5°	948.2	977.9	1079.4	1180.8
20°	940.1	953.6	1055.0	1156.5
22.5°	925.2	924.7	1024.4	1124.0
25°	899.5	884.3	972.2	1060.1
27.5°	868.4	843.1	912.6	982.0
30°	845.4	816.1	874.7	933.3
32.5°	818.3	787.7	830.1	872.4
35°	781.1	745.1	763.1	781.1
37.5°	745.3	701.6	695.7	689.8
40°	716.9	669.5	649.3	629.0
42.5°	689.8	640.7	618.6	596.5
45°	647.6	600.2	586.7	573.2
47.5°	606.0	557.5	547.6	537.7
50°	574.9	524.1	510.6	497.1
52.5°	539.7	484.9	476.8	468.7
55°	483.6	427.8	434.5	441.3
57.5°	426.1	365.7	371.5	377.4
60°	385.5	322.4	333.6	344.9
62.5°	354.4	293.1	300.7	308.4
65°	312.8	257.6	253.1	248.5
67.5°	274.2	224.5	209.7	194.8
70°	248.5	202.9	182.6	162.3
72.5°	220.1	182.6	162.3	142.0
75°	175.8	147.1	126.8	106.5
77.5°	130.5	110.5	93.8	77.1
80°	98.1	83.4	72.1	60.9
82.5°	69.7	59.5	50.0	40.6
85°	33.8	29.3	24.8	20.3
87.5°	10.9	9.4	6.9	4.5
90°	13.8	8.4	5.4	2.3
92.5°	29.7	20.7	14.6	8.4
95°	59.8	47.5	33.7	23.8
97.5°	95.2	75.4	61.8	45.4
100°	114.2	95.0	82.0	64.4
102.5°	135.0	118.9	101.0	83.4
105°	172.4	152.5	131.8	111.9
107.5°	207.0	185.1	160.3	142.4
110°	229.1	205.4	179.3	163.2

TEST NUMBER: P1435771

CATALOG NUMBER: SQ2W-FA-K-050U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	250.6	226.2	199.5	183.4
115°	279.7	252.9	228.4	214.6
117.5°	307.7	280.2	254.3	243.4
120°	324.9	297.3	272.0	263.6
122.5°	339.0	312.0	288.6	285.1
125°	360.2	332.6	312.6	317.2
127.5°	377.3	352.0	339.5	349.7
130°	387.7	365.5	357.9	372.4
132.5°	396.9	379.6	376.2	396.3
135°	410.7	400.8	403.8	431.4
137.5°	427.1	423.3	433.6	468.4
140°	437.5	439.8	454.4	493.5
142.5°	451.6	457.0	475.9	517.4
145°	473.6	485.1	509.6	551.0
147.5°	498.4	513.3	543.6	586.1
150°	514.9	534.1	566.3	606.9
152.5°	533.9	553.7	585.9	627.1
155°	563.2	585.4	619.2	654.4
157.5°	593.1	615.8	648.0	678.8
160°	611.5	636.0	665.1	693.5
162.5°	632.3	655.0	680.5	705.7
165°	662.8	681.2	701.9	723.4
167.5°	688.4	703.8	720.0	736.7
170°	705.0	717.2	731.0	744.1
172.5°	719.1	728.9	739.0	750.2
175°	737.9	743.3	749.4	756.3
177.5°	752.5	754.3	756.2	759.2
180°	758.6	758.6	758.6	758.6

TEST NUMBER: P1435771
 CATALOG NUMBER: SQ2W-FA-K-050U-075D-L840-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.81	18.76	18.68	19.65	20.78	19.01	19.96	19.88	20.85	21.98
	3H	18.91	19.76	19.79	20.66	21.82	20.26	21.11	21.14	22.01	23.17
	4H	19.26	20.07	20.16	20.98	22.14	20.65	21.46	21.55	22.37	23.53
	6H	19.43	20.17	20.34	21.09	22.26	20.82	21.56	21.73	22.48	23.65
	8H	19.47	20.17	20.38	21.10	22.28	20.85	21.55	21.77	22.49	23.66
	12H	19.46	20.14	20.39	21.06	22.27	20.83	21.51	21.76	22.43	23.64
4H	2H	18.69	19.49	19.59	20.40	21.57	19.60	20.41	20.51	21.32	22.48
	3H	20.09	20.76	21.00	21.70	22.88	21.08	21.75	21.99	22.69	23.87
	4H	20.54	21.16	21.47	22.09	23.30	21.56	22.17	22.48	23.10	24.31
	6H	20.78	21.31	21.72	22.27	23.47	21.78	22.31	22.72	23.27	24.47
	8H	20.84	21.33	21.78	22.28	23.50	21.83	22.33	22.78	23.28	24.50
	12H	20.85	21.29	21.81	22.26	23.48	21.83	22.27	22.79	23.24	24.47
8H	4H	20.94	21.43	21.88	22.38	23.60	21.76	22.25	22.70	23.20	24.42
	6H	21.29	21.70	22.26	22.69	23.91	22.08	22.48	23.05	23.48	24.70
	8H	21.41	21.77	22.39	22.75	23.99	22.17	22.53	23.15	23.52	24.75
	12H	21.45	21.77	22.43	22.74	24.03	22.19	22.51	23.17	23.48	24.77
12H	4H	20.94	21.39	21.91	22.36	23.58	21.73	22.18	22.69	23.15	24.37
	6H	21.36	21.72	22.34	22.70	23.94	22.09	22.46	23.07	23.44	24.67
	8H	21.51	21.83	22.49	22.80	24.09	22.21	22.53	23.19	23.51	24.79