

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1435941

Luminaire Tested: SQ2W-FB-K-050U-075D-L935-UNV-STD-W-WM-4

Issue Date: 3/24/2026

Test Information

Test Method: LM-79-2019
Report Number: P1435941
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-12)
Test Lab: INNOVATION CENTER
Issue Date: 3/24/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-FB-K-050U-075D-L935-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - FROSTED CONTINUOUS BATWING ROLL LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4866.8 lumens
Efficiency: N/A
Efficacy: 117.0 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.52
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 41.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1435941

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L935-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1435941

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L935-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	100	96	91	88	93	89	86	83	78	76	73	68	66	64	58	57	55	51
2	91	83	76	71	84	78	72	67	68	64	60	59	56	53	51	48	46	42
3	82	72	65	58	77	68	61	55	59	54	50	52	47	44	44	41	38	35
4	75	64	55	49	70	60	52	46	52	46	42	46	41	37	39	36	33	29
5	69	56	48	41	64	53	45	39	46	40	36	40	36	32	35	31	28	25
6	63	50	42	36	59	47	40	34	42	35	31	36	31	27	31	27	24	21
7	58	45	37	31	54	43	35	29	37	31	27	33	28	24	28	24	21	19
8	54	41	33	27	50	38	31	26	34	28	23	30	25	21	26	22	19	16
9	50	37	29	24	47	35	28	23	31	25	21	27	22	19	24	20	17	14
10	47	34	26	21	43	32	25	20	28	23	19	25	20	17	22	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4845	4845	4845	4845
5°	4723	8580	4723	8580
10°	4423	16698	4423	16698
15°	4003	19217	4003	19217
20°	3545	20127	3545	20127
25°	3135	20457	3135	20457
30°	2770	20709	2770	20709
35°	2474	22263	2474	22263
40°	2251	23654	2251	23654
45°	2076	24770	2076	24770
50°	1957	25218	1957	25218
55°	1908	25421	1908	25421
60°	1957	25294	1957	25294
65°	2040	24580	2040	24580
70°	2110	18590	2110	18590
75°	2339	10262	2339	10262
80°	2417	9521	2417	9521
85°	2408	4001	2408	4001

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 52.5°
 Luminance: 25649 cd/sqm



TEST NUMBER: P1435941

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L935-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.3	1.0
10°-20°	229.4	4.7
20°-30°	403.6	8.3
30°-40°	522.5	10.7
40°-50°	576.2	11.8
50°-60°	537.8	11.1
60°-70°	415.5	8.5
70°-80°	191.5	3.9
80°-90°	39.3	0.8
90°-100°	51.8	1.1
100°-110°	151.1	3.1
110°-120°	246.5	5.1
120°-130°	312.9	6.4
130°-140°	334.8	6.9
140°-150°	312.6	6.4
150°-160°	257.2	5.3
160°-170°	172.5	3.5
170°-180°	61.3	1.3
0°-30°	683.3	14.0
0°-40°	1205.8	24.8
0°-60°	2319.8	47.7
0°-90°	2966.2	60.9
90°-120°	449.4	9.2
90°-150°	1409.7	29.0
90°-180°	1901.0	39.1
0°-180°	4866.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	300	300	300	300	300	
5°	291	529	291	529	291	27
15°	240	1150	240	1150	240	67
25°	176	1148	176	1148	176	81
35°	126	1130	126	1130	126	79
45°	91	1085	91	1085	91	70
55°	68	903	68	903	68	61
65°	53	643	53	643	53	52
75°	38	164	38	164	38	38
85°	13	22	13	22	13	14
90°	2	14	2	28	2	2
95°	20	15	20	89	20	25
105°	96	154	96	212	96	102
115°	184	255	184	314	184	181
125°	272	404	272	385	272	244
135°	370	529	370	427	370	286
145°	473	610	473	436	473	296
155°	562	663	562	452	562	258
165°	621	691	621	521	621	175
175°	649	677	649	611	649	62
180°	651	651	651	651	651	



TEST NUMBER: P1435941

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1
2.5°	297.7	303.4	309.0	315.1	321.2	327.9	335.1	341.2	344.3	347.4	344.3
5°	291.4	310.6	329.9	357.8	388.5	423.5	462.6	496.1	512.8	529.4	512.8
7.5°	280.1	319.3	358.4	441.2	538.7	639.9	744.8	831.8	865.1	898.4	865.1
10°	269.8	324.3	378.8	519.3	688.6	818.7	909.8	982.6	1000.5	1018.5	1000.5
12.5°	258.2	332.2	406.2	579.7	786.4	921.7	985.6	1038.1	1056.5	1075.0	1056.5
15°	239.5	345.3	451.0	647.2	873.6	1012.7	1064.6	1108.7	1129.2	1149.7	1129.2
17.5°	220.1	360.9	501.7	701.9	921.8	1057.4	1108.9	1150.2	1161.4	1172.5	1161.4
20°	206.3	371.7	537.1	737.6	949.9	1078.1	1122.3	1157.3	1164.3	1171.4	1164.3
22.5°	193.6	378.5	563.4	764.2	970.2	1090.0	1123.5	1150.5	1158.0	1165.6	1158.0
25°	176.0	384.4	592.7	792.9	990.4	1099.7	1120.9	1138.0	1143.2	1148.3	1143.2
27.5°	159.0	379.1	599.3	797.0	987.1	1089.1	1103.0	1114.6	1119.6	1124.6	1119.6
30°	148.6	372.3	596.1	792.0	978.5	1077.0	1087.2	1096.7	1103.7	1110.8	1103.7
32.5°	139.4	364.1	588.9	782.4	965.3	1061.7	1071.5	1082.6	1097.8	1113.1	1097.8
35°	125.5	346.7	567.9	759.3	940.7	1039.1	1054.5	1073.1	1101.3	1129.5	1101.3
37.5°	113.7	324.4	535.0	724.5	906.8	1014.1	1046.3	1077.2	1104.4	1131.6	1104.4
40°	106.8	308.7	510.7	698.7	882.1	995.2	1038.2	1076.2	1099.2	1122.3	1099.2
42.5°	99.8	291.0	482.2	668.7	853.6	971.1	1021.2	1064.6	1087.7	1110.8	1087.7
45°	90.9	262.7	434.5	619.3	808.5	932.5	991.5	1041.2	1063.0	1084.8	1063.0
47.5°	82.5	231.8	381.0	566.6	764.4	894.5	957.1	1008.0	1023.9	1039.8	1023.9
50°	77.9	211.3	344.6	530.9	734.8	867.5	929.0	978.4	991.2	1004.0	991.2
52.5°	73.3	191.3	309.2	495.9	705.4	839.1	897.1	943.5	955.3	967.1	955.3
55°	67.8	164.0	260.1	444.8	658.9	791.3	842.0	882.5	892.8	903.1	892.8
57.5°	62.9	140.5	218.1	396.9	609.5	737.4	780.6	815.1	823.5	831.8	823.5
60°	60.6	127.9	195.2	366.9	573.3	696.1	735.2	766.7	775.0	783.3	775.0
62.5°	57.1	115.7	174.3	336.9	534.1	650.7	686.8	715.7	723.6	731.4	723.6
65°	53.4	100.8	148.3	294.8	474.3	579.1	609.2	633.1	638.3	643.4	638.3
67.5°	48.2	88.4	128.7	256.2	412.8	500.4	519.1	530.8	521.2	511.5	521.2
70°	44.7	81.9	119.1	232.7	371.9	444.6	451.0	449.0	421.4	393.8	421.4
72.5°	42.4	75.5	108.6	207.0	327.1	380.1	366.0	342.4	290.2	238.0	290.2
75°	37.5	64.4	91.4	165.4	255.2	269.3	207.7	161.9	163.2	164.5	163.2
77.5°	30.6	50.7	70.8	116.4	170.4	181.1	148.5	124.4	125.5	126.7	125.5
80°	26.0	42.0	58.0	76.0	94.6	103.2	101.9	101.1	101.8	102.4	101.8
82.5°	21.4	33.3	45.2	56.0	66.4	72.2	73.5	74.2	73.3	72.4	73.3
85°	13.0	20.0	27.1	31.3	34.5	33.5	28.4	24.2	22.9	21.6	22.9
87.5°	5.0	8.1	11.3	11.0	9.3	8.4	8.4	8.5	8.7	8.7	8.7
90°	2.0	4.6	7.9	10.5	12.5	13.2	13.2	13.8	14.5	14.5	14.5
92.5°	7.2	11.4	11.6	11.6	14.1	15.3	16.3	16.4	17.1	17.1	17.1
95°	20.4	22.4	33.5	32.9	22.4	17.8	15.1	15.1	15.1	15.1	15.1
97.5°	38.9	41.8	43.7	58.5	61.8	59.7	48.7	40.9	36.6	34.6	36.6
100°	55.2	56.5	60.5	61.1	77.6	93.4	85.5	75.6	72.3	70.4	72.3
102.5°	71.5	72.3	78.4	81.1	85.0	93.9	121.2	118.2	116.0	115.6	116.0
105°	96.0	96.7	107.8	113.1	115.7	115.7	115.1	128.2	149.3	153.9	149.3
107.5°	122.2	125.2	138.3	152.4	155.4	156.2	152.8	150.8	150.0	150.6	150.0
110°	140.1	144.7	160.4	178.2	182.8	184.1	182.8	180.8	179.5	179.5	179.5



TEST NUMBER: P1435941

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	157.4	164.1	182.0	202.4	210.1	214.1	211.2	209.8	208.4	209.5	208.4
115°	184.1	194.0	217.6	238.7	254.5	256.4	255.8	255.8	255.1	255.1	255.1
117.5°	208.8	224.6	251.2	275.6	293.9	299.2	301.8	301.0	300.2	301.5	300.2
120°	226.2	244.6	274.8	302.5	320.2	328.1	330.7	329.4	330.7	329.4	330.7
122.5°	244.6	267.2	296.9	325.6	346.5	355.5	358.6	358.9	359.1	358.4	359.1
125°	272.2	299.8	334.7	364.3	386.0	396.5	399.1	399.8	401.1	404.4	401.1
127.5°	300.1	331.4	369.7	398.2	420.4	433.2	437.3	438.7	441.5	442.9	441.5
130°	319.6	355.1	393.9	420.8	442.5	456.3	463.6	465.5	468.8	468.2	468.8
132.5°	340.1	377.2	416.5	444.5	464.6	479.5	485.6	491.3	492.5	493.4	492.5
135°	370.2	410.3	449.7	477.4	496.4	510.9	518.8	524.0	527.3	529.3	527.3
137.5°	401.9	444.2	482.1	506.7	525.9	538.4	547.3	552.8	556.3	557.8	556.3
140°	423.4	464.2	501.0	526.7	543.8	556.3	564.2	570.7	574.7	574.7	574.7
142.5°	444.0	484.2	520.0	545.6	560.6	572.0	580.5	585.5	589.9	589.9	589.9
145°	472.8	512.9	545.7	571.4	583.9	594.4	603.6	607.6	610.2	610.2	610.2
147.5°	502.9	538.4	568.4	593.0	603.5	615.8	623.1	626.2	629.5	628.1	629.5
150°	520.8	553.6	582.6	605.6	616.1	627.9	635.2	637.8	641.1	639.1	641.1
152.5°	538.1	569.4	595.7	617.2	626.1	637.9	646.2	648.8	651.1	649.6	651.1
155°	561.5	589.1	613.5	633.2	641.1	652.3	660.2	663.4	666.1	662.8	666.1
157.5°	582.4	606.2	627.4	645.6	654.0	663.6	670.9	675.0	677.6	676.2	677.6
160°	595.1	616.8	635.8	652.9	660.8	669.4	677.3	681.9	684.5	682.5	684.5
162.5°	605.6	625.2	643.2	658.7	665.5	673.0	682.5	686.6	689.2	686.7	689.2
165°	620.7	636.5	652.3	665.4	671.3	677.3	687.1	691.7	693.7	691.1	693.7
167.5°	632.1	644.2	657.0	668.3	672.6	678.4	688.3	692.1	694.6	691.3	694.6
170°	638.5	649.0	660.2	669.4	672.6	677.9	687.8	691.1	693.0	689.7	693.0
172.5°	643.7	651.6	660.7	668.8	670.5	674.8	684.1	687.4	688.8	686.1	688.8
175°	649.0	653.6	660.2	665.4	664.8	667.4	675.3	677.9	680.5	676.6	680.5
177.5°	651.5	653.6	655.7	658.8	656.7	656.7	662.5	664.1	664.6	662.5	664.6
180°	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9



TEST NUMBER: P1435941

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1
2.5°	341.2	335.1	327.9	321.2	315.1	309.0	303.4	297.7	303.4	309.0	315.1
5°	496.1	462.6	423.5	388.5	357.8	329.9	310.6	291.4	310.6	329.9	357.8
7.5°	831.8	744.8	639.9	538.7	441.2	358.4	319.3	280.1	319.3	358.4	441.2
10°	982.6	909.8	818.7	688.6	519.3	378.8	324.3	269.8	324.3	378.8	519.3
12.5°	1038.1	985.6	921.7	786.4	579.7	406.2	332.2	258.2	332.2	406.2	579.7
15°	1108.7	1064.6	1012.7	873.6	647.2	451.0	345.3	239.5	345.3	451.0	647.2
17.5°	1150.2	1108.9	1057.4	921.8	701.9	501.7	360.9	220.1	360.9	501.7	701.9
20°	1157.3	1122.3	1078.1	949.9	737.6	537.1	371.7	206.3	371.7	537.1	737.6
22.5°	1150.5	1123.5	1090.0	970.2	764.2	563.4	378.5	193.6	378.5	563.4	764.2
25°	1138.0	1120.9	1099.7	990.4	792.9	592.7	384.4	176.0	384.4	592.7	792.9
27.5°	1114.6	1103.0	1089.1	987.1	797.0	599.3	379.1	159.0	379.1	599.3	797.0
30°	1096.7	1087.2	1077.0	978.5	792.0	596.1	372.3	148.6	372.3	596.1	792.0
32.5°	1082.6	1071.5	1061.7	965.3	782.4	588.9	364.1	139.4	364.1	588.9	782.4
35°	1073.1	1054.5	1039.1	940.7	759.3	567.9	346.7	125.5	346.7	567.9	759.3
37.5°	1077.2	1046.3	1014.1	906.8	724.5	535.0	324.4	113.7	324.4	535.0	724.5
40°	1076.2	1038.2	995.2	882.1	698.7	510.7	308.7	106.8	308.7	510.7	698.7
42.5°	1064.6	1021.2	971.1	853.6	668.7	482.2	291.0	99.8	291.0	482.2	668.7
45°	1041.2	991.5	932.5	808.5	619.3	434.5	262.7	90.9	262.7	434.5	619.3
47.5°	1008.0	957.1	894.5	764.4	566.6	381.0	231.8	82.5	231.8	381.0	566.6
50°	978.4	929.0	867.5	734.8	530.9	344.6	211.3	77.9	211.3	344.6	530.9
52.5°	943.5	897.1	839.1	705.4	495.9	309.2	191.3	73.3	191.3	309.2	495.9
55°	882.5	842.0	791.3	658.9	444.8	260.1	164.0	67.8	164.0	260.1	444.8
57.5°	815.1	780.6	737.4	609.5	396.9	218.1	140.5	62.9	140.5	218.1	396.9
60°	766.7	735.2	696.1	573.3	366.9	195.2	127.9	60.6	127.9	195.2	366.9
62.5°	715.7	686.8	650.7	534.1	336.9	174.3	115.7	57.1	115.7	174.3	336.9
65°	633.1	609.2	579.1	474.3	294.8	148.3	100.8	53.4	100.8	148.3	294.8
67.5°	530.8	519.1	500.4	412.8	256.2	128.7	88.4	48.2	88.4	128.7	256.2
70°	449.0	451.0	444.6	371.9	232.7	119.1	81.9	44.7	81.9	119.1	232.7
72.5°	342.4	366.0	380.1	327.1	207.0	108.6	75.5	42.4	75.5	108.6	207.0
75°	161.9	207.7	269.3	255.2	165.4	91.4	64.4	37.5	64.4	91.4	165.4
77.5°	124.4	148.5	181.1	170.4	116.4	70.8	50.7	30.6	50.7	70.8	116.4
80°	101.1	101.9	103.2	94.6	76.0	58.0	42.0	26.0	42.0	58.0	76.0
82.5°	74.2	73.5	72.2	66.4	56.0	45.2	33.3	21.4	33.3	45.2	56.0
85°	24.2	28.4	33.5	34.5	31.3	27.1	20.0	13.0	20.0	27.1	31.3
87.5°	8.5	8.4	8.4	9.3	11.0	11.3	8.1	5.0	8.1	11.2	11.2
90°	13.8	13.2	13.2	12.5	10.5	7.9	4.6	2.0	4.6	7.2	11.8
92.5°	16.4	16.3	15.3	14.1	11.6	11.6	11.4	7.2	12.5	17.8	25.5
95°	15.1	15.1	17.8	22.4	32.9	33.5	22.4	20.4	28.9	40.8	51.3
97.5°	40.9	48.7	59.7	61.8	58.5	43.7	41.8	38.9	53.0	64.7	81.7
100°	75.6	85.5	93.4	77.6	61.1	60.5	56.5	55.2	70.4	81.5	98.0
102.5°	118.2	121.2	93.9	85.0	81.1	78.4	72.3	71.5	86.7	102.0	115.9
105°	128.2	115.1	115.7	115.7	113.1	107.8	96.7	96.0	113.1	130.8	147.9
107.5°	150.8	152.8	156.2	155.4	152.4	138.3	125.2	122.2	137.6	158.9	177.7
110°	180.8	182.8	184.1	182.8	178.2	160.4	144.7	140.1	153.9	176.2	196.6



TEST NUMBER: P1435941

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	209.8	211.2	214.1	210.1	202.4	182.0	164.1	157.4	171.2	194.1	215.0
115°	255.8	255.8	256.4	254.5	238.7	217.6	194.0	184.1	195.9	217.0	240.0
117.5°	301.0	301.8	299.2	293.9	275.6	251.2	224.6	208.8	218.2	240.4	264.1
120°	329.4	330.7	328.1	320.2	302.5	274.8	244.6	226.2	233.4	255.1	278.8
122.5°	358.9	358.6	355.5	346.5	325.6	296.9	267.2	244.6	247.6	267.7	290.9
125°	399.8	399.1	396.5	386.0	364.3	334.7	299.8	272.2	268.3	285.4	309.0
127.5°	438.7	437.3	433.2	420.4	398.2	369.7	331.4	300.1	291.3	302.1	323.8
130°	465.5	463.6	456.3	442.5	420.8	393.9	355.1	319.6	307.1	313.6	332.7
132.5°	491.3	485.6	479.5	464.6	444.5	416.5	377.2	340.1	322.8	325.7	340.6
135°	524.0	518.8	510.9	496.4	477.4	449.7	410.3	370.2	346.5	343.9	352.4
137.5°	552.8	547.3	538.4	525.9	506.7	482.1	444.2	401.9	372.0	363.2	366.5
140°	570.7	564.2	556.3	543.8	526.7	501.0	464.2	423.4	389.9	377.4	375.4
142.5°	585.5	580.5	572.0	560.6	545.6	520.0	484.2	444.0	408.3	392.1	387.5
145°	607.6	603.6	594.4	583.9	571.4	545.7	512.9	472.8	437.3	416.2	406.4
147.5°	626.2	623.1	615.8	603.5	593.0	568.4	538.4	502.9	466.4	440.4	427.7
150°	637.8	635.2	627.9	616.1	605.6	582.6	553.6	520.8	485.9	458.3	441.9
152.5°	648.8	646.2	637.9	626.1	617.2	595.7	569.4	538.1	502.7	475.1	458.2
155°	663.4	660.2	652.3	641.1	633.2	613.5	589.1	561.5	531.3	502.3	483.3
157.5°	675.0	670.9	663.6	654.0	645.6	627.4	606.2	582.4	556.0	528.4	508.9
160°	681.9	677.3	669.4	660.8	652.9	635.8	616.8	595.1	570.7	545.7	524.7
162.5°	686.6	682.5	673.0	665.5	658.7	643.2	625.2	605.6	583.9	562.1	542.6
165°	691.7	687.1	677.3	671.3	665.4	652.3	636.5	620.7	602.3	584.5	568.8
167.5°	692.1	688.3	678.4	672.6	668.3	657.0	644.2	632.1	617.8	603.9	590.7
170°	691.1	687.8	677.9	672.6	669.4	660.2	649.0	638.5	627.3	615.4	604.9
172.5°	687.4	684.1	674.8	670.5	668.8	660.7	651.6	643.7	634.1	625.4	617.0
175°	677.9	675.3	667.4	664.8	665.4	660.2	653.6	649.0	643.1	637.8	633.2
177.5°	664.1	662.5	656.7	656.7	658.8	655.7	653.6	651.5	648.8	647.3	645.7
180°	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9



TEST NUMBER: P1435941

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1
2.5°	321.2	327.9	335.1	341.2	344.3	347.4	344.3	341.2	335.1	327.9	321.2
5°	388.5	423.5	462.6	496.1	512.8	529.4	512.8	496.1	462.6	423.5	388.5
7.5°	538.7	639.9	744.8	831.8	865.1	898.4	865.1	831.8	744.8	639.9	538.7
10°	688.6	818.7	909.8	982.6	1000.5	1018.5	1000.5	982.6	909.8	818.7	688.6
12.5°	786.4	921.7	985.6	1038.1	1056.5	1075.0	1056.5	1038.1	985.6	921.7	786.4
15°	873.6	1012.7	1064.6	1108.7	1129.2	1149.7	1129.2	1108.7	1064.6	1012.7	873.6
17.5°	921.8	1057.4	1108.9	1150.2	1161.4	1172.5	1161.4	1150.2	1108.9	1057.4	921.8
20°	949.9	1078.1	1122.3	1157.3	1164.3	1171.4	1164.3	1157.3	1122.3	1078.1	949.9
22.5°	970.2	1090.0	1123.5	1150.5	1158.0	1165.6	1158.0	1150.5	1123.5	1090.0	970.2
25°	990.4	1099.7	1120.9	1138.0	1143.2	1148.3	1143.2	1138.0	1120.9	1099.7	990.4
27.5°	987.1	1089.1	1103.0	1114.6	1119.6	1124.6	1119.6	1114.6	1103.0	1089.1	987.1
30°	978.5	1077.0	1087.2	1096.7	1103.7	1110.8	1103.7	1096.7	1087.2	1077.0	978.5
32.5°	965.3	1061.7	1071.5	1082.6	1097.8	1113.1	1097.8	1082.6	1071.5	1061.7	965.3
35°	940.7	1039.1	1054.5	1073.1	1101.3	1129.5	1101.3	1073.1	1054.5	1039.1	940.7
37.5°	906.8	1014.1	1046.3	1077.2	1104.4	1131.6	1104.4	1077.2	1046.3	1014.1	906.8
40°	882.1	995.2	1038.2	1076.2	1099.2	1122.3	1099.2	1076.2	1038.2	995.2	882.1
42.5°	853.6	971.1	1021.2	1064.6	1087.7	1110.8	1087.7	1064.6	1021.2	971.1	853.6
45°	808.5	932.5	991.5	1041.2	1063.0	1084.8	1063.0	1041.2	991.5	932.5	808.5
47.5°	764.4	894.5	957.1	1008.0	1023.9	1039.8	1023.9	1008.0	957.1	894.5	764.4
50°	734.8	867.5	929.0	978.4	991.2	1004.0	991.2	978.4	929.0	867.5	734.8
52.5°	705.4	839.1	897.1	943.5	955.3	967.1	955.3	943.5	897.1	839.1	705.4
55°	658.9	791.3	842.0	882.5	892.8	903.1	892.8	882.5	842.0	791.3	658.9
57.5°	609.5	737.4	780.6	815.1	823.5	831.8	823.5	815.1	780.6	737.4	609.5
60°	573.3	696.1	735.2	766.7	775.0	783.3	775.0	766.7	735.2	696.1	573.3
62.5°	534.1	650.7	686.8	715.7	723.6	731.4	723.6	715.7	686.8	650.7	534.1
65°	474.3	579.1	609.2	633.1	638.3	643.4	638.3	633.1	609.2	579.1	474.3
67.5°	412.8	500.4	519.1	530.8	521.2	511.5	521.2	530.8	519.1	500.4	412.8
70°	371.9	444.6	451.0	449.0	421.4	393.8	421.4	449.0	451.0	444.6	371.9
72.5°	327.1	380.1	366.0	342.4	290.2	238.0	290.2	342.4	366.0	380.1	327.1
75°	255.2	269.3	207.7	161.9	163.2	164.5	163.2	161.9	207.7	269.3	255.2
77.5°	170.4	181.1	148.5	124.4	125.5	126.7	125.5	124.4	148.5	181.1	170.4
80°	94.6	103.2	101.9	101.1	101.8	102.4	101.8	101.1	101.9	103.2	94.6
82.5°	66.4	72.2	73.5	74.2	73.3	72.4	73.3	74.2	73.5	72.2	66.4
85°	34.5	33.5	28.4	24.2	22.9	21.6	22.9	24.2	28.4	33.5	34.5
87.5°	9.8	9.7	10.6	11.2	11.7	11.4	11.7	11.2	10.6	9.7	9.8
90°	15.1	19.7	24.3	27.0	29.6	28.3	29.6	27.0	24.3	19.7	15.1
92.5°	30.4	38.1	43.8	48.5	50.6	50.4	50.6	48.5	43.8	38.1	30.4
95°	61.1	70.4	79.6	86.1	90.1	88.8	90.1	86.1	79.6	70.4	61.1
97.5°	94.3	106.7	116.9	123.1	127.0	129.7	127.0	123.1	116.9	106.7	94.3
100°	116.4	128.2	140.1	147.3	153.9	156.5	153.9	147.3	140.1	128.2	116.4
102.5°	134.3	149.8	162.7	170.4	176.0	178.6	176.0	170.4	162.7	149.8	134.3
105°	163.7	180.2	194.0	203.8	209.8	211.7	209.8	203.8	194.0	180.2	163.7
107.5°	193.2	210.1	222.9	233.8	241.0	245.3	241.0	233.8	222.9	210.1	193.2
110°	216.3	230.1	243.9	253.8	261.0	263.7	261.0	253.8	243.9	230.1	216.3



TEST NUMBER: P1435941

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	235.8	251.2	265.0	274.8	283.1	286.8	283.1	274.8	265.0	251.2	235.8
115°	263.0	283.4	295.9	305.1	311.0	314.3	311.0	305.1	295.9	283.4	263.0
117.5°	285.6	306.9	320.6	327.7	330.5	332.8	330.5	327.7	320.6	306.9	285.6
120°	299.8	319.6	335.3	344.5	347.8	349.1	347.8	344.5	335.3	319.6	299.8
122.5°	313.0	331.7	346.9	358.2	363.6	364.9	363.6	358.2	346.9	331.7	313.0
125°	331.4	349.1	364.9	376.1	382.0	385.3	382.0	376.1	364.9	349.1	331.4
127.5°	347.4	366.6	381.1	391.2	397.0	399.6	397.0	391.2	381.1	366.6	347.4
130°	356.4	376.1	390.6	401.7	407.0	409.6	407.0	401.7	390.6	376.1	356.4
132.5°	363.2	384.0	399.0	409.1	414.9	417.5	414.9	409.1	399.0	384.0	363.2
135°	371.5	393.2	409.0	418.8	424.1	426.7	424.1	418.8	409.0	393.2	371.5
137.5°	378.7	398.5	414.9	425.3	430.0	431.7	430.0	425.3	414.9	398.5	378.7
140°	384.0	401.1	417.5	427.4	432.7	433.3	432.7	427.4	417.5	401.1	384.0
142.5°	390.8	404.2	418.6	428.4	433.7	434.9	433.7	428.4	418.6	404.2	390.8
145°	403.1	411.0	420.8	430.0	434.6	435.9	434.6	430.0	420.8	411.0	403.1
147.5°	418.4	420.9	426.1	432.1	436.6	437.5	436.6	432.1	426.1	420.9	418.4
150°	430.0	429.4	431.3	435.3	439.2	438.6	439.2	435.3	431.3	429.4	430.0
152.5°	443.2	439.4	439.2	441.1	442.9	442.8	442.9	441.1	439.2	439.4	443.2
155°	465.5	458.3	454.3	453.0	453.0	452.4	453.0	453.0	454.3	458.3	465.5
157.5°	490.1	480.0	474.1	470.9	470.0	468.6	470.0	470.9	474.1	480.0	490.1
160°	507.0	495.8	489.9	484.6	482.6	480.7	482.6	484.6	489.9	495.8	507.0
162.5°	522.7	512.1	505.6	500.9	498.9	495.9	498.9	500.9	505.6	512.1	522.7
165°	548.4	537.2	530.0	526.0	523.4	520.8	523.4	526.0	530.0	537.2	548.4
167.5°	574.0	561.8	557.1	552.6	550.1	545.4	550.1	552.6	557.1	561.8	574.0
170°	589.8	578.6	576.0	572.0	567.4	562.2	567.4	572.0	576.0	578.6	589.8
172.5°	603.5	596.0	593.4	589.4	588.0	583.8	588.0	589.4	593.4	596.0	603.5
175°	623.3	617.4	617.4	616.8	614.8	610.8	614.8	616.8	617.4	617.4	623.3
177.5°	639.9	636.7	638.9	638.9	638.3	634.6	638.3	638.9	638.9	636.7	639.9
180°	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9



TEST NUMBER: P1435941

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	300.1	300.1	300.1	300.1
2.5°	315.1	309.0	303.4	297.7
5°	357.8	329.9	310.6	291.4
7.5°	441.2	358.4	319.3	280.1
10°	519.3	378.8	324.3	269.8
12.5°	579.7	406.2	332.2	258.2
15°	647.2	451.0	345.3	239.5
17.5°	701.9	501.7	360.9	220.1
20°	737.6	537.1	371.7	206.3
22.5°	764.2	563.4	378.5	193.6
25°	792.9	592.7	384.4	176.0
27.5°	797.0	599.3	379.1	159.0
30°	792.0	596.1	372.3	148.6
32.5°	782.4	588.9	364.1	139.4
35°	759.3	567.9	346.7	125.5
37.5°	724.5	535.0	324.4	113.7
40°	698.7	510.7	308.7	106.8
42.5°	668.7	482.2	291.0	99.8
45°	619.3	434.5	262.7	90.9
47.5°	566.6	381.0	231.8	82.5
50°	530.9	344.6	211.3	77.9
52.5°	495.9	309.2	191.3	73.3
55°	444.8	260.1	164.0	67.8
57.5°	396.9	218.1	140.5	62.9
60°	366.9	195.2	127.9	60.6
62.5°	336.9	174.3	115.7	57.1
65°	294.8	148.3	100.8	53.4
67.5°	256.2	128.7	88.4	48.2
70°	232.7	119.1	81.9	44.7
72.5°	207.0	108.6	75.5	42.4
75°	165.4	91.4	64.4	37.5
77.5°	116.4	70.8	50.7	30.6
80°	76.0	58.0	42.0	26.0
82.5°	56.0	45.2	33.3	21.4
85°	31.3	27.1	20.0	13.0
87.5°	11.2	11.2	8.1	5.0
90°	11.8	7.2	4.6	2.0
92.5°	25.5	17.8	12.5	7.2
95°	51.3	40.8	28.9	20.4
97.5°	81.7	64.7	53.0	38.9
100°	98.0	81.5	70.4	55.2
102.5°	115.9	102.0	86.7	71.5
105°	147.9	130.8	113.1	96.0
107.5°	177.7	158.9	137.6	122.2
110°	196.6	176.2	153.9	140.1



TEST NUMBER: P1435941

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	215.0	194.1	171.2	157.4
115°	240.0	217.0	195.9	184.1
117.5°	264.1	240.4	218.2	208.8
120°	278.8	255.1	233.4	226.2
122.5°	290.9	267.7	247.6	244.6
125°	309.0	285.4	268.3	272.2
127.5°	323.8	302.1	291.3	300.1
130°	332.7	313.6	307.1	319.6
132.5°	340.6	325.7	322.8	340.1
135°	352.4	343.9	346.5	370.2
137.5°	366.5	363.2	372.0	401.9
140°	375.4	377.4	389.9	423.4
142.5°	387.5	392.1	408.3	444.0
145°	406.4	416.2	437.3	472.8
147.5°	427.7	440.4	466.4	502.9
150°	441.9	458.3	485.9	520.8
152.5°	458.2	475.1	502.7	538.1
155°	483.3	502.3	531.3	561.5
157.5°	508.9	528.4	556.0	582.4
160°	524.7	545.7	570.7	595.1
162.5°	542.6	562.1	583.9	605.6
165°	568.8	584.5	602.3	620.7
167.5°	590.7	603.9	617.8	632.1
170°	604.9	615.4	627.3	638.5
172.5°	617.0	625.4	634.1	643.7
175°	633.2	637.8	643.1	649.0
177.5°	645.7	647.3	648.8	651.5
180°	650.9	650.9	650.9	650.9



TEST NUMBER: P1435941
 CATALOG NUMBER: SQ2W-FB-K-050U-075D-L935-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.60	13.60	13.45	14.48	15.59	22.20	23.20	23.05	24.08	25.18
	3H	13.55	14.45	14.41	15.34	16.47	23.81	24.72	24.68	25.60	26.73
	4H	13.95	14.81	14.83	15.70	16.84	24.00	24.85	24.88	25.74	26.88
	6H	14.22	15.00	15.11	15.90	17.06	24.08	24.87	24.97	25.77	26.92
	8H	14.31	15.06	15.21	15.98	17.13	24.10	24.85	25.00	25.77	26.92
	12H	14.37	15.08	15.27	15.99	17.17	24.09	24.80	24.99	25.71	26.89
4H	2H	17.34	18.19	18.22	19.08	20.22	22.58	23.43	23.46	24.33	25.46
	3H	18.48	19.19	19.38	20.12	21.27	24.48	25.19	25.38	26.12	27.27
	4H	18.77	19.42	19.68	20.34	21.52	24.71	25.36	25.62	26.28	27.46
	6H	18.91	19.47	19.84	20.42	21.60	24.85	25.41	25.77	26.35	27.54
	8H	18.96	19.48	19.88	20.42	21.61	24.90	25.42	25.82	26.36	27.56
	12H	18.96	19.43	19.91	20.39	21.59	24.89	25.36	25.83	26.31	27.52
8H	4H	19.97	20.50	20.90	21.43	22.63	24.81	25.33	25.74	26.27	27.47
	6H	20.24	20.67	21.19	21.65	22.85	25.02	25.45	25.97	26.43	27.62
	8H	20.34	20.72	21.30	21.69	22.90	25.11	25.49	26.07	26.46	27.67
	12H	20.39	20.72	21.35	21.69	22.95	25.12	25.46	26.09	26.42	27.68
12H	4H	20.00	20.48	20.95	21.43	22.63	24.77	25.24	25.72	26.20	27.40
	6H	20.35	20.73	21.31	21.70	22.91	25.00	25.38	25.96	26.35	27.57
	8H	20.49	20.83	21.46	21.79	23.05	25.11	25.44	26.08	26.41	27.67