

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1435819

Luminaire Tested: SQ2W-FA-K-100U-075D-L840-UNV-STD-W-WM-4

Issue Date: 3/24/2026

Test Information

Test Method: LM-79-2019
Report Number: P1435819
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2502-345-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/24/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-FA-K-100U-075D-L840-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - FROSTED CONTINUOUS ASYMMETRIC ROLL LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7762.1 lumens
Efficiency: N/A
Efficacy: 129.8 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.23 / 1.34
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1435819

CATALOG NUMBER: SQ2W-FA-K-100U-075D-L840-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1435819

CATALOG NUMBER: SQ2W-FA-K-100U-075D-L840-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35	30
3	80	70	63	58	73	65	58	53	54	49	45	43	40	37	34	32	30	25
4	73	62	55	49	66	57	50	45	47	42	38	38	35	32	30	28	26	22
5	67	55	47	42	61	51	44	39	42	37	33	35	31	28	27	24	22	19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20	16
7	57	45	37	31	52	41	34	29	35	29	25	28	24	21	22	20	17	15
8	53	41	33	28	48	37	31	26	31	26	22	26	22	19	21	18	15	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21130	21130	21130	21130
5°	20881	21867	20881	17428
10°	20790	22120	20790	15799
15°	20433	22298	20433	17466
20°	19871	22137	19871	18214
25°	18885	21958	18885	18433
30°	17400	21466	17400	18628
35°	15396	20995	15396	18295
40°	13257	20419	13257	18495
45°	13088	19689	13088	18531
50°	12486	18728	12486	18602
55°	12422	17275	12422	18418
60°	11137	15396	11137	18345
65°	9494	13566	9494	17830
70°	7662	11495	7662	16522
75°	6644	9494	6644	15190
80°	5662	7076	5662	12264
85°	3761	3761	3761	7521

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 40°
 Vertical Angle: 45°
 Luminance: 20306 cd/sqm



TEST NUMBER: P1435819

CATALOG NUMBER: SQ2W-FA-K-100U-075D-L840-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.7	1.5
10°-20°	329.0	4.2
20°-30°	499.7	6.4
30°-40°	586.6	7.6
40°-50°	595.3	7.7
50°-60°	521.4	6.7
60°-70°	369.8	4.8
70°-80°	190.4	2.5
80°-90°	46.3	0.6
90°-100°	122.8	1.6
100°-110°	358.2	4.6
110°-120°	584.5	7.5
120°-130°	741.7	9.6
130°-140°	793.6	10.2
140°-150°	741.1	9.5
150°-160°	609.8	7.9
160°-170°	409.0	5.3
170°-180°	145.2	1.9
0°-30°	946.4	12.2
0°-40°	1533.0	19.8
0°-60°	2649.8	34.1
0°-90°	3256.3	42.0
90°-120°	1065.5	13.7
90°-150°	3341.8	43.1
90°-180°	4506.0	58.1
0°-180°	7762.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1309	1309	1309	1309	1309	
5°	1288	1349	1288	1075	1288	122
15°	1222	1334	1222	1045	1222	343
25°	1060	1233	1060	1035	1060	484
35°	781	1065	781	928	781	487
45°	573	862	573	812	573	438
55°	441	614	441	654	441	382
65°	248	355	248	467	248	248
75°	106	152	106	244	106	115
85°	20	20	20	41	20	26
90°	5	34	5	67	5	4
95°	48	36	48	210	48	58
105°	228	365	228	502	228	242
115°	436	605	436	745	436	430
125°	645	959	645	913	645	577
135°	878	1255	878	1012	878	678
145°	1121	1446	1121	1034	1121	701
155°	1331	1571	1331	1072	1331	612
165°	1472	1638	1472	1235	1472	414
175°	1538	1604	1538	1448	1538	146
180°	1543	1543	1543	1543	1543	



TEST NUMBER: P1435819

CATALOG NUMBER: SQ2W-FA-K-100U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7
2.5°	1300.5	1309.6	1318.6	1320.8	1320.8	1320.8	1320.8	1320.8	1320.8	1320.8	1320.8
5°	1288.4	1304.1	1319.9	1327.3	1331.8	1335.1	1337.4	1340.2	1344.7	1349.2	1344.7
7.5°	1276.2	1297.4	1318.6	1328.9	1335.7	1341.1	1345.2	1348.8	1351.0	1353.3	1351.0
10°	1268.1	1292.9	1317.7	1328.9	1335.7	1340.2	1342.5	1344.7	1347.0	1349.2	1347.0
12.5°	1255.9	1282.5	1309.1	1322.2	1330.7	1336.2	1338.4	1340.7	1342.9	1345.2	1342.9
15°	1222.4	1258.5	1294.6	1308.7	1315.4	1321.1	1325.6	1329.5	1331.8	1334.0	1331.8
17.5°	1180.8	1224.6	1268.3	1286.0	1295.0	1301.6	1305.6	1309.1	1310.9	1312.7	1310.9
20°	1156.5	1203.8	1251.2	1269.8	1278.8	1284.4	1286.7	1288.4	1288.4	1288.4	1288.4
22.5°	1124.0	1176.8	1229.5	1249.5	1258.5	1263.2	1263.7	1264.5	1266.3	1268.1	1266.3
25°	1060.1	1121.0	1181.8	1207.2	1220.7	1226.4	1224.1	1223.6	1228.1	1232.6	1228.1
27.5°	982.0	1058.6	1135.3	1161.2	1170.2	1175.9	1178.1	1179.8	1179.8	1179.8	1179.8
30°	933.3	1019.0	1104.6	1132.8	1141.8	1147.5	1149.7	1151.4	1151.4	1151.4	1151.4
32.5°	872.4	974.3	1076.2	1107.1	1114.3	1118.2	1118.6	1118.9	1118.9	1118.9	1118.9
35°	781.1	905.1	1029.1	1063.5	1068.0	1070.3	1070.3	1069.7	1067.4	1065.2	1067.4
37.5°	689.8	830.5	971.2	1011.4	1018.2	1020.0	1016.8	1013.9	1011.6	1009.4	1011.6
40°	629.0	782.3	935.6	979.0	985.7	985.7	979.0	973.3	971.1	968.8	971.1
42.5°	596.5	748.0	899.5	942.4	949.2	948.3	939.7	932.7	930.5	928.2	930.5
45°	573.2	708.4	843.7	882.6	889.3	888.2	879.2	871.3	866.8	862.3	866.8
47.5°	537.7	656.7	775.7	813.9	825.2	824.1	810.6	799.3	794.8	790.3	794.8
50°	497.1	614.3	731.5	769.3	780.6	779.4	765.9	754.6	750.1	745.6	750.1
52.5°	468.7	578.7	688.7	723.3	732.8	729.8	714.5	701.9	697.4	692.9	697.4
55°	441.3	533.7	626.1	654.3	661.1	656.6	640.8	627.3	620.5	613.7	620.5
57.5°	377.4	465.3	553.2	580.6	587.8	582.4	564.4	548.9	541.3	533.6	541.3
60°	344.9	423.8	502.7	529.2	538.2	533.7	515.7	499.3	488.1	476.8	488.1
62.5°	308.4	378.3	448.2	475.1	487.7	485.0	467.0	450.6	439.4	428.1	439.4
65°	248.5	309.4	370.3	397.3	413.1	412.0	393.9	377.6	366.3	355.1	366.3
67.5°	194.8	247.1	299.4	326.0	344.0	343.1	323.3	306.1	297.1	288.1	297.1
70°	162.3	207.4	252.5	277.3	295.3	295.3	277.3	261.5	252.5	243.5	252.5
72.5°	142.0	176.3	210.6	234.0	253.8	253.8	234.0	217.3	210.1	202.9	210.1
75°	106.5	126.8	147.1	169.1	191.6	193.9	175.8	161.2	156.7	152.2	156.7
77.5°	77.1	86.6	96.0	113.3	133.1	135.4	120.0	108.1	106.3	104.5	106.3
80°	60.9	63.1	65.4	79.5	97.5	99.8	86.2	76.1	76.1	76.1	76.1
82.5°	40.6	42.8	45.1	55.1	67.7	69.1	59.2	51.3	49.5	47.7	49.5
85°	20.3	20.3	20.3	23.7	28.2	28.2	23.7	20.3	20.3	20.3	20.3
87.5°	5.0	6.2	7.8	10.4	13.1	13.4	11.6	10.6	10.9	10.9	10.9
90°	4.7	10.9	18.7	24.9	29.6	31.2	31.2	32.7	34.3	34.3	34.3
92.5°	17.1	27.1	27.4	27.4	33.4	36.2	38.7	39.0	40.5	40.5	40.5
95°	48.3	53.0	79.5	77.9	53.0	42.1	35.9	35.9	35.9	35.9	35.9
97.5°	92.3	99.1	103.5	138.7	146.5	141.5	115.3	97.0	86.7	82.0	86.7
100°	130.9	134.1	143.4	145.0	183.9	221.3	202.6	179.3	171.5	166.8	171.5
102.5°	169.6	171.5	185.8	192.4	201.4	222.6	287.4	280.3	275.0	274.0	275.0
105°	227.6	229.1	255.6	268.1	274.3	274.3	272.8	304.0	353.8	364.8	353.8
107.5°	289.6	296.8	328.0	361.3	368.5	370.4	362.3	357.6	355.7	357.0	355.7
110°	332.0	342.9	380.3	422.4	433.3	436.5	433.3	428.7	425.5	425.5	425.5



TEST NUMBER: P1435819

CATALOG NUMBER: SQ2W-FA-K-100U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	373.2	389.1	431.5	479.8	498.2	507.5	500.7	497.2	494.1	496.6	494.1
115°	436.5	459.8	516.0	565.8	603.2	607.9	606.4	606.4	604.8	604.8	604.8
117.5°	495.1	532.5	595.5	653.4	696.8	709.2	715.5	713.6	711.7	714.9	711.7
120°	536.2	579.9	651.6	717.0	759.1	777.8	784.1	780.9	784.1	780.9	784.1
122.5°	579.9	633.5	703.9	771.9	821.5	842.7	850.2	850.8	851.4	849.5	851.4
125°	645.3	710.8	793.4	863.6	915.0	939.9	946.2	947.7	950.9	958.6	950.9
127.5°	711.4	785.6	876.3	944.0	996.7	1026.9	1036.6	1040.0	1046.6	1050.0	1046.6
130°	757.6	841.7	933.7	997.6	1049.1	1081.8	1098.9	1103.6	1111.4	1109.8	1111.4
132.5°	806.2	894.1	987.3	1053.7	1101.4	1136.7	1151.3	1164.7	1167.5	1169.7	1167.5
135°	877.6	972.7	1066.2	1131.7	1176.9	1211.2	1229.9	1242.3	1250.1	1254.8	1250.1
137.5°	952.7	1053.1	1142.9	1201.2	1246.7	1276.3	1297.5	1310.6	1318.7	1322.5	1318.7
140°	1003.9	1100.5	1187.8	1248.6	1289.1	1318.7	1337.4	1353.0	1362.4	1362.4	1362.4
142.5°	1052.5	1147.9	1232.7	1293.5	1329.0	1356.1	1376.1	1387.9	1398.5	1398.5	1398.5
145°	1120.8	1215.8	1293.8	1354.6	1384.2	1409.1	1431.0	1440.3	1446.5	1446.5	1446.5
147.5°	1192.2	1276.3	1347.4	1405.7	1430.6	1459.9	1477.1	1484.6	1492.4	1488.9	1492.4
150°	1234.6	1312.5	1381.1	1435.6	1460.6	1488.6	1505.8	1512.0	1519.8	1515.1	1519.8
152.5°	1275.7	1349.9	1412.3	1463.1	1484.3	1512.3	1532.0	1538.2	1543.5	1540.1	1543.5
155°	1331.2	1396.7	1454.3	1501.1	1519.8	1546.3	1565.0	1572.8	1579.0	1571.2	1579.0
157.5°	1380.8	1437.2	1487.4	1530.4	1550.4	1573.1	1590.6	1600.2	1606.5	1603.0	1606.5
160°	1410.7	1462.1	1507.3	1547.9	1566.6	1586.8	1605.5	1616.5	1622.7	1618.0	1622.7
162.5°	1435.6	1482.1	1524.8	1561.6	1577.8	1595.6	1618.0	1627.7	1633.9	1628.0	1633.9
165°	1471.5	1508.9	1546.3	1577.5	1591.5	1605.5	1628.9	1639.8	1644.5	1638.3	1644.5
167.5°	1498.6	1527.3	1557.5	1584.3	1594.6	1608.3	1631.7	1640.8	1646.7	1638.9	1646.7
170°	1513.6	1538.5	1565.0	1586.8	1594.6	1607.1	1630.5	1638.3	1643.0	1635.2	1643.0
172.5°	1526.0	1544.7	1566.3	1585.6	1589.6	1599.6	1621.8	1629.5	1633.0	1626.4	1633.0
175°	1538.5	1549.4	1565.0	1577.5	1575.9	1582.2	1600.9	1607.1	1613.3	1604.0	1613.3
177.5°	1544.4	1549.4	1554.4	1561.9	1556.9	1556.9	1570.6	1574.4	1575.6	1570.6	1575.6
180°	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2



TEST NUMBER: P1435819

CATALOG NUMBER: SQ2W-FA-K-100U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7
2.5°	1320.8	1320.8	1320.8	1320.8	1320.8	1318.6	1309.6	1300.5	1300.5	1300.5	1293.8
5°	1340.2	1337.4	1335.1	1331.8	1327.3	1319.9	1304.1	1288.4	1281.6	1274.8	1246.1
7.5°	1348.8	1345.2	1341.1	1335.7	1328.9	1318.6	1297.4	1276.2	1246.0	1215.8	1151.7
10°	1344.7	1342.5	1340.2	1335.7	1328.9	1317.7	1292.9	1268.1	1207.2	1146.3	1085.5
12.5°	1340.7	1338.4	1336.2	1330.7	1322.2	1309.1	1282.5	1255.9	1169.8	1083.7	1028.7
15°	1329.5	1325.6	1321.1	1315.4	1308.7	1294.6	1258.5	1222.4	1125.5	1028.5	982.3
17.5°	1309.1	1305.6	1301.6	1295.0	1286.0	1268.3	1224.6	1180.8	1079.4	977.9	948.2
20°	1288.4	1286.7	1284.4	1278.8	1269.8	1251.2	1203.8	1156.5	1055.0	953.6	940.1
22.5°	1264.5	1263.7	1263.2	1258.5	1249.5	1229.5	1176.8	1124.0	1024.4	924.7	925.2
25°	1223.6	1224.1	1226.4	1220.7	1207.2	1181.8	1121.0	1060.1	972.2	884.3	899.5
27.5°	1179.8	1178.1	1175.9	1170.2	1161.2	1135.3	1058.6	982.0	912.6	843.1	868.4
30°	1151.4	1149.7	1147.5	1141.8	1132.8	1104.6	1019.0	933.3	874.7	816.1	845.4
32.5°	1118.9	1118.6	1118.2	1114.3	1107.1	1076.2	974.3	872.4	830.1	787.7	818.3
35°	1069.7	1070.3	1070.3	1068.0	1063.5	1029.1	905.1	781.1	763.1	745.1	781.1
37.5°	1013.9	1016.8	1020.0	1018.2	1011.4	971.2	830.5	689.8	695.7	701.6	745.3
40°	973.3	979.0	985.7	985.7	979.0	935.6	782.3	629.0	649.3	669.5	716.9
42.5°	932.7	939.7	948.3	949.2	942.4	899.5	748.0	596.5	618.6	640.7	689.8
45°	871.3	879.2	888.2	889.3	882.6	843.7	708.4	573.2	586.7	600.2	647.6
47.5°	799.3	810.6	824.1	825.2	813.9	775.7	656.7	537.7	547.6	557.5	606.0
50°	754.6	765.9	779.4	780.6	769.3	731.5	614.3	497.1	510.6	524.1	574.9
52.5°	701.9	714.5	729.8	732.8	723.3	688.7	578.7	468.7	476.8	484.9	539.7
55°	627.3	640.8	656.6	661.1	654.3	626.1	533.7	441.3	434.5	427.8	483.6
57.5°	548.9	564.4	582.4	587.8	580.6	553.2	465.3	377.4	371.5	365.7	426.1
60°	499.3	515.7	533.7	538.2	529.2	502.7	423.8	344.9	333.6	322.4	385.5
62.5°	450.6	467.0	485.0	487.7	475.1	448.2	378.3	308.4	300.7	293.1	354.4
65°	377.6	393.9	412.0	413.1	397.3	370.3	309.4	248.5	253.1	257.6	312.8
67.5°	306.1	323.3	343.1	344.0	326.0	299.4	247.1	194.8	209.7	224.5	274.2
70°	261.5	277.3	295.3	295.3	277.3	252.5	207.4	162.3	182.6	202.9	248.5
72.5°	217.3	234.0	253.8	253.8	234.0	210.6	176.3	142.0	162.3	182.6	220.1
75°	161.2	175.8	193.9	191.6	169.1	147.1	126.8	106.5	126.8	147.1	175.8
77.5°	108.1	120.0	135.4	133.1	113.3	96.0	86.6	77.1	93.8	110.5	130.5
80°	76.1	86.2	99.8	97.5	79.5	65.4	63.1	60.9	72.1	83.4	98.1
82.5°	51.3	59.2	69.1	67.7	55.1	45.1	42.8	40.6	50.0	59.5	69.7
85°	20.3	23.7	28.2	28.2	23.7	20.3	20.3	20.3	24.8	29.3	33.8
87.5°	10.6	11.6	13.4	13.1	10.4	7.8	6.2	5.0	8.0	11.1	13.7
90°	32.7	31.2	31.2	29.6	24.9	18.7	10.9	4.7	10.9	17.1	28.1
92.5°	39.0	38.7	36.2	33.4	27.4	27.4	27.1	17.1	29.6	42.1	60.5
95°	35.9	35.9	42.1	53.0	77.9	79.5	53.0	48.3	68.6	96.6	121.6
97.5°	97.0	115.3	141.5	146.5	138.7	103.5	99.1	92.3	125.6	153.4	193.6
100°	179.3	202.6	221.3	183.9	145.0	143.4	134.1	130.9	166.8	193.3	232.3
102.5°	280.3	287.4	222.6	201.4	192.4	185.8	171.5	169.6	205.4	241.9	274.7
105°	304.0	272.8	274.3	274.3	268.1	255.6	229.1	227.6	268.1	310.2	350.7
107.5°	357.6	362.3	370.4	368.5	361.3	328.0	296.8	289.6	326.1	376.6	421.2
110°	428.7	433.3	436.5	433.3	422.4	380.3	342.9	332.0	364.8	417.8	466.1



TEST NUMBER: P1435819

CATALOG NUMBER: SQ2W-FA-K-100U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	497.2	500.7	507.5	498.2	479.8	431.5	389.1	373.2	405.9	460.2	509.7
115°	606.4	606.4	607.9	603.2	565.8	516.0	459.8	436.5	464.5	514.4	569.0
117.5°	713.6	715.5	709.2	696.8	653.4	595.5	532.5	495.1	517.2	569.9	626.0
120°	780.9	784.1	777.8	759.1	717.0	651.6	579.9	536.2	553.4	604.8	660.9
122.5°	850.8	850.2	842.7	821.5	771.9	703.9	633.5	579.9	587.0	634.7	689.6
125°	947.7	946.2	939.9	915.0	863.6	793.4	710.8	645.3	636.0	676.5	732.6
127.5°	1040.0	1036.6	1026.9	996.7	944.0	876.3	785.6	711.4	690.5	716.1	767.5
130°	1103.6	1098.9	1081.8	1049.1	997.6	933.7	841.7	757.6	727.9	743.5	788.7
132.5°	1164.7	1151.3	1136.7	1101.4	1053.7	987.3	894.1	806.2	765.4	772.2	807.4
135°	1242.3	1229.9	1211.2	1176.9	1131.7	1066.2	972.7	877.6	821.5	815.2	835.5
137.5°	1310.6	1297.5	1276.3	1246.7	1201.2	1142.9	1053.1	952.7	882.0	861.1	868.9
140°	1353.0	1337.4	1318.7	1289.1	1248.6	1187.8	1100.5	1003.9	924.4	894.7	890.1
142.5°	1387.9	1376.1	1356.1	1329.0	1293.5	1232.7	1147.9	1052.5	968.0	929.7	918.7
145°	1440.3	1431.0	1409.1	1384.2	1354.6	1293.8	1215.8	1120.8	1036.6	986.7	963.3
147.5°	1484.6	1477.1	1459.9	1430.6	1405.7	1347.4	1276.3	1192.2	1105.8	1044.1	1013.8
150°	1512.0	1505.8	1488.6	1460.6	1435.6	1381.1	1312.5	1234.6	1151.9	1086.5	1047.5
152.5°	1538.2	1532.0	1512.3	1484.3	1463.1	1412.3	1349.9	1275.7	1191.8	1126.4	1086.2
155°	1572.8	1565.0	1546.3	1519.8	1501.1	1454.3	1396.7	1331.2	1259.5	1190.9	1145.7
157.5°	1600.2	1590.6	1573.1	1550.4	1530.4	1487.4	1437.2	1380.8	1318.1	1252.6	1206.5
160°	1616.5	1605.5	1586.8	1566.6	1547.9	1507.3	1462.1	1410.7	1353.0	1293.8	1243.9
162.5°	1627.7	1618.0	1595.6	1577.8	1561.6	1524.8	1482.1	1435.6	1384.2	1332.4	1286.3
165°	1639.8	1628.9	1605.5	1591.5	1577.5	1546.3	1508.9	1471.5	1427.8	1385.8	1348.3
167.5°	1640.8	1631.7	1608.3	1594.6	1584.3	1557.5	1527.3	1498.6	1464.6	1431.6	1400.4
170°	1638.3	1630.5	1607.1	1594.6	1586.8	1565.0	1538.5	1513.6	1487.1	1459.0	1434.1
172.5°	1629.5	1621.8	1599.6	1589.6	1585.6	1566.3	1544.7	1526.0	1503.3	1482.7	1462.8
175°	1607.1	1600.9	1582.2	1575.9	1577.5	1565.0	1549.4	1538.5	1524.5	1512.0	1501.1
177.5°	1574.4	1570.6	1556.9	1556.9	1561.9	1554.4	1549.4	1544.4	1538.2	1534.5	1530.7
180°	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2



TEST NUMBER: P1435819

CATALOG NUMBER: SQ2W-FA-K-100U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7	1308.7
2.5°	1284.8	1277.5	1272.1	1267.6	1265.8	1264.0	1265.8	1267.6	1272.1	1277.5	1284.8
5°	1210.0	1171.7	1131.1	1097.9	1086.6	1075.3	1086.6	1097.9	1131.1	1171.7	1210.0
7.5°	1076.5	1030.2	1013.1	999.4	995.7	992.1	995.7	999.4	1013.1	1030.2	1076.5
10°	1024.6	987.4	973.9	963.7	963.7	963.7	963.7	963.7	973.9	987.4	1024.6
12.5°	984.0	961.3	960.4	961.9	971.0	980.0	971.0	961.9	960.4	961.3	984.0
15°	953.0	956.4	992.5	1022.3	1033.6	1044.9	1033.6	1022.3	992.5	956.4	953.0
17.5°	942.3	961.7	1006.3	1042.1	1051.1	1060.1	1051.1	1042.1	1006.3	961.7	942.3
20°	955.8	980.6	1014.5	1042.1	1051.1	1060.1	1051.1	1042.1	1014.5	980.6	955.8
22.5°	959.0	989.2	1015.8	1038.0	1047.0	1056.1	1047.0	1038.0	1015.8	989.2	959.0
25°	949.1	985.2	1007.7	1025.7	1030.2	1034.7	1030.2	1025.7	1007.7	985.2	949.1
27.5°	925.2	964.9	987.4	1005.1	1008.3	1011.4	1008.3	1005.1	987.4	964.9	925.2
30°	904.0	944.6	967.1	985.7	992.5	999.2	992.5	985.7	967.1	944.6	904.0
32.5°	873.3	914.8	942.8	964.1	965.4	966.8	965.4	964.1	942.8	914.8	873.3
35°	835.2	878.1	909.6	932.7	930.5	928.2	930.5	932.7	909.6	878.1	835.2
37.5°	801.6	843.6	871.1	892.4	895.1	897.8	895.1	892.4	871.1	843.6	801.6
40°	773.2	816.1	845.4	868.5	873.0	877.5	873.0	868.5	845.4	816.1	773.2
42.5°	748.0	791.7	821.0	844.1	848.7	853.2	848.7	844.1	821.0	791.7	748.0
45°	706.2	751.3	782.8	807.1	809.3	811.6	809.3	807.1	782.8	751.3	706.2
47.5°	667.3	712.6	741.9	764.5	766.7	769.0	766.7	764.5	741.9	712.6	667.3
50°	638.0	684.2	713.5	736.0	738.3	740.6	738.3	736.0	713.5	684.2	638.0
52.5°	610.0	658.0	683.7	703.6	705.8	708.1	705.8	703.6	683.7	658.0	610.0
55°	560.2	610.9	635.7	654.3	654.3	654.3	654.3	635.7	610.9	560.2	560.2
57.5°	508.6	560.7	582.3	599.2	601.9	604.6	601.9	599.2	582.3	560.7	508.6
60°	473.4	526.4	544.4	559.1	563.6	568.1	563.6	559.1	544.4	526.4	473.4
62.5°	438.7	489.9	507.9	522.1	524.8	527.5	524.8	522.1	507.9	489.9	438.7
65°	384.9	430.0	448.1	462.1	464.4	466.7	464.4	462.1	448.1	430.0	384.9
67.5°	335.6	372.5	385.2	395.1	396.9	398.7	396.9	395.1	385.2	372.5	335.6
70°	302.6	334.2	343.2	350.0	350.0	350.0	350.0	350.0	343.2	334.2	302.6
72.5°	263.4	289.6	298.6	305.8	307.6	309.4	307.6	305.8	298.6	289.6	263.4
75°	207.4	226.6	233.3	239.0	241.2	243.5	241.2	239.0	233.3	226.6	207.4
77.5°	151.7	164.3	168.4	172.0	174.3	176.5	174.3	172.0	168.4	164.3	151.7
80°	113.8	122.9	125.1	127.4	129.6	131.9	129.6	127.4	125.1	122.9	113.8
82.5°	80.0	86.3	88.6	90.4	90.9	91.3	90.9	90.4	88.6	86.3	80.0
85°	38.3	40.6	40.6	40.6	40.6	40.6	40.6	40.6	40.6	40.6	38.3
87.5°	15.3	17.5	19.7	20.9	22.1	21.5	22.1	20.9	19.7	17.5	15.3
90°	35.9	46.8	57.7	63.9	70.1	67.0	70.1	63.9	57.7	46.8	35.9
92.5°	72.0	90.4	103.8	115.0	120.0	119.4	120.0	115.0	103.8	90.4	72.0
95°	145.0	166.8	188.6	204.2	213.6	210.4	213.6	204.2	188.6	166.8	145.0
97.5°	223.5	252.8	277.2	291.8	301.2	307.4	301.2	291.8	277.2	252.8	223.5
100°	275.9	304.0	332.0	349.2	364.8	371.0	364.8	349.2	332.0	304.0	275.9
102.5°	318.3	355.1	385.6	404.0	417.1	423.4	417.1	404.0	385.6	355.1	318.3
105°	388.1	427.1	459.8	483.2	497.2	501.9	497.2	483.2	459.8	427.1	388.1
107.5°	458.0	498.2	528.4	554.3	571.4	581.4	571.4	554.3	528.4	498.2	458.0
110°	512.8	545.6	578.3	601.7	618.8	625.1	618.8	601.7	578.3	545.6	512.8



TEST NUMBER: P1435819

CATALOG NUMBER: SQ2W-FA-K-100U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	559.0	595.5	628.2	651.6	671.2	679.9	671.2	651.6	628.2	595.5	559.0
115°	623.5	671.8	701.4	723.3	737.3	745.1	737.3	723.3	701.4	671.8	623.5
117.5°	677.1	727.6	760.1	776.9	783.4	789.1	783.4	776.9	760.1	727.6	677.1
120°	710.8	757.6	795.0	816.8	824.6	827.7	824.6	816.8	795.0	757.6	710.8
122.5°	742.0	786.2	822.4	849.2	862.0	865.1	862.0	849.2	822.4	786.2	742.0
125°	785.6	827.7	865.1	891.6	905.6	913.4	905.6	891.6	865.1	827.7	785.6
127.5°	823.7	869.2	903.5	927.5	941.2	947.4	941.2	927.5	903.5	869.2	823.7
130°	844.9	891.6	925.9	952.4	964.9	971.1	964.9	952.4	925.9	891.6	844.9
132.5°	861.1	910.3	945.9	969.9	983.6	989.8	983.6	969.9	945.9	910.3	861.1
135°	880.7	932.1	969.6	992.9	1005.4	1011.6	1005.4	992.9	969.6	932.1	880.7
137.5°	897.9	944.6	983.6	1008.2	1019.4	1023.5	1019.4	1008.2	983.6	944.6	897.9
140°	910.3	950.9	989.8	1013.2	1025.7	1027.2	1025.7	1013.2	989.8	950.9	910.3
142.5°	926.5	958.3	992.3	1015.7	1028.2	1031.0	1028.2	1015.7	992.3	958.3	926.5
145°	955.5	974.2	997.6	1019.4	1030.4	1033.5	1030.4	1019.4	997.6	974.2	955.5
147.5°	992.0	997.9	1010.1	1024.4	1035.0	1037.2	1035.0	1024.4	1010.1	997.9	992.0
150°	1019.4	1017.9	1022.6	1031.9	1041.3	1039.7	1041.3	1031.9	1022.6	1017.9	1019.4
152.5°	1050.6	1041.6	1041.3	1045.6	1050.0	1049.7	1050.0	1045.6	1041.3	1041.6	1050.6
155°	1103.6	1086.5	1077.1	1074.0	1074.0	1072.4	1074.0	1074.0	1077.1	1086.5	1103.6
157.5°	1161.9	1137.9	1123.9	1116.4	1114.2	1110.8	1114.2	1116.4	1123.9	1137.9	1161.9
160°	1201.8	1175.3	1161.3	1148.8	1144.1	1139.5	1144.1	1148.8	1161.3	1175.3	1201.8
162.5°	1239.2	1214.0	1198.7	1187.5	1182.8	1175.6	1182.8	1187.5	1198.7	1214.0	1239.2
165°	1300.0	1273.5	1256.4	1247.0	1240.8	1234.6	1240.8	1247.0	1256.4	1273.5	1300.0
167.5°	1360.8	1331.8	1320.6	1310.0	1304.1	1292.8	1304.1	1310.0	1320.6	1331.8	1360.8
170°	1398.2	1371.7	1365.5	1356.1	1345.2	1332.8	1345.2	1356.1	1365.5	1371.7	1398.2
172.5°	1430.6	1412.9	1406.6	1397.3	1393.9	1383.9	1393.9	1397.3	1406.6	1412.9	1430.6
175°	1477.7	1463.7	1463.7	1462.1	1457.5	1448.1	1457.5	1462.1	1463.7	1463.7	1477.7
177.5°	1517.0	1509.5	1514.5	1514.5	1513.3	1504.5	1513.3	1514.5	1514.5	1509.5	1517.0
180°	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2



TEST NUMBER: P1435819

CATALOG NUMBER: SQ2W-FA-K-100U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1308.7	1308.7	1308.7	1308.7
2.5°	1293.8	1300.5	1300.5	1300.5
5°	1246.1	1274.8	1281.6	1288.4
7.5°	1151.7	1215.8	1246.0	1276.2
10°	1085.5	1146.3	1207.2	1268.1
12.5°	1028.7	1083.7	1169.8	1255.9
15°	982.3	1028.5	1125.5	1222.4
17.5°	948.2	977.9	1079.4	1180.8
20°	940.1	953.6	1055.0	1156.5
22.5°	925.2	924.7	1024.4	1124.0
25°	899.5	884.3	972.2	1060.1
27.5°	868.4	843.1	912.6	982.0
30°	845.4	816.1	874.7	933.3
32.5°	818.3	787.7	830.1	872.4
35°	781.1	745.1	763.1	781.1
37.5°	745.3	701.6	695.7	689.8
40°	716.9	669.5	649.3	629.0
42.5°	689.8	640.7	618.6	596.5
45°	647.6	600.2	586.7	573.2
47.5°	606.0	557.5	547.6	537.7
50°	574.9	524.1	510.6	497.1
52.5°	539.7	484.9	476.8	468.7
55°	483.6	427.8	434.5	441.3
57.5°	426.1	365.7	371.5	377.4
60°	385.5	322.4	333.6	344.9
62.5°	354.4	293.1	300.7	308.4
65°	312.8	257.6	253.1	248.5
67.5°	274.2	224.5	209.7	194.8
70°	248.5	202.9	182.6	162.3
72.5°	220.1	182.6	162.3	142.0
75°	175.8	147.1	126.8	106.5
77.5°	130.5	110.5	93.8	77.1
80°	98.1	83.4	72.1	60.9
82.5°	69.7	59.5	50.0	40.6
85°	33.8	29.3	24.8	20.3
87.5°	13.7	11.1	8.0	5.0
90°	28.1	17.1	10.9	4.7
92.5°	60.5	42.1	29.6	17.1
95°	121.6	96.6	68.6	48.3
97.5°	193.6	153.4	125.6	92.3
100°	232.3	193.3	166.8	130.9
102.5°	274.7	241.9	205.4	169.6
105°	350.7	310.2	268.1	227.6
107.5°	421.2	376.6	326.1	289.6
110°	466.1	417.8	364.8	332.0



TEST NUMBER: P1435819

CATALOG NUMBER: SQ2W-FA-K-100U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	509.7	460.2	405.9	373.2
115°	569.0	514.4	464.5	436.5
117.5°	626.0	569.9	517.2	495.1
120°	660.9	604.8	553.4	536.2
122.5°	689.6	634.7	587.0	579.9
125°	732.6	676.5	636.0	645.3
127.5°	767.5	716.1	690.5	711.4
130°	788.7	743.5	727.9	757.6
132.5°	807.4	772.2	765.4	806.2
135°	835.5	815.2	821.5	877.6
137.5°	868.9	861.1	882.0	952.7
140°	890.1	894.7	924.4	1003.9
142.5°	918.7	929.7	968.0	1052.5
145°	963.3	986.7	1036.6	1120.8
147.5°	1013.8	1044.1	1105.8	1192.2
150°	1047.5	1086.5	1151.9	1234.6
152.5°	1086.2	1126.4	1191.8	1275.7
155°	1145.7	1190.9	1259.5	1331.2
157.5°	1206.5	1252.6	1318.1	1380.8
160°	1243.9	1293.8	1353.0	1410.7
162.5°	1286.3	1332.4	1384.2	1435.6
165°	1348.3	1385.8	1427.8	1471.5
167.5°	1400.4	1431.6	1464.6	1498.6
170°	1434.1	1459.0	1487.1	1513.6
172.5°	1462.8	1482.7	1503.3	1526.0
175°	1501.1	1512.0	1524.5	1538.5
177.5°	1530.7	1534.5	1538.2	1544.4
180°	1543.2	1543.2	1543.2	1543.2



TEST NUMBER: P1435819
 CATALOG NUMBER: SQ2W-FA-K-100U-075D-L840-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.18	16.97	17.21	18.01	19.39	17.38	18.17	18.40	19.20	20.59
	3H	17.27	17.97	18.30	19.02	20.42	18.62	19.33	19.65	20.37	21.77
	4H	17.61	18.29	18.66	19.33	20.74	19.01	19.68	20.05	20.72	22.13
	6H	17.77	18.39	18.83	19.44	20.86	19.16	19.78	20.22	20.83	22.25
	8H	17.80	18.39	18.87	19.46	20.87	19.18	19.77	20.25	20.84	22.25
	12H	17.80	18.36	18.86	19.41	20.85	19.17	19.73	20.23	20.78	22.22
4H	2H	17.04	17.71	18.09	18.76	20.16	17.95	18.63	19.01	19.67	21.08
	3H	18.42	18.98	19.48	20.05	21.48	19.41	19.97	20.47	21.04	22.47
	4H	18.87	19.39	19.94	20.45	21.89	19.89	20.40	20.95	21.46	22.90
	6H	19.10	19.54	20.18	20.63	22.06	20.10	20.54	21.18	21.63	23.07
	8H	19.16	19.57	20.23	20.64	22.10	20.15	20.56	21.23	21.64	23.09
	12H	19.15	19.53	20.25	20.62	22.08	20.14	20.51	21.23	21.60	23.06
8H	4H	19.25	19.66	20.33	20.74	22.20	20.08	20.49	21.15	21.56	23.02
	6H	19.60	19.94	20.70	21.06	22.51	20.39	20.73	21.49	21.85	23.30
	8H	19.72	20.02	20.82	21.12	22.59	20.48	20.78	21.59	21.88	23.35
	12H	19.75	20.01	20.86	21.11	22.62	20.49	20.76	21.60	21.85	23.36
12H	4H	19.25	19.62	20.35	20.72	22.17	20.04	20.41	21.13	21.50	22.96
	6H	19.67	19.97	20.78	21.07	22.54	20.40	20.70	21.51	21.80	23.27
	8H	19.81	20.07	20.92	21.17	22.68	20.51	20.78	21.62	21.87	23.38