

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427835

Luminaire Tested: SQ2W-PH1-0U-100D-L935-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1427835
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-10)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PH1-0U-100D-L935-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE HEX LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT N/A - DIRECT ONLY
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4507.3 lumens
Efficiency: N/A
Efficacy: 119.9 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.02 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1427835

CATALOG NUMBER: SQ2W-PH1-0U-100D-L935-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1427835

CATALOG NUMBER: SQ2W-PH1-0U-100D-L935-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	109	105	101	97	107	103	99	96	99	96	93	95	92	90	91	89	87	85			85	
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72			72	
3	91	81	73	67	89	80	72	67	77	71	65	74	69	64	72	67	63	61			61	
4	84	72	64	57	82	71	63	57	69	62	56	66	60	55	64	59	55	53			53	
5	77	65	56	50	75	64	56	49	62	54	49	60	53	48	58	52	48	46			46	
6	72	59	50	44	70	58	49	43	56	48	43	54	48	43	53	47	42	40			40	
7	66	53	45	39	65	52	44	38	51	43	38	49	43	38	48	42	38	36			36	
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32			32	
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29			29	
10	54	41	34	28	53	41	33	28	40	33	28	39	33	28	38	32	28	26			26	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	32913	32913	32913	32913
5°	33102	30084	33102	30084
10°	32338	27346	32338	27346
15°	32484	26811	32484	26811
20°	31326	27027	31326	27027
25°	30752	26398	30752	26398
30°	30085	26613	30085	26613
35°	29857	31195	29857	31195
40°	29882	24731	29882	24731
45°	29893	21301	29893	21301
50°	29473	19974	29473	19974
55°	29100	19164	29100	19164
60°	28810	17976	28810	17976
65°	28305	15633	28305	15633
70°	26738	11169	26738	11169
75°	23836	8471	23836	8471
80°	19479	7931	19479	7931
85°	12208	5391	12208	5391

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 29893 cd/sqm



TEST NUMBER: P1427835

CATALOG NUMBER: SQ2W-PH1-0U-100D-L935-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.4	4.0
10°-20°	471.8	10.5
20°-30°	691.7	15.3
30°-40°	837.6	18.6
40°-50°	823.6	18.3
50°-60°	716.4	15.9
60°-70°	498.3	11.1
70°-80°	236.3	5.2
80°-90°	52.1	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1342.9	29.8
0°-40°	2180.5	48.4
0°-60°	3720.6	82.5
0°-90°	4507.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4507.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2038	2038	2038	2038	2038	
5°	2042	1856	2042	1856	2042	192
15°	1943	1604	1943	1604	1943	542
25°	1726	1482	1726	1482	1726	794
35°	1515	1583	1515	1583	1515	949
45°	1309	933	1309	933	1309	1006
55°	1034	681	1034	681	1034	924
65°	741	409	741	409	741	728
75°	382	136	382	136	382	405
85°	66	29	66	29	66	90
90°	0	0	0	0	0	



TEST NUMBER: P1427835

CATALOG NUMBER: SQ2W-PH1-0U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5
2.5°	2033.8	2043.5	2053.1	2039.5	2018.1	2003.3	1995.0	1988.5	1987.1	1985.7	1987.1
5°	2042.4	2041.5	2040.6	2000.3	1946.9	1906.8	1880.1	1859.6	1857.9	1856.2	1857.9
7.5°	2005.1	1978.4	1951.7	1897.5	1834.3	1787.9	1758.4	1736.0	1734.6	1733.2	1734.6
10°	1972.5	1932.0	1891.5	1830.3	1762.2	1714.8	1688.1	1668.0	1668.0	1668.0	1668.0
12.5°	1964.8	1900.8	1836.9	1769.8	1701.7	1657.7	1637.9	1624.1	1628.2	1632.3	1628.2
15°	1943.4	1846.9	1750.3	1682.2	1623.6	1591.7	1586.6	1585.1	1594.5	1604.0	1594.5
17.5°	1872.8	1768.9	1664.9	1605.1	1559.9	1542.8	1553.9	1564.9	1575.9	1587.0	1575.9
20°	1823.2	1720.6	1618.0	1562.6	1523.0	1513.5	1534.2	1552.3	1562.6	1573.0	1562.6
22.5°	1781.3	1677.3	1573.4	1524.4	1493.7	1489.7	1512.5	1530.9	1536.4	1542.0	1536.4
25°	1726.2	1609.0	1491.7	1456.0	1447.3	1452.9	1472.8	1487.0	1484.4	1481.8	1484.4
27.5°	1660.3	1537.9	1415.5	1392.5	1402.7	1413.8	1425.8	1435.3	1436.8	1438.4	1436.8
30°	1613.7	1491.3	1368.9	1350.6	1367.0	1381.2	1393.3	1405.1	1416.3	1427.5	1416.3
32.5°	1568.7	1442.2	1315.6	1302.5	1327.1	1353.8	1382.4	1410.3	1436.0	1461.7	1436.0
35°	1514.8	1382.9	1251.0	1240.7	1270.8	1309.6	1357.0	1413.7	1498.2	1582.7	1498.2
37.5°	1458.2	1316.8	1175.4	1170.7	1211.6	1252.4	1293.3	1330.7	1357.6	1384.5	1357.6
40°	1417.8	1269.6	1121.3	1121.1	1170.2	1221.1	1273.6	1297.6	1235.5	1173.4	1235.5
42.5°	1374.4	1226.1	1077.8	1073.5	1117.1	1173.1	1241.6	1266.7	1161.9	1057.1	1161.9
45°	1309.2	1154.9	1000.6	995.0	1039.0	1070.0	1088.1	1082.9	1007.9	932.9	1007.9
47.5°	1232.4	1085.3	938.3	937.1	984.5	987.9	947.4	909.7	880.4	851.1	880.4
50°	1173.4	1034.7	895.9	901.9	956.2	951.0	886.4	833.2	814.2	795.2	814.2
52.5°	1116.0	984.1	852.2	868.3	933.6	923.3	837.2	769.5	756.8	744.0	756.8
55°	1033.8	907.1	780.4	816.6	907.1	893.3	775.2	686.0	683.4	680.8	683.4
57.5°	946.5	826.7	706.9	732.0	805.4	791.0	688.5	612.9	617.3	621.8	617.3
60°	892.2	775.8	659.5	662.7	705.8	692.0	621.3	567.0	561.8	556.7	561.8
62.5°	834.8	723.9	613.1	597.0	612.5	596.3	548.4	511.1	506.0	500.8	506.0
65°	740.9	640.1	539.2	508.8	501.9	478.6	439.0	409.2	409.2	409.2	409.2
67.5°	637.7	549.8	461.9	427.9	411.8	388.7	358.6	330.8	310.1	289.4	310.1
70°	566.4	488.8	411.2	375.6	354.1	326.5	292.9	264.2	250.4	236.6	250.4
72.5°	490.3	423.8	357.2	320.8	294.4	267.5	240.1	215.6	199.7	183.9	199.7
75°	382.1	328.6	275.2	239.9	210.6	183.4	158.4	139.2	137.5	135.8	137.5
77.5°	276.2	237.2	198.3	169.6	144.5	125.6	113.0	103.6	103.8	104.0	103.8
80°	209.5	180.2	150.9	124.1	98.3	84.9	84.0	83.6	84.5	85.3	84.5
82.5°	147.4	125.7	104.0	86.9	71.4	64.2	65.4	66.4	66.5	66.7	66.5
85°	65.9	55.6	45.3	41.4	39.7	37.1	33.6	30.8	30.0	29.1	30.0
87.5°	14.0	13.3	12.6	10.9	8.8	7.8	7.8	7.8	7.8	7.8	7.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1427835

CATALOG NUMBER: SQ2W-PH1-OU-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5
2.5°	1988.5	1995.0	2003.3	2018.1	2039.5	2053.1	2043.5	2033.8	2043.5	2053.1	2039.5
5°	1859.6	1880.1	1906.8	1946.9	2000.3	2040.6	2041.5	2042.4	2041.5	2040.6	2000.3
7.5°	1736.0	1758.4	1787.9	1834.3	1897.5	1951.7	1978.4	2005.1	1978.4	1951.7	1897.5
10°	1668.0	1688.1	1714.8	1762.2	1830.3	1891.5	1932.0	1972.5	1932.0	1891.5	1830.3
12.5°	1624.1	1637.9	1657.7	1701.7	1769.8	1836.9	1900.8	1964.8	1900.8	1836.9	1769.8
15°	1585.1	1586.6	1591.7	1623.6	1682.2	1750.3	1846.9	1943.4	1846.9	1750.3	1682.2
17.5°	1564.9	1553.9	1542.8	1559.9	1605.1	1664.9	1768.9	1872.8	1768.9	1664.9	1605.1
20°	1552.3	1534.2	1513.5	1523.0	1562.6	1618.0	1720.6	1823.2	1720.6	1618.0	1562.6
22.5°	1530.9	1512.5	1489.7	1493.7	1524.4	1573.4	1677.3	1781.3	1677.3	1573.4	1524.4
25°	1487.0	1472.8	1452.9	1447.3	1456.0	1491.7	1609.0	1726.2	1609.0	1491.7	1456.0
27.5°	1435.3	1425.8	1413.8	1402.7	1392.5	1415.5	1537.9	1660.3	1537.9	1415.5	1392.5
30°	1405.1	1393.3	1381.2	1367.0	1350.6	1368.9	1491.3	1613.7	1491.3	1368.9	1350.6
32.5°	1410.3	1382.4	1353.8	1327.1	1302.5	1315.6	1442.2	1568.7	1442.2	1315.6	1302.5
35°	1413.7	1357.0	1309.6	1270.8	1240.7	1251.0	1382.9	1514.8	1382.9	1251.0	1240.7
37.5°	1330.7	1293.3	1252.4	1211.6	1170.7	1175.4	1316.8	1458.2	1316.8	1175.4	1170.7
40°	1297.6	1273.6	1221.1	1170.2	1121.1	1121.3	1269.6	1417.8	1269.6	1121.3	1121.1
42.5°	1266.7	1241.6	1173.1	1117.1	1073.5	1077.8	1226.1	1374.4	1226.1	1077.8	1073.5
45°	1082.9	1088.1	1070.0	1039.0	995.0	1000.6	1154.9	1309.2	1154.9	1000.6	995.0
47.5°	909.7	947.4	987.9	984.5	937.1	938.3	1085.3	1232.4	1085.3	938.3	937.1
50°	833.2	886.4	951.0	956.2	901.9	895.9	1034.7	1173.4	1034.7	895.9	901.9
52.5°	769.5	837.2	923.3	933.6	868.3	852.2	984.1	1116.0	984.1	852.2	868.3
55°	686.0	775.2	893.3	907.1	816.6	780.4	907.1	1033.8	907.1	780.4	816.6
57.5°	612.9	688.5	791.0	805.4	732.0	706.9	826.7	946.5	826.7	706.9	732.0
60°	567.0	621.3	692.0	705.8	662.7	659.5	775.8	892.2	775.8	659.5	662.7
62.5°	511.1	548.4	596.3	612.5	597.0	613.1	723.9	834.8	723.9	613.1	597.0
65°	409.2	439.0	478.6	501.9	508.8	539.2	640.1	740.9	640.1	539.2	508.8
67.5°	330.8	358.6	388.7	411.8	427.9	461.9	549.8	637.7	549.8	461.9	427.9
70°	264.2	292.9	326.5	354.1	375.6	411.2	488.8	566.4	488.8	411.2	375.6
72.5°	215.6	240.1	267.5	294.4	320.8	357.2	423.8	490.3	423.8	357.2	320.8
75°	139.2	158.4	183.4	210.6	239.9	275.2	328.6	382.1	328.6	275.2	239.9
77.5°	103.6	113.0	125.6	144.5	169.6	198.3	237.2	276.2	237.2	198.3	169.6
80°	83.6	84.0	84.9	98.3	124.1	150.9	180.2	209.5	180.2	150.9	124.1
82.5°	66.4	65.4	64.2	71.4	86.9	104.0	125.7	147.4	125.7	104.0	86.9
85°	30.8	33.6	37.1	39.7	41.4	45.3	55.6	65.9	55.6	45.3	41.4
87.5°	7.8	7.8	7.8	8.8	10.9	12.6	13.3	14.0	13.3	12.6	10.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1427835

CATALOG NUMBER: SQ2W-PH1-OU-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5	2038.5
2.5°	2018.1	2003.3	1995.0	1988.5	1987.1	1985.7	1987.1	1988.5	1995.0	2003.3	2018.1
5°	1946.9	1906.8	1880.1	1859.6	1857.9	1856.2	1857.9	1859.6	1880.1	1906.8	1946.9
7.5°	1834.3	1787.9	1758.4	1736.0	1734.6	1733.2	1734.6	1736.0	1758.4	1787.9	1834.3
10°	1762.2	1714.8	1688.1	1668.0	1668.0	1668.0	1668.0	1668.0	1688.1	1714.8	1762.2
12.5°	1701.7	1657.7	1637.9	1624.1	1628.2	1632.3	1628.2	1624.1	1637.9	1657.7	1701.7
15°	1623.6	1591.7	1586.6	1585.1	1594.5	1604.0	1594.5	1585.1	1586.6	1591.7	1623.6
17.5°	1559.9	1542.8	1553.9	1564.9	1575.9	1587.0	1575.9	1564.9	1553.9	1542.8	1559.9
20°	1523.0	1513.5	1534.2	1552.3	1562.6	1573.0	1562.6	1552.3	1534.2	1513.5	1523.0
22.5°	1493.7	1489.7	1512.5	1530.9	1536.4	1542.0	1536.4	1530.9	1512.5	1489.7	1493.7
25°	1447.3	1452.9	1472.8	1487.0	1484.4	1481.8	1484.4	1487.0	1472.8	1452.9	1447.3
27.5°	1402.7	1413.8	1425.8	1435.3	1436.8	1438.4	1436.8	1435.3	1425.8	1413.8	1402.7
30°	1367.0	1381.2	1393.3	1405.1	1416.3	1427.5	1416.3	1405.1	1393.3	1381.2	1367.0
32.5°	1327.1	1353.8	1382.4	1410.3	1436.0	1461.7	1436.0	1410.3	1382.4	1353.8	1327.1
35°	1270.8	1309.6	1357.0	1413.7	1498.2	1582.7	1498.2	1413.7	1357.0	1309.6	1270.8
37.5°	1211.6	1252.4	1293.3	1330.7	1357.6	1384.5	1357.6	1330.7	1293.3	1252.4	1211.6
40°	1170.2	1221.1	1273.6	1297.6	1235.5	1173.4	1235.5	1297.6	1273.6	1221.1	1170.2
42.5°	1117.1	1173.1	1241.6	1266.7	1161.9	1057.1	1161.9	1266.7	1241.6	1173.1	1117.1
45°	1039.0	1070.0	1088.1	1082.9	1007.9	932.9	1007.9	1082.9	1088.1	1070.0	1039.0
47.5°	984.5	987.9	947.4	909.7	880.4	851.1	880.4	909.7	947.4	987.9	984.5
50°	956.2	951.0	886.4	833.2	814.2	795.2	814.2	833.2	886.4	951.0	956.2
52.5°	933.6	923.3	837.2	769.5	756.8	744.0	756.8	769.5	837.2	923.3	933.6
55°	907.1	893.3	775.2	686.0	683.4	680.8	683.4	686.0	775.2	893.3	907.1
57.5°	805.4	791.0	688.5	612.9	617.3	621.8	617.3	612.9	688.5	791.0	805.4
60°	705.8	692.0	621.3	567.0	561.8	556.7	561.8	567.0	621.3	692.0	705.8
62.5°	612.5	596.3	548.4	511.1	506.0	500.8	506.0	511.1	548.4	596.3	612.5
65°	501.9	478.6	439.0	409.2	409.2	409.2	409.2	409.2	439.0	478.6	501.9
67.5°	411.8	388.7	358.6	330.8	310.1	289.4	310.1	330.8	358.6	388.7	411.8
70°	354.1	326.5	292.9	264.2	250.4	236.6	250.4	264.2	292.9	326.5	354.1
72.5°	294.4	267.5	240.1	215.6	199.7	183.9	199.7	215.6	240.1	267.5	294.4
75°	210.6	183.4	158.4	139.2	137.5	135.8	137.5	139.2	158.4	183.4	210.6
77.5°	144.5	125.6	113.0	103.6	103.8	104.0	103.8	103.6	113.0	125.6	144.5
80°	98.3	84.9	84.0	83.6	84.5	85.3	84.5	83.6	84.0	84.9	98.3
82.5°	71.4	64.2	65.4	66.4	66.5	66.7	66.5	66.4	65.4	64.2	71.4
85°	39.7	37.1	33.6	30.8	30.0	29.1	30.0	30.8	33.6	37.1	39.7
87.5°	8.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8	8.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1427835

CATALOG NUMBER: SQ2W-PH1-0U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	2038.5	2038.5	2038.5	2038.5
2.5°	2039.5	2053.1	2043.5	2033.8
5°	2000.3	2040.6	2041.5	2042.4
7.5°	1897.5	1951.7	1978.4	2005.1
10°	1830.3	1891.5	1932.0	1972.5
12.5°	1769.8	1836.9	1900.8	1964.8
15°	1682.2	1750.3	1846.9	1943.4
17.5°	1605.1	1664.9	1768.9	1872.8
20°	1562.6	1618.0	1720.6	1823.2
22.5°	1524.4	1573.4	1677.3	1781.3
25°	1456.0	1491.7	1609.0	1726.2
27.5°	1392.5	1415.5	1537.9	1660.3
30°	1350.6	1368.9	1491.3	1613.7
32.5°	1302.5	1315.6	1442.2	1568.7
35°	1240.7	1251.0	1382.9	1514.8
37.5°	1170.7	1175.4	1316.8	1458.2
40°	1121.1	1121.3	1269.6	1417.8
42.5°	1073.5	1077.8	1226.1	1374.4
45°	995.0	1000.6	1154.9	1309.2
47.5°	937.1	938.3	1085.3	1232.4
50°	901.9	895.9	1034.7	1173.4
52.5°	868.3	852.2	984.1	1116.0
55°	816.6	780.4	907.1	1033.8
57.5°	732.0	706.9	826.7	946.5
60°	662.7	659.5	775.8	892.2
62.5°	597.0	613.1	723.9	834.8
65°	508.8	539.2	640.1	740.9
67.5°	427.9	461.9	549.8	637.7
70°	375.6	411.2	488.8	566.4
72.5°	320.8	357.2	423.8	490.3
75°	239.9	275.2	328.6	382.1
77.5°	169.6	198.3	237.2	276.2
80°	124.1	150.9	180.2	209.5
82.5°	86.9	104.0	125.7	147.4
85°	41.4	45.3	55.6	65.9
87.5°	10.9	12.6	13.3	14.0
90°	0.0	0.0	0.0	0.0



TEST NUMBER: P1427835
 CATALOG NUMBER: SQ2W-PH1-0U-100D-L935-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	22.86	24.45	23.23	24.76	25.08	21.69	23.28	22.05	23.59	23.91
	3H	25.09	26.52	25.46	26.84	27.21	22.79	24.22	23.17	24.55	24.91
	4H	25.93	27.28	26.33	27.63	28.00	23.07	24.41	23.47	24.76	25.14
	6H	26.44	27.68	26.85	28.04	28.44	23.24	24.49	23.66	24.85	25.24
	8H	26.61	27.79	27.03	28.18	28.58	23.32	24.51	23.75	24.90	25.30
	12H	26.69	27.82	27.12	28.21	28.64	23.36	24.49	23.79	24.87	25.30
4H	2H	23.38	24.72	23.78	25.07	25.45	22.46	23.80	22.86	24.15	24.53
	3H	25.70	26.82	26.11	27.21	27.61	23.75	24.87	24.16	25.27	25.67
	4H	26.60	27.61	27.03	28.02	28.46	24.07	25.08	24.50	25.50	25.93
	6H	27.20	28.08	27.65	28.52	28.97	24.31	25.19	24.77	25.63	26.09
	8H	27.42	28.24	27.88	28.68	29.15	24.42	25.24	24.88	25.68	26.15
	12H	27.53	28.27	28.02	28.75	29.22	24.47	25.21	24.95	25.69	26.16
8H	4H	26.68	27.50	27.14	27.94	28.41	24.36	25.18	24.82	25.62	26.09
	6H	27.34	28.01	27.83	28.50	28.98	24.65	25.33	25.15	25.82	26.30
	8H	27.60	28.21	28.12	28.72	29.21	24.81	25.41	25.32	25.92	26.41
	12H	27.77	28.31	28.28	28.80	29.36	24.90	25.44	25.41	25.93	26.49
12H	4H	26.66	27.40	27.14	27.87	28.34	24.39	25.12	24.87	25.60	26.07
	6H	27.32	27.93	27.83	28.43	28.92	24.69	25.30	25.21	25.81	26.30
	8H	27.62	28.16	28.13	28.65	29.21	24.89	25.43	25.40	25.92	26.48