

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427839

Luminaire Tested: SQ2W-PH1-0U-125D-L840-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1427839  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-PH1-0U-125D-L840-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - PERCEIVE HEX LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT N/A - DIRECT ONLY  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6540.5 lumens  
Efficiency: N/A  
Efficacy: 132.9 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.02 / 1.23  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 49.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1427839

CATALOG NUMBER: SQ2W-PH1-0U-125D-L840-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1427839

CATALOG NUMBER: SQ2W-PH1-0U-125D-L840-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	103	99	96	99	96	93	95	92	90	91	89	87	85
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72
3	91	81	73	67	89	80	72	67	77	71	65	74	69	64	72	67	63	61
4	84	72	64	57	82	71	63	57	69	62	56	66	60	55	64	59	55	53
5	77	65	56	50	75	64	56	49	62	54	49	60	53	48	58	52	48	46
6	72	59	50	44	70	58	49	43	56	48	43	54	48	43	53	47	42	40
7	66	53	45	39	65	52	44	38	51	43	38	49	43	38	48	42	38	36
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29
10	54	41	34	28	53	41	33	28	40	33	28	39	33	28	38	32	28	26

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	47759	47759	47759	47759
5°	48033	43654	48033	43654
10°	46928	39683	46928	39683
15°	47138	38906	47138	38906
20°	45456	39219	45456	39219
25°	44624	38307	44624	38307
30°	43657	38620	43657	38620
35°	43325	45266	43325	45266
40°	43363	35889	43363	35889
45°	43379	30912	43379	30912
50°	42771	28984	42771	28984
55°	42226	27808	42226	27808
60°	41807	26085	41807	26085
65°	41073	22689	41073	22689
70°	38794	16211	38794	16211
75°	34591	12289	34591	12289
80°	28265	11511	28265	11511
85°	17728	7818	17728	7818

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 43379 cd/sqm

TEST NUMBER: P1427839

CATALOG NUMBER: SQ2W-PH1-0U-125D-L840-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	260.3	4.0
10°-20°	684.6	10.5
20°-30°	1003.8	15.3
30°-40°	1215.4	18.6
40°-50°	1195.2	18.3
50°-60°	1039.6	15.9
60°-70°	723.0	11.1
70°-80°	342.9	5.2
80°-90°	75.6	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1948.7	29.8
0°-40°	3164.1	48.4
0°-60°	5398.9	82.5
0°-90°	6540.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6540.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	2958	2958	2958	2958	2958	
5°	2964	2694	2964	2694	2964	279
15°	2820	2328	2820	2328	2820	786
25°	2505	2150	2505	2150	2505	1152
35°	2198	2297	2198	2297	2198	1377
45°	1900	1354	1900	1354	1900	1460
55°	1500	988	1500	988	1500	1340
65°	1075	594	1075	594	1075	1056
75°	554	197	554	197	554	588
85°	96	42	96	42	96	131
90°	0	0	0	0	0	



TEST NUMBER: P1427839

CATALOG NUMBER: SQ2W-PH1-OU-125D-L840-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2958.0	2958.0	2958.0	2958.0	2958.0	2958.0	2958.0	2958.0	2958.0	2958.0	2958.0
2.5°	2951.3	2965.3	2979.3	2959.5	2928.5	2907.0	2895.0	2885.5	2883.5	2881.5	2883.5
5°	2963.7	2962.4	2961.2	2902.7	2825.1	2767.0	2728.2	2698.5	2696.0	2693.5	2696.0
7.5°	2909.6	2870.9	2832.1	2753.5	2661.7	2594.4	2551.6	2519.0	2517.0	2515.0	2517.0
10°	2862.4	2803.6	2744.8	2656.0	2557.1	2488.3	2449.6	2420.5	2420.5	2420.5	2420.5
12.5°	2851.1	2758.3	2665.5	2568.1	2469.3	2405.5	2376.8	2356.7	2362.7	2368.7	2362.7
15°	2820.1	2680.0	2539.9	2441.1	2356.1	2309.8	2302.3	2300.1	2313.8	2327.6	2313.8
17.5°	2717.7	2566.8	2416.0	2329.1	2263.6	2238.8	2254.8	2270.8	2286.8	2302.8	2286.8
20°	2645.6	2496.8	2347.9	2267.6	2210.0	2196.3	2226.3	2252.5	2267.6	2282.6	2267.6
22.5°	2584.8	2434.0	2283.1	2212.0	2167.5	2161.7	2194.8	2221.5	2229.5	2237.5	2229.5
25°	2504.9	2334.8	2164.7	2112.8	2100.2	2108.4	2137.2	2157.8	2154.0	2150.3	2154.0
27.5°	2409.2	2231.6	2054.0	2020.6	2035.4	2051.5	2069.0	2082.7	2085.0	2087.2	2085.0
30°	2341.7	2164.0	1986.4	1959.8	1983.6	2004.2	2021.8	2039.0	2055.2	2071.5	2055.2
32.5°	2276.4	2092.7	1909.1	1890.0	1925.8	1964.5	2006.0	2046.5	2083.7	2121.0	2083.7
35°	2198.1	2006.7	1815.4	1800.3	1844.1	1900.4	1969.2	2051.5	2174.1	2296.6	2174.1
37.5°	2115.9	1910.8	1705.7	1698.8	1758.1	1817.4	1876.7	1930.9	1970.0	2009.0	1970.0
40°	2057.4	1842.3	1627.1	1626.8	1698.1	1771.9	1848.2	1882.9	1792.8	1702.8	1792.8
42.5°	1994.4	1779.2	1564.1	1557.7	1621.0	1702.3	1801.7	1838.1	1686.0	1533.9	1686.0
45°	1899.8	1675.9	1452.0	1443.8	1507.6	1552.7	1578.9	1571.4	1462.6	1353.8	1462.6
47.5°	1788.3	1574.9	1361.5	1359.8	1428.6	1433.6	1374.8	1320.1	1277.5	1235.0	1277.5
50°	1702.8	1501.4	1300.0	1308.7	1387.6	1380.0	1286.2	1209.0	1181.5	1153.9	1181.5
52.5°	1619.5	1428.1	1236.7	1260.0	1354.8	1339.8	1214.9	1116.7	1098.2	1079.6	1098.2
55°	1500.1	1316.3	1132.4	1184.9	1316.3	1296.2	1124.9	995.4	991.6	987.9	991.6
57.5°	1373.5	1199.6	1025.7	1062.2	1168.8	1147.8	999.2	889.3	895.8	902.3	895.8
60°	1294.7	1125.8	956.9	961.6	1024.2	1004.2	901.6	822.8	815.3	807.8	815.3
62.5°	1211.4	1050.5	889.6	866.3	888.8	865.3	795.8	741.7	734.2	726.7	734.2
65°	1075.1	928.8	782.4	738.3	728.3	694.6	637.0	593.9	593.9	593.9	593.9
67.5°	925.4	797.8	670.2	620.9	597.6	564.1	520.3	480.0	449.9	419.9	449.9
70°	821.8	709.3	596.7	545.1	513.8	473.8	425.0	383.4	363.4	343.4	363.4
72.5°	711.5	614.9	518.4	465.5	427.2	388.2	348.4	312.8	289.8	266.8	289.8
75°	554.5	476.9	399.3	348.1	305.5	266.1	229.9	202.0	199.5	197.0	199.5
77.5°	400.8	344.2	287.7	246.2	209.6	182.3	164.0	150.4	150.6	150.9	150.6
80°	304.0	261.4	218.9	180.1	142.6	123.2	122.0	121.3	122.6	123.8	122.6
82.5°	213.9	182.4	150.9	126.1	103.6	93.2	94.9	96.3	96.6	96.8	96.6
85°	95.7	80.7	65.7	60.0	57.5	53.8	48.8	44.7	43.5	42.2	43.5
87.5°	20.3	19.3	18.3	15.8	12.8	11.3	11.3	11.3	11.3	11.3	11.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1427839

CATALOG NUMBER: SQ2W-PH1-0U-125D-L840-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2958.0	2958.0	2958.0	2958.0	2958.0	2958.0	2958.0	2958.0	2958.0	2958.0	2958.0
2.5°	2885.5	2895.0	2907.0	2928.5	2959.5	2979.3	2965.3	2951.3	2965.3	2979.3	2959.5
5°	2698.5	2728.2	2767.0	2825.1	2902.7	2961.2	2962.4	2963.7	2962.4	2961.2	2902.7
7.5°	2519.0	2551.6	2594.4	2661.7	2753.5	2832.1	2870.9	2909.6	2870.9	2832.1	2753.5
10°	2420.5	2449.6	2488.3	2557.1	2656.0	2744.8	2803.6	2862.4	2803.6	2744.8	2656.0
12.5°	2356.7	2376.8	2405.5	2469.3	2568.1	2665.5	2758.3	2851.1	2758.3	2665.5	2568.1
15°	2300.1	2302.3	2309.8	2356.1	2441.1	2539.9	2680.0	2820.1	2680.0	2539.9	2441.1
17.5°	2270.8	2254.8	2238.8	2263.6	2329.1	2416.0	2566.8	2717.7	2566.8	2416.0	2329.1
20°	2252.5	2226.3	2196.3	2210.0	2267.6	2347.9	2496.8	2645.6	2496.8	2347.9	2267.6
22.5°	2221.5	2194.8	2161.7	2167.5	2212.0	2283.1	2434.0	2584.8	2434.0	2283.1	2212.0
25°	2157.8	2137.2	2108.4	2100.2	2112.8	2164.7	2334.8	2504.9	2334.8	2164.7	2112.8
27.5°	2082.7	2069.0	2051.5	2035.4	2020.6	2054.0	2231.6	2409.2	2231.6	2054.0	2020.6
30°	2039.0	2021.8	2004.2	1983.6	1959.8	1986.4	2164.0	2341.7	2164.0	1986.4	1959.8
32.5°	2046.5	2006.0	1964.5	1925.8	1890.0	1909.1	2092.7	2276.4	2092.7	1909.1	1890.0
35°	2051.5	1969.2	1900.4	1844.1	1800.3	1815.4	2006.7	2198.1	2006.7	1815.4	1800.3
37.5°	1930.9	1876.7	1817.4	1758.1	1698.8	1705.7	1910.8	2115.9	1910.8	1705.7	1698.8
40°	1882.9	1848.2	1771.9	1698.1	1626.8	1627.1	1842.3	2057.4	1842.3	1627.1	1626.8
42.5°	1838.1	1801.7	1702.3	1621.0	1557.7	1564.1	1779.2	1994.4	1779.2	1564.1	1557.7
45°	1571.4	1578.9	1552.7	1507.6	1443.8	1452.0	1675.9	1899.8	1675.9	1452.0	1443.8
47.5°	1320.1	1374.8	1433.6	1428.6	1359.8	1361.5	1574.9	1788.3	1574.9	1361.5	1359.8
50°	1209.0	1286.2	1380.0	1387.6	1308.7	1300.0	1501.4	1702.8	1501.4	1300.0	1308.7
52.5°	1116.7	1214.9	1339.8	1354.8	1260.0	1236.7	1428.1	1619.5	1428.1	1236.7	1260.0
55°	995.4	1124.9	1296.2	1316.3	1184.9	1132.4	1316.3	1500.1	1316.3	1132.4	1184.9
57.5°	889.3	999.2	1147.8	1168.8	1062.2	1025.7	1199.6	1373.5	1199.6	1025.7	1062.2
60°	822.8	901.6	1004.2	1024.2	961.6	956.9	1125.8	1294.7	1125.8	956.9	961.6
62.5°	741.7	795.8	865.3	888.8	866.3	889.6	1050.5	1211.4	1050.5	889.6	866.3
65°	593.9	637.0	694.6	728.3	738.3	782.4	928.8	1075.1	928.8	782.4	738.3
67.5°	480.0	520.3	564.1	597.6	620.9	670.2	797.8	925.4	797.8	670.2	620.9
70°	383.4	425.0	473.8	513.8	545.1	596.7	709.3	821.8	709.3	596.7	545.1
72.5°	312.8	348.4	388.2	427.2	465.5	518.4	614.9	711.5	614.9	518.4	465.5
75°	202.0	229.9	266.1	305.5	348.1	399.3	476.9	554.5	476.9	399.3	348.1
77.5°	150.4	164.0	182.3	209.6	246.2	287.7	344.2	400.8	344.2	287.7	246.2
80°	121.3	122.0	123.2	142.6	180.1	218.9	261.4	304.0	261.4	218.9	180.1
82.5°	96.3	94.9	93.2	103.6	126.1	150.9	182.4	213.9	182.4	150.9	126.1
85°	44.7	48.8	53.8	57.5	60.0	65.7	80.7	95.7	80.7	65.7	60.0
87.5°	11.3	11.3	11.3	12.8	15.8	18.3	19.3	20.3	19.3	18.3	15.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1427839

CATALOG NUMBER: SQ2W-PH1-0U-125D-L840-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2958.0	2958.0	2958.0	2958.0	2958.0	2958.0	2958.0	2958.0	2958.0	2958.0	2958.0
2.5°	2928.5	2907.0	2895.0	2885.5	2883.5	2881.5	2883.5	2885.5	2895.0	2907.0	2928.5
5°	2825.1	2767.0	2728.2	2698.5	2696.0	2693.5	2696.0	2698.5	2728.2	2767.0	2825.1
7.5°	2661.7	2594.4	2551.6	2519.0	2517.0	2515.0	2517.0	2519.0	2551.6	2594.4	2661.7
10°	2557.1	2488.3	2449.6	2420.5	2420.5	2420.5	2420.5	2420.5	2449.6	2488.3	2557.1
12.5°	2469.3	2405.5	2376.8	2356.7	2362.7	2368.7	2362.7	2356.7	2376.8	2405.5	2469.3
15°	2356.1	2309.8	2302.3	2300.1	2313.8	2327.6	2313.8	2300.1	2302.3	2309.8	2356.1
17.5°	2263.6	2238.8	2254.8	2270.8	2286.8	2302.8	2286.8	2270.8	2254.8	2238.8	2263.6
20°	2210.0	2196.3	2226.3	2252.5	2267.6	2282.6	2267.6	2252.5	2226.3	2196.3	2210.0
22.5°	2167.5	2161.7	2194.8	2221.5	2229.5	2237.5	2229.5	2221.5	2194.8	2161.7	2167.5
25°	2100.2	2108.4	2137.2	2157.8	2154.0	2150.3	2154.0	2157.8	2137.2	2108.4	2100.2
27.5°	2035.4	2051.5	2069.0	2082.7	2085.0	2087.2	2085.0	2082.7	2069.0	2051.5	2035.4
30°	1983.6	2004.2	2021.8	2039.0	2055.2	2071.5	2055.2	2039.0	2021.8	2004.2	1983.6
32.5°	1925.8	1964.5	2006.0	2046.5	2083.7	2121.0	2083.7	2046.5	2006.0	1964.5	1925.8
35°	1844.1	1900.4	1969.2	2051.5	2174.1	2296.6	2174.1	2051.5	1969.2	1900.4	1844.1
37.5°	1758.1	1817.4	1876.7	1930.9	1970.0	2009.0	1970.0	1930.9	1876.7	1817.4	1758.1
40°	1698.1	1771.9	1848.2	1882.9	1792.8	1702.8	1792.8	1882.9	1848.2	1771.9	1698.1
42.5°	1621.0	1702.3	1801.7	1838.1	1686.0	1533.9	1686.0	1838.1	1801.7	1702.3	1621.0
45°	1507.6	1552.7	1578.9	1571.4	1462.6	1353.8	1462.6	1571.4	1578.9	1552.7	1507.6
47.5°	1428.6	1433.6	1374.8	1320.1	1277.5	1235.0	1277.5	1320.1	1374.8	1433.6	1428.6
50°	1387.6	1380.0	1286.2	1209.0	1181.5	1153.9	1181.5	1209.0	1286.2	1380.0	1387.6
52.5°	1354.8	1339.8	1214.9	1116.7	1098.2	1079.6	1098.2	1116.7	1214.9	1339.8	1354.8
55°	1316.3	1296.2	1124.9	995.4	991.6	987.9	991.6	995.4	1124.9	1296.2	1316.3
57.5°	1168.8	1147.8	999.2	889.3	895.8	902.3	895.8	889.3	999.2	1147.8	1168.8
60°	1024.2	1004.2	901.6	822.8	815.3	807.8	815.3	822.8	901.6	1004.2	1024.2
62.5°	888.8	865.3	795.8	741.7	734.2	726.7	734.2	741.7	795.8	865.3	888.8
65°	728.3	694.6	637.0	593.9	593.9	593.9	593.9	637.0	694.6	728.3	728.3
67.5°	597.6	564.1	520.3	480.0	449.9	419.9	449.9	520.3	564.1	597.6	597.6
70°	513.8	473.8	425.0	383.4	363.4	343.4	363.4	425.0	473.8	513.8	513.8
72.5°	427.2	388.2	348.4	312.8	289.8	266.8	289.8	348.4	388.2	427.2	427.2
75°	305.5	266.1	229.9	202.0	199.5	197.0	199.5	229.9	266.1	305.5	305.5
77.5°	209.6	182.3	164.0	150.4	150.6	150.9	150.6	164.0	182.3	209.6	209.6
80°	142.6	123.2	122.0	121.3	122.6	123.8	122.6	121.3	122.0	123.2	142.6
82.5°	103.6	93.2	94.9	96.3	96.6	96.8	96.6	93.2	94.9	93.2	103.6
85°	57.5	53.8	48.8	44.7	43.5	42.2	43.5	44.7	48.8	53.8	57.5
87.5°	12.8	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	12.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1427839

CATALOG NUMBER: SQ2W-PH1-0U-125D-L840-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	2958.0	2958.0	2958.0	2958.0
2.5°	2959.5	2979.3	2965.3	2951.3
5°	2902.7	2961.2	2962.4	2963.7
7.5°	2753.5	2832.1	2870.9	2909.6
10°	2656.0	2744.8	2803.6	2862.4
12.5°	2568.1	2665.5	2758.3	2851.1
15°	2441.1	2539.9	2680.0	2820.1
17.5°	2329.1	2416.0	2566.8	2717.7
20°	2267.6	2347.9	2496.8	2645.6
22.5°	2212.0	2283.1	2434.0	2584.8
25°	2112.8	2164.7	2334.8	2504.9
27.5°	2020.6	2054.0	2231.6	2409.2
30°	1959.8	1986.4	2164.0	2341.7
32.5°	1890.0	1909.1	2092.7	2276.4
35°	1800.3	1815.4	2006.7	2198.1
37.5°	1698.8	1705.7	1910.8	2115.9
40°	1626.8	1627.1	1842.3	2057.4
42.5°	1557.7	1564.1	1779.2	1994.4
45°	1443.8	1452.0	1675.9	1899.8
47.5°	1359.8	1361.5	1574.9	1788.3
50°	1308.7	1300.0	1501.4	1702.8
52.5°	1260.0	1236.7	1428.1	1619.5
55°	1184.9	1132.4	1316.3	1500.1
57.5°	1062.2	1025.7	1199.6	1373.5
60°	961.6	956.9	1125.8	1294.7
62.5°	866.3	889.6	1050.5	1211.4
65°	738.3	782.4	928.8	1075.1
67.5°	620.9	670.2	797.8	925.4
70°	545.1	596.7	709.3	821.8
72.5°	465.5	518.4	614.9	711.5
75°	348.1	399.3	476.9	554.5
77.5°	246.2	287.7	344.2	400.8
80°	180.1	218.9	261.4	304.0
82.5°	126.1	150.9	182.4	213.9
85°	60.0	65.7	80.7	95.7
87.5°	15.8	18.3	19.3	20.3
90°	0.0	0.0	0.0	0.0



TEST NUMBER: P1427839  
 CATALOG NUMBER: SQ2W-PH1-0U-125D-L840-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	24.15	25.74	24.52	26.06	26.37	22.98	24.57	23.35	24.89	25.20
	3H	26.38	27.81	26.76	28.14	28.50	24.08	25.52	24.46	25.84	26.20
	4H	27.23	28.57	27.62	28.92	29.30	24.36	25.71	24.76	26.05	26.43
	6H	27.73	28.97	28.14	29.34	29.73	24.54	25.78	24.95	26.15	26.54
	8H	27.90	29.09	28.33	29.48	29.88	24.62	25.80	25.04	26.19	26.59
	12H	27.98	29.12	28.41	29.50	29.93	24.65	25.79	25.08	26.17	26.60
4H	2H	24.67	26.02	25.07	26.37	26.74	23.75	25.09	24.15	25.44	25.82
	3H	26.99	28.11	27.40	28.51	28.91	25.04	26.16	25.45	26.56	26.96
	4H	27.89	28.90	28.32	29.31	29.75	25.37	26.37	25.80	26.79	27.23
	6H	28.49	29.37	28.95	29.81	30.27	25.60	26.48	26.06	26.92	27.38
	8H	28.71	29.53	29.17	29.97	30.44	25.71	26.53	26.17	26.97	27.44
	12H	28.83	29.56	29.31	30.04	30.51	25.77	26.50	26.25	26.98	27.45
8H	4H	27.97	28.79	28.43	29.23	29.70	25.65	26.47	26.11	26.91	27.38
	6H	28.63	29.31	29.12	29.80	30.27	25.95	26.63	26.44	27.12	27.59
	8H	28.90	29.51	29.41	30.01	30.50	26.10	26.71	26.61	27.22	27.70
	12H	29.06	29.60	29.57	30.09	30.65	26.20	26.73	26.70	27.22	27.79
12H	4H	27.96	28.69	28.44	29.17	29.64	25.68	26.41	26.16	26.89	27.36
	6H	28.61	29.22	29.12	29.73	30.21	25.99	26.60	26.50	27.10	27.59
	8H	28.92	29.45	29.42	29.94	30.51	26.18	26.72	26.69	27.21	27.77