

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427937

Luminaire Tested: SQ2W-PH1-K-100U-125D-L935-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1427937
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-10)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PH1-K-100U-125D-L935-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE HEX LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9484.0 lumens
Efficiency: N/A
Efficacy: 115.2 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.02 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 82.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1427937

CATALOG NUMBER: SQ2W-PH1-K-100U-125D-L935-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1427937

CATALOG NUMBER: SQ2W-PH1-K-100U-125D-L935-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65	59				59
1	100	96	92	89	93	90	86	83	78	76	73	67	66	64	58	56	55	50				50
2	91	84	78	73	85	79	73	69	69	65	61	59	56	54	51	49	47	43				43
3	83	74	67	61	78	69	63	58	61	56	51	53	49	46	45	42	40	36				36
4	76	65	58	51	71	61	54	49	54	48	44	47	43	39	40	37	34	31				31
5	70	58	50	44	65	55	48	42	48	42	38	42	38	34	36	33	30	27				27
6	65	52	44	38	60	49	42	37	44	38	33	38	33	30	33	29	27	24				24
7	60	47	39	34	56	45	37	32	40	34	29	35	30	26	30	26	24	21				21
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	28	24	21	19				19
9	52	39	32	27	48	37	30	26	33	27	23	29	25	21	26	22	19	17				17
10	48	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	17	15				15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	40981	40981	40981	40981
5°	41217	37458	41217	37458
10°	40267	34050	40267	34050
15°	40449	33385	40449	33385
20°	39006	33652	39006	33652
25°	38291	32870	38291	32870
30°	37460	33138	37460	33138
35°	37177	38843	37177	38843
40°	37208	30795	37208	30795
45°	37223	26523	37223	26523
50°	36700	24872	36700	24872
55°	36233	23862	36233	23862
60°	35872	22381	35872	22381
65°	35247	19469	35247	19469
70°	33290	13907	33290	13907
75°	29681	10549	29681	10549
80°	24249	9884	24249	9884
85°	15209	6706	15209	6706

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 37223 cd/sqm



TEST NUMBER: P1427937

CATALOG NUMBER: SQ2W-PH1-K-100U-125D-L935-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	223.3	2.4
10°-20°	587.5	6.2
20°-30°	861.3	9.1
30°-40°	1042.9	11.0
40°-50°	1025.5	10.8
50°-60°	892.1	9.4
60°-70°	620.4	6.5
70°-80°	294.2	3.1
80°-90°	70.4	0.7
90°-100°	105.4	1.1
100°-110°	307.3	3.2
110°-120°	501.5	5.3
120°-130°	636.4	6.7
130°-140°	681.0	7.2
140°-150°	635.9	6.7
150°-160°	523.2	5.5
160°-170°	350.9	3.7
170°-180°	124.6	1.3
0°-30°	1672.1	17.6
0°-40°	2715.0	28.6
0°-60°	4632.7	48.8
0°-90°	5617.7	59.2
90°-120°	914.2	9.6
90°-150°	2867.5	30.2
90°-180°	3866.0	40.8
0°-180°	9484.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2538	2538	2538	2538	2538	
5°	2543	2311	2543	2311	2543	239
15°	2420	1997	2420	1997	2420	675
25°	2149	1845	2149	1845	2149	988
35°	1886	1971	1886	1971	1886	1181
45°	1630	1162	1630	1162	1630	1253
55°	1287	848	1287	848	1287	1150
65°	923	510	923	510	923	907
75°	476	169	476	169	476	504
85°	82	36	82	36	82	110
90°	4	29	4	58	4	6
95°	42	31	42	181	42	50
105°	195	313	195	431	195	208
115°	374	519	374	639	374	369
125°	554	823	554	784	554	495
135°	753	1077	753	868	753	582
145°	962	1241	962	887	962	602
155°	1142	1348	1142	920	1142	525
165°	1263	1406	1263	1059	1263	355
175°	1320	1376	1320	1243	1320	125
180°	1324	1324	1324	1324	1324	



TEST NUMBER: P1427937

CATALOG NUMBER: SQ2W-PH1-K-100U-125D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2538.2	2538.2	2538.2	2538.2	2538.2	2538.2	2538.2	2538.2	2538.2	2538.2	2538.2
2.5°	2532.4	2544.4	2556.5	2539.5	2512.9	2494.4	2484.1	2476.0	2474.3	2472.5	2474.3
5°	2543.1	2542.0	2540.9	2490.7	2424.2	2374.3	2341.0	2315.5	2313.4	2311.2	2313.4
7.5°	2496.7	2463.4	2430.1	2362.7	2283.9	2226.2	2189.5	2161.5	2159.8	2158.1	2159.8
10°	2456.1	2405.7	2355.2	2279.0	2194.2	2135.2	2101.9	2076.9	2076.9	2076.9	2076.9
12.5°	2446.5	2366.8	2287.2	2203.7	2118.9	2064.1	2039.4	2022.2	2027.4	2032.5	2027.4
15°	2419.9	2299.7	2179.5	2094.7	2021.7	1982.0	1975.5	1973.6	1985.4	1997.3	1985.4
17.5°	2332.0	2202.5	2073.1	1998.5	1942.3	1921.0	1934.8	1948.5	1962.3	1976.0	1962.3
20°	2270.2	2142.4	2014.7	1945.7	1896.4	1884.5	1910.3	1932.8	1945.7	1958.6	1945.7
22.5°	2218.0	2088.5	1959.1	1898.1	1859.9	1854.9	1883.3	1906.2	1913.1	1920.0	1913.1
25°	2149.4	2003.4	1857.4	1812.9	1802.2	1809.1	1833.8	1851.5	1848.3	1845.1	1848.3
27.5°	2067.3	1914.9	1762.5	1733.8	1746.5	1760.4	1775.4	1787.1	1789.1	1791.0	1789.1
30°	2009.3	1856.9	1704.5	1681.7	1702.1	1719.8	1734.8	1749.6	1763.5	1777.5	1763.5
32.5°	1953.3	1795.7	1638.2	1621.8	1652.5	1685.7	1721.3	1756.0	1788.0	1820.0	1788.0
35°	1886.2	1721.9	1557.7	1544.8	1582.4	1630.7	1689.7	1760.3	1865.5	1970.7	1865.5
37.5°	1815.6	1639.6	1463.6	1457.7	1508.6	1559.5	1610.4	1656.9	1690.4	1723.9	1690.4
40°	1765.4	1580.8	1396.2	1395.9	1457.1	1520.4	1585.9	1615.7	1538.4	1461.1	1538.4
42.5°	1711.3	1526.7	1342.1	1336.7	1391.0	1460.7	1546.0	1577.2	1446.7	1316.2	1446.7
45°	1630.2	1438.0	1245.9	1238.9	1293.7	1332.3	1354.8	1348.4	1255.0	1161.6	1255.0
47.5°	1534.5	1351.4	1168.3	1166.8	1225.8	1230.1	1179.7	1132.7	1096.2	1059.7	1096.2
50°	1461.1	1288.3	1115.5	1123.0	1190.6	1184.2	1103.7	1037.4	1013.8	990.2	1013.8
52.5°	1389.6	1225.4	1061.2	1081.1	1162.5	1149.6	1042.5	958.2	942.3	926.4	942.3
55°	1287.2	1129.4	971.7	1016.7	1129.4	1112.3	965.2	854.1	850.9	847.7	850.9
57.5°	1178.5	1029.4	880.2	911.4	1002.9	984.9	857.3	763.1	768.7	774.3	768.7
60°	1110.9	966.0	821.1	825.1	878.8	861.6	773.6	706.0	699.6	693.1	699.6
62.5°	1039.4	901.4	763.4	743.4	762.7	742.5	682.8	636.4	630.0	623.6	630.0
65°	922.6	797.0	671.4	633.5	625.0	596.0	546.6	509.6	509.6	509.6	509.6
67.5°	794.1	684.6	575.1	532.8	512.8	484.0	446.5	411.8	386.1	360.3	386.1
70°	705.2	608.6	512.0	467.7	440.9	406.5	364.7	329.0	311.8	294.6	311.8
72.5°	610.5	527.7	444.8	399.5	366.6	333.1	299.0	268.4	248.7	228.9	248.7
75°	475.8	409.2	342.7	298.7	262.2	228.4	197.2	173.3	171.2	169.1	171.2
77.5°	343.9	295.4	246.9	211.2	179.9	156.4	140.7	129.0	129.2	129.4	129.2
80°	260.8	224.3	187.8	154.6	122.4	105.7	104.7	104.1	105.2	106.3	105.2
82.5°	183.5	156.5	129.4	108.2	88.9	80.0	81.5	82.6	82.9	83.1	82.9
85°	82.1	69.2	56.4	51.5	49.4	46.2	41.9	38.4	37.3	36.2	37.3
87.5°	18.2	18.4	18.9	17.8	16.0	15.0	15.0	15.3	15.5	15.5	15.5
90°	4.0	9.4	16.1	21.4	25.4	26.8	26.8	28.1	29.4	29.4	29.4
92.5°	14.7	23.3	23.5	23.5	28.6	31.0	33.2	33.4	34.8	34.8	34.8
95°	41.5	45.5	68.2	66.9	45.5	36.1	30.8	30.8	30.8	30.8	30.8
97.5°	79.2	85.1	88.8	119.0	125.7	121.4	99.0	83.2	74.4	70.4	74.4
100°	112.4	115.0	123.1	124.4	157.8	189.9	173.9	153.8	147.1	143.1	147.1
102.5°	145.5	147.1	159.4	165.1	172.8	191.0	246.6	240.5	235.9	235.1	235.9
105°	195.3	196.6	219.4	230.1	235.4	235.4	234.1	260.8	303.6	313.0	303.6
107.5°	248.5	254.7	281.4	310.0	316.2	317.8	310.8	306.8	305.2	306.3	305.2
110°	284.9	294.3	326.4	362.5	371.8	374.5	371.8	367.8	365.1	365.1	365.1



TEST NUMBER: P1427937

CATALOG NUMBER: SQ2W-PH1-K-100U-125D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	320.2	333.9	370.2	411.7	427.5	435.5	429.6	426.7	424.0	426.1	424.0
115°	374.5	394.6	442.7	485.5	517.6	521.6	520.3	520.3	519.0	519.0	519.0
117.5°	424.8	456.9	510.9	560.7	597.9	608.6	613.9	612.3	610.7	613.4	610.7
120°	460.1	497.6	559.1	615.3	651.4	667.4	672.8	670.1	672.8	670.1	672.8
122.5°	497.6	543.6	604.0	662.4	704.9	723.1	729.5	730.0	730.6	729.0	730.6
125°	553.7	609.9	680.8	741.0	785.1	806.5	811.9	813.2	815.9	822.6	815.9
127.5°	610.5	674.1	752.0	810.0	855.2	881.2	889.5	892.4	898.0	901.0	898.0
130°	650.0	722.3	801.2	856.0	900.2	928.3	943.0	947.0	953.7	952.3	953.7
132.5°	691.8	767.2	847.2	904.2	945.1	975.3	987.9	999.4	1001.8	1003.7	1001.8
135°	753.0	834.6	914.9	971.1	1009.8	1039.3	1055.3	1066.0	1072.7	1076.7	1072.7
137.5°	817.5	903.6	980.7	1030.7	1069.8	1095.2	1113.4	1124.6	1131.6	1134.8	1131.6
140°	861.4	944.3	1019.2	1071.4	1106.1	1131.6	1147.6	1161.0	1169.0	1169.0	1169.0
142.5°	903.1	985.0	1057.7	1109.9	1140.4	1163.7	1180.8	1190.9	1200.0	1200.0	1200.0
145°	961.7	1043.3	1110.2	1162.3	1187.7	1209.1	1227.9	1235.9	1241.2	1241.2	1241.2
147.5°	1023.0	1095.2	1156.2	1206.2	1227.6	1252.7	1267.5	1273.9	1280.6	1277.6	1280.6
150°	1059.3	1126.2	1185.1	1231.9	1253.3	1277.4	1292.1	1297.4	1304.1	1300.1	1304.1
152.5°	1094.6	1158.3	1211.8	1255.4	1273.6	1297.7	1314.5	1319.9	1324.4	1321.5	1324.4
155°	1142.3	1198.4	1247.9	1288.1	1304.1	1326.8	1342.9	1349.6	1354.9	1348.2	1354.9
157.5°	1184.8	1233.2	1276.3	1313.2	1330.3	1349.9	1364.8	1373.1	1378.5	1375.5	1378.5
160°	1210.5	1254.6	1293.4	1328.2	1344.2	1361.6	1377.7	1387.0	1392.4	1388.4	1392.4
162.5°	1231.9	1271.7	1308.4	1340.0	1353.9	1369.1	1388.4	1396.7	1402.0	1396.9	1402.0
165°	1262.6	1294.7	1326.8	1353.6	1365.6	1377.7	1397.7	1407.1	1411.1	1405.8	1411.1
167.5°	1285.9	1310.5	1336.5	1359.5	1368.3	1380.1	1400.1	1407.9	1413.0	1406.3	1413.0
170°	1298.8	1320.2	1342.9	1361.6	1368.3	1379.0	1399.1	1405.8	1409.8	1403.1	1409.8
172.5°	1309.5	1325.5	1344.0	1360.6	1364.0	1372.6	1391.6	1398.3	1401.2	1395.6	1401.2
175°	1320.2	1329.5	1342.9	1353.6	1352.3	1357.6	1373.7	1379.0	1384.4	1376.3	1384.4
177.5°	1325.2	1329.5	1333.8	1340.2	1335.9	1335.9	1347.7	1350.9	1352.0	1347.7	1352.0
180°	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2

TEST NUMBER: P1427937

CATALOG NUMBER: SQ2W-PH1-K-100U-125D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2538.2	2538.2	2538.2	2538.2	2538.2	2538.2	2538.2	2538.2	2538.2	2538.2	2538.2
2.5°	2476.0	2484.1	2494.4	2512.9	2539.5	2556.5	2544.4	2532.4	2544.4	2556.5	2539.5
5°	2315.5	2341.0	2374.3	2424.2	2490.7	2540.9	2542.0	2543.1	2542.0	2540.9	2490.7
7.5°	2161.5	2189.5	2226.2	2283.9	2362.7	2430.1	2463.4	2496.7	2463.4	2430.1	2362.7
10°	2076.9	2101.9	2135.2	2194.2	2279.0	2355.2	2405.7	2456.1	2405.7	2355.2	2279.0
12.5°	2022.2	2039.4	2064.1	2118.9	2203.7	2287.2	2366.8	2446.5	2366.8	2287.2	2203.7
15°	1973.6	1975.5	1982.0	2021.7	2094.7	2179.5	2299.7	2419.9	2299.7	2179.5	2094.7
17.5°	1948.5	1934.8	1921.0	1942.3	1998.5	2073.1	2202.5	2332.0	2202.5	2073.1	1998.5
20°	1932.8	1910.3	1884.5	1896.4	1945.7	2014.7	2142.4	2270.2	2142.4	2014.7	1945.7
22.5°	1906.2	1883.3	1854.9	1859.9	1898.1	1959.1	2088.5	2218.0	2088.5	1959.1	1898.1
25°	1851.5	1833.8	1809.1	1802.2	1812.9	1857.4	2003.4	2149.4	2003.4	1857.4	1812.9
27.5°	1787.1	1775.4	1760.4	1746.5	1733.8	1762.5	1914.9	2067.3	1914.9	1762.5	1733.8
30°	1749.6	1734.8	1719.8	1702.1	1681.7	1704.5	1856.9	2009.3	1856.9	1704.5	1681.7
32.5°	1756.0	1721.3	1685.7	1652.5	1621.8	1638.2	1795.7	1953.3	1795.7	1638.2	1621.8
35°	1760.3	1689.7	1630.7	1582.4	1544.8	1557.7	1721.9	1886.2	1721.9	1557.7	1544.8
37.5°	1656.9	1610.4	1559.5	1508.6	1457.7	1463.6	1639.6	1815.6	1639.6	1463.6	1457.7
40°	1615.7	1585.9	1520.4	1457.1	1395.9	1396.2	1580.8	1765.4	1580.8	1396.2	1395.9
42.5°	1577.2	1546.0	1460.7	1391.0	1336.7	1342.1	1526.7	1711.3	1526.7	1342.1	1336.7
45°	1348.4	1354.8	1332.3	1293.7	1238.9	1245.9	1438.0	1630.2	1438.0	1245.9	1238.9
47.5°	1132.7	1179.7	1230.1	1225.8	1166.8	1168.3	1351.4	1534.5	1351.4	1168.3	1166.8
50°	1037.4	1103.7	1184.2	1190.6	1123.0	1115.5	1288.3	1461.1	1288.3	1115.5	1123.0
52.5°	958.2	1042.5	1149.6	1162.5	1081.1	1061.2	1225.4	1389.6	1225.4	1061.2	1081.1
55°	854.1	965.2	1112.3	1129.4	1016.7	971.7	1129.4	1287.2	1129.4	971.7	1016.7
57.5°	763.1	857.3	984.9	1002.9	911.4	880.2	1029.4	1178.5	1029.4	880.2	911.4
60°	706.0	773.6	861.6	878.8	825.1	821.1	966.0	1110.9	966.0	821.1	825.1
62.5°	636.4	682.8	742.5	762.7	743.4	763.4	901.4	1039.4	901.4	763.4	743.4
65°	509.6	546.6	596.0	625.0	633.5	671.4	797.0	922.6	797.0	671.4	633.5
67.5°	411.8	446.5	484.0	512.8	532.8	575.1	684.6	794.1	684.6	575.1	532.8
70°	329.0	364.7	406.5	440.9	467.7	512.0	608.6	705.2	608.6	512.0	467.7
72.5°	268.4	299.0	333.1	366.6	399.5	444.8	527.7	610.5	527.7	444.8	399.5
75°	173.3	197.2	228.4	262.2	298.7	342.7	409.2	475.8	409.2	342.7	298.7
77.5°	129.0	140.7	156.4	179.9	211.2	246.9	295.4	343.9	295.4	246.9	211.2
80°	104.1	104.7	105.7	122.4	154.6	187.8	224.3	260.8	224.3	187.8	154.6
82.5°	82.6	81.5	80.0	88.9	108.2	129.4	156.5	183.5	156.5	129.4	108.2
85°	38.4	41.9	46.2	49.4	51.5	56.4	69.2	82.1	69.2	56.4	51.5
87.5°	15.3	15.0	15.0	16.0	17.8	18.9	18.4	18.2	18.4	18.6	18.3
90°	28.1	26.8	26.8	25.4	21.4	16.1	9.4	4.0	9.4	14.7	24.1
92.5°	33.4	33.2	31.0	28.6	23.5	23.5	23.3	14.7	25.4	36.1	51.9
95°	30.8	30.8	36.1	45.5	66.9	68.2	45.5	41.5	58.9	82.9	104.3
97.5°	83.2	99.0	121.4	125.7	119.0	88.8	85.1	79.2	107.8	131.6	166.1
100°	153.8	173.9	189.9	157.8	124.4	123.1	115.0	112.4	143.1	165.9	199.3
102.5°	240.5	246.6	191.0	172.8	165.1	159.4	147.1	145.5	176.3	207.6	235.7
105°	260.8	234.1	235.4	235.4	230.1	219.4	196.6	195.3	230.1	266.2	300.9
107.5°	306.8	310.8	317.8	316.2	310.0	281.4	254.7	248.5	279.8	323.2	361.4
110°	367.8	371.8	374.5	371.8	362.5	326.4	294.3	284.9	313.0	358.5	399.9



TEST NUMBER: P1427937

CATALOG NUMBER: SQ2W-PH1-K-100U-125D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	426.7	429.6	435.5	427.5	411.7	370.2	333.9	320.2	348.3	394.8	437.4
115°	520.3	520.3	521.6	517.6	485.5	442.7	394.6	374.5	398.6	441.4	488.2
117.5°	612.3	613.9	608.6	597.9	560.7	510.9	456.9	424.8	443.8	489.0	537.2
120°	670.1	672.8	667.4	651.4	615.3	559.1	497.6	460.1	474.8	519.0	567.1
122.5°	730.0	729.5	723.1	704.9	662.4	604.0	543.6	497.6	503.7	544.6	591.7
125°	813.2	811.9	806.5	785.1	741.0	680.8	609.9	553.7	545.7	580.5	628.6
127.5°	892.4	889.5	881.2	855.2	810.0	752.0	674.1	610.5	592.5	614.5	658.6
130°	947.0	943.0	928.3	900.2	856.0	801.2	722.3	650.0	624.6	638.0	676.8
132.5°	999.4	987.9	975.3	945.1	904.2	847.2	767.2	691.8	656.7	662.6	692.8
135°	1066.0	1055.3	1039.3	1009.8	971.1	914.9	834.6	753.0	704.9	699.5	716.9
137.5°	1124.6	1113.4	1095.2	1069.8	1030.7	980.7	903.6	817.5	756.8	738.9	745.5
140°	1161.0	1147.6	1131.6	1106.1	1071.4	1019.2	944.3	861.4	793.2	767.8	763.7
142.5°	1190.9	1180.8	1163.7	1140.4	1109.9	1057.7	985.0	903.1	830.6	797.7	788.3
145°	1235.9	1227.9	1209.1	1187.7	1162.3	1110.2	1043.3	961.7	889.5	846.7	826.6
147.5°	1273.9	1267.5	1252.7	1227.6	1206.2	1156.2	1095.2	1023.0	948.9	895.9	869.9
150°	1297.4	1292.1	1277.4	1253.3	1231.9	1185.1	1126.2	1059.3	988.4	932.3	898.8
152.5°	1319.9	1314.5	1297.7	1273.6	1255.4	1211.8	1158.3	1094.6	1022.7	966.5	932.0
155°	1349.6	1342.9	1326.8	1304.1	1288.1	1247.9	1198.4	1142.3	1080.7	1021.9	983.1
157.5°	1373.1	1364.8	1349.9	1330.3	1313.2	1276.3	1233.2	1184.8	1131.0	1074.9	1035.3
160°	1387.0	1377.7	1361.6	1344.2	1328.2	1293.4	1254.6	1210.5	1161.0	1110.2	1067.4
162.5°	1396.7	1388.4	1369.1	1353.9	1340.0	1308.4	1271.7	1231.9	1187.7	1143.3	1103.7
165°	1407.1	1397.7	1377.7	1365.6	1353.6	1326.8	1294.7	1262.6	1225.2	1189.1	1157.0
167.5°	1407.9	1400.1	1380.1	1368.3	1359.5	1336.5	1310.5	1285.9	1256.8	1228.4	1201.7
170°	1405.8	1399.1	1379.0	1368.3	1361.6	1342.9	1320.2	1298.8	1276.0	1251.9	1230.5
172.5°	1398.3	1391.6	1372.6	1364.0	1360.6	1344.0	1325.5	1309.5	1289.9	1272.3	1255.2
175°	1379.0	1373.7	1357.6	1352.3	1353.6	1342.9	1329.5	1320.2	1308.1	1297.4	1288.1
177.5°	1350.9	1347.7	1335.9	1335.9	1340.2	1333.8	1329.5	1325.2	1319.9	1316.7	1313.5
180°	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2



TEST NUMBER: P1427937

CATALOG NUMBER: SQ2W-PH1-K-100U-125D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2538.2	2538.2	2538.2	2538.2	2538.2	2538.2	2538.2	2538.2	2538.2	2538.2	2538.2
2.5°	2512.9	2494.4	2484.1	2476.0	2474.3	2472.5	2474.3	2476.0	2484.1	2494.4	2512.9
5°	2424.2	2374.3	2341.0	2315.5	2313.4	2311.2	2313.4	2315.5	2341.0	2374.3	2424.2
7.5°	2283.9	2226.2	2189.5	2161.5	2159.8	2158.1	2159.8	2161.5	2189.5	2226.2	2283.9
10°	2194.2	2135.2	2101.9	2076.9	2076.9	2076.9	2076.9	2076.9	2101.9	2135.2	2194.2
12.5°	2118.9	2064.1	2039.4	2022.2	2027.4	2032.5	2027.4	2022.2	2039.4	2064.1	2118.9
15°	2021.7	1982.0	1975.5	1973.6	1985.4	1997.3	1985.4	1973.6	1975.5	1982.0	2021.7
17.5°	1942.3	1921.0	1934.8	1948.5	1962.3	1976.0	1962.3	1948.5	1934.8	1921.0	1942.3
20°	1896.4	1884.5	1910.3	1932.8	1945.7	1958.6	1945.7	1932.8	1910.3	1884.5	1896.4
22.5°	1859.9	1854.9	1883.3	1906.2	1913.1	1920.0	1913.1	1906.2	1883.3	1854.9	1859.9
25°	1802.2	1809.1	1833.8	1851.5	1848.3	1845.1	1848.3	1851.5	1833.8	1809.1	1802.2
27.5°	1746.5	1760.4	1775.4	1787.1	1789.1	1791.0	1789.1	1787.1	1775.4	1760.4	1746.5
30°	1702.1	1719.8	1734.8	1749.6	1763.5	1777.5	1763.5	1749.6	1734.8	1719.8	1702.1
32.5°	1652.5	1685.7	1721.3	1756.0	1788.0	1820.0	1788.0	1756.0	1721.3	1685.7	1652.5
35°	1582.4	1630.7	1689.7	1760.3	1865.5	1970.7	1865.5	1760.3	1689.7	1630.7	1582.4
37.5°	1508.6	1559.5	1610.4	1656.9	1690.4	1723.9	1690.4	1656.9	1610.4	1559.5	1508.6
40°	1457.1	1520.4	1585.9	1615.7	1538.4	1461.1	1538.4	1615.7	1585.9	1520.4	1457.1
42.5°	1391.0	1460.7	1546.0	1577.2	1446.7	1316.2	1446.7	1577.2	1546.0	1460.7	1391.0
45°	1293.7	1332.3	1354.8	1348.4	1255.0	1161.6	1255.0	1348.4	1354.8	1332.3	1293.7
47.5°	1225.8	1230.1	1179.7	1132.7	1096.2	1059.7	1096.2	1132.7	1179.7	1230.1	1225.8
50°	1190.6	1184.2	1103.7	1037.4	1013.8	990.2	1013.8	1037.4	1103.7	1184.2	1190.6
52.5°	1162.5	1149.6	1042.5	958.2	942.3	926.4	942.3	958.2	1042.5	1149.6	1162.5
55°	1129.4	1112.3	965.2	854.1	850.9	847.7	850.9	854.1	965.2	1112.3	1129.4
57.5°	1002.9	984.9	857.3	763.1	768.7	774.3	768.7	763.1	857.3	984.9	1002.9
60°	878.8	861.6	773.6	706.0	699.6	693.1	699.6	706.0	773.6	861.6	878.8
62.5°	762.7	742.5	682.8	636.4	630.0	623.6	630.0	636.4	682.8	742.5	762.7
65°	625.0	596.0	546.6	509.6	509.6	509.6	509.6	509.6	546.6	596.0	625.0
67.5°	512.8	484.0	446.5	411.8	386.1	360.3	386.1	411.8	446.5	484.0	512.8
70°	440.9	406.5	364.7	329.0	311.8	294.6	311.8	329.0	364.7	406.5	440.9
72.5°	366.6	333.1	299.0	268.4	248.7	228.9	248.7	268.4	299.0	333.1	366.6
75°	262.2	228.4	197.2	173.3	171.2	169.1	171.2	173.3	197.2	228.4	262.2
77.5°	179.9	156.4	140.7	129.0	129.2	129.4	129.2	129.0	140.7	156.4	179.9
80°	122.4	105.7	104.7	104.1	105.2	106.3	105.2	104.1	104.7	105.7	122.4
82.5°	88.9	80.0	81.5	82.6	82.9	83.1	82.9	82.6	81.5	80.0	88.9
85°	49.4	46.2	41.9	38.4	37.3	36.2	37.3	38.4	41.9	46.2	49.4
87.5°	17.1	17.7	19.6	20.6	21.7	21.2	21.7	20.6	19.6	17.7	17.1
90°	30.8	40.1	49.5	54.8	60.2	57.5	60.2	54.8	49.5	40.1	30.8
92.5°	61.8	77.6	89.1	98.7	103.0	102.5	103.0	98.7	89.1	77.6	61.8
95°	124.4	143.1	161.8	175.2	183.2	180.6	183.2	175.2	161.8	143.1	124.4
97.5°	191.8	216.9	237.8	250.4	258.4	263.8	258.4	250.4	237.8	216.9	191.8
100°	236.7	260.8	284.9	299.6	313.0	318.3	313.0	299.6	284.9	260.8	236.7
102.5°	273.1	304.7	330.9	346.7	357.9	363.3	357.9	346.7	330.9	304.7	273.1
105°	333.0	366.5	394.6	414.6	426.7	430.7	426.7	414.6	394.6	366.5	333.0
107.5°	393.0	427.5	453.4	475.6	490.3	498.9	490.3	475.6	453.4	427.5	393.0
110°	440.1	468.1	496.2	516.3	531.0	536.4	531.0	516.3	496.2	468.1	440.1



TEST NUMBER: P1427937

CATALOG NUMBER: SQ2W-PH1-K-100U-125D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	479.6	510.9	539.0	559.1	575.9	583.4	575.9	559.1	539.0	510.9	479.6
115°	535.0	576.5	601.9	620.6	632.7	639.3	632.7	620.6	601.9	576.5	535.0
117.5°	581.0	624.4	652.2	666.6	672.3	677.1	672.3	666.6	652.2	624.4	581.0
120°	609.9	650.0	682.1	700.9	707.6	710.2	707.6	700.9	682.1	650.0	609.9
122.5°	636.7	674.7	705.7	728.7	739.7	742.3	739.7	728.7	705.7	674.7	636.7
125°	674.1	710.2	742.3	765.1	777.1	783.8	777.1	765.1	742.3	710.2	674.1
127.5°	706.8	745.8	775.2	795.8	807.6	813.0	807.6	795.8	775.2	745.8	706.8
130°	724.9	765.1	794.5	817.2	827.9	833.3	827.9	817.2	794.5	765.1	724.9
132.5°	738.9	781.1	811.6	832.2	844.0	849.3	844.0	832.2	811.6	781.1	738.9
135°	755.7	799.9	832.0	852.0	862.7	868.1	862.7	852.0	832.0	799.9	755.7
137.5°	770.4	810.6	844.0	865.1	874.8	878.2	874.8	865.1	844.0	810.6	770.4
140°	781.1	815.9	849.3	869.4	880.1	881.4	880.1	869.4	849.3	815.9	781.1
142.5°	795.0	822.3	851.5	871.5	882.2	884.7	882.2	871.5	851.5	822.3	795.0
145°	819.9	836.0	856.0	874.8	884.1	886.8	884.1	874.8	856.0	836.0	819.9
147.5°	851.2	856.3	866.7	879.0	888.1	890.0	888.1	879.0	866.7	856.3	851.2
150°	874.8	873.4	877.4	885.5	893.5	892.1	893.5	885.5	877.4	873.4	874.8
152.5°	901.5	893.7	893.5	897.2	901.0	900.7	901.0	897.2	893.5	893.7	901.5
155°	947.0	932.3	924.2	921.6	921.6	920.2	921.6	921.6	924.2	932.3	947.0
157.5°	997.0	976.4	964.4	957.9	956.1	953.1	956.1	957.9	964.4	976.4	997.0
160°	1031.2	1008.5	996.5	985.8	981.8	977.7	981.8	985.8	996.5	1008.5	1031.2
162.5°	1063.3	1041.7	1028.6	1018.9	1014.9	1008.8	1014.9	1018.9	1028.6	1041.7	1063.3
165°	1115.5	1092.8	1078.1	1070.0	1064.7	1059.3	1064.7	1070.0	1078.1	1092.8	1115.5
167.5°	1167.7	1142.8	1133.2	1124.1	1119.0	1109.4	1119.0	1124.1	1133.2	1142.8	1167.7
170°	1199.8	1177.0	1171.7	1163.7	1154.3	1143.6	1154.3	1163.7	1171.7	1177.0	1199.8
172.5°	1227.6	1212.4	1207.0	1199.0	1196.0	1187.5	1196.0	1199.0	1207.0	1212.4	1227.6
175°	1268.0	1256.0	1256.0	1254.6	1250.6	1242.6	1250.6	1254.6	1256.0	1256.0	1268.0
177.5°	1301.7	1295.3	1299.6	1299.6	1298.5	1291.0	1298.5	1299.6	1299.6	1295.3	1301.7
180°	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2



TEST NUMBER: P1427937

CATALOG NUMBER: SQ2W-PH1-K-100U-125D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	2538.2	2538.2	2538.2	2538.2
2.5°	2539.5	2556.5	2544.4	2532.4
5°	2490.7	2540.9	2542.0	2543.1
7.5°	2362.7	2430.1	2463.4	2496.7
10°	2279.0	2355.2	2405.7	2456.1
12.5°	2203.7	2287.2	2366.8	2446.5
15°	2094.7	2179.5	2299.7	2419.9
17.5°	1998.5	2073.1	2202.5	2332.0
20°	1945.7	2014.7	2142.4	2270.2
22.5°	1898.1	1959.1	2088.5	2218.0
25°	1812.9	1857.4	2003.4	2149.4
27.5°	1733.8	1762.5	1914.9	2067.3
30°	1681.7	1704.5	1856.9	2009.3
32.5°	1621.8	1638.2	1795.7	1953.3
35°	1544.8	1557.7	1721.9	1886.2
37.5°	1457.7	1463.6	1639.6	1815.6
40°	1395.9	1396.2	1580.8	1765.4
42.5°	1336.7	1342.1	1526.7	1711.3
45°	1238.9	1245.9	1438.0	1630.2
47.5°	1166.8	1168.3	1351.4	1534.5
50°	1123.0	1115.5	1288.3	1461.1
52.5°	1081.1	1061.2	1225.4	1389.6
55°	1016.7	971.7	1129.4	1287.2
57.5°	911.4	880.2	1029.4	1178.5
60°	825.1	821.1	966.0	1110.9
62.5°	743.4	763.4	901.4	1039.4
65°	633.5	671.4	797.0	922.6
67.5°	532.8	575.1	684.6	794.1
70°	467.7	512.0	608.6	705.2
72.5°	399.5	444.8	527.7	610.5
75°	298.7	342.7	409.2	475.8
77.5°	211.2	246.9	295.4	343.9
80°	154.6	187.8	224.3	260.8
82.5°	108.2	129.4	156.5	183.5
85°	51.5	56.4	69.2	82.1
87.5°	18.3	18.6	18.4	18.2
90°	24.1	14.7	9.4	4.0
92.5°	51.9	36.1	25.4	14.7
95°	104.3	82.9	58.9	41.5
97.5°	166.1	131.6	107.8	79.2
100°	199.3	165.9	143.1	112.4
102.5°	235.7	207.6	176.3	145.5
105°	300.9	266.2	230.1	195.3
107.5°	361.4	323.2	279.8	248.5
110°	399.9	358.5	313.0	284.9



TEST NUMBER: P1427937

CATALOG NUMBER: SQ2W-PH1-K-100U-125D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	437.4	394.8	348.3	320.2
115°	488.2	441.4	398.6	374.5
117.5°	537.2	489.0	443.8	424.8
120°	567.1	519.0	474.8	460.1
122.5°	591.7	544.6	503.7	497.6
125°	628.6	580.5	545.7	553.7
127.5°	658.6	614.5	592.5	610.5
130°	676.8	638.0	624.6	650.0
132.5°	692.8	662.6	656.7	691.8
135°	716.9	699.5	704.9	753.0
137.5°	745.5	738.9	756.8	817.5
140°	763.7	767.8	793.2	861.4
142.5°	788.3	797.7	830.6	903.1
145°	826.6	846.7	889.5	961.7
147.5°	869.9	895.9	948.9	1023.0
150°	898.8	932.3	988.4	1059.3
152.5°	932.0	966.5	1022.7	1094.6
155°	983.1	1021.9	1080.7	1142.3
157.5°	1035.3	1074.9	1131.0	1184.8
160°	1067.4	1110.2	1161.0	1210.5
162.5°	1103.7	1143.3	1187.7	1231.9
165°	1157.0	1189.1	1225.2	1262.6
167.5°	1201.7	1228.4	1256.8	1285.9
170°	1230.5	1251.9	1276.0	1298.8
172.5°	1255.2	1272.3	1289.9	1309.5
175°	1288.1	1297.4	1308.1	1320.2
177.5°	1313.5	1316.7	1319.9	1325.2
180°	1324.2	1324.2	1324.2	1324.2



TEST NUMBER: P1427937

CATALOG NUMBER: SQ2W-PH1-K-100U-125D-L935-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.59	21.53	21.47	22.43	23.56	19.42	20.36	20.29	21.26	22.39
	3H	22.77	23.61	23.66	24.52	25.68	20.47	21.32	21.36	22.22	23.38
	4H	23.59	24.39	24.49	25.30	26.46	20.72	21.52	21.63	22.43	23.60
	6H	24.06	24.79	24.97	25.71	26.89	20.87	21.60	21.78	22.52	23.70
	8H	24.21	24.91	25.14	25.85	27.03	20.93	21.63	21.85	22.56	23.74
	12H	24.28	24.94	25.20	25.87	27.08	20.94	21.61	21.87	22.54	23.74
4H	2H	21.04	21.83	21.94	22.74	23.91	20.11	20.91	21.02	21.82	22.99
	3H	23.30	23.96	24.21	24.90	26.08	21.35	22.01	22.27	22.95	24.14
	4H	24.17	24.78	25.10	25.71	26.92	21.65	22.25	22.58	23.19	24.40
	6H	24.74	25.26	25.68	26.22	27.43	21.85	22.37	22.79	23.33	24.54
	8H	24.94	25.43	25.89	26.38	27.60	21.94	22.43	22.89	23.38	24.60
	12H	25.03	25.46	25.99	26.44	27.67	21.97	22.40	22.93	23.38	24.61
8H	4H	24.20	24.69	25.15	25.64	26.86	21.88	22.37	22.83	23.32	24.54
	6H	24.83	25.23	25.81	26.23	27.45	22.15	22.55	23.12	23.55	24.77
	8H	25.10	25.45	26.08	26.44	27.68	22.30	22.65	23.28	23.64	24.88
	12H	25.23	25.54	26.22	26.52	27.81	22.37	22.68	23.35	23.66	24.95
12H	4H	24.16	24.59	25.12	25.57	26.80	21.88	22.32	22.85	23.29	24.52
	6H	24.81	25.16	25.79	26.15	27.39	22.19	22.54	23.17	23.53	24.77
	8H	25.09	25.40	26.07	26.38	27.66	22.35	22.67	23.34	23.64	24.93