

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428267

Luminaire Tested: SQ2W-PR1-K-100U-100D-L935-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428267
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-9)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PR1-K-100U-100D-L935-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE RIPPLE LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8449.4 lumens
Efficiency: N/A
Efficacy: 119.5 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.34 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 70.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428267

CATALOG NUMBER: SQ2W-PR1-K-100U-100D-L935-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428267

CATALOG NUMBER: SQ2W-PR1-K-100U-100D-L935-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54	54	54	54	
1	99	95	92	88	92	89	86	83	76	74	72	65	63	62	54	53	52	47	47	47	47	
2	91	84	78	73	84	78	73	69	68	64	60	58	55	52	48	47	45	40	40	40	40	
3	83	74	67	62	77	69	63	58	60	55	52	51	48	45	43	41	39	35	35	35	35	
4	77	66	59	53	71	62	55	50	54	49	44	46	42	39	39	36	34	31	31	31	31	
5	71	59	51	46	65	56	49	43	48	43	39	42	38	34	36	32	30	27	27	27	27	
6	65	53	45	40	60	50	43	38	44	38	34	38	34	30	32	29	27	24	24	24	24	
7	60	48	41	35	56	45	38	33	40	34	30	35	30	27	30	26	24	21	21	21	21	
8	56	44	36	31	52	41	35	30	36	31	27	32	27	24	27	24	21	19	19	19	19	
9	52	40	33	28	49	38	31	27	33	28	24	29	25	22	25	22	19	17	17	17	17	
10	49	37	30	25	45	35	28	24	31	26	22	27	23	20	23	20	18	16	16	16	16	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30720	30720	30720	30720
5°	30680	31246	30680	31246
10°	31004	32276	31004	32276
15°	30993	31414	30993	31414
20°	30492	31992	30492	31992
25°	30406	33308	30406	33308
30°	30374	33629	30374	33629
35°	30085	31309	30085	31309
40°	29391	27553	29391	27553
45°	27811	21790	27811	21790
50°	25284	16904	25284	16904
55°	22221	13157	22221	13157
60°	19226	10834	19226	10834
65°	16599	9486	16599	9486
70°	14922	8422	14922	8422
75°	13674	7742	13674	7742
80°	11901	7578	11901	7578
85°	8614	3594	8614	3594

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 29859 cd/sqm



TEST NUMBER: P1428267

CATALOG NUMBER: SQ2W-PR1-K-100U-100D-L935-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.8	2.2
10°-20°	531.9	6.3
20°-30°	822.3	9.7
30°-40°	988.9	11.7
40°-50°	888.0	10.5
50°-60°	595.0	7.0
60°-70°	346.1	4.1
70°-80°	177.8	2.1
80°-90°	49.3	0.6
90°-100°	105.4	1.2
100°-110°	307.3	3.6
110°-120°	501.5	5.9
120°-130°	636.4	7.5
130°-140°	681.0	8.1
140°-150°	635.9	7.5
150°-160°	523.2	6.2
160°-170°	350.9	4.2
170°-180°	124.6	1.5
0°-30°	1538.0	18.2
0°-40°	2526.8	29.9
0°-60°	4009.8	47.5
0°-90°	4583.1	54.2
90°-120°	914.2	10.8
90°-150°	2867.5	33.9
90°-180°	3866.0	45.8
0°-180°	8449.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1903	1903	1903	1903	1903	
5°	1893	1928	1893	1928	1893	181
15°	1854	1879	1854	1879	1854	521
25°	1707	1870	1707	1870	1707	787
35°	1526	1588	1526	1588	1526	952
45°	1218	954	1218	954	1218	932
55°	789	467	789	467	789	709
65°	434	248	434	248	434	439
75°	219	124	219	124	219	233
85°	46	19	46	19	46	58
90°	4	29	4	58	4	5
95°	42	31	42	181	42	50
105°	195	313	195	431	195	208
115°	374	519	374	639	374	369
125°	554	823	554	784	554	495
135°	753	1077	753	868	753	582
145°	962	1241	962	887	962	602
155°	1142	1348	1142	920	1142	525
165°	1263	1406	1263	1059	1263	355
175°	1320	1376	1320	1243	1320	125
180°	1324	1324	1324	1324	1324	



TEST NUMBER: P1428267

CATALOG NUMBER: SQ2W-PR1-K-100U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7
2.5°	1895.0	1905.3	1915.6	1911.0	1901.3	1896.9	1897.5	1898.6	1900.6	1902.7	1900.6
5°	1893.0	1907.7	1922.3	1918.9	1909.4	1905.5	1907.2	1910.7	1919.3	1927.9	1919.3
7.5°	1892.6	1913.5	1934.4	1935.9	1931.1	1931.2	1936.2	1942.8	1954.2	1965.6	1954.2
10°	1891.1	1916.1	1941.1	1944.7	1941.3	1940.0	1940.9	1944.5	1956.6	1968.7	1956.6
12.5°	1881.8	1910.9	1940.0	1937.0	1923.2	1915.7	1914.5	1915.2	1921.8	1928.3	1921.8
15°	1854.2	1888.7	1923.2	1909.2	1879.0	1865.2	1867.8	1870.8	1875.1	1879.4	1875.1
17.5°	1805.7	1841.8	1877.8	1865.2	1836.4	1826.7	1836.0	1845.1	1853.5	1862.0	1853.5
20°	1774.7	1810.0	1845.4	1836.8	1813.5	1807.9	1820.0	1832.7	1847.3	1862.0	1847.3
22.5°	1746.8	1782.1	1817.5	1811.9	1792.8	1791.7	1808.6	1826.3	1846.5	1866.6	1846.5
25°	1706.8	1737.9	1768.9	1769.5	1760.0	1769.5	1798.0	1824.9	1847.3	1869.7	1847.3
27.5°	1664.9	1683.2	1701.5	1713.5	1723.5	1747.8	1786.2	1819.0	1834.7	1850.3	1834.7
30°	1629.2	1641.3	1653.4	1675.8	1701.6	1731.4	1765.0	1791.7	1797.8	1803.8	1797.8
32.5°	1590.4	1597.7	1604.9	1636.5	1676.1	1704.8	1722.6	1734.0	1726.2	1718.5	1726.2
35°	1526.4	1532.5	1538.5	1578.8	1630.5	1649.5	1635.7	1621.3	1604.9	1588.5	1604.9
37.5°	1450.4	1462.8	1475.2	1508.1	1547.7	1547.4	1507.0	1472.1	1453.3	1434.5	1453.3
40°	1394.5	1415.2	1435.9	1457.9	1480.3	1461.4	1401.0	1350.4	1328.8	1307.3	1328.8
42.5°	1326.3	1359.4	1392.5	1397.4	1392.9	1352.2	1275.3	1211.1	1184.7	1158.3	1184.7
45°	1218.0	1262.9	1307.7	1282.1	1232.9	1166.5	1082.9	1012.9	983.6	954.3	983.6
47.5°	1090.4	1136.5	1182.5	1134.1	1054.3	977.1	902.4	839.6	812.2	784.7	812.2
50°	1006.6	1043.7	1080.8	1026.0	940.7	863.1	793.3	733.4	703.2	673.0	703.2
52.5°	921.3	948.0	974.7	920.5	839.3	763.8	694.0	634.8	607.3	579.9	607.3
55°	789.4	803.2	817.0	766.8	695.2	626.3	559.9	505.4	486.4	467.4	486.4
57.5°	668.4	677.2	686.0	638.4	572.0	510.6	454.2	408.5	394.5	380.5	394.5
60°	595.4	601.5	607.5	559.2	492.9	437.7	393.7	358.0	346.8	335.5	346.8
62.5°	528.7	533.4	538.0	491.5	427.9	378.6	343.6	315.2	306.8	298.3	306.8
65°	434.5	438.8	443.1	403.4	349.1	308.6	281.9	260.3	254.3	248.3	254.3
67.5°	359.6	361.8	364.1	331.4	287.1	254.4	233.4	216.2	210.5	204.8	210.5
70°	316.1	317.0	317.9	289.0	250.2	221.3	202.4	187.1	182.8	178.4	182.8
72.5°	277.4	276.2	274.9	249.2	215.2	190.5	174.9	162.6	159.6	156.7	159.6
75°	219.2	216.6	214.0	192.7	165.1	146.1	135.8	127.6	125.9	124.1	125.9
77.5°	163.7	160.9	158.2	140.4	117.7	104.6	101.1	98.5	98.5	98.5	98.5
80°	128.0	124.6	121.1	107.3	90.1	81.5	81.5	81.5	81.5	81.5	81.5
82.5°	95.4	90.6	85.8	77.3	67.7	62.8	62.8	62.7	62.0	61.3	62.0
85°	46.5	42.2	37.9	36.9	36.9	34.3	29.1	24.6	22.0	19.4	22.0
87.5°	13.2	14.3	15.6	14.1	11.5	10.0	10.0	10.3	10.5	10.5	10.5
90°	4.0	9.4	16.1	21.4	25.4	26.8	26.8	28.1	29.4	29.4	29.4
92.5°	14.7	23.3	23.5	23.5	28.6	31.0	33.2	33.4	34.8	34.8	34.8
95°	41.5	45.5	68.2	66.9	45.5	36.1	30.8	30.8	30.8	30.8	30.8
97.5°	79.2	85.1	88.8	119.0	125.7	121.4	99.0	83.2	74.4	70.4	74.4
100°	112.4	115.0	123.1	124.4	157.8	189.9	173.9	153.8	147.1	143.1	147.1
102.5°	145.5	147.1	159.4	165.1	172.8	191.0	246.6	240.5	235.9	235.1	235.9
105°	195.3	196.6	219.4	230.1	235.4	235.4	234.1	260.8	303.6	313.0	303.6
107.5°	248.5	254.7	281.4	310.0	316.2	317.8	310.8	306.8	305.2	306.3	305.2
110°	284.9	294.3	326.4	362.5	371.8	374.5	371.8	367.8	365.1	365.1	365.1

TEST NUMBER: P1428267

CATALOG NUMBER: SQ2W-PR1-K-100U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	320.2	333.9	370.2	411.7	427.5	435.5	429.6	426.7	424.0	426.1	424.0
115°	374.5	394.6	442.7	485.5	517.6	521.6	520.3	520.3	519.0	519.0	519.0
117.5°	424.8	456.9	510.9	560.7	597.9	608.6	613.9	612.3	610.7	613.4	610.7
120°	460.1	497.6	559.1	615.3	651.4	667.4	672.8	670.1	672.8	670.1	672.8
122.5°	497.6	543.6	604.0	662.4	704.9	723.1	729.5	730.0	730.6	729.0	730.6
125°	553.7	609.9	680.8	741.0	785.1	806.5	811.9	813.2	815.9	822.6	815.9
127.5°	610.5	674.1	752.0	810.0	855.2	881.2	889.5	892.4	898.0	901.0	898.0
130°	650.0	722.3	801.2	856.0	900.2	928.3	943.0	947.0	953.7	952.3	953.7
132.5°	691.8	767.2	847.2	904.2	945.1	975.3	987.9	999.4	1001.8	1003.7	1001.8
135°	753.0	834.6	914.9	971.1	1009.8	1039.3	1055.3	1066.0	1072.7	1076.7	1072.7
137.5°	817.5	903.6	980.7	1030.7	1069.8	1095.2	1113.4	1124.6	1131.6	1134.8	1131.6
140°	861.4	944.3	1019.2	1071.4	1106.1	1131.6	1147.6	1161.0	1169.0	1169.0	1169.0
142.5°	903.1	985.0	1057.7	1109.9	1140.4	1163.7	1180.8	1190.9	1200.0	1200.0	1200.0
145°	961.7	1043.3	1110.2	1162.3	1187.7	1209.1	1227.9	1235.9	1241.2	1241.2	1241.2
147.5°	1023.0	1095.2	1156.2	1206.2	1227.6	1252.7	1267.5	1273.9	1280.6	1277.6	1280.6
150°	1059.3	1126.2	1185.1	1231.9	1253.3	1277.4	1292.1	1297.4	1304.1	1300.1	1304.1
152.5°	1094.6	1158.3	1211.8	1255.4	1273.6	1297.7	1314.5	1319.9	1324.4	1321.5	1324.4
155°	1142.3	1198.4	1247.9	1288.1	1304.1	1326.8	1342.9	1349.6	1354.9	1348.2	1354.9
157.5°	1184.8	1233.2	1276.3	1313.2	1330.3	1349.9	1364.8	1373.1	1378.5	1375.5	1378.5
160°	1210.5	1254.6	1293.4	1328.2	1344.2	1361.6	1377.7	1387.0	1392.4	1388.4	1392.4
162.5°	1231.9	1271.7	1308.4	1340.0	1353.9	1369.1	1388.4	1396.7	1402.0	1396.9	1402.0
165°	1262.6	1294.7	1326.8	1353.6	1365.6	1377.7	1397.7	1407.1	1411.1	1405.8	1411.1
167.5°	1285.9	1310.5	1336.5	1359.5	1368.3	1380.1	1400.1	1407.9	1413.0	1406.3	1413.0
170°	1298.8	1320.2	1342.9	1361.6	1368.3	1379.0	1399.1	1405.8	1409.8	1403.1	1409.8
172.5°	1309.5	1325.5	1344.0	1360.6	1364.0	1372.6	1391.6	1398.3	1401.2	1395.6	1401.2
175°	1320.2	1329.5	1342.9	1353.6	1352.3	1357.6	1373.7	1379.0	1384.4	1376.3	1384.4
177.5°	1325.2	1329.5	1333.8	1340.2	1335.9	1335.9	1347.7	1350.9	1352.0	1347.7	1352.0
180°	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2



TEST NUMBER: P1428267

CATALOG NUMBER: SQ2W-PR1-K-100U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7
2.5°	1898.6	1897.5	1896.9	1901.3	1911.0	1915.6	1905.3	1895.0	1905.3	1915.6	1911.0
5°	1910.7	1907.2	1905.5	1909.4	1918.9	1922.3	1907.7	1893.0	1907.7	1922.3	1918.9
7.5°	1942.8	1936.2	1931.2	1931.1	1935.9	1934.4	1913.5	1892.6	1913.5	1934.4	1935.9
10°	1944.5	1940.9	1940.0	1941.3	1944.7	1941.1	1916.1	1891.1	1916.1	1941.1	1944.7
12.5°	1915.2	1914.5	1915.7	1923.2	1937.0	1940.0	1910.9	1881.8	1910.9	1940.0	1937.0
15°	1870.8	1867.8	1865.2	1879.0	1909.2	1923.2	1888.7	1854.2	1888.7	1923.2	1909.2
17.5°	1845.1	1836.0	1826.7	1836.4	1865.2	1877.8	1841.8	1805.7	1841.8	1877.8	1865.2
20°	1832.7	1820.0	1807.9	1813.5	1836.8	1845.4	1810.0	1774.7	1810.0	1845.4	1836.8
22.5°	1826.3	1808.6	1791.7	1792.8	1811.9	1817.5	1782.1	1746.8	1782.1	1817.5	1811.9
25°	1824.9	1798.0	1769.5	1760.0	1769.5	1768.9	1737.9	1706.8	1737.9	1768.9	1769.5
27.5°	1819.0	1786.2	1747.8	1723.5	1713.5	1701.5	1683.2	1664.9	1683.2	1701.5	1713.5
30°	1791.7	1765.0	1731.4	1701.6	1675.8	1653.4	1641.3	1629.2	1641.3	1653.4	1675.8
32.5°	1734.0	1722.6	1704.8	1676.1	1636.5	1604.9	1597.7	1590.4	1597.7	1604.9	1636.5
35°	1621.3	1635.7	1649.5	1630.5	1578.8	1538.5	1532.5	1526.4	1532.5	1538.5	1578.8
37.5°	1472.1	1507.0	1547.4	1547.7	1508.1	1475.2	1462.8	1450.4	1462.8	1475.2	1508.1
40°	1350.4	1401.0	1461.4	1480.3	1457.9	1435.9	1415.2	1394.5	1415.2	1435.9	1457.9
42.5°	1211.1	1275.3	1352.2	1392.9	1397.4	1392.5	1359.4	1326.3	1359.4	1392.5	1397.4
45°	1012.9	1082.9	1166.5	1232.9	1282.1	1307.7	1262.9	1218.0	1262.9	1307.7	1282.1
47.5°	839.6	902.4	977.1	1054.3	1134.1	1182.5	1136.5	1090.4	1136.5	1182.5	1134.1
50°	733.4	793.3	863.1	940.7	1026.0	1080.8	1043.7	1006.6	1043.7	1080.8	1026.0
52.5°	634.8	694.0	763.8	839.3	920.5	974.7	948.0	921.3	948.0	974.7	920.5
55°	505.4	559.9	626.3	695.2	766.8	817.0	803.2	789.4	803.2	817.0	766.8
57.5°	408.5	454.2	510.6	572.0	638.4	686.0	677.2	668.4	677.2	686.0	638.4
60°	358.0	393.7	437.7	492.9	559.2	607.5	601.5	595.4	601.5	607.5	559.2
62.5°	315.2	343.6	378.6	427.9	491.5	538.0	533.4	528.7	533.4	538.0	491.5
65°	260.3	281.9	308.6	349.1	403.4	443.1	438.8	434.5	438.8	443.1	403.4
67.5°	216.2	233.4	254.4	287.1	331.4	364.1	361.8	359.6	361.8	364.1	331.4
70°	187.1	202.4	221.3	250.2	289.0	317.9	317.0	316.1	317.0	317.9	289.0
72.5°	162.6	174.9	190.5	215.2	249.2	274.9	276.2	277.4	276.2	274.9	249.2
75°	127.6	135.8	146.1	165.1	192.7	214.0	216.6	219.2	216.6	214.0	192.7
77.5°	98.5	101.1	104.6	117.7	140.4	158.2	160.9	163.7	160.9	158.2	140.4
80°	81.5	81.5	81.5	90.1	107.3	121.1	124.6	128.0	124.6	121.1	107.3
82.5°	62.7	62.8	62.8	67.7	77.3	85.8	90.6	95.4	90.6	85.8	77.3
85°	24.6	29.1	34.3	36.9	36.9	37.9	42.2	46.5	42.2	37.9	36.9
87.5°	10.3	10.0	10.0	11.5	14.1	15.6	14.3	13.2	14.3	15.4	14.6
90°	28.1	26.8	26.8	25.4	21.4	16.1	9.4	4.0	9.4	14.7	24.1
92.5°	33.4	33.2	31.0	28.6	23.5	23.5	23.3	14.7	25.4	36.1	51.9
95°	30.8	30.8	36.1	45.5	66.9	68.2	45.5	41.5	58.9	82.9	104.3
97.5°	83.2	99.0	121.4	125.7	119.0	88.8	85.1	79.2	107.8	131.6	166.1
100°	153.8	173.9	189.9	157.8	124.4	123.1	115.0	112.4	143.1	165.9	199.3
102.5°	240.5	246.6	191.0	172.8	165.1	159.4	147.1	145.5	176.3	207.6	235.7
105°	260.8	234.1	235.4	235.4	230.1	219.4	196.6	195.3	230.1	266.2	300.9
107.5°	306.8	310.8	317.8	316.2	310.0	281.4	254.7	248.5	279.8	323.2	361.4
110°	367.8	371.8	374.5	371.8	362.5	326.4	294.3	284.9	313.0	358.5	399.9



TEST NUMBER: P1428267

CATALOG NUMBER: SQ2W-PR1-K-100U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	426.7	429.6	435.5	427.5	411.7	370.2	333.9	320.2	348.3	394.8	437.4
115°	520.3	520.3	521.6	517.6	485.5	442.7	394.6	374.5	398.6	441.4	488.2
117.5°	612.3	613.9	608.6	597.9	560.7	510.9	456.9	424.8	443.8	489.0	537.2
120°	670.1	672.8	667.4	651.4	615.3	559.1	497.6	460.1	474.8	519.0	567.1
122.5°	730.0	729.5	723.1	704.9	662.4	604.0	543.6	497.6	503.7	544.6	591.7
125°	813.2	811.9	806.5	785.1	741.0	680.8	609.9	553.7	545.7	580.5	628.6
127.5°	892.4	889.5	881.2	855.2	810.0	752.0	674.1	610.5	592.5	614.5	658.6
130°	947.0	943.0	928.3	900.2	856.0	801.2	722.3	650.0	624.6	638.0	676.8
132.5°	999.4	987.9	975.3	945.1	904.2	847.2	767.2	691.8	656.7	662.6	692.8
135°	1066.0	1055.3	1039.3	1009.8	971.1	914.9	834.6	753.0	704.9	699.5	716.9
137.5°	1124.6	1113.4	1095.2	1069.8	1030.7	980.7	903.6	817.5	756.8	738.9	745.5
140°	1161.0	1147.6	1131.6	1106.1	1071.4	1019.2	944.3	861.4	793.2	767.8	763.7
142.5°	1190.9	1180.8	1163.7	1140.4	1109.9	1057.7	985.0	903.1	830.6	797.7	788.3
145°	1235.9	1227.9	1209.1	1187.7	1162.3	1110.2	1043.3	961.7	889.5	846.7	826.6
147.5°	1273.9	1267.5	1252.7	1227.6	1206.2	1156.2	1095.2	1023.0	948.9	895.9	869.9
150°	1297.4	1292.1	1277.4	1253.3	1231.9	1185.1	1126.2	1059.3	988.4	932.3	898.8
152.5°	1319.9	1314.5	1297.7	1273.6	1255.4	1211.8	1158.3	1094.6	1022.7	966.5	932.0
155°	1349.6	1342.9	1326.8	1304.1	1288.1	1247.9	1198.4	1142.3	1080.7	1021.9	983.1
157.5°	1373.1	1364.8	1349.9	1330.3	1313.2	1276.3	1233.2	1184.8	1131.0	1074.9	1035.3
160°	1387.0	1377.7	1361.6	1344.2	1328.2	1293.4	1254.6	1210.5	1161.0	1110.2	1067.4
162.5°	1396.7	1388.4	1369.1	1353.9	1340.0	1308.4	1271.7	1231.9	1187.7	1143.3	1103.7
165°	1407.1	1397.7	1377.7	1365.6	1353.6	1326.8	1294.7	1262.6	1225.2	1189.1	1157.0
167.5°	1407.9	1400.1	1380.1	1368.3	1359.5	1336.5	1310.5	1285.9	1256.8	1228.4	1201.7
170°	1405.8	1399.1	1379.0	1368.3	1361.6	1342.9	1320.2	1298.8	1276.0	1251.9	1230.5
172.5°	1398.3	1391.6	1372.6	1364.0	1360.6	1344.0	1325.5	1309.5	1289.9	1272.3	1255.2
175°	1379.0	1373.7	1357.6	1352.3	1353.6	1342.9	1329.5	1320.2	1308.1	1297.4	1288.1
177.5°	1350.9	1347.7	1335.9	1335.9	1340.2	1333.8	1329.5	1325.2	1319.9	1316.7	1313.5
180°	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2



TEST NUMBER: P1428267

CATALOG NUMBER: SQ2W-PR1-K-100U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7
2.5°	1901.3	1896.9	1897.5	1898.6	1900.6	1902.7	1900.6	1898.6	1897.5	1896.9	1901.3
5°	1909.4	1905.5	1907.2	1910.7	1919.3	1927.9	1919.3	1910.7	1907.2	1905.5	1909.4
7.5°	1931.1	1931.2	1936.2	1942.8	1954.2	1965.6	1954.2	1942.8	1936.2	1931.2	1931.1
10°	1941.3	1940.0	1940.9	1944.5	1956.6	1968.7	1956.6	1944.5	1940.9	1940.0	1941.3
12.5°	1923.2	1915.7	1914.5	1915.2	1921.8	1928.3	1921.8	1915.2	1914.5	1915.7	1923.2
15°	1879.0	1865.2	1867.8	1870.8	1875.1	1879.4	1875.1	1870.8	1867.8	1865.2	1879.0
17.5°	1836.4	1826.7	1836.0	1845.1	1853.5	1862.0	1853.5	1845.1	1836.0	1826.7	1836.4
20°	1813.5	1807.9	1820.0	1832.7	1847.3	1862.0	1847.3	1832.7	1820.0	1807.9	1813.5
22.5°	1792.8	1791.7	1808.6	1826.3	1846.5	1866.6	1846.5	1826.3	1808.6	1791.7	1792.8
25°	1760.0	1769.5	1798.0	1824.9	1847.3	1869.7	1847.3	1824.9	1798.0	1769.5	1760.0
27.5°	1723.5	1747.8	1786.2	1819.0	1834.7	1850.3	1834.7	1819.0	1786.2	1747.8	1723.5
30°	1701.6	1731.4	1765.0	1791.7	1797.8	1803.8	1797.8	1791.7	1765.0	1731.4	1701.6
32.5°	1676.1	1704.8	1722.6	1734.0	1726.2	1718.5	1726.2	1734.0	1722.6	1704.8	1676.1
35°	1630.5	1649.5	1635.7	1621.3	1604.9	1588.5	1604.9	1621.3	1635.7	1649.5	1630.5
37.5°	1547.7	1547.4	1507.0	1472.1	1453.3	1434.5	1453.3	1472.1	1507.0	1547.4	1547.7
40°	1480.3	1461.4	1401.0	1350.4	1328.8	1307.3	1328.8	1350.4	1401.0	1461.4	1480.3
42.5°	1392.9	1352.2	1275.3	1211.1	1184.7	1158.3	1184.7	1211.1	1275.3	1352.2	1392.9
45°	1232.9	1166.5	1082.9	1012.9	983.6	954.3	983.6	1012.9	1082.9	1166.5	1232.9
47.5°	1054.3	977.1	902.4	839.6	812.2	784.7	812.2	902.4	977.1	1054.3	
50°	940.7	863.1	793.3	733.4	703.2	673.0	703.2	793.3	863.1	940.7	
52.5°	839.3	763.8	694.0	634.8	607.3	579.9	607.3	694.0	763.8	839.3	
55°	695.2	626.3	559.9	505.4	486.4	467.4	486.4	559.9	626.3	695.2	
57.5°	572.0	510.6	454.2	408.5	394.5	380.5	394.5	454.2	510.6	572.0	
60°	492.9	437.7	393.7	358.0	346.8	335.5	346.8	393.7	437.7	492.9	
62.5°	427.9	378.6	343.6	315.2	306.8	298.3	306.8	343.6	378.6	427.9	
65°	349.1	308.6	281.9	260.3	254.3	248.3	254.3	281.9	308.6	349.1	
67.5°	287.1	254.4	233.4	216.2	210.5	204.8	210.5	233.4	254.4	287.1	
70°	250.2	221.3	202.4	187.1	182.8	178.4	182.8	202.4	221.3	250.2	
72.5°	215.2	190.5	174.9	162.6	159.6	156.7	159.6	174.9	190.5	215.2	
75°	165.1	146.1	135.8	127.6	125.9	124.1	125.9	135.8	146.1	165.1	
77.5°	117.7	104.6	101.1	98.5	98.5	98.5	98.5	101.1	104.6	117.7	
80°	90.1	81.5	81.5	81.5	81.5	81.5	81.5	81.5	81.5	90.1	
82.5°	67.7	62.8	62.8	62.7	62.0	61.3	62.0	62.7	62.8	62.8	67.7
85°	36.9	34.3	29.1	24.6	22.0	19.4	22.0	24.6	29.1	34.3	36.9
87.5°	12.5	12.7	14.6	15.6	16.7	16.2	16.7	14.6	12.7	12.5	
90°	30.8	40.1	49.5	54.8	60.2	57.5	60.2	49.5	40.1	30.8	
92.5°	61.8	77.6	89.1	98.7	103.0	102.5	103.0	89.1	77.6	61.8	
95°	124.4	143.1	161.8	175.2	183.2	180.6	183.2	161.8	143.1	124.4	
97.5°	191.8	216.9	237.8	250.4	258.4	263.8	258.4	237.8	216.9	191.8	
100°	236.7	260.8	284.9	299.6	313.0	318.3	313.0	284.9	260.8	236.7	
102.5°	273.1	304.7	330.9	346.7	357.9	363.3	357.9	330.9	304.7	273.1	
105°	333.0	366.5	394.6	414.6	426.7	430.7	426.7	394.6	366.5	333.0	
107.5°	393.0	427.5	453.4	475.6	490.3	498.9	490.3	453.4	427.5	393.0	
110°	440.1	468.1	496.2	516.3	531.0	536.4	531.0	496.2	468.1	440.1	



TEST NUMBER: P1428267

CATALOG NUMBER: SQ2W-PR1-K-100U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	479.6	510.9	539.0	559.1	575.9	583.4	575.9	559.1	539.0	510.9	479.6
115°	535.0	576.5	601.9	620.6	632.7	639.3	632.7	620.6	601.9	576.5	535.0
117.5°	581.0	624.4	652.2	666.6	672.3	677.1	672.3	666.6	652.2	624.4	581.0
120°	609.9	650.0	682.1	700.9	707.6	710.2	707.6	700.9	682.1	650.0	609.9
122.5°	636.7	674.7	705.7	728.7	739.7	742.3	739.7	728.7	705.7	674.7	636.7
125°	674.1	710.2	742.3	765.1	777.1	783.8	777.1	765.1	742.3	710.2	674.1
127.5°	706.8	745.8	775.2	795.8	807.6	813.0	807.6	795.8	775.2	745.8	706.8
130°	724.9	765.1	794.5	817.2	827.9	833.3	827.9	817.2	794.5	765.1	724.9
132.5°	738.9	781.1	811.6	832.2	844.0	849.3	844.0	832.2	811.6	781.1	738.9
135°	755.7	799.9	832.0	852.0	862.7	868.1	862.7	852.0	832.0	799.9	755.7
137.5°	770.4	810.6	844.0	865.1	874.8	878.2	874.8	865.1	844.0	810.6	770.4
140°	781.1	815.9	849.3	869.4	880.1	881.4	880.1	869.4	849.3	815.9	781.1
142.5°	795.0	822.3	851.5	871.5	882.2	884.7	882.2	871.5	851.5	822.3	795.0
145°	819.9	836.0	856.0	874.8	884.1	886.8	884.1	874.8	856.0	836.0	819.9
147.5°	851.2	856.3	866.7	879.0	888.1	890.0	888.1	879.0	866.7	856.3	851.2
150°	874.8	873.4	877.4	885.5	893.5	892.1	893.5	885.5	877.4	873.4	874.8
152.5°	901.5	893.7	893.5	897.2	901.0	900.7	901.0	897.2	893.5	893.7	901.5
155°	947.0	932.3	924.2	921.6	921.6	920.2	921.6	921.6	924.2	932.3	947.0
157.5°	997.0	976.4	964.4	957.9	956.1	953.1	956.1	957.9	964.4	976.4	997.0
160°	1031.2	1008.5	996.5	985.8	981.8	977.7	981.8	985.8	996.5	1008.5	1031.2
162.5°	1063.3	1041.7	1028.6	1018.9	1014.9	1008.8	1014.9	1018.9	1028.6	1041.7	1063.3
165°	1115.5	1092.8	1078.1	1070.0	1064.7	1059.3	1064.7	1070.0	1078.1	1092.8	1115.5
167.5°	1167.7	1142.8	1133.2	1124.1	1119.0	1109.4	1119.0	1124.1	1133.2	1142.8	1167.7
170°	1199.8	1177.0	1171.7	1163.7	1154.3	1143.6	1154.3	1163.7	1171.7	1177.0	1199.8
172.5°	1227.6	1212.4	1207.0	1199.0	1196.0	1187.5	1196.0	1199.0	1207.0	1212.4	1227.6
175°	1268.0	1256.0	1256.0	1254.6	1250.6	1242.6	1250.6	1254.6	1256.0	1256.0	1268.0
177.5°	1301.7	1295.3	1299.6	1299.6	1298.5	1291.0	1298.5	1299.6	1299.6	1295.3	1301.7
180°	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2	1324.2



TEST NUMBER: P1428267

CATALOG NUMBER: SQ2W-PR1-K-100U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1902.7	1902.7	1902.7	1902.7
2.5°	1911.0	1915.6	1905.3	1895.0
5°	1918.9	1922.3	1907.7	1893.0
7.5°	1935.9	1934.4	1913.5	1892.6
10°	1944.7	1941.1	1916.1	1891.1
12.5°	1937.0	1940.0	1910.9	1881.8
15°	1909.2	1923.2	1888.7	1854.2
17.5°	1865.2	1877.8	1841.8	1805.7
20°	1836.8	1845.4	1810.0	1774.7
22.5°	1811.9	1817.5	1782.1	1746.8
25°	1769.5	1768.9	1737.9	1706.8
27.5°	1713.5	1701.5	1683.2	1664.9
30°	1675.8	1653.4	1641.3	1629.2
32.5°	1636.5	1604.9	1597.7	1590.4
35°	1578.8	1538.5	1532.5	1526.4
37.5°	1508.1	1475.2	1462.8	1450.4
40°	1457.9	1435.9	1415.2	1394.5
42.5°	1397.4	1392.5	1359.4	1326.3
45°	1282.1	1307.7	1262.9	1218.0
47.5°	1134.1	1182.5	1136.5	1090.4
50°	1026.0	1080.8	1043.7	1006.6
52.5°	920.5	974.7	948.0	921.3
55°	766.8	817.0	803.2	789.4
57.5°	638.4	686.0	677.2	668.4
60°	559.2	607.5	601.5	595.4
62.5°	491.5	538.0	533.4	528.7
65°	403.4	443.1	438.8	434.5
67.5°	331.4	364.1	361.8	359.6
70°	289.0	317.9	317.0	316.1
72.5°	249.2	274.9	276.2	277.4
75°	192.7	214.0	216.6	219.2
77.5°	140.4	158.2	160.9	163.7
80°	107.3	121.1	124.6	128.0
82.5°	77.3	85.8	90.6	95.4
85°	36.9	37.9	42.2	46.5
87.5°	14.6	15.4	14.3	13.2
90°	24.1	14.7	9.4	4.0
92.5°	51.9	36.1	25.4	14.7
95°	104.3	82.9	58.9	41.5
97.5°	166.1	131.6	107.8	79.2
100°	199.3	165.9	143.1	112.4
102.5°	235.7	207.6	176.3	145.5
105°	300.9	266.2	230.1	195.3
107.5°	361.4	323.2	279.8	248.5
110°	399.9	358.5	313.0	284.9



TEST NUMBER: P1428267

CATALOG NUMBER: SQ2W-PR1-K-100U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	437.4	394.8	348.3	320.2
115°	488.2	441.4	398.6	374.5
117.5°	537.2	489.0	443.8	424.8
120°	567.1	519.0	474.8	460.1
122.5°	591.7	544.6	503.7	497.6
125°	628.6	580.5	545.7	553.7
127.5°	658.6	614.5	592.5	610.5
130°	676.8	638.0	624.6	650.0
132.5°	692.8	662.6	656.7	691.8
135°	716.9	699.5	704.9	753.0
137.5°	745.5	738.9	756.8	817.5
140°	763.7	767.8	793.2	861.4
142.5°	788.3	797.7	830.6	903.1
145°	826.6	846.7	889.5	961.7
147.5°	869.9	895.9	948.9	1023.0
150°	898.8	932.3	988.4	1059.3
152.5°	932.0	966.5	1022.7	1094.6
155°	983.1	1021.9	1080.7	1142.3
157.5°	1035.3	1074.9	1131.0	1184.8
160°	1067.4	1110.2	1161.0	1210.5
162.5°	1103.7	1143.3	1187.7	1231.9
165°	1157.0	1189.1	1225.2	1262.6
167.5°	1201.7	1228.4	1256.8	1285.9
170°	1230.5	1251.9	1276.0	1298.8
172.5°	1255.2	1272.3	1289.9	1309.5
175°	1288.1	1297.4	1308.1	1320.2
177.5°	1313.5	1316.7	1319.9	1325.2
180°	1324.2	1324.2	1324.2	1324.2



TEST NUMBER: P1428267
 CATALOG NUMBER: SQ2W-PR1-K-100U-100D-L935-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.96	19.82	19.89	20.76	21.97	15.33	16.19	16.26	17.13	18.34
	3H	20.17	20.93	21.11	21.88	23.12	16.49	17.26	17.43	18.20	19.44
	4H	20.65	21.37	21.61	22.33	23.57	16.95	17.68	17.91	18.63	19.88
	6H	20.95	21.61	21.91	22.57	23.83	17.30	17.96	18.26	18.92	20.18
	8H	21.05	21.68	22.02	22.66	23.92	17.43	18.06	18.41	19.04	20.30
	12H	21.09	21.69	22.07	22.66	23.94	17.46	18.06	18.44	19.03	20.31
4H	2H	19.06	19.78	20.02	20.74	21.98	16.04	16.76	17.00	17.72	18.96
	3H	20.52	21.12	21.49	22.11	23.37	17.39	17.99	18.37	18.98	20.24
	4H	21.15	21.70	22.13	22.67	23.96	17.94	18.48	18.92	19.46	20.75
	6H	21.58	22.05	22.57	23.05	24.34	18.37	18.84	19.36	19.84	21.13
	8H	21.74	22.18	22.73	23.17	24.47	18.56	18.99	19.55	19.99	21.29
	12H	21.81	22.20	22.82	23.21	24.51	18.60	19.00	19.61	20.01	21.31
8H	4H	21.18	21.61	22.17	22.61	23.91	18.27	18.70	19.26	19.70	21.00
	6H	21.71	22.07	22.73	23.11	24.40	18.81	19.17	19.82	20.21	21.50
	8H	21.94	22.26	22.97	23.29	24.60	19.07	19.39	20.10	20.41	21.73
	12H	22.06	22.34	23.09	23.36	24.72	19.16	19.44	20.19	20.46	21.82
12H	4H	21.13	21.53	22.15	22.54	23.84	18.29	18.68	19.30	19.69	20.99
	6H	21.70	22.02	22.72	23.04	24.35	18.88	19.20	19.90	20.22	21.54
	8H	21.95	22.23	22.98	23.25	24.61	19.17	19.45	20.20	20.47	21.83