

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427929

Luminaire Tested: SQ2W-PH1-K-100U-100D-L840-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1427929
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-10)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PH1-K-100U-100D-L840-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE HEX LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9765.0 lumens
Efficiency: N/A
Efficacy: 138.1 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.02 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 70.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1427929

CATALOG NUMBER: SQ2W-PH1-K-100U-100D-L840-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1427929

CATALOG NUMBER: SQ2W-PH1-K-100U-100D-L840-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54				
1	99	95	91	87	92	88	85	82	75	73	71	64	62	60	53	52	51	46				
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	39				
3	82	73	66	60	76	68	61	56	58	54	50	50	46	43	42	39	37	33				
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32	28				
5	69	58	49	43	64	54	47	41	47	41	37	40	36	32	34	30	28	25				
6	64	52	44	38	59	48	41	36	42	36	32	36	32	28	31	27	24	22				
7	59	47	39	33	55	44	37	31	38	32	28	33	28	25	28	24	22	19				
8	55	42	35	29	51	40	33	28	35	29	25	30	26	22	26	22	19	17				
9	51	39	31	26	47	36	30	25	32	26	22	28	23	20	24	20	18	15				
10	48	36	28	24	44	33	27	22	29	24	20	26	21	18	22	19	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	38357	38357	38357	38357
5°	38576	35059	38576	35059
10°	37688	31870	37688	31870
15°	37858	31246	37858	31246
20°	36506	31498	36506	31498
25°	35838	30764	35838	30764
30°	35061	31015	35061	31015
35°	34794	36355	34794	36355
40°	34825	28822	34825	28822
45°	34839	24824	34839	24824
50°	34349	23279	34349	23279
55°	33914	22333	33914	22333
60°	33576	20947	33576	20947
65°	32989	18219	32989	18219
70°	31156	13020	31156	13020
75°	27779	9869	27779	9869
80°	22696	9251	22696	9251
85°	14246	6280	14246	6280

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 34839 cd/sqm



TEST NUMBER: P1427929

CATALOG NUMBER: SQ2W-PH1-K-100U-100D-L840-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	209.0	2.1
10°-20°	549.8	5.6
20°-30°	806.1	8.3
30°-40°	976.1	10.0
40°-50°	959.9	9.8
50°-60°	834.9	8.6
60°-70°	580.7	5.9
70°-80°	275.4	2.8
80°-90°	67.1	0.7
90°-100°	122.8	1.3
100°-110°	358.2	3.7
110°-120°	584.5	6.0
120°-130°	741.7	7.6
130°-140°	793.6	8.1
140°-150°	741.1	7.6
150°-160°	609.8	6.2
160°-170°	409.0	4.2
170°-180°	145.2	1.5
0°-30°	1565.0	16.0
0°-40°	2541.1	26.0
0°-60°	4336.0	44.4
0°-90°	5259.2	53.9
90°-120°	1065.5	10.9
90°-150°	3341.8	34.2
90°-180°	4506.0	46.1
0°-180°	9765.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2376	2376	2376	2376	2376	
5°	2380	2163	2380	2163	2380	224
15°	2265	1869	2265	1869	2265	631
25°	2012	1727	2012	1727	2012	925
35°	1765	1844	1765	1844	1765	1106
45°	1526	1087	1526	1087	1526	1173
55°	1205	793	1205	793	1205	1076
65°	864	477	864	477	864	848
75°	445	158	445	158	445	472
85°	77	34	77	34	77	103
90°	5	34	5	67	5	6
95°	48	36	48	210	48	58
105°	228	365	228	502	228	242
115°	436	605	436	745	436	430
125°	645	959	645	913	645	577
135°	878	1255	878	1012	878	678
145°	1121	1446	1121	1034	1121	701
155°	1331	1571	1331	1072	1331	612
165°	1472	1638	1472	1235	1472	414
175°	1538	1604	1538	1448	1538	146
180°	1543	1543	1543	1543	1543	



TEST NUMBER: P1427929

CATALOG NUMBER: SQ2W-PH1-K-100U-100D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2375.7	2375.7	2375.7	2375.7	2375.7	2375.7	2375.7	2375.7	2375.7	2375.7	2375.7
2.5°	2370.2	2381.5	2392.7	2376.9	2351.9	2334.7	2325.0	2317.4	2315.8	2314.2	2315.8
5°	2380.2	2379.2	2378.2	2331.2	2268.9	2222.2	2191.1	2167.2	2165.2	2163.2	2165.2
7.5°	2336.8	2305.6	2274.5	2211.4	2137.7	2083.6	2049.3	2023.1	2021.5	2019.9	2021.5
10°	2298.8	2251.6	2204.4	2133.0	2053.7	1998.4	1967.3	1943.9	1943.9	1943.9	1943.9
12.5°	2289.8	2215.2	2140.7	2062.5	1983.1	1931.9	1908.8	1892.7	1897.5	1902.3	1897.5
15°	2264.9	2152.4	2039.9	1960.5	1892.2	1855.0	1849.0	1847.2	1858.3	1869.3	1858.3
17.5°	2182.6	2061.5	1940.3	1870.5	1817.9	1798.0	1810.9	1823.7	1836.6	1849.4	1836.6
20°	2124.7	2005.2	1885.7	1821.1	1774.9	1763.8	1788.0	1809.1	1821.1	1833.2	1821.1
22.5°	2075.9	1954.8	1833.6	1776.5	1740.7	1736.1	1762.6	1784.1	1790.6	1797.0	1790.6
25°	2011.7	1875.1	1738.5	1696.8	1686.7	1693.3	1716.4	1733.0	1729.9	1726.9	1729.9
27.5°	1934.9	1792.2	1649.6	1622.8	1634.7	1647.6	1661.7	1672.7	1674.5	1676.3	1674.5
30°	1880.6	1738.0	1595.3	1574.0	1593.1	1609.6	1623.7	1637.5	1650.6	1663.6	1650.6
32.5°	1828.2	1680.7	1533.2	1517.9	1546.6	1577.7	1611.0	1643.5	1673.5	1703.4	1673.5
35°	1765.3	1611.6	1457.9	1445.9	1481.0	1526.3	1581.5	1647.6	1746.0	1844.5	1746.0
37.5°	1699.3	1534.6	1369.8	1364.4	1412.0	1459.6	1507.2	1550.8	1582.1	1613.5	1582.1
40°	1652.3	1479.5	1306.7	1306.5	1363.8	1423.0	1484.3	1512.2	1439.9	1367.5	1439.9
42.5°	1601.7	1428.9	1256.1	1251.0	1301.9	1367.2	1446.9	1476.2	1354.1	1231.9	1354.1
45°	1525.8	1345.9	1166.1	1159.6	1210.8	1247.0	1268.1	1262.0	1174.6	1087.2	1174.6
47.5°	1436.2	1264.9	1093.5	1092.1	1147.3	1151.3	1104.1	1060.2	1026.0	991.9	1026.0
50°	1367.5	1205.8	1044.0	1051.1	1114.4	1108.3	1033.0	971.0	948.9	926.8	948.9
52.5°	1300.6	1146.9	993.2	1011.9	1088.0	1076.0	975.7	896.8	881.9	867.1	881.9
55°	1204.8	1057.1	909.4	951.6	1057.1	1041.0	903.4	799.4	796.4	793.4	796.4
57.5°	1103.1	963.4	823.8	853.1	938.7	921.8	802.4	714.2	719.5	724.7	719.5
60°	1039.8	904.1	768.5	772.3	822.5	806.5	724.1	660.8	654.8	648.7	654.8
62.5°	972.9	843.7	714.5	695.7	713.8	694.9	639.1	595.7	589.7	583.6	589.7
65°	863.5	745.9	628.4	593.0	584.9	557.8	511.6	476.9	476.9	476.9	476.9
67.5°	743.2	640.7	538.3	498.6	480.0	453.0	417.9	385.5	361.4	337.2	361.4
70°	660.0	569.6	479.2	437.8	412.6	380.5	341.3	307.9	291.8	275.8	291.8
72.5°	571.4	493.9	416.3	373.9	343.1	311.8	279.8	251.3	232.8	214.3	232.8
75°	445.3	383.0	320.7	279.5	245.4	213.7	184.6	162.2	160.2	158.2	160.2
77.5°	321.9	276.5	231.1	197.7	168.4	146.4	131.7	120.8	121.0	121.2	121.0
80°	244.1	210.0	175.8	144.7	114.5	99.0	97.9	97.4	98.5	99.5	98.5
82.5°	171.8	146.5	121.2	101.3	83.2	74.8	76.2	77.4	77.6	77.8	77.6
85°	76.9	64.8	52.7	48.2	46.2	43.2	39.2	35.9	34.9	33.9	34.9
87.5°	17.2	17.7	18.4	17.6	16.2	15.3	15.3	15.6	15.9	15.9	15.9
90°	4.7	10.9	18.7	24.9	29.6	31.2	31.2	32.7	34.3	34.3	34.3
92.5°	17.1	27.1	27.4	27.4	33.4	36.2	38.7	39.0	40.5	40.5	40.5
95°	48.3	53.0	79.5	77.9	53.0	42.1	35.9	35.9	35.9	35.9	35.9
97.5°	92.3	99.1	103.5	138.7	146.5	141.5	115.3	97.0	86.7	82.0	86.7
100°	130.9	134.1	143.4	145.0	183.9	221.3	202.6	179.3	171.5	166.8	171.5
102.5°	169.6	171.5	185.8	192.4	201.4	222.6	287.4	280.3	275.0	274.0	275.0
105°	227.6	229.1	255.6	268.1	274.3	274.3	272.8	304.0	353.8	364.8	353.8
107.5°	289.6	296.8	328.0	361.3	368.5	370.4	362.3	357.6	355.7	357.0	355.7
110°	332.0	342.9	380.3	422.4	433.3	436.5	433.3	428.7	425.5	425.5	425.5



TEST NUMBER: P1427929

CATALOG NUMBER: SQ2W-PH1-K-100U-100D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	373.2	389.1	431.5	479.8	498.2	507.5	500.7	497.2	494.1	496.6	494.1
115°	436.5	459.8	516.0	565.8	603.2	607.9	606.4	606.4	604.8	604.8	604.8
117.5°	495.1	532.5	595.5	653.4	696.8	709.2	715.5	713.6	711.7	714.9	711.7
120°	536.2	579.9	651.6	717.0	759.1	777.8	784.1	780.9	784.1	780.9	784.1
122.5°	579.9	633.5	703.9	771.9	821.5	842.7	850.2	850.8	851.4	849.5	851.4
125°	645.3	710.8	793.4	863.6	915.0	939.9	946.2	947.7	950.9	958.6	950.9
127.5°	711.4	785.6	876.3	944.0	996.7	1026.9	1036.6	1040.0	1046.6	1050.0	1046.6
130°	757.6	841.7	933.7	997.6	1049.1	1081.8	1098.9	1103.6	1111.4	1109.8	1111.4
132.5°	806.2	894.1	987.3	1053.7	1101.4	1136.7	1151.3	1164.7	1167.5	1169.7	1167.5
135°	877.6	972.7	1066.2	1131.7	1176.9	1211.2	1229.9	1242.3	1250.1	1254.8	1250.1
137.5°	952.7	1053.1	1142.9	1201.2	1246.7	1276.3	1297.5	1310.6	1318.7	1322.5	1318.7
140°	1003.9	1100.5	1187.8	1248.6	1289.1	1318.7	1337.4	1353.0	1362.4	1362.4	1362.4
142.5°	1052.5	1147.9	1232.7	1293.5	1329.0	1356.1	1376.1	1387.9	1398.5	1398.5	1398.5
145°	1120.8	1215.8	1293.8	1354.6	1384.2	1409.1	1431.0	1440.3	1446.5	1446.5	1446.5
147.5°	1192.2	1276.3	1347.4	1405.7	1430.6	1459.9	1477.1	1484.6	1492.4	1488.9	1492.4
150°	1234.6	1312.5	1381.1	1435.6	1460.6	1488.6	1505.8	1512.0	1519.8	1515.1	1519.8
152.5°	1275.7	1349.9	1412.3	1463.1	1484.3	1512.3	1532.0	1538.2	1543.5	1540.1	1543.5
155°	1331.2	1396.7	1454.3	1501.1	1519.8	1546.3	1565.0	1572.8	1579.0	1571.2	1579.0
157.5°	1380.8	1437.2	1487.4	1530.4	1550.4	1573.1	1590.6	1600.2	1606.5	1603.0	1606.5
160°	1410.7	1462.1	1507.3	1547.9	1566.6	1586.8	1605.5	1616.5	1622.7	1618.0	1622.7
162.5°	1435.6	1482.1	1524.8	1561.6	1577.8	1595.6	1618.0	1627.7	1633.9	1628.0	1633.9
165°	1471.5	1508.9	1546.3	1577.5	1591.5	1605.5	1628.9	1639.8	1644.5	1638.3	1644.5
167.5°	1498.6	1527.3	1557.5	1584.3	1594.6	1608.3	1631.7	1640.8	1646.7	1638.9	1646.7
170°	1513.6	1538.5	1565.0	1586.8	1594.6	1607.1	1630.5	1638.3	1643.0	1635.2	1643.0
172.5°	1526.0	1544.7	1566.3	1585.6	1589.6	1599.6	1621.8	1629.5	1633.0	1626.4	1633.0
175°	1538.5	1549.4	1565.0	1577.5	1575.9	1582.2	1600.9	1607.1	1613.3	1604.0	1613.3
177.5°	1544.4	1549.4	1554.4	1561.9	1556.9	1556.9	1570.6	1574.4	1575.6	1570.6	1575.6
180°	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2



TEST NUMBER: P1427929

CATALOG NUMBER: SQ2W-PH1-K-100U-100D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2375.7	2375.7	2375.7	2375.7	2375.7	2375.7	2375.7	2375.7	2375.7	2375.7	2375.7
2.5°	2317.4	2325.0	2334.7	2351.9	2376.9	2392.7	2381.5	2370.2	2381.5	2392.7	2376.9
5°	2167.2	2191.1	2222.2	2268.9	2331.2	2378.2	2379.2	2380.2	2379.2	2378.2	2331.2
7.5°	2023.1	2049.3	2083.6	2137.7	2211.4	2274.5	2305.6	2336.8	2305.6	2274.5	2211.4
10°	1943.9	1967.3	1998.4	2053.7	2133.0	2204.4	2251.6	2298.8	2251.6	2204.4	2133.0
12.5°	1892.7	1908.8	1931.9	1983.1	2062.5	2140.7	2215.2	2289.8	2215.2	2140.7	2062.5
15°	1847.2	1849.0	1855.0	1892.2	1960.5	2039.9	2152.4	2264.9	2152.4	2039.9	1960.5
17.5°	1823.7	1810.9	1798.0	1817.9	1870.5	1940.3	2061.5	2182.6	2061.5	1940.3	1870.5
20°	1809.1	1788.0	1763.8	1774.9	1821.1	1885.7	2005.2	2124.7	2005.2	1885.7	1821.1
22.5°	1784.1	1762.6	1736.1	1740.7	1776.5	1833.6	1954.8	2075.9	1954.8	1833.6	1776.5
25°	1733.0	1716.4	1693.3	1686.7	1696.8	1738.5	1875.1	2011.7	1875.1	1738.5	1696.8
27.5°	1672.7	1661.7	1647.6	1634.7	1622.8	1649.6	1792.2	1934.9	1792.2	1649.6	1622.8
30°	1637.5	1623.7	1609.6	1593.1	1574.0	1595.3	1738.0	1880.6	1738.0	1595.3	1574.0
32.5°	1643.5	1611.0	1577.7	1546.6	1517.9	1533.2	1680.7	1828.2	1680.7	1533.2	1517.9
35°	1647.6	1581.5	1526.3	1481.0	1445.9	1457.9	1611.6	1765.3	1611.6	1457.9	1445.9
37.5°	1550.8	1507.2	1459.6	1412.0	1364.4	1369.8	1534.6	1699.3	1534.6	1369.8	1364.4
40°	1512.2	1484.3	1423.0	1363.8	1306.5	1306.7	1479.5	1652.3	1479.5	1306.7	1306.5
42.5°	1476.2	1446.9	1367.2	1301.9	1251.0	1256.1	1428.9	1601.7	1428.9	1256.1	1251.0
45°	1262.0	1268.1	1247.0	1210.8	1159.6	1166.1	1345.9	1525.8	1345.9	1166.1	1159.6
47.5°	1060.2	1104.1	1151.3	1147.3	1092.1	1093.5	1264.9	1436.2	1264.9	1093.5	1092.1
50°	971.0	1033.0	1108.3	1114.4	1051.1	1044.0	1205.8	1367.5	1205.8	1044.0	1051.1
52.5°	896.8	975.7	1076.0	1088.0	1011.9	993.2	1146.9	1300.6	1146.9	993.2	1011.9
55°	799.4	903.4	1041.0	1057.1	951.6	909.4	1057.1	1204.8	1057.1	909.4	951.6
57.5°	714.2	802.4	921.8	938.7	853.1	823.8	963.4	1103.1	963.4	823.8	853.1
60°	660.8	724.1	806.5	822.5	772.3	768.5	904.1	1039.8	904.1	768.5	772.3
62.5°	595.7	639.1	694.9	713.8	695.7	714.5	843.7	972.9	843.7	714.5	695.7
65°	476.9	511.6	557.8	584.9	593.0	628.4	745.9	863.5	745.9	628.4	593.0
67.5°	385.5	417.9	453.0	480.0	498.6	538.3	640.7	743.2	640.7	538.3	498.6
70°	307.9	341.3	380.5	412.6	437.8	479.2	569.6	660.0	569.6	479.2	437.8
72.5°	251.3	279.8	311.8	343.1	373.9	416.3	493.9	571.4	493.9	416.3	373.9
75°	162.2	184.6	213.7	245.4	279.5	320.7	383.0	445.3	383.0	320.7	279.5
77.5°	120.8	131.7	146.4	168.4	197.7	231.1	276.5	321.9	276.5	231.1	197.7
80°	97.4	97.9	99.0	114.5	144.7	175.8	210.0	244.1	210.0	175.8	144.7
82.5°	77.4	76.2	74.8	83.2	101.3	121.2	146.5	171.8	146.5	121.2	101.3
85°	35.9	39.2	43.2	46.2	48.2	52.7	64.8	76.9	64.8	52.7	48.2
87.5°	15.6	15.3	15.3	16.2	17.6	18.4	17.7	17.2	17.7	18.1	18.3
90°	32.7	31.2	31.2	29.6	24.9	18.7	10.9	4.7	10.9	17.1	28.1
92.5°	39.0	38.7	36.2	33.4	27.4	27.4	27.1	17.1	29.6	42.1	60.5
95°	35.9	35.9	42.1	53.0	77.9	79.5	53.0	48.3	68.6	96.6	121.6
97.5°	97.0	115.3	141.5	146.5	138.7	103.5	99.1	92.3	125.6	153.4	193.6
100°	179.3	202.6	221.3	183.9	145.0	143.4	134.1	130.9	166.8	193.3	232.3
102.5°	280.3	287.4	222.6	201.4	192.4	185.8	171.5	169.6	205.4	241.9	274.7
105°	304.0	272.8	274.3	274.3	268.1	255.6	229.1	227.6	268.1	310.2	350.7
107.5°	357.6	362.3	370.4	368.5	361.3	328.0	296.8	289.6	326.1	376.6	421.2
110°	428.7	433.3	436.5	433.3	422.4	380.3	342.9	332.0	364.8	417.8	466.1



TEST NUMBER: P1427929

CATALOG NUMBER: SQ2W-PH1-K-100U-100D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	497.2	500.7	507.5	498.2	479.8	431.5	389.1	373.2	405.9	460.2	509.7
115°	606.4	606.4	607.9	603.2	565.8	516.0	459.8	436.5	464.5	514.4	569.0
117.5°	713.6	715.5	709.2	696.8	653.4	595.5	532.5	495.1	517.2	569.9	626.0
120°	780.9	784.1	777.8	759.1	717.0	651.6	579.9	536.2	553.4	604.8	660.9
122.5°	850.8	850.2	842.7	821.5	771.9	703.9	633.5	579.9	587.0	634.7	689.6
125°	947.7	946.2	939.9	915.0	863.6	793.4	710.8	645.3	636.0	676.5	732.6
127.5°	1040.0	1036.6	1026.9	996.7	944.0	876.3	785.6	711.4	690.5	716.1	767.5
130°	1103.6	1098.9	1081.8	1049.1	997.6	933.7	841.7	757.6	727.9	743.5	788.7
132.5°	1164.7	1151.3	1136.7	1101.4	1053.7	987.3	894.1	806.2	765.4	772.2	807.4
135°	1242.3	1229.9	1211.2	1176.9	1131.7	1066.2	972.7	877.6	821.5	815.2	835.5
137.5°	1310.6	1297.5	1276.3	1246.7	1201.2	1142.9	1053.1	952.7	882.0	861.1	868.9
140°	1353.0	1337.4	1318.7	1289.1	1248.6	1187.8	1100.5	1003.9	924.4	894.7	890.1
142.5°	1387.9	1376.1	1356.1	1329.0	1293.5	1232.7	1147.9	1052.5	968.0	929.7	918.7
145°	1440.3	1431.0	1409.1	1384.2	1354.6	1293.8	1215.8	1120.8	1036.6	986.7	963.3
147.5°	1484.6	1477.1	1459.9	1430.6	1405.7	1347.4	1276.3	1192.2	1105.8	1044.1	1013.8
150°	1512.0	1505.8	1488.6	1460.6	1435.6	1381.1	1312.5	1234.6	1151.9	1086.5	1047.5
152.5°	1538.2	1532.0	1512.3	1484.3	1463.1	1412.3	1349.9	1275.7	1191.8	1126.4	1086.2
155°	1572.8	1565.0	1546.3	1519.8	1501.1	1454.3	1396.7	1331.2	1259.5	1190.9	1145.7
157.5°	1600.2	1590.6	1573.1	1550.4	1530.4	1487.4	1437.2	1380.8	1318.1	1252.6	1206.5
160°	1616.5	1605.5	1586.8	1566.6	1547.9	1507.3	1462.1	1410.7	1353.0	1293.8	1243.9
162.5°	1627.7	1618.0	1595.6	1577.8	1561.6	1524.8	1482.1	1435.6	1384.2	1332.4	1286.3
165°	1639.8	1628.9	1605.5	1591.5	1577.5	1546.3	1508.9	1471.5	1427.8	1385.8	1348.3
167.5°	1640.8	1631.7	1608.3	1594.6	1584.3	1557.5	1527.3	1498.6	1464.6	1431.6	1400.4
170°	1638.3	1630.5	1607.1	1594.6	1586.8	1565.0	1538.5	1513.6	1487.1	1459.0	1434.1
172.5°	1629.5	1621.8	1599.6	1589.6	1585.6	1566.3	1544.7	1526.0	1503.3	1482.7	1462.8
175°	1607.1	1600.9	1582.2	1575.9	1577.5	1565.0	1549.4	1538.5	1524.5	1512.0	1501.1
177.5°	1574.4	1570.6	1556.9	1556.9	1561.9	1554.4	1549.4	1544.4	1538.2	1534.5	1530.7
180°	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2



TEST NUMBER: P1427929

CATALOG NUMBER: SQ2W-PH1-K-100U-100D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2375.7	2375.7	2375.7	2375.7	2375.7	2375.7	2375.7	2375.7	2375.7	2375.7	2375.7
2.5°	2351.9	2334.7	2325.0	2317.4	2315.8	2314.2	2315.8	2317.4	2325.0	2334.7	2351.9
5°	2268.9	2222.2	2191.1	2167.2	2165.2	2163.2	2165.2	2167.2	2191.1	2222.2	2268.9
7.5°	2137.7	2083.6	2049.3	2023.1	2021.5	2019.9	2021.5	2023.1	2049.3	2083.6	2137.7
10°	2053.7	1998.4	1967.3	1943.9	1943.9	1943.9	1943.9	1943.9	1967.3	1998.4	2053.7
12.5°	1983.1	1931.9	1908.8	1892.7	1897.5	1902.3	1897.5	1892.7	1908.8	1931.9	1983.1
15°	1892.2	1855.0	1849.0	1847.2	1858.3	1869.3	1858.3	1847.2	1849.0	1855.0	1892.2
17.5°	1817.9	1798.0	1810.9	1823.7	1836.6	1849.4	1836.6	1823.7	1810.9	1798.0	1817.9
20°	1774.9	1763.8	1788.0	1809.1	1821.1	1833.2	1821.1	1809.1	1788.0	1763.8	1774.9
22.5°	1740.7	1736.1	1762.6	1784.1	1790.6	1797.0	1790.6	1784.1	1762.6	1736.1	1740.7
25°	1686.7	1693.3	1716.4	1733.0	1729.9	1726.9	1729.9	1733.0	1716.4	1693.3	1686.7
27.5°	1634.7	1647.6	1661.7	1672.7	1674.5	1676.3	1674.5	1672.7	1661.7	1647.6	1634.7
30°	1593.1	1609.6	1623.7	1637.5	1650.6	1663.6	1650.6	1637.5	1623.7	1609.6	1593.1
32.5°	1546.6	1577.7	1611.0	1643.5	1673.5	1703.4	1673.5	1643.5	1611.0	1577.7	1546.6
35°	1481.0	1526.3	1581.5	1647.6	1746.0	1844.5	1746.0	1647.6	1581.5	1526.3	1481.0
37.5°	1412.0	1459.6	1507.2	1550.8	1582.1	1613.5	1582.1	1550.8	1507.2	1459.6	1412.0
40°	1363.8	1423.0	1484.3	1512.2	1439.9	1367.5	1439.9	1512.2	1484.3	1423.0	1363.8
42.5°	1301.9	1367.2	1446.9	1476.2	1354.1	1231.9	1354.1	1476.2	1446.9	1367.2	1301.9
45°	1210.8	1247.0	1268.1	1262.0	1174.6	1087.2	1174.6	1262.0	1268.1	1247.0	1210.8
47.5°	1147.3	1151.3	1104.1	1060.2	1026.0	991.9	1026.0	1060.2	1104.1	1151.3	1147.3
50°	1114.4	1108.3	1033.0	971.0	948.9	926.8	948.9	971.0	1033.0	1108.3	1114.4
52.5°	1088.0	1076.0	975.7	896.8	881.9	867.1	881.9	896.8	975.7	1076.0	1088.0
55°	1057.1	1041.0	903.4	799.4	796.4	793.4	796.4	799.4	903.4	1041.0	1057.1
57.5°	938.7	921.8	802.4	714.2	719.5	724.7	719.5	714.2	802.4	921.8	938.7
60°	822.5	806.5	724.1	660.8	654.8	648.7	654.8	660.8	724.1	806.5	822.5
62.5°	713.8	694.9	639.1	595.7	589.7	583.6	589.7	595.7	639.1	694.9	713.8
65°	584.9	557.8	511.6	476.9	476.9	476.9	476.9	476.9	511.6	557.8	584.9
67.5°	480.0	453.0	417.9	385.5	361.4	337.2	361.4	385.5	417.9	453.0	480.0
70°	412.6	380.5	341.3	307.9	291.8	275.8	291.8	307.9	341.3	380.5	412.6
72.5°	343.1	311.8	279.8	251.3	232.8	214.3	232.8	251.3	279.8	311.8	343.1
75°	245.4	213.7	184.6	162.2	160.2	158.2	160.2	162.2	184.6	213.7	245.4
77.5°	168.4	146.4	131.7	120.8	121.0	121.2	121.0	120.8	131.7	146.4	168.4
80°	114.5	99.0	97.9	97.4	98.5	99.5	98.5	97.4	97.9	99.0	114.5
82.5°	83.2	74.8	76.2	77.4	77.6	77.8	77.6	77.4	76.2	74.8	83.2
85°	46.2	43.2	39.2	35.9	34.9	33.9	34.9	35.9	39.2	43.2	46.2
87.5°	17.4	18.4	20.6	21.8	23.1	22.4	23.1	21.8	20.6	18.4	17.4
90°	35.9	46.8	57.7	63.9	70.1	67.0	70.1	63.9	57.7	46.8	35.9
92.5°	72.0	90.4	103.8	115.0	120.0	119.4	120.0	115.0	103.8	90.4	72.0
95°	145.0	166.8	188.6	204.2	213.6	210.4	213.6	204.2	188.6	166.8	145.0
97.5°	223.5	252.8	277.2	291.8	301.2	307.4	301.2	291.8	277.2	252.8	223.5
100°	275.9	304.0	332.0	349.2	364.8	371.0	364.8	349.2	332.0	304.0	275.9
102.5°	318.3	355.1	385.6	404.0	417.1	423.4	417.1	404.0	385.6	355.1	318.3
105°	388.1	427.1	459.8	483.2	497.2	501.9	497.2	483.2	459.8	427.1	388.1
107.5°	458.0	498.2	528.4	554.3	571.4	581.4	571.4	554.3	528.4	498.2	458.0
110°	512.8	545.6	578.3	601.7	618.8	625.1	618.8	601.7	578.3	545.6	512.8



TEST NUMBER: P1427929

CATALOG NUMBER: SQ2W-PH1-K-100U-100D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	559.0	595.5	628.2	651.6	671.2	679.9	671.2	651.6	628.2	595.5	559.0
115°	623.5	671.8	701.4	723.3	737.3	745.1	737.3	723.3	701.4	671.8	623.5
117.5°	677.1	727.6	760.1	776.9	783.4	789.1	783.4	776.9	760.1	727.6	677.1
120°	710.8	757.6	795.0	816.8	824.6	827.7	824.6	816.8	795.0	757.6	710.8
122.5°	742.0	786.2	822.4	849.2	862.0	865.1	862.0	849.2	822.4	786.2	742.0
125°	785.6	827.7	865.1	891.6	905.6	913.4	905.6	891.6	865.1	827.7	785.6
127.5°	823.7	869.2	903.5	927.5	941.2	947.4	941.2	927.5	903.5	869.2	823.7
130°	844.9	891.6	925.9	952.4	964.9	971.1	964.9	952.4	925.9	891.6	844.9
132.5°	861.1	910.3	945.9	969.9	983.6	989.8	983.6	969.9	945.9	910.3	861.1
135°	880.7	932.1	969.6	992.9	1005.4	1011.6	1005.4	992.9	969.6	932.1	880.7
137.5°	897.9	944.6	983.6	1008.2	1019.4	1023.5	1019.4	1008.2	983.6	944.6	897.9
140°	910.3	950.9	989.8	1013.2	1025.7	1027.2	1025.7	1013.2	989.8	950.9	910.3
142.5°	926.5	958.3	992.3	1015.7	1028.2	1031.0	1028.2	1015.7	992.3	958.3	926.5
145°	955.5	974.2	997.6	1019.4	1030.4	1033.5	1030.4	1019.4	997.6	974.2	955.5
147.5°	992.0	997.9	1010.1	1024.4	1035.0	1037.2	1035.0	1024.4	1010.1	997.9	992.0
150°	1019.4	1017.9	1022.6	1031.9	1041.3	1039.7	1041.3	1031.9	1022.6	1017.9	1019.4
152.5°	1050.6	1041.6	1041.3	1045.6	1050.0	1049.7	1050.0	1045.6	1041.3	1041.6	1050.6
155°	1103.6	1086.5	1077.1	1074.0	1074.0	1072.4	1074.0	1074.0	1077.1	1086.5	1103.6
157.5°	1161.9	1137.9	1123.9	1116.4	1114.2	1110.8	1114.2	1116.4	1123.9	1137.9	1161.9
160°	1201.8	1175.3	1161.3	1148.8	1144.1	1139.5	1144.1	1148.8	1161.3	1175.3	1201.8
162.5°	1239.2	1214.0	1198.7	1187.5	1182.8	1175.6	1182.8	1187.5	1198.7	1214.0	1239.2
165°	1300.0	1273.5	1256.4	1247.0	1240.8	1234.6	1240.8	1247.0	1256.4	1273.5	1300.0
167.5°	1360.8	1331.8	1320.6	1310.0	1304.1	1292.8	1304.1	1310.0	1320.6	1331.8	1360.8
170°	1398.2	1371.7	1365.5	1356.1	1345.2	1332.8	1345.2	1356.1	1365.5	1371.7	1398.2
172.5°	1430.6	1412.9	1406.6	1397.3	1393.9	1383.9	1393.9	1397.3	1406.6	1412.9	1430.6
175°	1477.7	1463.7	1463.7	1462.1	1457.5	1448.1	1457.5	1462.1	1463.7	1463.7	1477.7
177.5°	1517.0	1509.5	1514.5	1514.5	1513.3	1504.5	1513.3	1514.5	1514.5	1509.5	1517.0
180°	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2



TEST NUMBER: P1427929

CATALOG NUMBER: SQ2W-PH1-K-100U-100D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	2375.7	2375.7	2375.7	2375.7
2.5°	2376.9	2392.7	2381.5	2370.2
5°	2331.2	2378.2	2379.2	2380.2
7.5°	2211.4	2274.5	2305.6	2336.8
10°	2133.0	2204.4	2251.6	2298.8
12.5°	2062.5	2140.7	2215.2	2289.8
15°	1960.5	2039.9	2152.4	2264.9
17.5°	1870.5	1940.3	2061.5	2182.6
20°	1821.1	1885.7	2005.2	2124.7
22.5°	1776.5	1833.6	1954.8	2075.9
25°	1696.8	1738.5	1875.1	2011.7
27.5°	1622.8	1649.6	1792.2	1934.9
30°	1574.0	1595.3	1738.0	1880.6
32.5°	1517.9	1533.2	1680.7	1828.2
35°	1445.9	1457.9	1611.6	1765.3
37.5°	1364.4	1369.8	1534.6	1699.3
40°	1306.5	1306.7	1479.5	1652.3
42.5°	1251.0	1256.1	1428.9	1601.7
45°	1159.6	1166.1	1345.9	1525.8
47.5°	1092.1	1093.5	1264.9	1436.2
50°	1051.1	1044.0	1205.8	1367.5
52.5°	1011.9	993.2	1146.9	1300.6
55°	951.6	909.4	1057.1	1204.8
57.5°	853.1	823.8	963.4	1103.1
60°	772.3	768.5	904.1	1039.8
62.5°	695.7	714.5	843.7	972.9
65°	593.0	628.4	745.9	863.5
67.5°	498.6	538.3	640.7	743.2
70°	437.8	479.2	569.6	660.0
72.5°	373.9	416.3	493.9	571.4
75°	279.5	320.7	383.0	445.3
77.5°	197.7	231.1	276.5	321.9
80°	144.7	175.8	210.0	244.1
82.5°	101.3	121.2	146.5	171.8
85°	48.2	52.7	64.8	76.9
87.5°	18.3	18.1	17.7	17.2
90°	28.1	17.1	10.9	4.7
92.5°	60.5	42.1	29.6	17.1
95°	121.6	96.6	68.6	48.3
97.5°	193.6	153.4	125.6	92.3
100°	232.3	193.3	166.8	130.9
102.5°	274.7	241.9	205.4	169.6
105°	350.7	310.2	268.1	227.6
107.5°	421.2	376.6	326.1	289.6
110°	466.1	417.8	364.8	332.0



TEST NUMBER: P1427929

CATALOG NUMBER: SQ2W-PH1-K-100U-100D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	509.7	460.2	405.9	373.2
115°	569.0	514.4	464.5	436.5
117.5°	626.0	569.9	517.2	495.1
120°	660.9	604.8	553.4	536.2
122.5°	689.6	634.7	587.0	579.9
125°	732.6	676.5	636.0	645.3
127.5°	767.5	716.1	690.5	711.4
130°	788.7	743.5	727.9	757.6
132.5°	807.4	772.2	765.4	806.2
135°	835.5	815.2	821.5	877.6
137.5°	868.9	861.1	882.0	952.7
140°	890.1	894.7	924.4	1003.9
142.5°	918.7	929.7	968.0	1052.5
145°	963.3	986.7	1036.6	1120.8
147.5°	1013.8	1044.1	1105.8	1192.2
150°	1047.5	1086.5	1151.9	1234.6
152.5°	1086.2	1126.4	1191.8	1275.7
155°	1145.7	1190.9	1259.5	1331.2
157.5°	1206.5	1252.6	1318.1	1380.8
160°	1243.9	1293.8	1353.0	1410.7
162.5°	1286.3	1332.4	1384.2	1435.6
165°	1348.3	1385.8	1427.8	1471.5
167.5°	1400.4	1431.6	1464.6	1498.6
170°	1434.1	1459.0	1487.1	1513.6
172.5°	1462.8	1482.7	1503.3	1526.0
175°	1501.1	1512.0	1524.5	1538.5
177.5°	1530.7	1534.5	1538.2	1544.4
180°	1543.2	1543.2	1543.2	1543.2



TEST NUMBER: P1427929
 CATALOG NUMBER: SQ2W-PH1-K-100U-100D-L840-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.90	20.79	20.82	21.73	22.94	18.72	19.61	19.65	20.56	21.77
	3H	22.07	22.87	23.01	23.82	25.06	19.78	20.57	20.71	21.52	22.76
	4H	22.89	23.64	23.84	24.60	25.85	20.02	20.78	20.97	21.73	22.98
	6H	23.36	24.05	24.32	25.01	26.27	20.17	20.86	21.13	21.82	23.08
	8H	23.51	24.17	24.48	25.15	26.41	20.23	20.88	21.19	21.86	23.12
	12H	23.57	24.20	24.54	25.17	26.45	20.24	20.87	21.21	21.84	23.12
4H	2H	20.34	21.09	21.29	22.04	23.29	19.41	20.16	20.37	21.12	22.37
	3H	22.59	23.22	23.56	24.20	25.46	20.64	21.27	21.61	22.26	23.52
	4H	23.46	24.04	24.44	25.01	26.30	20.94	21.51	21.91	22.49	23.78
	6H	24.03	24.52	25.01	25.52	26.81	21.14	21.63	22.13	22.63	23.92
	8H	24.23	24.69	25.22	25.68	26.98	21.23	21.69	22.22	22.68	23.98
	12H	24.31	24.73	25.32	25.74	27.05	21.25	21.67	22.26	22.68	23.99
8H	4H	23.49	23.95	24.48	24.94	26.24	21.17	21.63	22.16	22.62	23.92
	6H	24.12	24.50	25.13	25.54	26.83	21.44	21.82	22.45	22.86	24.15
	8H	24.38	24.72	25.41	25.74	27.06	21.59	21.92	22.61	22.94	24.26
	12H	24.52	24.81	25.54	25.83	27.19	21.65	21.94	22.68	22.96	24.33
12H	4H	23.44	23.86	24.45	24.87	26.17	21.17	21.58	22.18	22.59	23.90
	6H	24.10	24.43	25.12	25.46	26.77	21.47	21.81	22.50	22.83	24.15
	8H	24.37	24.66	25.40	25.68	27.04	21.64	21.93	22.66	22.95	24.31