

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428315

Luminaire Tested: SQ2W-PR1-K-150U-100D-L935-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1428315  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-PR1-K-150U-100D-L935-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - PERCEIVE RIPPLE LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10400.2 lumens  
Efficiency: N/A  
Efficacy: 112.2 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.34 / 1.36  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 92.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1428315

CATALOG NUMBER: SQ2W-PR1-K-150U-100D-L935-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1428315

CATALOG NUMBER: SQ2W-PR1-K-150U-100D-L935-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33
3	81	72	65	60	74	67	61	56	56	51	48	46	43	40	37	34	33	28
4	75	64	57	51	68	59	53	48	50	45	41	41	38	35	33	31	29	25
5	69	57	50	44	63	53	46	41	45	40	36	37	33	30	30	27	25	22
6	63	52	44	38	58	48	41	36	40	35	31	34	30	27	27	24	22	19
7	58	47	39	34	54	43	36	32	37	31	28	31	27	24	25	22	20	17
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18	16
9	51	39	31	26	46	36	29	25	31	26	22	26	22	19	21	18	16	14
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	30720	30720	30720	30720
5°	30680	31246	30680	31246
10°	31004	32276	31004	32276
15°	30993	31414	30993	31414
20°	30492	31992	30492	31992
25°	30406	33308	30406	33308
30°	30374	33629	30374	33629
35°	30085	31309	30085	31309
40°	29391	27553	29391	27553
45°	27811	21790	27811	21790
50°	25284	16904	25284	16904
55°	22221	13157	22221	13157
60°	19226	10834	19226	10834
65°	16599	9486	16599	9486
70°	14922	8422	14922	8422
75°	13674	7742	13674	7742
80°	11901	7578	11901	7578
85°	8614	3594	8614	3594

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 20°  
 Vertical Angle: 45°  
 Luminance: 29859 cd/sqm



TEST NUMBER: P1428315

CATALOG NUMBER: SQ2W-PR1-K-150U-100D-L935-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	183.8	1.8
10°-20°	531.9	5.1
20°-30°	822.3	7.9
30°-40°	988.9	9.5
40°-50°	888.0	8.5
50°-60°	595.0	5.7
60°-70°	346.1	3.3
70°-80°	177.8	1.7
80°-90°	52.1	0.5
90°-100°	158.5	1.5
100°-110°	462.2	4.4
110°-120°	754.2	7.3
120°-130°	957.1	9.2
130°-140°	1024.1	9.8
140°-150°	956.3	9.2
150°-160°	786.9	7.6
160°-170°	527.7	5.1
170°-180°	187.4	1.8
0°-30°	1538.0	14.8
0°-40°	2526.8	24.3
0°-60°	4009.8	38.6
0°-90°	4585.8	44.1
90°-120°	1374.9	13.2
90°-150°	4312.4	41.5
90°-180°	5814.0	55.9
0°-180°	10400.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1903	1903	1903	1903	1903	
5°	1893	1928	1893	1928	1893	181
15°	1854	1879	1854	1879	1854	521
25°	1707	1870	1707	1870	1707	787
35°	1526	1588	1526	1588	1526	952
45°	1218	954	1218	954	1218	932
55°	789	467	789	467	789	709
65°	434	248	434	248	434	439
75°	219	124	219	124	219	233
85°	46	19	46	19	46	58
90°	6	44	6	86	6	7
95°	62	46	62	272	62	75
105°	294	471	294	648	294	312
115°	563	780	563	962	563	555
125°	833	1237	833	1179	833	745
135°	1132	1619	1132	1306	1132	875
145°	1446	1867	1446	1334	1446	905
155°	1718	2028	1718	1384	1718	790
165°	1899	2114	1899	1593	1899	535
175°	1985	2070	1985	1869	1985	188
180°	1991	1991	1991	1991	1991	

TEST NUMBER: P1428315

CATALOG NUMBER: SQ2W-PR1-K-150U-100D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7
2.5°	1895.0	1905.3	1915.6	1911.0	1901.3	1896.9	1897.5	1898.6	1900.6	1902.7	1900.6
5°	1893.0	1907.7	1922.3	1918.9	1909.4	1905.5	1907.2	1910.7	1919.3	1927.9	1919.3
7.5°	1892.6	1913.5	1934.4	1935.9	1931.1	1931.2	1936.2	1942.8	1954.2	1965.6	1954.2
10°	1891.1	1916.1	1941.1	1944.7	1941.3	1940.0	1940.9	1944.5	1956.6	1968.7	1956.6
12.5°	1881.8	1910.9	1940.0	1937.0	1923.2	1915.7	1914.5	1915.2	1921.8	1928.3	1921.8
15°	1854.2	1888.7	1923.2	1909.2	1879.0	1865.2	1867.8	1870.8	1875.1	1879.4	1875.1
17.5°	1805.7	1841.8	1877.8	1865.2	1836.4	1826.7	1836.0	1845.1	1853.5	1862.0	1853.5
20°	1774.7	1810.0	1845.4	1836.8	1813.5	1807.9	1820.0	1832.7	1847.3	1862.0	1847.3
22.5°	1746.8	1782.1	1817.5	1811.9	1792.8	1791.7	1808.6	1826.3	1846.5	1866.6	1846.5
25°	1706.8	1737.9	1768.9	1769.5	1760.0	1769.5	1798.0	1824.9	1847.3	1869.7	1847.3
27.5°	1664.9	1683.2	1701.5	1713.5	1723.5	1747.8	1786.2	1819.0	1834.7	1850.3	1834.7
30°	1629.2	1641.3	1653.4	1675.8	1701.6	1731.4	1765.0	1791.7	1797.8	1803.8	1797.8
32.5°	1590.4	1597.7	1604.9	1636.5	1676.1	1704.8	1722.6	1734.0	1726.2	1718.5	1726.2
35°	1526.4	1532.5	1538.5	1578.8	1630.5	1649.5	1635.7	1621.3	1604.9	1588.5	1604.9
37.5°	1450.4	1462.8	1475.2	1508.1	1547.7	1547.4	1507.0	1472.1	1453.3	1434.5	1453.3
40°	1394.5	1415.2	1435.9	1457.9	1480.3	1461.4	1401.0	1350.4	1328.8	1307.3	1328.8
42.5°	1326.3	1359.4	1392.5	1397.4	1392.9	1352.2	1275.3	1211.1	1184.7	1158.3	1184.7
45°	1218.0	1262.9	1307.7	1282.1	1232.9	1166.5	1082.9	1012.9	983.6	954.3	983.6
47.5°	1090.4	1136.5	1182.5	1134.1	1054.3	977.1	902.4	839.6	812.2	784.7	812.2
50°	1006.6	1043.7	1080.8	1026.0	940.7	863.1	793.3	733.4	703.2	673.0	703.2
52.5°	921.3	948.0	974.7	920.5	839.3	763.8	694.0	634.8	607.3	579.9	607.3
55°	789.4	803.2	817.0	766.8	695.2	626.3	559.9	505.4	486.4	467.4	486.4
57.5°	668.4	677.2	686.0	638.4	572.0	510.6	454.2	408.5	394.5	380.5	394.5
60°	595.4	601.5	607.5	559.2	492.9	437.7	393.7	358.0	346.8	335.5	346.8
62.5°	528.7	533.4	538.0	491.5	427.9	378.6	343.6	315.2	306.8	298.3	306.8
65°	434.5	438.8	443.1	403.4	349.1	308.6	281.9	260.3	254.3	248.3	254.3
67.5°	359.6	361.8	364.1	331.4	287.1	254.4	233.4	216.2	210.5	204.8	210.5
70°	316.1	317.0	317.9	289.0	250.2	221.3	202.4	187.1	182.8	178.4	182.8
72.5°	277.4	276.2	274.9	249.2	215.2	190.5	174.9	162.6	159.6	156.7	159.6
75°	219.2	216.6	214.0	192.7	165.1	146.1	135.8	127.6	125.9	124.1	125.9
77.5°	163.7	160.9	158.2	140.4	117.7	104.6	101.1	98.5	98.5	98.5	98.5
80°	128.0	124.6	121.1	107.3	90.1	81.5	81.5	81.5	81.5	81.5	81.5
82.5°	95.4	90.6	85.8	77.3	67.7	62.8	62.8	62.7	62.0	61.3	62.0
85°	46.5	42.2	37.9	36.9	36.9	34.3	29.1	24.6	22.0	19.4	22.0
87.5°	13.6	15.2	17.2	16.3	14.0	12.7	12.7	13.1	13.5	13.5	13.5
90°	6.0	14.1	24.1	32.2	38.2	40.2	40.2	42.2	44.3	44.3	44.3
92.5°	22.1	35.0	35.4	35.4	43.0	46.7	49.9	50.3	52.3	52.3	52.3
95°	62.4	68.4	102.6	100.6	68.4	54.3	46.3	46.3	46.3	46.3	46.3
97.5°	119.1	127.9	133.6	179.0	189.1	182.6	148.8	125.1	111.8	105.8	111.8
100°	169.0	173.0	185.1	187.1	237.4	285.6	261.5	231.3	221.3	215.2	221.3
102.5°	218.8	221.3	239.8	248.2	259.9	287.2	370.9	361.7	354.8	353.6	354.8
105°	293.7	295.7	329.9	346.0	354.0	354.0	352.0	392.2	456.6	470.7	456.6
107.5°	373.7	383.0	423.2	466.3	475.5	477.9	467.5	461.4	459.0	460.6	459.0
110°	428.4	442.5	490.8	545.1	559.2	563.2	559.2	553.2	549.1	549.1	549.1



TEST NUMBER: P1428315

CATALOG NUMBER: SQ2W-PR1-K-150U-100D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	481.5	502.1	556.8	619.1	642.9	654.9	646.1	641.7	637.6	640.9	637.6
115°	563.2	593.4	665.8	730.2	778.4	784.5	782.5	782.5	780.5	780.5	780.5
117.5°	638.8	687.1	768.4	843.2	899.1	915.2	923.3	920.9	918.4	922.5	918.4
120°	692.0	748.3	840.8	925.3	979.6	1003.7	1011.8	1007.8	1011.8	1007.8	1011.8
122.5°	748.3	817.5	908.4	996.1	1060.1	1087.4	1097.1	1097.9	1098.7	1096.3	1098.7
125°	832.8	917.2	1023.8	1114.4	1180.7	1212.9	1221.0	1223.0	1227.0	1237.1	1227.0
127.5°	918.0	1013.8	1130.9	1218.2	1286.1	1325.2	1337.6	1342.1	1350.5	1354.9	1350.5
130°	977.6	1086.2	1204.9	1287.3	1353.7	1396.0	1418.1	1424.1	1434.2	1432.2	1434.2
132.5°	1040.3	1153.8	1274.1	1359.8	1421.3	1466.8	1485.7	1503.0	1506.6	1509.4	1506.6
135°	1132.5	1255.2	1375.9	1460.3	1518.7	1562.9	1587.1	1603.2	1613.2	1619.2	1613.2
137.5°	1229.4	1359.0	1474.8	1550.0	1608.8	1647.0	1674.4	1691.3	1701.7	1706.5	1701.7
140°	1295.4	1420.1	1532.8	1611.2	1663.5	1701.7	1725.9	1746.0	1758.0	1758.0	1758.0
142.5°	1358.2	1481.3	1590.7	1669.1	1715.0	1750.0	1775.7	1791.0	1804.7	1804.7	1804.7
145°	1446.3	1569.0	1669.5	1748.0	1786.2	1818.4	1846.5	1858.6	1866.7	1866.7	1866.7
147.5°	1538.4	1647.0	1738.7	1814.0	1846.1	1884.0	1906.1	1915.7	1925.8	1921.4	1925.8
150°	1593.1	1693.7	1782.2	1852.6	1884.8	1921.0	1943.1	1951.1	1961.2	1955.2	1961.2
152.5°	1646.2	1741.9	1822.4	1888.0	1915.3	1951.5	1976.9	1984.9	1991.8	1987.3	1991.8
155°	1717.8	1802.3	1876.7	1937.1	1961.2	1995.4	2019.5	2029.6	2037.6	2027.6	2037.6
157.5°	1781.8	1854.6	1919.4	1974.9	2000.6	2030.0	2052.5	2065.0	2073.0	2068.6	2073.0
160°	1820.4	1886.8	1945.1	1997.4	2021.5	2047.7	2071.8	2085.9	2094.0	2087.9	2094.0
162.5°	1852.6	1912.5	1967.6	2015.1	2036.0	2059.0	2087.9	2100.4	2108.4	2100.8	2108.4
165°	1898.8	1947.1	1995.4	2035.6	2053.7	2071.8	2102.0	2116.1	2122.1	2114.1	2122.1
167.5°	1933.8	1970.9	2009.9	2044.5	2057.7	2075.4	2105.6	2117.3	2124.9	2114.9	2124.9
170°	1953.2	1985.3	2019.5	2047.7	2057.7	2073.8	2104.0	2114.1	2120.1	2110.0	2120.1
172.5°	1969.2	1993.4	2021.1	2046.1	2051.3	2064.2	2092.7	2102.8	2107.2	2098.8	2107.2
175°	1985.3	1999.4	2019.5	2035.6	2033.6	2041.7	2065.8	2073.8	2081.9	2069.8	2081.9
177.5°	1993.0	1999.4	2005.9	2015.5	2009.1	2009.1	2026.8	2031.6	2033.2	2026.8	2033.2
180°	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1428315

CATALOG NUMBER: SQ2W-PR1-K-150U-100D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7
2.5°	1898.6	1897.5	1896.9	1901.3	1911.0	1915.6	1905.3	1895.0	1905.3	1915.6	1911.0
5°	1910.7	1907.2	1905.5	1909.4	1918.9	1922.3	1907.7	1893.0	1907.7	1922.3	1918.9
7.5°	1942.8	1936.2	1931.2	1931.1	1935.9	1934.4	1913.5	1892.6	1913.5	1934.4	1935.9
10°	1944.5	1940.9	1940.0	1941.3	1944.7	1941.1	1916.1	1891.1	1916.1	1941.1	1944.7
12.5°	1915.2	1914.5	1915.7	1923.2	1937.0	1940.0	1910.9	1881.8	1910.9	1940.0	1937.0
15°	1870.8	1867.8	1865.2	1879.0	1909.2	1923.2	1888.7	1854.2	1888.7	1923.2	1909.2
17.5°	1845.1	1836.0	1826.7	1836.4	1865.2	1877.8	1841.8	1805.7	1841.8	1877.8	1865.2
20°	1832.7	1820.0	1807.9	1813.5	1836.8	1845.4	1810.0	1774.7	1810.0	1845.4	1836.8
22.5°	1826.3	1808.6	1791.7	1792.8	1811.9	1817.5	1782.1	1746.8	1782.1	1817.5	1811.9
25°	1824.9	1798.0	1769.5	1760.0	1769.5	1768.9	1737.9	1706.8	1737.9	1768.9	1769.5
27.5°	1819.0	1786.2	1747.8	1723.5	1713.5	1701.5	1683.2	1664.9	1683.2	1701.5	1713.5
30°	1791.7	1765.0	1731.4	1701.6	1675.8	1653.4	1641.3	1629.2	1641.3	1653.4	1675.8
32.5°	1734.0	1722.6	1704.8	1676.1	1636.5	1604.9	1597.7	1590.4	1597.7	1604.9	1636.5
35°	1621.3	1635.7	1649.5	1630.5	1578.8	1538.5	1532.5	1526.4	1532.5	1538.5	1578.8
37.5°	1472.1	1507.0	1547.4	1547.7	1508.1	1475.2	1462.8	1450.4	1462.8	1475.2	1508.1
40°	1350.4	1401.0	1461.4	1480.3	1457.9	1435.9	1415.2	1394.5	1415.2	1435.9	1457.9
42.5°	1211.1	1275.3	1352.2	1392.9	1397.4	1392.5	1359.4	1326.3	1359.4	1392.5	1397.4
45°	1012.9	1082.9	1166.5	1232.9	1282.1	1307.7	1262.9	1218.0	1262.9	1307.7	1282.1
47.5°	839.6	902.4	977.1	1054.3	1134.1	1182.5	1136.5	1090.4	1136.5	1182.5	1134.1
50°	733.4	793.3	863.1	940.7	1026.0	1080.8	1043.7	1006.6	1043.7	1080.8	1026.0
52.5°	634.8	694.0	763.8	839.3	920.5	974.7	948.0	921.3	948.0	974.7	920.5
55°	505.4	559.9	626.3	695.2	766.8	817.0	803.2	789.4	803.2	817.0	766.8
57.5°	408.5	454.2	510.6	572.0	638.4	686.0	677.2	668.4	677.2	686.0	638.4
60°	358.0	393.7	437.7	492.9	559.2	607.5	601.5	595.4	601.5	607.5	559.2
62.5°	315.2	343.6	378.6	427.9	491.5	538.0	533.4	528.7	533.4	538.0	491.5
65°	260.3	281.9	308.6	349.1	403.4	443.1	438.8	434.5	438.8	443.1	403.4
67.5°	216.2	233.4	254.4	287.1	331.4	364.1	361.8	359.6	361.8	364.1	331.4
70°	187.1	202.4	221.3	250.2	289.0	317.9	317.0	316.1	317.0	317.9	289.0
72.5°	162.6	174.9	190.5	215.2	249.2	274.9	276.2	277.4	276.2	274.9	249.2
75°	127.6	135.8	146.1	165.1	192.7	214.0	216.6	219.2	216.6	214.0	192.7
77.5°	98.5	101.1	104.6	117.7	140.4	158.2	160.9	163.7	160.9	158.2	140.4
80°	81.5	81.5	81.5	90.1	107.3	121.1	124.6	128.0	124.6	121.1	107.3
82.5°	62.7	62.8	62.8	67.7	77.3	85.8	90.6	95.4	90.6	85.8	77.3
85°	24.6	29.1	34.3	36.9	36.9	37.9	42.2	46.5	42.2	37.9	36.9
87.5°	13.1	12.7	12.7	14.0	16.3	17.2	15.2	13.6	15.2	16.8	17.1
90°	42.2	40.2	40.2	38.2	32.2	24.1	14.1	6.0	14.1	22.1	36.2
92.5°	50.3	49.9	46.7	43.0	35.4	35.4	35.0	22.1	38.2	54.3	78.0
95°	46.3	46.3	54.3	68.4	100.6	102.6	68.4	62.4	88.5	124.7	156.9
97.5°	125.1	148.8	182.6	189.1	179.0	133.6	127.9	119.1	162.1	197.9	249.8
100°	231.3	261.5	285.6	237.4	187.1	185.1	173.0	169.0	215.2	249.4	299.7
102.5°	361.7	370.9	287.2	259.9	248.2	239.8	221.3	218.8	265.1	312.2	354.4
105°	392.2	352.0	354.0	354.0	346.0	329.9	295.7	293.7	346.0	400.3	452.6
107.5°	461.4	467.5	477.9	475.5	466.3	423.2	383.0	373.7	420.8	486.0	543.5
110°	553.2	559.2	563.2	559.2	545.1	490.8	442.5	428.4	470.7	539.1	601.4



TEST NUMBER: P1428315

CATALOG NUMBER: SQ2W-PR1-K-150U-100D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	641.7	646.1	654.9	642.9	619.1	556.8	502.1	481.5	523.8	593.8	657.8
115°	782.5	782.5	784.5	778.4	730.2	665.8	593.4	563.2	599.4	663.8	734.2
117.5°	920.9	923.3	915.2	899.1	843.2	768.4	687.1	638.8	667.4	735.4	807.8
120°	1007.8	1011.8	1003.7	979.6	925.3	840.8	748.3	692.0	714.1	780.5	852.9
122.5°	1097.9	1097.1	1087.4	1060.1	996.1	908.4	817.5	748.3	757.5	819.1	889.9
125°	1223.0	1221.0	1212.9	1180.7	1114.4	1023.8	917.2	832.8	820.7	873.0	945.4
127.5°	1342.1	1337.6	1325.2	1286.1	1218.2	1130.9	1013.8	918.0	891.1	924.1	990.5
130°	1424.1	1418.1	1396.0	1353.7	1287.3	1204.9	1086.2	977.6	939.4	959.5	1017.8
132.5°	1503.0	1485.7	1466.8	1421.3	1359.8	1274.1	1153.8	1040.3	987.6	996.5	1041.9
135°	1603.2	1587.1	1562.9	1518.7	1460.3	1375.9	1255.2	1132.5	1060.1	1052.0	1078.2
137.5°	1691.3	1674.4	1647.0	1608.8	1550.0	1474.8	1359.0	1229.4	1138.1	1111.1	1121.2
140°	1746.0	1725.9	1701.7	1663.5	1611.2	1532.8	1420.1	1295.4	1192.8	1154.6	1148.6
142.5°	1791.0	1775.7	1750.0	1715.0	1669.1	1590.7	1481.3	1358.2	1249.1	1199.6	1185.6
145°	1858.6	1846.5	1818.4	1786.2	1748.0	1669.5	1569.0	1446.3	1337.6	1273.3	1243.1
147.5°	1915.7	1906.1	1884.0	1846.1	1814.0	1738.7	1647.0	1538.4	1426.9	1347.3	1308.3
150°	1951.1	1943.1	1921.0	1884.8	1852.6	1782.2	1693.7	1593.1	1486.5	1402.0	1351.7
152.5°	1984.9	1976.9	1951.5	1915.3	1888.0	1822.4	1741.9	1646.2	1538.0	1453.5	1401.6
155°	2029.6	2019.5	1995.4	1961.2	1937.1	1876.7	1802.3	1717.8	1625.3	1536.8	1478.4
157.5°	2065.0	2052.5	2030.0	2000.6	1974.9	1919.4	1854.6	1781.8	1700.9	1616.4	1556.9
160°	2085.9	2071.8	2047.7	2021.5	1997.4	1945.1	1886.8	1820.4	1746.0	1669.5	1605.2
162.5°	2100.4	2087.9	2059.0	2036.0	2015.1	1967.6	1912.5	1852.6	1786.2	1719.4	1659.9
165°	2116.1	2102.0	2071.8	2053.7	2035.6	1995.4	1947.1	1898.8	1842.5	1788.2	1739.9
167.5°	2117.3	2105.6	2075.4	2057.7	2044.5	2009.9	1970.9	1933.8	1890.0	1847.3	1807.1
170°	2114.1	2104.0	2073.8	2057.7	2047.7	2019.5	1985.3	1953.2	1919.0	1882.7	1850.6
172.5°	2102.8	2092.7	2064.2	2051.3	2046.1	2021.1	1993.4	1969.2	1939.9	1913.3	1887.6
175°	2073.8	2065.8	2041.7	2033.6	2035.6	2019.5	1999.4	1985.3	1967.2	1951.1	1937.1
177.5°	2031.6	2026.8	2009.1	2009.1	2015.5	2005.9	1999.4	1993.0	1984.9	1980.1	1975.3
180°	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1428315

CATALOG NUMBER: SQ2W-PR1-K-150U-100D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7	1902.7
2.5°	1901.3	1896.9	1897.5	1898.6	1900.6	1902.7	1900.6	1898.6	1897.5	1896.9	1901.3
5°	1909.4	1905.5	1907.2	1910.7	1919.3	1927.9	1919.3	1910.7	1907.2	1905.5	1909.4
7.5°	1931.1	1931.2	1936.2	1942.8	1954.2	1965.6	1954.2	1942.8	1936.2	1931.2	1931.1
10°	1941.3	1940.0	1940.9	1944.5	1956.6	1968.7	1956.6	1944.5	1940.9	1940.0	1941.3
12.5°	1923.2	1915.7	1914.5	1915.2	1921.8	1928.3	1921.8	1915.2	1914.5	1915.7	1923.2
15°	1879.0	1865.2	1867.8	1870.8	1875.1	1879.4	1875.1	1870.8	1867.8	1865.2	1879.0
17.5°	1836.4	1826.7	1836.0	1845.1	1853.5	1862.0	1853.5	1845.1	1836.0	1826.7	1836.4
20°	1813.5	1807.9	1820.0	1832.7	1847.3	1862.0	1847.3	1832.7	1820.0	1807.9	1813.5
22.5°	1792.8	1791.7	1808.6	1826.3	1846.5	1866.6	1846.5	1826.3	1808.6	1791.7	1792.8
25°	1760.0	1769.5	1798.0	1824.9	1847.3	1869.7	1847.3	1824.9	1798.0	1769.5	1760.0
27.5°	1723.5	1747.8	1786.2	1819.0	1834.7	1850.3	1834.7	1819.0	1786.2	1747.8	1723.5
30°	1701.6	1731.4	1765.0	1791.7	1797.8	1803.8	1797.8	1791.7	1765.0	1731.4	1701.6
32.5°	1676.1	1704.8	1722.6	1734.0	1726.2	1718.5	1726.2	1734.0	1722.6	1704.8	1676.1
35°	1630.5	1649.5	1635.7	1621.3	1604.9	1588.5	1604.9	1621.3	1635.7	1649.5	1630.5
37.5°	1547.7	1547.4	1507.0	1472.1	1453.3	1434.5	1453.3	1472.1	1507.0	1547.4	1547.7
40°	1480.3	1461.4	1401.0	1350.4	1328.8	1307.3	1328.8	1350.4	1401.0	1461.4	1480.3
42.5°	1392.9	1352.2	1275.3	1211.1	1184.7	1158.3	1184.7	1211.1	1275.3	1352.2	1392.9
45°	1232.9	1166.5	1082.9	1012.9	983.6	954.3	983.6	1012.9	1082.9	1166.5	1232.9
47.5°	1054.3	977.1	902.4	839.6	812.2	784.7	812.2	839.6	902.4	977.1	1054.3
50°	940.7	863.1	793.3	733.4	703.2	673.0	703.2	733.4	793.3	863.1	940.7
52.5°	839.3	763.8	694.0	634.8	607.3	579.9	607.3	634.8	694.0	763.8	839.3
55°	695.2	626.3	559.9	505.4	486.4	467.4	486.4	505.4	559.9	626.3	695.2
57.5°	572.0	510.6	454.2	408.5	394.5	380.5	394.5	408.5	454.2	510.6	572.0
60°	492.9	437.7	393.7	358.0	346.8	335.5	346.8	358.0	393.7	437.7	492.9
62.5°	427.9	378.6	343.6	315.2	306.8	298.3	306.8	315.2	343.6	378.6	427.9
65°	349.1	308.6	281.9	260.3	254.3	248.3	254.3	260.3	281.9	308.6	349.1
67.5°	287.1	254.4	233.4	216.2	210.5	204.8	210.5	216.2	233.4	254.4	287.1
70°	250.2	221.3	202.4	187.1	182.8	178.4	182.8	187.1	202.4	221.3	250.2
72.5°	215.2	190.5	174.9	162.6	159.6	156.7	159.6	162.6	174.9	190.5	215.2
75°	165.1	146.1	135.8	127.6	125.9	124.1	125.9	127.6	135.8	146.1	165.1
77.5°	117.7	104.6	101.1	98.5	98.5	98.5	98.5	98.5	101.1	104.6	117.7
80°	90.1	81.5	81.5	81.5	81.5	81.5	81.5	81.5	81.5	81.5	90.1
82.5°	67.7	62.8	62.8	62.7	62.0	61.3	62.0	62.7	62.8	62.8	67.7
85°	36.9	34.3	29.1	24.6	22.0	19.4	22.0	24.6	29.1	34.3	36.9
87.5°	15.6	16.7	19.5	21.1	22.8	22.0	22.8	21.1	19.5	16.7	15.6
90°	46.3	60.3	74.4	82.5	90.5	86.5	90.5	82.5	74.4	60.3	46.3
92.5°	92.9	116.7	134.0	148.4	154.9	154.1	154.9	148.4	134.0	116.7	92.9
95°	187.1	215.2	243.4	263.5	275.6	271.6	275.6	263.5	243.4	215.2	187.1
97.5°	288.4	326.3	357.6	376.5	388.6	396.7	388.6	376.5	357.6	326.3	288.4
100°	356.0	392.2	428.4	450.6	470.7	478.7	470.7	450.6	428.4	392.2	356.0
102.5°	410.7	458.2	497.6	521.4	538.3	546.3	538.3	521.4	497.6	458.2	410.7
105°	500.9	551.1	593.4	623.6	641.7	647.7	641.7	623.6	593.4	551.1	500.9
107.5°	591.0	642.9	681.9	715.3	737.4	750.3	737.4	715.3	681.9	642.9	591.0
110°	661.8	704.0	746.3	776.4	798.6	806.6	798.6	776.4	746.3	704.0	661.8



TEST NUMBER: P1428315

CATALOG NUMBER: SQ2W-PR1-K-150U-100D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	721.3	768.4	810.6	840.8	866.1	877.4	866.1	840.8	810.6	768.4	721.3
115°	804.6	866.9	905.2	933.3	951.4	961.5	951.4	933.3	905.2	866.9	804.6
117.5°	873.8	939.0	980.8	1002.5	1011.0	1018.2	1011.0	1002.5	980.8	939.0	873.8
120°	917.2	977.6	1025.9	1054.0	1064.1	1068.1	1064.1	1054.0	1025.9	977.6	917.2
122.5°	957.5	1014.6	1061.3	1095.9	1112.4	1116.4	1112.4	1095.9	1061.3	1014.6	957.5
125°	1013.8	1068.1	1116.4	1150.6	1168.7	1178.7	1168.7	1150.6	1116.4	1068.1	1013.8
127.5°	1062.9	1121.6	1165.9	1196.8	1214.5	1222.6	1214.5	1196.8	1165.9	1121.6	1062.9
130°	1090.2	1150.6	1194.8	1229.0	1245.1	1253.2	1245.1	1229.0	1194.8	1150.6	1090.2
132.5°	1111.1	1174.7	1220.6	1251.5	1269.2	1277.3	1269.2	1251.5	1220.6	1174.7	1111.1
135°	1136.5	1202.9	1251.1	1281.3	1297.4	1305.5	1297.4	1281.3	1251.1	1202.9	1136.5
137.5°	1158.6	1219.0	1269.2	1301.0	1315.5	1320.7	1315.5	1301.0	1269.2	1219.0	1158.6
140°	1174.7	1227.0	1277.3	1307.5	1323.6	1325.6	1323.6	1307.5	1277.3	1227.0	1174.7
142.5°	1195.6	1236.7	1280.5	1310.7	1326.8	1330.4	1326.8	1310.7	1280.5	1236.7	1195.6
145°	1233.0	1257.2	1287.3	1315.5	1329.6	1333.6	1329.6	1315.5	1287.3	1257.2	1233.0
147.5°	1280.1	1287.8	1303.4	1321.9	1335.6	1338.4	1335.6	1321.9	1303.4	1287.8	1280.1
150°	1315.5	1313.5	1319.5	1331.6	1343.7	1341.7	1343.7	1331.6	1319.5	1313.5	1315.5
152.5°	1355.7	1344.1	1343.7	1349.3	1354.9	1354.5	1354.9	1349.3	1343.7	1344.1	1355.7
155°	1424.1	1402.0	1389.9	1385.9	1385.9	1383.9	1385.9	1385.9	1389.9	1402.0	1424.1
157.5°	1499.4	1468.4	1450.3	1440.6	1437.8	1433.4	1437.8	1440.6	1450.3	1468.4	1499.4
160°	1550.9	1516.7	1498.6	1482.5	1476.4	1470.4	1476.4	1482.5	1498.6	1516.7	1550.9
162.5°	1599.1	1566.5	1546.8	1532.3	1526.3	1517.1	1526.3	1532.3	1546.8	1566.5	1599.1
165°	1677.6	1643.4	1621.3	1609.2	1601.1	1593.1	1601.1	1609.2	1621.3	1643.4	1677.6
167.5°	1756.0	1718.6	1704.1	1690.5	1682.8	1668.3	1682.8	1690.5	1704.1	1718.6	1756.0
170°	1804.3	1770.1	1762.1	1750.0	1735.9	1719.8	1735.9	1750.0	1762.1	1770.1	1804.3
172.5°	1846.1	1823.2	1815.2	1803.1	1798.7	1785.8	1798.7	1803.1	1815.2	1823.2	1846.1
175°	1906.9	1888.8	1888.8	1886.8	1880.7	1868.7	1880.7	1886.8	1888.8	1888.8	1906.9
177.5°	1957.6	1947.9	1954.4	1954.4	1952.7	1941.5	1952.7	1954.4	1954.4	1947.9	1957.6
180°	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1428315

CATALOG NUMBER: SQ2W-PR1-K-150U-100D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	1902.7	1902.7	1902.7	1902.7
2.5°	1911.0	1915.6	1905.3	1895.0
5°	1918.9	1922.3	1907.7	1893.0
7.5°	1935.9	1934.4	1913.5	1892.6
10°	1944.7	1941.1	1916.1	1891.1
12.5°	1937.0	1940.0	1910.9	1881.8
15°	1909.2	1923.2	1888.7	1854.2
17.5°	1865.2	1877.8	1841.8	1805.7
20°	1836.8	1845.4	1810.0	1774.7
22.5°	1811.9	1817.5	1782.1	1746.8
25°	1769.5	1768.9	1737.9	1706.8
27.5°	1713.5	1701.5	1683.2	1664.9
30°	1675.8	1653.4	1641.3	1629.2
32.5°	1636.5	1604.9	1597.7	1590.4
35°	1578.8	1538.5	1532.5	1526.4
37.5°	1508.1	1475.2	1462.8	1450.4
40°	1457.9	1435.9	1415.2	1394.5
42.5°	1397.4	1392.5	1359.4	1326.3
45°	1282.1	1307.7	1262.9	1218.0
47.5°	1134.1	1182.5	1136.5	1090.4
50°	1026.0	1080.8	1043.7	1006.6
52.5°	920.5	974.7	948.0	921.3
55°	766.8	817.0	803.2	789.4
57.5°	638.4	686.0	677.2	668.4
60°	559.2	607.5	601.5	595.4
62.5°	491.5	538.0	533.4	528.7
65°	403.4	443.1	438.8	434.5
67.5°	331.4	364.1	361.8	359.6
70°	289.0	317.9	317.0	316.1
72.5°	249.2	274.9	276.2	277.4
75°	192.7	214.0	216.6	219.2
77.5°	140.4	158.2	160.9	163.7
80°	107.3	121.1	124.6	128.0
82.5°	77.3	85.8	90.6	95.4
85°	36.9	37.9	42.2	46.5
87.5°	17.1	16.8	15.2	13.6
90°	36.2	22.1	14.1	6.0
92.5°	78.0	54.3	38.2	22.1
95°	156.9	124.7	88.5	62.4
97.5°	249.8	197.9	162.1	119.1
100°	299.7	249.4	215.2	169.0
102.5°	354.4	312.2	265.1	218.8
105°	452.6	400.3	346.0	293.7
107.5°	543.5	486.0	420.8	373.7
110°	601.4	539.1	470.7	428.4



TEST NUMBER: P1428315

CATALOG NUMBER: SQ2W-PR1-K-150U-100D-L935-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	657.8	593.8	523.8	481.5
115°	734.2	663.8	599.4	563.2
117.5°	807.8	735.4	667.4	638.8
120°	852.9	780.5	714.1	692.0
122.5°	889.9	819.1	757.5	748.3
125°	945.4	873.0	820.7	832.8
127.5°	990.5	924.1	891.1	918.0
130°	1017.8	959.5	939.4	977.6
132.5°	1041.9	996.5	987.6	1040.3
135°	1078.2	1052.0	1060.1	1132.5
137.5°	1121.2	1111.1	1138.1	1229.4
140°	1148.6	1154.6	1192.8	1295.4
142.5°	1185.6	1199.6	1249.1	1358.2
145°	1243.1	1273.3	1337.6	1446.3
147.5°	1308.3	1347.3	1426.9	1538.4
150°	1351.7	1402.0	1486.5	1593.1
152.5°	1401.6	1453.5	1538.0	1646.2
155°	1478.4	1536.8	1625.3	1717.8
157.5°	1556.9	1616.4	1700.9	1781.8
160°	1605.2	1669.5	1746.0	1820.4
162.5°	1659.9	1719.4	1786.2	1852.6
165°	1739.9	1788.2	1842.5	1898.8
167.5°	1807.1	1847.3	1890.0	1933.8
170°	1850.6	1882.7	1919.0	1953.2
172.5°	1887.6	1913.3	1939.9	1969.2
175°	1937.1	1951.1	1967.2	1985.3
177.5°	1975.3	1980.1	1984.9	1993.0
180°	1991.4	1991.4	1991.4	1991.4



TEST NUMBER: P1428315  
 CATALOG NUMBER: SQ2W-PR1-K-150U-100D-L935-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.99	18.77	19.00	19.78	21.14	14.36	15.14	15.37	16.15	17.51
	3H	19.19	19.88	20.22	20.91	22.29	15.51	16.21	16.54	17.24	18.61
	4H	19.67	20.33	20.71	21.36	22.74	15.97	16.63	17.01	17.66	19.04
	6H	19.96	20.57	21.01	21.60	23.00	16.31	16.92	17.36	17.95	19.35
	8H	20.07	20.64	21.12	21.69	23.08	16.45	17.02	17.50	18.07	19.46
	12H	20.10	20.65	21.16	21.69	23.11	16.48	17.02	17.53	18.06	19.48
4H	2H	18.08	18.74	19.13	19.77	21.15	15.06	15.72	16.10	16.75	18.13
	3H	19.54	20.08	20.59	21.14	22.54	16.41	16.95	17.46	18.01	19.41
	4H	20.16	20.66	21.22	21.71	23.13	16.95	17.45	18.01	18.50	19.92
	6H	20.59	21.01	21.66	22.09	23.50	17.38	17.81	18.45	18.88	20.29
	8H	20.75	21.14	21.81	22.21	23.64	17.56	17.96	18.63	19.02	20.45
	12H	20.81	21.17	21.89	22.25	23.68	17.60	17.96	18.69	19.04	20.48
8H	4H	20.18	20.58	21.25	21.64	23.07	17.27	17.67	18.34	18.73	20.16
	6H	20.71	21.04	21.80	22.15	23.57	17.81	18.14	18.90	19.24	20.67
	8H	20.94	21.23	22.04	22.32	23.77	18.07	18.36	19.17	19.45	20.90
	12H	21.06	21.31	22.16	22.40	23.89	18.16	18.42	19.26	19.50	20.99
12H	4H	20.14	20.50	21.22	21.57	23.01	17.29	17.65	18.37	18.73	20.16
	6H	20.70	20.99	21.80	22.08	23.53	17.88	18.17	18.98	19.26	20.71
	8H	20.95	21.20	22.05	22.29	23.77	18.17	18.42	19.27	19.51	20.99