

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428516

Luminaire Tested: SQ2W-WBM-K-050U-050D-L935-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428516
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2104-222-6)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-WBM-K-050U-050D-L935-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - WHITE DISCREET BAFFLE, MEDIUM 80-DEGREE OPTIC
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4095.7 lumens
Efficiency: N/A
Efficacy: 124.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.18 / 1.17
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 33
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428516

CATALOG NUMBER: SQ2W-WBM-K-050U-050D-L935-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428516

CATALOG NUMBER: SQ2W-WBM-K-050U-050D-L935-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54				
1	100	97	94	91	93	90	87	85	78	76	74	66	65	64	55	55	54	49				
2	93	87	82	78	86	81	77	73	70	67	65	61	58	56	51	50	49	44				
3	86	78	72	67	80	73	68	64	64	60	57	55	53	50	47	45	44	40				
4	80	71	64	59	75	67	61	56	58	54	50	51	48	45	44	42	40	36				
5	74	64	57	52	69	60	54	50	53	49	45	47	43	40	41	38	36	33				
6	69	59	51	46	65	55	49	44	49	44	40	43	39	36	38	35	33	30				
7	65	54	46	41	60	51	44	40	45	40	36	40	36	33	35	32	30	27				
8	60	49	42	37	56	47	40	36	42	37	33	37	33	30	32	30	27	25				
9	56	45	38	34	53	43	37	33	38	34	30	34	30	28	30	27	25	23				
10	53	42	35	31	50	40	34	30	36	31	28	32	28	25	28	25	23	21				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	22630	22630	22630	22630
5°	22836	22825	22836	22825
10°	23066	23056	23066	23056
15°	23450	23035	23450	23035
20°	23561	22661	23561	22661
25°	23077	22024	23077	22024
30°	21897	20593	21897	20593
35°	19692	18581	19692	18581
40°	16145	15293	16145	15293
45°	10095	9480	10095	9480
50°	3949	3612	3949	3612
55°	1948	1928	1948	1928
60°	911	823	911	823
65°	821	772	821	772
70°	793	760	793	760
75°	798	711	798	711
80°	753	688	753	688
85°	741	630	741	630

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°
 Vertical Angle: 45°
 Luminance: 11490 cd/sqm



TEST NUMBER: P1428516

CATALOG NUMBER: SQ2W-WBM-K-050U-050D-L935-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.0	3.3
10°-20°	391.8	9.6
20°-30°	579.4	14.1
30°-40°	599.4	14.6
40°-50°	360.6	8.8
50°-60°	86.2	2.1
60°-70°	23.6	0.6
70°-80°	13.2	0.3
80°-90°	6.9	0.2
90°-100°	51.8	1.3
100°-110°	151.1	3.7
110°-120°	246.5	6.0
120°-130°	312.9	7.6
130°-140°	334.8	8.2
140°-150°	312.6	7.6
150°-160°	257.2	6.3
160°-170°	172.5	4.2
170°-180°	61.3	1.5
0°-30°	1105.2	27.0
0°-40°	1704.7	41.6
0°-60°	2151.4	52.5
0°-90°	2195.1	53.6
90°-120°	449.4	11.0
90°-150°	1409.7	34.4
90°-180°	1901.0	46.4
0°-180°	4095.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1402	1402	1402	1402	1402	
5°	1409	1408	1409	1408	1409	134
15°	1403	1378	1403	1378	1403	395
25°	1295	1236	1295	1236	1295	592
35°	999	943	999	943	999	613
45°	442	415	442	415	442	342
55°	69	68	69	68	69	69
65°	22	20	22	20	22	22
75°	13	11	13	11	13	13
85°	4	3	4	3	4	4
90°	2	14	2	28	2	2
95°	20	15	20	89	20	25
105°	96	154	96	212	96	102
115°	184	255	184	314	184	181
125°	272	404	272	385	272	244
135°	370	529	370	427	370	286
145°	473	610	473	436	473	296
155°	562	663	562	452	562	258
165°	621	691	621	521	621	175
175°	649	677	649	611	649	62
180°	651	651	651	651	651	



TEST NUMBER: P1428516

CATALOG NUMBER: SQ2W-WBM-K-050U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1401.6	1401.6	1401.6	1401.6	1401.6	1401.6	1401.6	1401.6	1401.6	1401.6	1401.6
2.5°	1408.6	1406.9	1405.2	1401.0	1396.0	1396.1	1401.4	1405.0	1403.8	1402.6	1403.8
5°	1409.0	1406.9	1404.8	1400.0	1394.3	1395.7	1404.0	1410.1	1409.2	1408.3	1409.2
7.5°	1407.5	1406.6	1405.7	1402.2	1397.8	1398.8	1405.2	1409.6	1408.2	1406.8	1408.2
10°	1406.9	1407.2	1407.5	1402.9	1396.6	1396.8	1403.4	1408.1	1407.2	1406.3	1407.2
12.5°	1406.4	1408.9	1411.3	1405.1	1395.9	1393.9	1399.1	1402.4	1400.3	1398.2	1400.3
15°	1402.9	1407.7	1412.5	1404.0	1391.2	1384.8	1384.8	1384.0	1381.0	1378.1	1381.0
17.5°	1388.0	1393.7	1399.3	1387.9	1370.8	1359.9	1355.3	1350.9	1347.3	1343.7	1347.3
20°	1371.3	1377.0	1382.7	1369.1	1349.1	1335.3	1327.9	1321.9	1320.4	1318.9	1320.4
22.5°	1345.0	1351.1	1357.3	1342.8	1321.3	1306.5	1298.3	1291.6	1289.1	1286.7	1289.1
25°	1295.4	1300.2	1305.0	1289.8	1268.0	1254.1	1248.2	1242.9	1239.6	1236.3	1239.6
27.5°	1229.3	1231.9	1234.6	1219.9	1199.5	1185.8	1179.0	1172.8	1168.3	1163.7	1168.3
30°	1174.5	1175.7	1176.9	1165.1	1148.9	1136.4	1127.4	1118.9	1111.8	1104.6	1111.8
32.5°	1109.4	1110.6	1111.8	1101.5	1087.2	1075.9	1067.4	1059.6	1053.9	1048.2	1053.9
35°	999.1	998.5	997.9	991.3	982.6	973.3	963.5	954.6	948.6	942.7	948.6
37.5°	861.1	861.9	862.8	857.8	851.0	843.6	835.9	828.5	822.5	816.5	822.5
40°	766.0	766.6	767.2	763.0	757.4	748.9	737.5	728.6	727.1	725.6	727.1
42.5°	649.9	658.8	667.8	664.1	656.3	648.0	639.3	631.0	624.1	617.1	624.1
45°	442.1	469.3	496.5	503.2	503.2	498.0	487.6	472.6	443.9	415.2	443.9
47.5°	249.7	280.6	311.5	331.9	348.7	341.5	310.5	278.5	243.6	208.8	243.6
50°	157.2	178.1	199.0	225.1	252.9	245.2	202.2	167.1	155.4	143.8	155.4
52.5°	111.5	122.2	132.8	157.4	186.6	183.0	146.7	117.9	111.8	105.6	111.8
55°	69.2	73.1	77.0	88.9	103.5	102.7	86.2	73.3	70.9	68.5	70.9
57.5°	41.1	45.1	49.1	54.4	60.2	60.2	54.4	49.2	45.4	41.7	45.4
60°	28.2	31.5	34.8	39.2	44.0	43.4	37.4	32.1	28.8	25.5	28.8
62.5°	24.5	25.8	27.2	30.6	34.7	34.3	29.5	25.7	24.5	23.4	24.5
65°	21.5	21.8	22.1	22.4	22.7	22.5	21.9	21.4	20.8	20.2	20.8
67.5°	18.9	19.2	19.5	19.4	19.2	19.1	19.0	18.8	18.3	17.7	18.3
70°	16.8	17.1	17.4	17.5	17.5	17.3	17.0	16.7	16.4	16.1	16.4
72.5°	15.2	15.5	15.8	15.7	15.4	15.3	15.2	15.1	14.5	14.0	14.5
75°	12.8	12.8	12.8	12.8	12.8	12.6	12.3	12.0	11.7	11.4	11.7
77.5°	9.7	10.0	10.3	10.1	9.8	9.7	9.7	9.6	9.3	9.0	9.3
80°	8.1	8.4	8.7	8.5	8.2	8.1	8.1	8.0	7.7	7.4	7.7
82.5°	6.5	6.5	6.6	6.5	6.5	6.5	6.5	6.4	6.1	5.8	6.1
85°	4.0	4.0	4.0	3.8	3.5	3.4	3.4	3.4	3.4	3.4	3.4
87.5°	1.5	2.2	3.1	3.5	3.7	3.7	3.7	3.8	4.0	4.0	4.0
90°	2.0	4.6	7.9	10.5	12.5	13.2	13.2	13.8	14.5	14.5	14.5
92.5°	7.2	11.4	11.6	11.6	14.1	15.3	16.3	16.4	17.1	17.1	17.1
95°	20.4	22.4	33.5	32.9	22.4	17.8	15.1	15.1	15.1	15.1	15.1
97.5°	38.9	41.8	43.7	58.5	61.8	59.7	48.7	40.9	36.6	34.6	36.6
100°	55.2	56.5	60.5	61.1	77.6	93.4	85.5	75.6	72.3	70.4	72.3
102.5°	71.5	72.3	78.4	81.1	85.0	93.9	121.2	118.2	116.0	115.6	116.0
105°	96.0	96.7	107.8	113.1	115.7	115.7	115.1	128.2	149.3	153.9	149.3
107.5°	122.2	125.2	138.3	152.4	155.4	156.2	152.8	150.8	150.0	150.6	150.0
110°	140.1	144.7	160.4	178.2	182.8	184.1	182.8	180.8	179.5	179.5	179.5



TEST NUMBER: P1428516

CATALOG NUMBER: SQ2W-WBM-K-050U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	157.4	164.1	182.0	202.4	210.1	214.1	211.2	209.8	208.4	209.5	208.4
115°	184.1	194.0	217.6	238.7	254.5	256.4	255.8	255.8	255.1	255.1	255.1
117.5°	208.8	224.6	251.2	275.6	293.9	299.2	301.8	301.0	300.2	301.5	300.2
120°	226.2	244.6	274.8	302.5	320.2	328.1	330.7	329.4	330.7	329.4	330.7
122.5°	244.6	267.2	296.9	325.6	346.5	355.5	358.6	358.9	359.1	358.4	359.1
125°	272.2	299.8	334.7	364.3	386.0	396.5	399.1	399.8	401.1	404.4	401.1
127.5°	300.1	331.4	369.7	398.2	420.4	433.2	437.3	438.7	441.5	442.9	441.5
130°	319.6	355.1	393.9	420.8	442.5	456.3	463.6	465.5	468.8	468.2	468.8
132.5°	340.1	377.2	416.5	444.5	464.6	479.5	485.6	491.3	492.5	493.4	492.5
135°	370.2	410.3	449.7	477.4	496.4	510.9	518.8	524.0	527.3	529.3	527.3
137.5°	401.9	444.2	482.1	506.7	525.9	538.4	547.3	552.8	556.3	557.8	556.3
140°	423.4	464.2	501.0	526.7	543.8	556.3	564.2	570.7	574.7	574.7	574.7
142.5°	444.0	484.2	520.0	545.6	560.6	572.0	580.5	585.5	589.9	589.9	589.9
145°	472.8	512.9	545.7	571.4	583.9	594.4	603.6	607.6	610.2	610.2	610.2
147.5°	502.9	538.4	568.4	593.0	603.5	615.8	623.1	626.2	629.5	628.1	629.5
150°	520.8	553.6	582.6	605.6	616.1	627.9	635.2	637.8	641.1	639.1	641.1
152.5°	538.1	569.4	595.7	617.2	626.1	637.9	646.2	648.8	651.1	649.6	651.1
155°	561.5	589.1	613.5	633.2	641.1	652.3	660.2	663.4	666.1	662.8	666.1
157.5°	582.4	606.2	627.4	645.6	654.0	663.6	670.9	675.0	677.6	676.2	677.6
160°	595.1	616.8	635.8	652.9	660.8	669.4	677.3	681.9	684.5	682.5	684.5
162.5°	605.6	625.2	643.2	658.7	665.5	673.0	682.5	686.6	689.2	686.7	689.2
165°	620.7	636.5	652.3	665.4	671.3	677.3	687.1	691.7	693.7	691.1	693.7
167.5°	632.1	644.2	657.0	668.3	672.6	678.4	688.3	692.1	694.6	691.3	694.6
170°	638.5	649.0	660.2	669.4	672.6	677.9	687.8	691.1	693.0	689.7	693.0
172.5°	643.7	651.6	660.7	668.8	670.5	674.8	684.1	687.4	688.8	686.1	688.8
175°	649.0	653.6	660.2	665.4	664.8	667.4	675.3	677.9	680.5	676.6	680.5
177.5°	651.5	653.6	655.7	658.8	656.7	656.7	662.5	664.1	664.6	662.5	664.6
180°	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9



TEST NUMBER: P1428516

CATALOG NUMBER: SQ2W-WBM-K-050U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1401.6	1401.6	1401.6	1401.6	1401.6	1401.6	1401.6	1401.6	1401.6	1401.6	1401.6
2.5°	1405.0	1401.4	1396.1	1396.0	1401.0	1405.2	1406.9	1408.6	1406.9	1405.2	1401.0
5°	1410.1	1404.0	1395.7	1394.3	1400.0	1404.8	1406.9	1409.0	1406.9	1404.8	1400.0
7.5°	1409.6	1405.2	1398.8	1397.8	1402.2	1405.7	1406.6	1407.5	1406.6	1405.7	1402.2
10°	1408.1	1403.4	1396.8	1396.6	1402.9	1407.5	1407.2	1406.9	1407.2	1407.5	1402.9
12.5°	1402.4	1399.1	1393.9	1395.9	1405.1	1411.3	1408.9	1406.4	1408.9	1411.3	1405.1
15°	1384.0	1384.8	1384.8	1391.2	1404.0	1412.5	1407.7	1402.9	1407.7	1412.5	1404.0
17.5°	1350.9	1355.3	1359.9	1370.8	1387.9	1399.3	1393.7	1388.0	1393.7	1399.3	1387.9
20°	1321.9	1327.9	1335.3	1349.1	1369.1	1382.7	1377.0	1371.3	1377.0	1382.7	1369.1
22.5°	1291.6	1298.3	1306.5	1321.3	1342.8	1357.3	1351.1	1345.0	1351.1	1357.3	1342.8
25°	1242.9	1248.2	1254.1	1268.0	1289.8	1305.0	1300.2	1295.4	1300.2	1305.0	1289.8
27.5°	1172.8	1179.0	1185.8	1199.5	1219.9	1234.6	1231.9	1229.3	1231.9	1234.6	1219.9
30°	1118.9	1127.4	1136.4	1148.9	1165.1	1176.9	1175.7	1174.5	1175.7	1176.9	1165.1
32.5°	1059.6	1067.4	1075.9	1087.2	1101.5	1111.8	1110.6	1109.4	1110.6	1111.8	1101.5
35°	954.6	963.5	973.3	982.6	991.3	997.9	998.5	999.1	998.5	997.9	991.3
37.5°	828.5	835.9	843.6	851.0	857.8	862.8	861.9	861.1	861.9	862.8	857.8
40°	728.6	737.5	748.9	757.4	763.0	767.2	766.6	766.0	766.6	767.2	763.0
42.5°	631.0	639.3	648.0	656.3	664.1	667.8	658.8	649.9	658.8	667.8	664.1
45°	472.6	487.6	498.0	503.2	503.2	496.5	469.3	442.1	469.3	496.5	503.2
47.5°	278.5	310.5	341.5	348.7	331.9	311.5	280.6	249.7	280.6	311.5	331.9
50°	167.1	202.2	245.2	252.9	225.1	199.0	178.1	157.2	178.1	199.0	225.1
52.5°	117.9	146.7	183.0	186.6	157.4	132.8	122.2	111.5	122.2	132.8	157.4
55°	73.3	86.2	102.7	103.5	88.9	77.0	73.1	69.2	73.1	77.0	88.9
57.5°	49.2	54.4	60.2	60.2	54.4	49.1	45.1	41.1	45.1	49.1	54.4
60°	32.1	37.4	43.4	44.0	39.2	34.8	31.5	28.2	31.5	34.8	39.2
62.5°	25.7	29.5	34.3	34.7	30.6	27.2	25.8	24.5	25.8	27.2	30.6
65°	21.4	21.9	22.5	22.7	22.4	22.1	21.8	21.5	21.8	22.1	22.4
67.5°	18.8	19.0	19.1	19.2	19.4	19.5	19.2	18.9	19.2	19.5	19.4
70°	16.7	17.0	17.3	17.5	17.5	17.4	17.1	16.8	17.1	17.4	17.5
72.5°	15.1	15.2	15.3	15.4	15.7	15.8	15.5	15.2	15.5	15.8	15.7
75°	12.0	12.3	12.6	12.8	12.8	12.8	12.8	12.8	12.8	12.8	12.8
77.5°	9.6	9.7	9.7	9.8	10.1	10.3	10.0	9.7	10.0	10.3	10.1
80°	8.0	8.1	8.1	8.2	8.5	8.7	8.4	8.1	8.4	8.7	8.5
82.5°	6.4	6.5	6.5	6.5	6.5	6.6	6.5	6.5	6.5	6.6	6.5
85°	3.4	3.4	3.4	3.5	3.8	4.0	4.0	4.0	4.0	4.0	3.8
87.5°	3.8	3.7	3.7	3.7	3.5	3.1	2.2	1.5	2.2	3.0	3.8
90°	13.8	13.2	13.2	12.5	10.5	7.9	4.6	2.0	4.6	7.2	11.8
92.5°	16.4	16.3	15.3	14.1	11.6	11.6	11.4	7.2	12.5	17.8	25.5
95°	15.1	15.1	17.8	22.4	32.9	33.5	22.4	20.4	28.9	40.8	51.3
97.5°	40.9	48.7	59.7	61.8	58.5	43.7	41.8	38.9	53.0	64.7	81.7
100°	75.6	85.5	93.4	77.6	61.1	60.5	56.5	55.2	70.4	81.5	98.0
102.5°	118.2	121.2	93.9	85.0	81.1	78.4	72.3	71.5	86.7	102.0	115.9
105°	128.2	115.1	115.7	115.7	113.1	107.8	96.7	96.0	113.1	130.8	147.9
107.5°	150.8	152.8	156.2	155.4	152.4	138.3	125.2	122.2	137.6	158.9	177.7
110°	180.8	182.8	184.1	182.8	178.2	160.4	144.7	140.1	153.9	176.2	196.6



TEST NUMBER: P1428516

CATALOG NUMBER: SQ2W-WBM-K-050U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	209.8	211.2	214.1	210.1	202.4	182.0	164.1	157.4	171.2	194.1	215.0
115°	255.8	255.8	256.4	254.5	238.7	217.6	194.0	184.1	195.9	217.0	240.0
117.5°	301.0	301.8	299.2	293.9	275.6	251.2	224.6	208.8	218.2	240.4	264.1
120°	329.4	330.7	328.1	320.2	302.5	274.8	244.6	226.2	233.4	255.1	278.8
122.5°	358.9	358.6	355.5	346.5	325.6	296.9	267.2	244.6	247.6	267.7	290.9
125°	399.8	399.1	396.5	386.0	364.3	334.7	299.8	272.2	268.3	285.4	309.0
127.5°	438.7	437.3	433.2	420.4	398.2	369.7	331.4	300.1	291.3	302.1	323.8
130°	465.5	463.6	456.3	442.5	420.8	393.9	355.1	319.6	307.1	313.6	332.7
132.5°	491.3	485.6	479.5	464.6	444.5	416.5	377.2	340.1	322.8	325.7	340.6
135°	524.0	518.8	510.9	496.4	477.4	449.7	410.3	370.2	346.5	343.9	352.4
137.5°	552.8	547.3	538.4	525.9	506.7	482.1	444.2	401.9	372.0	363.2	366.5
140°	570.7	564.2	556.3	543.8	526.7	501.0	464.2	423.4	389.9	377.4	375.4
142.5°	585.5	580.5	572.0	560.6	545.6	520.0	484.2	444.0	408.3	392.1	387.5
145°	607.6	603.6	594.4	583.9	571.4	545.7	512.9	472.8	437.3	416.2	406.4
147.5°	626.2	623.1	615.8	603.5	593.0	568.4	538.4	502.9	466.4	440.4	427.7
150°	637.8	635.2	627.9	616.1	605.6	582.6	553.6	520.8	485.9	458.3	441.9
152.5°	648.8	646.2	637.9	626.1	617.2	595.7	569.4	538.1	502.7	475.1	458.2
155°	663.4	660.2	652.3	641.1	633.2	613.5	589.1	561.5	531.3	502.3	483.3
157.5°	675.0	670.9	663.6	654.0	645.6	627.4	606.2	582.4	556.0	528.4	508.9
160°	681.9	677.3	669.4	660.8	652.9	635.8	616.8	595.1	570.7	545.7	524.7
162.5°	686.6	682.5	673.0	665.5	658.7	643.2	625.2	605.6	583.9	562.1	542.6
165°	691.7	687.1	677.3	671.3	665.4	652.3	636.5	620.7	602.3	584.5	568.8
167.5°	692.1	688.3	678.4	672.6	668.3	657.0	644.2	632.1	617.8	603.9	590.7
170°	691.1	687.8	677.9	672.6	669.4	660.2	649.0	638.5	627.3	615.4	604.9
172.5°	687.4	684.1	674.8	670.5	668.8	660.7	651.6	643.7	634.1	625.4	617.0
175°	677.9	675.3	667.4	664.8	665.4	660.2	653.6	649.0	643.1	637.8	633.2
177.5°	664.1	662.5	656.7	656.7	658.8	655.7	653.6	651.5	648.8	647.3	645.7
180°	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9



TEST NUMBER: P1428516

CATALOG NUMBER: SQ2W-WBM-K-050U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1401.6	1401.6	1401.6	1401.6	1401.6	1401.6	1401.6	1401.6	1401.6	1401.6	1401.6
2.5°	1396.0	1396.1	1401.4	1405.0	1403.8	1402.6	1403.8	1405.0	1401.4	1396.1	1396.0
5°	1394.3	1395.7	1404.0	1410.1	1409.2	1408.3	1409.2	1410.1	1404.0	1395.7	1394.3
7.5°	1397.8	1398.8	1405.2	1409.6	1408.2	1406.8	1408.2	1409.6	1405.2	1398.8	1397.8
10°	1396.6	1396.8	1403.4	1408.1	1407.2	1406.3	1407.2	1408.1	1403.4	1396.8	1396.6
12.5°	1395.9	1393.9	1399.1	1402.4	1400.3	1398.2	1400.3	1402.4	1399.1	1393.9	1395.9
15°	1391.2	1384.8	1384.8	1384.0	1381.0	1378.1	1381.0	1384.0	1384.8	1384.8	1391.2
17.5°	1370.8	1359.9	1355.3	1350.9	1347.3	1343.7	1347.3	1350.9	1355.3	1359.9	1370.8
20°	1349.1	1335.3	1327.9	1321.9	1320.4	1318.9	1320.4	1321.9	1327.9	1335.3	1349.1
22.5°	1321.3	1306.5	1298.3	1291.6	1289.1	1286.7	1289.1	1291.6	1298.3	1306.5	1321.3
25°	1268.0	1254.1	1248.2	1242.9	1239.6	1236.3	1239.6	1242.9	1248.2	1254.1	1268.0
27.5°	1199.5	1185.8	1179.0	1172.8	1168.3	1163.7	1168.3	1172.8	1179.0	1185.8	1199.5
30°	1148.9	1136.4	1127.4	1118.9	1111.8	1104.6	1111.8	1118.9	1127.4	1136.4	1148.9
32.5°	1087.2	1075.9	1067.4	1059.6	1053.9	1048.2	1053.9	1059.6	1067.4	1075.9	1087.2
35°	982.6	973.3	963.5	954.6	948.6	942.7	948.6	954.6	963.5	973.3	982.6
37.5°	851.0	843.6	835.9	828.5	822.5	816.5	822.5	828.5	835.9	843.6	851.0
40°	757.4	748.9	737.5	728.6	727.1	725.6	727.1	728.6	737.5	748.9	757.4
42.5°	656.3	648.0	639.3	631.0	624.1	617.1	624.1	631.0	639.3	648.0	656.3
45°	503.2	498.0	487.6	472.6	443.9	415.2	443.9	472.6	487.6	498.0	503.2
47.5°	348.7	341.5	310.5	278.5	243.6	208.8	243.6	278.5	310.5	341.5	348.7
50°	252.9	245.2	202.2	167.1	155.4	143.8	155.4	167.1	202.2	245.2	252.9
52.5°	186.6	183.0	146.7	117.9	111.8	105.6	111.8	117.9	146.7	183.0	186.6
55°	103.5	102.7	86.2	73.3	70.9	68.5	70.9	73.3	86.2	102.7	103.5
57.5°	60.2	60.2	54.4	49.2	45.4	41.7	45.4	49.2	54.4	60.2	60.2
60°	44.0	43.4	37.4	32.1	28.8	25.5	28.8	32.1	37.4	43.4	44.0
62.5°	34.7	34.3	29.5	25.7	24.5	23.4	24.5	25.7	29.5	34.3	34.7
65°	22.7	22.5	21.9	21.4	20.8	20.2	20.8	21.4	21.9	22.5	22.7
67.5°	19.2	19.1	19.0	18.8	18.3	17.7	18.3	18.8	19.0	19.1	19.2
70°	17.5	17.3	17.0	16.7	16.4	16.1	16.4	16.7	17.0	17.3	17.5
72.5°	15.4	15.3	15.2	15.1	14.5	14.0	14.5	15.1	15.2	15.3	15.4
75°	12.8	12.6	12.3	12.0	11.7	11.4	11.7	12.0	12.3	12.6	12.8
77.5°	9.8	9.7	9.7	9.6	9.3	9.0	9.3	9.6	9.7	9.7	9.8
80°	8.2	8.1	8.1	8.0	7.7	7.4	7.7	8.0	8.1	8.1	8.2
82.5°	6.5	6.5	6.5	6.4	6.1	5.8	6.1	6.4	6.5	6.5	6.5
85°	3.5	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.5
87.5°	4.2	5.0	5.9	6.5	7.0	6.7	7.0	6.5	5.9	5.0	4.2
90°	15.1	19.7	24.3	27.0	29.6	28.3	29.6	27.0	24.3	19.7	15.1
92.5°	30.4	38.1	43.8	48.5	50.6	50.4	50.6	48.5	43.8	38.1	30.4
95°	61.1	70.4	79.6	86.1	90.1	88.8	90.1	86.1	79.6	70.4	61.1
97.5°	94.3	106.7	116.9	123.1	127.0	129.7	127.0	123.1	116.9	106.7	94.3
100°	116.4	128.2	140.1	147.3	153.9	156.5	153.9	147.3	140.1	128.2	116.4
102.5°	134.3	149.8	162.7	170.4	176.0	178.6	176.0	170.4	162.7	149.8	134.3
105°	163.7	180.2	194.0	203.8	209.8	211.7	209.8	203.8	194.0	180.2	163.7
107.5°	193.2	210.1	222.9	233.8	241.0	245.3	241.0	233.8	222.9	210.1	193.2
110°	216.3	230.1	243.9	253.8	261.0	263.7	261.0	253.8	243.9	230.1	216.3



TEST NUMBER: P1428516

CATALOG NUMBER: SQ2W-WBM-K-050U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	235.8	251.2	265.0	274.8	283.1	286.8	283.1	274.8	265.0	251.2	235.8
115°	263.0	283.4	295.9	305.1	311.0	314.3	311.0	305.1	295.9	283.4	263.0
117.5°	285.6	306.9	320.6	327.7	330.5	332.8	330.5	327.7	320.6	306.9	285.6
120°	299.8	319.6	335.3	344.5	347.8	349.1	347.8	344.5	335.3	319.6	299.8
122.5°	313.0	331.7	346.9	358.2	363.6	364.9	363.6	358.2	346.9	331.7	313.0
125°	331.4	349.1	364.9	376.1	382.0	385.3	382.0	376.1	364.9	349.1	331.4
127.5°	347.4	366.6	381.1	391.2	397.0	399.6	397.0	391.2	381.1	366.6	347.4
130°	356.4	376.1	390.6	401.7	407.0	409.6	407.0	401.7	390.6	376.1	356.4
132.5°	363.2	384.0	399.0	409.1	414.9	417.5	414.9	409.1	399.0	384.0	363.2
135°	371.5	393.2	409.0	418.8	424.1	426.7	424.1	418.8	409.0	393.2	371.5
137.5°	378.7	398.5	414.9	425.3	430.0	431.7	430.0	425.3	414.9	398.5	378.7
140°	384.0	401.1	417.5	427.4	432.7	433.3	432.7	427.4	417.5	401.1	384.0
142.5°	390.8	404.2	418.6	428.4	433.7	434.9	433.7	428.4	418.6	404.2	390.8
145°	403.1	411.0	420.8	430.0	434.6	435.9	434.6	430.0	420.8	411.0	403.1
147.5°	418.4	420.9	426.1	432.1	436.6	437.5	436.6	432.1	426.1	420.9	418.4
150°	430.0	429.4	431.3	435.3	439.2	438.6	439.2	435.3	431.3	429.4	430.0
152.5°	443.2	439.4	439.2	441.1	442.9	442.8	442.9	441.1	439.2	439.4	443.2
155°	465.5	458.3	454.3	453.0	453.0	452.4	453.0	453.0	454.3	458.3	465.5
157.5°	490.1	480.0	474.1	470.9	470.0	468.6	470.0	470.9	474.1	480.0	490.1
160°	507.0	495.8	489.9	484.6	482.6	480.7	482.6	484.6	489.9	495.8	507.0
162.5°	522.7	512.1	505.6	500.9	498.9	495.9	498.9	500.9	505.6	512.1	522.7
165°	548.4	537.2	530.0	526.0	523.4	520.8	523.4	526.0	530.0	537.2	548.4
167.5°	574.0	561.8	557.1	552.6	550.1	545.4	550.1	552.6	557.1	561.8	574.0
170°	589.8	578.6	576.0	572.0	567.4	562.2	567.4	572.0	576.0	578.6	589.8
172.5°	603.5	596.0	593.4	589.4	588.0	583.8	588.0	589.4	593.4	596.0	603.5
175°	623.3	617.4	617.4	616.8	614.8	610.8	614.8	616.8	617.4	617.4	623.3
177.5°	639.9	636.7	638.9	638.9	638.3	634.6	638.3	638.9	638.9	636.7	639.9
180°	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9



TEST NUMBER: P1428516

CATALOG NUMBER: SQ2W-WBM-K-050U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1401.6	1401.6	1401.6	1401.6
2.5°	1401.0	1405.2	1406.9	1408.6
5°	1400.0	1404.8	1406.9	1409.0
7.5°	1402.2	1405.7	1406.6	1407.5
10°	1402.9	1407.5	1407.2	1406.9
12.5°	1405.1	1411.3	1408.9	1406.4
15°	1404.0	1412.5	1407.7	1402.9
17.5°	1387.9	1399.3	1393.7	1388.0
20°	1369.1	1382.7	1377.0	1371.3
22.5°	1342.8	1357.3	1351.1	1345.0
25°	1289.8	1305.0	1300.2	1295.4
27.5°	1219.9	1234.6	1231.9	1229.3
30°	1165.1	1176.9	1175.7	1174.5
32.5°	1101.5	1111.8	1110.6	1109.4
35°	991.3	997.9	998.5	999.1
37.5°	857.8	862.8	861.9	861.1
40°	763.0	767.2	766.6	766.0
42.5°	664.1	667.8	658.8	649.9
45°	503.2	496.5	469.3	442.1
47.5°	331.9	311.5	280.6	249.7
50°	225.1	199.0	178.1	157.2
52.5°	157.4	132.8	122.2	111.5
55°	88.9	77.0	73.1	69.2
57.5°	54.4	49.1	45.1	41.1
60°	39.2	34.8	31.5	28.2
62.5°	30.6	27.2	25.8	24.5
65°	22.4	22.1	21.8	21.5
67.5°	19.4	19.5	19.2	18.9
70°	17.5	17.4	17.1	16.8
72.5°	15.7	15.8	15.5	15.2
75°	12.8	12.8	12.8	12.8
77.5°	10.1	10.3	10.0	9.7
80°	8.5	8.7	8.4	8.1
82.5°	6.5	6.6	6.5	6.5
85°	3.8	4.0	4.0	4.0
87.5°	3.8	3.0	2.2	1.5
90°	11.8	7.2	4.6	2.0
92.5°	25.5	17.8	12.5	7.2
95°	51.3	40.8	28.9	20.4
97.5°	81.7	64.7	53.0	38.9
100°	98.0	81.5	70.4	55.2
102.5°	115.9	102.0	86.7	71.5
105°	147.9	130.8	113.1	96.0
107.5°	177.7	158.9	137.6	122.2
110°	196.6	176.2	153.9	140.1

TEST NUMBER: P1428516

CATALOG NUMBER: SQ2W-WBM-K-050U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	215.0	194.1	171.2	157.4
115°	240.0	217.0	195.9	184.1
117.5°	264.1	240.4	218.2	208.8
120°	278.8	255.1	233.4	226.2
122.5°	290.9	267.7	247.6	244.6
125°	309.0	285.4	268.3	272.2
127.5°	323.8	302.1	291.3	300.1
130°	332.7	313.6	307.1	319.6
132.5°	340.6	325.7	322.8	340.1
135°	352.4	343.9	346.5	370.2
137.5°	366.5	363.2	372.0	401.9
140°	375.4	377.4	389.9	423.4
142.5°	387.5	392.1	408.3	444.0
145°	406.4	416.2	437.3	472.8
147.5°	427.7	440.4	466.4	502.9
150°	441.9	458.3	485.9	520.8
152.5°	458.2	475.1	502.7	538.1
155°	483.3	502.3	531.3	561.5
157.5°	508.9	528.4	556.0	582.4
160°	524.7	545.7	570.7	595.1
162.5°	542.6	562.1	583.9	605.6
165°	568.8	584.5	602.3	620.7
167.5°	590.7	603.9	617.8	632.1
170°	604.9	615.4	627.3	638.5
172.5°	617.0	625.4	634.1	643.7
175°	633.2	637.8	643.1	649.0
177.5°	645.7	647.3	648.8	651.5
180°	650.9	650.9	650.9	650.9



TEST NUMBER: P1428516
 CATALOG NUMBER: SQ2W-WBM-K-050U-050D-L935-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.10	3.84	4.06	4.79	6.02	3.09	3.83	4.05	4.78	6.01
	3H	3.79	4.44	4.76	5.40	6.66	3.71	4.37	4.68	5.33	6.58
	4H	4.15	4.77	5.14	5.73	7.00	4.02	4.63	5.00	5.60	6.86
	6H	4.43	4.99	5.42	5.96	7.24	4.25	4.81	5.24	5.78	7.06
	8H	4.55	5.08	5.55	6.07	7.34	4.35	4.88	5.34	5.87	7.14
	12H	4.62	5.13	5.63	6.11	7.40	4.40	4.91	5.40	5.88	7.18
4H	2H	3.19	3.81	4.18	4.77	6.04	3.18	3.80	4.17	4.76	6.03
	3H	4.13	4.64	5.13	5.64	6.91	4.05	4.56	5.05	5.55	6.83
	4H	4.64	5.10	5.64	6.09	7.39	4.49	4.95	5.50	5.94	7.24
	6H	5.07	5.47	6.09	6.48	7.78	4.87	5.26	5.88	6.27	7.57
	8H	5.26	5.63	6.28	6.63	7.94	5.04	5.40	6.05	6.41	7.72
	12H	5.39	5.72	6.42	6.74	8.05	5.13	5.46	6.16	6.48	7.79
8H	4H	4.76	5.13	5.77	6.13	7.44	4.62	4.99	5.64	5.99	7.31
	6H	5.34	5.64	6.37	6.68	7.99	5.14	5.44	6.18	6.49	7.80
	8H	5.63	5.89	6.67	6.93	8.26	5.41	5.68	6.46	6.71	8.04
	12H	5.84	6.08	6.89	7.10	8.48	5.59	5.82	6.63	6.84	8.22
12H	4H	4.74	5.07	5.77	6.09	7.40	4.61	4.94	5.64	5.96	7.27
	6H	5.37	5.64	6.42	6.67	8.00	5.19	5.45	6.23	6.49	7.82
	8H	5.70	5.93	6.74	6.96	8.33	5.49	5.73	6.54	6.75	8.13