

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428519

Luminaire Tested: SQ2W-WBM-K-050U-075D-L935-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428519
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2104-222-6)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-WBM-K-050U-075D-L935-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - WHITE DISCREET BAFFLE, MEDIUM 80-DEGREE OPTIC
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5166.3 lumens
Efficiency: N/A
Efficacy: 121.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.18 / 1.17
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 42.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428519

CATALOG NUMBER: SQ2W-WBM-K-050U-075D-L935-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428519

CATALOG NUMBER: SQ2W-WBM-K-050U-075D-L935-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	63				
1	103	99	96	93	97	94	91	89	83	81	79	73	72	70	64	63	62	58				
2	96	90	85	80	90	85	80	77	76	72	69	67	65	63	59	57	56	52				
3	89	81	75	70	84	77	71	67	69	65	61	62	58	56	55	52	51	47				
4	83	74	67	62	78	70	64	59	63	58	55	57	53	50	51	48	46	43				
5	77	67	60	55	73	64	57	53	58	53	49	52	48	45	47	44	42	39				
6	72	61	54	49	68	58	52	47	53	48	44	48	44	41	43	40	38	35				
7	67	56	49	44	63	54	47	43	49	44	40	45	40	37	40	37	35	32				
8	63	52	45	40	59	49	43	39	45	40	36	41	37	34	38	34	32	30				
9	59	48	41	36	56	46	39	35	42	37	33	38	34	31	35	32	29	27				
10	55	44	38	33	52	42	36	32	39	34	30	36	32	29	33	29	27	25				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	33680	33680	33680	33680
5°	33987	33970	33987	33970
10°	34330	34314	34330	34314
15°	34901	34283	34901	34283
20°	35068	33728	35068	33728
25°	34347	32779	34347	32779
30°	32588	30650	32588	30650
35°	29309	27653	29309	27653
40°	24027	22763	24027	22763
45°	15024	14111	15024	14111
50°	5878	5375	5878	5375
55°	2899	2871	2899	2871
60°	1356	1227	1356	1227
65°	1223	1146	1223	1146
70°	1180	1133	1180	1133
75°	1185	1060	1185	1060
80°	1116	1023	1116	1023
85°	1111	926	1111	926

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°
 Vertical Angle: 45°
 Luminance: 17102 cd/sqm



TEST NUMBER: P1428519

CATALOG NUMBER: SQ2W-WBM-K-050U-075D-L935-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	199.4	3.9
10°-20°	583.2	11.3
20°-30°	862.3	16.7
30°-40°	892.2	17.3
40°-50°	536.6	10.4
50°-60°	128.3	2.5
60°-70°	35.1	0.7
70°-80°	19.6	0.4
80°-90°	8.9	0.2
90°-100°	51.8	1.0
100°-110°	151.1	2.9
110°-120°	246.5	4.8
120°-130°	312.9	6.1
130°-140°	334.8	6.5
140°-150°	312.6	6.1
150°-160°	257.2	5.0
160°-170°	172.5	3.3
170°-180°	61.3	1.2
0°-30°	1644.9	31.8
0°-40°	2537.1	49.1
0°-60°	3202.0	62.0
0°-90°	3265.6	63.2
90°-120°	449.4	8.7
90°-150°	1409.7	27.3
90°-180°	1901.0	36.8
0°-180°	5166.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2086	2086	2086	2086	2086	
5°	2097	2096	2097	2096	2097	200
15°	2088	2051	2088	2051	2088	588
25°	1928	1840	1928	1840	1928	881
35°	1487	1403	1487	1403	1487	913
45°	658	618	658	618	658	509
55°	103	102	103	102	103	103
65°	32	30	32	30	32	32
75°	19	17	19	17	19	20
85°	6	5	6	5	6	6
90°	2	14	2	28	2	2
95°	20	15	20	89	20	25
105°	96	154	96	212	96	102
115°	184	255	184	314	184	181
125°	272	404	272	385	272	244
135°	370	529	370	427	370	286
145°	473	610	473	436	473	296
155°	562	663	562	452	562	258
165°	621	691	621	521	621	175
175°	649	677	649	611	649	62
180°	651	651	651	651	651	



TEST NUMBER: P1428519

CATALOG NUMBER: SQ2W-WBM-K-050U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2086.0	2086.0	2086.0	2086.0	2086.0	2086.0	2086.0	2086.0	2086.0	2086.0	2086.0
2.5°	2096.4	2093.9	2091.4	2085.2	2077.7	2077.9	2085.7	2091.2	2089.4	2087.6	2089.4
5°	2097.0	2093.9	2090.8	2083.7	2075.2	2077.2	2089.7	2098.7	2097.3	2096.0	2097.3
7.5°	2094.8	2093.5	2092.1	2086.9	2080.4	2081.9	2091.3	2097.9	2095.8	2093.8	2095.8
10°	2094.0	2094.4	2094.9	2088.0	2078.7	2078.9	2088.7	2095.7	2094.3	2093.0	2094.3
12.5°	2093.2	2096.8	2100.5	2091.2	2077.6	2074.6	2082.3	2087.2	2084.1	2081.0	2084.1
15°	2088.0	2095.1	2102.2	2089.7	2070.6	2061.0	2061.0	2059.9	2055.4	2051.0	2055.4
17.5°	2065.8	2074.2	2082.7	2065.7	2040.2	2024.0	2017.1	2010.6	2005.2	1999.8	2005.2
20°	2041.0	2049.4	2057.9	2037.7	2007.9	1987.4	1976.3	1967.4	1965.2	1963.0	1965.2
22.5°	2001.8	2011.0	2020.1	1998.5	1966.6	1944.5	1932.3	1922.3	1918.6	1915.0	1918.6
25°	1928.0	1935.1	1942.2	1919.7	1887.2	1866.6	1857.7	1849.8	1844.9	1840.0	1844.9
27.5°	1829.6	1833.5	1837.4	1815.6	1785.2	1764.9	1754.8	1745.5	1738.8	1732.0	1738.8
30°	1748.0	1749.8	1751.6	1734.0	1710.0	1691.3	1678.0	1665.3	1654.7	1644.0	1654.7
32.5°	1651.2	1653.0	1654.8	1639.3	1618.2	1601.3	1588.7	1577.1	1568.5	1560.0	1568.5
35°	1487.0	1486.1	1485.2	1475.3	1462.4	1448.7	1434.0	1420.8	1411.9	1403.0	1411.9
37.5°	1281.6	1282.8	1284.1	1276.7	1266.5	1255.6	1244.1	1233.2	1224.2	1215.2	1224.2
40°	1140.0	1140.9	1141.8	1135.7	1127.2	1114.6	1097.7	1084.4	1082.2	1080.0	1082.2
42.5°	967.2	980.5	993.9	988.5	976.8	964.5	951.5	939.2	928.8	918.4	928.8
45°	658.0	698.4	738.9	749.0	749.0	741.2	725.7	703.3	660.7	618.0	660.7
47.5°	371.6	417.6	463.7	493.9	518.9	508.3	462.1	414.4	362.6	310.8	362.6
50°	234.0	265.1	296.2	335.0	376.3	365.0	301.0	248.7	231.3	214.0	231.3
52.5°	166.0	181.8	197.6	234.2	277.7	272.4	218.3	175.5	166.4	157.2	166.4
55°	103.0	108.8	114.6	132.3	154.1	152.8	128.3	109.1	105.6	102.0	105.6
57.5°	61.2	67.2	73.1	81.0	89.5	89.5	81.0	73.2	67.6	62.0	67.6
60°	42.0	46.9	51.8	58.3	65.4	64.6	55.7	47.8	42.9	38.0	42.9
62.5°	36.4	38.4	40.5	45.5	51.6	51.0	43.9	38.2	36.5	34.8	36.5
65°	32.0	32.4	32.9	33.3	33.8	33.6	32.7	31.8	30.9	30.0	30.9
67.5°	28.2	28.6	29.1	28.9	28.6	28.4	28.3	28.0	27.2	26.4	27.2
70°	25.0	25.4	25.9	26.0	26.0	25.8	25.3	24.9	24.4	24.0	24.4
72.5°	22.6	23.0	23.5	23.3	23.0	22.8	22.7	22.4	21.6	20.8	21.6
75°	19.0	19.0	19.0	19.0	19.0	18.8	18.3	17.9	17.4	17.0	17.4
77.5°	14.4	14.8	15.3	15.1	14.6	14.4	14.4	14.3	13.8	13.4	13.8
80°	12.0	12.4	12.9	12.7	12.2	12.0	12.0	11.9	11.4	11.0	11.4
82.5°	9.6	9.7	9.8	9.7	9.6	9.6	9.6	9.5	9.0	8.6	9.0
85°	6.0	6.0	6.0	5.7	5.2	5.0	5.0	5.0	5.0	5.0	5.0
87.5°	2.0	2.9	3.9	4.2	4.3	4.2	4.2	4.4	4.5	4.5	4.5
90°	2.0	4.6	7.9	10.5	12.5	13.2	13.2	13.8	14.5	14.5	14.5
92.5°	7.2	11.4	11.6	11.6	14.1	15.3	16.3	16.4	17.1	17.1	17.1
95°	20.4	22.4	33.5	32.9	22.4	17.8	15.1	15.1	15.1	15.1	15.1
97.5°	38.9	41.8	43.7	58.5	61.8	59.7	48.7	40.9	36.6	34.6	36.6
100°	55.2	56.5	60.5	61.1	77.6	93.4	85.5	75.6	72.3	70.4	72.3
102.5°	71.5	72.3	78.4	81.1	85.0	93.9	121.2	118.2	116.0	115.6	116.0
105°	96.0	96.7	107.8	113.1	115.7	115.7	115.1	128.2	149.3	153.9	149.3
107.5°	122.2	125.2	138.3	152.4	155.4	156.2	152.8	150.8	150.0	150.6	150.0
110°	140.1	144.7	160.4	178.2	182.8	184.1	182.8	180.8	179.5	179.5	179.5



TEST NUMBER: P1428519

CATALOG NUMBER: SQ2W-WBM-K-050U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	157.4	164.1	182.0	202.4	210.1	214.1	211.2	209.8	208.4	209.5	208.4
115°	184.1	194.0	217.6	238.7	254.5	256.4	255.8	255.8	255.1	255.1	255.1
117.5°	208.8	224.6	251.2	275.6	293.9	299.2	301.8	301.0	300.2	301.5	300.2
120°	226.2	244.6	274.8	302.5	320.2	328.1	330.7	329.4	330.7	329.4	330.7
122.5°	244.6	267.2	296.9	325.6	346.5	355.5	358.6	358.9	359.1	358.4	359.1
125°	272.2	299.8	334.7	364.3	386.0	396.5	399.1	399.8	401.1	404.4	401.1
127.5°	300.1	331.4	369.7	398.2	420.4	433.2	437.3	438.7	441.5	442.9	441.5
130°	319.6	355.1	393.9	420.8	442.5	456.3	463.6	465.5	468.8	468.2	468.8
132.5°	340.1	377.2	416.5	444.5	464.6	479.5	485.6	491.3	492.5	493.4	492.5
135°	370.2	410.3	449.7	477.4	496.4	510.9	518.8	524.0	527.3	529.3	527.3
137.5°	401.9	444.2	482.1	506.7	525.9	538.4	547.3	552.8	556.3	557.8	556.3
140°	423.4	464.2	501.0	526.7	543.8	556.3	564.2	570.7	574.7	574.7	574.7
142.5°	444.0	484.2	520.0	545.6	560.6	572.0	580.5	585.5	589.9	589.9	589.9
145°	472.8	512.9	545.7	571.4	583.9	594.4	603.6	607.6	610.2	610.2	610.2
147.5°	502.9	538.4	568.4	593.0	603.5	615.8	623.1	626.2	629.5	628.1	629.5
150°	520.8	553.6	582.6	605.6	616.1	627.9	635.2	637.8	641.1	639.1	641.1
152.5°	538.1	569.4	595.7	617.2	626.1	637.9	646.2	648.8	651.1	649.6	651.1
155°	561.5	589.1	613.5	633.2	641.1	652.3	660.2	663.4	666.1	662.8	666.1
157.5°	582.4	606.2	627.4	645.6	654.0	663.6	670.9	675.0	677.6	676.2	677.6
160°	595.1	616.8	635.8	652.9	660.8	669.4	677.3	681.9	684.5	682.5	684.5
162.5°	605.6	625.2	643.2	658.7	665.5	673.0	682.5	686.6	689.2	686.7	689.2
165°	620.7	636.5	652.3	665.4	671.3	677.3	687.1	691.7	693.7	691.1	693.7
167.5°	632.1	644.2	657.0	668.3	672.6	678.4	688.3	692.1	694.6	691.3	694.6
170°	638.5	649.0	660.2	669.4	672.6	677.9	687.8	691.1	693.0	689.7	693.0
172.5°	643.7	651.6	660.7	668.8	670.5	674.8	684.1	687.4	688.8	686.1	688.8
175°	649.0	653.6	660.2	665.4	664.8	667.4	675.3	677.9	680.5	676.6	680.5
177.5°	651.5	653.6	655.7	658.8	656.7	656.7	662.5	664.1	664.6	662.5	664.6
180°	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9



TEST NUMBER: P1428519

CATALOG NUMBER: SQ2W-WBM-K-050U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2086.0	2086.0	2086.0	2086.0	2086.0	2086.0	2086.0	2086.0	2086.0	2086.0	2086.0
2.5°	2091.2	2085.7	2077.9	2077.7	2085.2	2091.4	2093.9	2096.4	2093.9	2091.4	2085.2
5°	2098.7	2089.7	2077.2	2075.2	2083.7	2090.8	2093.9	2097.0	2093.9	2090.8	2083.7
7.5°	2097.9	2091.3	2081.9	2080.4	2086.9	2092.1	2093.5	2094.8	2093.5	2092.1	2086.9
10°	2095.7	2088.7	2078.9	2078.7	2088.0	2094.9	2094.4	2094.0	2094.4	2094.9	2088.0
12.5°	2087.2	2082.3	2074.6	2077.6	2091.2	2100.5	2096.8	2093.2	2096.8	2100.5	2091.2
15°	2059.9	2061.0	2061.0	2070.6	2089.7	2102.2	2095.1	2088.0	2095.1	2102.2	2089.7
17.5°	2010.6	2017.1	2024.0	2040.2	2065.7	2082.7	2074.2	2065.8	2074.2	2082.7	2065.7
20°	1967.4	1976.3	1987.4	2007.9	2037.7	2057.9	2049.4	2041.0	2049.4	2057.9	2037.7
22.5°	1922.3	1932.3	1944.5	1966.6	1998.5	2020.1	2011.0	2001.8	2011.0	2020.1	1998.5
25°	1849.8	1857.7	1866.6	1887.2	1919.7	1942.2	1935.1	1928.0	1935.1	1942.2	1919.7
27.5°	1745.5	1754.8	1764.9	1785.2	1815.6	1837.4	1833.5	1829.6	1833.5	1837.4	1815.6
30°	1665.3	1678.0	1691.3	1710.0	1734.0	1751.6	1749.8	1748.0	1749.8	1751.6	1734.0
32.5°	1577.1	1588.7	1601.3	1618.2	1639.3	1654.8	1653.0	1651.2	1653.0	1654.8	1639.3
35°	1420.8	1434.0	1448.7	1462.4	1475.3	1485.2	1486.1	1487.0	1486.1	1485.2	1475.3
37.5°	1233.2	1244.1	1255.6	1266.5	1276.7	1284.1	1282.8	1281.6	1282.8	1284.1	1276.7
40°	1084.4	1097.7	1114.6	1127.2	1135.7	1141.8	1140.9	1140.0	1140.9	1141.8	1135.7
42.5°	939.2	951.5	964.5	976.8	988.5	993.9	980.5	967.2	980.5	993.9	988.5
45°	703.3	725.7	741.2	749.0	749.0	738.9	698.4	658.0	698.4	738.9	749.0
47.5°	414.4	462.1	508.3	518.9	493.9	463.7	417.6	371.6	417.6	463.7	493.9
50°	248.7	301.0	365.0	376.3	335.0	296.2	265.1	234.0	265.1	296.2	335.0
52.5°	175.5	218.3	272.4	277.7	234.2	197.6	181.8	166.0	181.8	197.6	234.2
55°	109.1	128.3	152.8	154.1	132.3	114.6	108.8	103.0	108.8	114.6	132.3
57.5°	73.2	81.0	89.5	89.5	81.0	73.1	67.2	61.2	67.2	73.1	81.0
60°	47.8	55.7	64.6	65.4	58.3	51.8	46.9	42.0	46.9	51.8	58.3
62.5°	38.2	43.9	51.0	51.6	45.5	40.5	38.4	36.4	38.4	40.5	45.5
65°	31.8	32.7	33.6	33.8	33.3	32.9	32.4	32.0	32.4	32.9	33.3
67.5°	28.0	28.3	28.4	28.6	28.9	29.1	28.6	28.2	28.6	29.1	28.9
70°	24.9	25.3	25.8	26.0	26.0	25.9	25.4	25.0	25.4	25.9	26.0
72.5°	22.4	22.7	22.8	23.0	23.3	23.5	23.0	22.6	23.0	23.5	23.3
75°	17.9	18.3	18.8	19.0	19.0	19.0	19.0	19.0	19.0	19.0	19.0
77.5°	14.3	14.4	14.4	14.6	15.1	15.3	14.8	14.4	14.8	15.3	15.1
80°	11.9	12.0	12.0	12.2	12.7	12.9	12.4	12.0	12.4	12.9	12.7
82.5°	9.5	9.6	9.6	9.6	9.7	9.8	9.7	9.6	9.7	9.8	9.7
85°	5.0	5.0	5.0	5.2	5.7	6.0	6.0	6.0	6.0	6.0	5.7
87.5°	4.4	4.2	4.2	4.3	4.2	3.9	2.9	2.0	2.9	3.8	4.5
90°	13.8	13.2	13.2	12.5	10.5	7.9	4.6	2.0	4.6	7.2	11.8
92.5°	16.4	16.3	15.3	14.1	11.6	11.6	11.4	7.2	12.5	17.8	25.5
95°	15.1	15.1	17.8	22.4	32.9	33.5	22.4	20.4	28.9	40.8	51.3
97.5°	40.9	48.7	59.7	61.8	58.5	43.7	41.8	38.9	53.0	64.7	81.7
100°	75.6	85.5	93.4	77.6	61.1	60.5	56.5	55.2	70.4	81.5	98.0
102.5°	118.2	121.2	93.9	85.0	81.1	78.4	72.3	71.5	86.7	102.0	115.9
105°	128.2	115.1	115.7	115.7	113.1	107.8	96.7	96.0	113.1	130.8	147.9
107.5°	150.8	152.8	156.2	155.4	152.4	138.3	125.2	122.2	137.6	158.9	177.7
110°	180.8	182.8	184.1	182.8	178.2	160.4	144.7	140.1	153.9	176.2	196.6



TEST NUMBER: P1428519

CATALOG NUMBER: SQ2W-WBM-K-050U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	209.8	211.2	214.1	210.1	202.4	182.0	164.1	157.4	171.2	194.1	215.0
115°	255.8	255.8	256.4	254.5	238.7	217.6	194.0	184.1	195.9	217.0	240.0
117.5°	301.0	301.8	299.2	293.9	275.6	251.2	224.6	208.8	218.2	240.4	264.1
120°	329.4	330.7	328.1	320.2	302.5	274.8	244.6	226.2	233.4	255.1	278.8
122.5°	358.9	358.6	355.5	346.5	325.6	296.9	267.2	244.6	247.6	267.7	290.9
125°	399.8	399.1	396.5	386.0	364.3	334.7	299.8	272.2	268.3	285.4	309.0
127.5°	438.7	437.3	433.2	420.4	398.2	369.7	331.4	300.1	291.3	302.1	323.8
130°	465.5	463.6	456.3	442.5	420.8	393.9	355.1	319.6	307.1	313.6	332.7
132.5°	491.3	485.6	479.5	464.6	444.5	416.5	377.2	340.1	322.8	325.7	340.6
135°	524.0	518.8	510.9	496.4	477.4	449.7	410.3	370.2	346.5	343.9	352.4
137.5°	552.8	547.3	538.4	525.9	506.7	482.1	444.2	401.9	372.0	363.2	366.5
140°	570.7	564.2	556.3	543.8	526.7	501.0	464.2	423.4	389.9	377.4	375.4
142.5°	585.5	580.5	572.0	560.6	545.6	520.0	484.2	444.0	408.3	392.1	387.5
145°	607.6	603.6	594.4	583.9	571.4	545.7	512.9	472.8	437.3	416.2	406.4
147.5°	626.2	623.1	615.8	603.5	593.0	568.4	538.4	502.9	466.4	440.4	427.7
150°	637.8	635.2	627.9	616.1	605.6	582.6	553.6	520.8	485.9	458.3	441.9
152.5°	648.8	646.2	637.9	626.1	617.2	595.7	569.4	538.1	502.7	475.1	458.2
155°	663.4	660.2	652.3	641.1	633.2	613.5	589.1	561.5	531.3	502.3	483.3
157.5°	675.0	670.9	663.6	654.0	645.6	627.4	606.2	582.4	556.0	528.4	508.9
160°	681.9	677.3	669.4	660.8	652.9	635.8	616.8	595.1	570.7	545.7	524.7
162.5°	686.6	682.5	673.0	665.5	658.7	643.2	625.2	605.6	583.9	562.1	542.6
165°	691.7	687.1	677.3	671.3	665.4	652.3	636.5	620.7	602.3	584.5	568.8
167.5°	692.1	688.3	678.4	672.6	668.3	657.0	644.2	632.1	617.8	603.9	590.7
170°	691.1	687.8	677.9	672.6	669.4	660.2	649.0	638.5	627.3	615.4	604.9
172.5°	687.4	684.1	674.8	670.5	668.8	660.7	651.6	643.7	634.1	625.4	617.0
175°	677.9	675.3	667.4	664.8	665.4	660.2	653.6	649.0	643.1	637.8	633.2
177.5°	664.1	662.5	656.7	656.7	658.8	655.7	653.6	651.5	648.8	647.3	645.7
180°	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9



TEST NUMBER: P1428519

CATALOG NUMBER: SQ2W-WBM-K-050U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2086.0	2086.0	2086.0	2086.0	2086.0	2086.0	2086.0	2086.0	2086.0	2086.0	2086.0
2.5°	2077.7	2077.9	2085.7	2091.2	2089.4	2087.6	2089.4	2091.2	2085.7	2077.9	2077.7
5°	2075.2	2077.2	2089.7	2098.7	2097.3	2096.0	2097.3	2098.7	2089.7	2077.2	2075.2
7.5°	2080.4	2081.9	2091.3	2097.9	2095.8	2093.8	2095.8	2097.9	2091.3	2081.9	2080.4
10°	2078.7	2078.9	2088.7	2095.7	2094.3	2093.0	2094.3	2095.7	2088.7	2078.9	2078.7
12.5°	2077.6	2074.6	2082.3	2087.2	2084.1	2081.0	2084.1	2087.2	2082.3	2074.6	2077.6
15°	2070.6	2061.0	2061.0	2059.9	2055.4	2051.0	2055.4	2059.9	2061.0	2061.0	2070.6
17.5°	2040.2	2024.0	2017.1	2010.6	2005.2	1999.8	2005.2	2010.6	2017.1	2024.0	2040.2
20°	2007.9	1987.4	1976.3	1967.4	1965.2	1963.0	1965.2	1967.4	1976.3	1987.4	2007.9
22.5°	1966.6	1944.5	1932.3	1922.3	1918.6	1915.0	1918.6	1922.3	1932.3	1944.5	1966.6
25°	1887.2	1866.6	1857.7	1849.8	1844.9	1840.0	1844.9	1849.8	1857.7	1866.6	1887.2
27.5°	1785.2	1764.9	1754.8	1745.5	1738.8	1732.0	1738.8	1745.5	1754.8	1764.9	1785.2
30°	1710.0	1691.3	1678.0	1665.3	1654.7	1644.0	1654.7	1665.3	1678.0	1691.3	1710.0
32.5°	1618.2	1601.3	1588.7	1577.1	1568.5	1560.0	1568.5	1577.1	1588.7	1601.3	1618.2
35°	1462.4	1448.7	1434.0	1420.8	1411.9	1403.0	1411.9	1420.8	1434.0	1448.7	1462.4
37.5°	1266.5	1255.6	1244.1	1233.2	1224.2	1215.2	1224.2	1233.2	1244.1	1255.6	1266.5
40°	1127.2	1114.6	1097.7	1084.4	1082.2	1080.0	1082.2	1084.4	1097.7	1114.6	1127.2
42.5°	976.8	964.5	951.5	939.2	928.8	918.4	928.8	939.2	951.5	964.5	976.8
45°	749.0	741.2	725.7	703.3	660.7	618.0	660.7	703.3	725.7	741.2	749.0
47.5°	518.9	508.3	462.1	414.4	362.6	310.8	362.6	414.4	462.1	508.3	518.9
50°	376.3	365.0	301.0	248.7	231.3	214.0	231.3	248.7	301.0	365.0	376.3
52.5°	277.7	272.4	218.3	175.5	166.4	157.2	166.4	175.5	218.3	272.4	277.7
55°	154.1	152.8	128.3	109.1	105.6	102.0	105.6	109.1	128.3	152.8	154.1
57.5°	89.5	89.5	81.0	73.2	67.6	62.0	67.6	73.2	81.0	89.5	89.5
60°	65.4	64.6	55.7	47.8	42.9	38.0	42.9	47.8	55.7	64.6	65.4
62.5°	51.6	51.0	43.9	38.2	36.5	34.8	36.5	38.2	43.9	51.0	51.6
65°	33.8	33.6	32.7	31.8	30.9	30.0	30.9	31.8	32.7	33.6	33.8
67.5°	28.6	28.4	28.3	28.0	27.2	26.4	27.2	28.0	28.3	28.4	28.6
70°	26.0	25.8	25.3	24.9	24.4	24.0	24.4	24.9	25.3	25.8	26.0
72.5°	23.0	22.8	22.7	22.4	21.6	20.8	21.6	22.4	22.7	22.8	23.0
75°	19.0	18.8	18.3	17.9	17.4	17.0	17.4	17.9	18.3	18.8	19.0
77.5°	14.6	14.4	14.4	14.3	13.8	13.4	13.8	14.3	14.4	14.4	14.6
80°	12.2	12.0	12.0	11.9	11.4	11.0	11.4	11.9	12.0	12.0	12.2
82.5°	9.6	9.6	9.6	9.5	9.0	8.6	9.0	9.5	9.6	9.6	9.6
85°	5.2	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.2
87.5°	4.8	5.5	6.5	7.0	7.5	7.3	7.5	7.0	6.5	5.5	4.8
90°	15.1	19.7	24.3	27.0	29.6	28.3	29.6	27.0	24.3	19.7	15.1
92.5°	30.4	38.1	43.8	48.5	50.6	50.4	50.6	48.5	43.8	38.1	30.4
95°	61.1	70.4	79.6	86.1	90.1	88.8	90.1	86.1	79.6	70.4	61.1
97.5°	94.3	106.7	116.9	123.1	127.0	129.7	127.0	123.1	116.9	106.7	94.3
100°	116.4	128.2	140.1	147.3	153.9	156.5	153.9	147.3	140.1	128.2	116.4
102.5°	134.3	149.8	162.7	170.4	176.0	178.6	176.0	170.4	162.7	149.8	134.3
105°	163.7	180.2	194.0	203.8	209.8	211.7	209.8	203.8	194.0	180.2	163.7
107.5°	193.2	210.1	222.9	233.8	241.0	245.3	241.0	233.8	222.9	210.1	193.2
110°	216.3	230.1	243.9	253.8	261.0	263.7	261.0	253.8	243.9	230.1	216.3



TEST NUMBER: P1428519

CATALOG NUMBER: SQ2W-WBM-K-050U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	235.8	251.2	265.0	274.8	283.1	286.8	283.1	274.8	265.0	251.2	235.8
115°	263.0	283.4	295.9	305.1	311.0	314.3	311.0	305.1	295.9	283.4	263.0
117.5°	285.6	306.9	320.6	327.7	330.5	332.8	330.5	327.7	320.6	306.9	285.6
120°	299.8	319.6	335.3	344.5	347.8	349.1	347.8	344.5	335.3	319.6	299.8
122.5°	313.0	331.7	346.9	358.2	363.6	364.9	363.6	358.2	346.9	331.7	313.0
125°	331.4	349.1	364.9	376.1	382.0	385.3	382.0	376.1	364.9	349.1	331.4
127.5°	347.4	366.6	381.1	391.2	397.0	399.6	397.0	391.2	381.1	366.6	347.4
130°	356.4	376.1	390.6	401.7	407.0	409.6	407.0	401.7	390.6	376.1	356.4
132.5°	363.2	384.0	399.0	409.1	414.9	417.5	414.9	409.1	399.0	384.0	363.2
135°	371.5	393.2	409.0	418.8	424.1	426.7	424.1	418.8	409.0	393.2	371.5
137.5°	378.7	398.5	414.9	425.3	430.0	431.7	430.0	425.3	414.9	398.5	378.7
140°	384.0	401.1	417.5	427.4	432.7	433.3	432.7	427.4	417.5	401.1	384.0
142.5°	390.8	404.2	418.6	428.4	433.7	434.9	433.7	428.4	418.6	404.2	390.8
145°	403.1	411.0	420.8	430.0	434.6	435.9	434.6	430.0	420.8	411.0	403.1
147.5°	418.4	420.9	426.1	432.1	436.6	437.5	436.6	432.1	426.1	420.9	418.4
150°	430.0	429.4	431.3	435.3	439.2	438.6	439.2	435.3	431.3	429.4	430.0
152.5°	443.2	439.4	439.2	441.1	442.9	442.8	442.9	441.1	439.2	439.4	443.2
155°	465.5	458.3	454.3	453.0	453.0	452.4	453.0	453.0	454.3	458.3	465.5
157.5°	490.1	480.0	474.1	470.9	470.0	468.6	470.0	470.9	474.1	480.0	490.1
160°	507.0	495.8	489.9	484.6	482.6	480.7	482.6	484.6	489.9	495.8	507.0
162.5°	522.7	512.1	505.6	500.9	498.9	495.9	498.9	500.9	505.6	512.1	522.7
165°	548.4	537.2	530.0	526.0	523.4	520.8	523.4	526.0	530.0	537.2	548.4
167.5°	574.0	561.8	557.1	552.6	550.1	545.4	550.1	552.6	557.1	561.8	574.0
170°	589.8	578.6	576.0	572.0	567.4	562.2	567.4	572.0	576.0	578.6	589.8
172.5°	603.5	596.0	593.4	589.4	588.0	583.8	588.0	589.4	593.4	596.0	603.5
175°	623.3	617.4	617.4	616.8	614.8	610.8	614.8	616.8	617.4	617.4	623.3
177.5°	639.9	636.7	638.9	638.9	638.3	634.6	638.3	638.9	638.9	636.7	639.9
180°	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9	650.9



TEST NUMBER: P1428519

CATALOG NUMBER: SQ2W-WBM-K-050U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	2086.0	2086.0	2086.0	2086.0
2.5°	2085.2	2091.4	2093.9	2096.4
5°	2083.7	2090.8	2093.9	2097.0
7.5°	2086.9	2092.1	2093.5	2094.8
10°	2088.0	2094.9	2094.4	2094.0
12.5°	2091.2	2100.5	2096.8	2093.2
15°	2089.7	2102.2	2095.1	2088.0
17.5°	2065.7	2082.7	2074.2	2065.8
20°	2037.7	2057.9	2049.4	2041.0
22.5°	1998.5	2020.1	2011.0	2001.8
25°	1919.7	1942.2	1935.1	1928.0
27.5°	1815.6	1837.4	1833.5	1829.6
30°	1734.0	1751.6	1749.8	1748.0
32.5°	1639.3	1654.8	1653.0	1651.2
35°	1475.3	1485.2	1486.1	1487.0
37.5°	1276.7	1284.1	1282.8	1281.6
40°	1135.7	1141.8	1140.9	1140.0
42.5°	988.5	993.9	980.5	967.2
45°	749.0	738.9	698.4	658.0
47.5°	493.9	463.7	417.6	371.6
50°	335.0	296.2	265.1	234.0
52.5°	234.2	197.6	181.8	166.0
55°	132.3	114.6	108.8	103.0
57.5°	81.0	73.1	67.2	61.2
60°	58.3	51.8	46.9	42.0
62.5°	45.5	40.5	38.4	36.4
65°	33.3	32.9	32.4	32.0
67.5°	28.9	29.1	28.6	28.2
70°	26.0	25.9	25.4	25.0
72.5°	23.3	23.5	23.0	22.6
75°	19.0	19.0	19.0	19.0
77.5°	15.1	15.3	14.8	14.4
80°	12.7	12.9	12.4	12.0
82.5°	9.7	9.8	9.7	9.6
85°	5.7	6.0	6.0	6.0
87.5°	4.5	3.8	2.9	2.0
90°	11.8	7.2	4.6	2.0
92.5°	25.5	17.8	12.5	7.2
95°	51.3	40.8	28.9	20.4
97.5°	81.7	64.7	53.0	38.9
100°	98.0	81.5	70.4	55.2
102.5°	115.9	102.0	86.7	71.5
105°	147.9	130.8	113.1	96.0
107.5°	177.7	158.9	137.6	122.2
110°	196.6	176.2	153.9	140.1

TEST NUMBER: P1428519

CATALOG NUMBER: SQ2W-WBM-K-050U-075D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	215.0	194.1	171.2	157.4
115°	240.0	217.0	195.9	184.1
117.5°	264.1	240.4	218.2	208.8
120°	278.8	255.1	233.4	226.2
122.5°	290.9	267.7	247.6	244.6
125°	309.0	285.4	268.3	272.2
127.5°	323.8	302.1	291.3	300.1
130°	332.7	313.6	307.1	319.6
132.5°	340.6	325.7	322.8	340.1
135°	352.4	343.9	346.5	370.2
137.5°	366.5	363.2	372.0	401.9
140°	375.4	377.4	389.9	423.4
142.5°	387.5	392.1	408.3	444.0
145°	406.4	416.2	437.3	472.8
147.5°	427.7	440.4	466.4	502.9
150°	441.9	458.3	485.9	520.8
152.5°	458.2	475.1	502.7	538.1
155°	483.3	502.3	531.3	561.5
157.5°	508.9	528.4	556.0	582.4
160°	524.7	545.7	570.7	595.1
162.5°	542.6	562.1	583.9	605.6
165°	568.8	584.5	602.3	620.7
167.5°	590.7	603.9	617.8	632.1
170°	604.9	615.4	627.3	638.5
172.5°	617.0	625.4	634.1	643.7
175°	633.2	637.8	643.1	649.0
177.5°	645.7	647.3	648.8	651.5
180°	650.9	650.9	650.9	650.9

TEST NUMBER: P1428519
 CATALOG NUMBER: SQ2W-WBM-K-050U-075D-L935-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.35	6.15	6.22	7.01	8.09	5.33	6.13	6.20	6.99	8.08
	3H	6.04	6.74	6.92	7.62	8.73	5.96	6.66	6.84	7.54	8.65
	4H	6.40	7.07	7.30	7.95	9.07	6.26	6.93	7.16	7.81	8.93
	6H	6.68	7.28	7.58	8.17	9.30	6.50	7.10	7.41	7.99	9.12
	8H	6.80	7.37	7.71	8.27	9.40	6.60	7.17	7.51	8.07	9.21
	12H	6.87	7.42	7.79	8.32	9.47	6.65	7.19	7.57	8.09	9.24
4H	2H	5.45	6.11	6.35	6.99	8.11	5.43	6.10	6.34	6.98	8.10
	3H	6.39	6.93	7.30	7.85	8.98	6.31	6.85	7.22	7.76	8.90
	4H	6.90	7.39	7.82	8.30	9.46	6.75	7.24	7.67	8.15	9.31
	6H	7.32	7.74	8.26	8.68	9.84	7.13	7.55	8.06	8.48	9.64
	8H	7.51	7.91	8.45	8.83	10.01	7.29	7.68	8.23	8.61	9.78
	12H	7.64	7.99	8.59	8.94	10.11	7.38	7.73	8.33	8.68	9.85
8H	4H	7.02	7.41	7.95	8.33	9.51	6.88	7.27	7.82	8.20	9.37
	6H	7.59	7.91	8.55	8.88	10.05	7.40	7.72	8.36	8.69	9.86
	8H	7.88	8.16	8.85	9.12	10.32	7.66	7.95	8.63	8.91	10.10
	12H	8.10	8.35	9.07	9.30	10.54	7.83	8.08	8.80	9.03	10.28
12H	4H	7.00	7.35	7.95	8.29	9.47	6.87	7.22	7.82	8.16	9.34
	6H	7.63	7.91	8.59	8.87	10.06	7.44	7.73	8.41	8.69	9.88
	8H	7.95	8.20	8.92	9.15	10.39	7.74	7.99	8.71	8.94	10.19