

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428301

Luminaire Tested: SQ2W-PR1-K-150U-050D-L840-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428301
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-9)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PR1-K-150U-050D-L840-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE RIPPLE LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9536.2 lumens
Efficiency: N/A
Efficacy: 130.8 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.34 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 72.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428301

CATALOG NUMBER: SQ2W-PR1-K-150U-050D-L840-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428301

CATALOG NUMBER: SQ2W-PR1-K-150U-050D-L840-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	72	72	72	53	53	53	37	37	37	29				
1	93	89	86	82	84	80	77	74	63	61	59	47	46	45	33	32	32	25				
2	85	78	73	68	76	70	66	62	56	52	50	42	40	38	29	28	27	22				
3	78	69	62	57	70	62	56	52	49	45	42	37	35	33	26	25	23	19				
4	71	61	54	48	64	55	49	44	44	40	36	33	31	28	24	22	20	16				
5	66	55	47	41	59	49	43	38	39	35	31	30	27	24	21	20	18	14				
6	60	49	41	36	54	44	38	33	35	31	27	27	24	21	20	17	16	13				
7	56	44	37	31	50	40	33	29	32	27	24	25	21	19	18	16	14	11				
8	52	40	33	27	46	36	30	25	29	24	21	23	19	17	16	14	13	10				
9	48	36	29	24	43	33	27	23	27	22	19	21	17	15	15	13	11	9				
10	45	33	26	22	40	30	24	20	25	20	17	19	16	14	14	12	10	8				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	18459	18459	18459	18459
5°	18434	18774	18434	18774
10°	18629	19393	18629	19393
15°	18622	18876	18622	18876
20°	18323	19223	18323	19223
25°	18271	20015	18271	20015
30°	18250	20206	18250	20206
35°	18078	18813	18078	18813
40°	17660	16556	17660	16556
45°	16712	13093	16712	13093
50°	15191	10158	15191	10158
55°	13351	7907	13351	7907
60°	11554	6510	11554	6510
65°	9975	5700	9975	5700
70°	8969	5061	8969	5061
75°	8216	4654	8216	4654
80°	7150	4547	7150	4547
85°	5187	2167	5187	2167

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 17940 cd/sqm



TEST NUMBER: P1428301

CATALOG NUMBER: SQ2W-PR1-K-150U-050D-L840-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.4	1.2
10°-20°	319.6	3.4
20°-30°	494.1	5.2
30°-40°	594.2	6.2
40°-50°	533.6	5.6
50°-60°	357.5	3.7
60°-70°	208.0	2.2
70°-80°	106.8	1.1
80°-90°	35.9	0.4
90°-100°	184.7	1.9
100°-110°	538.6	5.6
110°-120°	879.0	9.2
120°-130°	1115.4	11.7
130°-140°	1193.5	12.5
140°-150°	1114.5	11.7
150°-160°	917.1	9.6
160°-170°	615.0	6.4
170°-180°	218.4	2.3
0°-30°	924.1	9.7
0°-40°	1518.3	15.9
0°-60°	2409.3	25.3
0°-90°	2760.1	28.9
90°-120°	1602.3	16.8
90°-150°	5025.7	52.7
90°-180°	6776.0	71.1
0°-180°	9536.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1143	1143	1143	1143	1143	
5°	1137	1158	1137	1158	1137	109
15°	1114	1129	1114	1129	1114	313
25°	1026	1124	1026	1124	1026	473
35°	917	954	917	954	917	572
45°	732	573	732	573	732	560
55°	474	281	474	281	474	426
65°	261	149	261	149	261	264
75°	132	75	132	75	132	140
85°	28	12	28	12	28	35
90°	7	52	7	101	7	7
95°	73	54	73	316	73	88
105°	342	548	342	755	342	364
115°	656	910	656	1120	656	647
125°	970	1442	970	1374	970	868
135°	1320	1887	1320	1521	1320	1020
145°	1686	2175	1686	1554	1686	1055
155°	2002	2363	2002	1613	2002	920
165°	2213	2464	2213	1857	2213	623
175°	2314	2412	2314	2178	2314	220
180°	2321	2321	2321	2321	2321	



TEST NUMBER: P1428301

CATALOG NUMBER: SQ2W-PR1-K-150U-050D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3
2.5°	1138.6	1144.8	1151.0	1148.2	1142.4	1139.7	1140.2	1140.8	1142.0	1143.3	1142.0
5°	1137.4	1146.2	1155.1	1153.0	1147.3	1145.0	1146.0	1148.1	1153.2	1158.4	1153.2
7.5°	1137.2	1149.7	1162.3	1163.2	1160.3	1160.4	1163.4	1167.4	1174.2	1181.0	1174.2
10°	1136.3	1151.3	1166.3	1168.5	1166.4	1165.7	1166.2	1168.4	1175.6	1182.9	1175.6
12.5°	1130.7	1148.2	1165.7	1163.9	1155.6	1151.1	1150.3	1150.8	1154.7	1158.7	1154.7
15°	1114.1	1134.9	1155.6	1147.2	1129.0	1120.7	1122.3	1124.1	1126.7	1129.3	1126.7
17.5°	1085.0	1106.6	1128.3	1120.7	1103.4	1097.6	1103.2	1108.6	1113.7	1118.8	1113.7
20°	1066.4	1087.6	1108.8	1103.6	1089.7	1086.3	1093.5	1101.2	1110.0	1118.8	1110.0
22.5°	1049.6	1070.8	1092.0	1088.7	1077.2	1076.6	1086.7	1097.4	1109.5	1121.6	1109.5
25°	1025.6	1044.2	1062.9	1063.2	1057.5	1063.2	1080.3	1096.5	1110.0	1123.5	1110.0
27.5°	1000.4	1011.4	1022.4	1029.6	1035.6	1050.2	1073.3	1092.9	1102.4	1111.8	1102.4
30°	978.9	986.2	993.4	1006.9	1022.5	1040.3	1060.5	1076.6	1080.2	1083.8	1080.2
32.5°	955.6	960.0	964.3	983.3	1007.1	1024.4	1035.0	1041.9	1037.2	1032.6	1037.2
35°	917.2	920.8	924.4	948.6	979.7	991.1	982.8	974.2	964.3	954.5	964.3
37.5°	871.5	879.0	886.4	906.1	930.0	929.8	905.5	884.5	873.2	861.9	873.2
40°	837.9	850.4	862.8	876.0	889.5	878.1	841.8	811.4	798.4	785.5	798.4
42.5°	796.9	816.8	836.7	839.6	836.9	812.5	766.3	727.7	711.8	696.0	711.8
45°	731.9	758.8	785.7	770.3	740.8	700.9	650.7	608.6	591.0	573.4	591.0
47.5°	655.2	682.9	710.5	681.5	633.5	587.1	542.2	504.5	488.0	471.5	488.0
50°	604.8	627.1	649.4	616.5	565.2	518.6	476.7	440.7	422.5	404.4	422.5
52.5°	553.6	569.6	585.7	553.1	504.3	458.9	417.0	381.4	364.9	348.5	364.9
55°	474.3	482.6	490.9	460.7	417.7	376.3	336.4	303.7	292.3	280.9	292.3
57.5°	401.6	406.9	412.2	383.6	343.7	306.8	272.9	245.4	237.0	228.7	237.0
60°	357.8	361.4	365.0	336.0	296.1	263.0	236.6	215.1	208.3	201.6	208.3
62.5°	317.7	320.5	323.3	295.3	257.1	227.5	206.4	189.4	184.3	179.2	184.3
65°	261.1	263.6	266.2	242.4	209.8	185.4	169.4	156.4	152.8	149.2	152.8
67.5°	216.1	217.4	218.8	199.1	172.5	152.9	140.2	129.9	126.5	123.1	126.5
70°	190.0	190.5	191.0	173.6	150.3	133.0	121.6	112.4	109.8	107.2	109.8
72.5°	166.7	165.9	165.2	149.7	129.3	114.4	105.1	97.7	95.9	94.2	95.9
75°	131.7	130.1	128.6	115.8	99.2	87.8	81.6	76.7	75.6	74.6	75.6
77.5°	98.4	96.7	95.0	84.4	70.7	62.8	60.8	59.2	59.2	59.2	59.2
80°	76.9	74.8	72.8	64.5	54.1	48.9	48.9	48.9	48.9	48.9	48.9
82.5°	57.3	54.4	51.5	46.5	40.7	37.8	37.8	37.7	37.2	36.8	37.2
85°	28.0	25.4	22.8	22.1	22.1	20.6	17.5	14.8	13.2	11.7	13.2
87.5°	8.9	10.7	13.1	13.4	12.7	12.2	12.2	12.6	13.1	13.1	13.1
90°	7.0	16.4	28.1	37.5	44.5	46.9	46.9	49.2	51.6	51.6	51.6
92.5°	25.8	40.8	41.3	41.3	50.2	54.4	58.1	58.6	60.9	60.9	60.9
95°	72.7	79.7	119.6	117.2	79.7	63.3	53.9	53.9	53.9	53.9	53.9
97.5°	138.8	149.1	155.7	208.6	220.4	212.9	173.5	145.8	130.3	123.3	130.3
100°	196.9	201.6	215.7	218.0	276.6	332.9	304.7	269.6	257.9	250.8	257.9
102.5°	255.0	257.9	279.4	289.3	302.9	334.7	432.3	421.5	413.5	412.1	413.5
105°	342.3	344.6	384.4	403.2	412.6	412.6	410.2	457.1	532.1	548.5	532.1
107.5°	435.5	446.3	493.2	543.4	554.2	557.0	544.8	537.8	534.9	536.8	534.9
110°	499.3	515.7	572.0	635.3	651.7	656.4	651.7	644.7	640.0	640.0	640.0



TEST NUMBER: P1428301

CATALOG NUMBER: SQ2W-PR1-K-150U-050D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	561.2	585.1	648.9	721.5	749.2	763.3	753.0	747.8	743.1	746.9	743.1
115°	656.4	691.5	775.9	850.9	907.2	914.2	911.9	911.9	909.5	909.5	909.5
117.5°	744.5	800.8	895.5	982.7	1047.9	1066.6	1076.0	1073.2	1070.4	1075.0	1070.4
120°	806.4	872.0	979.9	1078.3	1141.6	1169.7	1179.1	1174.4	1179.1	1174.4	1179.1
122.5°	872.0	952.7	1058.6	1160.8	1235.4	1267.3	1278.5	1279.5	1280.4	1277.6	1280.4
125°	970.5	1068.9	1193.2	1298.7	1376.0	1413.5	1422.9	1425.3	1430.0	1441.7	1430.0
127.5°	1069.9	1181.5	1317.9	1419.6	1498.9	1544.3	1558.9	1564.0	1573.9	1579.0	1573.9
130°	1139.3	1265.9	1404.2	1500.3	1577.6	1626.9	1652.7	1659.7	1671.4	1669.1	1671.4
132.5°	1212.4	1344.6	1484.8	1584.7	1656.4	1709.4	1731.4	1751.6	1755.8	1759.1	1755.8
135°	1319.8	1462.8	1603.4	1701.9	1769.9	1821.4	1849.6	1868.3	1880.0	1887.1	1880.0
137.5°	1432.8	1583.7	1718.8	1806.4	1874.9	1919.4	1951.3	1971.0	1983.2	1988.8	1983.2
140°	1509.7	1655.0	1786.3	1877.7	1938.6	1983.2	2011.3	2034.8	2048.8	2048.8	2048.8
142.5°	1582.8	1726.3	1853.8	1945.2	1998.7	2039.4	2069.4	2087.3	2103.2	2103.2	2103.2
145°	1685.5	1828.5	1945.7	2037.1	2081.6	2119.1	2152.0	2166.0	2175.4	2175.4	2175.4
147.5°	1792.8	1919.4	2026.3	2114.0	2151.5	2195.6	2221.3	2232.6	2244.3	2239.2	2244.3
150°	1856.6	1973.8	2076.9	2159.0	2196.5	2238.7	2264.5	2273.9	2285.6	2278.5	2285.6
152.5°	1918.5	2030.1	2123.8	2200.3	2232.1	2274.3	2303.9	2313.2	2321.2	2316.1	2321.2
155°	2001.9	2100.4	2187.1	2257.5	2285.6	2325.4	2353.6	2365.3	2374.7	2362.9	2374.7
157.5°	2076.5	2161.3	2236.8	2301.5	2331.5	2365.8	2392.0	2406.5	2415.9	2410.8	2415.9
160°	2121.5	2198.8	2266.8	2327.8	2355.9	2386.4	2414.5	2430.9	2440.3	2433.3	2440.3
162.5°	2159.0	2228.9	2293.1	2348.4	2372.8	2399.5	2433.3	2447.8	2457.2	2448.3	2457.2
165°	2212.9	2269.2	2325.4	2372.3	2393.4	2414.5	2449.7	2466.1	2473.1	2463.7	2473.1
167.5°	2253.7	2296.8	2342.3	2382.6	2398.1	2418.7	2453.9	2467.5	2476.4	2464.7	2476.4
170°	2276.2	2313.7	2353.6	2386.4	2398.1	2416.9	2452.0	2463.7	2470.8	2459.1	2470.8
172.5°	2295.0	2323.1	2355.4	2384.5	2390.6	2405.6	2438.9	2450.6	2455.8	2445.9	2455.8
175°	2313.7	2330.1	2353.6	2372.3	2370.0	2379.3	2407.5	2416.9	2426.2	2412.2	2426.2
177.5°	2322.6	2330.1	2337.6	2348.9	2341.4	2341.4	2362.0	2367.6	2369.5	2362.0	2369.5
180°	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7



TEST NUMBER: P1428301

CATALOG NUMBER: SQ2W-PR1-K-150U-050D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3
2.5°	1140.8	1140.2	1139.7	1142.4	1148.2	1151.0	1144.8	1138.6	1144.8	1151.0	1148.2
5°	1148.1	1146.0	1145.0	1147.3	1153.0	1155.1	1146.2	1137.4	1146.2	1155.1	1153.0
7.5°	1167.4	1163.4	1160.4	1160.3	1163.2	1162.3	1149.7	1137.2	1149.7	1162.3	1163.2
10°	1168.4	1166.2	1165.7	1166.4	1168.5	1166.3	1151.3	1136.3	1151.3	1166.3	1168.5
12.5°	1150.8	1150.3	1151.1	1155.6	1163.9	1165.7	1148.2	1130.7	1148.2	1165.7	1163.9
15°	1124.1	1122.3	1120.7	1129.0	1147.2	1155.6	1134.9	1114.1	1134.9	1155.6	1147.2
17.5°	1108.6	1103.2	1097.6	1103.4	1120.7	1128.3	1106.6	1085.0	1106.6	1128.3	1120.7
20°	1101.2	1093.5	1086.3	1089.7	1103.6	1108.8	1087.6	1066.4	1087.6	1108.8	1103.6
22.5°	1097.4	1086.7	1076.6	1077.2	1088.7	1092.0	1070.8	1049.6	1070.8	1092.0	1088.7
25°	1096.5	1080.3	1063.2	1057.5	1063.2	1062.9	1044.2	1025.6	1044.2	1062.9	1063.2
27.5°	1092.9	1073.3	1050.2	1035.6	1029.6	1022.4	1011.4	1000.4	1011.4	1022.4	1029.6
30°	1076.6	1060.5	1040.3	1022.5	1006.9	993.4	986.2	978.9	986.2	993.4	1006.9
32.5°	1041.9	1035.0	1024.4	1007.1	983.3	964.3	960.0	955.6	960.0	964.3	983.3
35°	974.2	982.8	991.1	979.7	948.6	924.4	920.8	917.2	920.8	924.4	948.6
37.5°	884.5	905.5	929.8	930.0	906.1	886.4	879.0	871.5	879.0	886.4	906.1
40°	811.4	841.8	878.1	889.5	876.0	862.8	850.4	837.9	850.4	862.8	876.0
42.5°	727.7	766.3	812.5	836.9	839.6	836.7	816.8	796.9	816.8	836.7	839.6
45°	608.6	650.7	700.9	740.8	770.3	785.7	758.8	731.9	758.8	785.7	770.3
47.5°	504.5	542.2	587.1	633.5	681.5	710.5	682.9	655.2	682.9	710.5	681.5
50°	440.7	476.7	518.6	565.2	616.5	649.4	627.1	604.8	627.1	649.4	616.5
52.5°	381.4	417.0	458.9	504.3	553.1	585.7	569.6	553.6	569.6	585.7	553.1
55°	303.7	336.4	376.3	417.7	460.7	490.9	482.6	474.3	482.6	490.9	460.7
57.5°	245.4	272.9	306.8	343.7	383.6	412.2	406.9	401.6	406.9	412.2	383.6
60°	215.1	236.6	263.0	296.1	336.0	365.0	361.4	357.8	361.4	365.0	336.0
62.5°	189.4	206.4	227.5	257.1	295.3	323.3	320.5	317.7	320.5	323.3	295.3
65°	156.4	169.4	185.4	209.8	242.4	266.2	263.6	261.1	263.6	266.2	242.4
67.5°	129.9	140.2	152.9	172.5	199.1	218.8	217.4	216.1	217.4	218.8	199.1
70°	112.4	121.6	133.0	150.3	173.6	191.0	190.5	190.0	190.5	191.0	173.6
72.5°	97.7	105.1	114.4	129.3	149.7	165.2	165.9	166.7	165.9	165.2	149.7
75°	76.7	81.6	87.8	99.2	115.8	128.6	130.1	131.7	130.1	128.6	115.8
77.5°	59.2	60.8	62.8	70.7	84.4	95.0	96.7	98.4	96.7	95.0	84.4
80°	48.9	48.9	48.9	54.1	64.5	72.8	74.8	76.9	74.8	72.8	64.5
82.5°	37.7	37.8	37.8	40.7	46.5	51.5	54.4	57.3	54.4	51.5	46.5
85°	14.8	17.5	20.6	22.1	22.1	22.8	25.4	28.0	25.4	22.8	22.1
87.5°	12.6	12.2	12.2	12.7	13.4	13.1	10.7	8.9	10.7	12.6	14.3
90°	49.2	46.9	46.9	44.5	37.5	28.1	16.4	7.0	16.4	25.8	42.2
92.5°	58.6	58.1	54.4	50.2	41.3	41.3	40.8	25.8	44.5	63.3	91.0
95°	53.9	53.9	63.3	79.7	117.2	119.6	79.7	72.7	103.1	145.3	182.8
97.5°	145.8	173.5	212.9	220.4	208.6	155.7	149.1	138.8	188.9	230.7	291.1
100°	269.6	304.7	332.9	276.6	218.0	215.7	201.6	196.9	250.8	290.7	349.3
102.5°	421.5	432.3	334.7	302.9	289.3	279.4	257.9	255.0	309.0	363.8	413.0
105°	457.1	410.2	412.6	412.6	403.2	384.4	344.6	342.3	403.2	466.5	527.4
107.5°	537.8	544.8	557.0	554.2	543.4	493.2	446.3	435.5	490.4	566.4	633.4
110°	644.7	651.7	656.4	651.7	635.3	572.0	515.7	499.3	548.5	628.2	700.9



TEST NUMBER: P1428301

CATALOG NUMBER: SQ2W-PR1-K-150U-050D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	747.8	753.0	763.3	749.2	721.5	648.9	585.1	561.2	610.4	692.0	766.5
115°	911.9	911.9	914.2	907.2	850.9	775.9	691.5	656.4	698.6	773.6	855.6
117.5°	1073.2	1076.0	1066.6	1047.9	982.7	895.5	800.8	744.5	777.8	857.0	941.4
120°	1174.4	1179.1	1169.7	1141.6	1078.3	979.9	872.0	806.4	832.2	909.5	993.9
122.5°	1279.5	1278.5	1267.3	1235.4	1160.8	1058.6	952.7	872.0	882.8	954.6	1037.1
125°	1425.3	1422.9	1413.5	1376.0	1298.7	1193.2	1068.9	970.5	956.4	1017.4	1101.8
127.5°	1564.0	1558.9	1544.3	1498.9	1419.6	1317.9	1181.5	1069.9	1038.5	1076.9	1154.3
130°	1659.7	1652.7	1626.9	1577.6	1500.3	1404.2	1265.9	1139.3	1094.7	1118.2	1186.2
132.5°	1751.6	1731.4	1709.4	1656.4	1584.7	1484.8	1344.6	1212.4	1151.0	1161.3	1214.3
135°	1868.3	1849.6	1821.4	1769.9	1701.9	1603.4	1462.8	1319.8	1235.4	1226.0	1256.5
137.5°	1971.0	1951.3	1919.4	1874.9	1806.4	1718.8	1583.7	1432.8	1326.3	1294.9	1306.6
140°	2034.8	2011.3	1983.2	1938.6	1877.7	1786.3	1655.0	1509.7	1390.1	1345.6	1338.5
142.5°	2087.3	2069.4	2039.4	1998.7	1945.2	1853.8	1726.3	1582.8	1455.7	1398.1	1381.7
145°	2166.0	2152.0	2119.1	2081.6	2037.1	1945.7	1828.5	1685.5	1558.9	1483.9	1448.7
147.5°	2232.6	2221.3	2195.6	2151.5	2114.0	2026.3	1919.4	1792.8	1663.0	1570.1	1524.7
150°	2273.9	2264.5	2238.7	2196.5	2159.0	2076.9	1973.8	1856.6	1732.4	1633.9	1575.3
152.5°	2313.2	2303.9	2274.3	2232.1	2200.3	2123.8	2030.1	1918.5	1792.4	1693.9	1633.4
155°	2365.3	2353.6	2325.4	2285.6	2257.5	2187.1	2100.4	2001.9	1894.1	1791.0	1723.0
157.5°	2406.5	2392.0	2365.8	2331.5	2301.5	2236.8	2161.3	2076.5	1982.2	1883.8	1814.4
160°	2430.9	2414.5	2386.4	2355.9	2327.8	2266.8	2198.8	2121.5	2034.8	1945.7	1870.7
162.5°	2447.8	2433.3	2399.5	2372.8	2348.4	2293.1	2228.9	2159.0	2081.6	2003.8	1934.4
165°	2466.1	2449.7	2414.5	2393.4	2372.3	2325.4	2269.2	2212.9	2147.3	2084.0	2027.7
167.5°	2467.5	2453.9	2418.7	2398.1	2382.6	2342.3	2296.8	2253.7	2202.6	2152.9	2106.0
170°	2463.7	2452.0	2416.9	2398.1	2386.4	2353.6	2313.7	2276.2	2236.4	2194.2	2156.7
172.5°	2450.6	2438.9	2405.6	2390.6	2384.5	2355.4	2323.1	2295.0	2260.7	2229.8	2199.8
175°	2416.9	2407.5	2379.3	2370.0	2372.3	2353.6	2330.1	2313.7	2292.6	2273.9	2257.5
177.5°	2367.6	2362.0	2341.4	2341.4	2348.9	2337.6	2330.1	2322.6	2313.2	2307.6	2302.0
180°	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7



TEST NUMBER: P1428301

CATALOG NUMBER: SQ2W-PR1-K-150U-050D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3
2.5°	1142.4	1139.7	1140.2	1140.8	1142.0	1143.3	1142.0	1140.8	1140.2	1139.7	1142.4
5°	1147.3	1145.0	1146.0	1148.1	1153.2	1158.4	1153.2	1148.1	1146.0	1145.0	1147.3
7.5°	1160.3	1160.4	1163.4	1167.4	1174.2	1181.0	1174.2	1167.4	1163.4	1160.4	1160.3
10°	1166.4	1165.7	1166.2	1168.4	1175.6	1182.9	1175.6	1168.4	1166.2	1165.7	1166.4
12.5°	1155.6	1151.1	1150.3	1150.8	1154.7	1158.7	1154.7	1150.8	1150.3	1151.1	1155.6
15°	1129.0	1120.7	1122.3	1124.1	1126.7	1129.3	1126.7	1124.1	1122.3	1120.7	1129.0
17.5°	1103.4	1097.6	1103.2	1108.6	1113.7	1118.8	1113.7	1108.6	1103.2	1097.6	1103.4
20°	1089.7	1086.3	1093.5	1101.2	1110.0	1118.8	1110.0	1101.2	1093.5	1086.3	1089.7
22.5°	1077.2	1076.6	1086.7	1097.4	1109.5	1121.6	1109.5	1097.4	1086.7	1076.6	1077.2
25°	1057.5	1063.2	1080.3	1096.5	1110.0	1123.5	1110.0	1096.5	1080.3	1063.2	1057.5
27.5°	1035.6	1050.2	1073.3	1092.9	1102.4	1111.8	1102.4	1092.9	1073.3	1050.2	1035.6
30°	1022.5	1040.3	1060.5	1076.6	1080.2	1083.8	1080.2	1076.6	1060.5	1040.3	1022.5
32.5°	1007.1	1024.4	1035.0	1041.9	1037.2	1032.6	1037.2	1041.9	1035.0	1024.4	1007.1
35°	979.7	991.1	982.8	974.2	964.3	954.5	964.3	974.2	982.8	991.1	979.7
37.5°	930.0	929.8	905.5	884.5	873.2	861.9	873.2	884.5	905.5	929.8	930.0
40°	889.5	878.1	841.8	811.4	798.4	785.5	798.4	811.4	841.8	878.1	889.5
42.5°	836.9	812.5	766.3	727.7	711.8	696.0	711.8	727.7	766.3	812.5	836.9
45°	740.8	700.9	650.7	608.6	591.0	573.4	591.0	608.6	650.7	700.9	740.8
47.5°	633.5	587.1	542.2	504.5	488.0	471.5	488.0	504.5	542.2	587.1	633.5
50°	565.2	518.6	476.7	440.7	422.5	404.4	422.5	440.7	476.7	518.6	565.2
52.5°	504.3	458.9	417.0	381.4	364.9	348.5	364.9	417.0	458.9	504.3	504.3
55°	417.7	376.3	336.4	303.7	292.3	280.9	292.3	303.7	336.4	376.3	417.7
57.5°	343.7	306.8	272.9	245.4	237.0	228.7	237.0	245.4	272.9	306.8	343.7
60°	296.1	263.0	236.6	215.1	208.3	201.6	208.3	215.1	236.6	263.0	296.1
62.5°	257.1	227.5	206.4	189.4	184.3	179.2	184.3	189.4	206.4	227.5	257.1
65°	209.8	185.4	169.4	156.4	152.8	149.2	152.8	169.4	185.4	209.8	209.8
67.5°	172.5	152.9	140.2	129.9	126.5	123.1	126.5	140.2	152.9	172.5	172.5
70°	150.3	133.0	121.6	112.4	109.8	107.2	109.8	121.6	133.0	150.3	150.3
72.5°	129.3	114.4	105.1	97.7	95.9	94.2	95.9	105.1	114.4	129.3	129.3
75°	99.2	87.8	81.6	76.7	75.6	74.6	75.6	81.6	87.8	99.2	99.2
77.5°	70.7	62.8	60.8	59.2	59.2	59.2	59.2	60.8	62.8	70.7	70.7
80°	54.1	48.9	48.9	48.9	48.9	48.9	48.9	48.9	48.9	54.1	54.1
82.5°	40.7	37.8	37.8	37.7	37.2	36.8	37.2	37.7	37.8	40.7	40.7
85°	22.1	20.6	17.5	14.8	13.2	11.7	13.2	14.8	17.5	20.6	22.1
87.5°	14.6	16.9	20.1	22.0	23.9	23.0	23.9	20.1	16.9	14.6	14.6
90°	53.9	70.3	86.7	96.1	105.5	100.8	105.5	86.7	70.3	53.9	53.9
92.5°	108.3	136.0	156.1	173.0	180.5	179.6	180.5	156.1	136.0	108.3	108.3
95°	218.0	250.8	283.6	307.1	321.2	316.5	321.2	283.6	250.8	218.0	218.0
97.5°	336.2	380.2	416.8	438.8	452.9	462.3	452.9	416.8	380.2	336.2	336.2
100°	414.9	457.1	499.3	525.1	548.5	557.9	548.5	499.3	457.1	414.9	414.9
102.5°	478.7	534.0	580.0	607.6	627.3	636.7	627.3	580.0	534.0	478.7	478.7
105°	583.7	642.3	691.5	726.7	747.8	754.8	747.8	691.5	642.3	583.7	583.7
107.5°	688.7	749.2	794.7	833.6	859.4	874.4	859.4	794.7	749.2	688.7	688.7
110°	771.2	820.5	869.7	904.9	930.6	940.0	930.6	869.7	820.5	771.2	771.2



TEST NUMBER: P1428301

CATALOG NUMBER: SQ2W-PR1-K-150U-050D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	840.6	895.5	944.7	979.9	1009.4	1022.5	1009.4	979.9	944.7	895.5	840.6
115°	937.7	1010.3	1054.9	1087.7	1108.8	1120.5	1108.8	1087.7	1054.9	1010.3	937.7
117.5°	1018.3	1094.3	1143.0	1168.3	1178.2	1186.6	1178.2	1168.3	1143.0	1094.3	1018.3
120°	1068.9	1139.3	1195.5	1228.4	1240.1	1244.8	1240.1	1228.4	1195.5	1139.3	1068.9
122.5°	1115.8	1182.4	1236.8	1277.1	1296.3	1301.0	1296.3	1277.1	1236.8	1182.4	1115.8
125°	1181.5	1244.8	1301.0	1340.9	1362.0	1373.7	1362.0	1340.9	1301.0	1244.8	1181.5
127.5°	1238.7	1307.1	1358.7	1394.8	1415.4	1424.8	1415.4	1394.8	1358.7	1307.1	1238.7
130°	1270.5	1340.9	1392.4	1432.3	1451.1	1460.4	1451.1	1432.3	1392.4	1340.9	1270.5
132.5°	1294.9	1369.0	1422.5	1458.6	1479.2	1488.6	1479.2	1458.6	1422.5	1369.0	1294.9
135°	1324.5	1401.8	1458.1	1493.2	1512.0	1521.4	1512.0	1493.2	1458.1	1401.8	1324.5
137.5°	1350.3	1420.6	1479.2	1516.2	1533.1	1539.2	1533.1	1516.2	1479.2	1420.6	1350.3
140°	1369.0	1430.0	1488.6	1523.7	1542.5	1544.8	1542.5	1523.7	1488.6	1430.0	1369.0
142.5°	1393.4	1441.2	1492.3	1527.5	1546.2	1550.4	1546.2	1527.5	1492.3	1441.2	1393.4
145°	1437.0	1465.1	1500.3	1533.1	1549.5	1554.2	1549.5	1533.1	1500.3	1465.1	1437.0
147.5°	1491.8	1500.7	1519.0	1540.6	1556.5	1559.8	1556.5	1540.6	1519.0	1500.7	1491.8
150°	1533.1	1530.8	1537.8	1551.9	1565.9	1563.6	1565.9	1551.9	1537.8	1530.8	1533.1
152.5°	1580.0	1566.4	1565.9	1572.5	1579.0	1578.6	1579.0	1572.5	1565.9	1566.4	1580.0
155°	1659.7	1633.9	1619.8	1615.1	1615.1	1612.8	1615.1	1615.1	1619.8	1633.9	1659.7
157.5°	1747.4	1711.3	1690.2	1678.9	1675.6	1670.5	1675.6	1678.9	1690.2	1711.3	1747.4
160°	1807.4	1767.5	1746.4	1727.7	1720.6	1713.6	1720.6	1727.7	1746.4	1767.5	1807.4
162.5°	1863.6	1825.7	1802.7	1785.8	1778.8	1768.0	1778.8	1785.8	1802.7	1825.7	1863.6
165°	1955.1	1915.2	1889.4	1875.3	1866.0	1856.6	1866.0	1875.3	1889.4	1915.2	1955.1
167.5°	2046.5	2002.9	1986.0	1970.1	1961.1	1944.3	1961.1	1970.1	1986.0	2002.9	2046.5
170°	2102.7	2062.9	2053.5	2039.4	2023.0	2004.3	2023.0	2039.4	2053.5	2062.9	2102.7
172.5°	2151.5	2124.8	2115.4	2101.3	2096.2	2081.2	2096.2	2101.3	2115.4	2124.8	2151.5
175°	2222.3	2201.2	2201.2	2198.8	2191.8	2177.7	2191.8	2198.8	2201.2	2201.2	2222.3
177.5°	2281.4	2270.1	2277.6	2277.6	2275.7	2262.6	2275.7	2277.6	2277.6	2270.1	2281.4
180°	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7



TEST NUMBER: P1428301

CATALOG NUMBER: SQ2W-PR1-K-150U-050D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1143.3	1143.3	1143.3	1143.3
2.5°	1148.2	1151.0	1144.8	1138.6
5°	1153.0	1155.1	1146.2	1137.4
7.5°	1163.2	1162.3	1149.7	1137.2
10°	1168.5	1166.3	1151.3	1136.3
12.5°	1163.9	1165.7	1148.2	1130.7
15°	1147.2	1155.6	1134.9	1114.1
17.5°	1120.7	1128.3	1106.6	1085.0
20°	1103.6	1108.8	1087.6	1066.4
22.5°	1088.7	1092.0	1070.8	1049.6
25°	1063.2	1062.9	1044.2	1025.6
27.5°	1029.6	1022.4	1011.4	1000.4
30°	1006.9	993.4	986.2	978.9
32.5°	983.3	964.3	960.0	955.6
35°	948.6	924.4	920.8	917.2
37.5°	906.1	886.4	879.0	871.5
40°	876.0	862.8	850.4	837.9
42.5°	839.6	836.7	816.8	796.9
45°	770.3	785.7	758.8	731.9
47.5°	681.5	710.5	682.9	655.2
50°	616.5	649.4	627.1	604.8
52.5°	553.1	585.7	569.6	553.6
55°	460.7	490.9	482.6	474.3
57.5°	383.6	412.2	406.9	401.6
60°	336.0	365.0	361.4	357.8
62.5°	295.3	323.3	320.5	317.7
65°	242.4	266.2	263.6	261.1
67.5°	199.1	218.8	217.4	216.1
70°	173.6	191.0	190.5	190.0
72.5°	149.7	165.2	165.9	166.7
75°	115.8	128.6	130.1	131.7
77.5°	84.4	95.0	96.7	98.4
80°	64.5	72.8	74.8	76.9
82.5°	46.5	51.5	54.4	57.3
85°	22.1	22.8	25.4	28.0
87.5°	14.3	12.6	10.7	8.9
90°	42.2	25.8	16.4	7.0
92.5°	91.0	63.3	44.5	25.8
95°	182.8	145.3	103.1	72.7
97.5°	291.1	230.7	188.9	138.8
100°	349.3	290.7	250.8	196.9
102.5°	413.0	363.8	309.0	255.0
105°	527.4	466.5	403.2	342.3
107.5°	633.4	566.4	490.4	435.5
110°	700.9	628.2	548.5	499.3



TEST NUMBER: P1428301

CATALOG NUMBER: SQ2W-PR1-K-150U-050D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	766.5	692.0	610.4	561.2
115°	855.6	773.6	698.6	656.4
117.5°	941.4	857.0	777.8	744.5
120°	993.9	909.5	832.2	806.4
122.5°	1037.1	954.6	882.8	872.0
125°	1101.8	1017.4	956.4	970.5
127.5°	1154.3	1076.9	1038.5	1069.9
130°	1186.2	1118.2	1094.7	1139.3
132.5°	1214.3	1161.3	1151.0	1212.4
135°	1256.5	1226.0	1235.4	1319.8
137.5°	1306.6	1294.9	1326.3	1432.8
140°	1338.5	1345.6	1390.1	1509.7
142.5°	1381.7	1398.1	1455.7	1582.8
145°	1448.7	1483.9	1558.9	1685.5
147.5°	1524.7	1570.1	1663.0	1792.8
150°	1575.3	1633.9	1732.4	1856.6
152.5°	1633.4	1693.9	1792.4	1918.5
155°	1723.0	1791.0	1894.1	2001.9
157.5°	1814.4	1883.8	1982.2	2076.5
160°	1870.7	1945.7	2034.8	2121.5
162.5°	1934.4	2003.8	2081.6	2159.0
165°	2027.7	2084.0	2147.3	2212.9
167.5°	2106.0	2152.9	2202.6	2253.7
170°	2156.7	2194.2	2236.4	2276.2
172.5°	2199.8	2229.8	2260.7	2295.0
175°	2257.5	2273.9	2292.6	2313.7
177.5°	2302.0	2307.6	2313.2	2322.6
180°	2320.7	2320.7	2320.7	2320.7



TEST NUMBER: P1428301
 CATALOG NUMBER: SQ2W-PR1-K-150U-050D-L840-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.41	15.09	15.54	16.20	17.75	10.78	11.46	11.90	12.57	14.12
	3H	15.60	16.21	16.74	17.33	18.90	11.93	12.53	13.06	13.66	15.22
	4H	16.08	16.66	17.22	17.78	19.35	12.38	12.96	13.52	14.08	15.65
	6H	16.37	16.90	17.52	18.02	19.60	12.71	13.24	13.87	14.37	15.95
	8H	16.47	16.97	17.62	18.11	19.68	12.85	13.35	14.00	14.49	16.06
	12H	16.50	16.98	17.66	18.11	19.70	12.87	13.35	14.03	14.48	16.08
4H	2H	14.49	15.07	15.64	16.19	17.76	11.47	12.04	12.62	13.17	14.73
	3H	15.94	16.41	17.09	17.56	19.14	12.81	13.28	13.96	14.43	16.01
	4H	16.56	17.00	17.71	18.13	19.73	13.34	13.78	14.50	14.92	16.52
	6H	16.98	17.35	18.14	18.51	20.10	13.77	14.14	14.93	15.30	16.89
	8H	17.13	17.48	18.30	18.64	20.24	13.95	14.30	15.11	15.45	17.06
	12H	17.19	17.51	18.37	18.67	20.28	13.99	14.31	15.17	15.47	17.08
8H	4H	16.57	16.92	17.73	18.07	19.68	13.66	14.01	14.82	15.16	16.77
	6H	17.10	17.38	18.28	18.58	20.18	14.19	14.48	15.38	15.68	17.28
	8H	17.33	17.58	18.52	18.75	20.38	14.46	14.71	15.64	15.88	17.50
	12H	17.44	17.66	18.63	18.83	20.49	14.54	14.76	15.73	15.93	17.59
12H	4H	16.52	16.84	17.70	18.00	19.61	13.67	13.99	14.85	15.15	16.76
	6H	17.09	17.34	18.27	18.51	20.13	14.27	14.52	15.45	15.69	17.31
	8H	17.33	17.55	18.52	18.72	20.38	14.55	14.77	15.74	15.94	17.59