

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428582

Luminaire Tested: SQ2W-WBN-0U-100D-L935-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428582
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2308-130-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-WBN-0U-100D-L935-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - WHITE DISCREET BAFFLE, NARROW 35-DEGREE OPTIC
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT N/A - DIRECT ONLY
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4376.6 lumens
Efficiency: N/A
Efficacy: 114.9 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.58 / 0.63
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 38.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428582

CATALOG NUMBER: SQ2W-WBN-0U-100D-L935-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428582

CATALOG NUMBER: SQ2W-WBN-0U-100D-L935-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93				
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	87				
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	81				
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75				
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70				
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66				
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62				
8	80	71	65	61	79	70	64	60	69	64	60	68	63	60	67	63	60	58				
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	60	57	55				
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	121689	121689	121689	121689
5°	117494	117624	117494	117624
10°	101558	101799	101558	101799
15°	80814	78579	80814	78579
20°	57409	57064	57409	57064
25°	41303	40206	41303	40206
30°	31557	30635	31557	30635
35°	24772	23717	24772	23717
40°	18769	17614	18769	17614
45°	10501	9373	10501	9373
50°	3695	3258	3695	3258
55°	2258	2145	2258	2145
60°	1728	1598	1728	1598
65°	1582	1482	1582	1482
70°	1515	1388	1515	1388
75°	1416	1335	1416	1335
80°	1246	1246	1246	1246
85°	1241	982	1241	982

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 40°
 Vertical Angle: 45°
 Luminance: 12453 cd/sqm



TEST NUMBER: P1428582

CATALOG NUMBER: SQ2W-WBN-0U-100D-L935-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	654.3	14.9
10°-20°	1300.3	29.7
20°-30°	1076.8	24.6
30°-40°	774.7	17.7
40°-50°	394.6	9.0
50°-60°	102.6	2.3
60°-70°	42.6	1.0
70°-80°	23.7	0.5
80°-90°	7.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3031.4	69.3
0°-40°	3806.1	87.0
0°-60°	4303.3	98.3
0°-90°	4376.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4376.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	7537	7537	7537	7537	7537	
5°	7250	7258	7250	7258	7250	654
15°	4835	4701	4835	4701	4835	1312
25°	2318	2257	2318	2257	2318	1091
35°	1257	1203	1257	1203	1257	789
45°	460	410	460	410	460	368
55°	80	76	80	76	80	79
65°	41	39	41	39	41	41
75°	23	21	23	21	23	24
85°	7	5	7	5	7	7
90°	0	0	0	0	0	



TEST NUMBER: P1428582

CATALOG NUMBER: SQ2W-WBN-0U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	7537.0	7537.0	7537.0	7537.0	7537.0	7537.0	7537.0	7537.0	7537.0	7537.0	7537.0
2.5°	7525.2	7519.5	7513.8	7488.5	7456.6	7454.0	7480.6	7498.9	7492.3	7485.6	7492.3
5°	7249.5	7244.8	7240.0	7218.3	7191.0	7200.5	7246.8	7278.9	7268.2	7257.5	7268.2
7.5°	6680.2	6684.2	6688.3	6677.2	6661.0	6673.4	6714.4	6742.3	6730.9	6719.5	6730.9
10°	6194.6	6205.3	6216.0	6200.8	6177.0	6195.2	6255.2	6290.1	6249.7	6209.3	6249.7
12.5°	5658.7	5651.8	5644.9	5631.1	5614.9	5611.6	5621.2	5622.9	5600.5	5578.2	5600.5
15°	4834.8	4809.8	4784.9	4746.5	4703.8	4689.8	4704.7	4714.2	4707.6	4701.1	4707.6
17.5°	3894.3	3903.9	3913.6	3887.6	3849.8	3830.2	3828.8	3825.9	3818.5	3811.1	3818.5
20°	3341.3	3344.3	3347.2	3331.0	3308.5	3303.1	3315.0	3323.6	3322.4	3321.2	3322.4
22.5°	2896.3	2896.9	2897.5	2876.1	2847.3	2841.7	2859.3	2869.9	2859.2	2848.5	2859.2
25°	2318.5	2316.7	2314.9	2300.6	2282.2	2268.5	2259.6	2253.4	2255.2	2256.9	2255.2
27.5°	1901.3	1893.9	1886.6	1874.4	1860.6	1856.7	1862.6	1866.0	1861.6	1857.2	1861.6
30°	1692.7	1686.8	1680.8	1668.6	1654.4	1649.0	1652.6	1653.9	1648.6	1643.2	1648.6
32.5°	1505.5	1505.8	1506.0	1495.0	1480.3	1472.1	1470.4	1468.2	1464.3	1460.3	1464.3
35°	1256.8	1260.4	1264.0	1255.0	1242.0	1231.0	1222.1	1214.0	1208.7	1203.3	1208.7
37.5°	1034.9	1038.2	1041.5	1034.1	1023.0	1011.0	997.9	987.0	982.4	977.9	982.4
40°	890.5	892.9	895.2	890.0	882.3	870.7	855.3	842.8	839.2	835.7	839.2
42.5°	733.2	743.2	753.2	749.9	742.2	731.1	716.6	703.7	695.9	688.0	695.9
45°	459.9	491.4	522.9	537.1	545.4	541.5	525.5	502.0	456.2	410.5	456.2
47.5°	232.6	276.3	319.9	351.2	378.4	369.7	325.2	280.5	235.6	190.7	235.6
50°	147.1	177.4	207.7	246.0	287.0	278.1	219.3	170.1	149.9	129.7	149.9
52.5°	112.8	128.4	144.0	180.4	223.8	219.6	167.9	126.4	115.2	104.0	115.2
55°	80.2	86.2	92.1	112.3	137.3	135.8	107.9	85.7	81.0	76.2	81.0
57.5°	62.0	65.4	68.7	76.2	85.1	84.3	73.7	65.0	62.1	59.1	62.1
60°	53.5	55.9	58.2	62.0	66.1	65.5	60.2	55.4	52.4	49.5	52.4
62.5°	48.1	49.6	51.0	52.7	54.5	53.6	50.2	47.3	46.3	45.2	46.3
65°	41.4	42.0	42.6	42.8	42.8	42.2	41.0	40.0	39.4	38.8	39.4
67.5°	35.3	35.9	36.5	36.5	36.4	36.1	35.5	34.9	34.3	33.7	34.3
70°	32.1	32.7	33.3	33.0	32.4	31.8	31.2	30.6	30.0	29.4	30.0
72.5°	27.8	28.4	29.0	28.7	28.1	27.8	27.6	27.4	26.8	26.2	26.8
75°	22.7	22.7	22.7	22.7	22.7	22.4	21.8	21.4	21.4	21.4	21.4
77.5°	17.6	17.8	17.9	17.5	16.9	16.6	16.6	16.5	16.0	15.5	16.0
80°	13.4	14.0	14.6	14.3	13.7	13.4	13.4	13.4	13.4	13.4	13.4
82.5°	11.2	11.4	11.5	11.1	10.5	10.2	10.2	10.2	10.2	10.2	10.2
85°	6.7	6.7	6.7	6.2	5.6	5.6	6.2	6.5	5.9	5.3	5.9
87.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1428582

CATALOG NUMBER: SQ2W-WBN-0U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	7537.0	7537.0	7537.0	7537.0	7537.0	7537.0	7537.0	7537.0	7537.0	7537.0	7537.0
2.5°	7498.9	7480.6	7454.0	7456.6	7488.5	7513.8	7519.5	7525.2	7519.5	7513.8	7488.5
5°	7278.9	7246.8	7200.5	7191.0	7218.3	7240.0	7244.8	7249.5	7244.8	7240.0	7218.3
7.5°	6742.3	6714.4	6673.4	6661.0	6677.2	6688.3	6684.2	6680.2	6684.2	6688.3	6677.2
10°	6290.1	6255.2	6195.2	6177.0	6200.8	6216.0	6205.3	6194.6	6205.3	6216.0	6200.8
12.5°	5622.9	5621.2	5611.6	5614.9	5631.1	5644.9	5651.8	5658.7	5651.8	5644.9	5631.1
15°	4714.2	4704.7	4689.8	4703.8	4746.5	4784.9	4809.8	4834.8	4809.8	4784.9	4746.5
17.5°	3825.9	3828.8	3830.2	3849.8	3887.6	3913.6	3903.9	3894.3	3903.9	3913.6	3887.6
20°	3323.6	3315.0	3303.1	3308.5	3331.0	3347.2	3344.3	3341.3	3344.3	3347.2	3331.0
22.5°	2869.9	2859.3	2841.7	2847.3	2876.1	2897.5	2896.9	2896.3	2896.9	2897.5	2876.1
25°	2253.4	2259.6	2268.5	2282.2	2300.6	2314.9	2316.7	2318.5	2316.7	2314.9	2300.6
27.5°	1866.0	1862.6	1856.7	1860.6	1874.4	1886.6	1893.9	1901.3	1893.9	1886.6	1874.4
30°	1653.9	1652.6	1649.0	1654.4	1668.6	1680.8	1686.8	1692.7	1686.8	1680.8	1668.6
32.5°	1468.2	1470.4	1472.1	1480.3	1495.0	1506.0	1505.8	1505.5	1505.8	1506.0	1495.0
35°	1214.0	1222.1	1231.0	1242.0	1255.0	1264.0	1260.4	1256.8	1260.4	1264.0	1255.0
37.5°	987.0	997.9	1011.0	1023.0	1034.1	1041.5	1038.2	1034.9	1038.2	1041.5	1034.1
40°	842.8	855.3	870.7	882.3	890.0	895.2	892.9	890.5	892.9	895.2	890.0
42.5°	703.7	716.6	731.1	742.2	749.9	753.2	743.2	733.2	743.2	753.2	749.9
45°	502.0	525.5	541.5	545.4	537.1	522.9	491.4	459.9	491.4	522.9	537.1
47.5°	280.5	325.2	369.7	378.4	351.2	319.9	276.3	232.6	276.3	319.9	351.2
50°	170.1	219.3	278.1	287.0	246.0	207.7	177.4	147.1	177.4	207.7	246.0
52.5°	126.4	167.9	219.6	223.8	180.4	144.0	128.4	112.8	128.4	144.0	180.4
55°	85.7	107.9	135.8	137.3	112.3	92.1	86.2	80.2	86.2	92.1	112.3
57.5°	65.0	73.7	84.3	85.1	76.2	68.7	65.4	62.0	65.4	68.7	76.2
60°	55.4	60.2	65.5	66.1	62.0	58.2	55.9	53.5	55.9	58.2	62.0
62.5°	47.3	50.2	53.6	54.5	52.7	51.0	49.6	48.1	49.6	51.0	52.7
65°	40.0	41.0	42.2	42.8	42.8	42.6	42.0	41.4	42.0	42.6	42.8
67.5°	34.9	35.5	36.1	36.4	36.5	36.5	35.9	35.3	35.9	36.5	36.5
70°	30.6	31.2	31.8	32.4	33.0	33.3	32.7	32.1	32.7	33.3	33.0
72.5°	27.4	27.6	27.8	28.1	28.7	29.0	28.4	27.8	28.4	29.0	28.7
75°	21.4	21.8	22.4	22.7	22.7	22.7	22.7	22.7	22.7	22.7	22.7
77.5°	16.5	16.6	16.6	16.9	17.5	17.9	17.8	17.6	17.8	17.9	17.5
80°	13.4	13.4	13.4	13.7	14.3	14.6	14.0	13.4	14.0	14.6	14.3
82.5°	10.2	10.2	10.2	10.5	11.1	11.5	11.4	11.2	11.4	11.5	11.1
85°	6.5	6.2	5.6	5.6	6.2	6.7	6.7	6.7	6.7	6.7	6.2
87.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1428582

CATALOG NUMBER: SQ2W-WBN-0U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	7537.0	7537.0	7537.0	7537.0	7537.0	7537.0	7537.0	7537.0	7537.0	7537.0	7537.0
2.5°	7456.6	7454.0	7480.6	7498.9	7492.3	7485.6	7492.3	7498.9	7480.6	7454.0	7456.6
5°	7191.0	7200.5	7246.8	7278.9	7268.2	7257.5	7268.2	7278.9	7246.8	7200.5	7191.0
7.5°	6661.0	6673.4	6714.4	6742.3	6730.9	6719.5	6730.9	6742.3	6714.4	6673.4	6661.0
10°	6177.0	6195.2	6255.2	6290.1	6249.7	6209.3	6249.7	6290.1	6255.2	6195.2	6177.0
12.5°	5614.9	5611.6	5621.2	5622.9	5600.5	5578.2	5600.5	5622.9	5621.2	5611.6	5614.9
15°	4703.8	4689.8	4704.7	4714.2	4707.6	4701.1	4707.6	4714.2	4704.7	4689.8	4703.8
17.5°	3849.8	3830.2	3828.8	3825.9	3818.5	3811.1	3818.5	3825.9	3828.8	3830.2	3849.8
20°	3308.5	3303.1	3315.0	3323.6	3322.4	3321.2	3322.4	3323.6	3315.0	3303.1	3308.5
22.5°	2847.3	2841.7	2859.3	2869.9	2859.2	2848.5	2859.2	2869.9	2859.3	2841.7	2847.3
25°	2282.2	2268.5	2259.6	2253.4	2255.2	2256.9	2255.2	2253.4	2259.6	2268.5	2282.2
27.5°	1860.6	1856.7	1862.6	1866.0	1861.6	1857.2	1861.6	1866.0	1862.6	1856.7	1860.6
30°	1654.4	1649.0	1652.6	1653.9	1648.6	1643.2	1648.6	1653.9	1652.6	1649.0	1654.4
32.5°	1480.3	1472.1	1470.4	1468.2	1464.3	1460.3	1464.3	1468.2	1470.4	1472.1	1480.3
35°	1242.0	1231.0	1222.1	1214.0	1208.7	1203.3	1208.7	1214.0	1222.1	1231.0	1242.0
37.5°	1023.0	1011.0	997.9	987.0	982.4	977.9	982.4	987.0	997.9	1011.0	1023.0
40°	882.3	870.7	855.3	842.8	839.2	835.7	839.2	842.8	855.3	870.7	882.3
42.5°	742.2	731.1	716.6	703.7	695.9	688.0	695.9	703.7	716.6	731.1	742.2
45°	545.4	541.5	525.5	502.0	456.2	410.5	456.2	502.0	525.5	541.5	545.4
47.5°	378.4	369.7	325.2	280.5	235.6	190.7	235.6	280.5	325.2	369.7	378.4
50°	287.0	278.1	219.3	170.1	149.9	129.7	149.9	170.1	219.3	278.1	287.0
52.5°	223.8	219.6	167.9	126.4	115.2	104.0	115.2	126.4	167.9	219.6	223.8
55°	137.3	135.8	107.9	85.7	81.0	76.2	81.0	85.7	107.9	135.8	137.3
57.5°	85.1	84.3	73.7	65.0	62.1	59.1	62.1	65.0	73.7	84.3	85.1
60°	66.1	65.5	60.2	55.4	52.4	49.5	52.4	55.4	60.2	65.5	66.1
62.5°	54.5	53.6	50.2	47.3	46.3	45.2	46.3	47.3	50.2	53.6	54.5
65°	42.8	42.2	41.0	40.0	39.4	38.8	39.4	40.0	41.0	42.2	42.8
67.5°	36.4	36.1	35.5	34.9	34.3	33.7	34.3	34.9	35.5	36.1	36.4
70°	32.4	31.8	31.2	30.6	30.0	29.4	30.0	30.6	31.2	31.8	32.4
72.5°	28.1	27.8	27.6	27.4	26.8	26.2	26.8	27.4	27.6	27.8	28.1
75°	22.7	22.4	21.8	21.4	21.4	21.4	21.4	21.4	21.8	22.4	22.7
77.5°	16.9	16.6	16.6	16.5	16.0	15.5	16.0	16.5	16.6	16.6	16.9
80°	13.7	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.7
82.5°	10.5	10.2	10.2	10.2	10.2	10.2	10.2	10.2	10.2	10.2	10.5
85°	5.6	5.6	6.2	6.5	5.9	5.3	5.9	6.5	6.2	5.6	5.6
87.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1428582

CATALOG NUMBER: SQ2W-WBN-0U-100D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	7537.0	7537.0	7537.0	7537.0
2.5°	7488.5	7513.8	7519.5	7525.2
5°	7218.3	7240.0	7244.8	7249.5
7.5°	6677.2	6688.3	6684.2	6680.2
10°	6200.8	6216.0	6205.3	6194.6
12.5°	5631.1	5644.9	5651.8	5658.7
15°	4746.5	4784.9	4809.8	4834.8
17.5°	3887.6	3913.6	3903.9	3894.3
20°	3331.0	3347.2	3344.3	3341.3
22.5°	2876.1	2897.5	2896.9	2896.3
25°	2300.6	2314.9	2316.7	2318.5
27.5°	1874.4	1886.6	1893.9	1901.3
30°	1668.6	1680.8	1686.8	1692.7
32.5°	1495.0	1506.0	1505.8	1505.5
35°	1255.0	1264.0	1260.4	1256.8
37.5°	1034.1	1041.5	1038.2	1034.9
40°	890.0	895.2	892.9	890.5
42.5°	749.9	753.2	743.2	733.2
45°	537.1	522.9	491.4	459.9
47.5°	351.2	319.9	276.3	232.6
50°	246.0	207.7	177.4	147.1
52.5°	180.4	144.0	128.4	112.8
55°	112.3	92.1	86.2	80.2
57.5°	76.2	68.7	65.4	62.0
60°	62.0	58.2	55.9	53.5
62.5°	52.7	51.0	49.6	48.1
65°	42.8	42.6	42.0	41.4
67.5°	36.5	36.5	35.9	35.3
70°	33.0	33.3	32.7	32.1
72.5°	28.7	29.0	28.4	27.8
75°	22.7	22.7	22.7	22.7
77.5°	17.5	17.9	17.8	17.6
80°	14.3	14.6	14.0	13.4
82.5°	11.1	11.5	11.4	11.2
85°	6.2	6.7	6.7	6.7
87.5°	2.1	2.1	2.1	2.1
90°	0.0	0.0	0.0	0.0



TEST NUMBER: P1428582
 CATALOG NUMBER: SQ2W-WBN-0U-100D-L935-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.15	8.21	7.52	8.53	8.84	6.77	7.84	7.14	8.15	8.46
	3H	8.39	9.32	8.77	9.66	10.02	7.99	8.93	8.38	9.26	9.63
	4H	8.92	9.78	9.33	10.14	10.52	8.52	9.38	8.93	9.74	10.13
	6H	9.28	10.07	9.70	10.44	10.84	8.86	9.65	9.28	10.02	10.42
	8H	9.43	10.17	9.87	10.57	10.97	9.01	9.75	9.44	10.14	10.55
	12H	9.53	10.24	9.96	10.62	11.05	9.08	9.79	9.52	10.17	10.60
4H	2H	7.50	8.36	7.90	8.71	9.10	7.18	8.05	7.59	8.40	8.79
	3H	9.00	9.70	9.42	10.11	10.52	8.66	9.36	9.07	9.77	10.17
	4H	9.65	10.27	10.08	10.69	11.14	9.29	9.92	9.73	10.34	10.79
	6H	10.14	10.68	10.61	11.13	11.60	9.76	10.29	10.23	10.74	11.21
	8H	10.35	10.85	10.82	11.30	11.77	9.95	10.45	10.42	10.90	11.37
	12H	10.49	10.93	10.99	11.41	11.89	10.06	10.50	10.55	10.98	11.46
8H	4H	9.81	10.31	10.28	10.76	11.23	9.49	9.99	9.97	10.44	10.91
	6H	10.44	10.84	10.95	11.34	11.83	10.09	10.48	10.59	10.99	11.47
	8H	10.75	11.10	11.28	11.62	12.12	10.36	10.72	10.90	11.24	11.74
	12H	10.99	11.30	11.51	11.79	12.37	10.57	10.88	11.09	11.38	11.96
12H	4H	9.80	10.23	10.29	10.72	11.19	9.49	9.92	9.98	10.41	10.89
	6H	10.46	10.82	10.99	11.34	11.84	10.12	10.48	10.65	11.00	11.50
	8H	10.83	11.14	11.35	11.63	12.21	10.46	10.77	10.98	11.27	11.84