

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428349

Luminaire Tested: SQ2W-PW1-K-025U-050D-L840-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1428349  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-PW1-K-025U-050D-L840-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - PERCEIVE WAVES LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3845.0 lumens  
Efficiency: N/A  
Efficacy: 152.0 lumens/watt  
Spacing Criteria (0/90/45): 1.27 / 1.11 / 1.23  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 25.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1428349

CATALOG NUMBER: SQ2W-PW1-K-025U-050D-L840-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1428349

CATALOG NUMBER: SQ2W-PW1-K-025U-050D-L840-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	71				71
1	103	99	95	92	98	94	91	88	84	82	80	76	74	72	68	66	65	61				61
2	95	88	82	77	89	83	78	73	75	71	67	68	64	62	61	58	56	53				53
3	87	78	71	65	82	74	68	62	67	62	58	60	56	53	54	51	49	45				45
4	80	69	62	56	76	66	59	54	60	54	50	54	50	46	49	46	43	40				40
5	74	62	54	48	70	59	52	47	54	48	44	49	44	41	45	41	38	35				35
6	68	56	48	42	65	54	46	41	49	43	39	45	40	36	41	37	33	31				31
7	63	51	43	38	60	49	42	37	45	39	34	41	36	32	37	33	30	28				28
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	30	27	25				25
9	55	43	35	30	52	41	34	30	38	32	28	35	30	26	32	28	25	23				23
10	52	40	32	28	49	38	31	27	35	29	25	32	27	24	30	26	23	21				21

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	19757	19757	19757	19757
5°	19625	19964	19625	19964
10°	19660	20138	19660	20138
15°	19655	20259	19655	20259
20°	19663	19864	19663	19864
25°	19557	18458	19557	18458
30°	19424	16686	19424	16686
35°	19273	15068	19273	15068
40°	18889	13314	18889	13314
45°	18148	11629	18148	11629
50°	16889	9952	16889	9952
55°	15451	8070	15451	8070
60°	13850	6962	13850	6962
65°	12111	6189	12111	6189
70°	9904	5613	9904	5613
75°	7704	5159	7704	5159
80°	5746	4547	5746	4547
85°	3890	2593	3890	2593

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 18148 cd/sqm



TEST NUMBER: P1428349

CATALOG NUMBER: SQ2W-PW1-K-025U-050D-L840-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	116.5	3.0
10°-20°	337.6	8.8
20°-30°	496.8	12.9
30°-40°	543.2	14.1
40°-50°	487.3	12.7
50°-60°	363.5	9.5
60°-70°	229.8	6.0
70°-80°	113.8	3.0
80°-90°	28.2	0.7
90°-100°	30.8	0.8
100°-110°	89.7	2.3
110°-120°	146.3	3.8
120°-130°	185.7	4.8
130°-140°	198.7	5.2
140°-150°	185.5	4.8
150°-160°	152.7	4.0
160°-170°	102.4	2.7
170°-180°	36.4	0.9
0°-30°	951.0	24.7
0°-40°	1494.2	38.9
0°-60°	2345.1	61.0
0°-90°	2716.9	70.7
90°-120°	266.8	6.9
90°-150°	836.7	21.8
90°-180°	1128.0	29.3
0°-180°	3845.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1224	1224	1224	1224	1224	
5°	1211	1232	1211	1232	1211	115
15°	1176	1212	1176	1212	1176	332
25°	1098	1036	1098	1036	1098	506
35°	978	764	978	764	978	610
45°	795	509	795	509	795	609
55°	549	287	549	287	549	490
65°	317	162	317	162	317	314
75°	124	83	124	83	124	136
85°	21	14	21	14	21	27
90°	1	9	1	17	1	2
95°	12	9	12	53	12	15
105°	57	91	57	126	57	61
115°	109	151	109	186	109	108
125°	162	240	162	229	162	145
135°	220	314	220	253	220	170
145°	281	362	281	259	281	176
155°	333	393	333	268	333	153
165°	368	410	368	309	368	104
175°	385	402	385	363	385	37
180°	386	386	386	386	386	



TEST NUMBER: P1428349

CATALOG NUMBER: SQ2W-PW1-K-025U-050D-L840-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1223.7	1223.7	1223.7	1223.7	1223.7	1223.7	1223.7	1223.7	1223.7	1223.7	1223.7
2.5°	1215.3	1222.3	1229.4	1227.7	1223.2	1221.1	1221.5	1222.1	1223.4	1224.6	1223.4
5°	1210.9	1219.7	1228.5	1227.2	1222.5	1220.4	1221.0	1222.5	1227.2	1231.8	1227.2
7.5°	1204.8	1213.7	1222.6	1222.2	1218.7	1217.8	1219.6	1222.0	1226.6	1231.1	1226.6
10°	1199.2	1208.5	1217.9	1217.9	1214.8	1214.5	1217.1	1220.1	1224.2	1228.3	1224.2
12.5°	1191.8	1201.5	1211.2	1212.0	1209.7	1210.0	1213.0	1216.3	1220.5	1224.6	1220.5
15°	1175.9	1186.3	1196.6	1198.8	1198.3	1199.9	1203.5	1206.9	1209.4	1212.0	1209.4
17.5°	1157.5	1167.8	1178.2	1180.3	1179.5	1179.6	1180.6	1181.6	1182.8	1184.1	1182.8
20°	1144.4	1154.8	1165.2	1166.6	1165.0	1162.4	1158.8	1156.1	1156.1	1156.1	1156.1
22.5°	1125.8	1137.0	1148.2	1148.2	1144.6	1137.9	1128.0	1119.8	1116.5	1113.2	1116.5
25°	1097.8	1108.7	1119.6	1114.5	1104.2	1088.9	1068.7	1051.6	1043.8	1036.1	1043.8
27.5°	1065.2	1074.0	1082.8	1069.6	1049.1	1024.5	995.8	971.6	960.8	950.0	960.8
30°	1041.9	1048.6	1055.3	1034.5	1004.5	973.6	942.0	915.8	905.4	895.0	905.4
32.5°	1017.6	1020.2	1022.8	995.3	957.8	922.7	889.8	862.4	851.2	840.0	851.2
35°	977.8	973.1	968.5	931.9	884.8	844.7	811.5	784.2	774.4	764.5	774.4
37.5°	930.7	916.8	902.9	861.8	811.5	769.1	734.4	705.6	694.7	683.9	694.7
40°	896.2	876.5	856.8	812.7	760.4	716.9	682.2	653.4	642.5	631.7	642.5
42.5°	858.0	833.3	808.7	763.3	711.0	667.4	632.7	603.9	592.6	581.3	592.6
45°	794.8	765.8	736.8	689.5	636.2	592.7	559.0	531.0	520.2	509.3	520.2
47.5°	723.7	694.9	666.1	619.0	565.7	522.8	490.2	463.4	454.0	444.7	454.0
50°	672.4	644.5	616.5	571.4	520.7	479.0	446.4	419.0	407.6	396.2	407.6
52.5°	620.2	595.2	570.1	526.7	477.2	435.7	402.2	373.2	357.7	342.2	357.7
55°	548.9	525.1	501.3	460.3	413.7	371.8	334.5	304.3	295.5	286.7	295.5
57.5°	475.5	454.9	434.3	397.5	355.3	317.3	283.4	256.2	249.0	241.7	249.0
60°	428.9	410.7	392.6	357.4	316.5	281.8	253.3	230.1	222.9	215.6	222.9
62.5°	384.1	368.1	352.0	318.2	278.6	247.4	224.7	206.2	200.2	194.2	200.2
65°	317.0	305.1	293.2	265.3	232.2	206.3	187.6	172.4	167.2	162.0	167.2
67.5°	251.7	245.1	238.5	217.6	192.0	171.1	154.7	141.6	138.1	134.7	138.1
70°	209.8	207.7	205.6	188.4	166.1	148.3	134.8	124.1	121.5	118.9	121.5
72.5°	173.4	174.2	175.1	160.7	141.4	126.4	115.8	107.5	105.7	104.0	105.7
75°	123.5	127.7	131.8	122.4	108.4	97.8	90.5	84.8	83.8	82.7	83.8
77.5°	84.1	90.4	96.6	90.4	80.2	72.4	67.0	62.7	61.9	61.1	61.9
80°	61.8	68.0	74.2	69.9	62.2	56.2	52.1	48.9	48.9	48.9	48.9
82.5°	43.1	48.1	53.1	50.0	44.3	40.5	38.4	36.8	36.8	36.8	36.8
85°	21.0	23.6	26.2	25.3	23.2	20.6	17.5	15.0	14.5	14.0	14.5
87.5°	5.8	7.4	9.0	8.1	6.2	5.1	4.7	4.4	4.5	4.5	4.5
90°	1.2	2.7	4.7	6.2	7.4	7.8	7.8	8.2	8.6	8.6	8.6
92.5°	4.3	6.8	6.9	6.9	8.4	9.1	9.7	9.8	10.1	10.1	10.1
95°	12.1	13.3	19.9	19.5	13.3	10.5	9.0	9.0	9.0	9.0	9.0
97.5°	23.1	24.8	25.9	34.7	36.7	35.4	28.9	24.3	21.7	20.5	21.7
100°	32.8	33.6	35.9	36.3	46.1	55.4	50.7	44.9	42.9	41.8	42.9
102.5°	42.5	42.9	46.5	48.2	50.4	55.7	72.0	70.2	68.8	68.6	68.8
105°	57.0	57.4	64.0	67.1	68.7	68.7	68.3	76.1	88.6	91.3	88.6
107.5°	72.5	74.3	82.1	90.5	92.3	92.7	90.7	89.5	89.1	89.4	89.1
110°	83.1	85.9	95.2	105.8	108.5	109.3	108.5	107.3	106.5	106.5	106.5



TEST NUMBER: P1428349

CATALOG NUMBER: SQ2W-PW1-K-025U-050D-L840-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	93.4	97.4	108.0	120.1	124.7	127.1	125.4	124.5	123.7	124.3	123.7
115°	109.3	115.1	129.2	141.7	151.0	152.2	151.8	151.8	151.4	151.4	151.4
117.5°	123.9	133.3	149.1	163.6	174.4	177.6	179.1	178.7	178.2	179.0	178.2
120°	134.3	145.2	163.1	179.5	190.1	194.7	196.3	195.5	196.3	195.5	196.3
122.5°	145.2	158.6	176.2	193.3	205.7	211.0	212.9	213.0	213.2	212.7	213.2
125°	161.6	178.0	198.6	216.2	229.1	235.3	236.9	237.3	238.1	240.0	238.1
127.5°	178.1	196.7	219.4	236.3	249.5	257.1	259.5	260.4	262.0	262.9	262.0
130°	189.7	210.7	233.8	249.8	262.7	270.8	275.1	276.3	278.3	277.9	278.3
132.5°	201.8	223.9	247.2	263.8	275.8	284.6	288.3	291.6	292.3	292.9	292.3
135°	219.7	243.5	266.9	283.3	294.7	303.2	307.9	311.0	313.0	314.2	313.0
137.5°	238.5	263.7	286.1	300.7	312.1	319.6	324.9	328.1	330.2	331.1	330.2
140°	251.3	275.5	297.4	312.6	322.8	330.2	334.8	338.8	341.1	341.1	341.1
142.5°	263.5	287.4	308.6	323.8	332.7	339.5	344.5	347.5	350.1	350.1	350.1
145°	280.6	304.4	323.9	339.1	346.6	352.8	358.3	360.6	362.2	362.2	362.2
147.5°	298.5	319.6	337.3	351.9	358.2	365.5	369.8	371.7	373.6	372.8	373.6
150°	309.1	328.6	345.8	359.4	365.7	372.7	377.0	378.6	380.5	379.3	380.5
152.5°	319.4	338.0	353.6	366.3	371.6	378.6	383.6	385.1	386.4	385.6	386.4
155°	333.3	349.7	364.1	375.8	380.5	387.1	391.8	393.8	395.3	393.4	395.3
157.5°	345.7	359.8	372.4	383.2	388.2	393.9	398.2	400.6	402.2	401.4	402.2
160°	353.2	366.1	377.4	387.5	392.2	397.3	402.0	404.7	406.3	405.1	406.3
162.5°	359.4	371.1	381.8	391.0	395.0	399.5	405.1	407.5	409.1	407.6	409.1
165°	368.4	377.8	387.1	395.0	398.5	402.0	407.8	410.6	411.7	410.2	411.7
167.5°	375.2	382.4	390.0	396.7	399.2	402.7	408.5	410.8	412.3	410.3	412.3
170°	379.0	385.2	391.8	397.3	399.2	402.4	408.2	410.2	411.3	409.4	411.3
172.5°	382.1	386.8	392.1	397.0	398.0	400.5	406.0	408.0	408.8	407.2	408.8
175°	385.2	387.9	391.8	395.0	394.6	396.1	400.8	402.4	403.9	401.6	403.9
177.5°	386.7	387.9	389.2	391.0	389.8	389.8	393.2	394.2	394.5	393.2	394.5
180°	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4



TEST NUMBER: P1428349

CATALOG NUMBER: SQ2W-PW1-K-025U-050D-L840-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1223.7	1223.7	1223.7	1223.7	1223.7	1223.7	1223.7	1223.7	1223.7	1223.7	1223.7
2.5°	1222.1	1221.5	1221.1	1223.2	1227.7	1229.4	1222.3	1215.3	1222.3	1229.4	1227.7
5°	1222.5	1221.0	1220.4	1222.5	1227.2	1228.5	1219.7	1210.9	1219.7	1228.5	1227.2
7.5°	1222.0	1219.6	1217.8	1218.7	1222.2	1222.6	1213.7	1204.8	1213.7	1222.6	1222.2
10°	1220.1	1217.1	1214.5	1214.8	1217.9	1217.9	1208.5	1199.2	1208.5	1217.9	1217.9
12.5°	1216.3	1213.0	1210.0	1209.7	1212.0	1211.2	1201.5	1191.8	1201.5	1211.2	1212.0
15°	1206.9	1203.5	1199.9	1198.3	1198.8	1196.6	1186.3	1175.9	1186.3	1196.6	1198.8
17.5°	1181.6	1180.6	1179.6	1179.5	1180.3	1178.2	1167.8	1157.5	1167.8	1178.2	1180.3
20°	1156.1	1158.8	1162.4	1165.0	1166.6	1165.2	1154.8	1144.4	1154.8	1165.2	1166.6
22.5°	1119.8	1128.0	1137.9	1144.6	1148.2	1148.2	1137.0	1125.8	1137.0	1148.2	1148.2
25°	1051.6	1068.7	1088.9	1104.2	1114.5	1119.6	1108.7	1097.8	1108.7	1119.6	1114.5
27.5°	971.6	995.8	1024.5	1049.1	1069.6	1082.8	1074.0	1065.2	1074.0	1082.8	1069.6
30°	915.8	942.0	973.6	1004.5	1034.5	1055.3	1048.6	1041.9	1048.6	1055.3	1034.5
32.5°	862.4	889.8	922.7	957.8	995.3	1022.8	1020.2	1017.6	1020.2	1022.8	995.3
35°	784.2	811.5	844.7	884.8	931.9	968.5	973.1	977.8	973.1	968.5	931.9
37.5°	705.6	734.4	769.1	811.5	861.8	902.9	916.8	930.7	916.8	902.9	861.8
40°	653.4	682.2	716.9	760.4	812.7	856.8	876.5	896.2	876.5	856.8	812.7
42.5°	603.9	632.7	667.4	711.0	763.3	808.7	833.3	858.0	833.3	808.7	763.3
45°	531.0	559.0	592.7	636.2	689.5	736.8	765.8	794.8	765.8	736.8	689.5
47.5°	463.4	490.2	522.8	565.7	619.0	666.1	694.9	723.7	694.9	666.1	619.0
50°	419.0	446.4	479.0	520.7	571.4	616.5	644.5	672.4	644.5	616.5	571.4
52.5°	373.2	402.2	435.7	477.2	526.7	570.1	595.2	620.2	595.2	570.1	526.7
55°	304.3	334.5	371.8	413.7	460.3	501.3	525.1	548.9	525.1	501.3	460.3
57.5°	256.2	283.4	317.3	355.3	397.5	434.3	454.9	475.5	454.9	434.3	397.5
60°	230.1	253.3	281.8	316.5	357.4	392.6	410.7	428.9	410.7	392.6	357.4
62.5°	206.2	224.7	247.4	278.6	318.2	352.0	368.1	384.1	368.1	352.0	318.2
65°	172.4	187.6	206.3	232.2	265.3	293.2	305.1	317.0	305.1	293.2	265.3
67.5°	141.6	154.7	171.1	192.0	217.6	238.5	245.1	251.7	245.1	238.5	217.6
70°	124.1	134.8	148.3	166.1	188.4	205.6	207.7	209.8	207.7	205.6	188.4
72.5°	107.5	115.8	126.4	141.4	160.7	175.1	174.2	173.4	174.2	175.1	160.7
75°	84.8	90.5	97.8	108.4	122.4	131.8	127.7	123.5	127.7	131.8	122.4
77.5°	62.7	67.0	72.4	80.2	90.4	96.6	90.4	84.1	90.4	96.6	90.4
80°	48.9	52.1	56.2	62.2	69.9	74.2	68.0	61.8	68.0	74.2	69.9
82.5°	36.8	38.4	40.5	44.3	50.0	53.1	48.1	43.1	48.1	53.1	50.0
85°	15.0	17.5	20.6	23.2	25.3	26.2	23.6	21.0	23.6	26.2	25.3
87.5°	4.4	4.7	5.1	6.2	8.1	9.0	7.4	5.8	7.4	8.9	8.2
90°	8.2	7.8	7.8	7.4	6.2	4.7	2.7	1.2	2.7	4.3	7.0
92.5°	9.8	9.7	9.1	8.4	6.9	6.9	6.8	4.3	7.4	10.5	15.1
95°	9.0	9.0	10.5	13.3	19.5	19.9	13.3	12.1	17.2	24.2	30.4
97.5°	24.3	28.9	35.4	36.7	34.7	25.9	24.8	23.1	31.5	38.4	48.5
100°	44.9	50.7	55.4	46.1	36.3	35.9	33.6	32.8	41.8	48.4	58.1
102.5°	70.2	72.0	55.7	50.4	48.2	46.5	42.9	42.5	51.4	60.6	68.8
105°	76.1	68.3	68.7	68.7	67.1	64.0	57.4	57.0	67.1	77.7	87.8
107.5°	89.5	90.7	92.7	92.3	90.5	82.1	74.3	72.5	81.6	94.3	105.5
110°	107.3	108.5	109.3	108.5	105.8	95.2	85.9	83.1	91.3	104.6	116.7



TEST NUMBER: P1428349

CATALOG NUMBER: SQ2W-PW1-K-025U-050D-L840-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	124.5	125.4	127.1	124.7	120.1	108.0	97.4	93.4	101.6	115.2	127.6
115°	151.8	151.8	152.2	151.0	141.7	129.2	115.1	109.3	116.3	128.8	142.4
117.5°	178.7	179.1	177.6	174.4	163.6	149.1	133.3	123.9	129.5	142.7	156.7
120°	195.5	196.3	194.7	190.1	179.5	163.1	145.2	134.3	138.5	151.4	165.5
122.5°	213.0	212.9	211.0	205.7	193.3	176.2	158.6	145.2	147.0	158.9	172.7
125°	237.3	236.9	235.3	229.1	216.2	198.6	178.0	161.6	159.2	169.4	183.4
127.5°	260.4	259.5	257.1	249.5	236.3	219.4	196.7	178.1	172.9	179.3	192.2
130°	276.3	275.1	270.8	262.7	249.8	233.8	210.7	189.7	182.3	186.2	197.5
132.5°	291.6	288.3	284.6	275.8	263.8	247.2	223.9	201.8	191.6	193.3	202.2
135°	311.0	307.9	303.2	294.7	283.3	266.9	243.5	219.7	205.7	204.1	209.2
137.5°	328.1	324.9	319.6	312.1	300.7	286.1	263.7	238.5	220.8	215.6	217.5
140°	338.8	334.8	330.2	322.8	312.6	297.4	275.5	251.3	231.4	224.0	222.8
142.5°	347.5	344.5	339.5	332.7	323.8	308.6	287.4	263.5	242.4	232.8	230.0
145°	360.6	358.3	352.8	346.6	339.1	323.9	304.4	280.6	259.5	247.0	241.2
147.5°	371.7	369.8	365.5	358.2	351.9	337.3	319.6	298.5	276.9	261.4	253.8
150°	378.6	377.0	372.7	365.7	359.4	345.8	328.6	309.1	288.4	272.0	262.3
152.5°	385.1	383.6	378.6	371.6	366.3	353.6	338.0	319.4	298.4	282.0	271.9
155°	393.8	391.8	387.1	380.5	375.8	364.1	349.7	333.3	315.3	298.2	286.8
157.5°	400.6	398.2	393.9	388.2	383.2	372.4	359.8	345.7	330.0	313.6	302.1
160°	404.7	402.0	397.3	392.2	387.5	377.4	366.1	353.2	338.8	323.9	311.4
162.5°	407.5	405.1	399.5	395.0	391.0	381.8	371.1	359.4	346.6	333.6	322.0
165°	410.6	407.8	402.0	398.5	395.0	387.1	377.8	368.4	357.5	346.9	337.6
167.5°	410.8	408.5	402.7	399.2	396.7	390.0	382.4	375.2	366.7	358.4	350.6
170°	410.2	408.2	402.4	399.2	397.3	391.8	385.2	379.0	372.3	365.3	359.0
172.5°	408.0	406.0	400.5	398.0	397.0	392.1	386.8	382.1	376.4	371.2	366.2
175°	402.4	400.8	396.1	394.6	395.0	391.8	387.9	385.2	381.7	378.6	375.8
177.5°	394.2	393.2	389.8	389.8	391.0	389.2	387.9	386.7	385.1	384.2	383.2
180°	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4



TEST NUMBER: P1428349

CATALOG NUMBER: SQ2W-PW1-K-025U-050D-L840-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1223.7	1223.7	1223.7	1223.7	1223.7	1223.7	1223.7	1223.7	1223.7	1223.7	1223.7
2.5°	1223.2	1221.1	1221.5	1222.1	1223.4	1224.6	1223.4	1222.1	1221.5	1221.1	1223.2
5°	1222.5	1220.4	1221.0	1222.5	1227.2	1231.8	1227.2	1222.5	1221.0	1220.4	1222.5
7.5°	1218.7	1217.8	1219.6	1222.0	1226.6	1231.1	1226.6	1222.0	1219.6	1217.8	1218.7
10°	1214.8	1214.5	1217.1	1220.1	1224.2	1228.3	1224.2	1220.1	1217.1	1214.5	1214.8
12.5°	1209.7	1210.0	1213.0	1216.3	1220.5	1224.6	1220.5	1216.3	1213.0	1210.0	1209.7
15°	1198.3	1199.9	1203.5	1206.9	1209.4	1212.0	1209.4	1206.9	1203.5	1199.9	1198.3
17.5°	1179.5	1179.6	1180.6	1181.6	1182.8	1184.1	1182.8	1181.6	1180.6	1179.6	1179.5
20°	1165.0	1162.4	1158.8	1156.1	1156.1	1156.1	1156.1	1156.1	1158.8	1162.4	1165.0
22.5°	1144.6	1137.9	1128.0	1119.8	1116.5	1113.2	1116.5	1119.8	1128.0	1137.9	1144.6
25°	1104.2	1088.9	1068.7	1051.6	1043.8	1036.1	1043.8	1051.6	1068.7	1088.9	1104.2
27.5°	1049.1	1024.5	995.8	971.6	960.8	950.0	960.8	971.6	995.8	1024.5	1049.1
30°	1004.5	973.6	942.0	915.8	905.4	895.0	905.4	915.8	942.0	973.6	1004.5
32.5°	957.8	922.7	889.8	862.4	851.2	840.0	851.2	862.4	889.8	922.7	957.8
35°	884.8	844.7	811.5	784.2	774.4	764.5	774.4	784.2	811.5	844.7	884.8
37.5°	811.5	769.1	734.4	705.6	694.7	683.9	694.7	705.6	734.4	769.1	811.5
40°	760.4	716.9	682.2	653.4	642.5	631.7	642.5	653.4	682.2	716.9	760.4
42.5°	711.0	667.4	632.7	603.9	592.6	581.3	592.6	603.9	632.7	667.4	711.0
45°	636.2	592.7	559.0	531.0	520.2	509.3	520.2	531.0	559.0	592.7	636.2
47.5°	565.7	522.8	490.2	463.4	454.0	444.7	454.0	463.4	490.2	522.8	565.7
50°	520.7	479.0	446.4	419.0	407.6	396.2	407.6	419.0	446.4	479.0	520.7
52.5°	477.2	435.7	402.2	373.2	357.7	342.2	357.7	373.2	402.2	435.7	477.2
55°	413.7	371.8	334.5	304.3	295.5	286.7	295.5	304.3	334.5	371.8	413.7
57.5°	355.3	317.3	283.4	256.2	249.0	241.7	249.0	256.2	283.4	317.3	355.3
60°	316.5	281.8	253.3	230.1	222.9	215.6	222.9	230.1	253.3	281.8	316.5
62.5°	278.6	247.4	224.7	206.2	200.2	194.2	200.2	206.2	224.7	247.4	278.6
65°	232.2	206.3	187.6	172.4	167.2	162.0	167.2	172.4	187.6	206.3	232.2
67.5°	192.0	171.1	154.7	141.6	138.1	134.7	138.1	141.6	154.7	171.1	192.0
70°	166.1	148.3	134.8	124.1	121.5	118.9	121.5	124.1	134.8	148.3	166.1
72.5°	141.4	126.4	115.8	107.5	105.7	104.0	105.7	107.5	115.8	126.4	141.4
75°	108.4	97.8	90.5	84.8	83.8	82.7	83.8	84.8	90.5	97.8	108.4
77.5°	80.2	72.4	67.0	62.7	61.9	61.1	61.9	62.7	67.0	72.4	80.2
80°	62.2	56.2	52.1	48.9	48.9	48.9	48.9	48.9	52.1	56.2	62.2
82.5°	44.3	40.5	38.4	36.8	36.8	36.8	36.8	36.8	38.4	40.5	44.3
85°	23.2	20.6	17.5	15.0	14.5	14.0	14.5	15.0	17.5	20.6	23.2
87.5°	6.6	5.9	6.0	6.0	6.3	6.2	6.3	6.0	6.0	5.9	6.6
90°	9.0	11.7	14.4	16.0	17.6	16.8	17.6	16.0	14.4	11.7	9.0
92.5°	18.0	22.6	26.0	28.8	30.1	29.9	30.1	28.8	26.0	22.6	18.0
95°	36.3	41.8	47.2	51.1	53.5	52.7	53.5	51.1	47.2	41.8	36.3
97.5°	56.0	63.3	69.4	73.1	75.4	77.0	75.4	73.1	69.4	63.3	56.0
100°	69.1	76.1	83.1	87.4	91.3	92.9	91.3	87.4	83.1	76.1	69.1
102.5°	79.7	88.9	96.6	101.2	104.4	106.0	104.4	101.2	96.6	88.9	79.7
105°	97.2	106.9	115.1	121.0	124.5	125.7	124.5	121.0	115.1	106.9	97.2
107.5°	114.7	124.7	132.3	138.8	143.1	145.6	143.1	138.8	132.3	124.7	114.7
110°	128.4	136.6	144.8	150.6	154.9	156.5	154.9	150.6	144.8	136.6	128.4



TEST NUMBER: P1428349

CATALOG NUMBER: SQ2W-PW1-K-025U-050D-L840-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	140.0	149.1	157.3	163.1	168.0	170.2	168.0	163.1	157.3	149.1	140.0
115°	156.1	168.2	175.6	181.1	184.6	186.5	184.6	181.1	175.6	168.2	156.1
117.5°	169.5	182.2	190.3	194.5	196.1	197.6	196.1	194.5	190.3	182.2	169.5
120°	178.0	189.7	199.0	204.5	206.5	207.2	206.5	204.5	199.0	189.7	178.0
122.5°	185.8	196.9	205.9	212.6	215.8	216.6	215.8	212.6	205.9	196.9	185.8
125°	196.7	207.2	216.6	223.2	226.7	228.7	226.7	223.2	216.6	207.2	196.7
127.5°	206.2	217.6	226.2	232.2	235.6	237.2	235.6	232.2	226.2	217.6	206.2
130°	211.5	223.2	231.8	238.5	241.6	243.1	241.6	238.5	231.8	223.2	211.5
132.5°	215.6	227.9	236.8	242.8	246.3	247.8	246.3	242.8	236.8	227.9	215.6
135°	220.5	233.4	242.7	248.6	251.7	253.3	251.7	248.6	242.7	233.4	220.5
137.5°	224.8	236.5	246.3	252.4	255.2	256.2	255.2	252.4	246.3	236.5	224.8
140°	227.9	238.1	247.8	253.7	256.8	257.2	256.8	253.7	247.8	238.1	227.9
142.5°	232.0	239.9	248.4	254.3	257.4	258.1	257.4	254.3	248.4	239.9	232.0
145°	239.2	243.9	249.8	255.2	258.0	258.7	258.0	255.2	249.8	243.9	239.2
147.5°	248.4	249.8	252.9	256.5	259.1	259.7	259.1	256.5	252.9	249.8	248.4
150°	255.2	254.8	256.0	258.4	260.7	260.3	260.7	258.4	256.0	254.8	255.2
152.5°	263.0	260.8	260.7	261.8	262.9	262.8	262.9	261.8	260.7	260.8	263.0
155°	276.3	272.0	269.7	268.9	268.9	268.5	268.9	268.9	269.7	272.0	276.3
157.5°	290.9	284.9	281.4	279.5	279.0	278.1	279.0	279.5	281.4	284.9	290.9
160°	300.9	294.3	290.7	287.6	286.5	285.3	286.5	287.6	290.7	294.3	300.9
162.5°	310.3	303.9	300.1	297.3	296.1	294.3	296.1	297.3	300.1	303.9	310.3
165°	325.5	318.8	314.6	312.2	310.7	309.1	310.7	312.2	314.6	318.8	325.5
167.5°	340.7	333.4	330.6	328.0	326.5	323.7	326.5	328.0	330.6	333.4	340.7
170°	350.1	343.4	341.9	339.5	336.8	333.7	336.8	339.5	341.9	343.4	350.1
172.5°	358.2	353.7	352.2	349.8	349.0	346.5	349.0	349.8	352.2	353.7	358.2
175°	370.0	366.5	366.5	366.1	364.9	362.6	364.9	366.1	366.5	366.5	370.0
177.5°	379.8	377.9	379.2	379.2	378.9	376.7	378.9	379.2	379.2	377.9	379.8
180°	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4



TEST NUMBER: P1428349

CATALOG NUMBER: SQ2W-PW1-K-025U-050D-L840-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	1223.7	1223.7	1223.7	1223.7
2.5°	1227.7	1229.4	1222.3	1215.3
5°	1227.2	1228.5	1219.7	1210.9
7.5°	1222.2	1222.6	1213.7	1204.8
10°	1217.9	1217.9	1208.5	1199.2
12.5°	1212.0	1211.2	1201.5	1191.8
15°	1198.8	1196.6	1186.3	1175.9
17.5°	1180.3	1178.2	1167.8	1157.5
20°	1166.6	1165.2	1154.8	1144.4
22.5°	1148.2	1148.2	1137.0	1125.8
25°	1114.5	1119.6	1108.7	1097.8
27.5°	1069.6	1082.8	1074.0	1065.2
30°	1034.5	1055.3	1048.6	1041.9
32.5°	995.3	1022.8	1020.2	1017.6
35°	931.9	968.5	973.1	977.8
37.5°	861.8	902.9	916.8	930.7
40°	812.7	856.8	876.5	896.2
42.5°	763.3	808.7	833.3	858.0
45°	689.5	736.8	765.8	794.8
47.5°	619.0	666.1	694.9	723.7
50°	571.4	616.5	644.5	672.4
52.5°	526.7	570.1	595.2	620.2
55°	460.3	501.3	525.1	548.9
57.5°	397.5	434.3	454.9	475.5
60°	357.4	392.6	410.7	428.9
62.5°	318.2	352.0	368.1	384.1
65°	265.3	293.2	305.1	317.0
67.5°	217.6	238.5	245.1	251.7
70°	188.4	205.6	207.7	209.8
72.5°	160.7	175.1	174.2	173.4
75°	122.4	131.8	127.7	123.5
77.5°	90.4	96.6	90.4	84.1
80°	69.9	74.2	68.0	61.8
82.5°	50.0	53.1	48.1	43.1
85°	25.3	26.2	23.6	21.0
87.5°	8.2	8.9	7.4	5.8
90°	7.0	4.3	2.7	1.2
92.5°	15.1	10.5	7.4	4.3
95°	30.4	24.2	17.2	12.1
97.5°	48.5	38.4	31.5	23.1
100°	58.1	48.4	41.8	32.8
102.5°	68.8	60.6	51.4	42.5
105°	87.8	77.7	67.1	57.0
107.5°	105.5	94.3	81.6	72.5
110°	116.7	104.6	91.3	83.1



TEST NUMBER: P1428349

CATALOG NUMBER: SQ2W-PW1-K-025U-050D-L840-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	127.6	115.2	101.6	93.4
115°	142.4	128.8	116.3	109.3
117.5°	156.7	142.7	129.5	123.9
120°	165.5	151.4	138.5	134.3
122.5°	172.7	158.9	147.0	145.2
125°	183.4	169.4	159.2	161.6
127.5°	192.2	179.3	172.9	178.1
130°	197.5	186.2	182.3	189.7
132.5°	202.2	193.3	191.6	201.8
135°	209.2	204.1	205.7	219.7
137.5°	217.5	215.6	220.8	238.5
140°	222.8	224.0	231.4	251.3
142.5°	230.0	232.8	242.4	263.5
145°	241.2	247.0	259.5	280.6
147.5°	253.8	261.4	276.9	298.5
150°	262.3	272.0	288.4	309.1
152.5°	271.9	282.0	298.4	319.4
155°	286.8	298.2	315.3	333.3
157.5°	302.1	313.6	330.0	345.7
160°	311.4	323.9	338.8	353.2
162.5°	322.0	333.6	346.6	359.4
165°	337.6	346.9	357.5	368.4
167.5°	350.6	358.4	366.7	375.2
170°	359.0	365.3	372.3	379.0
172.5°	366.2	371.2	376.4	382.1
175°	375.8	378.6	381.7	385.2
177.5°	383.2	384.2	385.1	386.7
180°	386.4	386.4	386.4	386.4



TEST NUMBER: P1428349  
 CATALOG NUMBER: SQ2W-PW1-K-025U-050D-L840-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.03	20.05	19.80	20.83	21.78	15.28	16.30	16.04	17.08	18.03
	3H	20.34	21.26	21.12	22.05	23.03	16.56	17.47	17.34	18.27	19.24
	4H	20.76	21.62	21.56	22.42	23.41	17.07	17.93	17.87	18.73	19.72
	6H	20.95	21.74	21.76	22.55	23.55	17.39	18.18	18.20	18.99	19.99
	8H	21.00	21.75	21.81	22.58	23.58	17.51	18.26	18.33	19.09	20.09
	12H	21.00	21.72	21.83	22.54	23.57	17.54	18.26	18.37	19.08	20.11
4H	2H	19.18	20.04	19.98	20.84	21.83	16.11	16.97	16.91	17.77	18.76
	3H	20.74	21.45	21.55	22.28	23.29	17.57	18.28	18.38	19.12	20.12
	4H	21.29	21.94	22.11	22.77	23.80	18.15	18.80	18.98	19.63	20.67
	6H	21.61	22.17	22.45	23.02	24.06	18.55	19.10	19.39	19.96	21.00
	8H	21.70	22.22	22.55	23.08	24.12	18.70	19.22	19.55	20.07	21.12
	12H	21.73	22.20	22.60	23.07	24.13	18.75	19.22	19.61	20.09	21.14
8H	4H	21.34	21.86	22.18	22.71	23.76	18.51	19.03	19.36	19.88	20.93
	6H	21.77	22.20	22.64	23.09	24.14	19.01	19.44	19.88	20.33	21.38
	8H	21.94	22.32	22.82	23.21	24.28	19.23	19.61	20.11	20.50	21.56
	12H	22.02	22.36	22.91	23.24	24.36	19.32	19.65	20.20	20.53	21.65
12H	4H	21.30	21.77	22.17	22.65	23.70	18.53	19.00	19.40	19.88	20.93
	6H	21.76	22.14	22.64	23.03	24.10	19.08	19.46	19.97	20.35	21.42
	8H	21.96	22.29	22.84	23.17	24.30	19.33	19.67	20.22	20.55	21.67