

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428391

Luminaire Tested: SQ2W-PW1-K-050U-125D-L840-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428391
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PW1-K-050U-125D-L840-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE WAVES LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8775.7 lumens
Efficiency: N/A
Efficacy: 136.9 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.11 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 64.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428391

CATALOG NUMBER: SQ2W-PW1-K-050U-125D-L840-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428391

CATALOG NUMBER: SQ2W-PW1-K-050U-125D-L840-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	97	97	97	88	88	88	79	79	79	75
1	104	100	96	93	99	95	92	89	87	84	82	79	77	75	71	70	68	65
2	96	88	82	77	91	84	79	75	77	73	69	70	67	64	64	61	59	56
3	88	79	71	66	83	75	69	63	69	63	59	63	59	55	57	54	51	48
4	81	70	62	56	77	67	60	55	62	56	51	56	52	48	52	48	45	42
5	75	63	55	49	71	60	53	48	56	50	45	51	46	42	47	43	40	37
6	69	57	49	43	66	55	47	42	51	44	40	47	41	37	43	39	35	33
7	64	52	44	38	61	50	43	37	46	40	35	43	37	33	39	35	32	29
8	60	47	40	34	57	46	38	33	42	36	32	39	34	30	36	32	29	26
9	56	44	36	31	53	42	35	30	39	33	29	36	31	27	34	29	26	24
10	52	40	33	28	50	39	32	27	36	30	26	34	29	25	31	27	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	47713	47713	47713	47713
5°	47395	48215	47395	48215
10°	47480	48635	47480	48635
15°	47468	48927	47468	48927
20°	47489	47971	47489	47971
25°	47232	44574	47232	44574
30°	46910	40297	46910	40297
35°	46543	36391	46543	36391
40°	45618	32152	45618	32152
45°	43828	28083	43828	28083
50°	40792	24035	40792	24035
55°	37314	19490	37314	19490
60°	33444	16814	33444	16814
65°	29245	14945	29245	14945
70°	23915	13553	23915	13553
75°	18608	12464	18608	12464
80°	13872	10990	13872	10990
85°	9392	6261	9392	6261

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 43828 cd/sqm



TEST NUMBER: P1428391

CATALOG NUMBER: SQ2W-PW1-K-050U-125D-L840-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	281.4	3.2
10°-20°	815.4	9.3
20°-30°	1199.9	13.7
30°-40°	1311.9	14.9
40°-50°	1176.9	13.4
50°-60°	877.9	10.0
60°-70°	554.9	6.3
70°-80°	274.9	3.1
80°-90°	67.5	0.8
90°-100°	60.4	0.7
100°-110°	176.1	2.0
110°-120°	287.3	3.3
120°-130°	364.6	4.2
130°-140°	390.1	4.4
140°-150°	364.3	4.2
150°-160°	299.8	3.4
160°-170°	201.0	2.3
170°-180°	71.4	0.8
0°-30°	2296.7	26.2
0°-40°	3608.6	41.1
0°-60°	5663.4	64.5
0°-90°	6560.7	74.8
90°-120°	523.8	6.0
90°-150°	1642.8	18.7
90°-180°	2215.0	25.2
0°-180°	8775.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2955	2955	2955	2955	2955	
5°	2924	2975	2924	2975	2924	278
15°	2840	2927	2840	2927	2840	802
25°	2651	2502	2651	2502	2651	1221
35°	2361	1846	2361	1846	2361	1473
45°	1920	1230	1920	1230	1920	1472
55°	1326	692	1326	692	1326	1184
65°	766	391	766	391	766	759
75°	298	200	298	200	298	329
85°	51	34	51	34	51	64
90°	2	17	2	33	2	4
95°	24	18	24	103	24	29
105°	112	179	112	247	112	119
115°	215	297	215	366	215	211
125°	317	471	317	449	317	284
135°	431	617	431	497	431	333
145°	551	711	551	508	551	345
155°	654	772	654	527	654	301
165°	723	805	723	607	723	204
175°	756	788	756	712	756	72
180°	759	759	759	759	759	



TEST NUMBER: P1428391

CATALOG NUMBER: SQ2W-PW1-K-050U-125D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2955.2	2955.2	2955.2	2955.2	2955.2	2955.2	2955.2	2955.2	2955.2	2955.2	2955.2
2.5°	2935.0	2952.0	2969.0	2965.0	2954.0	2949.0	2950.0	2951.5	2954.5	2957.5	2954.5
5°	2924.3	2945.5	2966.8	2963.7	2952.4	2947.4	2948.7	2952.4	2963.7	2974.9	2963.7
7.5°	2909.6	2931.2	2952.7	2951.7	2943.2	2941.0	2945.3	2951.2	2962.2	2973.3	2962.2
10°	2896.1	2918.7	2941.2	2941.2	2933.7	2933.0	2939.3	2946.5	2956.5	2966.5	2956.5
12.5°	2878.1	2901.6	2925.2	2926.9	2921.4	2922.3	2929.5	2937.5	2947.5	2957.5	2947.5
15°	2839.8	2864.9	2889.9	2895.2	2893.9	2897.7	2906.5	2914.6	2920.8	2927.1	2920.8
17.5°	2795.4	2820.4	2845.4	2850.4	2848.6	2848.9	2851.1	2853.5	2856.5	2859.6	2856.5
20°	2763.9	2788.9	2813.9	2817.3	2813.6	2807.3	2798.6	2792.0	2792.0	2792.0	2792.0
22.5°	2718.8	2745.8	2772.9	2773.1	2764.3	2748.0	2724.3	2704.4	2696.4	2688.4	2696.4
25°	2651.3	2677.5	2703.8	2691.6	2666.6	2629.7	2580.9	2539.6	2520.9	2502.1	2520.9
27.5°	2572.5	2593.7	2615.0	2583.2	2533.6	2474.2	2404.9	2346.4	2320.4	2294.4	2320.4
30°	2516.2	2532.4	2548.7	2498.4	2425.8	2351.4	2275.1	2211.6	2186.6	2161.5	2186.6
32.5°	2457.6	2463.9	2470.1	2403.8	2313.2	2228.3	2149.0	2082.7	2055.7	2028.7	2055.7
35°	2361.4	2350.1	2338.9	2250.7	2136.8	2039.9	1959.8	1893.9	1870.1	1846.3	1870.1
37.5°	2247.7	2214.2	2180.6	2081.2	1959.9	1857.3	1773.5	1704.1	1677.8	1651.6	1677.8
40°	2164.4	2116.8	2069.3	1962.7	1836.3	1731.2	1647.4	1578.0	1551.7	1525.5	1551.7
42.5°	2072.0	2012.5	1953.0	1843.3	1717.0	1611.9	1528.1	1458.4	1431.2	1403.9	1431.2
45°	1919.5	1849.5	1779.4	1665.3	1536.4	1431.3	1350.0	1282.5	1256.2	1229.9	1256.2
47.5°	1747.8	1678.3	1608.7	1494.9	1366.3	1262.6	1183.8	1119.1	1096.5	1074.0	1096.5
50°	1624.0	1556.4	1488.9	1380.1	1257.5	1156.8	1078.0	1012.0	984.5	956.9	984.5
52.5°	1497.9	1437.3	1376.8	1272.0	1152.4	1052.2	971.4	901.4	863.9	826.3	863.9
55°	1325.6	1268.1	1210.6	1111.7	999.2	897.8	807.8	734.9	713.6	692.4	713.6
57.5°	1148.3	1098.5	1048.8	959.9	858.1	766.3	684.5	618.8	601.2	583.7	601.2
60°	1035.7	992.0	948.2	863.1	764.3	680.5	611.7	555.7	538.2	520.7	538.2
62.5°	927.7	888.9	850.1	768.6	672.7	597.4	542.6	497.9	483.4	468.9	483.4
65°	765.5	736.8	708.0	640.8	560.7	498.2	453.1	416.2	403.7	391.2	403.7
67.5°	607.9	591.9	575.9	525.6	463.8	413.1	373.6	341.9	333.6	325.4	333.6
70°	506.6	501.6	496.6	455.0	401.2	358.1	325.5	299.6	293.3	287.1	293.3
72.5°	418.8	420.8	422.8	388.2	341.4	305.3	279.8	259.6	255.3	251.1	255.3
75°	298.3	308.3	318.4	295.5	261.8	236.1	218.6	204.8	202.3	199.8	202.3
77.5°	203.2	218.2	233.2	218.4	193.6	174.8	161.7	151.5	149.5	147.5	149.5
80°	149.2	164.2	179.2	168.9	150.1	135.7	125.7	118.2	118.2	118.2	118.2
82.5°	104.1	116.1	128.2	120.8	107.1	97.7	92.7	88.9	88.9	88.9	88.9
85°	50.7	56.9	63.2	61.0	56.0	49.7	42.2	36.3	35.0	33.8	35.0
87.5°	14.0	17.6	21.4	19.0	14.4	11.6	10.6	10.0	10.1	10.1	10.1
90°	2.3	5.4	9.2	12.3	14.6	15.3	15.3	16.1	16.9	16.9	16.9
92.5°	8.4	13.3	13.5	13.5	16.4	17.8	19.0	19.2	19.9	19.9	19.9
95°	23.8	26.1	39.1	38.3	26.1	20.7	17.6	17.6	17.6	17.6	17.6
97.5°	45.4	48.7	50.9	68.2	72.0	69.6	56.7	47.7	42.6	40.3	42.6
100°	64.4	65.9	70.5	71.3	90.4	108.8	99.6	88.1	84.3	82.0	84.3
102.5°	83.4	84.3	91.3	94.6	99.0	109.4	141.3	137.8	135.2	134.7	135.2
105°	111.9	112.6	125.7	131.8	134.9	134.9	134.1	149.4	173.9	179.3	173.9
107.5°	142.4	145.9	161.2	177.6	181.1	182.1	178.1	175.8	174.9	175.5	174.9
110°	163.2	168.6	187.0	207.7	213.0	214.6	213.0	210.7	209.2	209.2	209.2



TEST NUMBER: P1428391

CATALOG NUMBER: SQ2W-PW1-K-050U-125D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	183.4	191.3	212.1	235.9	244.9	249.5	246.1	244.4	242.9	244.1	242.9
115°	214.6	226.1	253.6	278.2	296.6	298.8	298.1	298.1	297.3	297.3	297.3
117.5°	243.4	261.8	292.7	321.2	342.5	348.7	351.7	350.8	349.9	351.4	349.9
120°	263.6	285.1	320.3	352.5	373.2	382.4	385.4	383.9	385.4	383.9	385.4
122.5°	285.1	311.4	346.1	379.5	403.8	414.3	417.9	418.2	418.5	417.6	418.5
125°	317.2	349.4	390.0	424.5	449.8	462.1	465.1	465.9	467.4	471.3	467.4
127.5°	349.7	386.2	430.8	464.1	490.0	504.8	509.6	511.3	514.5	516.2	514.5
130°	372.4	413.8	459.0	490.4	515.7	531.8	540.2	542.5	546.4	545.6	546.4
132.5°	396.3	439.5	485.4	518.0	541.5	558.8	566.0	572.6	573.9	575.0	573.9
135°	431.4	478.2	524.1	556.3	578.5	595.4	604.6	610.7	614.6	616.9	614.6
137.5°	468.4	517.7	561.8	590.5	612.9	627.4	637.9	644.3	648.3	650.1	648.3
140°	493.5	541.0	583.9	613.8	633.7	648.3	657.5	665.1	669.7	669.7	669.7
142.5°	517.4	564.3	606.0	635.9	653.3	666.7	676.5	682.3	687.5	687.5	687.5
145°	551.0	597.7	636.0	665.9	680.5	692.7	703.4	708.0	711.1	711.1	711.1
147.5°	586.1	627.4	662.4	691.0	703.3	717.7	726.1	729.8	733.6	732.0	733.6
150°	606.9	645.2	678.9	705.7	718.0	731.8	740.2	743.3	747.1	744.8	747.1
152.5°	627.1	663.6	694.2	719.2	729.7	743.4	753.1	756.2	758.8	757.1	758.8
155°	654.4	686.6	714.9	737.9	747.1	760.1	769.3	773.2	776.2	772.4	776.2
157.5°	678.8	706.5	731.2	752.3	762.1	773.3	781.9	786.7	789.7	788.0	789.7
160°	693.5	718.8	741.0	760.9	770.1	780.1	789.3	794.6	797.7	795.4	797.7
162.5°	705.7	728.6	749.6	767.7	775.6	784.4	795.4	800.1	803.2	800.3	803.2
165°	723.4	741.8	760.1	775.5	782.4	789.3	800.8	806.1	808.4	805.4	808.4
167.5°	736.7	750.8	765.7	778.8	783.9	790.6	802.1	806.6	809.5	805.7	809.5
170°	744.1	756.3	769.3	780.1	783.9	790.0	801.5	805.4	807.7	803.8	807.7
172.5°	750.2	759.4	770.0	779.5	781.5	786.4	797.2	801.1	802.8	799.5	802.8
175°	756.3	761.7	769.3	775.5	774.7	777.8	787.0	790.0	793.1	788.5	793.1
177.5°	759.2	761.7	764.1	767.8	765.4	765.4	772.1	773.9	774.6	772.1	774.6
180°	758.6	758.6	758.6	758.6	758.6	758.6	758.6	758.6	758.6	758.6	758.6



TEST NUMBER: P1428391

CATALOG NUMBER: SQ2W-PW1-K-050U-125D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2955.2	2955.2	2955.2	2955.2	2955.2	2955.2	2955.2	2955.2	2955.2	2955.2	2955.2
2.5°	2951.5	2950.0	2949.0	2954.0	2965.0	2969.0	2952.0	2935.0	2952.0	2969.0	2965.0
5°	2952.4	2948.7	2947.4	2952.4	2963.7	2966.8	2945.5	2924.3	2945.5	2966.8	2963.7
7.5°	2951.2	2945.3	2941.0	2943.2	2951.7	2952.7	2931.2	2909.6	2931.2	2952.7	2951.7
10°	2946.5	2939.3	2933.0	2933.7	2941.2	2941.2	2918.7	2896.1	2918.7	2941.2	2941.2
12.5°	2937.5	2929.5	2922.3	2921.4	2926.9	2925.2	2901.6	2878.1	2901.6	2925.2	2926.9
15°	2914.6	2906.5	2897.7	2893.9	2895.2	2889.9	2864.9	2839.8	2864.9	2889.9	2895.2
17.5°	2853.5	2851.1	2848.9	2848.6	2850.4	2845.4	2820.4	2795.4	2820.4	2845.4	2850.4
20°	2792.0	2798.6	2807.3	2813.6	2817.3	2813.9	2788.9	2763.9	2788.9	2813.9	2817.3
22.5°	2704.4	2724.3	2748.0	2764.3	2773.1	2772.9	2745.8	2718.8	2745.8	2772.9	2773.1
25°	2539.6	2580.9	2629.7	2666.6	2691.6	2703.8	2677.5	2651.3	2677.5	2703.8	2691.6
27.5°	2346.4	2404.9	2474.2	2533.6	2583.2	2615.0	2593.7	2572.5	2593.7	2615.0	2583.2
30°	2211.6	2275.1	2351.4	2425.8	2498.4	2548.7	2532.4	2516.2	2532.4	2548.7	2498.4
32.5°	2082.7	2149.0	2228.3	2313.2	2403.8	2470.1	2463.9	2457.6	2463.9	2470.1	2403.8
35°	1893.9	1959.8	2039.9	2136.8	2250.7	2338.9	2350.1	2361.4	2350.1	2338.9	2250.7
37.5°	1704.1	1773.5	1857.3	1959.9	2081.2	2180.6	2214.2	2247.7	2214.2	2180.6	2081.2
40°	1578.0	1647.4	1731.2	1836.3	1962.7	2069.3	2116.8	2164.4	2116.8	2069.3	1962.7
42.5°	1458.4	1528.1	1611.9	1717.0	1843.3	1953.0	2012.5	2072.0	2012.5	1953.0	1843.3
45°	1282.5	1350.0	1431.3	1536.4	1665.3	1779.4	1849.5	1919.5	1849.5	1779.4	1665.3
47.5°	1119.1	1183.8	1262.6	1366.3	1494.9	1608.7	1678.3	1747.8	1678.3	1608.7	1494.9
50°	1012.0	1078.0	1156.8	1257.5	1380.1	1488.9	1556.4	1624.0	1556.4	1488.9	1380.1
52.5°	901.4	971.4	1052.2	1152.4	1272.0	1376.8	1437.3	1497.9	1437.3	1376.8	1272.0
55°	734.9	807.8	897.8	999.2	1111.7	1210.6	1268.1	1325.6	1268.1	1210.6	1111.7
57.5°	618.8	684.5	766.3	858.1	959.9	1048.8	1098.5	1148.3	1098.5	1048.8	959.9
60°	555.7	611.7	680.5	764.3	863.1	948.2	992.0	1035.7	992.0	948.2	863.1
62.5°	497.9	542.6	597.4	672.7	768.6	850.1	888.9	927.7	888.9	850.1	768.6
65°	416.2	453.1	498.2	560.7	640.8	708.0	736.8	765.5	736.8	708.0	640.8
67.5°	341.9	373.6	413.1	463.8	525.6	575.9	591.9	607.9	591.9	575.9	525.6
70°	299.6	325.5	358.1	401.2	455.0	496.6	501.6	506.6	501.6	496.6	455.0
72.5°	259.6	279.8	305.3	341.4	388.2	422.8	420.8	418.8	420.8	422.8	388.2
75°	204.8	218.6	236.1	261.8	295.5	318.4	308.3	298.3	308.3	318.4	295.5
77.5°	151.5	161.7	174.8	193.6	218.4	233.2	218.2	203.2	218.2	233.2	218.4
80°	118.2	125.7	135.7	150.1	168.9	179.2	164.2	149.2	164.2	179.2	168.9
82.5°	88.9	92.7	97.7	107.1	120.8	128.2	116.1	104.1	116.1	128.2	120.8
85°	36.3	42.2	49.7	56.0	61.0	63.2	56.9	50.7	56.9	63.2	61.0
87.5°	10.0	10.6	11.6	14.4	19.0	21.4	17.6	14.0	17.6	21.2	19.3
90°	16.1	15.3	15.3	14.6	12.3	9.2	5.4	2.3	5.4	8.4	13.8
92.5°	19.2	19.0	17.8	16.4	13.5	13.5	13.3	8.4	14.6	20.7	29.7
95°	17.6	17.6	20.7	26.1	38.3	39.1	26.1	23.8	33.7	47.5	59.8
97.5°	47.7	56.7	69.6	72.0	68.2	50.9	48.7	45.4	61.8	75.4	95.2
100°	88.1	99.6	108.8	90.4	71.3	70.5	65.9	64.4	82.0	95.0	114.2
102.5°	137.8	141.3	109.4	99.0	94.6	91.3	84.3	83.4	101.0	118.9	135.0
105°	149.4	134.1	134.9	134.9	131.8	125.7	112.6	111.9	131.8	152.5	172.4
107.5°	175.8	178.1	182.1	181.1	177.6	161.2	145.9	142.4	160.3	185.1	207.0
110°	210.7	213.0	214.6	213.0	207.7	187.0	168.6	163.2	179.3	205.4	229.1



TEST NUMBER: P1428391

CATALOG NUMBER: SQ2W-PW1-K-050U-125D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	244.4	246.1	249.5	244.9	235.9	212.1	191.3	183.4	199.5	226.2	250.6
115°	298.1	298.1	298.8	296.6	278.2	253.6	226.1	214.6	228.4	252.9	279.7
117.5°	350.8	351.7	348.7	342.5	321.2	292.7	261.8	243.4	254.3	280.2	307.7
120°	383.9	385.4	382.4	373.2	352.5	320.3	285.1	263.6	272.0	297.3	324.9
122.5°	418.2	417.9	414.3	403.8	379.5	346.1	311.4	285.1	288.6	312.0	339.0
125°	465.9	465.1	462.1	449.8	424.5	390.0	349.4	317.2	312.6	332.6	360.2
127.5°	511.3	509.6	504.8	490.0	464.1	430.8	386.2	349.7	339.5	352.0	377.3
130°	542.5	540.2	531.8	515.7	490.4	459.0	413.8	372.4	357.9	365.5	387.7
132.5°	572.6	566.0	558.8	541.5	518.0	485.4	439.5	396.3	376.2	379.6	396.9
135°	610.7	604.6	595.4	578.5	556.3	524.1	478.2	431.4	403.8	400.8	410.7
137.5°	644.3	637.9	627.4	612.9	590.5	561.8	517.7	468.4	433.6	423.3	427.1
140°	665.1	657.5	648.3	633.7	613.8	583.9	541.0	493.5	454.4	439.8	437.5
142.5°	682.3	676.5	666.7	653.3	635.9	606.0	564.3	517.4	475.9	457.0	451.6
145°	708.0	703.4	692.7	680.5	665.9	636.0	597.7	551.0	509.6	485.1	473.6
147.5°	729.8	726.1	717.7	703.3	691.0	662.4	627.4	586.1	543.6	513.3	498.4
150°	743.3	740.2	731.8	718.0	705.7	678.9	645.2	606.9	566.3	534.1	514.9
152.5°	756.2	753.1	743.4	729.7	719.2	694.2	663.6	627.1	585.9	553.7	533.9
155°	773.2	769.3	760.1	747.1	737.9	714.9	686.6	654.4	619.2	585.4	563.2
157.5°	786.7	781.9	773.3	762.1	752.3	731.2	706.5	678.8	648.0	615.8	593.1
160°	794.6	789.3	780.1	770.1	760.9	741.0	718.8	693.5	665.1	636.0	611.5
162.5°	800.1	795.4	784.4	775.6	767.7	749.6	728.6	705.7	680.5	655.0	632.3
165°	806.1	800.8	789.3	782.4	775.5	760.1	741.8	723.4	701.9	681.2	662.8
167.5°	806.6	802.1	790.6	783.9	778.8	765.7	750.8	736.7	720.0	703.8	688.4
170°	805.4	801.5	790.0	783.9	780.1	769.3	756.3	744.1	731.0	717.2	705.0
172.5°	801.1	797.2	786.4	781.5	779.5	770.0	759.4	750.2	739.0	728.9	719.1
175°	790.0	787.0	777.8	774.7	775.5	769.3	761.7	756.3	749.4	743.3	737.9
177.5°	773.9	772.1	765.4	765.4	767.8	764.1	761.7	759.2	756.2	754.3	752.5
180°	758.6	758.6	758.6	758.6	758.6	758.6	758.6	758.6	758.6	758.6	758.6



TEST NUMBER: P1428391

CATALOG NUMBER: SQ2W-PW1-K-050U-125D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2955.2	2955.2	2955.2	2955.2	2955.2	2955.2	2955.2	2955.2	2955.2	2955.2	2955.2
2.5°	2954.0	2949.0	2950.0	2951.5	2954.5	2957.5	2954.5	2951.5	2950.0	2949.0	2954.0
5°	2952.4	2947.4	2948.7	2952.4	2963.7	2974.9	2963.7	2952.4	2948.7	2947.4	2952.4
7.5°	2943.2	2941.0	2945.3	2951.2	2962.2	2973.3	2962.2	2951.2	2945.3	2941.0	2943.2
10°	2933.7	2933.0	2939.3	2946.5	2956.5	2966.5	2956.5	2946.5	2939.3	2933.0	2933.7
12.5°	2921.4	2922.3	2929.5	2937.5	2947.5	2957.5	2947.5	2937.5	2929.5	2922.3	2921.4
15°	2893.9	2897.7	2906.5	2914.6	2920.8	2927.1	2920.8	2914.6	2906.5	2897.7	2893.9
17.5°	2848.6	2848.9	2851.1	2853.5	2856.5	2859.6	2856.5	2853.5	2851.1	2848.9	2848.6
20°	2813.6	2807.3	2798.6	2792.0	2792.0	2792.0	2792.0	2792.0	2798.6	2807.3	2813.6
22.5°	2764.3	2748.0	2724.3	2704.4	2696.4	2688.4	2696.4	2704.4	2724.3	2748.0	2764.3
25°	2666.6	2629.7	2580.9	2539.6	2520.9	2502.1	2520.9	2539.6	2580.9	2629.7	2666.6
27.5°	2533.6	2474.2	2404.9	2346.4	2320.4	2294.4	2320.4	2346.4	2404.9	2474.2	2533.6
30°	2425.8	2351.4	2275.1	2211.6	2186.6	2161.5	2186.6	2211.6	2275.1	2351.4	2425.8
32.5°	2313.2	2228.3	2149.0	2082.7	2055.7	2028.7	2055.7	2082.7	2149.0	2228.3	2313.2
35°	2136.8	2039.9	1959.8	1893.9	1870.1	1846.3	1870.1	1893.9	1959.8	2039.9	2136.8
37.5°	1959.9	1857.3	1773.5	1704.1	1677.8	1651.6	1677.8	1704.1	1773.5	1857.3	1959.9
40°	1836.3	1731.2	1647.4	1578.0	1551.7	1525.5	1551.7	1578.0	1647.4	1731.2	1836.3
42.5°	1717.0	1611.9	1528.1	1458.4	1431.2	1403.9	1431.2	1458.4	1528.1	1611.9	1717.0
45°	1536.4	1431.3	1350.0	1282.5	1256.2	1229.9	1256.2	1282.5	1350.0	1431.3	1536.4
47.5°	1366.3	1262.6	1183.8	1119.1	1096.5	1074.0	1096.5	1119.1	1183.8	1262.6	1366.3
50°	1257.5	1156.8	1078.0	1012.0	984.5	956.9	984.5	1012.0	1078.0	1156.8	1257.5
52.5°	1152.4	1052.2	971.4	901.4	863.9	826.3	863.9	901.4	971.4	1052.2	1152.4
55°	999.2	897.8	807.8	734.9	713.6	692.4	713.6	734.9	807.8	897.8	999.2
57.5°	858.1	766.3	684.5	618.8	601.2	583.7	601.2	618.8	684.5	766.3	858.1
60°	764.3	680.5	611.7	555.7	538.2	520.7	538.2	555.7	611.7	680.5	764.3
62.5°	672.7	597.4	542.6	497.9	483.4	468.9	483.4	497.9	542.6	597.4	672.7
65°	560.7	498.2	453.1	416.2	403.7	391.2	403.7	416.2	453.1	498.2	560.7
67.5°	463.8	413.1	373.6	341.9	333.6	325.4	333.6	341.9	373.6	413.1	463.8
70°	401.2	358.1	325.5	299.6	293.3	287.1	293.3	299.6	325.5	358.1	401.2
72.5°	341.4	305.3	279.8	259.6	255.3	251.1	255.3	259.6	279.8	305.3	341.4
75°	261.8	236.1	218.6	204.8	202.3	199.8	202.3	204.8	218.6	236.1	261.8
77.5°	193.6	174.8	161.7	151.5	149.5	147.5	149.5	151.5	161.7	174.8	193.6
80°	150.1	135.7	125.7	118.2	118.2	118.2	118.2	118.2	125.7	135.7	150.1
82.5°	107.1	97.7	92.7	88.9	88.9	88.9	88.9	88.9	92.7	97.7	107.1
85°	56.0	49.7	42.2	36.3	35.0	33.8	35.0	36.3	42.2	49.7	56.0
87.5°	15.0	13.1	13.2	13.0	13.7	13.3	13.7	13.0	13.2	13.1	15.0
90°	17.6	23.0	28.4	31.4	34.5	33.0	34.5	31.4	28.4	23.0	17.6
92.5°	35.4	44.4	51.0	56.6	59.0	58.7	59.0	56.6	51.0	44.4	35.4
95°	71.3	82.0	92.7	100.4	105.0	103.4	105.0	100.4	92.7	82.0	71.3
97.5°	109.9	124.3	136.2	143.4	148.0	151.1	148.0	143.4	136.2	124.3	109.9
100°	135.6	149.4	163.2	171.6	179.3	182.4	179.3	171.6	163.2	149.4	135.6
102.5°	156.5	174.6	189.6	198.6	205.1	208.1	205.1	198.6	189.6	174.6	156.5
105°	190.8	210.0	226.1	237.5	244.4	246.7	244.4	237.5	226.1	210.0	190.8
107.5°	225.1	244.9	259.8	272.5	280.9	285.8	280.9	272.5	259.8	244.9	225.1
110°	252.1	268.2	284.3	295.8	304.2	307.3	304.2	295.8	284.3	268.2	252.1



TEST NUMBER: P1428391

CATALOG NUMBER: SQ2W-PW1-K-050U-125D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	274.8	292.7	308.8	320.3	330.0	334.3	330.0	320.3	308.8	292.7	274.8
115°	306.5	330.3	344.8	355.6	362.5	366.3	362.5	355.6	344.8	330.3	306.5
117.5°	332.9	357.7	373.6	381.9	385.1	387.9	385.1	381.9	373.6	357.7	332.9
120°	349.4	372.4	390.8	401.5	405.4	406.9	405.4	401.5	390.8	372.4	349.4
122.5°	364.7	386.5	404.3	417.5	423.8	425.3	423.8	417.5	404.3	386.5	364.7
125°	386.2	406.9	425.3	438.3	445.2	449.0	445.2	438.3	425.3	406.9	386.2
127.5°	404.9	427.3	444.1	455.9	462.7	465.7	462.7	455.9	444.1	427.3	404.9
130°	415.3	438.3	455.2	468.2	474.3	477.4	474.3	468.2	455.2	438.3	415.3
132.5°	423.3	447.5	465.0	476.8	483.5	486.6	483.5	476.8	465.0	447.5	423.3
135°	432.9	458.2	476.6	488.1	494.3	497.3	494.3	488.1	476.6	458.2	432.9
137.5°	441.4	464.4	483.5	495.6	501.1	503.1	501.1	495.6	483.5	464.4	441.4
140°	447.5	467.4	486.6	498.1	504.2	505.0	504.2	498.1	486.6	467.4	447.5
142.5°	455.5	471.1	487.8	499.3	505.4	506.8	505.4	499.3	487.8	471.1	455.5
145°	469.7	478.9	490.4	501.1	506.5	508.0	506.5	501.1	490.4	478.9	469.7
147.5°	487.7	490.6	496.5	503.6	508.8	509.9	508.8	503.6	496.5	490.6	487.7
150°	501.1	500.4	502.7	507.3	511.9	511.1	511.9	507.3	502.7	500.4	501.1
152.5°	516.5	512.0	511.9	514.0	516.2	516.0	516.2	514.0	511.9	512.0	516.5
155°	542.5	534.1	529.5	528.0	528.0	527.2	528.0	528.0	529.5	534.1	542.5
157.5°	571.2	559.4	552.5	548.8	547.7	546.1	547.7	548.8	552.5	559.4	571.2
160°	590.8	577.8	570.9	564.7	562.4	560.2	562.4	564.7	570.9	577.8	590.8
162.5°	609.2	596.8	589.3	583.8	581.5	577.9	581.5	583.8	589.3	596.8	609.2
165°	639.1	626.1	617.6	613.0	610.0	606.9	610.0	613.0	617.6	626.1	639.1
167.5°	669.0	654.7	649.2	644.0	641.1	635.6	641.1	644.0	649.2	654.7	669.0
170°	687.4	674.3	671.3	666.7	661.3	655.2	661.3	666.7	671.3	674.3	687.4
172.5°	703.3	694.6	691.5	686.9	685.2	680.3	685.2	686.9	691.5	694.6	703.3
175°	726.4	719.5	719.5	718.8	716.5	711.9	716.5	718.8	719.5	719.5	726.4
177.5°	745.7	742.1	744.5	744.5	743.9	739.6	743.9	744.5	744.5	742.1	745.7
180°	758.6	758.6	758.6	758.6	758.6	758.6	758.6	758.6	758.6	758.6	758.6



TEST NUMBER: P1428391

CATALOG NUMBER: SQ2W-PW1-K-050U-125D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	2955.2	2955.2	2955.2	2955.2
2.5°	2965.0	2969.0	2952.0	2935.0
5°	2963.7	2966.8	2945.5	2924.3
7.5°	2951.7	2952.7	2931.2	2909.6
10°	2941.2	2941.2	2918.7	2896.1
12.5°	2926.9	2925.2	2901.6	2878.1
15°	2895.2	2889.9	2864.9	2839.8
17.5°	2850.4	2845.4	2820.4	2795.4
20°	2817.3	2813.9	2788.9	2763.9
22.5°	2773.1	2772.9	2745.8	2718.8
25°	2691.6	2703.8	2677.5	2651.3
27.5°	2583.2	2615.0	2593.7	2572.5
30°	2498.4	2548.7	2532.4	2516.2
32.5°	2403.8	2470.1	2463.9	2457.6
35°	2250.7	2338.9	2350.1	2361.4
37.5°	2081.2	2180.6	2214.2	2247.7
40°	1962.7	2069.3	2116.8	2164.4
42.5°	1843.3	1953.0	2012.5	2072.0
45°	1665.3	1779.4	1849.5	1919.5
47.5°	1494.9	1608.7	1678.3	1747.8
50°	1380.1	1488.9	1556.4	1624.0
52.5°	1272.0	1376.8	1437.3	1497.9
55°	1111.7	1210.6	1268.1	1325.6
57.5°	959.9	1048.8	1098.5	1148.3
60°	863.1	948.2	992.0	1035.7
62.5°	768.6	850.1	888.9	927.7
65°	640.8	708.0	736.8	765.5
67.5°	525.6	575.9	591.9	607.9
70°	455.0	496.6	501.6	506.6
72.5°	388.2	422.8	420.8	418.8
75°	295.5	318.4	308.3	298.3
77.5°	218.4	233.2	218.2	203.2
80°	168.9	179.2	164.2	149.2
82.5°	120.8	128.2	116.1	104.1
85°	61.0	63.2	56.9	50.7
87.5°	19.3	21.2	17.6	14.0
90°	13.8	8.4	5.4	2.3
92.5°	29.7	20.7	14.6	8.4
95°	59.8	47.5	33.7	23.8
97.5°	95.2	75.4	61.8	45.4
100°	114.2	95.0	82.0	64.4
102.5°	135.0	118.9	101.0	83.4
105°	172.4	152.5	131.8	111.9
107.5°	207.0	185.1	160.3	142.4
110°	229.1	205.4	179.3	163.2



TEST NUMBER: P1428391

CATALOG NUMBER: SQ2W-PW1-K-050U-125D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	250.6	226.2	199.5	183.4
115°	279.7	252.9	228.4	214.6
117.5°	307.7	280.2	254.3	243.4
120°	324.9	297.3	272.0	263.6
122.5°	339.0	312.0	288.6	285.1
125°	360.2	332.6	312.6	317.2
127.5°	377.3	352.0	339.5	349.7
130°	387.7	365.5	357.9	372.4
132.5°	396.9	379.6	376.2	396.3
135°	410.7	400.8	403.8	431.4
137.5°	427.1	423.3	433.6	468.4
140°	437.5	439.8	454.4	493.5
142.5°	451.6	457.0	475.9	517.4
145°	473.6	485.1	509.6	551.0
147.5°	498.4	513.3	543.6	586.1
150°	514.9	534.1	566.3	606.9
152.5°	533.9	553.7	585.9	627.1
155°	563.2	585.4	619.2	654.4
157.5°	593.1	615.8	648.0	678.8
160°	611.5	636.0	665.1	693.5
162.5°	632.3	655.0	680.5	705.7
165°	662.8	681.2	701.9	723.4
167.5°	688.4	703.8	720.0	736.7
170°	705.0	717.2	731.0	744.1
172.5°	719.1	728.9	739.0	750.2
175°	737.9	743.3	749.4	756.3
177.5°	752.5	754.3	756.2	759.2
180°	758.6	758.6	758.6	758.6



TEST NUMBER: P1428391
 CATALOG NUMBER: SQ2W-PW1-K-050U-125D-L840-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	22.41	23.48	23.13	24.22	25.09	18.66	19.73	19.38	20.46	21.33
	3H	23.73	24.69	24.46	25.43	26.33	19.94	20.90	20.68	21.65	22.55
	4H	24.15	25.05	24.90	25.80	26.72	20.46	21.36	21.21	22.11	23.03
	6H	24.34	25.17	25.10	25.93	26.86	20.78	21.61	21.54	22.37	23.30
	8H	24.38	25.17	25.16	25.96	26.89	20.90	21.69	21.67	22.47	23.40
	12H	24.39	25.14	25.17	25.92	26.88	20.93	21.69	21.71	22.46	23.42
4H	2H	22.57	23.47	23.32	24.22	25.14	19.49	20.40	20.25	21.15	22.06
	3H	24.13	24.87	24.89	25.66	26.59	20.96	21.71	21.73	22.50	23.43
	4H	24.68	25.36	25.46	26.15	27.11	21.55	22.22	22.33	23.01	23.97
	6H	25.00	25.59	25.80	26.40	27.37	21.94	22.52	22.74	23.34	24.31
	8H	25.10	25.64	25.90	26.45	27.43	22.09	22.64	22.90	23.45	24.43
	12H	25.13	25.62	25.95	26.45	27.43	22.15	22.64	22.97	23.47	24.45
8H	4H	24.73	25.28	25.54	26.09	27.07	21.90	22.45	22.71	23.26	24.24
	6H	25.16	25.61	25.99	26.46	27.45	22.40	22.85	23.24	23.71	24.69
	8H	25.33	25.73	26.18	26.58	27.58	22.62	23.02	23.47	23.87	24.87
	12H	25.42	25.77	26.26	26.61	27.67	22.71	23.07	23.56	23.91	24.96
12H	4H	24.70	25.19	25.52	26.02	27.01	21.93	22.42	22.75	23.25	24.24
	6H	25.16	25.56	26.00	26.41	27.40	22.48	22.88	23.32	23.73	24.73
	8H	25.36	25.71	26.20	26.55	27.60	22.73	23.09	23.58	23.92	24.98