

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427491

Luminaire Tested: SQ2W-BBM-0U-100D-L940-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1427491  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2104-222-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-BBM-0U-100D-L940-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - BLACK DISCREET BAFFLE, MEDIUM 80-DEGREE OPTIC  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT N/A - DIRECT ONLY  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4222.9 lumens  
Efficiency: N/A  
Efficacy: 110.8 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.17 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 38.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1427491

CATALOG NUMBER: SQ2W-BBM-0U-100D-L940-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1427491

CATALOG NUMBER: SQ2W-BBM-0U-100D-L940-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70
5	88	79	72	67	86	78	72	67	76	70	66	74	69	66	72	68	65	63
6	83	73	66	61	81	72	66	61	70	65	60	69	64	60	67	63	60	58
7	78	67	61	56	76	67	60	56	65	60	55	64	59	55	63	58	55	53
8	73	63	56	51	72	62	56	51	61	55	51	60	54	51	59	54	50	49
9	69	58	52	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	47	43	42

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	45614	45614	45614	45614
5°	45972	46040	45972	46040
10°	46549	46480	46549	46480
15°	47389	46443	47389	46443
20°	47449	45604	47449	45604
25°	46275	44464	46275	44464
30°	43500	41472	43500	41472
35°	38608	37159	38608	37159
40°	31663	29967	31663	29967
45°	18879	17716	18879	17716
50°	5893	5574	5893	5574
55°	2227	2227	2227	2227
60°	136	45	136	45
65°	0	0	0	0
70°	0	0	0	0
75°	0	0	0	0
80°	0	0	0	0
85°	0	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 40°  
 Vertical Angle: 45°  
 Luminance: 22100 cd/sqm



TEST NUMBER: P1427491

CATALOG NUMBER: SQ2W-BBM-OU-100D-L940-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	270.1	6.4
10°-20°	791.3	18.7
20°-30°	1164.1	27.6
30°-40°	1189.8	28.2
40°-50°	685.4	16.2
50°-60°	117.9	2.8
60°-70°	4.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2225.5	52.7
0°-40°	3415.3	80.9
0°-60°	4218.7	99.9
0°-90°	4222.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4222.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	2825	2825	2825	2825	2825	
5°	2836	2841	2836	2841	2836	271
15°	2835	2778	2835	2778	2835	798
25°	2598	2496	2598	2496	2598	1185
35°	1959	1885	1959	1885	1959	1210
45°	827	776	827	776	827	640
55°	79	79	79	79	79	84
65°	0	0	0	0	0	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P1427491

CATALOG NUMBER: SQ2W-BBM-0U-100D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2
2.5°	2837.6	2834.1	2830.6	2822.2	2812.1	2812.9	2824.4	2832.5	2830.0	2827.4	2830.0
5°	2836.5	2833.3	2830.2	2821.4	2810.7	2813.9	2830.8	2843.2	2842.0	2840.7	2842.0
7.5°	2834.8	2832.7	2830.5	2824.3	2816.8	2820.0	2833.9	2843.6	2840.5	2837.3	2840.5
10°	2839.3	2838.7	2838.1	2828.5	2815.9	2816.9	2831.3	2841.4	2838.2	2835.1	2838.2
12.5°	2841.6	2845.5	2849.4	2835.6	2816.0	2812.0	2823.4	2830.5	2824.9	2819.2	2824.9
15°	2835.1	2845.7	2856.4	2837.0	2807.4	2793.6	2795.5	2794.9	2786.7	2778.5	2786.7
17.5°	2803.4	2818.5	2833.6	2807.8	2768.5	2745.4	2738.5	2730.4	2718.9	2707.3	2718.9
20°	2761.6	2779.2	2796.8	2768.6	2725.3	2697.7	2685.7	2674.3	2664.2	2654.2	2664.2
22.5°	2702.8	2718.9	2734.9	2708.0	2666.6	2638.5	2623.5	2610.3	2602.3	2594.2	2602.3
25°	2597.6	2608.3	2619.0	2591.5	2551.3	2525.6	2514.3	2504.7	2500.3	2495.9	2500.3
27.5°	2448.7	2451.7	2454.7	2432.8	2402.7	2380.6	2366.5	2354.5	2348.9	2343.2	2348.9
30°	2333.3	2333.3	2333.3	2316.4	2293.8	2274.9	2259.9	2245.9	2235.2	2224.5	2235.2
32.5°	2198.8	2197.3	2195.8	2183.4	2167.3	2150.9	2134.4	2119.3	2108.6	2097.9	2108.6
35°	1958.8	1965.7	1972.6	1964.0	1950.2	1935.1	1918.8	1904.2	1894.8	1885.3	1894.8
37.5°	1699.1	1701.7	1704.3	1697.2	1686.8	1672.7	1655.2	1640.0	1632.1	1624.2	1632.1
40°	1502.3	1503.0	1503.6	1494.8	1482.9	1470.6	1458.0	1445.6	1433.7	1421.8	1433.7
42.5°	1272.8	1285.5	1298.2	1292.8	1281.4	1265.6	1245.5	1229.2	1224.3	1219.4	1224.3
45°	826.8	882.7	938.6	959.2	967.9	961.0	938.4	905.3	840.6	775.9	840.6
47.5°	415.5	485.1	554.7	602.9	644.0	632.3	567.9	502.4	433.9	365.5	433.9
50°	234.6	276.1	317.5	382.1	454.3	442.4	346.3	268.4	245.1	221.9	245.1
52.5°	156.6	174.9	193.3	245.3	308.4	304.3	232.8	175.9	162.7	149.5	162.7
55°	79.1	84.2	89.2	112.1	141.0	140.4	110.2	86.7	82.9	79.1	82.9
57.5°	26.9	33.6	40.4	50.6	61.9	62.2	51.5	42.0	35.8	29.7	35.8
60°	4.2	10.5	16.8	25.0	33.8	32.8	22.1	12.7	7.1	1.4	7.1
62.5°	0.8	2.6	4.4	11.0	19.3	19.1	10.5	3.5	1.9	0.3	1.9
65°	0.0	0.0	0.0	0.5	1.1	1.1	0.5	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1427491

CATALOG NUMBER: SQ2W-BBM-0U-100D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2
2.5°	2832.5	2824.4	2812.9	2812.1	2822.2	2830.6	2834.1	2837.6	2834.1	2830.6	2822.2
5°	2843.2	2830.8	2813.9	2810.7	2821.4	2830.2	2833.3	2836.5	2833.3	2830.2	2821.4
7.5°	2843.6	2833.9	2820.0	2816.8	2824.3	2830.5	2832.7	2834.8	2832.7	2830.5	2824.3
10°	2841.4	2831.3	2816.9	2815.9	2828.5	2838.1	2838.7	2839.3	2838.7	2838.1	2828.5
12.5°	2830.5	2823.4	2812.0	2816.0	2835.6	2849.4	2845.5	2841.6	2845.5	2849.4	2835.6
15°	2794.9	2795.5	2793.6	2807.4	2837.0	2856.4	2845.7	2835.1	2845.7	2856.4	2837.0
17.5°	2730.4	2738.5	2745.4	2768.5	2807.8	2833.6	2818.5	2803.4	2818.5	2833.6	2807.8
20°	2674.3	2685.7	2697.7	2725.3	2768.6	2796.8	2779.2	2761.6	2779.2	2796.8	2768.6
22.5°	2610.3	2623.5	2638.5	2666.6	2708.0	2734.9	2718.9	2702.8	2718.9	2734.9	2708.0
25°	2504.7	2514.3	2525.6	2551.3	2591.5	2619.0	2608.3	2597.6	2608.3	2619.0	2591.5
27.5°	2354.5	2366.5	2380.6	2402.7	2432.8	2454.7	2451.7	2448.7	2451.7	2454.7	2432.8
30°	2245.9	2259.9	2274.9	2293.8	2316.4	2333.3	2333.3	2333.3	2333.3	2333.3	2316.4
32.5°	2119.3	2134.4	2150.9	2167.3	2183.4	2195.8	2197.3	2198.8	2197.3	2195.8	2183.4
35°	1904.2	1918.8	1935.1	1950.2	1964.0	1972.6	1965.7	1958.8	1965.7	1972.6	1964.0
37.5°	1640.0	1655.2	1672.7	1686.8	1697.2	1704.3	1701.7	1699.1	1701.7	1704.3	1697.2
40°	1445.6	1458.0	1470.6	1482.9	1494.8	1503.6	1503.0	1502.3	1503.0	1503.6	1494.8
42.5°	1229.2	1245.5	1265.6	1281.4	1292.8	1298.2	1285.5	1272.8	1285.5	1298.2	1292.8
45°	905.3	938.4	961.0	967.9	959.2	938.6	882.7	826.8	882.7	938.6	959.2
47.5°	502.4	567.9	632.3	644.0	602.9	554.7	485.1	415.5	485.1	554.7	602.9
50°	268.4	346.3	442.4	454.3	382.1	317.5	276.1	234.6	276.1	317.5	382.1
52.5°	175.9	232.8	304.3	308.4	245.3	193.3	174.9	156.6	174.9	193.3	245.3
55°	86.7	110.2	140.4	141.0	112.1	89.2	84.2	79.1	84.2	89.2	112.1
57.5°	42.0	51.5	62.2	61.9	50.6	40.4	33.6	26.9	33.6	40.4	50.6
60°	12.7	22.1	32.8	33.8	25.0	16.8	10.5	4.2	10.5	16.8	25.0
62.5°	3.5	10.5	19.1	19.3	11.0	4.4	2.6	0.8	2.6	4.4	11.0
65°	0.0	0.5	1.1	1.1	0.5	0.0	0.0	0.0	0.0	0.0	0.5
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1427491

CATALOG NUMBER: SQ2W-BBM-0U-100D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2
2.5°	2812.1	2812.9	2824.4	2832.5	2830.0	2827.4	2830.0	2832.5	2824.4	2812.9	2812.1
5°	2810.7	2813.9	2830.8	2843.2	2842.0	2840.7	2842.0	2843.2	2830.8	2813.9	2810.7
7.5°	2816.8	2820.0	2833.9	2843.6	2840.5	2837.3	2840.5	2843.6	2833.9	2820.0	2816.8
10°	2815.9	2816.9	2831.3	2841.4	2838.2	2835.1	2838.2	2841.4	2831.3	2816.9	2815.9
12.5°	2816.0	2812.0	2823.4	2830.5	2824.9	2819.2	2824.9	2830.5	2823.4	2812.0	2816.0
15°	2807.4	2793.6	2795.5	2794.9	2786.7	2778.5	2786.7	2794.9	2795.5	2793.6	2807.4
17.5°	2768.5	2745.4	2738.5	2730.4	2718.9	2707.3	2718.9	2730.4	2738.5	2745.4	2768.5
20°	2725.3	2697.7	2685.7	2674.3	2664.2	2654.2	2664.2	2674.3	2685.7	2697.7	2725.3
22.5°	2666.6	2638.5	2623.5	2610.3	2602.3	2594.2	2602.3	2610.3	2623.5	2638.5	2666.6
25°	2551.3	2525.6	2514.3	2504.7	2500.3	2495.9	2500.3	2504.7	2514.3	2525.6	2551.3
27.5°	2402.7	2380.6	2366.5	2354.5	2348.9	2343.2	2348.9	2354.5	2366.5	2380.6	2402.7
30°	2293.8	2274.9	2259.9	2245.9	2235.2	2224.5	2235.2	2245.9	2259.9	2274.9	2293.8
32.5°	2167.3	2150.9	2134.4	2119.3	2108.6	2097.9	2108.6	2119.3	2134.4	2150.9	2167.3
35°	1950.2	1935.1	1918.8	1904.2	1894.8	1885.3	1894.8	1904.2	1918.8	1935.1	1950.2
37.5°	1686.8	1672.7	1655.2	1640.0	1632.1	1624.2	1632.1	1640.0	1655.2	1672.7	1686.8
40°	1482.9	1470.6	1458.0	1445.6	1433.7	1421.8	1433.7	1445.6	1458.0	1470.6	1482.9
42.5°	1281.4	1265.6	1245.5	1229.2	1224.3	1219.4	1224.3	1229.2	1245.5	1265.6	1281.4
45°	967.9	961.0	938.4	905.3	840.6	775.9	840.6	905.3	938.4	961.0	967.9
47.5°	644.0	632.3	567.9	502.4	433.9	365.5	433.9	502.4	567.9	632.3	644.0
50°	454.3	442.4	346.3	268.4	245.1	221.9	245.1	268.4	346.3	442.4	454.3
52.5°	308.4	304.3	232.8	175.9	162.7	149.5	162.7	175.9	232.8	304.3	308.4
55°	141.0	140.4	110.2	86.7	82.9	79.1	82.9	86.7	110.2	140.4	141.0
57.5°	61.9	62.2	51.5	42.0	35.8	29.7	35.8	42.0	51.5	62.2	61.9
60°	33.8	32.8	22.1	12.7	7.1	1.4	7.1	12.7	22.1	32.8	33.8
62.5°	19.3	19.1	10.5	3.5	1.9	0.3	1.9	3.5	10.5	19.1	19.3
65°	1.1	1.1	0.5	0.0	0.0	0.0	0.0	0.5	1.1	1.1	1.1
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1427491

CATALOG NUMBER: SQ2W-BBM-0U-100D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	2825.2	2825.2	2825.2	2825.2
2.5°	2822.2	2830.6	2834.1	2837.6
5°	2821.4	2830.2	2833.3	2836.5
7.5°	2824.3	2830.5	2832.7	2834.8
10°	2828.5	2838.1	2838.7	2839.3
12.5°	2835.6	2849.4	2845.5	2841.6
15°	2837.0	2856.4	2845.7	2835.1
17.5°	2807.8	2833.6	2818.5	2803.4
20°	2768.6	2796.8	2779.2	2761.6
22.5°	2708.0	2734.9	2718.9	2702.8
25°	2591.5	2619.0	2608.3	2597.6
27.5°	2432.8	2454.7	2451.7	2448.7
30°	2316.4	2333.3	2333.3	2333.3
32.5°	2183.4	2195.8	2197.3	2198.8
35°	1964.0	1972.6	1965.7	1958.8
37.5°	1697.2	1704.3	1701.7	1699.1
40°	1494.8	1503.6	1503.0	1502.3
42.5°	1292.8	1298.2	1285.5	1272.8
45°	959.2	938.6	882.7	826.8
47.5°	602.9	554.7	485.1	415.5
50°	382.1	317.5	276.1	234.6
52.5°	245.3	193.3	174.9	156.6
55°	112.1	89.2	84.2	79.1
57.5°	50.6	40.4	33.6	26.9
60°	25.0	16.8	10.5	4.2
62.5°	11.0	4.4	2.6	0.8
65°	0.5	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0



TEST NUMBER: P1427491  
 CATALOG NUMBER: SQ2W-BBM-0U-100D-L940-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.12	4.26	3.49	4.57	4.88	3.35	4.49	3.72	4.80	5.11
	3H	2.96	3.95	3.34	4.28	4.65	3.19	4.18	3.57	4.51	4.88
	4H	2.87	3.78	3.27	4.13	4.52	3.10	4.01	3.50	4.36	4.75
	6H	2.77	3.61	3.19	3.98	4.38	3.00	3.84	3.42	4.21	4.61
	8H	2.72	3.51	3.15	3.90	4.31	2.95	3.74	3.38	4.13	4.54
	12H	2.67	3.42	3.10	3.80	4.23	2.90	3.65	3.33	4.03	4.46
4H	2H	2.88	3.79	3.28	4.14	4.53	3.11	4.02	3.51	4.37	4.76
	3H	2.70	3.44	3.12	3.84	4.25	2.93	3.67	3.35	4.07	4.48
	4H	2.59	3.25	3.03	3.67	4.11	2.82	3.47	3.26	3.90	4.34
	6H	2.49	3.05	2.96	3.50	3.97	2.72	3.28	3.19	3.73	4.20
	8H	2.42	2.94	2.90	3.39	3.87	2.65	3.17	3.13	3.62	4.10
	12H	2.36	2.82	2.85	3.31	3.78	2.59	3.05	3.08	3.53	4.01
8H	4H	2.42	2.94	2.90	3.39	3.87	2.65	3.17	3.13	3.62	4.10
	6H	2.30	2.72	2.81	3.22	3.71	2.53	2.95	3.04	3.45	3.94
	8H	2.23	2.61	2.76	3.13	3.62	2.46	2.84	2.99	3.36	3.85
	12H	2.17	2.51	2.69	3.00	3.58	2.40	2.74	2.92	3.23	3.81
12H	4H	2.36	2.82	2.85	3.31	3.78	2.59	3.05	3.08	3.53	4.01
	6H	2.23	2.61	2.76	3.13	3.62	2.46	2.84	2.99	3.36	3.85
	8H	2.17	2.51	2.69	3.00	3.58	2.40	2.74	2.92	3.23	3.81