

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427530

Luminaire Tested: SQ2W-BBM-K-075U-125D-L940-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2024
Report Number: P1427530
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2104-222-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-BBM-K-075U-125D-L940-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - BLACK DISCREET BAFFLE, MEDIUM 80-DEGREE OPTIC
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8344.0 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.17 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 73.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1427530

CATALOG NUMBER: SQ2W-BBM-K-075U-125D-L940-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1427530

CATALOG NUMBER: SQ2W-BBM-K-075U-125D-L940-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	68	68	68	63
1	103	100	97	94	97	94	91	89	83	81	80	73	72	71	64	63	63	58
2	96	90	85	81	91	85	81	78	76	73	70	68	65	63	60	58	57	53
3	90	82	76	71	84	78	72	68	70	66	62	62	59	57	56	54	52	48
4	83	74	68	63	79	71	65	60	64	59	56	58	54	51	52	49	47	44
5	78	68	61	56	73	65	59	54	59	54	50	53	49	46	48	45	43	40
6	73	62	55	50	69	59	53	48	54	49	45	49	45	42	45	41	39	37
7	68	57	50	45	64	55	48	44	50	45	41	46	41	38	41	38	36	34
8	64	53	46	41	60	50	44	40	46	41	37	42	38	35	39	35	33	31
9	60	49	42	37	56	47	40	36	43	38	34	39	35	32	36	33	30	28
10	56	45	38	34	53	43	37	33	40	35	31	37	33	30	34	30	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	57087	57087	57087	57087
5°	57536	57622	57536	57622
10°	58258	58171	58258	58171
15°	59309	58127	59309	58127
20°	59384	57074	59384	57074
25°	57917	55648	57917	55648
30°	54444	51905	54444	51905
35°	48321	46508	48321	46508
40°	39628	37504	39628	37504
45°	23626	22173	23626	22173
50°	7375	6975	7375	6975
55°	2790	2790	2790	2790
60°	171	58	171	58
65°	0	0	0	0
70°	0	0	0	0
75°	0	0	0	0
80°	0	0	0	0
85°	0	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 40°
 Vertical Angle: 45°
 Luminance: 27660 cd/sqm



TEST NUMBER: P1427530

CATALOG NUMBER: SQ2W-BBM-K-075U-125D-L940-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	338.1	4.1
10°-20°	990.3	11.9
20°-30°	1456.9	17.5
30°-40°	1489.1	17.8
40°-50°	857.8	10.3
50°-60°	147.6	1.8
60°-70°	5.3	0.1
70°-80°	0.0	0.0
80°-90°	5.5	0.1
90°-100°	83.3	1.0
100°-110°	242.8	2.9
110°-120°	396.2	4.7
120°-130°	502.8	6.0
130°-140°	538.0	6.4
140°-150°	502.4	6.0
150°-160°	413.4	5.0
160°-170°	277.2	3.3
170°-180°	98.4	1.2
0°-30°	2785.3	33.4
0°-40°	4274.4	51.2
0°-60°	5279.9	63.3
0°-90°	5290.8	63.4
90°-120°	722.3	8.7
90°-150°	2265.4	27.2
90°-180°	3054.0	36.6
0°-180°	8344.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	3536	3536	3536	3536	3536	
5°	3550	3555	3550	3555	3550	339
15°	3548	3478	3548	3478	3548	999
25°	3251	3124	3251	3124	3251	1483
35°	2452	2360	2452	2360	2452	1514
45°	1035	971	1035	971	1035	801
55°	99	99	99	99	99	105
65°	0	0	0	0	0	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	3	23	3	45	3	3
95°	33	24	33	143	33	40
105°	154	247	154	340	154	164
115°	296	410	296	505	296	292
125°	438	650	438	619	438	391
135°	595	851	595	686	595	460
145°	760	981	760	701	760	475
155°	902	1065	902	727	902	415
165°	998	1111	998	837	998	281
175°	1043	1087	1043	982	1043	99
180°	1046	1046	1046	1046	1046	



TEST NUMBER: P1427530

CATALOG NUMBER: SQ2W-BBM-K-075U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8
2.5°	3551.4	3547.0	3542.6	3532.1	3519.5	3520.4	3534.9	3545.0	3541.8	3538.7	3541.8
5°	3550.0	3546.1	3542.1	3531.1	3517.8	3521.7	3542.9	3558.4	3556.9	3555.3	3556.9
7.5°	3547.9	3545.2	3542.5	3534.8	3525.3	3529.4	3546.8	3558.9	3555.0	3551.0	3555.0
10°	3553.5	3552.7	3552.0	3540.0	3524.2	3525.4	3543.5	3556.1	3552.1	3548.2	3552.1
12.5°	3556.4	3561.2	3566.1	3548.9	3524.4	3519.3	3533.6	3542.6	3535.5	3528.4	3535.5
15°	3548.2	3561.6	3574.9	3550.6	3513.6	3496.3	3498.7	3497.9	3487.7	3477.5	3487.7
17.5°	3508.6	3527.5	3546.3	3514.1	3464.9	3436.0	3427.4	3417.2	3402.8	3388.3	3402.8
20°	3456.2	3478.3	3500.3	3465.1	3410.8	3376.3	3361.3	3347.0	3334.4	3321.8	3334.4
22.5°	3382.7	3402.8	3422.9	3389.1	3337.4	3302.2	3283.5	3266.9	3256.9	3246.8	3256.9
25°	3251.1	3264.4	3277.8	3243.4	3193.1	3160.9	3146.7	3134.7	3129.2	3123.7	3129.2
27.5°	3064.6	3068.4	3072.2	3044.8	3007.1	2979.4	2961.8	2946.8	2939.8	2932.7	2939.8
30°	2920.3	2920.3	2920.3	2899.1	2870.8	2847.2	2828.3	2810.8	2797.5	2784.1	2797.5
32.5°	2751.9	2750.0	2748.1	2732.6	2712.4	2692.0	2671.2	2652.3	2639.0	2625.6	2639.0
35°	2451.6	2460.2	2468.9	2458.0	2440.8	2421.9	2401.4	2383.2	2371.4	2359.6	2371.4
37.5°	2126.5	2129.8	2133.1	2124.1	2111.0	2093.5	2071.5	2052.5	2042.6	2032.7	2042.6
40°	1880.2	1881.0	1881.8	1870.8	1855.9	1840.5	1824.8	1809.3	1794.4	1779.4	1794.4
42.5°	1593.0	1608.9	1624.7	1618.0	1603.7	1583.9	1558.8	1538.4	1532.3	1526.1	1532.3
45°	1034.7	1104.7	1174.7	1200.4	1211.4	1202.8	1174.5	1133.0	1052.0	971.1	1052.0
47.5°	520.0	607.1	694.2	754.6	806.0	791.4	710.7	628.8	543.1	457.4	543.1
50°	293.6	345.5	397.4	478.2	568.6	553.6	433.4	335.9	306.8	277.7	306.8
52.5°	196.0	218.9	241.9	306.9	386.0	380.8	291.4	220.2	203.6	187.1	203.6
55°	99.1	105.3	111.6	140.3	176.5	175.7	138.0	108.5	103.8	99.1	103.8
57.5°	33.6	42.1	50.6	63.3	77.5	77.9	64.5	52.6	44.8	37.1	44.8
60°	5.3	13.2	21.0	31.2	42.3	41.1	27.7	15.9	8.8	1.8	8.8
62.5°	1.1	3.3	5.5	13.8	24.2	23.9	13.1	4.4	2.4	0.4	2.4
65°	0.0	0.0	0.0	0.6	1.4	1.4	0.6	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.6	1.5	2.5	3.4	4.0	4.2	4.2	4.4	4.6	4.6	4.6
90°	3.2	7.4	12.7	16.9	20.1	21.1	21.1	22.2	23.2	23.2	23.2
92.5°	11.6	18.4	18.6	18.6	22.6	24.5	26.2	26.4	27.5	27.5	27.5
95°	32.8	35.9	53.9	52.8	35.9	28.5	24.3	24.3	24.3	24.3	24.3
97.5°	62.6	67.2	70.2	94.0	99.3	95.9	78.2	65.7	58.8	55.6	58.8
100°	88.8	90.9	97.2	98.3	124.7	150.0	137.4	121.5	116.2	113.1	116.2
102.5°	115.0	116.2	126.0	130.4	136.5	150.9	194.9	190.0	186.4	185.8	186.4
105°	154.3	155.3	173.3	181.7	186.0	186.0	184.9	206.1	239.9	247.3	239.9
107.5°	196.3	201.2	222.3	244.9	249.8	251.1	245.6	242.4	241.1	242.0	241.1
110°	225.1	232.5	257.8	286.4	293.8	295.9	293.8	290.6	288.5	288.5	288.5



TEST NUMBER: P1427530

CATALOG NUMBER: SQ2W-BBM-K-075U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	253.0	263.7	292.5	325.2	337.7	344.1	339.4	337.1	335.0	336.7	335.0
115°	295.9	311.7	349.8	383.6	408.9	412.1	411.0	411.0	410.0	410.0	410.0
117.5°	335.6	361.0	403.7	443.0	472.3	480.8	485.0	483.7	482.5	484.6	482.5
120°	363.5	393.1	441.7	486.1	514.6	527.3	531.5	529.4	531.5	529.4	531.5
122.5°	393.1	429.4	477.2	523.3	556.9	571.2	576.3	576.7	577.2	575.9	577.2
125°	437.5	481.8	537.8	585.4	620.3	637.2	641.4	642.5	644.6	649.9	644.6
127.5°	482.3	532.6	594.1	639.9	675.6	696.1	702.7	705.0	709.5	711.8	709.5
130°	513.5	570.6	632.9	676.3	711.1	733.3	745.0	748.1	753.4	752.4	753.4
132.5°	546.5	606.1	669.3	714.3	746.6	770.5	780.5	789.5	791.5	792.9	791.5
135°	594.9	659.4	722.8	767.1	797.8	821.0	833.7	842.2	847.5	850.6	847.5
137.5°	645.8	713.9	774.8	814.3	845.1	865.2	879.6	888.5	893.9	896.5	893.9
140°	680.5	746.0	805.2	846.4	873.9	893.9	906.6	917.2	923.5	923.5	923.5
142.5°	713.5	778.1	835.6	876.8	900.9	919.3	932.8	940.9	948.0	948.0	948.0
145°	759.7	824.2	877.0	918.3	938.3	955.2	970.0	976.4	980.6	980.6	980.6
147.5°	808.1	865.2	913.4	952.9	969.8	989.7	1001.3	1006.4	1011.7	1009.3	1011.7
150°	836.9	889.7	936.2	973.2	990.1	1009.1	1020.7	1025.0	1030.3	1027.1	1030.3
152.5°	864.8	915.1	957.3	991.8	1006.2	1025.2	1038.5	1042.7	1046.3	1044.0	1046.3
155°	902.4	946.8	985.9	1017.6	1030.3	1048.2	1060.9	1066.2	1070.4	1065.1	1070.4
157.5°	936.0	974.3	1008.3	1037.4	1051.0	1066.4	1078.2	1084.8	1089.0	1086.7	1089.0
160°	956.3	991.2	1021.8	1049.3	1062.0	1075.7	1088.4	1095.8	1100.0	1096.8	1100.0
162.5°	973.2	1004.7	1033.6	1058.6	1069.6	1081.6	1096.8	1103.4	1107.6	1103.6	1107.6
165°	997.5	1022.9	1048.2	1069.4	1078.9	1088.4	1104.2	1111.6	1114.8	1110.6	1114.8
167.5°	1015.9	1035.3	1055.8	1074.0	1081.0	1090.3	1106.1	1112.3	1116.3	1111.0	1116.3
170°	1026.0	1042.9	1060.9	1075.7	1081.0	1089.4	1105.3	1110.6	1113.7	1108.5	1113.7
172.5°	1034.5	1047.2	1061.7	1074.9	1077.6	1084.4	1099.4	1104.6	1107.0	1102.5	1107.0
175°	1042.9	1050.3	1060.9	1069.4	1068.3	1072.5	1085.2	1089.4	1093.7	1087.3	1093.7
177.5°	1047.0	1050.3	1053.7	1058.8	1055.4	1055.4	1064.7	1067.2	1068.1	1064.7	1068.1
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P1427530

CATALOG NUMBER: SQ2W-BBM-K-075U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8
2.5°	3545.0	3534.9	3520.4	3519.5	3532.1	3542.6	3547.0	3551.4	3547.0	3542.6	3532.1
5°	3558.4	3542.9	3521.7	3517.8	3531.1	3542.1	3546.1	3550.0	3546.1	3542.1	3531.1
7.5°	3558.9	3546.8	3529.4	3525.3	3534.8	3542.5	3545.2	3547.9	3545.2	3542.5	3534.8
10°	3556.1	3543.5	3525.4	3524.2	3540.0	3552.0	3552.7	3553.5	3552.7	3552.0	3540.0
12.5°	3542.6	3533.6	3519.3	3524.4	3548.9	3566.1	3561.2	3556.4	3561.2	3566.1	3548.9
15°	3497.9	3498.7	3496.3	3513.6	3550.6	3574.9	3561.6	3548.2	3561.6	3574.9	3550.6
17.5°	3417.2	3427.4	3436.0	3464.9	3514.1	3546.3	3527.5	3508.6	3527.5	3546.3	3514.1
20°	3347.0	3361.3	3376.3	3410.8	3465.1	3500.3	3478.3	3456.2	3478.3	3500.3	3465.1
22.5°	3266.9	3283.5	3302.2	3337.4	3389.1	3422.9	3402.8	3382.7	3402.8	3422.9	3389.1
25°	3134.7	3146.7	3160.9	3193.1	3243.4	3277.8	3264.4	3251.1	3264.4	3277.8	3243.4
27.5°	2946.8	2961.8	2979.4	3007.1	3044.8	3072.2	3068.4	3064.6	3068.4	3072.2	3044.8
30°	2810.8	2828.3	2847.2	2870.8	2899.1	2920.3	2920.3	2920.3	2920.3	2920.3	2899.1
32.5°	2652.3	2671.2	2692.0	2712.4	2732.6	2748.1	2750.0	2751.9	2750.0	2748.1	2732.6
35°	2383.2	2401.4	2421.9	2440.8	2458.0	2468.9	2460.2	2451.6	2460.2	2468.9	2458.0
37.5°	2052.5	2071.5	2093.5	2111.0	2124.1	2133.1	2129.8	2126.5	2129.8	2133.1	2124.1
40°	1809.3	1824.8	1840.5	1855.9	1870.8	1881.8	1881.0	1880.2	1881.0	1881.8	1870.8
42.5°	1538.4	1558.8	1583.9	1603.7	1618.0	1624.7	1608.9	1593.0	1608.9	1624.7	1618.0
45°	1133.0	1174.5	1202.8	1211.4	1200.4	1174.7	1104.7	1034.7	1104.7	1174.7	1200.4
47.5°	628.8	710.7	791.4	806.0	754.6	694.2	607.1	520.0	607.1	694.2	754.6
50°	335.9	433.4	553.6	568.6	478.2	397.4	345.5	293.6	345.5	397.4	478.2
52.5°	220.2	291.4	380.8	386.0	306.9	241.9	218.9	196.0	218.9	241.9	306.9
55°	108.5	138.0	175.7	176.5	140.3	111.6	105.3	99.1	105.3	111.6	140.3
57.5°	52.6	64.5	77.9	77.5	63.3	50.6	42.1	33.6	42.1	50.6	63.3
60°	15.9	27.7	41.1	42.3	31.2	21.0	13.2	5.3	13.2	21.0	31.2
62.5°	4.4	13.1	23.9	24.2	13.8	5.5	3.3	1.1	3.3	5.5	13.8
65°	0.0	0.6	1.4	1.4	0.6	0.0	0.0	0.0	0.0	0.0	0.6
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	4.4	4.2	4.2	4.0	3.4	2.5	1.5	0.6	1.5	2.3	3.8
90°	22.2	21.1	21.1	20.1	16.9	12.7	7.4	3.2	7.4	11.6	19.0
92.5°	26.4	26.2	24.5	22.6	18.6	18.6	18.4	11.6	20.1	28.5	41.0
95°	24.3	24.3	28.5	35.9	52.8	53.9	35.9	32.8	46.5	65.5	82.4
97.5°	65.7	78.2	95.9	99.3	94.0	70.2	67.2	62.6	85.2	104.0	131.2
100°	121.5	137.4	150.0	124.7	98.3	97.2	90.9	88.8	113.1	131.0	157.4
102.5°	190.0	194.9	150.9	136.5	130.4	126.0	116.2	115.0	139.3	164.0	186.2
105°	206.1	184.9	186.0	186.0	181.7	173.3	155.3	154.3	181.7	210.3	237.8
107.5°	242.4	245.6	251.1	249.8	244.9	222.3	201.2	196.3	221.1	255.3	285.5
110°	290.6	293.8	295.9	293.8	286.4	257.8	232.5	225.1	247.3	283.2	315.9



TEST NUMBER: P1427530

CATALOG NUMBER: SQ2W-BBM-K-075U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	337.1	339.4	344.1	337.7	325.2	292.5	263.7	253.0	275.2	311.9	345.5
115°	411.0	411.0	412.1	408.9	383.6	349.8	311.7	295.9	314.9	348.7	385.7
117.5°	483.7	485.0	480.8	472.3	443.0	403.7	361.0	335.6	350.6	386.3	424.4
120°	529.4	531.5	527.3	514.6	486.1	441.7	393.1	363.5	375.1	410.0	448.0
122.5°	576.7	576.3	571.2	556.9	523.3	477.2	429.4	393.1	397.9	430.3	467.5
125°	642.5	641.4	637.2	620.3	585.4	537.8	481.8	437.5	431.1	458.6	496.6
127.5°	705.0	702.7	696.1	675.6	639.9	594.1	532.6	482.3	468.1	485.4	520.3
130°	748.1	745.0	733.3	711.1	676.3	632.9	570.6	513.5	493.5	504.0	534.7
132.5°	789.5	780.5	770.5	746.6	714.3	669.3	606.1	546.5	518.8	523.5	547.4
135°	842.2	833.7	821.0	797.8	767.1	722.8	659.4	594.9	556.9	552.6	566.4
137.5°	888.5	879.6	865.2	845.1	814.3	774.8	713.9	645.8	597.9	583.7	589.0
140°	917.2	906.6	893.9	873.9	846.4	805.2	746.0	680.5	626.6	606.5	603.4
142.5°	940.9	932.8	919.3	900.9	876.8	835.6	778.1	713.5	656.2	630.2	622.8
145°	976.4	970.0	955.2	938.3	918.3	877.0	824.2	759.7	702.7	668.9	653.0
147.5°	1006.4	1001.3	989.7	969.8	952.9	913.4	865.2	808.1	749.6	707.8	687.3
150°	1025.0	1020.7	1009.1	990.1	973.2	936.2	889.7	836.9	780.9	736.5	710.1
152.5°	1042.7	1038.5	1025.2	1006.2	991.8	957.3	915.1	864.8	807.9	763.6	736.3
155°	1066.2	1060.9	1048.2	1030.3	1017.6	985.9	946.8	902.4	853.8	807.3	776.7
157.5°	1084.8	1078.2	1066.4	1051.0	1037.4	1008.3	974.3	936.0	893.5	849.1	817.9
160°	1095.8	1088.4	1075.7	1062.0	1049.3	1021.8	991.2	956.3	917.2	877.0	843.2
162.5°	1103.4	1096.8	1081.6	1069.6	1058.6	1033.6	1004.7	973.2	938.3	903.2	872.0
165°	1111.6	1104.2	1088.4	1078.9	1069.4	1048.2	1022.9	997.5	967.9	939.4	914.0
167.5°	1112.3	1106.1	1090.3	1081.0	1074.0	1055.8	1035.3	1015.9	992.9	970.5	949.3
170°	1110.6	1105.3	1089.4	1081.0	1075.7	1060.9	1042.9	1026.0	1008.1	989.0	972.1
172.5°	1104.6	1099.4	1084.4	1077.6	1074.9	1061.7	1047.2	1034.5	1019.1	1005.1	991.6
175°	1089.4	1085.2	1072.5	1068.3	1069.4	1060.9	1050.3	1042.9	1033.4	1025.0	1017.6
177.5°	1067.2	1064.7	1055.4	1055.4	1058.8	1053.7	1050.3	1047.0	1042.7	1040.2	1037.7
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P1427530

CATALOG NUMBER: SQ2W-BBM-K-075U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8
2.5°	3519.5	3520.4	3534.9	3545.0	3541.8	3538.7	3541.8	3545.0	3534.9	3520.4	3519.5
5°	3517.8	3521.7	3542.9	3558.4	3556.9	3555.3	3556.9	3558.4	3542.9	3521.7	3517.8
7.5°	3525.3	3529.4	3546.8	3558.9	3555.0	3551.0	3555.0	3558.9	3546.8	3529.4	3525.3
10°	3524.2	3525.4	3543.5	3556.1	3552.1	3548.2	3552.1	3556.1	3543.5	3525.4	3524.2
12.5°	3524.4	3519.3	3533.6	3542.6	3535.5	3528.4	3535.5	3542.6	3533.6	3519.3	3524.4
15°	3513.6	3496.3	3498.7	3497.9	3487.7	3477.5	3487.7	3497.9	3498.7	3496.3	3513.6
17.5°	3464.9	3436.0	3427.4	3417.2	3402.8	3388.3	3402.8	3417.2	3427.4	3436.0	3464.9
20°	3410.8	3376.3	3361.3	3347.0	3334.4	3321.8	3334.4	3347.0	3361.3	3376.3	3410.8
22.5°	3337.4	3302.2	3283.5	3266.9	3256.9	3246.8	3256.9	3266.9	3283.5	3302.2	3337.4
25°	3193.1	3160.9	3146.7	3134.7	3129.2	3123.7	3129.2	3134.7	3146.7	3160.9	3193.1
27.5°	3007.1	2979.4	2961.8	2946.8	2939.8	2932.7	2939.8	2946.8	2961.8	2979.4	3007.1
30°	2870.8	2847.2	2828.3	2810.8	2797.5	2784.1	2797.5	2810.8	2828.3	2847.2	2870.8
32.5°	2712.4	2692.0	2671.2	2652.3	2639.0	2625.6	2639.0	2652.3	2671.2	2692.0	2712.4
35°	2440.8	2421.9	2401.4	2383.2	2371.4	2359.6	2371.4	2383.2	2401.4	2421.9	2440.8
37.5°	2111.0	2093.5	2071.5	2052.5	2042.6	2032.7	2042.6	2052.5	2071.5	2093.5	2111.0
40°	1855.9	1840.5	1824.8	1809.3	1794.4	1779.4	1794.4	1809.3	1824.8	1840.5	1855.9
42.5°	1603.7	1583.9	1558.8	1538.4	1532.3	1526.1	1532.3	1538.4	1558.8	1583.9	1603.7
45°	1211.4	1202.8	1174.5	1133.0	1052.0	971.1	1052.0	1133.0	1174.5	1202.8	1211.4
47.5°	806.0	791.4	710.7	628.8	543.1	457.4	543.1	628.8	710.7	791.4	806.0
50°	568.6	553.6	433.4	335.9	306.8	277.7	306.8	335.9	433.4	553.6	568.6
52.5°	386.0	380.8	291.4	220.2	203.6	187.1	203.6	220.2	291.4	380.8	386.0
55°	176.5	175.7	138.0	108.5	103.8	99.1	103.8	108.5	138.0	175.7	176.5
57.5°	77.5	77.9	64.5	52.6	44.8	37.1	44.8	52.6	64.5	77.9	77.5
60°	42.3	41.1	27.7	15.9	8.8	1.8	8.8	15.9	27.7	41.1	42.3
62.5°	24.2	23.9	13.1	4.4	2.4	0.4	2.4	4.4	13.1	23.9	24.2
65°	1.4	1.4	0.6	0.0	0.0	0.0	0.0	0.6	1.4	1.4	1.4
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	4.9	6.3	7.8	8.7	9.5	9.1	9.5	8.7	7.8	6.3	4.9
90°	24.3	31.7	39.1	43.3	47.6	45.4	47.6	43.3	39.1	31.7	24.3
92.5°	48.8	61.3	70.4	78.0	81.4	80.9	81.4	78.0	70.4	61.3	48.8
95°	98.3	113.1	127.9	138.4	144.8	142.7	144.8	138.4	127.9	113.1	98.3
97.5°	151.5	171.4	187.9	197.8	204.1	208.4	204.1	197.8	187.9	171.4	151.5
100°	187.0	206.1	225.1	236.7	247.3	251.5	247.3	236.7	225.1	206.1	187.0
102.5°	215.8	240.7	261.4	273.9	282.8	287.0	282.8	273.9	261.4	240.7	215.8
105°	263.1	289.5	311.7	327.6	337.1	340.2	337.1	327.6	311.7	289.5	263.1
107.5°	310.5	337.7	358.2	375.8	387.4	394.1	387.4	375.8	358.2	337.7	310.5
110°	347.6	369.8	392.0	407.9	419.5	423.7	419.5	407.9	392.0	369.8	347.6



TEST NUMBER: P1427530

CATALOG NUMBER: SQ2W-BBM-K-075U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	378.9	403.7	425.8	441.7	455.0	460.9	455.0	441.7	425.8	403.7	378.9
115°	422.7	455.4	475.5	490.3	499.8	505.1	499.8	490.3	475.5	455.4	422.7
117.5°	459.0	493.3	515.2	526.6	531.1	534.9	531.1	526.6	515.2	493.3	459.0
120°	481.8	513.5	538.9	553.7	559.0	561.1	559.0	553.7	538.9	513.5	481.8
122.5°	503.0	533.0	557.5	575.7	584.3	586.5	584.3	575.7	557.5	533.0	503.0
125°	532.6	561.1	586.5	604.4	613.9	619.2	613.9	604.4	586.5	561.1	532.6
127.5°	558.3	589.2	612.4	628.7	638.0	642.2	638.0	628.7	612.4	589.2	558.3
130°	572.7	604.4	627.7	645.6	654.1	658.3	654.1	645.6	627.7	604.4	572.7
132.5°	583.7	617.1	641.2	657.5	666.8	671.0	666.8	657.5	641.2	617.1	583.7
135°	597.0	631.9	657.3	673.1	681.6	685.8	681.6	673.1	657.3	631.9	597.0
137.5°	608.6	640.3	666.8	683.5	691.1	693.8	691.1	683.5	666.8	640.3	608.6
140°	617.1	644.6	671.0	686.8	695.3	696.3	695.3	686.8	671.0	644.6	617.1
142.5°	628.1	649.6	672.7	688.5	697.0	698.9	697.0	688.5	672.7	649.6	628.1
145°	647.7	660.4	676.3	691.1	698.5	700.6	698.5	691.1	676.3	660.4	647.7
147.5°	672.5	676.5	684.7	694.4	701.6	703.1	701.6	694.4	684.7	676.5	672.5
150°	691.1	690.0	693.2	699.5	705.9	704.8	705.9	699.5	693.2	690.0	691.1
152.5°	712.2	706.1	705.9	708.8	711.8	711.6	711.8	708.8	705.9	706.1	712.2
155°	748.1	736.5	730.2	728.0	728.0	727.0	728.0	728.0	730.2	736.5	748.1
157.5°	787.6	771.4	761.9	756.8	755.3	753.0	755.3	756.8	761.9	771.4	787.6
160°	814.7	796.7	787.2	778.8	775.6	772.4	775.6	778.8	787.2	796.7	814.7
162.5°	840.1	822.9	812.6	805.0	801.8	796.9	801.8	805.0	812.6	822.9	840.1
165°	881.3	863.3	851.7	845.3	841.1	836.9	841.1	845.3	851.7	863.3	881.3
167.5°	922.5	902.8	895.2	888.0	884.0	876.4	884.0	888.0	895.2	902.8	922.5
170°	947.8	929.9	925.6	919.3	911.9	903.5	911.9	919.3	925.6	929.9	947.8
172.5°	969.8	957.8	953.5	947.2	944.9	938.1	944.9	947.2	953.5	957.8	969.8
175°	1001.7	992.2	992.2	991.2	988.0	981.7	988.0	991.2	992.2	992.2	1001.7
177.5°	1028.4	1023.3	1026.7	1026.7	1025.8	1019.9	1025.8	1026.7	1026.7	1023.3	1028.4
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P1427530

CATALOG NUMBER: SQ2W-BBM-K-075U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	3535.8	3535.8	3535.8	3535.8
2.5°	3532.1	3542.6	3547.0	3551.4
5°	3531.1	3542.1	3546.1	3550.0
7.5°	3534.8	3542.5	3545.2	3547.9
10°	3540.0	3552.0	3552.7	3553.5
12.5°	3548.9	3566.1	3561.2	3556.4
15°	3550.6	3574.9	3561.6	3548.2
17.5°	3514.1	3546.3	3527.5	3508.6
20°	3465.1	3500.3	3478.3	3456.2
22.5°	3389.1	3422.9	3402.8	3382.7
25°	3243.4	3277.8	3264.4	3251.1
27.5°	3044.8	3072.2	3068.4	3064.6
30°	2899.1	2920.3	2920.3	2920.3
32.5°	2732.6	2748.1	2750.0	2751.9
35°	2458.0	2468.9	2460.2	2451.6
37.5°	2124.1	2133.1	2129.8	2126.5
40°	1870.8	1881.8	1881.0	1880.2
42.5°	1618.0	1624.7	1608.9	1593.0
45°	1200.4	1174.7	1104.7	1034.7
47.5°	754.6	694.2	607.1	520.0
50°	478.2	397.4	345.5	293.6
52.5°	306.9	241.9	218.9	196.0
55°	140.3	111.6	105.3	99.1
57.5°	63.3	50.6	42.1	33.6
60°	31.2	21.0	13.2	5.3
62.5°	13.8	5.5	3.3	1.1
65°	0.6	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0
87.5°	3.8	2.3	1.5	0.6
90°	19.0	11.6	7.4	3.2
92.5°	41.0	28.5	20.1	11.6
95°	82.4	65.5	46.5	32.8
97.5°	131.2	104.0	85.2	62.6
100°	157.4	131.0	113.1	88.8
102.5°	186.2	164.0	139.3	115.0
105°	237.8	210.3	181.7	154.3
107.5°	285.5	255.3	221.1	196.3
110°	315.9	283.2	247.3	225.1

TEST NUMBER: P1427530

CATALOG NUMBER: SQ2W-BBM-K-075U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	345.5	311.9	275.2	253.0
115°	385.7	348.7	314.9	295.9
117.5°	424.4	386.3	350.6	335.6
120°	448.0	410.0	375.1	363.5
122.5°	467.5	430.3	397.9	393.1
125°	496.6	458.6	431.1	437.5
127.5°	520.3	485.4	468.1	482.3
130°	534.7	504.0	493.5	513.5
132.5°	547.4	523.5	518.8	546.5
135°	566.4	552.6	556.9	594.9
137.5°	589.0	583.7	597.9	645.8
140°	603.4	606.5	626.6	680.5
142.5°	622.8	630.2	656.2	713.5
145°	653.0	668.9	702.7	759.7
147.5°	687.3	707.8	749.6	808.1
150°	710.1	736.5	780.9	836.9
152.5°	736.3	763.6	807.9	864.8
155°	776.7	807.3	853.8	902.4
157.5°	817.9	849.1	893.5	936.0
160°	843.2	877.0	917.2	956.3
162.5°	872.0	903.2	938.3	973.2
165°	914.0	939.4	967.9	997.5
167.5°	949.3	970.5	992.9	1015.9
170°	972.1	989.0	1008.1	1026.0
172.5°	991.6	1005.1	1019.1	1034.5
175°	1017.6	1025.0	1033.4	1042.9
177.5°	1037.7	1040.2	1042.7	1047.0
180°	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P1427530
 CATALOG NUMBER: SQ2W-BBM-K-075U-125D-L940-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.89	1.67	1.77	2.53	3.62	1.12	1.90	2.00	2.76	3.84
	3H	0.71	1.39	1.59	2.26	3.37	0.93	1.62	1.82	2.49	3.60
	4H	0.60	1.24	1.50	2.12	3.24	0.83	1.47	1.73	2.35	3.47
	6H	0.49	1.08	1.40	1.97	3.10	0.72	1.31	1.63	2.20	3.33
	8H	0.43	0.99	1.35	1.89	3.02	0.66	1.22	1.58	2.12	3.25
	12H	0.38	0.90	1.30	1.80	2.95	0.60	1.13	1.52	2.03	3.18
4H	2H	0.61	1.25	1.52	2.13	3.25	0.84	1.48	1.74	2.36	3.48
	3H	0.41	0.94	1.33	1.85	2.98	0.64	1.17	1.55	2.08	3.21
	4H	0.30	0.78	1.22	1.69	2.85	0.53	1.01	1.45	1.91	3.07
	6H	0.19	0.60	1.13	1.53	2.69	0.42	0.83	1.36	1.76	2.92
	8H	0.13	0.51	1.06	1.43	2.60	0.36	0.73	1.29	1.66	2.83
	12H	0.06	0.40	1.01	1.34	2.52	0.29	0.62	1.24	1.57	2.74
8H	4H	0.13	0.51	1.06	1.43	2.60	0.36	0.73	1.29	1.66	2.83
	6H	0.01	0.32	0.97	1.29	2.46	0.24	0.55	1.20	1.51	2.69
	8H	0.00	0.22	0.92	1.18	2.37	0.17	0.45	1.14	1.41	2.60
	12H	0.00	0.12	0.85	1.07	2.31	0.11	0.35	1.08	1.30	2.54
12H	4H	0.06	0.40	1.01	1.34	2.52	0.29	0.62	1.24	1.57	2.74
	6H	0.00	0.22	0.92	1.18	2.37	0.17	0.45	1.14	1.41	2.60
	8H	0.00	0.12	0.85	1.07	2.31	0.11	0.35	1.08	1.30	2.54