

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427614

Luminaire Tested: SQ2W-BBN-K-075U-125D-L940-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2024
Report Number: P1427614
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2308-130-1)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-BBN-K-075U-125D-L940-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - BLACK DISCREET BAFFLE, NARROW 35-DEGREE OPTIC
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8368.3 lumens
Efficiency: N/A
Efficacy: 114.0 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.62
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 73.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1427614

CATALOG NUMBER: SQ2W-BBN-K-075U-125D-L940-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1427614

CATALOG NUMBER: SQ2W-BBN-K-075U-125D-L940-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69	64		
1	104	101	98	95	98	95	93	90	84	83	81	74	73	72	65	65	64	60		
2	98	92	88	84	92	87	83	80	78	75	73	70	68	66	62	61	60	56		
3	92	85	79	75	87	81	76	72	73	69	66	66	63	61	59	57	55	52		
4	86	78	72	68	82	75	69	65	68	64	61	62	59	56	56	54	52	49		
5	81	72	66	62	77	69	64	60	63	59	56	58	55	52	53	50	49	46		
6	77	67	61	57	73	65	59	55	60	55	52	55	51	49	50	48	46	43		
7	73	63	57	52	69	61	55	51	56	51	48	52	48	46	48	45	43	41		
8	69	59	53	49	66	57	51	47	53	48	45	49	45	43	45	43	41	39		
9	65	55	49	45	62	54	48	44	50	45	42	46	43	40	43	40	38	37		
10	62	52	46	42	59	51	45	42	47	43	40	44	41	38	41	38	36	35		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	158591	158591	158591	158591
5°	153288	153374	153288	153374
10°	131552	131552	131552	131552
15°	102109	101874	102109	101874
20°	73694	72113	73694	72113
25°	52254	50266	52254	50266
30°	38877	37523	38877	37523
35°	30249	28854	30249	28854
40°	22385	20444	22385	20444
45°	11439	9216	11439	9216
50°	2489	1824	2489	1824
55°	698	549	698	549
60°	113	58	113	58
65°	0	0	0	0
70°	0	0	0	0
75°	0	0	0	0
80°	0	0	0	0
85°	0	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 40°
 Vertical Angle: 45°
 Luminance: 13953 cd/sqm



TEST NUMBER: P1427614

CATALOG NUMBER: SQ2W-BBN-K-075U-125D-L940-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	849.4	10.2
10°-20°	1674.6	20.0
20°-30°	1350.9	16.1
30°-40°	938.4	11.2
40°-50°	433.5	5.2
50°-60°	60.7	0.7
60°-70°	2.1	0.0
70°-80°	0.0	0.0
80°-90°	5.5	0.1
90°-100°	83.3	1.0
100°-110°	242.8	2.9
110°-120°	396.2	4.7
120°-130°	502.8	6.0
130°-140°	538.0	6.4
140°-150°	502.4	6.0
150°-160°	413.4	4.9
160°-170°	277.2	3.3
170°-180°	98.4	1.2
0°-30°	3874.9	46.3
0°-40°	4813.3	57.5
0°-60°	5307.5	63.4
0°-90°	5315.1	63.5
90°-120°	722.3	8.6
90°-150°	2265.4	27.1
90°-180°	3054.0	36.5
0°-180°	8368.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	9823	9823	9823	9823	9823	
5°	9458	9463	9458	9463	9458	850
15°	6109	6095	6109	6095	6109	1682
25°	2933	2822	2933	2822	2933	1373
35°	1535	1464	1535	1464	1535	960
45°	501	404	501	404	501	405
55°	25	20	25	20	25	31
65°	0	0	0	0	0	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	3	23	3	45	3	3
95°	33	24	33	143	33	40
105°	154	247	154	340	154	164
115°	296	410	296	505	296	292
125°	438	650	438	619	438	391
135°	595	851	595	686	595	460
145°	760	981	760	701	760	475
155°	902	1065	902	727	902	415
165°	998	1111	998	837	998	281
175°	1043	1087	1043	982	1043	99
180°	1046	1046	1046	1046	1046	



TEST NUMBER: P1427614

CATALOG NUMBER: SQ2W-BBN-K-075U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6
2.5°	9817.0	9800.6	9784.2	9751.8	9714.1	9712.5	9747.1	9770.4	9759.7	9749.0	9759.7
5°	9458.0	9435.2	9412.3	9384.8	9355.7	9366.7	9417.8	9457.0	9460.1	9463.3	9460.1
7.5°	8665.6	8673.0	8680.4	8661.5	8633.8	8648.3	8704.9	8745.9	8739.8	8733.6	8739.8
10°	8024.1	8029.6	8035.2	8034.2	8031.0	8038.9	8057.8	8066.6	8045.4	8024.1	8045.4
12.5°	7280.7	7302.5	7324.4	7299.2	7258.3	7252.0	7280.3	7303.8	7312.8	7321.7	7312.8
15°	6108.8	6144.2	6179.6	6129.5	6050.8	6030.4	6068.1	6096.2	6095.5	6094.7	6095.5
17.5°	5009.9	5006.3	5002.7	4971.7	4931.6	4915.0	4922.1	4926.8	4924.5	4922.1	4924.5
20°	4289.1	4283.6	4278.1	4251.3	4217.5	4197.8	4192.3	4189.2	4193.1	4197.1	4193.1
22.5°	3671.7	3662.4	3653.1	3641.9	3630.1	3617.4	3603.7	3594.7	3599.9	3605.1	3599.9
25°	2933.2	2903.3	2873.4	2849.4	2827.3	2825.8	2844.6	2854.7	2838.2	2821.6	2838.2
27.5°	2354.3	2353.8	2353.4	2339.2	2320.5	2312.1	2314.2	2316.5	2319.7	2322.8	2319.7
30°	2085.3	2079.7	2074.2	2059.3	2041.2	2032.5	2033.3	2031.6	2022.1	2012.7	2022.1
32.5°	1845.9	1849.9	1853.8	1837.9	1815.4	1802.0	1797.8	1792.2	1782.8	1773.3	1782.8
35°	1534.7	1534.7	1534.7	1521.7	1504.4	1489.9	1478.1	1468.6	1466.3	1463.9	1466.3
37.5°	1246.2	1244.8	1243.4	1233.8	1221.5	1207.1	1190.4	1176.3	1170.2	1164.1	1170.2
40°	1062.1	1058.2	1054.2	1047.3	1039.5	1025.3	1004.9	987.4	978.7	970.0	978.7
42.5°	852.5	863.1	873.6	870.3	862.5	848.3	827.8	809.2	796.2	783.1	796.2
45°	501.0	545.0	589.1	604.8	611.1	602.4	578.8	543.6	473.6	403.6	473.6
47.5°	215.3	263.7	312.2	352.9	390.9	378.9	316.7	255.6	197.4	139.1	197.4
50°	99.1	136.9	174.7	225.4	280.5	269.1	191.2	126.1	99.3	72.6	99.3
52.5°	58.1	76.9	95.8	143.3	200.2	195.1	127.9	74.0	59.8	45.7	59.8
55°	24.8	31.1	37.4	63.1	95.4	93.8	58.4	30.5	25.0	19.5	25.0
57.5°	9.2	12.7	16.1	25.4	36.5	35.8	23.2	13.1	10.3	7.4	10.3
60°	3.5	5.1	6.7	11.2	16.7	16.3	10.0	4.9	3.3	1.8	3.3
62.5°	0.7	1.7	2.6	5.1	8.1	8.0	4.8	2.2	1.3	0.4	1.3
65°	0.0	0.0	0.0	0.6	1.4	1.4	0.6	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.6	1.5	2.5	3.4	4.0	4.2	4.2	4.4	4.6	4.6	4.6
90°	3.2	7.4	12.7	16.9	20.1	21.1	21.1	22.2	23.2	23.2	23.2
92.5°	11.6	18.4	18.6	18.6	22.6	24.5	26.2	26.4	27.5	27.5	27.5
95°	32.8	35.9	53.9	52.8	35.9	28.5	24.3	24.3	24.3	24.3	24.3
97.5°	62.6	67.2	70.2	94.0	99.3	95.9	78.2	65.7	58.8	55.6	58.8
100°	88.8	90.9	97.2	98.3	124.7	150.0	137.4	121.5	116.2	113.1	116.2
102.5°	115.0	116.2	126.0	130.4	136.5	150.9	194.9	190.0	186.4	185.8	186.4
105°	154.3	155.3	173.3	181.7	186.0	186.0	184.9	206.1	239.9	247.3	239.9
107.5°	196.3	201.2	222.3	244.9	249.8	251.1	245.6	242.4	241.1	242.0	241.1
110°	225.1	232.5	257.8	286.4	293.8	295.9	293.8	290.6	288.5	288.5	288.5



TEST NUMBER: P1427614

CATALOG NUMBER: SQ2W-BBN-K-075U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	253.0	263.7	292.5	325.2	337.7	344.1	339.4	337.1	335.0	336.7	335.0
115°	295.9	311.7	349.8	383.6	408.9	412.1	411.0	411.0	410.0	410.0	410.0
117.5°	335.6	361.0	403.7	443.0	472.3	480.8	485.0	483.7	482.5	484.6	482.5
120°	363.5	393.1	441.7	486.1	514.6	527.3	531.5	529.4	531.5	529.4	531.5
122.5°	393.1	429.4	477.2	523.3	556.9	571.2	576.3	576.7	577.2	575.9	577.2
125°	437.5	481.8	537.8	585.4	620.3	637.2	641.4	642.5	644.6	649.9	644.6
127.5°	482.3	532.6	594.1	639.9	675.6	696.1	702.7	705.0	709.5	711.8	709.5
130°	513.5	570.6	632.9	676.3	711.1	733.3	745.0	748.1	753.4	752.4	753.4
132.5°	546.5	606.1	669.3	714.3	746.6	770.5	780.5	789.5	791.5	792.9	791.5
135°	594.9	659.4	722.8	767.1	797.8	821.0	833.7	842.2	847.5	850.6	847.5
137.5°	645.8	713.9	774.8	814.3	845.1	865.2	879.6	888.5	893.9	896.5	893.9
140°	680.5	746.0	805.2	846.4	873.9	893.9	906.6	917.2	923.5	923.5	923.5
142.5°	713.5	778.1	835.6	876.8	900.9	919.3	932.8	940.9	948.0	948.0	948.0
145°	759.7	824.2	877.0	918.3	938.3	955.2	970.0	976.4	980.6	980.6	980.6
147.5°	808.1	865.2	913.4	952.9	969.8	989.7	1001.3	1006.4	1011.7	1009.3	1011.7
150°	836.9	889.7	936.2	973.2	990.1	1009.1	1020.7	1025.0	1030.3	1027.1	1030.3
152.5°	864.8	915.1	957.3	991.8	1006.2	1025.2	1038.5	1042.7	1046.3	1044.0	1046.3
155°	902.4	946.8	985.9	1017.6	1030.3	1048.2	1060.9	1066.2	1070.4	1065.1	1070.4
157.5°	936.0	974.3	1008.3	1037.4	1051.0	1066.4	1078.2	1084.8	1089.0	1086.7	1089.0
160°	956.3	991.2	1021.8	1049.3	1062.0	1075.7	1088.4	1095.8	1100.0	1096.8	1100.0
162.5°	973.2	1004.7	1033.6	1058.6	1069.6	1081.6	1096.8	1103.4	1107.6	1103.6	1107.6
165°	997.5	1022.9	1048.2	1069.4	1078.9	1088.4	1104.2	1111.6	1114.8	1110.6	1114.8
167.5°	1015.9	1035.3	1055.8	1074.0	1081.0	1090.3	1106.1	1112.3	1116.3	1111.0	1116.3
170°	1026.0	1042.9	1060.9	1075.7	1081.0	1089.4	1105.3	1110.6	1113.7	1108.5	1113.7
172.5°	1034.5	1047.2	1061.7	1074.9	1077.6	1084.4	1099.4	1104.6	1107.0	1102.5	1107.0
175°	1042.9	1050.3	1060.9	1069.4	1068.3	1072.5	1085.2	1089.4	1093.7	1087.3	1093.7
177.5°	1047.0	1050.3	1053.7	1058.8	1055.4	1055.4	1064.7	1067.2	1068.1	1064.7	1068.1
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P1427614

CATALOG NUMBER: SQ2W-BBN-K-075U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6
2.5°	9770.4	9747.1	9712.5	9714.1	9751.8	9784.2	9800.6	9817.0	9800.6	9784.2	9751.8
5°	9457.0	9417.8	9366.7	9355.7	9384.8	9412.3	9435.2	9458.0	9435.2	9412.3	9384.8
7.5°	8745.9	8704.9	8648.3	8633.8	8661.5	8680.4	8673.0	8665.6	8673.0	8680.4	8661.5
10°	8066.6	8057.8	8038.9	8031.0	8034.2	8035.2	8029.6	8024.1	8029.6	8035.2	8034.2
12.5°	7303.8	7280.3	7252.0	7258.3	7299.2	7324.4	7302.5	7280.7	7302.5	7324.4	7299.2
15°	6096.2	6068.1	6030.4	6050.8	6129.5	6179.6	6144.2	6108.8	6144.2	6179.6	6129.5
17.5°	4926.8	4922.1	4915.0	4931.6	4971.7	5002.7	5006.3	5009.9	5006.3	5002.7	4971.7
20°	4189.2	4192.3	4197.8	4217.5	4251.3	4278.1	4283.6	4289.1	4283.6	4278.1	4251.3
22.5°	3594.7	3603.7	3617.4	3630.1	3641.9	3653.1	3662.4	3671.7	3662.4	3653.1	3641.9
25°	2854.7	2844.6	2825.8	2827.3	2849.4	2873.4	2903.3	2933.2	2903.3	2873.4	2849.4
27.5°	2316.5	2314.2	2312.1	2320.5	2339.2	2353.4	2353.8	2354.3	2353.8	2353.4	2339.2
30°	2031.6	2033.3	2032.5	2041.2	2059.3	2074.2	2079.7	2085.3	2079.7	2074.2	2059.3
32.5°	1792.2	1797.8	1802.0	1815.4	1837.9	1853.8	1849.9	1845.9	1849.9	1853.8	1837.9
35°	1468.6	1478.1	1489.9	1504.4	1521.7	1534.7	1534.7	1534.7	1534.7	1534.7	1521.7
37.5°	1176.3	1190.4	1207.1	1221.5	1233.8	1243.4	1244.8	1246.2	1244.8	1243.4	1233.8
40°	987.4	1004.9	1025.3	1039.5	1047.3	1054.2	1058.2	1062.1	1058.2	1054.2	1047.3
42.5°	809.2	827.8	848.3	862.5	870.3	873.6	863.1	852.5	863.1	873.6	870.3
45°	543.6	578.8	602.4	611.1	604.8	589.1	545.0	501.0	545.0	589.1	604.8
47.5°	255.6	316.7	378.9	390.9	352.9	312.2	263.7	215.3	263.7	312.2	352.9
50°	126.1	191.2	269.1	280.5	225.4	174.7	136.9	99.1	136.9	174.7	225.4
52.5°	74.0	127.9	195.1	200.2	143.3	95.8	76.9	58.1	76.9	95.8	143.3
55°	30.5	58.4	93.8	95.4	63.1	37.4	31.1	24.8	31.1	37.4	63.1
57.5°	13.1	23.2	35.8	36.5	25.4	16.1	12.7	9.2	12.7	16.1	25.4
60°	4.9	10.0	16.3	16.7	11.2	6.7	5.1	3.5	5.1	6.7	11.2
62.5°	2.2	4.8	8.0	8.1	5.1	2.6	1.7	0.7	1.7	2.6	5.1
65°	0.0	0.6	1.4	1.4	0.6	0.0	0.0	0.0	0.0	0.0	0.6
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	4.4	4.2	4.2	4.0	3.4	2.5	1.5	0.6	1.5	2.3	3.8
90°	22.2	21.1	21.1	20.1	16.9	12.7	7.4	3.2	7.4	11.6	19.0
92.5°	26.4	26.2	24.5	22.6	18.6	18.6	18.4	11.6	20.1	28.5	41.0
95°	24.3	24.3	28.5	35.9	52.8	53.9	35.9	32.8	46.5	65.5	82.4
97.5°	65.7	78.2	95.9	99.3	94.0	70.2	67.2	62.6	85.2	104.0	131.2
100°	121.5	137.4	150.0	124.7	98.3	97.2	90.9	88.8	113.1	131.0	157.4
102.5°	190.0	194.9	150.9	136.5	130.4	126.0	116.2	115.0	139.3	164.0	186.2
105°	206.1	184.9	186.0	186.0	181.7	173.3	155.3	154.3	181.7	210.3	237.8
107.5°	242.4	245.6	251.1	249.8	244.9	222.3	201.2	196.3	221.1	255.3	285.5
110°	290.6	293.8	295.9	293.8	286.4	257.8	232.5	225.1	247.3	283.2	315.9



TEST NUMBER: P1427614

CATALOG NUMBER: SQ2W-BBN-K-075U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	337.1	339.4	344.1	337.7	325.2	292.5	263.7	253.0	275.2	311.9	345.5
115°	411.0	411.0	412.1	408.9	383.6	349.8	311.7	295.9	314.9	348.7	385.7
117.5°	483.7	485.0	480.8	472.3	443.0	403.7	361.0	335.6	350.6	386.3	424.4
120°	529.4	531.5	527.3	514.6	486.1	441.7	393.1	363.5	375.1	410.0	448.0
122.5°	576.7	576.3	571.2	556.9	523.3	477.2	429.4	393.1	397.9	430.3	467.5
125°	642.5	641.4	637.2	620.3	585.4	537.8	481.8	437.5	431.1	458.6	496.6
127.5°	705.0	702.7	696.1	675.6	639.9	594.1	532.6	482.3	468.1	485.4	520.3
130°	748.1	745.0	733.3	711.1	676.3	632.9	570.6	513.5	493.5	504.0	534.7
132.5°	789.5	780.5	770.5	746.6	714.3	669.3	606.1	546.5	518.8	523.5	547.4
135°	842.2	833.7	821.0	797.8	767.1	722.8	659.4	594.9	556.9	552.6	566.4
137.5°	888.5	879.6	865.2	845.1	814.3	774.8	713.9	645.8	597.9	583.7	589.0
140°	917.2	906.6	893.9	873.9	846.4	805.2	746.0	680.5	626.6	606.5	603.4
142.5°	940.9	932.8	919.3	900.9	876.8	835.6	778.1	713.5	656.2	630.2	622.8
145°	976.4	970.0	955.2	938.3	918.3	877.0	824.2	759.7	702.7	668.9	653.0
147.5°	1006.4	1001.3	989.7	969.8	952.9	913.4	865.2	808.1	749.6	707.8	687.3
150°	1025.0	1020.7	1009.1	990.1	973.2	936.2	889.7	836.9	780.9	736.5	710.1
152.5°	1042.7	1038.5	1025.2	1006.2	991.8	957.3	915.1	864.8	807.9	763.6	736.3
155°	1066.2	1060.9	1048.2	1030.3	1017.6	985.9	946.8	902.4	853.8	807.3	776.7
157.5°	1084.8	1078.2	1066.4	1051.0	1037.4	1008.3	974.3	936.0	893.5	849.1	817.9
160°	1095.8	1088.4	1075.7	1062.0	1049.3	1021.8	991.2	956.3	917.2	877.0	843.2
162.5°	1103.4	1096.8	1081.6	1069.6	1058.6	1033.6	1004.7	973.2	938.3	903.2	872.0
165°	1111.6	1104.2	1088.4	1078.9	1069.4	1048.2	1022.9	997.5	967.9	939.4	914.0
167.5°	1112.3	1106.1	1090.3	1081.0	1074.0	1055.8	1035.3	1015.9	992.9	970.5	949.3
170°	1110.6	1105.3	1089.4	1081.0	1075.7	1060.9	1042.9	1026.0	1008.1	989.0	972.1
172.5°	1104.6	1099.4	1084.4	1077.6	1074.9	1061.7	1047.2	1034.5	1019.1	1005.1	991.6
175°	1089.4	1085.2	1072.5	1068.3	1069.4	1060.9	1050.3	1042.9	1033.4	1025.0	1017.6
177.5°	1067.2	1064.7	1055.4	1055.4	1058.8	1053.7	1050.3	1047.0	1042.7	1040.2	1037.7
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P1427614

CATALOG NUMBER: SQ2W-BBN-K-075U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6
2.5°	9714.1	9712.5	9747.1	9770.4	9759.7	9749.0	9759.7	9770.4	9747.1	9712.5	9714.1
5°	9355.7	9366.7	9417.8	9457.0	9460.1	9463.3	9460.1	9457.0	9417.8	9366.7	9355.7
7.5°	8633.8	8648.3	8704.9	8745.9	8739.8	8733.6	8739.8	8745.9	8704.9	8648.3	8633.8
10°	8031.0	8038.9	8057.8	8066.6	8045.4	8024.1	8045.4	8066.6	8057.8	8038.9	8031.0
12.5°	7258.3	7252.0	7280.3	7303.8	7312.8	7321.7	7312.8	7303.8	7280.3	7252.0	7258.3
15°	6050.8	6030.4	6068.1	6096.2	6095.5	6094.7	6095.5	6096.2	6068.1	6030.4	6050.8
17.5°	4931.6	4915.0	4922.1	4926.8	4924.5	4922.1	4924.5	4926.8	4922.1	4915.0	4931.6
20°	4217.5	4197.8	4192.3	4189.2	4193.1	4197.1	4193.1	4189.2	4192.3	4197.8	4217.5
22.5°	3630.1	3617.4	3603.7	3594.7	3599.9	3605.1	3599.9	3594.7	3603.7	3617.4	3630.1
25°	2827.3	2825.8	2844.6	2854.7	2838.2	2821.6	2838.2	2854.7	2844.6	2825.8	2827.3
27.5°	2320.5	2312.1	2314.2	2316.5	2319.7	2322.8	2319.7	2316.5	2314.2	2312.1	2320.5
30°	2041.2	2032.5	2033.3	2031.6	2022.1	2012.7	2022.1	2031.6	2033.3	2032.5	2041.2
32.5°	1815.4	1802.0	1797.8	1792.2	1782.8	1773.3	1782.8	1792.2	1797.8	1802.0	1815.4
35°	1504.4	1489.9	1478.1	1468.6	1466.3	1463.9	1466.3	1468.6	1478.1	1489.9	1504.4
37.5°	1221.5	1207.1	1190.4	1176.3	1170.2	1164.1	1170.2	1176.3	1190.4	1207.1	1221.5
40°	1039.5	1025.3	1004.9	987.4	978.7	970.0	978.7	987.4	1004.9	1025.3	1039.5
42.5°	862.5	848.3	827.8	809.2	796.2	783.1	796.2	809.2	827.8	848.3	862.5
45°	611.1	602.4	578.8	543.6	473.6	403.6	473.6	543.6	578.8	602.4	611.1
47.5°	390.9	378.9	316.7	255.6	197.4	139.1	197.4	255.6	316.7	378.9	390.9
50°	280.5	269.1	191.2	126.1	99.3	72.6	99.3	126.1	191.2	269.1	280.5
52.5°	200.2	195.1	127.9	74.0	59.8	45.7	59.8	74.0	127.9	195.1	200.2
55°	95.4	93.8	58.4	30.5	25.0	19.5	25.0	30.5	58.4	93.8	95.4
57.5°	36.5	35.8	23.2	13.1	10.3	7.4	10.3	13.1	23.2	35.8	36.5
60°	16.7	16.3	10.0	4.9	3.3	1.8	3.3	4.9	10.0	16.3	16.7
62.5°	8.1	8.0	4.8	2.2	1.3	0.4	1.3	2.2	4.8	8.0	8.1
65°	1.4	1.4	0.6	0.0	0.0	0.0	0.0	0.6	1.4	1.4	1.4
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	4.9	6.3	7.8	8.7	9.5	9.1	9.5	8.7	7.8	6.3	4.9
90°	24.3	31.7	39.1	43.3	47.6	45.4	47.6	43.3	39.1	31.7	24.3
92.5°	48.8	61.3	70.4	78.0	81.4	80.9	81.4	78.0	70.4	61.3	48.8
95°	98.3	113.1	127.9	138.4	144.8	142.7	144.8	138.4	127.9	113.1	98.3
97.5°	151.5	171.4	187.9	197.8	204.1	208.4	204.1	197.8	187.9	171.4	151.5
100°	187.0	206.1	225.1	236.7	247.3	251.5	247.3	236.7	225.1	206.1	187.0
102.5°	215.8	240.7	261.4	273.9	282.8	287.0	282.8	273.9	261.4	240.7	215.8
105°	263.1	289.5	311.7	327.6	337.1	340.2	337.1	327.6	311.7	289.5	263.1
107.5°	310.5	337.7	358.2	375.8	387.4	394.1	387.4	375.8	358.2	337.7	310.5
110°	347.6	369.8	392.0	407.9	419.5	423.7	419.5	407.9	392.0	369.8	347.6



TEST NUMBER: P1427614

CATALOG NUMBER: SQ2W-BBN-K-075U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	378.9	403.7	425.8	441.7	455.0	460.9	455.0	441.7	425.8	403.7	378.9
115°	422.7	455.4	475.5	490.3	499.8	505.1	499.8	490.3	475.5	455.4	422.7
117.5°	459.0	493.3	515.2	526.6	531.1	534.9	531.1	526.6	515.2	493.3	459.0
120°	481.8	513.5	538.9	553.7	559.0	561.1	559.0	553.7	538.9	513.5	481.8
122.5°	503.0	533.0	557.5	575.7	584.3	586.5	584.3	575.7	557.5	533.0	503.0
125°	532.6	561.1	586.5	604.4	613.9	619.2	613.9	604.4	586.5	561.1	532.6
127.5°	558.3	589.2	612.4	628.7	638.0	642.2	638.0	628.7	612.4	589.2	558.3
130°	572.7	604.4	627.7	645.6	654.1	658.3	654.1	645.6	627.7	604.4	572.7
132.5°	583.7	617.1	641.2	657.5	666.8	671.0	666.8	657.5	641.2	617.1	583.7
135°	597.0	631.9	657.3	673.1	681.6	685.8	681.6	673.1	657.3	631.9	597.0
137.5°	608.6	640.3	666.8	683.5	691.1	693.8	691.1	683.5	666.8	640.3	608.6
140°	617.1	644.6	671.0	686.8	695.3	696.3	695.3	686.8	671.0	644.6	617.1
142.5°	628.1	649.6	672.7	688.5	697.0	698.9	697.0	688.5	672.7	649.6	628.1
145°	647.7	660.4	676.3	691.1	698.5	700.6	698.5	691.1	676.3	660.4	647.7
147.5°	672.5	676.5	684.7	694.4	701.6	703.1	701.6	694.4	684.7	676.5	672.5
150°	691.1	690.0	693.2	699.5	705.9	704.8	705.9	699.5	693.2	690.0	691.1
152.5°	712.2	706.1	705.9	708.8	711.8	711.6	711.8	708.8	705.9	706.1	712.2
155°	748.1	736.5	730.2	728.0	728.0	727.0	728.0	728.0	730.2	736.5	748.1
157.5°	787.6	771.4	761.9	756.8	755.3	753.0	755.3	756.8	761.9	771.4	787.6
160°	814.7	796.7	787.2	778.8	775.6	772.4	775.6	778.8	787.2	796.7	814.7
162.5°	840.1	822.9	812.6	805.0	801.8	796.9	801.8	805.0	812.6	822.9	840.1
165°	881.3	863.3	851.7	845.3	841.1	836.9	841.1	845.3	851.7	863.3	881.3
167.5°	922.5	902.8	895.2	888.0	884.0	876.4	884.0	888.0	895.2	902.8	922.5
170°	947.8	929.9	925.6	919.3	911.9	903.5	911.9	919.3	925.6	929.9	947.8
172.5°	969.8	957.8	953.5	947.2	944.9	938.1	944.9	947.2	953.5	957.8	969.8
175°	1001.7	992.2	992.2	991.2	988.0	981.7	988.0	991.2	992.2	992.2	1001.7
177.5°	1028.4	1023.3	1026.7	1026.7	1025.8	1019.9	1025.8	1026.7	1026.7	1023.3	1028.4
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P1427614

CATALOG NUMBER: SQ2W-BBN-K-075U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	9822.6	9822.6	9822.6	9822.6
2.5°	9751.8	9784.2	9800.6	9817.0
5°	9384.8	9412.3	9435.2	9458.0
7.5°	8661.5	8680.4	8673.0	8665.6
10°	8034.2	8035.2	8029.6	8024.1
12.5°	7299.2	7324.4	7302.5	7280.7
15°	6129.5	6179.6	6144.2	6108.8
17.5°	4971.7	5002.7	5006.3	5009.9
20°	4251.3	4278.1	4283.6	4289.1
22.5°	3641.9	3653.1	3662.4	3671.7
25°	2849.4	2873.4	2903.3	2933.2
27.5°	2339.2	2353.4	2353.8	2354.3
30°	2059.3	2074.2	2079.7	2085.3
32.5°	1837.9	1853.8	1849.9	1845.9
35°	1521.7	1534.7	1534.7	1534.7
37.5°	1233.8	1243.4	1244.8	1246.2
40°	1047.3	1054.2	1058.2	1062.1
42.5°	870.3	873.6	863.1	852.5
45°	604.8	589.1	545.0	501.0
47.5°	352.9	312.2	263.7	215.3
50°	225.4	174.7	136.9	99.1
52.5°	143.3	95.8	76.9	58.1
55°	63.1	37.4	31.1	24.8
57.5°	25.4	16.1	12.7	9.2
60°	11.2	6.7	5.1	3.5
62.5°	5.1	2.6	1.7	0.7
65°	0.6	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0
87.5°	3.8	2.3	1.5	0.6
90°	19.0	11.6	7.4	3.2
92.5°	41.0	28.5	20.1	11.6
95°	82.4	65.5	46.5	32.8
97.5°	131.2	104.0	85.2	62.6
100°	157.4	131.0	113.1	88.8
102.5°	186.2	164.0	139.3	115.0
105°	237.8	210.3	181.7	154.3
107.5°	285.5	255.3	221.1	196.3
110°	315.9	283.2	247.3	225.1



TEST NUMBER: P1427614

CATALOG NUMBER: SQ2W-BBN-K-075U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	345.5	311.9	275.2	253.0
115°	385.7	348.7	314.9	295.9
117.5°	424.4	386.3	350.6	335.6
120°	448.0	410.0	375.1	363.5
122.5°	467.5	430.3	397.9	393.1
125°	496.6	458.6	431.1	437.5
127.5°	520.3	485.4	468.1	482.3
130°	534.7	504.0	493.5	513.5
132.5°	547.4	523.5	518.8	546.5
135°	566.4	552.6	556.9	594.9
137.5°	589.0	583.7	597.9	645.8
140°	603.4	606.5	626.6	680.5
142.5°	622.8	630.2	656.2	713.5
145°	653.0	668.9	702.7	759.7
147.5°	687.3	707.8	749.6	808.1
150°	710.1	736.5	780.9	836.9
152.5°	736.3	763.6	807.9	864.8
155°	776.7	807.3	853.8	902.4
157.5°	817.9	849.1	893.5	936.0
160°	843.2	877.0	917.2	956.3
162.5°	872.0	903.2	938.3	973.2
165°	914.0	939.4	967.9	997.5
167.5°	949.3	970.5	992.9	1015.9
170°	972.1	989.0	1008.1	1026.0
172.5°	991.6	1005.1	1019.1	1034.5
175°	1017.6	1025.0	1033.4	1042.9
177.5°	1037.7	1040.2	1042.7	1047.0
180°	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P1427614
 CATALOG NUMBER: SQ2W-BBN-K-075U-125D-L940-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00