

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427734

Luminaire Tested: SQ2W-F-K-075U-075D-L940-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1427734
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-20)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-F-K-075U-075D-L940-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - FROSTED CONTINUOUS ROLL LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6202.9 lumens
Efficiency: N/A
Efficacy: 123.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 50.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1427734

CATALOG NUMBER: SQ2W-F-K-075U-075D-L940-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1427734

CATALOG NUMBER: SQ2W-F-K-075U-075D-L940-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	93	89	86	90	86	83	80	73	71	68	61	59	58	50	49	48	42
2	89	81	75	70	82	75	70	65	64	60	56	53	50	48	44	42	40	35
3	81	71	64	58	74	66	60	54	56	51	47	47	43	40	39	36	34	30
4	74	63	55	49	68	58	51	46	50	44	40	42	38	34	34	31	29	25
5	68	56	48	42	62	52	45	39	45	39	34	37	33	30	31	28	25	22
6	62	50	42	36	57	47	39	34	40	34	30	34	29	26	28	25	22	19
7	58	45	37	32	53	42	35	30	36	31	26	31	26	23	26	22	19	17
8	54	41	33	28	49	38	31	26	33	27	23	28	24	20	23	20	17	15
9	50	37	30	25	46	35	28	23	30	25	21	26	21	18	22	18	16	14
10	47	34	27	22	43	32	25	21	28	22	19	24	20	16	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	18038	18038	18038	18038
5°	17927	18131	17927	18131
10°	17864	18070	17864	18070
15°	17766	17989	17766	17989
20°	17654	17829	17654	17829
25°	17464	17617	17464	17617
30°	17279	17396	17279	17396
35°	17057	17166	17057	17166
40°	16863	16914	16863	16914
45°	16616	16616	16616	16616
50°	16284	16322	16284	16322
55°	15901	15924	15901	15924
60°	15471	15471	15471	15471
65°	14968	14907	14968	14907
70°	14261	14115	14261	14115
75°	13300	13007	13300	13007
80°	11855	11269	11855	11269
85°	9466	8021	9466	8021

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 16728 cd/sqm



TEST NUMBER: P1427734

CATALOG NUMBER: SQ2W-F-K-075U-075D-L940-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.7	1.7
10°-20°	302.0	4.9
20°-30°	454.6	7.3
30°-40°	543.7	8.8
40°-50°	561.4	9.1
50°-60°	506.4	8.2
60°-70°	387.9	6.3
70°-80°	224.2	3.6
80°-90°	62.6	1.0
90°-100°	83.3	1.3
100°-110°	242.8	3.9
110°-120°	396.2	6.4
120°-130°	502.8	8.1
130°-140°	538.0	8.7
140°-150°	502.4	8.1
150°-160°	413.4	6.7
160°-170°	277.2	4.5
170°-180°	98.4	1.6
0°-30°	862.4	13.9
0°-40°	1406.0	22.7
0°-60°	2473.8	39.9
0°-90°	3148.4	50.8
90°-120°	722.3	11.6
90°-150°	2265.4	36.5
90°-180°	3054.0	49.2
0°-180°	6202.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1117	1117	1117	1117	1117	
5°	1106	1119	1106	1119	1106	105
15°	1063	1076	1063	1076	1063	300
25°	980	989	980	989	980	452
35°	865	871	865	871	865	542
45°	728	728	728	728	728	561
55°	565	566	565	566	565	505
65°	392	390	392	390	392	387
75°	213	208	213	208	213	226
85°	51	43	51	43	51	60
90°	3	23	3	45	3	5
95°	33	24	33	143	33	40
105°	154	247	154	340	154	164
115°	296	410	296	505	296	292
125°	438	650	438	619	438	391
135°	595	851	595	686	595	460
145°	760	981	760	701	760	475
155°	902	1065	902	727	902	415
165°	998	1111	998	837	998	281
175°	1043	1087	1043	982	1043	99
180°	1046	1046	1046	1046	1046	



TEST NUMBER: P1427734

CATALOG NUMBER: SQ2W-F-K-075U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1117.2	1117.2	1117.2	1117.2	1117.2	1117.2	1117.2	1117.2	1117.2	1117.2	1117.2
2.5°	1111.5	1116.8	1122.1	1119.9	1115.1	1113.3	1114.4	1115.4	1116.0	1116.5	1116.0
5°	1106.1	1113.1	1120.1	1117.7	1112.1	1109.6	1110.3	1111.7	1115.2	1118.7	1115.2
7.5°	1097.2	1104.2	1111.2	1108.9	1103.6	1101.4	1102.2	1103.7	1107.4	1111.0	1107.4
10°	1089.6	1096.6	1103.6	1101.2	1095.6	1093.5	1094.9	1096.6	1099.4	1102.2	1099.4
12.5°	1080.2	1087.2	1094.2	1092.1	1087.1	1085.0	1085.8	1087.2	1090.3	1093.4	1090.3
15°	1062.9	1069.9	1076.9	1074.9	1070.0	1068.1	1069.2	1070.7	1073.4	1076.2	1073.4
17.5°	1041.9	1048.5	1055.1	1053.3	1048.8	1047.1	1048.3	1049.8	1052.2	1054.7	1052.2
20°	1027.5	1033.8	1040.1	1038.2	1033.7	1031.6	1031.9	1032.8	1035.2	1037.7	1035.2
22.5°	1009.8	1016.1	1022.4	1020.8	1016.5	1014.0	1013.3	1013.4	1016.4	1019.4	1016.4
25°	980.3	986.6	992.9	991.5	987.7	985.2	984.2	984.0	986.5	988.9	986.5
27.5°	949.4	954.7	959.9	958.8	955.6	953.6	952.9	952.9	954.6	956.3	954.6
30°	926.8	932.0	937.3	935.9	932.4	930.4	929.7	929.6	931.3	933.1	931.3
32.5°	902.9	907.8	912.8	911.0	906.9	904.8	904.7	905.1	907.1	909.1	907.1
35°	865.4	869.6	873.8	872.0	868.1	866.4	866.7	867.4	869.2	870.9	869.2
37.5°	827.8	831.0	834.2	832.4	828.8	827.0	826.9	827.2	828.7	830.2	828.7
40°	800.1	803.6	807.1	805.1	801.2	799.1	798.8	799.0	800.7	802.5	800.7
42.5°	771.8	774.4	777.1	775.3	772.0	770.5	770.7	771.1	772.0	772.9	772.0
45°	727.7	730.2	732.6	730.9	727.7	726.2	726.2	726.3	727.0	727.7	727.0
47.5°	681.6	683.5	685.4	684.0	681.6	680.2	679.7	679.7	680.8	681.9	680.8
50°	648.3	650.7	653.2	651.9	649.5	647.9	647.2	647.0	648.4	649.8	648.4
52.5°	615.5	618.3	621.0	619.8	617.4	615.7	614.7	614.2	615.4	616.5	615.4
55°	564.9	568.0	571.2	570.4	568.3	566.5	565.1	564.3	565.0	565.7	565.0
57.5°	513.1	516.2	519.3	518.7	516.8	515.1	513.4	512.4	513.4	514.4	513.4
60°	479.1	481.9	484.7	483.8	481.7	480.0	478.6	477.7	478.4	479.1	478.4
62.5°	444.5	447.3	450.1	449.0	446.6	444.7	443.3	442.5	443.2	443.9	443.2
65°	391.8	394.2	396.7	395.7	393.6	391.9	390.5	389.5	389.9	390.2	389.9
67.5°	338.6	340.7	342.8	341.8	339.8	337.8	335.7	334.3	334.9	335.5	334.9
70°	302.1	304.2	306.3	305.5	303.8	302.0	300.3	299.0	299.0	299.0	299.0
72.5°	266.9	268.7	270.5	269.4	267.4	265.7	264.2	263.1	263.1	263.1	263.1
75°	213.2	214.3	215.3	214.8	213.7	212.3	210.6	209.2	208.8	208.5	208.8
77.5°	161.4	161.4	161.4	160.4	159.1	157.8	156.5	155.4	154.9	154.5	154.9
80°	127.5	127.5	127.5	126.7	125.6	124.6	123.5	122.6	121.9	121.2	121.9
82.5°	96.0	95.4	94.9	93.9	92.9	91.6	89.9	88.9	89.6	90.3	89.6
85°	51.1	50.4	49.7	48.8	47.7	46.5	45.1	44.0	43.6	43.3	43.6
87.5°	16.4	16.7	17.2	17.2	17.0	16.3	15.1	14.4	14.4	14.1	14.4
90°	3.2	7.4	12.7	16.9	20.1	21.1	21.1	22.2	23.2	23.2	23.2
92.5°	11.6	18.4	18.6	18.6	22.6	24.5	26.2	26.4	27.5	27.5	27.5
95°	32.8	35.9	53.9	52.8	35.9	28.5	24.3	24.3	24.3	24.3	24.3
97.5°	62.6	67.2	70.2	94.0	99.3	95.9	78.2	65.7	58.8	55.6	58.8
100°	88.8	90.9	97.2	98.3	124.7	150.0	137.4	121.5	116.2	113.1	116.2
102.5°	115.0	116.2	126.0	130.4	136.5	150.9	194.9	190.0	186.4	185.8	186.4
105°	154.3	155.3	173.3	181.7	186.0	186.0	184.9	206.1	239.9	247.3	239.9
107.5°	196.3	201.2	222.3	244.9	249.8	251.1	245.6	242.4	241.1	242.0	241.1
110°	225.1	232.5	257.8	286.4	293.8	295.9	293.8	290.6	288.5	288.5	288.5



TEST NUMBER: P1427734

CATALOG NUMBER: SQ2W-F-K-075U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	253.0	263.7	292.5	325.2	337.7	344.1	339.4	337.1	335.0	336.7	335.0
115°	295.9	311.7	349.8	383.6	408.9	412.1	411.0	411.0	410.0	410.0	410.0
117.5°	335.6	361.0	403.7	443.0	472.3	480.8	485.0	483.7	482.5	484.6	482.5
120°	363.5	393.1	441.7	486.1	514.6	527.3	531.5	529.4	531.5	529.4	531.5
122.5°	393.1	429.4	477.2	523.3	556.9	571.2	576.3	576.7	577.2	575.9	577.2
125°	437.5	481.8	537.8	585.4	620.3	637.2	641.4	642.5	644.6	649.9	644.6
127.5°	482.3	532.6	594.1	639.9	675.6	696.1	702.7	705.0	709.5	711.8	709.5
130°	513.5	570.6	632.9	676.3	711.1	733.3	745.0	748.1	753.4	752.4	753.4
132.5°	546.5	606.1	669.3	714.3	746.6	770.5	780.5	789.5	791.5	792.9	791.5
135°	594.9	659.4	722.8	767.1	797.8	821.0	833.7	842.2	847.5	850.6	847.5
137.5°	645.8	713.9	774.8	814.3	845.1	865.2	879.6	888.5	893.9	896.5	893.9
140°	680.5	746.0	805.2	846.4	873.9	893.9	906.6	917.2	923.5	923.5	923.5
142.5°	713.5	778.1	835.6	876.8	900.9	919.3	932.8	940.9	948.0	948.0	948.0
145°	759.7	824.2	877.0	918.3	938.3	955.2	970.0	976.4	980.6	980.6	980.6
147.5°	808.1	865.2	913.4	952.9	969.8	989.7	1001.3	1006.4	1011.7	1009.3	1011.7
150°	836.9	889.7	936.2	973.2	990.1	1009.1	1020.7	1025.0	1030.3	1027.1	1030.3
152.5°	864.8	915.1	957.3	991.8	1006.2	1025.2	1038.5	1042.7	1046.3	1044.0	1046.3
155°	902.4	946.8	985.9	1017.6	1030.3	1048.2	1060.9	1066.2	1070.4	1065.1	1070.4
157.5°	936.0	974.3	1008.3	1037.4	1051.0	1066.4	1078.2	1084.8	1089.0	1086.7	1089.0
160°	956.3	991.2	1021.8	1049.3	1062.0	1075.7	1088.4	1095.8	1100.0	1096.8	1100.0
162.5°	973.2	1004.7	1033.6	1058.6	1069.6	1081.6	1096.8	1103.4	1107.6	1103.6	1107.6
165°	997.5	1022.9	1048.2	1069.4	1078.9	1088.4	1104.2	1111.6	1114.8	1110.6	1114.8
167.5°	1015.9	1035.3	1055.8	1074.0	1081.0	1090.3	1106.1	1112.3	1116.3	1111.0	1116.3
170°	1026.0	1042.9	1060.9	1075.7	1081.0	1089.4	1105.3	1110.6	1113.7	1108.5	1113.7
172.5°	1034.5	1047.2	1061.7	1074.9	1077.6	1084.4	1099.4	1104.6	1107.0	1102.5	1107.0
175°	1042.9	1050.3	1060.9	1069.4	1068.3	1072.5	1085.2	1089.4	1093.7	1087.3	1093.7
177.5°	1047.0	1050.3	1053.7	1058.8	1055.4	1055.4	1064.7	1067.2	1068.1	1064.7	1068.1
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P1427734

CATALOG NUMBER: SQ2W-F-K-075U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1117.2	1117.2	1117.2	1117.2	1117.2	1117.2	1117.2	1117.2	1117.2	1117.2	1117.2
2.5°	1115.4	1114.4	1113.3	1115.1	1119.9	1122.1	1116.8	1111.5	1116.8	1122.1	1119.9
5°	1111.7	1110.3	1109.6	1112.1	1117.7	1120.1	1113.1	1106.1	1113.1	1120.1	1117.7
7.5°	1103.7	1102.2	1101.4	1103.6	1108.9	1111.2	1104.2	1097.2	1104.2	1111.2	1108.9
10°	1096.6	1094.9	1093.5	1095.6	1101.2	1103.6	1096.6	1089.6	1096.6	1103.6	1101.2
12.5°	1087.2	1085.8	1085.0	1087.1	1092.1	1094.2	1087.2	1080.2	1087.2	1094.2	1092.1
15°	1070.7	1069.2	1068.1	1070.0	1074.9	1076.9	1069.9	1062.9	1069.9	1076.9	1074.9
17.5°	1049.8	1048.3	1047.1	1048.8	1053.3	1055.1	1048.5	1041.9	1048.5	1055.1	1053.3
20°	1032.8	1031.9	1031.6	1033.7	1038.2	1040.1	1033.8	1027.5	1033.8	1040.1	1038.2
22.5°	1013.4	1013.3	1014.0	1016.5	1020.8	1022.4	1016.1	1009.8	1016.1	1022.4	1020.8
25°	984.0	984.2	985.2	987.7	991.5	992.9	986.6	980.3	986.6	992.9	991.5
27.5°	952.9	952.9	953.6	955.6	958.8	959.9	954.7	949.4	954.7	959.9	958.8
30°	929.6	929.7	930.4	932.4	935.9	937.3	932.0	926.8	932.0	937.3	935.9
32.5°	905.1	904.7	904.8	906.9	911.0	912.8	907.8	902.9	907.8	912.8	911.0
35°	867.4	866.7	866.4	868.1	872.0	873.8	869.6	865.4	869.6	873.8	872.0
37.5°	827.2	826.9	827.0	828.8	832.4	834.2	831.0	827.8	831.0	834.2	832.4
40°	799.0	798.8	799.1	801.2	805.1	807.1	803.6	800.1	803.6	807.1	805.1
42.5°	771.1	770.7	770.5	772.0	775.3	777.1	774.4	771.8	774.4	777.1	775.3
45°	726.3	726.2	726.2	727.7	730.9	732.6	730.2	727.7	730.2	732.6	730.9
47.5°	679.7	679.7	680.2	681.6	684.0	685.4	683.5	681.6	683.5	685.4	684.0
50°	647.0	647.2	647.9	649.5	651.9	653.2	650.7	648.3	650.7	653.2	651.9
52.5°	614.2	614.7	615.7	617.4	619.8	621.0	618.3	615.5	618.3	621.0	619.8
55°	564.3	565.1	566.5	568.3	570.4	571.2	568.0	564.9	568.0	571.2	570.4
57.5°	512.4	513.4	515.1	516.8	518.7	519.3	516.2	513.1	516.2	519.3	518.7
60°	477.7	478.6	480.0	481.7	483.8	484.7	481.9	479.1	481.9	484.7	483.8
62.5°	442.5	443.3	444.7	446.6	449.0	450.1	447.3	444.5	447.3	450.1	449.0
65°	389.5	390.5	391.9	393.6	395.7	396.7	394.2	391.8	394.2	396.7	395.7
67.5°	334.3	335.7	337.8	339.8	341.8	342.8	340.7	338.6	340.7	342.8	341.8
70°	299.0	300.3	302.0	303.8	305.5	306.3	304.2	302.1	304.2	306.3	305.5
72.5°	263.1	264.2	265.7	267.4	269.4	270.5	268.7	266.9	268.7	270.5	269.4
75°	209.2	210.6	212.3	213.7	214.8	215.3	214.3	213.2	214.3	215.3	214.8
77.5°	155.4	156.5	157.8	159.1	160.4	161.4	161.4	161.4	161.4	161.4	160.4
80°	122.6	123.5	124.6	125.6	126.7	127.5	127.5	127.5	127.5	127.5	126.7
82.5°	88.9	89.9	91.6	92.9	93.9	94.9	95.4	96.0	95.4	94.9	93.9
85°	44.0	45.1	46.5	47.7	48.8	49.7	50.4	51.1	50.4	49.7	48.8
87.5°	14.4	15.1	16.3	17.0	17.2	17.2	16.7	16.4	16.7	16.9	17.7
90°	22.2	21.1	21.1	20.1	16.9	12.7	7.4	3.2	7.4	11.6	19.0
92.5°	26.4	26.2	24.5	22.6	18.6	18.6	18.4	11.6	20.1	28.5	41.0
95°	24.3	24.3	28.5	35.9	52.8	53.9	35.9	32.8	46.5	65.5	82.4
97.5°	65.7	78.2	95.9	99.3	94.0	70.2	67.2	62.6	85.2	104.0	131.2
100°	121.5	137.4	150.0	124.7	98.3	97.2	90.9	88.8	113.1	131.0	157.4
102.5°	190.0	194.9	150.9	136.5	130.4	126.0	116.2	115.0	139.3	164.0	186.2
105°	206.1	184.9	186.0	186.0	181.7	173.3	155.3	154.3	181.7	210.3	237.8
107.5°	242.4	245.6	251.1	249.8	244.9	222.3	201.2	196.3	221.1	255.3	285.5
110°	290.6	293.8	295.9	293.8	286.4	257.8	232.5	225.1	247.3	283.2	315.9



TEST NUMBER: P1427734

CATALOG NUMBER: SQ2W-F-K-075U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	337.1	339.4	344.1	337.7	325.2	292.5	263.7	253.0	275.2	311.9	345.5
115°	411.0	411.0	412.1	408.9	383.6	349.8	311.7	295.9	314.9	348.7	385.7
117.5°	483.7	485.0	480.8	472.3	443.0	403.7	361.0	335.6	350.6	386.3	424.4
120°	529.4	531.5	527.3	514.6	486.1	441.7	393.1	363.5	375.1	410.0	448.0
122.5°	576.7	576.3	571.2	556.9	523.3	477.2	429.4	393.1	397.9	430.3	467.5
125°	642.5	641.4	637.2	620.3	585.4	537.8	481.8	437.5	431.1	458.6	496.6
127.5°	705.0	702.7	696.1	675.6	639.9	594.1	532.6	482.3	468.1	485.4	520.3
130°	748.1	745.0	733.3	711.1	676.3	632.9	570.6	513.5	493.5	504.0	534.7
132.5°	789.5	780.5	770.5	746.6	714.3	669.3	606.1	546.5	518.8	523.5	547.4
135°	842.2	833.7	821.0	797.8	767.1	722.8	659.4	594.9	556.9	552.6	566.4
137.5°	888.5	879.6	865.2	845.1	814.3	774.8	713.9	645.8	597.9	583.7	589.0
140°	917.2	906.6	893.9	873.9	846.4	805.2	746.0	680.5	626.6	606.5	603.4
142.5°	940.9	932.8	919.3	900.9	876.8	835.6	778.1	713.5	656.2	630.2	622.8
145°	976.4	970.0	955.2	938.3	918.3	877.0	824.2	759.7	702.7	668.9	653.0
147.5°	1006.4	1001.3	989.7	969.8	952.9	913.4	865.2	808.1	749.6	707.8	687.3
150°	1025.0	1020.7	1009.1	990.1	973.2	936.2	889.7	836.9	780.9	736.5	710.1
152.5°	1042.7	1038.5	1025.2	1006.2	991.8	957.3	915.1	864.8	807.9	763.6	736.3
155°	1066.2	1060.9	1048.2	1030.3	1017.6	985.9	946.8	902.4	853.8	807.3	776.7
157.5°	1084.8	1078.2	1066.4	1051.0	1037.4	1008.3	974.3	936.0	893.5	849.1	817.9
160°	1095.8	1088.4	1075.7	1062.0	1049.3	1021.8	991.2	956.3	917.2	877.0	843.2
162.5°	1103.4	1096.8	1081.6	1069.6	1058.6	1033.6	1004.7	973.2	938.3	903.2	872.0
165°	1111.6	1104.2	1088.4	1078.9	1069.4	1048.2	1022.9	997.5	967.9	939.4	914.0
167.5°	1112.3	1106.1	1090.3	1081.0	1074.0	1055.8	1035.3	1015.9	992.9	970.5	949.3
170°	1110.6	1105.3	1089.4	1081.0	1075.7	1060.9	1042.9	1026.0	1008.1	989.0	972.1
172.5°	1104.6	1099.4	1084.4	1077.6	1074.9	1061.7	1047.2	1034.5	1019.1	1005.1	991.6
175°	1089.4	1085.2	1072.5	1068.3	1069.4	1060.9	1050.3	1042.9	1033.4	1025.0	1017.6
177.5°	1067.2	1064.7	1055.4	1055.4	1058.8	1053.7	1050.3	1047.0	1042.7	1040.2	1037.7
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P1427734

CATALOG NUMBER: SQ2W-F-K-075U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1117.2	1117.2	1117.2	1117.2	1117.2	1117.2	1117.2	1117.2	1117.2	1117.2	1117.2
2.5°	1115.1	1113.3	1114.4	1115.4	1116.0	1116.5	1116.0	1115.4	1114.4	1113.3	1115.1
5°	1112.1	1109.6	1110.3	1111.7	1115.2	1118.7	1115.2	1111.7	1110.3	1109.6	1112.1
7.5°	1103.6	1101.4	1102.2	1103.7	1107.4	1111.0	1107.4	1103.7	1102.2	1101.4	1103.6
10°	1095.6	1093.5	1094.9	1096.6	1099.4	1102.2	1099.4	1096.6	1094.9	1093.5	1095.6
12.5°	1087.1	1085.0	1085.8	1087.2	1090.3	1093.4	1090.3	1087.2	1085.8	1085.0	1087.1
15°	1070.0	1068.1	1069.2	1070.7	1073.4	1076.2	1073.4	1070.7	1069.2	1068.1	1070.0
17.5°	1048.8	1047.1	1048.3	1049.8	1052.2	1054.7	1052.2	1049.8	1048.3	1047.1	1048.8
20°	1033.7	1031.6	1031.9	1032.8	1035.2	1037.7	1035.2	1032.8	1031.9	1031.6	1033.7
22.5°	1016.5	1014.0	1013.3	1013.4	1016.4	1019.4	1016.4	1013.4	1013.3	1014.0	1016.5
25°	987.7	985.2	984.2	984.0	986.5	988.9	986.5	984.0	984.2	985.2	987.7
27.5°	955.6	953.6	952.9	952.9	954.6	956.3	954.6	952.9	952.9	953.6	955.6
30°	932.4	930.4	929.7	929.6	931.3	933.1	931.3	929.6	929.7	930.4	932.4
32.5°	906.9	904.8	904.7	905.1	907.1	909.1	907.1	905.1	904.7	904.8	906.9
35°	868.1	866.4	866.7	867.4	869.2	870.9	869.2	867.4	866.7	866.4	868.1
37.5°	828.8	827.0	826.9	827.2	828.7	830.2	828.7	827.2	826.9	827.0	828.8
40°	801.2	799.1	798.8	799.0	800.7	802.5	800.7	799.0	798.8	799.1	801.2
42.5°	772.0	770.5	770.7	771.1	772.0	772.9	772.0	771.1	770.7	770.5	772.0
45°	727.7	726.2	726.2	726.3	727.0	727.7	727.0	726.3	726.2	726.2	727.7
47.5°	681.6	680.2	679.7	679.7	680.8	681.9	680.8	679.7	679.7	680.2	681.6
50°	649.5	647.9	647.2	647.0	648.4	649.8	648.4	647.0	647.2	647.9	649.5
52.5°	617.4	615.7	614.7	614.2	615.4	616.5	615.4	614.2	614.7	615.7	617.4
55°	568.3	566.5	565.1	564.3	565.0	565.7	565.0	564.3	565.1	566.5	568.3
57.5°	516.8	515.1	513.4	512.4	513.4	514.4	513.4	512.4	513.4	515.1	516.8
60°	481.7	480.0	478.6	477.7	478.4	479.1	478.4	477.7	478.6	480.0	481.7
62.5°	446.6	444.7	443.3	442.5	443.2	443.9	443.2	442.5	443.3	444.7	446.6
65°	393.6	391.9	390.5	389.5	389.9	390.2	389.9	389.5	390.5	391.9	393.6
67.5°	339.8	337.8	335.7	334.3	334.9	335.5	334.9	334.3	335.7	337.8	339.8
70°	303.8	302.0	300.3	299.0	299.0	299.0	299.0	299.0	300.3	302.0	303.8
72.5°	267.4	265.7	264.2	263.1	263.1	263.1	263.1	264.2	265.7	267.4	267.4
75°	213.7	212.3	210.6	209.2	208.8	208.5	208.8	209.2	210.6	212.3	213.7
77.5°	159.1	157.8	156.5	155.4	154.9	154.5	154.9	155.4	156.5	157.8	159.1
80°	125.6	124.6	123.5	122.6	121.9	121.2	121.9	122.6	123.5	124.6	125.6
82.5°	92.9	91.6	89.9	88.9	89.6	90.3	89.6	88.9	89.9	91.6	92.9
85°	47.7	46.5	45.1	44.0	43.6	43.3	43.6	44.0	45.1	46.5	47.7
87.5°	17.9	18.4	18.7	18.7	19.2	18.5	19.2	18.7	18.7	18.4	17.9
90°	24.3	31.7	39.1	43.3	47.6	45.4	47.6	43.3	39.1	31.7	24.3
92.5°	48.8	61.3	70.4	78.0	81.4	80.9	81.4	78.0	70.4	61.3	48.8
95°	98.3	113.1	127.9	138.4	144.8	142.7	144.8	138.4	127.9	113.1	98.3
97.5°	151.5	171.4	187.9	197.8	204.1	208.4	204.1	197.8	187.9	171.4	151.5
100°	187.0	206.1	225.1	236.7	247.3	251.5	247.3	236.7	225.1	206.1	187.0
102.5°	215.8	240.7	261.4	273.9	282.8	287.0	282.8	273.9	261.4	240.7	215.8
105°	263.1	289.5	311.7	327.6	337.1	340.2	337.1	327.6	311.7	289.5	263.1
107.5°	310.5	337.7	358.2	375.8	387.4	394.1	387.4	375.8	358.2	337.7	310.5
110°	347.6	369.8	392.0	407.9	419.5	423.7	419.5	407.9	392.0	369.8	347.6



TEST NUMBER: P1427734

CATALOG NUMBER: SQ2W-F-K-075U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	378.9	403.7	425.8	441.7	455.0	460.9	455.0	441.7	425.8	403.7	378.9
115°	422.7	455.4	475.5	490.3	499.8	505.1	499.8	490.3	475.5	455.4	422.7
117.5°	459.0	493.3	515.2	526.6	531.1	534.9	531.1	526.6	515.2	493.3	459.0
120°	481.8	513.5	538.9	553.7	559.0	561.1	559.0	553.7	538.9	513.5	481.8
122.5°	503.0	533.0	557.5	575.7	584.3	586.5	584.3	575.7	557.5	533.0	503.0
125°	532.6	561.1	586.5	604.4	613.9	619.2	613.9	604.4	586.5	561.1	532.6
127.5°	558.3	589.2	612.4	628.7	638.0	642.2	638.0	628.7	612.4	589.2	558.3
130°	572.7	604.4	627.7	645.6	654.1	658.3	654.1	645.6	627.7	604.4	572.7
132.5°	583.7	617.1	641.2	657.5	666.8	671.0	666.8	657.5	641.2	617.1	583.7
135°	597.0	631.9	657.3	673.1	681.6	685.8	681.6	673.1	657.3	631.9	597.0
137.5°	608.6	640.3	666.8	683.5	691.1	693.8	691.1	683.5	666.8	640.3	608.6
140°	617.1	644.6	671.0	686.8	695.3	696.3	695.3	686.8	671.0	644.6	617.1
142.5°	628.1	649.6	672.7	688.5	697.0	698.9	697.0	688.5	672.7	649.6	628.1
145°	647.7	660.4	676.3	691.1	698.5	700.6	698.5	691.1	676.3	660.4	647.7
147.5°	672.5	676.5	684.7	694.4	701.6	703.1	701.6	694.4	684.7	676.5	672.5
150°	691.1	690.0	693.2	699.5	705.9	704.8	705.9	699.5	693.2	690.0	691.1
152.5°	712.2	706.1	705.9	708.8	711.8	711.6	711.8	708.8	705.9	706.1	712.2
155°	748.1	736.5	730.2	728.0	728.0	727.0	728.0	728.0	730.2	736.5	748.1
157.5°	787.6	771.4	761.9	756.8	755.3	753.0	755.3	756.8	761.9	771.4	787.6
160°	814.7	796.7	787.2	778.8	775.6	772.4	775.6	778.8	787.2	796.7	814.7
162.5°	840.1	822.9	812.6	805.0	801.8	796.9	801.8	805.0	812.6	822.9	840.1
165°	881.3	863.3	851.7	845.3	841.1	836.9	841.1	845.3	851.7	863.3	881.3
167.5°	922.5	902.8	895.2	888.0	884.0	876.4	884.0	888.0	895.2	902.8	922.5
170°	947.8	929.9	925.6	919.3	911.9	903.5	911.9	919.3	925.6	929.9	947.8
172.5°	969.8	957.8	953.5	947.2	944.9	938.1	944.9	947.2	953.5	957.8	969.8
175°	1001.7	992.2	992.2	991.2	988.0	981.7	988.0	991.2	992.2	992.2	1001.7
177.5°	1028.4	1023.3	1026.7	1026.7	1025.8	1019.9	1025.8	1026.7	1026.7	1023.3	1028.4
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P1427734

CATALOG NUMBER: SQ2W-F-K-075U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1117.2	1117.2	1117.2	1117.2
2.5°	1119.9	1122.1	1116.8	1111.5
5°	1117.7	1120.1	1113.1	1106.1
7.5°	1108.9	1111.2	1104.2	1097.2
10°	1101.2	1103.6	1096.6	1089.6
12.5°	1092.1	1094.2	1087.2	1080.2
15°	1074.9	1076.9	1069.9	1062.9
17.5°	1053.3	1055.1	1048.5	1041.9
20°	1038.2	1040.1	1033.8	1027.5
22.5°	1020.8	1022.4	1016.1	1009.8
25°	991.5	992.9	986.6	980.3
27.5°	958.8	959.9	954.7	949.4
30°	935.9	937.3	932.0	926.8
32.5°	911.0	912.8	907.8	902.9
35°	872.0	873.8	869.6	865.4
37.5°	832.4	834.2	831.0	827.8
40°	805.1	807.1	803.6	800.1
42.5°	775.3	777.1	774.4	771.8
45°	730.9	732.6	730.2	727.7
47.5°	684.0	685.4	683.5	681.6
50°	651.9	653.2	650.7	648.3
52.5°	619.8	621.0	618.3	615.5
55°	570.4	571.2	568.0	564.9
57.5°	518.7	519.3	516.2	513.1
60°	483.8	484.7	481.9	479.1
62.5°	449.0	450.1	447.3	444.5
65°	395.7	396.7	394.2	391.8
67.5°	341.8	342.8	340.7	338.6
70°	305.5	306.3	304.2	302.1
72.5°	269.4	270.5	268.7	266.9
75°	214.8	215.3	214.3	213.2
77.5°	160.4	161.4	161.4	161.4
80°	126.7	127.5	127.5	127.5
82.5°	93.9	94.9	95.4	96.0
85°	48.8	49.7	50.4	51.1
87.5°	17.7	16.9	16.7	16.4
90°	19.0	11.6	7.4	3.2
92.5°	41.0	28.5	20.1	11.6
95°	82.4	65.5	46.5	32.8
97.5°	131.2	104.0	85.2	62.6
100°	157.4	131.0	113.1	88.8
102.5°	186.2	164.0	139.3	115.0
105°	237.8	210.3	181.7	154.3
107.5°	285.5	255.3	221.1	196.3
110°	315.9	283.2	247.3	225.1

TEST NUMBER: P1427734

CATALOG NUMBER: SQ2W-F-K-075U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	345.5	311.9	275.2	253.0
115°	385.7	348.7	314.9	295.9
117.5°	424.4	386.3	350.6	335.6
120°	448.0	410.0	375.1	363.5
122.5°	467.5	430.3	397.9	393.1
125°	496.6	458.6	431.1	437.5
127.5°	520.3	485.4	468.1	482.3
130°	534.7	504.0	493.5	513.5
132.5°	547.4	523.5	518.8	546.5
135°	566.4	552.6	556.9	594.9
137.5°	589.0	583.7	597.9	645.8
140°	603.4	606.5	626.6	680.5
142.5°	622.8	630.2	656.2	713.5
145°	653.0	668.9	702.7	759.7
147.5°	687.3	707.8	749.6	808.1
150°	710.1	736.5	780.9	836.9
152.5°	736.3	763.6	807.9	864.8
155°	776.7	807.3	853.8	902.4
157.5°	817.9	849.1	893.5	936.0
160°	843.2	877.0	917.2	956.3
162.5°	872.0	903.2	938.3	973.2
165°	914.0	939.4	967.9	997.5
167.5°	949.3	970.5	992.9	1015.9
170°	972.1	989.0	1008.1	1026.0
172.5°	991.6	1005.1	1019.1	1034.5
175°	1017.6	1025.0	1033.4	1042.9
177.5°	1037.7	1040.2	1042.7	1047.0
180°	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P1427734

CATALOG NUMBER: SQ2W-F-K-075U-075D-L940-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.98	18.86	18.93	19.83	21.09	17.90	18.78	18.84	19.74	21.00
	3H	19.77	20.56	20.73	21.54	22.82	19.67	20.46	20.63	21.43	22.72
	4H	20.47	21.22	21.44	22.20	23.49	20.35	21.10	21.33	22.08	23.37
	6H	20.91	21.60	21.89	22.58	23.88	20.77	21.46	21.75	22.44	23.74
	8H	21.07	21.72	22.06	22.73	24.03	20.91	21.57	21.90	22.57	23.87
	12H	21.15	21.78	22.15	22.77	24.10	20.98	21.60	21.97	22.60	23.92
4H	2H	18.56	19.31	19.54	20.29	21.58	18.50	19.24	19.48	20.22	21.51
	3H	20.59	21.21	21.57	22.22	23.52	20.49	21.12	21.48	22.13	23.43
	4H	21.40	21.97	22.40	22.97	24.30	21.29	21.86	22.29	22.86	24.19
	6H	21.95	22.45	22.96	23.47	24.80	21.81	22.31	22.82	23.33	24.66
	8H	22.17	22.63	23.18	23.65	24.99	22.01	22.47	23.02	23.49	24.83
	12H	22.28	22.70	23.31	23.73	25.08	22.10	22.51	23.13	23.55	24.89
8H	4H	21.65	22.11	22.66	23.13	24.47	21.55	22.01	22.56	23.03	24.37
	6H	22.34	22.72	23.37	23.78	25.12	22.21	22.59	23.24	23.65	24.99
	8H	22.64	22.98	23.69	24.02	25.38	22.49	22.82	23.53	23.87	25.22
	12H	22.83	23.12	23.87	24.16	25.56	22.63	22.93	23.68	23.97	25.37
12H	4H	21.64	22.06	22.67	23.09	24.44	21.55	21.97	22.58	23.00	24.35
	6H	22.39	22.72	23.43	23.77	25.13	22.26	22.60	23.30	23.64	25.00
	8H	22.72	23.02	23.77	24.06	25.46	22.57	22.87	23.62	23.91	25.31