

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427746

Luminaire Tested: SQ2W-F-K-075U-125D-L940-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1427746
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-20)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-F-K-075U-125D-L940-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - FROSTED CONTINUOUS ROLL LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8322.4 lumens
Efficiency: N/A
Efficacy: 114.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 72.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1427746

CATALOG NUMBER: SQ2W-F-K-075U-125D-L940-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1427746

CATALOG NUMBER: SQ2W-F-K-075U-125D-L940-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	63
1	101	96	92	88	94	90	87	83	79	77	74	69	67	66	60	59	57	53
2	91	84	77	72	85	79	73	68	69	65	61	61	57	54	53	50	48	44
3	83	73	66	60	78	69	62	57	61	56	51	53	49	46	46	43	41	37
4	76	65	57	50	71	61	54	48	54	48	43	47	43	39	41	38	35	32
5	70	58	49	43	65	55	47	41	48	42	37	43	38	34	37	33	30	27
6	64	52	43	37	60	49	41	36	44	37	33	38	33	30	34	30	27	24
7	60	47	39	33	56	44	37	31	39	33	29	35	30	26	31	27	24	21
8	55	43	35	29	52	40	33	28	36	30	26	32	27	23	28	24	21	19
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	26	22	19	17
10	48	36	28	23	45	34	27	22	30	25	21	27	22	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30197	30197	30197	30197
5°	30013	30355	30013	30355
10°	29907	30251	29907	30251
15°	29743	30117	29743	30117
20°	29554	29848	29554	29848
25°	29236	29494	29236	29494
30°	28925	29123	28925	29123
35°	28556	28737	28556	28737
40°	28232	28314	28232	28314
45°	27818	27818	27818	27818
50°	27261	27326	27261	27326
55°	26620	26657	26620	26657
60°	25901	25901	25901	25901
65°	25058	24958	25058	24958
70°	23877	23627	23877	23627
75°	22264	21771	22264	21771
80°	19842	18856	19842	18856
85°	15857	13412	15857	13412

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 28005 cd/sqm



TEST NUMBER: P1427746

CATALOG NUMBER: SQ2W-F-K-075U-125D-L940-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.0	2.1
10°-20°	505.6	6.1
20°-30°	761.1	9.1
30°-40°	910.2	10.9
40°-50°	939.9	11.3
50°-60°	847.7	10.2
60°-70°	649.4	7.8
70°-80°	375.3	4.5
80°-90°	101.8	1.2
90°-100°	83.3	1.0
100°-110°	242.8	2.9
110°-120°	396.2	4.8
120°-130°	502.8	6.0
130°-140°	538.0	6.5
140°-150°	502.4	6.0
150°-160°	413.4	5.0
160°-170°	277.2	3.3
170°-180°	98.4	1.2
0°-30°	1443.7	17.3
0°-40°	2353.9	28.3
0°-60°	4141.5	49.8
0°-90°	5268.0	63.3
90°-120°	722.3	8.7
90°-150°	2265.4	27.2
90°-180°	3054.0	36.7
0°-180°	8322.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1870	1870	1870	1870	1870	
5°	1852	1873	1852	1873	1852	176
15°	1779	1802	1779	1802	1779	502
25°	1641	1656	1641	1656	1641	756
35°	1449	1458	1449	1458	1449	907
45°	1218	1218	1218	1218	1218	939
55°	946	947	946	947	946	845
65°	656	653	656	653	656	648
75°	357	349	357	349	357	378
85°	86	72	86	72	86	100
90°	3	23	3	45	3	6
95°	33	24	33	143	33	40
105°	154	247	154	340	154	164
115°	296	410	296	505	296	292
125°	438	650	438	619	438	391
135°	595	851	595	686	595	460
145°	760	981	760	701	760	475
155°	902	1065	902	727	902	415
165°	998	1111	998	837	998	281
175°	1043	1087	1043	982	1043	99
180°	1046	1046	1046	1046	1046	



TEST NUMBER: P1427746

CATALOG NUMBER: SQ2W-F-K-075U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3
2.5°	1860.8	1869.7	1878.6	1874.8	1866.9	1863.8	1865.7	1867.3	1868.3	1869.2	1868.3
5°	1851.8	1863.5	1875.2	1871.1	1861.8	1857.7	1858.8	1861.2	1867.0	1872.9	1867.0
7.5°	1836.8	1848.5	1860.2	1856.5	1847.6	1843.8	1845.2	1847.8	1853.9	1860.0	1853.9
10°	1824.2	1835.9	1847.6	1843.5	1834.1	1830.6	1832.9	1835.9	1840.5	1845.2	1840.5
12.5°	1808.4	1820.1	1831.8	1828.4	1819.9	1816.4	1817.8	1820.2	1825.3	1830.5	1825.3
15°	1779.4	1791.1	1802.8	1799.6	1791.4	1788.2	1789.9	1792.4	1797.1	1801.8	1797.1
17.5°	1744.3	1755.3	1766.4	1763.4	1755.8	1753.0	1755.0	1757.5	1761.6	1765.7	1761.6
20°	1720.1	1730.6	1741.2	1738.1	1730.5	1727.0	1727.6	1729.0	1733.1	1737.2	1733.1
22.5°	1690.6	1701.1	1711.7	1709.0	1701.8	1697.6	1696.3	1696.6	1701.6	1706.7	1701.6
25°	1641.1	1651.6	1662.2	1660.0	1653.5	1649.4	1647.7	1647.4	1651.5	1655.6	1651.5
27.5°	1589.5	1598.2	1607.0	1605.2	1599.8	1596.5	1595.3	1595.2	1598.1	1601.0	1598.1
30°	1551.5	1560.3	1569.1	1566.9	1561.0	1557.5	1556.4	1556.2	1559.1	1562.1	1559.1
32.5°	1511.5	1519.8	1528.1	1525.1	1518.3	1514.8	1514.6	1515.2	1518.6	1522.0	1518.6
35°	1448.8	1455.8	1462.8	1459.8	1453.3	1450.4	1451.0	1452.2	1455.1	1458.0	1455.1
37.5°	1385.8	1391.2	1396.6	1393.5	1387.5	1384.5	1384.3	1384.9	1387.3	1389.8	1387.3
40°	1339.5	1345.3	1351.2	1347.8	1341.4	1337.9	1337.3	1337.6	1340.5	1343.4	1340.5
42.5°	1292.1	1296.5	1301.0	1297.9	1292.4	1289.9	1290.2	1290.9	1292.4	1293.9	1292.4
45°	1218.3	1222.4	1226.5	1223.6	1218.3	1215.7	1215.7	1216.0	1217.1	1218.3	1217.1
47.5°	1141.1	1144.3	1147.4	1145.2	1141.1	1138.7	1138.0	1137.9	1139.8	1141.6	1139.8
50°	1085.3	1089.4	1093.5	1091.4	1087.3	1084.7	1083.5	1083.2	1085.6	1087.9	1085.6
52.5°	1030.5	1035.1	1039.6	1037.7	1033.6	1030.7	1029.1	1028.3	1030.2	1032.1	1030.2
55°	945.7	950.9	956.2	954.9	951.4	948.4	946.1	944.6	945.8	947.0	945.8
57.5°	859.0	864.2	869.3	868.3	865.3	862.3	859.5	857.8	859.5	861.1	859.5
60°	802.1	806.8	811.5	810.0	806.5	803.6	801.2	799.8	800.9	802.1	800.9
62.5°	744.2	748.8	753.5	751.7	747.7	744.6	742.2	740.8	741.9	743.1	741.9
65°	655.9	660.0	664.1	662.5	659.0	656.1	653.7	652.1	652.7	653.3	652.7
67.5°	566.9	570.4	573.9	572.2	568.8	565.4	562.0	559.7	560.7	561.6	560.7
70°	505.8	509.3	512.8	511.5	508.5	505.6	502.7	500.5	500.5	500.5	500.5
72.5°	446.8	449.8	452.8	451.1	447.7	444.7	442.3	440.4	440.4	440.4	440.4
75°	356.9	358.7	360.4	359.6	357.8	355.5	352.5	350.2	349.6	349.0	349.6
77.5°	270.3	270.3	270.3	268.6	266.4	264.1	261.9	260.1	259.4	258.7	259.4
80°	213.4	213.4	213.4	212.1	210.3	208.5	206.8	205.2	204.0	202.8	204.0
82.5°	160.7	159.7	158.8	157.3	155.5	153.3	150.6	148.9	150.0	151.2	150.0
85°	85.6	84.4	83.3	81.7	79.9	77.9	75.5	73.6	73.0	72.4	73.0
87.5°	27.0	26.9	27.0	26.6	25.8	24.4	22.5	21.2	20.9	20.5	20.9
90°	3.2	7.4	12.7	16.9	20.1	21.1	21.1	22.2	23.2	23.2	23.2
92.5°	11.6	18.4	18.6	18.6	22.6	24.5	26.2	26.4	27.5	27.5	27.5
95°	32.8	35.9	53.9	52.8	35.9	28.5	24.3	24.3	24.3	24.3	24.3
97.5°	62.6	67.2	70.2	94.0	99.3	95.9	78.2	65.7	58.8	55.6	58.8
100°	88.8	90.9	97.2	98.3	124.7	150.0	137.4	121.5	116.2	113.1	116.2
102.5°	115.0	116.2	126.0	130.4	136.5	150.9	194.9	190.0	186.4	185.8	186.4
105°	154.3	155.3	173.3	181.7	186.0	186.0	184.9	206.1	239.9	247.3	239.9
107.5°	196.3	201.2	222.3	244.9	249.8	251.1	245.6	242.4	241.1	242.0	241.1
110°	225.1	232.5	257.8	286.4	293.8	295.9	293.8	290.6	288.5	288.5	288.5



TEST NUMBER: P1427746

CATALOG NUMBER: SQ2W-F-K-075U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	253.0	263.7	292.5	325.2	337.7	344.1	339.4	337.1	335.0	336.7	335.0
115°	295.9	311.7	349.8	383.6	408.9	412.1	411.0	411.0	410.0	410.0	410.0
117.5°	335.6	361.0	403.7	443.0	472.3	480.8	485.0	483.7	482.5	484.6	482.5
120°	363.5	393.1	441.7	486.1	514.6	527.3	531.5	529.4	531.5	529.4	531.5
122.5°	393.1	429.4	477.2	523.3	556.9	571.2	576.3	576.7	577.2	575.9	577.2
125°	437.5	481.8	537.8	585.4	620.3	637.2	641.4	642.5	644.6	649.9	644.6
127.5°	482.3	532.6	594.1	639.9	675.6	696.1	702.7	705.0	709.5	711.8	709.5
130°	513.5	570.6	632.9	676.3	711.1	733.3	745.0	748.1	753.4	752.4	753.4
132.5°	546.5	606.1	669.3	714.3	746.6	770.5	780.5	789.5	791.5	792.9	791.5
135°	594.9	659.4	722.8	767.1	797.8	821.0	833.7	842.2	847.5	850.6	847.5
137.5°	645.8	713.9	774.8	814.3	845.1	865.2	879.6	888.5	893.9	896.5	893.9
140°	680.5	746.0	805.2	846.4	873.9	893.9	906.6	917.2	923.5	923.5	923.5
142.5°	713.5	778.1	835.6	876.8	900.9	919.3	932.8	940.9	948.0	948.0	948.0
145°	759.7	824.2	877.0	918.3	938.3	955.2	970.0	976.4	980.6	980.6	980.6
147.5°	808.1	865.2	913.4	952.9	969.8	989.7	1001.3	1006.4	1011.7	1009.3	1011.7
150°	836.9	889.7	936.2	973.2	990.1	1009.1	1020.7	1025.0	1030.3	1027.1	1030.3
152.5°	864.8	915.1	957.3	991.8	1006.2	1025.2	1038.5	1042.7	1046.3	1044.0	1046.3
155°	902.4	946.8	985.9	1017.6	1030.3	1048.2	1060.9	1066.2	1070.4	1065.1	1070.4
157.5°	936.0	974.3	1008.3	1037.4	1051.0	1066.4	1078.2	1084.8	1089.0	1086.7	1089.0
160°	956.3	991.2	1021.8	1049.3	1062.0	1075.7	1088.4	1095.8	1100.0	1096.8	1100.0
162.5°	973.2	1004.7	1033.6	1058.6	1069.6	1081.6	1096.8	1103.4	1107.6	1103.6	1107.6
165°	997.5	1022.9	1048.2	1069.4	1078.9	1088.4	1104.2	1111.6	1114.8	1110.6	1114.8
167.5°	1015.9	1035.3	1055.8	1074.0	1081.0	1090.3	1106.1	1112.3	1116.3	1111.0	1116.3
170°	1026.0	1042.9	1060.9	1075.7	1081.0	1089.4	1105.3	1110.6	1113.7	1108.5	1113.7
172.5°	1034.5	1047.2	1061.7	1074.9	1077.6	1084.4	1099.4	1104.6	1107.0	1102.5	1107.0
175°	1042.9	1050.3	1060.9	1069.4	1068.3	1072.5	1085.2	1089.4	1093.7	1087.3	1093.7
177.5°	1047.0	1050.3	1053.7	1058.8	1055.4	1055.4	1064.7	1067.2	1068.1	1064.7	1068.1
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P1427746

CATALOG NUMBER: SQ2W-F-K-075U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3
2.5°	1867.3	1865.7	1863.8	1866.9	1874.8	1878.6	1869.7	1860.8	1869.7	1878.6	1874.8
5°	1861.2	1858.8	1857.7	1861.8	1871.1	1875.2	1863.5	1851.8	1863.5	1875.2	1871.1
7.5°	1847.8	1845.2	1843.8	1847.6	1856.5	1860.2	1848.5	1836.8	1848.5	1860.2	1856.5
10°	1835.9	1832.9	1830.6	1834.1	1843.5	1847.6	1835.9	1824.2	1835.9	1847.6	1843.5
12.5°	1820.2	1817.8	1816.4	1819.9	1828.4	1831.8	1820.1	1808.4	1820.1	1831.8	1828.4
15°	1792.4	1789.9	1788.2	1791.4	1799.6	1802.8	1791.1	1779.4	1791.1	1802.8	1799.6
17.5°	1757.5	1755.0	1753.0	1755.8	1763.4	1766.4	1755.3	1744.3	1755.3	1766.4	1763.4
20°	1729.0	1727.6	1727.0	1730.5	1738.1	1741.2	1730.6	1720.1	1730.6	1741.2	1738.1
22.5°	1696.6	1696.3	1697.6	1701.8	1709.0	1711.7	1701.1	1690.6	1701.1	1711.7	1709.0
25°	1647.4	1647.7	1649.4	1653.5	1660.0	1662.2	1651.6	1641.1	1651.6	1662.2	1660.0
27.5°	1595.2	1595.3	1596.5	1599.8	1605.2	1607.0	1598.2	1589.5	1598.2	1607.0	1605.2
30°	1556.2	1556.4	1557.5	1561.0	1566.9	1569.1	1560.3	1551.5	1560.3	1569.1	1566.9
32.5°	1515.2	1514.6	1514.8	1518.3	1525.1	1528.1	1519.8	1511.5	1519.8	1528.1	1525.1
35°	1452.2	1451.0	1450.4	1453.3	1459.8	1462.8	1455.8	1448.8	1455.8	1462.8	1459.8
37.5°	1384.9	1384.3	1384.5	1387.5	1393.5	1396.6	1391.2	1385.8	1391.2	1396.6	1393.5
40°	1337.6	1337.3	1337.9	1341.4	1347.8	1351.2	1345.3	1339.5	1345.3	1351.2	1347.8
42.5°	1290.9	1290.2	1289.9	1292.4	1297.9	1301.0	1296.5	1292.1	1296.5	1301.0	1297.9
45°	1216.0	1215.7	1215.7	1218.3	1223.6	1226.5	1222.4	1218.3	1222.4	1226.5	1223.6
47.5°	1137.9	1138.0	1138.7	1141.1	1145.2	1147.4	1144.3	1141.1	1144.3	1147.4	1145.2
50°	1083.2	1083.5	1084.7	1087.3	1091.4	1093.5	1089.4	1085.3	1089.4	1093.5	1091.4
52.5°	1028.3	1029.1	1030.7	1033.6	1037.7	1039.6	1035.1	1030.5	1035.1	1039.6	1037.7
55°	944.6	946.1	948.4	951.4	954.9	956.2	950.9	945.7	950.9	956.2	954.9
57.5°	857.8	859.5	862.3	865.3	868.3	869.3	864.2	859.0	864.2	869.3	868.3
60°	799.8	801.2	803.6	806.5	810.0	811.5	806.8	802.1	806.8	811.5	810.0
62.5°	740.8	742.2	744.6	747.7	751.7	753.5	748.8	744.2	748.8	753.5	751.7
65°	652.1	653.7	656.1	659.0	662.5	664.1	660.0	655.9	660.0	664.1	662.5
67.5°	559.7	562.0	565.4	568.8	572.2	573.9	570.4	566.9	570.4	573.9	572.2
70°	500.5	502.7	505.6	508.5	511.5	512.8	509.3	505.8	509.3	512.8	511.5
72.5°	440.4	442.3	444.7	447.7	451.1	452.8	449.8	446.8	449.8	452.8	451.1
75°	350.2	352.5	355.5	357.8	359.6	360.4	358.7	356.9	358.7	360.4	359.6
77.5°	260.1	261.9	264.1	266.4	268.6	270.3	270.3	270.3	270.3	270.3	268.6
80°	205.2	206.8	208.5	210.3	212.1	213.4	213.4	213.4	213.4	213.4	212.1
82.5°	148.9	150.6	153.3	155.5	157.3	158.8	159.7	160.7	159.7	158.8	157.3
85°	73.6	75.5	77.9	79.9	81.7	83.3	84.4	85.6	84.4	83.3	81.7
87.5°	21.2	22.5	24.4	25.8	26.6	27.0	26.9	27.0	26.9	26.8	27.0
90°	22.2	21.1	21.1	20.1	16.9	12.7	7.4	3.2	7.4	11.6	19.0
92.5°	26.4	26.2	24.5	22.6	18.6	18.6	18.4	11.6	20.1	28.5	41.0
95°	24.3	24.3	28.5	35.9	52.8	53.9	35.9	32.8	46.5	65.5	82.4
97.5°	65.7	78.2	95.9	99.3	94.0	70.2	67.2	62.6	85.2	104.0	131.2
100°	121.5	137.4	150.0	124.7	98.3	97.2	90.9	88.8	113.1	131.0	157.4
102.5°	190.0	194.9	150.9	136.5	130.4	126.0	116.2	115.0	139.3	164.0	186.2
105°	206.1	184.9	186.0	186.0	181.7	173.3	155.3	154.3	181.7	210.3	237.8
107.5°	242.4	245.6	251.1	249.8	244.9	222.3	201.2	196.3	221.1	255.3	285.5
110°	290.6	293.8	295.9	293.8	286.4	257.8	232.5	225.1	247.3	283.2	315.9



TEST NUMBER: P1427746

CATALOG NUMBER: SQ2W-F-K-075U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	337.1	339.4	344.1	337.7	325.2	292.5	263.7	253.0	275.2	311.9	345.5
115°	411.0	411.0	412.1	408.9	383.6	349.8	311.7	295.9	314.9	348.7	385.7
117.5°	483.7	485.0	480.8	472.3	443.0	403.7	361.0	335.6	350.6	386.3	424.4
120°	529.4	531.5	527.3	514.6	486.1	441.7	393.1	363.5	375.1	410.0	448.0
122.5°	576.7	576.3	571.2	556.9	523.3	477.2	429.4	393.1	397.9	430.3	467.5
125°	642.5	641.4	637.2	620.3	585.4	537.8	481.8	437.5	431.1	458.6	496.6
127.5°	705.0	702.7	696.1	675.6	639.9	594.1	532.6	482.3	468.1	485.4	520.3
130°	748.1	745.0	733.3	711.1	676.3	632.9	570.6	513.5	493.5	504.0	534.7
132.5°	789.5	780.5	770.5	746.6	714.3	669.3	606.1	546.5	518.8	523.5	547.4
135°	842.2	833.7	821.0	797.8	767.1	722.8	659.4	594.9	556.9	552.6	566.4
137.5°	888.5	879.6	865.2	845.1	814.3	774.8	713.9	645.8	597.9	583.7	589.0
140°	917.2	906.6	893.9	873.9	846.4	805.2	746.0	680.5	626.6	606.5	603.4
142.5°	940.9	932.8	919.3	900.9	876.8	835.6	778.1	713.5	656.2	630.2	622.8
145°	976.4	970.0	955.2	938.3	918.3	877.0	824.2	759.7	702.7	668.9	653.0
147.5°	1006.4	1001.3	989.7	969.8	952.9	913.4	865.2	808.1	749.6	707.8	687.3
150°	1025.0	1020.7	1009.1	990.1	973.2	936.2	889.7	836.9	780.9	736.5	710.1
152.5°	1042.7	1038.5	1025.2	1006.2	991.8	957.3	915.1	864.8	807.9	763.6	736.3
155°	1066.2	1060.9	1048.2	1030.3	1017.6	985.9	946.8	902.4	853.8	807.3	776.7
157.5°	1084.8	1078.2	1066.4	1051.0	1037.4	1008.3	974.3	936.0	893.5	849.1	817.9
160°	1095.8	1088.4	1075.7	1062.0	1049.3	1021.8	991.2	956.3	917.2	877.0	843.2
162.5°	1103.4	1096.8	1081.6	1069.6	1058.6	1033.6	1004.7	973.2	938.3	903.2	872.0
165°	1111.6	1104.2	1088.4	1078.9	1069.4	1048.2	1022.9	997.5	967.9	939.4	914.0
167.5°	1112.3	1106.1	1090.3	1081.0	1074.0	1055.8	1035.3	1015.9	992.9	970.5	949.3
170°	1110.6	1105.3	1089.4	1081.0	1075.7	1060.9	1042.9	1026.0	1008.1	989.0	972.1
172.5°	1104.6	1099.4	1084.4	1077.6	1074.9	1061.7	1047.2	1034.5	1019.1	1005.1	991.6
175°	1089.4	1085.2	1072.5	1068.3	1069.4	1060.9	1050.3	1042.9	1033.4	1025.0	1017.6
177.5°	1067.2	1064.7	1055.4	1055.4	1058.8	1053.7	1050.3	1047.0	1042.7	1040.2	1037.7
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P1427746

CATALOG NUMBER: SQ2W-F-K-075U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3
2.5°	1866.9	1863.8	1865.7	1867.3	1868.3	1869.2	1868.3	1867.3	1865.7	1863.8	1866.9
5°	1861.8	1857.7	1858.8	1861.2	1867.0	1872.9	1867.0	1861.2	1858.8	1857.7	1861.8
7.5°	1847.6	1843.8	1845.2	1847.8	1853.9	1860.0	1853.9	1847.8	1845.2	1843.8	1847.6
10°	1834.1	1830.6	1832.9	1835.9	1840.5	1845.2	1840.5	1835.9	1832.9	1830.6	1834.1
12.5°	1819.9	1816.4	1817.8	1820.2	1825.3	1830.5	1825.3	1820.2	1817.8	1816.4	1819.9
15°	1791.4	1788.2	1789.9	1792.4	1797.1	1801.8	1797.1	1792.4	1789.9	1788.2	1791.4
17.5°	1755.8	1753.0	1755.0	1757.5	1761.6	1765.7	1761.6	1757.5	1755.0	1753.0	1755.8
20°	1730.5	1727.0	1727.6	1729.0	1733.1	1737.2	1733.1	1729.0	1727.6	1727.0	1730.5
22.5°	1701.8	1697.6	1696.3	1696.6	1701.6	1706.7	1701.6	1696.6	1696.3	1697.6	1701.8
25°	1653.5	1649.4	1647.7	1647.4	1651.5	1655.6	1651.5	1647.4	1647.7	1649.4	1653.5
27.5°	1599.8	1596.5	1595.3	1595.2	1598.1	1601.0	1598.1	1595.2	1595.3	1596.5	1599.8
30°	1561.0	1557.5	1556.4	1556.2	1559.1	1562.1	1559.1	1556.2	1556.4	1557.5	1561.0
32.5°	1518.3	1514.8	1514.6	1515.2	1518.6	1522.0	1518.6	1515.2	1514.6	1514.8	1518.3
35°	1453.3	1450.4	1451.0	1452.2	1455.1	1458.0	1455.1	1452.2	1451.0	1450.4	1453.3
37.5°	1387.5	1384.5	1384.3	1384.9	1387.3	1389.8	1387.3	1384.9	1384.3	1384.5	1387.5
40°	1341.4	1337.9	1337.3	1337.6	1340.5	1343.4	1340.5	1337.6	1337.3	1337.9	1341.4
42.5°	1292.4	1289.9	1290.2	1290.9	1292.4	1293.9	1292.4	1290.9	1290.2	1289.9	1292.4
45°	1218.3	1215.7	1215.7	1216.0	1217.1	1218.3	1217.1	1216.0	1215.7	1215.7	1218.3
47.5°	1141.1	1138.7	1138.0	1137.9	1139.8	1141.6	1139.8	1137.9	1138.0	1138.7	1141.1
50°	1087.3	1084.7	1083.5	1083.2	1085.6	1087.9	1085.6	1083.2	1083.5	1084.7	1087.3
52.5°	1033.6	1030.7	1029.1	1028.3	1030.2	1032.1	1030.2	1028.3	1029.1	1030.7	1033.6
55°	951.4	948.4	946.1	944.6	945.8	947.0	945.8	944.6	946.1	948.4	951.4
57.5°	865.3	862.3	859.5	857.8	859.5	861.1	859.5	857.8	859.5	862.3	865.3
60°	806.5	803.6	801.2	799.8	800.9	802.1	800.9	799.8	801.2	803.6	806.5
62.5°	747.7	744.6	742.2	740.8	741.9	743.1	741.9	740.8	742.2	744.6	747.7
65°	659.0	656.1	653.7	652.1	652.7	653.3	652.7	652.1	653.7	656.1	659.0
67.5°	568.8	565.4	562.0	559.7	560.7	561.6	560.7	559.7	562.0	565.4	568.8
70°	508.5	505.6	502.7	500.5	500.5	500.5	500.5	500.5	502.7	505.6	508.5
72.5°	447.7	444.7	442.3	440.4	440.4	440.4	440.4	440.4	442.3	444.7	447.7
75°	357.8	355.5	352.5	350.2	349.6	349.0	349.6	350.2	352.5	355.5	357.8
77.5°	266.4	264.1	261.9	260.1	259.4	258.7	259.4	260.1	261.9	264.1	266.4
80°	210.3	208.5	206.8	205.2	204.0	202.8	204.0	205.2	206.8	208.5	210.3
82.5°	155.5	153.3	150.6	148.9	150.0	151.2	150.0	148.9	150.6	153.3	155.5
85°	79.9	77.9	75.5	73.6	73.0	72.4	73.0	73.6	75.5	77.9	79.9
87.5°	26.6	26.5	26.1	25.4	25.8	24.9	25.8	25.4	26.1	26.5	26.6
90°	24.3	31.7	39.1	43.3	47.6	45.4	47.6	43.3	39.1	31.7	24.3
92.5°	48.8	61.3	70.4	78.0	81.4	80.9	81.4	78.0	70.4	61.3	48.8
95°	98.3	113.1	127.9	138.4	144.8	142.7	144.8	138.4	127.9	113.1	98.3
97.5°	151.5	171.4	187.9	197.8	204.1	208.4	204.1	197.8	187.9	171.4	151.5
100°	187.0	206.1	225.1	236.7	247.3	251.5	247.3	236.7	225.1	206.1	187.0
102.5°	215.8	240.7	261.4	273.9	282.8	287.0	282.8	273.9	261.4	240.7	215.8
105°	263.1	289.5	311.7	327.6	337.1	340.2	337.1	327.6	311.7	289.5	263.1
107.5°	310.5	337.7	358.2	375.8	387.4	394.1	387.4	375.8	358.2	337.7	310.5
110°	347.6	369.8	392.0	407.9	419.5	423.7	419.5	407.9	392.0	369.8	347.6



TEST NUMBER: P1427746

CATALOG NUMBER: SQ2W-F-K-075U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	378.9	403.7	425.8	441.7	455.0	460.9	455.0	441.7	425.8	403.7	378.9
115°	422.7	455.4	475.5	490.3	499.8	505.1	499.8	490.3	475.5	455.4	422.7
117.5°	459.0	493.3	515.2	526.6	531.1	534.9	531.1	526.6	515.2	493.3	459.0
120°	481.8	513.5	538.9	553.7	559.0	561.1	559.0	553.7	538.9	513.5	481.8
122.5°	503.0	533.0	557.5	575.7	584.3	586.5	584.3	575.7	557.5	533.0	503.0
125°	532.6	561.1	586.5	604.4	613.9	619.2	613.9	604.4	586.5	561.1	532.6
127.5°	558.3	589.2	612.4	628.7	638.0	642.2	638.0	628.7	612.4	589.2	558.3
130°	572.7	604.4	627.7	645.6	654.1	658.3	654.1	645.6	627.7	604.4	572.7
132.5°	583.7	617.1	641.2	657.5	666.8	671.0	666.8	657.5	641.2	617.1	583.7
135°	597.0	631.9	657.3	673.1	681.6	685.8	681.6	673.1	657.3	631.9	597.0
137.5°	608.6	640.3	666.8	683.5	691.1	693.8	691.1	683.5	666.8	640.3	608.6
140°	617.1	644.6	671.0	686.8	695.3	696.3	695.3	686.8	671.0	644.6	617.1
142.5°	628.1	649.6	672.7	688.5	697.0	698.9	697.0	688.5	672.7	649.6	628.1
145°	647.7	660.4	676.3	691.1	698.5	700.6	698.5	691.1	676.3	660.4	647.7
147.5°	672.5	676.5	684.7	694.4	701.6	703.1	701.6	694.4	684.7	676.5	672.5
150°	691.1	690.0	693.2	699.5	705.9	704.8	705.9	699.5	693.2	690.0	691.1
152.5°	712.2	706.1	705.9	708.8	711.8	711.6	711.8	708.8	705.9	706.1	712.2
155°	748.1	736.5	730.2	728.0	728.0	727.0	728.0	728.0	730.2	736.5	748.1
157.5°	787.6	771.4	761.9	756.8	755.3	753.0	755.3	756.8	761.9	771.4	787.6
160°	814.7	796.7	787.2	778.8	775.6	772.4	775.6	778.8	787.2	796.7	814.7
162.5°	840.1	822.9	812.6	805.0	801.8	796.9	801.8	805.0	812.6	822.9	840.1
165°	881.3	863.3	851.7	845.3	841.1	836.9	841.1	845.3	851.7	863.3	881.3
167.5°	922.5	902.8	895.2	888.0	884.0	876.4	884.0	888.0	895.2	902.8	922.5
170°	947.8	929.9	925.6	919.3	911.9	903.5	911.9	919.3	925.6	929.9	947.8
172.5°	969.8	957.8	953.5	947.2	944.9	938.1	944.9	947.2	953.5	957.8	969.8
175°	1001.7	992.2	992.2	991.2	988.0	981.7	988.0	991.2	992.2	992.2	1001.7
177.5°	1028.4	1023.3	1026.7	1026.7	1025.8	1019.9	1025.8	1026.7	1026.7	1023.3	1028.4
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P1427746

CATALOG NUMBER: SQ2W-F-K-075U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1870.3	1870.3	1870.3	1870.3
2.5°	1874.8	1878.6	1869.7	1860.8
5°	1871.1	1875.2	1863.5	1851.8
7.5°	1856.5	1860.2	1848.5	1836.8
10°	1843.5	1847.6	1835.9	1824.2
12.5°	1828.4	1831.8	1820.1	1808.4
15°	1799.6	1802.8	1791.1	1779.4
17.5°	1763.4	1766.4	1755.3	1744.3
20°	1738.1	1741.2	1730.6	1720.1
22.5°	1709.0	1711.7	1701.1	1690.6
25°	1660.0	1662.2	1651.6	1641.1
27.5°	1605.2	1607.0	1598.2	1589.5
30°	1566.9	1569.1	1560.3	1551.5
32.5°	1525.1	1528.1	1519.8	1511.5
35°	1459.8	1462.8	1455.8	1448.8
37.5°	1393.5	1396.6	1391.2	1385.8
40°	1347.8	1351.2	1345.3	1339.5
42.5°	1297.9	1301.0	1296.5	1292.1
45°	1223.6	1226.5	1222.4	1218.3
47.5°	1145.2	1147.4	1144.3	1141.1
50°	1091.4	1093.5	1089.4	1085.3
52.5°	1037.7	1039.6	1035.1	1030.5
55°	954.9	956.2	950.9	945.7
57.5°	868.3	869.3	864.2	859.0
60°	810.0	811.5	806.8	802.1
62.5°	751.7	753.5	748.8	744.2
65°	662.5	664.1	660.0	655.9
67.5°	572.2	573.9	570.4	566.9
70°	511.5	512.8	509.3	505.8
72.5°	451.1	452.8	449.8	446.8
75°	359.6	360.4	358.7	356.9
77.5°	268.6	270.3	270.3	270.3
80°	212.1	213.4	213.4	213.4
82.5°	157.3	158.8	159.7	160.7
85°	81.7	83.3	84.4	85.6
87.5°	27.0	26.8	26.9	27.0
90°	19.0	11.6	7.4	3.2
92.5°	41.0	28.5	20.1	11.6
95°	82.4	65.5	46.5	32.8
97.5°	131.2	104.0	85.2	62.6
100°	157.4	131.0	113.1	88.8
102.5°	186.2	164.0	139.3	115.0
105°	237.8	210.3	181.7	154.3
107.5°	285.5	255.3	221.1	196.3
110°	315.9	283.2	247.3	225.1

TEST NUMBER: P1427746

CATALOG NUMBER: SQ2W-F-K-075U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	345.5	311.9	275.2	253.0
115°	385.7	348.7	314.9	295.9
117.5°	424.4	386.3	350.6	335.6
120°	448.0	410.0	375.1	363.5
122.5°	467.5	430.3	397.9	393.1
125°	496.6	458.6	431.1	437.5
127.5°	520.3	485.4	468.1	482.3
130°	534.7	504.0	493.5	513.5
132.5°	547.4	523.5	518.8	546.5
135°	566.4	552.6	556.9	594.9
137.5°	589.0	583.7	597.9	645.8
140°	603.4	606.5	626.6	680.5
142.5°	622.8	630.2	656.2	713.5
145°	653.0	668.9	702.7	759.7
147.5°	687.3	707.8	749.6	808.1
150°	710.1	736.5	780.9	836.9
152.5°	736.3	763.6	807.9	864.8
155°	776.7	807.3	853.8	902.4
157.5°	817.9	849.1	893.5	936.0
160°	843.2	877.0	917.2	956.3
162.5°	872.0	903.2	938.3	973.2
165°	914.0	939.4	967.9	997.5
167.5°	949.3	970.5	992.9	1015.9
170°	972.1	989.0	1008.1	1026.0
172.5°	991.6	1005.1	1019.1	1034.5
175°	1017.6	1025.0	1033.4	1042.9
177.5°	1037.7	1040.2	1042.7	1047.0
180°	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P1427746
 CATALOG NUMBER: SQ2W-F-K-075U-125D-L940-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.84	21.85	21.67	22.71	23.77	20.76	21.77	21.59	22.62	23.69
	3H	22.64	23.55	23.49	24.42	25.51	22.54	23.45	23.38	24.31	25.41
	4H	23.34	24.20	24.20	25.08	26.18	23.23	24.09	24.09	24.96	26.06
	6H	23.79	24.58	24.66	25.46	26.58	23.65	24.44	24.52	25.32	26.44
	8H	23.95	24.71	24.84	25.61	26.72	23.80	24.55	24.68	25.45	26.57
	12H	24.04	24.76	24.93	25.65	26.80	23.87	24.59	24.75	25.48	26.62
4H	2H	21.44	22.30	22.30	23.17	24.27	21.37	22.23	22.24	23.10	24.21
	3H	23.47	24.19	24.35	25.10	26.22	23.38	24.10	24.26	25.00	26.12
	4H	24.29	24.95	25.18	25.85	27.00	24.18	24.84	25.07	25.74	26.88
	6H	24.86	25.42	25.76	26.35	27.49	24.71	25.28	25.62	26.21	27.35
	8H	25.07	25.60	25.98	26.52	27.68	24.91	25.44	25.82	26.36	27.52
	12H	25.19	25.67	26.12	26.61	27.78	25.01	25.49	25.93	26.42	27.59
8H	4H	24.55	25.08	25.46	26.00	27.16	24.45	24.98	25.36	25.90	27.06
	6H	25.25	25.69	26.18	26.65	27.81	25.12	25.55	26.05	26.52	27.68
	8H	25.55	25.94	26.50	26.89	28.07	25.40	25.79	26.34	26.74	27.92
	12H	25.74	26.09	26.69	27.03	28.26	25.55	25.89	26.50	26.84	28.07
12H	4H	24.55	25.03	25.48	25.97	27.14	24.46	24.94	25.39	25.87	27.04
	6H	25.30	25.69	26.24	26.64	27.82	25.17	25.56	26.12	26.51	27.69
	8H	25.64	25.98	26.59	26.93	28.16	25.49	25.83	26.44	26.78	28.00