

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428091

Luminaire Tested: SQ2W-PP3-K-100U-075D-L840-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428091
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-7)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PP3-K-100U-075D-L840-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE PRISM LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8517.6 lumens
Efficiency: N/A
Efficacy: 142.4 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.41 / 1.4
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428091

CATALOG NUMBER: SQ2W-PP3-K-100U-075D-L840-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428091

CATALOG NUMBER: SQ2W-PP3-K-100U-075D-L840-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47				47
1	98	94	90	87	90	86	83	80	72	70	68	60	58	57	48	47	46				41	
2	89	82	76	71	82	76	71	67	64	60	57	53	50	48	43	41	40				35	
3	82	73	66	60	75	67	61	56	57	52	49	47	44	41	38	36	34				30	
4	75	64	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30				26	
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26				23	
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23				20	
7	59	47	39	33	54	43	36	32	37	32	28	31	27	24	26	23	21				18	
8	54	42	35	30	50	39	33	28	34	29	25	29	25	22	24	21	18				16	
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17				14	
10	47	35	28	24	44	33	27	22	29	23	20	24	20	18	20	17	15				13	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	25678	25678	25678	25678
5°	25476	25940	25476	25940
10°	25605	26130	25605	26130
15°	25544	26191	25544	26191
20°	25362	26719	25362	26719
25°	25218	28122	25218	28122
30°	25073	28711	25073	28711
35°	24720	28763	24720	28763
40°	24059	26575	24059	26575
45°	23340	20230	23340	20230
50°	22423	16849	22423	16849
55°	20870	12115	20870	12115
60°	17970	8686	17970	8686
65°	15159	8542	15159	8542
70°	12618	8176	12618	8176
75°	10698	7654	10698	7654
80°	9065	6880	9065	6880
85°	7169	3742	7169	3742

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 40°
 Vertical Angle: 45°
 Luminance: 25532 cd/sqm



TEST NUMBER: P1428091

CATALOG NUMBER: SQ2W-PP3-K-100U-075D-L840-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.4	1.8
10°-20°	438.3	5.1
20°-30°	686.6	8.1
30°-40°	847.0	9.9
40°-50°	797.4	9.4
50°-60°	564.7	6.6
60°-70°	321.7	3.8
70°-80°	159.3	1.9
80°-90°	45.3	0.5
90°-100°	122.8	1.4
100°-110°	358.2	4.2
110°-120°	584.5	6.9
120°-130°	741.7	8.7
130°-140°	793.6	9.3
140°-150°	741.1	8.7
150°-160°	609.8	7.2
160°-170°	409.0	4.8
170°-180°	145.2	1.7
0°-30°	1276.4	15.0
0°-40°	2123.4	24.9
0°-60°	3485.5	40.9
0°-90°	4011.8	47.1
90°-120°	1065.5	12.5
90°-150°	3341.8	39.2
90°-180°	4506.0	52.9
0°-180°	8517.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1590	1590	1590	1590	1590	
5°	1572	1600	1572	1600	1572	150
15°	1528	1567	1528	1567	1528	431
25°	1416	1579	1416	1579	1416	652
35°	1254	1459	1254	1459	1254	782
45°	1022	886	1022	886	1022	787
55°	741	430	741	430	741	654
65°	397	224	397	224	397	398
75°	172	123	172	123	172	186
85°	39	20	39	20	39	45
90°	5	34	5	67	5	5
95°	48	36	48	210	48	58
105°	228	365	228	502	228	242
115°	436	605	436	745	436	430
125°	645	959	645	913	645	577
135°	878	1255	878	1012	878	678
145°	1121	1446	1121	1034	1121	701
155°	1331	1571	1331	1072	1331	612
165°	1472	1638	1472	1235	1472	414
175°	1538	1604	1538	1448	1538	146
180°	1543	1543	1543	1543	1543	



TEST NUMBER: P1428091

CATALOG NUMBER: SQ2W-PP3-K-100U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1590.4	1590.4	1590.4	1590.4	1590.4	1590.4	1590.4	1590.4	1590.4	1590.4	1590.4
2.5°	1578.3	1588.5	1598.6	1596.2	1589.7	1587.0	1588.2	1589.4	1590.5	1591.7	1590.5
5°	1571.9	1584.6	1597.3	1595.4	1588.7	1586.1	1587.6	1590.0	1595.3	1600.5	1595.3
7.5°	1565.9	1578.9	1591.9	1590.2	1583.6	1581.6	1584.1	1587.6	1594.1	1600.5	1594.1
10°	1561.8	1573.0	1584.2	1582.6	1576.6	1575.5	1579.2	1583.3	1588.5	1593.8	1588.5
12.5°	1549.7	1560.3	1570.9	1569.6	1564.2	1563.9	1568.9	1573.7	1578.4	1583.0	1578.4
15°	1528.2	1537.9	1547.6	1547.8	1544.8	1546.7	1553.4	1559.4	1563.1	1566.9	1563.1
17.5°	1498.9	1510.7	1522.6	1525.3	1525.0	1529.6	1539.2	1547.3	1551.2	1555.1	1551.2
20°	1476.1	1490.3	1504.5	1509.1	1510.6	1517.4	1529.3	1540.2	1547.6	1555.1	1547.6
22.5°	1451.9	1468.5	1485.0	1491.2	1493.9	1504.2	1522.1	1538.8	1551.7	1564.5	1551.7
25°	1415.6	1432.0	1448.4	1460.4	1470.8	1489.2	1515.3	1539.8	1559.2	1578.6	1559.2
27.5°	1373.2	1389.5	1405.8	1426.3	1448.3	1474.0	1503.4	1529.4	1544.7	1560.1	1544.7
30°	1344.9	1360.6	1376.3	1399.9	1426.0	1454.4	1485.0	1511.6	1525.8	1540.0	1525.8
32.5°	1310.0	1326.3	1342.6	1367.6	1395.5	1426.0	1459.0	1487.1	1500.1	1513.1	1500.1
35°	1254.2	1269.9	1285.5	1314.7	1348.3	1382.3	1416.7	1444.3	1451.8	1459.3	1451.8
37.5°	1189.9	1207.7	1225.5	1258.2	1295.9	1324.3	1343.6	1358.2	1358.6	1359.1	1358.6
40°	1141.5	1164.7	1187.8	1220.5	1256.4	1276.2	1279.9	1280.3	1270.6	1260.9	1270.6
42.5°	1094.5	1124.2	1153.9	1180.2	1205.3	1210.5	1195.7	1173.8	1130.6	1087.4	1130.6
45°	1022.2	1057.3	1092.4	1108.5	1118.2	1085.3	1009.8	945.8	915.9	886.0	915.9
47.5°	945.2	979.8	1014.5	1010.1	992.6	942.8	860.8	794.1	773.5	752.8	773.5
50°	892.7	925.6	958.5	934.7	892.1	836.1	766.6	709.6	690.2	670.8	690.2
52.5°	833.5	862.8	892.1	856.3	798.7	739.7	679.2	626.4	596.8	567.2	596.8
55°	741.4	761.6	781.8	742.5	683.5	618.5	547.5	487.2	458.8	430.4	458.8
57.5°	630.4	644.6	658.8	628.0	582.1	517.5	434.1	363.6	331.8	299.9	331.8
60°	556.5	567.7	578.9	550.9	509.8	448.1	365.9	300.4	284.7	269.0	284.7
62.5°	489.2	499.2	509.2	480.0	437.7	382.7	314.8	262.6	257.0	251.5	257.0
65°	396.8	406.5	416.2	385.6	341.5	298.5	256.7	225.1	224.3	223.6	224.3
67.5°	315.7	326.3	336.9	308.1	266.1	234.4	212.8	196.5	195.6	194.7	195.6
70°	267.3	278.5	289.7	262.8	223.2	197.4	185.5	176.2	174.7	173.2	174.7
72.5°	227.0	237.6	248.2	224.7	189.9	168.6	160.8	154.8	153.9	153.0	153.9
75°	171.5	179.7	187.9	170.9	145.5	130.9	127.2	124.2	123.5	122.7	123.5
77.5°	124.4	129.6	134.9	123.7	107.1	97.9	95.9	94.3	93.5	92.8	93.5
80°	97.5	99.8	102.0	94.1	82.9	77.0	76.2	75.5	74.7	74.0	74.7
82.5°	73.3	72.6	71.8	67.2	61.4	58.1	57.4	56.5	55.1	53.8	55.1
85°	38.7	37.2	35.7	34.2	32.7	30.4	27.5	24.7	22.4	20.2	22.4
87.5°	13.0	14.3	15.8	14.9	12.8	11.3	10.7	10.6	10.9	10.9	10.9
90°	4.7	10.9	18.7	24.9	29.6	31.2	31.2	32.7	34.3	34.3	34.3
92.5°	17.1	27.1	27.4	27.4	33.4	36.2	38.7	39.0	40.5	40.5	40.5
95°	48.3	53.0	79.5	77.9	53.0	42.1	35.9	35.9	35.9	35.9	35.9
97.5°	92.3	99.1	103.5	138.7	146.5	141.5	115.3	97.0	86.7	82.0	86.7
100°	130.9	134.1	143.4	145.0	183.9	221.3	202.6	179.3	171.5	166.8	171.5
102.5°	169.6	171.5	185.8	192.4	201.4	222.6	287.4	280.3	275.0	274.0	275.0
105°	227.6	229.1	255.6	268.1	274.3	274.3	272.8	304.0	353.8	364.8	353.8
107.5°	289.6	296.8	328.0	361.3	368.5	370.4	362.3	357.6	355.7	357.0	355.7
110°	332.0	342.9	380.3	422.4	433.3	436.5	433.3	428.7	425.5	425.5	425.5



TEST NUMBER: P1428091

CATALOG NUMBER: SQ2W-PP3-K-100U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	373.2	389.1	431.5	479.8	498.2	507.5	500.7	497.2	494.1	496.6	494.1
115°	436.5	459.8	516.0	565.8	603.2	607.9	606.4	606.4	604.8	604.8	604.8
117.5°	495.1	532.5	595.5	653.4	696.8	709.2	715.5	713.6	711.7	714.9	711.7
120°	536.2	579.9	651.6	717.0	759.1	777.8	784.1	780.9	784.1	780.9	784.1
122.5°	579.9	633.5	703.9	771.9	821.5	842.7	850.2	850.8	851.4	849.5	851.4
125°	645.3	710.8	793.4	863.6	915.0	939.9	946.2	947.7	950.9	958.6	950.9
127.5°	711.4	785.6	876.3	944.0	996.7	1026.9	1036.6	1040.0	1046.6	1050.0	1046.6
130°	757.6	841.7	933.7	997.6	1049.1	1081.8	1098.9	1103.6	1111.4	1109.8	1111.4
132.5°	806.2	894.1	987.3	1053.7	1101.4	1136.7	1151.3	1164.7	1167.5	1169.7	1167.5
135°	877.6	972.7	1066.2	1131.7	1176.9	1211.2	1229.9	1242.3	1250.1	1254.8	1250.1
137.5°	952.7	1053.1	1142.9	1201.2	1246.7	1276.3	1297.5	1310.6	1318.7	1322.5	1318.7
140°	1003.9	1100.5	1187.8	1248.6	1289.1	1318.7	1337.4	1353.0	1362.4	1362.4	1362.4
142.5°	1052.5	1147.9	1232.7	1293.5	1329.0	1356.1	1376.1	1387.9	1398.5	1398.5	1398.5
145°	1120.8	1215.8	1293.8	1354.6	1384.2	1409.1	1431.0	1440.3	1446.5	1446.5	1446.5
147.5°	1192.2	1276.3	1347.4	1405.7	1430.6	1459.9	1477.1	1484.6	1492.4	1488.9	1492.4
150°	1234.6	1312.5	1381.1	1435.6	1460.6	1488.6	1505.8	1512.0	1519.8	1515.1	1519.8
152.5°	1275.7	1349.9	1412.3	1463.1	1484.3	1512.3	1532.0	1538.2	1543.5	1540.1	1543.5
155°	1331.2	1396.7	1454.3	1501.1	1519.8	1546.3	1565.0	1572.8	1579.0	1571.2	1579.0
157.5°	1380.8	1437.2	1487.4	1530.4	1550.4	1573.1	1590.6	1600.2	1606.5	1603.0	1606.5
160°	1410.7	1462.1	1507.3	1547.9	1566.6	1586.8	1605.5	1616.5	1622.7	1618.0	1622.7
162.5°	1435.6	1482.1	1524.8	1561.6	1577.8	1595.6	1618.0	1627.7	1633.9	1628.0	1633.9
165°	1471.5	1508.9	1546.3	1577.5	1591.5	1605.5	1628.9	1639.8	1644.5	1638.3	1644.5
167.5°	1498.6	1527.3	1557.5	1584.3	1594.6	1608.3	1631.7	1640.8	1646.7	1638.9	1646.7
170°	1513.6	1538.5	1565.0	1586.8	1594.6	1607.1	1630.5	1638.3	1643.0	1635.2	1643.0
172.5°	1526.0	1544.7	1566.3	1585.6	1589.6	1599.6	1621.8	1629.5	1633.0	1626.4	1633.0
175°	1538.5	1549.4	1565.0	1577.5	1575.9	1582.2	1600.9	1607.1	1613.3	1604.0	1613.3
177.5°	1544.4	1549.4	1554.4	1561.9	1556.9	1556.9	1570.6	1574.4	1575.6	1570.6	1575.6
180°	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2



TEST NUMBER: P1428091

CATALOG NUMBER: SQ2W-PP3-K-100U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1590.4	1590.4	1590.4	1590.4	1590.4	1590.4	1590.4	1590.4	1590.4	1590.4	1590.4
2.5°	1589.4	1588.2	1587.0	1589.7	1596.2	1598.6	1588.5	1578.3	1588.5	1598.6	1596.2
5°	1590.0	1587.6	1586.1	1588.7	1595.4	1597.3	1584.6	1571.9	1584.6	1597.3	1595.4
7.5°	1587.6	1584.1	1581.6	1583.6	1590.2	1591.9	1578.9	1565.9	1578.9	1591.9	1590.2
10°	1583.3	1579.2	1575.5	1576.6	1582.6	1584.2	1573.0	1561.8	1573.0	1584.2	1582.6
12.5°	1573.7	1568.9	1563.9	1564.2	1569.6	1570.9	1560.3	1549.7	1560.3	1570.9	1569.6
15°	1559.4	1553.4	1546.7	1544.8	1547.8	1547.6	1537.9	1528.2	1537.9	1547.6	1547.8
17.5°	1547.3	1539.2	1529.6	1525.0	1525.3	1522.6	1510.7	1498.9	1510.7	1522.6	1525.3
20°	1540.2	1529.3	1517.4	1510.6	1509.1	1504.5	1490.3	1476.1	1490.3	1504.5	1509.1
22.5°	1538.8	1522.1	1504.2	1493.9	1491.2	1485.0	1468.5	1451.9	1468.5	1485.0	1491.2
25°	1539.8	1515.3	1489.2	1470.8	1460.4	1448.4	1432.0	1415.6	1432.0	1448.4	1460.4
27.5°	1529.4	1503.4	1474.0	1448.3	1426.3	1405.8	1389.5	1373.2	1389.5	1405.8	1426.3
30°	1511.6	1485.0	1454.4	1426.0	1399.9	1376.3	1360.6	1344.9	1360.6	1376.3	1399.9
32.5°	1487.1	1459.0	1426.0	1395.5	1367.6	1342.6	1326.3	1310.0	1326.3	1342.6	1367.6
35°	1444.3	1416.7	1382.3	1348.3	1314.7	1285.5	1269.9	1254.2	1269.9	1285.5	1314.7
37.5°	1358.2	1343.6	1324.3	1295.9	1258.2	1225.5	1207.7	1189.9	1207.7	1225.5	1258.2
40°	1280.3	1279.9	1276.2	1256.4	1220.5	1187.8	1164.7	1141.5	1164.7	1187.8	1220.5
42.5°	1173.8	1195.7	1210.5	1205.3	1180.2	1153.9	1124.2	1094.5	1124.2	1153.9	1180.2
45°	945.8	1009.8	1085.3	1118.2	1108.5	1092.4	1057.3	1022.2	1057.3	1092.4	1108.5
47.5°	794.1	860.8	942.8	992.6	1010.1	1014.5	979.8	945.2	979.8	1014.5	1010.1
50°	709.6	766.6	836.1	892.1	934.7	958.5	925.6	892.7	925.6	958.5	934.7
52.5°	626.4	679.2	739.7	798.7	856.3	892.1	862.8	833.5	862.8	892.1	856.3
55°	487.2	547.5	618.5	683.5	742.5	781.8	761.6	741.4	761.6	781.8	742.5
57.5°	363.6	434.1	517.5	582.1	628.0	658.8	644.6	630.4	644.6	658.8	628.0
60°	300.4	365.9	448.1	509.8	550.9	578.9	567.7	556.5	567.7	578.9	550.9
62.5°	262.6	314.8	382.7	437.7	480.0	509.2	499.2	489.2	499.2	509.2	480.0
65°	225.1	256.7	298.5	341.5	385.6	416.2	406.5	396.8	406.5	416.2	385.6
67.5°	196.5	212.8	234.4	266.1	308.1	336.9	326.3	315.7	326.3	336.9	308.1
70°	176.2	185.5	197.4	223.2	262.8	289.7	278.5	267.3	278.5	289.7	262.8
72.5°	154.8	160.8	168.6	189.9	224.7	248.2	237.6	227.0	237.6	248.2	224.7
75°	124.2	127.2	130.9	145.5	170.9	187.9	179.7	171.5	179.7	187.9	170.9
77.5°	94.3	95.9	97.9	107.1	123.7	134.9	129.6	124.4	129.6	134.9	123.7
80°	75.5	76.2	77.0	82.9	94.1	102.0	99.8	97.5	99.8	102.0	94.1
82.5°	56.5	57.4	58.1	61.4	67.2	71.8	72.6	73.3	72.6	71.8	67.2
85°	24.7	27.5	30.4	32.7	34.2	35.7	37.2	38.7	37.2	35.7	34.2
87.5°	10.6	10.7	11.3	12.8	14.9	15.8	14.3	13.0	14.3	15.5	15.5
90°	32.7	31.2	31.2	29.6	24.9	18.7	10.9	4.7	10.9	17.1	28.1
92.5°	39.0	38.7	36.2	33.4	27.4	27.4	27.1	17.1	29.6	42.1	60.5
95°	35.9	35.9	42.1	53.0	77.9	79.5	53.0	48.3	68.6	96.6	121.6
97.5°	97.0	115.3	141.5	146.5	138.7	103.5	99.1	92.3	125.6	153.4	193.6
100°	179.3	202.6	221.3	183.9	145.0	143.4	134.1	130.9	166.8	193.3	232.3
102.5°	280.3	287.4	222.6	201.4	192.4	185.8	171.5	169.6	205.4	241.9	274.7
105°	304.0	272.8	274.3	274.3	268.1	255.6	229.1	227.6	268.1	310.2	350.7
107.5°	357.6	362.3	370.4	368.5	361.3	328.0	296.8	289.6	326.1	376.6	421.2
110°	428.7	433.3	436.5	433.3	422.4	380.3	342.9	332.0	364.8	417.8	466.1



TEST NUMBER: P1428091

CATALOG NUMBER: SQ2W-PP3-K-100U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	497.2	500.7	507.5	498.2	479.8	431.5	389.1	373.2	405.9	460.2	509.7
115°	606.4	606.4	607.9	603.2	565.8	516.0	459.8	436.5	464.5	514.4	569.0
117.5°	713.6	715.5	709.2	696.8	653.4	595.5	532.5	495.1	517.2	569.9	626.0
120°	780.9	784.1	777.8	759.1	717.0	651.6	579.9	536.2	553.4	604.8	660.9
122.5°	850.8	850.2	842.7	821.5	771.9	703.9	633.5	579.9	587.0	634.7	689.6
125°	947.7	946.2	939.9	915.0	863.6	793.4	710.8	645.3	636.0	676.5	732.6
127.5°	1040.0	1036.6	1026.9	996.7	944.0	876.3	785.6	711.4	690.5	716.1	767.5
130°	1103.6	1098.9	1081.8	1049.1	997.6	933.7	841.7	757.6	727.9	743.5	788.7
132.5°	1164.7	1151.3	1136.7	1101.4	1053.7	987.3	894.1	806.2	765.4	772.2	807.4
135°	1242.3	1229.9	1211.2	1176.9	1131.7	1066.2	972.7	877.6	821.5	815.2	835.5
137.5°	1310.6	1297.5	1276.3	1246.7	1201.2	1142.9	1053.1	952.7	882.0	861.1	868.9
140°	1353.0	1337.4	1318.7	1289.1	1248.6	1187.8	1100.5	1003.9	924.4	894.7	890.1
142.5°	1387.9	1376.1	1356.1	1329.0	1293.5	1232.7	1147.9	1052.5	968.0	929.7	918.7
145°	1440.3	1431.0	1409.1	1384.2	1354.6	1293.8	1215.8	1120.8	1036.6	986.7	963.3
147.5°	1484.6	1477.1	1459.9	1430.6	1405.7	1347.4	1276.3	1192.2	1105.8	1044.1	1013.8
150°	1512.0	1505.8	1488.6	1460.6	1435.6	1381.1	1312.5	1234.6	1151.9	1086.5	1047.5
152.5°	1538.2	1532.0	1512.3	1484.3	1463.1	1412.3	1349.9	1275.7	1191.8	1126.4	1086.2
155°	1572.8	1565.0	1546.3	1519.8	1501.1	1454.3	1396.7	1331.2	1259.5	1190.9	1145.7
157.5°	1600.2	1590.6	1573.1	1550.4	1530.4	1487.4	1437.2	1380.8	1318.1	1252.6	1206.5
160°	1616.5	1605.5	1586.8	1566.6	1547.9	1507.3	1462.1	1410.7	1353.0	1293.8	1243.9
162.5°	1627.7	1618.0	1595.6	1577.8	1561.6	1524.8	1482.1	1435.6	1384.2	1332.4	1286.3
165°	1639.8	1628.9	1605.5	1591.5	1577.5	1546.3	1508.9	1471.5	1427.8	1385.8	1348.3
167.5°	1640.8	1631.7	1608.3	1594.6	1584.3	1557.5	1527.3	1498.6	1464.6	1431.6	1400.4
170°	1638.3	1630.5	1607.1	1594.6	1586.8	1565.0	1538.5	1513.6	1487.1	1459.0	1434.1
172.5°	1629.5	1621.8	1599.6	1589.6	1585.6	1566.3	1544.7	1526.0	1503.3	1482.7	1462.8
175°	1607.1	1600.9	1582.2	1575.9	1577.5	1565.0	1549.4	1538.5	1524.5	1512.0	1501.1
177.5°	1574.4	1570.6	1556.9	1556.9	1561.9	1554.4	1549.4	1544.4	1538.2	1534.5	1530.7
180°	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2



TEST NUMBER: P1428091

CATALOG NUMBER: SQ2W-PP3-K-100U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1590.4	1590.4	1590.4	1590.4	1590.4	1590.4	1590.4	1590.4	1590.4	1590.4	1590.4
2.5°	1589.7	1587.0	1588.2	1589.4	1590.5	1591.7	1590.5	1589.4	1588.2	1587.0	1589.7
5°	1588.7	1586.1	1587.6	1590.0	1595.3	1600.5	1595.3	1590.0	1587.6	1586.1	1588.7
7.5°	1583.6	1581.6	1584.1	1587.6	1594.1	1600.5	1594.1	1587.6	1584.1	1581.6	1583.6
10°	1576.6	1575.5	1579.2	1583.3	1588.5	1593.8	1588.5	1583.3	1579.2	1575.5	1576.6
12.5°	1564.2	1563.9	1568.9	1573.7	1578.4	1583.0	1578.4	1573.7	1568.9	1563.9	1564.2
15°	1544.8	1546.7	1553.4	1559.4	1563.1	1566.9	1563.1	1559.4	1553.4	1546.7	1544.8
17.5°	1525.0	1529.6	1539.2	1547.3	1551.2	1555.1	1551.2	1547.3	1539.2	1529.6	1525.0
20°	1510.6	1517.4	1529.3	1540.2	1547.6	1555.1	1547.6	1540.2	1529.3	1517.4	1510.6
22.5°	1493.9	1504.2	1522.1	1538.8	1551.7	1564.5	1551.7	1538.8	1522.1	1504.2	1493.9
25°	1470.8	1489.2	1515.3	1539.8	1559.2	1578.6	1559.2	1539.8	1515.3	1489.2	1470.8
27.5°	1448.3	1474.0	1503.4	1529.4	1544.7	1560.1	1544.7	1529.4	1503.4	1474.0	1448.3
30°	1426.0	1454.4	1485.0	1511.6	1525.8	1540.0	1525.8	1511.6	1485.0	1454.4	1426.0
32.5°	1395.5	1426.0	1459.0	1487.1	1500.1	1513.1	1500.1	1487.1	1459.0	1426.0	1395.5
35°	1348.3	1382.3	1416.7	1444.3	1451.8	1459.3	1451.8	1444.3	1416.7	1382.3	1348.3
37.5°	1295.9	1324.3	1343.6	1358.2	1358.6	1359.1	1358.6	1358.2	1343.6	1324.3	1295.9
40°	1256.4	1276.2	1279.9	1280.3	1270.6	1260.9	1270.6	1280.3	1279.9	1276.2	1256.4
42.5°	1205.3	1210.5	1195.7	1173.8	1130.6	1087.4	1130.6	1173.8	1195.7	1210.5	1205.3
45°	1118.2	1085.3	1009.8	945.8	915.9	886.0	915.9	945.8	1009.8	1085.3	1118.2
47.5°	992.6	942.8	860.8	794.1	773.5	752.8	773.5	794.1	860.8	942.8	992.6
50°	892.1	836.1	766.6	709.6	690.2	670.8	690.2	709.6	766.6	836.1	892.1
52.5°	798.7	739.7	679.2	626.4	596.8	567.2	596.8	626.4	679.2	739.7	798.7
55°	683.5	618.5	547.5	487.2	458.8	430.4	458.8	487.2	547.5	618.5	683.5
57.5°	582.1	517.5	434.1	363.6	331.8	299.9	331.8	363.6	434.1	517.5	582.1
60°	509.8	448.1	365.9	300.4	284.7	269.0	284.7	300.4	365.9	448.1	509.8
62.5°	437.7	382.7	314.8	262.6	257.0	251.5	257.0	262.6	314.8	382.7	437.7
65°	341.5	298.5	256.7	225.1	224.3	223.6	224.3	225.1	256.7	298.5	341.5
67.5°	266.1	234.4	212.8	196.5	195.6	194.7	195.6	196.5	212.8	234.4	266.1
70°	223.2	197.4	185.5	176.2	174.7	173.2	174.7	176.2	185.5	197.4	223.2
72.5°	189.9	168.6	160.8	154.8	153.9	153.0	153.9	154.8	160.8	168.6	189.9
75°	145.5	130.9	127.2	124.2	123.5	122.7	123.5	124.2	127.2	130.9	145.5
77.5°	107.1	97.9	95.9	94.3	93.5	92.8	93.5	94.3	95.9	97.9	107.1
80°	82.9	77.0	76.2	75.5	74.7	74.0	74.7	75.5	76.2	77.0	82.9
82.5°	61.4	58.1	57.4	56.5	55.1	53.8	55.1	56.5	57.4	58.1	61.4
85°	32.7	30.4	27.5	24.7	22.4	20.2	22.4	24.7	27.5	30.4	32.7
87.5°	14.0	14.4	16.0	16.8	18.1	17.4	18.1	16.8	16.0	14.4	14.0
90°	35.9	46.8	57.7	63.9	70.1	67.0	70.1	63.9	57.7	46.8	35.9
92.5°	72.0	90.4	103.8	115.0	120.0	119.4	120.0	115.0	103.8	90.4	72.0
95°	145.0	166.8	188.6	204.2	213.6	210.4	213.6	204.2	188.6	166.8	145.0
97.5°	223.5	252.8	277.2	291.8	301.2	307.4	301.2	291.8	277.2	252.8	223.5
100°	275.9	304.0	332.0	349.2	364.8	371.0	364.8	349.2	332.0	304.0	275.9
102.5°	318.3	355.1	385.6	404.0	417.1	423.4	417.1	404.0	385.6	355.1	318.3
105°	388.1	427.1	459.8	483.2	497.2	501.9	497.2	483.2	459.8	427.1	388.1
107.5°	458.0	498.2	528.4	554.3	571.4	581.4	571.4	554.3	528.4	498.2	458.0
110°	512.8	545.6	578.3	601.7	618.8	625.1	618.8	601.7	578.3	545.6	512.8



TEST NUMBER: P1428091

CATALOG NUMBER: SQ2W-PP3-K-100U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	559.0	595.5	628.2	651.6	671.2	679.9	671.2	651.6	628.2	595.5	559.0
115°	623.5	671.8	701.4	723.3	737.3	745.1	737.3	723.3	701.4	671.8	623.5
117.5°	677.1	727.6	760.1	776.9	783.4	789.1	783.4	776.9	760.1	727.6	677.1
120°	710.8	757.6	795.0	816.8	824.6	827.7	824.6	816.8	795.0	757.6	710.8
122.5°	742.0	786.2	822.4	849.2	862.0	865.1	862.0	849.2	822.4	786.2	742.0
125°	785.6	827.7	865.1	891.6	905.6	913.4	905.6	891.6	865.1	827.7	785.6
127.5°	823.7	869.2	903.5	927.5	941.2	947.4	941.2	927.5	903.5	869.2	823.7
130°	844.9	891.6	925.9	952.4	964.9	971.1	964.9	952.4	925.9	891.6	844.9
132.5°	861.1	910.3	945.9	969.9	983.6	989.8	983.6	969.9	945.9	910.3	861.1
135°	880.7	932.1	969.6	992.9	1005.4	1011.6	1005.4	992.9	969.6	932.1	880.7
137.5°	897.9	944.6	983.6	1008.2	1019.4	1023.5	1019.4	1008.2	983.6	944.6	897.9
140°	910.3	950.9	989.8	1013.2	1025.7	1027.2	1025.7	1013.2	989.8	950.9	910.3
142.5°	926.5	958.3	992.3	1015.7	1028.2	1031.0	1028.2	1015.7	992.3	958.3	926.5
145°	955.5	974.2	997.6	1019.4	1030.4	1033.5	1030.4	1019.4	997.6	974.2	955.5
147.5°	992.0	997.9	1010.1	1024.4	1035.0	1037.2	1035.0	1024.4	1010.1	997.9	992.0
150°	1019.4	1017.9	1022.6	1031.9	1041.3	1039.7	1041.3	1031.9	1022.6	1017.9	1019.4
152.5°	1050.6	1041.6	1041.3	1045.6	1050.0	1049.7	1050.0	1045.6	1041.3	1041.6	1050.6
155°	1103.6	1086.5	1077.1	1074.0	1074.0	1072.4	1074.0	1074.0	1077.1	1086.5	1103.6
157.5°	1161.9	1137.9	1123.9	1116.4	1114.2	1110.8	1114.2	1116.4	1123.9	1137.9	1161.9
160°	1201.8	1175.3	1161.3	1148.8	1144.1	1139.5	1144.1	1148.8	1161.3	1175.3	1201.8
162.5°	1239.2	1214.0	1198.7	1187.5	1182.8	1175.6	1182.8	1187.5	1198.7	1214.0	1239.2
165°	1300.0	1273.5	1256.4	1247.0	1240.8	1234.6	1240.8	1247.0	1256.4	1273.5	1300.0
167.5°	1360.8	1331.8	1320.6	1310.0	1304.1	1292.8	1304.1	1310.0	1320.6	1331.8	1360.8
170°	1398.2	1371.7	1365.5	1356.1	1345.2	1332.8	1345.2	1356.1	1365.5	1371.7	1398.2
172.5°	1430.6	1412.9	1406.6	1397.3	1393.9	1383.9	1393.9	1397.3	1406.6	1412.9	1430.6
175°	1477.7	1463.7	1463.7	1462.1	1457.5	1448.1	1457.5	1462.1	1463.7	1463.7	1477.7
177.5°	1517.0	1509.5	1514.5	1514.5	1513.3	1504.5	1513.3	1514.5	1514.5	1509.5	1517.0
180°	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2	1543.2



TEST NUMBER: P1428091

CATALOG NUMBER: SQ2W-PP3-K-100U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1590.4	1590.4	1590.4	1590.4
2.5°	1596.2	1598.6	1588.5	1578.3
5°	1595.4	1597.3	1584.6	1571.9
7.5°	1590.2	1591.9	1578.9	1565.9
10°	1582.6	1584.2	1573.0	1561.8
12.5°	1569.6	1570.9	1560.3	1549.7
15°	1547.8	1547.6	1537.9	1528.2
17.5°	1525.3	1522.6	1510.7	1498.9
20°	1509.1	1504.5	1490.3	1476.1
22.5°	1491.2	1485.0	1468.5	1451.9
25°	1460.4	1448.4	1432.0	1415.6
27.5°	1426.3	1405.8	1389.5	1373.2
30°	1399.9	1376.3	1360.6	1344.9
32.5°	1367.6	1342.6	1326.3	1310.0
35°	1314.7	1285.5	1269.9	1254.2
37.5°	1258.2	1225.5	1207.7	1189.9
40°	1220.5	1187.8	1164.7	1141.5
42.5°	1180.2	1153.9	1124.2	1094.5
45°	1108.5	1092.4	1057.3	1022.2
47.5°	1010.1	1014.5	979.8	945.2
50°	934.7	958.5	925.6	892.7
52.5°	856.3	892.1	862.8	833.5
55°	742.5	781.8	761.6	741.4
57.5°	628.0	658.8	644.6	630.4
60°	550.9	578.9	567.7	556.5
62.5°	480.0	509.2	499.2	489.2
65°	385.6	416.2	406.5	396.8
67.5°	308.1	336.9	326.3	315.7
70°	262.8	289.7	278.5	267.3
72.5°	224.7	248.2	237.6	227.0
75°	170.9	187.9	179.7	171.5
77.5°	123.7	134.9	129.6	124.4
80°	94.1	102.0	99.8	97.5
82.5°	67.2	71.8	72.6	73.3
85°	34.2	35.7	37.2	38.7
87.5°	15.5	15.5	14.3	13.0
90°	28.1	17.1	10.9	4.7
92.5°	60.5	42.1	29.6	17.1
95°	121.6	96.6	68.6	48.3
97.5°	193.6	153.4	125.6	92.3
100°	232.3	193.3	166.8	130.9
102.5°	274.7	241.9	205.4	169.6
105°	350.7	310.2	268.1	227.6
107.5°	421.2	376.6	326.1	289.6
110°	466.1	417.8	364.8	332.0



TEST NUMBER: P1428091

CATALOG NUMBER: SQ2W-PP3-K-100U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	509.7	460.2	405.9	373.2
115°	569.0	514.4	464.5	436.5
117.5°	626.0	569.9	517.2	495.1
120°	660.9	604.8	553.4	536.2
122.5°	689.6	634.7	587.0	579.9
125°	732.6	676.5	636.0	645.3
127.5°	767.5	716.1	690.5	711.4
130°	788.7	743.5	727.9	757.6
132.5°	807.4	772.2	765.4	806.2
135°	835.5	815.2	821.5	877.6
137.5°	868.9	861.1	882.0	952.7
140°	890.1	894.7	924.4	1003.9
142.5°	918.7	929.7	968.0	1052.5
145°	963.3	986.7	1036.6	1120.8
147.5°	1013.8	1044.1	1105.8	1192.2
150°	1047.5	1086.5	1151.9	1234.6
152.5°	1086.2	1126.4	1191.8	1275.7
155°	1145.7	1190.9	1259.5	1331.2
157.5°	1206.5	1252.6	1318.1	1380.8
160°	1243.9	1293.8	1353.0	1410.7
162.5°	1286.3	1332.4	1384.2	1435.6
165°	1348.3	1385.8	1427.8	1471.5
167.5°	1400.4	1431.6	1464.6	1498.6
170°	1434.1	1459.0	1487.1	1513.6
172.5°	1462.8	1482.7	1503.3	1526.0
175°	1501.1	1512.0	1524.5	1538.5
177.5°	1530.7	1534.5	1538.2	1544.4
180°	1543.2	1543.2	1543.2	1543.2

TEST NUMBER: P1428091
 CATALOG NUMBER: SQ2W-PP3-K-100U-075D-L840-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.45	19.26	19.44	20.25	21.57	14.22	15.03	15.21	16.03	17.34
	3H	19.51	20.23	20.51	21.23	22.57	15.53	16.25	16.53	17.25	18.59
	4H	19.87	20.56	20.89	21.56	22.91	16.08	16.76	17.10	17.77	19.12
	6H	20.06	20.69	21.09	21.70	23.06	16.44	17.07	17.47	18.08	19.44
	8H	20.13	20.72	21.15	21.75	23.10	16.57	17.17	17.60	18.20	19.55
	12H	20.14	20.71	21.18	21.73	23.11	16.60	17.17	17.64	18.19	19.57
4H	2H	18.56	19.24	19.58	20.25	21.60	15.13	15.81	16.14	16.82	18.16
	3H	19.85	20.42	20.88	21.45	22.81	16.54	17.11	17.57	18.15	19.50
	4H	20.36	20.87	21.39	21.90	23.28	17.16	17.68	18.20	18.71	20.09
	6H	20.67	21.11	21.72	22.17	23.54	17.61	18.05	18.65	19.10	20.48
	8H	20.78	21.19	21.82	22.24	23.63	17.77	18.19	18.82	19.23	20.62
	12H	20.82	21.19	21.88	22.25	23.65	17.82	18.19	18.88	19.25	20.65
8H	4H	20.37	20.79	21.42	21.83	23.22	17.47	17.88	18.51	18.93	20.32
	6H	20.78	21.13	21.85	22.21	23.60	18.02	18.37	19.09	19.45	20.84
	8H	20.96	21.26	22.04	22.34	23.74	18.27	18.57	19.35	19.65	21.05
	12H	21.06	21.32	22.14	22.39	23.84	18.37	18.64	19.45	19.70	21.15
12H	4H	20.33	20.70	21.39	21.76	23.16	17.48	17.85	18.54	18.91	20.31
	6H	20.78	21.08	21.85	22.15	23.56	18.09	18.39	19.17	19.46	20.87
	8H	20.97	21.24	22.05	22.30	23.75	18.36	18.63	19.44	19.69	21.14