

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428121

Luminaire Tested: SQ2W-PP3-K-125U-100D-L840-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1428121  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-PP3-K-125U-100D-L840-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - PERCEIVE PRISM LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 11106.1 lumens  
Efficiency: N/A  
Efficacy: 136.1 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.41 / 1.4  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 81.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1428121

CATALOG NUMBER: SQ2W-PP3-K-125U-100D-L840-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1428121

CATALOG NUMBER: SQ2W-PP3-K-125U-100D-L840-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49				
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	49	48	47	42				
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41	36				
3	82	73	66	60	75	68	61	56	57	53	49	48	45	42	39	37	35	31				
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	35	33	30	27				
5	69	58	50	44	64	54	47	42	46	41	36	39	35	32	32	29	27	24				
6	64	52	44	38	59	48	41	36	41	36	32	35	31	28	29	26	24	21				
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	27	23	21	18				
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	17				
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	23	19	17	15				
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	16	14				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	34524	34524	34524	34524
5°	34252	34876	34252	34876
10°	34427	35130	34427	35130
15°	34345	35214	34345	35214
20°	34099	35924	34099	35924
25°	33905	37812	33905	37812
30°	33713	38601	33713	38601
35°	33235	38671	33235	38671
40°	32348	35731	32348	35731
45°	31380	27199	31380	27199
50°	30149	22654	30149	22654
55°	28059	16290	28059	16290
60°	24160	11680	24160	11680
65°	20378	11484	20378	11484
70°	16966	10990	16966	10990
75°	14385	10293	14385	10293
80°	12189	9251	12189	9251
85°	9633	5020	9633	5020

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 40°  
 Vertical Angle: 45°  
 Luminance: 34328 cd/sqm



TEST NUMBER: P1428121

CATALOG NUMBER: SQ2W-PP3-K-125U-100D-L840-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	203.6	1.8
10°-20°	589.3	5.3
20°-30°	923.2	8.3
30°-40°	1138.8	10.3
40°-50°	1072.1	9.7
50°-60°	759.2	6.8
60°-70°	432.6	3.9
70°-80°	214.1	1.9
80°-90°	60.4	0.5
90°-100°	155.7	1.4
100°-110°	454.1	4.1
110°-120°	741.1	6.7
120°-130°	940.4	8.5
130°-140°	1006.2	9.1
140°-150°	939.6	8.5
150°-160°	773.1	7.0
160°-170°	518.5	4.7
170°-180°	184.1	1.7
0°-30°	1716.1	15.5
0°-40°	2854.9	25.7
0°-60°	4686.2	42.2
0°-90°	5393.4	48.6
90°-120°	1350.9	12.2
90°-150°	4237.0	38.2
90°-180°	5713.0	51.4
0°-180°	11106.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	2138	2138	2138	2138	2138	
5°	2113	2152	2113	2152	2113	201
15°	2055	2107	2055	2107	2055	579
25°	1903	2122	1903	2122	1903	877
35°	1686	1962	1686	1962	1686	1052
45°	1374	1191	1374	1191	1374	1058
55°	997	579	997	579	997	879
65°	533	301	533	301	533	536
75°	231	165	231	165	231	250
85°	52	27	52	27	52	61
90°	6	44	6	85	6	7
95°	61	46	61	267	61	74
105°	288	462	288	636	288	307
115°	553	767	553	945	553	545
125°	818	1215	818	1158	818	732
135°	1113	1591	1113	1283	1113	860
145°	1421	1834	1421	1310	1421	889
155°	1688	1992	1688	1360	1688	776
165°	1866	2077	1866	1565	1866	525
175°	1951	2034	1951	1836	1951	185
180°	1956	1956	1956	1956	1956	



TEST NUMBER: P1428121

CATALOG NUMBER: SQ2W-PP3-K-125U-100D-L840-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2138.3	2138.3	2138.3	2138.3	2138.3	2138.3	2138.3	2138.3	2138.3	2138.3	2138.3
2.5°	2122.0	2135.7	2149.4	2146.1	2137.3	2133.7	2135.3	2136.9	2138.5	2140.1	2138.5
5°	2113.4	2130.5	2147.6	2145.1	2136.1	2132.5	2134.5	2137.8	2144.8	2151.9	2144.8
7.5°	2105.3	2122.8	2140.3	2138.0	2129.2	2126.5	2129.9	2134.6	2143.2	2151.9	2143.2
10°	2099.9	2115.0	2130.0	2127.8	2119.7	2118.2	2123.2	2128.8	2135.8	2142.8	2135.8
12.5°	2083.6	2097.9	2112.1	2110.3	2103.0	2102.7	2109.4	2115.9	2122.1	2128.4	2122.1
15°	2054.7	2067.7	2080.8	2081.0	2077.0	2079.5	2088.6	2096.6	2101.6	2106.7	2101.6
17.5°	2015.3	2031.2	2047.1	2050.8	2050.4	2056.6	2069.4	2080.4	2085.6	2090.8	2085.6
20°	1984.6	2003.7	2022.8	2029.1	2031.1	2040.1	2056.2	2070.8	2080.8	2090.8	2080.8
22.5°	1952.1	1974.4	1996.7	2004.9	2008.6	2022.4	2046.5	2068.9	2086.2	2103.5	2086.2
25°	1903.2	1925.3	1947.4	1963.5	1977.6	2002.2	2037.3	2070.2	2096.4	2122.5	2096.4
27.5°	1846.3	1868.2	1890.1	1917.7	1947.2	1981.8	2021.4	2056.2	2076.9	2097.6	2076.9
30°	1808.3	1829.4	1850.5	1882.1	1917.3	1955.5	1996.7	2032.3	2051.4	2070.5	2051.4
32.5°	1761.3	1783.2	1805.1	1838.7	1876.3	1917.3	1961.7	1999.4	2016.9	2034.3	2016.9
35°	1686.2	1707.3	1728.4	1767.6	1812.8	1858.5	1904.7	1941.9	1952.0	1962.0	1952.0
37.5°	1599.9	1623.8	1647.7	1691.7	1742.3	1780.6	1806.5	1826.1	1826.7	1827.3	1826.7
40°	1534.8	1565.9	1597.1	1641.0	1689.3	1715.9	1720.9	1721.4	1708.3	1695.3	1708.3
42.5°	1471.5	1511.5	1551.5	1586.8	1620.5	1627.5	1607.6	1578.1	1520.1	1462.0	1520.1
45°	1374.3	1421.5	1468.7	1490.3	1503.4	1459.2	1357.7	1271.6	1231.4	1191.2	1231.4
47.5°	1270.8	1317.4	1364.0	1358.0	1334.5	1267.6	1157.3	1067.6	1039.9	1012.2	1039.9
50°	1200.3	1244.5	1288.7	1256.8	1199.5	1124.2	1030.7	954.1	928.0	901.9	928.0
52.5°	1120.7	1160.1	1199.5	1151.3	1073.9	994.6	913.2	842.2	802.4	762.6	802.4
55°	996.8	1023.9	1051.1	998.3	919.0	831.6	736.1	655.0	616.8	578.7	616.8
57.5°	847.6	866.7	885.8	844.3	782.6	695.7	583.6	488.8	446.0	403.3	446.0
60°	748.2	763.3	778.3	740.6	685.4	602.5	492.0	403.9	382.8	361.7	382.8
62.5°	657.8	671.2	684.7	645.4	588.6	514.5	423.3	353.0	345.6	338.2	345.6
65°	533.4	546.5	559.6	518.4	459.1	401.3	345.1	302.6	301.6	300.6	301.6
67.5°	424.5	438.8	453.0	414.3	357.8	315.1	286.2	264.2	263.0	261.8	263.0
70°	359.4	374.5	389.5	353.4	300.1	265.5	249.4	236.8	234.8	232.8	234.8
72.5°	305.2	319.4	333.7	302.1	255.3	226.7	216.2	208.1	206.9	205.7	206.9
75°	230.6	241.6	252.7	229.8	195.6	176.1	171.0	167.0	166.0	165.0	166.0
77.5°	167.3	174.3	181.3	166.4	144.1	131.6	129.0	126.8	125.8	124.8	125.8
80°	131.1	134.1	137.1	126.6	111.5	103.5	102.5	101.5	100.5	99.5	100.5
82.5°	98.6	97.5	96.5	90.4	82.6	78.2	77.2	75.9	74.1	72.3	74.1
85°	52.0	50.0	48.0	46.0	44.0	40.9	36.9	33.2	30.1	27.1	30.1
87.5°	17.5	19.0	21.0	19.6	16.8	14.7	13.9	13.7	14.1	14.1	14.1
90°	5.9	13.8	23.7	31.6	37.5	39.5	39.5	41.5	43.5	43.5	43.5
92.5°	21.7	34.4	34.8	34.8	42.3	45.9	49.0	49.4	51.4	51.4	51.4
95°	61.3	67.2	100.8	98.8	67.2	53.4	45.5	45.5	45.5	45.5	45.5
97.5°	117.0	125.7	131.2	175.9	185.8	179.4	146.2	122.9	109.9	104.0	109.9
100°	166.0	170.0	181.8	183.8	233.2	280.6	256.9	227.3	217.4	211.5	217.4
102.5°	215.0	217.4	235.6	243.9	255.3	282.2	364.4	355.3	348.6	347.4	348.6
105°	288.5	290.5	324.1	339.9	347.8	347.8	345.9	385.4	448.6	462.5	448.6
107.5°	367.2	376.3	415.8	458.1	467.2	469.6	459.3	453.4	451.0	452.6	451.0
110°	421.0	434.8	482.2	535.6	549.4	553.4	549.4	543.5	539.5	539.5	539.5

TEST NUMBER: P1428121

CATALOG NUMBER: SQ2W-PP3-K-125U-100D-L840-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	473.1	493.3	547.0	608.3	631.6	643.5	634.8	630.4	626.5	629.7	626.5
115°	553.4	583.0	654.2	717.4	764.8	770.8	768.8	768.8	766.8	766.8	766.8
117.5°	627.7	675.1	754.9	828.5	883.4	899.2	907.1	904.8	902.4	906.3	902.4
120°	679.8	735.2	826.1	909.1	962.5	986.2	994.1	990.1	994.1	990.1	994.1
122.5°	735.2	803.2	892.5	978.7	1041.5	1068.4	1077.9	1078.7	1079.5	1077.1	1079.5
125°	818.2	901.2	1005.9	1094.9	1160.1	1191.7	1199.6	1201.6	1205.5	1215.4	1205.5
127.5°	902.0	996.1	1111.1	1196.9	1263.7	1302.0	1314.2	1318.6	1326.9	1331.2	1326.9
130°	960.5	1067.2	1183.8	1264.8	1330.1	1371.6	1393.3	1399.2	1409.1	1407.1	1409.1
132.5°	1022.1	1133.6	1251.8	1336.0	1396.5	1441.1	1459.7	1476.7	1480.3	1483.0	1480.3
135°	1112.7	1233.2	1351.8	1434.8	1492.1	1535.6	1559.3	1575.1	1585.0	1590.9	1585.0
137.5°	1207.9	1335.2	1449.0	1522.9	1580.7	1618.2	1645.1	1661.7	1672.0	1676.7	1672.0
140°	1272.7	1395.3	1505.9	1583.0	1634.4	1672.0	1695.7	1715.4	1727.3	1727.3	1727.3
142.5°	1334.4	1455.4	1562.9	1639.9	1685.0	1719.4	1744.7	1759.7	1773.1	1773.1	1773.1
145°	1421.0	1541.5	1640.3	1717.4	1755.0	1786.6	1814.3	1826.1	1834.0	1834.0	1834.0
147.5°	1511.5	1618.2	1708.3	1782.2	1813.9	1851.0	1872.7	1882.2	1892.1	1887.8	1892.1
150°	1565.2	1664.1	1751.0	1820.2	1851.8	1887.4	1909.1	1917.0	1926.9	1921.0	1926.9
152.5°	1617.4	1711.5	1790.5	1855.0	1881.8	1917.4	1942.3	1950.2	1956.9	1952.6	1956.9
155°	1687.8	1770.8	1843.9	1903.2	1926.9	1960.5	1984.2	1994.1	2002.0	1992.1	2002.0
157.5°	1750.6	1822.2	1885.8	1940.3	1965.6	1994.5	2016.6	2028.9	2036.8	2032.4	2036.8
160°	1788.6	1853.8	1911.1	1962.5	1986.2	2011.9	2035.6	2049.4	2057.3	2051.4	2057.3
162.5°	1820.2	1879.1	1933.2	1979.9	2000.4	2022.9	2051.4	2063.7	2071.6	2064.1	2071.6
165°	1865.6	1913.1	1960.5	2000.0	2017.8	2035.6	2065.2	2079.1	2085.0	2077.1	2085.0
167.5°	1900.0	1936.4	1974.7	2008.7	2021.8	2039.2	2068.8	2080.3	2087.8	2077.9	2087.8
170°	1919.0	1950.6	1984.2	2011.9	2021.8	2037.6	2067.2	2077.1	2083.0	2073.1	2083.0
172.5°	1934.8	1958.5	1985.8	2010.3	2015.4	2028.1	2056.2	2066.0	2070.4	2062.1	2070.4
175°	1950.6	1964.5	1984.2	2000.0	1998.0	2006.0	2029.7	2037.6	2045.5	2033.6	2045.5
177.5°	1958.1	1964.5	1970.8	1980.3	1973.9	1973.9	1991.3	1996.1	1997.7	1991.3	1997.7
180°	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5



TEST NUMBER: P1428121

CATALOG NUMBER: SQ2W-PP3-K-125U-100D-L840-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2138.3	2138.3	2138.3	2138.3	2138.3	2138.3	2138.3	2138.3	2138.3	2138.3	2138.3
2.5°	2136.9	2135.3	2133.7	2137.3	2146.1	2149.4	2135.7	2122.0	2135.7	2149.4	2146.1
5°	2137.8	2134.5	2132.5	2136.1	2145.1	2147.6	2130.5	2113.4	2130.5	2147.6	2145.1
7.5°	2134.6	2129.9	2126.5	2129.2	2138.0	2140.3	2122.8	2105.3	2122.8	2140.3	2138.0
10°	2128.8	2123.2	2118.2	2119.7	2127.8	2130.0	2115.0	2099.9	2115.0	2130.0	2127.8
12.5°	2115.9	2109.4	2102.7	2103.0	2110.3	2112.1	2097.9	2083.6	2097.9	2112.1	2110.3
15°	2096.6	2088.6	2079.5	2077.0	2081.0	2080.8	2067.7	2054.7	2067.7	2080.8	2081.0
17.5°	2080.4	2069.4	2056.6	2050.4	2050.8	2047.1	2031.2	2015.3	2031.2	2047.1	2050.8
20°	2070.8	2056.2	2040.1	2031.1	2029.1	2022.8	2003.7	1984.6	2003.7	2022.8	2029.1
22.5°	2068.9	2046.5	2022.4	2008.6	2004.9	1996.7	1974.4	1952.1	1974.4	1996.7	2004.9
25°	2070.2	2037.3	2002.2	1977.6	1963.5	1947.4	1925.3	1903.2	1925.3	1947.4	1963.5
27.5°	2056.2	2021.4	1981.8	1947.2	1917.7	1890.1	1868.2	1846.3	1868.2	1890.1	1917.7
30°	2032.3	1996.7	1955.5	1917.3	1882.1	1850.5	1829.4	1808.3	1829.4	1850.5	1882.1
32.5°	1999.4	1961.7	1917.3	1876.3	1838.7	1805.1	1783.2	1761.3	1783.2	1805.1	1838.7
35°	1941.9	1904.7	1858.5	1812.8	1767.6	1728.4	1707.3	1686.2	1707.3	1728.4	1767.6
37.5°	1826.1	1806.5	1780.6	1742.3	1691.7	1647.7	1623.8	1599.9	1623.8	1647.7	1691.7
40°	1721.4	1720.9	1715.9	1689.3	1641.0	1597.1	1565.9	1534.8	1565.9	1597.1	1641.0
42.5°	1578.1	1607.6	1627.5	1620.5	1586.8	1551.5	1511.5	1471.5	1511.5	1551.5	1586.8
45°	1271.6	1357.7	1459.2	1503.4	1490.3	1468.7	1421.5	1374.3	1421.5	1468.7	1490.3
47.5°	1067.6	1157.3	1267.6	1334.5	1358.0	1364.0	1317.4	1270.8	1317.4	1364.0	1358.0
50°	954.1	1030.7	1124.2	1199.5	1256.8	1288.7	1244.5	1200.3	1244.5	1288.7	1256.8
52.5°	842.2	913.2	994.6	1073.9	1151.3	1199.5	1160.1	1120.7	1160.1	1199.5	1151.3
55°	655.0	736.1	831.6	919.0	998.3	1051.1	1023.9	996.8	1023.9	1051.1	998.3
57.5°	488.8	583.6	695.7	782.6	844.3	885.8	866.7	847.6	866.7	885.8	844.3
60°	403.9	492.0	602.5	685.4	740.6	778.3	763.3	748.2	763.3	778.3	740.6
62.5°	353.0	423.3	514.5	588.6	645.4	684.7	671.2	657.8	671.2	684.7	645.4
65°	302.6	345.1	401.3	459.1	518.4	559.6	546.5	533.4	546.5	559.6	518.4
67.5°	264.2	286.2	315.1	357.8	414.3	453.0	438.8	424.5	438.8	453.0	414.3
70°	236.8	249.4	265.5	300.1	353.4	389.5	374.5	359.4	374.5	389.5	353.4
72.5°	208.1	216.2	226.7	255.3	302.1	333.7	319.4	305.2	319.4	333.7	302.1
75°	167.0	171.0	176.1	195.6	229.8	252.7	241.6	230.6	241.6	252.7	229.8
77.5°	126.8	129.0	131.6	144.1	166.4	181.3	174.3	167.3	174.3	181.3	166.4
80°	101.5	102.5	103.5	111.5	126.6	137.1	134.1	131.1	134.1	137.1	126.6
82.5°	75.9	77.2	78.2	82.6	90.4	96.5	97.5	98.6	97.5	96.5	90.4
85°	33.2	36.9	40.9	44.0	46.0	48.0	50.0	52.0	50.0	48.0	46.0
87.5°	13.7	13.9	14.7	16.8	19.6	21.0	19.0	17.5	19.0	20.6	20.4
90°	41.5	39.5	39.5	37.5	31.6	23.7	13.8	5.9	13.8	21.7	35.6
92.5°	49.4	49.0	45.9	42.3	34.8	34.8	34.4	21.7	37.5	53.4	76.7
95°	45.5	45.5	53.4	67.2	98.8	100.8	67.2	61.3	87.0	122.5	154.2
97.5°	122.9	146.2	179.4	185.8	175.9	131.2	125.7	117.0	159.3	194.5	245.5
100°	227.3	256.9	280.6	233.2	183.8	181.8	170.0	166.0	211.5	245.1	294.5
102.5°	355.3	364.4	282.2	255.3	243.9	235.6	217.4	215.0	260.5	306.7	348.2
105°	385.4	345.9	347.8	347.8	339.9	324.1	290.5	288.5	339.9	393.3	444.7
107.5°	453.4	459.3	469.6	467.2	458.1	415.8	376.3	367.2	413.4	477.5	534.0
110°	543.5	549.4	553.4	549.4	535.6	482.2	434.8	421.0	462.5	529.7	590.9



TEST NUMBER: P1428121

CATALOG NUMBER: SQ2W-PP3-K-125U-100D-L840-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	630.4	634.8	643.5	631.6	608.3	547.0	493.3	473.1	514.6	583.4	646.3
115°	768.8	768.8	770.8	764.8	717.4	654.2	583.0	553.4	588.9	652.2	721.4
117.5°	904.8	907.1	899.2	883.4	828.5	754.9	675.1	627.7	655.7	722.5	793.7
120°	990.1	994.1	986.2	962.5	909.1	826.1	735.2	679.8	701.6	766.8	838.0
122.5°	1078.7	1077.9	1068.4	1041.5	978.7	892.5	803.2	735.2	744.3	804.8	874.3
125°	1201.6	1199.6	1191.7	1160.1	1094.9	1005.9	901.2	818.2	806.3	857.7	928.9
127.5°	1318.6	1314.2	1302.0	1263.7	1196.9	1111.1	996.1	902.0	875.5	907.9	973.1
130°	1399.2	1393.3	1371.6	1330.1	1264.8	1183.8	1067.2	960.5	922.9	942.7	1000.0
132.5°	1476.7	1459.7	1441.1	1396.5	1336.0	1251.8	1133.6	1022.1	970.4	979.1	1023.7
135°	1575.1	1559.3	1535.6	1492.1	1434.8	1351.8	1233.2	1112.7	1041.5	1033.6	1059.3
137.5°	1661.7	1645.1	1618.2	1580.7	1522.9	1449.0	1335.2	1207.9	1118.2	1091.7	1101.6
140°	1715.4	1695.7	1672.0	1634.4	1583.0	1505.9	1395.3	1272.7	1172.0	1134.4	1128.5
142.5°	1759.7	1744.7	1719.4	1685.0	1639.9	1562.9	1455.4	1334.4	1227.3	1178.7	1164.8
145°	1826.1	1814.3	1786.6	1755.0	1717.4	1640.3	1541.5	1421.0	1314.2	1251.0	1221.4
147.5°	1882.2	1872.7	1851.0	1813.9	1782.2	1708.3	1618.2	1511.5	1402.0	1323.7	1285.4
150°	1917.0	1909.1	1887.4	1851.8	1820.2	1751.0	1664.1	1565.2	1460.5	1377.5	1328.1
152.5°	1950.2	1942.3	1917.4	1881.8	1855.0	1790.5	1711.5	1617.4	1511.1	1428.1	1377.1
155°	1994.1	1984.2	1960.5	1926.9	1903.2	1843.9	1770.8	1687.8	1596.9	1509.9	1452.6
157.5°	2028.9	2016.6	1994.5	1965.6	1940.3	1885.8	1822.2	1750.6	1671.2	1588.2	1529.7
160°	2049.4	2035.6	2011.9	1986.2	1962.5	1911.1	1853.8	1788.6	1715.4	1640.3	1577.1
162.5°	2063.7	2051.4	2022.9	2000.4	1979.9	1933.2	1879.1	1820.2	1755.0	1689.3	1630.8
165°	2079.1	2065.2	2035.6	2017.8	2000.0	1960.5	1913.1	1865.6	1810.3	1756.9	1709.5
167.5°	2080.3	2068.8	2039.2	2021.8	2008.7	1974.7	1936.4	1900.0	1856.9	1815.0	1775.5
170°	2077.1	2067.2	2037.6	2021.8	2011.9	1984.2	1950.6	1919.0	1885.4	1849.8	1818.2
172.5°	2066.0	2056.2	2028.1	2015.4	2010.3	1985.8	1958.5	1934.8	1906.0	1879.9	1854.6
175°	2037.6	2029.7	2006.0	1998.0	2000.0	1984.2	1964.5	1950.6	1932.8	1917.0	1903.2
177.5°	1996.1	1991.3	1973.9	1973.9	1980.3	1970.8	1964.5	1958.1	1950.2	1945.5	1940.7
180°	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5



TEST NUMBER: P1428121

CATALOG NUMBER: SQ2W-PP3-K-125U-100D-L840-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2138.3	2138.3	2138.3	2138.3	2138.3	2138.3	2138.3	2138.3	2138.3	2138.3	2138.3
2.5°	2137.3	2133.7	2135.3	2136.9	2138.5	2140.1	2138.5	2136.9	2135.3	2133.7	2137.3
5°	2136.1	2132.5	2134.5	2137.8	2144.8	2151.9	2144.8	2137.8	2134.5	2132.5	2136.1
7.5°	2129.2	2126.5	2129.9	2134.6	2143.2	2151.9	2143.2	2134.6	2129.9	2126.5	2129.2
10°	2119.7	2118.2	2123.2	2128.8	2135.8	2142.8	2135.8	2128.8	2123.2	2118.2	2119.7
12.5°	2103.0	2102.7	2109.4	2115.9	2122.1	2128.4	2122.1	2115.9	2109.4	2102.7	2103.0
15°	2077.0	2079.5	2088.6	2096.6	2101.6	2106.7	2101.6	2096.6	2088.6	2079.5	2077.0
17.5°	2050.4	2056.6	2069.4	2080.4	2085.6	2090.8	2085.6	2080.4	2069.4	2056.6	2050.4
20°	2031.1	2040.1	2056.2	2070.8	2080.8	2090.8	2080.8	2070.8	2056.2	2040.1	2031.1
22.5°	2008.6	2022.4	2046.5	2068.9	2086.2	2103.5	2086.2	2068.9	2046.5	2022.4	2008.6
25°	1977.6	2002.2	2037.3	2070.2	2096.4	2122.5	2096.4	2070.2	2037.3	2002.2	1977.6
27.5°	1947.2	1981.8	2021.4	2056.2	2076.9	2097.6	2076.9	2056.2	2021.4	1981.8	1947.2
30°	1917.3	1955.5	1996.7	2032.3	2051.4	2070.5	2051.4	2032.3	1996.7	1955.5	1917.3
32.5°	1876.3	1917.3	1961.7	1999.4	2016.9	2034.3	2016.9	1999.4	1961.7	1917.3	1876.3
35°	1812.8	1858.5	1904.7	1941.9	1952.0	1962.0	1952.0	1941.9	1904.7	1858.5	1812.8
37.5°	1742.3	1780.6	1806.5	1826.1	1826.7	1827.3	1826.7	1826.1	1806.5	1780.6	1742.3
40°	1689.3	1715.9	1720.9	1721.4	1708.3	1695.3	1708.3	1721.4	1720.9	1715.9	1689.3
42.5°	1620.5	1627.5	1607.6	1578.1	1520.1	1462.0	1520.1	1578.1	1607.6	1627.5	1620.5
45°	1503.4	1459.2	1357.7	1271.6	1231.4	1191.2	1231.4	1271.6	1357.7	1459.2	1503.4
47.5°	1334.5	1267.6	1157.3	1067.6	1039.9	1012.2	1039.9	1067.6	1157.3	1267.6	1334.5
50°	1199.5	1124.2	1030.7	954.1	928.0	901.9	928.0	954.1	1030.7	1124.2	1199.5
52.5°	1073.9	994.6	913.2	842.2	802.4	762.6	802.4	842.2	913.2	994.6	1073.9
55°	919.0	831.6	736.1	655.0	616.8	578.7	616.8	655.0	736.1	831.6	919.0
57.5°	782.6	695.7	583.6	488.8	446.0	403.3	446.0	488.8	583.6	695.7	782.6
60°	685.4	602.5	492.0	403.9	382.8	361.7	382.8	403.9	492.0	602.5	685.4
62.5°	588.6	514.5	423.3	353.0	345.6	338.2	345.6	353.0	423.3	514.5	588.6
65°	459.1	401.3	345.1	302.6	301.6	300.6	301.6	302.6	345.1	401.3	459.1
67.5°	357.8	315.1	286.2	264.2	263.0	261.8	263.0	264.2	286.2	315.1	357.8
70°	300.1	265.5	249.4	236.8	234.8	232.8	234.8	236.8	249.4	265.5	300.1
72.5°	255.3	226.7	216.2	208.1	206.9	205.7	206.9	208.1	216.2	226.7	255.3
75°	195.6	176.1	171.0	167.0	166.0	165.0	166.0	167.0	171.0	176.1	195.6
77.5°	144.1	131.6	129.0	126.8	125.8	124.8	125.8	126.8	129.0	131.6	144.1
80°	111.5	103.5	102.5	101.5	100.5	99.5	100.5	101.5	102.5	103.5	111.5
82.5°	82.6	78.2	77.2	75.9	74.1	72.3	74.1	75.9	77.2	78.2	82.6
85°	44.0	40.9	36.9	33.2	30.1	27.1	30.1	33.2	36.9	40.9	44.0
87.5°	18.3	18.7	20.7	21.6	23.2	22.4	23.2	21.6	20.7	18.7	18.3
90°	45.5	59.3	73.1	81.0	88.9	85.0	88.9	81.0	73.1	59.3	45.5
92.5°	91.3	114.6	131.6	145.9	152.2	151.4	152.2	145.9	131.6	114.6	91.3
95°	183.8	211.5	239.1	258.9	270.8	266.8	270.8	258.9	239.1	211.5	183.8
97.5°	283.4	320.6	351.4	370.0	381.8	389.7	381.8	370.0	351.4	320.6	283.4
100°	349.8	385.4	421.0	442.7	462.5	470.4	462.5	442.7	421.0	385.4	349.8
102.5°	403.6	450.2	488.9	512.3	528.9	536.8	528.9	512.3	488.9	450.2	403.6
105°	492.1	541.5	583.0	612.7	630.4	636.4	630.4	612.7	583.0	541.5	492.1
107.5°	580.6	631.6	670.0	702.8	724.5	737.2	724.5	702.8	670.0	631.6	580.6
110°	650.2	691.7	733.2	762.9	784.6	792.5	784.6	762.9	733.2	691.7	650.2



TEST NUMBER: P1428121

CATALOG NUMBER: SQ2W-PP3-K-125U-100D-L840-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	708.7	754.9	796.5	826.1	851.0	862.1	851.0	826.1	796.5	754.9	708.7
115°	790.5	851.8	889.3	917.0	934.8	944.7	934.8	917.0	889.3	851.8	790.5
117.5°	858.5	922.5	963.6	985.0	993.3	1000.4	993.3	985.0	963.6	922.5	858.5
120°	901.2	960.5	1007.9	1035.6	1045.5	1049.4	1045.5	1035.6	1007.9	960.5	901.2
122.5°	940.7	996.8	1042.7	1076.7	1092.9	1096.9	1092.9	1076.7	1042.7	996.8	940.7
125°	996.1	1049.4	1096.9	1130.4	1148.2	1158.1	1148.2	1130.4	1096.9	1049.4	996.1
127.5°	1044.3	1102.0	1145.5	1175.9	1193.3	1201.2	1193.3	1175.9	1145.5	1102.0	1044.3
130°	1071.2	1130.4	1173.9	1207.5	1223.3	1231.2	1223.3	1207.5	1173.9	1130.4	1071.2
132.5°	1091.7	1154.2	1199.2	1229.7	1247.1	1255.0	1247.1	1229.7	1199.2	1154.2	1091.7
135°	1116.6	1181.8	1229.3	1258.9	1274.7	1282.6	1274.7	1258.9	1229.3	1181.8	1116.6
137.5°	1138.4	1197.6	1247.1	1278.3	1292.5	1297.6	1292.5	1278.3	1247.1	1197.6	1138.4
140°	1154.2	1205.5	1255.0	1284.6	1300.4	1302.4	1300.4	1284.6	1255.0	1205.5	1154.2
142.5°	1174.7	1215.0	1258.1	1287.8	1303.6	1307.1	1303.6	1287.8	1258.1	1215.0	1174.7
145°	1211.5	1235.2	1264.8	1292.5	1306.3	1310.3	1306.3	1292.5	1264.8	1235.2	1211.5
147.5°	1257.7	1265.2	1280.6	1298.8	1312.3	1315.0	1312.3	1298.8	1280.6	1265.2	1257.7
150°	1292.5	1290.5	1296.5	1308.3	1320.2	1318.2	1320.2	1308.3	1296.5	1290.5	1292.5
152.5°	1332.0	1320.6	1320.2	1325.7	1331.2	1330.8	1331.2	1325.7	1320.2	1320.6	1332.0
155°	1399.2	1377.5	1365.6	1361.7	1361.7	1359.7	1361.7	1361.7	1365.6	1377.5	1399.2
157.5°	1473.1	1442.7	1424.9	1415.4	1412.7	1408.3	1412.7	1415.4	1424.9	1442.7	1473.1
160°	1523.7	1490.1	1472.3	1456.5	1450.6	1444.7	1450.6	1456.5	1472.3	1490.1	1523.7
162.5°	1571.2	1539.1	1519.8	1505.6	1499.6	1490.5	1499.6	1505.6	1519.8	1539.1	1571.2
165°	1648.2	1614.6	1592.9	1581.0	1573.1	1565.2	1573.1	1581.0	1592.9	1614.6	1648.2
167.5°	1725.3	1688.6	1674.3	1660.9	1653.4	1639.1	1653.4	1660.9	1674.3	1688.6	1725.3
170°	1772.7	1739.2	1731.2	1719.4	1705.6	1689.7	1705.6	1719.4	1731.2	1739.2	1772.7
172.5°	1813.9	1791.3	1783.4	1771.6	1767.2	1754.6	1767.2	1771.6	1783.4	1791.3	1813.9
175°	1873.5	1855.8	1855.8	1853.8	1847.8	1836.0	1847.8	1853.8	1855.8	1855.8	1873.5
177.5°	1923.3	1913.9	1920.2	1920.2	1918.6	1907.5	1918.6	1920.2	1920.2	1913.9	1923.3
180°	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5



TEST NUMBER: P1428121

CATALOG NUMBER: SQ2W-PP3-K-125U-100D-L840-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	2138.3	2138.3	2138.3	2138.3
2.5°	2146.1	2149.4	2135.7	2122.0
5°	2145.1	2147.6	2130.5	2113.4
7.5°	2138.0	2140.3	2122.8	2105.3
10°	2127.8	2130.0	2115.0	2099.9
12.5°	2110.3	2112.1	2097.9	2083.6
15°	2081.0	2080.8	2067.7	2054.7
17.5°	2050.8	2047.1	2031.2	2015.3
20°	2029.1	2022.8	2003.7	1984.6
22.5°	2004.9	1996.7	1974.4	1952.1
25°	1963.5	1947.4	1925.3	1903.2
27.5°	1917.7	1890.1	1868.2	1846.3
30°	1882.1	1850.5	1829.4	1808.3
32.5°	1838.7	1805.1	1783.2	1761.3
35°	1767.6	1728.4	1707.3	1686.2
37.5°	1691.7	1647.7	1623.8	1599.9
40°	1641.0	1597.1	1565.9	1534.8
42.5°	1586.8	1551.5	1511.5	1471.5
45°	1490.3	1468.7	1421.5	1374.3
47.5°	1358.0	1364.0	1317.4	1270.8
50°	1256.8	1288.7	1244.5	1200.3
52.5°	1151.3	1199.5	1160.1	1120.7
55°	998.3	1051.1	1023.9	996.8
57.5°	844.3	885.8	866.7	847.6
60°	740.6	778.3	763.3	748.2
62.5°	645.4	684.7	671.2	657.8
65°	518.4	559.6	546.5	533.4
67.5°	414.3	453.0	438.8	424.5
70°	353.4	389.5	374.5	359.4
72.5°	302.1	333.7	319.4	305.2
75°	229.8	252.7	241.6	230.6
77.5°	166.4	181.3	174.3	167.3
80°	126.6	137.1	134.1	131.1
82.5°	90.4	96.5	97.5	98.6
85°	46.0	48.0	50.0	52.0
87.5°	20.4	20.6	19.0	17.5
90°	35.6	21.7	13.8	5.9
92.5°	76.7	53.4	37.5	21.7
95°	154.2	122.5	87.0	61.3
97.5°	245.5	194.5	159.3	117.0
100°	294.5	245.1	211.5	166.0
102.5°	348.2	306.7	260.5	215.0
105°	444.7	393.3	339.9	288.5
107.5°	534.0	477.5	413.4	367.2
110°	590.9	529.7	462.5	421.0



TEST NUMBER: P1428121

CATALOG NUMBER: SQ2W-PP3-K-125U-100D-L840-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	646.3	583.4	514.6	473.1
115°	721.4	652.2	588.9	553.4
117.5°	793.7	722.5	655.7	627.7
120°	838.0	766.8	701.6	679.8
122.5°	874.3	804.8	744.3	735.2
125°	928.9	857.7	806.3	818.2
127.5°	973.1	907.9	875.5	902.0
130°	1000.0	942.7	922.9	960.5
132.5°	1023.7	979.1	970.4	1022.1
135°	1059.3	1033.6	1041.5	1112.7
137.5°	1101.6	1091.7	1118.2	1207.9
140°	1128.5	1134.4	1172.0	1272.7
142.5°	1164.8	1178.7	1227.3	1334.4
145°	1221.4	1251.0	1314.2	1421.0
147.5°	1285.4	1323.7	1402.0	1511.5
150°	1328.1	1377.5	1460.5	1565.2
152.5°	1377.1	1428.1	1511.1	1617.4
155°	1452.6	1509.9	1596.9	1687.8
157.5°	1529.7	1588.2	1671.2	1750.6
160°	1577.1	1640.3	1715.4	1788.6
162.5°	1630.8	1689.3	1755.0	1820.2
165°	1709.5	1756.9	1810.3	1865.6
167.5°	1775.5	1815.0	1856.9	1900.0
170°	1818.2	1849.8	1885.4	1919.0
172.5°	1854.6	1879.9	1906.0	1934.8
175°	1903.2	1917.0	1932.8	1950.6
177.5°	1940.7	1945.5	1950.2	1958.1
180°	1956.5	1956.5	1956.5	1956.5



TEST NUMBER: P1428121  
 CATALOG NUMBER: SQ2W-PP3-K-125U-100D-L840-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.62	20.44	20.60	21.42	22.72	15.39	16.21	16.37	17.20	18.49
	3H	20.68	21.41	21.67	22.40	23.72	16.70	17.43	17.69	18.42	19.74
	4H	21.05	21.74	22.05	22.73	24.06	17.25	17.94	18.25	18.94	20.27
	6H	21.24	21.87	22.25	22.87	24.21	17.62	18.25	18.63	19.25	20.59
	8H	21.30	21.90	22.31	22.92	24.25	17.74	18.35	18.76	19.37	20.70
	12H	21.32	21.89	22.34	22.90	24.26	17.78	18.35	18.80	19.36	20.72
4H	2H	19.73	20.43	20.74	21.42	22.75	16.30	16.99	17.30	17.98	19.31
	3H	21.03	21.60	22.04	22.62	23.96	17.72	18.29	18.73	19.31	20.65
	4H	21.53	22.05	22.55	23.07	24.44	18.33	18.86	19.36	19.88	21.24
	6H	21.84	22.29	22.88	23.34	24.69	18.78	19.23	19.81	20.27	21.63
	8H	21.95	22.37	22.99	23.41	24.78	18.95	19.37	19.98	20.40	21.77
	12H	22.00	22.37	23.05	23.42	24.80	19.00	19.37	20.05	20.42	21.80
8H	4H	21.55	21.97	22.58	23.00	24.37	18.64	19.06	19.68	20.10	21.47
	6H	21.96	22.31	23.02	23.38	24.75	19.20	19.55	20.26	20.62	21.99
	8H	22.14	22.44	23.20	23.51	24.89	19.45	19.75	20.51	20.81	22.20
	12H	22.23	22.50	23.30	23.56	24.99	19.55	19.81	20.61	20.87	22.30
12H	4H	21.51	21.88	22.56	22.93	24.31	18.65	19.03	19.70	20.08	21.46
	6H	21.95	22.26	23.02	23.32	24.71	19.26	19.57	20.33	20.63	22.02
	8H	22.15	22.41	23.21	23.47	24.90	19.54	19.81	20.61	20.86	22.30