

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1435864

Luminaire Tested: SQ2W-FA-K-150U-050D-L940-UNV-STD-W-WM-4

Issue Date: 3/24/2026

Test Information

Test Method: LM-79-2019
Report Number: P1435864
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2502-345-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/24/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-FA-K-150U-050D-L940-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - FROSTED CONTINUOUS ASYMMETRIC ROLL LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8203.8 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.23 / 1.34
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 72.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1435864

CATALOG NUMBER: SQ2W-FA-K-150U-050D-L940-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1435864

CATALOG NUMBER: SQ2W-FA-K-150U-050D-L940-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	69	69	69	51	51	51	33	33	33	25				
1	92	88	84	81	82	79	75	73	61	59	57	44	43	42	29	29	28	21				
2	84	77	71	66	75	69	64	60	53	50	47	39	37	35	26	25	24	18				
3	77	68	61	55	68	60	54	50	47	43	39	34	32	30	23	21	20	15				
4	70	60	52	46	62	53	47	42	42	37	34	31	28	25	20	19	17	13				
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15	11				
6	59	47	40	34	52	42	36	31	33	28	25	25	21	19	17	15	13	10				
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9				
8	50	38	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10	8				
9	47	35	28	23	41	31	25	21	25	20	17	19	15	13	13	11	9	7				
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8	6				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13294	13294	13294	13294
5°	13138	13758	13138	10966
10°	13081	13917	13081	9942
15°	12856	14029	12856	10989
20°	12501	13928	12501	11460
25°	11882	13815	11882	11597
30°	10947	13507	10947	11721
35°	9688	13210	9688	11511
40°	8340	12848	8340	11636
45°	8234	12387	8234	11659
50°	7857	11783	7857	11702
55°	7817	10871	7817	11589
60°	7007	9687	7007	11541
65°	5975	8535	5975	11217
70°	4820	7232	4820	10395
75°	4180	5970	4180	9557
80°	3561	4454	3561	7717
85°	2371	2371	2371	4724

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 40°
 Vertical Angle: 45°
 Luminance: 12777 cd/sqm



TEST NUMBER: P1435864

CATALOG NUMBER: SQ2W-FA-K-150U-050D-L940-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.1	0.9
10°-20°	207.0	2.5
20°-30°	314.4	3.8
30°-40°	369.1	4.5
40°-50°	374.6	4.6
50°-60°	328.1	4.0
60°-70°	232.7	2.8
70°-80°	119.8	1.5
80°-90°	33.8	0.4
90°-100°	167.6	2.0
100°-110°	488.9	6.0
110°-120°	797.8	9.7
120°-130°	1012.4	12.3
130°-140°	1083.3	13.2
140°-150°	1011.5	12.3
150°-160°	832.4	10.1
160°-170°	558.2	6.8
170°-180°	198.2	2.4
0°-30°	595.5	7.3
0°-40°	964.6	11.8
0°-60°	1667.2	20.3
0°-90°	2053.5	25.0
90°-120°	1454.3	17.7
90°-150°	4561.5	55.6
90°-180°	6150.0	75.0
0°-180°	8203.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	823	823	823	823	823	
5°	811	849	811	677	811	77
15°	769	839	769	657	769	216
25°	667	776	667	651	667	304
35°	492	670	492	584	492	306
45°	361	542	361	511	361	276
55°	278	386	278	412	278	240
65°	156	223	156	294	156	156
75°	67	96	67	153	67	72
85°	13	13	13	26	13	16
90°	6	47	6	92	6	5
95°	66	49	66	287	66	80
105°	311	498	311	685	311	330
115°	596	826	596	1017	596	587
125°	881	1308	881	1247	881	788
135°	1198	1713	1198	1381	1198	926
145°	1530	1974	1530	1411	1530	957
155°	1817	2145	1817	1464	1817	835
165°	2008	2236	2008	1685	2008	565
175°	2100	2189	2100	1977	2100	199
180°	2106	2106	2106	2106	2106	



TEST NUMBER: P1435864

CATALOG NUMBER: SQ2W-FA-K-150U-050D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	823.4	823.4	823.4	823.4	823.4	823.4	823.4	823.4	823.4	823.4	823.4
2.5°	818.3	824.0	829.6	831.0	831.0	831.0	831.0	831.0	831.0	831.0	831.0
5°	810.6	820.5	830.5	835.1	837.9	840.1	841.5	843.2	846.1	848.9	846.1
7.5°	803.0	816.3	829.6	836.1	840.4	843.8	846.4	848.6	850.1	851.5	850.1
10°	797.9	813.5	829.1	836.1	840.4	843.2	844.7	846.1	847.5	848.9	847.5
12.5°	790.2	806.9	823.7	831.9	837.3	840.7	842.1	843.5	844.9	846.4	844.9
15°	769.1	791.8	814.5	823.4	827.6	831.2	834.0	836.5	837.9	839.3	837.9
17.5°	743.0	770.5	798.0	809.1	814.8	818.9	821.5	823.7	824.8	825.9	824.8
20°	727.6	757.4	787.2	798.9	804.6	808.1	809.6	810.6	810.6	810.6	810.6
22.5°	707.2	740.4	773.6	786.2	791.8	794.8	795.1	795.6	796.7	797.9	796.7
25°	667.0	705.3	743.6	759.6	768.1	771.6	770.2	769.8	772.7	775.5	772.7
27.5°	617.9	666.1	714.3	730.6	736.3	739.8	741.3	742.3	742.3	742.3	742.3
30°	587.2	641.1	695.0	712.7	718.4	722.0	723.4	724.5	724.5	724.5	724.5
32.5°	548.9	613.0	677.1	696.6	701.1	703.5	703.8	704.0	704.0	704.0	704.0
35°	491.5	569.5	647.5	669.1	672.0	673.4	673.4	673.0	671.6	670.2	671.6
37.5°	434.0	522.5	611.0	636.4	640.6	641.8	639.8	637.9	636.5	635.1	636.5
40°	395.7	492.2	588.6	615.9	620.2	620.2	615.9	612.4	611.0	609.6	611.0
42.5°	375.3	470.6	565.9	593.0	597.2	596.7	591.3	586.9	585.4	584.0	585.4
45°	360.6	445.7	530.8	555.3	559.6	558.9	553.2	548.2	545.4	542.5	545.4
47.5°	338.3	413.2	488.1	512.1	519.2	518.5	510.0	502.9	500.1	497.2	500.1
50°	312.8	386.5	460.3	484.0	491.1	490.4	481.9	474.8	472.0	469.1	472.0
52.5°	294.9	364.1	433.3	455.1	461.1	459.2	449.6	441.6	438.8	435.9	438.8
55°	277.7	335.8	394.0	411.7	415.9	413.1	403.2	394.7	390.4	386.2	390.4
57.5°	237.4	292.8	348.1	365.3	369.8	366.4	355.1	345.4	340.6	335.7	340.6
60°	217.0	266.7	316.3	333.0	338.6	335.8	324.5	314.2	307.1	300.0	307.1
62.5°	194.0	238.0	282.0	298.9	306.9	305.2	293.8	283.5	276.4	269.4	276.4
65°	156.4	194.7	233.0	250.0	259.9	259.2	247.9	237.6	230.5	223.4	230.5
67.5°	122.6	155.5	188.4	205.1	216.4	215.9	203.4	192.6	186.9	181.3	186.9
70°	102.1	130.5	158.9	174.5	185.8	185.8	174.5	164.5	158.9	153.2	158.9
72.5°	89.4	110.9	132.5	147.2	159.7	159.7	147.2	136.7	132.2	127.7	132.2
75°	67.0	79.8	92.6	106.4	120.6	122.0	110.6	101.4	98.6	95.7	98.6
77.5°	48.5	54.5	60.4	71.3	83.8	85.2	75.5	68.0	66.9	65.7	66.9
80°	38.3	39.7	41.1	50.0	61.3	62.8	54.3	47.9	47.9	47.9	47.9
82.5°	25.5	26.9	28.4	34.7	42.6	43.5	37.2	32.3	31.1	30.0	31.1
85°	12.8	12.8	12.8	14.9	17.7	17.7	14.9	12.8	12.8	12.8	12.8
87.5°	3.8	5.5	7.7	10.2	12.6	13.0	11.9	11.5	11.9	11.9	11.9
90°	6.4	14.9	25.5	34.0	40.4	42.6	42.6	44.7	46.8	46.8	46.8
92.5°	23.4	37.0	37.4	37.4	45.5	49.4	52.8	53.2	55.3	55.3	55.3
95°	66.0	72.3	108.5	106.4	72.3	57.4	48.9	48.9	48.9	48.9	48.9
97.5°	126.0	135.3	141.3	189.4	200.0	193.2	157.4	132.3	118.3	111.9	118.3
100°	178.7	183.0	195.7	197.9	251.1	302.1	276.6	244.7	234.0	227.7	234.0
102.5°	231.5	234.0	253.6	262.6	274.9	303.8	392.3	382.6	375.3	374.0	375.3
105°	310.6	312.8	348.9	366.0	374.5	374.5	372.3	414.9	483.0	497.9	483.0
107.5°	395.3	405.1	447.7	493.2	503.0	505.5	494.5	488.1	485.5	487.2	485.5
110°	453.2	468.1	519.2	576.6	591.5	595.8	591.5	585.1	580.9	580.9	580.9



TEST NUMBER: P1435864

CATALOG NUMBER: SQ2W-FA-K-150U-050D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	509.4	531.1	588.9	654.9	680.0	692.8	683.4	678.7	674.5	677.9	674.5
115°	595.8	627.7	704.3	772.3	823.4	829.8	827.7	827.7	825.5	825.5	825.5
117.5°	675.8	726.8	812.8	891.9	951.1	968.1	976.6	974.1	971.5	975.8	971.5
120°	731.9	791.5	889.4	978.7	1036.2	1061.7	1070.2	1066.0	1070.2	1066.0	1070.2
122.5°	791.5	864.7	960.9	1053.6	1121.3	1150.2	1160.4	1161.3	1162.1	1159.6	1162.1
125°	880.9	970.2	1083.0	1178.7	1248.9	1283.0	1291.5	1293.6	1297.9	1308.5	1297.9
127.5°	971.1	1072.4	1196.2	1288.5	1360.4	1401.7	1414.9	1419.6	1428.5	1433.2	1428.5
130°	1034.1	1148.9	1274.5	1361.7	1431.9	1476.6	1500.0	1506.4	1517.0	1514.9	1517.0
132.5°	1100.4	1220.4	1347.7	1438.3	1503.4	1551.5	1571.5	1589.8	1593.6	1596.6	1593.6
135°	1197.9	1327.7	1455.3	1544.7	1606.4	1653.2	1678.7	1695.8	1706.4	1712.8	1706.4
137.5°	1300.4	1437.5	1560.0	1639.6	1701.7	1742.1	1771.1	1789.0	1800.0	1805.1	1800.0
140°	1370.2	1502.1	1621.3	1704.3	1759.6	1800.0	1825.5	1846.8	1859.6	1859.6	1859.6
142.5°	1436.6	1566.8	1682.6	1765.5	1814.1	1851.1	1878.3	1894.5	1909.0	1909.0	1909.0
145°	1529.8	1659.6	1766.0	1849.0	1889.4	1923.4	1953.2	1966.0	1974.5	1974.5	1974.5
147.5°	1627.2	1742.1	1839.2	1918.7	1952.8	1992.8	2016.2	2026.4	2037.0	2032.4	2037.0
150°	1685.1	1791.5	1885.1	1959.6	1993.6	2031.9	2055.3	2063.8	2074.5	2068.1	2074.5
152.5°	1741.3	1842.6	1927.7	1997.0	2026.0	2064.3	2091.1	2099.6	2106.8	2102.1	2106.8
155°	1817.0	1906.4	1985.1	2049.0	2074.5	2110.7	2136.2	2146.8	2155.3	2144.7	2155.3
157.5°	1884.7	1961.7	2030.2	2089.0	2116.2	2147.3	2171.1	2184.3	2192.8	2188.1	2192.8
160°	1925.6	1995.8	2057.5	2112.8	2138.3	2166.0	2191.5	2206.4	2214.9	2208.5	2214.9
162.5°	1959.6	2023.0	2081.3	2131.5	2153.6	2177.9	2208.5	2221.7	2230.2	2222.1	2230.2
165°	2008.5	2059.6	2110.7	2153.2	2172.4	2191.5	2223.4	2238.3	2244.7	2236.2	2244.7
167.5°	2045.6	2084.7	2126.0	2162.6	2176.6	2195.3	2227.3	2239.6	2247.7	2237.0	2247.7
170°	2066.0	2100.0	2136.2	2166.0	2176.6	2193.6	2225.6	2236.2	2242.6	2231.9	2242.6
172.5°	2083.0	2108.5	2137.9	2164.3	2169.8	2183.4	2213.6	2224.3	2229.0	2220.0	2229.0
175°	2100.0	2114.9	2136.2	2153.2	2151.1	2159.6	2185.1	2193.6	2202.1	2189.4	2202.1
177.5°	2108.1	2114.9	2121.7	2131.9	2125.1	2125.1	2143.9	2149.0	2150.7	2143.9	2150.7
180°	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4



TEST NUMBER: P1435864

CATALOG NUMBER: SQ2W-FA-K-150U-050D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	823.4	823.4	823.4	823.4	823.4	823.4	823.4	823.4	823.4	823.4	823.4
2.5°	831.0	831.0	831.0	831.0	831.0	829.6	824.0	818.3	818.3	818.3	814.0
5°	843.2	841.5	840.1	837.9	835.1	830.5	820.5	810.6	806.4	802.1	784.0
7.5°	848.6	846.4	843.8	840.4	836.1	829.6	816.3	803.0	784.0	764.9	724.7
10°	846.1	844.7	843.2	840.4	836.1	829.1	813.5	797.9	759.6	721.3	683.0
12.5°	843.5	842.1	840.7	837.3	831.9	823.7	806.9	790.2	736.0	681.8	647.2
15°	836.5	834.0	831.2	827.6	823.4	814.5	791.8	769.1	708.1	647.1	618.1
17.5°	823.7	821.5	818.9	814.8	809.1	798.0	770.5	743.0	679.1	615.3	596.6
20°	810.6	809.6	808.1	804.6	798.9	787.2	757.4	727.6	663.8	600.0	591.5
22.5°	795.6	795.1	794.8	791.8	786.2	773.6	740.4	707.2	644.5	581.8	582.1
25°	769.8	770.2	771.6	768.1	759.6	743.6	705.3	667.0	611.7	556.4	565.9
27.5°	742.3	741.3	739.8	736.3	730.6	714.3	666.1	617.9	574.2	530.5	546.4
30°	724.5	723.4	722.0	718.4	712.7	695.0	641.1	587.2	550.3	513.5	531.9
32.5°	704.0	703.8	703.5	701.1	696.6	677.1	613.0	548.9	522.3	495.6	514.9
35°	673.0	673.4	673.4	672.0	669.1	647.5	569.5	491.5	480.1	468.8	491.5
37.5°	637.9	639.8	641.8	640.6	636.4	611.0	522.5	434.0	437.7	441.4	468.9
40°	612.4	615.9	620.2	620.2	615.9	588.6	492.2	395.7	408.5	421.3	451.1
42.5°	586.9	591.3	596.7	597.2	593.0	565.9	470.6	375.3	389.2	403.1	434.0
45°	548.2	553.2	558.9	559.6	555.3	530.8	445.7	360.6	369.1	377.7	407.4
47.5°	502.9	510.0	518.5	519.2	512.1	488.1	413.2	338.3	344.5	350.8	381.3
50°	474.8	481.9	490.4	491.1	484.0	460.3	386.5	312.8	321.3	329.8	361.7
52.5°	441.6	449.6	459.2	461.1	455.1	433.3	364.1	294.9	300.0	305.1	339.6
55°	394.7	403.2	413.1	415.9	411.7	394.0	335.8	277.7	273.4	269.1	304.2
57.5°	345.4	355.1	366.4	369.8	365.3	348.1	292.8	237.4	233.8	230.1	268.1
60°	314.2	324.5	335.8	338.6	333.0	316.3	266.7	217.0	209.9	202.8	242.5
62.5°	283.5	293.8	305.2	306.9	298.9	282.0	238.0	194.0	189.2	184.4	223.0
65°	237.6	247.9	259.2	259.9	250.0	233.0	194.7	156.4	159.2	162.1	196.8
67.5°	192.6	203.4	215.9	216.4	205.1	188.4	155.5	122.6	131.9	141.3	172.5
70°	164.5	174.5	185.8	185.8	174.5	158.9	130.5	102.1	114.9	127.7	156.4
72.5°	136.7	147.2	159.7	159.7	147.2	132.5	110.9	89.4	102.1	114.9	138.5
75°	101.4	110.6	122.0	120.6	106.4	92.6	79.8	67.0	79.8	92.6	110.6
77.5°	68.0	75.5	85.2	83.8	71.3	60.4	54.5	48.5	59.0	69.5	82.1
80°	47.9	54.3	62.8	61.3	50.0	41.1	39.7	38.3	45.4	52.5	61.7
82.5°	32.3	37.2	43.5	42.6	34.7	28.4	26.9	25.5	31.5	37.4	43.8
85°	12.8	14.9	17.7	17.7	14.9	12.8	12.8	12.8	15.6	18.4	21.3
87.5°	11.5	11.9	13.0	12.6	10.2	7.7	5.5	3.8	6.7	9.5	12.8
90°	44.7	42.6	42.6	40.4	34.0	25.5	14.9	6.4	14.9	23.4	38.3
92.5°	53.2	52.8	49.4	45.5	37.4	37.4	37.0	23.4	40.4	57.4	82.6
95°	48.9	48.9	57.4	72.3	106.4	108.5	72.3	66.0	93.6	131.9	166.0
97.5°	132.3	157.4	193.2	200.0	189.4	141.3	135.3	126.0	171.5	209.4	264.3
100°	244.7	276.6	302.1	251.1	197.9	195.7	183.0	178.7	227.7	263.8	317.0
102.5°	382.6	392.3	303.8	274.9	262.6	253.6	234.0	231.5	280.4	330.2	374.9
105°	414.9	372.3	374.5	374.5	366.0	348.9	312.8	310.6	366.0	423.4	478.7
107.5°	488.1	494.5	505.5	503.0	493.2	447.7	405.1	395.3	445.1	514.0	574.9
110°	585.1	591.5	595.8	591.5	576.6	519.2	468.1	453.2	497.9	570.2	636.2



TEST NUMBER: P1435864

CATALOG NUMBER: SQ2W-FA-K-150U-050D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	678.7	683.4	692.8	680.0	654.9	588.9	531.1	509.4	554.0	628.1	695.8
115°	827.7	827.7	829.8	823.4	772.3	704.3	627.7	595.8	634.0	702.1	776.6
117.5°	974.1	976.6	968.1	951.1	891.9	812.8	726.8	675.8	706.0	777.9	854.5
120°	1066.0	1070.2	1061.7	1036.2	978.7	889.4	791.5	731.9	755.3	825.5	902.1
122.5°	1161.3	1160.4	1150.2	1121.3	1053.6	960.9	864.7	791.5	801.3	866.4	941.3
125°	1293.6	1291.5	1283.0	1248.9	1178.7	1083.0	970.2	880.9	868.1	923.4	1000.0
127.5°	1419.6	1414.9	1401.7	1360.4	1288.5	1196.2	1072.4	971.1	942.6	977.5	1047.7
130°	1506.4	1500.0	1476.6	1431.9	1361.7	1274.5	1148.9	1034.1	993.6	1014.9	1076.6
132.5°	1589.8	1571.5	1551.5	1503.4	1438.3	1347.7	1220.4	1100.4	1044.7	1054.1	1102.1
135°	1695.8	1678.7	1653.2	1606.4	1544.7	1455.3	1327.7	1197.9	1121.3	1112.8	1140.4
137.5°	1789.0	1771.1	1742.1	1701.7	1639.6	1560.0	1437.5	1300.4	1203.8	1175.3	1186.0
140°	1846.8	1825.5	1800.0	1759.6	1704.3	1621.3	1502.1	1370.2	1261.7	1221.3	1214.9
142.5°	1894.5	1878.3	1851.1	1814.1	1765.5	1682.6	1566.8	1436.6	1321.3	1268.9	1254.1
145°	1966.0	1953.2	1923.4	1889.4	1849.0	1766.0	1659.6	1529.8	1414.9	1346.8	1314.9
147.5°	2026.4	2016.2	1992.8	1952.8	1918.7	1839.2	1742.1	1627.2	1509.4	1425.1	1383.8
150°	2063.8	2055.3	2031.9	1993.6	1959.6	1885.1	1791.5	1685.1	1572.4	1483.0	1429.8
152.5°	2099.6	2091.1	2064.3	2026.0	1997.0	1927.7	1842.6	1741.3	1626.8	1537.5	1482.6
155°	2146.8	2136.2	2110.7	2074.5	2049.0	1985.1	1906.4	1817.0	1719.2	1625.5	1563.8
157.5°	2184.3	2171.1	2147.3	2116.2	2089.0	2030.2	1961.7	1884.7	1799.2	1709.8	1646.8
160°	2206.4	2191.5	2166.0	2138.3	2112.8	2057.5	1995.8	1925.6	1846.8	1766.0	1697.9
162.5°	2221.7	2208.5	2177.9	2153.6	2131.5	2081.3	2023.0	1959.6	1889.4	1818.7	1755.8
165°	2238.3	2223.4	2191.5	2172.4	2153.2	2110.7	2059.6	2008.5	1949.0	1891.5	1840.4
167.5°	2239.6	2227.3	2195.3	2176.6	2162.6	2126.0	2084.7	2045.6	1999.2	1954.1	1911.5
170°	2236.2	2225.6	2193.6	2176.6	2166.0	2136.2	2100.0	2066.0	2029.8	1991.5	1957.5
172.5°	2224.3	2213.6	2183.4	2169.8	2164.3	2137.9	2108.5	2083.0	2051.9	2023.8	1996.6
175°	2193.6	2185.1	2159.6	2151.1	2153.2	2136.2	2114.9	2100.0	2080.9	2063.8	2049.0
177.5°	2149.0	2143.9	2125.1	2125.1	2131.9	2121.7	2114.9	2108.1	2099.6	2094.5	2089.4
180°	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4



TEST NUMBER: P1435864

CATALOG NUMBER: SQ2W-FA-K-150U-050D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	823.4	823.4	823.4	823.4	823.4	823.4	823.4	823.4	823.4	823.4	823.4
2.5°	808.3	803.8	800.4	797.6	796.4	795.3	796.4	797.6	800.4	803.8	808.3
5°	761.3	737.2	711.7	690.8	683.7	676.6	683.7	690.8	711.7	737.2	761.3
7.5°	677.3	648.2	637.4	628.8	626.5	624.2	626.5	628.8	637.4	648.2	677.3
10°	644.7	621.3	612.8	606.4	606.4	606.4	606.4	606.4	612.8	621.3	644.7
12.5°	619.1	604.8	604.2	605.2	610.9	616.6	610.9	605.2	604.2	604.8	619.1
15°	599.6	601.8	624.5	643.2	650.3	657.4	650.3	643.2	624.5	601.8	599.6
17.5°	592.9	605.1	633.2	655.7	661.3	667.0	661.3	655.7	633.2	605.1	592.9
20°	601.4	617.0	638.3	655.7	661.3	667.0	661.3	655.7	638.3	617.0	601.4
22.5°	603.4	622.4	639.1	653.1	658.8	664.5	658.8	653.1	639.1	622.4	603.4
25°	597.1	619.8	634.0	645.4	648.2	651.0	648.2	645.4	634.0	619.8	597.1
27.5°	582.1	607.1	621.3	632.4	634.4	636.4	634.4	632.4	621.3	607.1	582.1
30°	568.8	594.3	608.5	620.2	624.5	628.7	624.5	620.2	608.5	594.3	568.8
32.5°	549.5	575.6	593.2	606.6	607.4	608.3	607.4	606.6	593.2	575.6	549.5
35°	525.5	552.5	572.3	586.9	585.4	584.0	585.4	586.9	572.3	552.5	525.5
37.5°	504.4	530.8	548.1	561.5	563.2	564.9	563.2	561.5	548.1	530.8	504.4
40°	486.5	513.5	531.9	546.4	549.3	552.1	549.3	546.4	531.9	513.5	486.5
42.5°	470.6	498.1	516.6	531.1	534.0	536.8	534.0	531.1	516.6	498.1	470.6
45°	444.3	472.7	492.5	507.8	509.2	510.6	509.2	507.8	492.5	472.7	444.3
47.5°	419.8	448.4	466.8	481.0	482.4	483.8	482.4	481.0	466.8	448.4	419.8
50°	401.4	430.5	448.9	463.1	464.5	465.9	464.5	463.1	448.9	430.5	401.4
52.5°	383.8	414.0	430.2	442.7	444.1	445.5	444.1	442.7	430.2	414.0	383.8
55°	352.5	384.4	400.0	411.7	411.7	411.7	411.7	411.7	400.0	384.4	352.5
57.5°	320.0	352.8	366.4	377.0	378.7	380.4	378.7	377.0	366.4	352.8	320.0
60°	297.9	331.2	342.5	351.8	354.6	357.4	354.6	351.8	342.5	331.2	297.9
62.5°	276.0	308.2	319.6	328.5	330.2	331.9	330.2	328.5	319.6	308.2	276.0
65°	242.2	270.6	281.9	290.8	292.2	293.6	292.2	290.8	281.9	270.6	242.2
67.5°	211.1	234.4	242.3	248.6	249.7	250.8	249.7	248.6	242.3	234.4	211.1
70°	190.4	210.3	216.0	220.2	220.2	220.2	220.2	220.2	216.0	210.3	190.4
72.5°	165.7	182.2	187.9	192.4	193.5	194.7	193.5	192.4	187.9	182.2	165.7
75°	130.5	142.5	146.8	150.4	151.8	153.2	151.8	150.4	146.8	142.5	130.5
77.5°	95.5	103.4	106.0	108.2	109.6	111.1	109.6	108.2	106.0	103.4	95.5
80°	71.6	77.3	78.7	80.1	81.6	83.0	81.6	80.1	78.7	77.3	71.6
82.5°	50.4	54.3	55.7	56.9	57.2	57.4	57.2	56.9	55.7	54.3	50.4
85°	24.1	25.5	25.5	25.5	25.5	25.5	25.5	25.5	25.5	25.5	24.1
87.5°	14.9	17.9	20.9	22.6	24.3	23.4	24.3	22.6	20.9	17.9	14.9
90°	48.9	63.8	78.7	87.2	95.7	91.5	95.7	87.2	78.7	63.8	48.9
92.5°	98.3	123.4	141.7	157.0	163.8	163.0	163.8	157.0	141.7	123.4	98.3
95°	197.9	227.7	257.4	278.7	291.5	287.2	291.5	278.7	257.4	227.7	197.9
97.5°	305.1	345.1	378.3	398.3	411.1	419.6	411.1	398.3	378.3	345.1	305.1
100°	376.6	414.9	453.2	476.6	497.9	506.4	497.9	476.6	453.2	414.9	376.6
102.5°	434.5	484.7	526.4	551.5	569.4	577.9	569.4	551.5	526.4	484.7	434.5
105°	529.8	583.0	627.7	659.6	678.7	685.1	678.7	659.6	627.7	583.0	529.8
107.5°	625.1	680.0	721.3	756.6	780.0	793.6	780.0	756.6	721.3	680.0	625.1
110°	700.0	744.7	789.4	821.3	844.7	853.2	844.7	821.3	789.4	744.7	700.0



TEST NUMBER: P1435864

CATALOG NUMBER: SQ2W-FA-K-150U-050D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	763.0	812.8	857.5	889.4	916.2	928.1	916.2	889.4	857.5	812.8	763.0
115°	851.1	917.0	957.5	987.2	1006.4	1017.0	1006.4	987.2	957.5	917.0	851.1
117.5°	924.3	993.2	1037.5	1060.4	1069.4	1077.0	1069.4	1060.4	1037.5	993.2	924.3
120°	970.2	1034.1	1085.1	1114.9	1125.5	1129.8	1125.5	1114.9	1085.1	1034.1	970.2
122.5°	1012.8	1073.2	1122.6	1159.2	1176.6	1180.9	1176.6	1159.2	1122.6	1073.2	1012.8
125°	1072.4	1129.8	1180.9	1217.0	1236.2	1246.8	1236.2	1217.0	1180.9	1129.8	1072.4
127.5°	1124.3	1186.4	1233.2	1266.0	1284.7	1293.2	1284.7	1266.0	1233.2	1186.4	1124.3
130°	1153.2	1217.0	1263.8	1300.0	1317.0	1325.5	1317.0	1300.0	1263.8	1217.0	1153.2
132.5°	1175.3	1242.6	1291.1	1323.8	1342.6	1351.1	1342.6	1323.8	1291.1	1242.6	1175.3
135°	1202.1	1272.4	1323.4	1355.3	1372.4	1380.9	1372.4	1355.3	1323.4	1272.4	1202.1
137.5°	1225.5	1289.4	1342.6	1376.2	1391.5	1397.0	1391.5	1376.2	1342.6	1289.4	1225.5
140°	1242.6	1297.9	1351.1	1383.0	1400.0	1402.1	1400.0	1383.0	1351.1	1297.9	1242.6
142.5°	1264.7	1308.1	1354.5	1386.4	1403.4	1407.2	1403.4	1386.4	1354.5	1308.1	1264.7
145°	1304.3	1329.8	1361.7	1391.5	1406.4	1410.7	1406.4	1391.5	1361.7	1329.8	1304.3
147.5°	1354.1	1362.1	1378.7	1398.3	1412.8	1415.8	1412.8	1398.3	1378.7	1362.1	1354.1
150°	1391.5	1389.4	1395.8	1408.5	1421.3	1419.2	1421.3	1408.5	1395.8	1389.4	1391.5
152.5°	1434.1	1421.7	1421.3	1427.2	1433.2	1432.8	1433.2	1427.2	1421.3	1421.7	1434.1
155°	1506.4	1483.0	1470.2	1466.0	1466.0	1463.8	1466.0	1466.0	1470.2	1483.0	1506.4
157.5°	1586.0	1553.2	1534.1	1523.8	1520.9	1516.2	1520.9	1523.8	1534.1	1553.2	1586.0
160°	1640.4	1604.3	1585.1	1568.1	1561.7	1555.3	1561.7	1568.1	1585.1	1604.3	1640.4
162.5°	1691.5	1657.0	1636.2	1620.9	1614.5	1604.7	1614.5	1620.9	1636.2	1657.0	1691.5
165°	1774.5	1738.3	1714.9	1702.1	1693.6	1685.1	1693.6	1702.1	1714.9	1738.3	1774.5
167.5°	1857.5	1817.9	1802.6	1788.1	1780.0	1764.7	1780.0	1788.1	1802.6	1817.9	1857.5
170°	1908.5	1872.4	1863.8	1851.1	1836.2	1819.2	1836.2	1851.1	1863.8	1872.4	1908.5
172.5°	1952.8	1928.5	1920.0	1907.3	1902.6	1889.0	1902.6	1907.3	1920.0	1928.5	1952.8
175°	2017.0	1997.9	1997.9	1995.8	1989.4	1976.6	1989.4	1995.8	1997.9	1997.9	2017.0
177.5°	2070.7	2060.4	2067.3	2067.3	2065.6	2053.6	2065.6	2067.3	2067.3	2060.4	2070.7
180°	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4



TEST NUMBER: P1435864

CATALOG NUMBER: SQ2W-FA-K-150U-050D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	823.4	823.4	823.4	823.4
2.5°	814.0	818.3	818.3	818.3
5°	784.0	802.1	806.4	810.6
7.5°	724.7	764.9	784.0	803.0
10°	683.0	721.3	759.6	797.9
12.5°	647.2	681.8	736.0	790.2
15°	618.1	647.1	708.1	769.1
17.5°	596.6	615.3	679.1	743.0
20°	591.5	600.0	663.8	727.6
22.5°	582.1	581.8	644.5	707.2
25°	565.9	556.4	611.7	667.0
27.5°	546.4	530.5	574.2	617.9
30°	531.9	513.5	550.3	587.2
32.5°	514.9	495.6	522.3	548.9
35°	491.5	468.8	480.1	491.5
37.5°	468.9	441.4	437.7	434.0
40°	451.1	421.3	408.5	395.7
42.5°	434.0	403.1	389.2	375.3
45°	407.4	377.7	369.1	360.6
47.5°	381.3	350.8	344.5	338.3
50°	361.7	329.8	321.3	312.8
52.5°	339.6	305.1	300.0	294.9
55°	304.2	269.1	273.4	277.7
57.5°	268.1	230.1	233.8	237.4
60°	242.5	202.8	209.9	217.0
62.5°	223.0	184.4	189.2	194.0
65°	196.8	162.1	159.2	156.4
67.5°	172.5	141.3	131.9	122.6
70°	156.4	127.7	114.9	102.1
72.5°	138.5	114.9	102.1	89.4
75°	110.6	92.6	79.8	67.0
77.5°	82.1	69.5	59.0	48.5
80°	61.7	52.5	45.4	38.3
82.5°	43.8	37.4	31.5	25.5
85°	21.3	18.4	15.6	12.8
87.5°	12.8	9.5	6.7	3.8
90°	38.3	23.4	14.9	6.4
92.5°	82.6	57.4	40.4	23.4
95°	166.0	131.9	93.6	66.0
97.5°	264.3	209.4	171.5	126.0
100°	317.0	263.8	227.7	178.7
102.5°	374.9	330.2	280.4	231.5
105°	478.7	423.4	366.0	310.6
107.5°	574.9	514.0	445.1	395.3
110°	636.2	570.2	497.9	453.2



TEST NUMBER: P1435864

CATALOG NUMBER: SQ2W-FA-K-150U-050D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	695.8	628.1	554.0	509.4
115°	776.6	702.1	634.0	595.8
117.5°	854.5	777.9	706.0	675.8
120°	902.1	825.5	755.3	731.9
122.5°	941.3	866.4	801.3	791.5
125°	1000.0	923.4	868.1	880.9
127.5°	1047.7	977.5	942.6	971.1
130°	1076.6	1014.9	993.6	1034.1
132.5°	1102.1	1054.1	1044.7	1100.4
135°	1140.4	1112.8	1121.3	1197.9
137.5°	1186.0	1175.3	1203.8	1300.4
140°	1214.9	1221.3	1261.7	1370.2
142.5°	1254.1	1268.9	1321.3	1436.6
145°	1314.9	1346.8	1414.9	1529.8
147.5°	1383.8	1425.1	1509.4	1627.2
150°	1429.8	1483.0	1572.4	1685.1
152.5°	1482.6	1537.5	1626.8	1741.3
155°	1563.8	1625.5	1719.2	1817.0
157.5°	1646.8	1709.8	1799.2	1884.7
160°	1697.9	1766.0	1846.8	1925.6
162.5°	1755.8	1818.7	1889.4	1959.6
165°	1840.4	1891.5	1949.0	2008.5
167.5°	1911.5	1954.1	1999.2	2045.6
170°	1957.5	1991.5	2029.8	2066.0
172.5°	1996.6	2023.8	2051.9	2083.0
175°	2049.0	2063.8	2080.9	2100.0
177.5°	2089.4	2094.5	2099.6	2108.1
180°	2106.4	2106.4	2106.4	2106.4



TEST NUMBER: P1435864
 CATALOG NUMBER: SQ2W-FA-K-150U-050D-L940-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.42	13.09	13.56	14.22	15.81	13.61	14.29	14.76	15.42	17.01
	3H	13.49	14.09	14.64	15.24	16.84	14.84	15.45	16.00	16.59	18.19
	4H	13.83	14.41	14.99	15.55	17.16	15.22	15.80	16.39	16.94	18.55
	6H	13.98	14.51	15.15	15.66	17.28	15.37	15.90	16.54	17.05	18.67
	8H	14.01	14.51	15.18	15.67	17.29	15.39	15.89	16.57	17.05	18.67
	12H	14.00	14.48	15.18	15.63	17.27	15.37	15.85	16.55	17.00	18.63
4H	2H	13.26	13.83	14.43	14.97	16.58	14.17	14.75	15.34	15.89	17.50
	3H	14.63	15.11	15.80	16.28	17.90	15.62	16.10	16.79	17.27	18.89
	4H	15.08	15.52	16.25	16.67	18.31	16.09	16.53	17.26	17.68	19.32
	6H	15.29	15.67	16.48	16.85	18.48	16.30	16.67	17.48	17.85	19.48
	8H	15.35	15.70	16.53	16.87	18.52	16.34	16.69	17.52	17.86	19.51
	12H	15.34	15.66	16.54	16.84	18.49	16.32	16.64	17.52	17.82	19.47
8H	4H	15.44	15.80	16.62	16.97	18.61	16.27	16.62	17.45	17.79	19.43
	6H	15.79	16.08	16.99	17.29	18.93	16.57	16.86	17.77	18.08	19.72
	8H	15.90	16.15	17.11	17.35	19.01	16.67	16.92	17.87	18.11	19.77
	12H	15.93	16.15	17.14	17.34	19.04	16.67	16.89	17.88	18.08	19.78
12H	4H	15.44	15.76	16.64	16.94	18.59	16.23	16.55	17.42	17.73	19.38
	6H	15.86	16.11	17.06	17.30	18.96	16.59	16.84	17.79	18.03	19.70
	8H	15.99	16.21	17.20	17.40	19.10	16.69	16.92	17.90	18.10	19.80