

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1436020

Luminaire Tested: SQ2W-FB-K-125U-100D-L940-UNV-STD-W-WM-4

Issue Date: 3/24/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1436020  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/24/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-FB-K-125U-100D-L940-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - FROSTED CONTINUOUS BATWING ROLL LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 9407.1 lumens  
Efficiency: N/A  
Efficacy: 115.3 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.52  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 81.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1436020

CATALOG NUMBER: SQ2W-FB-K-125U-100D-L940-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1436020

CATALOG NUMBER: SQ2W-FB-K-125U-100D-L940-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	96	92	88	85	88	84	81	78	70	68	66	57	56	54	45	44	43	37
2	88	80	74	69	80	73	68	64	61	57	54	50	47	45	39	37	36	31
3	80	70	62	57	73	64	58	53	54	49	45	44	40	37	34	32	30	26
4	72	62	53	47	66	57	50	44	47	42	38	39	35	31	30	28	25	21
5	66	54	46	40	60	50	43	37	42	36	32	34	30	27	27	24	22	18
6	61	49	40	34	55	45	37	32	37	32	28	31	26	23	24	21	19	16
7	56	44	36	30	51	40	33	28	34	28	24	28	23	20	22	19	16	14
8	52	39	31	26	47	36	29	24	31	25	21	25	21	18	20	17	14	12
9	48	36	28	23	44	33	26	22	28	22	19	23	19	16	18	15	13	11
10	45	33	25	20	41	30	24	19	25	20	17	21	17	14	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	6889	6889	6889	6889
5°	6716	12202	6716	12202
10°	6291	23746	6291	23746
15°	5693	27331	5693	27331
20°	5041	28623	5041	28623
25°	4459	29093	4459	29093
30°	3939	29451	3939	29451
35°	3518	31662	3518	31662
40°	3199	33640	3199	33640
45°	2952	35227	2952	35227
50°	2783	35866	2783	35866
55°	2714	36152	2714	36152
60°	2783	35972	2783	35972
65°	2900	34956	2900	34956
70°	3002	26440	3002	26440
75°	3325	14591	3325	14591
80°	3431	13547	3431	13547
85°	3427	5706	3427	5706

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 52.5°  
 Luminance: 36478 cd/sqm



TEST NUMBER: P1436020

CATALOG NUMBER: SQ2W-FB-K-125U-100D-L940-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	71.5	0.8
10°-20°	326.2	3.5
20°-30°	574.1	6.1
30°-40°	743.1	7.9
40°-50°	819.5	8.7
50°-60°	764.9	8.1
60°-70°	590.9	6.3
70°-80°	272.4	2.9
80°-90°	59.4	0.6
90°-100°	141.3	1.5
100°-110°	412.2	4.4
110°-120°	672.6	7.2
120°-130°	853.5	9.1
130°-140°	913.3	9.7
140°-150°	852.8	9.1
150°-160°	701.7	7.5
160°-170°	470.6	5.0
170°-180°	167.1	1.8
0°-30°	971.8	10.3
0°-40°	1714.9	18.2
0°-60°	3299.2	35.1
0°-90°	4222.0	44.9
90°-120°	1226.1	13.0
90°-150°	3845.7	40.9
90°-180°	5185.0	55.1
0°-180°	9407.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	427	427	427	427	427	
5°	414	753	414	753	414	38
15°	341	1635	341	1635	341	95
25°	250	1633	250	1633	250	115
35°	178	1606	178	1606	178	112
45°	129	1543	129	1543	129	100
55°	96	1284	96	1284	96	87
65°	76	915	76	915	76	74
75°	53	234	53	234	53	55
85°	18	31	18	31	18	19
90°	5	40	5	77	5	5
95°	56	41	56	242	56	67
105°	262	420	262	578	262	279
115°	502	696	502	857	502	495
125°	743	1103	743	1051	743	664
135°	1010	1444	1010	1164	1010	780
145°	1290	1665	1290	1189	1290	807
155°	1532	1808	1532	1234	1532	704
165°	1693	1885	1693	1421	1693	477
175°	1770	1846	1770	1666	1770	168
180°	1776	1776	1776	1776	1776	



TEST NUMBER: P1436020

CATALOG NUMBER: SQ2W-FB-K-125U-100D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	426.7	426.7	426.7	426.7	426.7	426.7	426.7	426.7	426.7	426.7	426.7
2.5°	423.5	431.5	439.5	448.1	456.8	466.3	476.5	485.3	489.7	494.0	489.7
5°	414.4	441.8	469.1	508.8	552.6	602.3	657.9	705.5	729.2	752.9	729.2
7.5°	398.4	454.0	509.7	627.5	766.1	910.0	1059.2	1182.9	1230.3	1277.7	1230.3
10°	383.7	461.2	538.7	738.6	979.3	1164.4	1293.9	1397.4	1422.9	1448.4	1422.9
12.5°	367.2	472.5	577.7	824.5	1118.4	1310.8	1401.7	1476.3	1502.6	1528.9	1502.6
15°	340.6	491.0	641.5	920.5	1242.4	1440.2	1514.1	1576.8	1606.0	1635.1	1606.0
17.5°	313.1	513.3	713.5	998.2	1310.9	1503.9	1577.0	1635.8	1651.7	1667.5	1651.7
20°	293.4	528.6	763.9	1049.1	1350.9	1533.2	1596.1	1645.8	1655.9	1665.9	1655.9
22.5°	275.3	538.3	801.3	1086.8	1379.9	1550.2	1597.8	1636.2	1646.9	1657.7	1646.9
25°	250.3	546.6	843.0	1127.7	1408.5	1564.0	1594.1	1618.5	1625.8	1633.1	1625.8
27.5°	226.1	539.2	852.3	1133.4	1403.9	1549.0	1568.7	1585.2	1592.3	1599.4	1592.3
30°	211.3	529.5	847.8	1126.3	1391.7	1531.6	1546.2	1559.7	1569.7	1579.7	1569.7
32.5°	198.2	517.9	837.6	1112.7	1372.9	1509.9	1523.8	1539.6	1561.3	1583.0	1561.3
35°	178.5	493.1	807.6	1079.8	1337.9	1477.8	1499.7	1526.2	1566.3	1606.4	1566.3
37.5°	161.7	461.3	760.9	1030.3	1289.6	1442.2	1488.0	1532.0	1570.6	1609.3	1570.6
40°	151.8	439.0	726.3	993.7	1254.4	1415.4	1476.5	1530.5	1563.3	1596.1	1563.3
42.5°	142.0	413.9	685.8	951.0	1214.0	1381.1	1452.4	1514.1	1546.9	1579.7	1546.9
45°	129.3	373.6	618.0	880.8	1149.8	1326.2	1410.1	1480.8	1511.8	1542.8	1511.8
47.5°	117.4	329.6	541.9	805.9	1087.1	1272.2	1361.2	1433.6	1456.2	1478.8	1456.2
50°	110.8	300.4	490.1	755.0	1045.0	1233.7	1321.2	1391.4	1409.7	1427.9	1409.7
52.5°	104.2	272.0	439.8	705.2	1003.2	1193.4	1275.8	1341.8	1358.6	1375.4	1358.6
55°	96.4	233.2	370.0	632.6	937.1	1125.4	1197.5	1255.1	1269.7	1284.3	1269.7
57.5°	89.5	199.8	310.1	564.5	866.8	1048.7	1110.2	1159.2	1171.1	1183.0	1171.1
60°	86.2	181.9	277.7	521.8	815.4	990.0	1045.6	1090.3	1102.2	1114.0	1102.2
62.5°	81.2	164.6	247.9	479.1	759.6	925.5	976.7	1017.9	1029.0	1040.2	1029.0
65°	75.9	143.4	210.9	419.2	674.5	823.6	866.5	900.4	907.7	915.0	907.7
67.5°	68.5	125.8	183.0	364.4	587.0	711.7	738.3	754.9	741.2	727.5	741.2
70°	63.6	116.5	169.4	331.0	528.9	632.4	641.5	638.5	599.3	560.1	599.3
72.5°	60.3	107.4	154.4	294.3	465.2	540.6	520.6	487.0	412.7	338.5	412.7
75°	53.3	91.6	129.9	235.3	362.9	383.0	295.4	230.2	232.1	233.9	232.1
77.5°	43.5	72.1	100.8	165.5	242.3	257.5	211.2	176.8	178.5	180.1	178.5
80°	36.9	59.7	82.5	108.1	134.5	146.8	145.0	143.8	144.8	145.7	144.8
82.5°	30.4	47.3	64.3	79.6	94.4	102.7	104.5	105.5	104.3	103.0	104.3
85°	18.5	28.5	38.5	44.5	49.0	47.6	40.3	34.4	32.6	30.8	32.6
87.5°	7.6	12.7	18.2	18.3	16.5	15.4	15.4	15.7	16.1	16.1	16.1
90°	5.4	12.6	21.5	28.7	34.1	35.9	35.9	37.7	39.5	39.5	39.5
92.5°	19.7	31.2	31.6	31.6	38.4	41.6	44.5	44.8	46.6	46.6	46.6
95°	55.6	61.0	91.5	89.7	61.0	48.4	41.3	41.3	41.3	41.3	41.3
97.5°	106.2	114.1	119.1	159.6	168.6	162.9	132.7	111.6	99.7	94.4	99.7
100°	150.7	154.3	165.0	166.8	211.7	254.7	233.2	206.3	197.3	191.9	197.3
102.5°	195.2	197.3	213.8	221.4	231.8	256.2	330.8	322.5	316.4	315.3	316.4
105°	261.9	263.7	294.2	308.5	315.7	315.7	313.9	349.8	407.2	419.7	407.2
107.5°	333.3	341.5	377.4	415.8	424.0	426.2	416.9	411.5	409.3	410.8	409.3
110°	382.1	394.6	437.7	486.1	498.7	502.3	498.7	493.3	489.7	489.7	489.7



TEST NUMBER: P1436020

CATALOG NUMBER: SQ2W-FB-K-125U-100D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	429.4	447.7	496.5	552.1	573.3	584.1	576.2	572.2	568.6	571.5	568.6
115°	502.3	529.2	593.7	651.1	694.2	699.6	697.8	697.8	696.0	696.0	696.0
117.5°	569.7	612.8	685.2	752.0	801.8	816.2	823.3	821.2	819.0	822.6	819.0
120°	617.1	667.3	749.8	825.1	873.6	895.1	902.3	898.7	902.3	898.7	902.3
122.5°	667.3	729.0	810.1	888.3	945.3	969.7	978.3	979.0	979.8	977.6	979.8
125°	742.6	818.0	913.0	993.8	1052.9	1081.6	1088.8	1090.6	1094.2	1103.2	1094.2
127.5°	818.7	904.1	1008.5	1086.3	1146.9	1181.7	1192.9	1196.8	1204.3	1208.3	1204.3
130°	871.8	968.6	1074.5	1148.0	1207.2	1244.9	1264.6	1270.0	1279.0	1277.2	1279.0
132.5°	927.7	1028.9	1136.2	1212.6	1267.5	1308.0	1324.9	1340.3	1343.5	1346.1	1343.5
135°	1009.9	1119.3	1226.9	1302.3	1354.3	1393.8	1415.3	1429.6	1438.6	1444.0	1438.6
137.5°	1096.4	1211.9	1315.2	1382.3	1434.7	1468.7	1493.1	1508.2	1517.5	1521.8	1517.5
140°	1155.2	1266.4	1366.9	1436.8	1483.5	1517.5	1539.1	1557.0	1567.8	1567.8	1567.8
142.5°	1211.2	1320.9	1418.5	1488.5	1529.4	1560.6	1583.5	1597.2	1609.4	1609.4	1609.4
145°	1289.7	1399.1	1488.8	1558.8	1592.9	1621.6	1646.7	1657.5	1664.6	1664.6	1664.6
147.5°	1371.9	1468.7	1550.5	1617.6	1646.3	1680.1	1699.8	1708.4	1717.4	1713.4	1717.4
150°	1420.7	1510.4	1589.3	1652.1	1680.8	1713.1	1732.8	1740.0	1748.9	1743.6	1748.9
152.5°	1468.0	1553.4	1625.2	1683.6	1708.0	1740.3	1762.9	1770.1	1776.2	1772.3	1776.2
155°	1531.9	1607.2	1673.6	1727.4	1748.9	1779.4	1801.0	1809.9	1817.1	1808.1	1817.1
157.5°	1588.9	1653.9	1711.6	1761.1	1784.1	1810.3	1830.4	1841.5	1848.7	1844.7	1848.7
160°	1623.4	1682.6	1734.6	1781.2	1802.7	1826.1	1847.6	1860.1	1867.3	1861.9	1867.3
162.5°	1652.1	1705.5	1754.7	1797.0	1815.7	1836.1	1861.9	1873.1	1880.2	1873.4	1880.2
165°	1693.3	1736.4	1779.4	1815.3	1831.4	1847.6	1874.5	1887.1	1892.4	1885.3	1892.4
167.5°	1724.5	1757.5	1792.3	1823.2	1835.0	1850.8	1877.7	1888.1	1894.9	1886.0	1894.9
170°	1741.8	1770.5	1801.0	1826.1	1835.0	1849.4	1876.3	1885.3	1890.6	1881.7	1890.6
172.5°	1756.1	1777.6	1802.4	1824.6	1829.3	1840.8	1866.2	1875.2	1879.2	1871.6	1879.2
175°	1770.5	1783.0	1801.0	1815.3	1813.5	1820.7	1842.2	1849.4	1856.6	1845.8	1856.6
177.5°	1777.3	1783.0	1788.8	1797.4	1791.6	1791.6	1807.4	1811.7	1813.2	1807.4	1813.2
180°	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8



TEST NUMBER: P1436020

CATALOG NUMBER: SQ2W-FB-K-125U-100D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	426.7	426.7	426.7	426.7	426.7	426.7	426.7	426.7	426.7	426.7	426.7
2.5°	485.3	476.5	466.3	456.8	448.1	439.5	431.5	423.5	431.5	439.5	448.1
5°	705.5	657.9	602.3	552.6	508.8	469.1	441.8	414.4	441.8	469.1	508.8
7.5°	1182.9	1059.2	910.0	766.1	627.5	509.7	454.0	398.4	454.0	509.7	627.5
10°	1397.4	1293.9	1164.4	979.3	738.6	538.7	461.2	383.7	461.2	538.7	738.6
12.5°	1476.3	1401.7	1310.8	1118.4	824.5	577.7	472.5	367.2	472.5	577.7	824.5
15°	1576.8	1514.1	1440.2	1242.4	920.5	641.5	491.0	340.6	491.0	641.5	920.5
17.5°	1635.8	1577.0	1503.9	1310.9	998.2	713.5	513.3	313.1	513.3	713.5	998.2
20°	1645.8	1596.1	1533.2	1350.9	1049.1	763.9	528.6	293.4	528.6	763.9	1049.1
22.5°	1636.2	1597.8	1550.2	1379.9	1086.8	801.3	538.3	275.3	538.3	801.3	1086.8
25°	1618.5	1594.1	1564.0	1408.5	1127.7	843.0	546.6	250.3	546.6	843.0	1127.7
27.5°	1585.2	1568.7	1549.0	1403.9	1133.4	852.3	539.2	226.1	539.2	852.3	1133.4
30°	1559.7	1546.2	1531.6	1391.7	1126.3	847.8	529.5	211.3	529.5	847.8	1126.3
32.5°	1539.6	1523.8	1509.9	1372.9	1112.7	837.6	517.9	198.2	517.9	837.6	1112.7
35°	1526.2	1499.7	1477.8	1337.9	1079.8	807.6	493.1	178.5	493.1	807.6	1079.8
37.5°	1532.0	1488.0	1442.2	1289.6	1030.3	760.9	461.3	161.7	461.3	760.9	1030.3
40°	1530.5	1476.5	1415.4	1254.4	993.7	726.3	439.0	151.8	439.0	726.3	993.7
42.5°	1514.1	1452.4	1381.1	1214.0	951.0	685.8	413.9	142.0	413.9	685.8	951.0
45°	1480.8	1410.1	1326.2	1149.8	880.8	618.0	373.6	129.3	373.6	618.0	880.8
47.5°	1433.6	1361.2	1272.2	1087.1	805.9	541.9	329.6	117.4	329.6	541.9	805.9
50°	1391.4	1321.2	1233.7	1045.0	755.0	490.1	300.4	110.8	300.4	490.1	755.0
52.5°	1341.8	1275.8	1193.4	1003.2	705.2	439.8	272.0	104.2	272.0	439.8	705.2
55°	1255.1	1197.5	1125.4	937.1	632.6	370.0	233.2	96.4	233.2	370.0	632.6
57.5°	1159.2	1110.2	1048.7	866.8	564.5	310.1	199.8	89.5	199.8	310.1	564.5
60°	1090.3	1045.6	990.0	815.4	521.8	277.7	181.9	86.2	181.9	277.7	521.8
62.5°	1017.9	976.7	925.5	759.6	479.1	247.9	164.6	81.2	164.6	247.9	479.1
65°	900.4	866.5	823.6	674.5	419.2	210.9	143.4	75.9	143.4	210.9	419.2
67.5°	754.9	738.3	711.7	587.0	364.4	183.0	125.8	68.5	125.8	183.0	364.4
70°	638.5	641.5	632.4	528.9	331.0	169.4	116.5	63.6	116.5	169.4	331.0
72.5°	487.0	520.6	540.6	465.2	294.3	154.4	107.4	60.3	107.4	154.4	294.3
75°	230.2	295.4	383.0	362.9	235.3	129.9	91.6	53.3	91.6	129.9	235.3
77.5°	176.8	211.2	257.5	242.3	165.5	100.8	72.1	43.5	72.1	100.8	165.5
80°	143.8	145.0	146.8	134.5	108.1	82.5	59.7	36.9	59.7	82.5	108.1
82.5°	105.5	104.5	102.7	94.4	79.6	64.3	47.3	30.4	47.3	64.3	79.6
85°	34.4	40.3	47.6	49.0	44.5	38.5	28.5	18.5	28.5	38.5	44.5
87.5°	15.7	15.4	15.4	16.5	18.3	18.2	12.7	7.6	12.7	17.8	19.0
90°	37.7	35.9	35.9	34.1	28.7	21.5	12.6	5.4	12.6	19.7	32.3
92.5°	44.8	44.5	41.6	38.4	31.6	31.6	31.2	19.7	34.1	48.4	69.6
95°	41.3	41.3	48.4	61.0	89.7	91.5	61.0	55.6	78.9	111.2	139.9
97.5°	111.6	132.7	162.9	168.6	159.6	119.1	114.1	106.2	144.6	176.5	222.8
100°	206.3	233.2	254.7	211.7	166.8	165.0	154.3	150.7	191.9	222.4	267.3
102.5°	322.5	330.8	256.2	231.8	221.4	213.8	197.3	195.2	236.4	278.4	316.1
105°	349.8	313.9	315.7	315.7	308.5	294.2	263.7	261.9	308.5	357.0	403.6
107.5°	411.5	416.9	426.2	424.0	415.8	377.4	341.5	333.3	375.3	433.4	484.7
110°	493.3	498.7	502.3	498.7	486.1	437.7	394.6	382.1	419.7	480.7	536.3



TEST NUMBER: P1436020

CATALOG NUMBER: SQ2W-FB-K-125U-100D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	572.2	576.2	584.1	573.3	552.1	496.5	447.7	429.4	467.1	529.5	586.6
115°	697.8	697.8	699.6	694.2	651.1	593.7	529.2	502.3	534.5	591.9	654.7
117.5°	821.2	823.3	816.2	801.8	752.0	685.2	612.8	569.7	595.2	655.8	720.4
120°	898.7	902.3	895.1	873.6	825.1	749.8	667.3	617.1	636.8	696.0	760.6
122.5°	979.0	978.3	969.7	945.3	888.3	810.1	729.0	667.3	675.5	730.4	793.6
125°	1090.6	1088.8	1081.6	1052.9	993.8	913.0	818.0	742.6	731.9	778.5	843.1
127.5°	1196.8	1192.9	1181.7	1146.9	1086.3	1008.5	904.1	818.7	794.6	824.1	883.3
130°	1270.0	1264.6	1244.9	1207.2	1148.0	1074.5	968.6	871.8	837.7	855.6	907.7
132.5°	1340.3	1324.9	1308.0	1267.5	1212.6	1136.2	1028.9	927.7	880.7	888.6	929.2
135°	1429.6	1415.3	1393.8	1354.3	1302.3	1226.9	1119.3	1009.9	945.3	938.1	961.5
137.5°	1508.2	1493.1	1468.7	1434.7	1382.3	1315.2	1211.9	1096.4	1014.9	990.9	999.9
140°	1557.0	1539.1	1517.5	1483.5	1436.8	1366.9	1266.4	1155.2	1063.7	1029.6	1024.2
142.5°	1597.2	1583.5	1560.6	1529.4	1488.5	1418.5	1320.9	1211.2	1113.9	1069.8	1057.3
145°	1657.5	1646.7	1621.6	1592.9	1558.8	1488.8	1399.1	1289.7	1192.9	1135.5	1108.6
147.5°	1708.4	1699.8	1680.1	1646.3	1617.6	1550.5	1468.7	1371.9	1272.5	1201.5	1166.7
150°	1740.0	1732.8	1713.1	1680.8	1652.1	1589.3	1510.4	1420.7	1325.6	1250.3	1205.4
152.5°	1770.1	1762.9	1740.3	1708.0	1683.6	1625.2	1553.4	1468.0	1371.5	1296.2	1249.9
155°	1809.9	1801.0	1779.4	1748.9	1727.4	1673.6	1607.2	1531.9	1449.4	1370.4	1318.4
157.5°	1841.5	1830.4	1810.3	1784.1	1761.1	1711.6	1653.9	1588.9	1516.8	1441.5	1388.4
160°	1860.1	1847.6	1826.1	1802.7	1781.2	1734.6	1682.6	1623.4	1557.0	1488.8	1431.4
162.5°	1873.1	1861.9	1836.1	1815.7	1797.0	1754.7	1705.5	1652.1	1592.9	1533.3	1480.2
165°	1887.1	1874.5	1847.6	1831.4	1815.3	1779.4	1736.4	1693.3	1643.1	1594.7	1551.6
167.5°	1888.1	1877.7	1850.8	1835.0	1823.2	1792.3	1757.5	1724.5	1685.4	1647.4	1611.5
170°	1885.3	1876.3	1849.4	1835.0	1826.1	1801.0	1770.5	1741.8	1711.3	1679.0	1650.3
172.5°	1875.2	1866.2	1840.8	1829.3	1824.6	1802.4	1777.6	1756.1	1729.9	1706.2	1683.3
175°	1849.4	1842.2	1820.7	1813.5	1815.3	1801.0	1783.0	1770.5	1754.3	1740.0	1727.4
177.5°	1811.7	1807.4	1791.6	1791.6	1797.4	1788.8	1783.0	1777.3	1770.1	1765.8	1761.5
180°	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8



TEST NUMBER: P1436020

CATALOG NUMBER: SQ2W-FB-K-125U-100D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	426.7	426.7	426.7	426.7	426.7	426.7	426.7	426.7	426.7	426.7	426.7
2.5°	456.8	466.3	476.5	485.3	489.7	494.0	489.7	485.3	476.5	466.3	456.8
5°	552.6	602.3	657.9	705.5	729.2	752.9	729.2	705.5	657.9	602.3	552.6
7.5°	766.1	910.0	1059.2	1182.9	1230.3	1277.7	1230.3	1182.9	1059.2	910.0	766.1
10°	979.3	1164.4	1293.9	1397.4	1422.9	1448.4	1422.9	1397.4	1293.9	1164.4	979.3
12.5°	1118.4	1310.8	1401.7	1476.3	1502.6	1528.9	1502.6	1476.3	1401.7	1310.8	1118.4
15°	1242.4	1440.2	1514.1	1576.8	1606.0	1635.1	1606.0	1576.8	1514.1	1440.2	1242.4
17.5°	1310.9	1503.9	1577.0	1635.8	1651.7	1667.5	1651.7	1635.8	1577.0	1503.9	1310.9
20°	1350.9	1533.2	1596.1	1645.8	1655.9	1665.9	1655.9	1645.8	1596.1	1533.2	1350.9
22.5°	1379.9	1550.2	1597.8	1636.2	1646.9	1657.7	1646.9	1636.2	1597.8	1550.2	1379.9
25°	1408.5	1564.0	1594.1	1618.5	1625.8	1633.1	1625.8	1618.5	1594.1	1564.0	1408.5
27.5°	1403.9	1549.0	1568.7	1585.2	1592.3	1599.4	1592.3	1585.2	1568.7	1549.0	1403.9
30°	1391.7	1531.6	1546.2	1559.7	1569.7	1579.7	1569.7	1559.7	1546.2	1531.6	1391.7
32.5°	1372.9	1509.9	1523.8	1539.6	1561.3	1583.0	1561.3	1539.6	1523.8	1509.9	1372.9
35°	1337.9	1477.8	1499.7	1526.2	1566.3	1606.4	1566.3	1526.2	1499.7	1477.8	1337.9
37.5°	1289.6	1442.2	1488.0	1532.0	1570.6	1609.3	1570.6	1532.0	1488.0	1442.2	1289.6
40°	1254.4	1415.4	1476.5	1530.5	1563.3	1596.1	1563.3	1530.5	1476.5	1415.4	1254.4
42.5°	1214.0	1381.1	1452.4	1514.1	1546.9	1579.7	1546.9	1514.1	1452.4	1381.1	1214.0
45°	1149.8	1326.2	1410.1	1480.8	1511.8	1542.8	1511.8	1480.8	1410.1	1326.2	1149.8
47.5°	1087.1	1272.2	1361.2	1433.6	1456.2	1478.8	1456.2	1433.6	1361.2	1272.2	1087.1
50°	1045.0	1233.7	1321.2	1391.4	1409.7	1427.9	1409.7	1391.4	1321.2	1233.7	1045.0
52.5°	1003.2	1193.4	1275.8	1341.8	1358.6	1375.4	1358.6	1341.8	1275.8	1193.4	1003.2
55°	937.1	1125.4	1197.5	1255.1	1269.7	1284.3	1269.7	1255.1	1197.5	1125.4	937.1
57.5°	866.8	1048.7	1110.2	1159.2	1171.1	1183.0	1171.1	1159.2	1110.2	1048.7	866.8
60°	815.4	990.0	1045.6	1090.3	1102.2	1114.0	1102.2	1090.3	1045.6	990.0	815.4
62.5°	759.6	925.5	976.7	1017.9	1029.0	1040.2	1029.0	1017.9	976.7	925.5	759.6
65°	674.5	823.6	866.5	900.4	907.7	915.0	907.7	900.4	866.5	823.6	674.5
67.5°	587.0	711.7	738.3	754.9	741.2	727.5	741.2	754.9	738.3	711.7	587.0
70°	528.9	632.4	641.5	638.5	599.3	560.1	599.3	638.5	641.5	632.4	528.9
72.5°	465.2	540.6	520.6	487.0	412.7	338.5	412.7	487.0	520.6	540.6	465.2
75°	362.9	383.0	295.4	230.2	232.1	233.9	232.1	230.2	295.4	383.0	362.9
77.5°	242.3	257.5	211.2	176.8	178.5	180.1	178.5	176.8	211.2	257.5	242.3
80°	134.5	146.8	145.0	143.8	144.8	145.7	144.8	143.8	145.0	146.8	134.5
82.5°	94.4	102.7	104.5	105.5	104.3	103.0	104.3	105.5	104.5	102.7	94.4
85°	49.0	47.6	40.3	34.4	32.6	30.8	32.6	34.4	40.3	47.6	49.0
87.5°	17.9	19.0	21.5	22.9	24.4	23.6	24.4	22.9	21.5	19.0	17.9
90°	41.3	53.8	66.4	73.5	80.7	77.1	80.7	73.5	66.4	53.8	41.3
92.5°	82.9	104.0	119.5	132.4	138.1	137.4	138.1	132.4	119.5	104.0	82.9
95°	166.8	191.9	217.0	235.0	245.7	242.2	245.7	235.0	217.0	191.9	166.8
97.5°	257.2	291.0	318.9	335.8	346.6	353.7	346.6	335.8	318.9	291.0	257.2
100°	317.5	349.8	382.1	401.8	419.7	426.9	419.7	401.8	382.1	349.8	317.5
102.5°	366.3	408.6	443.8	464.9	480.0	487.2	480.0	464.9	443.8	408.6	366.3
105°	446.7	491.5	529.2	556.1	572.2	577.6	572.2	556.1	529.2	491.5	446.7
107.5°	527.0	573.3	608.1	637.9	657.6	669.1	657.6	608.1	573.3	527.0	527.0
110°	590.2	627.8	665.5	692.4	712.1	719.3	712.1	692.4	665.5	627.8	590.2



TEST NUMBER: P1436020

CATALOG NUMBER: SQ2W-FB-K-125U-100D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	643.2	685.2	722.9	749.8	772.4	782.4	772.4	749.8	722.9	685.2	643.2
115°	717.5	773.1	807.2	832.3	848.5	857.4	848.5	832.3	807.2	773.1	717.5
117.5°	779.2	837.3	874.6	894.0	901.6	908.0	901.6	894.0	874.6	837.3	779.2
120°	818.0	871.8	914.8	939.9	948.9	952.5	948.9	939.9	914.8	871.8	818.0
122.5°	853.8	904.8	946.4	977.3	992.0	995.5	992.0	977.3	946.4	904.8	853.8
125°	904.1	952.5	995.5	1026.0	1042.2	1051.2	1042.2	1026.0	995.5	952.5	904.1
127.5°	947.8	1000.2	1039.7	1067.3	1083.1	1090.3	1083.1	1067.3	1039.7	1000.2	947.8
130°	972.2	1026.0	1065.5	1096.0	1110.3	1117.5	1110.3	1096.0	1065.5	1026.0	972.2
132.5°	990.9	1047.6	1088.5	1116.1	1131.9	1139.0	1131.9	1116.1	1088.5	1047.6	990.9
135°	1013.5	1072.7	1115.7	1142.6	1157.0	1164.2	1157.0	1142.6	1115.7	1072.7	1013.5
137.5°	1033.2	1087.0	1131.9	1160.2	1173.1	1177.8	1173.1	1160.2	1131.9	1087.0	1033.2
140°	1047.6	1094.2	1139.0	1166.0	1180.3	1182.1	1180.3	1166.0	1139.0	1094.2	1047.6
142.5°	1066.2	1102.8	1141.9	1168.8	1183.2	1186.4	1183.2	1168.8	1141.9	1102.8	1066.2
145°	1099.6	1121.1	1148.0	1173.1	1185.7	1189.3	1185.7	1173.1	1148.0	1121.1	1099.6
147.5°	1141.6	1148.4	1162.4	1178.9	1191.1	1193.6	1191.1	1178.9	1162.4	1148.4	1141.6
150°	1173.1	1171.3	1176.7	1187.5	1198.2	1196.5	1198.2	1187.5	1176.7	1171.3	1173.1
152.5°	1209.0	1198.6	1198.2	1203.3	1208.3	1207.9	1208.3	1203.3	1198.2	1198.6	1209.0
155°	1270.0	1250.3	1239.5	1235.9	1235.9	1234.1	1235.9	1235.9	1239.5	1250.3	1270.0
157.5°	1337.1	1309.5	1293.3	1284.7	1282.2	1278.2	1282.2	1284.7	1293.3	1309.5	1337.1
160°	1383.0	1352.5	1336.4	1322.0	1316.6	1311.3	1316.6	1322.0	1336.4	1352.5	1383.0
162.5°	1426.1	1397.0	1379.4	1366.5	1361.1	1352.9	1361.1	1366.5	1379.4	1397.0	1426.1
165°	1496.0	1465.5	1445.8	1435.0	1427.8	1420.7	1427.8	1435.0	1445.8	1465.5	1496.0
167.5°	1566.0	1532.6	1519.7	1507.5	1500.7	1487.8	1500.7	1507.5	1519.7	1532.6	1566.0
170°	1609.0	1578.5	1571.4	1560.6	1548.0	1533.7	1548.0	1560.6	1571.4	1578.5	1609.0
172.5°	1646.3	1625.9	1618.7	1607.9	1604.0	1592.5	1604.0	1607.9	1618.7	1625.9	1646.3
175°	1700.5	1684.4	1684.4	1682.6	1677.2	1666.4	1677.2	1682.6	1684.4	1684.4	1700.5
177.5°	1745.7	1737.1	1742.8	1742.8	1741.4	1731.4	1741.4	1742.8	1742.8	1737.1	1745.7
180°	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8



TEST NUMBER: P1436020

CATALOG NUMBER: SQ2W-FB-K-125U-100D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	426.7	426.7	426.7	426.7
2.5°	448.1	439.5	431.5	423.5
5°	508.8	469.1	441.8	414.4
7.5°	627.5	509.7	454.0	398.4
10°	738.6	538.7	461.2	383.7
12.5°	824.5	577.7	472.5	367.2
15°	920.5	641.5	491.0	340.6
17.5°	998.2	713.5	513.3	313.1
20°	1049.1	763.9	528.6	293.4
22.5°	1086.8	801.3	538.3	275.3
25°	1127.7	843.0	546.6	250.3
27.5°	1133.4	852.3	539.2	226.1
30°	1126.3	847.8	529.5	211.3
32.5°	1112.7	837.6	517.9	198.2
35°	1079.8	807.6	493.1	178.5
37.5°	1030.3	760.9	461.3	161.7
40°	993.7	726.3	439.0	151.8
42.5°	951.0	685.8	413.9	142.0
45°	880.8	618.0	373.6	129.3
47.5°	805.9	541.9	329.6	117.4
50°	755.0	490.1	300.4	110.8
52.5°	705.2	439.8	272.0	104.2
55°	632.6	370.0	233.2	96.4
57.5°	564.5	310.1	199.8	89.5
60°	521.8	277.7	181.9	86.2
62.5°	479.1	247.9	164.6	81.2
65°	419.2	210.9	143.4	75.9
67.5°	364.4	183.0	125.8	68.5
70°	331.0	169.4	116.5	63.6
72.5°	294.3	154.4	107.4	60.3
75°	235.3	129.9	91.6	53.3
77.5°	165.5	100.8	72.1	43.5
80°	108.1	82.5	59.7	36.9
82.5°	79.6	64.3	47.3	30.4
85°	44.5	38.5	28.5	18.5
87.5°	19.0	17.8	12.7	7.6
90°	32.3	19.7	12.6	5.4
92.5°	69.6	48.4	34.1	19.7
95°	139.9	111.2	78.9	55.6
97.5°	222.8	176.5	144.6	106.2
100°	267.3	222.4	191.9	150.7
102.5°	316.1	278.4	236.4	195.2
105°	403.6	357.0	308.5	261.9
107.5°	484.7	433.4	375.3	333.3
110°	536.3	480.7	419.7	382.1



TEST NUMBER: P1436020

CATALOG NUMBER: SQ2W-FB-K-125U-100D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	586.6	529.5	467.1	429.4
115°	654.7	591.9	534.5	502.3
117.5°	720.4	655.8	595.2	569.7
120°	760.6	696.0	636.8	617.1
122.5°	793.6	730.4	675.5	667.3
125°	843.1	778.5	731.9	742.6
127.5°	883.3	824.1	794.6	818.7
130°	907.7	855.6	837.7	871.8
132.5°	929.2	888.6	880.7	927.7
135°	961.5	938.1	945.3	1009.9
137.5°	999.9	990.9	1014.9	1096.4
140°	1024.2	1029.6	1063.7	1155.2
142.5°	1057.3	1069.8	1113.9	1211.2
145°	1108.6	1135.5	1192.9	1289.7
147.5°	1166.7	1201.5	1272.5	1371.9
150°	1205.4	1250.3	1325.6	1420.7
152.5°	1249.9	1296.2	1371.5	1468.0
155°	1318.4	1370.4	1449.4	1531.9
157.5°	1388.4	1441.5	1516.8	1588.9
160°	1431.4	1488.8	1557.0	1623.4
162.5°	1480.2	1533.3	1592.9	1652.1
165°	1551.6	1594.7	1643.1	1693.3
167.5°	1611.5	1647.4	1685.4	1724.5
170°	1650.3	1679.0	1711.3	1741.8
172.5°	1683.3	1706.2	1729.9	1756.1
175°	1727.4	1740.0	1754.3	1770.5
177.5°	1761.5	1765.8	1770.1	1777.3
180°	1775.8	1775.8	1775.8	1775.8



TEST NUMBER: P1436020  
 CATALOG NUMBER: SQ2W-FB-K-125U-100D-L940-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.39	13.23	13.38	14.24	15.58	21.99	22.83	22.98	23.84	25.18
	3H	13.33	14.08	14.33	15.10	16.46	23.59	24.35	24.60	25.36	26.72
	4H	13.72	14.44	14.74	15.46	16.83	23.77	24.48	24.79	25.50	26.87
	6H	13.98	14.63	15.01	15.66	17.04	23.84	24.50	24.87	25.53	26.91
	8H	14.07	14.70	15.10	15.74	17.12	23.86	24.49	24.89	25.53	26.91
	12H	14.12	14.71	15.16	15.75	17.15	23.84	24.43	24.88	25.47	26.87
4H	2H	17.11	17.82	18.13	18.84	20.21	22.35	23.06	23.37	24.09	25.45
	3H	18.23	18.83	19.27	19.88	21.26	24.24	24.83	25.27	25.88	27.26
	4H	18.51	19.06	19.56	20.10	21.51	24.46	25.00	25.50	26.04	27.45
	6H	18.65	19.12	19.70	20.18	21.58	24.59	25.05	25.64	26.12	27.52
	8H	18.69	19.12	19.74	20.18	21.60	24.63	25.07	25.68	26.13	27.54
	12H	18.69	19.08	19.76	20.16	21.58	24.61	25.01	25.68	26.08	27.50
8H	4H	19.71	20.14	20.76	21.20	22.62	24.55	24.98	25.60	26.04	27.46
	6H	19.96	20.32	21.04	21.42	22.84	24.74	25.10	25.82	26.20	27.62
	8H	20.06	20.38	21.14	21.46	22.89	24.83	25.15	25.92	26.23	27.66
	12H	20.10	20.38	21.19	21.46	22.93	24.84	25.11	25.92	26.19	27.67
12H	4H	19.73	20.12	20.80	21.20	22.62	24.50	24.89	25.57	25.96	27.39
	6H	20.07	20.39	21.15	21.47	22.90	24.72	25.04	25.81	26.12	27.56
	8H	20.21	20.48	21.29	21.56	23.04	24.82	25.10	25.91	26.18	27.65