

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427842

Luminaire Tested: SQ2W-PH1-0U-125D-L940-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1427842  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-PH1-0U-125D-L940-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - PERCEIVE HEX LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT N/A - DIRECT ONLY  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5936.4 lumens  
Efficiency: N/A  
Efficacy: 120.7 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.02 / 1.23  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 49.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1427842

CATALOG NUMBER: SQ2W-PH1-0U-125D-L940-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1427842

CATALOG NUMBER: SQ2W-PH1-0U-125D-L940-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	103	99	96	99	96	93	95	92	90	91	89	87	85
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72
3	91	81	73	67	89	80	72	67	77	71	65	74	69	64	72	67	63	61
4	84	72	64	57	82	71	63	57	69	62	56	66	60	55	64	59	55	53
5	77	65	56	50	75	64	56	49	62	54	49	60	53	48	58	52	48	46
6	72	59	50	44	70	58	49	43	56	48	43	54	48	43	53	47	42	40
7	66	53	45	39	65	52	44	38	51	43	38	49	43	38	48	42	38	36
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29
10	54	41	34	28	53	41	33	28	40	33	28	39	33	28	38	32	28	26

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	43348	43348	43348	43348
5°	43597	39622	43597	39622
10°	42593	36017	42593	36017
15°	42786	35312	42786	35312
20°	41259	35597	41259	35597
25°	40503	34769	40503	34769
30°	39624	35053	39624	35053
35°	39324	41086	39324	41086
40°	39358	32574	39358	32574
45°	39371	28055	39371	28055
50°	38820	26309	38820	26309
55°	38328	25241	38328	25241
60°	37945	23676	37945	23676
65°	37279	20592	37279	20592
70°	35211	14714	35211	14714
75°	31390	11154	31390	11154
80°	25653	10451	25653	10451
85°	16098	7095	16098	7095

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 39371 cd/sqm



TEST NUMBER: P1427842

CATALOG NUMBER: SQ2W-PH1-0U-125D-L940-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	236.3	4.0
10°-20°	621.4	10.5
20°-30°	911.1	15.3
30°-40°	1103.2	18.6
40°-50°	1084.8	18.3
50°-60°	943.6	15.9
60°-70°	656.3	11.1
70°-80°	311.2	5.2
80°-90°	68.6	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1768.7	29.8
0°-40°	2871.9	48.4
0°-60°	4900.3	82.5
0°-90°	5936.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5936.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	2685	2685	2685	2685	2685	
5°	2690	2445	2690	2445	2690	253
15°	2560	2113	2560	2113	2560	714
25°	2274	1952	2274	1952	2274	1046
35°	1995	2084	1995	2084	1995	1250
45°	1724	1229	1724	1229	1724	1325
55°	1362	897	1362	897	1362	1216
65°	976	539	976	539	976	959
75°	503	179	503	179	503	533
85°	87	38	87	38	87	119
90°	0	0	0	0	0	



TEST NUMBER: P1427842

CATALOG NUMBER: SQ2W-PH1-OU-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2684.8	2684.8	2684.8	2684.8	2684.8	2684.8	2684.8	2684.8	2684.8	2684.8	2684.8
2.5°	2678.7	2691.4	2704.1	2686.2	2658.1	2638.5	2627.6	2619.0	2617.2	2615.4	2617.2
5°	2690.0	2688.8	2687.7	2634.6	2564.2	2511.4	2476.2	2449.3	2447.0	2444.7	2447.0
7.5°	2640.9	2605.7	2570.5	2499.2	2415.9	2354.8	2316.0	2286.4	2284.6	2282.8	2284.6
10°	2598.0	2544.6	2491.3	2410.7	2321.0	2258.5	2223.3	2196.9	2196.9	2196.9	2196.9
12.5°	2587.8	2503.5	2419.3	2331.0	2241.3	2183.4	2157.2	2139.0	2144.5	2149.9	2144.5
15°	2559.7	2432.5	2305.4	2215.7	2138.5	2096.4	2089.6	2087.6	2100.1	2112.6	2100.1
17.5°	2466.7	2329.8	2192.8	2114.0	2054.5	2032.0	2046.5	2061.1	2075.6	2090.1	2075.6
20°	2401.3	2266.2	2131.1	2058.1	2005.9	1993.4	2020.7	2044.5	2058.1	2071.8	2058.1
22.5°	2346.1	2209.2	2072.3	2007.7	1967.3	1962.1	1992.0	2016.3	2023.6	2030.9	2023.6
25°	2273.6	2119.2	1964.7	1917.6	1906.3	1913.7	1939.8	1958.5	1955.1	1951.7	1955.1
27.5°	2186.7	2025.5	1864.3	1834.0	1847.4	1862.1	1877.9	1890.4	1892.4	1894.5	1892.4
30°	2125.4	1964.2	1803.0	1778.8	1800.4	1819.1	1835.0	1850.6	1865.4	1880.2	1865.4
32.5°	2066.1	1899.5	1732.8	1715.5	1747.9	1783.0	1820.7	1857.5	1891.3	1925.1	1891.3
35°	1995.1	1821.4	1647.7	1634.1	1673.8	1724.9	1787.3	1862.0	1973.3	2084.5	1973.3
37.5°	1920.5	1734.3	1548.1	1541.9	1595.8	1649.6	1703.4	1752.6	1788.0	1823.4	1788.0
40°	1867.4	1672.1	1476.8	1476.5	1541.3	1608.2	1677.5	1709.0	1627.3	1545.5	1627.3
42.5°	1810.2	1614.9	1419.6	1413.9	1471.3	1545.1	1635.3	1668.4	1530.3	1392.2	1530.3
45°	1724.3	1521.1	1317.9	1310.5	1368.4	1409.3	1433.1	1426.3	1327.5	1228.7	1327.5
47.5°	1623.2	1429.5	1235.8	1234.2	1296.6	1301.2	1247.8	1198.1	1159.5	1120.9	1159.5
50°	1545.5	1362.7	1179.9	1187.9	1259.4	1252.6	1167.4	1097.3	1072.3	1047.4	1072.3
52.5°	1469.9	1296.2	1122.5	1143.6	1229.7	1216.0	1102.7	1013.5	996.7	979.9	996.7
55°	1361.6	1194.7	1027.8	1075.5	1194.7	1176.5	1021.0	903.5	900.1	896.7	900.1
57.5°	1246.6	1088.8	931.0	964.1	1060.8	1041.8	906.9	807.2	813.1	819.0	813.1
60°	1175.1	1021.8	868.6	872.8	929.6	911.4	818.3	746.8	740.0	733.2	740.0
62.5°	1099.5	953.5	807.5	786.3	806.7	785.4	722.3	673.2	666.4	659.6	666.4
65°	975.8	843.0	710.2	670.1	661.1	630.4	578.2	539.0	539.0	539.0	539.0
67.5°	839.9	724.1	608.3	563.5	542.4	512.0	472.3	435.6	408.4	381.1	408.4
70°	745.9	643.8	541.6	494.7	466.4	430.0	385.7	348.0	329.8	311.7	329.8
72.5°	645.8	558.1	470.5	422.5	387.8	352.4	316.3	284.0	263.1	242.2	263.1
75°	503.2	432.9	362.5	315.9	277.3	241.5	208.6	183.4	181.1	178.8	181.1
77.5°	363.8	312.5	261.1	223.4	190.3	165.4	148.8	136.5	136.7	136.9	136.7
80°	275.9	237.3	198.7	163.5	129.4	111.8	110.7	110.1	111.3	112.4	111.3
82.5°	194.1	165.5	136.9	114.4	94.0	84.6	86.2	87.4	87.6	87.9	87.6
85°	86.9	73.2	59.6	54.5	52.2	48.8	44.3	40.6	39.5	38.3	39.5
87.5°	18.4	17.5	16.6	14.3	11.6	10.2	10.2	10.2	10.2	10.2	10.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1427842

CATALOG NUMBER: SQ2W-PH1-0U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2684.8	2684.8	2684.8	2684.8	2684.8	2684.8	2684.8	2684.8	2684.8	2684.8	2684.8
2.5°	2619.0	2627.6	2638.5	2658.1	2686.2	2704.1	2691.4	2678.7	2691.4	2704.1	2686.2
5°	2449.3	2476.2	2511.4	2564.2	2634.6	2687.7	2688.8	2690.0	2688.8	2687.7	2634.6
7.5°	2286.4	2316.0	2354.8	2415.9	2499.2	2570.5	2605.7	2640.9	2605.7	2570.5	2499.2
10°	2196.9	2223.3	2258.5	2321.0	2410.7	2491.3	2544.6	2598.0	2544.6	2491.3	2410.7
12.5°	2139.0	2157.2	2183.4	2241.3	2331.0	2419.3	2503.5	2587.8	2503.5	2419.3	2331.0
15°	2087.6	2089.6	2096.4	2138.5	2215.7	2305.4	2432.5	2559.7	2432.5	2305.4	2215.7
17.5°	2061.1	2046.5	2032.0	2054.5	2114.0	2192.8	2329.8	2466.7	2329.8	2192.8	2114.0
20°	2044.5	2020.7	1993.4	2005.9	2058.1	2131.1	2266.2	2401.3	2266.2	2131.1	2058.1
22.5°	2016.3	1992.0	1962.1	1967.3	2007.7	2072.3	2209.2	2346.1	2209.2	2072.3	2007.7
25°	1958.5	1939.8	1913.7	1906.3	1917.6	1964.7	2119.2	2273.6	2119.2	1964.7	1917.6
27.5°	1890.4	1877.9	1862.1	1847.4	1834.0	1864.3	2025.5	2186.7	2025.5	1864.3	1834.0
30°	1850.6	1835.0	1819.1	1800.4	1778.8	1803.0	1964.2	2125.4	1964.2	1803.0	1778.8
32.5°	1857.5	1820.7	1783.0	1747.9	1715.5	1732.8	1899.5	2066.1	1899.5	1732.8	1715.5
35°	1862.0	1787.3	1724.9	1673.8	1634.1	1647.7	1821.4	1995.1	1821.4	1647.7	1634.1
37.5°	1752.6	1703.4	1649.6	1595.8	1541.9	1548.1	1734.3	1920.5	1734.3	1548.1	1541.9
40°	1709.0	1677.5	1608.2	1541.3	1476.5	1476.8	1672.1	1867.4	1672.1	1476.8	1476.5
42.5°	1668.4	1635.3	1545.1	1471.3	1413.9	1419.6	1614.9	1810.2	1614.9	1419.6	1413.9
45°	1426.3	1433.1	1409.3	1368.4	1310.5	1317.9	1521.1	1724.3	1521.1	1317.9	1310.5
47.5°	1198.1	1247.8	1301.2	1296.6	1234.2	1235.8	1429.5	1623.2	1429.5	1235.8	1234.2
50°	1097.3	1167.4	1252.6	1259.4	1187.9	1179.9	1362.7	1545.5	1362.7	1179.9	1187.9
52.5°	1013.5	1102.7	1216.0	1229.7	1143.6	1122.5	1296.2	1469.9	1296.2	1122.5	1143.6
55°	903.5	1021.0	1176.5	1194.7	1075.5	1027.8	1194.7	1361.6	1194.7	1027.8	1075.5
57.5°	807.2	906.9	1041.8	1060.8	964.1	931.0	1088.8	1246.6	1088.8	931.0	964.1
60°	746.8	818.3	911.4	929.6	872.8	868.6	1021.8	1175.1	1021.8	868.6	872.8
62.5°	673.2	722.3	785.4	806.7	786.3	807.5	953.5	1099.5	953.5	807.5	786.3
65°	539.0	578.2	630.4	661.1	670.1	710.2	843.0	975.8	843.0	710.2	670.1
67.5°	435.6	472.3	512.0	542.4	563.5	608.3	724.1	839.9	724.1	608.3	563.5
70°	348.0	385.7	430.0	466.4	494.7	541.6	643.8	745.9	643.8	541.6	494.7
72.5°	284.0	316.3	352.4	387.8	422.5	470.5	558.1	645.8	558.1	470.5	422.5
75°	183.4	208.6	241.5	277.3	315.9	362.5	432.9	503.2	432.9	362.5	315.9
77.5°	136.5	148.8	165.4	190.3	223.4	261.1	312.5	363.8	312.5	261.1	223.4
80°	110.1	110.7	111.8	129.4	163.5	198.7	237.3	275.9	237.3	198.7	163.5
82.5°	87.4	86.2	84.6	94.0	114.4	136.9	165.5	194.1	165.5	136.9	114.4
85°	40.6	44.3	48.8	52.2	54.5	59.6	73.2	86.9	73.2	59.6	54.5
87.5°	10.2	10.2	10.2	11.6	14.3	16.6	17.5	18.4	17.5	16.6	14.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1427842

CATALOG NUMBER: SQ2W-PH1-0U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2684.8	2684.8	2684.8	2684.8	2684.8	2684.8	2684.8	2684.8	2684.8	2684.8	2684.8
2.5°	2658.1	2638.5	2627.6	2619.0	2617.2	2615.4	2617.2	2619.0	2627.6	2638.5	2658.1
5°	2564.2	2511.4	2476.2	2449.3	2447.0	2444.7	2447.0	2449.3	2476.2	2511.4	2564.2
7.5°	2415.9	2354.8	2316.0	2286.4	2284.6	2282.8	2284.6	2286.4	2316.0	2354.8	2415.9
10°	2321.0	2258.5	2223.3	2196.9	2196.9	2196.9	2196.9	2196.9	2223.3	2258.5	2321.0
12.5°	2241.3	2183.4	2157.2	2139.0	2144.5	2149.9	2144.5	2139.0	2157.2	2183.4	2241.3
15°	2138.5	2096.4	2089.6	2087.6	2100.1	2112.6	2100.1	2087.6	2089.6	2096.4	2138.5
17.5°	2054.5	2032.0	2046.5	2061.1	2075.6	2090.1	2075.6	2061.1	2046.5	2032.0	2054.5
20°	2005.9	1993.4	2020.7	2044.5	2058.1	2071.8	2058.1	2044.5	2020.7	1993.4	2005.9
22.5°	1967.3	1962.1	1992.0	2016.3	2023.6	2030.9	2023.6	2016.3	1992.0	1962.1	1967.3
25°	1906.3	1913.7	1939.8	1958.5	1955.1	1951.7	1955.1	1958.5	1939.8	1913.7	1906.3
27.5°	1847.4	1862.1	1877.9	1890.4	1892.4	1894.5	1892.4	1890.4	1877.9	1862.1	1847.4
30°	1800.4	1819.1	1835.0	1850.6	1865.4	1880.2	1865.4	1850.6	1835.0	1819.1	1800.4
32.5°	1747.9	1783.0	1820.7	1857.5	1891.3	1925.1	1891.3	1857.5	1820.7	1783.0	1747.9
35°	1673.8	1724.9	1787.3	1862.0	1973.3	2084.5	1973.3	1862.0	1787.3	1724.9	1673.8
37.5°	1595.8	1649.6	1703.4	1752.6	1788.0	1823.4	1788.0	1752.6	1703.4	1649.6	1595.8
40°	1541.3	1608.2	1677.5	1709.0	1627.3	1545.5	1627.3	1709.0	1677.5	1608.2	1541.3
42.5°	1471.3	1545.1	1635.3	1668.4	1530.3	1392.2	1530.3	1668.4	1635.3	1545.1	1471.3
45°	1368.4	1409.3	1433.1	1426.3	1327.5	1228.7	1327.5	1426.3	1433.1	1409.3	1368.4
47.5°	1296.6	1301.2	1247.8	1198.1	1159.5	1120.9	1159.5	1198.1	1247.8	1301.2	1296.6
50°	1259.4	1252.6	1167.4	1097.3	1072.3	1047.4	1072.3	1097.3	1167.4	1252.6	1259.4
52.5°	1229.7	1216.0	1102.7	1013.5	996.7	979.9	996.7	1013.5	1102.7	1216.0	1229.7
55°	1194.7	1176.5	1021.0	903.5	900.1	896.7	900.1	903.5	1021.0	1176.5	1194.7
57.5°	1060.8	1041.8	906.9	807.2	813.1	819.0	813.1	807.2	906.9	1041.8	1060.8
60°	929.6	911.4	818.3	746.8	740.0	733.2	740.0	746.8	818.3	911.4	929.6
62.5°	806.7	785.4	722.3	673.2	666.4	659.6	666.4	673.2	722.3	785.4	806.7
65°	661.1	630.4	578.2	539.0	539.0	539.0	539.0	578.2	630.4	661.1	661.1
67.5°	542.4	512.0	472.3	435.6	408.4	381.1	408.4	435.6	472.3	512.0	542.4
70°	466.4	430.0	385.7	348.0	329.8	311.7	329.8	348.0	385.7	430.0	466.4
72.5°	387.8	352.4	316.3	284.0	263.1	242.2	263.1	284.0	316.3	352.4	387.8
75°	277.3	241.5	208.6	183.4	181.1	178.8	181.1	183.4	208.6	241.5	277.3
77.5°	190.3	165.4	148.8	136.5	136.7	136.9	136.7	136.5	148.8	165.4	190.3
80°	129.4	111.8	110.7	110.1	111.3	112.4	111.3	110.1	110.7	111.8	129.4
82.5°	94.0	84.6	86.2	87.4	87.6	87.9	87.6	87.4	86.2	84.6	94.0
85°	52.2	48.8	44.3	40.6	39.5	38.3	39.5	40.6	44.3	48.8	52.2
87.5°	11.6	10.2	10.2	10.2	10.2	10.2	10.2	10.2	10.2	10.2	11.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1427842

CATALOG NUMBER: SQ2W-PH1-0U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	2684.8	2684.8	2684.8	2684.8
2.5°	2686.2	2704.1	2691.4	2678.7
5°	2634.6	2687.7	2688.8	2690.0
7.5°	2499.2	2570.5	2605.7	2640.9
10°	2410.7	2491.3	2544.6	2598.0
12.5°	2331.0	2419.3	2503.5	2587.8
15°	2215.7	2305.4	2432.5	2559.7
17.5°	2114.0	2192.8	2329.8	2466.7
20°	2058.1	2131.1	2266.2	2401.3
22.5°	2007.7	2072.3	2209.2	2346.1
25°	1917.6	1964.7	2119.2	2273.6
27.5°	1834.0	1864.3	2025.5	2186.7
30°	1778.8	1803.0	1964.2	2125.4
32.5°	1715.5	1732.8	1899.5	2066.1
35°	1634.1	1647.7	1821.4	1995.1
37.5°	1541.9	1548.1	1734.3	1920.5
40°	1476.5	1476.8	1672.1	1867.4
42.5°	1413.9	1419.6	1614.9	1810.2
45°	1310.5	1317.9	1521.1	1724.3
47.5°	1234.2	1235.8	1429.5	1623.2
50°	1187.9	1179.9	1362.7	1545.5
52.5°	1143.6	1122.5	1296.2	1469.9
55°	1075.5	1027.8	1194.7	1361.6
57.5°	964.1	931.0	1088.8	1246.6
60°	872.8	868.6	1021.8	1175.1
62.5°	786.3	807.5	953.5	1099.5
65°	670.1	710.2	843.0	975.8
67.5°	563.5	608.3	724.1	839.9
70°	494.7	541.6	643.8	745.9
72.5°	422.5	470.5	558.1	645.8
75°	315.9	362.5	432.9	503.2
77.5°	223.4	261.1	312.5	363.8
80°	163.5	198.7	237.3	275.9
82.5°	114.4	136.9	165.5	194.1
85°	54.5	59.6	73.2	86.9
87.5°	14.3	16.6	17.5	18.4
90°	0.0	0.0	0.0	0.0



TEST NUMBER: P1427842  
 CATALOG NUMBER: SQ2W-PH1-0U-125D-L940-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	23.82	25.41	24.18	25.72	26.04	22.64	24.24	23.01	24.55	24.86
	3H	26.04	27.47	26.42	27.80	28.16	23.75	25.18	24.12	25.51	25.87
	4H	26.89	28.23	27.29	28.58	28.96	24.02	25.37	24.42	25.72	26.09
	6H	27.39	28.64	27.80	29.00	29.39	24.20	25.45	24.61	25.81	26.20
	8H	27.56	28.75	27.99	29.14	29.54	24.28	25.47	24.71	25.85	26.25
	12H	27.65	28.78	28.08	29.16	29.59	24.31	25.45	24.74	25.83	26.26
4H	2H	24.34	25.68	24.74	26.03	26.41	23.41	24.76	23.81	25.11	25.48
	3H	26.65	27.77	27.06	28.17	28.57	24.71	25.83	25.12	26.23	26.63
	4H	27.56	28.56	27.99	28.98	29.42	25.03	26.04	25.46	26.45	26.89
	6H	28.16	29.03	28.61	29.47	29.93	25.27	26.15	25.72	26.59	27.04
	8H	28.37	29.19	28.83	29.64	30.10	25.37	26.19	25.83	26.64	27.10
	12H	28.49	29.23	28.97	29.70	30.17	25.43	26.17	25.91	26.64	27.11
8H	4H	27.63	28.45	28.10	28.90	29.36	25.31	26.13	25.78	26.58	27.04
	6H	28.29	28.97	28.79	29.46	29.94	25.61	26.29	26.11	26.78	27.26
	8H	28.56	29.17	29.07	29.68	30.16	25.76	26.37	26.28	26.88	27.37
	12H	28.72	29.26	29.23	29.75	30.32	25.86	26.40	26.37	26.89	27.45
12H	4H	27.62	28.35	28.10	28.83	29.30	25.34	26.08	25.83	26.56	27.03
	6H	28.27	28.88	28.79	29.39	29.88	25.65	26.26	26.16	26.77	27.26
	8H	28.58	29.12	29.09	29.61	30.17	25.85	26.38	26.36	26.88	27.44