

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428361

Luminaire Tested: SQ2W-PW1-K-025U-100D-L840-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1428361  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-PW1-K-025U-100D-L840-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - PERCEIVE WAVES LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6396.2 lumens  
Efficiency: N/A  
Efficacy: 141.8 lumens/watt  
Spacing Criteria (0/90/45): 1.27 / 1.11 / 1.23  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 45.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1428361

CATALOG NUMBER: SQ2W-PW1-K-025U-100D-L840-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1428361

CATALOG NUMBER: SQ2W-PW1-K-025U-100D-L840-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	115	115	115	115	110	110	110	110	101	101	101	93	93	93	86	86	86	82
1	106	102	98	95	102	98	95	92	90	88	86	84	82	80	77	76	74	71
2	97	90	84	79	93	87	81	77	80	76	72	75	71	68	69	67	64	61
3	89	80	73	67	86	77	71	65	72	66	62	67	62	59	62	59	56	53
4	82	72	64	58	79	69	62	56	65	59	54	60	55	51	56	52	49	46
5	76	64	56	50	73	62	55	49	58	52	47	55	49	45	51	47	43	41
6	71	58	50	44	68	57	49	43	53	47	42	50	44	40	47	42	38	36
7	66	53	45	39	63	52	44	39	48	42	37	46	40	36	43	38	34	32
8	61	49	41	35	59	47	40	35	45	38	34	42	36	32	40	35	31	29
9	57	45	37	32	55	44	36	31	41	35	30	39	33	29	37	32	28	27
10	54	41	34	29	52	40	33	29	38	32	28	36	31	27	34	29	26	24

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	38320	38320	38320	38320
5°	38063	38722	38063	38722
10°	38132	39059	38132	39059
15°	38122	39294	38122	39294
20°	38138	38527	38138	38527
25°	37933	35799	37933	35799
30°	37674	32365	37674	32365
35°	37380	29226	37380	29226
40°	36635	25821	36635	25821
45°	35200	22555	35200	22555
50°	32759	19303	32759	19303
55°	29967	15654	29967	15654
60°	26860	13504	26860	13504
65°	23488	12004	23488	12004
70°	19208	10886	19208	10886
75°	14947	10012	14947	10012
80°	11139	8824	11139	8824
85°	7540	5020	7540	5020

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 35200 cd/sqm



TEST NUMBER: P1428361

CATALOG NUMBER: SQ2W-PW1-K-025U-100D-L840-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	226.0	3.5
10°-20°	654.8	10.2
20°-30°	963.7	15.1
30°-40°	1053.6	16.5
40°-50°	945.2	14.8
50°-60°	705.1	11.0
60°-70°	445.6	7.0
70°-80°	220.8	3.5
80°-90°	53.3	0.8
90°-100°	30.8	0.5
100°-110°	89.7	1.4
110°-120°	146.3	2.3
120°-130°	185.7	2.9
130°-140°	198.7	3.1
140°-150°	185.5	2.9
150°-160°	152.7	2.4
160°-170°	102.4	1.6
170°-180°	36.4	0.6
0°-30°	1844.5	28.8
0°-40°	2898.1	45.3
0°-60°	4548.4	71.1
0°-90°	5268.0	82.4
90°-120°	266.8	4.2
90°-150°	836.7	13.1
90°-180°	1128.0	17.6
0°-180°	6396.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	2373	2373	2373	2373	2373	
5°	2348	2389	2348	2389	2348	223
15°	2281	2351	2281	2351	2281	644
25°	2129	2010	2129	2010	2129	981
35°	1896	1483	1896	1483	1896	1183
45°	1542	988	1542	988	1542	1182
55°	1065	556	1065	556	1065	951
65°	615	314	615	314	615	609
75°	240	160	240	160	240	264
85°	41	27	41	27	41	52
90°	1	9	1	17	1	2
95°	12	9	12	53	12	15
105°	57	91	57	126	57	61
115°	109	151	109	186	109	108
125°	162	240	162	229	162	145
135°	220	314	220	253	220	170
145°	281	362	281	259	281	176
155°	333	393	333	268	333	153
165°	368	410	368	309	368	104
175°	385	402	385	363	385	37
180°	386	386	386	386	386	



TEST NUMBER: P1428361

CATALOG NUMBER: SQ2W-PW1-K-025U-100D-L840-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4
2.5°	2357.1	2370.8	2384.4	2381.2	2372.4	2368.4	2369.2	2370.4	2372.8	2375.2	2372.8
5°	2348.5	2365.6	2382.7	2380.2	2371.1	2367.1	2368.1	2371.1	2380.2	2389.2	2380.2
7.5°	2336.8	2354.1	2371.3	2370.5	2363.7	2362.0	2365.4	2370.2	2379.0	2387.9	2379.0
10°	2325.9	2344.0	2362.1	2362.1	2356.1	2355.6	2360.6	2366.4	2374.4	2382.4	2374.4
12.5°	2311.5	2330.4	2349.2	2350.6	2346.2	2346.9	2352.8	2359.1	2367.2	2375.2	2367.2
15°	2280.7	2300.8	2320.9	2325.2	2324.2	2327.2	2334.2	2340.7	2345.8	2350.8	2345.8
17.5°	2245.0	2265.1	2285.2	2289.2	2287.8	2288.0	2289.8	2291.7	2294.1	2296.5	2294.1
20°	2219.7	2239.8	2259.9	2262.6	2259.6	2254.6	2247.6	2242.3	2242.3	2242.3	2242.3
22.5°	2183.5	2205.2	2226.9	2227.1	2220.0	2207.0	2187.9	2172.0	2165.5	2159.1	2165.5
25°	2129.3	2150.4	2171.5	2161.7	2141.6	2111.9	2072.8	2039.6	2024.5	2009.5	2024.5
27.5°	2066.0	2083.1	2100.1	2074.6	2034.8	1987.1	1931.4	1884.5	1863.6	1842.7	1863.6
30°	2020.8	2033.8	2046.9	2006.5	1948.2	1888.4	1827.1	1776.2	1756.1	1736.0	1756.1
32.5°	1973.8	1978.8	1983.8	1930.5	1857.8	1789.6	1725.9	1672.7	1651.0	1629.3	1651.0
35°	1896.5	1887.4	1878.4	1807.5	1716.1	1638.3	1574.0	1521.0	1501.9	1482.8	1501.9
37.5°	1805.1	1778.2	1751.3	1671.5	1574.0	1491.6	1424.3	1368.6	1347.5	1326.4	1347.5
40°	1738.2	1700.1	1661.9	1576.2	1474.8	1390.4	1323.1	1267.3	1246.2	1225.1	1246.2
42.5°	1664.1	1616.3	1568.5	1480.4	1378.9	1294.5	1227.2	1171.3	1149.4	1127.5	1149.4
45°	1541.6	1485.3	1429.1	1337.4	1233.9	1149.5	1084.2	1030.0	1008.9	987.8	1008.9
47.5°	1403.7	1347.8	1292.0	1200.6	1097.3	1014.0	950.7	898.7	880.6	862.6	880.6
50°	1304.2	1250.0	1195.7	1108.3	1009.9	929.0	865.7	812.7	790.6	768.5	790.6
52.5°	1203.0	1154.4	1105.7	1021.5	925.5	845.0	780.1	723.9	693.8	663.6	693.8
55°	1064.6	1018.4	972.2	892.8	802.4	721.1	648.7	590.2	573.1	556.1	573.1
57.5°	922.2	882.3	842.3	770.9	689.2	615.4	549.7	496.9	482.9	468.8	482.9
60°	831.8	796.7	761.5	693.2	613.8	546.5	491.3	446.3	432.2	418.2	432.2
62.5°	745.0	713.9	682.7	617.2	540.3	479.8	435.8	399.9	388.2	376.6	388.2
65°	614.8	591.7	568.6	514.6	450.3	400.1	363.9	334.3	324.2	314.2	324.2
67.5°	488.2	475.4	462.5	422.1	372.5	331.8	300.0	274.6	267.9	261.3	267.9
70°	406.9	402.8	398.8	365.4	322.2	287.6	261.5	240.6	235.6	230.6	235.6
72.5°	336.3	338.0	339.6	311.8	274.2	245.2	224.7	208.5	205.0	201.6	205.0
75°	239.6	247.6	255.7	237.3	210.2	189.6	175.6	164.5	162.5	160.5	162.5
77.5°	163.2	175.3	187.3	175.4	155.5	140.3	129.9	121.7	120.1	118.4	120.1
80°	119.8	131.9	143.9	135.6	120.6	109.0	101.0	94.9	94.9	94.9	94.9
82.5°	83.6	93.3	102.9	97.0	86.0	78.5	74.4	71.4	71.4	71.4	71.4
85°	40.7	45.7	50.7	49.0	45.0	39.9	33.9	29.1	28.1	27.1	28.1
87.5°	11.1	13.8	16.6	14.5	10.7	8.4	7.6	7.1	7.1	7.1	7.1
90°	1.2	2.7	4.7	6.2	7.4	7.8	7.8	8.2	8.6	8.6	8.6
92.5°	4.3	6.8	6.9	6.9	8.4	9.1	9.7	9.8	10.1	10.1	10.1
95°	12.1	13.3	19.9	19.5	13.3	10.5	9.0	9.0	9.0	9.0	9.0
97.5°	23.1	24.8	25.9	34.7	36.7	35.4	28.9	24.3	21.7	20.5	21.7
100°	32.8	33.6	35.9	36.3	46.1	55.4	50.7	44.9	42.9	41.8	42.9
102.5°	42.5	42.9	46.5	48.2	50.4	55.7	72.0	70.2	68.8	68.6	68.8
105°	57.0	57.4	64.0	67.1	68.7	68.7	68.3	76.1	88.6	91.3	88.6
107.5°	72.5	74.3	82.1	90.5	92.3	92.7	90.7	89.5	89.1	89.4	89.1
110°	83.1	85.9	95.2	105.8	108.5	109.3	108.5	107.3	106.5	106.5	106.5

TEST NUMBER: P1428361

CATALOG NUMBER: SQ2W-PW1-K-025U-100D-L840-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	93.4	97.4	108.0	120.1	124.7	127.1	125.4	124.5	123.7	124.3	123.7
115°	109.3	115.1	129.2	141.7	151.0	152.2	151.8	151.8	151.4	151.4	151.4
117.5°	123.9	133.3	149.1	163.6	174.4	177.6	179.1	178.7	178.2	179.0	178.2
120°	134.3	145.2	163.1	179.5	190.1	194.7	196.3	195.5	196.3	195.5	196.3
122.5°	145.2	158.6	176.2	193.3	205.7	211.0	212.9	213.0	213.2	212.7	213.2
125°	161.6	178.0	198.6	216.2	229.1	235.3	236.9	237.3	238.1	240.0	238.1
127.5°	178.1	196.7	219.4	236.3	249.5	257.1	259.5	260.4	262.0	262.9	262.0
130°	189.7	210.7	233.8	249.8	262.7	270.8	275.1	276.3	278.3	277.9	278.3
132.5°	201.8	223.9	247.2	263.8	275.8	284.6	288.3	291.6	292.3	292.9	292.3
135°	219.7	243.5	266.9	283.3	294.7	303.2	307.9	311.0	313.0	314.2	313.0
137.5°	238.5	263.7	286.1	300.7	312.1	319.6	324.9	328.1	330.2	331.1	330.2
140°	251.3	275.5	297.4	312.6	322.8	330.2	334.8	338.8	341.1	341.1	341.1
142.5°	263.5	287.4	308.6	323.8	332.7	339.5	344.5	347.5	350.1	350.1	350.1
145°	280.6	304.4	323.9	339.1	346.6	352.8	358.3	360.6	362.2	362.2	362.2
147.5°	298.5	319.6	337.3	351.9	358.2	365.5	369.8	371.7	373.6	372.8	373.6
150°	309.1	328.6	345.8	359.4	365.7	372.7	377.0	378.6	380.5	379.3	380.5
152.5°	319.4	338.0	353.6	366.3	371.6	378.6	383.6	385.1	386.4	385.6	386.4
155°	333.3	349.7	364.1	375.8	380.5	387.1	391.8	393.8	395.3	393.4	395.3
157.5°	345.7	359.8	372.4	383.2	388.2	393.9	398.2	400.6	402.2	401.4	402.2
160°	353.2	366.1	377.4	387.5	392.2	397.3	402.0	404.7	406.3	405.1	406.3
162.5°	359.4	371.1	381.8	391.0	395.0	399.5	405.1	407.5	409.1	407.6	409.1
165°	368.4	377.8	387.1	395.0	398.5	402.0	407.8	410.6	411.7	410.2	411.7
167.5°	375.2	382.4	390.0	396.7	399.2	402.7	408.5	410.8	412.3	410.3	412.3
170°	379.0	385.2	391.8	397.3	399.2	402.4	408.2	410.2	411.3	409.4	411.3
172.5°	382.1	386.8	392.1	397.0	398.0	400.5	406.0	408.0	408.8	407.2	408.8
175°	385.2	387.9	391.8	395.0	394.6	396.1	400.8	402.4	403.9	401.6	403.9
177.5°	386.7	387.9	389.2	391.0	389.8	389.8	393.2	394.2	394.5	393.2	394.5
180°	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4



TEST NUMBER: P1428361

CATALOG NUMBER: SQ2W-PW1-K-025U-100D-L840-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4
2.5°	2370.4	2369.2	2368.4	2372.4	2381.2	2384.4	2370.8	2357.1	2370.8	2384.4	2381.2
5°	2371.1	2368.1	2367.1	2371.1	2380.2	2382.7	2365.6	2348.5	2365.6	2382.7	2380.2
7.5°	2370.2	2365.4	2362.0	2363.7	2370.5	2371.3	2354.1	2336.8	2354.1	2371.3	2370.5
10°	2366.4	2360.6	2355.6	2356.1	2362.1	2362.1	2344.0	2325.9	2344.0	2362.1	2362.1
12.5°	2359.1	2352.8	2346.9	2346.2	2350.6	2349.2	2330.4	2311.5	2330.4	2349.2	2350.6
15°	2340.7	2334.2	2327.2	2324.2	2325.2	2320.9	2300.8	2280.7	2300.8	2320.9	2325.2
17.5°	2291.7	2289.8	2288.0	2287.8	2289.2	2285.2	2265.1	2245.0	2265.1	2285.2	2289.2
20°	2242.3	2247.6	2254.6	2259.6	2262.6	2259.9	2239.8	2219.7	2239.8	2259.9	2262.6
22.5°	2172.0	2187.9	2207.0	2220.0	2227.1	2226.9	2205.2	2183.5	2205.2	2226.9	2227.1
25°	2039.6	2072.8	2111.9	2141.6	2161.7	2171.5	2150.4	2129.3	2150.4	2171.5	2161.7
27.5°	1884.5	1931.4	1987.1	2034.8	2074.6	2100.1	2083.1	2066.0	2083.1	2100.1	2074.6
30°	1776.2	1827.1	1888.4	1948.2	2006.5	2046.9	2033.8	2020.8	2033.8	2046.9	2006.5
32.5°	1672.7	1725.9	1789.6	1857.8	1930.5	1983.8	1978.8	1973.8	1978.8	1983.8	1930.5
35°	1521.0	1574.0	1638.3	1716.1	1807.5	1878.4	1887.4	1896.5	1887.4	1878.4	1807.5
37.5°	1368.6	1424.3	1491.6	1574.0	1671.5	1751.3	1778.2	1805.1	1778.2	1751.3	1671.5
40°	1267.3	1323.1	1390.4	1474.8	1576.2	1661.9	1700.1	1738.2	1700.1	1661.9	1576.2
42.5°	1171.3	1227.2	1294.5	1378.9	1480.4	1568.5	1616.3	1664.1	1616.3	1568.5	1480.4
45°	1030.0	1084.2	1149.5	1233.9	1337.4	1429.1	1485.3	1541.6	1485.3	1429.1	1337.4
47.5°	898.7	950.7	1014.0	1097.3	1200.6	1292.0	1347.8	1403.7	1347.8	1292.0	1200.6
50°	812.7	865.7	929.0	1009.9	1108.3	1195.7	1250.0	1304.2	1250.0	1195.7	1108.3
52.5°	723.9	780.1	845.0	925.5	1021.5	1105.7	1154.4	1203.0	1154.4	1105.7	1021.5
55°	590.2	648.7	721.1	802.4	892.8	972.2	1018.4	1064.6	1018.4	972.2	892.8
57.5°	496.9	549.7	615.4	689.2	770.9	842.3	882.3	922.2	882.3	842.3	770.9
60°	446.3	491.3	546.5	613.8	693.2	761.5	796.7	831.8	796.7	761.5	693.2
62.5°	399.9	435.8	479.8	540.3	617.2	682.7	713.9	745.0	713.9	682.7	617.2
65°	334.3	363.9	400.1	450.3	514.6	568.6	591.7	614.8	591.7	568.6	514.6
67.5°	274.6	300.0	331.8	372.5	422.1	462.5	475.4	488.2	475.4	462.5	422.1
70°	240.6	261.5	287.6	322.2	365.4	398.8	402.8	406.9	402.8	398.8	365.4
72.5°	208.5	224.7	245.2	274.2	311.8	339.6	338.0	336.3	338.0	339.6	311.8
75°	164.5	175.6	189.6	210.2	237.3	255.7	247.6	239.6	247.6	255.7	237.3
77.5°	121.7	129.9	140.3	155.5	175.4	187.3	175.3	163.2	175.3	187.3	175.4
80°	94.9	101.0	109.0	120.6	135.6	143.9	131.9	119.8	131.9	143.9	135.6
82.5°	71.4	74.4	78.5	86.0	97.0	102.9	93.3	83.6	93.3	102.9	97.0
85°	29.1	33.9	39.9	45.0	49.0	50.7	45.7	40.7	45.7	50.7	49.0
87.5°	7.1	7.6	8.4	10.7	14.5	16.6	13.8	11.1	13.8	16.5	14.7
90°	8.2	7.8	7.8	7.4	6.2	4.7	2.7	1.2	2.7	4.3	7.0
92.5°	9.8	9.7	9.1	8.4	6.9	6.9	6.8	4.3	7.4	10.5	15.1
95°	9.0	9.0	10.5	13.3	19.5	19.9	13.3	12.1	17.2	24.2	30.4
97.5°	24.3	28.9	35.4	36.7	34.7	25.9	24.8	23.1	31.5	38.4	48.5
100°	44.9	50.7	55.4	46.1	36.3	35.9	33.6	32.8	41.8	48.4	58.1
102.5°	70.2	72.0	55.7	50.4	48.2	46.5	42.9	42.5	51.4	60.6	68.8
105°	76.1	68.3	68.7	68.7	67.1	64.0	57.4	57.0	67.1	77.7	87.8
107.5°	89.5	90.7	92.7	92.3	90.5	82.1	74.3	72.5	81.6	94.3	105.5
110°	107.3	108.5	109.3	108.5	105.8	95.2	85.9	83.1	91.3	104.6	116.7



TEST NUMBER: P1428361

CATALOG NUMBER: SQ2W-PW1-K-025U-100D-L840-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	124.5	125.4	127.1	124.7	120.1	108.0	97.4	93.4	101.6	115.2	127.6
115°	151.8	151.8	152.2	151.0	141.7	129.2	115.1	109.3	116.3	128.8	142.4
117.5°	178.7	179.1	177.6	174.4	163.6	149.1	133.3	123.9	129.5	142.7	156.7
120°	195.5	196.3	194.7	190.1	179.5	163.1	145.2	134.3	138.5	151.4	165.5
122.5°	213.0	212.9	211.0	205.7	193.3	176.2	158.6	145.2	147.0	158.9	172.7
125°	237.3	236.9	235.3	229.1	216.2	198.6	178.0	161.6	159.2	169.4	183.4
127.5°	260.4	259.5	257.1	249.5	236.3	219.4	196.7	178.1	172.9	179.3	192.2
130°	276.3	275.1	270.8	262.7	249.8	233.8	210.7	189.7	182.3	186.2	197.5
132.5°	291.6	288.3	284.6	275.8	263.8	247.2	223.9	201.8	191.6	193.3	202.2
135°	311.0	307.9	303.2	294.7	283.3	266.9	243.5	219.7	205.7	204.1	209.2
137.5°	328.1	324.9	319.6	312.1	300.7	286.1	263.7	238.5	220.8	215.6	217.5
140°	338.8	334.8	330.2	322.8	312.6	297.4	275.5	251.3	231.4	224.0	222.8
142.5°	347.5	344.5	339.5	332.7	323.8	308.6	287.4	263.5	242.4	232.8	230.0
145°	360.6	358.3	352.8	346.6	339.1	323.9	304.4	280.6	259.5	247.0	241.2
147.5°	371.7	369.8	365.5	358.2	351.9	337.3	319.6	298.5	276.9	261.4	253.8
150°	378.6	377.0	372.7	365.7	359.4	345.8	328.6	309.1	288.4	272.0	262.3
152.5°	385.1	383.6	378.6	371.6	366.3	353.6	338.0	319.4	298.4	282.0	271.9
155°	393.8	391.8	387.1	380.5	375.8	364.1	349.7	333.3	315.3	298.2	286.8
157.5°	400.6	398.2	393.9	388.2	383.2	372.4	359.8	345.7	330.0	313.6	302.1
160°	404.7	402.0	397.3	392.2	387.5	377.4	366.1	353.2	338.8	323.9	311.4
162.5°	407.5	405.1	399.5	395.0	391.0	381.8	371.1	359.4	346.6	333.6	322.0
165°	410.6	407.8	402.0	398.5	395.0	387.1	377.8	368.4	357.5	346.9	337.6
167.5°	410.8	408.5	402.7	399.2	396.7	390.0	382.4	375.2	366.7	358.4	350.6
170°	410.2	408.2	402.4	399.2	397.3	391.8	385.2	379.0	372.3	365.3	359.0
172.5°	408.0	406.0	400.5	398.0	397.0	392.1	386.8	382.1	376.4	371.2	366.2
175°	402.4	400.8	396.1	394.6	395.0	391.8	387.9	385.2	381.7	378.6	375.8
177.5°	394.2	393.2	389.8	389.8	391.0	389.2	387.9	386.7	385.1	384.2	383.2
180°	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4



TEST NUMBER: P1428361

CATALOG NUMBER: SQ2W-PW1-K-025U-100D-L840-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4
2.5°	2372.4	2368.4	2369.2	2370.4	2372.8	2375.2	2372.8	2370.4	2369.2	2368.4	2372.4
5°	2371.1	2367.1	2368.1	2371.1	2380.2	2389.2	2380.2	2371.1	2368.1	2367.1	2371.1
7.5°	2363.7	2362.0	2365.4	2370.2	2379.0	2387.9	2379.0	2370.2	2365.4	2362.0	2363.7
10°	2356.1	2355.6	2360.6	2366.4	2374.4	2382.4	2374.4	2366.4	2360.6	2355.6	2356.1
12.5°	2346.2	2346.9	2352.8	2359.1	2367.2	2375.2	2367.2	2359.1	2352.8	2346.9	2346.2
15°	2324.2	2327.2	2334.2	2340.7	2345.8	2350.8	2345.8	2340.7	2334.2	2327.2	2324.2
17.5°	2287.8	2288.0	2289.8	2291.7	2294.1	2296.5	2294.1	2291.7	2289.8	2288.0	2287.8
20°	2259.6	2254.6	2247.6	2242.3	2242.3	2242.3	2242.3	2242.3	2247.6	2254.6	2259.6
22.5°	2220.0	2207.0	2187.9	2172.0	2165.5	2159.1	2165.5	2172.0	2187.9	2207.0	2220.0
25°	2141.6	2111.9	2072.8	2039.6	2024.5	2009.5	2024.5	2039.6	2072.8	2111.9	2141.6
27.5°	2034.8	1987.1	1931.4	1884.5	1863.6	1842.7	1863.6	1884.5	1931.4	1987.1	2034.8
30°	1948.2	1888.4	1827.1	1776.2	1756.1	1736.0	1756.1	1776.2	1827.1	1888.4	1948.2
32.5°	1857.8	1789.6	1725.9	1672.7	1651.0	1629.3	1651.0	1672.7	1725.9	1789.6	1857.8
35°	1716.1	1638.3	1574.0	1521.0	1501.9	1482.8	1501.9	1521.0	1574.0	1638.3	1716.1
37.5°	1574.0	1491.6	1424.3	1368.6	1347.5	1326.4	1347.5	1368.6	1424.3	1491.6	1574.0
40°	1474.8	1390.4	1323.1	1267.3	1246.2	1225.1	1246.2	1267.3	1323.1	1390.4	1474.8
42.5°	1378.9	1294.5	1227.2	1171.3	1149.4	1127.5	1149.4	1171.3	1227.2	1294.5	1378.9
45°	1233.9	1149.5	1084.2	1030.0	1008.9	987.8	1008.9	1030.0	1084.2	1149.5	1233.9
47.5°	1097.3	1014.0	950.7	898.7	880.6	862.6	880.6	898.7	950.7	1014.0	1097.3
50°	1009.9	929.0	865.7	812.7	790.6	768.5	790.6	812.7	865.7	929.0	1009.9
52.5°	925.5	845.0	780.1	723.9	693.8	663.6	693.8	723.9	780.1	845.0	925.5
55°	802.4	721.1	648.7	590.2	573.1	556.1	573.1	590.2	648.7	721.1	802.4
57.5°	689.2	615.4	549.7	496.9	482.9	468.8	482.9	496.9	549.7	615.4	689.2
60°	613.8	546.5	491.3	446.3	432.2	418.2	432.2	446.3	491.3	546.5	613.8
62.5°	540.3	479.8	435.8	399.9	388.2	376.6	388.2	399.9	435.8	479.8	540.3
65°	450.3	400.1	363.9	334.3	324.2	314.2	324.2	334.3	363.9	400.1	450.3
67.5°	372.5	331.8	300.0	274.6	267.9	261.3	267.9	274.6	300.0	331.8	372.5
70°	322.2	287.6	261.5	240.6	235.6	230.6	235.6	240.6	261.5	287.6	322.2
72.5°	274.2	245.2	224.7	208.5	205.0	201.6	205.0	208.5	224.7	245.2	274.2
75°	210.2	189.6	175.6	164.5	162.5	160.5	162.5	164.5	175.6	189.6	210.2
77.5°	155.5	140.3	129.9	121.7	120.1	118.4	120.1	121.7	129.9	140.3	155.5
80°	120.6	109.0	101.0	94.9	94.9	94.9	94.9	94.9	101.0	109.0	120.6
82.5°	86.0	78.5	74.4	71.4	71.4	71.4	71.4	71.4	74.4	78.5	86.0
85°	45.0	39.9	33.9	29.1	28.1	27.1	28.1	29.1	33.9	39.9	45.0
87.5°	11.0	9.2	8.9	8.6	8.9	8.8	8.9	8.6	8.9	9.2	11.0
90°	9.0	11.7	14.4	16.0	17.6	16.8	17.6	16.0	14.4	11.7	9.0
92.5°	18.0	22.6	26.0	28.8	30.1	29.9	30.1	28.8	26.0	22.6	18.0
95°	36.3	41.8	47.2	51.1	53.5	52.7	53.5	51.1	47.2	41.8	36.3
97.5°	56.0	63.3	69.4	73.1	75.4	77.0	75.4	73.1	69.4	63.3	56.0
100°	69.1	76.1	83.1	87.4	91.3	92.9	91.3	87.4	83.1	76.1	69.1
102.5°	79.7	88.9	96.6	101.2	104.4	106.0	104.4	101.2	96.6	88.9	79.7
105°	97.2	106.9	115.1	121.0	124.5	125.7	124.5	121.0	115.1	106.9	97.2
107.5°	114.7	124.7	132.3	138.8	143.1	145.6	143.1	138.8	132.3	124.7	114.7
110°	128.4	136.6	144.8	150.6	154.9	156.5	154.9	150.6	144.8	136.6	128.4



TEST NUMBER: P1428361

CATALOG NUMBER: SQ2W-PW1-K-025U-100D-L840-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	140.0	149.1	157.3	163.1	168.0	170.2	168.0	163.1	157.3	149.1	140.0
115°	156.1	168.2	175.6	181.1	184.6	186.5	184.6	181.1	175.6	168.2	156.1
117.5°	169.5	182.2	190.3	194.5	196.1	197.6	196.1	194.5	190.3	182.2	169.5
120°	178.0	189.7	199.0	204.5	206.5	207.2	206.5	204.5	199.0	189.7	178.0
122.5°	185.8	196.9	205.9	212.6	215.8	216.6	215.8	212.6	205.9	196.9	185.8
125°	196.7	207.2	216.6	223.2	226.7	228.7	226.7	223.2	216.6	207.2	196.7
127.5°	206.2	217.6	226.2	232.2	235.6	237.2	235.6	232.2	226.2	217.6	206.2
130°	211.5	223.2	231.8	238.5	241.6	243.1	241.6	238.5	231.8	223.2	211.5
132.5°	215.6	227.9	236.8	242.8	246.3	247.8	246.3	242.8	236.8	227.9	215.6
135°	220.5	233.4	242.7	248.6	251.7	253.3	251.7	248.6	242.7	233.4	220.5
137.5°	224.8	236.5	246.3	252.4	255.2	256.2	255.2	252.4	246.3	236.5	224.8
140°	227.9	238.1	247.8	253.7	256.8	257.2	256.8	253.7	247.8	238.1	227.9
142.5°	232.0	239.9	248.4	254.3	257.4	258.1	257.4	254.3	248.4	239.9	232.0
145°	239.2	243.9	249.8	255.2	258.0	258.7	258.0	255.2	249.8	243.9	239.2
147.5°	248.4	249.8	252.9	256.5	259.1	259.7	259.1	256.5	252.9	249.8	248.4
150°	255.2	254.8	256.0	258.4	260.7	260.3	260.7	258.4	256.0	254.8	255.2
152.5°	263.0	260.8	260.7	261.8	262.9	262.8	262.9	261.8	260.7	260.8	263.0
155°	276.3	272.0	269.7	268.9	268.9	268.5	268.9	268.9	269.7	272.0	276.3
157.5°	290.9	284.9	281.4	279.5	279.0	278.1	279.0	279.5	281.4	284.9	290.9
160°	300.9	294.3	290.7	287.6	286.5	285.3	286.5	287.6	290.7	294.3	300.9
162.5°	310.3	303.9	300.1	297.3	296.1	294.3	296.1	297.3	300.1	303.9	310.3
165°	325.5	318.8	314.6	312.2	310.7	309.1	310.7	312.2	314.6	318.8	325.5
167.5°	340.7	333.4	330.6	328.0	326.5	323.7	326.5	328.0	330.6	333.4	340.7
170°	350.1	343.4	341.9	339.5	336.8	333.7	336.8	339.5	341.9	343.4	350.1
172.5°	358.2	353.7	352.2	349.8	349.0	346.5	349.0	349.8	352.2	353.7	358.2
175°	370.0	366.5	366.5	366.1	364.9	362.6	364.9	366.1	366.5	366.5	370.0
177.5°	379.8	377.9	379.2	379.2	378.9	376.7	378.9	379.2	379.2	377.9	379.8
180°	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4



TEST NUMBER: P1428361

CATALOG NUMBER: SQ2W-PW1-K-025U-100D-L840-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	2373.4	2373.4	2373.4	2373.4
2.5°	2381.2	2384.4	2370.8	2357.1
5°	2380.2	2382.7	2365.6	2348.5
7.5°	2370.5	2371.3	2354.1	2336.8
10°	2362.1	2362.1	2344.0	2325.9
12.5°	2350.6	2349.2	2330.4	2311.5
15°	2325.2	2320.9	2300.8	2280.7
17.5°	2289.2	2285.2	2265.1	2245.0
20°	2262.6	2259.9	2239.8	2219.7
22.5°	2227.1	2226.9	2205.2	2183.5
25°	2161.7	2171.5	2150.4	2129.3
27.5°	2074.6	2100.1	2083.1	2066.0
30°	2006.5	2046.9	2033.8	2020.8
32.5°	1930.5	1983.8	1978.8	1973.8
35°	1807.5	1878.4	1887.4	1896.5
37.5°	1671.5	1751.3	1778.2	1805.1
40°	1576.2	1661.9	1700.1	1738.2
42.5°	1480.4	1568.5	1616.3	1664.1
45°	1337.4	1429.1	1485.3	1541.6
47.5°	1200.6	1292.0	1347.8	1403.7
50°	1108.3	1195.7	1250.0	1304.2
52.5°	1021.5	1105.7	1154.4	1203.0
55°	892.8	972.2	1018.4	1064.6
57.5°	770.9	842.3	882.3	922.2
60°	693.2	761.5	796.7	831.8
62.5°	617.2	682.7	713.9	745.0
65°	514.6	568.6	591.7	614.8
67.5°	422.1	462.5	475.4	488.2
70°	365.4	398.8	402.8	406.9
72.5°	311.8	339.6	338.0	336.3
75°	237.3	255.7	247.6	239.6
77.5°	175.4	187.3	175.3	163.2
80°	135.6	143.9	131.9	119.8
82.5°	97.0	102.9	93.3	83.6
85°	49.0	50.7	45.7	40.7
87.5°	14.7	16.5	13.8	11.1
90°	7.0	4.3	2.7	1.2
92.5°	15.1	10.5	7.4	4.3
95°	30.4	24.2	17.2	12.1
97.5°	48.5	38.4	31.5	23.1
100°	58.1	48.4	41.8	32.8
102.5°	68.8	60.6	51.4	42.5
105°	87.8	77.7	67.1	57.0
107.5°	105.5	94.3	81.6	72.5
110°	116.7	104.6	91.3	83.1



TEST NUMBER: P1428361

CATALOG NUMBER: SQ2W-PW1-K-025U-100D-L840-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	127.6	115.2	101.6	93.4
115°	142.4	128.8	116.3	109.3
117.5°	156.7	142.7	129.5	123.9
120°	165.5	151.4	138.5	134.3
122.5°	172.7	158.9	147.0	145.2
125°	183.4	169.4	159.2	161.6
127.5°	192.2	179.3	172.9	178.1
130°	197.5	186.2	182.3	189.7
132.5°	202.2	193.3	191.6	201.8
135°	209.2	204.1	205.7	219.7
137.5°	217.5	215.6	220.8	238.5
140°	222.8	224.0	231.4	251.3
142.5°	230.0	232.8	242.4	263.5
145°	241.2	247.0	259.5	280.6
147.5°	253.8	261.4	276.9	298.5
150°	262.3	272.0	288.4	309.1
152.5°	271.9	282.0	298.4	319.4
155°	286.8	298.2	315.3	333.3
157.5°	302.1	313.6	330.0	345.7
160°	311.4	323.9	338.8	353.2
162.5°	322.0	333.6	346.6	359.4
165°	337.6	346.9	357.5	368.4
167.5°	350.6	358.4	366.7	375.2
170°	359.0	365.3	372.3	379.0
172.5°	366.2	371.2	376.4	382.1
175°	375.8	378.6	381.7	385.2
177.5°	383.2	384.2	385.1	386.7
180°	386.4	386.4	386.4	386.4



TEST NUMBER: P1428361  
 CATALOG NUMBER: SQ2W-PW1-K-025U-100D-L840-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	22.22	23.39	22.84	24.03	24.75	18.47	19.64	19.09	20.27	21.00
	3H	23.54	24.59	24.18	25.24	26.00	19.76	20.81	20.40	21.45	22.21
	4H	23.97	24.95	24.63	25.61	26.38	20.28	21.27	20.94	21.92	22.70
	6H	24.16	25.07	24.83	25.74	26.52	20.60	21.51	21.28	22.18	22.97
	8H	24.21	25.08	24.90	25.77	26.56	20.73	21.59	21.41	22.28	23.07
	12H	24.22	25.05	24.91	25.73	26.55	20.77	21.59	21.46	22.27	23.09
4H	2H	22.39	23.38	23.05	24.03	24.80	19.31	20.30	19.98	20.96	21.73
	3H	23.95	24.77	24.63	25.47	26.26	20.79	21.61	21.46	22.30	23.09
	4H	24.51	25.25	25.21	25.95	26.77	21.38	22.12	22.07	22.82	23.64
	6H	24.84	25.48	25.55	26.20	27.04	21.78	22.42	22.49	23.14	23.98
	8H	24.94	25.53	25.65	26.26	27.10	21.94	22.53	22.65	23.25	24.10
	12H	24.97	25.51	25.71	26.25	27.10	21.99	22.53	22.73	23.27	24.12
8H	4H	24.57	25.17	25.29	25.89	26.73	21.74	22.34	22.46	23.06	23.90
	6H	25.01	25.50	25.75	26.26	27.11	22.25	22.74	22.99	23.50	24.35
	8H	25.18	25.62	25.94	26.38	27.24	22.47	22.91	23.23	23.67	24.53
	12H	25.27	25.66	26.03	26.41	27.33	22.56	22.95	23.32	23.71	24.63
12H	4H	24.55	25.08	25.28	25.83	26.67	21.78	22.31	22.51	23.06	23.90
	6H	25.00	25.44	25.76	26.21	27.07	22.32	22.76	23.08	23.53	24.39
	8H	25.20	25.59	25.96	26.35	27.27	22.58	22.97	23.34	23.72	24.65