

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427848

Luminaire Tested: SQ2W-PH1-K-025U-050D-L940-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1427848
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-10)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PH1-K-025U-050D-L940-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE HEX LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3483.5 lumens
Efficiency: N/A
Efficacy: 137.7 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.02 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 25.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1427848

CATALOG NUMBER: SQ2W-PH1-K-025U-050D-L940-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1427848

CATALOG NUMBER: SQ2W-PH1-K-025U-050D-L940-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75	71	71	71	71	
1	103	98	95	91	97	93	90	87	84	81	79	75	73	71	67	65	64	60	60	60	60	
2	94	86	80	75	88	82	76	72	74	69	66	66	63	60	59	57	54	51	51	51	51	
3	86	76	68	63	81	72	65	60	65	60	55	59	54	51	53	49	46	43	43	43	43	
4	78	67	59	53	74	64	57	51	58	52	47	52	48	44	47	43	40	37	37	37	37	
5	72	60	52	46	68	57	50	44	52	46	41	47	42	38	42	38	35	32	32	32	32	
6	67	54	46	40	63	52	44	39	47	41	36	43	37	33	39	34	31	28	28	28	28	
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	35	31	27	25	25	25	25	
8	57	45	37	31	54	43	35	30	39	33	28	36	30	27	32	28	25	23	23	23	23	
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	30	26	22	20	20	20	20	
10	50	38	30	25	47	36	29	25	33	27	23	30	25	22	28	23	20	18	18	18	18	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17949	17949	17949	17949
5°	18052	16407	18052	16407
10°	17637	14914	17637	14914
15°	17716	14622	17716	14622
20°	17084	14740	17084	14740
25°	16771	14396	16771	14396
30°	16408	14514	16408	14514
35°	16282	17012	16282	17012
40°	16296	13489	16296	13489
45°	16303	11618	16303	11618
50°	16076	10894	16076	10894
55°	15870	10452	15870	10452
60°	15713	9804	15713	9804
65°	15438	8527	15438	8527
70°	14582	6090	14582	6090
75°	13000	4616	13000	4616
80°	10618	4324	10618	4324
85°	6669	2945	6669	2945

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16303 cd/sqm



TEST NUMBER: P1427848

CATALOG NUMBER: SQ2W-PH1-K-025U-050D-L940-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.8	2.8
10°-20°	257.3	7.4
20°-30°	377.2	10.8
30°-40°	456.8	13.1
40°-50°	449.2	12.9
50°-60°	390.7	11.2
60°-70°	271.7	7.8
70°-80°	128.9	3.7
80°-90°	29.9	0.9
90°-100°	27.9	0.8
100°-110°	81.4	2.3
110°-120°	132.8	3.8
120°-130°	168.5	4.8
130°-140°	180.3	5.2
140°-150°	168.4	4.8
150°-160°	138.6	4.0
160°-170°	92.9	2.7
170°-180°	33.0	0.9
0°-30°	732.4	21.0
0°-40°	1189.2	34.1
0°-60°	2029.1	58.2
0°-90°	2459.5	70.6
90°-120°	242.1	7.0
90°-150°	759.4	21.8
90°-180°	1024.0	29.4
0°-180°	3483.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1112	1112	1112	1112	1112	
5°	1114	1012	1114	1012	1114	105
15°	1060	875	1060	875	1060	295
25°	941	808	941	808	941	433
35°	826	863	826	863	826	517
45°	714	509	714	509	714	549
55°	564	371	564	371	564	504
65°	404	223	404	223	404	397
75°	208	74	208	74	208	221
85°	36	16	36	16	36	48
90°	1	8	1	15	1	2
95°	11	8	11	48	11	13
105°	52	83	52	114	52	55
115°	99	137	99	169	99	98
125°	147	218	147	208	147	131
135°	199	285	199	230	199	154
145°	255	329	255	235	255	159
155°	302	357	302	244	302	139
165°	334	372	334	280	334	94
175°	350	364	350	329	350	33
180°	351	351	351	351	351	



TEST NUMBER: P1427848

CATALOG NUMBER: SQ2W-PH1-K-025U-050D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1111.7	1111.7	1111.7	1111.7	1111.7	1111.7	1111.7	1111.7	1111.7	1111.7	1111.7
2.5°	1109.2	1114.4	1119.7	1112.3	1100.6	1092.5	1088.0	1084.5	1083.7	1083.0	1083.7
5°	1113.8	1113.4	1112.9	1090.9	1061.8	1039.9	1025.3	1014.2	1013.2	1012.3	1013.2
7.5°	1093.5	1079.0	1064.4	1034.9	1000.3	975.1	959.0	946.7	946.0	945.2	946.0
10°	1075.8	1053.7	1031.6	998.2	961.0	935.2	920.6	909.7	909.7	909.7	909.7
12.5°	1071.5	1036.6	1001.8	965.2	928.0	904.1	893.3	885.7	888.0	890.2	888.0
15°	1059.9	1007.2	954.6	917.4	885.5	868.1	865.3	864.4	869.6	874.8	869.6
17.5°	1021.4	964.7	908.0	875.3	850.7	841.4	847.4	853.4	859.5	865.5	859.5
20°	994.3	938.4	882.4	852.2	830.6	825.4	836.7	846.6	852.2	857.9	852.2
22.5°	971.5	914.8	858.1	831.3	814.6	812.4	824.9	834.9	837.9	840.9	837.9
25°	941.4	877.5	813.5	794.0	789.3	792.4	803.2	811.0	809.6	808.1	809.6
27.5°	905.5	838.7	771.9	759.4	765.0	771.0	777.6	782.8	783.6	784.4	783.6
30°	880.1	813.3	746.6	736.6	745.5	753.3	759.8	766.3	772.4	778.5	772.4
32.5°	855.5	786.5	717.5	710.3	723.8	738.3	753.9	769.1	783.1	797.1	783.1
35°	826.1	754.2	682.3	676.6	693.1	714.2	740.1	771.0	817.1	863.1	817.1
37.5°	795.2	718.1	641.0	638.5	660.8	683.0	705.3	725.7	740.4	755.0	740.4
40°	773.2	692.4	611.5	611.4	638.2	665.9	694.6	707.7	673.8	640.0	673.8
42.5°	749.5	668.7	587.8	585.4	609.2	639.8	677.1	690.8	633.7	576.5	633.7
45°	714.0	629.8	545.7	542.6	566.6	583.5	593.4	590.6	549.7	508.8	549.7
47.5°	672.1	591.9	511.7	511.0	536.9	538.8	516.7	496.1	480.1	464.2	480.1
50°	640.0	564.3	488.6	491.9	521.5	518.7	483.4	454.4	444.0	433.7	444.0
52.5°	608.6	536.7	464.8	473.5	509.2	503.5	456.6	419.7	412.7	405.8	412.7
55°	563.8	494.7	425.6	445.3	494.7	487.2	422.8	374.1	372.7	371.3	372.7
57.5°	516.2	450.8	385.5	399.2	439.3	431.4	375.5	334.2	336.7	339.1	336.7
60°	486.6	423.1	359.6	361.4	384.9	377.4	338.8	309.2	306.4	303.6	306.4
62.5°	455.3	394.8	334.4	325.6	334.0	325.2	299.1	278.8	275.9	273.1	275.9
65°	404.1	349.1	294.1	277.5	273.7	261.0	239.4	223.2	223.2	223.2	223.2
67.5°	347.8	299.8	251.9	233.3	224.6	212.0	195.5	180.4	169.1	157.8	169.1
70°	308.9	266.6	224.2	204.9	193.1	178.1	159.7	144.1	136.6	129.0	136.6
72.5°	267.4	231.1	194.8	175.0	160.6	145.9	131.0	117.6	108.9	100.3	108.9
75°	208.4	179.2	150.1	130.8	114.8	100.0	86.4	75.9	75.0	74.0	75.0
77.5°	150.6	129.4	108.1	92.5	78.8	68.5	61.6	56.5	56.6	56.7	56.6
80°	114.2	98.3	82.3	67.7	53.6	46.3	45.8	45.6	46.1	46.5	46.1
82.5°	80.4	68.5	56.7	47.4	38.9	35.0	35.7	36.2	36.3	36.4	36.3
85°	36.0	30.3	24.7	22.6	21.6	20.2	18.3	16.8	16.3	15.9	16.3
87.5°	7.8	7.7	7.7	7.1	6.1	5.6	5.6	5.7	5.8	5.8	5.8
90°	1.1	2.5	4.3	5.7	6.7	7.1	7.1	7.4	7.8	7.8	7.8
92.5°	3.9	6.2	6.2	6.2	7.6	8.2	8.8	8.9	9.2	9.2	9.2
95°	11.0	12.0	18.1	17.7	12.0	9.6	8.1	8.1	8.1	8.1	8.1
97.5°	21.0	22.5	23.5	31.5	33.3	32.2	26.2	22.0	19.7	18.6	19.7
100°	29.8	30.5	32.6	32.9	41.8	50.3	46.0	40.7	39.0	37.9	39.0
102.5°	38.5	39.0	42.2	43.7	45.8	50.6	65.3	63.7	62.5	62.3	62.5
105°	51.7	52.1	58.1	60.9	62.3	62.3	62.0	69.1	80.4	82.9	80.4
107.5°	65.8	67.4	74.5	82.1	83.7	84.2	82.3	81.3	80.8	81.1	80.8
110°	75.4	77.9	86.4	96.0	98.5	99.2	98.5	97.4	96.7	96.7	96.7



TEST NUMBER: P1427848

CATALOG NUMBER: SQ2W-PH1-K-025U-050D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	84.8	88.4	98.0	109.0	113.2	115.3	113.8	113.0	112.3	112.9	112.3
115°	99.2	104.5	117.2	128.6	137.1	138.1	137.8	137.8	137.4	137.4	137.4
117.5°	112.5	121.0	135.3	148.5	158.3	161.2	162.6	162.2	161.7	162.4	161.7
120°	121.9	131.8	148.1	162.9	172.5	176.8	178.2	177.5	178.2	177.5	178.2
122.5°	131.8	144.0	160.0	175.4	186.7	191.5	193.2	193.3	193.5	193.1	193.5
125°	146.6	161.5	180.3	196.2	207.9	213.6	215.0	215.4	216.1	217.8	216.1
127.5°	161.7	178.5	199.1	214.5	226.5	233.4	235.6	236.3	237.8	238.6	237.8
130°	172.2	191.3	212.2	226.7	238.4	245.8	249.7	250.8	252.6	252.2	252.6
132.5°	183.2	203.2	224.4	239.5	250.3	258.3	261.6	264.7	265.3	265.8	265.3
135°	199.4	221.0	242.3	257.2	267.4	275.2	279.5	282.3	284.1	285.1	284.1
137.5°	216.5	239.3	259.7	273.0	283.3	290.0	294.9	297.8	299.7	300.5	299.7
140°	228.1	250.1	269.9	283.7	292.9	299.7	303.9	307.5	309.6	309.6	309.6
142.5°	239.2	260.9	280.1	293.9	302.0	308.2	312.7	315.4	317.8	317.8	317.8
145°	254.7	276.3	294.0	307.8	314.6	320.2	325.2	327.3	328.7	328.7	328.7
147.5°	270.9	290.0	306.2	319.4	325.1	331.8	335.7	337.4	339.1	338.4	339.1
150°	280.5	298.3	313.8	326.2	331.9	338.3	342.2	343.6	345.4	344.3	345.4
152.5°	289.9	306.8	320.9	332.5	337.3	343.7	348.1	349.5	350.8	350.0	350.8
155°	302.5	317.4	330.5	341.1	345.4	351.4	355.6	357.4	358.8	357.1	358.8
157.5°	313.8	326.6	338.0	347.8	352.3	357.5	361.4	363.6	365.1	364.3	365.1
160°	320.6	332.3	342.5	351.7	356.0	360.6	364.9	367.3	368.7	367.7	368.7
162.5°	326.2	336.8	346.5	354.9	358.5	362.6	367.7	369.9	371.3	370.0	371.3
165°	334.4	342.9	351.4	358.5	361.7	364.9	370.2	372.6	373.7	372.3	373.7
167.5°	340.6	347.1	353.9	360.0	362.4	365.5	370.8	372.9	374.2	372.4	374.2
170°	344.0	349.6	355.6	360.6	362.4	365.2	370.5	372.3	373.4	371.6	373.4
172.5°	346.8	351.0	355.9	360.3	361.2	363.5	368.5	370.3	371.1	369.6	371.1
175°	349.6	352.1	355.6	358.5	358.1	359.5	363.8	365.2	366.6	364.5	366.6
177.5°	351.0	352.1	353.2	354.9	353.8	353.8	356.9	357.8	358.0	356.9	358.0
180°	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7



TEST NUMBER: P1427848

CATALOG NUMBER: SQ2W-PH1-K-025U-050D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1111.7	1111.7	1111.7	1111.7	1111.7	1111.7	1111.7	1111.7	1111.7	1111.7	1111.7
2.5°	1084.5	1088.0	1092.5	1100.6	1112.3	1119.7	1114.4	1109.2	1114.4	1119.7	1112.3
5°	1014.2	1025.3	1039.9	1061.8	1090.9	1112.9	1113.4	1113.8	1113.4	1112.9	1090.9
7.5°	946.7	959.0	975.1	1000.3	1034.9	1064.4	1079.0	1093.5	1079.0	1064.4	1034.9
10°	909.7	920.6	935.2	961.0	998.2	1031.6	1053.7	1075.8	1053.7	1031.6	998.2
12.5°	885.7	893.3	904.1	928.0	965.2	1001.8	1036.6	1071.5	1036.6	1001.8	965.2
15°	864.4	865.3	868.1	885.5	917.4	954.6	1007.2	1059.9	1007.2	954.6	917.4
17.5°	853.4	847.4	841.4	850.7	875.3	908.0	964.7	1021.4	964.7	908.0	875.3
20°	846.6	836.7	825.4	830.6	852.2	882.4	938.4	994.3	938.4	882.4	852.2
22.5°	834.9	824.9	812.4	814.6	831.3	858.1	914.8	971.5	914.8	858.1	831.3
25°	811.0	803.2	792.4	789.3	794.0	813.5	877.5	941.4	877.5	813.5	794.0
27.5°	782.8	777.6	771.0	765.0	759.4	771.9	838.7	905.5	838.7	771.9	759.4
30°	766.3	759.8	753.3	745.5	736.6	746.6	813.3	880.1	813.3	746.6	736.6
32.5°	769.1	753.9	738.3	723.8	710.3	717.5	786.5	855.5	786.5	717.5	710.3
35°	771.0	740.1	714.2	693.1	676.6	682.3	754.2	826.1	754.2	682.3	676.6
37.5°	725.7	705.3	683.0	660.8	638.5	641.0	718.1	795.2	718.1	641.0	638.5
40°	707.7	694.6	665.9	638.2	611.4	611.5	692.4	773.2	692.4	611.5	611.4
42.5°	690.8	677.1	639.8	609.2	585.4	587.8	668.7	749.5	668.7	587.8	585.4
45°	590.6	593.4	583.5	566.6	542.6	545.7	629.8	714.0	629.8	545.7	542.6
47.5°	496.1	516.7	538.8	536.9	511.0	511.7	591.9	672.1	591.9	511.7	511.0
50°	454.4	483.4	518.7	521.5	491.9	488.6	564.3	640.0	564.3	488.6	491.9
52.5°	419.7	456.6	503.5	509.2	473.5	464.8	536.7	608.6	536.7	464.8	473.5
55°	374.1	422.8	487.2	494.7	445.3	425.6	494.7	563.8	494.7	425.6	445.3
57.5°	334.2	375.5	431.4	439.3	399.2	385.5	450.8	516.2	450.8	385.5	399.2
60°	309.2	338.8	377.4	384.9	361.4	359.6	423.1	486.6	423.1	359.6	361.4
62.5°	278.8	299.1	325.2	334.0	325.6	334.4	394.8	455.3	394.8	334.4	325.6
65°	223.2	239.4	261.0	273.7	277.5	294.1	349.1	404.1	349.1	294.1	277.5
67.5°	180.4	195.5	212.0	224.6	233.3	251.9	299.8	347.8	299.8	251.9	233.3
70°	144.1	159.7	178.1	193.1	204.9	224.2	266.6	308.9	266.6	224.2	204.9
72.5°	117.6	131.0	145.9	160.6	175.0	194.8	231.1	267.4	231.1	194.8	175.0
75°	75.9	86.4	100.0	114.8	130.8	150.1	179.2	208.4	179.2	150.1	130.8
77.5°	56.5	61.6	68.5	78.8	92.5	108.1	129.4	150.6	129.4	108.1	92.5
80°	45.6	45.8	46.3	53.6	67.7	82.3	98.3	114.2	98.3	82.3	67.7
82.5°	36.2	35.7	35.0	38.9	47.4	56.7	68.5	80.4	68.5	56.7	47.4
85°	16.8	18.3	20.2	21.6	22.6	24.7	30.3	36.0	30.3	24.7	22.6
87.5°	5.7	5.6	5.6	6.1	7.1	7.7	7.7	7.8	7.7	7.6	7.2
90°	7.4	7.1	7.1	6.7	5.7	4.3	2.5	1.1	2.5	3.9	6.4
92.5°	8.9	8.8	8.2	7.6	6.2	6.2	6.2	3.9	6.7	9.6	13.7
95°	8.1	8.1	9.6	12.0	17.7	18.1	12.0	11.0	15.6	22.0	27.6
97.5°	22.0	26.2	32.2	33.3	31.5	23.5	22.5	21.0	28.6	34.9	44.0
100°	40.7	46.0	50.3	41.8	32.9	32.6	30.5	29.8	37.9	43.9	52.8
102.5°	63.7	65.3	50.6	45.8	43.7	42.2	39.0	38.5	46.7	55.0	62.4
105°	69.1	62.0	62.3	62.3	60.9	58.1	52.1	51.7	60.9	70.5	79.7
107.5°	81.3	82.3	84.2	83.7	82.1	74.5	67.4	65.8	74.1	85.6	95.7
110°	97.4	98.5	99.2	98.5	96.0	86.4	77.9	75.4	82.9	94.9	105.9



TEST NUMBER: P1427848

CATALOG NUMBER: SQ2W-PH1-K-025U-050D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	113.0	113.8	115.3	113.2	109.0	98.0	88.4	84.8	92.2	104.6	115.8
115°	137.8	137.8	138.1	137.1	128.6	117.2	104.5	99.2	105.6	116.9	129.3
117.5°	162.2	162.6	161.2	158.3	148.5	135.3	121.0	112.5	117.5	129.5	142.3
120°	177.5	178.2	176.8	172.5	162.9	148.1	131.8	121.9	125.7	137.4	150.2
122.5°	193.3	193.2	191.5	186.7	175.4	160.0	144.0	131.8	133.4	144.2	156.7
125°	215.4	215.0	213.6	207.9	196.2	180.3	161.5	146.6	144.5	153.7	166.5
127.5°	236.3	235.6	233.4	226.5	214.5	199.1	178.5	161.7	156.9	162.7	174.4
130°	250.8	249.7	245.8	238.4	226.7	212.2	191.3	172.2	165.4	169.0	179.2
132.5°	264.7	261.6	258.3	250.3	239.5	224.4	203.2	183.2	173.9	175.5	183.5
135°	282.3	279.5	275.2	267.4	257.2	242.3	221.0	199.4	186.7	185.3	189.9
137.5°	297.8	294.9	290.0	283.3	273.0	259.7	239.3	216.5	200.4	195.7	197.4
140°	307.5	303.9	299.7	292.9	283.7	269.9	250.1	228.1	210.1	203.3	202.3
142.5°	315.4	312.7	308.2	302.0	293.9	280.1	260.9	239.2	220.0	211.3	208.8
145°	327.3	325.2	320.2	314.6	307.8	294.0	276.3	254.7	235.6	224.2	218.9
147.5°	337.4	335.7	331.8	325.1	319.4	306.2	290.0	270.9	251.3	237.3	230.4
150°	343.6	342.2	338.3	331.9	326.2	313.8	298.3	280.5	261.8	246.9	238.0
152.5°	349.5	348.1	343.7	337.3	332.5	320.9	306.8	289.9	270.8	256.0	246.8
155°	357.4	355.6	351.4	345.4	341.1	330.5	317.4	302.5	286.2	270.6	260.4
157.5°	363.6	361.4	357.5	352.3	347.8	338.0	326.6	313.8	299.5	284.7	274.2
160°	367.3	364.9	360.6	356.0	351.7	342.5	332.3	320.6	307.5	294.0	282.7
162.5°	369.9	367.7	362.6	358.5	354.9	346.5	336.8	326.2	314.6	302.8	292.3
165°	372.6	370.2	364.9	361.7	358.5	351.4	342.9	334.4	324.5	314.9	306.4
167.5°	372.9	370.8	365.5	362.4	360.0	353.9	347.1	340.6	332.8	325.3	318.2
170°	372.3	370.5	365.2	362.4	360.6	355.6	349.6	344.0	337.9	331.6	325.9
172.5°	370.3	368.5	363.5	361.2	360.3	355.9	351.0	346.8	341.6	336.9	332.4
175°	365.2	363.8	359.5	358.1	358.5	355.6	352.1	349.6	346.4	343.6	341.1
177.5°	357.8	356.9	353.8	353.8	354.9	353.2	352.1	351.0	349.5	348.7	347.8
180°	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7



TEST NUMBER: P1427848

CATALOG NUMBER: SQ2W-PH1-K-025U-050D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1111.7	1111.7	1111.7	1111.7	1111.7	1111.7	1111.7	1111.7	1111.7	1111.7	1111.7
2.5°	1100.6	1092.5	1088.0	1084.5	1083.7	1083.0	1083.7	1084.5	1088.0	1092.5	1100.6
5°	1061.8	1039.9	1025.3	1014.2	1013.2	1012.3	1013.2	1014.2	1025.3	1039.9	1061.8
7.5°	1000.3	975.1	959.0	946.7	946.0	945.2	946.0	946.7	959.0	975.1	1000.3
10°	961.0	935.2	920.6	909.7	909.7	909.7	909.7	909.7	920.6	935.2	961.0
12.5°	928.0	904.1	893.3	885.7	888.0	890.2	888.0	885.7	893.3	904.1	928.0
15°	885.5	868.1	865.3	864.4	869.6	874.8	869.6	864.4	865.3	868.1	885.5
17.5°	850.7	841.4	847.4	853.4	859.5	865.5	859.5	853.4	847.4	841.4	850.7
20°	830.6	825.4	836.7	846.6	852.2	857.9	852.2	846.6	836.7	825.4	830.6
22.5°	814.6	812.4	824.9	834.9	837.9	840.9	837.9	834.9	824.9	812.4	814.6
25°	789.3	792.4	803.2	811.0	809.6	808.1	809.6	811.0	803.2	792.4	789.3
27.5°	765.0	771.0	777.6	782.8	783.6	784.4	783.6	782.8	777.6	771.0	765.0
30°	745.5	753.3	759.8	766.3	772.4	778.5	772.4	766.3	759.8	753.3	745.5
32.5°	723.8	738.3	753.9	769.1	783.1	797.1	783.1	769.1	753.9	738.3	723.8
35°	693.1	714.2	740.1	771.0	817.1	863.1	817.1	771.0	740.1	714.2	693.1
37.5°	660.8	683.0	705.3	725.7	740.4	755.0	740.4	725.7	705.3	683.0	660.8
40°	638.2	665.9	694.6	707.7	673.8	640.0	673.8	707.7	694.6	665.9	638.2
42.5°	609.2	639.8	677.1	690.8	633.7	576.5	633.7	690.8	677.1	639.8	609.2
45°	566.6	583.5	593.4	590.6	549.7	508.8	549.7	590.6	593.4	583.5	566.6
47.5°	536.9	538.8	516.7	496.1	480.1	464.2	480.1	496.1	516.7	538.8	536.9
50°	521.5	518.7	483.4	454.4	444.0	433.7	444.0	454.4	483.4	518.7	521.5
52.5°	509.2	503.5	456.6	419.7	412.7	405.8	412.7	419.7	456.6	503.5	509.2
55°	494.7	487.2	422.8	374.1	372.7	371.3	372.7	374.1	422.8	487.2	494.7
57.5°	439.3	431.4	375.5	334.2	336.7	339.1	336.7	334.2	375.5	431.4	439.3
60°	384.9	377.4	338.8	309.2	306.4	303.6	306.4	309.2	338.8	377.4	384.9
62.5°	334.0	325.2	299.1	278.8	275.9	273.1	275.9	278.8	299.1	325.2	334.0
65°	273.7	261.0	239.4	223.2	223.2	223.2	223.2	223.2	239.4	261.0	273.7
67.5°	224.6	212.0	195.5	180.4	169.1	157.8	169.1	180.4	195.5	212.0	224.6
70°	193.1	178.1	159.7	144.1	136.6	129.0	136.6	144.1	159.7	178.1	193.1
72.5°	160.6	145.9	131.0	117.6	108.9	100.3	108.9	117.6	131.0	145.9	160.6
75°	114.8	100.0	86.4	75.9	75.0	74.0	75.0	75.9	86.4	100.0	114.8
77.5°	78.8	68.5	61.6	56.5	56.6	56.7	56.6	56.5	61.6	68.5	78.8
80°	53.6	46.3	45.8	45.6	46.1	46.5	46.1	45.6	45.8	46.3	53.6
82.5°	38.9	35.0	35.7	36.2	36.3	36.4	36.3	36.2	35.7	35.0	38.9
85°	21.6	20.2	18.3	16.8	16.3	15.9	16.3	16.8	18.3	20.2	21.6
87.5°	6.4	6.4	6.9	7.1	7.4	7.3	7.4	7.1	6.9	6.4	6.4
90°	8.1	10.6	13.1	14.5	15.9	15.2	15.9	14.5	13.1	10.6	8.1
92.5°	16.4	20.5	23.6	26.1	27.3	27.1	27.3	26.1	23.6	20.5	16.4
95°	32.9	37.9	42.9	46.4	48.5	47.8	48.5	46.4	42.9	37.9	32.9
97.5°	50.8	57.5	63.0	66.3	68.4	69.9	68.4	66.3	63.0	57.5	50.8
100°	62.7	69.1	75.4	79.3	82.9	84.3	82.9	79.3	75.4	69.1	62.7
102.5°	72.3	80.7	87.6	91.8	94.8	96.2	94.8	91.8	87.6	80.7	72.3
105°	88.2	97.1	104.5	109.8	113.0	114.1	113.0	109.8	104.5	97.1	88.2
107.5°	104.1	113.2	120.1	126.0	129.9	132.1	129.9	126.0	120.1	113.2	104.1
110°	116.5	124.0	131.4	136.7	140.6	142.0	140.6	136.7	131.4	124.0	116.5



TEST NUMBER: P1427848

CATALOG NUMBER: SQ2W-PH1-K-025U-050D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	127.0	135.3	142.8	148.1	152.5	154.5	152.5	148.1	142.8	135.3	127.0
115°	141.7	152.7	159.4	164.4	167.5	169.3	167.5	164.4	159.4	152.7	141.7
117.5°	153.9	165.4	172.7	176.5	178.0	179.3	178.0	176.5	172.7	165.4	153.9
120°	161.5	172.2	180.7	185.6	187.4	188.1	187.4	185.6	180.7	172.2	161.5
122.5°	168.6	178.7	186.9	193.0	195.9	196.6	195.9	193.0	186.9	178.7	168.6
125°	178.5	188.1	196.6	202.6	205.8	207.6	205.8	202.6	196.6	188.1	178.5
127.5°	187.2	197.5	205.3	210.8	213.9	215.3	213.9	210.8	205.3	197.5	187.2
130°	192.0	202.6	210.4	216.4	219.3	220.7	219.3	216.4	210.4	202.6	192.0
132.5°	195.7	206.9	214.9	220.4	223.5	224.9	223.5	220.4	214.9	206.9	195.7
135°	200.1	211.8	220.3	225.6	228.5	229.9	228.5	225.6	220.3	211.8	200.1
137.5°	204.0	214.7	223.5	229.1	231.7	232.6	231.7	229.1	223.5	214.7	204.0
140°	206.9	216.1	224.9	230.2	233.1	233.4	233.1	230.2	224.9	216.1	206.9
142.5°	210.6	217.8	225.5	230.8	233.6	234.3	233.6	230.8	225.5	217.8	210.6
145°	217.1	221.4	226.7	231.7	234.1	234.9	234.1	231.7	226.7	221.4	217.1
147.5°	225.4	226.8	229.5	232.8	235.2	235.7	235.2	232.8	229.5	226.8	225.4
150°	231.7	231.3	232.4	234.5	236.6	236.3	236.6	234.5	232.4	231.3	231.7
152.5°	238.7	236.7	236.6	237.6	238.6	238.5	238.6	237.6	236.6	236.7	238.7
155°	250.8	246.9	244.8	244.1	244.1	243.7	244.1	244.1	244.8	246.9	250.8
157.5°	264.0	258.6	255.4	253.7	253.2	252.4	253.2	253.7	255.4	258.6	264.0
160°	273.1	267.1	263.9	261.1	260.0	258.9	260.0	261.1	263.9	267.1	273.1
162.5°	281.6	275.9	272.4	269.8	268.8	267.2	268.8	269.8	272.4	275.9	281.6
165°	295.4	289.4	285.5	283.4	282.0	280.5	282.0	283.4	285.5	289.4	295.4
167.5°	309.2	302.6	300.1	297.7	296.3	293.8	296.3	297.7	300.1	302.6	309.2
170°	317.7	311.7	310.3	308.2	305.7	302.9	305.7	308.2	310.3	311.7	317.7
172.5°	325.1	321.1	319.7	317.5	316.7	314.5	316.7	317.5	319.7	321.1	325.1
175°	335.8	332.6	332.6	332.3	331.2	329.1	331.2	332.3	332.6	332.6	335.8
177.5°	344.7	343.0	344.2	344.2	343.9	341.9	343.9	344.2	344.2	343.0	344.7
180°	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7



TEST NUMBER: P1427848

CATALOG NUMBER: SQ2W-PH1-K-025U-050D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1111.7	1111.7	1111.7	1111.7
2.5°	1112.3	1119.7	1114.4	1109.2
5°	1090.9	1112.9	1113.4	1113.8
7.5°	1034.9	1064.4	1079.0	1093.5
10°	998.2	1031.6	1053.7	1075.8
12.5°	965.2	1001.8	1036.6	1071.5
15°	917.4	954.6	1007.2	1059.9
17.5°	875.3	908.0	964.7	1021.4
20°	852.2	882.4	938.4	994.3
22.5°	831.3	858.1	914.8	971.5
25°	794.0	813.5	877.5	941.4
27.5°	759.4	771.9	838.7	905.5
30°	736.6	746.6	813.3	880.1
32.5°	710.3	717.5	786.5	855.5
35°	676.6	682.3	754.2	826.1
37.5°	638.5	641.0	718.1	795.2
40°	611.4	611.5	692.4	773.2
42.5°	585.4	587.8	668.7	749.5
45°	542.6	545.7	629.8	714.0
47.5°	511.0	511.7	591.9	672.1
50°	491.9	488.6	564.3	640.0
52.5°	473.5	464.8	536.7	608.6
55°	445.3	425.6	494.7	563.8
57.5°	399.2	385.5	450.8	516.2
60°	361.4	359.6	423.1	486.6
62.5°	325.6	334.4	394.8	455.3
65°	277.5	294.1	349.1	404.1
67.5°	233.3	251.9	299.8	347.8
70°	204.9	224.2	266.6	308.9
72.5°	175.0	194.8	231.1	267.4
75°	130.8	150.1	179.2	208.4
77.5°	92.5	108.1	129.4	150.6
80°	67.7	82.3	98.3	114.2
82.5°	47.4	56.7	68.5	80.4
85°	22.6	24.7	30.3	36.0
87.5°	7.2	7.6	7.7	7.8
90°	6.4	3.9	2.5	1.1
92.5°	13.7	9.6	6.7	3.9
95°	27.6	22.0	15.6	11.0
97.5°	44.0	34.9	28.6	21.0
100°	52.8	43.9	37.9	29.8
102.5°	62.4	55.0	46.7	38.5
105°	79.7	70.5	60.9	51.7
107.5°	95.7	85.6	74.1	65.8
110°	105.9	94.9	82.9	75.4

TEST NUMBER: P1427848

CATALOG NUMBER: SQ2W-PH1-K-025U-050D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	115.8	104.6	92.2	84.8
115°	129.3	116.9	105.6	99.2
117.5°	142.3	129.5	117.5	112.5
120°	150.2	137.4	125.7	121.9
122.5°	156.7	144.2	133.4	131.8
125°	166.5	153.7	144.5	146.6
127.5°	174.4	162.7	156.9	161.7
130°	179.2	169.0	165.4	172.2
132.5°	183.5	175.5	173.9	183.2
135°	189.9	185.3	186.7	199.4
137.5°	197.4	195.7	200.4	216.5
140°	202.3	203.3	210.1	228.1
142.5°	208.8	211.3	220.0	239.2
145°	218.9	224.2	235.6	254.7
147.5°	230.4	237.3	251.3	270.9
150°	238.0	246.9	261.8	280.5
152.5°	246.8	256.0	270.8	289.9
155°	260.4	270.6	286.2	302.5
157.5°	274.2	284.7	299.5	313.8
160°	282.7	294.0	307.5	320.6
162.5°	292.3	302.8	314.6	326.2
165°	306.4	314.9	324.5	334.4
167.5°	318.2	325.3	332.8	340.6
170°	325.9	331.6	337.9	344.0
172.5°	332.4	336.9	341.6	346.8
175°	341.1	343.6	346.4	349.6
177.5°	347.8	348.7	349.5	351.0
180°	350.7	350.7	350.7	350.7



TEST NUMBER: P1427848
 CATALOG NUMBER: SQ2W-PH1-K-025U-050D-L940-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.63	19.70	19.39	20.48	21.43	17.46	18.53	18.22	19.31	20.25
	3H	20.82	21.78	21.59	22.57	23.55	18.53	19.49	19.30	20.28	21.25
	4H	21.64	22.55	22.43	23.35	24.33	18.78	19.68	19.57	20.48	21.47
	6H	22.12	22.96	22.93	23.76	24.76	18.93	19.77	19.74	20.57	21.57
	8H	22.28	23.08	23.09	23.90	24.90	19.00	19.79	19.81	20.62	21.62
	12H	22.35	23.10	23.17	23.92	24.95	19.01	19.77	19.83	20.59	21.62
4H	2H	19.09	20.00	19.89	20.80	21.78	18.17	19.07	18.96	19.87	20.86
	3H	21.36	22.12	22.17	22.95	23.95	19.42	20.17	20.22	21.00	22.01
	4H	22.24	22.93	23.07	23.76	24.79	19.72	20.40	20.54	21.23	22.26
	6H	22.82	23.41	23.65	24.26	25.30	19.93	20.52	20.77	21.38	22.41
	8H	23.02	23.57	23.86	24.43	25.47	20.02	20.57	20.86	21.43	22.47
	12H	23.12	23.61	23.98	24.49	25.54	20.06	20.55	20.92	21.43	22.48
8H	4H	22.28	22.84	23.13	23.69	24.73	19.96	20.52	20.81	21.37	22.42
	6H	22.92	23.38	23.79	24.27	25.32	20.24	20.70	21.11	21.59	22.64
	8H	23.19	23.59	24.07	24.48	25.54	20.39	20.79	21.27	21.68	22.75
	12H	23.33	23.68	24.21	24.56	25.68	20.46	20.82	21.35	21.70	22.82
12H	4H	22.25	22.74	23.11	23.61	24.67	19.97	20.47	20.83	21.34	22.39
	6H	22.90	23.30	23.78	24.19	25.26	20.28	20.68	21.16	21.57	22.64
	8H	23.18	23.54	24.06	24.42	25.54	20.45	20.81	21.33	21.69	22.80