

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428451

Luminaire Tested: SQ2W-PW1-K-125U-075D-L840-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428451
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PW1-K-125U-075D-L840-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE WAVES LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9637.9 lumens
Efficiency: N/A
Efficacy: 136.3 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.11 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 70.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428451

CATALOG NUMBER: SQ2W-PW1-K-125U-075D-L840-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428451

CATALOG NUMBER: SQ2W-PW1-K-125U-075D-L840-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	92	88	85	88	84	81	78	69	67	65	55	54	53	43	42	41	35
2	88	81	75	70	80	74	69	65	61	58	55	49	47	45	38	37	35	30
3	80	71	65	59	73	66	60	55	54	50	46	44	41	38	34	32	31	26
4	74	64	56	50	67	58	52	47	48	44	40	39	36	33	31	29	27	23
5	68	57	49	43	62	52	45	40	44	38	35	35	32	29	28	25	23	20
6	63	51	43	38	57	47	40	35	39	34	30	32	28	26	26	23	21	18
7	58	46	38	33	53	43	36	31	36	31	27	29	26	23	23	21	19	16
8	54	42	34	29	49	39	32	27	33	28	24	27	23	20	22	19	17	14
9	50	38	31	26	46	35	29	25	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	33	26	22	28	23	19	23	19	17	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	28500	28500	28500	28500
5°	28311	28800	28311	28800
10°	28361	29051	28361	29051
15°	28354	29225	28354	29225
20°	28365	28654	28365	28654
25°	28213	26626	28213	26626
30°	28021	24072	28021	24072
35°	27801	21738	27801	21738
40°	27248	19205	27248	19205
45°	26181	16776	26181	16776
50°	24364	14357	24364	14357
55°	22288	11642	22288	11642
60°	19979	10043	19979	10043
65°	17471	8928	17471	8928
70°	14285	8096	14285	8096
75°	11116	7448	11116	7448
80°	8284	6564	8284	6564
85°	5613	3742	5613	3742

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 26181 cd/sqm



TEST NUMBER: P1428451

CATALOG NUMBER: SQ2W-PW1-K-125U-075D-L840-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.1	1.7
10°-20°	487.0	5.1
20°-30°	716.7	7.4
30°-40°	783.7	8.1
40°-50°	703.0	7.3
50°-60°	524.4	5.4
60°-70°	331.4	3.4
70°-80°	164.2	1.7
80°-90°	46.5	0.5
90°-100°	155.7	1.6
100°-110°	454.1	4.7
110°-120°	741.1	7.7
120°-130°	940.4	9.8
130°-140°	1006.2	10.4
140°-150°	939.6	9.7
150°-160°	773.1	8.0
160°-170°	518.5	5.4
170°-180°	184.1	1.9
0°-30°	1371.9	14.2
0°-40°	2155.5	22.4
0°-60°	3382.9	35.1
0°-90°	3925.1	40.7
90°-120°	1350.9	14.0
90°-150°	4237.0	44.0
90°-180°	5713.0	59.3
0°-180°	9637.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1765	1765	1765	1765	1765	
5°	1747	1777	1747	1777	1747	166
15°	1696	1748	1696	1748	1696	479
25°	1584	1495	1584	1495	1584	729
35°	1410	1103	1410	1103	1410	880
45°	1147	735	1147	735	1147	879
55°	792	414	792	414	792	707
65°	457	234	457	234	457	453
75°	178	119	178	119	178	196
85°	30	20	30	20	30	39
90°	6	44	6	85	6	6
95°	61	46	61	267	61	74
105°	288	462	288	636	288	307
115°	553	767	553	945	553	545
125°	818	1215	818	1158	818	732
135°	1113	1591	1113	1283	1113	860
145°	1421	1834	1421	1310	1421	889
155°	1688	1992	1688	1360	1688	776
165°	1866	2077	1866	1565	1866	525
175°	1951	2034	1951	1836	1951	185
180°	1956	1956	1956	1956	1956	

TEST NUMBER: P1428451

CATALOG NUMBER: SQ2W-PW1-K-125U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1765.2	1765.2	1765.2	1765.2	1765.2	1765.2	1765.2	1765.2	1765.2	1765.2	1765.2
2.5°	1753.1	1763.3	1773.5	1771.1	1764.5	1761.5	1762.1	1763.0	1764.8	1766.6	1764.8
5°	1746.8	1759.5	1772.2	1770.3	1763.6	1760.6	1761.3	1763.6	1770.3	1777.0	1770.3
7.5°	1738.0	1750.9	1763.7	1763.1	1758.0	1756.8	1759.3	1762.9	1769.4	1776.0	1769.4
10°	1729.9	1743.4	1756.8	1756.8	1752.4	1752.0	1755.7	1760.0	1766.0	1772.0	1766.0
12.5°	1719.2	1733.2	1747.3	1748.3	1745.0	1745.6	1749.9	1754.6	1760.6	1766.6	1760.6
15°	1696.3	1711.3	1726.2	1729.4	1728.6	1730.9	1736.1	1741.0	1744.7	1748.4	1744.7
17.5°	1669.8	1684.7	1699.6	1702.6	1701.6	1701.7	1703.0	1704.5	1706.3	1708.1	1706.3
20°	1650.9	1665.9	1680.8	1682.9	1680.6	1676.9	1671.7	1667.7	1667.7	1667.7	1667.7
22.5°	1624.0	1640.2	1656.3	1656.4	1651.2	1641.5	1627.3	1615.4	1610.7	1605.9	1610.7
25°	1583.7	1599.4	1615.1	1607.8	1592.8	1570.8	1541.7	1517.0	1505.8	1494.6	1505.8
27.5°	1536.6	1549.3	1562.0	1543.0	1513.4	1477.9	1436.5	1401.6	1386.0	1370.5	1386.0
30°	1503.0	1512.7	1522.4	1492.3	1449.0	1404.5	1359.0	1321.0	1306.1	1291.2	1306.1
32.5°	1468.0	1471.8	1475.5	1435.8	1381.8	1331.0	1283.6	1244.1	1227.9	1211.8	1227.9
35°	1410.5	1403.8	1397.1	1344.4	1276.4	1218.5	1170.7	1131.3	1117.1	1102.9	1117.1
37.5°	1342.6	1322.6	1302.5	1243.2	1170.7	1109.4	1059.4	1017.9	1002.2	986.5	1002.2
40°	1292.8	1264.4	1236.0	1172.3	1096.9	1034.1	984.1	942.6	926.9	911.2	926.9
42.5°	1237.7	1202.1	1166.6	1101.1	1025.6	962.8	912.8	871.2	854.9	838.6	854.9
45°	1146.6	1104.7	1062.9	994.7	917.7	855.0	806.4	766.1	750.4	734.7	750.4
47.5°	1044.0	1002.5	960.9	892.9	816.1	754.2	707.1	668.4	655.0	641.5	655.0
50°	970.0	929.7	889.3	824.3	751.1	691.0	643.9	604.5	588.0	571.6	588.0
52.5°	894.7	858.6	822.4	759.8	688.4	628.5	580.2	538.4	516.0	493.6	516.0
55°	791.8	757.5	723.1	664.1	596.8	536.3	482.5	439.0	426.3	413.6	426.3
57.5°	685.9	656.2	626.4	573.4	512.6	457.7	408.9	369.6	359.1	348.7	359.1
60°	618.7	592.5	566.4	515.6	456.5	406.5	365.4	331.9	321.5	311.0	321.5
62.5°	554.1	531.0	507.8	459.1	401.8	356.9	324.1	297.4	288.8	280.1	288.8
65°	457.3	440.1	422.9	382.8	334.9	297.6	270.7	248.6	241.2	233.7	241.2
67.5°	363.1	353.6	344.0	313.9	277.0	246.8	223.1	204.2	199.3	194.3	199.3
70°	302.6	299.6	296.6	271.8	239.7	213.9	194.5	179.0	175.2	171.5	175.2
72.5°	250.2	251.4	252.6	231.9	203.9	182.4	167.1	155.0	152.5	150.0	152.5
75°	178.2	184.2	190.2	176.5	156.4	141.0	130.6	122.4	120.9	119.4	120.9
77.5°	121.4	130.3	139.3	130.5	115.7	104.4	96.6	90.5	89.3	88.1	89.3
80°	89.1	98.1	107.0	100.9	89.7	81.1	75.1	70.6	70.6	70.6	70.6
82.5°	62.2	69.4	76.6	72.2	64.0	58.4	55.4	53.1	53.1	53.1	53.1
85°	30.3	34.0	37.7	36.4	33.4	29.7	25.2	21.7	20.9	20.2	20.9
87.5°	9.3	12.6	16.4	16.2	14.4	13.0	12.4	12.3	12.7	12.7	12.7
90°	5.9	13.8	23.7	31.6	37.5	39.5	39.5	41.5	43.5	43.5	43.5
92.5°	21.7	34.4	34.8	34.8	42.3	45.9	49.0	49.4	51.4	51.4	51.4
95°	61.3	67.2	100.8	98.8	67.2	53.4	45.5	45.5	45.5	45.5	45.5
97.5°	117.0	125.7	131.2	175.9	185.8	179.4	146.2	122.9	109.9	104.0	109.9
100°	166.0	170.0	181.8	183.8	233.2	280.6	256.9	227.3	217.4	211.5	217.4
102.5°	215.0	217.4	235.6	243.9	255.3	282.2	364.4	355.3	348.6	347.4	348.6
105°	288.5	290.5	324.1	339.9	347.8	347.8	345.9	385.4	448.6	462.5	448.6
107.5°	367.2	376.3	415.8	458.1	467.2	469.6	459.3	453.4	451.0	452.6	451.0
110°	421.0	434.8	482.2	535.6	549.4	553.4	549.4	543.5	539.5	539.5	539.5

TEST NUMBER: P1428451

CATALOG NUMBER: SQ2W-PW1-K-125U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	473.1	493.3	547.0	608.3	631.6	643.5	634.8	630.4	626.5	629.7	626.5
115°	553.4	583.0	654.2	717.4	764.8	770.8	768.8	768.8	766.8	766.8	766.8
117.5°	627.7	675.1	754.9	828.5	883.4	899.2	907.1	904.8	902.4	906.3	902.4
120°	679.8	735.2	826.1	909.1	962.5	986.2	994.1	990.1	994.1	990.1	994.1
122.5°	735.2	803.2	892.5	978.7	1041.5	1068.4	1077.9	1078.7	1079.5	1077.1	1079.5
125°	818.2	901.2	1005.9	1094.9	1160.1	1191.7	1199.6	1201.6	1205.5	1215.4	1205.5
127.5°	902.0	996.1	1111.1	1196.9	1263.7	1302.0	1314.2	1318.6	1326.9	1331.2	1326.9
130°	960.5	1067.2	1183.8	1264.8	1330.1	1371.6	1393.3	1399.2	1409.1	1407.1	1409.1
132.5°	1022.1	1133.6	1251.8	1336.0	1396.5	1441.1	1459.7	1476.7	1480.3	1483.0	1480.3
135°	1112.7	1233.2	1351.8	1434.8	1492.1	1535.6	1559.3	1575.1	1585.0	1590.9	1585.0
137.5°	1207.9	1335.2	1449.0	1522.9	1580.7	1618.2	1645.1	1661.7	1672.0	1676.7	1672.0
140°	1272.7	1395.3	1505.9	1583.0	1634.4	1672.0	1695.7	1715.4	1727.3	1727.3	1727.3
142.5°	1334.4	1455.4	1562.9	1639.9	1685.0	1719.4	1744.7	1759.7	1773.1	1773.1	1773.1
145°	1421.0	1541.5	1640.3	1717.4	1755.0	1786.6	1814.3	1826.1	1834.0	1834.0	1834.0
147.5°	1511.5	1618.2	1708.3	1782.2	1813.9	1851.0	1872.7	1882.2	1892.1	1887.8	1892.1
150°	1565.2	1664.1	1751.0	1820.2	1851.8	1887.4	1909.1	1917.0	1926.9	1921.0	1926.9
152.5°	1617.4	1711.5	1790.5	1855.0	1881.8	1917.4	1942.3	1950.2	1956.9	1952.6	1956.9
155°	1687.8	1770.8	1843.9	1903.2	1926.9	1960.5	1984.2	1994.1	2002.0	1992.1	2002.0
157.5°	1750.6	1822.2	1885.8	1940.3	1965.6	1994.5	2016.6	2028.9	2036.8	2032.4	2036.8
160°	1788.6	1853.8	1911.1	1962.5	1986.2	2011.9	2035.6	2049.4	2057.3	2051.4	2057.3
162.5°	1820.2	1879.1	1933.2	1979.9	2000.4	2022.9	2051.4	2063.7	2071.6	2064.1	2071.6
165°	1865.6	1913.1	1960.5	2000.0	2017.8	2035.6	2065.2	2079.1	2085.0	2077.1	2085.0
167.5°	1900.0	1936.4	1974.7	2008.7	2021.8	2039.2	2068.8	2080.3	2087.8	2077.9	2087.8
170°	1919.0	1950.6	1984.2	2011.9	2021.8	2037.6	2067.2	2077.1	2083.0	2073.1	2083.0
172.5°	1934.8	1958.5	1985.8	2010.3	2015.4	2028.1	2056.2	2066.0	2070.4	2062.1	2070.4
175°	1950.6	1964.5	1984.2	2000.0	1998.0	2006.0	2029.7	2037.6	2045.5	2033.6	2045.5
177.5°	1958.1	1964.5	1970.8	1980.3	1973.9	1973.9	1991.3	1996.1	1997.7	1991.3	1997.7
180°	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5

TEST NUMBER: P1428451

CATALOG NUMBER: SQ2W-PW1-K-125U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1765.2	1765.2	1765.2	1765.2	1765.2	1765.2	1765.2	1765.2	1765.2	1765.2	1765.2
2.5°	1763.0	1762.1	1761.5	1764.5	1771.1	1773.5	1763.3	1753.1	1763.3	1773.5	1771.1
5°	1763.6	1761.3	1760.6	1763.6	1770.3	1772.2	1759.5	1746.8	1759.5	1772.2	1770.3
7.5°	1762.9	1759.3	1756.8	1758.0	1763.1	1763.7	1750.9	1738.0	1750.9	1763.7	1763.1
10°	1760.0	1755.7	1752.0	1752.4	1756.8	1756.8	1743.4	1729.9	1743.4	1756.8	1756.8
12.5°	1754.6	1749.9	1745.6	1745.0	1748.3	1747.3	1733.2	1719.2	1733.2	1747.3	1748.3
15°	1741.0	1736.1	1730.9	1728.6	1729.4	1726.2	1711.3	1696.3	1711.3	1726.2	1729.4
17.5°	1704.5	1703.0	1701.7	1701.6	1702.6	1699.6	1684.7	1669.8	1684.7	1699.6	1702.6
20°	1667.7	1671.7	1676.9	1680.6	1682.9	1680.8	1665.9	1650.9	1665.9	1680.8	1682.9
22.5°	1615.4	1627.3	1641.5	1651.2	1656.4	1656.3	1640.2	1624.0	1640.2	1656.3	1656.4
25°	1517.0	1541.7	1570.8	1592.8	1607.8	1615.1	1599.4	1583.7	1599.4	1615.1	1607.8
27.5°	1401.6	1436.5	1477.9	1513.4	1543.0	1562.0	1549.3	1536.6	1549.3	1562.0	1543.0
30°	1321.0	1359.0	1404.5	1449.0	1492.3	1522.4	1512.7	1503.0	1512.7	1522.4	1492.3
32.5°	1244.1	1283.6	1331.0	1381.8	1435.8	1475.5	1471.8	1468.0	1471.8	1475.5	1435.8
35°	1131.3	1170.7	1218.5	1276.4	1344.4	1397.1	1403.8	1410.5	1403.8	1397.1	1344.4
37.5°	1017.9	1059.4	1109.4	1170.7	1243.2	1302.5	1322.6	1342.6	1322.6	1302.5	1243.2
40°	942.6	984.1	1034.1	1096.9	1172.3	1236.0	1264.4	1292.8	1264.4	1236.0	1172.3
42.5°	871.2	912.8	962.8	1025.6	1101.1	1166.6	1202.1	1237.7	1202.1	1166.6	1101.1
45°	766.1	806.4	855.0	917.7	994.7	1062.9	1104.7	1146.6	1104.7	1062.9	994.7
47.5°	668.4	707.1	754.2	816.1	892.9	960.9	1002.5	1044.0	1002.5	960.9	892.9
50°	604.5	643.9	691.0	751.1	824.3	889.3	929.7	970.0	929.7	889.3	824.3
52.5°	538.4	580.2	628.5	688.4	759.8	822.4	858.6	894.7	858.6	822.4	759.8
55°	439.0	482.5	536.3	596.8	664.1	723.1	757.5	791.8	757.5	723.1	664.1
57.5°	369.6	408.9	457.7	512.6	573.4	626.4	656.2	685.9	656.2	626.4	573.4
60°	331.9	365.4	406.5	456.5	515.6	566.4	592.5	618.7	592.5	566.4	515.6
62.5°	297.4	324.1	356.9	401.8	459.1	507.8	531.0	554.1	531.0	507.8	459.1
65°	248.6	270.7	297.6	334.9	382.8	422.9	440.1	457.3	440.1	422.9	382.8
67.5°	204.2	223.1	246.8	277.0	313.9	344.0	353.6	363.1	353.6	344.0	313.9
70°	179.0	194.5	213.9	239.7	271.8	296.6	299.6	302.6	299.6	296.6	271.8
72.5°	155.0	167.1	182.4	203.9	231.9	252.6	251.4	250.2	251.4	252.6	231.9
75°	122.4	130.6	141.0	156.4	176.5	190.2	184.2	178.2	184.2	190.2	176.5
77.5°	90.5	96.6	104.4	115.7	130.5	139.3	130.3	121.4	130.3	139.3	130.5
80°	70.6	75.1	81.1	89.7	100.9	107.0	98.1	89.1	98.1	107.0	100.9
82.5°	53.1	55.4	58.4	64.0	72.2	76.6	69.4	62.2	69.4	76.6	72.2
85°	21.7	25.2	29.7	33.4	36.4	37.7	34.0	30.3	34.0	37.7	36.4
87.5°	12.3	12.4	13.0	14.4	16.2	16.4	12.6	9.3	12.6	16.0	17.0
90°	41.5	39.5	39.5	37.5	31.6	23.7	13.8	5.9	13.8	21.7	35.6
92.5°	49.4	49.0	45.9	42.3	34.8	34.8	34.4	21.7	37.5	53.4	76.7
95°	45.5	45.5	53.4	67.2	98.8	100.8	67.2	61.3	87.0	122.5	154.2
97.5°	122.9	146.2	179.4	185.8	175.9	131.2	125.7	117.0	159.3	194.5	245.5
100°	227.3	256.9	280.6	233.2	183.8	181.8	170.0	166.0	211.5	245.1	294.5
102.5°	355.3	364.4	282.2	255.3	243.9	235.6	217.4	215.0	260.5	306.7	348.2
105°	385.4	345.9	347.8	347.8	339.9	324.1	290.5	288.5	339.9	393.3	444.7
107.5°	453.4	459.3	469.6	467.2	458.1	415.8	376.3	367.2	413.4	477.5	534.0
110°	543.5	549.4	553.4	549.4	535.6	482.2	434.8	421.0	462.5	529.7	590.9



TEST NUMBER: P1428451

CATALOG NUMBER: SQ2W-PW1-K-125U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	630.4	634.8	643.5	631.6	608.3	547.0	493.3	473.1	514.6	583.4	646.3
115°	768.8	768.8	770.8	764.8	717.4	654.2	583.0	553.4	588.9	652.2	721.4
117.5°	904.8	907.1	899.2	883.4	828.5	754.9	675.1	627.7	655.7	722.5	793.7
120°	990.1	994.1	986.2	962.5	909.1	826.1	735.2	679.8	701.6	766.8	838.0
122.5°	1078.7	1077.9	1068.4	1041.5	978.7	892.5	803.2	735.2	744.3	804.8	874.3
125°	1201.6	1199.6	1191.7	1160.1	1094.9	1005.9	901.2	818.2	806.3	857.7	928.9
127.5°	1318.6	1314.2	1302.0	1263.7	1196.9	1111.1	996.1	902.0	875.5	907.9	973.1
130°	1399.2	1393.3	1371.6	1330.1	1264.8	1183.8	1067.2	960.5	922.9	942.7	1000.0
132.5°	1476.7	1459.7	1441.1	1396.5	1336.0	1251.8	1133.6	1022.1	970.4	979.1	1023.7
135°	1575.1	1559.3	1535.6	1492.1	1434.8	1351.8	1233.2	1112.7	1041.5	1033.6	1059.3
137.5°	1661.7	1645.1	1618.2	1580.7	1522.9	1449.0	1335.2	1207.9	1118.2	1091.7	1101.6
140°	1715.4	1695.7	1672.0	1634.4	1583.0	1505.9	1395.3	1272.7	1172.0	1134.4	1128.5
142.5°	1759.7	1744.7	1719.4	1685.0	1639.9	1562.9	1455.4	1334.4	1227.3	1178.7	1164.8
145°	1826.1	1814.3	1786.6	1755.0	1717.4	1640.3	1541.5	1421.0	1314.2	1251.0	1221.4
147.5°	1882.2	1872.7	1851.0	1813.9	1782.2	1708.3	1618.2	1511.5	1402.0	1323.7	1285.4
150°	1917.0	1909.1	1887.4	1851.8	1820.2	1751.0	1664.1	1565.2	1460.5	1377.5	1328.1
152.5°	1950.2	1942.3	1917.4	1881.8	1855.0	1790.5	1711.5	1617.4	1511.1	1428.1	1377.1
155°	1994.1	1984.2	1960.5	1926.9	1903.2	1843.9	1770.8	1687.8	1596.9	1509.9	1452.6
157.5°	2028.9	2016.6	1994.5	1965.6	1940.3	1885.8	1822.2	1750.6	1671.2	1588.2	1529.7
160°	2049.4	2035.6	2011.9	1986.2	1962.5	1911.1	1853.8	1788.6	1715.4	1640.3	1577.1
162.5°	2063.7	2051.4	2022.9	2000.4	1979.9	1933.2	1879.1	1820.2	1755.0	1689.3	1630.8
165°	2079.1	2065.2	2035.6	2017.8	2000.0	1960.5	1913.1	1865.6	1810.3	1756.9	1709.5
167.5°	2080.3	2068.8	2039.2	2021.8	2008.7	1974.7	1936.4	1900.0	1856.9	1815.0	1775.5
170°	2077.1	2067.2	2037.6	2021.8	2011.9	1984.2	1950.6	1919.0	1885.4	1849.8	1818.2
172.5°	2066.0	2056.2	2028.1	2015.4	2010.3	1985.8	1958.5	1934.8	1906.0	1879.9	1854.6
175°	2037.6	2029.7	2006.0	1998.0	2000.0	1984.2	1964.5	1950.6	1932.8	1917.0	1903.2
177.5°	1996.1	1991.3	1973.9	1973.9	1980.3	1970.8	1964.5	1958.1	1950.2	1945.5	1940.7
180°	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5



TEST NUMBER: P1428451

CATALOG NUMBER: SQ2W-PW1-K-125U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1765.2	1765.2	1765.2	1765.2	1765.2	1765.2	1765.2	1765.2	1765.2	1765.2	1765.2
2.5°	1764.5	1761.5	1762.1	1763.0	1764.8	1766.6	1764.8	1763.0	1762.1	1761.5	1764.5
5°	1763.6	1760.6	1761.3	1763.6	1770.3	1777.0	1770.3	1763.6	1761.3	1760.6	1763.6
7.5°	1758.0	1756.8	1759.3	1762.9	1769.4	1776.0	1769.4	1762.9	1759.3	1756.8	1758.0
10°	1752.4	1752.0	1755.7	1760.0	1766.0	1772.0	1766.0	1760.0	1755.7	1752.0	1752.4
12.5°	1745.0	1745.6	1749.9	1754.6	1760.6	1766.6	1760.6	1754.6	1749.9	1745.6	1745.0
15°	1728.6	1730.9	1736.1	1741.0	1744.7	1748.4	1744.7	1741.0	1736.1	1730.9	1728.6
17.5°	1701.6	1701.7	1703.0	1704.5	1706.3	1708.1	1706.3	1704.5	1703.0	1701.7	1701.6
20°	1680.6	1676.9	1671.7	1667.7	1667.7	1667.7	1667.7	1667.7	1671.7	1676.9	1680.6
22.5°	1651.2	1641.5	1627.3	1615.4	1610.7	1605.9	1610.7	1615.4	1627.3	1641.5	1651.2
25°	1592.8	1570.8	1541.7	1517.0	1505.8	1494.6	1505.8	1517.0	1541.7	1570.8	1592.8
27.5°	1513.4	1477.9	1436.5	1401.6	1386.0	1370.5	1386.0	1401.6	1436.5	1477.9	1513.4
30°	1449.0	1404.5	1359.0	1321.0	1306.1	1291.2	1306.1	1321.0	1359.0	1404.5	1449.0
32.5°	1381.8	1331.0	1283.6	1244.1	1227.9	1211.8	1227.9	1244.1	1283.6	1331.0	1381.8
35°	1276.4	1218.5	1170.7	1131.3	1117.1	1102.9	1117.1	1131.3	1170.7	1218.5	1276.4
37.5°	1170.7	1109.4	1059.4	1017.9	1002.2	986.5	1002.2	1017.9	1059.4	1109.4	1170.7
40°	1096.9	1034.1	984.1	942.6	926.9	911.2	926.9	942.6	984.1	1034.1	1096.9
42.5°	1025.6	962.8	912.8	871.2	854.9	838.6	854.9	871.2	912.8	962.8	1025.6
45°	917.7	855.0	806.4	766.1	750.4	734.7	750.4	766.1	806.4	855.0	917.7
47.5°	816.1	754.2	707.1	668.4	655.0	641.5	655.0	668.4	707.1	754.2	816.1
50°	751.1	691.0	643.9	604.5	588.0	571.6	588.0	604.5	643.9	691.0	751.1
52.5°	688.4	628.5	580.2	538.4	516.0	493.6	516.0	538.4	580.2	628.5	688.4
55°	596.8	536.3	482.5	439.0	426.3	413.6	426.3	439.0	482.5	536.3	596.8
57.5°	512.6	457.7	408.9	369.6	359.1	348.7	359.1	369.6	408.9	457.7	512.6
60°	456.5	406.5	365.4	331.9	321.5	311.0	321.5	331.9	365.4	406.5	456.5
62.5°	401.8	356.9	324.1	297.4	288.8	280.1	288.8	297.4	324.1	356.9	401.8
65°	334.9	297.6	270.7	248.6	241.2	233.7	241.2	248.6	270.7	297.6	334.9
67.5°	277.0	246.8	223.1	204.2	199.3	194.3	199.3	204.2	223.1	246.8	277.0
70°	239.7	213.9	194.5	179.0	175.2	171.5	175.2	179.0	194.5	213.9	239.7
72.5°	203.9	182.4	167.1	155.0	152.5	150.0	152.5	155.0	167.1	182.4	203.9
75°	156.4	141.0	130.6	122.4	120.9	119.4	120.9	122.4	130.6	141.0	156.4
77.5°	115.7	104.4	96.6	90.5	89.3	88.1	89.3	90.5	96.6	104.4	115.7
80°	89.7	81.1	75.1	70.6	70.6	70.6	70.6	70.6	75.1	81.1	89.7
82.5°	64.0	58.4	55.4	53.1	53.1	53.1	53.1	53.1	55.4	58.4	64.0
85°	33.4	29.7	25.2	21.7	20.9	20.2	20.9	21.7	25.2	29.7	33.4
87.5°	16.0	16.9	19.1	20.2	21.8	21.0	21.8	20.2	19.1	16.9	16.0
90°	45.5	59.3	73.1	81.0	88.9	85.0	88.9	81.0	73.1	59.3	45.5
92.5°	91.3	114.6	131.6	145.9	152.2	151.4	152.2	145.9	131.6	114.6	91.3
95°	183.8	211.5	239.1	258.9	270.8	266.8	270.8	258.9	239.1	211.5	183.8
97.5°	283.4	320.6	351.4	370.0	381.8	389.7	381.8	370.0	351.4	320.6	283.4
100°	349.8	385.4	421.0	442.7	462.5	470.4	462.5	442.7	421.0	385.4	349.8
102.5°	403.6	450.2	488.9	512.3	528.9	536.8	528.9	512.3	488.9	450.2	403.6
105°	492.1	541.5	583.0	612.7	630.4	636.4	630.4	612.7	583.0	541.5	492.1
107.5°	580.6	631.6	670.0	702.8	724.5	737.2	724.5	702.8	670.0	631.6	580.6
110°	650.2	691.7	733.2	762.9	784.6	792.5	784.6	762.9	733.2	691.7	650.2



TEST NUMBER: P1428451

CATALOG NUMBER: SQ2W-PW1-K-125U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	708.7	754.9	796.5	826.1	851.0	862.1	851.0	826.1	796.5	754.9	708.7
115°	790.5	851.8	889.3	917.0	934.8	944.7	934.8	917.0	889.3	851.8	790.5
117.5°	858.5	922.5	963.6	985.0	993.3	1000.4	993.3	985.0	963.6	922.5	858.5
120°	901.2	960.5	1007.9	1035.6	1045.5	1049.4	1045.5	1035.6	1007.9	960.5	901.2
122.5°	940.7	996.8	1042.7	1076.7	1092.9	1096.9	1092.9	1076.7	1042.7	996.8	940.7
125°	996.1	1049.4	1096.9	1130.4	1148.2	1158.1	1148.2	1130.4	1096.9	1049.4	996.1
127.5°	1044.3	1102.0	1145.5	1175.9	1193.3	1201.2	1193.3	1175.9	1145.5	1102.0	1044.3
130°	1071.2	1130.4	1173.9	1207.5	1223.3	1231.2	1223.3	1207.5	1173.9	1130.4	1071.2
132.5°	1091.7	1154.2	1199.2	1229.7	1247.1	1255.0	1247.1	1229.7	1199.2	1154.2	1091.7
135°	1116.6	1181.8	1229.3	1258.9	1274.7	1282.6	1274.7	1258.9	1229.3	1181.8	1116.6
137.5°	1138.4	1197.6	1247.1	1278.3	1292.5	1297.6	1292.5	1278.3	1247.1	1197.6	1138.4
140°	1154.2	1205.5	1255.0	1284.6	1300.4	1302.4	1300.4	1284.6	1255.0	1205.5	1154.2
142.5°	1174.7	1215.0	1258.1	1287.8	1303.6	1307.1	1303.6	1287.8	1258.1	1215.0	1174.7
145°	1211.5	1235.2	1264.8	1292.5	1306.3	1310.3	1306.3	1292.5	1264.8	1235.2	1211.5
147.5°	1257.7	1265.2	1280.6	1298.8	1312.3	1315.0	1312.3	1298.8	1280.6	1265.2	1257.7
150°	1292.5	1290.5	1296.5	1308.3	1320.2	1318.2	1320.2	1308.3	1296.5	1290.5	1292.5
152.5°	1332.0	1320.6	1320.2	1325.7	1331.2	1330.8	1331.2	1325.7	1320.2	1320.6	1332.0
155°	1399.2	1377.5	1365.6	1361.7	1361.7	1359.7	1361.7	1361.7	1365.6	1377.5	1399.2
157.5°	1473.1	1442.7	1424.9	1415.4	1412.7	1408.3	1412.7	1415.4	1424.9	1442.7	1473.1
160°	1523.7	1490.1	1472.3	1456.5	1450.6	1444.7	1450.6	1456.5	1472.3	1490.1	1523.7
162.5°	1571.2	1539.1	1519.8	1505.6	1499.6	1490.5	1499.6	1505.6	1519.8	1539.1	1571.2
165°	1648.2	1614.6	1592.9	1581.0	1573.1	1565.2	1573.1	1581.0	1592.9	1614.6	1648.2
167.5°	1725.3	1688.6	1674.3	1660.9	1653.4	1639.1	1653.4	1660.9	1674.3	1688.6	1725.3
170°	1772.7	1739.2	1731.2	1719.4	1705.6	1689.7	1705.6	1719.4	1731.2	1739.2	1772.7
172.5°	1813.9	1791.3	1783.4	1771.6	1767.2	1754.6	1767.2	1771.6	1783.4	1791.3	1813.9
175°	1873.5	1855.8	1855.8	1853.8	1847.8	1836.0	1847.8	1853.8	1855.8	1855.8	1873.5
177.5°	1923.3	1913.9	1920.2	1920.2	1918.6	1907.5	1918.6	1920.2	1920.2	1913.9	1923.3
180°	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5	1956.5



TEST NUMBER: P1428451

CATALOG NUMBER: SQ2W-PW1-K-125U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1765.2	1765.2	1765.2	1765.2
2.5°	1771.1	1773.5	1763.3	1753.1
5°	1770.3	1772.2	1759.5	1746.8
7.5°	1763.1	1763.7	1750.9	1738.0
10°	1756.8	1756.8	1743.4	1729.9
12.5°	1748.3	1747.3	1733.2	1719.2
15°	1729.4	1726.2	1711.3	1696.3
17.5°	1702.6	1699.6	1684.7	1669.8
20°	1682.9	1680.8	1665.9	1650.9
22.5°	1656.4	1656.3	1640.2	1624.0
25°	1607.8	1615.1	1599.4	1583.7
27.5°	1543.0	1562.0	1549.3	1536.6
30°	1492.3	1522.4	1512.7	1503.0
32.5°	1435.8	1475.5	1471.8	1468.0
35°	1344.4	1397.1	1403.8	1410.5
37.5°	1243.2	1302.5	1322.6	1342.6
40°	1172.3	1236.0	1264.4	1292.8
42.5°	1101.1	1166.6	1202.1	1237.7
45°	994.7	1062.9	1104.7	1146.6
47.5°	892.9	960.9	1002.5	1044.0
50°	824.3	889.3	929.7	970.0
52.5°	759.8	822.4	858.6	894.7
55°	664.1	723.1	757.5	791.8
57.5°	573.4	626.4	656.2	685.9
60°	515.6	566.4	592.5	618.7
62.5°	459.1	507.8	531.0	554.1
65°	382.8	422.9	440.1	457.3
67.5°	313.9	344.0	353.6	363.1
70°	271.8	296.6	299.6	302.6
72.5°	231.9	252.6	251.4	250.2
75°	176.5	190.2	184.2	178.2
77.5°	130.5	139.3	130.3	121.4
80°	100.9	107.0	98.1	89.1
82.5°	72.2	76.6	69.4	62.2
85°	36.4	37.7	34.0	30.3
87.5°	17.0	16.0	12.6	9.3
90°	35.6	21.7	13.8	5.9
92.5°	76.7	53.4	37.5	21.7
95°	154.2	122.5	87.0	61.3
97.5°	245.5	194.5	159.3	117.0
100°	294.5	245.1	211.5	166.0
102.5°	348.2	306.7	260.5	215.0
105°	444.7	393.3	339.9	288.5
107.5°	534.0	477.5	413.4	367.2
110°	590.9	529.7	462.5	421.0



TEST NUMBER: P1428451

CATALOG NUMBER: SQ2W-PW1-K-125U-075D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	646.3	583.4	514.6	473.1
115°	721.4	652.2	588.9	553.4
117.5°	793.7	722.5	655.7	627.7
120°	838.0	766.8	701.6	679.8
122.5°	874.3	804.8	744.3	735.2
125°	928.9	857.7	806.3	818.2
127.5°	973.1	907.9	875.5	902.0
130°	1000.0	942.7	922.9	960.5
132.5°	1023.7	979.1	970.4	1022.1
135°	1059.3	1033.6	1041.5	1112.7
137.5°	1101.6	1091.7	1118.2	1207.9
140°	1128.5	1134.4	1172.0	1272.7
142.5°	1164.8	1178.7	1227.3	1334.4
145°	1221.4	1251.0	1314.2	1421.0
147.5°	1285.4	1323.7	1402.0	1511.5
150°	1328.1	1377.5	1460.5	1565.2
152.5°	1377.1	1428.1	1511.1	1617.4
155°	1452.6	1509.9	1596.9	1687.8
157.5°	1529.7	1588.2	1671.2	1750.6
160°	1577.1	1640.3	1715.4	1788.6
162.5°	1630.8	1689.3	1755.0	1820.2
165°	1709.5	1756.9	1810.3	1865.6
167.5°	1775.5	1815.0	1856.9	1900.0
170°	1818.2	1849.8	1885.4	1919.0
172.5°	1854.6	1879.9	1906.0	1934.8
175°	1903.2	1917.0	1932.8	1950.6
177.5°	1940.7	1945.5	1950.2	1958.1
180°	1956.5	1956.5	1956.5	1956.5



TEST NUMBER: P1428451
 CATALOG NUMBER: SQ2W-PW1-K-125U-075D-L840-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.62	18.37	18.66	19.41	20.81	13.87	14.62	14.91	15.66	17.06
	3H	18.91	19.59	19.96	20.64	22.06	15.13	15.80	16.18	16.85	18.27
	4H	19.31	19.95	20.38	21.01	22.43	15.63	16.27	16.69	17.32	18.75
	6H	19.49	20.08	20.56	21.13	22.57	15.93	16.52	17.00	17.58	19.01
	8H	19.53	20.09	20.60	21.16	22.59	16.04	16.60	17.12	17.67	19.11
	12H	19.53	20.06	20.61	21.12	22.58	16.07	16.60	17.15	17.67	19.12
4H	2H	17.74	18.37	18.80	19.43	20.85	14.66	15.30	15.73	16.35	17.78
	3H	19.27	19.80	20.34	20.88	22.32	16.10	16.63	17.17	17.71	19.15
	4H	19.81	20.29	20.89	21.36	22.83	16.67	17.16	17.75	18.23	19.69
	6H	20.11	20.53	21.20	21.62	23.08	17.05	17.47	18.14	18.56	20.02
	8H	20.20	20.59	21.29	21.68	23.15	17.20	17.59	18.29	18.68	20.15
	12H	20.22	20.57	21.33	21.67	23.15	17.24	17.59	18.35	18.69	20.17
8H	4H	19.84	20.23	20.93	21.31	22.78	17.01	17.40	18.10	18.48	19.96
	6H	20.26	20.58	21.37	21.71	23.17	17.50	17.82	18.61	18.95	20.42
	8H	20.43	20.71	21.55	21.82	23.31	17.72	18.00	18.84	19.11	20.60
	12H	20.50	20.75	21.62	21.85	23.38	17.80	18.04	18.92	19.15	20.68
12H	4H	19.79	20.14	20.90	21.24	22.72	17.02	17.37	18.13	18.47	19.95
	6H	20.25	20.53	21.37	21.64	23.13	17.57	17.85	18.69	18.96	20.45
	8H	20.44	20.68	21.56	21.79	23.31	17.81	18.06	18.93	19.17	20.69