

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427980

Luminaire Tested: SQ2W-PH1-K-150U-100D-L940-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1427980
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-10)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PH1-K-150U-100D-L940-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE HEX LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10926.6 lumens
Efficiency: N/A
Efficacy: 117.9 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.02 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 92.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1427980

CATALOG NUMBER: SQ2W-PH1-K-150U-100D-L940-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1427980

CATALOG NUMBER: SQ2W-PH1-K-150U-100D-L940-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44				
1	97	92	89	85	88	85	81	79	70	68	66	57	55	54	45	44	43	37				
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	36	31				
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	27				
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	31	29	27	23				
5	67	56	48	42	61	52	45	39	43	38	34	36	32	29	28	26	23	20				
6	62	50	42	37	57	46	39	34	39	34	30	32	28	25	26	23	21	18				
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	16				
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14				
9	50	37	30	25	45	35	28	24	29	24	21	25	21	18	20	17	15	13				
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	18	16	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	34813	34813	34813	34813
5°	35012	31821	35012	31821
10°	34207	28927	34207	28927
15°	34361	28361	34361	28361
20°	33135	28589	33135	28589
25°	32528	27923	32528	27923
30°	31822	28151	31822	28151
35°	31581	32997	31581	32997
40°	31608	26160	31608	26160
45°	31619	22532	31619	22532
50°	31176	21129	31176	21129
55°	30781	20270	30781	20270
60°	30473	19013	30473	19013
65°	29940	16538	29940	16538
70°	28281	11816	28281	11816
75°	25215	8958	25215	8958
80°	20604	8396	20604	8396
85°	12930	5706	12930	5706

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 31619 cd/sqm



TEST NUMBER: P1427980

CATALOG NUMBER: SQ2W-PH1-K-150U-100D-L940-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.7	1.7
10°-20°	499.1	4.6
20°-30°	731.7	6.7
30°-40°	886.0	8.1
40°-50°	871.2	8.0
50°-60°	757.8	6.9
60°-70°	527.1	4.8
70°-80°	250.0	2.3
80°-90°	63.8	0.6
90°-100°	167.6	1.5
100°-110°	488.9	4.5
110°-120°	797.8	7.3
120°-130°	1012.4	9.3
130°-140°	1083.3	9.9
140°-150°	1011.5	9.3
150°-160°	832.4	7.6
160°-170°	558.2	5.1
170°-180°	198.2	1.8
0°-30°	1420.5	13.0
0°-40°	2306.5	21.1
0°-60°	3935.5	36.0
0°-90°	4776.3	43.7
90°-120°	1454.3	13.3
90°-150°	4561.5	41.7
90°-180°	6150.0	56.3
0°-180°	10926.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2156	2156	2156	2156	2156	
5°	2160	1963	2160	1963	2160	203
15°	2056	1697	2056	1697	2056	573
25°	1826	1567	1826	1567	1826	840
35°	1602	1674	1602	1674	1602	1004
45°	1385	987	1385	987	1385	1064
55°	1094	720	1094	720	1094	977
65°	784	433	784	433	784	770
75°	404	144	404	144	404	428
85°	70	31	70	31	70	94
90°	6	47	6	92	6	7
95°	66	49	66	287	66	80
105°	311	498	311	685	311	330
115°	596	826	596	1017	596	587
125°	881	1308	881	1247	881	788
135°	1198	1713	1198	1381	1198	926
145°	1530	1974	1530	1411	1530	957
155°	1817	2145	1817	1464	1817	835
165°	2008	2236	2008	1685	2008	565
175°	2100	2189	2100	1977	2100	199
180°	2106	2106	2106	2106	2106	



TEST NUMBER: P1427980

CATALOG NUMBER: SQ2W-PH1-K-150U-100D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2156.2	2156.2	2156.2	2156.2	2156.2	2156.2	2156.2	2156.2	2156.2	2156.2	2156.2
2.5°	2151.3	2161.5	2171.7	2157.3	2134.7	2119.0	2110.3	2103.4	2101.9	2100.4	2101.9
5°	2160.3	2159.4	2158.5	2115.9	2059.4	2017.0	1988.7	1967.0	1965.2	1963.4	1965.2
7.5°	2121.0	2092.7	2064.4	2007.2	1940.2	1891.2	1860.0	1836.2	1834.8	1833.3	1834.8
10°	2086.5	2043.6	2000.8	1936.0	1864.0	1813.8	1785.6	1764.4	1764.4	1764.4	1764.4
12.5°	2078.3	2010.6	1943.0	1872.0	1800.0	1753.5	1732.5	1717.9	1722.3	1726.6	1722.3
15°	2055.7	1953.6	1851.5	1779.4	1717.4	1683.7	1678.2	1676.6	1686.6	1696.7	1686.6
17.5°	1981.0	1871.1	1761.1	1697.8	1650.0	1631.9	1643.6	1655.3	1667.0	1678.6	1667.0
20°	1928.5	1820.0	1711.5	1652.9	1611.0	1600.9	1622.8	1642.0	1652.9	1663.9	1652.9
22.5°	1884.2	1774.2	1664.3	1612.4	1580.0	1575.8	1599.8	1619.4	1625.2	1631.0	1625.2
25°	1825.9	1701.9	1577.9	1540.1	1531.0	1536.9	1557.9	1572.9	1570.2	1567.4	1570.2
27.5°	1756.2	1626.7	1497.2	1472.9	1483.7	1495.4	1508.2	1518.2	1519.8	1521.5	1519.8
30°	1706.9	1577.5	1448.0	1428.6	1445.9	1461.0	1473.7	1486.3	1498.1	1510.0	1498.1
32.5°	1659.3	1525.5	1391.6	1377.7	1403.8	1432.0	1462.2	1491.7	1518.9	1546.1	1518.9
35°	1602.3	1462.8	1323.3	1312.3	1344.3	1385.3	1435.4	1495.4	1584.8	1674.1	1584.8
37.5°	1542.4	1392.9	1243.3	1238.4	1281.6	1324.8	1368.0	1407.5	1436.0	1464.4	1436.0
40°	1499.7	1342.9	1186.1	1185.8	1237.8	1291.6	1347.2	1372.5	1306.9	1241.2	1306.9
42.5°	1453.8	1296.9	1140.1	1135.5	1181.6	1240.9	1313.3	1339.9	1229.0	1118.1	1229.0
45°	1384.8	1221.6	1058.4	1052.5	1099.0	1131.8	1151.0	1145.5	1066.2	986.8	1066.2
47.5°	1303.6	1148.0	992.5	991.2	1041.4	1045.0	1002.1	962.2	931.2	900.2	931.2
50°	1241.2	1094.4	947.6	954.0	1011.4	1006.0	937.6	881.3	861.2	841.2	861.2
52.5°	1180.5	1041.0	901.5	918.4	987.6	976.6	885.6	814.0	800.5	787.0	800.5
55°	1093.5	959.5	825.4	863.7	959.5	944.9	820.0	725.6	722.8	720.1	722.8
57.5°	1001.2	874.4	747.7	774.3	852.0	836.6	728.3	648.3	653.0	657.7	653.0
60°	943.7	820.6	697.5	701.0	746.6	732.0	657.2	599.8	594.3	588.8	594.3
62.5°	883.0	765.8	648.5	631.5	647.9	630.8	580.1	540.7	535.2	529.7	535.2
65°	783.7	677.0	570.3	538.2	530.9	506.3	464.3	432.9	432.9	432.9	432.9
67.5°	674.6	581.6	488.6	452.6	435.6	411.2	379.3	349.9	328.0	306.1	328.0
70°	599.1	517.0	434.9	397.3	374.5	345.4	309.8	279.5	264.9	250.3	264.9
72.5°	518.6	448.3	377.9	339.3	311.4	283.0	254.0	228.0	211.3	194.5	211.3
75°	404.2	347.6	291.1	253.7	222.7	194.0	167.5	147.3	145.4	143.6	145.4
77.5°	292.1	250.9	209.7	179.4	152.8	132.9	119.5	109.6	109.8	110.0	109.8
80°	221.6	190.6	159.6	131.3	103.9	89.8	88.9	88.4	89.4	90.3	89.4
82.5°	155.9	132.9	110.0	91.9	75.5	67.9	69.2	70.2	70.4	70.6	70.4
85°	69.8	58.8	47.9	43.8	41.9	39.2	35.6	32.6	31.7	30.8	31.7
87.5°	16.0	17.0	18.4	18.3	17.4	16.7	16.7	17.1	17.6	17.6	17.6
90°	6.4	14.9	25.5	34.0	40.4	42.6	42.6	44.7	46.8	46.8	46.8
92.5°	23.4	37.0	37.4	37.4	45.5	49.4	52.8	53.2	55.3	55.3	55.3
95°	66.0	72.3	108.5	106.4	72.3	57.4	48.9	48.9	48.9	48.9	48.9
97.5°	126.0	135.3	141.3	189.4	200.0	193.2	157.4	132.3	118.3	111.9	118.3
100°	178.7	183.0	195.7	197.9	251.1	302.1	276.6	244.7	234.0	227.7	234.0
102.5°	231.5	234.0	253.6	262.6	274.9	303.8	392.3	382.6	375.3	374.0	375.3
105°	310.6	312.8	348.9	366.0	374.5	374.5	372.3	414.9	483.0	497.9	483.0
107.5°	395.3	405.1	447.7	493.2	503.0	505.5	494.5	488.1	485.5	487.2	485.5
110°	453.2	468.1	519.2	576.6	591.5	595.8	591.5	585.1	580.9	580.9	580.9



TEST NUMBER: P1427980

CATALOG NUMBER: SQ2W-PH1-K-150U-100D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	509.4	531.1	588.9	654.9	680.0	692.8	683.4	678.7	674.5	677.9	674.5
115°	595.8	627.7	704.3	772.3	823.4	829.8	827.7	827.7	825.5	825.5	825.5
117.5°	675.8	726.8	812.8	891.9	951.1	968.1	976.6	974.1	971.5	975.8	971.5
120°	731.9	791.5	889.4	978.7	1036.2	1061.7	1070.2	1066.0	1070.2	1066.0	1070.2
122.5°	791.5	864.7	960.9	1053.6	1121.3	1150.2	1160.4	1161.3	1162.1	1159.6	1162.1
125°	880.9	970.2	1083.0	1178.7	1248.9	1283.0	1291.5	1293.6	1297.9	1308.5	1297.9
127.5°	971.1	1072.4	1196.2	1288.5	1360.4	1401.7	1414.9	1419.6	1428.5	1433.2	1428.5
130°	1034.1	1148.9	1274.5	1361.7	1431.9	1476.6	1500.0	1506.4	1517.0	1514.9	1517.0
132.5°	1100.4	1220.4	1347.7	1438.3	1503.4	1551.5	1571.5	1589.8	1593.6	1596.6	1593.6
135°	1197.9	1327.7	1455.3	1544.7	1606.4	1653.2	1678.7	1695.8	1706.4	1712.8	1706.4
137.5°	1300.4	1437.5	1560.0	1639.6	1701.7	1742.1	1771.1	1789.0	1800.0	1805.1	1800.0
140°	1370.2	1502.1	1621.3	1704.3	1759.6	1800.0	1825.5	1846.8	1859.6	1859.6	1859.6
142.5°	1436.6	1566.8	1682.6	1765.5	1814.1	1851.1	1878.3	1894.5	1909.0	1909.0	1909.0
145°	1529.8	1659.6	1766.0	1849.0	1889.4	1923.4	1953.2	1966.0	1974.5	1974.5	1974.5
147.5°	1627.2	1742.1	1839.2	1918.7	1952.8	1992.8	2016.2	2026.4	2037.0	2032.4	2037.0
150°	1685.1	1791.5	1885.1	1959.6	1993.6	2031.9	2055.3	2063.8	2074.5	2068.1	2074.5
152.5°	1741.3	1842.6	1927.7	1997.0	2026.0	2064.3	2091.1	2099.6	2106.8	2102.1	2106.8
155°	1817.0	1906.4	1985.1	2049.0	2074.5	2110.7	2136.2	2146.8	2155.3	2144.7	2155.3
157.5°	1884.7	1961.7	2030.2	2089.0	2116.2	2147.3	2171.1	2184.3	2192.8	2188.1	2192.8
160°	1925.6	1995.8	2057.5	2112.8	2138.3	2166.0	2191.5	2206.4	2214.9	2208.5	2214.9
162.5°	1959.6	2023.0	2081.3	2131.5	2153.6	2177.9	2208.5	2221.7	2230.2	2222.1	2230.2
165°	2008.5	2059.6	2110.7	2153.2	2172.4	2191.5	2223.4	2238.3	2244.7	2236.2	2244.7
167.5°	2045.6	2084.7	2126.0	2162.6	2176.6	2195.3	2227.3	2239.6	2247.7	2237.0	2247.7
170°	2066.0	2100.0	2136.2	2166.0	2176.6	2193.6	2225.6	2236.2	2242.6	2231.9	2242.6
172.5°	2083.0	2108.5	2137.9	2164.3	2169.8	2183.4	2213.6	2224.3	2229.0	2220.0	2229.0
175°	2100.0	2114.9	2136.2	2153.2	2151.1	2159.6	2185.1	2193.6	2202.1	2189.4	2202.1
177.5°	2108.1	2114.9	2121.7	2131.9	2125.1	2125.1	2143.9	2149.0	2150.7	2143.9	2150.7
180°	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4



TEST NUMBER: P1427980

CATALOG NUMBER: SQ2W-PH1-K-150U-100D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2156.2	2156.2	2156.2	2156.2	2156.2	2156.2	2156.2	2156.2	2156.2	2156.2	2156.2
2.5°	2103.4	2110.3	2119.0	2134.7	2157.3	2171.7	2161.5	2151.3	2161.5	2171.7	2157.3
5°	1967.0	1988.7	2017.0	2059.4	2115.9	2158.5	2159.4	2160.3	2159.4	2158.5	2115.9
7.5°	1836.2	1860.0	1891.2	1940.2	2007.2	2064.4	2092.7	2121.0	2092.7	2064.4	2007.2
10°	1764.4	1785.6	1813.8	1864.0	1936.0	2000.8	2043.6	2086.5	2043.6	2000.8	1936.0
12.5°	1717.9	1732.5	1753.5	1800.0	1872.0	1943.0	2010.6	2078.3	2010.6	1943.0	1872.0
15°	1676.6	1678.2	1683.7	1717.4	1779.4	1851.5	1953.6	2055.7	1953.6	1851.5	1779.4
17.5°	1655.3	1643.6	1631.9	1650.0	1697.8	1761.1	1871.1	1981.0	1871.1	1761.1	1697.8
20°	1642.0	1622.8	1600.9	1611.0	1652.9	1711.5	1820.0	1928.5	1820.0	1711.5	1652.9
22.5°	1619.4	1599.8	1575.8	1580.0	1612.4	1664.3	1774.2	1884.2	1774.2	1664.3	1612.4
25°	1572.9	1557.9	1536.9	1531.0	1540.1	1577.9	1701.9	1825.9	1701.9	1577.9	1540.1
27.5°	1518.2	1508.2	1495.4	1483.7	1472.9	1497.2	1626.7	1756.2	1626.7	1497.2	1472.9
30°	1486.3	1473.7	1461.0	1445.9	1428.6	1448.0	1577.5	1706.9	1577.5	1448.0	1428.6
32.5°	1491.7	1462.2	1432.0	1403.8	1377.7	1391.6	1525.5	1659.3	1525.5	1391.6	1377.7
35°	1495.4	1435.4	1385.3	1344.3	1312.3	1323.3	1462.8	1602.3	1462.8	1323.3	1312.3
37.5°	1407.5	1368.0	1324.8	1281.6	1238.4	1243.3	1392.9	1542.4	1392.9	1243.3	1238.4
40°	1372.5	1347.2	1291.6	1237.8	1185.8	1186.1	1342.9	1499.7	1342.9	1186.1	1185.8
42.5°	1339.9	1313.3	1240.9	1181.6	1135.5	1140.1	1296.9	1453.8	1296.9	1140.1	1135.5
45°	1145.5	1151.0	1131.8	1099.0	1052.5	1058.4	1221.6	1384.8	1221.6	1058.4	1052.5
47.5°	962.2	1002.1	1045.0	1041.4	991.2	992.5	1148.0	1303.6	1148.0	992.5	991.2
50°	881.3	937.6	1006.0	1011.4	954.0	947.6	1094.4	1241.2	1094.4	947.6	954.0
52.5°	814.0	885.6	976.6	987.6	918.4	901.5	1041.0	1180.5	1041.0	901.5	918.4
55°	725.6	820.0	944.9	959.5	863.7	825.4	959.5	1093.5	959.5	825.4	863.7
57.5°	648.3	728.3	836.6	852.0	774.3	747.7	874.4	1001.2	874.4	747.7	774.3
60°	599.8	657.2	732.0	746.6	701.0	697.5	820.6	943.7	820.6	697.5	701.0
62.5°	540.7	580.1	630.8	647.9	631.5	648.5	765.8	883.0	765.8	648.5	631.5
65°	432.9	464.3	506.3	530.9	538.2	570.3	677.0	783.7	677.0	570.3	538.2
67.5°	349.9	379.3	411.2	435.6	452.6	488.6	581.6	674.6	581.6	488.6	452.6
70°	279.5	309.8	345.4	374.5	397.3	434.9	517.0	599.1	517.0	434.9	397.3
72.5°	228.0	254.0	283.0	311.4	339.3	377.9	448.3	518.6	448.3	377.9	339.3
75°	147.3	167.5	194.0	222.7	253.7	291.1	347.6	404.2	347.6	291.1	253.7
77.5°	109.6	119.5	132.9	152.8	179.4	209.7	250.9	292.1	250.9	209.7	179.4
80°	88.4	88.9	89.8	103.9	131.3	159.6	190.6	221.6	190.6	159.6	131.3
82.5°	70.2	69.2	67.9	75.5	91.9	110.0	132.9	155.9	132.9	110.0	91.9
85°	32.6	35.6	39.2	41.9	43.8	47.9	58.8	69.8	58.8	47.9	43.8
87.5°	17.1	16.7	16.7	17.4	18.3	18.4	17.0	16.0	17.0	18.0	19.1
90°	44.7	42.6	42.6	40.4	34.0	25.5	14.9	6.4	14.9	23.4	38.3
92.5°	53.2	52.8	49.4	45.5	37.4	37.4	37.0	23.4	40.4	57.4	82.6
95°	48.9	48.9	57.4	72.3	106.4	108.5	72.3	66.0	93.6	131.9	166.0
97.5°	132.3	157.4	193.2	200.0	189.4	141.3	135.3	126.0	171.5	209.4	264.3
100°	244.7	276.6	302.1	251.1	197.9	195.7	183.0	178.7	227.7	263.8	317.0
102.5°	382.6	392.3	303.8	274.9	262.6	253.6	234.0	231.5	280.4	330.2	374.9
105°	414.9	372.3	374.5	374.5	366.0	348.9	312.8	310.6	366.0	423.4	478.7
107.5°	488.1	494.5	505.5	503.0	493.2	447.7	405.1	395.3	445.1	514.0	574.9
110°	585.1	591.5	595.8	591.5	576.6	519.2	468.1	453.2	497.9	570.2	636.2



TEST NUMBER: P1427980

CATALOG NUMBER: SQ2W-PH1-K-150U-100D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	678.7	683.4	692.8	680.0	654.9	588.9	531.1	509.4	554.0	628.1	695.8
115°	827.7	827.7	829.8	823.4	772.3	704.3	627.7	595.8	634.0	702.1	776.6
117.5°	974.1	976.6	968.1	951.1	891.9	812.8	726.8	675.8	706.0	777.9	854.5
120°	1066.0	1070.2	1061.7	1036.2	978.7	889.4	791.5	731.9	755.3	825.5	902.1
122.5°	1161.3	1160.4	1150.2	1121.3	1053.6	960.9	864.7	791.5	801.3	866.4	941.3
125°	1293.6	1291.5	1283.0	1248.9	1178.7	1083.0	970.2	880.9	868.1	923.4	1000.0
127.5°	1419.6	1414.9	1401.7	1360.4	1288.5	1196.2	1072.4	971.1	942.6	977.5	1047.7
130°	1506.4	1500.0	1476.6	1431.9	1361.7	1274.5	1148.9	1034.1	993.6	1014.9	1076.6
132.5°	1589.8	1571.5	1551.5	1503.4	1438.3	1347.7	1220.4	1100.4	1044.7	1054.1	1102.1
135°	1695.8	1678.7	1653.2	1606.4	1544.7	1455.3	1327.7	1197.9	1121.3	1112.8	1140.4
137.5°	1789.0	1771.1	1742.1	1701.7	1639.6	1560.0	1437.5	1300.4	1203.8	1175.3	1186.0
140°	1846.8	1825.5	1800.0	1759.6	1704.3	1621.3	1502.1	1370.2	1261.7	1221.3	1214.9
142.5°	1894.5	1878.3	1851.1	1814.1	1765.5	1682.6	1566.8	1436.6	1321.3	1268.9	1254.1
145°	1966.0	1953.2	1923.4	1889.4	1849.0	1766.0	1659.6	1529.8	1414.9	1346.8	1314.9
147.5°	2026.4	2016.2	1992.8	1952.8	1918.7	1839.2	1742.1	1627.2	1509.4	1425.1	1383.8
150°	2063.8	2055.3	2031.9	1993.6	1959.6	1885.1	1791.5	1685.1	1572.4	1483.0	1429.8
152.5°	2099.6	2091.1	2064.3	2026.0	1997.0	1927.7	1842.6	1741.3	1626.8	1537.5	1482.6
155°	2146.8	2136.2	2110.7	2074.5	2049.0	1985.1	1906.4	1817.0	1719.2	1625.5	1563.8
157.5°	2184.3	2171.1	2147.3	2116.2	2089.0	2030.2	1961.7	1884.7	1799.2	1709.8	1646.8
160°	2206.4	2191.5	2166.0	2138.3	2112.8	2057.5	1995.8	1925.6	1846.8	1766.0	1697.9
162.5°	2221.7	2208.5	2177.9	2153.6	2131.5	2081.3	2023.0	1959.6	1889.4	1818.7	1755.8
165°	2238.3	2223.4	2191.5	2172.4	2153.2	2110.7	2059.6	2008.5	1949.0	1891.5	1840.4
167.5°	2239.6	2227.3	2195.3	2176.6	2162.6	2126.0	2084.7	2045.6	1999.2	1954.1	1911.5
170°	2236.2	2225.6	2193.6	2176.6	2166.0	2136.2	2100.0	2066.0	2029.8	1991.5	1957.5
172.5°	2224.3	2213.6	2183.4	2169.8	2164.3	2137.9	2108.5	2083.0	2051.9	2023.8	1996.6
175°	2193.6	2185.1	2159.6	2151.1	2153.2	2136.2	2114.9	2100.0	2080.9	2063.8	2049.0
177.5°	2149.0	2143.9	2125.1	2125.1	2131.9	2121.7	2114.9	2108.1	2099.6	2094.5	2089.4
180°	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4



TEST NUMBER: P1427980

CATALOG NUMBER: SQ2W-PH1-K-150U-100D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2156.2	2156.2	2156.2	2156.2	2156.2	2156.2	2156.2	2156.2	2156.2	2156.2	2156.2
2.5°	2134.7	2119.0	2110.3	2103.4	2101.9	2100.4	2101.9	2103.4	2110.3	2119.0	2134.7
5°	2059.4	2017.0	1988.7	1967.0	1965.2	1963.4	1965.2	1967.0	1988.7	2017.0	2059.4
7.5°	1940.2	1891.2	1860.0	1836.2	1834.8	1833.3	1834.8	1836.2	1860.0	1891.2	1940.2
10°	1864.0	1813.8	1785.6	1764.4	1764.4	1764.4	1764.4	1764.4	1785.6	1813.8	1864.0
12.5°	1800.0	1753.5	1732.5	1717.9	1722.3	1726.6	1722.3	1717.9	1732.5	1753.5	1800.0
15°	1717.4	1683.7	1678.2	1676.6	1686.6	1696.7	1686.6	1676.6	1678.2	1683.7	1717.4
17.5°	1650.0	1631.9	1643.6	1655.3	1667.0	1678.6	1667.0	1655.3	1643.6	1631.9	1650.0
20°	1611.0	1600.9	1622.8	1642.0	1652.9	1663.9	1652.9	1642.0	1622.8	1600.9	1611.0
22.5°	1580.0	1575.8	1599.8	1619.4	1625.2	1631.0	1625.2	1619.4	1599.8	1575.8	1580.0
25°	1531.0	1536.9	1557.9	1572.9	1570.2	1567.4	1570.2	1572.9	1557.9	1536.9	1531.0
27.5°	1483.7	1495.4	1508.2	1518.2	1519.8	1521.5	1519.8	1518.2	1508.2	1495.4	1483.7
30°	1445.9	1461.0	1473.7	1486.3	1498.1	1510.0	1498.1	1486.3	1473.7	1461.0	1445.9
32.5°	1403.8	1432.0	1462.2	1491.7	1518.9	1546.1	1518.9	1491.7	1462.2	1432.0	1403.8
35°	1344.3	1385.3	1435.4	1495.4	1584.8	1674.1	1584.8	1495.4	1435.4	1385.3	1344.3
37.5°	1281.6	1324.8	1368.0	1407.5	1436.0	1464.4	1436.0	1407.5	1368.0	1324.8	1281.6
40°	1237.8	1291.6	1347.2	1372.5	1306.9	1241.2	1306.9	1372.5	1347.2	1291.6	1237.8
42.5°	1181.6	1240.9	1313.3	1339.9	1229.0	1118.1	1229.0	1339.9	1313.3	1240.9	1181.6
45°	1099.0	1131.8	1151.0	1145.5	1066.2	986.8	1066.2	1145.5	1151.0	1131.8	1099.0
47.5°	1041.4	1045.0	1002.1	962.2	931.2	900.2	931.2	962.2	1002.1	1045.0	1041.4
50°	1011.4	1006.0	937.6	881.3	861.2	841.2	861.2	881.3	937.6	1006.0	1011.4
52.5°	987.6	976.6	885.6	814.0	800.5	787.0	800.5	814.0	885.6	976.6	987.6
55°	959.5	944.9	820.0	725.6	722.8	720.1	722.8	725.6	820.0	944.9	959.5
57.5°	852.0	836.6	728.3	648.3	653.0	657.7	653.0	648.3	728.3	836.6	852.0
60°	746.6	732.0	657.2	599.8	594.3	588.8	594.3	599.8	657.2	732.0	746.6
62.5°	647.9	630.8	580.1	540.7	535.2	529.7	535.2	540.7	580.1	630.8	647.9
65°	530.9	506.3	464.3	432.9	432.9	432.9	432.9	432.9	464.3	506.3	530.9
67.5°	435.6	411.2	379.3	349.9	328.0	306.1	328.0	349.9	379.3	411.2	435.6
70°	374.5	345.4	309.8	279.5	264.9	250.3	264.9	279.5	309.8	345.4	374.5
72.5°	311.4	283.0	254.0	228.0	211.3	194.5	211.3	228.0	254.0	283.0	311.4
75°	222.7	194.0	167.5	147.3	145.4	143.6	145.4	147.3	167.5	194.0	222.7
77.5°	152.8	132.9	119.5	109.6	109.8	110.0	109.8	109.6	119.5	132.9	152.8
80°	103.9	89.8	88.9	88.4	89.4	90.3	89.4	88.4	88.9	89.8	103.9
82.5°	75.5	67.9	69.2	70.2	70.4	70.6	70.4	70.2	69.2	67.9	75.5
85°	41.9	39.2	35.6	32.6	31.7	30.8	31.7	32.6	35.6	39.2	41.9
87.5°	19.1	21.0	24.0	25.7	27.4	26.5	27.4	25.7	24.0	21.0	19.1
90°	48.9	63.8	78.7	87.2	95.7	91.5	95.7	87.2	78.7	63.8	48.9
92.5°	98.3	123.4	141.7	157.0	163.8	163.0	163.8	157.0	141.7	123.4	98.3
95°	197.9	227.7	257.4	278.7	291.5	287.2	291.5	278.7	257.4	227.7	197.9
97.5°	305.1	345.1	378.3	398.3	411.1	419.6	411.1	398.3	378.3	345.1	305.1
100°	376.6	414.9	453.2	476.6	497.9	506.4	497.9	476.6	453.2	414.9	376.6
102.5°	434.5	484.7	526.4	551.5	569.4	577.9	569.4	551.5	526.4	484.7	434.5
105°	529.8	583.0	627.7	659.6	678.7	685.1	678.7	659.6	627.7	583.0	529.8
107.5°	625.1	680.0	721.3	756.6	780.0	793.6	780.0	756.6	721.3	680.0	625.1
110°	700.0	744.7	789.4	821.3	844.7	853.2	844.7	821.3	789.4	744.7	700.0



TEST NUMBER: P1427980

CATALOG NUMBER: SQ2W-PH1-K-150U-100D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	763.0	812.8	857.5	889.4	916.2	928.1	916.2	889.4	857.5	812.8	763.0
115°	851.1	917.0	957.5	987.2	1006.4	1017.0	1006.4	987.2	957.5	917.0	851.1
117.5°	924.3	993.2	1037.5	1060.4	1069.4	1077.0	1069.4	1060.4	1037.5	993.2	924.3
120°	970.2	1034.1	1085.1	1114.9	1125.5	1129.8	1125.5	1114.9	1085.1	1034.1	970.2
122.5°	1012.8	1073.2	1122.6	1159.2	1176.6	1180.9	1176.6	1159.2	1122.6	1073.2	1012.8
125°	1072.4	1129.8	1180.9	1217.0	1236.2	1246.8	1236.2	1217.0	1180.9	1129.8	1072.4
127.5°	1124.3	1186.4	1233.2	1266.0	1284.7	1293.2	1284.7	1266.0	1233.2	1186.4	1124.3
130°	1153.2	1217.0	1263.8	1300.0	1317.0	1325.5	1317.0	1300.0	1263.8	1217.0	1153.2
132.5°	1175.3	1242.6	1291.1	1323.8	1342.6	1351.1	1342.6	1323.8	1291.1	1242.6	1175.3
135°	1202.1	1272.4	1323.4	1355.3	1372.4	1380.9	1372.4	1355.3	1323.4	1272.4	1202.1
137.5°	1225.5	1289.4	1342.6	1376.2	1391.5	1397.0	1391.5	1376.2	1342.6	1289.4	1225.5
140°	1242.6	1297.9	1351.1	1383.0	1400.0	1402.1	1400.0	1383.0	1351.1	1297.9	1242.6
142.5°	1264.7	1308.1	1354.5	1386.4	1403.4	1407.2	1403.4	1386.4	1354.5	1308.1	1264.7
145°	1304.3	1329.8	1361.7	1391.5	1406.4	1410.7	1406.4	1391.5	1361.7	1329.8	1304.3
147.5°	1354.1	1362.1	1378.7	1398.3	1412.8	1415.8	1412.8	1398.3	1378.7	1362.1	1354.1
150°	1391.5	1389.4	1395.8	1408.5	1421.3	1419.2	1421.3	1408.5	1395.8	1389.4	1391.5
152.5°	1434.1	1421.7	1421.3	1427.2	1433.2	1432.8	1433.2	1427.2	1421.3	1421.7	1434.1
155°	1506.4	1483.0	1470.2	1466.0	1466.0	1463.8	1466.0	1466.0	1470.2	1483.0	1506.4
157.5°	1586.0	1553.2	1534.1	1523.8	1520.9	1516.2	1520.9	1523.8	1534.1	1553.2	1586.0
160°	1640.4	1604.3	1585.1	1568.1	1561.7	1555.3	1561.7	1568.1	1585.1	1604.3	1640.4
162.5°	1691.5	1657.0	1636.2	1620.9	1614.5	1604.7	1614.5	1620.9	1636.2	1657.0	1691.5
165°	1774.5	1738.3	1714.9	1702.1	1693.6	1685.1	1693.6	1702.1	1714.9	1738.3	1774.5
167.5°	1857.5	1817.9	1802.6	1788.1	1780.0	1764.7	1780.0	1788.1	1802.6	1817.9	1857.5
170°	1908.5	1872.4	1863.8	1851.1	1836.2	1819.2	1836.2	1851.1	1863.8	1872.4	1908.5
172.5°	1952.8	1928.5	1920.0	1907.3	1902.6	1889.0	1902.6	1907.3	1920.0	1928.5	1952.8
175°	2017.0	1997.9	1997.9	1995.8	1989.4	1976.6	1989.4	1995.8	1997.9	1997.9	2017.0
177.5°	2070.7	2060.4	2067.3	2067.3	2065.6	2053.6	2065.6	2067.3	2067.3	2060.4	2070.7
180°	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4



TEST NUMBER: P1427980

CATALOG NUMBER: SQ2W-PH1-K-150U-100D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	2156.2	2156.2	2156.2	2156.2
2.5°	2157.3	2171.7	2161.5	2151.3
5°	2115.9	2158.5	2159.4	2160.3
7.5°	2007.2	2064.4	2092.7	2121.0
10°	1936.0	2000.8	2043.6	2086.5
12.5°	1872.0	1943.0	2010.6	2078.3
15°	1779.4	1851.5	1953.6	2055.7
17.5°	1697.8	1761.1	1871.1	1981.0
20°	1652.9	1711.5	1820.0	1928.5
22.5°	1612.4	1664.3	1774.2	1884.2
25°	1540.1	1577.9	1701.9	1825.9
27.5°	1472.9	1497.2	1626.7	1756.2
30°	1428.6	1448.0	1577.5	1706.9
32.5°	1377.7	1391.6	1525.5	1659.3
35°	1312.3	1323.3	1462.8	1602.3
37.5°	1238.4	1243.3	1392.9	1542.4
40°	1185.8	1186.1	1342.9	1499.7
42.5°	1135.5	1140.1	1296.9	1453.8
45°	1052.5	1058.4	1221.6	1384.8
47.5°	991.2	992.5	1148.0	1303.6
50°	954.0	947.6	1094.4	1241.2
52.5°	918.4	901.5	1041.0	1180.5
55°	863.7	825.4	959.5	1093.5
57.5°	774.3	747.7	874.4	1001.2
60°	701.0	697.5	820.6	943.7
62.5°	631.5	648.5	765.8	883.0
65°	538.2	570.3	677.0	783.7
67.5°	452.6	488.6	581.6	674.6
70°	397.3	434.9	517.0	599.1
72.5°	339.3	377.9	448.3	518.6
75°	253.7	291.1	347.6	404.2
77.5°	179.4	209.7	250.9	292.1
80°	131.3	159.6	190.6	221.6
82.5°	91.9	110.0	132.9	155.9
85°	43.8	47.9	58.8	69.8
87.5°	19.1	18.0	17.0	16.0
90°	38.3	23.4	14.9	6.4
92.5°	82.6	57.4	40.4	23.4
95°	166.0	131.9	93.6	66.0
97.5°	264.3	209.4	171.5	126.0
100°	317.0	263.8	227.7	178.7
102.5°	374.9	330.2	280.4	231.5
105°	478.7	423.4	366.0	310.6
107.5°	574.9	514.0	445.1	395.3
110°	636.2	570.2	497.9	453.2



TEST NUMBER: P1427980

CATALOG NUMBER: SQ2W-PH1-K-150U-100D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	695.8	628.1	554.0	509.4
115°	776.6	702.1	634.0	595.8
117.5°	854.5	777.9	706.0	675.8
120°	902.1	825.5	755.3	731.9
122.5°	941.3	866.4	801.3	791.5
125°	1000.0	923.4	868.1	880.9
127.5°	1047.7	977.5	942.6	971.1
130°	1076.6	1014.9	993.6	1034.1
132.5°	1102.1	1054.1	1044.7	1100.4
135°	1140.4	1112.8	1121.3	1197.9
137.5°	1186.0	1175.3	1203.8	1300.4
140°	1214.9	1221.3	1261.7	1370.2
142.5°	1254.1	1268.9	1321.3	1436.6
145°	1314.9	1346.8	1414.9	1529.8
147.5°	1383.8	1425.1	1509.4	1627.2
150°	1429.8	1483.0	1572.4	1685.1
152.5°	1482.6	1537.5	1626.8	1741.3
155°	1563.8	1625.5	1719.2	1817.0
157.5°	1646.8	1709.8	1799.2	1884.7
160°	1697.9	1766.0	1846.8	1925.6
162.5°	1755.8	1818.7	1889.4	1959.6
165°	1840.4	1891.5	1949.0	2008.5
167.5°	1911.5	1954.1	1999.2	2045.6
170°	1957.5	1991.5	2029.8	2066.0
172.5°	1996.6	2023.8	2051.9	2083.0
175°	2049.0	2063.8	2080.9	2100.0
177.5°	2089.4	2094.5	2099.6	2108.1
180°	2106.4	2106.4	2106.4	2106.4



TEST NUMBER: P1427980
 CATALOG NUMBER: SQ2W-PH1-K-150U-100D-L940-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.60	19.40	19.61	20.42	21.78	17.42	18.23	18.44	19.25	20.60
	3H	20.77	21.48	21.79	22.51	23.89	18.47	19.19	19.49	20.22	21.60
	4H	21.58	22.26	22.61	23.29	24.67	18.71	19.39	19.75	20.42	21.81
	6H	22.04	22.67	23.08	23.70	25.10	18.85	19.48	19.89	20.51	21.91
	8H	22.19	22.79	23.24	23.84	25.23	18.91	19.50	19.96	20.55	21.95
	12H	22.25	22.81	23.30	23.86	25.28	18.92	19.48	19.97	20.53	21.95
4H	2H	19.02	19.70	20.06	20.73	22.12	18.10	18.78	19.14	19.81	21.20
	3H	21.27	21.84	22.32	22.89	24.29	19.33	19.89	20.37	20.95	22.35
	4H	22.14	22.66	23.20	23.71	25.13	19.61	20.13	20.67	21.18	22.61
	6H	22.70	23.14	23.76	24.21	25.63	19.81	20.25	20.87	21.33	22.75
	8H	22.90	23.31	23.96	24.38	25.81	19.90	20.31	20.96	21.38	22.81
	12H	22.98	23.35	24.06	24.43	25.87	19.92	20.29	21.00	21.37	22.81
8H	4H	22.16	22.57	23.22	23.64	25.07	19.84	20.25	20.90	21.32	22.75
	6H	22.79	23.13	23.87	24.24	25.67	20.10	20.45	21.19	21.55	22.98
	8H	23.05	23.35	24.14	24.44	25.89	20.25	20.55	21.35	21.64	23.09
	12H	23.18	23.44	24.28	24.53	26.02	20.31	20.58	21.41	21.66	23.15
12H	4H	22.11	22.48	23.19	23.56	25.00	19.83	20.21	20.92	21.29	22.73
	6H	22.76	23.06	23.86	24.15	25.60	20.14	20.44	21.23	21.53	22.98
	8H	23.03	23.29	24.13	24.38	25.87	20.30	20.56	21.40	21.65	23.14