

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428481

Luminaire Tested: SQ2W-PW1-K-150U-100D-L840-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428481
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PW1-K-150U-100D-L840-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE WAVES LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12052.2 lumens
Efficiency: N/A
Efficacy: 130.0 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.11 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 92.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428481

CATALOG NUMBER: SQ2W-PW1-K-150U-100D-L840-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428481

CATALOG NUMBER: SQ2W-PW1-K-150U-100D-L840-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50	44
1	97	93	89	86	89	85	82	79	71	69	67	57	56	55	45	44	44	38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	46	40	39	37	33
3	81	72	65	60	74	66	60	55	56	51	48	46	42	40	36	34	32	28
4	74	64	57	51	68	59	53	47	50	45	41	41	37	34	33	30	28	25
5	68	57	50	44	63	53	46	41	45	39	36	37	33	30	30	27	25	22
6	63	52	44	38	58	48	41	36	40	35	31	33	30	27	27	24	22	19
7	58	47	39	34	53	43	36	32	37	31	28	31	27	24	25	22	20	17
8	54	42	35	30	50	39	33	28	33	28	25	28	24	21	23	20	18	15
9	51	39	31	27	46	36	29	25	31	26	22	26	22	19	21	18	16	14
10	47	36	29	24	43	33	27	23	28	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	38320	38320	38320	38320
5°	38063	38722	38063	38722
10°	38132	39059	38132	39059
15°	38122	39294	38122	39294
20°	38138	38527	38138	38527
25°	37933	35799	37933	35799
30°	37674	32365	37674	32365
35°	37380	29226	37380	29226
40°	36635	25821	36635	25821
45°	35200	22555	35200	22555
50°	32759	19303	32759	19303
55°	29967	15654	29967	15654
60°	26860	13504	26860	13504
65°	23488	12004	23488	12004
70°	19208	10886	19208	10886
75°	14947	10012	14947	10012
80°	11139	8824	11139	8824
85°	7540	5020	7540	5020

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 35200 cd/sqm



TEST NUMBER: P1428481

CATALOG NUMBER: SQ2W-PW1-K-150U-100D-L840-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	226.0	1.9
10°-20°	654.8	5.4
20°-30°	963.7	8.0
30°-40°	1053.6	8.7
40°-50°	945.2	7.8
50°-60°	705.1	5.9
60°-70°	445.6	3.7
70°-80°	220.8	1.8
80°-90°	61.3	0.5
90°-100°	184.7	1.5
100°-110°	538.6	4.5
110°-120°	879.0	7.3
120°-130°	1115.4	9.3
130°-140°	1193.5	9.9
140°-150°	1114.5	9.2
150°-160°	917.1	7.6
160°-170°	615.0	5.1
170°-180°	218.4	1.8
0°-30°	1844.5	15.3
0°-40°	2898.1	24.0
0°-60°	4548.4	37.7
0°-90°	5276.0	43.8
90°-120°	1602.3	13.3
90°-150°	5025.7	41.7
90°-180°	6776.0	56.2
0°-180°	12052.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2373	2373	2373	2373	2373	
5°	2348	2389	2348	2389	2348	223
15°	2281	2351	2281	2351	2281	644
25°	2129	2010	2129	2010	2129	981
35°	1896	1483	1896	1483	1896	1183
45°	1542	988	1542	988	1542	1182
55°	1065	556	1065	556	1065	951
65°	615	314	615	314	615	609
75°	240	160	240	160	240	264
85°	41	27	41	27	41	52
90°	7	52	7	101	7	7
95°	73	54	73	316	73	88
105°	342	548	342	755	342	364
115°	656	910	656	1120	656	647
125°	970	1442	970	1374	970	868
135°	1320	1887	1320	1521	1320	1020
145°	1686	2175	1686	1554	1686	1055
155°	2002	2363	2002	1613	2002	920
165°	2213	2464	2213	1857	2213	623
175°	2314	2412	2314	2178	2314	220
180°	2321	2321	2321	2321	2321	



TEST NUMBER: P1428481

CATALOG NUMBER: SQ2W-PW1-K-150U-100D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4
2.5°	2357.1	2370.8	2384.4	2381.2	2372.4	2368.4	2369.2	2370.4	2372.8	2375.2	2372.8
5°	2348.5	2365.6	2382.7	2380.2	2371.1	2367.1	2368.1	2371.1	2380.2	2389.2	2380.2
7.5°	2336.8	2354.1	2371.3	2370.5	2363.7	2362.0	2365.4	2370.2	2379.0	2387.9	2379.0
10°	2325.9	2344.0	2362.1	2362.1	2356.1	2355.6	2360.6	2366.4	2374.4	2382.4	2374.4
12.5°	2311.5	2330.4	2349.2	2350.6	2346.2	2346.9	2352.8	2359.1	2367.2	2375.2	2367.2
15°	2280.7	2300.8	2320.9	2325.2	2324.2	2327.2	2334.2	2340.7	2345.8	2350.8	2345.8
17.5°	2245.0	2265.1	2285.2	2289.2	2287.8	2288.0	2289.8	2291.7	2294.1	2296.5	2294.1
20°	2219.7	2239.8	2259.9	2262.6	2259.6	2254.6	2247.6	2242.3	2242.3	2242.3	2242.3
22.5°	2183.5	2205.2	2226.9	2227.1	2220.0	2207.0	2187.9	2172.0	2165.5	2159.1	2165.5
25°	2129.3	2150.4	2171.5	2161.7	2141.6	2111.9	2072.8	2039.6	2024.5	2009.5	2024.5
27.5°	2066.0	2083.1	2100.1	2074.6	2034.8	1987.1	1931.4	1884.5	1863.6	1842.7	1863.6
30°	2020.8	2033.8	2046.9	2006.5	1948.2	1888.4	1827.1	1776.2	1756.1	1736.0	1756.1
32.5°	1973.8	1978.8	1983.8	1930.5	1857.8	1789.6	1725.9	1672.7	1651.0	1629.3	1651.0
35°	1896.5	1887.4	1878.4	1807.5	1716.1	1638.3	1574.0	1521.0	1501.9	1482.8	1501.9
37.5°	1805.1	1778.2	1751.3	1671.5	1574.0	1491.6	1424.3	1368.6	1347.5	1326.4	1347.5
40°	1738.2	1700.1	1661.9	1576.2	1474.8	1390.4	1323.1	1267.3	1246.2	1225.1	1246.2
42.5°	1664.1	1616.3	1568.5	1480.4	1378.9	1294.5	1227.2	1171.3	1149.4	1127.5	1149.4
45°	1541.6	1485.3	1429.1	1337.4	1233.9	1149.5	1084.2	1030.0	1008.9	987.8	1008.9
47.5°	1403.7	1347.8	1292.0	1200.6	1097.3	1014.0	950.7	898.7	880.6	862.6	880.6
50°	1304.2	1250.0	1195.7	1108.3	1009.9	929.0	865.7	812.7	790.6	768.5	790.6
52.5°	1203.0	1154.4	1105.7	1021.5	925.5	845.0	780.1	723.9	693.8	663.6	693.8
55°	1064.6	1018.4	972.2	892.8	802.4	721.1	648.7	590.2	573.1	556.1	573.1
57.5°	922.2	882.3	842.3	770.9	689.2	615.4	549.7	496.9	482.9	468.8	482.9
60°	831.8	796.7	761.5	693.2	613.8	546.5	491.3	446.3	432.2	418.2	432.2
62.5°	745.0	713.9	682.7	617.2	540.3	479.8	435.8	399.9	388.2	376.6	388.2
65°	614.8	591.7	568.6	514.6	450.3	400.1	363.9	334.3	324.2	314.2	324.2
67.5°	488.2	475.4	462.5	422.1	372.5	331.8	300.0	274.6	267.9	261.3	267.9
70°	406.9	402.8	398.8	365.4	322.2	287.6	261.5	240.6	235.6	230.6	235.6
72.5°	336.3	338.0	339.6	311.8	274.2	245.2	224.7	208.5	205.0	201.6	205.0
75°	239.6	247.6	255.7	237.3	210.2	189.6	175.6	164.5	162.5	160.5	162.5
77.5°	163.2	175.3	187.3	175.4	155.5	140.3	129.9	121.7	120.1	118.4	120.1
80°	119.8	131.9	143.9	135.6	120.6	109.0	101.0	94.9	94.9	94.9	94.9
82.5°	83.6	93.3	102.9	97.0	86.0	78.5	74.4	71.4	71.4	71.4	71.4
85°	40.7	45.7	50.7	49.0	45.0	39.9	33.9	29.1	28.1	27.1	28.1
87.5°	12.3	16.5	21.3	20.8	18.2	16.2	15.4	15.3	15.7	15.7	15.7
90°	7.0	16.4	28.1	37.5	44.5	46.9	46.9	49.2	51.6	51.6	51.6
92.5°	25.8	40.8	41.3	41.3	50.2	54.4	58.1	58.6	60.9	60.9	60.9
95°	72.7	79.7	119.6	117.2	79.7	63.3	53.9	53.9	53.9	53.9	53.9
97.5°	138.8	149.1	155.7	208.6	220.4	212.9	173.5	145.8	130.3	123.3	130.3
100°	196.9	201.6	215.7	218.0	276.6	332.9	304.7	269.6	257.9	250.8	257.9
102.5°	255.0	257.9	279.4	289.3	302.9	334.7	432.3	421.5	413.5	412.1	413.5
105°	342.3	344.6	384.4	403.2	412.6	412.6	410.2	457.1	532.1	548.5	532.1
107.5°	435.5	446.3	493.2	543.4	554.2	557.0	544.8	537.8	534.9	536.8	534.9
110°	499.3	515.7	572.0	635.3	651.7	656.4	651.7	644.7	640.0	640.0	640.0



TEST NUMBER: P1428481

CATALOG NUMBER: SQ2W-PW1-K-150U-100D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	561.2	585.1	648.9	721.5	749.2	763.3	753.0	747.8	743.1	746.9	743.1
115°	656.4	691.5	775.9	850.9	907.2	914.2	911.9	911.9	909.5	909.5	909.5
117.5°	744.5	800.8	895.5	982.7	1047.9	1066.6	1076.0	1073.2	1070.4	1075.0	1070.4
120°	806.4	872.0	979.9	1078.3	1141.6	1169.7	1179.1	1174.4	1179.1	1174.4	1179.1
122.5°	872.0	952.7	1058.6	1160.8	1235.4	1267.3	1278.5	1279.5	1280.4	1277.6	1280.4
125°	970.5	1068.9	1193.2	1298.7	1376.0	1413.5	1422.9	1425.3	1430.0	1441.7	1430.0
127.5°	1069.9	1181.5	1317.9	1419.6	1498.9	1544.3	1558.9	1564.0	1573.9	1579.0	1573.9
130°	1139.3	1265.9	1404.2	1500.3	1577.6	1626.9	1652.7	1659.7	1671.4	1669.1	1671.4
132.5°	1212.4	1344.6	1484.8	1584.7	1656.4	1709.4	1731.4	1751.6	1755.8	1759.1	1755.8
135°	1319.8	1462.8	1603.4	1701.9	1769.9	1821.4	1849.6	1868.3	1880.0	1887.1	1880.0
137.5°	1432.8	1583.7	1718.8	1806.4	1874.9	1919.4	1951.3	1971.0	1983.2	1988.8	1983.2
140°	1509.7	1655.0	1786.3	1877.7	1938.6	1983.2	2011.3	2034.8	2048.8	2048.8	2048.8
142.5°	1582.8	1726.3	1853.8	1945.2	1998.7	2039.4	2069.4	2087.3	2103.2	2103.2	2103.2
145°	1685.5	1828.5	1945.7	2037.1	2081.6	2119.1	2152.0	2166.0	2175.4	2175.4	2175.4
147.5°	1792.8	1919.4	2026.3	2114.0	2151.5	2195.6	2221.3	2232.6	2244.3	2239.2	2244.3
150°	1856.6	1973.8	2076.9	2159.0	2196.5	2238.7	2264.5	2273.9	2285.6	2278.5	2285.6
152.5°	1918.5	2030.1	2123.8	2200.3	2232.1	2274.3	2303.9	2313.2	2321.2	2316.1	2321.2
155°	2001.9	2100.4	2187.1	2257.5	2285.6	2325.4	2353.6	2365.3	2374.7	2362.9	2374.7
157.5°	2076.5	2161.3	2236.8	2301.5	2331.5	2365.8	2392.0	2406.5	2415.9	2410.8	2415.9
160°	2121.5	2198.8	2266.8	2327.8	2355.9	2386.4	2414.5	2430.9	2440.3	2433.3	2440.3
162.5°	2159.0	2228.9	2293.1	2348.4	2372.8	2399.5	2433.3	2447.8	2457.2	2448.3	2457.2
165°	2212.9	2269.2	2325.4	2372.3	2393.4	2414.5	2449.7	2466.1	2473.1	2463.7	2473.1
167.5°	2253.7	2296.8	2342.3	2382.6	2398.1	2418.7	2453.9	2467.5	2476.4	2464.7	2476.4
170°	2276.2	2313.7	2353.6	2386.4	2398.1	2416.9	2452.0	2463.7	2470.8	2459.1	2470.8
172.5°	2295.0	2323.1	2355.4	2384.5	2390.6	2405.6	2438.9	2450.6	2455.8	2445.9	2455.8
175°	2313.7	2330.1	2353.6	2372.3	2370.0	2379.3	2407.5	2416.9	2426.2	2412.2	2426.2
177.5°	2322.6	2330.1	2337.6	2348.9	2341.4	2341.4	2362.0	2367.6	2369.5	2362.0	2369.5
180°	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7



TEST NUMBER: P1428481

CATALOG NUMBER: SQ2W-PW1-K-150U-100D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4
2.5°	2370.4	2369.2	2368.4	2372.4	2381.2	2384.4	2370.8	2357.1	2370.8	2384.4	2381.2
5°	2371.1	2368.1	2367.1	2371.1	2380.2	2382.7	2365.6	2348.5	2365.6	2382.7	2380.2
7.5°	2370.2	2365.4	2362.0	2363.7	2370.5	2371.3	2354.1	2336.8	2354.1	2371.3	2370.5
10°	2366.4	2360.6	2355.6	2356.1	2362.1	2362.1	2344.0	2325.9	2344.0	2362.1	2362.1
12.5°	2359.1	2352.8	2346.9	2346.2	2350.6	2349.2	2330.4	2311.5	2330.4	2349.2	2350.6
15°	2340.7	2334.2	2327.2	2324.2	2325.2	2320.9	2300.8	2280.7	2300.8	2320.9	2325.2
17.5°	2291.7	2289.8	2288.0	2287.8	2289.2	2285.2	2265.1	2245.0	2265.1	2285.2	2289.2
20°	2242.3	2247.6	2254.6	2259.6	2262.6	2259.9	2239.8	2219.7	2239.8	2259.9	2262.6
22.5°	2172.0	2187.9	2207.0	2220.0	2227.1	2226.9	2205.2	2183.5	2205.2	2226.9	2227.1
25°	2039.6	2072.8	2111.9	2141.6	2161.7	2171.5	2150.4	2129.3	2150.4	2171.5	2161.7
27.5°	1884.5	1931.4	1987.1	2034.8	2074.6	2100.1	2083.1	2066.0	2083.1	2100.1	2074.6
30°	1776.2	1827.1	1888.4	1948.2	2006.5	2046.9	2033.8	2020.8	2033.8	2046.9	2006.5
32.5°	1672.7	1725.9	1789.6	1857.8	1930.5	1983.8	1978.8	1973.8	1978.8	1983.8	1930.5
35°	1521.0	1574.0	1638.3	1716.1	1807.5	1878.4	1887.4	1896.5	1887.4	1878.4	1807.5
37.5°	1368.6	1424.3	1491.6	1574.0	1671.5	1751.3	1778.2	1805.1	1778.2	1751.3	1671.5
40°	1267.3	1323.1	1390.4	1474.8	1576.2	1661.9	1700.1	1738.2	1700.1	1661.9	1576.2
42.5°	1171.3	1227.2	1294.5	1378.9	1480.4	1568.5	1616.3	1664.1	1616.3	1568.5	1480.4
45°	1030.0	1084.2	1149.5	1233.9	1337.4	1429.1	1485.3	1541.6	1485.3	1429.1	1337.4
47.5°	898.7	950.7	1014.0	1097.3	1200.6	1292.0	1347.8	1403.7	1347.8	1292.0	1200.6
50°	812.7	865.7	929.0	1009.9	1108.3	1195.7	1250.0	1304.2	1250.0	1195.7	1108.3
52.5°	723.9	780.1	845.0	925.5	1021.5	1105.7	1154.4	1203.0	1154.4	1105.7	1021.5
55°	590.2	648.7	721.1	802.4	892.8	972.2	1018.4	1064.6	1018.4	972.2	892.8
57.5°	496.9	549.7	615.4	689.2	770.9	842.3	882.3	922.2	882.3	842.3	770.9
60°	446.3	491.3	546.5	613.8	693.2	761.5	796.7	831.8	796.7	761.5	693.2
62.5°	399.9	435.8	479.8	540.3	617.2	682.7	713.9	745.0	713.9	682.7	617.2
65°	334.3	363.9	400.1	450.3	514.6	568.6	591.7	614.8	591.7	568.6	514.6
67.5°	274.6	300.0	331.8	372.5	422.1	462.5	475.4	488.2	475.4	462.5	422.1
70°	240.6	261.5	287.6	322.2	365.4	398.8	402.8	406.9	402.8	398.8	365.4
72.5°	208.5	224.7	245.2	274.2	311.8	339.6	338.0	336.3	338.0	339.6	311.8
75°	164.5	175.6	189.6	210.2	237.3	255.7	247.6	239.6	247.6	255.7	237.3
77.5°	121.7	129.9	140.3	155.5	175.4	187.3	175.3	163.2	175.3	187.3	175.4
80°	94.9	101.0	109.0	120.6	135.6	143.9	131.9	119.8	131.9	143.9	135.6
82.5°	71.4	74.4	78.5	86.0	97.0	102.9	93.3	83.6	93.3	102.9	97.0
85°	29.1	33.9	39.9	45.0	49.0	50.7	45.7	40.7	45.7	50.7	49.0
87.5°	15.3	15.4	16.2	18.2	20.8	21.3	16.5	12.3	16.5	20.8	21.7
90°	49.2	46.9	46.9	44.5	37.5	28.1	16.4	7.0	16.4	25.8	42.2
92.5°	58.6	58.1	54.4	50.2	41.3	41.3	40.8	25.8	44.5	63.3	91.0
95°	53.9	53.9	63.3	79.7	117.2	119.6	79.7	72.7	103.1	145.3	182.8
97.5°	145.8	173.5	212.9	220.4	208.6	155.7	149.1	138.8	188.9	230.7	291.1
100°	269.6	304.7	332.9	276.6	218.0	215.7	201.6	196.9	250.8	290.7	349.3
102.5°	421.5	432.3	334.7	302.9	289.3	279.4	257.9	255.0	309.0	363.8	413.0
105°	457.1	410.2	412.6	412.6	403.2	384.4	344.6	342.3	403.2	466.5	527.4
107.5°	537.8	544.8	557.0	554.2	543.4	493.2	446.3	435.5	490.4	566.4	633.4
110°	644.7	651.7	656.4	651.7	635.3	572.0	515.7	499.3	548.5	628.2	700.9



TEST NUMBER: P1428481

CATALOG NUMBER: SQ2W-PW1-K-150U-100D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	747.8	753.0	763.3	749.2	721.5	648.9	585.1	561.2	610.4	692.0	766.5
115°	911.9	911.9	914.2	907.2	850.9	775.9	691.5	656.4	698.6	773.6	855.6
117.5°	1073.2	1076.0	1066.6	1047.9	982.7	895.5	800.8	744.5	777.8	857.0	941.4
120°	1174.4	1179.1	1169.7	1141.6	1078.3	979.9	872.0	806.4	832.2	909.5	993.9
122.5°	1279.5	1278.5	1267.3	1235.4	1160.8	1058.6	952.7	872.0	882.8	954.6	1037.1
125°	1425.3	1422.9	1413.5	1376.0	1298.7	1193.2	1068.9	970.5	956.4	1017.4	1101.8
127.5°	1564.0	1558.9	1544.3	1498.9	1419.6	1317.9	1181.5	1069.9	1038.5	1076.9	1154.3
130°	1659.7	1652.7	1626.9	1577.6	1500.3	1404.2	1265.9	1139.3	1094.7	1118.2	1186.2
132.5°	1751.6	1731.4	1709.4	1656.4	1584.7	1484.8	1344.6	1212.4	1151.0	1161.3	1214.3
135°	1868.3	1849.6	1821.4	1769.9	1701.9	1603.4	1462.8	1319.8	1235.4	1226.0	1256.5
137.5°	1971.0	1951.3	1919.4	1874.9	1806.4	1718.8	1583.7	1432.8	1326.3	1294.9	1306.6
140°	2034.8	2011.3	1983.2	1938.6	1877.7	1786.3	1655.0	1509.7	1390.1	1345.6	1338.5
142.5°	2087.3	2069.4	2039.4	1998.7	1945.2	1853.8	1726.3	1582.8	1455.7	1398.1	1381.7
145°	2166.0	2152.0	2119.1	2081.6	2037.1	1945.7	1828.5	1685.5	1558.9	1483.9	1448.7
147.5°	2232.6	2221.3	2195.6	2151.5	2114.0	2026.3	1919.4	1792.8	1663.0	1570.1	1524.7
150°	2273.9	2264.5	2238.7	2196.5	2159.0	2076.9	1973.8	1856.6	1732.4	1633.9	1575.3
152.5°	2313.2	2303.9	2274.3	2232.1	2200.3	2123.8	2030.1	1918.5	1792.4	1693.9	1633.4
155°	2365.3	2353.6	2325.4	2285.6	2257.5	2187.1	2100.4	2001.9	1894.1	1791.0	1723.0
157.5°	2406.5	2392.0	2365.8	2331.5	2301.5	2236.8	2161.3	2076.5	1982.2	1883.8	1814.4
160°	2430.9	2414.5	2386.4	2355.9	2327.8	2266.8	2198.8	2121.5	2034.8	1945.7	1870.7
162.5°	2447.8	2433.3	2399.5	2372.8	2348.4	2293.1	2228.9	2159.0	2081.6	2003.8	1934.4
165°	2466.1	2449.7	2414.5	2393.4	2372.3	2325.4	2269.2	2212.9	2147.3	2084.0	2027.7
167.5°	2467.5	2453.9	2418.7	2398.1	2382.6	2342.3	2296.8	2253.7	2202.6	2152.9	2106.0
170°	2463.7	2452.0	2416.9	2398.1	2386.4	2353.6	2313.7	2276.2	2236.4	2194.2	2156.7
172.5°	2450.6	2438.9	2405.6	2390.6	2384.5	2355.4	2323.1	2295.0	2260.7	2229.8	2199.8
175°	2416.9	2407.5	2379.3	2370.0	2372.3	2353.6	2330.1	2313.7	2292.6	2273.9	2257.5
177.5°	2367.6	2362.0	2341.4	2341.4	2348.9	2337.6	2330.1	2322.6	2313.2	2307.6	2302.0
180°	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7



TEST NUMBER: P1428481

CATALOG NUMBER: SQ2W-PW1-K-150U-100D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4	2373.4
2.5°	2372.4	2368.4	2369.2	2370.4	2372.8	2375.2	2372.8	2370.4	2369.2	2368.4	2372.4
5°	2371.1	2367.1	2368.1	2371.1	2380.2	2389.2	2380.2	2371.1	2368.1	2367.1	2371.1
7.5°	2363.7	2362.0	2365.4	2370.2	2379.0	2387.9	2379.0	2370.2	2365.4	2362.0	2363.7
10°	2356.1	2355.6	2360.6	2366.4	2374.4	2382.4	2374.4	2366.4	2360.6	2355.6	2356.1
12.5°	2346.2	2346.9	2352.8	2359.1	2367.2	2375.2	2367.2	2359.1	2352.8	2346.9	2346.2
15°	2324.2	2327.2	2334.2	2340.7	2345.8	2350.8	2345.8	2340.7	2334.2	2327.2	2324.2
17.5°	2287.8	2288.0	2289.8	2291.7	2294.1	2296.5	2294.1	2291.7	2289.8	2288.0	2287.8
20°	2259.6	2254.6	2247.6	2242.3	2242.3	2242.3	2242.3	2242.3	2247.6	2254.6	2259.6
22.5°	2220.0	2207.0	2187.9	2172.0	2165.5	2159.1	2165.5	2172.0	2187.9	2207.0	2220.0
25°	2141.6	2111.9	2072.8	2039.6	2024.5	2009.5	2024.5	2039.6	2072.8	2111.9	2141.6
27.5°	2034.8	1987.1	1931.4	1884.5	1863.6	1842.7	1863.6	1884.5	1931.4	1987.1	2034.8
30°	1948.2	1888.4	1827.1	1776.2	1756.1	1736.0	1756.1	1776.2	1827.1	1888.4	1948.2
32.5°	1857.8	1789.6	1725.9	1672.7	1651.0	1629.3	1651.0	1672.7	1725.9	1789.6	1857.8
35°	1716.1	1638.3	1574.0	1521.0	1501.9	1482.8	1501.9	1521.0	1574.0	1638.3	1716.1
37.5°	1574.0	1491.6	1424.3	1368.6	1347.5	1326.4	1347.5	1368.6	1424.3	1491.6	1574.0
40°	1474.8	1390.4	1323.1	1267.3	1246.2	1225.1	1246.2	1267.3	1323.1	1390.4	1474.8
42.5°	1378.9	1294.5	1227.2	1171.3	1149.4	1127.5	1149.4	1171.3	1227.2	1294.5	1378.9
45°	1233.9	1149.5	1084.2	1030.0	1008.9	987.8	1008.9	1030.0	1084.2	1149.5	1233.9
47.5°	1097.3	1014.0	950.7	898.7	880.6	862.6	880.6	898.7	950.7	1014.0	1097.3
50°	1009.9	929.0	865.7	812.7	790.6	768.5	790.6	812.7	865.7	929.0	1009.9
52.5°	925.5	845.0	780.1	723.9	693.8	663.6	693.8	723.9	780.1	845.0	925.5
55°	802.4	721.1	648.7	590.2	573.1	556.1	573.1	590.2	648.7	721.1	802.4
57.5°	689.2	615.4	549.7	496.9	482.9	468.8	482.9	496.9	549.7	615.4	689.2
60°	613.8	546.5	491.3	446.3	432.2	418.2	432.2	446.3	491.3	546.5	613.8
62.5°	540.3	479.8	435.8	399.9	388.2	376.6	388.2	399.9	435.8	479.8	540.3
65°	450.3	400.1	363.9	334.3	324.2	314.2	324.2	334.3	363.9	400.1	450.3
67.5°	372.5	331.8	300.0	274.6	267.9	261.3	267.9	274.6	300.0	331.8	372.5
70°	322.2	287.6	261.5	240.6	235.6	230.6	235.6	240.6	261.5	287.6	322.2
72.5°	274.2	245.2	224.7	208.5	205.0	201.6	205.0	208.5	224.7	245.2	274.2
75°	210.2	189.6	175.6	164.5	162.5	160.5	162.5	164.5	175.6	189.6	210.2
77.5°	155.5	140.3	129.9	121.7	120.1	118.4	120.1	121.7	129.9	140.3	155.5
80°	120.6	109.0	101.0	94.9	94.9	94.9	94.9	94.9	101.0	109.0	120.6
82.5°	86.0	78.5	74.4	71.4	71.4	71.4	71.4	71.4	74.4	78.5	86.0
85°	45.0	39.9	33.9	29.1	28.1	27.1	28.1	29.1	33.9	39.9	45.0
87.5°	20.0	20.9	23.4	24.6	26.5	25.6	26.5	24.6	23.4	20.9	20.0
90°	53.9	70.3	86.7	96.1	105.5	100.8	105.5	96.1	86.7	70.3	53.9
92.5°	108.3	136.0	156.1	173.0	180.5	179.6	180.5	173.0	156.1	136.0	108.3
95°	218.0	250.8	283.6	307.1	321.2	316.5	321.2	307.1	283.6	250.8	218.0
97.5°	336.2	380.2	416.8	438.8	452.9	462.3	452.9	438.8	416.8	380.2	336.2
100°	414.9	457.1	499.3	525.1	548.5	557.9	548.5	525.1	499.3	457.1	414.9
102.5°	478.7	534.0	580.0	607.6	627.3	636.7	627.3	607.6	580.0	534.0	478.7
105°	583.7	642.3	691.5	726.7	747.8	754.8	747.8	726.7	691.5	642.3	583.7
107.5°	688.7	749.2	794.7	833.6	859.4	874.4	859.4	833.6	794.7	749.2	688.7
110°	771.2	820.5	869.7	904.9	930.6	940.0	930.6	904.9	869.7	820.5	771.2



TEST NUMBER: P1428481

CATALOG NUMBER: SQ2W-PW1-K-150U-100D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	840.6	895.5	944.7	979.9	1009.4	1022.5	1009.4	979.9	944.7	895.5	840.6
115°	937.7	1010.3	1054.9	1087.7	1108.8	1120.5	1108.8	1087.7	1054.9	1010.3	937.7
117.5°	1018.3	1094.3	1143.0	1168.3	1178.2	1186.6	1178.2	1168.3	1143.0	1094.3	1018.3
120°	1068.9	1139.3	1195.5	1228.4	1240.1	1244.8	1240.1	1228.4	1195.5	1139.3	1068.9
122.5°	1115.8	1182.4	1236.8	1277.1	1296.3	1301.0	1296.3	1277.1	1236.8	1182.4	1115.8
125°	1181.5	1244.8	1301.0	1340.9	1362.0	1373.7	1362.0	1340.9	1301.0	1244.8	1181.5
127.5°	1238.7	1307.1	1358.7	1394.8	1415.4	1424.8	1415.4	1394.8	1358.7	1307.1	1238.7
130°	1270.5	1340.9	1392.4	1432.3	1451.1	1460.4	1451.1	1432.3	1392.4	1340.9	1270.5
132.5°	1294.9	1369.0	1422.5	1458.6	1479.2	1488.6	1479.2	1458.6	1422.5	1369.0	1294.9
135°	1324.5	1401.8	1458.1	1493.2	1512.0	1521.4	1512.0	1493.2	1458.1	1401.8	1324.5
137.5°	1350.3	1420.6	1479.2	1516.2	1533.1	1539.2	1533.1	1516.2	1479.2	1420.6	1350.3
140°	1369.0	1430.0	1488.6	1523.7	1542.5	1544.8	1542.5	1523.7	1488.6	1430.0	1369.0
142.5°	1393.4	1441.2	1492.3	1527.5	1546.2	1550.4	1546.2	1527.5	1492.3	1441.2	1393.4
145°	1437.0	1465.1	1500.3	1533.1	1549.5	1554.2	1549.5	1533.1	1500.3	1465.1	1437.0
147.5°	1491.8	1500.7	1519.0	1540.6	1556.5	1559.8	1556.5	1540.6	1519.0	1500.7	1491.8
150°	1533.1	1530.8	1537.8	1551.9	1565.9	1563.6	1565.9	1551.9	1537.8	1530.8	1533.1
152.5°	1580.0	1566.4	1565.9	1572.5	1579.0	1578.6	1579.0	1572.5	1565.9	1566.4	1580.0
155°	1659.7	1633.9	1619.8	1615.1	1615.1	1612.8	1615.1	1615.1	1619.8	1633.9	1659.7
157.5°	1747.4	1711.3	1690.2	1678.9	1675.6	1670.5	1675.6	1678.9	1690.2	1711.3	1747.4
160°	1807.4	1767.5	1746.4	1727.7	1720.6	1713.6	1720.6	1727.7	1746.4	1767.5	1807.4
162.5°	1863.6	1825.7	1802.7	1785.8	1778.8	1768.0	1778.8	1785.8	1802.7	1825.7	1863.6
165°	1955.1	1915.2	1889.4	1875.3	1866.0	1856.6	1866.0	1875.3	1889.4	1915.2	1955.1
167.5°	2046.5	2002.9	1986.0	1970.1	1961.1	1944.3	1961.1	1970.1	1986.0	2002.9	2046.5
170°	2102.7	2062.9	2053.5	2039.4	2023.0	2004.3	2023.0	2039.4	2053.5	2062.9	2102.7
172.5°	2151.5	2124.8	2115.4	2101.3	2096.2	2081.2	2096.2	2101.3	2115.4	2124.8	2151.5
175°	2222.3	2201.2	2201.2	2198.8	2191.8	2177.7	2191.8	2198.8	2201.2	2201.2	2222.3
177.5°	2281.4	2270.1	2277.6	2277.6	2275.7	2262.6	2275.7	2277.6	2277.6	2270.1	2281.4
180°	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7	2320.7



TEST NUMBER: P1428481

CATALOG NUMBER: SQ2W-PW1-K-150U-100D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	2373.4	2373.4	2373.4	2373.4
2.5°	2381.2	2384.4	2370.8	2357.1
5°	2380.2	2382.7	2365.6	2348.5
7.5°	2370.5	2371.3	2354.1	2336.8
10°	2362.1	2362.1	2344.0	2325.9
12.5°	2350.6	2349.2	2330.4	2311.5
15°	2325.2	2320.9	2300.8	2280.7
17.5°	2289.2	2285.2	2265.1	2245.0
20°	2262.6	2259.9	2239.8	2219.7
22.5°	2227.1	2226.9	2205.2	2183.5
25°	2161.7	2171.5	2150.4	2129.3
27.5°	2074.6	2100.1	2083.1	2066.0
30°	2006.5	2046.9	2033.8	2020.8
32.5°	1930.5	1983.8	1978.8	1973.8
35°	1807.5	1878.4	1887.4	1896.5
37.5°	1671.5	1751.3	1778.2	1805.1
40°	1576.2	1661.9	1700.1	1738.2
42.5°	1480.4	1568.5	1616.3	1664.1
45°	1337.4	1429.1	1485.3	1541.6
47.5°	1200.6	1292.0	1347.8	1403.7
50°	1108.3	1195.7	1250.0	1304.2
52.5°	1021.5	1105.7	1154.4	1203.0
55°	892.8	972.2	1018.4	1064.6
57.5°	770.9	842.3	882.3	922.2
60°	693.2	761.5	796.7	831.8
62.5°	617.2	682.7	713.9	745.0
65°	514.6	568.6	591.7	614.8
67.5°	422.1	462.5	475.4	488.2
70°	365.4	398.8	402.8	406.9
72.5°	311.8	339.6	338.0	336.3
75°	237.3	255.7	247.6	239.6
77.5°	175.4	187.3	175.3	163.2
80°	135.6	143.9	131.9	119.8
82.5°	97.0	102.9	93.3	83.6
85°	49.0	50.7	45.7	40.7
87.5°	21.7	20.8	16.5	12.3
90°	42.2	25.8	16.4	7.0
92.5°	91.0	63.3	44.5	25.8
95°	182.8	145.3	103.1	72.7
97.5°	291.1	230.7	188.9	138.8
100°	349.3	290.7	250.8	196.9
102.5°	413.0	363.8	309.0	255.0
105°	527.4	466.5	403.2	342.3
107.5°	633.4	566.4	490.4	435.5
110°	700.9	628.2	548.5	499.3



TEST NUMBER: P1428481

CATALOG NUMBER: SQ2W-PW1-K-150U-100D-L840-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	766.5	692.0	610.4	561.2
115°	855.6	773.6	698.6	656.4
117.5°	941.4	857.0	777.8	744.5
120°	993.9	909.5	832.2	806.4
122.5°	1037.1	954.6	882.8	872.0
125°	1101.8	1017.4	956.4	970.5
127.5°	1154.3	1076.9	1038.5	1069.9
130°	1186.2	1118.2	1094.7	1139.3
132.5°	1214.3	1161.3	1151.0	1212.4
135°	1256.5	1226.0	1235.4	1319.8
137.5°	1306.6	1294.9	1326.3	1432.8
140°	1338.5	1345.6	1390.1	1509.7
142.5°	1381.7	1398.1	1455.7	1582.8
145°	1448.7	1483.9	1558.9	1685.5
147.5°	1524.7	1570.1	1663.0	1792.8
150°	1575.3	1633.9	1732.4	1856.6
152.5°	1633.4	1693.9	1792.4	1918.5
155°	1723.0	1791.0	1894.1	2001.9
157.5°	1814.4	1883.8	1982.2	2076.5
160°	1870.7	1945.7	2034.8	2121.5
162.5°	1934.4	2003.8	2081.6	2159.0
165°	2027.7	2084.0	2147.3	2212.9
167.5°	2106.0	2152.9	2202.6	2253.7
170°	2156.7	2194.2	2236.4	2276.2
172.5°	2199.8	2229.8	2260.7	2295.0
175°	2257.5	2273.9	2292.6	2313.7
177.5°	2302.0	2307.6	2313.2	2322.6
180°	2320.7	2320.7	2320.7	2320.7



TEST NUMBER: P1428481
 CATALOG NUMBER: SQ2W-PW1-K-150U-100D-L840-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.97	19.75	19.99	20.77	22.13	15.22	15.99	16.23	17.01	18.37
	3H	20.26	20.96	21.29	21.99	23.37	16.48	17.17	17.51	18.20	19.58
	4H	20.67	21.33	21.71	22.36	23.75	16.98	17.64	18.02	18.67	20.06
	6H	20.84	21.45	21.89	22.48	23.88	17.29	17.89	18.33	18.93	20.33
	8H	20.88	21.46	21.94	22.51	23.91	17.40	17.97	18.45	19.02	20.42
	12H	20.88	21.43	21.94	22.47	23.89	17.43	17.97	18.48	19.02	20.44
4H	2H	19.09	19.75	20.14	20.78	22.17	16.02	16.67	17.06	17.70	19.09
	3H	20.62	21.17	21.67	22.23	23.63	17.46	18.00	18.51	19.06	20.46
	4H	21.16	21.66	22.22	22.71	24.14	18.03	18.53	19.09	19.58	21.00
	6H	21.47	21.90	22.54	22.97	24.39	18.41	18.84	19.48	19.91	21.33
	8H	21.56	21.96	22.63	23.03	24.46	18.56	18.96	19.63	20.03	21.46
	12H	21.58	21.94	22.67	23.02	24.46	18.60	18.96	19.68	20.04	21.48
8H	4H	21.20	21.60	22.27	22.66	24.10	18.37	18.77	19.44	19.83	21.27
	6H	21.62	21.95	22.71	23.05	24.49	18.86	19.19	19.95	20.30	21.73
	8H	21.79	22.08	22.88	23.17	24.62	19.08	19.36	20.17	20.46	21.91
	12H	21.86	22.11	22.96	23.20	24.69	19.16	19.41	20.26	20.50	21.99
12H	4H	21.15	21.51	22.24	22.59	24.03	18.38	18.74	19.47	19.82	21.26
	6H	21.61	21.90	22.71	22.99	24.44	18.93	19.22	20.03	20.31	21.76
	8H	21.80	22.05	22.90	23.14	24.63	19.17	19.43	20.27	20.51	22.00