

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428274

Luminaire Tested: SQ2W-PR1-K-100U-125D-L940-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1428274  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-PR1-K-100U-125D-L940-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - PERCEIVE RIPPLE LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10124.5 lumens  
Efficiency: N/A  
Efficacy: 123.0 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.34 / 1.36  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 82.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1428274

CATALOG NUMBER: SQ2W-PR1-K-100U-125D-L940-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1428274

CATALOG NUMBER: SQ2W-PR1-K-100U-125D-L940-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	60				
1	101	97	93	90	94	90	87	84	79	77	74	68	67	65	59	57	56	52				
2	92	85	79	74	86	80	75	70	70	66	63	61	58	56	52	50	49	44				
3	85	76	68	63	79	71	65	60	62	58	54	54	51	48	47	44	42	38				
4	78	67	60	54	72	63	57	51	56	51	46	49	45	41	42	39	37	34				
5	72	60	52	47	67	57	50	44	50	45	40	44	40	36	39	35	32	30				
6	66	54	46	41	62	51	44	39	46	40	36	40	36	32	35	32	29	26				
7	61	49	41	36	57	47	39	34	41	36	32	37	32	29	32	29	26	23				
8	57	45	37	32	53	42	36	31	38	32	28	34	29	26	30	26	23	21				
9	53	41	34	29	50	39	32	28	35	29	25	31	26	23	27	24	21	19				
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	25	22	19	17				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	40461	40461	40461	40461
5°	40409	41153	40409	41153
10°	40834	42510	40834	42510
15°	40822	41377	40822	41377
20°	40161	42136	40161	42136
25°	40047	43870	40047	43870
30°	40005	44291	40005	44291
35°	39625	41237	39625	41237
40°	38711	36290	38711	36290
45°	36631	28697	36631	28697
50°	33301	22265	33301	22265
55°	29266	17331	29266	17331
60°	25326	14269	25326	14269
65°	21860	12493	21860	12493
70°	19657	11094	19657	11094
75°	18010	10199	18010	10199
80°	15676	9977	15676	9977
85°	11356	4724	11356	4724

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 20°  
 Vertical Angle: 45°  
 Luminance: 39326 cd/sqm



TEST NUMBER: P1428274

CATALOG NUMBER: SQ2W-PR1-K-100U-125D-L940-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	242.0	2.4
10°-20°	700.6	6.9
20°-30°	1083.0	10.7
30°-40°	1302.4	12.9
40°-50°	1169.6	11.6
50°-60°	783.7	7.7
60°-70°	455.9	4.5
70°-80°	234.1	2.3
80°-90°	63.6	0.6
90°-100°	111.5	1.1
100°-110°	325.1	3.2
110°-120°	530.5	5.2
120°-130°	673.2	6.6
130°-140°	720.3	7.1
140°-150°	672.6	6.6
150°-160°	553.5	5.5
160°-170°	371.2	3.7
170°-180°	131.8	1.3
0°-30°	2025.6	20.0
0°-40°	3328.0	32.9
0°-60°	5281.2	52.2
0°-90°	6034.8	59.6
90°-120°	967.1	9.6
90°-150°	3033.2	30.0
90°-180°	4090.0	40.4
0°-180°	10124.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	2506	2506	2506	2506	2506	
5°	2493	2539	2493	2539	2493	238
15°	2442	2475	2442	2475	2442	686
25°	2248	2463	2248	2463	2248	1037
35°	2010	2092	2010	2092	2010	1253
45°	1604	1257	1604	1257	1604	1227
55°	1040	616	1040	616	1040	934
65°	572	327	572	327	572	579
75°	289	164	289	164	289	306
85°	61	26	61	26	61	76
90°	4	31	4	61	4	6
95°	44	32	44	191	44	53
105°	207	331	207	456	207	220
115°	396	549	396	676	396	390
125°	586	870	586	829	586	524
135°	796	1139	796	918	796	616
145°	1017	1313	1017	938	1017	636
155°	1208	1426	1208	973	1208	555
165°	1336	1487	1336	1120	1336	376
175°	1396	1456	1396	1314	1396	132
180°	1401	1401	1401	1401	1401	



TEST NUMBER: P1428274

CATALOG NUMBER: SQ2W-PR1-K-100U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2506.0	2506.0	2506.0	2506.0	2506.0	2506.0	2506.0	2506.0	2506.0	2506.0	2506.0
2.5°	2495.8	2509.4	2523.1	2516.9	2504.2	2498.3	2499.2	2500.6	2503.3	2506.0	2503.3
5°	2493.3	2512.6	2531.9	2527.3	2514.8	2509.7	2512.0	2516.5	2527.9	2539.2	2527.9
7.5°	2492.7	2520.2	2547.7	2549.8	2543.4	2543.6	2550.1	2558.8	2573.8	2588.8	2573.8
10°	2490.7	2523.6	2556.6	2561.4	2556.8	2555.1	2556.3	2561.1	2577.0	2592.9	2577.0
12.5°	2478.4	2516.8	2555.2	2551.2	2533.0	2523.1	2521.5	2522.5	2531.1	2539.8	2531.1
15°	2442.2	2487.6	2533.0	2514.5	2474.8	2456.6	2460.0	2464.0	2469.7	2475.4	2469.7
17.5°	2378.3	2425.8	2473.2	2456.6	2418.7	2405.9	2418.2	2430.1	2441.3	2452.4	2441.3
20°	2337.4	2384.0	2430.5	2419.2	2388.5	2381.1	2397.0	2413.8	2433.1	2452.4	2433.1
22.5°	2300.6	2347.2	2393.7	2386.5	2361.3	2359.8	2382.0	2405.4	2431.9	2458.5	2431.9
25°	2248.0	2288.9	2329.8	2330.6	2318.1	2330.6	2368.1	2403.6	2433.1	2462.6	2433.1
27.5°	2192.8	2216.9	2241.0	2256.9	2270.0	2301.9	2352.6	2395.7	2416.4	2437.1	2416.4
30°	2145.8	2161.7	2177.6	2207.1	2241.2	2280.4	2324.7	2359.9	2367.8	2375.7	2367.8
32.5°	2094.7	2104.3	2113.8	2155.4	2207.6	2245.4	2268.8	2283.8	2273.6	2263.3	2273.6
35°	2010.4	2018.4	2026.3	2079.4	2147.5	2172.5	2154.4	2135.3	2113.8	2092.2	2113.8
37.5°	1910.3	1926.7	1943.0	1986.3	2038.5	2038.0	1984.9	1938.9	1914.1	1889.4	1914.1
40°	1836.7	1864.0	1891.2	1920.2	1949.7	1924.7	1845.2	1778.5	1750.2	1721.8	1750.2
42.5°	1746.8	1790.4	1834.0	1840.5	1834.6	1781.0	1679.7	1595.1	1560.3	1525.6	1560.3
45°	1604.3	1663.3	1722.3	1688.6	1623.9	1536.4	1426.3	1334.1	1295.4	1256.8	1295.4
47.5°	1436.2	1496.8	1557.4	1493.7	1388.6	1286.9	1188.6	1105.8	1069.7	1033.6	1069.7
50°	1325.8	1374.6	1423.5	1351.4	1239.0	1136.8	1044.8	965.9	926.2	886.4	926.2
52.5°	1213.4	1248.6	1283.8	1212.4	1105.4	1006.0	914.0	836.0	799.9	763.8	799.9
55°	1039.7	1057.9	1076.0	1009.9	915.7	824.8	737.4	665.6	640.6	615.7	640.6
57.5°	880.3	891.9	903.5	840.8	753.4	672.5	598.3	538.0	519.6	501.2	519.6
60°	784.3	792.2	800.1	736.6	649.1	576.5	518.6	471.5	456.7	441.9	456.7
62.5°	696.4	702.5	708.6	647.3	563.5	498.6	452.5	415.1	404.0	392.9	404.0
65°	572.2	577.9	583.6	531.3	459.8	406.5	371.3	342.9	334.9	327.0	334.9
67.5°	473.6	476.6	479.5	436.5	378.1	335.1	307.4	284.7	277.3	269.8	277.3
70°	416.4	417.5	418.7	380.6	329.5	291.5	266.5	246.4	240.7	235.0	240.7
72.5°	365.3	363.7	362.1	328.2	283.4	250.9	230.4	214.1	210.3	206.4	210.3
75°	288.7	285.3	281.9	253.8	217.4	192.4	178.8	168.0	165.8	163.5	165.8
77.5°	215.6	212.0	208.3	185.0	155.0	137.7	133.2	129.8	129.8	129.8	129.8
80°	168.6	164.1	159.5	141.4	118.6	107.3	107.3	107.3	107.3	107.3	107.3
82.5°	125.7	119.3	113.0	101.8	89.1	82.8	82.8	82.5	81.6	80.7	81.6
85°	61.3	55.6	50.0	48.5	48.5	45.1	38.3	32.4	29.0	25.5	29.0
87.5°	17.2	18.3	19.7	17.5	13.8	11.8	11.8	12.1	12.4	12.4	12.4
90°	4.2	9.9	17.0	22.6	26.9	28.3	28.3	29.7	31.1	31.1	31.1
92.5°	15.6	24.6	24.9	24.9	30.3	32.8	35.1	35.4	36.8	36.8	36.8
95°	43.9	48.1	72.2	70.7	48.1	38.2	32.5	32.5	32.5	32.5	32.5
97.5°	83.8	90.0	93.9	125.9	133.0	128.5	104.7	88.0	78.7	74.4	78.7
100°	118.8	121.7	130.2	131.6	166.9	200.9	183.9	162.7	155.6	151.4	155.6
102.5°	153.9	155.6	168.6	174.6	182.8	202.0	260.9	254.4	249.6	248.7	249.6
105°	206.6	208.0	232.0	243.3	249.0	249.0	247.6	275.9	321.2	331.1	321.2
107.5°	262.9	269.4	297.7	328.0	334.5	336.2	328.8	324.6	322.9	324.0	322.9
110°	301.4	311.3	345.2	383.4	393.3	396.1	393.3	389.1	386.2	386.2	386.2



TEST NUMBER: P1428274

CATALOG NUMBER: SQ2W-PR1-K-100U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	338.7	353.1	391.6	435.5	452.2	460.7	454.4	451.3	448.5	450.8	448.5
115°	396.1	417.4	468.3	513.6	547.5	551.8	550.4	550.4	548.9	548.9	548.9
117.5°	449.3	483.3	540.5	593.1	632.4	643.7	649.4	647.7	646.0	648.8	646.0
120°	486.7	526.3	591.4	650.8	689.0	706.0	711.6	708.8	711.6	708.8	711.6
122.5°	526.3	575.0	638.9	700.6	745.6	764.8	771.6	772.2	772.8	771.1	772.8
125°	585.7	645.2	720.1	783.8	830.5	853.1	858.8	860.2	863.0	870.1	863.0
127.5°	645.7	713.1	795.4	856.8	904.6	932.1	940.8	944.0	949.9	953.0	949.9
130°	687.6	764.0	847.5	905.5	952.2	981.9	997.4	1001.7	1008.8	1007.3	1008.8
132.5°	731.7	811.5	896.1	956.4	999.7	1031.7	1045.0	1057.1	1059.7	1061.7	1059.7
135°	796.5	882.8	967.7	1027.2	1068.2	1099.3	1116.3	1127.6	1134.7	1138.9	1134.7
137.5°	864.7	955.8	1037.3	1090.3	1131.6	1158.4	1177.7	1189.6	1196.9	1200.3	1196.9
140°	911.1	998.9	1078.1	1133.3	1170.0	1196.9	1213.9	1228.1	1236.5	1236.5	1236.5
142.5°	955.3	1041.9	1118.8	1174.0	1206.3	1230.9	1249.0	1259.7	1269.4	1269.4	1269.4
145°	1017.2	1103.6	1174.3	1229.5	1256.4	1279.0	1298.8	1307.3	1312.9	1312.9	1312.9
147.5°	1082.0	1158.4	1223.0	1275.9	1298.5	1325.1	1340.7	1347.5	1354.5	1351.4	1354.5
150°	1120.5	1191.3	1253.5	1303.0	1325.7	1351.1	1366.7	1372.4	1379.4	1375.2	1379.4
152.5°	1157.9	1225.2	1281.8	1327.9	1347.2	1372.6	1390.5	1396.1	1400.9	1397.8	1400.9
155°	1208.2	1267.7	1320.0	1362.5	1379.4	1403.5	1420.5	1427.5	1433.2	1426.1	1433.2
157.5°	1253.2	1304.5	1350.0	1389.1	1407.2	1427.8	1443.7	1452.4	1458.1	1455.0	1458.1
160°	1280.4	1327.1	1368.1	1404.9	1421.9	1440.3	1457.3	1467.2	1472.8	1468.6	1472.8
162.5°	1303.0	1345.2	1384.0	1417.4	1432.1	1448.2	1468.6	1477.3	1483.0	1477.6	1483.0
165°	1335.6	1369.5	1403.5	1431.8	1444.5	1457.3	1478.5	1488.4	1492.6	1487.0	1492.6
167.5°	1360.2	1386.2	1413.7	1438.0	1447.4	1459.8	1481.0	1489.2	1494.6	1487.5	1494.6
170°	1373.8	1396.4	1420.5	1440.3	1447.4	1458.7	1479.9	1487.0	1491.2	1484.1	1491.2
172.5°	1385.1	1402.1	1421.6	1439.1	1442.8	1451.9	1472.0	1479.0	1482.2	1476.2	1482.2
175°	1396.4	1406.3	1420.5	1431.8	1430.4	1436.0	1453.0	1458.7	1464.3	1455.8	1464.3
177.5°	1401.8	1406.3	1410.8	1417.6	1413.1	1413.1	1425.6	1429.0	1430.1	1425.6	1430.1
180°	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7



TEST NUMBER: P1428274

CATALOG NUMBER: SQ2W-PR1-K-100U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2506.0	2506.0	2506.0	2506.0	2506.0	2506.0	2506.0	2506.0	2506.0	2506.0	2506.0
2.5°	2500.6	2499.2	2498.3	2504.2	2516.9	2523.1	2509.4	2495.8	2509.4	2523.1	2516.9
5°	2516.5	2512.0	2509.7	2514.8	2527.3	2531.9	2512.6	2493.3	2512.6	2531.9	2527.3
7.5°	2558.8	2550.1	2543.6	2543.4	2549.8	2547.7	2520.2	2492.7	2520.2	2547.7	2549.8
10°	2561.1	2556.3	2555.1	2556.8	2561.4	2556.6	2523.6	2490.7	2523.6	2556.6	2561.4
12.5°	2522.5	2521.5	2523.1	2533.0	2551.2	2555.2	2516.8	2478.4	2516.8	2555.2	2551.2
15°	2464.0	2460.0	2456.6	2474.8	2514.5	2533.0	2487.6	2442.2	2487.6	2533.0	2514.5
17.5°	2430.1	2418.2	2405.9	2418.7	2456.6	2473.2	2425.8	2378.3	2425.8	2473.2	2456.6
20°	2413.8	2397.0	2381.1	2388.5	2419.2	2430.5	2384.0	2337.4	2384.0	2430.5	2419.2
22.5°	2405.4	2382.0	2359.8	2361.3	2386.5	2393.7	2347.2	2300.6	2347.2	2393.7	2386.5
25°	2403.6	2368.1	2330.6	2318.1	2330.6	2329.8	2288.9	2248.0	2288.9	2329.8	2330.6
27.5°	2395.7	2352.6	2301.9	2270.0	2256.9	2241.0	2216.9	2192.8	2216.9	2241.0	2256.9
30°	2359.9	2324.7	2280.4	2241.2	2207.1	2177.6	2161.7	2145.8	2161.7	2177.6	2207.1
32.5°	2283.8	2268.8	2245.4	2207.6	2155.4	2113.8	2104.3	2094.7	2104.3	2113.8	2155.4
35°	2135.3	2154.4	2172.5	2147.5	2079.4	2026.3	2018.4	2010.4	2018.4	2026.3	2079.4
37.5°	1938.9	1984.9	2038.0	2038.5	1986.3	1943.0	1926.7	1910.3	1926.7	1943.0	1986.3
40°	1778.5	1845.2	1924.7	1949.7	1920.2	1891.2	1864.0	1836.7	1864.0	1891.2	1920.2
42.5°	1595.1	1679.7	1781.0	1834.6	1840.5	1834.0	1790.4	1746.8	1790.4	1834.0	1840.5
45°	1334.1	1426.3	1536.4	1623.9	1688.6	1722.3	1663.3	1604.3	1663.3	1722.3	1688.6
47.5°	1105.8	1188.6	1286.9	1388.6	1493.7	1557.4	1496.8	1436.2	1496.8	1557.4	1493.7
50°	965.9	1044.8	1136.8	1239.0	1351.4	1423.5	1374.6	1325.8	1374.6	1423.5	1351.4
52.5°	836.0	914.0	1006.0	1105.4	1212.4	1283.8	1248.6	1213.4	1248.6	1283.8	1212.4
55°	665.6	737.4	824.8	915.7	1009.9	1076.0	1057.9	1039.7	1057.9	1076.0	1009.9
57.5°	538.0	598.3	672.5	753.4	840.8	903.5	891.9	880.3	891.9	903.5	840.8
60°	471.5	518.6	576.5	649.1	736.6	800.1	792.2	784.3	792.2	800.1	736.6
62.5°	415.1	452.5	498.6	563.5	647.3	708.6	702.5	696.4	702.5	708.6	647.3
65°	342.9	371.3	406.5	459.8	531.3	583.6	577.9	572.2	577.9	583.6	531.3
67.5°	284.7	307.4	335.1	378.1	436.5	479.5	476.6	473.6	476.6	479.5	436.5
70°	246.4	266.5	291.5	329.5	380.6	418.7	417.5	416.4	417.5	418.7	380.6
72.5°	214.1	230.4	250.9	283.4	328.2	362.1	363.7	365.3	363.7	362.1	328.2
75°	168.0	178.8	192.4	217.4	253.8	281.9	285.3	288.7	285.3	281.9	253.8
77.5°	129.8	133.2	137.7	155.0	185.0	208.3	212.0	215.6	212.0	208.3	185.0
80°	107.3	107.3	107.3	118.6	141.4	159.5	164.1	168.6	164.1	159.5	141.4
82.5°	82.5	82.8	82.8	89.1	101.8	113.0	119.3	125.7	119.3	113.0	101.8
85°	32.4	38.3	45.1	48.5	48.5	50.0	55.6	61.3	55.6	50.0	48.5
87.5°	12.1	11.8	11.8	13.8	17.5	19.7	18.3	17.2	18.3	19.5	18.0
90°	29.7	28.3	28.3	26.9	22.6	17.0	9.9	4.2	9.9	15.6	25.5
92.5°	35.4	35.1	32.8	30.3	24.9	24.9	24.6	15.6	26.9	38.2	54.9
95°	32.5	32.5	38.2	48.1	70.7	72.2	48.1	43.9	62.3	87.7	110.4
97.5°	88.0	104.7	128.5	133.0	125.9	93.9	90.0	83.8	114.0	139.2	175.7
100°	162.7	183.9	200.9	166.9	131.6	130.2	121.7	118.8	151.4	175.4	210.8
102.5°	254.4	260.9	202.0	182.8	174.6	168.6	155.6	153.9	186.5	219.6	249.3
105°	275.9	247.6	249.0	249.0	243.3	232.0	208.0	206.6	243.3	281.5	318.3
107.5°	324.6	328.8	336.2	334.5	328.0	297.7	269.4	262.9	296.0	341.8	382.3
110°	389.1	393.3	396.1	393.3	383.4	345.2	311.3	301.4	331.1	379.2	423.0



TEST NUMBER: P1428274

CATALOG NUMBER: SQ2W-PR1-K-100U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	451.3	454.4	460.7	452.2	435.5	391.6	353.1	338.7	368.4	417.7	462.6
115°	550.4	550.4	551.8	547.5	513.6	468.3	417.4	396.1	421.6	466.9	516.4
117.5°	647.7	649.4	643.7	632.4	593.1	540.5	483.3	449.3	469.4	517.3	568.2
120°	708.8	711.6	706.0	689.0	650.8	591.4	526.3	486.7	502.3	548.9	599.9
122.5°	772.2	771.6	764.8	745.6	700.6	638.9	575.0	526.3	532.8	576.1	625.9
125°	860.2	858.8	853.1	830.5	783.8	720.1	645.2	585.7	577.2	614.0	665.0
127.5°	944.0	940.8	932.1	904.6	856.8	795.4	713.1	645.7	626.8	650.0	696.7
130°	1001.7	997.4	981.9	952.2	905.5	847.5	764.0	687.6	660.7	674.9	715.9
132.5°	1057.1	1045.0	1031.7	999.7	956.4	896.1	811.5	731.7	694.7	700.9	732.9
135°	1127.6	1116.3	1099.3	1068.2	1027.2	967.7	882.8	796.5	745.6	739.9	758.3
137.5°	1189.6	1177.7	1158.4	1131.6	1090.3	1037.3	955.8	864.7	800.5	781.5	788.6
140°	1228.1	1213.9	1196.9	1170.0	1133.3	1078.1	998.9	911.1	839.0	812.1	807.9
142.5°	1259.7	1249.0	1230.9	1206.3	1174.0	1118.8	1041.9	955.3	878.6	843.8	833.9
145°	1307.3	1298.8	1279.0	1256.4	1229.5	1174.3	1103.6	1017.2	940.8	895.6	874.4
147.5°	1347.5	1340.7	1325.1	1298.5	1275.9	1223.0	1158.4	1082.0	1003.7	947.6	920.2
150°	1372.4	1366.7	1351.1	1325.7	1303.0	1253.5	1191.3	1120.5	1045.5	986.1	950.8
152.5°	1396.1	1390.5	1372.6	1347.2	1327.9	1281.8	1225.2	1157.9	1081.8	1022.3	985.8
155°	1427.5	1420.5	1403.5	1379.4	1362.5	1320.0	1267.7	1208.2	1143.2	1080.9	1039.9
157.5°	1452.4	1443.7	1427.8	1407.2	1389.1	1350.0	1304.5	1253.2	1196.4	1136.9	1095.1
160°	1467.2	1457.3	1440.3	1421.9	1404.9	1368.1	1327.1	1280.4	1228.1	1174.3	1129.0
162.5°	1477.3	1468.6	1448.2	1432.1	1417.4	1384.0	1345.2	1303.0	1256.4	1209.4	1167.5
165°	1488.4	1478.5	1457.3	1444.5	1431.8	1403.5	1369.5	1335.6	1296.0	1257.8	1223.8
167.5°	1489.2	1481.0	1459.8	1447.4	1438.0	1413.7	1386.2	1360.2	1329.4	1299.4	1271.1
170°	1487.0	1479.9	1458.7	1447.4	1440.3	1420.5	1396.4	1373.8	1349.7	1324.3	1301.6
172.5°	1479.0	1472.0	1451.9	1442.8	1439.1	1421.6	1402.1	1385.1	1364.4	1345.8	1327.7
175°	1458.7	1453.0	1436.0	1430.4	1431.8	1420.5	1406.3	1396.4	1383.7	1372.4	1362.5
177.5°	1429.0	1425.6	1413.1	1413.1	1417.6	1410.8	1406.3	1401.8	1396.1	1392.7	1389.3
180°	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7



TEST NUMBER: P1428274

CATALOG NUMBER: SQ2W-PR1-K-100U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2506.0	2506.0	2506.0	2506.0	2506.0	2506.0	2506.0	2506.0	2506.0	2506.0	2506.0
2.5°	2504.2	2498.3	2499.2	2500.6	2503.3	2506.0	2503.3	2500.6	2499.2	2498.3	2504.2
5°	2514.8	2509.7	2512.0	2516.5	2527.9	2539.2	2527.9	2516.5	2512.0	2509.7	2514.8
7.5°	2543.4	2543.6	2550.1	2558.8	2573.8	2588.8	2573.8	2558.8	2550.1	2543.6	2543.4
10°	2556.8	2555.1	2556.3	2561.1	2577.0	2592.9	2577.0	2561.1	2556.3	2555.1	2556.8
12.5°	2533.0	2523.1	2521.5	2522.5	2531.1	2539.8	2531.1	2522.5	2521.5	2523.1	2533.0
15°	2474.8	2456.6	2460.0	2464.0	2469.7	2475.4	2469.7	2464.0	2460.0	2456.6	2474.8
17.5°	2418.7	2405.9	2418.2	2430.1	2441.3	2452.4	2441.3	2430.1	2418.2	2405.9	2418.7
20°	2388.5	2381.1	2397.0	2413.8	2433.1	2452.4	2433.1	2413.8	2397.0	2381.1	2388.5
22.5°	2361.3	2359.8	2382.0	2405.4	2431.9	2458.5	2431.9	2405.4	2382.0	2359.8	2361.3
25°	2318.1	2330.6	2368.1	2403.6	2433.1	2462.6	2433.1	2403.6	2368.1	2330.6	2318.1
27.5°	2270.0	2301.9	2352.6	2395.7	2416.4	2437.1	2416.4	2395.7	2352.6	2301.9	2270.0
30°	2241.2	2280.4	2324.7	2359.9	2367.8	2375.7	2367.8	2359.9	2324.7	2280.4	2241.2
32.5°	2207.6	2245.4	2268.8	2283.8	2273.6	2263.3	2273.6	2283.8	2268.8	2245.4	2207.6
35°	2147.5	2172.5	2154.4	2135.3	2113.8	2092.2	2113.8	2135.3	2154.4	2172.5	2147.5
37.5°	2038.5	2038.0	1984.9	1938.9	1914.1	1889.4	1914.1	1938.9	1984.9	2038.0	2038.5
40°	1949.7	1924.7	1845.2	1778.5	1750.2	1721.8	1750.2	1778.5	1845.2	1924.7	1949.7
42.5°	1834.6	1781.0	1679.7	1595.1	1560.3	1525.6	1560.3	1595.1	1679.7	1781.0	1834.6
45°	1623.9	1536.4	1426.3	1334.1	1295.4	1256.8	1295.4	1334.1	1426.3	1536.4	1623.9
47.5°	1388.6	1286.9	1188.6	1105.8	1069.7	1033.6	1069.7	1105.8	1188.6	1286.9	1388.6
50°	1239.0	1136.8	1044.8	965.9	926.2	886.4	926.2	965.9	1044.8	1136.8	1239.0
52.5°	1105.4	1006.0	914.0	836.0	799.9	763.8	799.9	836.0	914.0	1006.0	1105.4
55°	915.7	824.8	737.4	665.6	640.6	615.7	640.6	665.6	737.4	824.8	915.7
57.5°	753.4	672.5	598.3	538.0	519.6	501.2	519.6	538.0	598.3	672.5	753.4
60°	649.1	576.5	518.6	471.5	456.7	441.9	456.7	471.5	518.6	576.5	649.1
62.5°	563.5	498.6	452.5	415.1	404.0	392.9	404.0	415.1	452.5	498.6	563.5
65°	459.8	406.5	371.3	342.9	334.9	327.0	334.9	342.9	371.3	406.5	459.8
67.5°	378.1	335.1	307.4	284.7	277.3	269.8	277.3	284.7	307.4	335.1	378.1
70°	329.5	291.5	266.5	246.4	240.7	235.0	240.7	246.4	266.5	291.5	329.5
72.5°	283.4	250.9	230.4	214.1	210.3	206.4	210.3	214.1	230.4	250.9	283.4
75°	217.4	192.4	178.8	168.0	165.8	163.5	165.8	168.0	178.8	192.4	217.4
77.5°	155.0	137.7	133.2	129.8	129.8	129.8	129.8	129.8	133.2	137.7	155.0
80°	118.6	107.3	107.3	107.3	107.3	107.3	107.3	107.3	107.3	107.3	118.6
82.5°	89.1	82.8	82.8	82.5	81.6	80.7	81.6	82.5	82.8	82.8	89.1
85°	48.5	45.1	38.3	32.4	29.0	25.5	29.0	32.4	38.3	45.1	48.5
87.5°	14.9	14.6	16.6	17.7	18.9	18.3	18.9	17.7	16.6	14.6	14.9
90°	32.5	42.4	52.3	58.0	63.7	60.8	63.7	58.0	52.3	42.4	32.5
92.5°	65.4	82.1	94.2	104.4	108.9	108.4	108.9	104.4	94.2	82.1	65.4
95°	131.6	151.4	171.2	185.3	193.8	191.0	193.8	185.3	171.2	151.4	131.6
97.5°	202.9	229.5	251.6	264.9	273.3	279.0	273.3	264.9	251.6	229.5	202.9
100°	250.4	275.9	301.4	316.9	331.1	336.7	331.1	316.9	301.4	275.9	250.4
102.5°	288.9	322.3	350.0	366.7	378.6	384.3	378.6	366.7	350.0	322.3	288.9
105°	352.3	387.7	417.4	438.6	451.3	455.6	451.3	438.6	417.4	387.7	352.3
107.5°	415.7	452.2	479.6	503.1	518.7	527.7	518.7	503.1	479.6	452.2	415.7
110°	465.5	495.2	524.9	546.1	561.7	567.3	561.7	546.1	524.9	495.2	465.5



TEST NUMBER: P1428274

CATALOG NUMBER: SQ2W-PR1-K-100U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	507.4	540.5	570.2	591.4	609.2	617.1	609.2	591.4	570.2	540.5	507.4
115°	565.9	609.8	636.7	656.5	669.2	676.3	669.2	656.5	636.7	609.8	565.9
117.5°	614.6	660.4	689.9	705.1	711.1	716.2	711.1	705.1	689.9	660.4	614.6
120°	645.2	687.6	721.6	741.4	748.4	751.3	748.4	741.4	721.6	687.6	645.2
122.5°	673.4	713.6	746.5	770.8	782.4	785.2	782.4	770.8	746.5	713.6	673.4
125°	713.1	751.3	785.2	809.3	822.0	829.1	822.0	809.3	785.2	751.3	713.1
127.5°	747.6	788.9	820.0	841.8	854.3	859.9	854.3	841.8	820.0	788.9	747.6
130°	766.8	809.3	840.4	864.4	875.8	881.4	875.8	864.4	840.4	809.3	766.8
132.5°	781.5	826.2	858.5	880.3	892.7	898.4	892.7	880.3	858.5	826.2	781.5
135°	799.4	846.1	880.0	901.2	912.6	918.2	912.6	901.2	880.0	846.1	799.4
137.5°	814.9	857.4	892.7	915.1	925.3	929.0	925.3	915.1	892.7	857.4	814.9
140°	826.2	863.0	898.4	919.6	930.9	932.4	930.9	919.6	898.4	863.0	826.2
142.5°	841.0	869.8	900.7	921.9	933.2	935.8	933.2	921.9	900.7	869.8	841.0
145°	867.3	884.3	905.5	925.3	935.2	938.0	935.2	925.3	905.5	884.3	867.3
147.5°	900.4	905.8	916.8	929.8	939.4	941.4	939.4	929.8	916.8	905.8	900.4
150°	925.3	923.9	928.1	936.6	945.1	943.7	945.1	936.6	928.1	923.9	925.3
152.5°	953.6	945.4	945.1	949.1	953.0	952.7	953.0	949.1	945.1	945.4	953.6
155°	1001.7	986.1	977.6	974.8	974.8	973.4	974.8	974.8	977.6	986.1	1001.7
157.5°	1054.6	1032.8	1020.1	1013.3	1011.3	1008.2	1011.3	1013.3	1020.1	1032.8	1054.6
160°	1090.8	1066.8	1054.0	1042.7	1038.5	1034.2	1038.5	1042.7	1054.0	1066.8	1090.8
162.5°	1124.8	1101.9	1088.0	1077.8	1073.6	1067.1	1073.6	1077.8	1088.0	1101.9	1124.8
165°	1180.0	1155.9	1140.3	1131.8	1126.2	1120.5	1126.2	1131.8	1140.3	1155.9	1180.0
167.5°	1235.1	1208.8	1198.6	1189.0	1183.6	1173.4	1183.6	1189.0	1198.6	1208.8	1235.1
170°	1269.1	1245.0	1239.4	1230.9	1221.0	1209.7	1221.0	1230.9	1239.4	1245.0	1269.1
172.5°	1298.5	1282.4	1276.7	1268.2	1265.1	1256.1	1265.1	1268.2	1276.7	1282.4	1298.5
175°	1341.2	1328.5	1328.5	1327.1	1322.8	1314.4	1322.8	1327.1	1328.5	1328.5	1341.2
177.5°	1376.9	1370.1	1374.6	1374.6	1373.5	1365.6	1373.5	1374.6	1374.6	1370.1	1376.9
180°	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7



TEST NUMBER: P1428274

CATALOG NUMBER: SQ2W-PR1-K-100U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	2506.0	2506.0	2506.0	2506.0
2.5°	2516.9	2523.1	2509.4	2495.8
5°	2527.3	2531.9	2512.6	2493.3
7.5°	2549.8	2547.7	2520.2	2492.7
10°	2561.4	2556.6	2523.6	2490.7
12.5°	2551.2	2555.2	2516.8	2478.4
15°	2514.5	2533.0	2487.6	2442.2
17.5°	2456.6	2473.2	2425.8	2378.3
20°	2419.2	2430.5	2384.0	2337.4
22.5°	2386.5	2393.7	2347.2	2300.6
25°	2330.6	2329.8	2288.9	2248.0
27.5°	2256.9	2241.0	2216.9	2192.8
30°	2207.1	2177.6	2161.7	2145.8
32.5°	2155.4	2113.8	2104.3	2094.7
35°	2079.4	2026.3	2018.4	2010.4
37.5°	1986.3	1943.0	1926.7	1910.3
40°	1920.2	1891.2	1864.0	1836.7
42.5°	1840.5	1834.0	1790.4	1746.8
45°	1688.6	1722.3	1663.3	1604.3
47.5°	1493.7	1557.4	1496.8	1436.2
50°	1351.4	1423.5	1374.6	1325.8
52.5°	1212.4	1283.8	1248.6	1213.4
55°	1009.9	1076.0	1057.9	1039.7
57.5°	840.8	903.5	891.9	880.3
60°	736.6	800.1	792.2	784.3
62.5°	647.3	708.6	702.5	696.4
65°	531.3	583.6	577.9	572.2
67.5°	436.5	479.5	476.6	473.6
70°	380.6	418.7	417.5	416.4
72.5°	328.2	362.1	363.7	365.3
75°	253.8	281.9	285.3	288.7
77.5°	185.0	208.3	212.0	215.6
80°	141.4	159.5	164.1	168.6
82.5°	101.8	113.0	119.3	125.7
85°	48.5	50.0	55.6	61.3
87.5°	18.0	19.5	18.3	17.2
90°	25.5	15.6	9.9	4.2
92.5°	54.9	38.2	26.9	15.6
95°	110.4	87.7	62.3	43.9
97.5°	175.7	139.2	114.0	83.8
100°	210.8	175.4	151.4	118.8
102.5°	249.3	219.6	186.5	153.9
105°	318.3	281.5	243.3	206.6
107.5°	382.3	341.8	296.0	262.9
110°	423.0	379.2	331.1	301.4



TEST NUMBER: P1428274

CATALOG NUMBER: SQ2W-PR1-K-100U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	462.6	417.7	368.4	338.7
115°	516.4	466.9	421.6	396.1
117.5°	568.2	517.3	469.4	449.3
120°	599.9	548.9	502.3	486.7
122.5°	625.9	576.1	532.8	526.3
125°	665.0	614.0	577.2	585.7
127.5°	696.7	650.0	626.8	645.7
130°	715.9	674.9	660.7	687.6
132.5°	732.9	700.9	694.7	731.7
135°	758.3	739.9	745.6	796.5
137.5°	788.6	781.5	800.5	864.7
140°	807.9	812.1	839.0	911.1
142.5°	833.9	843.8	878.6	955.3
145°	874.4	895.6	940.8	1017.2
147.5°	920.2	947.6	1003.7	1082.0
150°	950.8	986.1	1045.5	1120.5
152.5°	985.8	1022.3	1081.8	1157.9
155°	1039.9	1080.9	1143.2	1208.2
157.5°	1095.1	1136.9	1196.4	1253.2
160°	1129.0	1174.3	1228.1	1280.4
162.5°	1167.5	1209.4	1256.4	1303.0
165°	1223.8	1257.8	1296.0	1335.6
167.5°	1271.1	1299.4	1329.4	1360.2
170°	1301.6	1324.3	1349.7	1373.8
172.5°	1327.7	1345.8	1364.4	1385.1
175°	1362.5	1372.4	1383.7	1396.4
177.5°	1389.3	1392.7	1396.1	1401.8
180°	1400.7	1400.7	1400.7	1400.7



TEST NUMBER: P1428274  
 CATALOG NUMBER: SQ2W-PR1-K-100U-125D-L940-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.38	21.29	21.26	22.18	23.31	16.75	17.66	17.63	18.55	19.68
	3H	21.59	22.40	22.49	23.30	24.46	17.92	18.73	18.81	19.63	20.79
	4H	22.08	22.84	22.99	23.75	24.92	18.38	19.15	19.29	20.05	21.22
	6H	22.38	23.08	23.30	24.00	25.18	18.73	19.43	19.65	20.34	21.52
	8H	22.49	23.15	23.41	24.08	25.26	18.87	19.53	19.79	20.46	21.64
	12H	22.53	23.16	23.46	24.09	25.29	18.90	19.53	19.83	20.46	21.66
4H	2H	20.49	21.25	21.41	22.16	23.33	17.47	18.23	18.38	19.14	20.31
	3H	21.96	22.59	22.88	23.53	24.71	18.83	19.46	19.75	20.40	21.58
	4H	22.59	23.16	23.52	24.10	25.30	19.38	19.95	20.31	20.89	22.09
	6H	23.02	23.51	23.97	24.47	25.68	19.81	20.30	20.76	21.26	22.47
	8H	23.18	23.64	24.13	24.59	25.81	20.00	20.46	20.94	21.41	22.63
	12H	23.25	23.66	24.22	24.63	25.86	20.04	20.46	21.01	21.43	22.66
8H	4H	22.62	23.08	23.57	24.03	25.25	19.71	20.17	20.66	21.12	22.34
	6H	23.15	23.53	24.12	24.52	25.74	20.25	20.63	21.22	21.62	22.84
	8H	23.38	23.72	24.37	24.70	25.94	20.51	20.85	21.49	21.83	23.07
	12H	23.50	23.80	24.49	24.78	26.06	20.61	20.90	21.59	21.88	23.17
12H	4H	22.58	22.99	23.54	23.96	25.19	19.73	20.14	20.69	21.11	22.34
	6H	23.14	23.48	24.12	24.46	25.70	20.32	20.66	21.30	21.64	22.88
	8H	23.39	23.69	24.38	24.67	25.95	20.61	20.91	21.60	21.88	23.17