

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427512

Luminaire Tested: SQ2W-BBM-K-050U-075D-L940-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1427512  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2104-222-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-BBM-K-050U-075D-L940-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - BLACK DISCREET BAFFLE, MEDIUM 80-DEGREE OPTIC  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5173.9 lumens  
Efficiency: N/A  
Efficacy: 121.7 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.17 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 42.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1427512

CATALOG NUMBER: SQ2W-BBM-K-050U-075D-L940-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1427512

CATALOG NUMBER: SQ2W-BBM-K-050U-075D-L940-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	77	77	77	66	66	66	61
1	103	99	96	93	96	93	91	88	82	80	78	72	71	69	62	61	61	56
2	96	90	85	81	90	85	80	77	75	72	69	66	64	62	58	57	55	51
3	89	81	75	70	84	77	72	67	69	65	61	61	58	56	54	52	50	47
4	83	74	67	62	78	70	64	60	63	58	55	56	53	50	50	48	45	42
5	77	67	60	55	73	64	58	53	58	53	49	52	48	45	46	44	41	39
6	72	61	54	49	68	59	52	48	53	48	44	48	44	41	43	40	38	35
7	67	56	49	45	63	54	48	43	49	44	40	44	40	37	40	37	35	32
8	63	52	45	40	59	50	43	39	45	40	37	41	37	34	37	34	32	30
9	59	48	41	37	56	46	40	36	42	37	34	38	34	31	35	32	29	27
10	55	44	38	34	52	43	37	33	39	34	31	36	32	29	33	29	27	25

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	34140	34140	34140	34140
5°	34406	34458	34406	34458
10°	34840	34788	34840	34788
15°	35468	34761	35468	34761
20°	35513	34132	35513	34132
25°	34635	33278	34635	33278
30°	32559	31039	32559	31039
35°	28897	27813	28897	27813
40°	23698	22428	23698	22428
45°	14129	13259	14129	13259
50°	4411	4172	4411	4172
55°	1666	1666	1666	1666
60°	103	36	103	36
65°	0	0	0	0
70°	0	0	0	0
75°	0	0	0	0
80°	0	0	0	0
85°	0	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 40°  
 Vertical Angle: 45°  
 Luminance: 16543 cd/sqm



TEST NUMBER: P1427512

CATALOG NUMBER: SQ2W-BBM-K-050U-075D-L940-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	202.2	3.9
10°-20°	592.2	11.4
20°-30°	871.3	16.8
30°-40°	890.5	17.2
40°-50°	513.0	9.9
50°-60°	88.3	1.7
60°-70°	3.2	0.1
70°-80°	0.0	0.0
80°-90°	3.7	0.1
90°-100°	54.8	1.1
100°-110°	159.8	3.1
110°-120°	260.8	5.0
120°-130°	330.9	6.4
130°-140°	354.1	6.8
140°-150°	330.7	6.4
150°-160°	272.1	5.3
160°-170°	182.5	3.5
170°-180°	64.8	1.3
0°-30°	1665.7	32.2
0°-40°	2556.2	49.4
0°-60°	3157.4	61.0
0°-90°	3164.3	61.2
90°-120°	475.4	9.2
90°-150°	1491.1	28.8
90°-180°	2010.0	38.8
0°-180°	5173.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	2114	2114	2114	2114	2114	
5°	2123	2126	2123	2126	2123	203
15°	2122	2080	2122	2080	2122	597
25°	1944	1868	1944	1868	1944	887
35°	1466	1411	1466	1411	1466	906
45°	619	581	619	581	619	479
55°	59	59	59	59	59	63
65°	0	0	0	0	0	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	2	15	2	30	2	2
95°	22	16	22	94	22	26
105°	102	163	102	224	102	108
115°	195	270	195	332	195	192
125°	288	428	288	408	288	258
135°	392	560	392	451	392	303
145°	500	645	500	461	500	313
155°	594	701	594	478	594	273
165°	657	731	657	551	657	185
175°	686	716	686	646	686	65
180°	689	689	689	689	689	



TEST NUMBER: P1427512

CATALOG NUMBER: SQ2W-BBM-K-050U-075D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2114.5	2114.5	2114.5	2114.5	2114.5	2114.5	2114.5	2114.5	2114.5	2114.5	2114.5
2.5°	2123.8	2121.1	2118.5	2112.2	2104.7	2105.3	2113.9	2119.9	2118.0	2116.2	2118.0
5°	2122.9	2120.6	2118.2	2111.7	2103.7	2106.0	2118.7	2128.0	2127.0	2126.1	2127.0
7.5°	2121.7	2120.1	2118.5	2113.8	2108.2	2110.6	2121.0	2128.3	2125.9	2123.6	2125.9
10°	2125.1	2124.6	2124.1	2116.9	2107.5	2108.2	2119.1	2126.6	2124.2	2121.9	2124.2
12.5°	2126.7	2129.7	2132.6	2122.3	2107.6	2104.6	2113.1	2118.5	2114.3	2110.0	2114.3
15°	2121.9	2129.9	2137.9	2123.3	2101.2	2090.9	2092.3	2091.8	2085.7	2079.6	2085.7
17.5°	2098.2	2109.5	2120.7	2101.5	2072.1	2054.8	2049.6	2043.6	2034.9	2026.3	2034.9
20°	2066.9	2080.0	2093.2	2072.2	2039.7	2019.0	2010.1	2001.5	1994.0	1986.5	1994.0
22.5°	2022.9	2034.9	2046.9	2026.7	1995.8	1974.8	1963.6	1953.7	1947.7	1941.6	1947.7
25°	1944.2	1952.2	1960.2	1939.6	1909.5	1890.2	1881.8	1874.6	1871.3	1868.0	1871.3
27.5°	1832.7	1834.9	1837.2	1820.8	1798.3	1781.7	1771.2	1762.2	1758.0	1753.8	1758.0
30°	1746.4	1746.4	1746.4	1733.7	1716.8	1702.7	1691.4	1680.9	1672.9	1664.9	1672.9
32.5°	1645.7	1644.5	1643.4	1634.1	1622.1	1609.8	1597.4	1586.1	1578.1	1570.1	1578.1
35°	1466.1	1471.2	1476.4	1469.9	1459.6	1448.3	1436.1	1425.2	1418.1	1411.1	1418.1
37.5°	1271.6	1273.6	1275.6	1270.2	1262.4	1251.9	1238.8	1227.4	1221.5	1215.6	1221.5
40°	1124.4	1124.9	1125.3	1118.8	1109.8	1100.7	1091.3	1082.0	1073.0	1064.1	1073.0
42.5°	952.6	962.1	971.6	967.6	959.0	947.2	932.2	920.0	916.3	912.6	916.3
45°	618.8	660.6	702.5	717.9	724.5	719.3	702.4	677.6	629.1	580.7	629.1
47.5°	311.0	363.1	415.2	451.2	482.0	473.2	425.0	376.0	324.8	273.5	324.8
50°	175.6	206.6	237.6	285.9	340.0	331.1	259.2	200.9	183.5	166.1	183.5
52.5°	117.2	130.9	144.7	183.6	230.9	227.7	174.2	131.7	121.8	111.9	121.8
55°	59.2	63.0	66.8	83.9	105.5	105.1	82.5	64.9	62.1	59.2	62.1
57.5°	20.1	25.2	30.3	37.9	46.3	46.6	38.6	31.4	26.8	22.2	26.8
60°	3.2	7.9	12.6	18.7	25.3	24.6	16.6	9.5	5.3	1.1	5.3
62.5°	0.6	2.0	3.3	8.3	14.5	14.3	7.8	2.7	1.4	0.2	1.4
65°	0.0	0.0	0.0	0.4	0.8	0.8	0.4	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.4	1.0	1.7	2.2	2.6	2.8	2.8	2.9	3.1	3.1	3.1
90°	2.1	4.9	8.3	11.1	13.2	13.9	13.9	14.6	15.3	15.3	15.3
92.5°	7.7	12.1	12.2	12.2	14.9	16.1	17.2	17.4	18.1	18.1	18.1
95°	21.6	23.6	35.5	34.8	23.6	18.8	16.0	16.0	16.0	16.0	16.0
97.5°	41.2	44.2	46.2	61.9	65.4	63.2	51.5	43.3	38.7	36.6	38.7
100°	58.4	59.8	64.0	64.7	82.1	98.8	90.4	80.0	76.5	74.4	76.5
102.5°	75.7	76.5	82.9	85.8	89.9	99.3	128.3	125.1	122.7	122.3	122.7
105°	101.5	102.2	114.1	119.6	122.4	122.4	121.7	135.6	157.9	162.7	157.9
107.5°	129.2	132.4	146.3	161.2	164.4	165.3	161.6	159.5	158.7	159.3	158.7
110°	148.1	153.0	169.7	188.5	193.4	194.7	193.4	191.3	189.9	189.9	189.9



TEST NUMBER: P1427512

CATALOG NUMBER: SQ2W-BBM-K-050U-075D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	166.5	173.6	192.5	214.1	222.3	226.5	223.4	221.9	220.5	221.6	220.5
115°	194.7	205.2	230.2	252.5	269.2	271.2	270.6	270.6	269.9	269.9	269.9
117.5°	220.9	237.6	265.7	291.6	310.9	316.5	319.2	318.4	317.6	319.0	317.6
120°	239.3	258.7	290.7	319.9	338.7	347.1	349.8	348.4	349.8	348.4	349.8
122.5°	258.7	282.7	314.1	344.4	366.5	376.0	379.3	379.6	379.9	379.1	379.9
125°	287.9	317.2	354.0	385.3	408.3	419.4	422.2	422.9	424.3	427.7	424.3
127.5°	317.4	350.5	391.0	421.2	444.7	458.2	462.5	464.0	467.0	468.5	467.0
130°	338.0	375.6	416.6	445.1	468.1	482.7	490.3	492.4	495.9	495.2	495.9
132.5°	359.7	398.9	440.5	470.2	491.4	507.2	513.7	519.7	520.9	521.9	520.9
135°	391.6	434.0	475.7	504.9	525.1	540.4	548.8	554.3	557.8	559.9	557.8
137.5°	425.1	469.9	509.9	536.0	556.3	569.5	578.9	584.8	588.4	590.1	588.4
140°	447.9	491.0	530.0	557.1	575.2	588.4	596.7	603.7	607.9	607.9	607.9
142.5°	469.6	512.2	550.0	577.1	593.0	605.1	614.0	619.3	624.0	624.0	624.0
145°	500.1	542.5	577.3	604.4	617.6	628.7	638.5	642.6	645.4	645.4	645.4
147.5°	531.9	569.5	601.2	627.2	638.3	651.4	659.1	662.4	665.9	664.3	665.9
150°	550.8	585.6	616.2	640.6	651.7	664.2	671.9	674.6	678.1	676.0	678.1
152.5°	569.2	602.3	630.1	652.8	662.3	674.8	683.5	686.3	688.7	687.2	688.7
155°	594.0	623.2	648.9	669.8	678.1	689.9	698.3	701.8	704.5	701.1	704.5
157.5°	616.1	641.3	663.7	682.8	691.8	701.9	709.7	714.0	716.8	715.3	716.8
160°	629.4	652.4	672.6	690.6	699.0	708.0	716.4	721.2	724.0	721.9	724.0
162.5°	640.6	661.3	680.3	696.8	704.0	711.9	721.9	726.2	729.0	726.4	729.0
165°	656.6	673.3	689.9	703.9	710.1	716.4	726.8	731.7	733.8	731.0	733.8
167.5°	668.7	681.5	695.0	706.9	711.5	717.6	728.1	732.1	734.7	731.3	734.7
170°	675.3	686.5	698.3	708.0	711.5	717.1	727.5	731.0	733.1	729.6	733.1
172.5°	680.9	689.2	698.8	707.5	709.3	713.7	723.6	727.1	728.6	725.7	728.6
175°	686.5	691.3	698.3	703.9	703.2	705.9	714.3	717.1	719.9	715.7	719.9
177.5°	689.1	691.3	693.6	696.9	694.7	694.7	700.8	702.5	703.0	700.8	703.0
180°	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6



TEST NUMBER: P1427512

CATALOG NUMBER: SQ2W-BBM-K-050U-075D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2114.5	2114.5	2114.5	2114.5	2114.5	2114.5	2114.5	2114.5	2114.5	2114.5	2114.5
2.5°	2119.9	2113.9	2105.3	2104.7	2112.2	2118.5	2121.1	2123.8	2121.1	2118.5	2112.2
5°	2128.0	2118.7	2106.0	2103.7	2111.7	2118.2	2120.6	2122.9	2120.6	2118.2	2111.7
7.5°	2128.3	2121.0	2110.6	2108.2	2113.8	2118.5	2120.1	2121.7	2120.1	2118.5	2113.8
10°	2126.6	2119.1	2108.2	2107.5	2116.9	2124.1	2124.6	2125.1	2124.6	2124.1	2116.9
12.5°	2118.5	2113.1	2104.6	2107.6	2122.3	2132.6	2129.7	2126.7	2129.7	2132.6	2122.3
15°	2091.8	2092.3	2090.9	2101.2	2123.3	2137.9	2129.9	2121.9	2129.9	2137.9	2123.3
17.5°	2043.6	2049.6	2054.8	2072.1	2101.5	2120.7	2109.5	2098.2	2109.5	2120.7	2101.5
20°	2001.5	2010.1	2019.0	2039.7	2072.2	2093.2	2080.0	2066.9	2080.0	2093.2	2072.2
22.5°	1953.7	1963.6	1974.8	1995.8	2026.7	2046.9	2034.9	2022.9	2034.9	2046.9	2026.7
25°	1874.6	1881.8	1890.2	1909.5	1939.6	1960.2	1952.2	1944.2	1952.2	1960.2	1939.6
27.5°	1762.2	1771.2	1781.7	1798.3	1820.8	1837.2	1834.9	1832.7	1834.9	1837.2	1820.8
30°	1680.9	1691.4	1702.7	1716.8	1733.7	1746.4	1746.4	1746.4	1746.4	1746.4	1733.7
32.5°	1586.1	1597.4	1609.8	1622.1	1634.1	1643.4	1644.5	1645.7	1644.5	1643.4	1634.1
35°	1425.2	1436.1	1448.3	1459.6	1469.9	1476.4	1471.2	1466.1	1471.2	1476.4	1469.9
37.5°	1227.4	1238.8	1251.9	1262.4	1270.2	1275.6	1273.6	1271.6	1273.6	1275.6	1270.2
40°	1082.0	1091.3	1100.7	1109.8	1118.8	1125.3	1124.9	1124.4	1124.9	1125.3	1118.8
42.5°	920.0	932.2	947.2	959.0	967.6	971.6	962.1	952.6	962.1	971.6	967.6
45°	677.6	702.4	719.3	724.5	717.9	702.5	660.6	618.8	660.6	702.5	717.9
47.5°	376.0	425.0	473.2	482.0	451.2	415.2	363.1	311.0	363.1	415.2	451.2
50°	200.9	259.2	331.1	340.0	285.9	237.6	206.6	175.6	206.6	237.6	285.9
52.5°	131.7	174.2	227.7	230.9	183.6	144.7	130.9	117.2	130.9	144.7	183.6
55°	64.9	82.5	105.1	105.5	83.9	66.8	63.0	59.2	63.0	66.8	83.9
57.5°	31.4	38.6	46.6	46.3	37.9	30.3	25.2	20.1	25.2	30.3	37.9
60°	9.5	16.6	24.6	25.3	18.7	12.6	7.9	3.2	7.9	12.6	18.7
62.5°	2.7	7.8	14.3	14.5	8.3	3.3	2.0	0.6	2.0	3.3	8.3
65°	0.0	0.4	0.8	0.8	0.4	0.0	0.0	0.0	0.0	0.0	0.4
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	2.9	2.8	2.8	2.6	2.2	1.7	1.0	0.4	1.0	1.5	2.5
90°	14.6	13.9	13.9	13.2	11.1	8.3	4.9	2.1	4.9	7.7	12.5
92.5°	17.4	17.2	16.1	14.9	12.2	12.2	12.1	7.7	13.2	18.8	27.0
95°	16.0	16.0	18.8	23.6	34.8	35.5	23.6	21.6	30.6	43.1	54.2
97.5°	43.3	51.5	63.2	65.4	61.9	46.2	44.2	41.2	56.1	68.4	86.4
100°	80.0	90.4	98.8	82.1	64.7	64.0	59.8	58.4	74.4	86.2	103.6
102.5°	125.1	128.3	99.3	89.9	85.8	82.9	76.5	75.7	91.7	107.9	122.5
105°	135.6	121.7	122.4	122.4	119.6	114.1	102.2	101.5	119.6	138.4	156.5
107.5°	159.5	161.6	165.3	164.4	161.2	146.3	132.4	129.2	145.5	168.0	187.9
110°	191.3	193.4	194.7	193.4	188.5	169.7	153.0	148.1	162.7	186.4	208.0



TEST NUMBER: P1427512

CATALOG NUMBER: SQ2W-BBM-K-050U-075D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	221.9	223.4	226.5	222.3	214.1	192.5	173.6	166.5	181.1	205.3	227.4
115°	270.6	270.6	271.2	269.2	252.5	230.2	205.2	194.7	207.3	229.5	253.9
117.5°	318.4	319.2	316.5	310.9	291.6	265.7	237.6	220.9	230.8	254.3	279.3
120°	348.4	349.8	347.1	338.7	319.9	290.7	258.7	239.3	246.9	269.9	294.9
122.5°	379.6	379.3	376.0	366.5	344.4	314.1	282.7	258.7	261.9	283.2	307.7
125°	422.9	422.2	419.4	408.3	385.3	354.0	317.2	287.9	283.8	301.9	326.9
127.5°	464.0	462.5	458.2	444.7	421.2	391.0	350.5	317.4	308.1	319.5	342.5
130°	492.4	490.3	482.7	468.1	445.1	416.6	375.6	338.0	324.8	331.8	351.9
132.5°	519.7	513.7	507.2	491.4	470.2	440.5	398.9	359.7	341.5	344.6	360.3
135°	554.3	548.8	540.4	525.1	504.9	475.7	434.0	391.6	366.5	363.8	372.8
137.5°	584.8	578.9	569.5	556.3	536.0	509.9	469.9	425.1	393.5	384.2	387.7
140°	603.7	596.7	588.4	575.2	557.1	530.0	491.0	447.9	412.4	399.2	397.1
142.5°	619.3	614.0	605.1	593.0	577.1	550.0	512.2	469.6	431.9	414.8	409.9
145°	642.6	638.5	628.7	617.6	604.4	577.3	542.5	500.1	462.5	440.3	429.8
147.5°	662.4	659.1	651.4	638.3	627.2	601.2	569.5	531.9	493.4	465.9	452.4
150°	674.6	671.9	664.2	651.7	640.6	616.2	585.6	550.8	514.0	484.8	467.4
152.5°	686.3	683.5	674.8	662.3	652.8	630.1	602.3	569.2	531.8	502.6	484.6
155°	701.8	698.3	689.9	678.1	669.8	648.9	623.2	594.0	562.0	531.4	511.2
157.5°	714.0	709.7	701.9	691.8	682.8	663.7	641.3	616.1	588.1	558.9	538.3
160°	721.2	716.4	708.0	699.0	690.6	672.6	652.4	629.4	603.7	577.3	555.0
162.5°	726.2	721.9	711.9	704.0	696.8	680.3	661.3	640.6	617.6	594.5	573.9
165°	731.7	726.8	716.4	710.1	703.9	689.9	673.3	656.6	637.1	618.3	601.6
167.5°	732.1	728.1	717.6	711.5	706.9	695.0	681.5	668.7	653.5	638.8	624.8
170°	731.0	727.5	717.1	711.5	708.0	698.3	686.5	675.3	663.5	651.0	639.9
172.5°	727.1	723.6	713.7	709.3	707.5	698.8	689.2	680.9	670.7	661.6	652.7
175°	717.1	714.3	705.9	703.2	703.9	698.3	691.3	686.5	680.2	674.6	669.8
177.5°	702.5	700.8	694.7	694.7	696.9	693.6	691.3	689.1	686.3	684.7	683.0
180°	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6



TEST NUMBER: P1427512

CATALOG NUMBER: SQ2W-BBM-K-050U-075D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2114.5	2114.5	2114.5	2114.5	2114.5	2114.5	2114.5	2114.5	2114.5	2114.5	2114.5
2.5°	2104.7	2105.3	2113.9	2119.9	2118.0	2116.2	2118.0	2119.9	2113.9	2105.3	2104.7
5°	2103.7	2106.0	2118.7	2128.0	2127.0	2126.1	2127.0	2128.0	2118.7	2106.0	2103.7
7.5°	2108.2	2110.6	2121.0	2128.3	2125.9	2123.6	2125.9	2128.3	2121.0	2110.6	2108.2
10°	2107.5	2108.2	2119.1	2126.6	2124.2	2121.9	2124.2	2126.6	2119.1	2108.2	2107.5
12.5°	2107.6	2104.6	2113.1	2118.5	2114.3	2110.0	2114.3	2118.5	2113.1	2104.6	2107.6
15°	2101.2	2090.9	2092.3	2091.8	2085.7	2079.6	2085.7	2091.8	2092.3	2090.9	2101.2
17.5°	2072.1	2054.8	2049.6	2043.6	2034.9	2026.3	2034.9	2043.6	2049.6	2054.8	2072.1
20°	2039.7	2019.0	2010.1	2001.5	1994.0	1986.5	1994.0	2001.5	2010.1	2019.0	2039.7
22.5°	1995.8	1974.8	1963.6	1953.7	1947.7	1941.6	1947.7	1953.7	1963.6	1974.8	1995.8
25°	1909.5	1890.2	1881.8	1874.6	1871.3	1868.0	1871.3	1874.6	1881.8	1890.2	1909.5
27.5°	1798.3	1781.7	1771.2	1762.2	1758.0	1753.8	1758.0	1762.2	1771.2	1781.7	1798.3
30°	1716.8	1702.7	1691.4	1680.9	1672.9	1664.9	1672.9	1680.9	1691.4	1702.7	1716.8
32.5°	1622.1	1609.8	1597.4	1586.1	1578.1	1570.1	1578.1	1586.1	1597.4	1609.8	1622.1
35°	1459.6	1448.3	1436.1	1425.2	1418.1	1411.1	1418.1	1425.2	1436.1	1448.3	1459.6
37.5°	1262.4	1251.9	1238.8	1227.4	1221.5	1215.6	1221.5	1227.4	1238.8	1251.9	1262.4
40°	1109.8	1100.7	1091.3	1082.0	1073.0	1064.1	1073.0	1082.0	1091.3	1100.7	1109.8
42.5°	959.0	947.2	932.2	920.0	916.3	912.6	916.3	920.0	932.2	947.2	959.0
45°	724.5	719.3	702.4	677.6	629.1	580.7	629.1	677.6	702.4	719.3	724.5
47.5°	482.0	473.2	425.0	376.0	324.8	273.5	324.8	376.0	425.0	473.2	482.0
50°	340.0	331.1	259.2	200.9	183.5	166.1	183.5	200.9	259.2	331.1	340.0
52.5°	230.9	227.7	174.2	131.7	121.8	111.9	121.8	131.7	174.2	227.7	230.9
55°	105.5	105.1	82.5	64.9	62.1	59.2	62.1	64.9	82.5	105.1	105.5
57.5°	46.3	46.6	38.6	31.4	26.8	22.2	26.8	31.4	38.6	46.6	46.3
60°	25.3	24.6	16.6	9.5	5.3	1.1	5.3	9.5	16.6	24.6	25.3
62.5°	14.5	14.3	7.8	2.7	1.4	0.2	1.4	2.7	7.8	14.3	14.5
65°	0.8	0.8	0.4	0.0	0.0	0.0	0.0	0.4	0.8	0.8	0.8
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	3.2	4.2	5.1	5.7	6.3	6.0	6.3	5.7	5.1	4.2	3.2
90°	16.0	20.9	25.7	28.5	31.3	29.9	31.3	28.5	25.7	20.9	16.0
92.5°	32.1	40.3	46.3	51.3	53.6	53.3	53.6	51.3	46.3	40.3	32.1
95°	64.7	74.4	84.2	91.1	95.3	93.9	95.3	91.1	84.2	74.4	64.7
97.5°	99.7	112.8	123.7	130.2	134.4	137.2	134.4	130.2	123.7	112.8	99.7
100°	123.1	135.6	148.1	155.8	162.7	165.5	162.7	155.8	148.1	135.6	123.1
102.5°	142.0	158.4	172.1	180.3	186.1	188.9	186.1	180.3	172.1	158.4	142.0
105°	173.2	190.6	205.2	215.6	221.9	224.0	221.9	215.6	205.2	190.6	173.2
107.5°	204.3	222.3	235.8	247.3	255.0	259.4	255.0	247.3	235.8	222.3	204.3
110°	228.8	243.4	258.0	268.5	276.1	278.9	276.1	268.5	258.0	243.4	228.8



TEST NUMBER: P1427512

CATALOG NUMBER: SQ2W-BBM-K-050U-075D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	249.4	265.7	280.3	290.7	299.5	303.4	299.5	290.7	280.3	265.7	249.4
115°	278.2	299.8	313.0	322.7	329.0	332.5	329.0	322.7	313.0	299.8	278.2
117.5°	302.1	324.7	339.1	346.6	349.6	352.1	349.6	346.6	339.1	324.7	302.1
120°	317.2	338.0	354.7	364.4	367.9	369.3	367.9	364.4	354.7	338.0	317.2
122.5°	331.1	350.8	366.9	378.9	384.6	386.0	384.6	378.9	366.9	350.8	331.1
125°	350.5	369.3	386.0	397.8	404.1	407.6	404.1	397.8	386.0	369.3	350.5
127.5°	367.5	387.8	403.1	413.8	419.9	422.7	419.9	413.8	403.1	387.8	367.5
130°	377.0	397.8	413.1	425.0	430.5	433.3	430.5	425.0	413.1	397.8	377.0
132.5°	384.2	406.2	422.0	432.7	438.9	441.6	438.9	432.7	422.0	406.2	384.2
135°	393.0	415.9	432.6	443.0	448.6	451.4	448.6	443.0	432.6	415.9	393.0
137.5°	400.6	421.5	438.9	449.9	454.9	456.7	454.9	449.9	438.9	421.5	400.6
140°	406.2	424.3	441.6	452.1	457.6	458.3	457.6	452.1	441.6	424.3	406.2
142.5°	413.4	427.6	442.8	453.2	458.8	460.0	458.8	453.2	442.8	427.6	413.4
145°	426.3	434.7	445.1	454.9	459.7	461.1	459.7	454.9	445.1	434.7	426.3
147.5°	442.6	445.3	450.7	457.1	461.8	462.8	461.8	457.1	445.3	442.6	442.6
150°	454.9	454.2	456.3	460.4	464.6	463.9	464.6	460.4	456.3	454.2	454.9
152.5°	468.8	464.7	464.6	466.5	468.5	468.4	468.5	466.5	464.6	464.7	468.8
155°	492.4	484.8	480.6	479.2	479.2	478.5	479.2	479.2	480.6	484.8	492.4
157.5°	518.4	507.7	501.5	498.1	497.1	495.6	497.1	498.1	501.5	507.7	518.4
160°	536.2	524.4	518.2	512.6	510.5	508.4	510.5	512.6	518.2	524.4	536.2
162.5°	552.9	541.7	534.8	529.8	527.8	524.6	527.8	529.8	534.8	541.7	552.9
165°	580.1	568.2	560.6	556.4	553.6	550.8	553.6	556.4	560.6	568.2	580.1
167.5°	607.2	594.2	589.2	584.5	581.9	576.9	581.9	584.5	589.2	594.2	607.2
170°	623.9	612.0	609.3	605.1	600.2	594.7	600.2	605.1	609.3	612.0	623.9
172.5°	638.3	630.4	627.6	623.5	621.9	617.5	621.9	623.5	627.6	630.4	638.3
175°	659.3	653.1	653.1	652.4	650.3	646.1	650.3	652.4	653.1	653.1	659.3
177.5°	676.9	673.5	675.8	675.8	675.2	671.3	675.2	675.8	675.8	673.5	676.9
180°	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6



TEST NUMBER: P1427512

CATALOG NUMBER: SQ2W-BBM-K-050U-075D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	2114.5	2114.5	2114.5	2114.5
2.5°	2112.2	2118.5	2121.1	2123.8
5°	2111.7	2118.2	2120.6	2122.9
7.5°	2113.8	2118.5	2120.1	2121.7
10°	2116.9	2124.1	2124.6	2125.1
12.5°	2122.3	2132.6	2129.7	2126.7
15°	2123.3	2137.9	2129.9	2121.9
17.5°	2101.5	2120.7	2109.5	2098.2
20°	2072.2	2093.2	2080.0	2066.9
22.5°	2026.7	2046.9	2034.9	2022.9
25°	1939.6	1960.2	1952.2	1944.2
27.5°	1820.8	1837.2	1834.9	1832.7
30°	1733.7	1746.4	1746.4	1746.4
32.5°	1634.1	1643.4	1644.5	1645.7
35°	1469.9	1476.4	1471.2	1466.1
37.5°	1270.2	1275.6	1273.6	1271.6
40°	1118.8	1125.3	1124.9	1124.4
42.5°	967.6	971.6	962.1	952.6
45°	717.9	702.5	660.6	618.8
47.5°	451.2	415.2	363.1	311.0
50°	285.9	237.6	206.6	175.6
52.5°	183.6	144.7	130.9	117.2
55°	83.9	66.8	63.0	59.2
57.5°	37.9	30.3	25.2	20.1
60°	18.7	12.6	7.9	3.2
62.5°	8.3	3.3	2.0	0.6
65°	0.4	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0
87.5°	2.5	1.5	1.0	0.4
90°	12.5	7.7	4.9	2.1
92.5°	27.0	18.8	13.2	7.7
95°	54.2	43.1	30.6	21.6
97.5°	86.4	68.4	56.1	41.2
100°	103.6	86.2	74.4	58.4
102.5°	122.5	107.9	91.7	75.7
105°	156.5	138.4	119.6	101.5
107.5°	187.9	168.0	145.5	129.2
110°	208.0	186.4	162.7	148.1



TEST NUMBER: P1427512

CATALOG NUMBER: SQ2W-BBM-K-050U-075D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	227.4	205.3	181.1	166.5
115°	253.9	229.5	207.3	194.7
117.5°	279.3	254.3	230.8	220.9
120°	294.9	269.9	246.9	239.3
122.5°	307.7	283.2	261.9	258.7
125°	326.9	301.9	283.8	287.9
127.5°	342.5	319.5	308.1	317.4
130°	351.9	331.8	324.8	338.0
132.5°	360.3	344.6	341.5	359.7
135°	372.8	363.8	366.5	391.6
137.5°	387.7	384.2	393.5	425.1
140°	397.1	399.2	412.4	447.9
142.5°	409.9	414.8	431.9	469.6
145°	429.8	440.3	462.5	500.1
147.5°	452.4	465.9	493.4	531.9
150°	467.4	484.8	514.0	550.8
152.5°	484.6	502.6	531.8	569.2
155°	511.2	531.4	562.0	594.0
157.5°	538.3	558.9	588.1	616.1
160°	555.0	577.3	603.7	629.4
162.5°	573.9	594.5	617.6	640.6
165°	601.6	618.3	637.1	656.6
167.5°	624.8	638.8	653.5	668.7
170°	639.9	651.0	663.5	675.3
172.5°	652.7	661.6	670.7	680.9
175°	669.8	674.6	680.2	686.5
177.5°	683.0	684.7	686.3	689.1
180°	688.6	688.6	688.6	688.6



TEST NUMBER: P1427512  
 CATALOG NUMBER: SQ2W-BBM-K-050U-075D-L940-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.57	1.69	0.00	0.00	0.02	0.78	1.89
	3H	0.00	0.00	0.00	0.30	1.44	0.00	0.00	0.00	0.51	1.65
	4H	0.00	0.00	0.00	0.16	1.31	0.00	0.00	0.00	0.37	1.52
	6H	0.00	0.00	0.00	0.01	1.17	0.00	0.00	0.00	0.21	1.38
	8H	0.00	0.00	0.00	0.00	1.09	0.00	0.00	0.00	0.14	1.30
	12H	0.00	0.00	0.00	0.00	1.02	0.00	0.00	0.00	0.04	1.23
4H	2H	0.00	0.00	0.00	0.17	1.32	0.00	0.00	0.00	0.38	1.53
	3H	0.00	0.00	0.00	0.00	1.05	0.00	0.00	0.00	0.10	1.26
	4H	0.00	0.00	0.00	0.00	0.92	0.00	0.00	0.00	0.00	1.12
	6H	0.00	0.00	0.00	0.00	0.76	0.00	0.00	0.00	0.00	0.97
	8H	0.00	0.00	0.00	0.00	0.67	0.00	0.00	0.00	0.00	0.88
	12H	0.00	0.00	0.00	0.00	0.59	0.00	0.00	0.00	0.00	0.79
8H	4H	0.00	0.00	0.00	0.00	0.67	0.00	0.00	0.00	0.00	0.88
	6H	0.00	0.00	0.00	0.00	0.53	0.00	0.00	0.00	0.00	0.74
	8H	0.00	0.00	0.00	0.00	0.44	0.00	0.00	0.00	0.00	0.65
	12H	0.00	0.00	0.00	0.00	0.38	0.00	0.00	0.00	0.00	0.59
12H	4H	0.00	0.00	0.00	0.00	0.59	0.00	0.00	0.00	0.00	0.79
	6H	0.00	0.00	0.00	0.00	0.44	0.00	0.00	0.00	0.00	0.65
	8H	0.00	0.00	0.00	0.00	0.38	0.00	0.00	0.00	0.00	0.59