

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427515

Luminaire Tested: SQ2W-BBM-K-050U-100D-L940-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2024
Report Number: P1427515
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2104-222-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-BBM-K-050U-100D-L940-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - BLACK DISCREET BAFFLE, MEDIUM 80-DEGREE OPTIC
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6236.2 lumens
Efficiency: N/A
Efficacy: 117.7 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.17 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 53
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1427515

CATALOG NUMBER: SQ2W-BBM-K-050U-100D-L940-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1427515

CATALOG NUMBER: SQ2W-BBM-K-050U-100D-L940-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	68		
1	104	101	98	95	99	96	93	91	86	84	82	77	75	74	68	67	66	62		
2	97	92	87	83	92	87	83	79	79	75	73	71	68	66	64	62	60	57		
3	91	83	77	72	86	79	74	70	72	68	65	65	62	60	59	57	55	52		
4	85	76	69	64	80	72	67	62	66	62	58	60	57	54	55	52	50	47		
5	79	69	62	57	75	66	60	55	61	56	52	56	52	49	51	48	45	43		
6	74	63	56	51	70	61	55	50	56	51	47	51	47	44	47	44	42	39		
7	69	58	51	46	66	56	50	45	52	47	43	48	44	40	44	41	38	36		
8	65	54	47	42	62	52	45	41	48	43	39	44	40	37	41	38	35	33		
9	61	50	43	38	58	48	42	38	45	39	36	41	37	34	38	35	32	30		
10	57	46	40	35	54	45	39	34	42	36	33	39	34	31	36	32	30	28		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	45614	45614	45614	45614
5°	45972	46040	45972	46040
10°	46549	46480	46549	46480
15°	47389	46443	47389	46443
20°	47449	45604	47449	45604
25°	46275	44464	46275	44464
30°	43500	41472	43500	41472
35°	38608	37159	38608	37159
40°	31663	29967	31663	29967
45°	18879	17716	18879	17716
50°	5893	5574	5893	5574
55°	2227	2227	2227	2227
60°	136	45	136	45
65°	0	0	0	0
70°	0	0	0	0
75°	0	0	0	0
80°	0	0	0	0
85°	0	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 40°
 Vertical Angle: 45°
 Luminance: 22100 cd/sqm



TEST NUMBER: P1427515

CATALOG NUMBER: SQ2W-BBM-K-050U-100D-L940-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	270.1	4.3
10°-20°	791.3	12.7
20°-30°	1164.1	18.7
30°-40°	1189.8	19.1
40°-50°	685.4	11.0
50°-60°	117.9	1.9
60°-70°	4.2	0.1
70°-80°	0.0	0.0
80°-90°	3.7	0.1
90°-100°	54.8	0.9
100°-110°	159.8	2.6
110°-120°	260.8	4.2
120°-130°	330.9	5.3
130°-140°	354.1	5.7
140°-150°	330.7	5.3
150°-160°	272.1	4.4
160°-170°	182.5	2.9
170°-180°	64.8	1.0
0°-30°	2225.5	35.7
0°-40°	3415.3	54.8
0°-60°	4218.7	67.6
0°-90°	4226.6	67.8
90°-120°	475.4	7.6
90°-150°	1491.1	23.9
90°-180°	2010.0	32.2
0°-180°	6236.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2825	2825	2825	2825	2825	
5°	2836	2841	2836	2841	2836	271
15°	2835	2778	2835	2778	2835	798
25°	2598	2496	2598	2496	2598	1185
35°	1959	1885	1959	1885	1959	1210
45°	827	776	827	776	827	640
55°	79	79	79	79	79	84
65°	0	0	0	0	0	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	2	15	2	30	2	2
95°	22	16	22	94	22	26
105°	102	163	102	224	102	108
115°	195	270	195	332	195	192
125°	288	428	288	408	288	258
135°	392	560	392	451	392	303
145°	500	645	500	461	500	313
155°	594	701	594	478	594	273
165°	657	731	657	551	657	185
175°	686	716	686	646	686	65
180°	689	689	689	689	689	



TEST NUMBER: P1427515

CATALOG NUMBER: SQ2W-BBM-K-050U-100D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2
2.5°	2837.6	2834.1	2830.6	2822.2	2812.1	2812.9	2824.4	2832.5	2830.0	2827.4	2830.0
5°	2836.5	2833.3	2830.2	2821.4	2810.7	2813.9	2830.8	2843.2	2842.0	2840.7	2842.0
7.5°	2834.8	2832.7	2830.5	2824.3	2816.8	2820.0	2833.9	2843.6	2840.5	2837.3	2840.5
10°	2839.3	2838.7	2838.1	2828.5	2815.9	2816.9	2831.3	2841.4	2838.2	2835.1	2838.2
12.5°	2841.6	2845.5	2849.4	2835.6	2816.0	2812.0	2823.4	2830.5	2824.9	2819.2	2824.9
15°	2835.1	2845.7	2856.4	2837.0	2807.4	2793.6	2795.5	2794.9	2786.7	2778.5	2786.7
17.5°	2803.4	2818.5	2833.6	2807.8	2768.5	2745.4	2738.5	2730.4	2718.9	2707.3	2718.9
20°	2761.6	2779.2	2796.8	2768.6	2725.3	2697.7	2685.7	2674.3	2664.2	2654.2	2664.2
22.5°	2702.8	2718.9	2734.9	2708.0	2666.6	2638.5	2623.5	2610.3	2602.3	2594.2	2602.3
25°	2597.6	2608.3	2619.0	2591.5	2551.3	2525.6	2514.3	2504.7	2500.3	2495.9	2500.3
27.5°	2448.7	2451.7	2454.7	2432.8	2402.7	2380.6	2366.5	2354.5	2348.9	2343.2	2348.9
30°	2333.3	2333.3	2333.3	2316.4	2293.8	2274.9	2259.9	2245.9	2235.2	2224.5	2235.2
32.5°	2198.8	2197.3	2195.8	2183.4	2167.3	2150.9	2134.4	2119.3	2108.6	2097.9	2108.6
35°	1958.8	1965.7	1972.6	1964.0	1950.2	1935.1	1918.8	1904.2	1894.8	1885.3	1894.8
37.5°	1699.1	1701.7	1704.3	1697.2	1686.8	1672.7	1655.2	1640.0	1632.1	1624.2	1632.1
40°	1502.3	1503.0	1503.6	1494.8	1482.9	1470.6	1458.0	1445.6	1433.7	1421.8	1433.7
42.5°	1272.8	1285.5	1298.2	1292.8	1281.4	1265.6	1245.5	1229.2	1224.3	1219.4	1224.3
45°	826.8	882.7	938.6	959.2	967.9	961.0	938.4	905.3	840.6	775.9	840.6
47.5°	415.5	485.1	554.7	602.9	644.0	632.3	567.9	502.4	433.9	365.5	433.9
50°	234.6	276.1	317.5	382.1	454.3	442.4	346.3	268.4	245.1	221.9	245.1
52.5°	156.6	174.9	193.3	245.3	308.4	304.3	232.8	175.9	162.7	149.5	162.7
55°	79.1	84.2	89.2	112.1	141.0	140.4	110.2	86.7	82.9	79.1	82.9
57.5°	26.9	33.6	40.4	50.6	61.9	62.2	51.5	42.0	35.8	29.7	35.8
60°	4.2	10.5	16.8	25.0	33.8	32.8	22.1	12.7	7.1	1.4	7.1
62.5°	0.8	2.6	4.4	11.0	19.3	19.1	10.5	3.5	1.9	0.3	1.9
65°	0.0	0.0	0.0	0.5	1.1	1.1	0.5	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.4	1.0	1.7	2.2	2.6	2.8	2.8	2.9	3.1	3.1	3.1
90°	2.1	4.9	8.3	11.1	13.2	13.9	13.9	14.6	15.3	15.3	15.3
92.5°	7.7	12.1	12.2	12.2	14.9	16.1	17.2	17.4	18.1	18.1	18.1
95°	21.6	23.6	35.5	34.8	23.6	18.8	16.0	16.0	16.0	16.0	16.0
97.5°	41.2	44.2	46.2	61.9	65.4	63.2	51.5	43.3	38.7	36.6	38.7
100°	58.4	59.8	64.0	64.7	82.1	98.8	90.4	80.0	76.5	74.4	76.5
102.5°	75.7	76.5	82.9	85.8	89.9	99.3	128.3	125.1	122.7	122.3	122.7
105°	101.5	102.2	114.1	119.6	122.4	122.4	121.7	135.6	157.9	162.7	157.9
107.5°	129.2	132.4	146.3	161.2	164.4	165.3	161.6	159.5	158.7	159.3	158.7
110°	148.1	153.0	169.7	188.5	193.4	194.7	193.4	191.3	189.9	189.9	189.9



TEST NUMBER: P1427515

CATALOG NUMBER: SQ2W-BBM-K-050U-100D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	166.5	173.6	192.5	214.1	222.3	226.5	223.4	221.9	220.5	221.6	220.5
115°	194.7	205.2	230.2	252.5	269.2	271.2	270.6	270.6	269.9	269.9	269.9
117.5°	220.9	237.6	265.7	291.6	310.9	316.5	319.2	318.4	317.6	319.0	317.6
120°	239.3	258.7	290.7	319.9	338.7	347.1	349.8	348.4	349.8	348.4	349.8
122.5°	258.7	282.7	314.1	344.4	366.5	376.0	379.3	379.6	379.9	379.1	379.9
125°	287.9	317.2	354.0	385.3	408.3	419.4	422.2	422.9	424.3	427.7	424.3
127.5°	317.4	350.5	391.0	421.2	444.7	458.2	462.5	464.0	467.0	468.5	467.0
130°	338.0	375.6	416.6	445.1	468.1	482.7	490.3	492.4	495.9	495.2	495.9
132.5°	359.7	398.9	440.5	470.2	491.4	507.2	513.7	519.7	520.9	521.9	520.9
135°	391.6	434.0	475.7	504.9	525.1	540.4	548.8	554.3	557.8	559.9	557.8
137.5°	425.1	469.9	509.9	536.0	556.3	569.5	578.9	584.8	588.4	590.1	588.4
140°	447.9	491.0	530.0	557.1	575.2	588.4	596.7	603.7	607.9	607.9	607.9
142.5°	469.6	512.2	550.0	577.1	593.0	605.1	614.0	619.3	624.0	624.0	624.0
145°	500.1	542.5	577.3	604.4	617.6	628.7	638.5	642.6	645.4	645.4	645.4
147.5°	531.9	569.5	601.2	627.2	638.3	651.4	659.1	662.4	665.9	664.3	665.9
150°	550.8	585.6	616.2	640.6	651.7	664.2	671.9	674.6	678.1	676.0	678.1
152.5°	569.2	602.3	630.1	652.8	662.3	674.8	683.5	686.3	688.7	687.2	688.7
155°	594.0	623.2	648.9	669.8	678.1	689.9	698.3	701.8	704.5	701.1	704.5
157.5°	616.1	641.3	663.7	682.8	691.8	701.9	709.7	714.0	716.8	715.3	716.8
160°	629.4	652.4	672.6	690.6	699.0	708.0	716.4	721.2	724.0	721.9	724.0
162.5°	640.6	661.3	680.3	696.8	704.0	711.9	721.9	726.2	729.0	726.4	729.0
165°	656.6	673.3	689.9	703.9	710.1	716.4	726.8	731.7	733.8	731.0	733.8
167.5°	668.7	681.5	695.0	706.9	711.5	717.6	728.1	732.1	734.7	731.3	734.7
170°	675.3	686.5	698.3	708.0	711.5	717.1	727.5	731.0	733.1	729.6	733.1
172.5°	680.9	689.2	698.8	707.5	709.3	713.7	723.6	727.1	728.6	725.7	728.6
175°	686.5	691.3	698.3	703.9	703.2	705.9	714.3	717.1	719.9	715.7	719.9
177.5°	689.1	691.3	693.6	696.9	694.7	694.7	700.8	702.5	703.0	700.8	703.0
180°	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6



TEST NUMBER: P1427515

CATALOG NUMBER: SQ2W-BBM-K-050U-100D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2
2.5°	2832.5	2824.4	2812.9	2812.1	2822.2	2830.6	2834.1	2837.6	2834.1	2830.6	2822.2
5°	2843.2	2830.8	2813.9	2810.7	2821.4	2830.2	2833.3	2836.5	2833.3	2830.2	2821.4
7.5°	2843.6	2833.9	2820.0	2816.8	2824.3	2830.5	2832.7	2834.8	2832.7	2830.5	2824.3
10°	2841.4	2831.3	2816.9	2815.9	2828.5	2838.1	2838.7	2839.3	2838.7	2838.1	2828.5
12.5°	2830.5	2823.4	2812.0	2816.0	2835.6	2849.4	2845.5	2841.6	2845.5	2849.4	2835.6
15°	2794.9	2795.5	2793.6	2807.4	2837.0	2856.4	2845.7	2835.1	2845.7	2856.4	2837.0
17.5°	2730.4	2738.5	2745.4	2768.5	2807.8	2833.6	2818.5	2803.4	2818.5	2833.6	2807.8
20°	2674.3	2685.7	2697.7	2725.3	2768.6	2796.8	2779.2	2761.6	2779.2	2796.8	2768.6
22.5°	2610.3	2623.5	2638.5	2666.6	2708.0	2734.9	2718.9	2702.8	2718.9	2734.9	2708.0
25°	2504.7	2514.3	2525.6	2551.3	2591.5	2619.0	2608.3	2597.6	2608.3	2619.0	2591.5
27.5°	2354.5	2366.5	2380.6	2402.7	2432.8	2454.7	2451.7	2448.7	2451.7	2454.7	2432.8
30°	2245.9	2259.9	2274.9	2293.8	2316.4	2333.3	2333.3	2333.3	2333.3	2333.3	2316.4
32.5°	2119.3	2134.4	2150.9	2167.3	2183.4	2195.8	2197.3	2198.8	2197.3	2195.8	2183.4
35°	1904.2	1918.8	1935.1	1950.2	1964.0	1972.6	1965.7	1958.8	1965.7	1972.6	1964.0
37.5°	1640.0	1655.2	1672.7	1686.8	1697.2	1704.3	1701.7	1699.1	1701.7	1704.3	1697.2
40°	1445.6	1458.0	1470.6	1482.9	1494.8	1503.6	1503.0	1502.3	1503.0	1503.6	1494.8
42.5°	1229.2	1245.5	1265.6	1281.4	1292.8	1298.2	1285.5	1272.8	1285.5	1298.2	1292.8
45°	905.3	938.4	961.0	967.9	959.2	938.6	882.7	826.8	882.7	938.6	959.2
47.5°	502.4	567.9	632.3	644.0	602.9	554.7	485.1	415.5	485.1	554.7	602.9
50°	268.4	346.3	442.4	454.3	382.1	317.5	276.1	234.6	276.1	317.5	382.1
52.5°	175.9	232.8	304.3	308.4	245.3	193.3	174.9	156.6	174.9	193.3	245.3
55°	86.7	110.2	140.4	141.0	112.1	89.2	84.2	79.1	84.2	89.2	112.1
57.5°	42.0	51.5	62.2	61.9	50.6	40.4	33.6	26.9	33.6	40.4	50.6
60°	12.7	22.1	32.8	33.8	25.0	16.8	10.5	4.2	10.5	16.8	25.0
62.5°	3.5	10.5	19.1	19.3	11.0	4.4	2.6	0.8	2.6	4.4	11.0
65°	0.0	0.5	1.1	1.1	0.5	0.0	0.0	0.0	0.0	0.0	0.5
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	2.9	2.8	2.8	2.6	2.2	1.7	1.0	0.4	1.0	1.5	2.5
90°	14.6	13.9	13.9	13.2	11.1	8.3	4.9	2.1	4.9	7.7	12.5
92.5°	17.4	17.2	16.1	14.9	12.2	12.2	12.1	7.7	13.2	18.8	27.0
95°	16.0	16.0	18.8	23.6	34.8	35.5	23.6	21.6	30.6	43.1	54.2
97.5°	43.3	51.5	63.2	65.4	61.9	46.2	44.2	41.2	56.1	68.4	86.4
100°	80.0	90.4	98.8	82.1	64.7	64.0	59.8	58.4	74.4	86.2	103.6
102.5°	125.1	128.3	99.3	89.9	85.8	82.9	76.5	75.7	91.7	107.9	122.5
105°	135.6	121.7	122.4	122.4	119.6	114.1	102.2	101.5	119.6	138.4	156.5
107.5°	159.5	161.6	165.3	164.4	161.2	146.3	132.4	129.2	145.5	168.0	187.9
110°	191.3	193.4	194.7	193.4	188.5	169.7	153.0	148.1	162.7	186.4	208.0



TEST NUMBER: P1427515

CATALOG NUMBER: SQ2W-BBM-K-050U-100D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	221.9	223.4	226.5	222.3	214.1	192.5	173.6	166.5	181.1	205.3	227.4
115°	270.6	270.6	271.2	269.2	252.5	230.2	205.2	194.7	207.3	229.5	253.9
117.5°	318.4	319.2	316.5	310.9	291.6	265.7	237.6	220.9	230.8	254.3	279.3
120°	348.4	349.8	347.1	338.7	319.9	290.7	258.7	239.3	246.9	269.9	294.9
122.5°	379.6	379.3	376.0	366.5	344.4	314.1	282.7	258.7	261.9	283.2	307.7
125°	422.9	422.2	419.4	408.3	385.3	354.0	317.2	287.9	283.8	301.9	326.9
127.5°	464.0	462.5	458.2	444.7	421.2	391.0	350.5	317.4	308.1	319.5	342.5
130°	492.4	490.3	482.7	468.1	445.1	416.6	375.6	338.0	324.8	331.8	351.9
132.5°	519.7	513.7	507.2	491.4	470.2	440.5	398.9	359.7	341.5	344.6	360.3
135°	554.3	548.8	540.4	525.1	504.9	475.7	434.0	391.6	366.5	363.8	372.8
137.5°	584.8	578.9	569.5	556.3	536.0	509.9	469.9	425.1	393.5	384.2	387.7
140°	603.7	596.7	588.4	575.2	557.1	530.0	491.0	447.9	412.4	399.2	397.1
142.5°	619.3	614.0	605.1	593.0	577.1	550.0	512.2	469.6	431.9	414.8	409.9
145°	642.6	638.5	628.7	617.6	604.4	577.3	542.5	500.1	462.5	440.3	429.8
147.5°	662.4	659.1	651.4	638.3	627.2	601.2	569.5	531.9	493.4	465.9	452.4
150°	674.6	671.9	664.2	651.7	640.6	616.2	585.6	550.8	514.0	484.8	467.4
152.5°	686.3	683.5	674.8	662.3	652.8	630.1	602.3	569.2	531.8	502.6	484.6
155°	701.8	698.3	689.9	678.1	669.8	648.9	623.2	594.0	562.0	531.4	511.2
157.5°	714.0	709.7	701.9	691.8	682.8	663.7	641.3	616.1	588.1	558.9	538.3
160°	721.2	716.4	708.0	699.0	690.6	672.6	652.4	629.4	603.7	577.3	555.0
162.5°	726.2	721.9	711.9	704.0	696.8	680.3	661.3	640.6	617.6	594.5	573.9
165°	731.7	726.8	716.4	710.1	703.9	689.9	673.3	656.6	637.1	618.3	601.6
167.5°	732.1	728.1	717.6	711.5	706.9	695.0	681.5	668.7	653.5	638.8	624.8
170°	731.0	727.5	717.1	711.5	708.0	698.3	686.5	675.3	663.5	651.0	639.9
172.5°	727.1	723.6	713.7	709.3	707.5	698.8	689.2	680.9	670.7	661.6	652.7
175°	717.1	714.3	705.9	703.2	703.9	698.3	691.3	686.5	680.2	674.6	669.8
177.5°	702.5	700.8	694.7	694.7	696.9	693.6	691.3	689.1	686.3	684.7	683.0
180°	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6



TEST NUMBER: P1427515

CATALOG NUMBER: SQ2W-BBM-K-050U-100D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2	2825.2
2.5°	2812.1	2812.9	2824.4	2832.5	2830.0	2827.4	2830.0	2832.5	2824.4	2812.9	2812.1
5°	2810.7	2813.9	2830.8	2843.2	2842.0	2840.7	2842.0	2843.2	2830.8	2813.9	2810.7
7.5°	2816.8	2820.0	2833.9	2843.6	2840.5	2837.3	2840.5	2843.6	2833.9	2820.0	2816.8
10°	2815.9	2816.9	2831.3	2841.4	2838.2	2835.1	2838.2	2841.4	2831.3	2816.9	2815.9
12.5°	2816.0	2812.0	2823.4	2830.5	2824.9	2819.2	2824.9	2830.5	2823.4	2812.0	2816.0
15°	2807.4	2793.6	2795.5	2794.9	2786.7	2778.5	2786.7	2794.9	2795.5	2793.6	2807.4
17.5°	2768.5	2745.4	2738.5	2730.4	2718.9	2707.3	2718.9	2730.4	2738.5	2745.4	2768.5
20°	2725.3	2697.7	2685.7	2674.3	2664.2	2654.2	2664.2	2674.3	2685.7	2697.7	2725.3
22.5°	2666.6	2638.5	2623.5	2610.3	2602.3	2594.2	2602.3	2610.3	2623.5	2638.5	2666.6
25°	2551.3	2525.6	2514.3	2504.7	2500.3	2495.9	2500.3	2504.7	2514.3	2525.6	2551.3
27.5°	2402.7	2380.6	2366.5	2354.5	2348.9	2343.2	2348.9	2354.5	2366.5	2380.6	2402.7
30°	2293.8	2274.9	2259.9	2245.9	2235.2	2224.5	2235.2	2245.9	2259.9	2274.9	2293.8
32.5°	2167.3	2150.9	2134.4	2119.3	2108.6	2097.9	2108.6	2119.3	2134.4	2150.9	2167.3
35°	1950.2	1935.1	1918.8	1904.2	1894.8	1885.3	1894.8	1904.2	1918.8	1935.1	1950.2
37.5°	1686.8	1672.7	1655.2	1640.0	1632.1	1624.2	1632.1	1640.0	1655.2	1672.7	1686.8
40°	1482.9	1470.6	1458.0	1445.6	1433.7	1421.8	1433.7	1445.6	1458.0	1470.6	1482.9
42.5°	1281.4	1265.6	1245.5	1229.2	1224.3	1219.4	1224.3	1229.2	1245.5	1265.6	1281.4
45°	967.9	961.0	938.4	905.3	840.6	775.9	840.6	905.3	938.4	961.0	967.9
47.5°	644.0	632.3	567.9	502.4	433.9	365.5	433.9	502.4	567.9	632.3	644.0
50°	454.3	442.4	346.3	268.4	245.1	221.9	245.1	268.4	346.3	442.4	454.3
52.5°	308.4	304.3	232.8	175.9	162.7	149.5	162.7	175.9	232.8	304.3	308.4
55°	141.0	140.4	110.2	86.7	82.9	79.1	82.9	86.7	110.2	140.4	141.0
57.5°	61.9	62.2	51.5	42.0	35.8	29.7	35.8	42.0	51.5	62.2	61.9
60°	33.8	32.8	22.1	12.7	7.1	1.4	7.1	12.7	22.1	32.8	33.8
62.5°	19.3	19.1	10.5	3.5	1.9	0.3	1.9	3.5	10.5	19.1	19.3
65°	1.1	1.1	0.5	0.0	0.0	0.0	0.0	0.5	1.1	1.1	1.1
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	3.2	4.2	5.1	5.7	6.3	6.0	6.3	5.7	5.1	4.2	3.2
90°	16.0	20.9	25.7	28.5	31.3	29.9	31.3	28.5	25.7	20.9	16.0
92.5°	32.1	40.3	46.3	51.3	53.6	53.3	53.6	51.3	46.3	40.3	32.1
95°	64.7	74.4	84.2	91.1	95.3	93.9	95.3	91.1	84.2	74.4	64.7
97.5°	99.7	112.8	123.7	130.2	134.4	137.2	134.4	130.2	123.7	112.8	99.7
100°	123.1	135.6	148.1	155.8	162.7	165.5	162.7	155.8	148.1	135.6	123.1
102.5°	142.0	158.4	172.1	180.3	186.1	188.9	186.1	180.3	172.1	158.4	142.0
105°	173.2	190.6	205.2	215.6	221.9	224.0	221.9	215.6	205.2	190.6	173.2
107.5°	204.3	222.3	235.8	247.3	255.0	259.4	255.0	247.3	235.8	222.3	204.3
110°	228.8	243.4	258.0	268.5	276.1	278.9	276.1	268.5	258.0	243.4	228.8



TEST NUMBER: P1427515

CATALOG NUMBER: SQ2W-BBM-K-050U-100D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	249.4	265.7	280.3	290.7	299.5	303.4	299.5	290.7	280.3	265.7	249.4
115°	278.2	299.8	313.0	322.7	329.0	332.5	329.0	322.7	313.0	299.8	278.2
117.5°	302.1	324.7	339.1	346.6	349.6	352.1	349.6	346.6	339.1	324.7	302.1
120°	317.2	338.0	354.7	364.4	367.9	369.3	367.9	364.4	354.7	338.0	317.2
122.5°	331.1	350.8	366.9	378.9	384.6	386.0	384.6	378.9	366.9	350.8	331.1
125°	350.5	369.3	386.0	397.8	404.1	407.6	404.1	397.8	386.0	369.3	350.5
127.5°	367.5	387.8	403.1	413.8	419.9	422.7	419.9	413.8	403.1	387.8	367.5
130°	377.0	397.8	413.1	425.0	430.5	433.3	430.5	425.0	413.1	397.8	377.0
132.5°	384.2	406.2	422.0	432.7	438.9	441.6	438.9	432.7	422.0	406.2	384.2
135°	393.0	415.9	432.6	443.0	448.6	451.4	448.6	443.0	432.6	415.9	393.0
137.5°	400.6	421.5	438.9	449.9	454.9	456.7	454.9	449.9	438.9	421.5	400.6
140°	406.2	424.3	441.6	452.1	457.6	458.3	457.6	452.1	441.6	424.3	406.2
142.5°	413.4	427.6	442.8	453.2	458.8	460.0	458.8	453.2	442.8	427.6	413.4
145°	426.3	434.7	445.1	454.9	459.7	461.1	459.7	454.9	445.1	434.7	426.3
147.5°	442.6	445.3	450.7	457.1	461.8	462.8	461.8	457.1	445.3	442.6	442.6
150°	454.9	454.2	456.3	460.4	464.6	463.9	464.6	460.4	456.3	454.2	454.9
152.5°	468.8	464.7	464.6	466.5	468.5	468.4	468.5	466.5	464.6	464.7	468.8
155°	492.4	484.8	480.6	479.2	479.2	478.5	479.2	479.2	480.6	484.8	492.4
157.5°	518.4	507.7	501.5	498.1	497.1	495.6	497.1	498.1	501.5	507.7	518.4
160°	536.2	524.4	518.2	512.6	510.5	508.4	510.5	512.6	518.2	524.4	536.2
162.5°	552.9	541.7	534.8	529.8	527.8	524.6	527.8	529.8	534.8	541.7	552.9
165°	580.1	568.2	560.6	556.4	553.6	550.8	553.6	556.4	560.6	568.2	580.1
167.5°	607.2	594.2	589.2	584.5	581.9	576.9	581.9	584.5	589.2	594.2	607.2
170°	623.9	612.0	609.3	605.1	600.2	594.7	600.2	605.1	609.3	612.0	623.9
172.5°	638.3	630.4	627.6	623.5	621.9	617.5	621.9	623.5	627.6	630.4	638.3
175°	659.3	653.1	653.1	652.4	650.3	646.1	650.3	652.4	653.1	653.1	659.3
177.5°	676.9	673.5	675.8	675.8	675.2	671.3	675.2	675.8	675.8	673.5	676.9
180°	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6



TEST NUMBER: P1427515

CATALOG NUMBER: SQ2W-BBM-K-050U-100D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	2825.2	2825.2	2825.2	2825.2
2.5°	2822.2	2830.6	2834.1	2837.6
5°	2821.4	2830.2	2833.3	2836.5
7.5°	2824.3	2830.5	2832.7	2834.8
10°	2828.5	2838.1	2838.7	2839.3
12.5°	2835.6	2849.4	2845.5	2841.6
15°	2837.0	2856.4	2845.7	2835.1
17.5°	2807.8	2833.6	2818.5	2803.4
20°	2768.6	2796.8	2779.2	2761.6
22.5°	2708.0	2734.9	2718.9	2702.8
25°	2591.5	2619.0	2608.3	2597.6
27.5°	2432.8	2454.7	2451.7	2448.7
30°	2316.4	2333.3	2333.3	2333.3
32.5°	2183.4	2195.8	2197.3	2198.8
35°	1964.0	1972.6	1965.7	1958.8
37.5°	1697.2	1704.3	1701.7	1699.1
40°	1494.8	1503.6	1503.0	1502.3
42.5°	1292.8	1298.2	1285.5	1272.8
45°	959.2	938.6	882.7	826.8
47.5°	602.9	554.7	485.1	415.5
50°	382.1	317.5	276.1	234.6
52.5°	245.3	193.3	174.9	156.6
55°	112.1	89.2	84.2	79.1
57.5°	50.6	40.4	33.6	26.9
60°	25.0	16.8	10.5	4.2
62.5°	11.0	4.4	2.6	0.8
65°	0.5	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0
87.5°	2.5	1.5	1.0	0.4
90°	12.5	7.7	4.9	2.1
92.5°	27.0	18.8	13.2	7.7
95°	54.2	43.1	30.6	21.6
97.5°	86.4	68.4	56.1	41.2
100°	103.6	86.2	74.4	58.4
102.5°	122.5	107.9	91.7	75.7
105°	156.5	138.4	119.6	101.5
107.5°	187.9	168.0	145.5	129.2
110°	208.0	186.4	162.7	148.1



TEST NUMBER: P1427515

CATALOG NUMBER: SQ2W-BBM-K-050U-100D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	227.4	205.3	181.1	166.5
115°	253.9	229.5	207.3	194.7
117.5°	279.3	254.3	230.8	220.9
120°	294.9	269.9	246.9	239.3
122.5°	307.7	283.2	261.9	258.7
125°	326.9	301.9	283.8	287.9
127.5°	342.5	319.5	308.1	317.4
130°	351.9	331.8	324.8	338.0
132.5°	360.3	344.6	341.5	359.7
135°	372.8	363.8	366.5	391.6
137.5°	387.7	384.2	393.5	425.1
140°	397.1	399.2	412.4	447.9
142.5°	409.9	414.8	431.9	469.6
145°	429.8	440.3	462.5	500.1
147.5°	452.4	465.9	493.4	531.9
150°	467.4	484.8	514.0	550.8
152.5°	484.6	502.6	531.8	569.2
155°	511.2	531.4	562.0	594.0
157.5°	538.3	558.9	588.1	616.1
160°	555.0	577.3	603.7	629.4
162.5°	573.9	594.5	617.6	640.6
165°	601.6	618.3	637.1	656.6
167.5°	624.8	638.8	653.5	668.7
170°	639.9	651.0	663.5	675.3
172.5°	652.7	661.6	670.7	680.9
175°	669.8	674.6	680.2	686.5
177.5°	683.0	684.7	686.3	689.1
180°	688.6	688.6	688.6	688.6



TEST NUMBER: P1427515
 CATALOG NUMBER: SQ2W-BBM-K-050U-100D-L940-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.48	1.29	1.31	2.11	3.11	0.71	1.52	1.54	2.34	3.34
	3H	0.30	1.01	1.14	1.84	2.87	0.53	1.24	1.37	2.07	3.10
	4H	0.19	0.86	1.05	1.70	2.75	0.42	1.09	1.28	1.93	2.98
	6H	0.09	0.70	0.95	1.54	2.60	0.32	0.93	1.18	1.77	2.83
	8H	0.03	0.60	0.91	1.46	2.53	0.26	0.83	1.14	1.69	2.75
	12H	0.00	0.52	0.85	1.37	2.45	0.20	0.75	1.08	1.60	2.68
4H	2H	0.20	0.87	1.07	1.70	2.75	0.43	1.10	1.30	1.93	2.98
	3H	0.01	0.55	0.88	1.42	2.48	0.24	0.78	1.11	1.65	2.71
	4H	0.00	0.39	0.78	1.26	2.35	0.13	0.62	1.00	1.48	2.58
	6H	0.00	0.21	0.68	1.10	2.20	0.02	0.44	0.91	1.33	2.42
	8H	0.00	0.11	0.62	1.00	2.10	0.00	0.34	0.85	1.23	2.33
	12H	0.00	0.00	0.57	0.91	2.02	0.00	0.23	0.80	1.14	2.24
8H	4H	0.00	0.11	0.62	1.00	2.10	0.00	0.34	0.85	1.23	2.33
	6H	0.00	0.00	0.52	0.85	1.96	0.00	0.15	0.75	1.08	2.19
	8H	0.00	0.00	0.47	0.75	1.87	0.00	0.05	0.70	0.98	2.10
	12H	0.00	0.00	0.40	0.64	1.81	0.00	0.00	0.63	0.86	2.04
12H	4H	0.00	0.00	0.57	0.91	2.02	0.00	0.23	0.80	1.14	2.24
	6H	0.00	0.00	0.47	0.75	1.87	0.00	0.05	0.70	0.98	2.10
	8H	0.00	0.00	0.40	0.63	1.81	0.00	0.00	0.63	0.86	2.04