

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427518

Luminaire Tested: SQ2W-BBM-K-050U-125D-L940-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1427518  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2104-222-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-BBM-K-050U-125D-L940-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - BLACK DISCREET BAFFLE, MEDIUM 80-DEGREE OPTIC  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7298.5 lumens  
Efficiency: N/A  
Efficacy: 112.8 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.17 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 64.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1427518

CATALOG NUMBER: SQ2W-BBM-K-050U-125D-L940-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1427518

CATALOG NUMBER: SQ2W-BBM-K-050U-125D-L940-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	72
1	106	102	99	97	100	97	95	93	88	86	85	80	79	77	72	71	70	67
2	99	93	88	84	94	89	85	81	81	78	75	74	72	69	67	66	64	61
3	92	85	79	74	88	81	76	72	74	70	67	68	65	63	63	60	58	55
4	86	77	71	66	82	74	68	64	68	64	60	63	59	56	58	55	53	50
5	80	71	64	59	77	68	62	57	63	58	54	58	54	51	54	51	48	46
6	75	65	58	53	72	62	56	52	58	53	49	54	50	47	50	47	44	42
7	70	60	53	48	67	58	51	47	54	48	45	50	46	43	47	43	40	38
8	66	55	48	43	63	53	47	43	50	45	41	47	42	39	44	40	37	35
9	62	51	44	40	59	49	43	39	46	41	37	43	39	36	41	37	34	33
10	58	47	41	36	56	46	40	36	43	38	34	41	36	33	38	34	32	30

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	57087	57087	57087	57087
5°	57536	57622	57536	57622
10°	58258	58171	58258	58171
15°	59309	58127	59309	58127
20°	59384	57074	59384	57074
25°	57917	55648	57917	55648
30°	54444	51905	54444	51905
35°	48321	46508	48321	46508
40°	39628	37504	39628	37504
45°	23626	22173	23626	22173
50°	7375	6975	7375	6975
55°	2790	2790	2790	2790
60°	171	58	171	58
65°	0	0	0	0
70°	0	0	0	0
75°	0	0	0	0
80°	0	0	0	0
85°	0	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 40°  
 Vertical Angle: 45°  
 Luminance: 27660 cd/sqm



TEST NUMBER: P1427518

CATALOG NUMBER: SQ2W-BBM-K-050U-125D-L940-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	338.1	4.6
10°-20°	990.3	13.6
20°-30°	1456.9	20.0
30°-40°	1489.1	20.4
40°-50°	857.8	11.8
50°-60°	147.6	2.0
60°-70°	5.3	0.1
70°-80°	0.0	0.0
80°-90°	3.7	0.1
90°-100°	54.8	0.8
100°-110°	159.8	2.2
110°-120°	260.8	3.6
120°-130°	330.9	4.5
130°-140°	354.1	4.9
140°-150°	330.7	4.5
150°-160°	272.1	3.7
160°-170°	182.5	2.5
170°-180°	64.8	0.9
0°-30°	2785.3	38.2
0°-40°	4274.4	58.6
0°-60°	5279.9	72.3
0°-90°	5288.9	72.5
90°-120°	475.4	6.5
90°-150°	1491.1	20.4
90°-180°	2010.0	27.5
0°-180°	7298.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	3536	3536	3536	3536	3536	
5°	3550	3555	3550	3555	3550	339
15°	3548	3478	3548	3478	3548	999
25°	3251	3124	3251	3124	3251	1483
35°	2452	2360	2452	2360	2452	1514
45°	1035	971	1035	971	1035	801
55°	99	99	99	99	99	105
65°	0	0	0	0	0	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	2	15	2	30	2	2
95°	22	16	22	94	22	26
105°	102	163	102	224	102	108
115°	195	270	195	332	195	192
125°	288	428	288	408	288	258
135°	392	560	392	451	392	303
145°	500	645	500	461	500	313
155°	594	701	594	478	594	273
165°	657	731	657	551	657	185
175°	686	716	686	646	686	65
180°	689	689	689	689	689	



TEST NUMBER: P1427518

CATALOG NUMBER: SQ2W-BBM-K-050U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8
2.5°	3551.4	3547.0	3542.6	3532.1	3519.5	3520.4	3534.9	3545.0	3541.8	3538.7	3541.8
5°	3550.0	3546.1	3542.1	3531.1	3517.8	3521.7	3542.9	3558.4	3556.9	3555.3	3556.9
7.5°	3547.9	3545.2	3542.5	3534.8	3525.3	3529.4	3546.8	3558.9	3555.0	3551.0	3555.0
10°	3553.5	3552.7	3552.0	3540.0	3524.2	3525.4	3543.5	3556.1	3552.1	3548.2	3552.1
12.5°	3556.4	3561.2	3566.1	3548.9	3524.4	3519.3	3533.6	3542.6	3535.5	3528.4	3535.5
15°	3548.2	3561.6	3574.9	3550.6	3513.6	3496.3	3498.7	3497.9	3487.7	3477.5	3487.7
17.5°	3508.6	3527.5	3546.3	3514.1	3464.9	3436.0	3427.4	3417.2	3402.8	3388.3	3402.8
20°	3456.2	3478.3	3500.3	3465.1	3410.8	3376.3	3361.3	3347.0	3334.4	3321.8	3334.4
22.5°	3382.7	3402.8	3422.9	3389.1	3337.4	3302.2	3283.5	3266.9	3256.9	3246.8	3256.9
25°	3251.1	3264.4	3277.8	3243.4	3193.1	3160.9	3146.7	3134.7	3129.2	3123.7	3129.2
27.5°	3064.6	3068.4	3072.2	3044.8	3007.1	2979.4	2961.8	2946.8	2939.8	2932.7	2939.8
30°	2920.3	2920.3	2920.3	2899.1	2870.8	2847.2	2828.3	2810.8	2797.5	2784.1	2797.5
32.5°	2751.9	2750.0	2748.1	2732.6	2712.4	2692.0	2671.2	2652.3	2639.0	2625.6	2639.0
35°	2451.6	2460.2	2468.9	2458.0	2440.8	2421.9	2401.4	2383.2	2371.4	2359.6	2371.4
37.5°	2126.5	2129.8	2133.1	2124.1	2111.0	2093.5	2071.5	2052.5	2042.6	2032.7	2042.6
40°	1880.2	1881.0	1881.8	1870.8	1855.9	1840.5	1824.8	1809.3	1794.4	1779.4	1794.4
42.5°	1593.0	1608.9	1624.7	1618.0	1603.7	1583.9	1558.8	1538.4	1532.3	1526.1	1532.3
45°	1034.7	1104.7	1174.7	1200.4	1211.4	1202.8	1174.5	1133.0	1052.0	971.1	1052.0
47.5°	520.0	607.1	694.2	754.6	806.0	791.4	710.7	628.8	543.1	457.4	543.1
50°	293.6	345.5	397.4	478.2	568.6	553.6	433.4	335.9	306.8	277.7	306.8
52.5°	196.0	218.9	241.9	306.9	386.0	380.8	291.4	220.2	203.6	187.1	203.6
55°	99.1	105.3	111.6	140.3	176.5	175.7	138.0	108.5	103.8	99.1	103.8
57.5°	33.6	42.1	50.6	63.3	77.5	77.9	64.5	52.6	44.8	37.1	44.8
60°	5.3	13.2	21.0	31.2	42.3	41.1	27.7	15.9	8.8	1.8	8.8
62.5°	1.1	3.3	5.5	13.8	24.2	23.9	13.1	4.4	2.4	0.4	2.4
65°	0.0	0.0	0.0	0.6	1.4	1.4	0.6	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.4	1.0	1.7	2.2	2.6	2.8	2.8	2.9	3.1	3.1	3.1
90°	2.1	4.9	8.3	11.1	13.2	13.9	13.9	14.6	15.3	15.3	15.3
92.5°	7.7	12.1	12.2	12.2	14.9	16.1	17.2	17.4	18.1	18.1	18.1
95°	21.6	23.6	35.5	34.8	23.6	18.8	16.0	16.0	16.0	16.0	16.0
97.5°	41.2	44.2	46.2	61.9	65.4	63.2	51.5	43.3	38.7	36.6	38.7
100°	58.4	59.8	64.0	64.7	82.1	98.8	90.4	80.0	76.5	74.4	76.5
102.5°	75.7	76.5	82.9	85.8	89.9	99.3	128.3	125.1	122.7	122.3	122.7
105°	101.5	102.2	114.1	119.6	122.4	122.4	121.7	135.6	157.9	162.7	157.9
107.5°	129.2	132.4	146.3	161.2	164.4	165.3	161.6	159.5	158.7	159.3	158.7
110°	148.1	153.0	169.7	188.5	193.4	194.7	193.4	191.3	189.9	189.9	189.9



TEST NUMBER: P1427518

CATALOG NUMBER: SQ2W-BBM-K-050U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	166.5	173.6	192.5	214.1	222.3	226.5	223.4	221.9	220.5	221.6	220.5
115°	194.7	205.2	230.2	252.5	269.2	271.2	270.6	270.6	269.9	269.9	269.9
117.5°	220.9	237.6	265.7	291.6	310.9	316.5	319.2	318.4	317.6	319.0	317.6
120°	239.3	258.7	290.7	319.9	338.7	347.1	349.8	348.4	349.8	348.4	349.8
122.5°	258.7	282.7	314.1	344.4	366.5	376.0	379.3	379.6	379.9	379.1	379.9
125°	287.9	317.2	354.0	385.3	408.3	419.4	422.2	422.9	424.3	427.7	424.3
127.5°	317.4	350.5	391.0	421.2	444.7	458.2	462.5	464.0	467.0	468.5	467.0
130°	338.0	375.6	416.6	445.1	468.1	482.7	490.3	492.4	495.9	495.2	495.9
132.5°	359.7	398.9	440.5	470.2	491.4	507.2	513.7	519.7	520.9	521.9	520.9
135°	391.6	434.0	475.7	504.9	525.1	540.4	548.8	554.3	557.8	559.9	557.8
137.5°	425.1	469.9	509.9	536.0	556.3	569.5	578.9	584.8	588.4	590.1	588.4
140°	447.9	491.0	530.0	557.1	575.2	588.4	596.7	603.7	607.9	607.9	607.9
142.5°	469.6	512.2	550.0	577.1	593.0	605.1	614.0	619.3	624.0	624.0	624.0
145°	500.1	542.5	577.3	604.4	617.6	628.7	638.5	642.6	645.4	645.4	645.4
147.5°	531.9	569.5	601.2	627.2	638.3	651.4	659.1	662.4	665.9	664.3	665.9
150°	550.8	585.6	616.2	640.6	651.7	664.2	671.9	674.6	678.1	676.0	678.1
152.5°	569.2	602.3	630.1	652.8	662.3	674.8	683.5	686.3	688.7	687.2	688.7
155°	594.0	623.2	648.9	669.8	678.1	689.9	698.3	701.8	704.5	701.1	704.5
157.5°	616.1	641.3	663.7	682.8	691.8	701.9	709.7	714.0	716.8	715.3	716.8
160°	629.4	652.4	672.6	690.6	699.0	708.0	716.4	721.2	724.0	721.9	724.0
162.5°	640.6	661.3	680.3	696.8	704.0	711.9	721.9	726.2	729.0	726.4	729.0
165°	656.6	673.3	689.9	703.9	710.1	716.4	726.8	731.7	733.8	731.0	733.8
167.5°	668.7	681.5	695.0	706.9	711.5	717.6	728.1	732.1	734.7	731.3	734.7
170°	675.3	686.5	698.3	708.0	711.5	717.1	727.5	731.0	733.1	729.6	733.1
172.5°	680.9	689.2	698.8	707.5	709.3	713.7	723.6	727.1	728.6	725.7	728.6
175°	686.5	691.3	698.3	703.9	703.2	705.9	714.3	717.1	719.9	715.7	719.9
177.5°	689.1	691.3	693.6	696.9	694.7	694.7	700.8	702.5	703.0	700.8	703.0
180°	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6



TEST NUMBER: P1427518

CATALOG NUMBER: SQ2W-BBM-K-050U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8
2.5°	3545.0	3534.9	3520.4	3519.5	3532.1	3542.6	3547.0	3551.4	3547.0	3542.6	3532.1
5°	3558.4	3542.9	3521.7	3517.8	3531.1	3542.1	3546.1	3550.0	3546.1	3542.1	3531.1
7.5°	3558.9	3546.8	3529.4	3525.3	3534.8	3542.5	3545.2	3547.9	3545.2	3542.5	3534.8
10°	3556.1	3543.5	3525.4	3524.2	3540.0	3552.0	3552.7	3553.5	3552.7	3552.0	3540.0
12.5°	3542.6	3533.6	3519.3	3524.4	3548.9	3566.1	3561.2	3556.4	3561.2	3566.1	3548.9
15°	3497.9	3498.7	3496.3	3513.6	3550.6	3574.9	3561.6	3548.2	3561.6	3574.9	3550.6
17.5°	3417.2	3427.4	3436.0	3464.9	3514.1	3546.3	3527.5	3508.6	3527.5	3546.3	3514.1
20°	3347.0	3361.3	3376.3	3410.8	3465.1	3500.3	3478.3	3456.2	3478.3	3500.3	3465.1
22.5°	3266.9	3283.5	3302.2	3337.4	3389.1	3422.9	3402.8	3382.7	3402.8	3422.9	3389.1
25°	3134.7	3146.7	3160.9	3193.1	3243.4	3277.8	3264.4	3251.1	3264.4	3277.8	3243.4
27.5°	2946.8	2961.8	2979.4	3007.1	3044.8	3072.2	3068.4	3064.6	3068.4	3072.2	3044.8
30°	2810.8	2828.3	2847.2	2870.8	2899.1	2920.3	2920.3	2920.3	2920.3	2920.3	2899.1
32.5°	2652.3	2671.2	2692.0	2712.4	2732.6	2748.1	2750.0	2751.9	2750.0	2748.1	2732.6
35°	2383.2	2401.4	2421.9	2440.8	2458.0	2468.9	2460.2	2451.6	2460.2	2468.9	2458.0
37.5°	2052.5	2071.5	2093.5	2111.0	2124.1	2133.1	2129.8	2126.5	2129.8	2133.1	2124.1
40°	1809.3	1824.8	1840.5	1855.9	1870.8	1881.8	1881.0	1880.2	1881.0	1881.8	1870.8
42.5°	1538.4	1558.8	1583.9	1603.7	1618.0	1624.7	1608.9	1593.0	1608.9	1624.7	1618.0
45°	1133.0	1174.5	1202.8	1211.4	1200.4	1174.7	1104.7	1034.7	1104.7	1174.7	1200.4
47.5°	628.8	710.7	791.4	806.0	754.6	694.2	607.1	520.0	607.1	694.2	754.6
50°	335.9	433.4	553.6	568.6	478.2	397.4	345.5	293.6	345.5	397.4	478.2
52.5°	220.2	291.4	380.8	386.0	306.9	241.9	218.9	196.0	218.9	241.9	306.9
55°	108.5	138.0	175.7	176.5	140.3	111.6	105.3	99.1	105.3	111.6	140.3
57.5°	52.6	64.5	77.9	77.5	63.3	50.6	42.1	33.6	42.1	50.6	63.3
60°	15.9	27.7	41.1	42.3	31.2	21.0	13.2	5.3	13.2	21.0	31.2
62.5°	4.4	13.1	23.9	24.2	13.8	5.5	3.3	1.1	3.3	5.5	13.8
65°	0.0	0.6	1.4	1.4	0.6	0.0	0.0	0.0	0.0	0.0	0.6
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	2.9	2.8	2.8	2.6	2.2	1.7	1.0	0.4	1.0	1.5	2.5
90°	14.6	13.9	13.9	13.2	11.1	8.3	4.9	2.1	4.9	7.7	12.5
92.5°	17.4	17.2	16.1	14.9	12.2	12.2	12.1	7.7	13.2	18.8	27.0
95°	16.0	16.0	18.8	23.6	34.8	35.5	23.6	21.6	30.6	43.1	54.2
97.5°	43.3	51.5	63.2	65.4	61.9	46.2	44.2	41.2	56.1	68.4	86.4
100°	80.0	90.4	98.8	82.1	64.7	64.0	59.8	58.4	74.4	86.2	103.6
102.5°	125.1	128.3	99.3	89.9	85.8	82.9	76.5	75.7	91.7	107.9	122.5
105°	135.6	121.7	122.4	122.4	119.6	114.1	102.2	101.5	119.6	138.4	156.5
107.5°	159.5	161.6	165.3	164.4	161.2	146.3	132.4	129.2	145.5	168.0	187.9
110°	191.3	193.4	194.7	193.4	188.5	169.7	153.0	148.1	162.7	186.4	208.0



TEST NUMBER: P1427518

CATALOG NUMBER: SQ2W-BBM-K-050U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	221.9	223.4	226.5	222.3	214.1	192.5	173.6	166.5	181.1	205.3	227.4
115°	270.6	270.6	271.2	269.2	252.5	230.2	205.2	194.7	207.3	229.5	253.9
117.5°	318.4	319.2	316.5	310.9	291.6	265.7	237.6	220.9	230.8	254.3	279.3
120°	348.4	349.8	347.1	338.7	319.9	290.7	258.7	239.3	246.9	269.9	294.9
122.5°	379.6	379.3	376.0	366.5	344.4	314.1	282.7	258.7	261.9	283.2	307.7
125°	422.9	422.2	419.4	408.3	385.3	354.0	317.2	287.9	283.8	301.9	326.9
127.5°	464.0	462.5	458.2	444.7	421.2	391.0	350.5	317.4	308.1	319.5	342.5
130°	492.4	490.3	482.7	468.1	445.1	416.6	375.6	338.0	324.8	331.8	351.9
132.5°	519.7	513.7	507.2	491.4	470.2	440.5	398.9	359.7	341.5	344.6	360.3
135°	554.3	548.8	540.4	525.1	504.9	475.7	434.0	391.6	366.5	363.8	372.8
137.5°	584.8	578.9	569.5	556.3	536.0	509.9	469.9	425.1	393.5	384.2	387.7
140°	603.7	596.7	588.4	575.2	557.1	530.0	491.0	447.9	412.4	399.2	397.1
142.5°	619.3	614.0	605.1	593.0	577.1	550.0	512.2	469.6	431.9	414.8	409.9
145°	642.6	638.5	628.7	617.6	604.4	577.3	542.5	500.1	462.5	440.3	429.8
147.5°	662.4	659.1	651.4	638.3	627.2	601.2	569.5	531.9	493.4	465.9	452.4
150°	674.6	671.9	664.2	651.7	640.6	616.2	585.6	550.8	514.0	484.8	467.4
152.5°	686.3	683.5	674.8	662.3	652.8	630.1	602.3	569.2	531.8	502.6	484.6
155°	701.8	698.3	689.9	678.1	669.8	648.9	623.2	594.0	562.0	531.4	511.2
157.5°	714.0	709.7	701.9	691.8	682.8	663.7	641.3	616.1	588.1	558.9	538.3
160°	721.2	716.4	708.0	699.0	690.6	672.6	652.4	629.4	603.7	577.3	555.0
162.5°	726.2	721.9	711.9	704.0	696.8	680.3	661.3	640.6	617.6	594.5	573.9
165°	731.7	726.8	716.4	710.1	703.9	689.9	673.3	656.6	637.1	618.3	601.6
167.5°	732.1	728.1	717.6	711.5	706.9	695.0	681.5	668.7	653.5	638.8	624.8
170°	731.0	727.5	717.1	711.5	708.0	698.3	686.5	675.3	663.5	651.0	639.9
172.5°	727.1	723.6	713.7	709.3	707.5	698.8	689.2	680.9	670.7	661.6	652.7
175°	717.1	714.3	705.9	703.2	703.9	698.3	691.3	686.5	680.2	674.6	669.8
177.5°	702.5	700.8	694.7	694.7	696.9	693.6	691.3	689.1	686.3	684.7	683.0
180°	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6



TEST NUMBER: P1427518

CATALOG NUMBER: SQ2W-BBM-K-050U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8	3535.8
2.5°	3519.5	3520.4	3534.9	3545.0	3541.8	3538.7	3541.8	3545.0	3534.9	3520.4	3519.5
5°	3517.8	3521.7	3542.9	3558.4	3556.9	3555.3	3556.9	3558.4	3542.9	3521.7	3517.8
7.5°	3525.3	3529.4	3546.8	3558.9	3555.0	3551.0	3555.0	3558.9	3546.8	3529.4	3525.3
10°	3524.2	3525.4	3543.5	3556.1	3552.1	3548.2	3552.1	3556.1	3543.5	3525.4	3524.2
12.5°	3524.4	3519.3	3533.6	3542.6	3535.5	3528.4	3535.5	3542.6	3533.6	3519.3	3524.4
15°	3513.6	3496.3	3498.7	3497.9	3487.7	3477.5	3487.7	3497.9	3498.7	3496.3	3513.6
17.5°	3464.9	3436.0	3427.4	3417.2	3402.8	3388.3	3402.8	3417.2	3427.4	3436.0	3464.9
20°	3410.8	3376.3	3361.3	3347.0	3334.4	3321.8	3334.4	3347.0	3361.3	3376.3	3410.8
22.5°	3337.4	3302.2	3283.5	3266.9	3256.9	3246.8	3256.9	3266.9	3283.5	3302.2	3337.4
25°	3193.1	3160.9	3146.7	3134.7	3129.2	3123.7	3129.2	3134.7	3146.7	3160.9	3193.1
27.5°	3007.1	2979.4	2961.8	2946.8	2939.8	2932.7	2939.8	2946.8	2961.8	2979.4	3007.1
30°	2870.8	2847.2	2828.3	2810.8	2797.5	2784.1	2797.5	2810.8	2828.3	2847.2	2870.8
32.5°	2712.4	2692.0	2671.2	2652.3	2639.0	2625.6	2639.0	2652.3	2671.2	2692.0	2712.4
35°	2440.8	2421.9	2401.4	2383.2	2371.4	2359.6	2371.4	2383.2	2401.4	2421.9	2440.8
37.5°	2111.0	2093.5	2071.5	2052.5	2042.6	2032.7	2042.6	2052.5	2071.5	2093.5	2111.0
40°	1855.9	1840.5	1824.8	1809.3	1794.4	1779.4	1794.4	1809.3	1824.8	1840.5	1855.9
42.5°	1603.7	1583.9	1558.8	1538.4	1532.3	1526.1	1532.3	1538.4	1558.8	1583.9	1603.7
45°	1211.4	1202.8	1174.5	1133.0	1052.0	971.1	1052.0	1133.0	1174.5	1202.8	1211.4
47.5°	806.0	791.4	710.7	628.8	543.1	457.4	543.1	628.8	710.7	791.4	806.0
50°	568.6	553.6	433.4	335.9	306.8	277.7	306.8	335.9	433.4	553.6	568.6
52.5°	386.0	380.8	291.4	220.2	203.6	187.1	203.6	220.2	291.4	380.8	386.0
55°	176.5	175.7	138.0	108.5	103.8	99.1	103.8	108.5	138.0	175.7	176.5
57.5°	77.5	77.9	64.5	52.6	44.8	37.1	44.8	52.6	64.5	77.9	77.5
60°	42.3	41.1	27.7	15.9	8.8	1.8	8.8	15.9	27.7	41.1	42.3
62.5°	24.2	23.9	13.1	4.4	2.4	0.4	2.4	4.4	13.1	23.9	24.2
65°	1.4	1.4	0.6	0.0	0.0	0.0	0.0	0.6	1.4	1.4	1.4
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	3.2	4.2	5.1	5.7	6.3	6.0	6.3	5.7	5.1	4.2	3.2
90°	16.0	20.9	25.7	28.5	31.3	29.9	31.3	28.5	25.7	20.9	16.0
92.5°	32.1	40.3	46.3	51.3	53.6	53.3	53.6	51.3	46.3	40.3	32.1
95°	64.7	74.4	84.2	91.1	95.3	93.9	95.3	91.1	84.2	74.4	64.7
97.5°	99.7	112.8	123.7	130.2	134.4	137.2	134.4	130.2	123.7	112.8	99.7
100°	123.1	135.6	148.1	155.8	162.7	165.5	162.7	155.8	148.1	135.6	123.1
102.5°	142.0	158.4	172.1	180.3	186.1	188.9	186.1	180.3	172.1	158.4	142.0
105°	173.2	190.6	205.2	215.6	221.9	224.0	221.9	215.6	205.2	190.6	173.2
107.5°	204.3	222.3	235.8	247.3	255.0	259.4	255.0	247.3	235.8	222.3	204.3
110°	228.8	243.4	258.0	268.5	276.1	278.9	276.1	268.5	258.0	243.4	228.8



TEST NUMBER: P1427518

CATALOG NUMBER: SQ2W-BBM-K-050U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	249.4	265.7	280.3	290.7	299.5	303.4	299.5	290.7	280.3	265.7	249.4
115°	278.2	299.8	313.0	322.7	329.0	332.5	329.0	322.7	313.0	299.8	278.2
117.5°	302.1	324.7	339.1	346.6	349.6	352.1	349.6	346.6	339.1	324.7	302.1
120°	317.2	338.0	354.7	364.4	367.9	369.3	367.9	364.4	354.7	338.0	317.2
122.5°	331.1	350.8	366.9	378.9	384.6	386.0	384.6	378.9	366.9	350.8	331.1
125°	350.5	369.3	386.0	397.8	404.1	407.6	404.1	397.8	386.0	369.3	350.5
127.5°	367.5	387.8	403.1	413.8	419.9	422.7	419.9	413.8	403.1	387.8	367.5
130°	377.0	397.8	413.1	425.0	430.5	433.3	430.5	425.0	413.1	397.8	377.0
132.5°	384.2	406.2	422.0	432.7	438.9	441.6	438.9	432.7	422.0	406.2	384.2
135°	393.0	415.9	432.6	443.0	448.6	451.4	448.6	443.0	432.6	415.9	393.0
137.5°	400.6	421.5	438.9	449.9	454.9	456.7	454.9	449.9	438.9	421.5	400.6
140°	406.2	424.3	441.6	452.1	457.6	458.3	457.6	452.1	441.6	424.3	406.2
142.5°	413.4	427.6	442.8	453.2	458.8	460.0	458.8	453.2	442.8	427.6	413.4
145°	426.3	434.7	445.1	454.9	459.7	461.1	459.7	454.9	445.1	434.7	426.3
147.5°	442.6	445.3	450.7	457.1	461.8	462.8	461.8	457.1	445.3	442.6	442.6
150°	454.9	454.2	456.3	460.4	464.6	463.9	464.6	460.4	456.3	454.2	454.9
152.5°	468.8	464.7	464.6	466.5	468.5	468.4	468.5	466.5	464.6	464.7	468.8
155°	492.4	484.8	480.6	479.2	479.2	478.5	479.2	479.2	480.6	484.8	492.4
157.5°	518.4	507.7	501.5	498.1	497.1	495.6	497.1	498.1	501.5	507.7	518.4
160°	536.2	524.4	518.2	512.6	510.5	508.4	510.5	512.6	518.2	524.4	536.2
162.5°	552.9	541.7	534.8	529.8	527.8	524.6	527.8	529.8	534.8	541.7	552.9
165°	580.1	568.2	560.6	556.4	553.6	550.8	553.6	556.4	560.6	568.2	580.1
167.5°	607.2	594.2	589.2	584.5	581.9	576.9	581.9	584.5	589.2	594.2	607.2
170°	623.9	612.0	609.3	605.1	600.2	594.7	600.2	605.1	609.3	612.0	623.9
172.5°	638.3	630.4	627.6	623.5	621.9	617.5	621.9	623.5	627.6	630.4	638.3
175°	659.3	653.1	653.1	652.4	650.3	646.1	650.3	652.4	653.1	653.1	659.3
177.5°	676.9	673.5	675.8	675.8	675.2	671.3	675.2	675.8	675.8	673.5	676.9
180°	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6



TEST NUMBER: P1427518

CATALOG NUMBER: SQ2W-BBM-K-050U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	3535.8	3535.8	3535.8	3535.8
2.5°	3532.1	3542.6	3547.0	3551.4
5°	3531.1	3542.1	3546.1	3550.0
7.5°	3534.8	3542.5	3545.2	3547.9
10°	3540.0	3552.0	3552.7	3553.5
12.5°	3548.9	3566.1	3561.2	3556.4
15°	3550.6	3574.9	3561.6	3548.2
17.5°	3514.1	3546.3	3527.5	3508.6
20°	3465.1	3500.3	3478.3	3456.2
22.5°	3389.1	3422.9	3402.8	3382.7
25°	3243.4	3277.8	3264.4	3251.1
27.5°	3044.8	3072.2	3068.4	3064.6
30°	2899.1	2920.3	2920.3	2920.3
32.5°	2732.6	2748.1	2750.0	2751.9
35°	2458.0	2468.9	2460.2	2451.6
37.5°	2124.1	2133.1	2129.8	2126.5
40°	1870.8	1881.8	1881.0	1880.2
42.5°	1618.0	1624.7	1608.9	1593.0
45°	1200.4	1174.7	1104.7	1034.7
47.5°	754.6	694.2	607.1	520.0
50°	478.2	397.4	345.5	293.6
52.5°	306.9	241.9	218.9	196.0
55°	140.3	111.6	105.3	99.1
57.5°	63.3	50.6	42.1	33.6
60°	31.2	21.0	13.2	5.3
62.5°	13.8	5.5	3.3	1.1
65°	0.6	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0
87.5°	2.5	1.5	1.0	0.4
90°	12.5	7.7	4.9	2.1
92.5°	27.0	18.8	13.2	7.7
95°	54.2	43.1	30.6	21.6
97.5°	86.4	68.4	56.1	41.2
100°	103.6	86.2	74.4	58.4
102.5°	122.5	107.9	91.7	75.7
105°	156.5	138.4	119.6	101.5
107.5°	187.9	168.0	145.5	129.2
110°	208.0	186.4	162.7	148.1



TEST NUMBER: P1427518

CATALOG NUMBER: SQ2W-BBM-K-050U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	227.4	205.3	181.1	166.5
115°	253.9	229.5	207.3	194.7
117.5°	279.3	254.3	230.8	220.9
120°	294.9	269.9	246.9	239.3
122.5°	307.7	283.2	261.9	258.7
125°	326.9	301.9	283.8	287.9
127.5°	342.5	319.5	308.1	317.4
130°	351.9	331.8	324.8	338.0
132.5°	360.3	344.6	341.5	359.7
135°	372.8	363.8	366.5	391.6
137.5°	387.7	384.2	393.5	425.1
140°	397.1	399.2	412.4	447.9
142.5°	409.9	414.8	431.9	469.6
145°	429.8	440.3	462.5	500.1
147.5°	452.4	465.9	493.4	531.9
150°	467.4	484.8	514.0	550.8
152.5°	484.6	502.6	531.8	569.2
155°	511.2	531.4	562.0	594.0
157.5°	538.3	558.9	588.1	616.1
160°	555.0	577.3	603.7	629.4
162.5°	573.9	594.5	617.6	640.6
165°	601.6	618.3	637.1	656.6
167.5°	624.8	638.8	653.5	668.7
170°	639.9	651.0	663.5	675.3
172.5°	652.7	661.6	670.7	680.9
175°	669.8	674.6	680.2	686.5
177.5°	683.0	684.7	686.3	689.1
180°	688.6	688.6	688.6	688.6



TEST NUMBER: P1427518

CATALOG NUMBER: SQ2W-BBM-K-050U-125D-L940-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	1.66	2.50	2.44	3.27	4.19	1.89	2.73	2.67	3.49	4.42
	3H	1.48	2.21	2.27	2.99	3.95	1.71	2.44	2.50	3.22	4.18
	4H	1.38	2.07	2.18	2.85	3.82	1.60	2.29	2.41	3.08	4.05
	6H	1.27	1.90	2.09	2.70	3.68	1.50	2.13	2.32	2.93	3.90
	8H	1.21	1.81	2.04	2.62	3.60	1.44	2.04	2.27	2.85	3.83
	12H	1.15	1.72	1.98	2.53	3.53	1.38	1.95	2.21	2.75	3.76
4H	2H	1.39	2.07	2.20	2.86	3.83	1.61	2.30	2.42	3.09	4.06
	3H	1.19	1.75	2.01	2.58	3.56	1.42	1.98	2.24	2.80	3.79
	4H	1.08	1.59	1.91	2.41	3.42	1.31	1.81	2.14	2.64	3.65
	6H	0.97	1.41	1.82	2.25	3.27	1.20	1.63	2.05	2.48	3.50
	8H	0.91	1.31	1.76	2.15	3.18	1.13	1.54	1.99	2.38	3.41
	12H	0.84	1.20	1.71	2.06	3.09	1.07	1.43	1.93	2.29	3.32
8H	4H	0.91	1.31	1.76	2.15	3.18	1.13	1.54	1.99	2.38	3.41
	6H	0.79	1.12	1.66	2.00	3.03	1.02	1.34	1.89	2.23	3.26
	8H	0.72	1.02	1.61	1.90	2.94	0.95	1.24	1.84	2.12	3.17
	12H	0.66	0.92	1.54	1.78	2.89	0.89	1.14	1.77	2.01	3.12
12H	4H	0.84	1.20	1.71	2.06	3.09	1.07	1.43	1.93	2.29	3.32
	6H	0.72	1.02	1.61	1.90	2.94	0.95	1.24	1.84	2.12	3.17
	8H	0.66	0.92	1.54	1.78	2.89	0.89	1.14	1.77	2.01	3.11