

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428574

Luminaire Tested: SQ2W-WBM-K-150U-125D-L940-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1428574  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2104-222-6)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-WBM-K-150U-125D-L940-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - WHITE DISCREET BAFFLE, MEDIUM 80-DEGREE OPTIC  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11919.4 lumens  
Efficiency: N/A  
Efficacy: 113.6 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.18 / 1.17  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 104.9  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1428574

CATALOG NUMBER: SQ2W-WBM-K-150U-125D-L940-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1428574

CATALOG NUMBER: SQ2W-WBM-K-150U-125D-L940-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48				48
1	99	95	92	89	91	88	86	83	75	73	71	62	61	60	51	50	49				44	
2	92	86	80	76	85	79	75	71	68	65	62	57	55	53	47	46	45				40	
3	85	77	71	66	78	72	66	62	61	58	54	52	49	47	43	42	40				36	
4	79	69	62	57	73	65	59	54	56	51	48	48	45	42	40	38	36				33	
5	73	63	56	50	67	59	52	48	51	46	43	44	40	38	37	35	33				30	
6	68	57	50	45	63	54	47	43	47	42	38	40	37	34	34	32	30				27	
7	63	52	45	40	59	49	43	38	43	38	34	37	34	31	32	29	27				25	
8	59	48	41	36	55	45	39	34	40	35	31	34	31	28	30	27	25				23	
9	55	44	37	33	51	41	35	31	37	32	28	32	28	26	28	25	23				21	
10	52	41	34	30	48	38	32	28	34	29	26	30	26	24	26	23	21				19	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	59458	59458	59458	59458
5°	59999	59972	59999	59972
10°	60606	60578	60606	60578
15°	61615	60522	61615	60522
20°	61909	59543	61909	59543
25°	60636	57867	60636	57867
30°	57531	54108	57531	54108
35°	51741	48820	51741	48820
40°	42419	40184	42419	40184
45°	26523	24911	26523	24911
50°	10376	9490	10376	9490
55°	5117	5070	5117	5070
60°	2393	2167	2393	2167
65°	2159	2025	2159	2025
70°	2082	2002	2082	2002
75°	2090	1871	2090	1871
80°	1971	1804	1971	1804
85°	1964	1630	1964	1630

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 30°  
 Vertical Angle: 45°  
 Luminance: 30192 cd/sqm



TEST NUMBER: P1428574

CATALOG NUMBER: SQ2W-WBM-K-150U-125D-L940-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	352.1	3.0
10°-20°	1029.6	8.6
20°-30°	1522.3	12.8
30°-40°	1575.0	13.2
40°-50°	947.4	7.9
50°-60°	226.5	1.9
60°-70°	61.9	0.5
70°-80°	34.6	0.3
80°-90°	19.6	0.2
90°-100°	167.6	1.4
100°-110°	488.9	4.1
110°-120°	797.8	6.7
120°-130°	1012.4	8.5
130°-140°	1083.3	9.1
140°-150°	1011.5	8.5
150°-160°	832.4	7.0
160°-170°	558.2	4.7
170°-180°	198.2	1.7
0°-30°	2903.9	24.4
0°-40°	4479.0	37.6
0°-60°	5652.9	47.4
0°-90°	5769.1	48.4
90°-120°	1454.3	12.2
90°-150°	4561.5	38.3
90°-180°	6150.0	51.6
0°-180°	11919.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	3683	3683	3683	3683	3683	
5°	3702	3700	3702	3700	3702	353
15°	3686	3621	3686	3621	3686	1039
25°	3404	3248	3404	3248	3404	1556
35°	2625	2477	2625	2477	2625	1611
45°	1162	1091	1162	1091	1162	898
55°	182	180	182	180	182	182
65°	56	53	56	53	56	57
75°	34	30	34	30	34	35
85°	11	9	11	9	11	11
90°	6	47	6	92	6	6
95°	66	49	66	287	66	80
105°	311	498	311	685	311	330
115°	596	826	596	1017	596	587
125°	881	1308	881	1247	881	788
135°	1198	1713	1198	1381	1198	926
145°	1530	1974	1530	1411	1530	957
155°	1817	2145	1817	1464	1817	835
165°	2008	2236	2008	1685	2008	565
175°	2100	2189	2100	1977	2100	199
180°	2106	2106	2106	2106	2106	



TEST NUMBER: P1428574

CATALOG NUMBER: SQ2W-WBM-K-150U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	3682.6	3682.6	3682.6	3682.6	3682.6	3682.6	3682.6	3682.6	3682.6	3682.6	3682.6
2.5°	3701.0	3696.6	3692.2	3681.2	3668.0	3668.3	3682.2	3691.7	3688.6	3685.4	3688.6
5°	3702.0	3696.5	3691.1	3678.5	3663.6	3667.1	3689.1	3705.0	3702.6	3700.3	3702.6
7.5°	3698.2	3695.8	3693.5	3684.3	3672.8	3675.4	3692.0	3703.6	3700.0	3696.4	3700.0
10°	3696.7	3697.5	3698.3	3686.2	3669.7	3670.1	3687.3	3699.7	3697.3	3695.0	3697.3
12.5°	3695.3	3701.8	3708.2	3691.8	3667.8	3662.5	3676.0	3684.8	3679.3	3673.8	3679.3
15°	3686.2	3698.7	3711.3	3689.1	3655.4	3638.5	3638.5	3636.5	3628.7	3620.8	3628.7
17.5°	3647.0	3661.9	3676.8	3646.7	3601.7	3573.1	3561.0	3549.6	3540.0	3530.4	3540.0
20°	3603.2	3618.1	3633.0	3597.3	3544.7	3508.6	3489.0	3473.3	3469.4	3465.5	3469.4
22.5°	3534.0	3550.1	3566.3	3528.1	3471.8	3432.8	3411.3	3393.6	3387.2	3380.7	3387.2
25°	3403.7	3416.2	3428.8	3389.0	3331.7	3295.2	3279.5	3265.6	3257.0	3248.3	3257.0
27.5°	3230.0	3236.9	3243.8	3205.3	3151.6	3115.8	3097.9	3081.5	3069.6	3057.7	3069.6
30°	3085.9	3089.1	3092.2	3061.2	3018.8	2985.9	2962.3	2940.0	2921.1	2902.3	2921.1
32.5°	2915.0	2918.2	2921.3	2894.1	2856.7	2826.9	2804.6	2784.2	2769.1	2754.0	2769.1
35°	2625.1	2623.6	2622.0	2604.6	2581.8	2557.5	2531.6	2508.2	2492.5	2476.9	2492.5
37.5°	2262.5	2264.7	2266.9	2253.9	2235.9	2216.7	2196.3	2177.0	2161.2	2145.3	2161.2
40°	2012.6	2014.1	2015.7	2004.9	1990.0	1967.6	1937.8	1914.5	1910.6	1906.6	1910.6
42.5°	1707.5	1731.0	1754.6	1745.0	1724.5	1702.7	1679.8	1658.1	1639.7	1621.3	1639.7
45°	1161.6	1233.0	1304.4	1322.3	1322.3	1308.6	1281.1	1241.7	1166.3	1091.0	1166.3
47.5°	656.0	737.3	818.6	872.0	916.1	897.3	815.7	731.7	640.2	548.7	640.2
50°	413.1	468.0	523.0	591.4	664.4	644.4	531.4	439.0	408.4	377.8	408.4
52.5°	293.1	321.0	348.9	413.5	490.2	480.9	385.4	309.8	293.7	277.5	293.7
55°	181.8	192.0	202.2	233.6	272.1	269.7	226.6	192.6	186.3	180.1	186.3
57.5°	108.0	118.6	129.1	143.0	158.1	158.1	143.0	129.2	119.3	109.5	119.3
60°	74.1	82.8	91.4	103.0	115.5	114.0	98.3	84.3	75.7	67.1	75.7
62.5°	64.3	67.9	71.5	80.4	91.1	90.1	77.6	67.4	64.4	61.4	64.4
65°	56.5	57.3	58.1	58.8	59.6	59.2	57.7	56.1	54.5	53.0	54.5
67.5°	49.8	50.6	51.4	51.1	50.5	50.1	49.9	49.4	48.0	46.6	48.0
70°	44.1	44.9	45.7	45.9	45.9	45.5	44.7	43.9	43.2	42.4	43.2
72.5°	39.9	40.7	41.5	41.2	40.6	40.2	40.0	39.5	38.1	36.7	38.1
75°	33.5	33.5	33.5	33.5	33.5	33.2	32.4	31.6	30.8	30.0	30.8
77.5°	25.4	26.2	27.0	26.6	25.8	25.4	25.4	25.2	24.4	23.7	24.4
80°	21.2	22.0	22.8	22.4	21.6	21.2	21.2	21.0	20.2	19.4	20.2
82.5°	16.9	17.1	17.3	17.2	17.0	16.9	16.9	16.8	16.0	15.2	16.0
85°	10.6	10.6	10.6	10.0	9.2	8.8	8.8	8.8	8.8	8.8	8.8
87.5°	4.1	6.4	9.2	10.6	11.2	11.3	11.3	11.8	12.2	12.2	12.2
90°	6.4	14.9	25.5	34.0	40.4	42.6	42.6	44.7	46.8	46.8	46.8
92.5°	23.4	37.0	37.4	37.4	45.5	49.4	52.8	53.2	55.3	55.3	55.3
95°	66.0	72.3	108.5	106.4	72.3	57.4	48.9	48.9	48.9	48.9	48.9
97.5°	126.0	135.3	141.3	189.4	200.0	193.2	157.4	132.3	118.3	111.9	118.3
100°	178.7	183.0	195.7	197.9	251.1	302.1	276.6	244.7	234.0	227.7	234.0
102.5°	231.5	234.0	253.6	262.6	274.9	303.8	392.3	382.6	375.3	374.0	375.3
105°	310.6	312.8	348.9	366.0	374.5	374.5	372.3	414.9	483.0	497.9	483.0
107.5°	395.3	405.1	447.7	493.2	503.0	505.5	494.5	488.1	485.5	487.2	485.5
110°	453.2	468.1	519.2	576.6	591.5	595.8	591.5	585.1	580.9	580.9	580.9

TEST NUMBER: P1428574

CATALOG NUMBER: SQ2W-WBM-K-150U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	509.4	531.1	588.9	654.9	680.0	692.8	683.4	678.7	674.5	677.9	674.5
115°	595.8	627.7	704.3	772.3	823.4	829.8	827.7	827.7	825.5	825.5	825.5
117.5°	675.8	726.8	812.8	891.9	951.1	968.1	976.6	974.1	971.5	975.8	971.5
120°	731.9	791.5	889.4	978.7	1036.2	1061.7	1070.2	1066.0	1070.2	1066.0	1070.2
122.5°	791.5	864.7	960.9	1053.6	1121.3	1150.2	1160.4	1161.3	1162.1	1159.6	1162.1
125°	880.9	970.2	1083.0	1178.7	1248.9	1283.0	1291.5	1293.6	1297.9	1308.5	1297.9
127.5°	971.1	1072.4	1196.2	1288.5	1360.4	1401.7	1414.9	1419.6	1428.5	1433.2	1428.5
130°	1034.1	1148.9	1274.5	1361.7	1431.9	1476.6	1500.0	1506.4	1517.0	1514.9	1517.0
132.5°	1100.4	1220.4	1347.7	1438.3	1503.4	1551.5	1571.5	1589.8	1593.6	1596.6	1593.6
135°	1197.9	1327.7	1455.3	1544.7	1606.4	1653.2	1678.7	1695.8	1706.4	1712.8	1706.4
137.5°	1300.4	1437.5	1560.0	1639.6	1701.7	1742.1	1771.1	1789.0	1800.0	1805.1	1800.0
140°	1370.2	1502.1	1621.3	1704.3	1759.6	1800.0	1825.5	1846.8	1859.6	1859.6	1859.6
142.5°	1436.6	1566.8	1682.6	1765.5	1814.1	1851.1	1878.3	1894.5	1909.0	1909.0	1909.0
145°	1529.8	1659.6	1766.0	1849.0	1889.4	1923.4	1953.2	1966.0	1974.5	1974.5	1974.5
147.5°	1627.2	1742.1	1839.2	1918.7	1952.8	1992.8	2016.2	2026.4	2037.0	2032.4	2037.0
150°	1685.1	1791.5	1885.1	1959.6	1993.6	2031.9	2055.3	2063.8	2074.5	2068.1	2074.5
152.5°	1741.3	1842.6	1927.7	1997.0	2026.0	2064.3	2091.1	2099.6	2106.8	2102.1	2106.8
155°	1817.0	1906.4	1985.1	2049.0	2074.5	2110.7	2136.2	2146.8	2155.3	2144.7	2155.3
157.5°	1884.7	1961.7	2030.2	2089.0	2116.2	2147.3	2171.1	2184.3	2192.8	2188.1	2192.8
160°	1925.6	1995.8	2057.5	2112.8	2138.3	2166.0	2191.5	2206.4	2214.9	2208.5	2214.9
162.5°	1959.6	2023.0	2081.3	2131.5	2153.6	2177.9	2208.5	2221.7	2230.2	2222.1	2230.2
165°	2008.5	2059.6	2110.7	2153.2	2172.4	2191.5	2223.4	2238.3	2244.7	2236.2	2244.7
167.5°	2045.6	2084.7	2126.0	2162.6	2176.6	2195.3	2227.3	2239.6	2247.7	2237.0	2247.7
170°	2066.0	2100.0	2136.2	2166.0	2176.6	2193.6	2225.6	2236.2	2242.6	2231.9	2242.6
172.5°	2083.0	2108.5	2137.9	2164.3	2169.8	2183.4	2213.6	2224.3	2229.0	2220.0	2229.0
175°	2100.0	2114.9	2136.2	2153.2	2151.1	2159.6	2185.1	2193.6	2202.1	2189.4	2202.1
177.5°	2108.1	2114.9	2121.7	2131.9	2125.1	2125.1	2143.9	2149.0	2150.7	2143.9	2150.7
180°	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4



TEST NUMBER: P1428574

CATALOG NUMBER: SQ2W-WBM-K-150U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	3682.6	3682.6	3682.6	3682.6	3682.6	3682.6	3682.6	3682.6	3682.6	3682.6	3682.6
2.5°	3691.7	3682.2	3668.3	3668.0	3681.2	3692.2	3696.6	3701.0	3696.6	3692.2	3681.2
5°	3705.0	3689.1	3667.1	3663.6	3678.5	3691.1	3696.5	3702.0	3696.5	3691.1	3678.5
7.5°	3703.6	3692.0	3675.4	3672.8	3684.3	3693.5	3695.8	3698.2	3695.8	3693.5	3684.3
10°	3699.7	3687.3	3670.1	3669.7	3686.2	3698.3	3697.5	3696.7	3697.5	3698.3	3686.2
12.5°	3684.8	3676.0	3662.5	3667.8	3691.8	3708.2	3701.8	3695.3	3701.8	3708.2	3691.8
15°	3636.5	3638.5	3638.5	3655.4	3689.1	3711.3	3698.7	3686.2	3698.7	3711.3	3689.1
17.5°	3549.6	3561.0	3573.1	3601.7	3646.7	3676.8	3661.9	3647.0	3661.9	3676.8	3646.7
20°	3473.3	3489.0	3508.6	3544.7	3597.3	3633.0	3618.1	3603.2	3618.1	3633.0	3597.3
22.5°	3393.6	3411.3	3432.8	3471.8	3528.1	3566.3	3550.1	3534.0	3550.1	3566.3	3528.1
25°	3265.6	3279.5	3295.2	3331.7	3389.0	3428.8	3416.2	3403.7	3416.2	3428.8	3389.0
27.5°	3081.5	3097.9	3115.8	3151.6	3205.3	3243.8	3236.9	3230.0	3236.9	3243.8	3205.3
30°	2940.0	2962.3	2985.9	3018.8	3061.2	3092.2	3089.1	3085.9	3089.1	3092.2	3061.2
32.5°	2784.2	2804.6	2826.9	2856.7	2894.1	2921.3	2918.2	2915.0	2918.2	2921.3	2894.1
35°	2508.2	2531.6	2557.5	2581.8	2604.6	2622.0	2623.6	2625.1	2623.6	2622.0	2604.6
37.5°	2177.0	2196.3	2216.7	2235.9	2253.9	2266.9	2264.7	2262.5	2264.7	2266.9	2253.9
40°	1914.5	1937.8	1967.6	1990.0	2004.9	2015.7	2014.1	2012.6	2014.1	2015.7	2004.9
42.5°	1658.1	1679.8	1702.7	1724.5	1745.0	1754.6	1731.0	1707.5	1731.0	1754.6	1745.0
45°	1241.7	1281.1	1308.6	1322.3	1322.3	1304.4	1233.0	1161.6	1233.0	1304.4	1322.3
47.5°	731.7	815.7	897.3	916.1	872.0	818.6	737.3	656.0	737.3	818.6	872.0
50°	439.0	531.4	644.4	664.4	591.4	523.0	468.0	413.1	468.0	523.0	591.4
52.5°	309.8	385.4	480.9	490.2	413.5	348.9	321.0	293.1	321.0	348.9	413.5
55°	192.6	226.6	269.7	272.1	233.6	202.2	192.0	181.8	192.0	202.2	233.6
57.5°	129.2	143.0	158.1	158.1	143.0	129.1	118.6	108.0	118.6	129.1	143.0
60°	84.3	98.3	114.0	115.5	103.0	91.4	82.8	74.1	82.8	91.4	103.0
62.5°	67.4	77.6	90.1	91.1	80.4	71.5	67.9	64.3	67.9	71.5	80.4
65°	56.1	57.7	59.2	59.6	58.8	58.1	57.3	56.5	57.3	58.1	58.8
67.5°	49.4	49.9	50.1	50.5	51.1	51.4	50.6	49.8	50.6	51.4	51.1
70°	43.9	44.7	45.5	45.9	45.9	45.7	44.9	44.1	44.9	45.7	45.9
72.5°	39.5	40.0	40.2	40.6	41.2	41.5	40.7	39.9	40.7	41.5	41.2
75°	31.6	32.4	33.2	33.5	33.5	33.5	33.5	33.5	33.5	33.5	33.5
77.5°	25.2	25.4	25.4	25.8	26.6	27.0	26.2	25.4	26.2	27.0	26.6
80°	21.0	21.2	21.2	21.6	22.4	22.8	22.0	21.2	22.0	22.8	22.4
82.5°	16.8	16.9	16.9	17.0	17.2	17.3	17.1	16.9	17.1	17.3	17.2
85°	8.8	8.8	8.8	9.2	10.0	10.6	10.6	10.6	10.6	10.6	10.0
87.5°	11.8	11.3	11.3	11.2	10.6	9.2	6.4	4.1	6.4	8.8	11.4
90°	44.7	42.6	42.6	40.4	34.0	25.5	14.9	6.4	14.9	23.4	38.3
92.5°	53.2	52.8	49.4	45.5	37.4	37.4	37.0	23.4	40.4	57.4	82.6
95°	48.9	48.9	57.4	72.3	106.4	108.5	72.3	66.0	93.6	131.9	166.0
97.5°	132.3	157.4	193.2	200.0	189.4	141.3	135.3	126.0	171.5	209.4	264.3
100°	244.7	276.6	302.1	251.1	197.9	195.7	183.0	178.7	227.7	263.8	317.0
102.5°	382.6	392.3	303.8	274.9	262.6	253.6	234.0	231.5	280.4	330.2	374.9
105°	414.9	372.3	374.5	374.5	366.0	348.9	312.8	310.6	366.0	423.4	478.7
107.5°	488.1	494.5	505.5	503.0	493.2	447.7	405.1	395.3	445.1	514.0	574.9
110°	585.1	591.5	595.8	591.5	576.6	519.2	468.1	453.2	497.9	570.2	636.2



TEST NUMBER: P1428574

CATALOG NUMBER: SQ2W-WBM-K-150U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	678.7	683.4	692.8	680.0	654.9	588.9	531.1	509.4	554.0	628.1	695.8
115°	827.7	827.7	829.8	823.4	772.3	704.3	627.7	595.8	634.0	702.1	776.6
117.5°	974.1	976.6	968.1	951.1	891.9	812.8	726.8	675.8	706.0	777.9	854.5
120°	1066.0	1070.2	1061.7	1036.2	978.7	889.4	791.5	731.9	755.3	825.5	902.1
122.5°	1161.3	1160.4	1150.2	1121.3	1053.6	960.9	864.7	791.5	801.3	866.4	941.3
125°	1293.6	1291.5	1283.0	1248.9	1178.7	1083.0	970.2	880.9	868.1	923.4	1000.0
127.5°	1419.6	1414.9	1401.7	1360.4	1288.5	1196.2	1072.4	971.1	942.6	977.5	1047.7
130°	1506.4	1500.0	1476.6	1431.9	1361.7	1274.5	1148.9	1034.1	993.6	1014.9	1076.6
132.5°	1589.8	1571.5	1551.5	1503.4	1438.3	1347.7	1220.4	1100.4	1044.7	1054.1	1102.1
135°	1695.8	1678.7	1653.2	1606.4	1544.7	1455.3	1327.7	1197.9	1121.3	1112.8	1140.4
137.5°	1789.0	1771.1	1742.1	1701.7	1639.6	1560.0	1437.5	1300.4	1203.8	1175.3	1186.0
140°	1846.8	1825.5	1800.0	1759.6	1704.3	1621.3	1502.1	1370.2	1261.7	1221.3	1214.9
142.5°	1894.5	1878.3	1851.1	1814.1	1765.5	1682.6	1566.8	1436.6	1321.3	1268.9	1254.1
145°	1966.0	1953.2	1923.4	1889.4	1849.0	1766.0	1659.6	1529.8	1414.9	1346.8	1314.9
147.5°	2026.4	2016.2	1992.8	1952.8	1918.7	1839.2	1742.1	1627.2	1509.4	1425.1	1383.8
150°	2063.8	2055.3	2031.9	1993.6	1959.6	1885.1	1791.5	1685.1	1572.4	1483.0	1429.8
152.5°	2099.6	2091.1	2064.3	2026.0	1997.0	1927.7	1842.6	1741.3	1626.8	1537.5	1482.6
155°	2146.8	2136.2	2110.7	2074.5	2049.0	1985.1	1906.4	1817.0	1719.2	1625.5	1563.8
157.5°	2184.3	2171.1	2147.3	2116.2	2089.0	2030.2	1961.7	1884.7	1799.2	1709.8	1646.8
160°	2206.4	2191.5	2166.0	2138.3	2112.8	2057.5	1995.8	1925.6	1846.8	1766.0	1697.9
162.5°	2221.7	2208.5	2177.9	2153.6	2131.5	2081.3	2023.0	1959.6	1889.4	1818.7	1755.8
165°	2238.3	2223.4	2191.5	2172.4	2153.2	2110.7	2059.6	2008.5	1949.0	1891.5	1840.4
167.5°	2239.6	2227.3	2195.3	2176.6	2162.6	2126.0	2084.7	2045.6	1999.2	1954.1	1911.5
170°	2236.2	2225.6	2193.6	2176.6	2166.0	2136.2	2100.0	2066.0	2029.8	1991.5	1957.5
172.5°	2224.3	2213.6	2183.4	2169.8	2164.3	2137.9	2108.5	2083.0	2051.9	2023.8	1996.6
175°	2193.6	2185.1	2159.6	2151.1	2153.2	2136.2	2114.9	2100.0	2080.9	2063.8	2049.0
177.5°	2149.0	2143.9	2125.1	2125.1	2131.9	2121.7	2114.9	2108.1	2099.6	2094.5	2089.4
180°	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4



TEST NUMBER: P1428574

CATALOG NUMBER: SQ2W-WBM-K-150U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	3682.6	3682.6	3682.6	3682.6	3682.6	3682.6	3682.6	3682.6	3682.6	3682.6	3682.6
2.5°	3668.0	3668.3	3682.2	3691.7	3688.6	3685.4	3688.6	3691.7	3682.2	3668.3	3668.0
5°	3663.6	3667.1	3689.1	3705.0	3702.6	3700.3	3702.6	3705.0	3689.1	3667.1	3663.6
7.5°	3672.8	3675.4	3692.0	3703.6	3700.0	3696.4	3700.0	3703.6	3692.0	3675.4	3672.8
10°	3669.7	3670.1	3687.3	3699.7	3697.3	3695.0	3697.3	3699.7	3687.3	3670.1	3669.7
12.5°	3667.8	3662.5	3676.0	3684.8	3679.3	3673.8	3679.3	3684.8	3676.0	3662.5	3667.8
15°	3655.4	3638.5	3638.5	3636.5	3628.7	3620.8	3628.7	3636.5	3638.5	3638.5	3655.4
17.5°	3601.7	3573.1	3561.0	3549.6	3540.0	3530.4	3540.0	3549.6	3561.0	3573.1	3601.7
20°	3544.7	3508.6	3489.0	3473.3	3469.4	3465.5	3469.4	3473.3	3489.0	3508.6	3544.7
22.5°	3471.8	3432.8	3411.3	3393.6	3387.2	3380.7	3387.2	3393.6	3411.3	3432.8	3471.8
25°	3331.7	3295.2	3279.5	3265.6	3257.0	3248.3	3257.0	3265.6	3279.5	3295.2	3331.7
27.5°	3151.6	3115.8	3097.9	3081.5	3069.6	3057.7	3069.6	3081.5	3097.9	3115.8	3151.6
30°	3018.8	2985.9	2962.3	2940.0	2921.1	2902.3	2921.1	2940.0	2962.3	2985.9	3018.8
32.5°	2856.7	2826.9	2804.6	2784.2	2769.1	2754.0	2769.1	2784.2	2804.6	2826.9	2856.7
35°	2581.8	2557.5	2531.6	2508.2	2492.5	2476.9	2492.5	2508.2	2531.6	2557.5	2581.8
37.5°	2235.9	2216.7	2196.3	2177.0	2161.2	2145.3	2161.2	2177.0	2196.3	2216.7	2235.9
40°	1990.0	1967.6	1937.8	1914.5	1910.6	1906.6	1910.6	1914.5	1937.8	1967.6	1990.0
42.5°	1724.5	1702.7	1679.8	1658.1	1639.7	1621.3	1639.7	1658.1	1679.8	1702.7	1724.5
45°	1322.3	1308.6	1281.1	1241.7	1166.3	1091.0	1166.3	1241.7	1281.1	1308.6	1322.3
47.5°	916.1	897.3	815.7	731.7	640.2	548.7	640.2	731.7	815.7	897.3	916.1
50°	664.4	644.4	531.4	439.0	408.4	377.8	408.4	439.0	531.4	644.4	664.4
52.5°	490.2	480.9	385.4	309.8	293.7	277.5	293.7	309.8	385.4	480.9	490.2
55°	272.1	269.7	226.6	192.6	186.3	180.1	186.3	192.6	226.6	269.7	272.1
57.5°	158.1	158.1	143.0	129.2	119.3	109.5	119.3	129.2	143.0	158.1	158.1
60°	115.5	114.0	98.3	84.3	75.7	67.1	75.7	84.3	98.3	114.0	115.5
62.5°	91.1	90.1	77.6	67.4	64.4	61.4	64.4	67.4	77.6	90.1	91.1
65°	59.6	59.2	57.7	56.1	54.5	53.0	54.5	56.1	57.7	59.2	59.6
67.5°	50.5	50.1	49.9	49.4	48.0	46.6	48.0	49.4	49.9	50.1	50.5
70°	45.9	45.5	44.7	43.9	43.2	42.4	43.2	43.9	44.7	45.5	45.9
72.5°	40.6	40.2	40.0	39.5	38.1	36.7	38.1	39.5	40.0	40.2	40.6
75°	33.5	33.2	32.4	31.6	30.8	30.0	30.8	31.6	32.4	33.2	33.5
77.5°	25.8	25.4	25.4	25.2	24.4	23.7	24.4	25.2	25.4	25.4	25.8
80°	21.6	21.2	21.2	21.0	20.2	19.4	20.2	21.0	21.2	21.2	21.6
82.5°	17.0	16.9	16.9	16.8	16.0	15.2	16.0	16.8	16.9	16.9	17.0
85°	9.2	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8	9.2
87.5°	12.9	15.6	18.6	20.3	22.0	21.1	22.0	20.3	18.6	15.6	12.9
90°	48.9	63.8	78.7	87.2	95.7	91.5	95.7	87.2	78.7	63.8	48.9
92.5°	98.3	123.4	141.7	157.0	163.8	163.0	163.8	157.0	141.7	123.4	98.3
95°	197.9	227.7	257.4	278.7	291.5	287.2	291.5	278.7	257.4	227.7	197.9
97.5°	305.1	345.1	378.3	398.3	411.1	419.6	411.1	398.3	378.3	345.1	305.1
100°	376.6	414.9	453.2	476.6	497.9	506.4	497.9	476.6	453.2	414.9	376.6
102.5°	434.5	484.7	526.4	551.5	569.4	577.9	569.4	551.5	526.4	484.7	434.5
105°	529.8	583.0	627.7	659.6	678.7	685.1	678.7	659.6	627.7	583.0	529.8
107.5°	625.1	680.0	721.3	756.6	780.0	793.6	780.0	756.6	721.3	680.0	625.1
110°	700.0	744.7	789.4	821.3	844.7	853.2	844.7	821.3	789.4	744.7	700.0



TEST NUMBER: P1428574

CATALOG NUMBER: SQ2W-WBM-K-150U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	763.0	812.8	857.5	889.4	916.2	928.1	916.2	889.4	857.5	812.8	763.0
115°	851.1	917.0	957.5	987.2	1006.4	1017.0	1006.4	987.2	957.5	917.0	851.1
117.5°	924.3	993.2	1037.5	1060.4	1069.4	1077.0	1069.4	1060.4	1037.5	993.2	924.3
120°	970.2	1034.1	1085.1	1114.9	1125.5	1129.8	1125.5	1114.9	1085.1	1034.1	970.2
122.5°	1012.8	1073.2	1122.6	1159.2	1176.6	1180.9	1176.6	1159.2	1122.6	1073.2	1012.8
125°	1072.4	1129.8	1180.9	1217.0	1236.2	1246.8	1236.2	1217.0	1180.9	1129.8	1072.4
127.5°	1124.3	1186.4	1233.2	1266.0	1284.7	1293.2	1284.7	1266.0	1233.2	1186.4	1124.3
130°	1153.2	1217.0	1263.8	1300.0	1317.0	1325.5	1317.0	1300.0	1263.8	1217.0	1153.2
132.5°	1175.3	1242.6	1291.1	1323.8	1342.6	1351.1	1342.6	1323.8	1291.1	1242.6	1175.3
135°	1202.1	1272.4	1323.4	1355.3	1372.4	1380.9	1372.4	1355.3	1323.4	1272.4	1202.1
137.5°	1225.5	1289.4	1342.6	1376.2	1391.5	1397.0	1391.5	1376.2	1342.6	1289.4	1225.5
140°	1242.6	1297.9	1351.1	1383.0	1400.0	1402.1	1400.0	1383.0	1351.1	1297.9	1242.6
142.5°	1264.7	1308.1	1354.5	1386.4	1403.4	1407.2	1403.4	1386.4	1354.5	1308.1	1264.7
145°	1304.3	1329.8	1361.7	1391.5	1406.4	1410.7	1406.4	1391.5	1361.7	1329.8	1304.3
147.5°	1354.1	1362.1	1378.7	1398.3	1412.8	1415.8	1412.8	1398.3	1378.7	1362.1	1354.1
150°	1391.5	1389.4	1395.8	1408.5	1421.3	1419.2	1421.3	1408.5	1395.8	1389.4	1391.5
152.5°	1434.1	1421.7	1421.3	1427.2	1433.2	1432.8	1433.2	1427.2	1421.3	1421.7	1434.1
155°	1506.4	1483.0	1470.2	1466.0	1466.0	1463.8	1466.0	1466.0	1470.2	1483.0	1506.4
157.5°	1586.0	1553.2	1534.1	1523.8	1520.9	1516.2	1520.9	1523.8	1534.1	1553.2	1586.0
160°	1640.4	1604.3	1585.1	1568.1	1561.7	1555.3	1561.7	1568.1	1585.1	1604.3	1640.4
162.5°	1691.5	1657.0	1636.2	1620.9	1614.5	1604.7	1614.5	1620.9	1636.2	1657.0	1691.5
165°	1774.5	1738.3	1714.9	1702.1	1693.6	1685.1	1693.6	1702.1	1714.9	1738.3	1774.5
167.5°	1857.5	1817.9	1802.6	1788.1	1780.0	1764.7	1780.0	1788.1	1802.6	1817.9	1857.5
170°	1908.5	1872.4	1863.8	1851.1	1836.2	1819.2	1836.2	1851.1	1863.8	1872.4	1908.5
172.5°	1952.8	1928.5	1920.0	1907.3	1902.6	1889.0	1902.6	1907.3	1920.0	1928.5	1952.8
175°	2017.0	1997.9	1997.9	1995.8	1989.4	1976.6	1989.4	1995.8	1997.9	1997.9	2017.0
177.5°	2070.7	2060.4	2067.3	2067.3	2065.6	2053.6	2065.6	2067.3	2067.3	2060.4	2070.7
180°	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4	2106.4



TEST NUMBER: P1428574

CATALOG NUMBER: SQ2W-WBM-K-150U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	3682.6	3682.6	3682.6	3682.6
2.5°	3681.2	3692.2	3696.6	3701.0
5°	3678.5	3691.1	3696.5	3702.0
7.5°	3684.3	3693.5	3695.8	3698.2
10°	3686.2	3698.3	3697.5	3696.7
12.5°	3691.8	3708.2	3701.8	3695.3
15°	3689.1	3711.3	3698.7	3686.2
17.5°	3646.7	3676.8	3661.9	3647.0
20°	3597.3	3633.0	3618.1	3603.2
22.5°	3528.1	3566.3	3550.1	3534.0
25°	3389.0	3428.8	3416.2	3403.7
27.5°	3205.3	3243.8	3236.9	3230.0
30°	3061.2	3092.2	3089.1	3085.9
32.5°	2894.1	2921.3	2918.2	2915.0
35°	2604.6	2622.0	2623.6	2625.1
37.5°	2253.9	2266.9	2264.7	2262.5
40°	2004.9	2015.7	2014.1	2012.6
42.5°	1745.0	1754.6	1731.0	1707.5
45°	1322.3	1304.4	1233.0	1161.6
47.5°	872.0	818.6	737.3	656.0
50°	591.4	523.0	468.0	413.1
52.5°	413.5	348.9	321.0	293.1
55°	233.6	202.2	192.0	181.8
57.5°	143.0	129.1	118.6	108.0
60°	103.0	91.4	82.8	74.1
62.5°	80.4	71.5	67.9	64.3
65°	58.8	58.1	57.3	56.5
67.5°	51.1	51.4	50.6	49.8
70°	45.9	45.7	44.9	44.1
72.5°	41.2	41.5	40.7	39.9
75°	33.5	33.5	33.5	33.5
77.5°	26.6	27.0	26.2	25.4
80°	22.4	22.8	22.0	21.2
82.5°	17.2	17.3	17.1	16.9
85°	10.0	10.6	10.6	10.6
87.5°	11.4	8.8	6.4	4.1
90°	38.3	23.4	14.9	6.4
92.5°	82.6	57.4	40.4	23.4
95°	166.0	131.9	93.6	66.0
97.5°	264.3	209.4	171.5	126.0
100°	317.0	263.8	227.7	178.7
102.5°	374.9	330.2	280.4	231.5
105°	478.7	423.4	366.0	310.6
107.5°	574.9	514.0	445.1	395.3
110°	636.2	570.2	497.9	453.2



TEST NUMBER: P1428574

CATALOG NUMBER: SQ2W-WBM-K-150U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	695.8	628.1	554.0	509.4
115°	776.6	702.1	634.0	595.8
117.5°	854.5	777.9	706.0	675.8
120°	902.1	825.5	755.3	731.9
122.5°	941.3	866.4	801.3	791.5
125°	1000.0	923.4	868.1	880.9
127.5°	1047.7	977.5	942.6	971.1
130°	1076.6	1014.9	993.6	1034.1
132.5°	1102.1	1054.1	1044.7	1100.4
135°	1140.4	1112.8	1121.3	1197.9
137.5°	1186.0	1175.3	1203.8	1300.4
140°	1214.9	1221.3	1261.7	1370.2
142.5°	1254.1	1268.9	1321.3	1436.6
145°	1314.9	1346.8	1414.9	1529.8
147.5°	1383.8	1425.1	1509.4	1627.2
150°	1429.8	1483.0	1572.4	1685.1
152.5°	1482.6	1537.5	1626.8	1741.3
155°	1563.8	1625.5	1719.2	1817.0
157.5°	1646.8	1709.8	1799.2	1884.7
160°	1697.9	1766.0	1846.8	1925.6
162.5°	1755.8	1818.7	1889.4	1959.6
165°	1840.4	1891.5	1949.0	2008.5
167.5°	1911.5	1954.1	1999.2	2045.6
170°	1957.5	1991.5	2029.8	2066.0
172.5°	1996.6	2023.8	2051.9	2083.0
175°	2049.0	2063.8	2080.9	2100.0
177.5°	2089.4	2094.5	2099.6	2108.1
180°	2106.4	2106.4	2106.4	2106.4



TEST NUMBER: P1428574

CATALOG NUMBER: SQ2W-WBM-K-150U-125D-L940-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.96	6.67	6.96	7.66	8.97	5.94	6.65	6.94	7.64	8.95
	3H	6.65	7.28	7.66	8.28	9.61	6.56	7.19	7.57	8.19	9.52
	4H	7.01	7.60	8.03	8.61	9.94	6.87	7.46	7.89	8.46	9.80
	6H	7.28	7.82	8.31	8.83	10.18	7.10	7.64	8.13	8.65	10.00
	8H	7.39	7.91	8.43	8.94	10.28	7.19	7.71	8.23	8.73	10.08
	12H	7.47	7.96	8.51	8.98	10.34	7.24	7.74	8.29	8.75	10.12
4H	2H	6.05	6.64	7.08	7.65	8.98	6.03	6.63	7.06	7.63	8.97
	3H	6.99	7.48	8.02	8.51	9.86	6.90	7.39	7.94	8.42	9.77
	4H	7.49	7.94	8.53	8.96	10.34	7.34	7.79	8.38	8.81	10.19
	6H	7.92	8.30	8.97	9.35	10.72	7.72	8.10	8.77	9.15	10.52
	8H	8.11	8.46	9.16	9.50	10.88	7.88	8.24	8.93	9.28	10.66
	12H	8.23	8.55	9.30	9.61	10.99	7.97	8.29	9.04	9.35	10.73
8H	4H	7.61	7.96	8.66	9.00	10.38	7.47	7.83	8.52	8.87	10.25
	6H	8.18	8.48	9.26	9.56	10.94	7.99	8.28	9.06	9.36	10.74
	8H	8.48	8.73	9.56	9.80	11.20	8.26	8.51	9.34	9.58	10.98
	12H	8.69	8.92	9.77	9.98	11.42	8.43	8.65	9.51	9.71	11.15
12H	4H	7.58	7.90	8.65	8.96	10.34	7.46	7.78	8.52	8.83	10.21
	6H	8.22	8.48	9.30	9.54	10.94	8.04	8.29	9.12	9.36	10.76
	8H	8.54	8.77	9.63	9.83	11.27	8.34	8.56	9.42	9.62	11.06