

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428592

Luminaire Tested: SQ2W-WBN-K-025U-075D-L940-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428592
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2308-130-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-WBN-K-025U-075D-L940-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - WHITE DISCREET BAFFLE, NARROW 35-DEGREE OPTIC
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4490.2 lumens
Efficiency: N/A
Efficacy: 127.9 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.58 / 0.63
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 35.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428592

CATALOG NUMBER: SQ2W-WBN-K-025U-075D-L940-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428592

CATALOG NUMBER: SQ2W-WBN-K-025U-075D-L940-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	518.0	11.5
10°-20°	1029.4	22.9
20°-30°	852.5	19.0
30°-40°	613.3	13.7
40°-50°	312.4	7.0
50°-60°	81.2	1.8
60°-70°	33.7	0.8
70°-80°	18.7	0.4
80°-90°	7.0	0.2
90°-100°	27.9	0.6
100°-110°	81.4	1.8
110°-120°	132.8	3.0
120°-130°	168.5	3.8
130°-140°	180.3	4.0
140°-150°	168.4	3.8
150°-160°	138.6	3.1
160°-170°	92.9	2.1
170°-180°	33.0	0.7
0°-30°	2399.9	53.4
0°-40°	3013.2	67.1
0°-60°	3406.8	75.9
0°-90°	3466.3	77.2
90°-120°	242.1	5.4
90°-150°	759.4	16.9
90°-180°	1024.0	22.8
0°-180°	4490.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	5967	5967	5967	5967	5967	
5°	5739	5746	5739	5746	5739	518
15°	3828	3722	3828	3722	3828	1039
25°	1836	1787	1836	1787	1836	863
35°	995	953	995	953	995	624
45°	364	325	364	325	364	291
55°	64	60	64	60	64	62
65°	33	31	33	31	33	33
75°	18	17	18	17	18	19
85°	5	4	5	4	5	6
90°	1	8	1	15	1	1
95°	11	8	11	48	11	13
105°	52	83	52	114	52	55
115°	99	137	99	169	99	98
125°	147	218	147	208	147	131
135°	199	285	199	230	199	154
145°	255	329	255	235	255	159
155°	302	357	302	244	302	139
165°	334	372	334	280	334	94
175°	350	364	350	329	350	33
180°	351	351	351	351	351	



TEST NUMBER: P1428592

CATALOG NUMBER: SQ2W-WBN-K-025U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8
2.5°	5957.5	5953.0	5948.5	5928.4	5903.2	5901.2	5922.2	5936.7	5931.5	5926.2	5931.5
5°	5739.3	5735.5	5731.7	5714.6	5692.9	5700.4	5737.1	5762.5	5754.1	5745.6	5754.1
7.5°	5288.5	5291.7	5294.9	5286.1	5273.3	5283.2	5315.6	5337.7	5328.7	5319.7	5328.7
10°	4904.1	4912.6	4921.0	4909.0	4890.2	4904.6	4952.1	4979.7	4947.7	4915.7	4947.7
12.5°	4479.8	4474.4	4468.9	4458.0	4445.2	4442.6	4450.2	4451.5	4433.8	4416.1	4433.8
15°	3827.6	3807.8	3788.1	3757.7	3723.8	3712.8	3724.6	3732.1	3726.9	3721.7	3726.9
17.5°	3083.0	3090.6	3098.3	3077.7	3047.8	3032.3	3031.2	3028.9	3023.0	3017.2	3023.0
20°	2645.2	2647.6	2649.9	2637.1	2619.2	2615.0	2624.4	2631.2	2630.3	2629.3	2630.3
22.5°	2292.9	2293.4	2293.9	2276.9	2254.2	2249.7	2263.7	2272.0	2263.5	2255.1	2263.5
25°	1835.5	1834.0	1832.6	1821.3	1806.8	1795.9	1788.9	1783.9	1785.4	1786.8	1785.4
27.5°	1505.2	1499.4	1493.5	1483.9	1473.0	1469.9	1474.6	1477.2	1473.8	1470.3	1473.8
30°	1340.1	1335.4	1330.7	1321.0	1309.7	1305.5	1308.3	1309.4	1305.1	1300.9	1305.1
32.5°	1191.9	1192.1	1192.3	1183.6	1171.9	1165.4	1164.1	1162.3	1159.2	1156.1	1159.2
35°	995.0	997.8	1000.6	993.6	983.2	974.5	967.5	961.1	956.9	952.7	956.9
37.5°	819.3	821.9	824.6	818.7	809.9	800.4	790.0	781.3	777.8	774.2	777.8
40°	705.0	706.9	708.7	704.6	698.5	689.3	677.1	667.2	664.4	661.6	664.4
42.5°	580.5	588.4	596.3	593.7	587.6	578.8	567.3	557.1	550.9	544.7	550.9
45°	364.1	389.1	414.0	425.2	431.8	428.7	416.0	397.4	361.2	325.0	361.2
47.5°	184.2	218.7	253.2	278.0	299.6	292.7	257.4	222.1	186.5	150.9	186.5
50°	116.4	140.4	164.4	194.8	227.2	220.2	173.6	134.7	118.7	102.7	118.7
52.5°	89.3	101.7	114.0	142.8	177.2	173.9	132.9	100.0	91.2	82.4	91.2
55°	63.5	68.2	72.9	88.9	108.7	107.5	85.4	67.9	64.1	60.3	64.1
57.5°	49.1	51.7	54.4	60.3	67.4	66.7	58.4	51.5	49.1	46.8	49.1
60°	42.3	44.2	46.1	49.0	52.3	51.9	47.6	43.9	41.5	39.2	41.5
62.5°	38.1	39.2	40.4	41.7	43.1	42.5	39.7	37.5	36.6	35.8	36.6
65°	32.8	33.3	33.8	33.9	33.9	33.4	32.5	31.6	31.2	30.7	31.2
67.5°	27.9	28.4	28.9	28.9	28.8	28.6	28.1	27.6	27.1	26.7	27.1
70°	25.4	25.9	26.3	26.1	25.6	25.2	24.7	24.2	23.8	23.3	23.8
72.5°	22.0	22.5	23.0	22.7	22.3	22.0	21.9	21.7	21.2	20.7	21.2
75°	18.0	18.0	18.0	18.0	18.0	17.8	17.3	16.9	16.9	16.9	16.9
77.5°	14.0	14.1	14.2	13.8	13.4	13.1	13.1	13.0	12.7	12.3	12.7
80°	10.6	11.1	11.5	11.3	10.8	10.6	10.6	10.6	10.6	10.6	10.6
82.5°	8.9	9.0	9.1	8.8	8.3	8.0	8.0	8.0	8.0	8.0	8.0
85°	5.3	5.3	5.3	4.9	4.5	4.5	4.9	5.2	4.7	4.2	4.7
87.5°	1.9	2.2	2.5	2.8	3.0	3.1	3.1	3.2	3.3	3.3	3.3
90°	1.1	2.5	4.3	5.7	6.7	7.1	7.1	7.4	7.8	7.8	7.8
92.5°	3.9	6.2	6.2	6.2	7.6	8.2	8.8	8.9	9.2	9.2	9.2
95°	11.0	12.0	18.1	17.7	12.0	9.6	8.1	8.1	8.1	8.1	8.1
97.5°	21.0	22.5	23.5	31.5	33.3	32.2	26.2	22.0	19.7	18.6	19.7
100°	29.8	30.5	32.6	32.9	41.8	50.3	46.0	40.7	39.0	37.9	39.0
102.5°	38.5	39.0	42.2	43.7	45.8	50.6	65.3	63.7	62.5	62.3	62.5
105°	51.7	52.1	58.1	60.9	62.3	62.3	62.0	69.1	80.4	82.9	80.4
107.5°	65.8	67.4	74.5	82.1	83.7	84.2	82.3	81.3	80.8	81.1	80.8
110°	75.4	77.9	86.4	96.0	98.5	99.2	98.5	97.4	96.7	96.7	96.7



TEST NUMBER: P1428592

CATALOG NUMBER: SQ2W-WBN-K-025U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	84.8	88.4	98.0	109.0	113.2	115.3	113.8	113.0	112.3	112.9	112.3
115°	99.2	104.5	117.2	128.6	137.1	138.1	137.8	137.8	137.4	137.4	137.4
117.5°	112.5	121.0	135.3	148.5	158.3	161.2	162.6	162.2	161.7	162.4	161.7
120°	121.9	131.8	148.1	162.9	172.5	176.8	178.2	177.5	178.2	177.5	178.2
122.5°	131.8	144.0	160.0	175.4	186.7	191.5	193.2	193.3	193.5	193.1	193.5
125°	146.6	161.5	180.3	196.2	207.9	213.6	215.0	215.4	216.1	217.8	216.1
127.5°	161.7	178.5	199.1	214.5	226.5	233.4	235.6	236.3	237.8	238.6	237.8
130°	172.2	191.3	212.2	226.7	238.4	245.8	249.7	250.8	252.6	252.2	252.6
132.5°	183.2	203.2	224.4	239.5	250.3	258.3	261.6	264.7	265.3	265.8	265.3
135°	199.4	221.0	242.3	257.2	267.4	275.2	279.5	282.3	284.1	285.1	284.1
137.5°	216.5	239.3	259.7	273.0	283.3	290.0	294.9	297.8	299.7	300.5	299.7
140°	228.1	250.1	269.9	283.7	292.9	299.7	303.9	307.5	309.6	309.6	309.6
142.5°	239.2	260.9	280.1	293.9	302.0	308.2	312.7	315.4	317.8	317.8	317.8
145°	254.7	276.3	294.0	307.8	314.6	320.2	325.2	327.3	328.7	328.7	328.7
147.5°	270.9	290.0	306.2	319.4	325.1	331.8	335.7	337.4	339.1	338.4	339.1
150°	280.5	298.3	313.8	326.2	331.9	338.3	342.2	343.6	345.4	344.3	345.4
152.5°	289.9	306.8	320.9	332.5	337.3	343.7	348.1	349.5	350.8	350.0	350.8
155°	302.5	317.4	330.5	341.1	345.4	351.4	355.6	357.4	358.8	357.1	358.8
157.5°	313.8	326.6	338.0	347.8	352.3	357.5	361.4	363.6	365.1	364.3	365.1
160°	320.6	332.3	342.5	351.7	356.0	360.6	364.9	367.3	368.7	367.7	368.7
162.5°	326.2	336.8	346.5	354.9	358.5	362.6	367.7	369.9	371.3	370.0	371.3
165°	334.4	342.9	351.4	358.5	361.7	364.9	370.2	372.6	373.7	372.3	373.7
167.5°	340.6	347.1	353.9	360.0	362.4	365.5	370.8	372.9	374.2	372.4	374.2
170°	344.0	349.6	355.6	360.6	362.4	365.2	370.5	372.3	373.4	371.6	373.4
172.5°	346.8	351.0	355.9	360.3	361.2	363.5	368.5	370.3	371.1	369.6	371.1
175°	349.6	352.1	355.6	358.5	358.1	359.5	363.8	365.2	366.6	364.5	366.6
177.5°	351.0	352.1	353.2	354.9	353.8	353.8	356.9	357.8	358.0	356.9	358.0
180°	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7



TEST NUMBER: P1428592

CATALOG NUMBER: SQ2W-WBN-K-025U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8
2.5°	5936.7	5922.2	5901.2	5903.2	5928.4	5948.5	5953.0	5957.5	5953.0	5948.5	5928.4
5°	5762.5	5737.1	5700.4	5692.9	5714.6	5731.7	5735.5	5739.3	5735.5	5731.7	5714.6
7.5°	5337.7	5315.6	5283.2	5273.3	5286.1	5294.9	5291.7	5288.5	5291.7	5294.9	5286.1
10°	4979.7	4952.1	4904.6	4890.2	4909.0	4921.0	4912.6	4904.1	4912.6	4921.0	4909.0
12.5°	4451.5	4450.2	4442.6	4445.2	4458.0	4468.9	4474.4	4479.8	4474.4	4468.9	4458.0
15°	3732.1	3724.6	3712.8	3723.8	3757.7	3788.1	3807.8	3827.6	3807.8	3788.1	3757.7
17.5°	3028.9	3031.2	3032.3	3047.8	3077.7	3098.3	3090.6	3083.0	3090.6	3098.3	3077.7
20°	2631.2	2624.4	2615.0	2619.2	2637.1	2649.9	2647.6	2645.2	2647.6	2649.9	2637.1
22.5°	2272.0	2263.7	2249.7	2254.2	2276.9	2293.9	2293.4	2292.9	2293.4	2293.9	2276.9
25°	1783.9	1788.9	1795.9	1806.8	1821.3	1832.6	1834.0	1835.5	1834.0	1832.6	1821.3
27.5°	1477.2	1474.6	1469.9	1473.0	1483.9	1493.5	1499.4	1505.2	1499.4	1493.5	1483.9
30°	1309.4	1308.3	1305.5	1309.7	1321.0	1330.7	1335.4	1340.1	1335.4	1330.7	1321.0
32.5°	1162.3	1164.1	1165.4	1171.9	1183.6	1192.3	1192.1	1191.9	1192.1	1192.3	1183.6
35°	961.1	967.5	974.5	983.2	993.6	1000.6	997.8	995.0	997.8	1000.6	993.6
37.5°	781.3	790.0	800.4	809.9	818.7	824.6	821.9	819.3	821.9	824.6	818.7
40°	667.2	677.1	689.3	698.5	704.6	708.7	706.9	705.0	706.9	708.7	704.6
42.5°	557.1	567.3	578.8	587.6	593.7	596.3	588.4	580.5	588.4	596.3	593.7
45°	397.4	416.0	428.7	431.8	425.2	414.0	389.1	364.1	389.1	414.0	425.2
47.5°	222.1	257.4	292.7	299.6	278.0	253.2	218.7	184.2	218.7	253.2	278.0
50°	134.7	173.6	220.2	227.2	194.8	164.4	140.4	116.4	140.4	164.4	194.8
52.5°	100.0	132.9	173.9	177.2	142.8	114.0	101.7	89.3	101.7	114.0	142.8
55°	67.9	85.4	107.5	108.7	88.9	72.9	68.2	63.5	68.2	72.9	88.9
57.5°	51.5	58.4	66.7	67.4	60.3	54.4	51.7	49.1	51.7	54.4	60.3
60°	43.9	47.6	51.9	52.3	49.0	46.1	44.2	42.3	44.2	46.1	49.0
62.5°	37.5	39.7	42.5	43.1	41.7	40.4	39.2	38.1	39.2	40.4	41.7
65°	31.6	32.5	33.4	33.9	33.9	33.8	33.3	32.8	33.3	33.8	33.9
67.5°	27.6	28.1	28.6	28.8	28.9	28.9	28.4	27.9	28.4	28.9	28.9
70°	24.2	24.7	25.2	25.6	26.1	26.3	25.9	25.4	25.9	26.3	26.1
72.5°	21.7	21.9	22.0	22.3	22.7	23.0	22.5	22.0	22.5	23.0	22.7
75°	16.9	17.3	17.8	18.0	18.0	18.0	18.0	18.0	18.0	18.0	18.0
77.5°	13.0	13.1	13.1	13.4	13.8	14.2	14.1	14.0	14.1	14.2	13.8
80°	10.6	10.6	10.6	10.8	11.3	11.5	11.1	10.6	11.1	11.5	11.3
82.5°	8.0	8.0	8.0	8.3	8.8	9.1	9.0	8.9	9.0	9.1	8.8
85°	5.2	4.9	4.5	4.5	4.9	5.3	5.3	5.3	5.3	5.3	4.9
87.5°	3.2	3.1	3.1	3.0	2.8	2.5	2.2	1.9	2.2	2.5	3.0
90°	7.4	7.1	7.1	6.7	5.7	4.3	2.5	1.1	2.5	3.9	6.4
92.5°	8.9	8.8	8.2	7.6	6.2	6.2	6.2	3.9	6.7	9.6	13.7
95°	8.1	8.1	9.6	12.0	17.7	18.1	12.0	11.0	15.6	22.0	27.6
97.5°	22.0	26.2	32.2	33.3	31.5	23.5	22.5	21.0	28.6	34.9	44.0
100°	40.7	46.0	50.3	41.8	32.9	32.6	30.5	29.8	37.9	43.9	52.8
102.5°	63.7	65.3	50.6	45.8	43.7	42.2	39.0	38.5	46.7	55.0	62.4
105°	69.1	62.0	62.3	62.3	60.9	58.1	52.1	51.7	60.9	70.5	79.7
107.5°	81.3	82.3	84.2	83.7	82.1	74.5	67.4	65.8	74.1	85.6	95.7
110°	97.4	98.5	99.2	98.5	96.0	86.4	77.9	75.4	82.9	94.9	105.9



TEST NUMBER: P1428592

CATALOG NUMBER: SQ2W-WBN-K-025U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	113.0	113.8	115.3	113.2	109.0	98.0	88.4	84.8	92.2	104.6	115.8
115°	137.8	137.8	138.1	137.1	128.6	117.2	104.5	99.2	105.6	116.9	129.3
117.5°	162.2	162.6	161.2	158.3	148.5	135.3	121.0	112.5	117.5	129.5	142.3
120°	177.5	178.2	176.8	172.5	162.9	148.1	131.8	121.9	125.7	137.4	150.2
122.5°	193.3	193.2	191.5	186.7	175.4	160.0	144.0	131.8	133.4	144.2	156.7
125°	215.4	215.0	213.6	207.9	196.2	180.3	161.5	146.6	144.5	153.7	166.5
127.5°	236.3	235.6	233.4	226.5	214.5	199.1	178.5	161.7	156.9	162.7	174.4
130°	250.8	249.7	245.8	238.4	226.7	212.2	191.3	172.2	165.4	169.0	179.2
132.5°	264.7	261.6	258.3	250.3	239.5	224.4	203.2	183.2	173.9	175.5	183.5
135°	282.3	279.5	275.2	267.4	257.2	242.3	221.0	199.4	186.7	185.3	189.9
137.5°	297.8	294.9	290.0	283.3	273.0	259.7	239.3	216.5	200.4	195.7	197.4
140°	307.5	303.9	299.7	292.9	283.7	269.9	250.1	228.1	210.1	203.3	202.3
142.5°	315.4	312.7	308.2	302.0	293.9	280.1	260.9	239.2	220.0	211.3	208.8
145°	327.3	325.2	320.2	314.6	307.8	294.0	276.3	254.7	235.6	224.2	218.9
147.5°	337.4	335.7	331.8	325.1	319.4	306.2	290.0	270.9	251.3	237.3	230.4
150°	343.6	342.2	338.3	331.9	326.2	313.8	298.3	280.5	261.8	246.9	238.0
152.5°	349.5	348.1	343.7	337.3	332.5	320.9	306.8	289.9	270.8	256.0	246.8
155°	357.4	355.6	351.4	345.4	341.1	330.5	317.4	302.5	286.2	270.6	260.4
157.5°	363.6	361.4	357.5	352.3	347.8	338.0	326.6	313.8	299.5	284.7	274.2
160°	367.3	364.9	360.6	356.0	351.7	342.5	332.3	320.6	307.5	294.0	282.7
162.5°	369.9	367.7	362.6	358.5	354.9	346.5	336.8	326.2	314.6	302.8	292.3
165°	372.6	370.2	364.9	361.7	358.5	351.4	342.9	334.4	324.5	314.9	306.4
167.5°	372.9	370.8	365.5	362.4	360.0	353.9	347.1	340.6	332.8	325.3	318.2
170°	372.3	370.5	365.2	362.4	360.6	355.6	349.6	344.0	337.9	331.6	325.9
172.5°	370.3	368.5	363.5	361.2	360.3	355.9	351.0	346.8	341.6	336.9	332.4
175°	365.2	363.8	359.5	358.1	358.5	355.6	352.1	349.6	346.4	343.6	341.1
177.5°	357.8	356.9	353.8	353.8	354.9	353.2	352.1	351.0	349.5	348.7	347.8
180°	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7



TEST NUMBER: P1428592

CATALOG NUMBER: SQ2W-WBN-K-025U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8
2.5°	5903.2	5901.2	5922.2	5936.7	5931.5	5926.2	5931.5	5936.7	5922.2	5901.2	5903.2
5°	5692.9	5700.4	5737.1	5762.5	5754.1	5745.6	5754.1	5762.5	5737.1	5700.4	5692.9
7.5°	5273.3	5283.2	5315.6	5337.7	5328.7	5319.7	5328.7	5337.7	5315.6	5283.2	5273.3
10°	4890.2	4904.6	4952.1	4979.7	4947.7	4915.7	4947.7	4979.7	4952.1	4904.6	4890.2
12.5°	4445.2	4442.6	4450.2	4451.5	4433.8	4416.1	4433.8	4451.5	4450.2	4442.6	4445.2
15°	3723.8	3712.8	3724.6	3732.1	3726.9	3721.7	3726.9	3732.1	3724.6	3712.8	3723.8
17.5°	3047.8	3032.3	3031.2	3028.9	3023.0	3017.2	3023.0	3028.9	3031.2	3032.3	3047.8
20°	2619.2	2615.0	2624.4	2631.2	2630.3	2629.3	2630.3	2631.2	2624.4	2615.0	2619.2
22.5°	2254.2	2249.7	2263.7	2272.0	2263.5	2255.1	2263.5	2272.0	2263.7	2249.7	2254.2
25°	1806.8	1795.9	1788.9	1783.9	1785.4	1786.8	1785.4	1783.9	1788.9	1795.9	1806.8
27.5°	1473.0	1469.9	1474.6	1477.2	1473.8	1470.3	1473.8	1477.2	1474.6	1469.9	1473.0
30°	1309.7	1305.5	1308.3	1309.4	1305.1	1300.9	1305.1	1309.4	1308.3	1305.5	1309.7
32.5°	1171.9	1165.4	1164.1	1162.3	1159.2	1156.1	1159.2	1162.3	1164.1	1165.4	1171.9
35°	983.2	974.5	967.5	961.1	956.9	952.7	956.9	961.1	967.5	974.5	983.2
37.5°	809.9	800.4	790.0	781.3	777.8	774.2	777.8	781.3	790.0	800.4	809.9
40°	698.5	689.3	677.1	667.2	664.4	661.6	664.4	667.2	677.1	689.3	698.5
42.5°	587.6	578.8	567.3	557.1	550.9	544.7	550.9	557.1	567.3	578.8	587.6
45°	431.8	428.7	416.0	397.4	361.2	325.0	361.2	397.4	416.0	428.7	431.8
47.5°	299.6	292.7	257.4	222.1	186.5	150.9	186.5	222.1	257.4	292.7	299.6
50°	227.2	220.2	173.6	134.7	118.7	102.7	118.7	134.7	173.6	220.2	227.2
52.5°	177.2	173.9	132.9	100.0	91.2	82.4	91.2	100.0	132.9	173.9	177.2
55°	108.7	107.5	85.4	67.9	64.1	60.3	64.1	67.9	85.4	107.5	108.7
57.5°	67.4	66.7	58.4	51.5	49.1	46.8	49.1	51.5	58.4	66.7	67.4
60°	52.3	51.9	47.6	43.9	41.5	39.2	41.5	43.9	47.6	51.9	52.3
62.5°	43.1	42.5	39.7	37.5	36.6	35.8	36.6	37.5	39.7	42.5	43.1
65°	33.9	33.4	32.5	31.6	31.2	30.7	31.2	31.6	32.5	33.4	33.9
67.5°	28.8	28.6	28.1	27.6	27.1	26.7	27.1	27.6	28.1	28.6	28.8
70°	25.6	25.2	24.7	24.2	23.8	23.3	23.8	24.2	24.7	25.2	25.6
72.5°	22.3	22.0	21.9	21.7	21.2	20.7	21.2	21.7	21.9	22.0	22.3
75°	18.0	17.8	17.3	16.9	16.9	16.9	16.9	16.9	17.3	17.8	18.0
77.5°	13.4	13.1	13.1	13.0	12.7	12.3	12.7	13.0	13.1	13.1	13.4
80°	10.8	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.8
82.5°	8.3	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.3
85°	4.5	4.5	4.9	5.2	4.7	4.2	4.7	5.2	4.9	4.5	4.5
87.5°	3.3	3.8	4.3	4.6	4.9	4.7	4.9	4.6	4.3	3.8	3.3
90°	8.1	10.6	13.1	14.5	15.9	15.2	15.9	14.5	13.1	10.6	8.1
92.5°	16.4	20.5	23.6	26.1	27.3	27.1	27.3	26.1	23.6	20.5	16.4
95°	32.9	37.9	42.9	46.4	48.5	47.8	48.5	46.4	42.9	37.9	32.9
97.5°	50.8	57.5	63.0	66.3	68.4	69.9	68.4	66.3	63.0	57.5	50.8
100°	62.7	69.1	75.4	79.3	82.9	84.3	82.9	79.3	75.4	69.1	62.7
102.5°	72.3	80.7	87.6	91.8	94.8	96.2	94.8	91.8	87.6	80.7	72.3
105°	88.2	97.1	104.5	109.8	113.0	114.1	113.0	109.8	104.5	97.1	88.2
107.5°	104.1	113.2	120.1	126.0	129.9	132.1	129.9	126.0	120.1	113.2	104.1
110°	116.5	124.0	131.4	136.7	140.6	142.0	140.6	136.7	131.4	124.0	116.5



TEST NUMBER: P1428592

CATALOG NUMBER: SQ2W-WBN-K-025U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	127.0	135.3	142.8	148.1	152.5	154.5	152.5	148.1	142.8	135.3	127.0
115°	141.7	152.7	159.4	164.4	167.5	169.3	167.5	164.4	159.4	152.7	141.7
117.5°	153.9	165.4	172.7	176.5	178.0	179.3	178.0	176.5	172.7	165.4	153.9
120°	161.5	172.2	180.7	185.6	187.4	188.1	187.4	185.6	180.7	172.2	161.5
122.5°	168.6	178.7	186.9	193.0	195.9	196.6	195.9	193.0	186.9	178.7	168.6
125°	178.5	188.1	196.6	202.6	205.8	207.6	205.8	202.6	196.6	188.1	178.5
127.5°	187.2	197.5	205.3	210.8	213.9	215.3	213.9	210.8	205.3	197.5	187.2
130°	192.0	202.6	210.4	216.4	219.3	220.7	219.3	216.4	210.4	202.6	192.0
132.5°	195.7	206.9	214.9	220.4	223.5	224.9	223.5	220.4	214.9	206.9	195.7
135°	200.1	211.8	220.3	225.6	228.5	229.9	228.5	225.6	220.3	211.8	200.1
137.5°	204.0	214.7	223.5	229.1	231.7	232.6	231.7	229.1	223.5	214.7	204.0
140°	206.9	216.1	224.9	230.2	233.1	233.4	233.1	230.2	224.9	216.1	206.9
142.5°	210.6	217.8	225.5	230.8	233.6	234.3	233.6	230.8	225.5	217.8	210.6
145°	217.1	221.4	226.7	231.7	234.1	234.9	234.1	231.7	226.7	221.4	217.1
147.5°	225.4	226.8	229.5	232.8	235.2	235.7	235.2	232.8	229.5	226.8	225.4
150°	231.7	231.3	232.4	234.5	236.6	236.3	236.6	234.5	232.4	231.3	231.7
152.5°	238.7	236.7	236.6	237.6	238.6	238.5	238.6	237.6	236.6	236.7	238.7
155°	250.8	246.9	244.8	244.1	244.1	243.7	244.1	244.1	244.8	246.9	250.8
157.5°	264.0	258.6	255.4	253.7	253.2	252.4	253.2	253.7	255.4	258.6	264.0
160°	273.1	267.1	263.9	261.1	260.0	258.9	260.0	261.1	263.9	267.1	273.1
162.5°	281.6	275.9	272.4	269.8	268.8	267.2	268.8	269.8	272.4	275.9	281.6
165°	295.4	289.4	285.5	283.4	282.0	280.5	282.0	283.4	285.5	289.4	295.4
167.5°	309.2	302.6	300.1	297.7	296.3	293.8	296.3	297.7	300.1	302.6	309.2
170°	317.7	311.7	310.3	308.2	305.7	302.9	305.7	308.2	310.3	311.7	317.7
172.5°	325.1	321.1	319.7	317.5	316.7	314.5	316.7	317.5	319.7	321.1	325.1
175°	335.8	332.6	332.6	332.3	331.2	329.1	331.2	332.3	332.6	332.6	335.8
177.5°	344.7	343.0	344.2	344.2	343.9	341.9	343.9	344.2	344.2	343.0	344.7
180°	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7



TEST NUMBER: P1428592

CATALOG NUMBER: SQ2W-WBN-K-025U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	5966.8	5966.8	5966.8	5966.8
2.5°	5928.4	5948.5	5953.0	5957.5
5°	5714.6	5731.7	5735.5	5739.3
7.5°	5286.1	5294.9	5291.7	5288.5
10°	4909.0	4921.0	4912.6	4904.1
12.5°	4458.0	4468.9	4474.4	4479.8
15°	3757.7	3788.1	3807.8	3827.6
17.5°	3077.7	3098.3	3090.6	3083.0
20°	2637.1	2649.9	2647.6	2645.2
22.5°	2276.9	2293.9	2293.4	2292.9
25°	1821.3	1832.6	1834.0	1835.5
27.5°	1483.9	1493.5	1499.4	1505.2
30°	1321.0	1330.7	1335.4	1340.1
32.5°	1183.6	1192.3	1192.1	1191.9
35°	993.6	1000.6	997.8	995.0
37.5°	818.7	824.6	821.9	819.3
40°	704.6	708.7	706.9	705.0
42.5°	593.7	596.3	588.4	580.5
45°	425.2	414.0	389.1	364.1
47.5°	278.0	253.2	218.7	184.2
50°	194.8	164.4	140.4	116.4
52.5°	142.8	114.0	101.7	89.3
55°	88.9	72.9	68.2	63.5
57.5°	60.3	54.4	51.7	49.1
60°	49.0	46.1	44.2	42.3
62.5°	41.7	40.4	39.2	38.1
65°	33.9	33.8	33.3	32.8
67.5°	28.9	28.9	28.4	27.9
70°	26.1	26.3	25.9	25.4
72.5°	22.7	23.0	22.5	22.0
75°	18.0	18.0	18.0	18.0
77.5°	13.8	14.2	14.1	14.0
80°	11.3	11.5	11.1	10.6
82.5°	8.8	9.1	9.0	8.9
85°	4.9	5.3	5.3	5.3
87.5°	3.0	2.5	2.2	1.9
90°	6.4	3.9	2.5	1.1
92.5°	13.7	9.6	6.7	3.9
95°	27.6	22.0	15.6	11.0
97.5°	44.0	34.9	28.6	21.0
100°	52.8	43.9	37.9	29.8
102.5°	62.4	55.0	46.7	38.5
105°	79.7	70.5	60.9	51.7
107.5°	95.7	85.6	74.1	65.8
110°	105.9	94.9	82.9	75.4



TEST NUMBER: P1428592

CATALOG NUMBER: SQ2W-WBN-K-025U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	115.8	104.6	92.2	84.8
115°	129.3	116.9	105.6	99.2
117.5°	142.3	129.5	117.5	112.5
120°	150.2	137.4	125.7	121.9
122.5°	156.7	144.2	133.4	131.8
125°	166.5	153.7	144.5	146.6
127.5°	174.4	162.7	156.9	161.7
130°	179.2	169.0	165.4	172.2
132.5°	183.5	175.5	173.9	183.2
135°	189.9	185.3	186.7	199.4
137.5°	197.4	195.7	200.4	216.5
140°	202.3	203.3	210.1	228.1
142.5°	208.8	211.3	220.0	239.2
145°	218.9	224.2	235.6	254.7
147.5°	230.4	237.3	251.3	270.9
150°	238.0	246.9	261.8	280.5
152.5°	246.8	256.0	270.8	289.9
155°	260.4	270.6	286.2	302.5
157.5°	274.2	284.7	299.5	313.8
160°	282.7	294.0	307.5	320.6
162.5°	292.3	302.8	314.6	326.2
165°	306.4	314.9	324.5	334.4
167.5°	318.2	325.3	332.8	340.6
170°	325.9	331.6	337.9	344.0
172.5°	332.4	336.9	341.6	346.8
175°	341.1	343.6	346.4	349.6
177.5°	347.8	348.7	349.5	351.0
180°	350.7	350.7	350.7	350.7



TEST NUMBER: P1428592
 CATALOG NUMBER: SQ2W-WBN-K-025U-075D-L940-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.45	5.28	5.17	5.99	6.83	4.07	4.91	4.80	5.61	6.45
	3H	5.68	6.41	6.42	7.13	8.01	5.28	6.02	6.02	6.74	7.61
	4H	6.20	6.89	6.96	7.62	8.51	5.80	6.49	6.56	7.22	8.10
	6H	6.56	7.19	7.32	7.93	8.82	6.14	6.77	6.90	7.51	8.40
	8H	6.70	7.30	7.48	8.06	8.95	6.28	6.87	7.05	7.63	8.53
	12H	6.80	7.37	7.58	8.12	9.04	6.35	6.91	7.12	7.66	8.58
4H	2H	4.78	5.46	5.54	6.20	7.08	4.47	5.15	5.23	5.88	6.77
	3H	6.27	6.84	7.04	7.61	8.51	5.93	6.50	6.70	7.27	8.16
	4H	6.92	7.43	7.70	8.20	9.13	6.56	7.07	7.34	7.84	8.77
	6H	7.41	7.85	8.21	8.64	9.58	7.03	7.46	7.83	8.25	9.19
	8H	7.62	8.03	8.42	8.82	9.76	7.22	7.62	8.02	8.41	9.36
	12H	7.76	8.12	8.58	8.93	9.88	7.33	7.68	8.14	8.50	9.45
8H	4H	7.08	7.49	7.88	8.28	9.22	6.76	7.17	7.56	7.96	8.90
	6H	7.72	8.04	8.54	8.88	9.83	7.36	7.69	8.19	8.52	9.47
	8H	8.03	8.32	8.87	9.15	10.12	7.64	7.93	8.48	8.76	9.73
	12H	8.26	8.51	9.10	9.33	10.36	7.84	8.09	8.68	8.91	9.94
12H	4H	7.06	7.42	7.88	8.23	9.18	6.76	7.11	7.57	7.93	8.88
	6H	7.75	8.03	8.59	8.87	9.83	7.40	7.69	8.25	8.53	9.49
	8H	8.10	8.35	8.94	9.17	10.20	7.73	7.98	8.56	8.80	9.83