

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427626

Luminaire Tested: SQ2W-BBN-K-100U-125D-L940-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1427626  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2308-130-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-BBN-K-100U-125D-L940-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - BLACK DISCREET BAFFLE, NARROW 35-DEGREE OPTIC  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 9405.0 lumens  
Efficiency: N/A  
Efficacy: 113.4 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.62  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 82.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1427626

CATALOG NUMBER: SQ2W-BBN-K-100U-125D-L940-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1427626

CATALOG NUMBER: SQ2W-BBN-K-100U-125D-L940-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57				
1	102	99	96	93	95	92	90	88	80	79	77	69	68	67	59	58	58	53				
2	96	90	85	81	89	85	81	77	74	71	69	65	63	61	56	55	54	50				
3	90	82	77	72	84	78	73	69	69	65	62	61	58	56	53	51	50	47				
4	84	76	70	65	79	72	66	62	64	60	57	57	54	52	50	48	47	44				
5	79	70	64	59	74	66	61	57	60	55	52	53	50	48	48	45	44	41				
6	74	65	58	54	70	62	56	52	56	51	48	50	47	45	45	43	41	39				
7	70	60	54	49	66	58	52	48	52	48	45	47	44	42	43	40	39	36				
8	66	56	50	46	63	54	48	44	49	45	42	45	41	39	41	38	36	34				
9	63	53	47	43	59	51	45	41	46	42	39	43	39	37	39	36	34	33				
10	60	50	44	40	57	48	42	39	44	40	37	40	37	35	37	34	33	31				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	158591	158591	158591	158591
5°	153288	153374	153288	153374
10°	131552	131552	131552	131552
15°	102109	101874	102109	101874
20°	73694	72113	73694	72113
25°	52254	50266	52254	50266
30°	38877	37523	38877	37523
35°	30249	28854	30249	28854
40°	22385	20444	22385	20444
45°	11439	9216	11439	9216
50°	2489	1824	2489	1824
55°	698	549	698	549
60°	113	58	113	58
65°	0	0	0	0
70°	0	0	0	0
75°	0	0	0	0
80°	0	0	0	0
85°	0	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 40°  
 Vertical Angle: 45°  
 Luminance: 13953 cd/sqm



TEST NUMBER: P1427626

CATALOG NUMBER: SQ2W-BBN-K-100U-125D-L940-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	849.4	9.0
10°-20°	1674.6	17.8
20°-30°	1350.9	14.4
30°-40°	938.4	10.0
40°-50°	433.5	4.6
50°-60°	60.7	0.6
60°-70°	2.1	0.0
70°-80°	0.0	0.0
80°-90°	7.4	0.1
90°-100°	111.5	1.2
100°-110°	325.1	3.5
110°-120°	530.5	5.6
120°-130°	673.2	7.2
130°-140°	720.3	7.7
140°-150°	672.6	7.2
150°-160°	553.5	5.9
160°-170°	371.2	3.9
170°-180°	131.8	1.4
0°-30°	3874.9	41.2
0°-40°	4813.3	51.2
0°-60°	5307.5	56.4
0°-90°	5317.0	56.5
90°-120°	967.1	10.3
90°-150°	3033.2	32.3
90°-180°	4090.0	43.5
0°-180°	9405.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	9823	9823	9823	9823	9823	
5°	9458	9463	9458	9463	9458	850
15°	6109	6095	6109	6095	6109	1682
25°	2933	2822	2933	2822	2933	1373
35°	1535	1464	1535	1464	1535	960
45°	501	404	501	404	501	405
55°	25	20	25	20	25	31
65°	0	0	0	0	0	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	4	31	4	61	4	3
95°	44	32	44	191	44	53
105°	207	331	207	456	207	220
115°	396	549	396	676	396	390
125°	586	870	586	829	586	524
135°	796	1139	796	918	796	616
145°	1017	1313	1017	938	1017	636
155°	1208	1426	1208	973	1208	555
165°	1336	1487	1336	1120	1336	376
175°	1396	1456	1396	1314	1396	132
180°	1401	1401	1401	1401	1401	



TEST NUMBER: P1427626

CATALOG NUMBER: SQ2W-BBN-K-100U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6
2.5°	9817.0	9800.6	9784.2	9751.8	9714.1	9712.5	9747.1	9770.4	9759.7	9749.0	9759.7
5°	9458.0	9435.2	9412.3	9384.8	9355.7	9366.7	9417.8	9457.0	9460.1	9463.3	9460.1
7.5°	8665.6	8673.0	8680.4	8661.5	8633.8	8648.3	8704.9	8745.9	8739.8	8733.6	8739.8
10°	8024.1	8029.6	8035.2	8034.2	8031.0	8038.9	8057.8	8066.6	8045.4	8024.1	8045.4
12.5°	7280.7	7302.5	7324.4	7299.2	7258.3	7252.0	7280.3	7303.8	7312.8	7321.7	7312.8
15°	6108.8	6144.2	6179.6	6129.5	6050.8	6030.4	6068.1	6096.2	6095.5	6094.7	6095.5
17.5°	5009.9	5006.3	5002.7	4971.7	4931.6	4915.0	4922.1	4926.8	4924.5	4922.1	4924.5
20°	4289.1	4283.6	4278.1	4251.3	4217.5	4197.8	4192.3	4189.2	4193.1	4197.1	4193.1
22.5°	3671.7	3662.4	3653.1	3641.9	3630.1	3617.4	3603.7	3594.7	3599.9	3605.1	3599.9
25°	2933.2	2903.3	2873.4	2849.4	2827.3	2825.8	2844.6	2854.7	2838.2	2821.6	2838.2
27.5°	2354.3	2353.8	2353.4	2339.2	2320.5	2312.1	2314.2	2316.5	2319.7	2322.8	2319.7
30°	2085.3	2079.7	2074.2	2059.3	2041.2	2032.5	2033.3	2031.6	2022.1	2012.7	2022.1
32.5°	1845.9	1849.9	1853.8	1837.9	1815.4	1802.0	1797.8	1792.2	1782.8	1773.3	1782.8
35°	1534.7	1534.7	1534.7	1521.7	1504.4	1489.9	1478.1	1468.6	1466.3	1463.9	1466.3
37.5°	1246.2	1244.8	1243.4	1233.8	1221.5	1207.1	1190.4	1176.3	1170.2	1164.1	1170.2
40°	1062.1	1058.2	1054.2	1047.3	1039.5	1025.3	1004.9	987.4	978.7	970.0	978.7
42.5°	852.5	863.1	873.6	870.3	862.5	848.3	827.8	809.2	796.2	783.1	796.2
45°	501.0	545.0	589.1	604.8	611.1	602.4	578.8	543.6	473.6	403.6	473.6
47.5°	215.3	263.7	312.2	352.9	390.9	378.9	316.7	255.6	197.4	139.1	197.4
50°	99.1	136.9	174.7	225.4	280.5	269.1	191.2	126.1	99.3	72.6	99.3
52.5°	58.1	76.9	95.8	143.3	200.2	195.1	127.9	74.0	59.8	45.7	59.8
55°	24.8	31.1	37.4	63.1	95.4	93.8	58.4	30.5	25.0	19.5	25.0
57.5°	9.2	12.7	16.1	25.4	36.5	35.8	23.2	13.1	10.3	7.4	10.3
60°	3.5	5.1	6.7	11.2	16.7	16.3	10.0	4.9	3.3	1.8	3.3
62.5°	0.7	1.7	2.6	5.1	8.1	8.0	4.8	2.2	1.3	0.4	1.3
65°	0.0	0.0	0.0	0.6	1.4	1.4	0.6	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.8	2.0	3.4	4.5	5.4	5.7	5.7	5.9	6.2	6.2	6.2
90°	4.2	9.9	17.0	22.6	26.9	28.3	28.3	29.7	31.1	31.1	31.1
92.5°	15.6	24.6	24.9	24.9	30.3	32.8	35.1	35.4	36.8	36.8	36.8
95°	43.9	48.1	72.2	70.7	48.1	38.2	32.5	32.5	32.5	32.5	32.5
97.5°	83.8	90.0	93.9	125.9	133.0	128.5	104.7	88.0	78.7	74.4	78.7
100°	118.8	121.7	130.2	131.6	166.9	200.9	183.9	162.7	155.6	151.4	155.6
102.5°	153.9	155.6	168.6	174.6	182.8	202.0	260.9	254.4	249.6	248.7	249.6
105°	206.6	208.0	232.0	243.3	249.0	249.0	247.6	275.9	321.2	331.1	321.2
107.5°	262.9	269.4	297.7	328.0	334.5	336.2	328.8	324.6	322.9	324.0	322.9
110°	301.4	311.3	345.2	383.4	393.3	396.1	393.3	389.1	386.2	386.2	386.2



TEST NUMBER: P1427626

CATALOG NUMBER: SQ2W-BBN-K-100U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	338.7	353.1	391.6	435.5	452.2	460.7	454.4	451.3	448.5	450.8	448.5
115°	396.1	417.4	468.3	513.6	547.5	551.8	550.4	550.4	548.9	548.9	548.9
117.5°	449.3	483.3	540.5	593.1	632.4	643.7	649.4	647.7	646.0	648.8	646.0
120°	486.7	526.3	591.4	650.8	689.0	706.0	711.6	708.8	711.6	708.8	711.6
122.5°	526.3	575.0	638.9	700.6	745.6	764.8	771.6	772.2	772.8	771.1	772.8
125°	585.7	645.2	720.1	783.8	830.5	853.1	858.8	860.2	863.0	870.1	863.0
127.5°	645.7	713.1	795.4	856.8	904.6	932.1	940.8	944.0	949.9	953.0	949.9
130°	687.6	764.0	847.5	905.5	952.2	981.9	997.4	1001.7	1008.8	1007.3	1008.8
132.5°	731.7	811.5	896.1	956.4	999.7	1031.7	1045.0	1057.1	1059.7	1061.7	1059.7
135°	796.5	882.8	967.7	1027.2	1068.2	1099.3	1116.3	1127.6	1134.7	1138.9	1134.7
137.5°	864.7	955.8	1037.3	1090.3	1131.6	1158.4	1177.7	1189.6	1196.9	1200.3	1196.9
140°	911.1	998.9	1078.1	1133.3	1170.0	1196.9	1213.9	1228.1	1236.5	1236.5	1236.5
142.5°	955.3	1041.9	1118.8	1174.0	1206.3	1230.9	1249.0	1259.7	1269.4	1269.4	1269.4
145°	1017.2	1103.6	1174.3	1229.5	1256.4	1279.0	1298.8	1307.3	1312.9	1312.9	1312.9
147.5°	1082.0	1158.4	1223.0	1275.9	1298.5	1325.1	1340.7	1347.5	1354.5	1351.4	1354.5
150°	1120.5	1191.3	1253.5	1303.0	1325.7	1351.1	1366.7	1372.4	1379.4	1375.2	1379.4
152.5°	1157.9	1225.2	1281.8	1327.9	1347.2	1372.6	1390.5	1396.1	1400.9	1397.8	1400.9
155°	1208.2	1267.7	1320.0	1362.5	1379.4	1403.5	1420.5	1427.5	1433.2	1426.1	1433.2
157.5°	1253.2	1304.5	1350.0	1389.1	1407.2	1427.8	1443.7	1452.4	1458.1	1455.0	1458.1
160°	1280.4	1327.1	1368.1	1404.9	1421.9	1440.3	1457.3	1467.2	1472.8	1468.6	1472.8
162.5°	1303.0	1345.2	1384.0	1417.4	1432.1	1448.2	1468.6	1477.3	1483.0	1477.6	1483.0
165°	1335.6	1369.5	1403.5	1431.8	1444.5	1457.3	1478.5	1488.4	1492.6	1487.0	1492.6
167.5°	1360.2	1386.2	1413.7	1438.0	1447.4	1459.8	1481.0	1489.2	1494.6	1487.5	1494.6
170°	1373.8	1396.4	1420.5	1440.3	1447.4	1458.7	1479.9	1487.0	1491.2	1484.1	1491.2
172.5°	1385.1	1402.1	1421.6	1439.1	1442.8	1451.9	1472.0	1479.0	1482.2	1476.2	1482.2
175°	1396.4	1406.3	1420.5	1431.8	1430.4	1436.0	1453.0	1458.7	1464.3	1455.8	1464.3
177.5°	1401.8	1406.3	1410.8	1417.6	1413.1	1413.1	1425.6	1429.0	1430.1	1425.6	1430.1
180°	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7



TEST NUMBER: P1427626

CATALOG NUMBER: SQ2W-BBN-K-100U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6
2.5°	9770.4	9747.1	9712.5	9714.1	9751.8	9784.2	9800.6	9817.0	9800.6	9784.2	9751.8
5°	9457.0	9417.8	9366.7	9355.7	9384.8	9412.3	9435.2	9458.0	9435.2	9412.3	9384.8
7.5°	8745.9	8704.9	8648.3	8633.8	8661.5	8680.4	8673.0	8665.6	8673.0	8680.4	8661.5
10°	8066.6	8057.8	8038.9	8031.0	8034.2	8035.2	8029.6	8024.1	8029.6	8035.2	8034.2
12.5°	7303.8	7280.3	7252.0	7258.3	7299.2	7324.4	7302.5	7280.7	7302.5	7324.4	7299.2
15°	6096.2	6068.1	6030.4	6050.8	6129.5	6179.6	6144.2	6108.8	6144.2	6179.6	6129.5
17.5°	4926.8	4922.1	4915.0	4931.6	4971.7	5002.7	5006.3	5009.9	5006.3	5002.7	4971.7
20°	4189.2	4192.3	4197.8	4217.5	4251.3	4278.1	4283.6	4289.1	4283.6	4278.1	4251.3
22.5°	3594.7	3603.7	3617.4	3630.1	3641.9	3653.1	3662.4	3671.7	3662.4	3653.1	3641.9
25°	2854.7	2844.6	2825.8	2827.3	2849.4	2873.4	2903.3	2933.2	2903.3	2873.4	2849.4
27.5°	2316.5	2314.2	2312.1	2320.5	2339.2	2353.4	2353.8	2354.3	2353.8	2353.4	2339.2
30°	2031.6	2033.3	2032.5	2041.2	2059.3	2074.2	2079.7	2085.3	2079.7	2074.2	2059.3
32.5°	1792.2	1797.8	1802.0	1815.4	1837.9	1853.8	1849.9	1845.9	1849.9	1853.8	1837.9
35°	1468.6	1478.1	1489.9	1504.4	1521.7	1534.7	1534.7	1534.7	1534.7	1534.7	1521.7
37.5°	1176.3	1190.4	1207.1	1221.5	1233.8	1243.4	1244.8	1246.2	1244.8	1243.4	1233.8
40°	987.4	1004.9	1025.3	1039.5	1047.3	1054.2	1058.2	1062.1	1058.2	1054.2	1047.3
42.5°	809.2	827.8	848.3	862.5	870.3	873.6	863.1	852.5	863.1	873.6	870.3
45°	543.6	578.8	602.4	611.1	604.8	589.1	545.0	501.0	545.0	589.1	604.8
47.5°	255.6	316.7	378.9	390.9	352.9	312.2	263.7	215.3	263.7	312.2	352.9
50°	126.1	191.2	269.1	280.5	225.4	174.7	136.9	99.1	136.9	174.7	225.4
52.5°	74.0	127.9	195.1	200.2	143.3	95.8	76.9	58.1	76.9	95.8	143.3
55°	30.5	58.4	93.8	95.4	63.1	37.4	31.1	24.8	31.1	37.4	63.1
57.5°	13.1	23.2	35.8	36.5	25.4	16.1	12.7	9.2	12.7	16.1	25.4
60°	4.9	10.0	16.3	16.7	11.2	6.7	5.1	3.5	5.1	6.7	11.2
62.5°	2.2	4.8	8.0	8.1	5.1	2.6	1.7	0.7	1.7	2.6	5.1
65°	0.0	0.6	1.4	1.4	0.6	0.0	0.0	0.0	0.0	0.0	0.6
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	5.9	5.7	5.7	5.4	4.5	3.4	2.0	0.8	2.0	3.1	5.1
90°	29.7	28.3	28.3	26.9	22.6	17.0	9.9	4.2	9.9	15.6	25.5
92.5°	35.4	35.1	32.8	30.3	24.9	24.9	24.6	15.6	26.9	38.2	54.9
95°	32.5	32.5	38.2	48.1	70.7	72.2	48.1	43.9	62.3	87.7	110.4
97.5°	88.0	104.7	128.5	133.0	125.9	93.9	90.0	83.8	114.0	139.2	175.7
100°	162.7	183.9	200.9	166.9	131.6	130.2	121.7	118.8	151.4	175.4	210.8
102.5°	254.4	260.9	202.0	182.8	174.6	168.6	155.6	153.9	186.5	219.6	249.3
105°	275.9	247.6	249.0	249.0	243.3	232.0	208.0	206.6	243.3	281.5	318.3
107.5°	324.6	328.8	336.2	334.5	328.0	297.7	269.4	262.9	296.0	341.8	382.3
110°	389.1	393.3	396.1	393.3	383.4	345.2	311.3	301.4	331.1	379.2	423.0



TEST NUMBER: P1427626

CATALOG NUMBER: SQ2W-BBN-K-100U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	451.3	454.4	460.7	452.2	435.5	391.6	353.1	338.7	368.4	417.7	462.6
115°	550.4	550.4	551.8	547.5	513.6	468.3	417.4	396.1	421.6	466.9	516.4
117.5°	647.7	649.4	643.7	632.4	593.1	540.5	483.3	449.3	469.4	517.3	568.2
120°	708.8	711.6	706.0	689.0	650.8	591.4	526.3	486.7	502.3	548.9	599.9
122.5°	772.2	771.6	764.8	745.6	700.6	638.9	575.0	526.3	532.8	576.1	625.9
125°	860.2	858.8	853.1	830.5	783.8	720.1	645.2	585.7	577.2	614.0	665.0
127.5°	944.0	940.8	932.1	904.6	856.8	795.4	713.1	645.7	626.8	650.0	696.7
130°	1001.7	997.4	981.9	952.2	905.5	847.5	764.0	687.6	660.7	674.9	715.9
132.5°	1057.1	1045.0	1031.7	999.7	956.4	896.1	811.5	731.7	694.7	700.9	732.9
135°	1127.6	1116.3	1099.3	1068.2	1027.2	967.7	882.8	796.5	745.6	739.9	758.3
137.5°	1189.6	1177.7	1158.4	1131.6	1090.3	1037.3	955.8	864.7	800.5	781.5	788.6
140°	1228.1	1213.9	1196.9	1170.0	1133.3	1078.1	998.9	911.1	839.0	812.1	807.9
142.5°	1259.7	1249.0	1230.9	1206.3	1174.0	1118.8	1041.9	955.3	878.6	843.8	833.9
145°	1307.3	1298.8	1279.0	1256.4	1229.5	1174.3	1103.6	1017.2	940.8	895.6	874.4
147.5°	1347.5	1340.7	1325.1	1298.5	1275.9	1223.0	1158.4	1082.0	1003.7	947.6	920.2
150°	1372.4	1366.7	1351.1	1325.7	1303.0	1253.5	1191.3	1120.5	1045.5	986.1	950.8
152.5°	1396.1	1390.5	1372.6	1347.2	1327.9	1281.8	1225.2	1157.9	1081.8	1022.3	985.8
155°	1427.5	1420.5	1403.5	1379.4	1362.5	1320.0	1267.7	1208.2	1143.2	1080.9	1039.9
157.5°	1452.4	1443.7	1427.8	1407.2	1389.1	1350.0	1304.5	1253.2	1196.4	1136.9	1095.1
160°	1467.2	1457.3	1440.3	1421.9	1404.9	1368.1	1327.1	1280.4	1228.1	1174.3	1129.0
162.5°	1477.3	1468.6	1448.2	1432.1	1417.4	1384.0	1345.2	1303.0	1256.4	1209.4	1167.5
165°	1488.4	1478.5	1457.3	1444.5	1431.8	1403.5	1369.5	1335.6	1296.0	1257.8	1223.8
167.5°	1489.2	1481.0	1459.8	1447.4	1438.0	1413.7	1386.2	1360.2	1329.4	1299.4	1271.1
170°	1487.0	1479.9	1458.7	1447.4	1440.3	1420.5	1396.4	1373.8	1349.7	1324.3	1301.6
172.5°	1479.0	1472.0	1451.9	1442.8	1439.1	1421.6	1402.1	1385.1	1364.4	1345.8	1327.7
175°	1458.7	1453.0	1436.0	1430.4	1431.8	1420.5	1406.3	1396.4	1383.7	1372.4	1362.5
177.5°	1429.0	1425.6	1413.1	1413.1	1417.6	1410.8	1406.3	1401.8	1396.1	1392.7	1389.3
180°	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7



TEST NUMBER: P1427626

CATALOG NUMBER: SQ2W-BBN-K-100U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6	9822.6
2.5°	9714.1	9712.5	9747.1	9770.4	9759.7	9749.0	9759.7	9770.4	9747.1	9712.5	9714.1
5°	9355.7	9366.7	9417.8	9457.0	9460.1	9463.3	9460.1	9457.0	9417.8	9366.7	9355.7
7.5°	8633.8	8648.3	8704.9	8745.9	8739.8	8733.6	8739.8	8745.9	8704.9	8648.3	8633.8
10°	8031.0	8038.9	8057.8	8066.6	8045.4	8024.1	8045.4	8066.6	8057.8	8038.9	8031.0
12.5°	7258.3	7252.0	7280.3	7303.8	7312.8	7321.7	7312.8	7303.8	7280.3	7252.0	7258.3
15°	6050.8	6030.4	6068.1	6096.2	6095.5	6094.7	6095.5	6096.2	6068.1	6030.4	6050.8
17.5°	4931.6	4915.0	4922.1	4926.8	4924.5	4922.1	4924.5	4926.8	4922.1	4915.0	4931.6
20°	4217.5	4197.8	4192.3	4189.2	4193.1	4197.1	4193.1	4189.2	4192.3	4197.8	4217.5
22.5°	3630.1	3617.4	3603.7	3594.7	3599.9	3605.1	3599.9	3594.7	3603.7	3617.4	3630.1
25°	2827.3	2825.8	2844.6	2854.7	2838.2	2821.6	2838.2	2854.7	2844.6	2825.8	2827.3
27.5°	2320.5	2312.1	2314.2	2316.5	2319.7	2322.8	2319.7	2316.5	2314.2	2312.1	2320.5
30°	2041.2	2032.5	2033.3	2031.6	2022.1	2012.7	2022.1	2031.6	2033.3	2032.5	2041.2
32.5°	1815.4	1802.0	1797.8	1792.2	1782.8	1773.3	1782.8	1792.2	1797.8	1802.0	1815.4
35°	1504.4	1489.9	1478.1	1468.6	1466.3	1463.9	1466.3	1468.6	1478.1	1489.9	1504.4
37.5°	1221.5	1207.1	1190.4	1176.3	1170.2	1164.1	1170.2	1176.3	1190.4	1207.1	1221.5
40°	1039.5	1025.3	1004.9	987.4	978.7	970.0	978.7	987.4	1004.9	1025.3	1039.5
42.5°	862.5	848.3	827.8	809.2	796.2	783.1	796.2	809.2	827.8	848.3	862.5
45°	611.1	602.4	578.8	543.6	473.6	403.6	473.6	543.6	578.8	602.4	611.1
47.5°	390.9	378.9	316.7	255.6	197.4	139.1	197.4	255.6	316.7	378.9	390.9
50°	280.5	269.1	191.2	126.1	99.3	72.6	99.3	126.1	191.2	269.1	280.5
52.5°	200.2	195.1	127.9	74.0	59.8	45.7	59.8	74.0	127.9	195.1	200.2
55°	95.4	93.8	58.4	30.5	25.0	19.5	25.0	30.5	58.4	93.8	95.4
57.5°	36.5	35.8	23.2	13.1	10.3	7.4	10.3	13.1	23.2	35.8	36.5
60°	16.7	16.3	10.0	4.9	3.3	1.8	3.3	4.9	10.0	16.3	16.7
62.5°	8.1	8.0	4.8	2.2	1.3	0.4	1.3	2.2	4.8	8.0	8.1
65°	1.4	1.4	0.6	0.0	0.0	0.0	0.0	0.6	1.4	1.4	1.4
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	6.5	8.5	10.5	11.6	12.7	12.2	12.7	11.6	10.5	8.5	6.5
90°	32.5	42.4	52.3	58.0	63.7	60.8	63.7	58.0	52.3	42.4	32.5
92.5°	65.4	82.1	94.2	104.4	108.9	108.4	108.9	104.4	94.2	82.1	65.4
95°	131.6	151.4	171.2	185.3	193.8	191.0	193.8	185.3	171.2	151.4	131.6
97.5°	202.9	229.5	251.6	264.9	273.3	279.0	273.3	264.9	251.6	229.5	202.9
100°	250.4	275.9	301.4	316.9	331.1	336.7	331.1	316.9	301.4	275.9	250.4
102.5°	288.9	322.3	350.0	366.7	378.6	384.3	378.6	366.7	350.0	322.3	288.9
105°	352.3	387.7	417.4	438.6	451.3	455.6	451.3	438.6	417.4	387.7	352.3
107.5°	415.7	452.2	479.6	503.1	518.7	527.7	518.7	503.1	479.6	452.2	415.7
110°	465.5	495.2	524.9	546.1	561.7	567.3	561.7	546.1	524.9	495.2	465.5



TEST NUMBER: P1427626

CATALOG NUMBER: SQ2W-BBN-K-100U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	507.4	540.5	570.2	591.4	609.2	617.1	609.2	591.4	570.2	540.5	507.4
115°	565.9	609.8	636.7	656.5	669.2	676.3	669.2	656.5	636.7	609.8	565.9
117.5°	614.6	660.4	689.9	705.1	711.1	716.2	711.1	705.1	689.9	660.4	614.6
120°	645.2	687.6	721.6	741.4	748.4	751.3	748.4	741.4	721.6	687.6	645.2
122.5°	673.4	713.6	746.5	770.8	782.4	785.2	782.4	770.8	746.5	713.6	673.4
125°	713.1	751.3	785.2	809.3	822.0	829.1	822.0	809.3	785.2	751.3	713.1
127.5°	747.6	788.9	820.0	841.8	854.3	859.9	854.3	841.8	820.0	788.9	747.6
130°	766.8	809.3	840.4	864.4	875.8	881.4	875.8	864.4	840.4	809.3	766.8
132.5°	781.5	826.2	858.5	880.3	892.7	898.4	892.7	880.3	858.5	826.2	781.5
135°	799.4	846.1	880.0	901.2	912.6	918.2	912.6	901.2	880.0	846.1	799.4
137.5°	814.9	857.4	892.7	915.1	925.3	929.0	925.3	915.1	892.7	857.4	814.9
140°	826.2	863.0	898.4	919.6	930.9	932.4	930.9	919.6	898.4	863.0	826.2
142.5°	841.0	869.8	900.7	921.9	933.2	935.8	933.2	921.9	900.7	869.8	841.0
145°	867.3	884.3	905.5	925.3	935.2	938.0	935.2	925.3	905.5	884.3	867.3
147.5°	900.4	905.8	916.8	929.8	939.4	941.4	939.4	929.8	916.8	905.8	900.4
150°	925.3	923.9	928.1	936.6	945.1	943.7	945.1	936.6	928.1	923.9	925.3
152.5°	953.6	945.4	945.1	949.1	953.0	952.7	953.0	949.1	945.1	945.4	953.6
155°	1001.7	986.1	977.6	974.8	974.8	973.4	974.8	974.8	977.6	986.1	1001.7
157.5°	1054.6	1032.8	1020.1	1013.3	1011.3	1008.2	1011.3	1013.3	1020.1	1032.8	1054.6
160°	1090.8	1066.8	1054.0	1042.7	1038.5	1034.2	1038.5	1042.7	1054.0	1066.8	1090.8
162.5°	1124.8	1101.9	1088.0	1077.8	1073.6	1067.1	1073.6	1077.8	1088.0	1101.9	1124.8
165°	1180.0	1155.9	1140.3	1131.8	1126.2	1120.5	1126.2	1131.8	1140.3	1155.9	1180.0
167.5°	1235.1	1208.8	1198.6	1189.0	1183.6	1173.4	1183.6	1189.0	1198.6	1208.8	1235.1
170°	1269.1	1245.0	1239.4	1230.9	1221.0	1209.7	1221.0	1230.9	1239.4	1245.0	1269.1
172.5°	1298.5	1282.4	1276.7	1268.2	1265.1	1256.1	1265.1	1268.2	1276.7	1282.4	1298.5
175°	1341.2	1328.5	1328.5	1327.1	1322.8	1314.4	1322.8	1327.1	1328.5	1328.5	1341.2
177.5°	1376.9	1370.1	1374.6	1374.6	1373.5	1365.6	1373.5	1374.6	1374.6	1370.1	1376.9
180°	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7



TEST NUMBER: P1427626

CATALOG NUMBER: SQ2W-BBN-K-100U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	9822.6	9822.6	9822.6	9822.6
2.5°	9751.8	9784.2	9800.6	9817.0
5°	9384.8	9412.3	9435.2	9458.0
7.5°	8661.5	8680.4	8673.0	8665.6
10°	8034.2	8035.2	8029.6	8024.1
12.5°	7299.2	7324.4	7302.5	7280.7
15°	6129.5	6179.6	6144.2	6108.8
17.5°	4971.7	5002.7	5006.3	5009.9
20°	4251.3	4278.1	4283.6	4289.1
22.5°	3641.9	3653.1	3662.4	3671.7
25°	2849.4	2873.4	2903.3	2933.2
27.5°	2339.2	2353.4	2353.8	2354.3
30°	2059.3	2074.2	2079.7	2085.3
32.5°	1837.9	1853.8	1849.9	1845.9
35°	1521.7	1534.7	1534.7	1534.7
37.5°	1233.8	1243.4	1244.8	1246.2
40°	1047.3	1054.2	1058.2	1062.1
42.5°	870.3	873.6	863.1	852.5
45°	604.8	589.1	545.0	501.0
47.5°	352.9	312.2	263.7	215.3
50°	225.4	174.7	136.9	99.1
52.5°	143.3	95.8	76.9	58.1
55°	63.1	37.4	31.1	24.8
57.5°	25.4	16.1	12.7	9.2
60°	11.2	6.7	5.1	3.5
62.5°	5.1	2.6	1.7	0.7
65°	0.6	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0
87.5°	5.1	3.1	2.0	0.8
90°	25.5	15.6	9.9	4.2
92.5°	54.9	38.2	26.9	15.6
95°	110.4	87.7	62.3	43.9
97.5°	175.7	139.2	114.0	83.8
100°	210.8	175.4	151.4	118.8
102.5°	249.3	219.6	186.5	153.9
105°	318.3	281.5	243.3	206.6
107.5°	382.3	341.8	296.0	262.9
110°	423.0	379.2	331.1	301.4

TEST NUMBER: P1427626

CATALOG NUMBER: SQ2W-BBN-K-100U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	462.6	417.7	368.4	338.7
115°	516.4	466.9	421.6	396.1
117.5°	568.2	517.3	469.4	449.3
120°	599.9	548.9	502.3	486.7
122.5°	625.9	576.1	532.8	526.3
125°	665.0	614.0	577.2	585.7
127.5°	696.7	650.0	626.8	645.7
130°	715.9	674.9	660.7	687.6
132.5°	732.9	700.9	694.7	731.7
135°	758.3	739.9	745.6	796.5
137.5°	788.6	781.5	800.5	864.7
140°	807.9	812.1	839.0	911.1
142.5°	833.9	843.8	878.6	955.3
145°	874.4	895.6	940.8	1017.2
147.5°	920.2	947.6	1003.7	1082.0
150°	950.8	986.1	1045.5	1120.5
152.5°	985.8	1022.3	1081.8	1157.9
155°	1039.9	1080.9	1143.2	1208.2
157.5°	1095.1	1136.9	1196.4	1253.2
160°	1129.0	1174.3	1228.1	1280.4
162.5°	1167.5	1209.4	1256.4	1303.0
165°	1223.8	1257.8	1296.0	1335.6
167.5°	1271.1	1299.4	1329.4	1360.2
170°	1301.6	1324.3	1349.7	1373.8
172.5°	1327.7	1345.8	1364.4	1385.1
175°	1362.5	1372.4	1383.7	1396.4
177.5°	1389.3	1392.7	1396.1	1401.8
180°	1400.7	1400.7	1400.7	1400.7



TEST NUMBER: P1427626  
 CATALOG NUMBER: SQ2W-BBN-K-100U-125D-L940-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00